

OCTRON® XPS® ECOLOGIC®3

EXtended PErformance Super Fluorescent Lamps



SYLVANIA OCTRON Extended Performance Super ECOLOGIC3 (XPS) lamps deliver the highest performance of all OCTRON lamps with initial and mean lumens that are up to 11% higher and substantially longer lamp life than standard T8 fluorescent lamps. These lamps are available in 2, 3, and 4-foot lengths, in a choice of correlated color temperatures with high lumen maintenance of 94%.

When OCTRON XPS ECOLOGIC lamps are operated on existing instant start ballasts as a retrofit lamp, they deliver higher lumen output than the installed system. In new installations paired with OSRAM QUICKTRONIC PSX ballasts, 2-lamp systems deliver light levels comparable to 3-lamp 700 series T8 lamps, while maximizing energy savings and lamp life.

Application Information

Applications

- Hospitals
- Industrial
- Office
- Retail
- Schools

Key Features & Benefits

- Highest lumen 4-foot OCTRON T8 lamps
- Also available in 2-foot (F017) and 3-foot (F025) sizes
- Longer lamp life than standard T8 lamps
 - 40,000 hours rated life @ 12 hrs/start on instant start ballast
 - 42,000 hours rated life @ 12 hrs/start on programmed rapid start ballasts
- 94% Lumen maintenance
- TCLP compliant
- Lead free glass
- QUICK 60+® system warranty when paired with OSRAM QUICKTRONIC® electronic ballasts
- Meets CEE Standards

SYLVANIA OCTRON 800 XPS ECOLOGIC3 fluorescent lamps are designed to satisfy the Federal Toxicity Characteristic Leaching Procedure (TCLP) criteria for classification as non-hazardous waste in most states.²

ECOLOGIC3 represents a more comprehensive approach to sustainability encompassing high efficiency, long life and RoHS/TCLP compliance.

1. TCLP test results are based on NEMA LL Series standards and are available on request.
2. Regulations may vary. Check your local and state regulations.



Product Offering

Ordering Abbreviation	Watts	Nominal Length (in)	CCT
F017/800/XPS/ECO3	17	24	3000K, 3500K, 4100k
F025/800/XPS/ECO3	25	36	3000K, 3500K, 4100k
F032/800/XPS/ECO3	32	48	3000K, 3500K, 4100K, 5000K, 6500K

Application Notes

1. Minimum lamp starting temperature determined by ballast.
2. Operation below 50°F may affect lumen output or lamp operation.
3. For cold temperature applications, use in enclosed fixtures or use tube guards to maximize lamp performance.
4. Good ballast to socket to lamp contact essential for correct operation of system.
5. Actual lamp life dependent on ballast type, switching cycle and hours of operation per start.
6. These lamps may help facilitate compliance with national energy codes such as ASHRAE/IES 90.1 or IECC and state energy codes such as California Title 24. For more information contact your local building inspection office.



Specification Data

Fixture Description	Type
Project/Job	
SYLVANIA lamp	
OSRAM ballast	
Notes	

Ordering Information

Item Number	Abbreviation	Ordering Watts	Nominal Length (in)	Initial Lumens	Mean Lumens ¹	Lumens per Watt	Average Rated Life				CCT	CRI
							Instant Start 3 hrs/start	12 hrs/start	Programmed 3 hrs/start	Rapid Start 12 hrs/start		
22150	F017/830/XPS/EC03	17	24	1400	1315	82	24,000	40,000	40,000	42,000	3000K	85
22151	F017/835/XPS/EC03	17	24	1400	1315	82	24,000	40,000	40,000	42,000	3500K	85
22152	F017/841/XPS/EC03	17	24	1400	1315	82	24,000	40,000	40,000	42,000	4100K	85
22153	F025/830/XPS/EC03	25	36	2200	2070	88	24,000	40,000	40,000	42,000	3000K	85
22154	F025/835/XPS/EC03	25	36	2200	2070	88	24,000	40,000	40,000	42,000	3500K	85
22155	F025/841/XPS/EC03	25	36	2200	2070	88	24,000	40,000	40,000	42,000	4100K	85
21680	F032/830/XPS/EC03	32	48	3100	2915	97	24,000	40,000	40,000	42,000	3000K	85
21697	F032/835/XPS/EC03	32	48	3100	2915	97	24,000	40,000	40,000	42,000	3500K	85
21681	F032/841/XPS/EC03	32	48	3100	2915	97	24,000	40,000	40,000	42,000	4100K	85
21660	F032/850/XPS/EC03	32	48	3100	2915	97	24,000	40,000	40,000	42,000	5000K	81
21659	F032/865/XPS/EC03	32	48	3000	2820	94	24,000	40,000	40,000	42,000	6500K	81


1. Mean Lumens measured at 40% of rated life.

Ordering Guide


F0	32	/	8	35	XPS	/	EC03
Fluorescent OCTRON®	Wattage: 17, 25, or 32 watts		8 = 81-85 CRI	30 = 3000K 35 = 3500K 41 = 4100K 50 = 5000K 65 = 6500K	Extended Performance Super		ECOLOGIC3

Lamp Dimensions

Item Number	(A) Max. Overall Length (in.)	(B) Base Face to Opposite Pin (in.)		(C) Max. Base Face to Base Face (in.)	(D) Max. Outside Diameter (in.)
		Min.	Max.		
F017	23.78	23.41	23.50	23.22	1.1
F025	35.78	35.40	35.50	35.22	1.1
F032	47.78	47.41	47.50	47.22	1.1



Technical Information



Sample Specification

Lamp(s) shall be (a) OCTRON® EXTENDED Performance Super XPS®/ECO3 2-foot, 3-foot, or 4-foot lamp(s) having medium bi-pin bases. Lamps shall pass the existing Federal TCLP limits. Lamp(s) shall have initial lumens of (1400, 2200, 3100, 3000), an average rated life of (24,000, 40,000) hours on (instant start, programmed rapid start) ballasts, a CRI of (85, 81), 94% lumen maintenance and a correlated color temperature of (3000K, 3500K, 4100K, 5000K or 6500K). Lamps shall be operated on OSRAM QUICKTRONIC ballasts with complete system warranty covering lamps and ballasts.

Related Literature

For optimum system performance and warranty pair with these QUICKTRONIC Ballast Systems:

OSRAM Ballast Technology Applications & Specification Guide (Literature Code: ECS-ELECTRONIC2009)

QUICK 60+® System Warranty (Literature Code: ECS140)

LEDVANCE LLC
200 Ballardvale Street
Wilmington, MA 01887 USA
Phone 1-800-LIGHTBULB (1-800-544-4828)
www.sylvania.com

SYLVANIA and LEDVANCE are registered trademarks.
All other trademarks are those of their respective owners.
Product Licensee of Trademark SYLVANIA in General Lighting.
Specifications subject to change without notice.

