



Dual remote foot switch

DUAL POWER CONTROL
Control puller from either end

HIGH RANGE
Communicates up to 1500'
between walls and up to
1.5 miles line of sight



FORCE GAUGE METER
Amp type force gauge monitors
approximate pull tension

SAFETY
Stop the cable pull from either end
immediately. Eliminate safety
issues associated with feeding wire



Features & Benefits

DUAL POWER CONTROL

- Each pedal has the ability to control the puller's power source
- Works with any Maxis[®] cable puller and most other pullers
- Saves time by avoiding unnecessary stops and restarts
- Helps reduce the risk of wire feeding mishaps

VISUAL COMMUNICATION

- LED lights on each footswitch indicate the cable pullers status
- Amp type force gauge- monitors pull tension based on the number of amps the motor is drawing. Useful when superior accuracy is not required (accuracy is +/- 20%). Amp usage is then translated into a tension reading shown on the display.

SAFETY

- Stop the cable pull from either end immediately
- No more audio miscommunication
- Increases safety by reducing issues associated with feeding wire

FORCE GAUGE

- Amp type force gauge- monitors pull tension based on the number of amps the motor is drawing. Useful when superior accuracy is not required (accuracy is +/- 20%). Amp usage is then translated into a tension reading shown on the display.

RANGE

- Will communicate up to 1500' between walls and up to 1.5 miles line of sight 100' antenna extension available for added strength to your Triggers[®] communication



Specifications

MODEL #	STOCK#	DESCRIPTION	HEIGHT	WIDTH	WEIGHT	LENGTH
TR01	56824401	Dual Remote Foot Switch	6.5"	16.5"	21 lbs	23.5"


Southwire[™]
TOOLS & EQUIPMENT

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.[™]

1-855-SWTOOLS
(855-798-6657)

Southwiretools.com