


RSL-2

RSL-4


RSL-5



RSL-8

RSL-9


RSL-11



RSL-12

RSL-13


RSL-14



RSL-15

RSL-16

RSL-17



RSL-18

RSL-19

4¹¹/₁₆" Square Surface Covers

½" deep—7.5 cubic inch capacity

Cat. No.	Dia. Hole (in.)	Description	Std. Ctn.
RSL-2*	—	For one toggle switch and one duplex flush receptacle	10
RSL-4	1 ¹⁹ / ₃₂ "	For one 4-wire twist-lock single receptacle	10
RSL-5	—	For two toggle switches	10
RSL-8*	—	For two duplex, flush receptacles	10
RSL-9	—	For one toggle switch	10
RSL-11	1 ¹³ / ₃₂ "	For one single, flush receptacle	10
RSL-12*	—	For one duplex, flush receptacle	10
RSL-13	2 ⁷ / ₃₂ "	For one 30 or 50 amp. dryer or range receptacle	10
For Recept.			
RSL-14	2 ¹⁵ / ₃₂ "	No.	Amps
		7112	30
		7301	60
		7512	50
		9430	30
		Wire	
		9450	50
		9650	60
RSL-15	1¾"	For #3330—30A 250 V twist-lock receptacle	10
RSL-16	—	For one ground fault receptacle	10
RSL-17	—	For two ground fault receptacles	10
RSL-18	—	For one ground fault receptacle and one toggle switch	10
RSL-19*	—	For one ground fault receptacle and one duplex receptacle	10

*Now manufactured to meet new code C4 and to conform to the 1996 N.E.C. change

Table 370-16(a). Metal Boxes

Box Dimension, (in.) Trade Size or Type	Min. Cu. In. Cap.	Maximum Number of Conductors						
		No. 18	No. 16	No. 14	No. 12	No. 10	No. 8	No. 6
4 x 1½ Round or Octagonal	12.5	8	7	6	5	5	4	2
4 x 1½ Round or Octagonal	15.5	10	8	7	6	6	5	3
4 x 2½ Round or Octagonal	21.5	14	12	10	9	8	7	4
4 x 1½ Square	18.0	12	10	9	8	7	6	3
4 x 1½ Square	21.0	14	12	10	9	8	7	4
4 x 2½ Square	30.3	20	17	15	13	12	10	6
4½ x 1½ Square	25.5	17	14	12	11	10	8	5
4½ x 1½ Square	29.5	19	16	14	13	11	9	5
4½ x 2½ Square	42.0	28	24	21	18	16	14	8
3 x 2 x 1½ Device	7.5	5	4	3	3	3	2	1
3 x 2 x 2 Device	10.0	6	5	5	4	4	3	2
3 x 2 x 2½ Device	10.5	7	6	5	4	4	3	2
3 x 2 x 2½ Device	12.5	8	7	6	5	5	4	2
3 x 2 x 2½ Device	14.0	9	8	7	6	5	4	2
3 x 2 x 3½ Device	18.0	12	10	9	8	7	6	3
4 x 2½ x 1½ Device	10.3	6	5	5	4	4	3	2
4 x 2½ x 1½ Device	13.0	8	7	6	5	5	4	2
4 x 2½ x 2½ Device	14.5	9	8	7	6	5	4	2
3½ x 2 x 2½ Masonry Box/Gang	14.0	9	8	7	6	5	4	2
3½ x 2 x 3½ Masonry Box/Gang	21.0	14	12	10	9	8	7	4
FS—Minimum Internal Depth 1½ Single Cover/Gang	13.5	9	7	6	6	5	4	2
FD—Minimum Internal Depth 2½ Single Cover/Gang	18.0	12	10	9	8	7	6	3
FS—Minimum Internal Depth 1½ Multiple Cover/Gang	18.0	12	10	9	8	7	6	3
FD—Minimum Internal Depth 2½ Multiple Cover/Gang	24.0	16	13	12	10	9	8	4

Underwriters Laboratories Inc. File Number: E2969 (U.L. 514A)

Canadian Standards Association File Number: LR 12798

Federal Manufacture Number: 56501 (Cage Code)

Products Designed To Meet Federal Specification Number: W-J-800

Verification of file numbers and compliance with federal specifications for individual items available upon request.

Box and Cover Material and Plating Specification: .062" minimum thickness, Hot Rolled, Pre galvanized steel, minimum spangle.

ASTM G-90-U, AISI C-1008

Bracket Material: All brackets except MS style; 16 gauge (.060") Hot Rolled, Pre galvanized Steel AISI C-1008, G-90-U. MS Style bracket; 20 gauge (.036") Cold Rolled Spring Steel AISI C-1055, Heat Treated to R. 35 Zinc Plated .0005 thick.

Patent Number 5,031,789 - Standoff for Outlet Boxes - SS-1 Patent Number 5,004,199 - Metal Stud Bracket - Type MS - Eccentric Knockouts - Type Eko