

# SolarEdge Three Phase Revenue Grade Meters for Commercial Installations

for North America SE-RWND-3D-208-MB SE-RWND-3D-480-MB



### SolarEdge Three Phase Revenue Grade Meters for Commercial Installations

- High accuracy revenue grade meter readings for production monitoring
- Small and easy to install fits in standard electrical panel
- Supports commercial and utility-size installations
- Supports RS485 120Ω line termination
- Communicates over RS485 to provide monitoring data




# **SolarEdge Three Phase Revenue Grade Meter for Commercial Installations**

for North America SE-RWND-3D-208-MB / SE-RWND-3D-480-MB


When ordering a meter, order current transformers as well:


CURRENT TRANSFORMER MODELS(*)	CLASS	RATED RMS CURRENT	DIMENSIONS (INTERNAL/ EXTERNAL)
SEACTL-1250-150-C3	0.3	150 A	
SEACTL-1250-300-C3	0.3	300 A	1.83 x 1.26 in. / 4.50 x 3.30 in.
SEACTL-1250-600-C3	0.3	600 A	

<sup>\*</sup> One current transformer per phase; Sold in kits of 3 CTs. For other ratings contact SolarEdge



#### **Current Transformer Dimensions**





	SE-RWND-3D-208-MB	SE-RWND-3D-480-MB	UNITS		
ELECTRICAL SERVICE					
Operating Voltage Range - Line to Line	208-240	480	Vac		
AC Frequency	6	60			
Grids Supported: Three Phase*	4-wire WYE (L1-L2-L3-N) or 3 wire Delta	4-wire WYE (L1-L2-L3-N)			
Power Consumption (typ.)	1	1.8			
COMMUNICATION					
Supported Communication Interfaces	RS	RS485			
Default Device ID (Modbus)		1			
RS485 Line Termination	1	120			
ACCURACY (@25°C, PF: 1)**					
1% - 100% of Rated CT Current	±(	±0.5			
STANDARD COMPLIANCE					
Safety		IEC 61010-1, CAN/CSA-C22.2 No. 61010-1-04, IEC 61010-1:2010 (3rd Edition)			
Immunity		EN 61326 -1:2013, EN 61000-4-2, EN 61000-4-3, EN 61000-4-4,			
Emissions		EN 61000-4-5, EN 61000-4-6, EN 61000-4-11 FCC Part 15: Class B, CISPR11: 2009: Class B			
Revenue metering		ANSI C12.20-2010 class 0.5**			
INSTALLATION SPECIFICATIONS	ANSI C12.20 2	010 01035 0.5			
Dimensions (HxWxD)	6.02 × 3.	6.02 × 3.35 × 1.50			
Weight		11			
Enclosure type		High impact, ABS and/or ABS/PC plastic UL 94V-0, IEC FV-0			
Operating Temperature Range		-40 to 167			
Relative Humidity (noncondensing)		5 - 90			
Protection Rating	Indoor (Outdoor when insta	Indoor (Outdoor when installed in an outdoor enclosure)			
Mounting Type		DIN Rail / Wall mount			

<sup>\*</sup> PE (Protective Earth) connection is not required for meter operation

## RoHS (E

<sup>\*\*</sup> Using Opt C0.3 CT models available from CCS