

TYPE HS-T-PF

THIN-WALL HEAT SHRINK TUBING

CROSS-LINKED POLYOLEFIN

25 FOOT REELS

Type HS-T-PF is a flexible thin wall, flame retardant heat shrink tubing made of cross-linked polyolefin. The 2:1 shrink ratio allows for faster shrink recovery, covering wire sizes #18 AWG to 300 kcmil. Operating temperatures from -55° C to 135° C with a shrink temperature of 120° C.



Meets MIL-I-25053/5
600 VOLTS



SPECIFY COLOR CODE IN THIRD POSITION OF CATALOG NUMBER:

Example: HSC116T300PF

B: BLACK
BL: BLUE
C: CLEAR
G: GREEN
R: RED
W: WHITE
Y: YELLOW

Catalog Number	Nominal Diameter Inches	Min. Exp. ID In.	Max. Recov. ID In.	Nom. Wall Thickness In.	Conductor Range
HS_116T300PF	1/16	0.06	0.03	0.018	#18
HS_332T300PF	3/32	0.09	0.05	0.020	#18-16
HS_18T300PF	1/8	0.12	0.06	0.020	#18-14
HS_316T300PF	3/16	0.19	0.09	0.020	#18-12
HS_14T300PF	1/4	0.25	0.12	0.180	#14-10
HS_38T300PF	3/8	0.38	0.19	0.020	#8-6
HS_12T300PF	1/2	0.50	0.12	0.020	#6-2
HS_34T300PF	3/4	0.75	0.38	0.020	#1 - 3/0
HS_100T300PF	1	1.00	0.50	0.180	2/0 - 300