


Kindorf® Straps for EMT





STEEL — GALV-KROM® FINISH					
CAT. NO.	EMT SIZE (IN.)	O.D. SIZE (IN.)	STEEL STRAP THICKNESS	DESIGN LOAD (LBS.)	WT. LBS./C
C-106-3/8	3/8	0.577	14 ga.	750	13
C-106-1/2	1/2	0.706	14 ga.	750	14
C-106-3/4	3/4	0.922	14 ga.	750	13
C-106-1	1	1.163	14 ga.	750	16
C-106-1-1/4	1 1/4	1.510	14 ga.	750	19
C-106-1-1/2	1 1/2	1.740	12 ga.	800	20
C-106-2	2	2.197	12 ga.	800	22

Kindorf® Straps for O.D. Tubing

CAT. NO.	TUBING O.D. (IN.)	STEEL STRAP THICKNESS	DESIGN LOAD (LBS.)
Galv-Krom® Finish			
701 1/4	1/4	14 ga.	750
701-3/8	3/8	14 ga.	750
701-1/2-STR	1/2	14 ga.	750
701-5/8	5/8	14 ga.	750
701-3/4	3/4	14 ga.	750
701-7/8	7/8	14 ga.	750
701-1-STR	1	14 ga.	750
701-1-1/8	1 1/8	14 ga.	1,000
701-1-1/4	1 1/4	14 ga.	1,000
701-1-3/8	1 3/8	14 ga.	1,000
701-1-1/2	1 1/2	14 ga.	1,000
701-1-5/8	1 5/8	14 ga.	1,000
701-1-3/4	1 3/4	12 ga.	1,000
701-1-7/8	1 7/8	12 ga.	1,000
701-2	2	12 ga.	1,000
701-2-1/8	2 1/8	12 ga.	1,300
701-2-1/4	2 1/4	12 ga.	1,300
701-2-3/8	2 3/8	12 ga.	1,300
701-2-1/2	2 1/2	12 ga.	1,300
701-2-5/8	2 5/8	12 ga.	1,300
701-2-3/4	2 3/4	12 ga.	1,300
701-2-7/8	2 7/8	12 ga.	1,300
701-3	3	12 ga.	1,300
701-3-1/8	3 1/8	12 ga.	1,300
701-3-1/4	3 1/4	12 ga.	1,300
701-3-3/8	3 3/8	12 ga.	1,300
701-3-1/2	3 1/2	12 ga.	1,300
701-3-5/8	3 5/8	11 ga.	1,650
701-3-3/4	3 3/4	11 ga.	1,650
701-3-7/8	3 7/8	11 ga.	1,650

CAT. NO.	TUBING O.D. (IN.)	STEEL STRAP THICKNESS	DESIGN LOAD (LBS.)
Galv-Krom® Finish			
701-4	4	11 ga.	1,650
701-4-1/8	4 1/8	11 ga.	1,650
701-4-1/4	4 1/4	11 ga.	1,650
701-4-3/8	4 3/8	11 ga.	1,650
701-4-1/2	4 1/2	11 ga.	1,650
701-4-5/8	4 5/8	11 ga.	1,650
701-4-3/4	4 3/4	11 ga.	1,650
701-4-7/8	4 7/8	11 ga.	1,650
701-5	5	11 ga.	1,650
701-5-1/8	5 1/8	11 ga.	1,650
701-5-1/4	5 1/4	11 ga.	1,650
701-5-3/8	5 3/8	11 ga.	1,650
701-5-1/2	5 1/2	11 ga.	1,650
701-5-5/8	5 5/8	10 ga.	1,650
701-5-3/4	5 3/4	10 ga.	1,650
701-5-7/8	5 7/8	10 ga.	1,650
701-6	6	10 ga.	1,650
701-6-1/8	6 1/8	10 ga.	1,650
701-6-1/4	6 1/4	10 ga.	1,650
701-6-3/8	6 3/8	10 ga.	1,650
701-6-1/2	6 1/2	10 ga.	1,650
701-6-5/8	6 5/8	10 ga.	1,650
701-6-3/4	6 3/4	10 ga.	1,650
701-6-7/8	6 7/8	10 ga.	1,650
701-8	8	10 ga.	1,650

C-708-U Short Strap for Channel or Wall Mounting



CAT. NO.	PIPE SIZE (IN.)	DIMENSIONS (IN.)		HOLE SIZE (IN.)	STOCK SIZE (IN.)	DESIGN LOAD (LBS.)
		A	B			
C708U 1/2	1/2	2 7/8	2	7/32	1/8 x 1 1/8	650
C-708-U-3/4	3/4	3 1/8	2 3/8	7/32	1/8 x 1 1/8	650
C-708-U-1	1	3 3/8	2 7/8	7/32	1/8 x 1 1/8	650
C-708-U-1-1/4	1 1/4	3 1/8	2 7/8	7/32	1/8 x 1 1/8	650
C-708-U-1-1/2	1 1/2	3 1/8	3 1/8	7/32	1/8 x 1 1/8	650
C-708-U-2	2	5 1/4	4 1/4	7/16	1/4 x 1 1/8	650
C-708-U-2-1/2	2 1/2	6 3/8	4 7/8	7/16	1/4 x 1 1/8	1,000
C-708-U-3	3	6 3/8	5 3/8	7/16	1/4 x 1 1/8	1,000
C-708-U-3-1/2	3 1/2	7 3/8	5 7/8	7/16	1/4 x 1 1/8	1,000
C-708-U-4	4	7 3/8	6 3/8	7/16	1/4 x 1 1/8	1,200
C-708-U-5	5	8 3/8	7 3/4	7/16	1/4 x 1 1/8	1,200
C-708-U-6	6	9 3/8	8 3/8	7/16	1/4 x 1 1/8	1,200