




MAT PRE-BUILT ELECTRIC FLOOR HEATING SYSTEM



Single Standard Mat



Multiple Standard Mats



Custom Mat

PRODUCT OVERVIEW

Pre-built like an electric blanket, Nuheat Mat is an electric floor heating system that brings soothing heat to the following surfaces:

- Ceramic or porcelain tile
- Granite
- Marble
- Natural Stone
- Laminate/Engineered wood floors

Nuheat Mat is a pre-built floor heating system meaning it does not require any on-site manipulation during installation. Thinset is applied to the subfloor, the pre-built Nuheat Mat is pressed onto the thinset, and flooring can be installed immediately. Nuheat Mat is compatible with all standard subfloor material and is only 1/8" thick and making it ideal for installations where minimal floor buildup is desired. The pre-built aspect of Nuheat Mat guarantees even heat distribution as the heating wires are evenly spaced during production.

Nuheat Mat is available in over 70 standard mat sizes (squares and rectangles of various dimensions) and are available off-the-shelf. A single standard mat can provide adequate floor heat coverage for most standard bathroom and living areas. Installers can also combine multiple standard mats to heat the desired area.

When full coverage cannot be achieved with Nuheat standard mats (example: areas with curves, angles, or obstructions), Nuheat custom mats are available to provide optimal coverage. Once area dimensions are submitted/confirmed, Nuheat custom mats are manufactured in only three days and will fit the exact shape of the area indicated in the submitted drawings. Just like Nuheat standard mats, Nuheat custom mats are pre-built thereby guaranteeing even heat distribution without cold spots.

Nuheat standard and custom mats are available in 120 V and 240 V and produces 12 watts per sqft (up to 15 watts per sqft when required/specified).

KIT CONTENTS

- 1 Nuheat Mat floor heating system
- 1 Installation instruction manual

NUHEAT MAT

NUHEAT STANDARD MAT SELECTION TABLE

120 VOLT STANDARD MATS

	Dimensions (inches)	Ohms	Amps	Watts	Model Number
3.5 ft series	40x27	160	0.8	90	F1006
	40x32	135	0.9	107	F1008
	40x40	108	1.1	133	F1010
	40x48	90	1.3	160	F1012
4 ft series	48x24	150	0.8	96	F1206
	48x30	120	1.0	120	F1208
	48x36	100	1.2	144	F1209
	48x48	75	1.6	192	F1212
5 ft series	60x24	120	1.0	120	F1506
	60x30	96	1.3	150	F1508
	60x36	80	1.5	180	F1509
	60x42	69	1.8	210	F1510
	60x48	60	2.0	240	F1512
	60x60	48	2.5	300	F1515
6 ft series	72x24	100	1.2	144	F1806
	72x30	80	1.5	180	F1808
	72x36	67	1.8	216	F1809
	72x42	57	2.1	252	F1810
	72x48	50	2.4	288	F1812
	72x60	40	3.0	360	F1815
	72x72	33	3.6	432	F1818
7 ft series	84x24	86	1.4	168	F2106
	84x30	69	1.8	210	F2108
	84x36	57	2.1	252	F2109
	84x42	49	2.5	294	F2110
	84x48	43	2.8	336	F2112
	84x60	34	3.5	420	F2115
	84x72	29	4.2	504	F2118
	84x84	25	4.9	588	F2121
8 ft series	96x24	75	1.6	192	F2506
	96x30	60	2.0	240	F2508
	96x36	50	2.4	288	F2509
	96x42	43	2.8	336	F2510
	96x48	38	3.2	384	F2512
	96x60	30	4.0	480	F2515
	96x72	25	4.8	576	F2518
	96x84	21	5.6	672	F2521
	96x96	19	6.4	768	F2525
9 ft series	108x24	67	1.8	216	F2706
	108x30	53	2.3	270	F2708
	108x36	44	2.7	324	F2709
	108x42	38	3.2	378	F2710
	108x48	33	3.6	432	F2712
	108x60	27	4.5	540	F2715
	108x72	22	5.4	648	F2718
	108x84	19	6.3	756	F2721
	108x96	17	7.2	864	F2725
10 ft series	108x108	15	8.1	972	F2727
	118x24	61	2.0	236	F3006
	118x30	49	2.5	295	F3008
	118x36	41	3.0	354	F3009
	118x42	35	3.4	413	F3010
	118x48	31	3.9	472	F3012
	118x60	24	4.9	590	F3015
	118x72	20	5.9	708	F3018
	118x84	17	6.9	826	F3021
	118x96	15	7.9	944	F3025
	118x108	14	8.9	1062	F3027
	118x116	13	9.5	1141	F3030

240 VOLT STANDARD MATS

	Dimensions (inches)	Ohms	Amps	Watts	Model Number
5 ft series	60 x 36	320	0.8	180	G1509
	60 x 42	274	0.9	210	G1510
	60 x 48	240	1.0	240	G1512
	60 x 60	192	1.3	300	G1515
6 ft series	72 x 30	320	0.8	180	G1808
	72 x 36	267	0.9	216	G1809
	72 x 42	229	1.1	252	G1810
	72 x 48	200	1.2	288	G1812
	72 x 60	160	1.5	360	G1815
	72 x 72	133	1.8	432	G1818
7 ft series	84 x 24	343	0.7	168	G2106
	84 x 30	274	0.9	210	G2108
	84 x 36	229	1.1	252	G2109
	84 x 42	196	1.2	294	G2110
	84 x 48	171	1.4	336	G2112
	84 x 60	137	1.8	420	G2115
	84 x 72	114	2.1	504	G2118
	84 x 84	98	2.5	588	G2121
8 ft series	96 x 24	300	0.8	192	G2506
	96 x 30	240	1.0	240	G2508
	96 x 36	200	1.2	288	G2509
	96 x 42	171	1.4	336	G2510
	96 x 48	150	1.6	384	G2512
	96 x 60	120	2.0	480	G2515
	96 x 72	100	2.4	576	G2518
	96 x 84	86	2.8	672	G2521
	96 x 96	75	3.2	768	G2525

	Dimensions (inches)	Ohms	Amps	Watts	Model Number
9 ft series	108 x 24	267	0.9	216	G2706
	108 x 30	213	1.1	270	G2708
	108 x 36	178	1.4	324	G2709
	108 x 42	152	1.6	378	G2710
	108 x 48	133	1.8	432	G2712
	108 x 60	107	2.3	540	G2715
	108 x 72	89	2.7	648	G2718
	108 x 84	76	3.2	756	G2721
	108 x 96	67	3.6	864	G2725
10 ft series	108 x 108	59	4.1	972	G2727
	118 x 24	244	1.0	236	G3006
	118 x 30	195	1.2	295	G3008
	118 x 36	163	1.5	354	G3009
	118 x 42	140	1.7	413	G3010
	118 x 48	122	2.0	472	G3012
	118 x 60	98	2.5	590	G3015
	118 x 72	81	3.0	708	G3018
	118 x 84	70	3.4	826	G3021
12 ft series	118 x 96	61	3.9	944	G3025
	118 x 108	54	4.4	1062	G3027
	118 x 116	51	4.8	1141	G3030
	144 x 36	133	1.8	432	G144036
	144 x 60	80	3.0	720	G144060
	144 x 72	67	3.6	864	G144072
	144 x 96	50	4.8	1152	G144096
	144 x 108	44	5.4	1296	G144108
	144 x 120	40	6.0	1440	G144120
14 ft series	144 x 140	34	7.0	1679	G144140
	168 x 96	43	5.6	1344	G168096
	168 x 108	38	6.3	1512	G168108
	168 x 120	34	7.0	1680	G168120
20 ft series	168 x 140	29	8.2	1960	G168140
	240 x 120	24	10.0	2400	G240120

NUHEAT CUSTOM MAT – ORDERING DETAILS

- If desired coverage cannot be obtained using one or a combination of standard mats, Nuheat Custom Mats can provide the desired coverage for any area regardless of shape or size.
1. Provide an accurate drawing of the area including the full on-site perimeter dimensions, voltage, and desired thermostat location with all obstructions identified (vanities, toilets, vents, etc.). Please ensure that the installer or contractor contact information is provided in the event that we need to verify or confirm the dimensions.
 2. Submit the drawing to Nuheat Customer Care Team at res.customercare@pentair.com. Nuheat Customer Care will provide a quote and AutoCAD drawing to confirm the submitted dimensions within 24 hours.
 3. Once dimensions are accepted by the customer and payment is confirmed, the Nuheat Custom Mat will be manufactured within three days and shipped to desired location.

APPROVALS



“-W” wet rating for Canada as per Table 1 of C22.2 NO.130-16 and CEC section 62-104.

NUHEAT MAT SPECIFICATIONS

Operating voltage	120 V, 208 V, and 240 V
Power output	12 watts per square foot (15 watts per square foot when required/specified)
Maximum continuous exposure temperature	194°F (90°C)
Minimum installation temperature	50°F (10°C)
Heating cable	Single wire with ground braid outer layer
Cold lead	2-wire, 18 AWG plus ground braid layer; 10 ft (3m) length

ACCESSORIES

	Catalog number	Description
SIGNATURE thermostat	AC0055	WiFi-enabled floor heating thermostat. This programmable thermostat can be controlled using a mobile smart phone app (iOS and Android) or web browser.
HOME thermostat	AC0056	Color touchscreen programmable floor heating thermostat with intuitive user interface and energy usage information.
Element thermostat	AC0057	Non-programmable thermostat for simple control of any electric floor heating system.



WWW.NUHEAT.COM

NORTH AMERICA

Tel: +1.800.545.6258
Fax: +1.800.527.5703
Tel: +1.650.216.1526
Fax: +1.650.474.7711
thermal.info@pentair.com

Pentair is owned by Pentair or its global affiliates. All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

© 2005–2017 Pentair.

 @PentairThermal