

# LAMP HOLDERS



## GU24 LED LAMP HOLDERS

LIGHTING PRODUCTS



### TYPICAL APPLICATIONS:

- Closets
- Garages
- Attics
- Utility Rooms
- Basements
- Storage Buildings
- Commercial, Industrial, and Residential Lighting
- And more...



### Lamp Comparison

	60-watt	9-watt
Annual Energy Cost	\$36.75*	\$5.52*
Lumen Output	890	800

Annual Energy Savings using a 9-watt vs. a 60-watt = 85% or \$31.23 Savings!

\*The kWh of electricity used per day is 1.44 kWh for a 60-watt Incandescent Lamp vs. 0.312 kWh for a 9-watt LED Lamp based on operating 24 hours a day, 365 days at \$0.07 per kWh per day. Your actual savings will vary based on the amount of electricity you use and your supplier's cost per day may be more or less than the estimated savings presented in this example.

- Includes 9-watt Bi-Pin LED Lamp and Polycarbonate Lamp Diffuser:
  - » Lamp Output = 800 Lumens
  - » Efficacy = 88 Lm/W
  - » Lamp Color = 2700K (Soft White)
- Can be used with a standard wall switch.
- 7" Conductors simplify installation.
- Medium Base fits 3.25 inch or 4.0 inch Outlet Box.
- Meets the requirements of the 2017 National Electrical Code: Articles 410.16(A)(1), 410.52, 410.74(A)(B).
- Impact resistant construction.
- Suitable for indoor use only.
- Lamp Holder Rating: 120W-250VAC, 60Hz



Catalog Number	UPC Number	Description	Order Unit	Order Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
16531	16531	GU24 LED Lamp Holder: Keyless	EA	1	BX	24	24	24	Yes	11
16536	16536	GU24 LED Lamp Holder: Pull Chain	EA	1	BX	24	24	24	Yes	11
15676	15676	GU24 Bi-Pin LED Lamp: 9-Watt	EA	1	BX	25	25	25	Yes	8

Part Number 16531 Includes GU24 Base; Part Number 16530. Part Number 16536 Includes GU24 Base; Part Number 16535.

**Note:** GU24 LED Lamp Holders are sold ONLY in case quantities of 24 per Carton.

### UNITS OF MEASURE KEY

Order Unit: The Unit to be ordered; Order Qty: Number of pieces in each Unit; Unit Pkg: Packaging types - BG (Bag), BX (Box), BN (Bulk); Units/Case: Unit packages contained in the Case; TL Case Qty: The total number of items in each Master Case; Min Order Qty: The smallest Unit that can be ordered; MM Req: Must order multiples of the Unit in the stated quantities; Ship Wt (Lbs): Total weight of the Units per Carton

Specifications subject to change without prior notice.

[www.engproducts.com](http://www.engproducts.com)

5401 SMETANA DRIVE | MINNETONKA, MN 55343  
P 800.336.1976 | F 800.336.2801



# LAMP HOLDERS

## PORCELAIN AND PLASTIC LAMP HOLDERS

- UL Listed. File Number: E236781.
- Nickel-plated Brass Screw Shell will not corrode.
- For Commercial, Industrial, Residential and Agricultural Lighting Applications.
- Medium Base fits 3.25 inch or 4.0 inch Outlet Box.
- UV resistant Lamp Holders will not fade or discolor.
- Optional Plastic and Metal Safety Cages fit all Edison Base (E26) Lamp Holders.
- Includes corrosion resistant stainless steel mounting screws.
- Meets the requirements of the 2017 National Electrical Code:
  - Part Numbers: 16500, 16502, 16510, 16512 and 16514 - Articles 410.74(A)(B) and 410.122
  - Part Numbers: 16520, 16522, 16524 and 16526 - Articles 410.52, 410.74(A)(B) and 410.122



Catalog Number	UPC Number	Description	Order Unit	Order Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
16500	16500	Porcelain Lamp Holder: Keyless, 4-Terminal	EA	1	BX	48	48	48	Yes	33
16502	16502	Porcelain Lamp Holder: Pull Chain	EA	1	BX	48	48	48	Yes	35
16510	16510	Plastic Lamp Holder: Keyless, 4-Terminal	EA	1	BX	48	48	48	Yes	11
16512	16512	Plastic Lamp Holder: Pull Chain	EA	1	BX	48	48	48	Yes	13
16514	16514	Porcelain Lamp Holder: Pull Chain and 15 AMP Receptacle	EA	1	BX	48	48	48	Yes	40
16520	16520	Porcelain Lamp Holder: Keyless, 4-Terminal with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	33
16522	16522	Porcelain Lamp Holder: Pull Chain with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	35
16524	16524	Plastic Lamp Holder: Keyless, 4-Terminal with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	11
16526	16526	Plastic Lamp Holder: Pull Chain with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	13
16100	16100	Safety Cage: Yellow	EA	1	BX	10	10	10	Yes	1
16501	16501	Safety Cage: Metal	EA	1	BX	12	12	12	Yes	6

**Note:** Lamp Holders are sold ONLY in case quantities of 48 per Carton.

Specifications subject to change without prior notice.

E02-150-011 A1 2/17-SP)  
©2017 Engineered Products Company. All Rights Reserved.

### UNITS OF MEASURE KEY

Order Unit: The Unit to be ordered; Order Qty: Number of pieces in each Unit; Unit Pkg: Packaging types - BG (Bag), BX (Box), BN (Bulk); Units/Case: Unit packages contained in the Case; TL Case Qty: The total number of items in each Master Case; Min Order Qty: The smallest Unit that can be ordered; MM Req: Must order multiples of the Unit in the stated quantities; Ship Wt (Lbs): Total weight of the Units per Carton

[www.engproducts.com](http://www.engproducts.com)  
5401 SMETANA DRIVE | MINNETONKA, MN 55343  
P 800.336.1976 | F 800.336.2801

