



DIRECT BURIAL TRANSFORMERS DB SERIES

SPECIFICATIONS & FEATURES

- Heavy duty, high temperature, fiberglass reinforced composite construction.
- 1/2" NPS & 3/4" NPS bottom hubs for line voltage input, feed through & low voltage output
- 1/2" NPS hubs on cover for fixture and or photocell mounting (consult factory for details)
- 120 volt primary, 12.5v secondary, 50/60hz standard
- Multi Volt 12.5v / 13.5v / 14.5v options available (see Transformer Options below)
- Isolation type magnetic transformer no contact between 120v and 12v windings (compact electronic Halogen transformers available, see ordering information below)
- Magnetic circuit breaker for secondary overload/short circuit protection
- Long life, high temperature (130°C) transformer core
- Single phase, open core and coil
- Completely potted for longer life, more efficiency and reduced noise
- 2 feet of 12/2 direct burial cable for low voltage connections (1 per circuit and/or voltage tap)
- 1/2" NPS mounting hubs available on cover (specify at time of order if tapping required)
- NEMA 6 rated enclosure for below grade direct burial applications
- UL 1838 and UL 1598 certified
- 3 year warranty on enclosure and mechanical/electrical components

ORDERING INFORMATION

CATALOG NO.	DESCRIPTION	CIRCUITS	SHIP WEIGHT
DB-12-60LED*	60w Electronic LED Transformer	1	1 lbs.
DB-12-75E** 1	75w Electronic Halogen** Transformer	1	1 lbs.
DB-12-150E**1	150w Electronic Halogen** Transformer	1	1 lbs.
DB-12-LED10**	10w 700mA LED Driver	1	1 lbs.
DBS-12-25M	25w Magnetic Transformer	1	2 lbs.
DBS-12-60M	60w Magnetic Transformer	1	4 lbs.
DBS-12-100M	100w Magnetic Transformer	1	6 lbs.
DBS-12-75E 1	75w Electronic Halogen** Transformer	1	1 lbs.
DBS-12-150E 1	150w Electronic Halogen** Transformer	1	1 lbs.
DBS-12-LED10	10w 700mA LED Driver	1	1 lbs
DB-12-60M	60w magnetic transformer	1	4 lbs.
DB-12-100M	100w magnetic transformer	1	6 lbs.
DB-12-200	200w magnetic transformer, (1 core)	1	11 lbs.
DB-12-300	300w magnetic transformer, (1 core)	1	13 lbs.
DB-212-300	300w magnetic transformer, (1 core split)	2	13 lbs.
DB-212-600	600w magnetic transformer, (1 core split)	2	24 lbs.
DB-212-600-2C	600w magnetic transformer, (2 core)	2	24 lbs.
DB-312-900	900w magnetic transformer, (2 core)	3	32 lbs.
DB-312-900-3C	900w magnetic transformer, (3 core)	3	32 lbs.
DB-412-1200	1200w magnetic transformer, (2 core)	4	41 lbs.
DB-412-1200-4C	1200w magnetic transformer, (4 core)	4	41 lbs.

^{*} Optional Brass lid available on small round DB. Add -BRS to end of part number

¹IMPORTANT NOTE: Low voltage **electronic transformers** must be tested under load with a analog meter to achieve accurate results. Testing the transformer with a digital meter will produce an invalid reading of "no output". This characteristic is unique to electronic transformers that produce a square sine wave. We recommend use of an analog meter for testing with the transformer loaded to at least 20% of its rated output. Most electronic transformers returned as defective are actually good due to testing methods in the field that did not follow the above requirements.

TRANSFORMER OPTIONS

ADD -MV	12.5v / 13.5v / 14.5v Multi Voltage output on any single circuit transformer	
ADD -MV1	(1) 12.5v / 13.5v / 14.5v Multi Voltage output on 2, 3 or 4 circuit transformer	
ADD -MV2	(2) 12.5v / 13.5v / 14.5v Multi Voltage outputs on 2, 3 or 4 circuit transformer	
ADD -MV3	(3) 12.5v / 13.5v / 14.5v Multi Voltage outputs on 3 or 4 circuit transformer	
ADD -MV4	(4) 12.5v / 13.5v / 14.5v Multi Voltage outputs on 4 circuit transformer	
ADD -PC	Photocell mounted on top	
ADD -RPC	Remote photocell with 19' cord	
ADD -R	24V AC Relay control. (For use with existing irrigation controllers)	
ADD -220V	220v Input / 12.5v output in 300w increments (no multi voltage)	
ADD -240V	240v Input / 12.5v output in 300w increments (no multi voltage)	
ADD -277V	270v Input / 12.5v output in 300w increments (no multi voltage)	



rema









Optional cast brass lid on small DB only add **-BRS** to part #





DB-12-75E DB-12-150E DB-12-60-LED DB-12-LED10

(2) 1/2"NPS threaded ports available on bottom





DBS-12-25M DBS-12-60M DBS-12-100M DBS-12-75E DBS-12-150E DBS-12-LED10

(2) 3/4" NPS and (2) 1/2" NPS threaded ports available on bottom







DB-12-60M DB-12-100M

(2) 3/4"NPS and (3) 1/2"NPS threaded ports available on bottom DB-12-200 DB-12-300 DB-212-300

(2) 3/4" NPS and (4) 1/2" NPS threaded ports available on bottom





DB-212-600 DB-312-900 DB-412-1200

(4) 3/4"NPS and (6) 1/2"NPS threaded ports available on bottom

JOB INFORMATION	
Туре:	Date:
Job Name:	
Cat. No.:	
Lamp(s):	
Specifier:	
Contractor:	
Notes:	
FOCUS INDUSTRIES INC. 25301 COMMERCENTRE DRIVE LAKE FOREST, CA 92630	www.focusindustries.com sales@focusindustries.com (949) 830-1350 • FAX (949) 830-3390

^{**} Important Note: 75w and 150w electronic transformers are not for use with LED



DIRECT BURIAL TRANSFORMERS DB SERIES









