


enhance



The bright white radiance of the GE energy smart® LED reflector lamps is not just something you see, it's something you feel.

GE energy smart® LED reflector lamps

GE offers an energy smart® dimmable 12-watt LED reflector lamp for all of your recessed can and downlighting application needs in the restaurant, hospitality and property management sectors.

LOW-COST OPERATION

- Using only 12 watts of energy, save over \$145 in energy costs over the rated life of the lamp versus a standard 65-watt incandescent reflector based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources

EXCELLENT COLOR RENDERING

- Available with a CRI of 80 to 83

COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K and 3000K

LONG LIFE

- Up to 25,000 hours rated life (L70)

DIMMABLE

- Dims from 100% to 10%

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy,
go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.

ecomaginationSM







imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

GE energy smart® LED reflector lamps

Reflector Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Equivalent	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
BR30																	
	MED	10	68158	LED10DR30V-W/TP	120	3	5.37	700		2700	80	65W	25,000	Yes		Damp	Frosted, White body
			69060	LED10DR30V-S/TP	120	3	5.37	700		2700	80	65W	25,000	Yes		Damp	Frosted, Silver body
			68160	LED10DR30V/827W	120	6	5.37	700		2700	80	65W	25,000	Yes		Damp	Frosted, White body
		12	65389	LED12DBR30/827	120	6	5.37	750		2700	83	65W	50,000	Yes	★	Damp	Frosted, Silver
			65388	LED12DBR30/TP	120	3	5.37	750		2700	83	65W	50,000	Yes	★	Damp	Frosted, Silver
			65390	LED12DBR30/830	120	6	5.37	750		3000	83	65W	50,000	Yes	★	Damp	Frosted, Silver
BR30 Reveal																	
		12	69193	LED12DR30RVL/TP	120	3	5.37	630		2850	90	65W	25,000	Yes		Damp	Frosted, White body
Floodlight																	
	MED	10	68161	LED10DR30V/830W	120	6	5.37	700		3000	80	-	25,000	Yes	★	Damp	Frosted, White body
		12	69918	LED12DR30N/827W	120	6	5.37	800		2700	80	-	25,000	Yes	★	Damp	Frosted, White body

Get more information at
GELighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: Certified as meeting ENERGY STAR® guidelines.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

^ Incandescent or Halogen wattage equivalencies based on ENERGY STAR® guidelines using lumens or CBCP according to lamp type

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.
2) LED A19 Locking device works on PC: 66390, 65385, 64128, 65386, 64130 and 64018

ecomaginationSM



Product is compliant with material restriction requirements of RoHS

energy smart® is a registered trademark of GE
ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks
© 2013 GE 66636 10/28/2013 Printed in USA