### **J**–2

#### Conduit Outlet Boxes and Bodies: Malleable Iron or Aluminum; Explosionproof, Dust-Ignitionproof

UNILETS® for use with Threaded Metal Conduit.

#### **Applications**

- Meet a wide range of classified area requirements.
- Corrosion-resistant-ideal indoors or out.
- For pulling of wires.
- Connect conduit lengths and change direction of conduit.
- Provide access for maintenance.

#### **Features: All Bodies and Boxes**

- Malleable iron bodies have high tensile strength and ductility. Provides great resistance to corrosion, impact, and shock.
- Accurately tapped, tapered hub threads for tight, rigid joints and ground continuity.
- Furnished with covers.
- General purpose wiring.

#### **Features: GR and GRF**

**1**GR offers ten hub arrangements.

**2**GRF has integral mounting flange.


- Function as sealing fittings when used with sealing covers (see NEC for restrictions).
- Internally threaded body with externally threaded cover.
- Covers have pry notches for bar or wrench.
- Accommodate sealing, dome, hub and union hub covers, and canopies.
- Standard O-rings provide raintight fit. NEMA 3,4.
- Internal ground screw standard.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: GRH**

- ❸Designed for use in Class I, Groups A, B, C, and D; Class II, Groups E, F, and G; and Class III.
- Internally threaded body with externally threaded covers.
- Standard O-rings provide raintight fit. NEMA 3,4.
- Internal ground screw standard.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: ELBD**

**©**Exclusive built-in pulling rollers in each end (2-1/2 thru 4" sizes) protect cable from damage and make cable pulling easier.





#### Conduit Outlet Boxes and Bodies: Malleable Iron or Aluminum; Explosionproof, Dust-Ignitionproof

UNILETS® for use with Threaded Metal Conduit.

- Excellent for use in wiring of motors, panelboards, circuit breakers, entrances to buildings, etc.
- Body and cover have ground mating surfaces to meet classified-location requirements.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: ELBY**

- Serve as pulling fittings.
- Make 90° bends in conduit.
- Threaded cover opening permits easy access for pulling conductors thru hubs.
- Easily removable threaded cover.

#### **Features: CPU**

- Universal design with four threaded universal hubs and three close-up plugs.
- Serve as mounting outlets for lighting fixtures when used with hub cover.
- Wide, accurately ground explosion-proof mating surfaces.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: GRU and GRUE**

- Universal design with five threaded universal hubs and three close-up plugs.
- Copper-free aluminum body and cover provide resistance to corrosive atmospheres.
- Function as sealing fittings when used with sealing covers (see NEC for restrictions).
- GRU has internally threaded body and externally threaded cover. GRUE has externally threaded body and internally threaded overlapping cover.
- Standard O-Rings provide raintight fit. NEMA 3,4.
- Covers have pry notches for bar or wrench
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: GRJS**

- Universal design with five threaded openings and three close-up plugs.
- Compact round box for use where space is limited.
- Serve as mounting means for lighting fixtures when used with hub cover.

- Function as sealing fittings when used with sealing covers (see NEC for restrictions).
- Internally threaded body with externally threaded cover.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: GRJ**

- <sup>8</sup> Small, round conduit outlet boxes.
- Function as sealing fittings when used with sealing covers (see NEC for restrictions).
- Externally threaded body with internally threaded cover.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: ER**

- <sup>9</sup> Compact, rectangular conduit outlet boxes are ideal in classified locations where space is limited.
- Six different hub arrangements.
- Ground surface contact between body and cover assures a flame-tight joint.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### **Features: GRUO and GRUJ**

- Threaded universal hubs for wiring flexibility.
- GRUO has eight hubs.
- GRUJ offers up to eleven hubs.
- Ideally suited for use where space is limited, such as for gasoline pumps.
- Function as sealing fittings when used with sealing cover (see NEC for restrictions).
- Externally threaded body with internally threaded covers.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### Features: GRU (Union Hubs)

- <sup>12</sup> Union hubs permit easy wiring.
- Function as sealing fittings when used with sealing covers (see NEC for restrictions).
- Externally threaded body with internally threaded cover.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

#### Features: GRSS and GRSSA

- Multiple hubs permit flexibility.
- Copper-free aluminum body and cover provide superior corrosion resistance.
- Internal ground screw standard.

#### Features: GU

- Designed for Class I, Groups B,C,D; Class II, Groups E,F,G; and Class III.
- Externally threaded body with internally threaded cover.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.
- Internal ground screw standard.

#### Standard Materials

- GR, GRF, GRH, and GRJS: Malleable iron bodies with aluminum covers.
- Aluminum GR Series: Copper-free body and cover.
- GU, GRUO, GRUJ, GRU (Union), GRJ, CPU, ER, ELBD and ELBY: Malleable iron bodies and covers.
- GRU, GRUE, and GRSS: Aluminum copper-free bodies and covers.
- GRG O-Rings: Neoprene.

#### **Standard Finishes**

- Malleable iron bodies and covers (except ELBY) triple-coat—(1)zinc electroplate, (2) dichromate, and (3) epoxy powder coat.
- Aluminum bodies and covers: epoxy powder coat.
- ELBY malleable iron body and cover: zinc electroplate and clear chromate.

#### **Options**

PVC available—consult factory.

#### **Compliances**

- UL Standard 886.
- Federal Spec. W-C-586B.
- Appleton malleable iron products conform to ASTM A47-77, Grade 32510, which has the following properties: tensile strength, 50,000 psi; yield, 32,000 psi; and elongation, 10%.
- Appleton aluminum products are produced from a high strength copperfree (4/10 of 1% max.) alloy.
- Suitable for Class I, Div. 1 & 2, if installed in compliance with NEC 501-4(a)(b) and for Class II, Div. 1 & 2, if in compliance with NEC 502-4(a)(b).
- GR Series: CSA -LR25875-30.




Class I, Div. 1 and 2 Groups D Class II, Div. 1 and 2 Groups E,F,G Class III

## **ER Conduit Outlet Boxes: Explosionproof, Dust-Ignitionproof**

UNILETS® for use with Threaded Metal Conduit.

|                         | Box<br>Type | Conduit<br>Size (Inches) | Catalog Number<br>Malleable Iron |
|-------------------------|-------------|--------------------------|----------------------------------|
|                         | ERC         | 1/2<br>3/4               | ERC50<br>ERC75                   |
|                         | ERLB        | 1/2<br>3/4               | ERLB50<br>ERLB75                 |
|                         | ERLL        | 1/2<br>3/4               | ERLL50<br>ERLL75                 |
| CO CONTRACTOR OF STREET | ERLR        | 1/2<br>3/4               | ERLR50<br>ERLR75                 |
|                         | ERT         | 1/2<br>3/4               | ERT50<br>ERT75                   |
|                         | ERTB        | 1/2<br>3/4               | ERTB50<br>ERTB75                 |

#### **ER Dimensions**



| Dimensions in Inches |              |              |              |              |            |            |              |              |
|----------------------|--------------|--------------|--------------|--------------|------------|------------|--------------|--------------|
| Hub<br>Size (In.)    | Α            | В            | С            | D            | E          | F          | G            | н            |
| 1/2<br>3/4           | 3.69<br>4.00 | 1.50<br>1.75 | 2.00<br>2.13 | 5.00<br>5.44 | .56<br>.69 | .69<br>.69 | 1.50<br>1.75 | 1.06<br>1.13 |
| Dimensions i         | n Centimete  | ers          |              |              |            |            |              |              |
| 1/2<br>3/4           | 9.4<br>10.2  | 3.8<br>4.5   | 5.1<br>5.4   | 12.7<br>13.8 | 1.4<br>1.8 | 1.8<br>1.8 | 3.8<br>4.5   | 2.7<br>2.9   |

For cubic inches information, see page J-19

<sup>\*</sup>If bigger sizes needed, see GR Series on page J-4



## Wiring Capacity: Explosionproof Conduit Outlet Boxes

# CPU AA GR GRF **GRH** GRJ **GRJS** GRK **GRU Union Hub**

#### **Volume in Cubic Inches and Cubic Centimeters**

| Wiring Capacity  |                   |              |             |  |  |  |  |
|------------------|-------------------|--------------|-------------|--|--|--|--|
| Туре             | Size              | Vol./cu. in. | Vol./cu. cm |  |  |  |  |
| CPU              | Form 20           | 21.0         | 344.1       |  |  |  |  |
| ER               | 1/2"              | 4.8          | 78.7        |  |  |  |  |
| ER               | 3/4"              | 7.3          | 119.3       |  |  |  |  |
| GR               | Form 1            | 18.0         | 295.0       |  |  |  |  |
| GR               | Form 2            | 31.0         | 508.0       |  |  |  |  |
| GR               | Form 3 (1-1/2")   | 72.0         | 1179.9      |  |  |  |  |
|                  | Form 3 (2")       | 76.0         | 1245.4      |  |  |  |  |
| GRF              | All               | 18.0         | 295.0       |  |  |  |  |
| GRH              | All               | 13.8         | 226.2       |  |  |  |  |
| GRJ              | All               | 7.3          | 119.3       |  |  |  |  |
| GRJS             | All               | 12.5         | 204.8       |  |  |  |  |
| GRK (Canopy)-    | -50C, -75C, -100C | 16.0         | 262.2       |  |  |  |  |
| GRK (Dome)       | 1DC               | 6.0          | 98.3        |  |  |  |  |
| GRU (Union Hubs) | 1/2", 3/4"        | 19.0         | 311.4       |  |  |  |  |
| GRU (Universal)  | 1/2", 3/4"        | 13.5         | 221.2       |  |  |  |  |
|                  | 1"                | 17.5         | 286.8       |  |  |  |  |
| GRUE             | 1/2", 3/4"        | 15.3         | 250.7       |  |  |  |  |
|                  | 1"                | 18.5         | 303.2       |  |  |  |  |
| GRUJ             | All               | 25.0         | 409.7       |  |  |  |  |
| GRUO             | All               | 25.0         | 409.7       |  |  |  |  |
| GRSS             | All               | 29.0         | 475.2       |  |  |  |  |
| GRSSA            | All               | 29.0         | 475.2       |  |  |  |  |
| GU               | All               | 19.0         | 311.4       |  |  |  |  |

#### **ELBD 90° Pulling Unilets**

| Size                          | 1/2   | 3/4   | 1     | 1-1/4 | 1-1/2  | 2      | 2-1/2  | 3      | 3-1/2  | 4      |
|-------------------------------|-------|-------|-------|-------|--------|--------|--------|--------|--------|--------|
| Capacity in Cubic Inches      |       |       |       |       |        |        |        |        |        |        |
| ELBD                          | 7.0   | 7.0   | 25.0  | 25.0  | 69.0   | 69.0   | 240.0  | 240.0  | 540.0  | 540.0  |
| Capacity in Cubic Centimeters |       |       |       |       |        |        |        |        |        |        |
| ELBD                          | 114.7 | 114.7 | 409.7 | 409.7 | 1130.7 | 1130.7 | 3932.9 | 3932.9 | 8849.0 | 8849.0 |









GRU



**GRUJ** 

**GRUE**