


Decora Plus™ Duplex Receptacles

Heavy-Duty Industrial Specification Grade

Tamper-Resistant

15 A & 20 A, 125 V



Brass self-grounding clip is permanently staked on for secure and reliable performance

Wide receptacle face shelf provides exceptional support to the wallplate or box cover

Patented tamper-resistant safety shutter mechanism prevents insertion of foreign objects ; provides compliance with National Electrical Code Article 406 for tamper-resistant receptacles

Body and face made of impact-resistant advanced engineering polymer for extreme durability

“Universal” strap design provides ample support for electrical box installations, and includes multiple “break-off” tabs to eliminate interference with virtually any cover or wallplate

Ground terminal clamp allows for both back and side wiring

Oversized brass terminal screw heads provide superior clamping force and electrical conductivity

External wiring clamps allow for back or side wiring, and provide visual verification of termination and a faster, easier installation

Molded in ribs prevent terminal screws from making contact with wall box

Common Applications:

- Educational Facilities
- Office Environments
- Commercial/Retail Facilities
- Hospitality
- Day Care Centers

Ordering Information

Ratings		15 A/ 125 V	20 A/ 125 V
NEMA Config.		5-15R	5-20R
Order ID	Brown	TDR15	TDR20
	White	TDR15-W	TDR20-W
	Gray	TDR15-GY	TDR20-GY
	Black	TDR15-E	TDR20-E
	Ivory	TDR15-I	TDR20-I
	Light Almond	TDR15-T	TDR20-T
	Red	TDR15-R	—
	Blue	TDR15-BU	—


Specifications

Series	TDR15	TDR20
AC Horsepower Rating		
At Rated Voltage	½ HP	1 HP
Electrical Specifications		
Amperage	15 A	20 A
NEMA	5-15R	5-20R
Voltage	125 V	
Grounding	Self-Grounding*	
Pole	2	
Wire	3	
Dielectric Voltage	Withstands 3000 V min	
Temperature Rise	Max 30 °C temperature rise at full rated current	
Environmental Specifications		
Flammability	UL94 V0	
Operating Temperature	Maximum Continuous 75 °C, minimum -40 °C (w/o impact)	
Material Specifications		
Face	PBT Polyester Blend	
Body	PBT Polyester Blend	
Strap	Steel (Galvanized G60)	
Ground Contact	0.030" Brass	
Ground Screw	#8 Hex Head, Triple-Drive Brass	
Ground Clamp	Steel	
Mounting Screw	Triple-Drive Plated Steel	
Line Contacts	0.030" Phosphor Bronze	
Terminal Clamp	Brass	
Terminal Screws	#8 Triple-Drive Brass	
Ground Clip	Brass	
Shutter Mechanism	Acetal	
Mechanical Specifications		
Product ID	Ratings are permanent part of devices	
Terminal ID	Brass - Hot, Silver - Neutral, Green - Ground	
Terminal Accommodation	#14 - #10 AWG	
Wire Types	Stranded or Solid	
Termination	Back and Side Wire	
Standards & Certifications		
NEMA	WD 1 & WD 6	
ANSI	C-73	
Certification/Listing	cULus, NOM-ANCE	
Applicable Standards	UL498, Fed Spec W-C-596, CSA C22.2 No.42	
RoHS	RoHS Compliant	
Warranty		
Product Warranty	10 Years	


* Self-grounding when installed in a properly grounded metallic box

Dimensions

Front View



Side View



Visit our Website at:
www.leviton.com/commercial
 email: commercial@leviton.com

Q-1080

100417

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
 Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

© 2017 Leviton Manufacturing Co., Inc. All rights reserved.

