

Circuit Breaker Product Selection

Loadcenters & Circuit Breakers

Type BR Loadcenters & Circuit Breakers

Plug-on Circuit Breakers, Types BR 10,000/22,000/42,000 Amperes Interrupting Capacity 120 Vac, 120/240 Vac and 240 Vac







BR320

Table 3-112. Type BR Breakers, 1-Inch (25.4 mm) per Pole 120/240, 10,000, 22,000 and 42,000 AIC

Ampere Rating	Wire Size Range Cu/Al	1-Pole 120/2 Requires On		5.4 mm) Space	• •-^-	2-Pole 120/240 Vac Common Trip Requires Two 1-Inch (25.4 mm) Spaces 5 per Shelf Carton						
	60°C or 75°C	10 per Shelf	Carton									
	75 C	10 kAIC		22 kAIC		10 kAIC		22 kAIC		42 kAIC		
		Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	
10 15 20 25 30	#14 – 4	BR110 BR115 ①2 BR120 ①2 BR125 BR130		— BRH115 BRH120 BRH125 BRH130		BR210 BR215 3 BR220 3 BR225 3 BR230 3		— BRH215 BRH220 BRH225 BRH230				
35 40 45 50	#14 – 4	BR135 BR140 — BR150		BRH135 BRH140 BRH145 BRH150		BR235 3 BR240 3 BR245 3 BR250 3		BRH235 BRH240 ③ BRH245 BRH250 ③		= =		
55	#14 – 3	BR150		BRH155		BR255		BRH255		_		
60 70 80 90 100 110	#4 – 1/0	BR160 BR170 — — —		BRH160 BRH170 — — —		BR260 BR270 BR280 BR290 BR2100 BR2110		BRH260 BRH270 BRH280 BRH290 BRH2100 BRH2110		BRHH260 BRHH270 BRHH280 BRHH290 BRHH2100 BRHH2110		
125 150	#4 – 2/0	_		_		BR2125 BR2150 4		BRH2125 —		BRHH2125		

① One pole, 1-inch (25.4 mm) per pole circuit breakers are available with high magnetic setting for switching large tungsten lamp loads. Add suffix H to catalog number.

Note: All Type BR 1-, 2-, and 3-pole circuit breakers carry listing for HACR application.

For circuit breakers with a shunt trip, add ST suffix and obtain pricing from table on Page 3-76.

² Switching duty rated.

³ On the black handle breaker, add suffix "B" to the catalog number and \$4.00 to the list price to obtain a tapped molded opening for proper use with hold-down kits.

④ For use as a branch circuit breaker in 400 and 600 ampere panels only.

Loadcenters & Circuit Breakers Type BR Loadcenters & Circuit Breakers

FAT-N

January 2008

Circuit Breaker Product Selection

Table 3-113. Type BR Breakers, 1-Inch (25.4 mm) per Pole 240 Vac, 10,000, 22,000 and 42,000 AIC

Ampere Rating	Wire Size Range Cu/Al 60°C or 75°C	3-Pole 240 Vac Common Trip Requires Three 1-Inch (25.4 mm) Spaces							
		5 per Shelf Carton							
		10 kAIC		22 kAIC					
		Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$				
10 15 20 25 30 35 40 45 50	#14 – 4 #14 – 4	BR310 BR315		— BRH315 BRH320 BRH325 BRH330 BRH335 BRH340 BRH345 BRH350					
55	#14 – 3	BR355		BRH355					
60 70 80 90 100	#4 – 1/0	BR360 BR370 BR380 BR390 BR3100		BRH360 BRH370 BRH380 BRH390 BRH3100					

① One pole, 1-inch (25.4 mm) per pole circuit breakers are available with high magnetic setting for switching large tungsten lamp loads. Add suffix H to catalog number.

Note: All Type BR 1-, 2- and 3-pole circuit breakers carry listing for HACR application. For circuit breakers with a shunt trip, add ST suffix and obtain pricing from table on **Page 3-76**.

Special Application Circuit Breaker Product Selection

Type BR Loadcenters & Circuit Breakers

Loadcenters & Circuit Breakers

Plug-on Branch Feeder Type Arc Fault Circuit Breakers, Type BR 10,000 Amperes Interrupting Capacity 120 Vac and 120/240 Vac



Type BR AFCI Circuit Breaker

A Branch Feeder Type Arc Fault Circuit Interrupter is a device intended to mitigate parallel arcing faults in the complete circuit, including connected cords. Parallel arcing faults can occur from line to neutral or line to ground. These arcing faults are in parallel with the load and produce the most energy of all arcing faults.

The Branch Feeder Type AFCI is required in the 1999, 2002 and 2005 National Electrical Code.

As of January 1, 2008, the Combination Type AFCI is required.

Product Selection

Table 3-114. Type BR, 1-Inch (25.4 mm) wide FIRE-GUARD™ AFCI Circuit Breakers

Poles	Ampere Rating	Configuration	Catalog Number	Price U.S. \$
Single-Pole 10 kAIC	15	AFCI AFCI with GFCI	BR115AF ① BR115AFGF	
	20	AFCI AFCI with GFCI	BR120AF ① BR120AFGF	
Single-Pole	15	AFCI	BRH115AF	
22 kAIC	20	AFCI	BRH120AF	
Double-Pole 10 kAIC 23	15	AFCI Common Trip AFCI Independent Trip AFCI Common Trip with GFCI	BR215AF BR215AFIT BR215AFGF	
	20	AFCI Common Trip AFCI Independent Trip AFCI Common Trip with GFCI	BR220AF BR220AFIT BR220AFGF	

- ① Clamshell packaging available with CS modification code on the end of catalog number.
- 2 Common trip refers to 2-pole 240 volt load application sourced by 120/240 Vac (see Figure 3-19).
- 3 Independent trip refers to 2-pole multi-wire, home run or shared neutral circuits (see Figure 3-18 and Figure 3-20).




Figure 3-17. 1-Pole 120 Volt Load Application Sourced by 120/240 Vac




Figure 3-19. 2-Pole 240 Volt Load Application Sourced by 120/240 Vac




Figure 3-18. 2-Pole Shared Neutral with **Multi-Duplex Receptacle Application**




Figure 3-20. 2-Pole Shared Neutral with **Duplex Receptacle Application**

Loadcenters & Circuit Breakers Type BR Loadcenters & Circuit Breakers

Special Application Circuit Breaker Product Selection

January 2008

Plug-on Combination Type Arc Fault Circuit Breakers, Type BR 10,000 Amperes Interrupting Capacity 120 Vac and 120/240 Vac



Type BR AFCI Circuit Breaker

A Combination Type Arc Fault Circuit Interrupter is a device that includes all of the protection offered by the Branch Feeder AFCI (mitigation of parallel arcing faults in the complete circuit, including connected cords). In addition it provides direct detection of persistent low current arcing faults down to 5 amps with associated mitigation of fire hazards in the cords connected to the outlets. Parallel arcing faults can occur from line to neutral or line to ground. These arcing faults are in parallel with the load and produce the most energy of all arcing faults. The current level of low current arcing faults is limited by the load.

Product Selection

Table 3-115. Type BR, 1-Inch (25.4 mm) wide FIRE-GUARD™ Combination Type AFCI Circuit Breakers

Poles	Ampere Rating	Configuration	Catalog Number	Price U.S. \$
Single-Pole	15	AFCI	BR115CAF 1	
10 kAIC	20	AFCI	BR120CAF®	

① Clamshell packaging available with CS modification code on the end of catalog number.




Figure 3-21. 1-Pole 120 Volt Load Application Sourced by 120/240 Vac



Special Application Circuit Breaker Product Selection

Type BR Loadcenters & Circuit Breakers

Loadcenters & Circuit Breakers

Plug-on Ground Fault Circuit Breakers, Type GFCB and GFEP 10,000/22,000 Amperes Interrupting Capacity 120 Vac and 120/240 Vac

Table 3-116. Type GFCB Ground Fault Circuit Breakers — 5 Milliampere — 1-Inch (25.4 mm) per Pole 120 Vac or 120/240 Vac, 10,000 AIC

Ampere Rating	Wire Size Range Cu/Al 60°C or 75°C	1-Pole 120 Vac Requires One 1-Inch (25.4 mm) Space	-	2-Pole 120/240 Vac Common Trip Requires Two 1-Inch (25.4 mm) Spaces			
		1 per Shelf Car	ton	1 per Shelf Carton			
		10,000 AIC		10,000 AIC			
		Catalog Number ①	Price U.S. \$	Catalog Number	Price U.S. \$		
15 20 25 30 40 50	#14 – 4	GFCB115 GFCB120 GFCB125 GFCB130 GFCB140		GFCB215 GFCB220 GFCB225 GFCB230 GFCB240 GFCB250 ②			



Type GFCB 1-Pole

Table 3-117. Type GFCBH Ground Fault Breakers — 5 Milliampere — 1-Inch (25.4 mm) per Pole 120 Vac or 120/240 Vac, 22,000 AIC

1 111011 (23.	4 mm, per i die 120 i	VUC 01 120/240 V	uc, 22,000 Alo				
Ampere Rating	Wire Size Range Cu/Al 60°C or 75°C	1-Pole 120 Vac Requires One 1-Inch (25.4 mm) Space	—	2-Pole 120/240 Vac Common Trip Requires Two 1-Inch (25.4 mm) Spaces			
		1 per Shelf Cart	ton	1 per Shelf Carton			
		22,000 AIC		22,000 AIC			
		Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$		
15 20 25 30	#14 – 4	GFCBH115 GFCBH120 GFCBH125 GFCBH130		GFCBH215 GFCBH220 GFCBH225 GFCBH230			

Table 3-118. Type GFEP Ground Fault Equipment Protectors — 30 Milliampere — 1-Inch (25.4 mm) per Pole 120 Vac or 120/240 Vac, 10,000 AIC

Ampere Rating	Wire Size Range Cu/Al 60°C or 75°C	1-Pole 120 Vac Requires One 1-Inch Space	-	2-Pole 120/240 Vac Common Trip Requires Two 1-Inch Spaces				
		1 per Shelf Cart	on	1 per Shelf Carton				
		10,000 AIC		10,000 AIC				
		Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$			
15	#14 – 4	GFEP115		GFEP215				
20		GFEP120		GFEP220				
25		GFEP125		GFEP225				
30		GFEP130		GFEP230				
40		-		GFEP240				
50		-		GFEP250 3				

³ For use with copper wire only.

① Available with bell alarm or auxiliary switch. See circuit breaker accessories on Page 3-75.

² For use with copper wire only.

FATON

January 2008

Special Application Circuit Breaker Product Selection

Ground Fault Application Notes

Single-pole GFCBs are designed for use in 2-wire, 120 Vac circuits. **Figure 3-22** shows a typical wiring configuration.

Two-pole GFCBs are designed for use in 3-wire, 120/240 Vac circuits, 120 Vac multiwire circuits employing common, neutral and 2-wire, 240 Vac circuits obtained from a 120/240 Vac source.

Figure 3-23 and Figure 3-24 illustrate typical wiring configurations for a 120/240 Vac multiwire circuits.

Figure 3-25 depicts a 240 Vac, 2-wire circuit. Note the "panel neutral" conductor connects to the neutral bar, even though the neutral is not included in the load circuit. This connection is necessary to supply a 120 Vac power source to the ground fault sensing circuit.

The figures are shown with a 120/240 Vac, single-phase, 3-wire power source, but are also applicable to a 120/208 Vac, 3-phase, 4-wire power supply. For all figures, the electrical operation of the GFCB is not affected by the equipment ground.




Figure 3-22. 1-Pole 120 Volt Duplex Receptacle Application




Figure 3-23. 2-Pole 120 Volt Multi-Duplex Receptacle Application




Figure 3-24. 2-Pole 120 Volt Duplex Receptacle Application




Figure 3-25. 2-Pole 240 Volt Duplex Receptacle Application



Loadcenters & Circuit Breakers Type BR Loadcenters & Circuit Breakers

Special Application Circuit Breaker Product Selection

CTL Plug-on Circuit Breakers, Type BD Duplex, BQ and BQC Quadplex 10,000 Amperes Interrupting Capacity 120/240 Vac







BQ2302115

BQ230230

Duplex and Independent Trip Quadplex Breakers

Table 3-119. Class CTL, 1-Inch (25.4 mm) per Pole 10,000 AIC — All Circuit Breakers Have Rejection Tab Feature

Type BD I (UL Type			Wire Size Range	Type BQ Qu (UL Type Bl	uadplex Indepe RD)	ndent Trip			Type BQ Quad (UL Type BRD	dplex Independ)	ent Trip	
1-Pole ^②		120/240 Vac 120/240 Vac	Cu/Al 65°C or 75°C	2-Pole ^① and 1-Pole ^①	2		→120 Vac → 120/240 Vac →120 Vac		2-Pole 120/240 Vac 120/240 Vac			3
	One 1-Inch			Requires Tv					Requires Two 1-Inch			
(25.4 mm	•			(25.4 mm) S	•				(25.4 mm) Spa			
10 per Sh	elf Carton			5 per Shelf	Carton				5 per Shelf Carton			
Ampere	10,000 AIC			10,000 AIC					10,000 AIC			
Rating	120 Vac			120 Vac					120/240 Vac		Catalog	Price
	Catalog	Price		Ampere Ra	Ampere Rating U.S. \$				Ampere Ratin	g	Number	U.S. \$
	Number	U.S. \$		Outer Left 1-Pole	Center 2-Poles Independent Trip	Outer Right 1-Pole			Outer 2-Poles Independent Trip	Center 2-Poles Independent Trip		
10 – 10	BD1010		#14 – 4	15	20	15	BQ2202115		15	15	BQ215215	
15 – 15	BD1515			20	20	20	BQ2202120		15	20	BQ215220	
15 – 20	BD1520			15	30	15	BQ2302115		15	30	BQ215230	
15 – 30	BD1530			20	30	20	BQ2302120		15	40	BQ215240	
20 – 15	BD2015			15	40	15	BQ2402115		15	50	BQ215250	
20 - 20	BD2020			20	40	20	BQ2402120		20	20	BQ220220	
20 - 30	BD2030			15	50	15	BQ2502115		20	30	BQ220230	
25 – 25	BD2525			20	50	20	BQ2502120		20	40	BQ220240	
30 – 15	BD3015			_	_	-	-		20	50	BQ220250	
30 – 20	BD3020			-	_	_	-		25	25	BQ225225	
30 – 30	BD3030			_	_	-	-		30	30	BQ230230	
30 – 40	BD3040					-	-		30	40	BQ230240	
30 – 50	BD3050				-	_	-		30	50	BQ230250	
50 – 30	BD5030			-	-	-	-		40	40	BQ240240	
50 – 50	BD5050			-	-	-	-		40	50	BQ240250	
-	-			_	_	_	-		50	50	BQ250250	
I —	-			_	_	_	-		-	_		
_	—			_	_	_	-		<u> </u>	_	_	

① All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications.

② All 15 and 20 ampere single poles are switch-duty rated.

Special Application Circuit Breaker Product Selection

Non-CTL Plug-on Replacement Circuit Breakers, Type BRD 10,000 Amperes Interrupting Capacity 120/240 Vac

Non-CTL 10,000 AIC for **Replacement Purposes Only**

For replacement in enclosures manufactured prior to 1968 with unnotched stabs. Circuit breakers do not have rejection tab.



BR1515

Table 3-120. Class Non-CTL, 1-Inch (25.4 mm) per Pole 10,000 AIC — Breakers Do Not Have Rejection Tab Feature

Type BR I	Duplex		Wire Size	Type Brand BRD C	Quadplex Independ	dent Trip Type BRD Quadplex Common Trip center and Outer Poles							
1-Pole <	12	0/240 Vac 0/240 Vac	Range Cu/Al 65°C or	2-Pole		2-Pole	< <	120/240 Vac					
Requires (25.4 mm	One 1-Incl) Space	1	75°C	Requires Two 1-Inch (25.4 mm) Spaces				Requires Two 1-Inch (25.4 mm) Spaces					
10 per Sh	elf Carton			5 per Shelf Carton				5 per Shelf Carton					
Ampere	10,000 AI	С		10,000 AIC			10,000 AIC						
Rating	120 Vac	120 Vac		120/240 Vac	120/240 Vac	Catalog	Price	120/240 Vac		Catalog	Price		
	Catalog	Price		Ampere Rating		Number	U.S. \$	Ampere Rating		Number	U.S. \$		
	Number	U.S. \$		Outer 2-Poles Independent Trip	Center 2-Poles Independent Trip			Outer 2-Poles Common Trip	Center 2-Poles Common Trip				
15 – 15	BR1515		#14 – 4	15	15	BR415		15	15	BRDC215215			
15 – 20	BR1520			20	20	BR420		30	30	BRDC230230			
20 – 15	BR2015			30 30 BR430		30	40	BRDC230240					
20 – 20	BR2020			20 30		BRD220230		30	50	BRDC230250			
30 - 30	BR3030			30	40	BRD230240		-	-	-			
	BR3050			30	50	BRD230250							

Note: Type BD Duplex, BQ and BQC Quadplex (CTL) circuit breakers conform to Section 384-15 of the latest National Electrical Code. Install breaker only in panel positions that have notched bus stabs.




Figure 3-26. CTL and Non-CTL Breakers



Type BR Loadcenters & Circuit Breakers

Loadcenters & Circuit Breakers

Circuit Breaker Product Selection

Common Trip Quadplex Breakers





BQC2302115 BQC230230

Table 3-121. Class CTL, 1-Inch (25.4 mm) per Pole 10,000 AIC — All Circuit Breakers Have Rejection Tab Feature

Type BQC Qua (UL Type BRD)	dplex Common Trip C	enter Poles			Wire Size	Type BQC Quadr (UL Type BRD)	olex Common Trip C	enter and Outer P	Poles	
2-Pole ^① and 1-Pole ^②			120 Vac 120/240 Vac 120 Vac		Range Cu/Al 65°C or 75°C	2-Pole ①		120/240 Vac		
Requires Two	1-Inch (25.4 mm) Spac	es				Requires Two 1-Inch (25.4 mm) Spaces				
5 per Shelf Car	ton				1	5 per Shelf Carto				
10,000 AIC					1	10,000 AIC				
120 Vac	120/240 Vac	120 Vac	Catalog	Price	1	120/240 Vac		Catalog	Price	
Ampere Rating			Number	U.S. \$		Ampere Rating		Number	U.S. \$	
Outer Left 1-Pole	Center 2-Poles Common Trip	Outer Right 1-Pole				Outer 2-Poles Common Trip	Center 2-Poles Common Trip			
15 15 15 15 15 15 —————————————————————	20 25 30 40 50 — — — — 15 20 25	15 15 15 15 15 15 —————————————————————	BQC2202115 BQC2252115 BQC2302115 BQC2402115 BQC2502115 — — BQC2152120 BQC2202120 BQC2252120		#14 – 4 #14 – 4	15 15 15 20 20 20 20 20 20 20 30 30	15 20 30 15 20 30 40 50 25 30 41 50	BQC215215 BQC215220 BQC215230 BQC220215 BQC220220 BQC220230 BQC220240 BQC220250 BQC22525 BQC225230 BQC230215		
20 20 20 20 30	30 40 50	20 20 20 20	BQC2302120 BQC2402120 BQC2502120		#14 – 4	30 30 30 30	30 40 50	BQC230230 BQC230240 BQC230250 BQC240230		
					# 14 - 4	40 40 40 50 50	40 50 20 50	BQC240240 BQC240250 BQC250220 BQC250250		

All Type BQC Quadplex circuit breakers carry listing for HACR applications.
 All 15 and 20 ampere single poles are switch-duty rated.

Loadcenters & Circuit Breakers Type BR Loadcenters & Circuit Breakers

Circuit Breaker Product Selection

January 2008

Plug-on Circuit Breakers, Types BJ and BJH 10,000/22,000 Amperes Interrupting Capacity 120/240 Vac and 240 Vac

For Use in Single-Phase and 3-Phase Loadcenters 150 Amperes and Above



Table 3-122. Types BJ and BJH Breakers, 1-Inch (25.4 mm) per Pole, 120/240 or 240 Vac, 10,000, 22,000 AIC

Ampere Rating	<u> </u>	ip ur 1-Inch (25.4 ı	mm) Spaces ①		Wire Size Range Cu/Al 60°C or 75°C	3-Pole 240 Vac Common Trip Requires Six 1-Inch (25.4 mm) Spaces ②				
	10 per Shelf	Carton			/3 0	5 per Shelf Carton				
	10,000 AIC		22,000 AIC	22,000 AIC		10,000 AIC		22,000 AIC	22,000 AIC	
	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$		Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	
125	BJ2125		BJH2125		#2 – 300 kcmil	BJ3125		BJH3125		
150	BJ2150		BJH2150			BJ3150		BJH3150		
175	BJ2175		BJH2175			BJ3175		BJH3175		
200	BJ2200		BJH2200			BJ3200		BJH3200		
225	BJ2225		BJH2225			BJ3225		BJH3225		

① Breaker uses two 1-inch (25.4 mm) pole spaces on left side and two 1-inch (25.4 mm) pole spaces on right side of loadcenter.

Plug-on Special Application Circuit Breakers

10,000 Amperes Interrupting Capacity 120 Vac, 120/240 Vac and 240 Vac



Water Heater Breaker



BRSN220 Switching Neutral Breaker

Table 3-123. Special Application Circuit Breakers, 1-Inch (25.4 mm) per Pole

Water Heate	er Breakers		Switching N	leutral Breake	rs	Wire Size Range	240 V Break	ers		Non-Automatic Molded Case Switches		
2-Pole 120/240 Vac Common Tr Requires Tw (25.4 mm) S	ip /o 1-Inch	LINE	2-Pole 120 Vac Common Tri Requires Tw (25.4 mm) S	o 1-Inch	OUT IN	Cu/AI 60°C or 75°C	2-Pole 240 Vac Common Tri Requires Tw (25.4 mm) S	o 1-Inch		2-Pole 240 Vac Requires Two 1-Inch (25.4 mm) Spaces		
for Separate	With Isolated Line Terminals for Separately Metered Water Heaters 5 per Shelf Carton			ing Neutral oline Pump			Where Voltage to Ground is 240 Vac			For Use as Disconnect Contains No Magnetic or Thermal Trip Properties		
5 per Shelf (5 per Shelf C	arton		5 per Shelf	Carton	
10,000 AIC	00 AIC 10,000 AIC]	10,000 AIC			5,000 AIC		
Ampere Rating	Catalog Number	Price U.S. \$	Ampere Rating	Catalog Price U.S.\$			Ampere Rating	Catalog Number	Price U.S. \$	Ampere Rating	Catalog Number	Price U.S. \$
15 20 30 — — — — —	BRWH215 BRWH220 BRWH230 — — — —		15 20 25 30 — — —	BRSN215 BRSN220 BRSN225 BRSN230 — —		#14 – 4	10 15 20 25 30 35 40 45 50	BR210H BR215H BR220H BR225H BR230H BR235H BR240H BR245H BR250H BR255H			 BR250NA	
_ _ _ _			_ _ _ _	_ _ _ _		#4 – 1/0	60 70 80 90 100	BR260H BR270H BR280H BR290H BR2100H		60 — — — — 100	BR260NA BR2100NA	

Discount Symbol 22CD

² Breaker uses three 1-inch (25.4 mm) pole spaces on left side and three 1-inch (25.4 mm) pole spaces on right side of loadcenter. Note: If BJ or BJH breakers are used as a main or a back feed device, a hold-down kit is required. See Page 3-75.