

PVC COATED GRC 90° STANDARD ELBOWS

Description:


PVC Coated GRC 90° Standard Elbows are available in standard & special radius dimensions and in various degrees as required. All elbows are manufactured from Calbond PVC coated conduit and meet all applicable standards.

Features:

- Exterior PVC coating thickness is a minimum 0.040"
- Interior Urethane coating thickness is a minimum 0.002"
- Specialized corrosion resistant coating provided on threads
- Sizes available are 1/2" to 6"
- Available in 90, 60, 45, and 30 degree bends

UL Listings Include:

- Calbond PVC coated conduit is UL/CUL listed in accordance to UL6 & ANSI C80.1 Standards
- Calbond PVC coated conduit is UL/cUL listed rigid ferrous metal conduit with polyvinyl chloride coating verified for PVC adhesion performance
- Calbond PVC coated conduit complies with NEMA RN-1
- UL File Number E226472



Item Number	Trade Size	Metric Size (mm)	Weight Per 100 (lbs)	Standard Radius A	Offset B	Tangent T
PV0590EL00	1/2"	16	70	4.25	6.0	1.7
PV0790EL00	3/4"	21	100	4.50	6.7	2.2
PV1090EL00	1"	27	190	5.75	8.0	2.4
PV1290EL00	1-1/4"	35	310	7.25	9.6	2.8
PV1590EL00	1-1/2"	41	400	8.25	10.6	2.6
PV2090EL00	2"	53	640	9.50	12.0	3.5
PV2590EL00	2-1/2"	63	1210	10.50	14.8	4.7
PV3090EL00	3"	78	1950	13.00	17.0	5.3
PV3590EL00	3-1/2"	91	2630	15.00	20.9	6.1
PV4090EL00	4"	103	3280	16.00	21.0	6.5
PV5090EL00	5"	129	6750	24.00	32.0	11.2
PV6090EL00	6"	155	10510	30.00	41.0	12.1

PVC COATED ALUMINUM 90° ELBOWS

Description:


PVC Coated Aluminum 90° Elbows are available in standard & special radius dimensions and in various degrees as required. All elbows are manufactured from Calbond PVC coated conduit and meet all applicable standards.

Features:

- Exterior PVC coating thickness is a minimum 0.040"
- Interior Urethane coating thickness is a minimum 0.002"
- Specialized corrosion resistant coating provided on threads
- Sizes available are 1/2" to 6"
- Available in 90, 60, 45, and 30 degree bends

UL Listings Include:

- Calbond PVC coated conduit is UL/CUL listed in accordance to UL6A & ANSI C80.5
- Calbond PVC coated conduit is UL/cUL listed rigid nonferrous metal conduit with polyvinyl chloride coating verified for PVC adhesion performance
- Calbond PVC coated conduit complies with NEMA RN-1
- UL File Number E230584



Aluminum Item Number	Trade Size	Metric Size (mm)	Weight Per 100 (lbs)	Standard Radius A	Offset B	Tangent T
PA0590EL00	1/2"	16	31	4.25	6.0	1.7
PA0790EL00	3/4"	21	42	4.50	6.7	2.2
PA1090EL00	1"	27	76	5.75	8.0	2.4
PA1290EL00	1-1/4"	35	118	7.25	9.6	2.8
PA1590EL00	1-1/2"	41	157	8.25	10.6	2.6
PA2090EL00	2"	53	238	9.50	12.0	3.5
PA2590EL00	2-1/2"	63	449	10.50	14.8	4.7
PA3090EL00	3"	78	707	13.00	17.0	5.3
PA3590EL00	3-1/2"	91	970	15.00	20.9	6.1
PA4090EL00	4"	103	1114	16.00	21.0	6.5
PA5090EL00	5"	129	2223	24.00	32.0	11.2
PA6090EL00	6"	155	3261	30.00	41.0	12.1

PVC COATED GALVANIZED RIGID ELBOWS - 45°

Description:


PVC Coated GRC Elbows are to be installed on conduit raceways for underground stub-ups, and interconnection of conduit runs and other fittings.

Features:

- Fabricated from UL listed hot-dipped galvanized rigid conduit
- Threaded ends (NPT)

Features:

- UL & CUL Listed - UL6
- Threaded ends (NPT)
- UL File Number E226472
- UL6 with statements of conformance
- ANSI C80.1
- CalTrans Specification 86-2.05
- ASTM A239



Options:

- Available in any degree of bend from 5° to 90°, and special radius

Item Number	Trade Size	Weight (lbs)	Box Qty	A	B	C	T	Cut Length
PV0545EL00	1/2" X 45"	0.70	50	4.0	7.0	2.9	1.9	8.0
PV0745EL00	3/4" X 45"	0.90	50	4.5	7.4	3.0	2.0	9.0
PV1045EL00	1" X 45"	1.60	25	5.8	9.5	4.0	2.7	10.0
PV1245EL00	1-1/4" X 45"	2.90	20	7.3	13.1	5.4	4.3	15.5
PV1545EL00	1-1/2" X 45"	3.80	15	8.3	14.0	5.8	4.3	16.5
PV2045EL00	2" X 45"	5.40	10	9.5	16.1	6.6	5.4	18.5
PV2545EL00	2-1/2" X 45"	10.80	50	10.5	19.0	7.9	6.8	22.5
PV3045EL00	3" X 45"	14.70	35	13.00	20.5	8.5	6.7	23.5
PV3545EL00	3-1/2" X 45"	19.50	35	15.00	22.8	9.5	7.1	26.0
PV4045EL00	4" X 45"	29.30	35	16.00	29.2	12.1	10.5	33.5
PV5045EL00	5" X 45"	50.20	bulk	24.0	36.1	15.0	11.2	43.0
PV6045EL00	6" X 45"	77.60	bulk	30.00	42.9	17.8	12.8	48.0

*All dimensions are for informational purposes only *Tolerances +/- 5%*

PVC COATED GALVANIZED RIGID ELBOWS - 30°

Description:


PVC Coated GRC Elbows are to be installed on conduit raceways for underground stub-ups, and interconnection of conduit runs and other fittings.

Features:

- Fabricated from UL listed hot-dipped galvanized rigid conduit
- Threaded ends (NPT)

Features:

- UL & CUL Listed - UL6
- Threaded ends (NPT)
- UL File Number E226472
- UL6 with statements of conformance
- ANSI C80.1
- CalTrans Specification 86-2.05
- ASTM A239



Options:

- Available in any degree of bend from 5° to 90°, and special radius

Item Number	Trade Size	Weight Each	A	B	C	T	Cut Length
PV1230EL00	1-1/4" X 30"	2.5	7.3	12.8	3.50	4.9	13.5
PV1530EL00	1-1/2" X 30"	3.3	8.3	12.1	3.25	4.3	15.0
PV2030EL00	2" X 30"	5.0	9.5	15.4	4.11	5.7	17.0
PV2530EL00	2-1/2" X 30"	9.1	10.5	17.3	4.66	6.4	19.5
PV3030EL00	3" X 30"	12.5	13.00	18.8	5.05	6.6	20.0
PV3530EL00	3-1/2" X 30"	17.6	15.00	22.5	6.00	8.1	24.0
PV4030EL00	4" X 30"	23.2	16.00	25.4	6.75	9.3	27.0
PV5030EL00	5" X 30"	42.0	24.0	33.9	9.12	11.7	36.0
PV6030EL00	6" X 30"	61.3	30.00	37.7	10.09	12.2	40.0

*All dimensions are for informational purposes only *Tolerances +/- 5%*

PVC COATED GALVANIZED RIGID ELBOWS - 22-1/2°

Description:


PVC Coated GRC Elbows are to be installed on conduit raceways for underground stub-ups, and interconnection of conduit runs and other fittings.

Features:

- Fabricated from UL listed hot-dipped galvanized rigid conduit
- Threaded ends (NPT)

Features:

- UL & CUL Listed - UL6
- Threaded ends (NPT)
- UL File Number E226472
- UL6 with statements of conformance
- ANSI C80.1
- CalTrans Specification 86-2.05
- ASTM A239



Options:

- Available in any degree of bend from 5° to 90°, and special radius

Item Number	Trade Size	Weight Each	A	B	C	T	Cut Length
PV1222EL00	1-1/4" X 22-1/2"	2.2	7.3	11.6	2.32	4.6	12.0
PV1522EL00	1-1/2" X 22-1/2"	3.0	8.3	13.0	2.95	5.1	13.5
PV2022EL00	2" X 22-1/2"	4.5	9.5	14.9	2.95	5.9	15.5
PV2522EL00	2-1/2" X 22-1/2"	6.5	10.5	13.5	2.68	4.9	14.0
PV3022EL00	3" X 22-1/2"	11.1	13.00	17.2	3.42	6.4	17.8
PV3522EL00	3-1/2" X 22-1/2"	17.6	15.00	23.2	4.62	9.1	24.0
PV4022EL00	4" X 22-1/2"	22.1	16.00	24.9	4.96	9.8	25.8
PV5022EL00	5" X 22-1/2"	38.5	24.0	31.9	6.35	11.8	33.0
PV6022EL00	6" X 22-1/2"	55.2	30.00	34.8	6.91	12.2	36.0

*All dimensions are for informational purposes only *Tolerances +/- 5%*

PVC COATED GALVANIZED RIGID ELBOWS - 15°

Description:


PVC Coated GRC Elbows are to be installed on conduit raceways for underground stub-ups, and interconnection of conduit runs and other fittings.

Features:

- Fabricated from UL listed hot-dipped galvanized rigid conduit
- Threaded ends (NPT)

Features:

- UL & CUL Listed - UL6
- Threaded ends (NPT)
- UL File Number E226472
- UL6 with statements of conformance
- ANSI C80.1
- CalTrans Specification 86-2.05
- ASTM A239



Options:

- Available in any degree of bend from 5° to 90°, and special radius

Item Number	Trade Size	Weight Each	A	B	C	T	Cut Length
PV1215EL00	1-1/4" X 15"	2.1	7.3	11.3	1.53	4.8	11.5
PV1515EL00	1-1/2" X 15"	2.8	8.3	12.8	1.69	5.4	13.0
PV2015EL00	2" X 15"	4.1	9.5	13.8	1.84	5.8	14.0
PV2515EL00	2-1/2" X 15"	7.5	10.5	15.8	2.08	6.6	16.0
PV3015EL00	3" X 15"	10.2	13.00	16.0	2.14	6.4	16.3
PV3515EL00	3-1/2" X 15"	13.9	15.00	18.6	2.49	7.5	19.0
PV4015EL00	4" X 15"	19.7	16.00	22.7	3.00	9.4	23.0
PV5015EL00	5" X 15"	32.7	24.0	27.6	3.64	10.9	28.0
PV6015EL00	6" X 15"	49.1	30.00	31.5	4.16	12.1	32.0

*All dimensions are for informational purposes only *Tolerances +/- 5%*

PVC COATED GALVANIZED RIGID ELBOWS - 11-1/4°

Description:


PVC Coated GRC Elbows are to be installed on conduit raceways for underground stub-ups, and interconnection of conduit runs and other fittings.

Features:

- Fabricated from UL listed hot-dipped galvanized rigid conduit
- Threaded ends (NPT)

Certifications and Compliances:

- UL & CUL Listed - UL6
- Threaded ends (NPT)
- UL File Number E226472
- UL6 with statements of conformance
- ANSI C80.1
- CalTrans Specification 86-2.05
- ASTM A239



Options:

- Available in any degree of bend from 5° to 90°, and special radius

Item Number	Trade Size	Weight Each	A	B	C	T	Cut Length
PV1211EL00	1-1/4" X 11-1/4"	2.0	7.3	10.9	0.98	4.8	11.0
PV1511EL00	1-1/2" X 11-1/4"	2.2	8.3	9.9	1.00	4.2	10.0
PV2011EL00	2" X 11-1/4"	3.8	9.5	12.9	1.29	5.6	13.0
PV2511EL00	2-1/2" X 11-1/4"	7.2	10.5	15.4	1.56	6.7	15.5
PV3011EL00	3" X 11-1/4"	10.6	13.00	16.8	1.64	7.2	17.0
PV3511EL00	3-1/2" X 11-1/4"	15.4	15.00	20.8	2.07	9.0	21.0
PV4011EL00	4" X 11-1/4"	18.0	16.00	20.8	2.08	8.9	21.0
PV5011EL00	5" X 11-1/4"	30.7	24.0	26.0	2.56	10.8	26.3
PV6011EL00	6" X 11-1/4"	46.0	30.00	29.7	2.91	12.1	30.0

*All dimensions are for informational purposes only *Tolerances +/- 5%*