

TYPE CL50-1 COPPER LAY-IN QIKLUG™ For Copper



The Lay-In QIKLUG™ is manufactured from high strength pure electrolytic copper to ensure maximum strength and conductivity. UL467 Listed for Direct Burial in earth or concrete. The open-faced design allows for fast lay-in of the conductor without the need for cutting or breaking.

Catalog Number	Conductor Range Copper	Stud Hole
CL50-1	14 - 4 AWG	10

NOTE: Stainless Steel Screws

Type KPB

For Copper




UL467 Listed for direct burial application in earth or concrete.

Catalog Number	Cable Range	Stud Hole
KPB4CG1	10 - 4 str.	10*

*To be assembled with TMH322 stainless steel hardware kit, ordered separately.

UNIVERSAL TERMINAL Type K11A-U



For Aluminum and Copper
Conductors

Dual-rated panelboard lugs are constructed from high strength extruded aluminum alloy and electro tin-plated to provide low contact resistance.

Catalog Number	Conductor Range	Stud Hole Size	Figure Number
K11A30U*	Two: 6 str. - 300 kcmil	5/16	1
K11A34U-2	Two: 4/0 str. - 500 kcmil	1/4	2
K11A36U-2	Two: 2 str. - 600 kcmil	3/8	3
K21A36U-2	Three: 2 str. - 600 kcmil	3/8	4
K22A36U-2	Four: 2 str. - 600 kcmil	3/8	5
K11A39U-2	Two: 1/0 str. - 750 kcmil	3/8	3
K22A39U-2	Four: 1/0 str. - 750 kcmil	3/8	5

* Not CSA listed