369549c 1 10.07.14


### PowPak™ Relay Module

The PowPak™ Relay Module is a radio frequency (RF) device capable of controlling up to 5 A of general-purpose load based on input from Pico® controls and Radio Powr Savr™ occupancy and daylight sensors. An optional, low-voltage dry contact closure output is available to communicate occupancy status to 3rd-party systems such as HVAC controllers.

Communication with RF input devices, such as Pico<sub>®</sub> controls and Radio Powr Savr<sub>™</sub> sensors, is accomplished using Lutron Clear Connect<sub>™</sub> RF Technology.

### **Features**

- Capable of switching 5 A of general-purpose loads
- Optional low-voltage dry contact closure output provides integration to building management systems, HVAC, VAV, etc.
- Various operating voltages available refer to model number chart below for details on voltage requirements
- Receives wireless inputs from up to nine Pico<sub>®</sub> controls, six Radio Powr Savr<sub>™</sub> occupancy/vacancy sensors, and one Radio Powr Savr<sub>™</sub> daylight sensor
- Utilizes Lutron Clear Connect™ RF Technology refer to model number chart below for frequency band data
- Mounts to a junction box through a standard half-inch (NPT trade size) knockout
- Complies with requirements for use in a compartment handling environmental air (plenum) per NEC<sub>®</sub> 2011 300.22(C)(3)



Description	Model Number	Operating Voltage	Frequency Band	Region
PowPak™ Relay Module	RMJ-5R-DV-B	120/277 V∼	431.0 – 437.0 MHz	U.S.A., Canada, Mexico
	RMQ-5R-DV-B	220-240 V~	433.05 – 434.79 MHz	Hong Kong, Macau
	RMM-5R-DV-B	220-240 V~	868.125 – 868.475 MHz	China, Singapore
PowPak™ Relay Module with Occupancy-Status	RMJ-5RCCO1-DV-B	120/277 V∼	431.0 – 437.0 MHz	U.S.A., Canada, Mexico
cco	RMQ-5RCCO1-DV-B	220-240 V~	433.05 – 434.79 MHz	Hong Kong, Macau
	RMM-5RCCO1-DV-B	220-240 V~	868.125 – 868.475 MHz	China, Singapore

**NOTE:** Contact Lutron for frequency band compatibility for your geographic region if it is not indicated above.

<b>\$LUTRON</b> ®	SPECIFICATION	SUBMITTAL
-------------------	---------------	-----------

Job Name:	Model Numbers:
Job Number:	

369549c 2 10.07.14

# **Specifications**

### **Regulatory Approvals**

### RMJ- models only

- UL Listed
- UL 2043 Plenum Rated
- FCC approved. Complies with the limits for a Class B device, pursuant to Part 15 of the FCC rules.
- CSA and IC
- COFETEL
- NOM

#### **Power**

• Operating voltage:

**RMJ- models**  $120/277 \text{ V} \sim 50/60 \text{ Hz}$  **RMQ- models**  $220-240 \text{ V} \sim 50/60 \text{ Hz}$  **RMM- models**  $220-240 \text{ V} \sim 50/60 \text{ Hz}$ 

#### **System Communication**

- Operates using Clear Connect<sub>™</sub> RF Technology for reliable wireless communication; refer to model number chart on page 1 for frequency band details
- RF range is 30 ft (10 m)

### **Environment**

- Ambient operating temperature: 32 °F to 131 °F (0 °C to 55 °C)
- 0% to 90% humidity, non-condensing
- For indoor use only

#### Load

- Maximum load: 5 A general purpose. No minimum load requirements.
- Load types include (but are not limited to):
  - Incandescent
  - MLV
  - FI V
  - Resistive
  - Inductive
  - Magnetic fluorescent
  - Electronic fluorescent
- Motor rating:

**RMJ- models** 1/6 HP (120 V~), 1/3 HP (277 V~)

RMQ- models 1/2 HP (220-240 V~) RMM- models 1/2 HP (220-240 V~)

Load relay is non-latching

#### **SPECIFICATION SUBMITTAL**

# Key Design Features


- LED status indicator shows current load status and provides programming feedback
- Power failure memory: If power is interrupted, connected loads will return to the previous level prior to interruption
- Daylighting can be overridden by pressing the ON button on any associated Pico®
  - Daylighting will be re-enabled after 2 hours or after the area becomes unoccupied

### Contact Closure Output (CCO version only)

- Provides occupancy status to 3rd-party equipment such as building management systems, HVAC, and VAV controllers
- Provides both normally open (NO) and normally closed (NC) dry contacts
- Maintained output type
- CCO terminals accept 20 to 16 AWG (0.5 to 1.5 mm²) solid or stranded wire
- Output is latching
- Not for voltages greater than 24 V

Switching	Resistive	
Voltage	Load R	
0-24 V===	1.0 A	
0-24 V~	0.5 A	


 The CCO is not rated to control unclamped, inductive loads. Inductive loads include, but are not limited to, relays, solenoids, and motors. To control these types of equipment, a flyback diode must be used (DC voltages only). See diagram below. For more information, please see Application Note #434 (p/n 048434).



The state of Earlie of Copies		ı ago
Job Name:	Model Numbers:	
Job Number:		


369549c 3 10.07.14

# System Diagram



Radio Powr Savr™ Daylight Sensor (up to 1)

# Wiring Diagram




### **LUTRON** SPECIFICATION SUBMITTAL

Job Number:

369549c 4 10.07.14


# Wiring Diagram



CCO operation affected only by associated occupancy or vacancy sensors.

**Room Occupied:** NO = Close NC = Open Room Unoccupied: NO = Open NC = Close

In some applications, a PowPak<sub>TM</sub> module can be installed inside a 4 in x 4 in (102 mm x 102 mm) junction box. For information about how to perform this installation, please see Application Note #423 (p/n 048423).




### **LUTRON** SPECIFICATION SUBMITTAL


Job Name:	Model Numbers:	
Job Number:		

369549c 5 10.07.14


### **Dimensions**

Dimensions are shown as: in (mm)





# Range Diagram



All Wireless Transmitters must be installed within 30 ft (10 m) of the PowPak $_{\text{TM}}$  Relay Module.

• Contact Lutron first for applications using foil-backed or metallic ceiling tiles.

### **LUTRON** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:	
Job Number:		

### 369549c 6 10.07.14

# **Default Operation**

Transmitting Device	Transmitted Command	Load Relay Default Action	CCO Default Action
Pico <sub>®</sub>	On	Close	No Action
	Off	Open	No Action
	Raise	No Action	No Action
	Lower	No Action	No Action
	Preset	Close	No Action
Radio Powr Savr™	Occupied	Close	NO = Close, NC = Open
Occupancy Sensor	Unoccupied	Open	NO = Open, NC = Close
Radio Powr Savr™	Occupied	No Action	NO = Close, NC = Open
Vacancy Sensor	Unoccupied	Open	NO = Open, NC = Close
Radio Powr Savr™ Daylight Sensor	Ambient Light Below Target Level	Close	No Action
	Ambient Light Above Target Level	Open	No Action

# **LUTRON** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	