

HELL MAY FREEZE OVER

BUT YOU WILL BE WARM



Insulated Gear

www.mcrcsafety.com 800-955-6887
#weprotectpeople



MCR SAFETY

Vortex™ Hi-Vis Insulated Gear

VT38JH Vortex™ Jacket Sizes: S-X5

ANSI/ISEA 107-2015, Type R, Class 3, CSA Z96-15, Class 2, Level 2, Hi-Vis Fluorescent Lime to Black, Quality Rip-Stop Polyester/PU Material, Double Insulation, Permanent Quilted Liner, Removable Fleece Liner, Protects in Temperatures 5° to -27° Fahrenheit, Drawstring Waist and Adjustable Hook and Loop Wrists, Two Way Front Zipper, 10 Outer Pockets, 2 Inner Pockets, 2 Mic-Tab Holders, 2" Silver Reflective Stripes Trimmed in Orange, Black Shading Hides Soiling.

VT38BP Vortex™ Bib Pants Sizes: S-X5

ANSI/ISEA 107-2015, Class E, Hi-Vis Fluorescent Lime to Black, Quality Rip-Stop Polyester/PU Material, Quilted Insulating Liner, Protects in Temperatures 5° To -27° Fahrenheit, Easy Release Suspenders, 4 Front and 2 Back Pockets, Hammer Loop, Zippered Front Bib Gusset and Ankle Gussets, Dual 2" Silver Reflective Stripes Trimmed in Orange, Black Shading Hides Soiling.



UltraTech™ Hi-Vis Rainwear

UT38JH UltraTech™ Jacket Sizes: S-X5

ANSI/ISEA 107-2015, Type R, Class 3, Hi-Vis Fluorescent Lime to Black, Breathable Polyester Coated PU Material, Waterproof and Wind Resistant, Attached / Hook And Loop Adjustable Hide-Away Hood with Locking Drawstring, Lined in Cool Polyester Satin, Weather Sealed Zippers, 3 Outer Pockets, Made Tough - Rugged and Long Lasting Design, Black Trim Hides Soiling, 2" Silver Reflective Stripes.

UT38BP UltraTech™ Bib Pants Sizes: S-X5

ANSI/ISEA 107-2015, Class E, Hi-Vis Fluorescent Lime to Black, Breathable Polyester Coated PU Material, Waterproof and Wind Resistant, Inner Knee Pockets Accept Knee Pads for Comfort On Hard Surface, Expandable Zipper Bib and Ankle Gussets, Lined In Cool Polyester Satin, Weather Sealed Zippers, 4 Outer Pockets, Made Tough - Rugged and Long Lasting Design, Black Trim Hides Soiling, 2" Silver Reflective Stripes.




Reversed to
Black Side



BRCL3L Reversible Bomber Jacket Sizes: M-X5
Type R, Class 3, Luminator™, Reversible Bomber Jacket, Fluorescent Lime to Black, PU/Cotton Polyester Material, Attached Hide-Away Hood, Teflon Treated on Fluorescent Lime Side, 2" Silver Reflective Stripes.



S2CL3LZ Hoodie Sizes: M-X5
ANSI/ISEA 107-2015, Type R, Class 3, Luminator™, Hi-Vis Lime/Black, Polyester Material with Soft Fleece Inner Texture, Attached Drawstring Hood, Zipper Front Closure, Slanted Front Pockets, 2" Silver Reflective Stripes.



BWCL2L Body Warmer Sizes: L-X4
Type R, Class 2, Hi-Vis Fluorescent Lime Body Warmer Vest, Water Resistant Polyester Outer Shell with Insulated Polyester Fleece Liner, Zipper Front, Elastic Waist, 2" Silver Reflective Stripes.



LSTSC3MO Sizes: S-X5
Type R, Class 3, Fluorescent Orange, Long Sleeve Polyester Birdseye Mesh Fabric, Left Breast Pocket, 2" Silver Reflective Stripes.

Polarized Safety Glasses Offer Greater Vision by Reducing Glare and Easing Eye Fatigue

Excellent Options for Both Bright and Reflective Outdoor Areas: Offshore Rigs, Waterways, Roofing, Transportation, Aviation, and Snow Environments.

Polarized Benefits

- Reduction of reflected light (glare).
- Minimizes eye fatigue.
- Improves optical clarity.
- Enhances contrast and depth perception.

Crews 3

Translucent Brown Frame
CR132BAFZ Brown Anti-Fog Lens

Dominator™ 3

Black Frame, Black TPR
DM1337BZ BossMan® Black Mirror Lens

Dominator™ 3

Clear Frame, Blue TPR
DM1328BZ BossMan® Blue Diamond Mirror

Dominator™ 3

Gun Metal Color Frame, Red TPR
DM131RZ BossMan® Fire Mirror Lens

Tribal® V

Graphite Frame With Vent
TB112AFZ Gray Anti-Fog Lens

Swagger®

Black Frame
SR112Z Gray Lens

USS Defense®

Dark Blue Frame, Gray TPR
UD128BZ BossMan® Blue Diamond Mirror

USS Defense®

Gun Metal Color Frame, Gray TPR
UD11RZ BossMan® Fire Mirror Lens



Garments



POCKET
3-out
2-liner



BPCL3L 4-in-1 Insulated Bomber Jacket Sizes: L-X4
Type R, Class 3, Luminator™, 4-in-1 Insulated Bomber Jacket, Zip Out Liner, Zip Off Outer Sleeves, 2" White Reflective Stripes.

POCKET
3-out
3-in



BP2CL3O 2-in-1 Insulated Bomber Jacket Sizes: M-X5
Type R, Class 3, Luminator™, 2-in-1 Bomber Jacket with Removable Zip Out Fleece Liner, PU/Cotton Polyester Material, Attached Hide-Away Hood, 2" Silver Reflective Stripes.

POCKET
3-out
1-in



BBCL3L Insulated Bomber Jacket Sizes: L-X4
Type R, Class 3, Two Tone Bomber Jacket, Insulated and Water Resistant, Fluorescent Lime/Black, 2" Silver Reflective Stripes.

POCKET
3-out
3-in



VBBCL3L Value Bomber Jacket Sizes: S-X5
Type R, Class 3, Two Tone Value Bomber Jacket, Insulated and Water Resistant, Fluorescent Lime/Black, 2" Silver Reflective Stripes.

POCKET
3-out
2-in



BMRCL3L Insulated Jacket Sizes: L-X4
Type R, Class 3, Luminator™, Hi-Vis Insulated Jacket, Attached Drawstring Hood, Fluorescent Lime, 2" Silver Reflective Stripes.

POCKET
3-out



BMRCL3LP Insulated Pants Sizes: L-X4
Class E, Luminator™, Hi-Vis Insulated Elastic Waist Pant, Draw String Waist, Fluorescent Lime, 2" Silver Reflective Stripes.



Insulated Ninja® Gloves



HYDROPELLENT™ TECHNOLOGY

Unique Features of Ninja® Ice HPT™

Independent Testing Endorses the Ninja® Ice HPT™ Polymer remains soft and flexible on the glove after 10,000 flexes at -4°F and after 4 hours of exposure at -58°F/-20°C



N9690FCO Ninja® Ice Fully Coated

Sizes: S-XXL

15-Gauge Hi-Vis Orange Nylon Exterior Shell over a 7-Gauge, Brushed Acrylic Interior Liner with Hi-Vis Orange Proprietary HPT™ (Hydropellent Technology™) Fully Coated for Extra Liquid Protection, ANSI Cut Level A3.



N9690HV Ninja® Ice Hi-Vis

Sizes: M-XXL

15-Gauge Hi-Vis Lime Nylon Exterior Shell over a 7-Gauge Brushed Acrylic Interior Liner with Hi-Vis Lime Proprietary HPT™ (Hydropellent Technology™) Coating on Palm and Fingertips with Additional Over-the-Knuckle Coating, ANSI Cut Level A3.



N9690FC Ninja® Ice Fully Coated

Sizes: M-XXL

15-Gauge Nylon Exterior Shell over a 7-Gauge Brushed Acrylic Interior Liner with Black Proprietary HPT™ (Hydropellent Technology™) Fully Coated for Extra Liquid Protection, ANSI Cut Level A3.



N9690 Ninja® Ice Sizes: S-XXL

15-Gauge Nylon Exterior Shell over a 7-Gauge Brushed Acrylic Interior Liner with Black Proprietary HPT™ (Hydropellent Technology™) Coating on Palm and Fingertips, ANSI Cut Level A3.



N9695 Ninja® Coral Sizes: M-XXL

15-Gauge Hi-Vis Orange Nylon Exterior Shell over a 7-Gauge Acrylic Terry Interior Shell with Black Coral Over-the-Knuckle Coating Over Premium Clear PVC Full Dip, ANSI Cut Level A3.



N9690TC Ninja® Thermo Force

Sizes: S-XXL

13-Gauge Dyneema®/Synthetic Outer Shell over a Brushed Acrylic Interior Liner with Black Textured Bi-Polymer Coating on Palm and Fingertips, ANSI Cut Level A5.



Ninja® is a registered trademark of Midas Safety, Inc. MCR Safety is the exclusive distributor for Ninja® products in the United States. Dyneema® is a registered trademark of Royal DSM™ N.V.

Insulated Gloves



1925W Snort-N-Boar Sizes: S-XL
Wool Lining, Premium Grain Pigskin,
Shirred Elastic Back, 2.5" Rubberized
Safety Cuff, Wing Thumb.

14 CAL
CAT 2



MU36211 Mustang Sizes: M-XXL
Fleece Lining, Premium Brown
Goatskin Leather, Second Layer of
Premium Brown Goatskin in the Palm,
Fingertips and Knuckle, Sewn with
Dupont™ Kevlar® Thread, Shirred
Elastic Back, Wing Thumb,
Arc Rating of 14 cal/cm2 / CAT 2,
Waterproof Lining*.



9622 Thermastat™
Sizes: One Size Fits All
10-Gauge, 100% DuPont® Thermastat™,
Blue color hollow-core hydrophobic
polyester fiber that traps air inside the
fiber, keeping your hands warm. These
fibers then move moisture away from
your skin, keeping your hands dry.

9620 Same as above, White color.



1450 Size: L

Foam Lining, Premium Split Leather
Palm Glove, Blue/Yellow/Black Stripe
Fabric with Shirred Elastic Back,
2.5" Plasticized Safety Cuff,
Wing Thumb.



995 Multi-Task Sizes: XS-XXL
Fleece Lining, Mossy Oak Break Up
Infinity® Back and Thumb, Gray Synthetic
Leather Palm and Fingers, Reinforced
Thumb Crotch, Expandable Slip-On Cuff,
Hemmed, Wing Thumb.

3750 Driver Sizes: S-XL

Red Fleece Lining, Beige Synthetic Split
Cowhide Texture, Shirred Elastic Back,
Keystone Thumb.






Insulated Gloves


ThermoSock® Lining - By using finely spun polyester, our ThermoSock® high loft fiber traps air as it moves through the multi-layer lining, using your body heat to warm the cool air before it reaches your skin. The higher gram weight fibers in the lining, the more friction and heat is created as the air moves through the lining.

Our ThermoSock® fabric inner lining quickly wicks away any body perspiration, keeping your hands dry and warm.

All ThermoSock® offerings are constructed with a full sock lining (glove inside a glove) and are 40 gram weight unless otherwise noted.



ThermoSock®
Liner Shown



1956 Artic Jack™ Sizes: S-XL
ThermoSock® Lining, Split Pigskin
Leather, Blue Fabric Back, Shirred
Elastic Back, Knit Wrist, Wing Thumb.



19261 Luminator™ Sizes: S-XL
ThermoSock® Lining, Grain Pigskin,
Orange Material Back with
Lime/Silver Retro-Reflective
Material on Knuckles and Cuff,
2.5" Safety Cuff, Wing Thumb.



1965 Artic Jack™ Sizes: M-XXL
ThermoSock® Lining, Premium Grain
Pigskin, 2.5" Rubberized Safety Cuff,
Wing Thumb.



3440 Luminator™ Sizes: S-XL
ThermoSock® Lining, Grain
Pigskin Palm, Orange Material
Back with Lime/Silver Retro-
Reflective Material, Knit Wrist,
Wing Thumb.



3460 Artic Jack™ Sizes: S-XL
ThermoSock® Lining, Premium
Grade Grain Pigskin, , Shirred Elastic
Back, Keystone Thumb.



34411 Luminator™ Sizes: S-XL
ThermoSock® Lining, Black Grain
Pigskin, Orange Mesh Back with
Lime/Silver Retro-Reflective
Material, Knit Wrist, Wing Thumb,
Breathable Waterproof Lining*.



Insulated Gloves



918 MCR Safety Multi-Task

Sizes: S-XXXL

40 Gram **Thinsulate**® Palm, 70 Gram **Thinsulate**® Back, Synthetic Leather Palm Reinforced with Specialized PVC Coated Material, Reinforced Thumb Crotch, Dupont™ Kevlar® Full Sock Liner, Adjustable Wrist Closure, Wing Thumb, Breathable Waterproof Lining*, ANSI Cut Level A3.



HV200 Forceflex® Sizes: M-XXXL

40 Gram **Thinsulate**® Palm, 70 Gram **Thinsulate**® Back, Clarino® Leather, Rough Kevlar® Palm with EVA Padding, Injection Molded TPR Padding on the Back of Hand and Fingers, Reinforced Palm, Neoprene Slip-On Cuff with Side Flex Panels, Reflexite® Micro-Prismatic, Retroreflective Material on Both Sides of Cuff, with Pocket in the Cuff for Heat Pack, Wing Thumb, Breathable Waterproof Lining*, EN511 Contact Cold Level 2.



904 Fasguard Sizes: S-XL

100 Gram **ThermoSock**® Lining, Synthetic Leather Palm and Fingers, Multi-Layered Knuckle Protection Including Foam Pads, Blue Spandex Fabric Back, Adjustable Wrist Closure, Wing Thumb.



968 Luminator™ Sizes: S-XL

180 Gram **ThermoSock**® Lining, High Visibility Material with Quality Reflective Stripe, Premium Grain Goatskin Leather, Adjustable Wrist Closure, 2 Silver Reflective Stripes on Back and on 3 Fingertips, Keystone Thumb.



6712F Size: L

Premium Foam Lined, Orange Double Dipped PVC, Fluorescent Orange, Smooth Finish, 12" Length, Waterproof.



926 Multi-Task Sizes: S-XXL

ThermoSock® Lining, Synthetic Leather Palm with PVC Dots, Hi-Vis Lime Green Fabric Back, Black Synthetic Fingertips and Reinforced Thumb Crotch, Neoprene Wrist, Terry Cloth Thumb, Adjustable Wrist Closure, Wing Thumb, Breathable Waterproof Lining*.



* Our Breathable Waterproof Liners Stop Water From the Outside, Yet Allow Moisture and Body Steam to Exit.

Kevlar® is a registered trademark of E. I. du Pont de Nemours and Company.