




Self-holding clamping nut with spring attached.  
For use with 1/4" deep channels.



Square nuts for use with channel and spot-type concrete inserts.

### Channel Nuts—continued

#### B-912 Series

Cat. No.	Size	Thickness	Wt. lbs./C
<b>B-912-1/4</b>	1/4 - 20	3/16	8.0
<b>B-912-3/8</b>	3/8 - 18	5/16	7.5
<b>B-912-1/2</b>	1/2 - 16	5/16	9.5
<b>B-912-3/4</b>	3/4 - 13	5/16	9.8

Standard finish: Galv-Krom

#### B-914 Series

Cat. No.	Size	Thickness	Wt. lbs./C
<b>B-914-1/4</b>	1/4 - 20	3/16	10.50
<b>B-914-3/8</b>	3/8 - 16	5/16	13.25
<b>B-914-1/2</b>	1/2 - 13	3/8	14.00
<b>B-914-3/4</b>	3/4 - 11	3/8	14.00
<b>B-914-1"</b>	1" - 10	1/2	12.00
<b>B-914-1 1/4"</b>	1 1/4" - 9	3/4	10.50
<b>B-914-1 1/2"</b>	1 1/2" - 8	1/2	12.00
<b>B-914-1 3/4"</b>	1 3/4" - 7	1/2	11.00

\*\* Standard Pipe Threads.

Standard finish: Galv-Krom

#### Load Ratings of Steel Channel and Insert Nuts

(B-910 1/2 or B-91VA) when used in slot of 12 ga. Kindorf channel and tightened to a torque of 50 ft. Pounds are as follows:


Withdrawal resistance to pull out safe load rating - 1600 lbs. Slip resistance safe loading rating = 400 lbs.

(B-910 1/2 or B-912 1/2) when used in slot of 14 ga. Kindorf channel and tightened to a torque of 50 ft. Pounds are as follows:

Withdrawal resistance to pull out safe load rating - 1300 lbs. Slip resistance safe load rating = 400 lbs.

Load ratings are based on safety factor of 3.

### Galv-Krom®



ASTM Spec. For Finish: B-633-85

### The Galv-Krom® Superior Finish


Galv-Krom is the time-tested and proved metal finish that provides Kindorf with an outstanding measure of product value. It is not a paint—won't chip or peel. Stands up under rough handling.

Galv-Krom is a superior galvanized finish, plus zinc chromate, resulting in an attractive bronze lustre that needs no painting for protection or appearance. The finish is smooth, clean and remarkably tough. When colorizing is necessary for coding, you'll find Galv-Krom an excellent bond for the paint of your choice. The surface does not require an acid wash preparation and is non-porous and non-crystalline.

Unlike paint or enamel this surface also offers a minimum of electrical resistance so that electrical applications are easily grounded as required under most electrical codes.

Galv-Krom protects the steel against rust and corrosion. Kindorf channels, fittings and accessories, including all threaded parts, are Galv-Krom finish. Channel and fittings with bolt holes are finished after holes are punched so that it has complete Galv-Krom protection.

Galv-Krom is a combination of a .5 mil of electrogalvanizing on steel and gold zinc chromate. The base zinc thickness is in compliance with ASTM B633-85 Type LS coating. Zinc, unlike organic coatings, is a sacrificial type plating protecting the base steel from corrosion even though it is exposed at cut edges or scratches. The additional gold zinc chromate film provides a passivating nonporous barrier against moisture and other corrosive elements.



**ThomasiBetts**