



# Kindorf®

## Pipe Supports



- Fits E.M.T., I.M.C., rigid conduit.
- Size range ½" thru 2".
- Can be used on 1½" or 1¾" channel.
- Saves inventory dollars.
- Corrosion resistant Galv-Kröm finish.
- One piece construction means no assembly required.
- Installs directly over conduit for easy installation.
- 50% reduction of installation time.
- No twisting required to install.
- Slotted hex head screw.

### C-200 Universal Pipe Straps

Cat. No.	EMT, IMC, Rigid Pipe Size	Pipe O.D. Range	Strap Thickness	Wt. lbs./C
C-200-1/2	½"	.706 – .804	14 ga.	12
C-200-3/4	¾"	.922 – 1.060	14 ga.	13
C-200-1	1"	1.163 – 1.315	14 ga.	14
C-200-1-1/4	1¼"	1.508 – 1.660	14 ga.	16
C-200-1-1/2	1½"	1.738 – 1.900	12 ga.	27
C-200-2	2"	2.196 – 2.375	12 ga.	31

Design load equal to C-105 straps.

### EZ-Strap

The C-108 Universal Pipe Strap

Cat. No. & Size	Dimensions (in.)			Thickness Steel	O.D. Size	Wt. lbs./C
	Conduit or Pipe Size					
C-108-1/2	½ EMT	½ IMC	½ Rigid	16 ga.	7/8	8
C-108-3/4	¾ EMT	¾ IMC	¾ Rigid	16 ga.	1 <sup>23</sup> / <sub>32</sub>	10
C-108-1	1 EMT	1 IMC	1 Rigid	16 ga.	1 <sup>11</sup> / <sub>32</sub>	10
C-108-1-1/4	1¼ EMT	1¼ IMC	1¼ Rigid	14 ga.	1 <sup>11</sup> / <sub>16</sub>	15
C-108-1-1/2	1½ EMT	1½ IMC	1½ Rigid	14 ga.	1 <sup>15</sup> / <sub>16</sub>	16
C-108-2	2 EMT	2 IMC	2 Rigid	14 ga.	2 <sup>13</sup> / <sub>32</sub>	19

### Framing Channel Clamp

Cat. No.	Channel Size	Maximum Tie Width Accom.	Unit Quan.	Std. Pkg.
TC5363X	1.5 & 1.625	.301	50	250

Mounting bases for heavy duty applications are made from high-impact weather-resistant nylon.

### Ty-Rap® Installation



- Installs with a push and twist.
- Smooth design protects cable insulation.

- Designed for indoor or outdoor use.
- Takes range of cable diameters.

When fastening wire bundles, cables, or hoses to framing channels, you can cut costs considerably by using the TY-RAP® cable clamp. It is made of smooth, weather-resistant nylon and designed to protect cable insulation and hoses from wear or damage as can occur with metal clamps. The clamp may be used for both indoor or outdoor applications. It installs in the framing channel with a simple push and twist. It requires no screws, nuts or tools. The clamp fits all 1½" and 1¾" channels regardless of channel depth.

**Thomas & Betts**