

Pass & Seymour



Pin & Sleeve Devices


Ratings, compliances visible
on strap for fast, long-lasting I.D.

Arrives ready to wire, with cord grip open and cable-ready; terminal screws come backed out and ready to wire; front and back body require no disassembly prior to assembly.

Cover with integral neoprene gasket provides watertight seal.

Revolutionary, hinged cord grip for durable performance and ease of installation.

Combination-head screws for added convenience and quick installation.



Nylon construction for high-impact and corrosion resistance.

Nickel-plated brass pins provide extra corrosion resistance without sacrificing electrical conductivity.

Natural-rubber grommets provide watertight protection at cable entry.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.



P&S Pin & Sleeve products provide installation ease, enduring performance in harsh conditions, and guaranteed IEC 309 compatibility.

Pin & Sleeve Devices North American Watertight Devices Ordering Information

Pass & Seymour



North American Product Offering

				Watertight			Back Boxes					
Configuration									Replacement Parts			
Poles & Wires	Recep./ Conn.	Plug/ Inlet	Voltage/ Color Coding	Receptacle	Plug	Connector	Metallic Back Box	Non-Metallic Back Box	Bodies		Caps	
									Plug	Connector	Receptacle	Connector
20 Amps												
2P3W			125	PS320R4W	PS320P4W	PS320C4W	PSBB201W	PSBBN201W	PS320P4WR	PS320C4WR	PS320R4WL	PS320C4WL
2P3W			250	PS320R6W	PS320P6W	PS320C6W	PSBB201W	PSBBN201W	PS320P6WR	PS320C6WR	PS320R6WL	PS320C6WL
2P3W			480	PS320R7W	PS320P7W	PS320C7W	PSBB201W	PSBBN201W	PS320P7WR	PS320C7WR	PS320R7WL	PS320C7WL
2P3W			277	PS320R5W	PS320P5W	PS320C5W	PSBB201W	PSBBN201W	PS320P5WR	PS320C5WR	PS320R5WL	PS320C5WL
3P4W			125/250	PS420R12W	PS420P12W	PS420C12W	PSBB202W	PSBBN202W	PS420P12WR	PS420C12WR	PS420R12WL	PS420C12WL
3P4W			3ø 250	PS420R9W	PS420P9W	PS420C9W	PSBB202W	PSBBN202W	PS420P9WR	PS420C9WR	PS420R9WL	PS420C9WL
3P4W			3ø 480	PS420R7W	PS420P7W	PS420C7W	PSBB202W	PSBBN202W	PS420P7WR	PS420C7WR	PS420R7WL	PS420C7WL
3P4W			3ø 600	PS420R5W	PS420P5W	PS420C5W	PSBB202W	PSBBN202W	PS420P5WR	PS420C5WR	PS420R5WL	PS420C5WL
4P5W			3øY 120/208	PS520R9W	PS520P9W	PS520C9W	PSBB202W	PSBBN202W	PS520P9WR	PS520C9WR	PS520R9WL	PS520C9WL
4P5W			3øY 277/480	PS520R7W	PS520P7W	PS520C7W	PSBB202W	PSBBN202W	PS520P7WR	PS520C7WR	PS520R7WL	PS520C7WL
4P5W			3øY 347/600	PS520R5W	PS520P5W	PS520C5W	PSBB202W	PSBBN202W	PS520P5WR	PS520C5WR	PS520R5WL	PS520C5WL
30 Amps												
2P3W			125	PS330R4W	PS330P4W	PS330C4W	PSBB301W	PSBBN301W	PS330P4WR	PS330C4WR	PS330R4WL	PS330C4WL
2P3W			250	PS330R6W	PS330P6W	PS330C6W	PSBB301W	PSBBN301W	PS330P6WR	PS330C6WR	PS330R6WL	PS330C6WL
2P3W			480	PS330R7W	PS330P7W	PS330C7W	PSBB301W	PSBBN301W	PS330P7WR	PS330C7WR	PS330R7WL	PS330C7WL
3P4W			125/250	PS430R12W	PS430P12W	PS430C12W	PSBB301W	PSBBN301W	PS430P12WR	PS430C12WR	PS430R12WL	PS430C12WL
3P4W			3ø 250	PS430R9W	PS430P9W	PS430C9W	PSBB301W	PSBBN301W	PS430P9WR	PS430C9WR	PS430R9WL	PS430C9WL
3P4W			3ø 480	PS430R7W	PS430P7W	PS430C7W	PSBB301W	PSBBN301W	PS430P7WR	PS430C7WR	PS430R7WL	PS430C7WL
3P4W			3ø 600	PS430R5W	PS430P5W	PS430C5W	PSBB301W	PSBBN301W	PS430P5WR	PS430C5WR	PS430R5WL	PS430C5WL
3P4W*			380/440	PS430R3W	PS430P3W	PS430C3W	PSBB301W	PSBBN301W	PS430P3WR	PS430C3WR	PS430R3WL	PS430C3WL
4P5W			3øY 120/208	PS530R9W	PS530P9W	PS530C9W	PSBB301W	PSBBN301W	PS530P9WR	PS530C9WR	PS530R9WL	PS530C9WL
4P5W			3øY 277/480	PS530R7W	PS530P7W	PS530C7W	PSBB301W	PSBBN301W	PS530P7WR	PS530C7WR	PS530R7WL	PS530C7WL
4P5W			3øY 347/600	PS530R5W	PS530P5W	PS530C5W	PSBB301W	PSBBN301W	PS530P5WR	PS530C5WR	PS530R5WL	PS530C5WL

*Application specific, reference Page K-2.



PS330C4WR

PS330P4WR