



Low Profile.
High Performance.



The versatile, low-profile LED garage luminaire



GARAGE LUMINAIRES

- Low-Profile Design Ideal for Parking Garages
- 26W Replaces up to 100W MH Luminaires
52W Replaces 175W MH Luminaires
78W Replaces 250W MH Luminaires
- 100,000-Hour LED Lifespan
- Up to 25% Reduction in Fixture Count
- Hanging Plate with Hooks Included for Easy Wiring
- 5-Year Warranty

IP65
RATING



Specifications

UL Listing: Ceiling Mount - Suitable for wet locations with covered ceiling.
Pendant Mount - Suitable for wet locations.

LEDs: Multi-chip, high-output, long-life LEDs

Lifespan: 100,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

Drivers: Constant Current, 720mA, Class 2 with 6 kV surge protection, 100 -277VAC, 50/60 Hz

Nominal Watts	26W	52W	78W
Input Watts @ 120VAC	30	59	88
Output Lumens*	2812	4975	7053
Lumens per Watt*	94.0	84.5	79.9
Color Accuracy (CRI)*	69	68	68
Correlated Color Temp. (Nominal CCT)*	5000K	5000K	5000K

Cold Weather Starting: Minimum starting temperature is -40°C (-40°F)

Ambient Temperature: Suitable for use in 40°C (104°F) ambient temperatures

Thermal Management: Superior heat sinking with integrated Air-Flow fins

Housing: Precision die-cast aluminum housing and door frame

Mounting: Easy hanging plate with hooks for ceiling mount

Lens: Prismatic polycarbonate lens

Reflector: Semi-specular anodized aluminum with ultra-white, 97% reflective optics

Gaskets: High-temperature silicone

Finish: Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contain no VOC or toxic heavy metals.

Color Stability: RAB LED performance exceeds industry standards for chromatic stability

Color Uniformity: RAB's range of CCT (Correlated Color Temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2011.

Green Technology: Mercury and UV free, and RoHS compliant. Polyester powder coat finish formulated without the use of VOC or toxic heavy metals.

IESNA LM-79 & LM-80 Testing: RAB LED luminaires have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80, and have received the Department of Energy "Lighting Facts" label.

California Title 24: GLED26/D10 with 10V dimming driver complies with 2013 California Title 24 building and electrical codes as a non-residential indoor fixture when used with the RAB Stealth Dimmer. Use catalog code STLDIM10 to order a Stealth Dimmer module.

*Values shown for cool temperature. Visit rabweb.com for neutral and warm.


Photometrics

GLED26/GPLED26

(Cool Light - 5000K)

@ 10' Mounting Ht.

Photometric Report #ITL81203




GLED52/GPLED52

(Cool Light - 5000K)

@ 10' Mounting Ht.

Photometric Report #ITL79959




GLED78/GPLED78

(Cool Light - 5000K)

@ 10' Mounting Ht.


Photometric Report #ITL79965




Multiples of Mounting Height • Values Shown in Footcandles

Dimensions & Weight

Ceiling Mount: 18.2 lbs.



Pendant Mount (Pendant by others): 18.2 lbs.



Ordering Information

Product Family

GLED Ceiling Mount
GPLED Pendant Mount

Wattage

26 26W
52 52W
78 78W

Color Temperature

Blank 5000K
N 4000K
Y 3000K

Finish

Blank Bronze
W White

Options

/D10 10V Dimming Driver

