





Gangable Masonry Boxes



GW-135-G



GW-235-G

Cat. No.	Lgth. In.	Cu. In. Cap.	Eccentric Knockouts ½" & ¾"			Std. Ctn.
			Ea. Side	Ea. End	Bottom	
2½" deep—3¾" high—with eccentric conduit KOs						
GW-125-G*	1⅞	15.0	2	2	2	20
GW-225-G*	3¾	31.6	2	4	4	10
GW-325-G*	5⅞	47.4	2	6	6	5
GW-425-G	7⅞	64.0	2	8	8	5
GW-525-G	9⅞	79.0	2	10	10	5
GW-625-G*	11	94.8	2	12	12	1

3½" deep—3¾" high—with eccentric conduit KOs

GW-135-G*	1⅞	22.0	4	2	2	20
GW-235-G*	3¾	46.9	4	4	4	10
GW-335-G	5⅞	71.0	4	6	6	10
GW-435-G*†	7⅞	93.5	4	8	8	5
GW-535-G†	9⅞	111.7	4	10	10	5
GW-635-G†	11	134.0	4	12	12	1

*Per N.E.C. suitable for use without a bonding jumper in circuits above or below 250 volts.

† 4, 5, and 6 gang supplied with partitions.



Masonry Box Partitions



PGW-25



PGW-35

Cat. No.	Description	Std. Ctn.
PGW-25-G	Nonmetallic partition for 2½" deep steel tile wall boxes	25
PGW-35-G	Nonmetallic partition for 3½" deep steel tile wall boxes	25

Table 370-16(a). Metal Boxes

Box Dimension, (in.) Trade Size or Type	Min. Cu. In. Cap.	Maximum Number of Conductors						
		No. 18	No. 16	No. 14	No. 12	No. 10	No. 8	No. 6
4 x 1½ Round or Octagonal	12.5	8	7	6	5	5	4	2
4 x 1½ Round or Octagonal	15.5	10	8	7	6	6	5	3
4 x 2½ Round or Octagonal	21.5	14	12	10	9	8	7	4
4 x 1½ Square	18.0	12	10	9	8	7	6	3
4 x 1½ Square	21.0	14	12	10	9	8	7	4
4 x 2½ Square	30.3	20	17	15	13	12	10	6
4½ x 1½ Square	25.5	17	14	12	11	10	8	5
4½ x 1½ Square	29.5	19	16	14	13	11	9	5
4½ x 2½ Square	42.0	28	24	21	18	16	14	8
3 x 2 x 1½ Device	7.5	5	4	3	3	3	2	1
3 x 2 x 2 Device	10.0	6	5	5	4	4	3	2
3 x 2 x 2½ Device	10.5	7	6	5	4	4	3	2
3 x 2 x 2½ Device	12.5	8	7	6	5	5	4	2
3 x 2 x 2½ Device	14.0	9	8	7	6	5	4	2
3 x 2 x 3½ Device	18.0	12	10	9	8	7	6	3
4 x 2½ x 1½ Device	10.3	6	5	5	4	4	3	2
4 x 2½ x 1½ Device	13.0	8	7	6	5	5	4	2
4 x 2½ x 2½ Device	14.5	9	8	7	6	5	4	2
3½ x 2 x 2½ Masonry Box/Gang	14.0	9	8	7	6	5	4	2
3½ x 2 x 3½ Masonry Box/Gang	21.0	14	12	10	9	8	7	4
FS—Minimum Internal Depth 1½ Single Cover/Gang	13.5	9	7	6	6	5	4	2
FD—Minimum Internal Depth 2½ Single Cover/Gang	18.0	12	10	9	8	7	6	3
FS—Minimum Internal Depth 1½ Multiple Cover/Gang	18.0	12	10	9	8	7	6	3
FD—Minimum Internal Depth 2½ Multiple Cover/Gang	24.0	16	13	12	10	9	8	4

Underwriters Laboratories Inc. File Number: E2969 (U.L. 514A)

Canadian Standards Association File Number: LR 12798

Federal Manufacture Number: 56501 (Cage Code)

Products Designed To Meet Federal Specification Number: W-J-800

Verification of file numbers and compliance with federal specifications for individual items available upon request.

Box and Cover Material and Plating Specification: .062" minimum thickness, Hot Rolled, Pre galvanized steel, minimum spangle.

ASTM G-90-U, AISI C-1008

Bracket Material: All brackets except MS style; 16 gauge (.060") Hot Rolled, Pre galvanized Steel AISI C-1008, G-90-U. MS Style bracket; 20 gauge (.036") Cold Rolled Spring Steel AISI C-1055, Heat Treated to R. 35 Zinc Plated .0005 thick.

Patent Number 5,031,789 - Standoff for Outlet Boxes - SS-1 Patent Number 5,004,199 - Metal Stud Bracket - Type MS - Eccentric Knockouts - Type Eko