

D-Series LED Flood, Size 3

Flood Luminaire

Advanced Engineering. Extensive Configurability.

An array of optical distributions and lumen packages allow the D-Series LED Flood Luminaire, Size 3, to be used virtually anywhere. Its precision optics ensure light is placed exactly where it is needed, and its controls compatibility means it can generate even greater savings than traditional options or other comparable LED floodlights.

Key Features:

- Energy savings of 70% vs. comparable metal halide luminaires; saves up to \$158 per luminaire, per year over 400W metal halide
- 20+ years expected service life means maintenance costs are reduced (with lumen maintenance of L96/100,000 hours)
- Proprietary precision optics deliver low field-to-beam ratios and greater on-target illumination
- Control options from Acuity Controls, ranging from standalone photocell and dimming to ROAM® wireless monitoring and control



Quick Facts:

- 250-400W MH replacement
- Performance packages up to 18,992 lumens
- Input watts from 129-183W
- Multiple optics, covering narrow spot to wide flood distribution
- Available in 3000K, 4000K & 5000K CCT
- 10kV surge protection
- Weight: 21 lbs; EPA: 1.4 ft²

D-Series LED Flood Luminaire, Size 3

Ordering Information

EXAMPLE: DSXF3 LED 6 P2 40K FL MVOLT THK DDBXD

DSXF3 LED

Series	Light Engines	Performance Package	Color Temperature	Distribution	Voltage	Mounting	Options	Finish <i>(required)</i>
DSXF3 LED	6 Six COB engines	P1 P2	30K 3000 K	NSP Narrow spot	MVOLT ¹	Shipped included THK Knuckle with 3/4" NPT threaded pipe YKC62 Yoke with 16-3 SO cord IS Integral slipfitter (fits 2-3/8" O.D. tenon) Shipped separately ² FTS CG6 Tenon slipfitter (fits 2-3/8" to 2-7/8" O.D. tenon. YKC62 required)	Shipped installed PER NEMA twist-lock receptacle only (no controls) ³ PER5 Five-wire receptacle only (no controls) ^{3,4} DMG 0-10V dimming driver (no controls) SF Single fuse (120, 277, 347V) ⁵ DF Double fuse (208, 240, 480V) ⁵ WTB Utility terminal block PNMTDD3 Part night, dim till dawn ⁶ PNMT5D3 Part night, dim 5 hrs. ⁶ NMT6D3 Part night, dim 6 hrs. ⁶ PNMT7D3 Part night, dim 7 hrs. ⁶ BL30 Bi-level switched dimming, 30% ⁷ BL50 Bi-level switched dimming, 50% ⁷ Shipped separately ² UBV Upper/bottom visor (universal) FV Full visor VG Vandal guard WG Wire guard DSHORT Shorting cap ⁸ SBK U DLL127F Photocell-SSL twist-lock (120-277V) ⁸ DLL347F 1.5 Photocell-SSL twist-lock (347V) ⁸ DLL480F 1.5 Photocell-SSL twist-lock (480V) ⁸	DDBXD Dark bronze DBLXD Black DNAXD Natural aluminum DWHXD White
			40K 4000 K	MSP Medium spot	120 ¹			
			50K 5000 K	MFL Medium flood	208 ¹			
				FL Flood	240 ¹			
				WFL Wide flood	277 ¹			
				WFR Wide flood rectangular	347			
				HMF Horizontal medium flood	480			

Accessories Ordered and shipped separately

FTS CG6 DDBXD U	Slipfitter for 2-3/8" to 2-7/8" OD tenons; mates with yoke mount (specify finish)
FRWB DDBXD U	Radius wall bracket, 2-3/8" OD tenon (specify finish)
FSPB DDBXD U	Steel square pole bracket, 2-3/8" OD tenon (specify finish)
DSXF3UBV DDBXD U	Upper/bottom visor accessory (specify finish)
DSXF3FV DDBXD U	Full visor accessory (specify finish)
DSXF3VG U	Vandal guard accessory
DSXF3WG U	Wire guard accessory

For more mounting options, visit our Floodlighting Accessories pages.
For more control options, visit DTL and ROAM online.

Notes

- MVOLT driver operates on any line voltage from 120-277V. Specify 120, 208, 240 or 277 options only when ordering with fusing (SF, DF options).
- Also available as separate accessories; see Accessories information at left.
- For units with a photocontrol receptacle, the mounting must be restricted to $\pm 45^\circ$ from horizontal aim per ANSI C136.10-2010.
- Specifies a ROAM® enabled luminaire with 0-10V dimming capability; PER5 option required. Not available with 347 or 480V. Additional hardware and services required for ROAM® deployment; must be purchased separately. Call 1-800-442-6745 or email: sales@roamservices.net.
- Single fuse (SF) requires 120, 277 or 347 voltage option. Double fuse (DF) requires 208, 240 or 480 voltage option.
- Dimming driver standard. MVOLT only. Not available with 347V, 480V, PER5, BL30 or BL50.
- Requires an additional switched circuit. Dimming driver standard. MVOLT only. Not available with 347V, 480V, or PER5 as a separate line item.
- Requires luminaire to be specified with PER option. Ordered and shipped as a separate line item.



DSXF1



DSXF2



DSXF3

Visit www.lithonialighting.com for more information