SHC Flexible Fixture Hangers

Outlet Box Mounted Series

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

NEC/CEC:

Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of HID, fluorescent and incandescent lighting fixtures.
- SHC fixture hanger covers for mounting to 3-1/4" and 4" octagonal boxes and 4" square boxes.

Features

- · Protect fixture against wind and vibration damage.
- Cushion type for added protection where lighting fixtures are subjected to vibration.
- Ball type swivel joint permits 20° swing from vertical.
- Support fixtures with a maximum weight of 22.7 kg (50 lbs).

Standard Materials

· Steel and malleable iron

Standard Finishes

 Malleable iron and steel parts: zinc electroplate and clear chromate

NEC/CEC Certifications and Compliances

CSA Certified: 065180UL Listed: E2527UL Standard: 514A





8438R

8458R

Illustrated Features



Ball Type Swivel Fixture Hanger Covers shown with octagonal and with square stamped steel outlet boxes.

		Fixture Stem Size (Inches)	Length A mm (in)	Support Weight kg (lbs)	Catalog Number
SHC Ball Type Swivel Hanger Cover	s - Permit 20° swing from	vertical			
	For 3-1/4" and 4" Oct	agonal Boxes			
A APPLETO		1/2	44.5 (1.75)	22.5 (50)	8438R
		3/4	50.8 (2.00)	22.5 (50)	8436R
	For 4" Square Boxes				
A APPLETON		1/2	44.5 (1.75)	22.5 (50)	8458R
		3/4	50.8 (2.00)	22.5 (50)	8456R

