

DURALITE™

Surprisingly Light.
Exceptionally Strong.





PROTECTING vital infrastructure.

ENGINEERED TO WITHSTAND HEAVY LOADS, Duralite™ intelligently blends composite materials to provide durable, accessible security for our necessary infrastructure. To bring you innovative products like this, Oldcastle Infrastructure prioritizes rigorous product testing and material science. The result—a lightweight cover and body design that allows for safer installation conditions, plus a uniquely strong configuration that delivers unexpected Tier 15 and Tier 22 performance.

At Oldcastle Infrastructure, the wants and needs of our customers guide the products we create. Our commitment to innovation demands that we do more.



LIGHTWEIGHT DESIGN
Easier handling and installation, with multiple handholes for single-person lifts.



HIGH-STRENGTH
Durable, single-piece body engineered to resist bowing during installation and withstand heavy loads.




CHIP AND CRACK RESISTANT
Unique material blend resists chipping and cracking, unlike polymer concrete.



FIRE RESISTANT
Material blend is fire resistant, following the ASTM D635 standards.



EASILY MODIFIABLE DURALITE
Easily modified in the field with 18V power tools.



Actual load rating is determined by the box and cover combinations.

Dimensions may vary slightly.

 Available soon

MODEL	SIZE (LxW)	SHAPE	DEPTHS	
1015	10" x 15"	Rectangle	12", 18"	
1118	11" x 18"		12", 18"	
1212	12" x 12"	Square	12", 18"	
1324	13" x 24"	Rectangle	12", 18"	24"
1730	17" x 30"		12", 18"	24"
2436	24" x 36"		24"	18", 36"
3048	30" x 48"		18", 24", 36"	

MATERIAL	Polyolefin Blend
WALL TYPE	Straight
PERFORMANCE	Tier 15, Tier 22
RATING	Medium Duty, Heavy Duty

Oldcastle Polymer and Duralite covers are available for this product line.



www.oldcastleinfrastructure.com

(888) 965-3227