

FLAT HEAD SPLIT DRIVE ANCHOR



- Can be used in concrete, hard masonry and stone
- Load can be applied immediately
- High grade steel with a memory
- One piece, pre-expanded anchor
- Exact hole depth not required to set anchor
- Fast, permanent installation

Safety glasses should be worn for any driving applications. See Pages 220-222



STOCK NO.	UPC NO.	JAR UPC NO.	SIZE	MASONRY DRILL SIZE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
JFSD141	81594	81594	1/4 x 1 1/2	1/4 x 4	1.22	50	54.56/c
JFSD142	81596	81596	1/4 x 2	1/4 x 4	1.58	50	62.10/c
JFSD1421	81598	81598	1/4 x 2 1/2	1/4 x 4	1.87	50	68.20/c
JFSD143	81600	81600	1/4 x 3	1/4 x 4	2.27	50	74.26/c
JFSD1431	81602	81602	1/4 x 3 1/2	1/4 x 6	1.35	25	81.80/c
JFSD144	81604	81604	1/4 x 4	1/4 x 6	1.50	25	89.40/c

SLEEVE TYPE ANCHOR

STEEL ZINC CHROMATE



* = acorn nuts



STOCK NO.	UPC NO.	DIAMETER & LENGTH	FASTENS MATERIAL UP TO	DEPTH IN LENGTH	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
STEEL ZINC CHROMATE – HEX (Acorn)							
J2505	77405	1/4 x 5/8	1 1/4	1	1.57	100	41.25/c NEW
J2513*	80883	1/4 x 1 3/8	3/8	1	2.32	100	41.55/c
J2522*	80884	1/4 x 2 1/4	1 1/4	1	3.14	100	58.98/c
J3114	80885	5/16 x 1 1/2	1/2	1	3.54	100	69.08/c
J3124	80886	5/16 x 2 1/2	1 1/2	1	5.24	100	90.50/c
J3717	80887	3/8 x 1 7/8	5/8	1 1/4	3.58	50	92.36/c
J3730	80888	3/8 x 3	1 3/4	1 1/4	5.15	50	119.20/c
J3732	77310	3/8 x 4	1 3/4	1 1/4	6.71	50	119.20/c NEW
J5022	80889	1/2 x 2 1/4	3/4	1 1/2	3.24	25	130.72/c
J5026	80890	1/2 x 3	1 1/4	1 1/2	4.07	25	172.72/c
J5040	81131	1/2 x 4	2 1/2	1 1/2	5.02	25	285.00/c
J5060	81135	1/2 x 6	4 1/2	1 1/2	7.15	25	401.40/c
J6222	80891	5/8 x 2 1/4	1/4	2	6.60	25	251.00/c
J6242	81345	5/8 x 4 1/4	2 1/4	2	4.14	10	353.80/c
J6256	81350	5/8 x 6	3 3/4	2	5.30	10	476.00/c
J7524	80892	3/4 x 2 1/2	1/2	2	4.07	10	377.00/c
J7542	81360	3/4 x 4 1/4	1 3/4	2 1/2	3.23	5	582.00/c
J7562	81365	3/4 x 6 1/4	3 3/4	2 1/2	4.75	5	698.60/c

LARGER DIAMETERS & LENGTHS AVAILABLE BY SPECIAL REQUEST.

CONTINUED ON NEXT PAGE