




**Straight Blade Devices**  
**15 and 20 Ampere, 125 Volts**  
*2 Pole, 3 Wire Grounding*  
**Insulgrip® Flanged Inlets and Receptacles**




**HBL5278C**




**HBL61CM64**



**HBL5279C**



**HBL5256**



**HBL61CM65**



**15A 125V**  
**NEMA 5-15P**  
 UL CSA



**20A 125V**  
**NEMA 5-20P**  
 UL CSA

**Flanged Inlets**

| Description   | Catalog Numbers    |                 |
|---|--------------------|-----------------|
| Nylon casing, back wired.   | <b>HBL5278C</b>    | <b>HBL5378C</b> |
| Weatherproof, gray, with lift cover and multiple drive screws.  | <b>HBL61CM64</b>   |                 |
| Weatherproof, black, with lift cover and boot, multiple drive screws.   | <b>HBL61CM64BK</b> | -               |
| Stainless steel flange, phenolic body, miniature style, for molded on connectors only, multiple drive screws. | <b>HBL5240*</b>    | -               |

*Notes: \*Specially designed to accept "molded-on" connector bodies. Catalog number HBL5240 will not accept re-wireable size connector bodies listed in this catalog or molded connectors having a "rejection obstruction" as required by Underwriters Laboratories Inc. standard #817 cord sets and power supply cords" effective 7/1/81. See page A-45 for accessories.*



**15A 125V**  
**NEMA 5-15R**  
 UL CSA  
 0.5 HP



**20A 125V**  
**NEMA 5-20R**  
 UL CSA  
 1 HP

**Flanged Receptacles**

| Description  | Catalog Numbers |                   |
|--|-----------------|-------------------|
| Nylon casing, back wired.  | <b>HBL5279C</b> | <b>HBL5379C</b>   |
| Stainless steel flange, phenolic body, covered terminals, multiple drive screws. | <b>HBL5279</b>  | -                 |
| Stainless steel flange, brown phenolic (mounting screws packed separately).      | <b>HBL5256</b>  | -                 |
| Weatherproof, gray nylon, with lift cover and boot, multiple drive screws.       | -               | <b>HBL61CM65*</b> |

*Notes: \*Not CSA Certified. See page A-45 for accessories.*