


Commercial Grade

Commercial Spec Grade Receptacles

Leviton offers a large selection of 15 and 20 Amp Commercial Spec Grade receptacles, including Decora® devices available in a wide variety of colors, wiring options and other features. Leviton's Commercial Receptacles are manufactured to withstand the demands of commercial and institutional applications. These commercial receptacles provide long-lasting service life and are a cost-saving alternative to the industrial devices.

Features and Benefits

- Manufactured to withstand the demands of commercial and institutional applications
- Heavy-Duty Brass Power contacts for maximum conductivity and plug retention
- Shallow design for maximum wiring room in box
- UL Listed 498 (UL File #E-13399)
- CSA Certified where applicable (CSA File #LR-406)
- NOM Certified (#057)
- Meets NEMA WD-1 & 6, and ANSI standards
- Backed by a Limited Ten-Year Warranty
- All commercial side-wired receptacles have #8-32 triple combination head terminal screws
- All commercial back and side-wired receptacles have #10-32 triple combination head terminal screws



Related Products

Leviton offers a complete line of Commercial Grade SmartLockPro® GFCI receptacles.

See page 153 for more information.







Decora Plus™ Receptacles


Specifications and Features

- Back Wire and Side Wire terminal options
- Heavy-gauge zinc-plated steel locked-in wraparound strap
- Back wire terminals accept up to No. 10 copper or copper-clad wire, solid or stranded
- Brass staked on self-grounding clip
- Heavy-duty triple-wipe brass contacts for long service life
- Impact-resistant thermoplastic construction


DECORA PLUS

Heavy-Duty Back and Side Wired, Self-Grounding

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Duplex, Tamper Resistant	White	TDR15-W		TDR20-W	
	Ivory	TDR15-I		TDR20-I	
	Light Almond	TDR15-T		TDR20-T	
	Grey	TDR15-GY		TDR20-GY	
	Black	TDR15-E		TDR20-E	
	Brown	TDR15		TDR20	
Duplex	White	16252-W	16662-W	16352-W	16462-W
	Ivory	16252-I	16662-I	16352-I	16462-I
	Light Almond	16252-T	—	16352-T	—
	Grey	16252-GY	—	16352-GY	—
	Black	16252-E	—	16352-E	—
	Brown	16252	—	16352	—
Single	White	16251-W	16651-W	16351-W	16451-W
	Ivory	16251-I	16651-I	16351-I	16451-I
	Brown	16251	—	16351	—
NEMA					
		5-15R	6-15R		
Rating		15A-125V/15A-250V			
Duplex,	White	16292-W			
Dual Voltage	Ivory	16292-I			



Commercial Grade



DECORA PLUS™ SPEC GRADE RECEPTACLES

Side Wired, Self-Grounding

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Duplex, Tamper Resistant	White	DR15S-W	—	—	—
	Ivory	DR15S-I	—	—	—
	Light Almond	DR15S-T	—	—	—
	Grey	DR15S-GY	—	—	—
	Black	DR15S-E	—	—	—
	Brown	DR15S	—	—	—
Duplex	White	16242-W	—	16342-W	—
	Ivory	16242-I	—	16342-I	—
	Grey	—	—	16342-GY	—
	Black	16242-E	—	16342-E	—
	Brown	16242	—	16342	—
Single	White	16241-W	16641-W	16341-W	16441-W
	Ivory	16241-I	16641-I	16341-I	16441-I
	Light Almond	—	—	16341-T	16441-R
	Grey	—	—	16341-GY	—
	Black	—	—	16341-E	—
	Brown	—	—	16341	—

† Self-grounding when installed in a properly grounded metal wallbox.

TESTING AND CODE COMPLIANCE

Meets all NEMA WD 6, UL 498 and ANSI C-73 requirements

- UL Listed (File #E-13399)
- CSA Certified (File #152105)
- NOM Certified (#057)

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2
Operating Temperature: -40°C to 60°C

MECHANICAL

Terminal I.D.: Brass-Hot, White-Neutral, Green-Grounding
Terminal Accom.: #14-#10 AWG
Product I.D.: Ratings are permanently stamped on device

ELECTRICAL

Dielectric Voltage: Withstands 2000V for UL 498

Current Interr.: Full rated current

Temp. Rise: Max 30°C at full rated current after 250 cycles overload at 200% of rated current

HORSEPOWER

15A - 125V — 1½
15A - 250V — 1½
20A - 125V — 1
20A - 250V — 2