

The Improved HandiMark® Portable Label Maker

*Fast.
Easy.
Powerful.*



Featuring Increased Print Speed and More!

HandiMark® Version 3.0 Printer Gives You The Power To Create Custom Labels Anytime, Anywhere.

That Means Productivity Improvements & Cost Savings

The HandiMark® Portable Label Maker from Brady lets you create high visibility labels throughout your facility. Ideal for:

- Safety Department
- Mechanical Maintenance
- Plant Engineering
- Production & Operations
- Warehouse & Storeroom
- Fire/Emergency Response
- Laboratory
- Field Service Crews

The HandiMark® Portable Printer runs on a rechargeable battery or AC power supply giving you the flexibility and convenience of taking the unit wherever labeling is needed.

Version 3.0 Offers These Enhanced Features:

- **Faster Printing Speeds**
Print labels 30% faster than before
- **Auto Recall**
Remembers the last label printed
- **Sleep Mode**
Power saving sleep mode increases battery life
- **Clearer Display**
Higher screen resolution for optimal use





Limitless Applications Mean Real Value


The HandiMark® Portable Printer can customize labels with various colors, type styles and an extensive library of symbols and pictograms with multi-language capability. Create your own bar codes and store frequently used labels for printing without re-entering.

More Features:

113 Built-in Symbols



EXPAND text
Condense text
Bold text
Underline text
Italics text



Text Sizes .08" to

1.7"
(2mm to 43mm)



1/2", 1" and 2" Tape Widths



5-year outdoor grade vinyl
14 colors
7 ribbon colors

12 Resident Operating Languages



English
Spanish
French
German
Italian
Finnish
Dutch
Norwegian
Swedish
Danish
Portuguese
Hungarian

Pipe Marker Application Built-in



113 built-in symbols

Speciality Tapes



Reflective
Repositionable
Tamper-resistant

Alpha-numeric Sequencing



Bar codes
Batch labels

Repeat Print



10,000 byte memory
Download to your PC

HandiMark® Portable Label Maker Examples

GAS TO #2 DR

This Pipe Marker costs under \$2; custom labels save time and money

←←←←← WATER TO MIXER 14 ←←←←←

This Pipe Marker costs only \$1.26 with the Brady HandiMark®. Durable Brady materials are suitable for the most demanding applications

BIN A-60

BIN A-61

BIN A-62

Quick auto-sequencing feature saves time

**DANGEROUS
PINCH**



**FIRE EXTINGUISHER
No. 22A**

Various pictograms for clear identification



All the sample labels on this page are shown actual size.

PRO
UNIVER

I.D. No.

Customized As

RYER

AIR COMPRESSOR #1
ACP-1
DISCONNECT LOCATION: Panel 237, Breaker #13

SWITCH 2Q-041
MIXER 17

This label costs only \$0.20; and accurately promotes facility safety

PANEL 237
ACP-1 Main Disconnect

Identify all components in a system

BREAKER #13
ACP-1 Disconnect

 **480 VOLT 30 60Amp**

PROPERTY OF
UNIVERSITY HOSPITAL
100293

PROPERTY OF
UNIVERSITY HOSPITAL


100293

Asset I.D. Labels

Reclaim Pump No.12A
LOCKOUT PROCEDURE

1. Notify all affected personnel
2. Bring machine to "Zero Energy State" by de-energizing in this order: disc switch, steam valve, block swing arm, hydr. line
3. Test and verify zero energy state
4. Apply locks and tags
5. Perform scheduled maintenance
6. Bring equipment back on line in reverse order of shutdown sequence above
7. Notify all affected personnel

Made using MarkWare™
Facility Identification
Software



Get Your HandiMark® Portable Label Maker TODAY



AC Power Supply - 42006



Quick Charger - 42124

HandiMark® Portable Label Maker

Includes everything you see at right:

- HandiMark® Portable Label Maker
- Rechargeable battery
- 1 sample roll of 2" tape
- Cleaning strip
- Hard carrying case
- Battery charger
- Black ribbon
- Tutorial and symbols reference chart.

Description	Catalog Number
HandiMark® Portable Label Maker	42001

HandiMark® Combo Packages

Description	Catalog Number
HandiMark®, MarkWare™, Cable Kit	20709
HandiMark®, LOTO toolbox, Lockout Pro Software	80159
HandiMark®, GlobalMark™ MonoColor & ValuePlus Pkg.	89235
HandiMark®, GlobalMark™ MultiColor & ValuePlus Pkg.	89238
HandiMark®, GlobalMark™ Color & Cut & ValuePlus Pkg.	89241
HandiMark®, PowerMark™ & ValuePlus Pkg.	30652
HandiMark®, GlobalMark™ MonoColor, PowerMark® & ValuePlus Combo Pkg.	89237
HandiMark®, GlobalMark™ MultiColor, PowerMark® & ValuePlus Combo Pkg.	89240
HandiMark®, GlobalMark™ Color & Cut, PowerMark® & ValuePlus Combo Pkg.	89243
HandiMark® w/ AC Power & Quick Charger	102860

All PowerMark® combo packages include the BLS1200 & serial cable

HandiMark® Accessories

Description	Catalog Number
Spare Battery (Std. Battery)	42008
AC Power Supply	42006
Standard Battery Charger	42007
Quick Charger	42124
Super Charge*	42073
Mega Charge**	42072
Alcohol Cleaning Strips (5 per pkg.)	42009
Soft Case	49199
Spare Hard Carrying Case	42010
Protective Dust Cover for Printer	42005
PC Connecting Cable	42004
USB to 8 DB9 Serial Adapter Cable	81701

*Contents: Quick charger and spare battery.

**Contents: Quick charger, spare battery and AC Power Supply.



Industrial Grade Ribbons

Super-tough, smear-proof ribbons produce printed text that lasts for years outdoors and in industrial areas. One size fits all tape widths. 75 ft. (23m) per cartridge.

Description	Catalog Number						
Size	Black	White	Red	Blue	Green	Magenta	Yellow
2" x 75' (51mm x 23m)	42011	42012	42013	42014	42015	42016	42123

Your HandiMark® Printer Ships “Ready-to-Use” with easy-loading supplies and long-lasting materials



Unlike other products designed for office use, the HandiMark® system prints on Brady's high-quality, industrial strength tapes and adhesives for maximum durability.



Indoor/Outdoor Grade Vinyl Tape (B-580)

Labels adhere well to pipes, walls, equipment, doors — most clean, dry surfaces. Conforms well to irregular, curved or rough surfaces. It even stands up to grease, oil and most industrial chemicals. Five-year average outdoor durability in temperatures from 180°F to -40°F (82°C to -40°C). Tape can be applied as low as 0°F (-18°C). 50 feet (15.2m) per roll.

Description	Catalog Number													
	White	Clear	Yellow	Green	Red	Blue	Light Blue	Orange	Black	Tan (sand)	Grey	Brown	Gold	Violet
.5" x 50' (13mm x 15.2m)	42018	42076	42022	42026	42030	42034	—	42038	42042	—	42046	42050	42054	42058
1" x 50' (25mm x 15.2m)	42019	42077	42023	42027	42031	42035	42133	42039	42043	42135	42047	42051	42055	42059
2" x 50' (51mm x 15.2m)	42021	42079	42025	42029	42033	42037	42134	42041	42045	42136	42049	42053	42057	42061

Economy Polypropylene Tape (B-529)

This economical tape is ideal for use indoors on smooth, flat surfaces. 50 feet (15.2m) per roll.



Size	White
.5" x 50' (13mm x 15.2m)	42068
1" x 50' (25mm x 15.2m)	42069
2" x 50' (51mm x 15.2m)	42071

Repositionable Vinyl Tape (B-581)

Durable vinyl tape has a special adhesive that allows you to easily remove the label and re-apply again and again. This is the label of choice for marking where frequent repositioning is required, such as storage shelves and racks in warehouse facilities. 50 feet (15.2m) per roll.



Size	Yellow	White
.5" x 50' (13mm x 15.2m)	42103	42100
1" x 50' (25mm x 15.2m)	42104	42101
2" x 50' (51mm x 15.2m)	42105	42102

Tamper Resistant Tape (B-530)

This tape destructs into tiny fragments when tampered with making removal very tedious and difficult. 50 feet (15.2m) per roll.



Size	White
.5" x 50' (13mm x 15.2m)	42137
1" x 50' (25mm x 15.2m)	42138
2" x 50' (51mm x 15.2m)	42139



Reflective Tape (B-584)

Indoor/outdoor use. Reflective capabilities are ideal for reading labels in low light conditions with a flashlight or from a vehicle. Applications include utility I.D., door I.D., and labeling roof-top equipment. 33 feet (10m) per roll.

Size	Reflective White	Reflective Orange	Reflective Yellow
1" x 33' (25mm x 10m)	42062	42066	42064
2" x 33' (51mm x 10m)	42063	42067	42065

Need to Add Even More Power to Your Printer?

SurfOnSigns™ Signs and Labels Database, ChemLabel™ Hazardous Material Labeling Software and Markware™ Facility Identification Software offers a choice of features and print technologies for your identification needs.

- Markware™ premium software allows you to design and customize signs and labels
- ChemLabel™ enables you to create labels for hazardous material markings
- SurfOnSigns™ allows for quick and easy sign, label and pipe marker creation



Need to Mark Wire & Cable?

The TLS2200® Thermal Labeling Printers, IDXPERT™ Handheld Labeler and the ID Pal™ Labeling Tool are your solution!

- Portable... goes where you go
- Built-in wire and cable marking applications
- Wide range of continuous and die cut materials for voice/data, wire marking, and general identification

Need Larger Signs & Labels?

The GlobalMark® Industrial Label Maker, MiniMark™ Industrial Label Printer and PowerMark® Sign and Label Maker printers are your high performance solution!

- Create multi-color output up to 10 inches wide
- Large selection of specialty materials including glow-in-the-dark, tagstock, and magnetic



Brady Worldwide, Inc.
6555 W. Good Hope Road
Milwaukee, WI 53223
1-888-272-3946
www.bradyid.com

Brady Canada
355 Apple Creek Blvd.
Markham, ON L3R 9X7
1-800-263-6179
www.bradycanada.com

