




# HALO<sup>™</sup> SeleCCTable Family



# RL SeleCCTable Series



RL4069S1EWH 4" LED Retrofit Baffle-Trim, 600 lumen



RL4099S1EWH 4" LED Retrofit Baffle-Trim, 900 lumen



**RL56069S1EWH / RL56099S1EWH** 5"/6" LED Retrofit Baffle-Trim, 600 lumen / 900 lumen



**RL56129S1EWH** 5"/ 6" LED Retrofit Baffle-Trim, 1200 lumen

# RA SeleCCTable Series



RA4069S1EWH 4" LED Adjustable Gimbal



RA56069S1EWH 5"/6" LED Adjustable Gimbal



2700K • 3000K • 3500K 4000K • 5000K

The HALO Sele**CCT**able family includes the RL LED recessed downlight and RA adjustable gimbal. The Sele**CCT**able technology puts flexibility at your fingertips. By using the switch located on the back of the fixture, the user can choose from a range of five color temperatures 2700K - 5000K.



# **RL4 SeleCCTable Series**



- 600 Series: up to 621 lumens<sup>1</sup>
- 900 Series: up to 1006 lumens<sup>1</sup>
- Use to replace 60W PAR16, 50W PAR20 or 40W R20 lamp
- 2700K, 3000K, 3500K, 4000K, 5000K CCT<sup>2</sup> all in one
- 90 CRI
- 600 Series: 7.6W, 120V900 Series: 11.7W, 120V
- L70 @ 70.000 hrs
- HALO matte white finish
- Push-N-Twist universal installation clips pre-installed

- Compatible with most 4" recessed housings
- Dimmable to 5% with select dimmers
- Damp and wet location listed (shower rated)
- Rated for IC, ICAT and may be used in Non-IC housings
- AIR-TITE™ certified per ASTM-E283
- Diffusing, regressed lens
- · Five-year limited warranty
  - Lumens per selected CCT
     CCT Correlated Color Temperature

### RL4 Designer Trims (Order Separately)



### RL4TRMWHB White Baffle (Paintable)

RL4TRMWH White (Paintable)



# Tuscan Bronze Baffle

RL4TRMTBZ Tuscan Bronze



### RL4TRMSNB

Satin Nickel Baffle

### **RL4TRMSN**

Satin Nickel



<sup>&</sup>lt;sup>a</sup> Savings are over the life of the HALO RL4 luminaire. (600 series) Energy savings: \$315

Savings based on \$0.128 per kilowatt hour, average six hours use per day, 70,000 hours of lamp usage, and 60W PAR16 lamp lumen equivalent.

Replacement lamp savings: \$88



### Ordering Information

Sample Number: RL4069S1EWH Order HALO housing separately. RL4 - 4" LED Retrofit Baffle - Trim

RL4069S1EWH= 600 lumen, 90 CRI, 2700K - 5000K CCT

RL4099S1EWH= 900 lumen, 90 CRI, 2700K - 5000K CCT

# LED Housings (Order Separately)

See Housing Compatibility section

### Accessories (Order Separately)

Baffle

RL4TRMSNB=Satin Nickel Trim Ring RL4TRMTBZB=Tuscan Bronze Trim Ring RL4TRMWHB=White Paintable Trim Ring

RL4TRMSN=Satin Nickel Trim Ring RL4TRMTBZ=Tuscan Bronze Trim Ring RL4TRMWH=White Paintable Trim Ring



HE26LED=Replacement screw base adapter (one included with unit)

RL4 Energy Data	600 Series	900 Series
Max. Lumens	621 @ 4000K	1006 @ 5000K
Input Voltage	120V	120V
Input Frequency	50/60 Hz	50/60 Hz
Input Power	7.6W	11.7W
Input Current	0.075A - 0.0875A (Per input power)	0.075A - 0.0875A (Per input power)
Power Factor	>0.90	>0.90
THD	<20%	<20%
EMI/RFI	FCC Title 47 CFR, Part 15, FCC Title 47 CFR, Par Class B (Consumer) Class B (Consume	
Sound Rating	Class A	Class A
Minimum Starting Temp	-30°C (-22°F)	-30°C (-22°F)











Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Title 20 Appliance Efficiency Database.







# RL56 SeleCCTable Series 600 Lumen 900 Lumen

- 600 Series: up to 712 lumens<sup>1</sup> 900 Series: up to 1006 lumens<sup>1</sup> 1200 Series: up to 1272 lumens<sup>1</sup>
- 600 Series: use to replace 65W BR30 or 50W PAR30 lamp 900 Series: use to replace 75W PAR30 lamp 1200 Series: use to replace 90W BR40 lamp
- 2700K, 3000K, 3500K, 4000K, 5000K CCT<sup>2</sup> all in one
- 90 CRI
- 600 Series: 7.6W, 120V 900 Series: 12.1W, 120V 1200 Series: 14W, 120V
- L70 @ 70,000 hrs
- HALO matte white finish
- Torsion springs pre-installed

Optional Push-N-Twist universal installation two piece clips

1200 Lumen

- Compatible with most 5" and 6" standard and shallow recessed housings
- Dimmable to 5% with select dimmers
- Damp and wet location listed (shower rated)
- Rated for IC, ICAT and may be used in Non-IC housings
- AIR-TITE™ certified per ASTM-E283
- · Diffusing, regressed lens
- · Five-year limited warranty
  - Lumens per selected CCT
     CCT Correlated Color Temperature

### RL56 Designer Trims (Order Separately)



### RL56TRMWHB White Baffle (Paintable)

RL56TRMWH White (Paintable)



### RL56TRMTBZB Tuscan Bronze Baffle

RL56TRMTBZ
Tuscan Bronze



### RL56TRMSNB Satin Nickel Baffle


RL56TRMSN Satin Nickel




 $<sup>^{\</sup>rm a}$  Savings are over the life of the HALO RL56 600 Lumen luminaire. Energy savings: \$348

Replacement lamp savings: \$61

Savings based on \$0.128 per kilowatt hour, average six hours use per day, 70,000 hours of lamp usage, and 65W BR30 lamp lumen equivalent.





Once the torsion springs are removed, install the friction clips and make sure to rotate the clips into position before installing into the housing.

# **RL56 SeleCCTable Series**

### Ordering Information

Sample Number: **RL56069S1EWH** Order HALO housing separately.

### RL56 - 5"/6" LED Retrofit Baffle - Trim

RL56069S1EWH= 600 lumen 90 CRI, 2700K - 5000K CCT RL56099S1EWH= 900 lumen 90 CRI, 2700K - 5000K CCT RL56129S1EWH= 1200 lumen 90 CRI, 2700K - 5000K CCT

### LED Housings (Order Separately)

See Housing Compatibility section

### Accessories (Order Separately)

### **Baffle**

RL56TRMSNB=Satin Nickel Trim Ring RL56TRMTBZB=Tuscan Bronze Trim Ring RL56TRMWHB=White Paintable Trim Ring

### Splay

RL56TRMSN=Satin Nickel Trim Ring RL56TRMTBZ=Tuscan Bronze Trim Ring RL56TRMWH=White Paintable Trim Ring

OT400P=Oversize Flat White Metal Trim Ring, 6\* I.D. x 9-1/4\* O.D. (Ring slips behind RL56 ring in stepped configuration.)

HE26LED=Replacement screw base adapter (one included with unit)

OT403P=Oversize White Plastic Trim Ring, 6" I.D. x 8" O.D. (Ring slips behind RL56 ring in stepped configuration.)

TRM690WH=Oversize Matte White Metal Trim Ring. Designed for RL56 ring to inset into oversize ring for an even (non-stepped) trim surface.

RL56 Energy Data	600 Series	900 Series	1200 Series
Max. Lumens	712 @ 4000K	1006 @ 4000K	1272 @ 5000K
Input Voltage	120V	120V	120V
Input Frequency	50/60 Hz	50/60 Hz	50/60 Hz
Input Power	7.6W	12.1W	14W
Input Current	0.15 A	0.15 A	0.15 A
Power Factor	>0.90	>0.90	>0.90
THD	<20%	<20%	<20%
EMI/RFI	FCC Title 47 CFR, Part 15, Class B (Consumer)	FCC Title 47 CFR, Part 15, Class B (Consumer)	FCC Title 47 CFR, Part 15, Class B (Consumer)
Sound Rating	Class A	Class A	Class A
Minimum Starting Temp	-30°C (-22°F)	-30°C (-22°F)	-30°C (-22°F)











Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Title 20 Appliance Efficiency Database.





HF26LFD


Edison Base Adapter

for retrofit (included)


# **RL4 / RL56 SeleCCTable Series**


RL4 600 Lumen







**RL4** 900 Lumen






# RL56






# **RL56** 1200 Lumen




# **RA4 SeleCCTable Series**



- · Adjustable Gimbal for accent, task, grazing and downlighting
- 35° Tilt, up to 360° rotation
- 615 lumens @ 3000K
- Use to replace 40W R40 lamp or 60W PAR16 lamp
- 2700K, 3000K, 3500K, 4000K, 5000K CCT all in one
- 90 CRI
- 600 Series: 7.8W, 120V
- L70 @ 70,000 hrs
- · HALO matte white finish
- · Compatible with most 4" recessed housings
- · Flexible mounting with friction blades
- Dimmable to 5% with select dimmers
- · Damp location listed
- · Rated for IC, ICAT and may be used in Non-IC housings
- Five-year limited warranty







A Savings are over the life of the HALO RA4 600 Lumen luminaire. Energy savings: \$520

Replacement lamp savings: \$77

Savings based on \$0.128 per kilowatt hour, average six hours use per day, 70,000 hours of lamp usage, and 60W PAR16 lamp lumen equivalent.



# **Ordering Information**

Sample Number: **RL4069S1EWH** Order HALO housing separately.

### RA4 - 4" LED Adjustable Gimbal

RA4069S1EWH= 600 lumen, 90 CRI, 2700K - 5000K CCT

### **LED Housings (Order Separately)**

See Housing Compatibility section

### Accessories (Order Separately)

**HE26LED**=Replacement screw base adapter (one included with unit)



RA4 Energy Data	600 Series @ 3000K		
Max. Lumens	615 @ 3000K		
Input Voltage	120V		
Input Frequency	50/60 Hz		
Input Power	7.0W		
Input Current	0.065A		
Power Factor	>0.90		
THD	<20%		
EMI/RFI	FCC Title 47 CFR, Part 15, Class B (Consumer)		
Sound Rating	Class A		
Minimum Starting Temp	-30°C (-22°F)		











Refer to ENERGY STAR® Certified Products List.
Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Title 20 Appliance Efficiency Database.




# **RA56 SeleCCTable Series**








- · Adjustable Gimbal for accent, task, grazing and downlighting
- · 35° Tilt, up to 360° rotation
- 630 lumens @ 3000K
- Use to replace 65W BR30 lamp
- 2700K, 3000K, 3500K, 4000K, 5000K CCT all in one
- 90 CRI
- 600 Series: 7.0W, 120V
- L70 @ 70,000 hrs
- · HALO matte white finish
- Compatible with most 5" and 6" recessed housings
- · Flexible mounting with friction blades and torsion springs
- · Dimmable to 5% with select dimmers
- · Damp location listed
- · Rated for IC, ICAT and may be used in Non-IC housings
- Five-year limited warranty








A Savings are over the life of the HALO RA56 600 Lumen luminaire. Energy savings: \$520

Replacement lamp savings: \$84

Savings based on \$0.128 per kilowatt hour, average six hours use per day, 70,000 hours of lamp usage, and 65W BR30 lamp lumen equivalent.





# Ordering Information

Sample Number: **RL4069S1EWH** Order HALO housing separately.

RA56 - 5"/6" LED Adjustable Gimbal

RA56069S1EWH= 600 lumen, 90 CRI, 2700K - 5000K CCT

### LED Housings (Order Separately)

See Housing Compatibility section

### Accessories (Order Separately)

**HE26LED**=Replacement screw base adapter (one included with unit)



RA56 Energy Data	600 Series	
Max. Lumens	630 @ 3000K	
Input Voltage	120V	
Input Frequency	50/60 Hz	
Input Power	7.0VV	
Input Current	0.065A	
Power Factor	>0.90	
THD	<20%	
EMI/RFI	FCC Title 47 CFR, Part 15, Class B (Consumer)	
Sound Rating	Class A	
Minimum Starting Temp	-30°C (-22°F)	













# **RL4/RA4 Housing Compatibility**

# RL4/RA4 SeleCCTable LED are rated for installation in 4" HALO and other housings.

HALO LED <sup>1</sup>	H995ICAT, H995RICAT, H245ICAT, H245RICAT
HALO	H99ICAT, H99RTAT, H99TAT, E4ICATSB, E4TATSB, E4RTATSB
Other Brands	The RL and RA SeleCCTable Series is UL Certified for use with any 4" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 62.3 in <sup>3</sup> in addition to those noted above.

<sup>1</sup> HALO LED housings are non-screw base, high-efficacy code compliant.

### H995ICAT


4" LED, IC, AIR-TITE, New Construction Housing






4" LED, IC, AIR-TITE, Remodel Housing








### **H245ICAT**


4" LED, Ultra-shallow, IC, AIR-TITE, New Construction Housing



### **H245RICAT**

4" LED, Ultra-shallow, IC, AIR-TITE, Remodel Housing





14

# **RL56/RA56 Housing Compatibility**

# RL56/RA56 SeleCCTable LED are rated for installation in 5" and 6" HALO and other housings.


TIALO and other in	ousnigs.
HALO 5" LED <sup>1</sup>	H550ICAT, H550RICAT, E550ICAT, E550RICAT
HALO 6" LED <sup>1</sup>	H750ICAT, H750RICAT, H750T, H750TCP, H2750ICAT, H2750RICAT, E750ICAT, E750RICAT
HALO 5"	H5ICAT, H5RICAT, H5ICATNB, H5T, H5RT, H25ICAT, H25ICATNB, E5TAT, E5RTAT, H5TNB, E5TATNB, E5ICAT, E5RICAT, E5ICATNB
HALO 6"	H7ICAT, H7RICAT, H7ICT, H7RICT, H7ICATNB, H7ICTNB, H7T, H7RT, H7TNB, H7TCP, H7UICT, H7UICAT, H27ICAT, H27RICAT, H27T, H27RT, E7ICAT, E7RICAT, E27ICAT, E27RICAT, E7ICATNB, E7TAT, E7RTAT, E7TATNB, E27TAT, E27RTAT
HALO LED Retrofit	ML7BXRFK, ML7E26RFK
Other Brands*	The RL SeleCCTable Series is UL Certified for use with any 5"/6" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 107.9 in addition to those noted above.

<sup>\*</sup>When using RL56/RA56 torsion springs for retrofit some housings will not have torsion spring receiver brackets –use HALO ML7RAB retrofit adapter band (order separately)

### H750ICAT

6" LED, IC, AIR-TITE, Standard New Construction Housing






# **H2750ICAT**

6" LED, IC, AIR-TITE, Shallow New Construction Housing






### H750RICAT

6" LED, IC, AIR-TITE, Standard Remodel Housing





<sup>1</sup> HALO LED housings are non-screw base, high-efficacy code compliant.

# **Product and Photometric Data**


### RL4069S1EWH

RL4 SeleCCTable - 600 Series



Cat No.	CRI	CCT	Lumens	Power (W)	LPW
RL4069S1EWH	91	2700K	549	7.6	72.3
	91	3000K	580	7.6	76.3
	94	3500K	610	7.6	80.3
	94	4000K	621	7.6	81.7
	92	5000K	598	7.6	78.6

RL4069S1EWH-3000K				
Luminair	e lumens	575		
Input	Input watts			
LER (	LPW)	75.7		
	0-180	1.18		
Spacing Criteria	90-270	1.18		
Ontona	Diagonal	1.26		
Beam angl	e (degrees)	93.1		
Field angle	e (degrees)	141.1		
Zonal lumen	Lumens	% Lumens		
0-30	203	35.3		
0-40	322	56		
0-60	511	88.8		
<b>0-90</b> 575		100		



<sup>\*</sup> Tested in accordance with IES LM63. Field results may vary.

# **Color Metric Summary**

	-
TM-30-15	Rf = 91.1
1101-30-13	R <sub>g</sub> = 100.9
CRI/CIE	Ra = 93.1
CNI/CIE	R <sub>9</sub> = 64.9



CCT - Range of 2700K- 5000K

16

<sup>\*</sup>Additional photometric ies files available online.



### **RL4099S1EWH**

RL4 SeleCCTable - 900 Series

Cat No.	CRI	CCT	Lumens	Power (W)	LPW
RL4099S1EWH	92	2700K	891	11.7	76.2
	93	3000K	915	11.7	78.2
	94	3500K	951	11.7	81.2
	94	4000K	976	11.7	83.4
	91	5000K	1006	11.7	86.0

RL4099S1EWH-3000K					
	Luminaire lumens 915				
	watts	11.7			
LER (	LPW)	78.2			
	0-180	1.17			
Spacing Criteria	90-270	1.17			
Cittella	Diagonal	1.25			
Beam angl	e (degrees)	93.1			
Field angle	e (degrees)	141.1			
Zonal lumen	Lumens	% Lumens			
0-30	323	35.3			
0-40	512	56			
0-60	813	88.8			
0-90	915	100			
* Tested in accordance with IES IM63. Field results may vary					

<sup>\*</sup> Tested in accordance with IES LM63. Field results may vary.

# **Color Metric Summary**

		•			
	TM-30-15	Rf = 91.1			
	1101-30-13	R <sub>g</sub> = 100.9			
	CRI/CIE	Ra = 93.1			
	CNI/CIE	R9 = 64.9	93°		
	CCT - Range of 2700K- 5000K				
- 0	inm d				

<sup>\*</sup>Additional photometric ies files available online.

# **Product and Photometric Data**

### **RL56069S1EWH**

RL56 SeleCCTable - 600 Series



Cat No.	CRI	CCT	Lumens	Power (W)	LPW
	92	2700K	630	7.6	82.9
	92	3000K	665	7.6	87.5
RL56069S1EWH	94	3500K	700	7.6	92.1
	94	4000K	712	7.6	93.6
	92	5000K	685	7.6	90.2

RL56069S1EWH-3000K				
Luminair	665			
Input	7.6			
LER (	LPW)	87.5		
	0-180	1.14		
Spacing Criteria	90-270	1.14		
Ontona	Diagonal	1.22		
Beam angl	e (degrees)	87.8		
Field angle	e (degrees)	139		
Zonal lumen	Lumens	% Lumens		
0-30	247	37.2		
0-30 0-40	247 387	37.2 58.2		
0-40	387	58.2		

<sup>\*</sup> Tested in accordance with IES LM63. Field results may vary.

# **Color Metric Summary**

Th 4 00 45	Rf = 89.8	
TM-30-15	R <sub>g</sub> = 98	
ODI/OIE	Ra = 93.7	
CRI/CIE	R9 = 69.1	93°
CCT - Rang	ge of 2700K- 5000K	

18

<sup>\*</sup>Additional photometric ies files available online.


### **RL56099S1EWH**

RL56 SeleCCTable - 900 Series



Cat No.	CRI	ССТ	Lumens	Power (W)	LPW
	90	2700K	890	12.1	73.6
	90	3000K	940	12.1	77.7
RL56099S1EWH	93	3500K	989	12.1	81.7
	93	4000K	1006	12.1	83.1
	91	5000K	969	12.1	80

RL56	099S1EWH-3	3000K
Luminair		940
Input	12.1	
LER (	LPW)	77.7
	0-180	1.16
Spacing Criteria	90-270	1.16
Citteria	Diagonal	1.22
Beam angl	e (degrees)	88.9
Field angle	(degrees)	140
Zonal lumen	Lumens	% Lumens
0-30	345	36.7
0-40	541	57.5
0-60	838	89.1
0-90	940	100



<sup>\*</sup> Tested in accordance with IES LM63. Field results may vary.

# **Color Metric Summary**

TM-30-15	Rf = 89.9	
1101-30-13	$R_{\text{g}}=97.7$	
CDIVOLE	Ra = 93.1	
CRI/CIE	R9 = 64.6	93°
CCT - Rang	ge of 2700K- 5000K	

\*Additional photometric ies files available online.

# **Product and Photometric Data**

### **RL56129S1EWH**

RL56 SeleCCTable - 1200 Series




Cat No.	CRI	CCT	Lumens	Power (W)	LPW
	91	2700K	1205	14	86.1
	93	3000K	1221	14	87.2
RL56099S1EWH	94	3500K	1227	14	87.6
	95	4000K	1249	14	89.2
	93	5000K	1272	14	90.8

RL56129S1EWH-3000K				
Luminair	1221			
Input	14			
LER (	LPW)	87.2		
	0-180	1.21		
Spacing Criteria	90-270	1.21		
Ontona	Diagonal	1.31		
Beam angl	e (degrees)	93		
Field angle	e (degrees)	140		
Zonal lumen	Lumens	% Lumens		
0-30	345	31.7		
0-30 0-40	345 541	31.7 51.5		
0-40	541	51.5		

<sup>\*</sup> Tested in accordance with IES LM63. Field results may vary.

# **Color Metric Summary**

TM-30-15	Rf = 89.9
1101-30-13	R <sub>g</sub> = 97.7
CDL/CIE	Ra = 93.1
CRI/CIE	R9 = 64.6



20

93°

<sup>\*</sup>Additional photometric ies files available online.




### **RA4069S1EWH**

RA4 SeleCCTable - 600 Series

Cat No.	CRI	CCT	Lumens	Power (W)	LPW
	91	2700K	549	7.6	72.3
	91	3000K	580	7.6	76.3
RA4069S1EWH	94	3500K	610	7.6	80.3
	94	4000K	621	7.6	81.7
	92	5000K	598	7.6	78.6

RA4069S1EWHR-3000K				
Luminaire lumens 575				
Input	7.6			
LER (	LPW)	75.7		
	0-180	1.18		
Spacing Criteria	90-270	1.18		
Ontona	Diagonal	1.26		
Beam angl	e (degrees)	93.1		
Field angle	(degrees)	141.1		
Zonal lumen	Lumens	% Lumens		
0-30	203	35.3		
0-40	322	56		
0-60	511	88.8		
0-90	575	100		



### **Color Metric Summary**

TM-30-15	Rf = 90
	R <sub>g</sub> = 98
CRI/CIE	Ra = 95
UNI/UIE	R9 = 77



CCT - Range of 2700K- 5000K

<sup>\*</sup>Additional photometric ies files available online.

# **Product and Photometric Data**

### R564069S1EWH

RA56 SeleCCTable - 600 Series



Cat No.	CRI	ССТ	Lumens	Power (W)	LPW
RA56069S1EWH	92	2700K	630	7.6	82.9
	92	3000K	665	7.6	87.5
	94	3500K	700	7.6	92.1
	94	4000K	712	7.6	93.6
	92	5000K	685	7.6	90.2

RA56069S1EWH-3000K						
Luminair	665					
Input	7.6					
LER (	87.5					
Spacing Criteria	0-180	1.14				
	90-270	1.14				
	Diagonal	1.22				
	070					
Beam angl	e (degrees)	87.8				
Field angle		139				
Field angle	e (degrees)	139				
Field angle Zonal lumen	(degrees) Lumens	139 % Lumens				
Field angle Zonal lumen 0-30	(degrees)  Lumens 247	139 % Lumens 37.2				
Field angle Zonal lumen 0-30 0-40	Lumens 247 387	139 <b>% Lumens</b> 37.2  58.2				



### **Color Metric Summary**

		-
	TM-30-15	Rf = 90
		$R_g = 98$
	CRI/CIE	Ra = 95
		R9 = 77



CCT - Range of 2700K- 5000K



- Maximum spacing criteria
- · Optimized design for general downlighting
- Exceeds 86% of light between 0-60° cone-of-light zone
- ENERGY STAR® and California Title 24 zonal and efficacy requirements

# **Lighting Control Solution**

Eaton dimmers offer versatile options to set the mood and reduce energy consumption. These compatible LED dimmers are ideal for both residential and light commercial applications and are compatible with decorator (screw-less) style devices and wallplates.

Refer to www.eaton.com for additional information.



Decorator WBSD-DEC-\*



Slide WBSD-SLD-\*



Toggle WBSD-TOG-\*



Smart WBSD-SMT-\*



### Eaton

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.eaton.com/lighting

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8

P: 905-501-3000 F: 905-501-3172

### Our Lighting Product Lines

Ametrix AtLite Corelite Ephesus Fail-Safe

HALO

Invue

HALO Commercial

io IRiS Lumark Lumière

McGraw-Edison

MWS Neo-Ray Portfolio

Metalux

RSA

Shaper Streetworks Sure-Lites

### **Our Controls Product Lines**

Fifth Light Technology Greengate iLight (International Only) iLumin Zero 88

### Connected Lighting Systems

Distributed Low-Voltage Power HALO Home iLumen Plus LumaWatt Pro WaveLinx

### Eaton

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.eaton.com/lighting

© 2018 Eaton All Rights Reserved Printed in USA Publication No. BR518046EN August 2018

Products, specifications and compliances are subject to change without notice.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

