





E-Z-Code®

| | |
|--|---------|
| Overview | P2 |
| E-Z-Coder™ Wire Marker Printer | P3 |
| E-Z-Coder™ Wire Marker Printer & Labels | P4 |
| Identification Software | P5-P6 |
| Wire Marker Books | P7-P9 |
| Wire Marker Cards – Vinyl Cloth | P10-P16 |
| Wire Marker Cards – Vinyl Cloth – Mini Books | P17 |
| Cable Markers – Vinyl Cloth | P18-P19 |
| Wire Marker Cards – Vinyl Self-Laminating | P20-P21 |
| Write-On Markers & Roll Tape Markers | P22 |
| Standard Wire Marker Combination Packs | P23 |
| Conduit and Electrical Markers – Cards | P24 |
| Industrial Markers | P25 |
| Markers and PCB Warning Labels | P26 |
| Roll Wire Marker Dispenser | P27 |
| Color-Coded I.D. Tape | P28 |
| Protect-A-Line® Warning Tapes | P29 |
| Tape and Markers | P30 |
| Customized Embossed Tags Stainless Steel Tape Embossing System | P31 |
| Stainless Steel I.D. Tag | P32 |
| PVC Sleeve and Clip-On Markers | P33 |
| Lockout/Tagout | P34-P44 |
| Accident Prevention Tags | P45 |
| Transformer Safety Labels | P46 |
| Electrical Safety Cards and Labels | P47 |
| Safety Signs | P48-P52 |
| Custom Sign Express Order Form | P53 |

E-Z-Code®

Overview



Industrial construction, in-plant operations, and telecommunications. Computer installations and power facilities. Transportation and panel equipment. Wherever electrical and electronic components and systems are used to connect, fasten, insulate and identify wire and conduits, you'll find a Thomas & Betts quality product performing to industry-wide standards of excellence. For over a hundred years, Thomas & Betts has developed the products you need, with the quality you demand and at the right price.

E-Z-Code Identification Products are marketed nationally through an exclusive network of authorized stocking distributors, where emphasis is placed on customer service, experience and product knowledge. Staffed by trained professionals with a background in federal, state and local codes and regulations, your local T&B distributor can provide you with quotation service, up-to-date pricing, shipping costs and competitive product line evaluations when needed.

Automated Wire Markers & Accessories

The E-Z-Coder™ Wire Marker Printer is one of the smallest, most portable wire marker printers in the industry. It is a simple, easy-to-use, and reliable tool that'll have you marking wires almost as soon as you pull it from the box. E-Z-Code Labeling Software is a full-featured labeling system for creating custom labels for your cabling and wire marking needs. E-Z-Code® Laser Printable Markers let you print your own markers to your requirements.

Wire Marker Book, Cards and Labels

Pocket pack wire marker books are easy to carry, easy to use. T&B maintenance and production labels have been designed to provide extra-added convenience through positive, protected clear identification. Wire marking is simple, clean and fast...just pull tape out, tear and wrap. Compact size fits in your pocket or hangs from work belt.

Lockout / Tagout

E-Z-Code offers an inclusive product line to supply the general requirements of the OSHA Lockout/Tagout standard. From comprehensive training videos to circuit breaker locking devices, E-Z-Code Lockout/Tagout products help insure that general industry workers will be protected from accidents during maintenance and servicing of equipment.

Identification Tapes

Bright colors are not the only advantages of these Barricade and Burial Tapes. T&B's attention-getting Tapes are also inexpensive and easy to handle. Protect-A-Line tape is ideal for marking hazardous or off-limit barricade areas. A large assortment of Buried Utility Tape and Foil Backed Detectable Buried Utility Tapes help prevent potential accidents during excavations and underground installations.

Electrical Hazard Safety Signs

T&B provides a large assortment of necessary Electrical Hazard Safety Signs to complete your construction and maintenance projects. Choose from either Aluminum, Plastic, or Self Sticking material to suit your environments. Or create your own sign to your specifications by ordering from our Specials Form.



E-Z-Code®

E-Z-Coder™ Wire Marker Printer



The E-Z-Coder Wire Marker Printer is sold with one battery pack, a battery charger, one ribbon for general use labels and a wrist cord. The E-Z-Case, accessory batteries and all printing media are sold separately.

The E-Z-Coder™ Wire Marker Printer from Thomas & Betts. It's how to run wires without running wild.

The E-Z-Coder™ Wire Marker Printer is one of the smallest, most portable wire marker printers in the industry. It is a simple, easy-to-use, and reliable tool that'll have you marking wires almost as soon as you pull it from the box. When compared with other larger, more complicated systems, the E-Z-Coder™ printer is also one of the most affordable devices for producing custom labels for wire, face plates, outlets and electrical components. And the E-Z-Coder wire marker printer makes sharp, impressive labels that reflect the quality and professionalism that's required even on the toughest jobs.

- Compact unit that fits easily in the palm of your hand.
- Simple to use, no elaborate training is required.
- Weighs only a little over a pound.

- Powered from a single rechargeable battery, prints up to 250 labels from a single charge.
- Easy-loading label system.
- Wide, user-friendly buttons, with common electrical notations.
- Large, easy-to-read LCD display.
- Heavy-duty printing head for years of quality label printing.
- Self-adjusts the label to the correct printing position.
- Automatic label serialization.
- Three different printing position modes and either small or large type size, bold and normal type.
- Rugged construction.
- Simple instructions on the back of the printer.
- Wide variety of labels, including heat-shrinkable tubing.



E-Z-Coder™ Wire Marker Printer

| Cat. No. | Description | UPC No. |
|---------------------|---|--------------|
| EZ-CODER | Printer (includes EZ-RBLACK Ribbon, battery, user's guide, battery charger and wrist/belt cord) | 786210-37635 |
| EZ-BATTERY A | Battery Pack | 786210-37636 |
| EZ-CHARGER B | Battery Charger | 786210-37637 |
| EZ-CASE C | Hard Shell Carrying Case | 786210-37638 |
| EZ-RBLACK D | Black Printer Ribbon for General Use Labels | 786210-37639 |
| EZ-RBLACKHS | Black Printer Ribbon for Heat Shrinkable Labels only | 786210-37640 |

E-Z-Coder™ Wire Marker Printer Specifications

- Weight 1.6 lbs.
- Shuttle head impact printer.
- Two type sizes with normal and bold type available.
- Prints up to eight variable lines of text.
- Two-line liquid crystal display (LCD), 16 characters wide max.
- Operating temperature range: 40°F to 120°F.
- UL listed battery charger (120 VAC, 60 HZ input/9V DC 75 mA output).
- FCC class A approved.
- Prints up to 250 labels between battery charges.
- 6 month warranty.
- Automatic label serialization.
- 3 printing modes; wire, center and strip.

Thomas & Betts



Perfect for Datacom faceplates and Category 5 networks.



Component labels keep your entire job well-organized.

E-Z-Coder™ Wire Marker Label Materials

| Type | Max. Service Temp. °F (°C) | Use | Special Properties |
|----------------------|----------------------------|---------------------------------------|---|
| Vinyl | 150 (66) | Wire and cable labels | Heat and solvent resistant; conformable |
| Vinyl Cloth | 180 (82) | General marking | Oil, water and humidity resistant; permanent or removable |
| Polyester | 311 (155) | Tag for outdoor or harsh environments | Solvent, heat, abrasion resistant |
| Polyester Metallized | 311 (155) | Metallized permanent label | Print receptive; CSA |
| Polyolefin | 275 (135) | Wire ID and insulation | Permanent, shrinkable |

| Cat. No. | Material | Label Size (In.) Width x Height | Wire Size (AWG) | Qty. Per Roll |
|----------|----------|---------------------------------|-----------------|---------------|
|----------|----------|---------------------------------|-----------------|---------------|

Self-Laminating White/Transparent Vinyl Labels

Wire Markers

| | | | | |
|------------|-------|------------|---------|---------|
| EZL-21-V75 | Vinyl | 1.0 X .75 | 10 - 16 | 250 |
| EZL-21-V1 | Vinyl | 1.0 X 1.0 | 10 - 12 | 250 |
| EZL-30-V | Vinyl | .5 X 1.25 | 6 - 10 | 250 |
| EZL-30-V2S | Vinyl | .5 X 1.25 | 6 - 10 | 250/500 |
| EZL-31-V | Vinyl | 1.0 X 1.25 | 6 - 10 | 250 |
| EZL-32-V | Vinyl | 1.5 X 1.25 | 6 - 10 | 250 |

Cable Markers

| | | | | |
|----------|-------|-----------|-------|-----|
| EZL-51-V | Vinyl | 1.0 X 2.5 | Cable | 100 |
| EZL-52-V | Vinyl | 1.5 X 2.5 | Cable | 100 |
| EZL-71-V | Vinyl | 1.0 X 4.0 | Cable | 100 |
| EZL-72-V | Vinyl | 1.5 X 4.0 | Cable | 100 |

Wire Markers


| | | | | |
|----------|-------|------------|---------|-----|
| EZL-50-C | Cloth | .5 X .75 | 10 - 16 | 250 |
| EZL-51-C | Cloth | 1.0 X .75 | 10 - 16 | 250 |
| EZL-70-C | Cloth | .5 X 1.0 | 10 - 12 | 250 |
| EZL-71-C | Cloth | 1.0 X 1.0 | 10 - 12 | 250 |
| EZL-90-C | Cloth | .5 X 1.25 | 6 - 10 | 250 |
| EZL-92-C | Cloth | 1.5 X 1.25 | 6 - 10 | 250 |

Component and General Identification Labels

| | | | | |
|-----------|----------------------|------------|--|-----|
| EZL-22-PW | Polyester White | 1.5 X .4 | | 500 |
| EZL-30-PW | Polyester White | .5 X .5 | | 500 |
| EZL-31-PW | Polyester White | 1.0 X .5 | | 500 |
| EZL-32-PW | Polyester White | 1.5 X .5 | | 500 |
| EZL-52-PW | Polyester White | 1.5 X .75 | | 250 |
| EZL-92-PW | Polyester White | 1.5 X 1.25 | | 250 |
| EZL-22-PC | Polyester Cloth | 1.5 X .4 | | 500 |
| EZL-52-PC | Polyester Cloth | 1.5 X .75 | | 250 |
| EZL-31-PM | Polyester Metallized | 1.0 X .5 | | 500 |
| EZL-52-PM | Polyester Metallized | 1.5 X .75 | | 250 |
| EZL-92-PM | Polyester Metallized | 1.5 X 1.25 | | 250 |

Heat-Shrink White Polyolefin Labels

| | | | | |
|------------|-------------|------------|---------|-----|
| EZS-11-125 | Heat Shrink | 1.0 X .235 | 22 - 16 | 100 |
| EZS-11-187 | Heat Shrink | 1.0 X .335 | 18 - 12 | 100 |
| EZS-21-250 | Heat Shrink | 1.0 X .439 | 16 - 10 | 100 |
| EZS-31-375 | Heat Shrink | 1.0 X .645 | 12 - 6 | 100 |
| EZS-41-500 | Heat Shrink | 1.0 X .851 | 8 - 1 | 100 |



Cloth Markers

| Cat. No. | Sheet Size (in.) | Markers per Sheet | Marker Size (in.) | | Max Wire Dia. (in.) |
|-----------|------------------|-------------------|-------------------|--------|---------------------|
| | | | W | L | |
| WEC-12112 | 9½ x 12 | 104 | ½ | 1 7/16 | 7/16 |
| WEC-10112 | 9½ x 12 | 64 | 29/32 | 1 7/16 | 7/16 |

Paper Markers

| Cat. No. | Sheet Size (in.) | Markers per Sheet | Marker Size (in.) | | Max Wire Dia. (in.) |
|----------|------------------|-------------------|-------------------|-----|---------------------|
| | | | W | L | |
| WEL-3414 | 9½ x 11 | 297 | ¾ | 1 ¼ | ¼ |
| WEL-1012 | 9½ x 11 | 154 | 1 | ¾ | ¾ |

Labels for use with the E-Z-Code High-Volume Wire Marking System Self-Laminating Markers

| Cat. No. | Sheet Size (in.) | Markers per Sheet | Marker Size (in.) | | Print Area (in.) | | Max Wire Dia. (in.) |
|-----------|------------------|-------------------|-------------------|-----|------------------|---|---------------------|
| | | | W | L | W | L | |
| WES-12112 | 9½ x 8 | 64 | ½ | 1 ½ | ½ | ½ | 5/16 |
| WES-1112 | 9½ x 8 | 32 | 1 | 1 ½ | 1 | ½ | 5/16 |
| WES-2112 | 9½ x 8 | 16 | 2 | 1 ½ | 2 | ½ | 5/16 |
| WES-12214 | 9½ x 9 | 48 | ½ | 2 ¼ | ½ | ¾ | 15/32 |
| WES-1214 | 9½ x 9 | 24 | 1 | 2 ¼ | 1 | ¾ | 15/32 |
| WES-2214 | 9½ x 9 | 12 | 2 | 2 ¼ | 2 | ¾ | 15/32 |
| WES-12334 | 9½ x 9 | 32 | ½ | 3 ¾ | ½ | 1 | 7/8 |
| WES-1334 | 9½ x 9 | 16 | 1 | 3 ¾ | 1 | 1 | 7/8 |
| WES-2334 | 9½ x 9 | 8 | 2 | 3 ¾ | 2 | 1 | 7/8 |
| WES-2512 | 9½ x 12 | 8 | 2 | 5 ½ | 2 | 1 | 1 ½ |
| WES-2128 | 9½ x 9 | 3 | 2 ½ | 8 ½ | 2 ½ | 2 | 2 |

Standard package is 25 sheets.

Add suffix **A** for 500 sheets, **B** for 1,000 sheets.

WEC, WEL, and WES labels may be used on any standard pin-feed dot-matrix printer. WLP labels may be used on any standard laser printer.

P

E-Z-code®

E-Z-Code®

Identification Software



- 1 Mil Polyester (same material as WPR rolls).
- Works on most laser printers.
- More markers per sheet than leading manufacturer's sheets.
- Leader template included with each 25 pack.

Laser Printable Markers

E-Z-Code® Laser Printable Markers let you print your own markers to your requirements. These self-laminating markers have a clear overlay of polyester that protects the legend against

oils, grease, water, chemicals and foreign matter. They also feature a strong adhesive for maximum adhesion to the wire and are available in a variety of sizes both as standard and specials.

| Cat. No. | Sheet Size | Markers Per Sheet | Marker Size | Max. Wire Dia. |
|-----------|------------|-------------------|-------------|----------------|
| WLP-1112 | 8½" x 11" | 48 | 1" x 1½" | ⅝" |
| WLP-1214 | 8½" x 11" | 32 | 1" x 2¼" | ⅝" |
| WLP-12112 | 8½" x 11" | 96 | ½" x 1½" | ⅝" |
| WLP-12214 | 8½" x 11" | 64 | ½" x 2¼" | ⅝" |
| WLP-12300 | 8½" x 11" | 48 | ½" x 3" | ⅞" |
| WLP-1300 | 8½" x 11" | 24 | 1" x 3" | ⅞" |
| WLP-1500 | 8½" x 11" | 16 | 1" x 5" | 1¼" |
| WLP-1900 | 8½" x 11" | 8 | 1" x 9" | 2" |
| WLP-2112 | 8½" x 11" | 24 | 2" x 1½" | ⅝" |
| WLP-2214 | 8½" x 11" | 16 | 2" x 2¼" | ⅝" |
| WLP-2300 | 8½" x 11" | 12 | 2" x 3" | ⅞" |
| WLP-2500 | 8½" x 11" | 8 | 2" x 5" | 1¼" |
| WLP-2900 | 8½" x 11" | 4 | 2" x 9" | 2" |

Standard package is 25 sheets to a package. Case quantity is 30 packages (of 25 sheets each).

Add suffix **A** for 500 sheets, **B** for 1,000 sheets.

WEC, WEL, and WES labels may be used on any standard pin-feed dot-matrix printer. WLP labels may be used on any standard laser printer.

Typewriter Printable Markers, self laminating

| Cat. No. | Description | Sheet Size | Marker Size | | Write-On Area | | Character per Marker | Max. Wire Size | No. per Sheet |
|-----------|--------------------------|------------|-------------|-----|---------------|----|----------------------|----------------|---------------|
| | | | W | L | W | L | | | |
| WTW-12112 | 25 sheets, 1,600 markers | 9" x 8" | ½" | 1½" | ½" | ½" | 4 | #4 | 64 |
| WTW-1112 | 25 sheets, 800 markers | 9" x 8" | 1" | 1½" | 1" | ½" | 9 | #4 | 32 |
| WTW-2112 | 25 sheets, 400 markers | 9" x 8" | 2" | 1½" | 2" | ½" | 19 | #4 | 16 |
| WTW-1214 | 25 sheets, 600 markers | 9" x 9" | 1" | 2¼" | 1" | ¾" | 9 | #1 | 24 |
| WTW-2214 | 25 sheets, 300 markers | 9" x 9" | 2" | 2¼" | 2" | ¾" | 19 | #1 | 12 |
| WTW-1334 | 25 sheets, 400 markers | 9" x 9" | 1" | 3¾" | 1" | 1" | 9 | 400 | 16 |
| WTW-2334 | 25 sheets, 200 markers | 9" x 9" | 2" | 3¾" | 2" | 1" | 19 | 400 | 8 |

Order by sheets—Standard package 25 identical individual sheets per poly bag.



E-Z-Code®

Wire Marker Books



Pocket pack wire marker books are easy to carry, easy to use. The material is an all purpose vinyl coated cloth tape exclusively designed to resist abrasion, oil, water and dirt. From Thomas & Betts you get the one-piece wire marker and terminal marker. A slight die-cut allows you to easily remove the terminal marker if you need it or leave it in place for a longer marker.

- Size 3" x 5" (76 mm x 146 mm).
- Quantity of pages: 10.
- Material: vinyl cloth.
- Cover keeps markers clean.
- Books are 3" x 5 1/2" pocket size.
- 10 pages per book.



Vinyl Cloth, Standard Books

| Cat. No. | Number of Markers and Legends |
|---|---|
| WM-0 thru 9 | 40 Markers each: 0 thru 9; 10 Markers each: T1, T2, T3, L1, L2, L3, WM-0 thru -9 |
| WM-0-9M | 46 Markers each page; full page of 1, full page of 2, etc. |
| WM-0-45 | 10 Markers each: 0 thru 45 |
| WM-46-90 | 10 Markers each 46 thru 90 |
| WM-A-Z | 10 Markers each: A thru Z, +, -, and 0 thru 15 |
| WM-123 | 150 Markers each: 1, 2, 3 |
| WM-ABC | 150 Markers each: A, B, C |
| WM-A-33 | 10 Markers each: 1 thru 33, A, B, C, +, -, T1, T2, T3, L1, L2, L3 |
| WM-A-90 | 6 Markers each: 0 thru 15; 4 Markers each: 16 thru 90; 2 Markers each: A thru Z |
| WM-0 thru WM-9 | 460 Markers each of any number 0 thru 9 |
| WM-A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T, or X | 460 Markers each of any letter; -A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T or X |
| WM-GRD | 120 Markers 7/16" x 2 1/2" or 240 Markers 7/16" x 1 1/4" with "GRD" legend |
| WMLC-1 | 24 Legends, 2 legends each per page, 480 markers per book for house wiring and circuit breakers; 5/8" x 1 9/16" (16mm x 10mm) |
| WM-T3 | 10 Pages T ₁ , T ₂ , T ₃ ; 140 Markers ea.; total 420 |
| WM-L3 | 10 Pages L ₁ , L ₂ , L ₃ ; 140 markers ea.; total 420 |
| WM-9T | 3 Pages 1, 2, 3; 42 markers ea.; 3 Pages A, B, C; 42 markers ea.; 2 Pages T ₁ , T ₂ , T ₃ ; 28 markers ea.; 2 Pages L ₁ , L ₂ , L ₃ ; 28 markers ea.; total 140 |
| WM-1-30 | 10 Pages 1-30; 14 markers ea.; total 140 |
| WM-12 | A-Z 8 1/2 Pages, 14 markers ea.; Blank Write Ons 1 Page, 22 markers ea.; Plus & Minus 1/2 Page, 7 markers ea.; total 393 |
| WM-13 | Plus & Minus, AC, DC, 1 Page ea., 46 markers ea.; Pos. Neg. Gnd. 1 Page ea., 28 markers ea.; Spare, Neut. 1 Page ea., 22 markers ea.; Blank Write Ons 1 Page ea., 22 markers ea.; total 256 |
| WM-0-90 | 5 Pages ea. 0-45; 5 markers ea.; 5 Pages ea. 46-90; 5 markers ea.; total 455 |


Minimum order quantity is 10.

E-Z-Code®


Wire Marker Books




- **Bold letters / numbers, easy to apply and read.**
- **Convenient alphanumeric and loadcenter legends.**
- **E-Z-Snap feature, removes the entire sheet more easily from the booklet.**
- **Custom / private label covers available.**
- **Vinyl coated cloth.**



Make your own laminated markers by using these blank write-ons.



Clear area covers print legend for extra protection.



Use these clear markers to protect labels or to apply over non-sticking markers.

E-Z-Code® Compact Wire Marker Books

Introducing a handy solution to your identification needs. The new E-Z-Code® Compact Wire Marker books from T&B feature:

| Cat. No. | Legend | Sheets Per Book | Markers Per Page | Marker Size | Wt /Lbs. 100 Books |
|----------|---|-----------------|------------------|-------------|--------------------|
| WCMB-0-9 | 128 markers 0-9, ABC, +, -, marker size ¼" x 1½" | | | | |
| WCMB-LC | 176 markers Loadcenter Labels; marker size 1½" x ¾" | | | | |

Standard package is 20 books. Case quantity is 480 books (24 cartons).

Vinyl Self Laminating, Standard Books

| Cat. No. | Number of Markers and Legends |
|----------------|--|
| WMSL 1-33, A-G | 400 Markers: ¼" x 1¼" – printed area ¾"; 10 markers each: 1 thru 33 and A thru G |
| WMSL-0-9 | 40 Markers each 0 thru 9; 10 Markers each: T1, T2, T3, L1, L2, L3 |
| WMSL-0-45 | 10 Markers each 0 thru 45 |
| WMSL-46-90 | 10 Markers each 46 thru 90 |
| WMSL-A-Z | 10 Markers each: A thru Z; +, -, and 0 thru 15 |
| WMSL-A-90 | 6 Markers each: 0 thru 15; 4 markers each 16 thru 90; 2 markers each A thru Z |

Minimum order quantity is 10.

| Cat. No. | Number of Markers and Legends |
|----------|---|
| WM-BW3 | 30 1" x 4⅞" blank write-on self-laminating transparent vinyl markers; marking area: 1" x 1" |
| WM-BW5 | 50 1" x 2¾" blank write-on, self laminating transparent vinyl markers; marking area: 1" x ¾" |
| WM-BW12 | 200 ½" x 1¼" blank write-on, self laminating transparent vinyl markers; marking area: ½" x ⅝" |
| WM-BW14 | 400 ¼" x 1¼" blank write-on, self-laminating transparent vinyl markers; marking area: ¼" x ⅝" |
| WM-BW34 | 140 ¾" x 1¼" blank write-on, self-laminating transparent vinyl markers; marking area: ¾" x ⅝" |

Minimum order quantity is 10.

Vinyl Self Laminating, Standard Laminator Book

| Cat. No. | Number of Markers and Legends |
|----------|-------------------------------------|
| WM-LAM | 50, 3½" x 5" Clear Cable Laminators |

Minimum order quantity is 10.


P

E-Z-code®


Thomas & Betts

E-Z-Code®

Wire Marker Books



When you need to color code your wiring, this book can solve your problems. Available in two sizes, it allows you to color rather than number your wires for coding and other applications.



E-Z-Code® Pocket Pack Production Quality Control Markers.

- Easy to carry – marker books fit in shirt pocket.
- Easy to use – just peel the marker from the page.
- Clean and convenient – markers are tabbed so that fingers never touch the adhesive.

Vinyl, Color Coding Standard Books

| Cat. No. | Size W L | Number of Markers and Legends |
|----------|-------------|---|
| WM-COL14 | ¼" x 1¼" | 460 Markers each: 1 page yellow and blue, 2 pages red, white, green and black |
| WM-COL1 | 1" x 2¼" | 50 Markers each: 1 page yellow and blue, 2 pages red, white, green and black |

Minimum order quantity is 10.

Polyolefin E-Z-Code® Pocket Pack Markers

Our line of E-Z-Code pre-printed quality control, production and maintenance labels help prevent problems before they occur. Now you can positively identify defective products, tools in need of calibration etc. by using these T&B labels. Available on cards with a choice of 8 legends or in our exclusive book design of 22 different legends.

Twenty two legends highlight the variety that our exclusive Pocket Pack

label books are available in. Each book contains 240 identical labels. The Pocket Pack keeps the markers clean, handy and ready to use.



Order exactly what you need from our large selection of stock labels for dating, coding, inspection, calibration, etc. or contact T&B for a special application or legend requirement to suit your particular needs.

Pocket Pack Markers


| Cat. No. | Legends 240 Identical per Book | Description |
|----------|-----------------------------------|----------------------|
| WTMP-1B | CALIBRATED (blk) _____ | |
| WTMP-2B | CERTIFICATION (blk) _____ | |
| WTMP-3B | MAINTENANCE (blue) _____ | |
| WTMP-4B | REJECTED (red) _____ | |
| WTMP-5B | ACCEPTED (green) _____ | |
| WTMP-6B | HOLD (red) _____ | |
| WTMP-7B | RETURN TO VENDOR (orange) _____ | 15 Pages per Book |
| WTMP-8B | REWORK (blk) _____ | |
| WTMP-9B | HOLD FOR INSPECTION (blue) _____ | |
| WTMP-11B | CAUTION (blk) _____ | 16 Markers per Page |
| WTMP-16B | DATE INSTALLED (blk) _____ | |
| WTMP-18B | DUE FOR INSPECTION (orange) _____ | Each Label is |
| WTMP-19B | DO NOT USE AFTER (red) _____ | ½" x ¾" |
| WTMP-20B | INSPECTED (blk) _____ | |
| WTMP-21B | BLANK HEADING _____ | Each Book Contains |
| WTMP-22B | REPAIRED BY (orange) _____ | 240 Identical Labels |
| WTMP-24B | SCRAPPED (orange) _____ | |
| WTMP-25B | TESTED (green) _____ | |
| WTMP-26B | CALIBRATION (green) _____ | |
| WTMP-52B | PROPERTY TAG (blk) _____ | |
| WTMP-53B | SERIAL NO. (blk) _____ | |
| WTMP-55B | TOOL NO. (blue) _____ | |

Minimum order quantity is 10.

Thomas & Betts



Printed in groups of 5 identical, 5 legends per card.



Solid Numbers

| Cat. No. | Legend | Markers per Legend | |
|----------------------------|--|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WCZEROS | 0 | 36 | 72 |
| WC1S thru WC99S | 1 thru 99 | 36 | 72 |
| WC100S | 100 | 25 | 50 |
| WC101S thru WC600S | 101 thru 600 | 25 | 50 |
| WC601 thru 605S | 601, 602, 603, 604, 605 | 5 | 10 |
| WC606-610S thru WC996-999S | 606, 607, 608, 609, 610 thru 996, 997, 998, 999 | 5 | 10 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.
Minimum order quantity is 25.

Numbers in Sequence

| Cat. No. | Legend | Markers per Legend | |
|--|----------------------------------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WC1 thru 33S | 1 thru 33 | 1 | 2 |
| WC34 thru 66S | 34 thru 66 | 1 | 2 |
| WC67 thru 99S | 67 thru 99 | 1 | 2 |
| WC100 thru 124S | 100 thru 124 | 1 | 2 |
| WC125 thru 149S thru WC275 thru 299S | 125 thru 149 thru 275 thru 299 | 1 | 2 |
| WC300 thru 324S thru WC1975 thru 1999S | 300 thru 324 thru 1975 thru 1999 | 1 | 2 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.
Minimum order quantity is 25.


Numbers in Sequence Repeated

| Cat. No. | Legend | Markers per Legend | |
|---------------|--------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WC1 thru 3S | 1-3 | 12 | 24 |
| WC1 thru 4S | 1-4 | 9 | 18 |
| WC1 thru 5S | 1-5 | 7 | 14 |
| WC0 thru 10S | 0-10 | 3 | 6 |
| WC1 thru 12S | 1-12 | 3 | 6 |
| WC1 thru 18S | 1-18 | 2 | 4 |
| WC19 thru 36S | 19-36 | 2 | 4 |



When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.
Minimum quantity is 25.

E-Z-Code®

Wire Marker Cards – Vinyl Cloth



Fast and Easy to use paired markers in sequence to mark both ends of the wire with the same legend.



Paired Numbers in Sequence

| Cat. No. | Legend | Markers per Legend | |
|----------------|------------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WC1 thru 16PS | 1 thru 16 | 16 | 32 |
| WC17 thru 32PS | 17 thru 32 | 16 | 32 |
| WC33 thru 48PS | 33 thru 48 | 16 | 32 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

Suffix Numbers

| Cat. No. | Legend | Markers per Legend | |
|------------------|------------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WC00S | 00 | 36 | 72 |
| WC01S thru WC09S | 01 thru 09 | 36 | 72 |
| WC0009S | 00 thru 09 | 36 | 72 |

Catalog No. WC0009S has three sequences of 00 thru 09 on a card. WC0009D has six sequences of 00 thru 09 on a card.


When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

Solid Numbers on a Colored Background

| Cat. No. | Legend | Background Color | Markers per Card | |
|---------------------|-----------|------------------|------------------|------------|
| | | | 1½" (38 mm) | ¾" (19 mm) |
| WCBLZEROS | 0 | Dark Blue | 36 | 72 |
| WCBL1S thru WCBL50S | 1 thru 50 | Dark Blue | 36 | 72 |
| WCGRZEROS | 0 | Dark Green | 36 | 72 |
| WCGR1S thru WCGR50S | 1 thru 50 | Dark Green | 36 | 72 |
| WCORZEROS | 0 | Orange | 36 | 72 |
| WCOR1S thru WCOR50S | 1 thru 50 | Orange | 36 | 72 |
| WCRDZEROS | 0 | Red | 36 | 72 |
| WCRD1S thru WCRD50S | 1 thru 50 | Red | 36 | 72 |
| WCYLZEROS | 0 | Yellow | 36 | 72 |
| WCYL1S thru WCYL50S | 1 thru 50 | Yellow | 36 | 72 |

Dark blue, dark green and red markers have white legends; orange and yellow markers have black legends.


When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



Numbers in Sequence on a Colored Background

| Cat. No. | Legend | Sequences per Card | |
|---------------------------------------|--------------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| On Black White Characters | | | |
| WCBK1 thru 33S | 1 thru 33 | 1 | 2 |
| WCBK34 thru 66S | 34 thru 66 | 1 | 2 |
| WCBK67 thru 99S | 67 thru 99 | 1 | 2 |
| WCBK100 thru 124S | 100 thru 124 | 1 | 2 |
| On Dark Blue White Characters | | | |
| WCBL1 thru 33S | 1 thru 33 | 1 | 2 |
| WCBL34 thru 66S | 34 thru 66 | 1 | 2 |
| WCBL67 thru 99S | 67 thru 99 | 1 | 2 |
| WCBL100 thru 124S | 100 thru 124 | 1 | 2 |
| On Brown White Characters | | | |
| WCBR1 thru 33S | 1 thru 33 | 1 | 2 |
| WCBR34 thru 66S | 34 thru 66 | 1 | 2 |
| WCBR67 thru 99S | 67 thru 99 | 1 | 2 |
| WCBR100 thru 124S | 100 thru 124 | 1 | 2 |
| On Dark Green White Characters | | | |
| WCGR1 thru 33S | 1 thru 33 | 1 | 2 |
| WCGR34 thru 66S | 34 thru 66 | 1 | 2 |
| WCGR67 thru 99S | 67 thru 99 | 1 | 2 |
| WCGR100 thru 124S | 100 thru 124 | 1 | 2 |
| On Red White Characters | | | |
| WCRD1 thru 33S | 1 thru 33 | 1 | 2 |
| WCRD34 thru 66S | 34 thru 66 | 1 | 2 |
| WCRD67 thru 99S | 67 thru 99 | 1 | 2 |
| WCRD100 thru 124S | 100 thru 124 | 1 | 2 |
| On Orange Black Characters | | | |
| WCOR1 thru 33S | 1 thru 33 | 1 | 2 |
| WCOR34 thru 66S | 34 thru 66 | 1 | 2 |
| WCOR67 thru 99S | 67 thru 99 | 1 | 2 |
| WCOR100 thru 124S | 100 thru 124 | 1 | 2 |
| On Yellow Black Characters | | | |
| WCYL1 thru 33S | 1 thru 33 | 1 | 2 |
| WCYL34 thru 66S | 34 thru 66 | 1 | 2 |
| WCYL67 thru 99S | 67 thru 99 | 1 | 2 |
| WCYL100 thru 124S | 100 thru 124 | 1 | 2 |

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.






Solid Letters

| Cat. No. | Legend | Markers per Legend | |
|-------------------------|----------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WCAS | A | 36 | 72 |
| WCBS thru WCZS | B thru Z | 36 | 72 |
| WCLAS | a | 36 | 72 |
| WCLBS thru WCLZS | b thru z | 36 | 72 |

Order by cards – not by individual markers. Standard box – 25 cards.

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



Letters in Sequence

| Cat. No. | Legend | Sequences per Legend | |
|-----------|------------------------|----------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WCAZAJJS | A thru Z plus A thru J | 1 | 2 |
| WCAZ09S | A thru Z plus 0 thru 9 | 1 | 2 |
| WCLAZAJJS | a thru Z plus a thru J | 1 | 2 |

Order by cards – not by individual markers. Standard box – 25 cards.

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

Letters in Sequence on a Colored Background


| Cat. No. | Legend A-Z and A-J | Markers per Legend | |
|----------|---------------------------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WCBKA-ZS | Black (White legend) | 36 | 72 |
| WCBLA-ZS | Dark Blue (White legend) | 36 | 72 |
| WCBRA-ZS | Brown (White legend) | 36 | 72 |
| WCGRA-ZS | Dark Green (White legend) | 36 | 72 |
| WCRDA-ZS | Red (White legend) | 36 | 72 |
| WCORA-ZS | Orange (Black legend) | 36 | 72 |
| WCYLA-ZS | Yellow (Black legend) | 36 | 72 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

Solid Letters and Numbers

| Cat. No. | Legend | Markers per Card | |
|--------------------|--------------|------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WCA1S thru WCA5S | A1 thru A5 | 36 | 72 |
| WCB1S thru WCB5S | B1 thru B5 | 36 | 72 |
| WCC1S thru WCC5S | C1 thru C5 | 36 | 72 |
| WCD1S thru WCD5S | D1 thru D5 | 36 | 72 |
| WCE1S thru WCE5S | E1 thru E5 | 36 | 72 |
| WCF1S thru WCF4S | F1 thru F4 | 36 | 72 |
| WCG1S thru WCG4S | G1 thru G4 | 36 | 72 |
| WCH1S thru WCH5S | H1 thru H5 | 36 | 72 |
| WCJ1S thru WCJ4S | J1 thru J4 | 36 | 72 |
| WCK1S thru WCK4S | K1 thru K4 | 36 | 72 |
| WCL1S thru WCL5S | L1 thru L5 | 36 | 72 |
| WCM1S thru WCM5S | M1 thru M5 | 36 | 72 |
| WCP1S thru WCP4S | P1 thru P4 | 36 | 72 |
| WCR1S thru WCR5S | R1 thru R5 | 36 | 72 |
| WCS1S thru WCS5S | S1 thru S5 | 36 | 72 |
| WCT0S thru WCT9S | T0 thru T9 | 36 | 72 |
| WCT10S thru WCT15S | T10 thru T15 | 26 | 52 |
| WCU1S thru WCU2S | U1 thru U2 | 36 | 72 |
| WCV1S thru WCV2S | V1 thru V2 | 36 | 72 |
| WCW1S thru WCW2S | W1 thru W2 | 36 | 72 |
| WCX1S thru WCX4S | X1 thru X4 | 36 | 72 |
| WCY1S thru WCY4S | Y1 thru Y4 | 36 | 72 |
| WCZ1S thru WCZ4S | Z1 thru Z4 | 36 | 72 |

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



Solid Symbols – Miscellaneous

| Cat. No. | Legend | Markers per Card | |
|----------|---------|------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WCPLSS | + | 36 | 72 |
| WCMINS | - | 36 | 72 |
| WCAPLSS | A± | 25 | 50 |
| WCAMINS | A- | 25 | 50 |
| WCBPLSS | B+ | 25 | 50 |
| WCBMINS | B- | 25 | 50 |
| WCPOSS | POS | 25 | 50 |
| WCNEGS | NEG | 25 | 50 |
| WCPHS | Phase | 18 | 36 |
| WCPHAS | Phase A | 18 | 36 |
| WCPHBS | Phase B | 18 | 36 |
| WCPHCS | Phase C | 18 | 36 |
| WC1PHS | 1 Phase | 18 | 36 |
| WC2PHS | 2 Phase | 18 | 36 |
| WC3PHS | 3 Phase | 18 | 36 |
| WCINS | IN | 36 | 72 |
| WCOUTS | OUT | 25 | 50 |
| WCHOTS | HOT | 25 | 50 |
| WCGRDS | GRD | 25 | 50 |
| WCNEUTS | NEUT | 22 | 44 |
| WCLINES | LINE | 22 | 44 |
| WCLPLS | L+ | 25 | 50 |
| WCLMIS | L- | 25 | 50 |
| WLOADS | LOAD | 22 | 44 |
| WCPUS | PU | 36 | 72 |
| WGRCS | | 36 | 72 |
| WGENS | GEN | 25 | 50 |
| WCACS | AC | 36 | 72 |
| WCDCS | DC | 36 | 72 |
| WCCOMS | COM | 25 | 50 |
| WCBATS | BAT | 25 | 50 |
| WCBBS | BB | 36 | 72 |
| WCCBS | CB | 36 | 72 |
| WCCTS | CT | 36 | 72 |
| WCIGNS | IGN | 25 | 50 |
| WCSIGS | SIG | 25 | 50 |
| WCSECS | SEC | 25 | 50 |
| WCPSS | PS | 36 | 72 |
| WCPRIS | PRI | 25 | 50 |
| WCPLS | PL | 36 | 72 |
| WCTBS | TB | 36 | 72 |
| WCSSS | SS | 36 | 72 |
| WCSPARES | SPARE | 18 | 36 |
| WCCYSS | ~ | 36 | 72 |
| WGRSS | | 36 | 72 |
| WCPEs | PE | 36 | 72 |
| WCPENS | PEN | 25 | 50 |
| WC1US | 1U | 36 | 72 |
| WC2US | 2U | 36 | 72 |
| WC1VS | 1V | 36 | 72 |
| WC2VS | 2V | 36 | 72 |
| WC1WS | 1W | 36 | 72 |
| WC2WS | 2W | 36 | 72 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.





Solid Symbols – Voltages

| Cat. No. | Legend | Markers per Card | |
|----------|--------|------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WC3VS | 3V | 36 | 72 |
| WC6VS | 6V | 36 | 72 |
| WC12VS | 12V | 25 | 50 |
| WC24VS | 24V | 25 | 50 |
| WC110VS | 110V | 22 | 44 |
| WC115VS | 115V | 22 | 44 |
| WC120VS | 120V | 22 | 44 |
| WC125VS | 125V | 22 | 44 |
| WC180VS | 180V | 22 | 44 |
| WC220VS | 220V | 22 | 44 |
| WC230VS | 230V | 22 | 44 |
| WC240VS | 240V | 22 | 44 |
| WC270VS | 270V | 22 | 44 |
| WC280VS | 280V | 22 | 44 |
| WC440VS | 440V | 22 | 44 |
| WC460VS | 460V | 22 | 44 |
| WC480VS | 480V | 22 | 44 |

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

E-Z-Code®

Wire Marker Cards – Vinyl Cloth



Solid Machine Tool Markers


| Cat. No. | Legend | Markers per Card | |
|--------------------|--------------|------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WC1L1S | 1L1 | 25 | 50 |
| WC1L2S | 1L2 | 25 | 50 |
| WC1L3S | 1L3 | 25 | 50 |
| WC2L1S | 2L1 | 25 | 50 |
| WC2L2S | 2L2 | 25 | 50 |
| WC2L3S thru WC6L1S | 2L3 thru 6L1 | 25 | 50 |
| WC6L2S | 6L2 | 25 | 50 |
| WC6L3S | 6L3 | 25 | 50 |
| WC1T1S | 1T1 | 25 | 50 |
| WC1T2S | 1T2 | 25 | 50 |
| WC1T3S | 1T3 | 25 | 50 |
| WC2T1S | 2T1 | 25 | 50 |
| WC2T2S | 2T2 | 25 | 50 |
| WC2T3S thru WC7T1S | 2T3 thru 7T1 | 25 | 50 |
| WC7T2S | 7T2 | 25 | 50 |
| WC7T3S | 7T3 | 25 | 50 |
| WCLL1S | LL1 | 25 | 50 |
| WCLL2S | LL2 | 25 | 50 |
| WCLL3S | LL3 | 25 | 50 |

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

Machine Tool Markers in Sequence


| Cat. No. | Legend | Sequences per Card | |
|------------|---|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WC1T1-3T3S | 1T1, 1T2, 1T3 2T1, 2T2, 2T3 3T1, 3T2, 3T3 | 3 | 6 |
| WC4T1-6T3S | 4T1, 4T2, 4T3 5T1, 5T2, 5T3 6T1, 6T2, 6T3 | 3 | 6 |
| WC7T1-9T3S | 7T1, 7T2, 7T3 8T1, 8T2, 8T3 9T1, 9T2, 9T3 | 3 | 6 |
| WCLL1-LL3S | LL1, LL2, LL3 | 9 | 18 |
| WCA1-S2S | A1, A2, F1 F2, S1, S2 | 6 | 12 |

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.




Terminal Markers

| Cat. No. | Legend | Sequences per Card Marker Size 5/16" x 3/16" |
|----------------|------------|---|
| WC1 thru 48TM | 1 thru 48 | 3 |
| WC49 thru 96TM | 49 thru 96 | 3 |
| WCA thru ZTM | A thru Z | 3 |




Solid Numbers – Mini Markers

| Cat. No. | Legend | Markers per Card 1/2" (13 mm) |
|------------------------|--------------|----------------------------------|
| WCZEROMIN | 0 | 150 |
| WC1MIN thru WC99MIN | 1 thru 99 | 150 |
| WC100MIN | 100 | 102 |
| WC101MIN thru WC250MIN | 101 thru 250 | 102 |




Numbers in Sequence – Mini Markers

| Cat. No. | Legend | Markers per Card 1/2" (13 mm) |
|--|--------------------------------|----------------------------------|
| WC0 thru 49MIN | 0 thru 49 | 3 |
| WC50 thru 99MIN | 50 thru 99 | 3 |
| WC100 thru 132MIN | 100 thru 132 | 3 |
| WC133 thru 165MIN thru WC463 thru 495MIN | 133 thru 165 thru 463 thru 495 | 3 |



Solid Letters – Mini Markers

| Cat. No. | Legend | Markers per Card 1/2" (13 mm) |
|--------------------|----------|----------------------------------|
| WCAMIN | A | 150 |
| WCBMIN thru WCZMIN | B thru Z | 150 |




Letters in Sequence – Mini Markers



| Cat. No. | Legend | Sequences per Card 1/2" (13 mm) |
|----------|----------|------------------------------------|
| WCAZMIN | A thru Z | 6 |

E-Z-Code®

Cable Markers – Vinyl Cloth



Vinyl Cloth cable markers are a large 3½" (89mm) x ½" (13mm) marker that have many uses including large conductors, multi-wire circuits, electrical cables and tubing for hydraulic systems. Help prevent dangerous mistakes, and time consuming trial and error searches during electrical or hydraulic systems repair.



Solid Numbers – Cable Markers

| Cat. No. | Legend | Markers per Card | |
|----------|--------|------------------|-------------|
| | | 3½" (89 mm) | 1¾" (45 mm) |
| WCCM0S | 0 | 18 | 36 |
| WCCM1S | 1 | 18 | 36 |
| WCCM2S | 2 | 18 | 36 |
| WCCM3S | 3 | 18 | 36 |
| WCCM4S | 4 | 18 | 36 |
| WCCM5S | 5 | 18 | 36 |
| WCCM6S | 6 | 18 | 36 |
| WCCM7S | 7 | 18 | 36 |
| WCCM8S | 8 | 18 | 36 |
| WCCM9S | 9 | 18 | 36 |

When 1¾" length cable markers are required substitute the last **S** in the part number with a **D**, eg. WCCM1S would become WCCM1D.

Solid Letters – Cable Markers

| Cat. No. | Legend | Markers per Card | |
|----------|--------|------------------|-------------|
| | | 3½" (89 mm) | 1¾" (45 mm) |
| WCCMAS | A | 18 | 36 |
| WCCMBS | B | 18 | 36 |
| WCCMCS | C | 18 | 36 |
| WCCMDS | D | 18 | 36 |
| WCCMES | E | 18 | 36 |
| WCCMFS | F | 18 | 36 |
| WCCMNS | N | 18 | 36 |

When 1¾" length cable markers are required substitute the last **S** in the part number with a **D**, eg. WCCM1S would become WCCM1D.




Numbers or Letters in Sequence – Cable Markers

| Cat. No. | Legend | Markers per Card | |
|------------|------------|------------------|-------------|
| | | 3½" (89 mm) | 1¾" (45 mm) |
| WCCM01-09S | 01 thru 09 | 2 | 4 |
| WCCM1-9S | 1 thru 9 | 2 | 4 |
| WCCM1-18S | 1 thru 18 | 1 | 2 |
| WCCM19-36S | 19 thru 36 | 1 | 2 |
| WCCM37-54S | 37 thru 54 | 1 | 2 |
| WCCM55-72S | 55 thru 72 | 1 | 2 |
| WCCM73-90S | 73 thru 90 | 1 | 2 |
| WCCM91-99S | 91 thru 99 | 2 | 4 |
| WCCMA-IS | A thru I | 2 | 4 |
| WCCMJ-RS | J thru R | 2 | 4 |
| WCCMS-ZS | S thru Z | 2 | 4 |

When 1¾" length cable markers are required substitute the last **S** in the part number with a **D**, eg. WCCM1S would become WCCM1D.

E-Z-Code®

Cable Markers – Vinyl Cloth



T&B maintenance and production labels have been designed to provide extra-added convenience through positive, protected clear identification. Coding, dating, testing, inspecting and recordkeeping data are maintained through consistent labeling.

Solid NEMA Color Markers – No Printing

| Cat. No. | Legend | Markers per Legend | |
|----------|-------------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WCBLKS | Black | 36 | 72 |
| WCBLDS | Blue-dark | 36 | 72 |
| WCBLLS | Blue-light | 36 | 72 |
| WCBRNS | Brown | 36 | 72 |
| WCGRYS | Gray | 36 | 72 |
| WCDGRS | Green-dark | 36 | 72 |
| WCGRLS | Green-light | 36 | 72 |
| WCMARS | Maroon | 36 | 72 |
| WCOLIS | Olive | 36 | 72 |
| WCORAS | Orange | 36 | 72 |
| WCPINS | Pink | 36 | 72 |
| WCPURS | Purple | 36 | 72 |
| WCREDS | Red | 36 | 72 |
| WCTANS | Tan | 36 | 72 |
| WCWHIS | White | 36 | 72 |
| WCYELS | Yellow | 36 | 72 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.




Blank Write-On Markers

| Cat. No. | Marker Size | Markers per Card |
|---------------|-------------|------------------|
| WCBW14X34D | ¾" x ¾" | 72 |
| WCBW14X112S | ¾" x 1½" | 36 |
| WCBW1132X112S | 1½" x 1½" | 26 |
| WCBW12X12D | ½" x ½" | 54 |
| WCBW12X112S | ½" x 1½" | 18 |
| WCBW58X112S | ⅝" x 1½" | 14 |
| WCBW34X12D | ¾" x ½" | 36 |
| WCBW34X214S | ¾" x 2¾" | 12 |
| WCBW1X112S | 1" x 1½" | 9 |
| WCBW112X112S | 1½" x 1½" | 6 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

Vinyl Cloth, Maintenance and Production Labels (Cards)

| Cat. No. | Wording | Colors White Background | Labels per Card | Label Size W L |
|----------|--------------------|-------------------------|-----------------|----------------|
| WCMP5 | Accepted | Green | 14 | 1½" x ⅝" |
| WCMP1 | Calibrated | Black | 14 | 1½" x ⅝" |
| WCMP26 | Calibration | Green | 14 | 1½" x ⅝" |
| WCMP2 | Certification | Black | 14 | 1½" x ⅝" |
| WCMP18 | Due For Inspection | Orange | 14 | 1½" x ⅝" |
| WCMP4 | Rejected | Red | 14 | 1½" x ⅝" |
| WCMP25 | Tested | Green | 14 | 1½" x ⅝" |
| WCMP75 | Calibration | Green | 9 | 2¾" x 1" |



Solid Numbers

| Cat. No. | Legend | Markers per Card | |
|--------------------|--------------|------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WSZEROS | 0 | 36 | 100 |
| WS1S thru WS99S | 1 thru 99 | 36 | 100 |
| WS100S | 100 | 25 | 68 |
| WS101S thru WS600S | 101 thru 600 | 25 | |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.

Numbers in Sequence

| Cat. No. | Legend | Markers per Card | |
|--------------------------------------|--------------------------------|------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WS1 thru 9S | 1 thru 9 | 4 | |
| WS0 thru 49D* | 0 thru 49 | | 2 |
| WS50 thru 99D* | 50 thru 99 | | 2 |
| WS1 thru 33S | 1 thru 33 | 1 | |
| WS34 thru 66S | 34 thru 66 | 1 | |
| WS67 thru 99S | 67 thru 99 | 1 | |
| WS100 thru 124S | 100 thru 124 | 1 | |
| WS125 thru 149S thru WS975 thru 999S | 125 thru 149 thru 975 thru 999 | 1 | |



* Only available in double tab.

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.

Solid Letters

| Cat. No. | Legend | Pairs of Markers per Card | |
|----------------|----------|---------------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WSAS | A | 36 | 100 |
| WSBS thru WSZS | B thru Z | 36 | 100 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.



Solid Letters and Numbers

| Cat. No. | Legend | Markers per Card | |
|-------------------------|------------|------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WSA1S | A1 | 36 | 100 |
| WSA2S | A2 | 36 | 100 |
| WSA3S | A3 | 36 | 100 |
| WSA4S | A4 | 36 | 100 |
| WSD1S thru WSD5S | D1 thru D5 | 36 | 100 |
| WSF1S | F1 | 36 | 100 |
| WSF2S | F2 | 36 | 100 |
| WSL1S thru WSL5S | L1 thru L5 | 36 | 100 |
| WSS1S | S1 | 36 | 100 |
| WSS2S | S2 | 36 | 100 |
| WST1S thru WST6S | T1 thru T6 | 36 | 100 |
| WSX1S | X1 | 36 | 100 |
| WSX2S | X2 | 36 | 100 |
| WSSPARES | SPARE | 18 | 25 |
| WSGRDS | GROUND | 18 | 25 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.



Letters and Numbers in Sequence

| Cat. No. | Legend | Sequences per Card | |
|----------------|------------------------|--------------------|------------|
| | | 1½" (38 mm) | ¾" (19 mm) |
| WSAZ09S | A thru Z plus 0 thru 9 | 1 | 2 |

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.

E-Z-Code®

Write-On Markers & Roll Tape Markers




Blank Write-On Markers

| Cat. No. | Description | Width of Each Marker | Markers per Card 1½" (38 mm) |
|--------------|---------------------------------|----------------------|---------------------------------|
| WSBW14x112S | | ¼" (6mm) | 36 |
| WSBW38x112S | | ⅝" (10mm) | 26 |
| WSBW12x112S | Single markers 1½" (38mm) | ½" (13 mm) | 18 |
| WSBW34x112S | | ¾" (19mm) | 12 |
| WSBW1x112S | | 1" (25mm) | 9 |
| WSBW112x112S | | 1½" (38mm) | 6 |

Blank Write-On Markers

| Cat. No. | Description | Width of Each Marker | Markers per Card 1¾" (38 mm) |
|-------------|--------------------------------|----------------------|---------------------------------|
| WSBW18x34D | | ⅙" (3mm) | 144 |
| WSBW950x34D | | ⅜" (5mm) | 100 |
| WSBW14x34D | Double markers ¾" (19mm) | ¼" (6mm) | 72 |
| WSBW38x34D | | ⅝" (10mm) | 52 |
| WSBW12x34D | | ½" (13mm) | 36 |
| WSBW34x34D | | ¾" (19mm) | 24 |
| WSBW1x34D | | 1" (25mm) | 18 |
| WSBW112x34D | | 1½" (38mm) | 12 |






Self-laminating write-on markers are made from a durable Vinyl material to provide excellent legend protection. These self-laminating write-on markers protect your code, even when submerged in water and oils. Constructed of Vinyl plastic with a write-on area and a transparent extension that laminates the code when wrapped around itself.

1. Apply legend area to cable first.
 2. Roll the clear area around the cable, making sure it covers the legend.
 3. Legend is protected against water, grease, chemicals and other foreign matter.
- Make your own laminated markers by using these blank write-ons.

Write-On Cable Markers


| Cat. No. | Overall Marker Size | Width Height Write-on Area | Markers per Card |
|----------|---------------------|----------------------------|------------------|
| WSLM33 | 1" x 2¾" | 1" x ¾" | 3 |
| WSLM35 | 1" x 5" | 1" x 1" | 3 |
| WSLM123 | 1½" x 3" | 1½" x ¾" | 2 |
| WSLM23 | 2" x 3" | 2" x ¾" | 2 |
| WSLM125 | 1½" x 5" | 1½" x 1" | 2 |
| WSLM25 | 2" x 5" | 2" x 1" | 2 |
| WSLM48 | 2" x 8" | 2" x 3¾" | 2 |
| WSLM95 | 2¼" x 5" | 2½" x 2¼" | 2 |
| WSLM410 | 2" x 10" | 2" x 4½" | 2 |
| WSLM415 | 2" x 15" | 2" x 7" | 2 |





T&B offers three styles of combination packs to help you to easily meet your needs for wire identification. In addition to the convenience of ordering sets of marker cards by the pack you save money over buying individual cards.

- WBC Vinyl Cloth
- WBC Vinyl Cloth mini's
- WSL Vinyl Self-Laminating



WBC Vinyl Cloth

| Cat. No. Single Markers 1½" (38 mm) | Legend (one card each legend in each pack) |
|---|--|
| WCCP1 thru 25S | 1 thru 25 |
| WCCP26 thru 50S | 26 thru 50 |
| WCCP51 thru 75S | 51 thru 75 |
| WCCP76 thru 100S76 thru 100 | |
| WCCP101 thru 125S thru WCCP576 thru 600S | 101 thru 125 thru 576 thru 600 |
| WCCPA thru ZS | A thru Z |

When ¾" length markers are required substitute the last S in the part number with a D, e.g., WCCP1-25D.

WSL Vinyl Self-Lam

| Cat. No. Single Markers 1½" (38 mm) | Legend (one card each legend in each pack) |
|---|--|
| WSCP1 thru 25S | 1 thru 25 |
| WSCP26 thru 50S | 26 thru 50 |
| WSCP51 thru 75S | 51 thru 75 |
| WSCP76 thru 100S | 76 thru 100 |
| WSCP101 thru 125S thru WSCP576 thru 600S | 101 thru 125 thru 576 thru 600 |
| WSCP A thru ZS | A thru Z |

When ¾" length markers are required substitute the last S in the part number with a D, e.g., WSCP1-25S, WSCP1-25D.

WBC Vinyl Cloth Mini-Marker

| Cat. No. Triple Markers ½" (13 mm) | Legend (one card each legend in each pack) | Markers per Card |
|--|--|------------------------|
| WCCP1 thru 25MIN | 1 thru 25 | 150 |
| WCCP26 thru 50MIN thru WCCP226 thru 250MIN | 26 thru 50 thru 226 thru 250 | 150 |
| WCCPA thru ZMIN | A thru Z | 150 |

How to order: Each catalog number is for one pack of assorted marker cards. For example: Catalog number WCCP1-25S is one pack of cloth wire markers containing one card each of a solid card number 1, 2, 3 etc. thru 25.

Important: Order combination packs by the pack not by the card; letter packs A to Z contain 26 cards.

E-Z-Code®

Conduit and Electrical Markers – Cards



Identify all electrical systems, including conduits, buss ducts, cable trays, load centers, circuit breakers, switches or any other vital electrical equipment with T&B's Self-Sticking WDA Vinyl Electrical markers. Help prevent dangerous mistakes, time consuming trial and error searching during electrical service work. Manufactured of rugged WDA Self-Sticking Vinyl with high contrast black printing for OSHA compliance and visibility.



STYLE A: 2¼" x 9"
(1 marker per card)



STYLE B: 2½" x 4½"
(4 markers per 2¼" x 9" card)



STYLE C: ½" x 2¼"
(18 markers per 2¼" x 9" card)
Black letters on orange background




WDA Vinyl, Conduit and Electrical Markers

| Style A 2¼" x 9" | Style B 1½" x 4½" | Style C ½" x 2¼" | Legend (Black on Orange) |
|---------------------|----------------------|---------------------|-----------------------------|
| WJT-5010 | WDT-5010 | WAT-5010 | 110 VOLTS |
| WJT-5011 | WDT-5011 | WAT-5011 | 115 VOLTS |
| WJT-5012 | WDT-5012 | WAT-5012 | 120 VOLTS |
| WJT-5045 | WDT-5045 | WAT-5045 | 120/208 VOLTS |
| WJT-5013 | WDT-5013 | WAT-5013 | 208 VOLTS |
| WJT-5014 | WDT-5014 | WAT-5014 | 220 VOLTS |
| WJT-5015 | WDT-5015 | WAT-5015 | 230 VOLTS |
| WJT-5016 | WDT-5016 | WAT-5016 | 240 VOLTS |
| WJT-5017 | WDT-5017 | WAT-5017 | 250 VOLTS |
| WJT-5018 | WDT-5018 | WAT-5018 | 277 VOLTS |
| WJT-5046 | WDT-5046 | WAT-5046 | 277/480 VOLTS |
| WJT-5057 | WDT-5057 | WAT-5057 | 380 VOLTS |
| WJT-5044 | WDT-5044 | WAT-5044 | 415 VOLTS |
| WJT-5019 | WDT-5019 | WAT-5019 | 440 VOLTS |
| WJT-5020 | WDT-5020 | WAT-5020 | 460 VOLTS |
| WJT-5021 | WDT-5021 | WAT-5021 | 480 VOLTS |
| WJT-5022 | WDT-5022 | WAT-5022 | 550 VOLTS |
| WJT-5023 | WDT-5023 | WAT-5023 | 600 VOLTS |
| WJT-5024 | WDT-5024 | WAT-5024 | 2200 VOLTS |
| WJT-5025 | WDT-5025 | WAT-5025 | 2300 VOLTS |
| WJT-5026 | WDT-5026 | WAT-5026 | 2400 VOLTS |
| WJT-5027 | WDT-5027 | WAT-5027 | 4160 VOLTS |
| WJT-5028 | WDT-5028 | WAT-5028 | 4800 VOLTS |
| WJT-5058 | WDT-5058 | WAT-5058 | 5000 VOLTS |
| WJT-5029 | WDT-5029 | WAT-5029 | 6900 VOLTS |
| WJT-5030 | WDT-5030 | WAT-5030 | 7200 VOLTS |
| WJT-5059 | WDT-5059 | WAT-5059 | 12,000 VOLTS |
| WJT-5060 | WDT-5060 | WAT-5060 | 13,000 VOLTS |
| WJT-5047 | WDT-5047 | WAT-5047 | 13,200 VOLTS |
| WJT-5031 | WDT-5031 | WAT-5031 | 13,800 VOLTS |
| WJT-5032 | WDT-5032 | WAT-5032 | AC |
| WJT-5043 | WDT-5043 | WAT-5043 | Air Conditioning |
| WJT-5052 | WDT-5052 | WAT-5052 | Circuit Breaker |
| WJT-5051 | WDT-5051 | WAT-5051 | Circuit # ___ |
| WJT-5038 | WDT-5038 | WAT-5038 | DC |
| WJT-5050 | WDT-5050 | WAT-5050 | Electric Out of Service |
| WJT-5033 | WDT-5033 | WAT-5033 | Emergency Service |
| WJT-5039 | WDT-5039 | WAT-5039 | Exit Lights |
| WJT-5040 | WDT-5040 | WAT-5040 | Fire Alarm |
| WJT-5053 | WDT-5053 | WAT-5053 | Fuse Box |
| WJT-5041 | WDT-5041 | WAT-5041 | Heating Circuit |
| WJT-5037 | WDT-5037 | WAT-5037 | Lights |
| WJT-5042 | WDT-5042 | WAT-5042 | Light & Power |
| WJT-5048 | WDT-5048 | WAT-5048 | On/Off |
| WJT-5036 | WDT-5036 | WAT-5036 | Power |
| WJT-5034 | WDT-5034 | WAT-5034 | Single Phase |
| WJT-5055 | WDT-5055 | WAT-5055 | Spare |
| WJT-5056 | WDT-5056 | WAT-5056 | Telephone |
| WJT-5035 | WDT-5035 | WAT-5035 | Three Phase |
| WJT-5054 | WDT-5054 | WAT-5054 | ___ VOLTS |

Standard package quantity 25 cards.

E-Z-Code®

Industrial Markers



Number or Letters, WBC Vinyl Cloth

Series 003

| Cat. No. | Description | Legend | Character Height | Marker Size W L | Marker per Card |
|------------------------|---------------------------------------|--------------------------------|------------------|-----------------|-----------------|
| WCNL003A thru WCNL003Z | Letters | A thru Z | 5/16" | 3/8" x 1/2" | 78 |
| WCNL003ZERO | Numbers | 0 | 5/16" | 3/8" x 1/2" | 78 |
| WCNL0031 thru WCNL0039 | Numbers | 1 thru 9 | 5/16" | 3/8" x 1/2" | 78 |
| WCNL003AZ | Letters in sequence | A thru Z (3 each) | 5/16" | 3/8" x 1/2" | 78 |
| WCNL00309 | Numbers in sequence | 0 thru 9 (7 each) | 5/16" | 3/8" x 1/2" | 70 |
| WCNL003AZ09 | Letter & Number Combination – in seq. | A thru Z and 0 thru 9 (2 each) | 5/16" | 3/8" x 1/2" | 72 |

Series 063

| Cat. No. | Description | Legend | Character Height | Marker Size W L | Marker per Card |
|------------------------|---------------------|-------------------|------------------|-----------------|-----------------|
| WCNL063A thru WCNL063Z | Letters | A thru Z | 5/8" | 9/16" x 3/4" | 32 |
| WCNL063ZERO | Numbers | 0 | 5/8" | 9/16" x 3/4" | 32 |
| WCNL0631 thru WCNL0639 | Numbers | 1 thru 9 | 5/8" | 9/16" x 3/4" | 32 |
| WCNL063AZ | Letters in sequence | A thru Z (1 each) | 5/8" | 9/16" x 3/4" | 32 |
| WCNL06309 | Numbers in sequence | 0 thru 9 (3 each) | 5/8" | 9/16" x 3/4" | 32 |

Series 100

| Cat. No. | Description | Legend | Character Height | Marker Size W L | Marker per Card |
|------------------------|---------------------|----------|------------------|-----------------|-----------------|
| WCNL100A thru WCNL100Z | Letters | A thru Z | 1" | 7/8" x 1 1/2" | 10 |
| WCNL100ZERO | Numbers | 0 | 1" | 7/8" x 1 1/2" | 10 |
| WCNL1001 thru WCNL1009 | Numbers | 1 thru 9 | 1" | 7/8" x 1 1/2" | 10 |
| WCNL100AJ | Letters in sequence | A thru J | 1" | 7/8" x 1 1/2" | 10 |
| WCNL100KT | Letters in sequence | K thru T | 1" | 7/8" x 1 1/2" | 10 |
| WCNL100UZ | Letters in sequence | U thru Z | 1" | 7/8" x 1 1/2" | 10 |
| WCNL10009 | Numbers in sequence | 0 thru 9 | 1" | 7/8" x 1 1/2" | 10 |

Series 200

| Cat. No. | Description | Legend | Character Height | Marker Size W L | Marker per Card |
|------------------------|---------------------|----------|------------------|-----------------|-----------------|
| WCNL200A thru WCNL200Z | Letters | A thru Z | 2" | 7/8" x 2 1/4" | 10 |
| WCNL200ZERO | Numbers | 0 | 2" | 7/8" x 2 1/4" | 10 |
| WCNL2001 thru WCNL2009 | Numbers | 1 thru 9 | 2" | 7/8" x 2 1/4" | 10 |
| WCNL200AJ | Letters in sequence | A thru J | 2" | 7/8" x 2 1/4" | 10 |
| WCNL200KT | Letters in sequence | K thru T | 2" | 7/8" x 2 1/4" | 10 |
| WCNL200UZ | Letters in sequence | U thru Z | 2" | 7/8" x 2 1/4" | 10 |
| WCNL20009 | Numbers in sequence | 0 thru 9 | 2" | 7/8" x 2 1/4" | 10 |

Packed 5 identical per plastic bag.

P

E-Z-code®

Thomas & Betts



High contrast reflective yellow on a black background, three standard sizes are available. Durable, trouble-free WRM Reflective Industrial Markers reflect light up to 100 times brighter than white or yellow painted surfaces. Manufactured from self-sticking WRM reflective material, these markers keep right on performing even in the most severe weather conditions.



T&B has put our most popular size reflective markers in a kit. Manufactured from the same tough materials as the individual markers, the kit will keep the WRUM series markers organized and free from damage and that means economy.

Reflective Industrial Markers

| Cat. No. | Size | Description | |
|----------|----------|------------------|-------------|
| | | Character Height | Marker Size |
| WRSUM* | Small | 1½" | 1¾" x 1¾" |
| WRUM* | Standard | 2½" | 1¾" x 2¾" |
| WRLUM* | Large | 3¾" | 2¾" x 4¾" |

* Add Letter (A-Z) or Number (0-9) desired in place of asterisk to complete Cat. No. Example **WRSUM1**, **WRSUM2**, **WRSUMA** etc.
25 single markers per bag.


Reflective Industrial Marker Kits

| Cat. No. | Marker Series | Contents |
|----------|---|---|
| NB-0056 | WRUM Markers | 50 zeros |
| | Marker Size 1¾" x 2¾" | 50 number one |
| | Character Height 2½" | 25 each two thru nine total 300 reflective markers |
| NB-0057 | WRUM Markers | Letter Kit |
| | Marker Size 1¾" x 2¾" Character Height 2½" | 320 letters A-Z |

Each kit is shipped within its own sealed plastic bag to insure factory newness until needed.

E-Z-Code®

Roll Wire Marker Dispenser



- Wire marking is simple, clean and fast...just pull tape out, tear and wrap. Compact size fits in your pocket or hangs from work belt.
- Unique design allows easy access to all legends during use or when refilling.
- Lifetime guarantee on T&B pack dispenser.

Wire Marker Dispenser

| Cat. No. | Description |
|-----------|--|
| WDFP | Empty Dispenser |
| WDFP-0-9 | Loaded Dispenser with Legends 0 thru 9 |
| WDFP-NEMA | Loaded Dispenser with 10 NEMA colors |

Refills – Polyester Tape

| Cat. No. | Legend | Rolls | Cat. No. | Legend | Rolls |
|----------------|--------|-------|-----------|--------|-------|
| WDFPR-0 | 0 | 10 | WDFPR-T1 | T1 | 10 |
| WDFPR-1 | 1 | 10 | WDFPR-T2 | T2 | 10 |
| WDFPR-2 | 2 | 10 | WDFPR-T3 | T3 | 10 |
| thru WDFPR-9 | thru 9 | 10 | WDFPR-MIN | - | 10 |
| WDFPR-0-9 | 0-9 | 1* | WDFPR-BLS | + | 10 |
| WDFPR-10-19 | 10-19 | 1* | WDFPR-YEL | YELLOW | 10 |
| WDFPR-A | A | 10 | WDFPR-WHT | WHITE | 10 |
| thru WDFPR-B-Z | thru Z | 10 | WDFPR-BLK | BLACK | 10 |
| WDFPR-L1 | L1 | 10 | WDFPR-BRN | ORANGE | 10 |
| WDFPR-L2 | L2 | 10 | WDFPR-BLU | BLUE | 10 |
| WDFPR-L3 | L3 | 10 | WDFPR-GRN | GREEN | 10 |
| | | | WDFPR-RED | RED | 10 |

*1 Pkg. equals 10 rolls, one of each number in the series.

P

E-Z-code®

Thomas & Betts

E-Z-Code®

Color-Coded I.D. Tape



Color-Coded I.D. Tape

| Cat. No. 1" Wide | Cat. No. 2" Wide | Cat. No. 3" Wide | Cat. No. 4" Wide | Color |
|------------------------|------------------------|------------------------|------------------------|--------|
| AA-1121 | BA-1121 | CA-1121 | NA-1121 | Silver |
| AA-1122 | BA-1122 | CA-1122 | NA-1122 | Black |
| AA-1123 | BA-1123 | CA-1123 | NA-1123 | Blue |
| AA-1124 | BA-1124 | CA-1124 | NA-1124 | Brown |
| AA-1125 | BA-1125 | CA-1125 | NA-1125 | Green |
| AA-1126 | BA-1126 | CA-1126 | NA-1126 | Orange |
| AA-1127 | BA-1127 | CA-1127 | NA-1127 | Purple |
| AA-1128 | BA-1128 | CA-1128 | NA-1128 | Red |
| AA-1129 | BA-1129 | CA-1129 | NA-1129 | White |
| AA-1130 | BA-1130 | CA-1130 | NA-1130 | Yellow |
| AA-1131 | BA-1131 | CA-1131 | NA-1131 | Clear |

60 yards per roll

Tel-A-Code Kits

| Cat. No. | Description |
|----------|--|
| NB-0060 | Tel-A-Code Kits contain ten 20-foot rolls of 12 different colors and are packed and sold as individual kits; 1" wide rolls |



P

E-Z-code®

Thomas & Betts

E-Z-Code®

Protect-A-Line® Warning Tapes



Barricade Tape

Bright colors are not the only advantages of these Barricade Tapes. T&B's attention-getting Barricade Tape is also inexpensive and easy to handle. Protect-A-Line tape is ideal for marking hazardous or off-limit areas. Convenient and reusable, it performs well both indoors and out-of-doors.

- Available in 3" X 1000' rolls.



Buried Utility Tape

Now you can help insure against costly dig-ins. Place T&B's Buried Utility Tape 1 to 1½ feet below the ground surface directly above the pipeline or cable below. Bright fade resistant colors warn equipment operators that a vital pipeline or cable is BURIED BELOW, before damage occurs. Buried utility tapes are printed black on a bright background.

- Available in 3" and 6" widths.



Foil Backed Detectable Buried Utility Tape

In addition to bright colors, the Foil Backed Detectable Tape features a metallic backing that is designed to be detectable under normal earthen surfaces up to 18" with common metal detectors. A simple and fast method to relocating lines, cables and conduit for future renovation.

- Available in 3" and 6" widths.

Protect-A-Line® Barricade and Burial Tapes

| Cat. No. | Legend | Color |
|--|---------------------------|-------------|
| Surveyors Tape 1½" x 1000' | | |
| NA-0200 | No Legend, No Printing | Yellow |
| NA-0201 | No Legend, No Printing | Red |
| NA-0202 | No Legend, No Printing | Green |
| NA-0203 | No Legend, No Printing | Blue |
| NA-0204 | No Legend, No Printing | Orange |
| Barricade Tape 3" x 1000' | | |
| NA-0250 | CAUTION | Yellow |
| NA-0253 | CAUTION CONSTRUCTION AREA | Yellow |
| NA-0254 | CAUTION DO NOT ENTER | Yellow |
| NA-0256 | CAUTION HARD HAT AREA | Yellow |
| NA-0257 | CAUTION HIGH VOLTAGE | Yellow |
| NA-0258 | CAUTION MEN WORKING | Yellow |
| NA-0261 | CAUTION OPEN TRENCH | Yellow |
| NA-0267 | DANGER, on Stripes | Red & White |
| Buried Utility Tape 3" x 1000' | | |
| NA-0600 | ELECTRIC LINE | Red |
| NA-0608 | ELECTRIC LINE | Yellow |
| NA-0601 | WATER LINE | Blue |
| NA-0602 | TELEPHONE LINE | Orange |
| NA-0603 | GAS LINE | Yellow |
| NA-0605 | SEWER LINE | Green |
| NA-0606 | HIGH VOLTAGE LINE | Red |
| NA-0609 | FIBER OPTIC CABLE | Orange |
| Foil Backed Detectable Buried Utility Tape 3" x 1000' | | |
| NAF-0600 | ELECTRIC LINE | Red |
| NAF-0608 | ELECTRIC LINE | Yellow |
| NAF-0601 | WATER LINE | Blue |
| NAF-0602 | TELEPHONE LINE | Orange |
| NAF-0603 | GAS LINE | Yellow |
| NAF-0604 | OIL LINE | Yellow |
| NAF-0605 | SEWER LINE | Green |
| NAF-0606 | HIGH VOLTAGE LINE | Red |
| NAF-0607 | CABLE TV LINE | Orange |
| NAF-0609 | FIBER OPTIC CABLE | Orange |
| Buried Utility Tape 6" x 1000' | | |
| NA-0700 | ELECTRIC LINE | Red |
| NA-0708 | ELECTRIC LINE | Yellow |
| NA-0701 | WATER LINE | Blue |
| NA-0702 | TELEPHONE LINE | Orange |
| NA-0703 | GAS LINE | Yellow |
| NA-0706 | HIGH VOLTAGE LINE | Red |
| NA-0709 | FIBER OPTIC CABLE | Orange |
| Foil Backed Detectable Buried Utility Tape 6" x 1000' | | |
| NAF-0700 | ELECTRIC LINE | Red |
| NAF-0708 | ELECTRIC LINE | Yellow |
| NAF-0701 | WATER LINE | Blue |
| NAF-0702 | TELEPHONE LINE | Orange |
| NAF-0703 | GAS LINE | Yellow |
| NAF-0704 | OIL LINE | Yellow |
| NAF-0705 | SEWER LINE | Green |
| NAF-0706 | HIGH VOLTAGE LINE | Red |
| NAF-0707 | CABLE TV LINE | Orange |
| NAF-0709 | FIBER OPTIC CABLE | Orange |

Note: All tapes are WBT 4 MIL polyethylene. They are not pressure sensitive. All legends are printed in black. Standard Package is 1 Roll.

Thomas & Betts


E-Z-Code®

Tape And Markers



Fast one step application of Self-Sticking HAZARDSTRIPE roll tapes save time and money over painting. Bold HAZARDSTRIPE tapes effectively warn of hazards, identify the protection equipment, traffic and housekeeping markings. All purpose tape, ideal for temporary hazards or markings. vinyl cloth HAZARDSTRIPE tapes are in 30 yard rolls.

Long-lasting, smooth laminated vinyl roll tape is ideal temporary or permanent marking. WPV tapes are available in 18 yard rolls. Made of reflective material for permanent, all weather performance. Light that is directed on WRM reflective tape is bounced back with amazing brilliance—up to 200 times greater reflection than white or yellow paint surfaces.



Each T&B WVP Rigid Vinyl Sign still comes with self-sticking mounting pads and drilled corner mounting holes. This tape is easy to use and provides maximum adhesion on most all smooth clean dry surfaces.

P

E-Z-code®

Self-Sticking Vinyl Cloth Tape

| Cat. No. 2" Wide | Cat. No. 3" Wide | Cat. No. 4" Wide | Color |
|---------------------|---------------------|---------------------|--|
| AZ-1100 | BZ-1100 | CZ-1100 | Black & Yellow Stripe |
| AZ-1102 | BZ-1102 | CZ-1102 | Red & White Stripe |
| AZ-1303 | BZ-1303 | CZ-1303 | Magenta and Yellow Stripe and Radiation Symbol |

Length each roll—30 yards

Self-Sticking Laminated Vinyl Tape

| Cat. No. 2" Wide | Cat. No. 3" Wide | Cat. No. 4" Wide | Color |
|---------------------|---------------------|---------------------|------------------------|
| AZ-2104 | BZ-2104 | CZ-2104 | Black & Yellow Stripes |
| AZ-2106 | BZ-2106 | CZ-2106 | Red & White Stripe |

Length each roll—18 yards

Self-Sticking Reflective Roll Tape

| Cat. No. 2" Wide | Cat. No. 3" Wide | Cat. No. 4" Wide | Color |
|---------------------|---------------------|---------------------|-----------------------|
| AZ-3108 | BZ-3108 | CZ-3108 | Black & Yellow Stripe |
| AZ-3110 | BZ-3110 | CZ-3110 | Red & White Stripe |

Length each roll—5 yards


Foam Mounting Tape—2 sided

| Cat. No. | Description |
|----------|--|
| NA-0365 | 2-Sided Foam Mounting Tape, length each roll—9 yards |

Thomas & Betts


E-Z-Code®

Customized Embossed Tags Stainless Steel Tape Embossing System



Identify your cable bundles with permanent, Type 304 stainless steel imprinted tags applied with stainless steel cable ties. After imprinting the tags, merely slip a tie through slots in the tag and fasten with the installation tool.

- Works with 1/4" wide ties.



For imprinting Thomas & Betts stainless steel I.D. tags. Includes special tag holder which provides quick, accurate positioning of tag. Comes with a 3/8" character imprinting wheel.



After making your tag, apply with stainless steel cable ties.

I.D. Tagging System

| Cat. No. | Width | | Length | | Weight | |
|----------|-------|-------|--------|----|--------|-----|
| | in. | mm | in. | mm | lbs. | kg. |
| SSID100 | .75 | 19.05 | 2.0 | 51 | 0.5 | .22 |
| SSID101 | 1.50 | 38.10 | 2.5 | 63 | 1.2 | .55 |
| SSID102 | .75 | 19.05 | 3.5 | 89 | 0.8 | .36 |

304 Stainless Steel

Packaging Quantity: 100/box

.015" (.254mm) Thickness

Note: Customized pre-embossed tags are available. Please consult Customer Service for details.

Add suffix (316) for 316 Stainless Steel.

I.D. Tag Imprinter

| Cat. No. | Description | Weight | |
|----------|----------------------------------|--------|-------|
| | | lbs. | kg. |
| WTID200 | I.D. Tag Imprinter | 29.5 | 13.41 |
| WTID281 | 1/8" character imprinting wheel | - | - |
| WTID283 | 3/16" character imprinting wheel | - | - |
| WTID290 | 3/8" character imprinting wheel | - | - |

Packaging Quantity: 1/box

S.S. Tape Embossing System

| Cat. No. | Description | Weight | |
|----------|---|--------|------|
| | | lbs. | kg. |
| WTID400 | Hand-held tool for embossing S.S. I.D. Tape | 2.57 | 1.17 |
| WTID405 | Replacement S.S. tape (21' long) | .18 | .01 |

304 Stainless Steel

Packaging Quantity: 1/box

Note: The embossing tool comes complete with two rolls of stainless steel tape.


P

E-Z-code®

Thomas & Betts

E-Z-Code®

Stainless Steel I.D. Tag



The Thomas & Betts Stainless Steel R.D. Tagging System includes a complete range of individual letters, numbers, and symbols—slip them over carriers (shown above) or strips (below) and attach to your cable or hose with a variety of Thomas & Betts Stainless Steel Cable Ties.



Thomas & Betts Stainless Steel I.D. Tag

| Cat. No. | Description | Length | Width | Std. Pkg. | Wt. per 100 |
|----------|--------------|--------|-------|-----------|-------------|
| ER010 | A | .445" | 375" | 100 | .31 |
| ER011 | B | .445" | 375" | 100 | .31 |
| ER012 | C | .445" | 375" | 100 | .31 |
| ER013 | D | .445" | 375" | 100 | .31 |
| ER014 | E | .445" | 375" | 100 | .31 |
| ER015 | F | .445" | 375" | 100 | .31 |
| ER016 | G | .445" | 375" | 100 | .31 |
| ER017 | H | .445" | 375" | 100 | .31 |
| ER018 | I | .445" | 375" | 100 | .31 |
| ER019 | J | .445" | 375" | 100 | .31 |
| ER020 | K | .445" | 375" | 100 | .31 |
| ER021 | L | .445" | 375" | 100 | .31 |
| ER022 | M | .445" | 375" | 100 | .31 |
| ER023 | N | .445" | 375" | 100 | .31 |
| ER024 | O | .445" | 375" | 100 | .31 |
| ER025 | P | .445" | 375" | 100 | .31 |
| ER026 | Q | .445" | 375" | 100 | .31 |
| ER027 | R | .445" | 375" | 100 | .31 |
| ER028 | S | .445" | 375" | 100 | .31 |
| ER029 | T | .445" | 375" | 100 | .31 |
| ER030 | U | .445" | 375" | 100 | .31 |
| ER031 | V | .445" | 375" | 100 | .31 |
| ER032 | W | .445" | 375" | 100 | .31 |
| ER033 | Y | .445" | 375" | 100 | .31 |
| ER034 | Z | .445" | 375" | 100 | .31 |
| ER018 | 1 | .445" | 375" | 100 | .31 |
| ER037 | 2 | .445" | 375" | 100 | .31 |
| ER038 | 3 | .445" | 375" | 100 | .31 |
| ER039 | 4 | .445" | 375" | 100 | .31 |
| ER040 | 5 | .445" | 375" | 100 | .31 |
| ER041 | 6 | .445" | 375" | 100 | .31 |
| ER021 | 7 | .445" | 375" | 100 | .31 |
| ER042 | 8 | .445" | 375" | 100 | .31 |
| ER041 | 9 | .445" | 375" | 100 | .31 |
| ER024 | 0 | .445" | 375" | 100 | .31 |
| ER035 | Minus/Hyphen | .445" | 375" | 100 | .31 |
| ER036 | Blank | .445" | 375" | 100 | .31 |
| ER046 | Plus + | .445" | 375" | 100 | .31 |
| ER047 | Earth | .445" | 375" | 100 | .31 |
| ER048 | Sine | .445" | 375" | 100 | .31 |
| ER049 | Slash / | .445" | 375" | 100 | .31 |

Character size .218"
Material .025 316 stainless steel

Thomas & Betts Stainless Steel I.D. Tag Strips/Carriers

| Cat. No. | Description | Length | Width | Std. Pkg. | Wt. per 100 |
|----------|----------------------|--------|-------|-----------|-------------|
| ER043 | 6 Character Carrier | 3.64" | .38" | 100 | .73 |
| ER044 | 10 Character Carrier | 5.14" | .38" | 100 | 1.25 |
| ER045 | 16 Character Carrier | 7.39" | .38" | 100 | 1.47 |
| ER050 | Short Strip | 4.25" | .38" | 100 | .98 |
| ER051 | Medium Strip | 5.75" | .38" | 100 | 1.33 |
| ER052 | Long Strip | 8.0" | .38" | 100 | 1.85 |
| ER060 | I.D. Tag Kit | — | — | 1 | — |


I.D. Tag Kit contains 50 of each letter, number, symbol, carrier and strip in a handy carrying case.

E-Z-Code®

PVC Sleeve and Clip-On Markers



The pre-printed sleeve wire markers permanently identify wires, cables, leads, harnesses, terminals, connectors and component parts to facilitate the installation, repair and servicing of equipment during production or maintenance. Sleeve markers are available in a variety of sizes and materials to meet all your needs—resistant to most chemicals, oils, solvents, fungus. Performs well in low and high temperatures.



Sleeve Markers

| Cat. No. | Recommended Wire Range | AWG | Standard Legends | Color | Package |
|----------|------------------------|-------|----------------------------|---------|-------------------------|
| SMS118* | .051-.118 | 22-16 | A-Z | | 10 strips of 25 markers |
| SMS196* | .098-.196 | 16-10 | | White | 10 strips of 25 markers |
| SMS394* | .157-.394 | 10-4 | 0-9 | w/Black | 10 strips of 25 markers |
| SMS630* | .315-.630 | 6-00 | / = SLA, + = PLS, = = GRD, | Legend | 20/Bag Loose |
| †SMS984* | .551-.984 | 0-350 | - = MIN and blank | | 20/Bag Loose |

* To Order: Add letter, number or symbol desired in place of asterisk to complete each Cat. No.

† Must be ordered as special item.

Other colors are available as specials. Contact customer service for availability.

Sleeve Markers

(1000 continuous on a reel)

| Cat. No. | Recommended Wire Range | AWG | Standard Legends | Color | Package |
|----------|------------------------|-------|---|---------|--------------|
| SMR118* | .051-.118 | 22-16 | A-Z | White | 1000 markers |
| SMR196* | .098-.196 | 16-10 | 0-9 | w/Black | continuous |
| SMR394* | .157-.394 | 10-4 | / = SLA, + = PLS, = = GRD, - = MIN and blank | Legend | on a reel |

* To Order: Add letter, number or symbol desired in place of asterisk to complete each Cat. No.

Clip-on Markers

| Cat. No. | Recommended Wire Range | AWG | Standard Legends | Color | Package |
|----------|------------------------|-------|-------------------|---------|------------------|
| SMC118* | .094-.118 | 18-16 | A-Z | White | 200/bag attached |
| SMC157* | .118-.157 | 16-14 | 0-9 | w/Black | 200/bag attached |
| SMC197* | .157-.197 | 12-10 | / = SLA, + = PLS, | Legend | 200/bag attached |
| SMC244* | .197-.244 | 8-6 | - = MIN and blank | | 200/bag attached |

* To Order: Add letter, number or symbol desired in place of asterisk to complete each Cat. No.

Magazine Dispenser Feeds Left or Right

| Cat. No. | Description | Recommended Wire Range | AWG | Legend | Color | Pkg. |
|------------|--|------------------------|-------|---------------------|--------------------------|------|
| SMPP196A | 20 Strips of 25 Markers | .098-.196 | 16-10 | 0-9 0-9 and tool | White w/ Black legend | 1 |
| SMPPT196A | 20 Strips of 25 Markers w/tool | .098-.196 | 16-10 | 0-9 0-9 | White w/ Black legend | 1 |
| SMPPCT196A | 21 Strips of Markers w/tool, assorted colors | .098-.196 | 16-10 | 0-9 0-9 | Assorted Colors | 1 |

Application tools

| Cat. No. | Description | Recommended Wire Range | AWG | Package |
|----------|------------------|------------------------|-------|---------|
| SMAT118 | Application Tool | .051-.118 | 22-16 | 5/bag |
| SMAT196 | Application Tool | .098-.196 | 16-10 | 5/bag |

Thomas & Betts

E-Z-Code®

Lockout/Tagout



Single Pole Circuit Breaker Lockout

'No Hole' Circuit Breaker Lockout device will lock out most single pole circuit breakers. Easy to install, provides secure locking protection. Device also available for 480/600 volt switches.



Multi Pole Circuit Breaker Lockout

Multi-Pole lockout works with most major multi-pole breakers with tie-bar. Very convenient because no self-locking tie or screwdriver is needed to install.



Plug Lockout

Designed for heavy duty applications, the Plug Lockout is an inexpensive way to safely lock out electrical plugs. Made of rugged polypropylene, the lockouts are available in two sizes: one to fit standard 110-volt grounded plugs and a larger size for 220- and 550-volt plugs.



Gate Valve Lockout

Make locking out valves safe and easy. Available in five sizes to fit valve handles from 1 to 13 inches in diameter. Made of durable, non-adherent plastic to resist chemicals and hot and cold temperatures. Stainless steel hinge design adds strength & security. Unique knockout feature accommodates OS&Y or 'rising stem' gate valves.



Cable Lockout

Flexible cable will lock out ALL sizes of gate valves & multiple disconnects in various energy distribution centers. Better than chains and just as effective, but a lot less weight. Great for security use too.



Standard Ball Valve Lockout

Fits all major brand ball valves. Simple one-piece design makes it easy to use.

E-Z Code® Lockout Devices

It is vitally important to control hazardous energy sources during servicing and maintenance of machines and equipment. The unexpected start up of the machines or equipment or release of stored energy could cause injury to employees. OSHA generally requires that energy sources for equipment be turned off or disconnected and that the switch either be locked or labeled with a warning tag. OSHA estimates compliance with the standard will prevent about 120 fatalities and approximately 28,000 serious and 32,000 minor injuries each year.



E-Z-Code offers an inclusive product line to supply the general requirements of the OSHA Lockout/Tagout standard. From comprehensive training videos to circuit breaker locking devices, E-Z-Code Lockout/Tagout products help insure that general industry workers will be protected from accidents during maintenance and servicing of equipment.

Three Steps for Compliance

OSHA: Lockout/Tagout standard (29 CFR 1910.147) requires that all energy sources be turned off and "locked out" while machines are being serviced or maintained. Compliance with this regulation requires three basic steps ...

Step 1: Develop a Written Program

This involves identifying and writing procedures for the control of hazardous energy. This also includes preparation for shutdown, equipment isolation, Lockout/Tagout application, release of stored energy and verification of energy isolation to each piece of equipment.

Step 2: Training Employees

Both affected and authorized employees must be trained in the specific energy control procedures established by the company. Verification of this training is required.

Step 3: Implement the Program

In addition to developing formal written procedures and training employees, T&B offers a variety of padlocks, tags, signs and lockout devices to help you implement lockout procedures for many different energy sources including: electricity, pneumatics, steam, gas, liquids, and many others.

E-Z-Code®

Lockout/Tagout



The Lockout Compliance Manual helps you format your written program.

Lockout Compliance Manual

This two volume compliance set contains samples that highlight what OSHA is looking for and demonstrates what you must do to comply with Lockout/Tagout regulations. It helps you format your written program and gets you started on compliance. Remember, not having a thorough, written energy control program is the most common violation cited by OSHA.

Hazardous Energy Control Manual

85-page manual includes:

- Step-by-step instructions for developing your Lockout/Tagout compliance program.
- Suggested training program including outlines, training notes and handout materials.

- Forms and checklists for developing your hazardous energy control procedures.
- Sample programs and procedures.
- Copy of OSHA Standard 29 CFR 1910.147.


Hazardous Energy Control Procedures

Includes:

- Sample programs and forms for completing your inventory listing, equipment procedures and employee training log.
- Three ring binder designed to contain your written program and related information.

Compliance Manuals

| Cat. No. | Description | Qty. |
|----------|--------------------------------------|--------|
| LO16-103 | Lockout/Tagout Manual and Procedures | 1/pkg. |




Learn from other worker's tragic mistakes in this dramatic Lockout for Life Video.

Lockout for Life (Video)


- Video analyzes real-life scenarios to demonstrate what went wrong and how following proper lockout procedures could have saved lives.
- Examines various elements of the Lockout/Tagout Standard and demonstrates effective lockout techniques.
- Motivational program appropriate for new and experienced employees – ideal for annual retraining program.
- Running time: 19 minutes.

Lockout Videos

| Cat. No. | Description | Qty. |
|----------|---------------------------------------|---------|
| LO16-300 | "Lockout For Life" Training Video | 1/pkg. |
| LO16-301 | "Controlling the Beast" Lockout Video | 1/pkg. |
| LO16-104 | Lockout Training Handbooks | 10/pkg. |



Lockout/Tagout: Controlling the Beast Video



Thomas & Betts

E-Z-Code®

Lockout/Tagout



E-Z-Code® Ball Valve Lockout Devices come in two sizes to lock out 1/4" to 1" and 1/4" to 3" ball valves.

Ball Valve Lockout Devices

- Best available method for locking out ball valves.
- Fits all major brand ball valves.
- Two new models accept 3/8" shackle padlocks.
- Simple one-piece design makes it easy to use.
- Assists in compliance with OSHA's Lockout Standard.

Ball Valve Lockout Device

| Cat. No. | Valve Size | Padlock Shackle Max. Diameter | Min. Padlock Shackle Clearance | Material |
|----------|------------|-------------------------------|--------------------------------|-------------------|
| LO16-403 | 1/4"-1" | 3/32" | 1" | Super Tough Nylon |
| LO16-406 | 1/4"-1" | 3/8" | 3/4" | Heavy Steel |
| LO16-404 | 1 1/4"-3" | 3/32" | 3/4" | Heavy Steel |
| LO16-405 | 1 1/4"-3" | 3/8" | 3/4" | Heavy Steel |



Fits various shaped ball valve handles, as well as Block, Stop, Butterfly and T-handle valves.

Universal Ball Valve Lockout Device

- Designed to lock out virtually any quarter turn valve – round, square or flat – and with odd shaped handles, straight or with angles.
- Accommodates handles up to 1 1/4" thick and 1 3/8" wide in almost any length.
- Unique design works with valves on insulated pipes.
- Constructed of durable nylon and steel materials making it strong, lightweight and resistant to most chemicals.

Valve Handle Maximum

| Cat. No. | Description | Thickness | Width |
|----------|---|-----------|--------|
| LO16-400 | Small Universal Ball Valve Lockout Device | 3/4" | 1" |
| LO16-401 | Large Universal Ball Valve Lockout Device | 1 1/4" | 1 3/8" |

P

E-Z-code®

Thomas & Betts

E-Z-Code®

Lockout/Tagout



Unique knockout feature can be removed by hand to accommodate OS&Y or "rising stem" gate valves.

Gate Valve Lockouts

- Makes locking out valves safe and easy.
- Available in five sizes to fit valve handles from 1" to 13" in diameter.
- Made of durable, non-adherent plastic to resist chemicals and hot and cold temperatures.
- Stainless steel hinge design for added strength and security.
- Available in red.
- Unique knockout feature accommodates OS&Y or "rising stem" gate valves.
- Service temperatures -20°F to 300°F.
- Designed to accept all locks with up to 3/8" shackle diameter and 3/4" or greater vertical shackle clearance.

Gate Valve Lockouts

| Cat. No. | Valve Handle Diameter |
|----------|-----------------------|
| LO16-420 | 1"-2½" |
| LO16-421 | 2½"-5" |
| LO16-422 | 5"-6½" |
| LO16-423 | 6½"-10" |
| LO16-424 | 10"-13" |



The Cable Lockout Device enables you to lock out several disconnects in various energy distribution centers.

Cable Lockout Device

- Flexible, cost-effective cable locks out gate valves of all sizes and may also be used to lock out multiple valves all with one device.
- Lighter than chains, device is easy to carry and easy to use.
- Ideal for security use as well.
- 6 ft. cable is made of galvanized steel and is 1/8" diameter.

| Cat. No. | Description |
|----------|----------------------|
| LO16-402 | Cable Lockout Device |



Cable Lockout device provides an easy and efficient method to lock out large gate valves.

P

E-Z-code®

Thomas & Betts

E-Z-Code®

Lockout/Tagout



Universal Multi-Pole Lockout works with most two or three pole breakers utilizing a tie-bar.

Circuit Breaker Lockout Devices

Universal Multi-Pole Breaker Lockout

- One multi-pole lockout works with most major multi-pole breakers with tie-bar.

- No self-locking tie needed.
- Applicable with GE, ITE, Sylvania, Challenger, Bryant, Westinghouse and General Switch Co.

| Cat. No. | Description | Qty. |
|----------|--------------------------------------|------|
| LO16-500 | Universal Multi-Pole Breaker Lockout | 5/pk |



Single Pole Circuit Breaker Lockout

Single Pole Circuit Breaker Lockout

- Locks out most major brand breaker switches (except Federal Pacific and most other 277 volt breakers).

- Simple design snaps onto breaker switch and accepts up to 3/2" shackle diameter lock or nylon tie.

| Cat. No. | Description | Qty. |
|----------|---------------------|------|
| LO16-501 | Single Pole Lockout | 5/pk |



Oversized Breaker Lockout Device

Oversized Breaker Lockout Device

- Oversized 480/600 volt frame lockout fits breakers up to 2 1/2" wide by 7/8" thick.

| Cat. No. | Description | Qty. |
|----------|---------------------------------|------|
| LO16-502 | Overize Circuit Breaker Lockout | 1/pk |



Covering a breaker with a piece of duct tape to "lock it out" isn't safe or effective and certainly doesn't satisfy OSHA. The E-Z-Code® "No Hole" Circuit Breaker Lockout Device gives you a new level of safety and compliance.

"No Hole" Circuit Breaker Lockout

- Enhanced device will lock out most single pole circuit breakers (including most Federal Pacific breakers).
- Easy to install.

- Provides secure locking protection.
- Accepts up to 3/2" shackle diameter lock.
- Fits wider and thicker tongue switches: 277- 1 3/20" wide by 23/50" thick; 480/600 - 1 3/8" wide by 1 1/20" thick.

| Cat. No. | Description | Qty. |
|----------|--|------|
| LO16-503 | Universal Small Pole Lockout 277 Volt No Hole | 5/pk |
| LO16-504 | Universal Breaker Lockout 480/600 Volt No Hole | 1/pk |



Step 1

Step 2

Step 3

Lockout Cleats

- Works in conjunction with "No Hole" Circuit Breaker Lockout (sold above).
- Assures positive lockout for those hard to lock out long sliding switch throws and switches with large

angular rotation commonly found with some Westinghouse, ITE, Square D and Federal Pacific breakers.

- Snap-on and off feature allows for use only when needed.

| Cat. No. | Description | Qty. |
|----------|--|------|
| LO16-510 | General Use Cleat 277 Volt No Hole | 5/pk |
| LO16-520 | Large General Use Cleat 480/600 Volt No Hole | 5/pk |

Thomas & Betts

E-Z-Code[®]

Lockout/Tagout



110 Volt, 220/250 Volt Plug Lockout

Electrical Lockout Devices

T&B Plug Lockout

- Designed for heavy-duty applications.
- Cost-effective way to safely lock out electrical plugs.
- Made of rugged polypropylene.
- Available in two sizes: one to fit standard 110-volt grounded plugs and a larger size for 220- and 550-volt plugs.

- Ideal for situations where plug is not under the exclusive control of the person performing the service or maintenance. Should maintenance personnel temporarily leave the area, device prevents anyone else from putting the plug back into the outlet.

| Cat. No. | Description | Qty. |
|----------|---------------------------|------|
| LO16-531 | 110 Volt Plug Lockout | 1/pk |
| LO16-532 | 220/550 Volt Plug Lockout | 1/pk |



Plug-Safe™

Plug-Safe™

- Safe and effective method for locking out electrical plugs.
- Made of durable plastic.
- Chemically resistant.
- Lockout size: 6" tall and 3½" diameter.
- Adjusts to lock out a variety of plug sizes.

- Ability to lock out a plug up to 3" wide and 5⅞" long with a maximum cord diameter of 1¼".
- Accepts standard locks up to ⅜" shackle diameter.
- Standard package: one device.

| Cat. No. | Description | Qty. |
|----------|-------------------------|------|
| LO16-530 | Electrical Plug Lockout | 1/pk |



Stoppower™

Stoppower™

- Ideal for office and other frequently locked out cords.
- Device slides over cord prongs and locks.

- Cord cannot be plugged in with Stoppower™ in place.
- Device cannot be removed without a key.

| Cat. No. | Description | Qty. |
|----------|-----------------|------|
| LO16-533 | Stoppower – Red | 1/pk |

P

E-Z-code[®]

E-Z-Code®

Lockout/Tagout



Wall Switch Lockout

Electrical Lockout Devices (continued)

Wall Switch Lockout

- Device may be used with most wall-mounted switches.
- Easy to install using existing screws.
- Locks switch in "on" or "off" position.

| Cat. No. | Description | Qty. |
|----------|---------------------|------|
| LO16-540 | Wall Switch Lockout | 5/pk |



Fuse Blockout Devices

Fuse Blockout Devices

- Unique locking mechanism prevents device from being accidentally removed from fuse block.
- Available in two sizes for most commonly used fuses.

| Cat. No. | Description | Qty. |
|----------|------------------------------------|------|
| LO16-552 | 1/4", 9/32", 13/32" & 9/16" Fuses | 5/pk |
| LO16-553 | 13/16", 1 1/16" & Blade Type Fuses | 5/pk |

E-Z-Code®

Lockout/Tagout



Using T&B's Pneumatic Quick-Disconnect Lockout to isolate pneumatic energy provides worker safety in lock out situations.

Pneumatic Lockout Devices

Pneumatic Quick-Disconnect Lockout

- Isolates pneumatic energy without the expense and inconvenience of installing in-line lockout valves.
- Device is applied to the male fitting, isolating equipment from all compressed air sources.

- With a "glove fit," lockout meets OSHA standards and accommodates the majority of 1/4", 3/8" and 1/2" male fittings.
- Center of device allows for permanent storage on an air hose and a loop on the side can be used to hang the hose and lockout device.
- Lockout using a padlock with 1/4" or 3/8" shackle.

| Cat. No. | Description | Qty. |
|----------|-------------------|-------|
| LO16-600 | Pneumatic Lockout | 5/pkg |



Lockout Tool Box with Components

Lockout Kits

Lockout Tool Box With Components

- Everything you need to lock and mark your equipment and prevent its use until repairs have been completed.
- Kit contains: 1 - Plastic Lockout Tool Box w/Tray; 1 - 1" to 2 1/2" Gate Valve Lockout; 1 - Small Ball Valve Lockout; 1 - 3/4" Blue Padlock; 1 - 2" Blue

- Padlock; 1 - Labeled Lockout Hasp; 5 - Lockout Tags; 1 - Universal Multi-Pole Lockout; 1 - 277 Volt "No Hole" Lockout; 1 - 480/600 Volt "No Hole" Lockout; 1 - Wall Switch Lockout; 1 - Small E-Z-Code® Plug Lockout.
- Toolbox also sold individually.

| Cat. No. | Description | Qty. |
|----------|--------------------------------------|-------|
| LO16-770 | Lockout Tool Box Kit with Components | 1/pkg |
| LO16-700 | Lockout Tool Box | 1/pkg |



Electrical Lockout Starter Kit

Electrical Lockout Pouch

- Lightweight, portable pouch contains lockout devices to secure electrical equipment.
- Metal loops on pouch for hanging on a belt.
- Pouch kit contains: pouch, (1) 2" blue padlock, (1) labeled lockout hasp, (2)

- heavy duty lockout tags, (1) 277" "no hole" breaker lockout, (1) universal multi-pole lockout, (1) small plug lockout.
- Pouch made of heavy duty nylon. 4 3/4"H, 7 1/2"W, 2"D.

| Cat. No. | Description | Qty. |
|----------|------------------------|-------|
| LO16-710 | Electrical Lockout Kit | 1/pkg |

E-Z-Code®

Lockout/Tagout



E-Z-Code®'s high visibility Lockout Stations make your locks, tags and lockouts easy to find and use. Built for the toughest conditions, Lockout Stations are made of durable plastic material.

Lockout Stations

Four Lock Station

- Station with components.
- Components include: 4 blue bumper padlocks; 25 "Do Not Operate" tags; and three 1" safety lockouts.
- Station size: 8" x 12".
- Station also sold individually.

| Cat. No. | Description | Qty. |
|----------|--------------------------------|-------|
| LO16-760 | 4 Lock Station with Components | 1/pkg |
| LO16-750 | 4 Lock Station Only | |

Ten Lock Station

- Station with components.
- Components include: 10 blue bumper padlocks; 25 "Do Not Operate" tags; and three 1" safety lockouts.
- Station size: 19" x 12".
- Station also sold individually.

| Cat. No. | Description | Qty. |
|----------|---------------------------------|-------|
| LO16-740 | 10 Lock Station with Components | 1/pkg |
| LO16-730 | 10 Lock Station Only | |



13 Lock Group Lock Box

13 Lock Group Lock Box

- Simplifies lockout of large equipment.
- After machine or process is locked out, the key or keys are placed in a lock box. Then, each authorized work team member places a personal lock or tagout device in the group lock box.
- Ensures that no one employee has access to the box unless ALL employees have removed their locks or tags.
- Accepts up to 13 individual locks.
- Heavy steel construction.

| Cat. No. | Description | Qty. |
|----------|------------------------|-------|
| LO16-811 | 13 Lock Group Lock Box | 1/pkg |

P

E-Z-code®

E-Z-Code[®]

Lockout/Tagout



High security #3 Master Lock Padlocks are an ideal size for lockout applications.



- Allows up to six workers to lock out a single energy source.
- Constructed of vinyl-coated high tensile steel.
- Plated to resist rust.



- Allows up to six workers to lock out a piece of equipment and begin servicing it.
- Up to 5 additional employees can affix their locks and tags to the Labeled Lockout Hasps to assist in the servicing operation.
- Hasp size 7¼ x 3 x ¾.
- Constructed from tough 5052 anodized aluminum alloy.

Padlocks

Master Lock Padlocks

- Constructed of rustproofed steel case and nickel-plated shackle.
- Locks are 1½" wide with ½" shackle diameter.
- Pair of brass keys included with each lock.
- Available in six different colored bumpers to provide easy visual identification by department or work team.
- Key numbers are ink-stamped on the bottom of the lock for easy lock/key identification.
- Standard package: 6 locks.

| Cat. No. | Description | Qty. |
|----------|---------------------------|------|
| LO16-900 | ¾" Blue Bumper Pad Lock | 6 |
| LO16-901 | ¾" Black Bumper Pad Lock | 6 |
| LO16-902 | ¾" White Bumper Pad Lock | 6 |
| LO16-903 | ¾" Red Bumper Pad Lock | 6 |
| LO16-904 | ¾" Green Bumper Pad Lock | 6 |
| LO16-905 | ¾" Yellow Bumper Pad Lock | 6 |
| LO16-906 | 2" Blue Bumper Pad Lock | 6 |
| LO16-907 | 2" Black Bumper Pad Lock | 6 |
| LO16-908 | 2" White Bumper Pad Lock | 6 |
| LO16-909 | 2" Red Bumper Pad Lock | 6 |
| LO16-910 | 2" Green Bumper Pad Lock | 6 |
| LO16-911 | 2" Yellow Bumper Pad Lock | 6 |

Hasps

| Cat. No. | Size | Qty. |
|----------|------|-------|
| LO16-800 | 1" | 12/pk |
| LO16-801 | 1.5" | 12/pk |

Labeled Lockout Hasp

| Cat. No. | Size | Qty. |
|----------|------|------|
| LO16-810 | - | 5/pk |

E-Z-Code® Lockout/Tagout

Durable Lockout Tags

OSHA requirements for Lockout Tags are very specific, and E-Z-Code® Lockout Tags have been designed to comply with every performance standard. Tags are available in two sturdy materials: reusable dura-tag and economical vinyl. All tags have a reinforcing brass grommet 7/16" diameter to accept most padlocks. All tag surfaces allow employees to easily personalize tags with their name, department and estimated completion information as required by regulations.



Reusable Dura-Tag

Durable, plastic tags are encapsulated in matte polyester laminate. Tag meets OSHA 50 lb. pull requirement. These tags are designed for harsh plant environments and are chemically resistant. Supplied with heavy duty 3/8" ID brass grommet and nylon ties. Matte finish accepts pencil, pen and marker. 25/pkg.

Economy Polyester

Rigid polyester surface is easy to write on and stays legible longer. Wipes clean easily, ready to use again and again. Exceeds OSHA 50 pound pull-out requirement. 25/pkg.

Lockout/Tagout Tags

| Lockout/Tagout Tags | | | |
|--|------------------------|--|------------------------|
| | | | |
| Reusable Dura-Tag | | | |
| TG65502 - Rev. Side #1 TG65670 - Rev. Side #2 | TG65503 - Rev. Side #1 | TG65504 - Rev. Side #1 | TG65505 - Rev. Side #1 |
| Economy Polyester | | | |
| TG66050 - Rev. Side #1 TG66052 - Rev. Side #2 | TG66053 - Rev. Side #1 | TG66055 - Rev. Side #1 | TG66057 - Rev. Side #1 |
| | | | |
| Reusable Dura-Tag | | | |
| TG65506 - Rev. Side #1 | TG65515 - Rev. Side #1 | TG65520 - Rev. Side #1 TG65671 - Rev. Side #2 | TG65526 - Rev. Side #1 |
| Economy Polyester | | | |
| TG66059 - Rev. Side #1 | TG66061 - Rev. Side #1 | TG66063 - Rev. Side #1 TG66065 - Rev. Side #2 | TG66066 - Rev. Side #1 |

Reverse Side Options



Reverse Side #1



Reverse Side #2

How to Order

Choose tag & material, order by part number for reverse side wanted.

E-Z-Code® Dura-Tag and economy polyester Lockout Tags exceed OSHA's 50 lb. pullout requirement. All tags have write-on surfaces and come in packages of 25 tags.

| Description | Size | Grommet |
|-------------------|-------------|-------------|
| Reusable Dura-Tag | 5 1/2" x 3" | 7/16" Brass |
| Economy Polyester | 5 3/4" x 3" | 3/8" Brass |

E-Z-Code®

Accident Prevention Tags

There's an E-Z-Code® tag for every application and budget.

Reusable Dura-Tag

Durable, plastic tags are encapsulated in matte polyester laminate. Tag meets OSHA 50 lb. pull requirement. These tags are designed for harsh plant environments and are chemically resistant. Supplied with heavy duty 3/8" ID brass grommet and nylon ties. Matte finish accepts pencil, pen and marker. 25/pkg.

Economy Polyester

Chemically resistant polyester tag meets OSHA's 50 lb. pull requirement. Supplied with 3/8" ID metal grommet and nylon ties. 25/pkg.

Cardstock

Economical yet durable cardstock. These disposable tags come with a 3/8" grommet. 100/pkg.


| Description | Size | Grommet |
|-------------------|-------------|---------|
| Reusable Dura-Tag | 5 3/4" x 3" | 3/8" |
| Economy Polyester | 5 3/4" x 3" | 3/8" |
| Card Stock Tags | 5 3/4" x 3" | 3/8" |

Accident Prevention Tags



| Reusable Dura-Tag | | | | |
|-----------------------|-----------------------|-----------------------|---------------------|---------------------|
| TG86425 - Rev. Side 1 | TG86424 - Rev. Side 1 | TG86414 - Rev. Side 1 | TG86416 - Same Back | TG86417 - Same Back |
| Economy Polyester | | | | |
| TG86544 - Rev. Side 1 | TG86543 - Rev. Side 1 | TG86533 - Rev. Side 1 | TG86535 - Same Back | TG86536 - Same Back |
| Cardstock Tags | | | | |
| TG86654 - Rev. Side 1 | TG86653 - Rev. Side 1 | TG86643 - Rev. Side 1 | TG86645 - Same Back | TG86646 - Same Back |

Reusable Dura-Tag



| Reusable Dura-Tag | | | |
|-----------------------|---------------------|---------------------|---------------------|
| TG86418 - Rev. Side 1 | TG86442 - Same Back | TG86454 - Same Back | TG86438 - Same Back |
| Economy Polyester | | | |
| TG86537 - Rev. Side 1 | TG86556 - Same Back | TG86574 - Same Back | TG86565 - Same Back |
| Cardstock Tags | | | |
| TG86647 - Rev. Side 1 | TG86666 - Same Back | TG86684 - Same Back | TG86675 - Same Back |



Reverse Side 1
(For Caution Tags)



Reverse Side 1
(For Danger Tags)

E-Z-Code®

Transformer Safety Labels

Fig. 1



Fig. 2

Designed to keep children away from switchgear and transformers.
 Made of WPM pressure sensitive destructible vinyl film, making one piece removal virtually impossible.
 These labels meet both NEMA and Underwriters Laboratory applicable standards.

Choose from four visual warning legends for use on machines and other equipment.

“Mr. Ouch” Nema Safety Labels

| Cat. No. | Legend | Fig. | Nema Label Size |
|----------|---------------------|------|-----------------|
| WUT-0366 | WARNING | 2 | 4½" x 8" |
| WUT-0367 | DANGER | 1 | 4½" x 8" |
| WUT-0368 | WARNING (Bilingual) | 4 | 5" x 10½" |
| WUT-0369 | DANGER (Bilingual) | 3 | 5" x 10½" |

Standard package quantity 5 labels.




Fig. 3





Fig. 4

Magnetic Signs



| Cat. No. | Label Size | Cat. No. | Label Size | Cat. No. | Label Size | Cat. No. | Label Size |
|----------|------------|----------|------------|----------|------------|----------|------------|
| MG66002 | 5" x 3½" | MG66004 | 5" x 3½" | MG66006 | 5" x 3½" | MG66008 | 5" x 3½" |
| MG66003 | 7" x 5" | MG66005 | 7" x 5" | MG66007 | 7" x 5" | MG66009 | 7" x 5" |

P

E-Z-code®

Thomas & Betts




Fig. 1



Fig. 2



Fig. 3



Vinyl Pressure Sensitive Accident Prevention Cards

| Cat. No. | Figure | Legend | Color | Size |
|----------------------|--------|---|--------------------------------------|----------------------|
| WJA-1100 WQA-1100 | 1 | DANGER | White letters in a red oval on black | 2¼" x 9" 5" x 14" |
| WJA-0076 WQA-0076 | 2 | HIGH VOLTAGE | Red on white | 2¼" x 9" 5" x 14" |
| WHF-0076 | 3 | DANGER HIGH VOLTAGE | Red and black on white | 2 per Card |
| LB86871 | 4 | DANGER HIGH VOLTAGE | Red and black on white | 3.5 x 5 |
| LB86860 | 5 | DANGER HIGH VOLTAGE | Red and black on white | 3.5 x 5 |
| LB86234 | 6 | DANGER HIGH VOLTAGE PELIGRO ALTO VOLTAJE | Red and black on white | 3.5 x 5 |
| LB86235 | 7 | DANGER HIGH VOLTAGE PELIGRO ALTO VOLTAJE | Red and black on white | 3.5 x 5 |
| LB86877 | 8 | DANGER HIGH VOLTAGE | Red and black on white | 3.5 x 5 |
| LB86861 | 9 | DANGER HIGH VOLTAGE | Red and black on white | 3.5 x 5 |
| LB86245 | 10 | LOCKOUT HERE | Red and black on white | 3.5 x 5 |
| LB86204 | 11 | LOCKOUT POINT | Red and black on white | 3.5 x 5 |
| LB86248 | 12 | REMEMBER LOCKOUT ALL POWER SOURCES | Red and black on white | 3.5 x 5 |
| LB86250 | 13 | REMEMBER LOCK, TAG, CLEAR, TRY | Red and black on white | 3.5 x 5 |
| LB94913 LB94914 | 14 | WARNING ARC FLASH AND SHOCK | Orange and black on white | 3.5" x 5" 5" x 7" |

Order by cards. Standard package 5 identical cards per poly bag.



LB86871
Fig. 4



LB86860
Fig. 5



LB86234
Fig. 6



LB86235
Fig. 7



LB86877
Fig. 8



LB86861
Fig. 9



LB86245
Fig. 10



LB86204
Fig. 11



LB86248
Fig. 12



LB86250
Fig. 13



New 2002 National Electric Code Requirement
110.16 Flash Protection

The new requirement is intended to reduce the occurrence of serious injury or death due to arcing faults to workers who work on or near energized electrical equipment. The warning label should remind a qualified worker who intends to open the equipment for analysis or work that a serious hazard exists and that the worker should follow appropriate work practices and wear appropriate personal protection equipment (PPE) for the specific hazard.



Electrical Hazard Safety Signs



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP84827 | SS | 7x10 |
| BP84828 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP84843 | SS | 7x10 |
| BP84844 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43089 | AL | 7x10 |
| BP43090 | AL | 10x14 |
| BP25512 | PL | 7x10 |
| BP25513 | PL | 10x14 |
| BP84847 | SS | 7x10 |
| BP84848 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP84859 | SS | 7x10 |
| BP84860 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43101 | AL | 7x10 |
| BP43102 | AL | 10x14 |
| BP25524 | PL | 7x10 |
| BP25525 | PL | 10x14 |
| BP84863 | SS | 7x10 |
| BP84864 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40657 | AL | 7x10 |
| BP40658 | AL | 10x14 |
| BP22093 | PL | 7x10 |
| BP22094 | PL | 10x14 |
| BP84068 | SS | 7x10 |
| BP84069 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40655 | AL | 7x10 |
| BP40656 | AL | 10x14 |
| BP22091 | PL | 7x10 |
| BP22092 | PL | 10x14 |
| BP84066 | SS | 7x10 |
| BP84067 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43109 | AL | 7x10 |
| BP43110 | AL | 10x14 |
| BP25532 | PL | 7x10 |
| BP25533 | PL | 10x14 |
| BP84876 | SS | 7x10 |
| BP84877 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43477 | AL | 10x14 |
| BP25900 | PL | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43115 | AL | 7x10 |
| BP43116 | AL | 10x14 |
| BP25538 | PL | 7x10 |
| BP25539 | PL | 10x14 |
| BP84882 | SS | 7x10 |
| BP84883 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43117 | AL | 7x10 |
| BP43118 | AL | 10x14 |
| BP25540 | PL | 7x10 |
| BP25541 | PL | 10x14 |
| BP84886 | SS | 7x10 |
| BP84887 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43119 | AL | 7x10 |
| BP43120 | AL | 10x14 |
| BP25542 | PL | 7x10 |
| BP25543 | PL | 10x14 |
| BP84888 | SS | 7x10 |
| BP84889 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40667 | AL | 7x10 |
| BP40668 | AL | 10x14 |
| BP22103 | PL | 7x10 |
| BP22104 | PL | 10x14 |
| BP84083 | SS | 7x10 |
| BP84084 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40669 | AL | 7x10 |
| BP40670 | AL | 10x14 |
| BP22105 | PL | 7x10 |
| BP22106 | PL | 10x14 |
| BP84085 | SS | 7x10 |
| BP84086 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43129 | AL | 7x10 |
| BP43130 | AL | 10x14 |
| BP25552 | PL | 7x10 |
| BP25553 | PL | 10x14 |
| BP84903 | SS | 7x10 |
| BP84904 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40675 | AL | 7x10 |
| BP40676 | AL | 10x14 |
| BP22111 | PL | 7x10 |
| BP22112 | PL | 10x14 |
| BP84095 | SS | 7x10 |
| BP84093 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40691 | AL | 7x10 |
| BP40692 | AL | 10x14 |
| BP22127 | PL | 7x10 |
| BP22128 | PL | 10x14 |
| BP84113 | SS | 7x10 |
| BP84114 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43141 | AL | 7x10 |
| BP43142 | AL | 10x14 |
| BP25564 | PL | 7x10 |
| BP25565 | PL | 10x14 |
| BP84927 | SS | 7x10 |
| BP84928 | SS | 10x14 |




| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43143 | AL | 7x10 |
| BP43144 | AL | 10x14 |
| BP25566 | PL | 7x10 |
| BP25567 | PL | 10x14 |
| BP84929 | SS | 7x10 |
| BP84930 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43145 | AL | 7x10 |
| BP43146 | AL | 10x14 |
| BP25568 | PL | 7x10 |
| BP25569 | PL | 10x14 |
| BP84933 | SS | 7x10 |
| BP84934 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40761 | AL | 7x10 |
| BP40762 | AL | 10x14 |
| BP22197 | PL | 7x10 |
| BP22198 | PL | 10x14 |
| BP84197 | SS | 7x10 |
| BP84198 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41126 | AL | 7x10 |
| BP41127 | AL | 10x14 |
| BP22562 | PL | 7x10 |
| BP22563 | PL | 10x14 |
| BP84941 | SS | 7x10 |
| BP84942 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41128 | AL | 7x10 |
| BP41129 | AL | 10x14 |
| BP22564 | PL | 7x10 |
| BP22565 | PL | 10x14 |
| BP84943 | SS | 7x10 |
| BP84944 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP84937 | SS | 7x10 |
| BP84938 | SS | 10x14 |

E-Z-code®



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42739 | AL | 10x14 |
| BP25162 | PL | 10x14 |
| BP89153 | SS | 3x3 |
| BP88497 | SS | 10x10 |




| Cat No. | Mat. | Size |
|---------|------|------|
| BP89152 | SS | 3x3 |




| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42740 | AL | 10x14 |
| BP25163 | PL | 10x14 |
| BP88498 | SS | 10x10 |



| Cat No. | Mat. | Size |
|---------|------|------|
| BP42753 | AL | 7x10 |
| BP25176 | PL | 7x10 |
| BP88512 | SS | 7x7 |



| Cat No. | Mat. | Size |
|---------|------|--------|
| BP84949 | SS | 3.5x10 |



| Cat No. | Mat. | Size |
|---------|------|--------|
| BP84963 | SS | 3.5x10 |

AL - Aluminum
5-8 yr durability
PL - Plastic
1-2 yr durability
SS - Self Sticking
5-8 yr durability

Electrical Hazard Safety Signs



New 2002 National Electric Code Requirement 110.16 Flash Protection

The new requirement is intended to reduce the occurrence of serious injury or death due to arcing faults to workers who work on or near energized electrical equipment. The warning label should remind a qualified worker who intends to open the equipment for analysis or work that a serious hazard exists and that the worker should follow appropriate work practices and wear appropriate personal protection equipment (PPE) for the specific hazard.



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42560 | AL | 7x10 |
| BP42561 | AL | 10x14 |
| BP23037 | PL | 7x10 |
| BP23038 | PL | 10x14 |
| BP88183 | SS | 7x10 |
| BP88184 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42564 | AL | 7x10 |
| BP42565 | AL | 10x14 |
| BP23041 | PL | 7x10 |
| BP23042 | PL | 10x14 |
| BP88187 | SS | 7x10 |
| BP88188 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42584 | AL | 7x10 |
| BP42585 | AL | 10x14 |
| BP23061 | PL | 7x10 |
| BP23062 | PL | 10x14 |
| BP88217 | SS | 7x10 |
| BP88218 | SS | 10x14 |

Vinyl Pressure Sensitive Accident Prevention Cards

| Cat. No. | Legend | Color | Size |
|----------|-----------------|---------------------------|-----------|
| LB94915 | WARNING ARC | Orange and black on white | 7" x 10" |
| LB94916 | FLASH AND SHOCK | | 10" x 14" |

Order by cards. Standard package 5 identical cards per poly bag.

Chemical & Hazardous Material




| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43237 | AL | 7x10 |
| BP43238 | AL | 10x14 |
| BP25660 | PL | 7x10 |
| BP25661 | PL | 10x14 |
| BP85175 | SS | 7x10 |
| BP85176 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40988 | AL | 7x10 |
| BP40989 | AL | 10x14 |
| BP22424 | PL | 7x10 |
| BP22425 | PL | 10x14 |
| BP84562 | SS | 7x10 |
| BP84563 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43517 | AL | 7x10 |
| BP43518 | AL | 10x14 |
| BP25920 | PL | 7x10 |
| BP25921 | PL | 10x14 |
| BP65950 | SS | 7x10 |
| BP65949 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43005 | AL | 7x10 |
| BP43006 | AL | 10x14 |
| BP25428 | PL | 7x10 |
| BP25429 | PL | 10x14 |
| BP84375 | SS | 7x10 |
| BP84376 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43319 | AL | 7x10 |
| BP43320 | AL | 10x14 |
| BP25742 | PL | 7x10 |
| BP25743 | PL | 10x14 |
| BP85553 | SS | 7x10 |
| BP85554 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40875 | AL | 7x10 |
| BP40876 | AL | 10x14 |
| BP22311 | PL | 7x10 |
| BP22312 | PL | 10x14 |
| BP84351 | SS | 7x10 |
| BP84352 | SS | 10x14 |

First Aid



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41225 | AL | 7x10 |
| BP41226 | AL | 10x14 |
| BP22661 | PL | 7x10 |
| BP22662 | PL | 10x14 |
| BP85349 | SS | 7x10 |
| BP85350 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41229 | AL | 7x10 |
| BP22665 | PL | 7x10 |
| BP85354 | SS | 7x10 |
| BP85355 | SS | 10x14 |

Fire Extinguisher



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43294 | AL | 14x10 |
| BP25717 | PL | 14x10 |
| BP86091 | SS | 14x10 |



| Cat No. | Mat. | Size |
|---------|------|--------|
| BP43295 | AL | 10x7 |
| BP25718 | PL | 10x7 |
| BP85261 | SS | 14x3.5 |

Handicap



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP91370 | SS | 14x10 |

AL - Aluminum
5-8 yr durability
PL - Plastic
1-2 yr durability
SS - Self Sticking
5-8 yr durability

E-Z-Code®

Safety Signs

No Smoking



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42653 | AL | 7x10 |
| BP42654 | AL | 10x14 |
| BP25076 | PL | 7x10 |
| BP25077 | PL | 10x14 |
| BP88370 | SS | 7x10 |
| BP88371 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42696 | AL | 10x7 |
| BP42697 | AL | 14x10 |
| BP25119 | PL | 10x7 |
| BP25120 | PL | 14x10 |
| BP88427 | SS | 10x7 |
| BP88428 | SS | 14x10 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42694 | AL | 7x10 |
| BP42695 | AL | 10x14 |
| BP25117 | PL | 7x10 |
| BP25118 | PL | 10x14 |
| BP88425 | SS | 7x10 |
| BP88426 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42711 | AL | 7x10 |
| BP42712 | AL | 10x14 |
| BP25134 | PL | 7x10 |
| BP25135 | PL | 10x14 |
| BP88451 | SS | 7x10 |
| BP88452 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42659 | AL | 7x10 |
| BP42660 | AL | 10x14 |
| BP25082 | PL | 7x10 |
| BP25083 | PL | 10x14 |
| BP88378 | SS | 7x10 |
| BP88379 | SS | 10x14 |

Sign Blanks



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42933 | AL | 7x10 |
| BP42934 | AL | 10x14 |
| BP25356 | PL | 7x10 |
| BP25357 | PL | 10x14 |
| BP88918 | SS | 7x10 |
| BP88919 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42937 | AL | 7x10 |
| BP42938 | AL | 10x14 |
| BP25360 | PL | 7x10 |
| BP25361 | PL | 10x14 |
| BP88925 | SS | 7x10 |
| BP88926 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42941 | AL | 7x10 |
| BP42942 | AL | 10x14 |
| BP25364 | PL | 7x10 |
| BP25365 | PL | 10x14 |
| BP88932 | SS | 7x10 |
| BP88933 | SS | 10x14 |

AL - Aluminum
5-8 yr durability
PL - Plastic
1-2 yr durability
SS - Self Sticking
5-8 yr durability

Lockout



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42454 | AL | 10x7 |
| BP42455 | AL | 14x10 |
| BP22931 | PL | 10x7 |
| BP22932 | PL | 14x10 |
| BP85892 | SS | 10x7 |
| BP85893 | SS | 14x10 |




| Cat No. | Mat. | Size |
|---------|------|----------|
| BP88302 | SS | 2.25x4.5 |



| Cat No. | Mat. | Size |
|---------|------|----------|
| BP88304 | SS | 2.25x4.5 |



| Cat No. | Mat. | Size |
|---------|------|----------|
| BP88316 | SS | 2.25x4.5 |



| Cat No. | Mat. | Size |
|---------|------|----------|
| BP88320 | SS | 2.25x4.5 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43089 | AL | 7x10 |
| BP43090 | AL | 10x14 |
| BP25512 | PL | 7x10 |
| BP25513 | PL | 10x14 |
| BP84847 | SS | 7x10 |
| BP84848 | SS | 10x14 |

AL - Aluminum
5-8 yr durability
PL - Plastic
1-2 yr durability
SS - Self Sticking
5-8 yr durability

Personal Protection



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42402 | AL | 7x10 |
| BP42403 | AL | 10x14 |
| BP22879 | PL | 7x10 |
| BP22880 | PL | 10x14 |
| BP85797 | SS | 7x10 |
| BP85798 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40969 | AL | 7x10 |
| BP40970 | AL | 10x14 |
| BP22405 | PL | 7x10 |
| BP22406 | PL | 10x14 |
| BP84535 | SS | 7x10 |
| BP84536 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42440 | AL | 7x10 |
| BP42441 | AL | 10x14 |
| BP22917 | PL | 7x10 |
| BP22918 | PL | 10x14 |
| BP85858 | SS | 7x10 |
| BP85859 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41336 | AL | 7x10 |
| BP41337 | AL | 10x14 |
| BP22772 | PL | 7x10 |
| BP22773 | PL | 10x14 |
| BP85598 | SS | 7x10 |
| BP85599 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42627 | AL | 7x10 |
| BP42628 | AL | 10x14 |
| BP25050 | PL | 7x10 |
| BP25051 | PL | 10x14 |
| BP88310 | SS | 7x10 |
| BP88311 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42484 | AL | 7x10 |
| BP42485 | AL | 10x14 |
| BP22961 | PL | 7x10 |
| BP22962 | PL | 10x14 |
| BP85957 | SS | 7x10 |
| BP85958 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43041 | AL | 7x10 |
| BP43042 | AL | 10x14 |
| BP25464 | PL | 7x10 |
| BP25465 | PL | 10x14 |
| BP84784 | SS | 7x10 |
| BP84785 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40971 | AL | 7x10 |
| BP40972 | AL | 10x14 |
| BP22407 | PL | 7x10 |
| BP22408 | PL | 10x14 |
| BP84537 | SS | 7x10 |
| BP84538 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40963 | AL | 7x10 |
| BP40964 | AL | 10x14 |
| BP22399 | PL | 7x10 |
| BP22400 | PL | 10x14 |
| BP84529 | SS | 7x10 |
| BP84530 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41190 | AL | 7x10 |
| BP41191 | AL | 10x14 |
| BP22626 | PL | 7x10 |
| BP22627 | PL | 10x14 |
| BP85035 | SS | 7x10 |
| BP85036 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40967 | AL | 7x10 |
| BP40968 | AL | 10x14 |
| BP22403 | PL | 7x10 |
| BP22404 | PL | 10x14 |
| BP84533 | SS | 7x10 |
| BP84534 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42506 | AL | 7x10 |
| BP42507 | AL | 10x14 |
| BP22983 | PL | 7x10 |
| BP22984 | PL | 10x14 |
| BP88101 | SS | 7x10 |
| BP88102 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42508 | AL | 7x10 |
| BP42509 | AL | 10x14 |
| BP22985 | PL | 7x10 |
| BP22986 | PL | 10x14 |
| BP88107 | SS | 7x10 |
| BP88108 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP42562 | AL | 7x10 |
| BP42563 | AL | 10x14 |
| BP23039 | PL | 7x10 |
| BP23040 | PL | 10x14 |
| BP88185 | SS | 7x10 |
| BP88186 | SS | 10x14 |

Admittance and Exit



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40623 | AL | 7x10 |
| BP40624 | AL | 10x14 |
| BP22059 | PL | 7x10 |
| BP22060 | PL | 10x14 |
| BP84008 | SS | 7x10 |
| BP84009 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40997 | AL | 7x10 |
| BP40998 | AL | 10x14 |
| BP22433 | PL | 7x10 |
| BP22434 | PL | 10x14 |
| BP84571 | SS | 7x10 |
| BP84572 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40705 | AL | 7x10 |
| BP40706 | AL | 10x14 |
| BP22141 | PL | 7x10 |
| BP22142 | PL | 10x14 |
| BP84129 | SS | 7x10 |
| BP84130 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40707 | AL | 7x10 |
| BP40708 | AL | 10x14 |
| BP22143 | PL | 7x10 |
| BP22144 | PL | 10x14 |
| BP84131 | SS | 7x10 |
| BP84132 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40727 | AL | 7x10 |
| BP40728 | AL | 10x14 |
| BP22163 | PL | 7x10 |
| BP22164 | PL | 10x14 |
| BP84155 | SS | 7x10 |
| BP84156 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP40753 | AL | 7x10 |
| BP40754 | AL | 10x14 |
| BP22189 | PL | 7x10 |
| BP22190 | PL | 10x14 |
| BP84187 | SS | 7x10 |
| BP84188 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41053 | AL | 7x10 |
| BP41054 | AL | 10x14 |
| BP22489 | PL | 7x10 |
| BP22490 | PL | 10x14 |
| BP84673 | SS | 7x10 |
| BP84674 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP43338 | AL | 7x10 |
| BP43339 | AL | 10x14 |
| BP25761 | PL | 7x10 |
| BP25762 | PL | 10x14 |
| BP84617 | SS | 7x10 |
| BP84618 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41065 | AL | 7x10 |
| BP41066 | AL | 10x14 |
| BP22501 | PL | 7x10 |
| BP22502 | PL | 10x14 |
| BP84687 | SS | 7x10 |
| BP84688 | SS | 10x14 |



| Cat No. | Mat. | Size |
|---------|------|-------|
| BP41101 | AL | 7x10 |
| BP41102 | AL | 10x14 |
| BP22537 | PL | 7x10 |
| BP22538 | PL | 10x14 |
| BP84732 | SS | 7x10 |
| BP84733 | SS | 10x14 |

AL - Aluminum
5-8 yr durability

PL - Plastic
1-2 yr durability

SS - Self Sticking
5-8 yr durability

E-Z-Code®

Custom Sign Express Order Form

This Custom Sign Order Form is for the convenience of you and your authorized Thomas & Betts Distributor. To help expedite your order, please copy the order form and use a separate form to order signs that require different legends, different sizes, different headers or different materials.



**Fax your order to:
901-252-1321**

Materials (Check appropriate material)

| Material | Sizes Available | | | |
|--|-------------------------------|--------------------------------|-------------------------------|--|
| <input type="checkbox"/> Aluminum | <input type="checkbox"/> 7x10 | <input type="checkbox"/> 10x14 | | |
| <input type="checkbox"/> Plastic | <input type="checkbox"/> 7x10 | <input type="checkbox"/> 10x14 | | |
| <input type="checkbox"/> Self-Sticking | <input type="checkbox"/> 3x5 | <input type="checkbox"/> 5x7 | <input type="checkbox"/> 7x10 | <input type="checkbox"/> 9x12 <input type="checkbox"/> 10x14 |

Header/Color (Check one of the options below)

| | | | | | | | | | | | | | |
|--------------------------|---|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|
| <input type="checkbox"/> | | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> | <input type="checkbox"/> | |
| | Red & Black Header on White | | | Blue Header on White | | | Black Header on Yellow | | | Green Header on White | | | Black Header on Orange |
| <input type="checkbox"/> | NO HEADER colors listed to the right | | | | | | | | | | | | |
| | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |

Quantity _____
No minimum order. Orders for 50+ signs are welcome, call for delivery and additional volume discounts.

Legend (Please print clearly)

- Layout best way
 Layout exactly as shown

Pictograms:

A pictogram can be included on your custom sign, in black, at no additional charge. Please indicate pictogram number when placing order.



Distributor Billing Location

Distributor Name: _____
Distributor Address: _____
P.O. Number: _____
Contact Name: _____
Phone Number: _____
Fax Number: _____

Shipping Location

Your Name/Title: _____
Company Name: _____
Attn: _____
Address: _____
City: _____ State: _____ Zip: _____
Phone/Fax Number: _____
P.O. Number: _____

Fax your order to: 901-252-1321

Thomas & Betts