

Table of Contents

Load Rating / Materials / Coatings	2-3
Pictorial Index	4-45
Black Claw™ Spring Steel	4-19
Minerallac® Traditional	20-33
Impact™ Staples	34-37
Masterstrut	38-45
Section 1	Black Claw™ Spring Steel 47-109
	Conduit/Cable 48-63
	Hangers 64-68
	Beam/Purlin 70-85
	Metal Stud 86-95
	Acoustical 96-100
	Voice/Data & Low Voltage 102-105
	Hardware/Accessories 106-109
Section 2	Minerallac® Traditional 111-183
	Conduit/Cable/Wire 112-139
	Beams 140-147
	Metal Stud & Drywall 148-156
	Acoustical 158-162
	Voice/Data & Low Voltage 164-175
	Hardware/Accessories 176-183
Section 3	Impact™ Staples 184-212
	Features / Packaging 185-187
	Non-Insulated Metal Staples 188-193
	Non-Insulated Metal Utility Staples 194
	Insulated Metal Staples 196-197
	Insulated Plastic Staples 198-212
Section 4	MasterStrut 214-287
	Channel 215-241
	Beam & Pipe Clamps 242-253
	Fittings 254-275
	Hardware/Accessories 276-286
Dimension and Load Charts	288-295
Galvanic Corrosion Compatibility of Metals Chart	296
Size Reference Chart	297-299
Index by Catalog Part Number	300-327
Index by Product Name/Use	328-332
Cross References	334-347
The Minerallac Advantage	348-349
Warranty	350

Load Rating / Materials

Load Rating

Minerallac fasteners are designed with two load limits:

Static Load Limit is a rated stationary load limit. The listed static load capacity has a safety factor of three.

Ultimate Static Load is the rated stationary load limit which, if exceeded, may cause failure of the fastener.

Fasteners with no load ratings are to be used for positioning only and not supporting loads.

Load limits are for loads applied VERTICALLY except where may be diagrammed otherwise. The load capacity of a fastener having more than one component is equal to the load capacity of the lowest rated component.

Materials

Steel

We specify commercial quality (CQ) hot rolled pickled and oil (HRPO) or cold rolled (CR) steel for our parts where a specific material specification is not needed.

Spring Steel

We specify a high carbon, cold rolled, annealed, spring steel for all Black Claw™ products.

Stainless Steel

We specify 304 stainless steel for all our stocked products. However, other grades are available but minimum quantities may apply.

Aluminum

We specify 3003-H14 on all aluminum products unless otherwise specified.

Brass

We specify a 70/30 brass C260 1/4 hard material for all our stock products. Formerly named as Everdur® in past catalogs.

Coatings

Coatings

Pre-Galvanized Zinc

This coating of zinc is applied directly at the mills by rolling the material through molten zinc. Parts fabricated from this material have exposed edges where the material has been cut; but the zinc near the uncoated metal becomes a sacrificial anode to protect the bare areas for a short period of time. These parts are recommended for indoor use in dry areas.

Zinc Plated or Electro-Galvanized

We have our parts plated after fabrication to commercial quality standards, and recommend them for indoor, relatively dry environments. Zinc plating is the process by which a coating of zinc is deposited on the steel by electrolysis from a bath of zinc salts. A maximum of .5 mils of zinc can be applied by this method.

Hot Dipped Galvanized

We submerge our parts after fabrication into a molten bath of zinc thus coating all the edges of the parts. This process deposits on average 1000 times more zinc than commercially electroplated parts. Parts are recommended for indoor/outdoor use and mildly corrosive environments.

Phosphate and Oil

We have most of our high carbon spring steel parts (Black Claw™) coated with this process after fabrication and heat-treating. The process applies a base of crystalline zinc phosphate of 1000 milligrams a square foot and then a synthetic organic corrosion inhibitor with a particular affinity for zinc compounds. These parts are recommended for indoor, non-corrosive environments.

Copper Plated

We specify a commercial grade finish on all stock copper plated parts.

Paint


A Urethane coating applied by an electro-deposition process (commonly known as powder coating) is used on many of our MasterStrut fittings and channel. Material thickness is between 1.8 and 2.2 mils thick.

For information on materials and coatings used in the Minerallac MasterStrut line, turn to page 216-217.



CONDUIT/CABLE




See page 48



See page 49



See page 50




See page 51



CONDUIT/CABLE




See page 52



See page 53



See page 54




See page 55



CONDUIT/CABLE




See page 55



See page 56



See page 57




See page 58



CONDUIT/CABLE





See page 59



See page 60




See page 61





See page 62




HANGERS





See page 63



See page 64




See page 65





See page 66


HANGERS




See page 67





See page 68



BEAM/PURLIN




See page 70




See page 70


BEAM/PURLIN





See page 71



See page 72



See page 73




Combination - Black Claw™ & Traditional!

See page 74 & 143

BEAM/PURLIN





See page 75 & 144




Combination - Black Claw™ & Traditional!



See page 76



See page 77




See page 78



BEAM/PURLIN





See page 79



See page 80




See page 81





See page 82




BEAM/PURLIN



See page 82 & 83





See page 84



See page 85

METAL STUD





See page 86




METAL STUD






See page 87



See page 88



See page 89




See page 90




METAL STUD





See page 91



See page 92




See page 93




See page 94

METAL STUD





See page 95





ACOUSTICAL



See page 96




See page 97





See page 98


ACOUSTICAL




See page 99




See page 100



VOICE/DATA & LOW VOLTAGE




See page 102




See page 103


VOICE/DATA & LOW VOLTAGE




See page 104




See page 105



HARDWARE/ACCESSORIES



See page 106





See page 107




HARDWARE/ACCESSORIES




See page 107




See page 108




See page 109





CONDUIT/CABLE/WIRE




See page 112-113



See page 114





See page 116-120




See page 121


CONDUIT/CABLE/WIRE




See page 122-123



See page 124-126



See page 127




See page 128

CONDUIT/CABLE/WIRE




See page 129




Service Entrance

.....




See page 130



Service Entrance

.....





Service Entrance




See page 131

.....





See page 132-133




CONDUIT/CABLE/WIRE




See page 134-135



See page 136



See page 137



See page 138


CONDUIT/CABLE/WIRE






See page 139





BEAMS



See page 140-141




See page 142




See page 74 & 143

Combination - Black Claw™ & Traditional!


BEAMS






See page 75 & 144



Combination - Black Claw™ & Traditional!





See page 145




See page 146-147

METAL STUD & DRYWALL





See page 148



METAL STUD & DRYWALL





See page 149



See page 150




See page 151





See page 152




METAL STUD & DRYWALL




See page 153



See page 154




See page 155




See page 156


ACOUSTICAL



See page 158



See page 159




See page 160




See page 161



ACOUSTICAL





See page 162





HARDWARE/ACCESSORIES



See page 164-165



See page 166-167





See page 168



VOICE/DATA & LOW VOLTAGE




See page 169



See page 170-171



See page 172





See page 173


VOICE/DATA & LOW VOLTAGE



See page 174




See page 175



HARDWARE/ACCESSORIES



See page 176




See page 177



HARDWARE/ACCESSORIES




See page 178



See page 179




See page 180





See page 181


CONDUIT/CABLE/WIRE



See page 182




See page 183



A Tradition of Quality Since 1894




NON-INSULATED METAL STAPLES




Cable Staples
See pages 188-191



Stacking Staples
See page 191




Service Entrance Staples
See page 192-193




Utility Staples
See page 194

INSULATED METAL STAPLES



**Plastic Insulator
Cable Staples**
See page 196

INSULATED METAL STAPLES



PVC Dipped Cable Staples

See page 197

INSULATED PLASTIC STAPLES



Plastic Cable Staples

See page 198




Stacking Cable Staples

See page 199



Service Entrance Staples - Style SER


See page 200



Service Entrance Staples - Style SEU

See page 201

INSULATED PLASTIC STAPLES




Bell & Thermostat Staples

See page 202




Telephone Cable Staples - 1-Nail

See page 203




Coaxial & Sound Staples

See page 204



Coaxial & Sound Staples W/Cement Nails

See page 205




Coaxial & Sound Staples W/Screws

See page 206-207




INSULATED PLASTIC STAPLES



Non-Metallic Sheathed Cable Staples

See page 208




AC/MC Staples

See page 209




UF Cable Staples

See page 210



Data/Com Staples

See page 211




Water Pipe & Copper Tubing Staples

See page 212


Taking the Electrical Industry by Storm!

CHANNEL




By Size
See pages 220-235

.....




By Hole Pattern
See pages 236-240

.....




Welded Back-to-Back
See pages 221, 223,
225, 227, 229, 231,
233, 235, 241

BEAM & PIPE CLAMPS



**Universal, Rigid Conduit/Pipe,
Thinwall (EMT), O.D. Tubing**
See page 242-243

.....



**Cushion Clamps
by Hydra-Zorb™**
See page 244-245

.....




**Parallel Pipe Clamp
MPPC Series**
See page 246

.....

BEAM & PIPE CLAMPS




Grip Hanger
See page 246



Swing Gate Hangers
See page 247




**Malleable Pipe Clamps -
Right Angle**
See page 248



**Malleable Pipe Clamps -
Parallel**
See page 249




**Malleable Beam Clamps -
Edge**
See page 249



Heavy Duty
See page 250

BEAM & PIPE CLAMPS




**Heavy Duty &
Heavy Duty Wide Mouth**
See page 250-251

.....




Beam Clamp
See page 251

.....




"C" Beam Clamp
See page 252

.....




U-Bolt Beam Clamp
See page 252

.....



Z-Clamp
See page 253


FITTINGS



Flat Plate Fittings
See pages 254-256, 260


.....

FITTINGS




90 Degree Fittings

See pages 256-264, 266,
268-270




Corner Connectors

See pages 262, 272




Clevis Connectors

See pages 263-264




Closed Angle Fittings

See page 264-265



Open Angle Fittings


See page 265



U-Support Fittings


See page 257

FITTINGS



Column Attachment
See page 267

.....




**Bracket Support,
Single & Double**
See page 271

.....




4-Hole Splice Clevis
See page 273

.....




Internal Channel Joiners
See page 273

.....



**Post Bases -
6" x 6" x 1-5/8" High**
See page 274


.....



**Post Bases -
6" x 6" x 3-1/2" High**
See page 275


.....

FITTINGS




**Double Column Post Bases -
6" x 6" x 3-1/2" High**
See page 275

HARDWARE/ACCESSORIES




Spring Nuts
See page 276-277



**Square Washers &
Guided Square Washers**
278-279



Continuous Threaded Rod
See page 280



Hexagon Rod Coupling
See page 280




Safety End Caps
See page 281

HARDWARE/ACCESSORIES




Touch-Up Paint

See page 281




Round Head Machine Screw

See page 282




Hex Head Machine Screw

See page 282



**Slotted Hex Head
Machine Screw**

See page 283



Square Nut

See page 283




Hex Nut

See page 284




HARDWARE/ACCESSORIES




Swivel Nut
See page 284

.....




Fender Washer
See page 285

.....




Lock Washer
See page 285

.....



Flat Washer
See page 286

.....



Safety Anchor Strap
See page 286

.....

Building For Tomorrow



The Seals of Approval

Not only do you have *our* guarantee of your customer's complete satisfaction, Minerallac products are UL, cUL, and CSA listed, so you have the *industry's* highest quality assurance.



*Not all fasteners are listed.
Please refer to index for
individual parts.*

Black Claw™

Strong, Swift and Efficient




Spring Steel -- Time and Labor-Saving Fasteners

Our Black Claw™ line of premium fasteners is constructed from high carbon steel that has been engineered and manufactured to ensure a tight, secure “claw grip” on flanges, conduit, cable, studs and T-bars. Winning rave reviews by contractors, these products are hailed for their strength and efficient installation.



Conduit/Cable

- No fastener required.
- Available both non-keyholed and keyholed for 1/4"-20 screw.
- Ultimate Static Load Limit:
25 lbs vertical position
15 lbs horizontal position



Conduit Clip



HIC75




HIC75T

Catalog Number	Fits		Standard Package
	EMT	Rigid/IMC	
HIC50	1/2"	---	100
HIC75	3/4"	1/2"	100
HIC100	1"	3/4"	100

Catalog Number	With Thread Impression for 1/4"-20		Standard Package
	EMT	Rigid/IMC	
HIC50T	1/2"	---	100
HIC75T	3/4"	1/2"	100
HIC100T	1"	3/4"	100

Static Load Limit




15 LBS



25 LBS




- No fastener required.
- Available both non-keyholed and keyholed for 1/4"-20 screw.
- Ultimate Static Load Limit:
100 lbs vertical position
25 lbs horizontal position



Conduit Clip

Static Load Limit



25 LBS



100 LBS



KC1234



KC1234T


Catalog Number	Fits Conduit	Standard Package
KC38	3/8"	100
KC1234	1/2", 3/4"	100
KC1	1"	100
KC114	1-1/4"	100
KC112	1-1/2"	100
KC2	2"	100

Catalog Number	With Thread Impression for 1/4"-20	Standard Package
KC38T	3/8"	100
KC1234T	1/2", 3/4"	100
KC1T	1"	100
KC114T	1-1/4"	100
KC112T	1-1/2"	100
KC2T	2"	100


Conduit/Cable

- No fastener required
- Designed to quickly secure one conduit run to another
- Ultimate Static Load Limit: 25 lbs

NOTE: Top conduit to be used for support only, not a raceway



Conduit to Conduit Trapeze Assembly




HIC7575

Catalog Number	Connects Conduit		Standard Package
	EMT	Rigid/IMC	
HIC5050	1/2" to 1/2"	---	100
HIC5075	1/2" to 3/4"	---	100
HIC50100	1/2" to 1"	---	100
HIC7575	3/4" to 3/4"	1/2" to 1/2"	100
HIC75100	3/4" to 1"	1/2" to 3/4"	100
HIC100100	1" to 1"	3/4" to 3/4"	100



- *No fastener required*
- *Designed to quickly secure one conduit run to another*
- *Total load of trapeze must not exceed 100 lbs*




Conduit to Conduit Trapeze Assembly



KC1234KC1234

Catalog Number	Connects Conduit	Standard Package
KC38KC1	3/8" to 1"	100
KC1234KC1	1/2" or 3/4" to 1"	100
KC1KC1	1" to 1"	100
KC114KC1	1-1/4" to 1"	100
KC112KC1	1-1/2" to 1"	100
KC2KC1	2" to 1"	100
KC1234KC1234	1/2" or 3/4" to 1/2" or 3/4"	100

Conduit/Cable



Cable Clips

- Clip for MC, AC, or BX. Supports cable from #12 to #8 wire in horizontal or vertical position. O.D.'s from .433 to .535

NOTE: These products are designed for positioning only. No load rating.

Cable Size	#12 Wire	#10 Wire	#8 & #9 Wire	Std Pkg
14-2 Cable	FSBX	FSBX	FSBX	100
14-3 Cable	FSBX	FSBX	FSBX	100
12-2 Cable	FSBX	FSBX	FSBX	100
12-3 Cable	FSBX	FS1	FS1	100

FSBX




FS1





FS2




Conduit Clips


- Supports conduit and all types of cable from rods or flanges

Static Load Limit


Vertical Flange



Vertical Wire or Rod



Horizontal Flange




Conduit Size	#10 & #12 Wire	#8 & #9 Wire	3/16" to 1/4" Rod	Std Pkg
1/2" EMT	FS1	FS1	FS1	100
1/2" RIGID	FS1	FS2	FS2	100
3/4" EMT	FS2	FS2	FS2	100
3/4" RIGID	FS2	FS2	FS3	100
1" EMT	---	FS3	FS3	100
1" RIGID	---	---	---	100
1-1/4" EMT	---	FS4	FS4	100

Conduit Size	1/8" to 1/4" Flange	5/16" to 3/8" Flange	5/16" to 3/8" Flange	Std Pkg
1/2" EMT	FS1	FS2	FS2	100
1/2" RIGID	FS2	FS2	FS3	100
3/4" EMT	FS2	FS3	FS3	100
3/4" RIGID	FS3	FS4*	FS4*	100
1" EMT	FS3	FS4*	FS4*	100
1" RIGID	FS4*	FS4*	FS4*	100
1-1/4" EMT	FS4	---	---	100

*For horizontal applications only.

Conduit/Cable




Multi-Function Clip

- Attaches conduit or boxes to flanges, wire or rod

Catalog Number	Description	Standard Package
APS	Fits 1/8" to 3/8" flanges; attaches to #12 wire through 3/8" rod; attaches #10-24 or 1/4"-20 Threaded Bridle Rings (position only)	100

Static Load Limit





50 LBS



25 LBS



APS





Multi-Function Clip Assemblies

- Attaches conduit to flanges, wire or rod


Catalog Number	Fits		Standard Package
	EMT	Rigid/IMC	
APS50	1/2"	---	100
APS75	3/4"	1/2"	100
APS100	1"	3/4"	100

Catalog Number	Fits Conduit	Standard Package
APSKC1234	1/2" & 3/4"	100
APSKC1	1"	100

Static Load Limit




Static Load Limit




Conduit/Cable

- Supports flexible conduit and all types of cable from rods or flanges
- Flexible Conduit/Cable Clip Adaptor available for use with F2 series
- Made from high carbon steel; zinc plated




Flexible Conduit/Cable Clip

F2A




Catalog Number	Description		Std Pkg
	AC/MC Cable O.D.	Flange Size	
F2A	.218" - .281"	1/16" - 3/16"	100
F2B	.312" - .375"	1/16" - 3/16"	100
F2C	.375" - .437"	1/16" - 3/16"	100
F2D	.468" - .562"	1/16" - 3/16"	100
F2E	.562" - .718"	1/16" - 3/16"	100
F2F	.750" - .937"	1/16" - 3/16"	100
F2G	.968" - 1.250"	1/16" - 3/16"	100
F4A	.218" - .281"	3/16" - 9/32"	100
F4B	.312" - .375"	3/16" - 9/32"	100
F4C	.375" - .437"	3/16" - 9/32"	100
F4D	.468" - .562"	3/16" - 9/32"	100
F4E	.562" - .718"	3/16" - 9/32"	100
F4F	.750" - .937"	3/16" - 9/32"	100
F4G	.968" - 1.250"	3/16" - 9/32"	100
F8A	.218" - .281"	5/16" - 1/2"	100
F8B	.312" - .375"	5/16" - 1/2"	100
F8C	.375" - .437"	5/16" - 1/2"	100
F8D	.468" - .562"	5/16" - 1/2"	100
F8E	.562" - .718"	5/16" - 1/2"	100
F8F	.750" - .937"	5/16" - 1/2"	100
F8G	.968" - 1.250"	5/16" - 1/2"	100



Flexible Conduit/Cable Clip Adaptor

- *Flange adaptor for cable clips*
- *For use with F2 series Minerallac Flexible Conduit/Cable Clip*
- *Made from high carbon steel; zinc plated*


Catalog Number	Description	Standard Package
F15XR	Fits flanges 5/8" to 3/4"	100



F15XR


Conduit/Cable

- Suspends conduit from bottom of beam
- Will pivot 360 degrees
- Installs with hammer only
- Ultimate Static Load Limit: 25 lbs




Flange Mount Conduit Clip Assembly

Static Load Limit



25 LBS


Bottom Mount



BC1875


Catalog Number	Fits		Std Pkg
	Flange	EMT Rigid/IMC	
BC1850	1/8"-1/4"	1/2"	100
BC1875	1/8"-1/4"	3/4"	100
BC18100	1/8"-1/4"	1"	100
BC51650	5/16"-1/2"	1/2"	100
BC51675	5/16"-1/2"	3/4"	100
BC516100	5/16"-1/2"	1"	100
BC91650	9/16"-3/4"	1/2"	100
BC91675	9/16"-3/4"	3/4"	100
BC916100	9/16"-3/4"	1"	100

- Suspends conduit from bottom of beam
- Will pivot 360 degrees
- Installs with hammer only
- Ultimate Static Load Limit:
75 lbs




Flange Mount Conduit Clip Assembly

Static Load Limit



75 LBS

Bottom Mount




BC516KC1

Catalog Number	Fits		Std Pkg
	Flange	Conduit	
BC18KC38	1/8"-1/4"	3/8"	100
BC18KC1234	1/8"-1/4"	1/2" & 3/4"	100
BC18KC1	1/8"-1/4"	1"	100
BC18KC114	1/8"-1/4"	1-1/4"	100
BC18KC112	1/8"-1/4"	1-1/2"	100
BC18KC2	1/8"-1/4"	2"	100
BC516KC38	5/16"-1/2"	3/8"	100
BC516KC1234	5/16"-1/2"	1/2" & 3/4"	100
BC516KC1	5/16"-1/2"	1"	100
BC516KC114	5/16"-1/2"	1-1/4"	100
BC516KC112	5/16"-1/2"	1-1/2"	100
BC516KC2	5/16"-1/2"	2"	100
BC916KC38	9/16"-3/4"	3/8"	100
BC916KC1234	9/16"-3/4"	1/2" & 3/4"	100
BC916KC1	9/16"-3/4"	1"	100
BC916KC114	9/16"-3/4"	1-1/4"	100
BC916KC112	9/16"-3/4"	1-1/2"	100
BC916KC2	9/16"-3/4"	2"	100


Conduit/Cable

- Suspends conduit from side of beam
- Will pivot 360 degrees
- Installs with hammer only
- Ultimate Static Load Limit: 15 lbs




Flange Mount Conduit Clip Assembly

Static Load Limit



15 LBS


Side Mount



SFC1875


Catalog Number	Fits			Std Pkg
	Flange	EMT	Rigid/IMC	
SFC1850	1/8"-1/4"	1/2"	---	100
SFC1875	1/8"-1/4"	3/4"	1/2"	100
SFC18100	1/8"-1/4"	1"	3/4"	100
SFC51650	5/16"-1/2"	1/2"	---	100
SFC51675	5/16"-1/2"	3/4"	1/2"	100
SFC516100	5/16"-1/2"	1"	3/4"	100
SFC91650	9/16"-3/4"	1/2"	---	100
SFC91675	9/16"-3/4"	3/4"	1/2"	100
SFC916100	9/16"-3/4"	1"	3/4"	100

- Suspends conduit from side of beam
- Will pivot 360 degrees
- Installs with hammer only
- Ultimate Static Load Limit: 25 lbs




Flange Mount Conduit Clip Assembly

Static Load Limit




Side Mount



SFC516KC1

Catalog Number	Flange	Fits Conduit	Std Pkg
SFC18KC38	1/8"-1/4"	3/8"	100
SFC18KC1234	1/8"-1/4"	1/2"-3/4"	100
SFC18KC1	1/8"-1/4"	1"	100
SFC18KC114	1/8"-1/4"	1-1/4"	100
SFC18KC112	1/8"-1/4"	1-1/2"	100
SFC18KC2	1/8"-1/4"	2"	100
SFC516KC38	5/16"-1/2"	3/8"	100
SFC516KC1234	5/16"-1/2"	1/2"-3/4"	100
SFC516KC1	5/16"-1/2"	1"	100
SFC516KC114	5/16"-1/2"	1-1/4"	100
SFC516KC112	5/16"-1/2"	1-1/2"	100
SFC516KC2	5/16"-1/2"	2"	100
SFC916KC38	9/16"-3/4"	3/8"	100
SFC916KC1234	9/16"-3/4"	1/2"-3/4"	100
SFC916KC1	9/16"-3/4"	1"	100
SFC916KC114	9/16"-3/4"	1-1/4"	100
SFC916KC112	9/16"-3/4"	1-1/2"	100
SFC916KC2	9/16"-3/4"	2"	100

Conduit/Cable



Nail/Conduit Bracket


- Attaches conduit to wood, steel and concrete
- Eliminates offset bends on 1-1/2" box
- Position only -- No load rating

Catalog Number	Fits		Std Pkg
	EMT	Rigid/IMC	
NB50	1/2"	---	100
NB75	3/4"	1/2"	100
NB100	1"	3/4"	100


Catalog Number	Fits Conduit	Std Pkg
NBKC1234	1/2" or 3/4"	100



NB75



NBKC1234



Metal Deck/Conduit Bracket


- Provides spacing between conduit and deck surface
- Eliminates offset bends on 2-1/8" box
- Position only -- No load rating

Catalog Number	Fits		Std Pkg
	EMT	Rigid/IMC	
RS50	1/2"	---	100
RS75	3/4"	1/2"	100
RS100	1"	3/4"	100

Catalog Number	Fits Conduit	Std Pkg
RSKC1234	1/2" or 3/4"	100




RS75



RSKC1234

Hangers




Rod/Wire - Bracket Support


- Suspends #8 wire, 1/4" AND 3/8" plain or threaded rod from overhead mountings with a clearance hole for 1/4" bolt
- Static Load Capacity: Not to exceed 160 lbs
- Hangers made from high carbon steel; zinc phosphate & oil finish. Angle bracket made from pre-galvanized steel

Catalog Number	Angle Bracket Supports For Use With	Std Pkg
RA14	#8 wire or 1/4" plain rod	100
RA38	3/8" plain rod	100
RA14T	1/4" threaded rod w/thread impression	100
RA38T	3/8" threaded rod w/thread impression	100
RA1438N	1/4" to 3/8" threaded rod, nut required	100


Angle Brackets



RA14



RA14T




Rod/Wire - Bracket Support


- Suspends #8 wire, 1/4" AND 3/8" plain or threaded rod from overhead mountings with a clearance hole for 1/4" bolt
- Static Load Capacity: Not to exceed 160 lbs
- Hangers made from high carbon steel; zinc phosphate & oil finish. Offset bracket made from pre-galvanized steel

Catalog Number	Angle Bracket Supports For Use With	Std Pkg
RO14	#8 wire or 1/4" plain rod	100
RO38	3/8" plain rod	100
RO14T	1/4" threaded rod w/thread impression	100
RO38T	3/8" threaded rod w/thread impression	100
RO1438N	1/4" to 3/8" threaded rod, nut required	100

Offset Brackets




RO38



RO38T


Hangers




Rod/Wire Beam Assemblies

- Suspends #8 wire, 1/4" AND 3/8" plain rod from overhead mountings with a clearance hole for 1/4" bolt
- Static Load Capacity: Not to exceed 200 lbs

Catalog Number	Flange Thickness	For Use With	Std Pkg
R1814	1/8"-1/4"	#8 wire or 1/4" plain rod	100
R51614	5/16"-1/2"	#8 wire or 1/4" plain rod	100
R91614	9/16"-3/4"	#8 wire or 1/4" plain rod	100
R1838	1/8"-1/4"	3/8" plain rod	100
R51638	5/16"-1/2"	3/8" plain rod	100
R91638	9/16"-3/4"	3/8" plain rod	100




R1814



R1838




- Suspends 1/4" AND 3/8" threaded rod from overhead mountings with a clearance hole for 1/4" bolt
- Static Load Capacity: Not to exceed 160 lbs




Hangers

Threaded Rod to Beam Assemblies



R181438N




R1814T


Catalog Number	Flange Thickness	For Use With	Std Pkg
R1814T	1/8"-1/4"	1/4" threaded rod	100
R51614T	5/16"-1/2"	1/4" threaded rod	100
R91614T	9/16"-3/4"	1/4" threaded rod	100
R1838T	1/8"-1/4"	3/8" threaded rod	100
R51638T	5/16"-1/2"	3/8" threaded rod	100
R91638T	9/16"-3/4"	3/8" plain rod	100
R181438N	1/8"-1/4"	1/4" or 3/8" threaded rod, nut required	100
R5161438N	5/16"-1/2"	1/4" or 3/8" threaded rod, nut required	100
R9161438N	9/16"-3/4"	1/4" or 3/8" threaded rod, nut required	100

Hangers


- Suspends strapping thru 1" wide from beam flanges 1/8" to 3/4" thick, parallel or at right angles to beam
- Static Load Capacity: 200 lbs



Strap Hangers



PSF18



PSF18R

Catalog Number	Flange Thickness	Standard Package
PSF18	1/8" to 1/4"	100
PSF516	5/16" to 1/2"	100
PSF916	9/16" to 3/4"	100

Catalog Number	Right Angle Strap Fits Flange Thickness	Standard Package
PSF18R	1/8" to 1/4"	100
PSF516R	5/16" to 1/2"	100
PSF916R	9/16" to 3/4"	100

The PS and the PSR are also sold separately on page 109..

FREE Catalog or Product Sample!



Would you like an additional copy of our catalog or a complimentary sample of one of our products shown here? Can we add you to our mailing list for new product updates and samples, promotions and company newsletter? Phone, fax or e-mail your request. Or simply fill out the postage paid request card attached to this catalog. We look forward to hearing from you...and thank you for your interest in Minerallac.



100 Gast Road • Hampshire, IL 60140
PHONE TOLL FREE 1-877-285-2200
FAX TOLL FREE 1-800-824-8942
CustomerService@minerallac.com

Hang with Minerallac®...

Beam/Purlin



Beam Clamps

- Can be used to suspend boxes, fixtures & bridle rings to beam flanges 1/8" to 3/4" thick
- Beam Clamp with 1.4"-20 x 3/8" staked stud used to suspend box from bottom of beam
- Ultimate Static Load Limit:
75 lbs or 100 lbs (see illustration)
Note: Static load limits cannot be combined.

Catalog Number	Flange Thickness	Standard Package
BC18	1/8"-1/4"	100
BC516	5/16"-1/2"	100
BC916	9/16"-3/4"	100


Bottom & Back Tapped 1/4"-20.

Metric size M6 available upon request. May require minimum quantities. Call Customer Service for pricing and availability.

Catalog Number	Flange Thickness	Standard Package
BC18ST	1/8"-1/4"	100
BC516ST	5/16"-1/2"	100
BC916ST	9/16"-3/4"	100




BC18




BC18ST

Static Load Limit



75 Lbs 100 Lbs




Beam Clamp

- *Fast installation; fits beam flange to 1/2"*
- *Used with 1/4" and 3/8" threaded rod, "S" hooks, conduit hangers, electrical boxes, and #10-24 or 1/4"-20 bridle rings*
- *Static Load Capacity: 100 lbs*

Beam/Purlin


Catalog Number	Accommodates		Standard Package
	Flange	Drop Rod	
500	Up to 1/2" thick	1/4" -3/8"	100

Tapping 1/4"-20 bottom and back. Also #10-24 tapping on back.



500


Beam/Purlin




Beam Clamp to Conduit Hanger Assemblies

- Our #500 beam clamp with conduit hanger attached
- Static Load Capacity:
25 lbs vertical position
15 lbs horizontal position

Catalog Number	Fits		Standard Package
	EMT	Rigid/IMC	
50050	1/2"	---	100
50075	3/4"	1/2"	100
500100	1"	3/4"	100
50050B	1/2"	---	100
50075B	3/4"	1/2"	100
500100B	1"	3/4"	100




50050




50050B

- Part #500 beam clamp with conduit hanger attached.


- Static Load Capacity:
100 lbs vertical position
25 lbs horizontal position



Beam Clamp to Conduit Hanger Assemblies



500KC1234




500KC1234B

Beam/Purlin

Catalog Number	Fits Conduit	Standard Package
500KC1234	1/2" & 3/4"	100
500KC1	1"	100
500KC114	1-1/4"	100
500KC112	1-1/2"	100
500KC2	2"	100
500KC1234B	1/2" & 3/4"	100
500KC1B	1"	100
500KC114B	1-1/4"	100
500KC112B	1-1/2"	100
500KC2B	2"	100


Beam/Purlin




Beam Clamp to Conduit Hanger

- Combination of Black Claw™ spring steel part and Traditional Minerallac part
- Black Claw™ part made from high carbon steel; zinc phosphate & oil finish. Traditional part zinc plated steel

Catalog Number	Fits		Standard Package
	EMT	Rigid/IMC	
60050	1/2"	---	100
60075	3/4"	1/2"	100
600100	1"	3/4"	100
60050B	1/2"	---	100
60075B	3/4"	1/2"	100
600100B	1"	3/4"	100



60075




60075B




- Universal beam clamp with Black Claw™ hanger assemblies


- Black Claw™ part made from high carbon steel; zinc phosphate & oil finish. Traditional part zinc plated steel



Beam Clamp to Conduit Hanger



600KC1234




600KC1234B

Beam/Purlin

Catalog Number	Fits Conduit	Standard Package
600KC1234	1/2"-3/4"	100
600KC1	1"	100
600KC114	1-1/4"	100
600KC112	1-1/2"	100
600KC2	2"	100
600KC1234B	1/2"-3/4"	100
600KC1B	1"	100
600KC114B	1-1/4"	100
600KC112B	1-1/2"	100
600KC2B	2"	100


Beam/Purlin




Flange Beam Clamp

- Installed with hammer on bulb tees and beams with Static Load Capacity of 200 lbs.
- Clearance for 1/4" bolt in tab.

Catalog Number	Flange Thickness	Standard Package
SFC18	1/8" - 1/4"	100
SFC516	5/16" - 1/2"	100
SFC916	9/16" - 3/4"	100



SFC18




“Z” Purlin Hanger

- *Installed without power tools.*
- *Compensates for angle of purlin.*
- *Static Load Capacity: 100 lbs*

Catalog Number	Description	Std Pkg
P	1/4" bottom hole	100
PH	For wire, S-hooks, perforated strap and jack chain	100

**P****PH**

Beam/Purlin



“Z” Purlin Hanger Assemblies

- *Installed without power tools*
- *Compensates for angle of purlin*
- *Static Load Capacity: 100 lbs*


Catalog Number	For Use With	Standard Package
PH14T	1/4" threaded rod	100
PH38T	3/8" threaded rod	100
PH1438N	1/4" or 3/8" threaded rod, nut required	100



PH1438N



PH14T




“Z” Purlin Hanger Assemblies

- *Installed without power tools*
- *Compensates for angle of purlin*
- *Static Load Capacity: 100 lbs*

Catalog Number	Description	Standard Package
PH14	#8 wire or 1/4" plain rod	100
PH38	3/8" plain rod	100

**PH14****PH38**


Beam/Purlin




“Z” Purlin Hanger Assemblies

- *Installed without power tools*
- *Static Load Capacity: 25 lbs*
- *Compensates for angle of purlin*

Catalog Number	Description	Standard Package
P50	1/2" conduit to Z Purlin	100
P75	3/4" conduit to Z Purlin	100
P100	1" conduit to Z Purlin	50



P50




“Z” Purlin Hanger Assemblies

- *Installed without power tools*
- *Static Load Capacity: 100 lbs*
- *Compensates for angle of purlin*


Beam/Purlin

Catalog Number	Description	Standard Package
PKC38	3/8" cable to Z Purlin	100
PKC1234	1/2" or 3/4" conduit to Z Purlin	100
PKC1	1" conduit to Z Purlin	100
PKC114	1-1/4' conduit to Z Purlin	50



PKC1234


Beam/Purlin




“Z” Purlin Flange Hanger

- Fits 1/16” to 1/4” thick Z-Purlin (ABC25) or vertical flanges (VBC25)
- Accommodates tooling for floor installations


Catalog Number	Flange Thickness	For Use With	Std Pkg
ABC25	1/16”-1/4”	Angled Z-Purlin for S-Hooks, perforated strap & wire	100
VBC25	1/16”-1/4”	Vertical Flange for S-Hooks, perforated strap & wire	100



ABC25



VBC25



Flange Hanger


- Suspends #12, #10, #9 or #8 wire, 1/4" or 3/8" plain or threaded rod from vertical flanges

Catalog Number	Flange Thickness	For Use With	Std Pkg
FH116	1/16"-5/16"	S-Hooks, perforated strap & wire	100
FH532	5/32"-1/4"	S-Hooks, perforated strap & wire	100



FH116


Beam/Purlin




Rod to Flange Hanger

- Suspends #8 wire, and 1/4" or 3/8" plain rod from vertical flange 1/16" to 1/4" thick
- Static Load Capacity: 160 lbs


Catalog Number	Flange Thickness	For Use With	Std Pkg
RF11614	1/16"-5/32"	#8 wire or 1/4" plain rod	100
RF53214	5/32"-1/4"	#8 wire or 1/4" plain rod	100
RF11638	1/16"-5/32"	3/8" plain rod	100
RF53238	5/32"-1/4"	3/8" plain rod	100



RF11614




RF11638




Rod to Flange Hanger

- Suspends 1/4" or 3/8" threaded rod from vertical flange 1/16" to 1/4" thick
- Static Load Capacity: 160 lbs

Catalog Number	Flange Thickness	For Use With	Std Pkg
RF11614T	1/16"-5/32"	1/4" threaded rod	100
RF53214T	5/32"-1/4"	1/4" threaded rod	100
RF11638T	1/16"-5/32"	3/8" threaded rod	100
RF53238T	5/32"-1/4"	3/8" threaded rod	100
RF1161438N*	1/16"-5/32"	1/4, 3/8" threaded rod	100
RF5321438N*	5/32"-1/4"	1/4", 3/8" threaded rod, nut required	100




RF1161438N



RF11638T


Metal Stud



Conduit/Cable Support

- Designed to secure horizontal runs of Rigid, EMT, AC, MC, BX or PVC through metal studs


Catalog Number	Fits Conduit	Std Pkg
BAKC38	3/8" or BX	100
BAKC1234	1/2" or 3/4"	100
BA50	1/2" EMT	100
BA75	3/4" EMT or 1/2" Rigid	100



BAKC1234




BA75



Flexible Conduit/Cable Fastener


- Push clip attaches BX, MC or AC cable to metal studs

Catalog Number	Description	Std Pkg
BXC	MC, AC, or BX to metal stud	100



BXC


Metal Stud




Flexible Conduit/Cable Fastener

- *Installed using hammer only*
- *Secures conduit to most metal studs*

Catalog Number	Description	Std Pkg
SROM	Romex® or non-metallic cable (14-2 w/g and 12-2 w/g) to metal studs	100
SBX	MC or BX (12-2 thru 10-3) to metal studs	100




SROM



Plaster Ring to Stud Support


- *Secures plaster rings to most metal studs*
- *Installed using hammer only*

Catalog Number	Description	Std Pkg
SRING	Plaster ring support	100



SRING

Metal Stud




Conduit to Stud Support


- Screw attached support for horizontal runs of Rigid, EMT, AC, MC, BX or PVC to metal studs

Catalog Number	Fits		Std Pkg
	EMT	Rigid/IMC	
SS50	1/2"	---	100
SS75	3/4"	1/2"	100
SS100	1"	3/4"	100


Catalog Number	Fits Conduit	Std Pkg
SSKC1234	1/2" or 3/4"	100
SSKC1	1"	100



SS75




SSKC1234



Box to Stud Fastener


- Screw attached support for box and conduit. For use with either metal or wood studs

Catalog Number	Description	Std Pkg
SS	Electrical box support clip secured with self-tapping screws for wood or metal studs	100



SS

Metal Stud



Box to Stud Support


- *Installed using hammer only*
- *Secures boxes to most metal studs*

Catalog Number	Description	Std Pkg
----------------	-------------	---------

S1900

Hammer installed electrical box support


100




S1900




- *Installed using hammer only*
- *Secures boxes to most metal studs*
- *Series includes adjustable and preset versions*



Box to Stud Support



SBC




SB14

Catalog Number	Description	Std Pkg
SBC	Adjustable for 1/4" through 3/4" drywall	100
S	1/4"-20 thread impression	100
SBO	Flush wall	100

Catalog Number	Description	Std Pkg
SB14	Offset for 1/4" drywall	100
SB38	Offset for 3/8" drywall	100
SB12	Offset for 1/2" drywall	100
SB58	Offset for 5/8" drywall	100
SB34	Offset for 3/4" drywall	100


Acoustical



Lighting - Troffer Fastener

- *Clip-on positive support for troffers and lay-in fixtures*
- *Complies with NEC Article 410-16 means of support*
- *Fits round or rectangular head T-bars*


Catalog Number	Description	Std Pkg
FT	T-bar clip for troffers	100




FT

Metal Stud


- Designed to quickly secure horizontal runs of Rigid, EMT, AC, MC, BX or PVC to metal studs



Conduit to Stud Fastener




SB50



SBKC1234

Catalog Number	Fits		Std Pkg
	EMT	Rigid/IMC	
SB50	1/2"	---	100
SB75	3/4"	1/2"	100
SB100	1"	3/4"	100

Catalog Number	Fits Conduit	Std Pkg
SBKC38	3/8" or BX	100
SBKC1234	1/2", 3/4"	100
SBKC1	1"	100
SBKC114	1-1/4"	100



Far Side Box Support


- Clips on electrical boxes for additional support

Catalog Number	Metal Stud Size	Std Pkg
SBS	2-1/2" thru 4", sized by bending at premarked lines	100
SBS2.5	2-1/2"	100
SBS3.5	3-1/2"	100
SBS4	4"	100
SBS6	6"	100


Metal Stud



SBS



SBS2.5



Twist On T-Bar Hanger


- Supports electrical fixtures to T-Bar 15/16" wide.
- Assembled with 1" OD wing nut washer
- 1/4"-20 stud 5/8" long

Catalog Number	Description	Std Pkg
SCT3	Has 1/4"-20 x 5/8" stud with wing nut washer	100



SCT3

Acoustical




T-Bar Fasteners


- *Positive method of supporting conduit and outlet boxes above acoustical T-bar*

Catalog Number	Description	Std Pkg
TBT	With 1/4"-20 thread impression	100
TB	With plain hole	100

Catalog Number	Description	Std Pkg
TST	With 1/4"-20 thread impression	100
TS	With plain hole	100



TB




TS




- Top mounted acoustical T-bar fastener. Riveted assembly fits 3/8" to 1" condui*


- Supports boxes and con-duit above T-bar*



T-Bar Fasteners



TBKC1234




TB50

Catalog Number	Fits		Std Pkg
	EMT	Rigid/IMC	
TB50	1/2"	---	100
TB75	3/4"	1/2"	100
TB100	1"	3/4"	100


Catalog Number	Fits Conduit	Std Pkg
TBKC38	3/8" or BX	100
TBKC1234	1/2", 3/4"	100
TBKC1	1"	100

Acoustical


- Side mounted acoustical T-bar fastener. Riveted assembly fits 3/8" to 1" conduit
- Supports boxes and conduit above T-bar



T-Bar Fasteners



TSKC1




TS50

Catalog Number	Fits		Std Pkg
	EMT	Rigid/IMC	
TS50	1/2"	---	100
TS75	3/4"	1/2"	100
TS100	1"	3/4"	100

Catalog Number	Fits Conduit	Std Pkg
TSKC38	3/8" or BX	100
TSKC1234	1/2", 3/4"	100
TSKC1	1"	100

Voice/Data & Low Voltage




Plastic Cable Tie Fastener

- *For securing data/com cables*
- *Supports cable ties up to 5/16" in width*
- *Secures directly to wall*

Catalog Number	Description	Standard Package
PCTF	Screw directly to wall	100



PCTF



Plastic Cable Tie Fastener


- For securing data/com cables to rod or flanges
- Supports cable ties up to 5/16" in width
- Plastic part made from quality UV stabilized and fire resistant material

Catalog Number	For Use With	Standard Package
APSPCTF	#12 wire thru 1/4" rod and 1/8" thru 3/8" flange	100



APSPCTF


Voice/Data & Low Voltage




Plastic Cable Tie Fastener

- *For securing data/com cables to flanges*
- *Supports cable ties up to 5/16" in width*
- *Plastic part made from quality UV stabilized and fire resistant material*


Catalog Number	For Use With	Std Pkg
ABC25PCTF	1/16" thru 1/4" angled purlin	100
VBC25PCTF	1/16" thru 1/4 vertical flange	100



ABC25PCTF





VBC25PCTF



Plastic Cable Tie Fastener


- *For securing data/com cables to flanges*
- *Supports cable ties up to 5/16" in width*
- *Plastic part made from quality UV stabilized and fire resistant material*

Catalog Number	For Use With	Std Pkg
SFC18PCTF	1/8" thru 1/4" flange	100
SFC516PCTF	5/16" thru 1/2" flange	100
SFC916PCTF	9/16" thru 3/4" flange	100



SFC18PCTF

Hardware/Accessories




Box to Bar Fastener

- *T-Bar mounting and retaining clips*

Catalog Number	Description	Std Pkg
BBC	Box mounting clip with screw	100
BSC	Two bar retaining clip	100

See page 149 of our Traditional line for complete Box to Bar Fastener Assemblies.




BBC



BSC




- Provides thread impression for unthreaded hole

**UN14**

U Nut

Catalog Number	For Use With	Std Pkg
UN14	Provides 1/4"-20 thread	100

- For use with plain rod.


**PN8**

Push Nut


Catalog Number	For Use With	Std Pkg
PN8	#8 wire	100
PN14	1/4" plain rod	100
PN38	3/8" plain rod	100

Hardware/Accessories

- Used for hanging rod
- Static Load Capacity:
160 lbs.



Rod Hangers



R38T




R38



R14

Catalog Number	For Use With	Std Pkg
R14	#8 wire or 1/4" plain rod	100
R38	3/8" plain rod	100
R1438N	1/4" or 3/8" threaded rod, nut required	100
R14T	1/4" threaded rod, with threaded impression	100
R38T	3/8" threaded rod, with threaded impression	100
R14M	Metric thread M6	100




Strap Brackets


- Used for hanging straps

Catalog Number	Description	Std Pkg
PS	Strap Hanger	100
PSR	Right Angle Strap Hanger	100

Flange Beam Fastener found on page 68.



PS



PSR


Did you know?

Minerallac invented and patented the original Conduit Hanger in 1904, U.S. Patent No. 773,710.



Did you know?

Minerallac invented and patented the one-hole “Jiffy Clip” in 1914.



Did you know?

Question: How did Minerallac get its name?

Answer: Founded in 1894, Minerallac is known for inventions that electrified an industry. Born out of the need to solve an over-heating problem associated with early 1900 electrical transformers, our founder, Mr. Louis Ferguson, invented a cooling agent made from mineral oil and lacquer -- thus the name “Minerallac” was born!

M Minerallac®
A Tradition of Quality Since 1894



Traditional Minerallac -- For Quality That Saves You Time

For over a hundred years, Minerallac has provided the electrical contractor with time-saving and innovative fasteners. Our "Traditional" line has expanded from the conduit hanger and one-hole "Min-E®" strap, invented and patented by Minerallac, to well

over a thousand different sizes, styles and finishes of electrical fasteners from which to choose. We're sure to have the fastener, style, finish and quality you require.



That's the Minerallac Advantage!

Conduit/Cable/Wire**Conduit Hangers**

See page 176 to order bolts and nuts separately.

Turn to page 288 for Dimension Chart on these parts.

W/Bolts Attached

Catalog Number	Zinc Plated Steel Fits EMT	Rigid	Std Pkg
0B	1/2"	3/8"-1/2"	100
1B	3/4"	3/4"	100
2B	1"	1"	100
2-1/2B	1-1/4"	---	100
3B	1-1/2"	1-1/4"	100
4B	---	1-1/2"	100
5B	2"	2"	50
6B	2-1/2"	2-1/2"	50
7B	3"	3"	25
8B	3-1/2"	3-1/2"	25
9B	4"	4"	10
10B	---	5"	10

W/Bolts Attached

Catalog Number	STAINLESS STEEL Fits EMT	Rigid	Std Pkg
0SB	1/2"	3/8"-1/2"	100
1SB	3/4"	3/4"	100
2SB	1"	1"	100
2-1/2SB	1-1/4"	---	100
3SB	1-1/2"	1-1/4"	100
4SB	---	1-1/2"	100
5SB	2"	2"	50
6SB	2-1/2"	2-1/2"	50
7SB	3"	3"	25
8SB	3-1/2"	3-1/2"	25
9SB	4"	4"	10



0B

•Our standard Conduit Hangers come Zinc Plated or made from 304 Stainless Steel

•Available with or without bolt and nut attached

•The original conduit hanger available for 1-1/2" through 5" conduit



0


Available made from Aluminum or brass, or steel that has been Hot Dip Galvanized or Copper Plated. Call Customer Service for pricing and minimum order quantities.

Catalog Number	Zinc Plated Steel Fits EMT	Rigid	Std Pkg
0	1/2"	3/8"-1/2"	100
1	3/4"	3/4"	100
2	1"	1"	100
2-1/2	1-1/4"	---	100
3	1-1/2"	1-1/4"	100
4	---	1-1/2"	100
5	2"	2"	50
6	2-1/2"	2-1/2"	50
7	3"	3"	25
8	3-1/2"	3-1/2"	25
9	4"	4"	10
10	---	5"	10

Catalog Number	STAINLESS STEEL Fits EMT	Rigid	Std Pkg
0S	1/2"	3/8"-1/2"	100
1S	3/4"	3/4"	100
2S	1"	1"	100
2-1/2S	1-1/4"	---	100
3S	1-1/2"	1-1/4"	100
4S	---	1-1/2"	100
5S	2"	2"	50
6S	2-1/2"	2-1/2"	50
7S	3"	3"	25
8S	3-1/2"	3-1/2"	25
9S	4"	4"	10

Conduit/Cable/Wire

Our Most
Economical
Conduit Hanger -
NO NUT NEEDED!



Conduit Hanger

- Modeled after Minerallac's Standard Conduit Hangers, the K Series incorporates value and ease of use.
- Parts come with bolts only. Keyhole design eliminates need for nut.
- Made from pre-galvanized steel
- Turn to page 288 for Dimension Chart on these parts.


Catalog Number	Zinc Plated Steel Fits EMT	Rigid	Std Pkg
K0B	1/2"	3/8"-1/2"	100
K1B	3/4"	3/4"	100
K2B	1"	1"	100

**K0B**

U.S. Patent No. 4,479,625



ONE-HOLE STRAPS



Minerallac has the widest variety of one-hole straps in the industry. If you can't find it at Minerallac, it probably doesn't exist.

Minerallac manufactures five grades of one-hole straps to fit any budget, any application. And many of our one-hole straps are available in other materials, other finishes -- stainless steel, brass, copper plated steel or hot dip galvanized steel.

From our most economical K-series one-hole straps to our best quality heavy-duty one-hole straps, you can't find a wider selection or better value anywhere.

As the grade goes up, so does the thickness and width of material used to manufacture the part. See our dimension charts on pages 288 and 290 for comparison.

Conduit/Cable/Wire**One-Hole Jiffy Clips in Five Grades**

K-Series
Most Economical



“Standard” Series
The “original” Jiffy Clip



“Min-E®” Series
Best Value



“Medium” Series
Most Popular



“Heavy Duty” Series
Best Quality

• *Precision made one-hole pipe straps with snap-on feature*

• *Pre-Galvanized Steel*

**Our Most
Economical
Jiffy Clip!**



K45


K-Series One-Hole Strap, Jiffy Clip

Catalog Number	Fits EMT	Std Pkg
K30	1/2"	100
K45	3/4"	100
K55	1"	100

**One-Hole Strap - Jiffy Clip**

•These one-hole pipe straps are ideal for hanging tubing, pipe, conduit and BX cable.

•Pre-Galvanized Steel

**165****STANDARD Series One-Hole Strap, Jiffy Clip**

Catalog Number	Fits Tube Size	Marking on Clip	Std Pkg
102	1/8"	---	100
103	3/16"	---	100
105	1/4"	---	100
110	5/16"	---	100
115	3/8"	115	100
125	1/2"	125	100
135	3/4"	750	100
150	1"	150	100
165	1-1/2"	1-1/4"	100

STANDARD Series One-Hole Strap, Jiffy Clip

Catalog Number	Fits EMT	Marking on Clip	Std Pkg
130	1/2"	130	100
145	3/4"	145	100
155	1"	1"	100
165	1-1/4"	1-1/4"	100
170	1-1/2"	1-1/4"	100

STANDARD Series One-Hole Strap, Jiffy Clip

Catalog Number	Fits Rigid	Marking on Clip	Std Pkg
120	1/8"	120	100
121	BX, 2-14, 3-14, 2-12	---	100
125	1/4"	125	100
140	1/2"	140	100
150	3/4"	150	100
160	1"	1"	100
170	1-1/4"	1-1/4"	100

Parts above also available Copper Plated or made from Brass.
Call Customer Service for pricing and minimum order quantities.

Conduit/Cable/Wire

- *MinE® clips have an inverted rib providing more strength at the bend of the clip. Snap-on feature leaves both hands free to work.*

- *Pre-Galvanized Steel*

MINE30

MIN-E® Series One-Hole Strap, Jiffy Clip

Catalog Number	Fits EMT	Std Pkg
MINE30	1/2"	100
MINE45	3/4"	100
MINE55	1"	100

Catalog Number	Fits Rigid	Flexible Conduit	Std Pkg
MINE28	---	3/8"	100
MINE40	1/2"	1/2"	100
MINE50	3/4"	3/4"	100

Parts above also available Copper Plated. Call Customer Service for pricing and minimum order quantities.

- *No hole spotting necessary*
- *Minerallac's best-selling zinc plated one-hole strap coupled with the patented Rawl Spike®*
- *Ideal for all masonry product!*
- *Rubber washer secures spike to strap*

MED30RS


MEDIUM Series, Jiffy Clip W/Rawl Spike®

Catalog Number	Fits EMT	Std Pkg
MED30RS	1/2" with Rawl Spike®	100
MED45RS	3/4" with Rawl Spike®	100
MED55RS	1" with Rawl Spike®	100

Table showing Rawl Spike® Load Capacities shown on page 295.



MED30



- Our best-selling precision made one-hole conduit and pipe straps
- Clips have an inverted rib providing more strength at the bend of the clip and holding the clip on the conduit, leaving both hands free to work.
- Both zinc plated steel and stainless steel Medium Jiffy Clips are available.

MEDIUM Series One-Hole Strap, Jiffy Clip

Catalog Number	Zinc Plated Steel		Std Pkg
	Fits EMT	Fits Rigid/IMC	
MED30	1/2"	---	100
MED40	---	1/2"	100
MED45	3/4"	---	100
MED50	---	3/4"	100
MED55	1"	---	100
MED60	---	1"	100
MED65	1-1/4"	---	100
MED70	---	1-1/4"	100
MED75	1-1/2"	---	50
MED80	---	1-1/2"	50
MED85	2"	---	50
MED90	---	2"	50



Catalog Number	STAINLESS STEEL		Std Pkg
	Fits EMT	Fits Rigid/IMC	
MED30SS	1/2"	---	100
MED40SS	---	1/2"	100
MED45SS	3/4"	---	100
MED50SS	3/4"	3/4"	100
MED55SS	1"	---	100
MED60SS	---	1"	100
MED70SS	---	1-1/4"	100
MED80SS	---	1-1/2"	50
MED90SS	---	2"	50

Also available hot dip galvanized steel. Call Customer Service for pricing and minimum order quantities.


Conduit/Cable/Wire

- *With the same original inverted rib and "Snap-On" features as the medium Jiffy clip, this is our best quality, heavy-duty one-hole strap series.*

- *Zinc plated steel*

**H30****HEAVY DUTY Series One-Hole Strap, Jiffy Clip**

Catalog Number	Fits EMT	Fits Rigid/IMC	Std Pkg
H30	1/2"	---	100
H40	---	1/2"	100
H45	3/4"	---	100
H50	---	3/4"	100
H55	1"	---	100
H60	---	1"	100
H65	1-1/4"	---	100
H70	---	1-1/4"	100
H75	1-1/2"	---	50
H80	---	1-1/2"	50
H85	2"	---	25
H90	---	2"	25
H92	2-1/2"	2-1/2"	25
H94	3"	3"	10
H95	3-1/2"	3-1/2"	10
H96	4"	4"	10
H97	---	5"	10
H98	---	6"	10




One-Hole Slotted Jiffy Clip

- *Slotted Jiffy Clips are a one-hole pipe strap with slotted mounting hole. This enables the installer to final position the clips after the run is completed.*
- *Copper Plated Steel*

Catalog Number	Copper Tubing	Rigid/IMC	Std Pkg
105SC	1/4"	---	100
115SC	3/8"	---	100
125SC	1/2"	1/4"	100

Also available made from Brass. Call Customer Service for pricing and minimum order quantities.




125SC

Traditional

M Minerallac®

Conduit/Cable/Wire




One-Hole Duplex Jiffy Clip


- *For positioning double lines, these one-hole pipe clamps are ideal for cable, conduit, tube, BX or combinations thereof*
- *Zinc plated steel*
- *Turn to page 291 for Dimension Chart on these parts.*

Catalog Number	Fits O.D.	Fits O.D.	Std Pkg
300A	.125"	.125"	100
300	.250"	.250"	100
301	.375"	.375"	100
305	.500"	.500"	100

Also available made from brass or copper plated steel. Call Customer Service for pricing and minimum order quantities.



300A




Slotted Duplex Jiffy Clip



- *For positioning double lines*
- *These copper plated steel parts provide compatibility with copper*
- *Turn to page 291 for Dimension Chart on these parts.*

Catalog Number	Fits O.D.	Fits O.D.	Std Pkg
300SC	.250"	.250"	100
301SC	.375"	.375"	100

Other sizes are also available. Call Customer Service for pricing and minimum order quantities.



300SC

Conduit/Cable/Wire**Conduit Strap - Two-Hole Metal****230**

Catalog Number	Zinc Plated Steel Fits EMT	Std Pkg
230	1/2"	100
245	3/4"	100
255	1"	100
265	1-1/4"	100
275	1-1/2"	100
285	2"	100
292	2-1/2"	50
294	3"	25

Catalog Number	STAINLESS STEEL Fits EMT	Std Pkg
230SS	1/2"	100
245SS	3/4"	100

Also available made from Brass or Hot Dip Galvanized steel. Call Customer Service for pricing and minimum order quantities.

For information on Plastic Two-Hole Straps, available in nine sizes, turn to page 173.



- *Two-hole metal straps are designed for use on loads too heavy to be supported by one-hole Jiffy Clips.*
- *Pre-Galvanized steel or zinc plated after fabrication depending on size*
- *Available in zinc plated steel or made from stainless steel for corrosive environments*
- *Turn to page 292 for Dimension Chart on these parts.*

Catalog Number	Zinc Plated Steel Fits Rigid or BX	Std Pkg
225	1/4"	100
228	3/8"	100
240	1/2"	100
250	3/4"	100
260	1"	100
270	1-1/4"	100
280	1-1/2"	100
290	2"	50
292	2-1/2"	50
294	3"	25


Catalog Number	STAINLESS STEEL Fits Rigid or BX	Std Pkg
240SS	1/2"	100
250SS	3/4"	100

Also available made from Brass or Hot Dip Galvanized steel. Call Customer Service for pricing and minimum order quantities.


For information on Plastic Two-Hole Straps, available in nine sizes, turn to page 173.

Conduit/Cable/Wire

- *Heavy-Duty Two-Hole Straps are designed for heavy loads.*
- *Pre-Galvanized Steel*
- *Turn to page 292 for Dimension Chart on these parts.*



Conduit Strap - Two-Hole Metal




Heavy Duty!

HD260

Catalog Number	Fits EMT	Fits Rigid	Std Pkg
HD260	---	1"	100
HD270	---	1-1/4"	100
HD280	---	1-1/2"	50
HD290	---	2"	25
HD292	2-1/2"	2-1/2"	25
HD294	3"	3"	10
HD295	3-1/2"	3-1/2"	10
HD296	4"	4"	10
HD297	---	5"	10
HD298	---	6"	10


Also available in hot dip galvanized steel. Call Customer Service for pricing and minimum order quantities.



Multi-Purpose Closed Clip

- *Supports tubing pipe in sizes 1/4" O.D.*
- *Pre-Galvanized Steel*


Catalog Number	Tubing O.D.	Std Pkg
1105	1/4"	100



1105

Conduit/Cable/Wire

- Secures type SEU service entrance cables
- Available in Zinc Plated Steel or made from Aluminum
- Turn to page 293 for Dimension Chart on these parts.



Service Entrance Straps - One Hole

MED2




Description for SEU

Catalog Number	Inside Dia.	Cable Size	Std Pkg
MED2	.460	NM (Romex)	100
MED3	.550	UF	100
MED5	1.050	---	100
MED7	.835	6,4	100
MED9	.970	---	100
MED12	1.090	2	100
MED13	1.275	1/0 & 2/0	100
MED14	1.465	---	100
MED16	1.675	---	100
H12	1.209	---	100
H14	1.330	---	100
H16	1.570	4/0	100

ALUMINUM

MED12A	1.090	2	100
MED13A	1.275	1/0 & 2/0	100
H16A	1.570	4/0	100




Service Entrance Straps - One Hole


- Secures type SER service entrance cables
- Pre-Galvanized Steel
- Turn to page 289 for Dimension Chart on these parts.

Description for SER & BX

Catalog Number	Zinc Plated Steel Fits Rigid or BX	Std Pkg
121	BX, 2-14, 3-14, 2-12	100
125	BX, 3-12, 2-10, 3-10 SER 8	100
130	6, 4	100
140	2	100
145	1, 1/0	100
150	2/0	100
155	3/0	100
160	4/0	50




Traditional

M Minerallac®**Conduit/Cable/Wire****Service Entrance Straps - Two Hole**


- *Secures type SEU service entrance cables*
- *Pre-Galvanized Steel*
- *Turn to page 293 for Dimension Chart on these parts.*

Catalog Number	Description for SEU	Std Pkg
221	UF	100
212	Inside Width .635"	100
223	2	100
2203	1, 1/0, 2/0	100
2403	3/0, 4/0	100


**221**



- Secures type SER & BX service entrance cables
- Available made from pre-galvanized steel or stainless steel
- Turn to page 294 for Dimension Chart on these parts.



Service Entrance Straps - Two Hole




250

Catalog Number	Zinc Plated Steel Description for SER & BX	Std Pkg
225	BX, SER 8	100
228	6	100
230	4	100
240	2	100
245	1, 1/0	100
250	2/0	100
255	3/0	100
260	4/0	100

Catalog Number	STAINLESS STEEL Description for SER & BX	Std Pkg
230SS	4	100
240SS	2	100
245SS	1, 1/0	100
250SS	2/0	100



Traditional

M Minerallac®**Conduit/Cable/Wire****Conduit & Box Support Fasteners**


- *Secures conduit and electrical boxes to most structures*
- *Provides conduit support on both sides of electrical box*
- *With hole for screw or threaded rod mount or with 1/4"-20 x 5/8" stud*
- *Made from pre-galvanized steel with Black Claw™ spring steel fasteners riveted to part*

Catalog Number	Mount 4" square boxes For Use With	Std Pkg
CBS18KC38	3/8" conduit	25
CBS18KC1234	1/2", 3/4" conduit	25
CBS18KC1	1" conduit	25

Catalog Number	Stud Mount 4" square boxes For Use With	Std Pkg
CBS18KC38ST	3/8" conduit	25
CBS18KC1234ST	1/2", 3/4" conduit	25
CBS18KC1ST	1" conduit	25

CBS18KC1234**CBS18KC1234ST**

This part with beam clamp attachment found on page 146.




Conduit & Box Support Fasteners

- Secures conduit and electrical boxes to most structures
- Provides conduit support on both sides of electrical box
- With hole for screw or threaded rod mount or with 1/4"-20 x 5/8" stud
- Made from pre-galvanized steel with Black Claw™ spring steel fasteners riveted to part

Catalog Number	Mount 4" square boxes For Use With	Std Pkg
CBS18HIC50	1/2" conduit	25
CBS18HIC75	3/4" conduit	25
CBS18HIC100	1" conduit	25


Catalog Number	Stud mount 4" square boxes For Use With	Std Pkg
CBS18HIC50ST	1/2" conduit	25
CBS18HIC75ST	3/4" conduit	25
CBS18HIC100ST	1" conduit	25

CBS18HIC100




CBS18HIC100ST

This part with beam clamp attachment found on page 146.


Conduit/Cable/Wire**Conduit & Box Support Assembly**

- *Provides conduit support on both sides of electrical box.*
- *Attaches to #12 wire thru 1/4" rod.*
- *Made from pre-galvanized steel with Black Claw™ spring steel fasteners riveted to part.*

Catalog Number	Mount 4" Square Boxes For Use With	Std Pkg
CBS18KC38APS	3/8" conduit	25
CBS18KC1234APS	1/2" to 3/4" conduit	25
CBS18KC1APS	1" conduit	25

**CBS18KC1234APS**


This part with beam clamp attachment, instead of multi-function clip shown above, found on page 146



Conduit & Box Support Assembly

- Provides conduit support on both sides of electrical box.
- Attaches to #12 wire thru 1/4" rod.
- Made from pre-galvanized steel with Black Claw™ spring steel fasteners riveted to part.

Catalog Number	Mount 4" Square Boxes For Use With	Std Pkg
CBS18HIC50APS	1/2" conduit	25
CBS18HIC75APS	3/4" conduit	25
CBS18HIC100APS	1" conduit	25




CBS18HIC100APS


This part with beam clamp attachment, instead of multi-function clip shown above, found on page 146.

Conduit/Cable/Wire

- For rigid, IMC or EMT conduit
- Knurling on shank of round nail straps, and barbs on flat nail straps minimize back-out
- Round nail straps are zinc plated after fabrication
- Flat nail straps are made from pre-galvanized steel.



Nail Straps



NS100



NS75



NS50

Catalog Number	Description Fits Rigid Conduit, IMC or EMT	Std Pkg
NS50	1/2" Flat Style	100
NS75	3/4" Flat Style	100
NS100	1" Flat Style	100



RNS100





RNS75



RNS50

Catalog Number	Description Fits Rigid Conduit, IMC or EMT	Std Pkg
RNS50	1/2" Round Style	100
RNS75	3/4" Round Style	100
RNS100	1" Round Style	100



Wire/Cable Support


- Provides for secure installation of a variety of cable combinations quickly and easily
- Mount support to either wood or metal studs with nails or screws.
- Made from high quality UV protected material

Catalog Number	Description	Std Pkg
----------------	-------------	---------

C6

Multi-Wire/Cable Support


100



C6

Patent Pending

Traditional

M Minerallac®**Conduit/Cable/Wire****Ground Wire Clip**


- *Easy to use. Simply place wire into elbow, hammer nail through hole, then bend extension over nail head.*
- *Made from pre-galvanized steel*

Catalog Number	Description	Standard Package
----------------	-------------	------------------


GWC1

Ground Wire Clips

1000

**GWC1**

Also available in copper. Call Customer Service for pricing and minimum order quantities.



Multi-Use Wire Clip

- *Easy to use. Simply place wire into elbow, and secure with nail or screw.*
- *Made from pre-galvanized steel*


Catalog Number	Description	Standard Package
----------------	-------------	------------------

GH3


Wire Clip

1000

GH3



Beams




Beam Clamps - Universal


- Used with Minerallac conduit hangers #0 to #5, bridle rings and threaded rod. Tapped for rods bottom and back except #602 (bottom only)
- Case hardened steel set screw tapped at an angle locks on beam
- Available in Zinc Plated Steel or made from Stainless Steel
- Turn to page 294 for Dimension Chart on these parts.

Catalog Number	Zinc Plated Steel			Std Pkg
	Fits Flange	Tapping	Drop Rod	
600	1/2"	1/4"-20	1/4"	50
60010	1/2"	#10-24	#10-24	50
602	3/4"	3/8" bottom only	3/8"	25
602B	3/4"	3/8"-16	3/8"	25

Catalog Number	STAINLESS STEEL			Std Pkg
	Fits Flange	Tapping	Drop Rod	
602BSS	3/4"	3/8"-16	3/8"	25

600






Beam Clamps - Malleable

- Used with Conduit Hangers, Bridle Rings and Drop Rods, 3/8" to 1/2". Tapped for rods bottom and back on all sizes
- Malleable Zinc Plated Steel
- Turn to page 295 for Dimension Chart on these parts.


Catalog Number	Zinc Plated Steel			Std Pkg
	Fits Flange	Tapping	Drop Rod	
700	To 3/4" thick	1/4"-20	1/4"	50
70010	To 3/4" thick	#10-24	#10-24	50
701	To 3/4" thick	5/16"-18	5/16"	25
702	To 3/4" thick	3/8"-16	3/8"	25
703	To 7/8" thick	1/2"-13	1/2"	25




700

Beams


- Our #600 beam clamp with #0 through #5 Conduit Hangers attached
- Offered with or without nut bolt attached
- Zinc plated steel



Beam Clamp Assemblies



A0600



A0600B


Catalog Number	Fits EMT	Fits Rigid/IMC	Std Pkg
A0600	1/2"	3/8"-1/2"	100
A1600	3/4"	3/4"	100
A2600	1"	1"	100
A2-1/2 600	1-1/4"	---	100
A3600	1-1/2"	1-1/4"	100
A4600	---	1-1/2"	50
A5600	2"	2"	50

W/Bolt

Catalog Number	Fits EMT	Fits Rigid/IMC	Std Pkg
A0600B	1/2"	3/8"-1/2"	100
A1600B	3/4"	3/4"	100
A2600B	1"	1"	100
A2-1/2 600B	1-1/4"	---	100
A3600B	1-1/2"	1-1/4"	100
A4600B	---	1-1/2"	50
A5600B	2"	2"	50




- Our #600 zinc plated beam clamp with Black Claw™ Spring Steel Fast Support hanger attached
- Bottom or back mounted




Beams

Beam Clamp Assemblies



60075



60075B

BOTTOM MOUNTED


Catalog Number	Fits EMT	Fits Rigid/IMC	Std Pkg
60050	1/2"	---	100
60075	3/4"	1/2"	100
600100	1"	3/4"	100

BACK MOUNTED


Catalog Number	Fits EMT	Fits Rigid/IMC	Std Pkg
60050B	1/2"	---	100
60075B	3/4"	1/2"	100
600100B	1"	3/4"	100

Beams


- Our #600 zinc plated beam clamp with Black Claw™ Spring Steel Kombo Clip attached
- Bottom or back mounted



Beam Clamp Assemblies



600KC1234




600KC1234B

BOTTOM MOUNTED

Catalog Number	Fits Conduit	Std Pkg
600KC1234	1/2"-3/4"	100
600KC1	1"	100
600KC114	1-1/4"	100
600KC112	1-1/2"	100
600KC2	2"	100

BACK MOUNTED


Catalog Number	Fits Conduit	Std Pkg
600KC1234B	1/2"-3/4"	100
600KC1B	1"	100
600KC114B	1-1/4"	100
600KC112B	1-1/2"	100
600KC2B	2"	100



Beam Clamp - Two Piece


- Fits flanges from 1-5/8" to 2-5/8" width with Static Load Capacity of 100 lbs
- 1/4"-20 stud with square nut
- Zinc plated steel

Catalog Number	Description	Std Pkg
2SC4	Fits 1-5/8" to 2-5/8" Flanges	100



2SC4


Beams




Beam Mount Conduit & Box Support Assembly

- Provides conduit support on both sides of electrical box
- Attaches to beam flanges from 1/8" to 1/2" thick
- Made from pre-galvanized steel with Black Claw™ spring steel fasteners riveted to part

Catalog Number	Mount 4" Square Boxes Conduit Size	Flange Thickness	Std Pkg
CBS18KC3818	3/8"	1/8"-1/4"	25
CBS18KC38516	3/8"	5/16"-1/2"	25
CBS18KC123418	1/2"-3/4"	1/8"-1/4"	25
CBS18KC1234516	1/2"-3/4"	5/16"-1/2"	25
CBS18KC118	1"	1/8"-1/4"	25
CBS18KC1516	1"	5/16"-1/2"	25




CBS18KC123418



Beam Mount Conduit & Box Support Assembly


- Provides conduit support on both sides of electrical box
- Attaches to beam flanges from 1/8" to 1/2" thick
- Made from pre-galvanized steel with Black Claw™ spring steel fasteners riveted to part

Catalog Number	Mount 4" Square Boxes Conduit Size	Flange Thickness	Std Pkg
CBS18HIC5018	1/2"	1/8"-1/4"	25
CBS18HIC50516	1/2"	5/16"-1/2"	25
CBS18HIC7518	3/4"	1/8"-1/4"	25
CBS18HIC75516	3/4"	5/16"-1/2"	25
CBS18HIC10018	1"	1/8"-1/4"	25
CBS18HIC100516	1"	5/16"-1/2"	25



CBS18HIC10018


Metal Stud & Drywall




Box Mounting Bracket

- Supports electrical boxes located between studs on 16" or 24" centers. Boxes attach using self-tapping screws
- Made from pre-galvanized steel

Catalog Number	Description	Std Pkg
BMB16	1-1/2" box to studs on 16" centers	50
BMB16D	2-1/2" box to studs on 16" centers	50
BMB24	1-1/2" box to studs on 24" centers	50
BMB24D	2-1/2" box to studs on 24" centers	50




BMB16




Box to Bar Fastener

- *Black Claw™ Spring Steel hardware is included.*
- *Bars made from pre-galvanized steel*

Catalog Number	Description	Std Pkg
BAR	1 Straight 26"-long bar 1 BBC, 2 BSC	50
RBAR	1 Offset 26"-long bar 2 BBC, 2 BSC	50




Metal Stud & Drywall




Universal Front-Mount Bracket

- For “between the studs” mounting of a variety of box types, shapes and sizes
- Freedom of hanging a box at any point between the studs
- No need to fabricate special brackets in the shop or on the job site
- Made from 22 gauge pre-galvanized steel

Catalog Number	Description	Std Pkg
UFMB16	For 16” stud spacing	25
UFMB24	For 24” stud spacing	25




UFMB24



UFMB16

US Patent No. 5,330,137



Box Mounting Bracket

- *Bracket supports electrical boxes from floor or channels*
- *Can be used at three heights*
- *Made from pre-galvanized steel*

Catalog Number	Description	Std Pkg
----------------	-------------	---------

BS18


Break-A-Way feature for
12", 16", 18" lengths

50



BS18

Metal Stud & Drywall



Additional Box Support


- Provides additional support for boxes by supporting to drywall
- Installed using screwdriver only
- Made from pre-galvanized steel


Catalog Number	Description	Std Pkg
----------------	-------------	---------

BS

Mounts box directly to wall

100



BS



Box Stabilizer Support


- *Screw attached support for electrical boxes*
- *Made from pre-galvanized steel*

Catalog Number	Description	Std Pkg
FBO23	Box support for 2-1/2" and 3-1/2" wood or metal studs	100
FBO234	Box support for 2-1/2", 3-1/2" and 4" wood or metal studs	100
FBO6	Box support for 6" wood or metal studs	100



FBO234


Metal Stud & Drywall




Far Side Box Support

- *No tools required. Mounts quickly in the back of the box -- just push in and snap tight*
- *Designed for 3-5/8" steel studs*
- *May be used on standard 1-1/2" or 2-1/8" deep boxes*

Catalog Number	Description	Std Pkg
DLS1	Designed for use with 3-5/8" steel studs. May be used on standard 1-1/2" boxes or 2-1/8" deep boxes.	100



DLS1



Box Support


- *Quick installation*
- *One-piece break-away design*
- *Box is supported by drywall. No stud is necessary*
- *Prevents box from pulling out of drywall*
- *Made from pre-galvanized steel*

Catalog Number	Description	Std Pkg
----------------	-------------	---------


BST

Secures electrical box to finished drywall

100 sets



BST


Metal Stud & Drywall**Outlet Retainer**

- *Mounts standard outlets and wall switches in oversize openings, lending stability and preventing broken cover plates*
- *Made from pre-galvanized steel*

Catalog Number	Description	Std Pkg
----------------	-------------	---------

ORMounts standard outlets
in oversize openings


100

**OR**



A Tradition of Quality Since 1894

The Minerallac Idea Network




Do you have an idea or suggestion regarding our products? Perhaps you know a way to make a job easier. Your thoughts are important to us and to the industry, and we welcome them. Please write to us via fax, mail, or e-mail. With your input, we will continue to provide the quality hardware and the valuable information contractors need to get the job done efficiently.



100 Gast Road • Hampshire, IL 60140
Toll Free Phone: 1-877-285-2200
Toll Free Fax: 1-800-824-8942
e-mail: CustomerService@minerallac.com

Acoustical



Box to T-Bar Fastener


- *Snap-on 24" span box hanger with dual height adjustment allows flush or 3/4" offset mount.*
- *Zinc plated steel with Black Claw™ spring steel hardware included.*


Catalog Number	Description	Std Pkg
----------------	-------------	---------

TBAR

 24"-long box hanger,
1 BBC mounting clip
with screw

50



TBAR



Lighting Support Assembly


- *Snap-on 24" fixed span with adjustable fixture position.*
- *Installed with screwdriver.*
- *Zinc plated steel with Black Claw™ spring steel hardware.*

Catalog Number	Description	Std Pkg
LSBAR	Fits LIGHTOILER 5 and CALCULITE® Series fixtures	25 Sets



LSBAR

Acoustical



T-Bar Hanger, Two Piece


- Mounts fixtures or boxes to 1" T-bar with Static Load Capacity of 75 lbs
- Stud is flat head, square shouder carriage bolt which will not turn when posiitoned in slot. Assembled with 1" OD wing nut washer


Catalog Number	Description	Std Pkg
----------------	-------------	---------

SCT2

Has 1/4"-20 x 5/8" Stud with wing nut & washer

50



SCT2



T-Bar Scissor Clips


- *Two-piece zinc plated clip used for mounting fixtures or boxes to 1" T-bar with Static Load Capacity of 100 lbs*
- *Includes wing nut washer*

Catalog Number	For Use With		Std Pkg
	Stud Length	T-Bar	
SCX1W	5/8"	1"	50
SCX1XL	2"	1"	50



SCX1W

Acoustical



T-Bar Drop Wire Clip

• These pre-galvanized clips support fixtures transmitting the weight of the fixture directly to the building structure, thus relieving the tee grid from any load stress. Also adds rigidity and support for truer alignment of the tee grid. Made from one-piece construction to accommodate various styles of tee grid.

• Includes wing nut washer

Catalog Number	For Use With		Standard Package
	Stud Length	T-Bar	


DWC1

5/8"

1"

50


DWC1



Voice/Data & Low Voltage

Another Solution for Today's Challenging Installations!

The new 2" J-Hook cable support system, designed to be versatile, can be attached to a wide variety of structures using beam clamps, clips, and many other support components available from Minerallac. The wide-base support eliminates the undesirable impact of point-loads that can cause band-width deterioration and damage to Category 5, fiber-optic, and other sensitive cables. This unique system is labor and time-saving -- another efficient method of cable installation!



J-Hook Cable System

- *Cost effective alternative to expensive cable tray*
- *Accommodates Category 5, fiber-optic and interduct*
- *Provides support without stress to sensitive voice/data cables*
- *Continuous wide-base radius supports natural curve of cable eliminating kinking, bending and crimping*
- *Cable wire retainer is supplied with every part.*



A Tradition of Quality Since 1894



Fig 1



Fig 2



Fig 3



Fig 4



Fig 5



Fig 6




Fig 7



Fig 8




Fig 9



Fig 10





Fig 11



Patent
Pending

Catalog Number	Fig	Description	Std Pkg
J200	1	2" J Hook	50
J200B	2	2" J Hook W/Bracket	50
J200ABC25	3	Hammer on - 1/16"-1/4" angled Z Purlin	50
J200APS	4	Fits #12 wire thru 1/4" rod and 1/8"-3/8" flange	50
J200SFC18	5	Hammer on - 1/8"-1/4" flange	50
J200SFC516	5	Hammer on - 5/16"-1/2" flange	50
J200SFC916	5	Hammer on - 9/16"-3/4" flange	50
J200VBC25	6	Hammer on - 1/16"-1/4" vertical flange	50
J200600	7	Screw on - Up to 1/2" flange	50
J200500	8	Screw on - Up to 1/2" flange	50
J200BBC18	9	Hammer on - 1/8"-1/4" flange	50
J200BBC516	9	Hammer on - 5/16"-1/2" flange	50
J200BBC916	9	Hammer on - 9/16"-3/4" flange	50
J200B600	10	Screw on - Up to 1/2" flange	50
J200B500	11	Screw on - Up to 1/2" flange	50

Voice/Data & Low Voltage



Cable Support - Bridle Rings


- *Supports communications cable and other low voltage uses. Used with Minerallac Beam Clamps*
- *Zinc plated steel*

Catalog Number	Ring Size	Thread	Std Pkg
634R	1" Dia.	10-24	100
646R	1-1/2" Dia.	1/4"-20	100
648R	2" Dia.	1/4"-20	100
654R	4" Dia.	1/4"-20	50

Also available in stainless steel. Call Customer Service for pricing and minimum order quantities.



648R



Cable Support - Bridle Rings

- *Supports communications cable and other low voltage uses from wood beams*
- *Zinc plated steel*

Catalog Number	Ring Size	Thread	Std Pkg
634RW	1" Dia.	3/16"	100
646RW	1-1/2" Dia.	1/4"	100
648RW	2" Dia.	1/4"	100


Also available in stainless steel. Call Customer Service for pricing and minimum order quantities.




648RW

Voice/Data & Low Voltage

- Cost effective alternative to cable tray
- Wide surface saddle provides support without stress for category 5, fiber-optic, and other sensitive voice/datacom cables.
- Available as assembled units or saddle only for retrofit
- Saddle molded onto 4" bridle ring




Cable Support - Bridle Rings



BRS2

US Patent No. 6,325,338



648RS

Catalog Number	Mechanical Thread Saddle Assy Description	Std Pkg
----------------	---	---------

646RS	1-1/2" Bridle Ring W/Saddle	50
--------------	-----------------------------	----

648RS	2" Bridle Ring W/Saddle	50
--------------	-------------------------	----

654RS	4" Bridle Ring W/Saddle	50
--------------	-------------------------	----

Catalog Number	Lag Thread Saddle Assy Description	Std Pkg
----------------	------------------------------------	---------


646RWS	1-1/2" Bridle Ring W/Saddle	50
---------------	-----------------------------	----

648RWS	2" Bridle Ring W/Saddle	50
---------------	-------------------------	----

Catalog Number	SADDLE ONLY Description	Std Pkg
----------------	-------------------------	---------

BRS15	Snaps into 1-1/2" Bridle Ring	50
--------------	-------------------------------	----

BRS2	Snaps into 2" Bridle Ring	50
-------------	---------------------------	----



Universal Metal Stud Grommet


- *Protects wires from damage by metal studs*
- *All pieces are the same shape eliminating the hassle of stocking right and left grommet parts.*
- *Easy to install - no tools required*
- *Complies with 2002 NEC Article 300.4(I)*

Catalog Number	Description	Std Pkg
----------------	-------------	---------

G100

Grommets for metal studs

50



G100

Traditional

M **Minerallac®**

Voice/Data & Low Voltage Cable Protection - Nail Plates



BJNP



NP6



BJNPH



NP6P



BJNPWO



NP6M



NP3



NP12



NP18



NP6STW




NP6ST



NP8




NP18FHA



- Protects data/com, PVC plumbing and electrical from punctures by nails or screws
- Styles with teeth attach to wood studs with hammer
- Styles with holes attach to wood or metal studs using nails or screws and a hammer or screwdriver
- Required for compliance with NEC 1990 Article 300.4A or Plumbing Code 305.8
- Constructed from pre-galvanized steel for corrosion resistance

Catalog Number	Size (Length x Width)	Std Pkg
BJNP	2-1/2" x 1-1/2"	100
BJNPH	2-1/2" x 1-1/2"	100
BJNPWO	2-1/2" x 1-1/2"	100
NP3	3" x 1-1/2"	100
NP6	6" x 1-1/2"	50
NP6P	6" x 1-1/2"	50
NP6M	6" x 1-1/2"	50
NP6ST	6" x 3-1/2"	50
NP6STW	6" x 3-1/2"	25
NP8	8" x 4-7/8"	25
NP12	12" x 1-1/2"	50
NP18	18" x 1-1/2"	50
NP18FHA	18" x 3-1/2"	25


Voice/Data & Low Voltage




Cable Support - D-Rings

- *Used to support multiple cable runs*
- *Smooth non-conductive surface won't damage cable*
- *Lower cost than steel distribution rings (D-rings)*
- *Parts made from high-strength, UV stabilized non-metallic composite*

Catalog Number	Ring Size (inside opening) Height x Width	Std Pkg
DR20	2.25" x 2"	50
DR30	3.25" x 3"	25
DR40	3.25" x 5"	10




DR40



Multi-Use 2-Hole Plastic Straps

- *Designed for strength*
- *Easy to install - Plastic straps fit snugly over PVC or rigid conduit*
- *Made from high quality UV stabilized and fire resistant material*


Catalog Number	Trade Size	Color	Std Pkg
PS50	1/2"	Gray	50
PS75	3/4"	Gray	50
PS100	1"	Gray	25
PS125	1-1/4"	Gray	25
PS150	1-1/2"	Gray	25
PS200	2"	Gray	25
PS250	2-1/2"	Gray	25
PS300	3"	Gray	10
PS400	4"	Gray	10



Metal two-hole straps, available in various sizes, found on pages 63 and 64.




Voice/Data & Low Voltage




Low Voltage Mounting Bracket

- *Provides base for securing communications lines without use of electrical box. Mounts standard plate*
- *Hardware included*
- *Made from Pre-galvanized steel*

Catalog Number	Description	Std Pkg
WBF1	Mounts standard low voltage plates	100




WBF1




Universal Front-Mount Bracket

- For “between the studs” mounting of a variety of box types, shapes and sizes
- Freedom of hanging a box at any point between the studs
- No need to fabricate special brackets in the shop or on the job site
- Made from 22 gauge pre-galvanized steel

Catalog Number	Description	Std Pkg
UFMB16	For 16” stud spacing	25
UFMB24	For 24” stud spacing	25



UFMB24



UFMB16


US Patent No. 5,330,137

Hardware/Accessories

- Available in zinc plated steel, aluminum or stainless steel.



Stove Bolt with Nut

**9408**


Catalog Number	Zinc Plated Steel Thread	Length	Std Pkg
9408	1/4"-20	1"	100
9410	1/4"-20	1-1/4"	100
9412	1/4"-20	1-1/2"	100
9816	1/2"-13	2-1/2"	25

ALUMINUM

9410A	1/4"-20	1"	100
--------------	---------	----	-----

STAINLESS STEEL

9408S	1/4"-20	1"	100
9410S	1/4"-20	1-1/4"	100
9412S	1/4"-20	1-1/2"	100
9816S	1/2"-13	2-1/2"	25



Wing Nut Washer

- Made from pre-galvanized steel.

Catalog Number	Wing Nut Washer Combo	Std Pkg
----------------	-----------------------	---------

14WNW

Fits 1/4"-20 bolt

100




14WNW

Traditional

M Minerallac®

Hardware/Accessories



Jack Chain

- *For support of light fixtures and signs*
- *Max. work load limit: 29 lbs*
- *Zinc plated steel*


Catalog Number	Description	Standard Package
----------------	-------------	------------------

JC12100

#12 Single Jack Chain

100 ft

**JC12100**



S-Hooks

- *For hanging Jack Chain to various overhead hangers*
- *Made from Pre-galvanized steel*

Catalog Number	Length	Standard Package
SH212	1-1/4"	100




SH212

Traditional


M Minerallac®

Hardware/Accessories

- Used for hanging large size pipe or duct
- Zinc plated steel



Perforated Strapping

**410C**

Catalog Number	Perforated Strap .035" x 3/4"	Std Pkg
----------------	-------------------------------	---------


410C	10 Foot Coils	100'
-------------	---------------	------

410C100	100 Foot Coils	100'
----------------	----------------	------

Catalog Number	Perforated Strap .05" x 7/8"	Std Pkg
----------------	------------------------------	---------

478C	10 Foot Coils	100'
-------------	---------------	------


Other lengths of .035" x 3/4" and .05" x 7/8" perforated strapping available. Call Customer Service for pricing and minimum order quantities.



Stud Clip Adapter


- *Right angle fixture for attaching “S” hooks, or Jack Chain to drop rods, scissor clips or stud clips*
- *Zinc plated steel*

Catalog Number	Description	Std Pkg
SCH48	For “S” hooks or fixture chain, used with SCX1X, 2SC4, SCT3 and SCT2	100



SCH48

Hardware/Accessories







Brackets

• *These components, used riveted to other Minerallac products, are available separately for a variety of applications.*

• *Zinc plated steel*

Catalog Number	Bolt Size	Std Pkg
BA	Angle bracket - 1/4" mounting hole	100
PBA	Angle bracket - 1/4" mounting hole with Torx hole at other end	100
BO	Offset bracket - 1/4" mounting hole	100


**BA****BO****PBA**



Bar Joist Washers

- *Durable, rugged washers simplify and speed up the job of hanging conduit from bar joists*
- *Zinc plated steel*

Catalog Number	Bolt Size	Std Pkg
BJW4	1/4"	50 pr
BJW6	3/8"	50 pr




BJW4



IMPACTTM STAPLES

***Taking the electrical industry
by storm!***

NEW!
Part Numbers



ImpactTM Staples -- The right staple for the job!

Minerallac has the largest selection of both fully insulated and non-insulated staples in the industry. We're sure to have the size, style, and packaging option that meets your specific requirements. Our most popular sizes of metal staples come with the standard dimple at the top -- or try our new "flat top" version. All plastic staples are made from high quality UV stabilized material for protection against harsh environments. We've added many new styles for a broader range of applications. For the toughest jobs, try staples with Phillips head screws or cement nails.

Packaging Options



Impact™ staples are packaged in conveniently sized individual boxes. Our most popular styles of impact™ staples are available in polybags, kraft bags or bulk packed in kegs and reusable plastic pails.



Square Jars

New square jars with finger indent for pouring ease.

Plastic Pails

Try Impact™ staples in our unique square-shaped pails. This weather-tight, sturdy, tip-resistant pail is easy to carry from job to job and has various other storage uses once the pail is empty.

Four sizes of plastic pails are available. Call Customer Service for details.

Features

Non-Insulated & Insulated Metal Impact™ Staples



- *Designed for mosts cable types*
- *Leg design minimizes wood splitting*
- *Staples are deburred and polished*
- *Rust inhibitor applied for longer shelf life*
- *Box or bulk packed*
- *Available in reusable plastic pails*
- *Electro-galvanized finish available for corrosive environments.*
- *Heavy-Duty 1" x 1/2" available to help eliminate "bending" when driven into hard wood.*
- *New "Flat Top" Version available for 1" x 1/2" and 1-1/4" x 9/16".*
- *Two new types of insulated metal cable staples now available for 1" x 1/2" and 1-1/4" x 9/16" sizes -- PVC dipped and with Plastic Insulator, both in optic blue for high visibility*
- *New line of Utility Staples now available for voice/data installations.*






Insulated Plastic Impact™ Staples

- *Provide secure mounting without damage to wire and cable*
- *Zinc plated nails are designed to minimize wood splitting*
- *Pre-positioned nails ensure quick installation, even in vertical and overhead positions.*
- *Hardened Nails, Cement Nails, Phillips Head and Phillips Hex Head Screws are now available on some styles.*
- *Box, bag or bulk packed*
- *Available in reusable plastic pails*
- *Staples are made from high impact UV stabilized material for severe weather conditions.*
- *A variety of new staples added for a broader range of applications.*



Non-Insulated Metal Staples

Cable Staples



**Standard Style
Cable Staple**



**Flat Top Style
Cable Staple**

Cable Size: 2 Conductor (#12 & #14) Romex®. and other type NM cable

Catalog Number	Style and Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I10A	Standard Style 1" x 1/2"	Box of 100	10,000
I10C		Box of 500	10,000
I10G		Jar of 500	3,000
I10M		Keg of 5,000	5,000
I10N		Keg of 10,000	10,000
I10R		Pail of 5,000	5,000
I10T		Pail of 10,000	10,000
I10HA	Standard Style HEAVY DUTY 1" X 1/2"	Box of 100	10,000
I10HC		Box of 500	10,000
I10HG		Jar of 500	3,000
I10HM		Keg of 5,000	5,000
I10HN		Keg of 10,000	10,000
I10HR		Pail of 5,000	5,000
I10HT		Pail of 10,000	10,000
I10HFA	Flat Top Style HEAVY DUTY 1" x 1/2"	Box of 100	10,000
I10HFC		Box of 500	10,000
I10HFG		Jar of 500	3,000
I10HFM		Keg of 5,000	5,000
I10HFN		Keg of 10,000	10,000
I10HFR		Pail of 5,000	5,000
I10HFT		Pail of 10,000	10,000



Cable Size: 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other cable

Catalog Number	Style and Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I12A	Standard Style	Box of 100	5,000
I12B	1-1/4" x 9/16"	Box of 250	5,000
I12C		Box of 500	5,000
I12G		Jar of 500	3,000
I12M		Keg of 5,000	5,000
I12R		Pail of 5,000	5,000
I12S		Pail of 7,500	7,500
I12FA	Flat Top Style	Box of 100	5,000
I12FB	1-1/4" x 9/16"	Box of 250	5,000
I12FC		Box of 500	5,000
I12FG		Jar of 500	3,000
I12FM		Keg of 5,000	5,000
I12FR		Pail of 5,000	5,000

Cable Size: S.E.U. 6/3 Cable


Catalog Number	Std style only Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I13A	1-5/16" x 3/4"	Box of 100	2,000
I13R		Pail of 5,000	5,000

Cable Size: S.E.U. 2/3 Cable

Catalog Number	Std style only Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I15A	1-1/2" x 1"	Box of 100	2,000
I15Q		Pail of 4,000	4,000

Non-Insulated Metal Staples

- Electro-galvanized after fabrication.



Electro-Galvanized Cable Staples

Cable Size: 2 Conductor (#12 & #14) Romex®, and other type NM cable

Catalog Number	Std style only Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I10ZA	Standard Style	Box of 100	10,000
I10ZC	1" x 1/2"	Box of 500	10,000
I10ZM		Keg of 5,000	5,000
I10ZN		Keg of 10,000	10,000
I10ZR		Pail of 5,000	5,000
I10ZT		Pail of 10,000	10,000

Cable Size: 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other cable

Catalog Number	Std style only Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I12ZA	1-1/4" x 9/16"	Box of 100	5,000
I12ZB		Box of 250	5,000
I12ZC		Box of 500	5,000
I12ZM		Keg of 5,000	5,000
I12ZR		Pail of 5,000	5,000
I12ZS		Pail of 7,500	7,500

Cable Size: S.E.U. 6/3 Cable

Catalog Number	Style and Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I13ZA	Standard Style	Box of 100	2,000
I13ZR	1-5/16" x 3/4"	Pail of 5,000	5,000





Taking the electrical industry by storm!

Electro-Galvanized Cable Staples (con't)

Cable Size: S.E.U. 2/3 Cable

Catalog Number	Std style only Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I15ZA	1-1/2" x 1"	Box of 100	2,000
I15ZQ		Pail of 4,000	4,000

IMPACTTM
STAPLES




Stacking Staples

Cable Size: Multiple 14/2 & 12/2 NM Cables


Catalog Number	Std style only Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
I17A	1-3/4" x 1/2"	Box of 100	2,000
I17R		Pail of 5,000	5,000



Non-Insulated Metal Staples



ISE13A



Service Entrance Staples

Cable Size: 6/3 S.E. 8-3 BX Range Cords

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
ISE13A	1-3/8" x 13/16"	Box of 100	2,000

Cable Size: 4/3 S.E.R. 2/3 S.E. 3/4" EMT

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
ISE14A	1-7/16" x 1-1/16"	Box of 100	2,000

Cable Size: 2/0 S.E., 1" EMT

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
ISE18U	1-7/8" x 1-11/32"	Box of 50	1,000

Cable Size: 2/3 BX, 1" EMT, 1" Greenfield, 2/3 SER

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
ISE22U	2-1/4" x 1-3/16"	Box of 50	1,000




Taking the electrical industry by storm!

Non-Insulated Metal Staples

Service Entrance Staples (con't)

Cable Size: 4/0 S.E. Greenfield, Large BX, Romex®, Tubing

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
ISE23U	2-1/8" x 1-5/8"	Box of 50	1,000



ISE13ZA

- Electro-galvanized service entrance staples are zinc plated after fabrication.

Electro-Galvanized Service Entrance Staples

Cable Size: 6/3 S.E. 8-3 BX Range Cords

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
ISE13ZA	1-3/8" x 13/16"	Box of 100	2,000

Cable Size: 4/3 S.E.R. 2/3 S.E. 3/4" EMT

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
ISE14ZA	1-7/16" x 1-1/16"	Box of 100	2,000

Non-Insulated Metal Staples



Cut Point



Diamond Point

Non-Insulated Utility Staples

- Diamond Point Staples sold in boxes. Points multi-faceted the same as a nail.
- Cut Point Staples sold in bulk economically by weight. Staple points are slashed at an angle.
- Copperclad - Factory bonding on bright wire base. Copper thickness minimum of 6% of wire diameter. Excellent corrosion protection.
- Hot Dip Galvanized - Formed bright wire parts are submerged in a molten bath of zinc. For use in harsh environments.

Catalog Number	Copperclad (L x W x wire dia)	Point	Shipper Pkg qty
IUS1218C	1-1/4" x 3/16" x .114"	Cut	Keg of 50 LBS
IUS1025C	1" x 1/4" x .114"	Diamond	Box of 500 pcs
IUS1225C	1-1/4" x 1/4" x .114"	Diamond	Box of 500 pcs
IUS1531I	1-1/2" x 5/16" x .144"	Diamond	Box of 500 pcs
IUS2050Q	2" x 1/2" x .162"	Diamond	Box of 100 pcs

Catalog Number	Hot Dip Galv. (L x W x wire dia)	Point	Shipper Pkg qty
IUS2063Q	2" x 5/8" x .162"	Diamond	Box of 100 pcs
IUS3090W	3" x 1-1/16" x .250"	Diamond	Box of 100 pcs



Taking the electrical industry by storm!


Notes:

[illegible]



Insulated Metal Staples

- Highly visible optic blue plastic insulator
- Standard or new flat top staple style
- Packed in boxes, jars and square plastic pails



Insulated Metal Staples

Plastic Insulator Cable Staples



Cable Size: 2 Conductor (#12 & #14) Romex®, and other type NM cable

Catalog Number	Style and Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
IPN1A	Standard Style 1" x 1/2"	Box of 100	5,000
IPN1C		Box of 500	5,000
IPN1E		Jar of 200	1,200
IPN1R		Pail of 5,000	5,000
IPN1HA	Standard Style HEAVY DUTY 1" x 1/2"	Box of 100	5,000
IPN1HC		Box of 500	5,000
IPN1HE		Jar of 200	1,200
IPN1HR		Pail of 5,000	5,000
IPNHF1A	Flat Top Style HEAVY DUTY 1" x 1/2"	Box of 100	5,000
IPNHF1C		Box of 500	5,000
IPNHF1E		Jar of 200	1,200
IPNHF1R		Pail of 5,000	5,000


Cable Size: 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other cable

Catalog Number	Style and Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
IPN2A	Standard Style 1-1/4" x 9/16"	Box of 100	5,000
IPN2C		Box of 500	5,000
IPN2E		Jar of 200	1,200
IPN2R		Pail of 5,000	5,000
IPN2FA	Flat Top Style 1-1/4" x 9/16"	Box of 100	5,000
IPN2FC		Box of 500	5,000
IPN2FE		Jar of 200	1,200
IPN2FR		Pail of 5,000	5,000




Taking the electrical industry by storm!

- Top of staple dipped in high impact hot melt PVC
- Highly visible optic blue
- Packed in boxes, jars and square plastic pails



PVC Dipped Cable Staples



IPVC1HA

Cable Size: 2 Conductor (#12 & #14) Romex®, and other type NM cable

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
IPVC1HA	HEAVY DUTY	Box of 100	5,000
IPVC1HC	1" X 1/2"	Box of 500	5,000
IPVC1HF		Jar of 350	2,100
IPVC1HR		Pail of 5,000	5,000


Cable Size: 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other cable

Catalog Number	Size (L x W)	Pkg Qty (Pieces)	Shipper (Pieces)
IPVC2A	1-1/4" x 9/16"	Box of 100	5,000
IPVC2C		Box of 500	5,000
IPVC2F		Jar of 350	2,100
IPVC2R		Pail of 5,000	5,000

Insulated Metal Staples

Insulated Plastic Staples

- Our top selling insulated staples
- For 1/2" and 3/4" wide single cables
- UL and CSA Listed
- Made from UV stabilized high impact plastic



Plastic Cable Staples



IPS50

Cable Size: 2 & 3-wire NM cable up to #12, 2-wire UF cable up to #12 & other cable up to 1/2" wide


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IPS50H	White	Polybag of 100	1,000
IPS50J		Polybag of 500	2,500
IPS50K		Kraft Bag of 500	2,500
IPS50A		Box of 100	1,000
IPS50C		Box of 500	2,500
IPS50E		Jar of 200	1,200
IPS50M		Keg of 5,000	5,000
IPS50P		Pail of 2,000	2,000

Cable Size: 2-wire NM and UF cable up to #8, 3-wire UF cable up to #12 & other cable up to 3/4" wide

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IPS75H	White	Polybag of 100	1,000
IPS75J		Polybag of 500	2,500
IPS75L		Kraft Bag of 250	2,500
IPS75A		Box of 100	1,000
IPS75C		Box of 500	2,500
IPS75D		Jar of 150	900
IPS75M		Keg of 5,000	5,000
IPS75P		Pail of 2,000	2,000



- For stacking multiple 1/2" wide cables
- Made from UV stabilized high impact plastic



Stacking Cable Staples



IPS504

Cable Size: For stacking two 2-wire #14 or #12 NM cable

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IPS502	Tan	Box of 50	500

Cable Size: For stacking three 2-wire or a 2-wire and a 3-wire #4 and #12 NM cable


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IPS503	Gray	Box of 50	500

Cable Size: For stacking two 3-wire or four 2-wire #14 or #12 NM cable

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IPS504	White	Box of 50	500

Insulated Plastic Staples

- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength and durability



Service Entrance Staples - Style SER



ISER40

**Cable Size: #6 Type SE, Style SER,
1/2" EMT (.718" dia.)**

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISER10	Gray	Box of 50	1,000

**Cable Size: #2 Type SE, Style SER,
3/4" EMT (.937" dia.)**

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISER20	Gray	Box of 25	500

**Cable Size: #2/0 Type SE, Style SER,
1" EMT (1.160" dia.)**


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISER30	Gray	Box of 25	500

**Cable Size: #4/0 Type SE, Style SER,
1/2" EMT (1.438" dia.)**

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISER40	Gray	Box of 10	200



- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength and durability



Service Entrance Staples - Style SEU



ISEU50

**Cable Size: #6 Type SE, Style SEU,
(.437" x .750")**

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISEU50	Gray	Box of 50	1,000

**Cable Size: #2 Type SE, Style SEU,
(.550" x .972")**

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISEU60	Gray	Box of 50	1,000

**Cable Size: #2/0 Type SE, Style SEU,
(.775" x 1.265")**


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISEU70	Gray	Box of 25	500

**Cable Size: #4/0 Type SE, Style SEU,
(.855" x 1.500")**

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ISEU80	Gray	Box of 25	500

Insulated Plastic Staples

- Available in black, white, tan or gray
- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability



Bell & Thermostat Staples



IBT251T



IBT252W

Cable Size: 1/4" 1-Nail

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IBT251B	Black	Box of 100	1,000
IBT251W	White	Box of 100	1,000
IBT251T	Tan	Box of 100	1,000
IBT251G	Gray	Box of 100	1,000

Cable Size: 1/4" 2-Nail


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IBT252B	Black	Box of 100	1,000
IBT252W	White	Box of 100	1,000
IBT252T	Tan	Box of 100	1,000
IBT252G	Gray	Box of 100	1,000

Cable Size: 5/16" 1-Nail

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IBT312B	Black	Box of 100	1,000
IBT312W	White	Box of 100	1,000
IBT312T	Tan	Box of 100	1,000
IBT312G	Gray	Box of 100	1,000



- Available in either gray or tan
- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability



Telephone Cable 1-Nail Staples



ITC25G

Cable Size: 4-con., 22 AWG Station Wire (.140" dia.)

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ITC12G	Gray	Box of 100	1,000
ITC12T	Tan	Box of 100	1,000

Cable Size: 6 pair, 24 AWG Inside Cable (.250" dia.)


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ITC25G	Gray	Box of 100	1,000
ITC25T	Tan	Box of 100	1,000

Cable Size: 25 pair, 24 AWG Inside Cable (.4418" dia.)

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
ITC42G	Gray	Box of 50	500
ITC42T	Tan	Box of 50	500

Insulated Plastic Staples

- Available in either black or white
- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability



Coaxial & Sound Staples



ICS37B




I25DB

Catalog Number	Cable Size	Color
ICS12B	1/8" Coax (.125" dia.)	Black
ICS12W		White
ICS18B	3/16" Coax (.140" dia.)	Black
ICS18W		White
ICS25B	1/4" Coax (.250" dia.)	Black
ICS25W		White
ICS37B	3/8" Coax (.375" dia.)	Black
ICS37W		White
ICS43B	7/16" Coax (.4375" dia.)	Black
ICS43W		White
I242B	.242 dia. 59/u	Black
I242W		White
I275B	.275 dia. 6/u	Black
I275W		White
I300B	.300" dia. RG6 Quad Shield	Black
I300W		White
I395B	RG11 (.395" dia.)	Black
I395W		White
I25DB	RG59 Dual (.250" x .500")	Black
I25DW		White
I305DB	RG6 Dual (.305" x .594")	Black
I305DW		White

NOTE: All staples above are packed in boxes of 100 pieces with shipper quantities of 1,000 pieces.




- Available in either black or white
- All staples are UV stabilized for severe weather conditions
- Nails made from high carbon steel that has been hardened and zinc plated for use in concrete, block, or masonry materials.



Coaxial & Sound Staples W Cement Nails



ICS37BC




I25DBC

Catalog Number	Cable Size	Color
ICS12BC	1/8" Coax (.125" dia.)	Black
ICS12WC		White
ICS18BC	3/16" Coax (.140" dia.)	Black
ICS18WC		White
ICS25BC	1/4" Coax (.250" dia.)	Black
ICS25WC		White
ICS37BC	3/8" Coax (.375" dia.)	Black
ICS37WC		White
ICS43BC	7/16" Coax (.4375" dia.)	Black
ICS43WC		White
I242BC	.242 dia. 59/u	Black
I242WC		White
I275BC	.275 dia. 6/u	Black
I275WC		White
I300BC	.300" dia. RG6 Quad Shield	Black
I300WC		White
I395BC	RG11 (.395" dia.)	Black
I395WC		White
I25DBC	RG59 Dual (.250" x .500")	Black
I25DWC		White
I305DBC	RG6 Dual (.305" x .594")	Black
I305DWC		White


NOTE: All staples above are packed in boxes of 100 pieces with shipper quantities of 1,000 pieces.

Insulated Plastic Staples


- Available in either black, white
- All staples UV stabilized for severe weather conditions
- Hardened #6 x 1" Phillips Head Self-Tapping Screw for tough jobs



Coaxial & Sound Staples W/#6 x 1" Screw



I275BP



I305DBP

Catalog Number	Cable Size	Color
I242BP	.242 dia. 59/u	Black
I242WP		White
I275BP	.275 dia. 6/u	Black
I275WP		White
I300BP	.300" dia. RG6 Quad Shield	Black
I300WP		White
I395BP	RG11 (.395" dia.)	Black
I395WP		White

NOTE: All staples above are packed in boxes of 100 pieces with shipper quantities of 1,000 pieces.


Cable Size: RG6 Dual (.305" x .594")

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
I305DBP	Black	Box of 50	500
I305DWP	White	Box of 50	500




Taking the electrical industry by storm!

- Available in either black or white
- All staples UV stabilized for severe weather conditions
- Hardened #8 x 1" Slotted Phillips Hex Head Type AB Tapping Screws for the toughest jobs



Coaxial & Sound Staples W/ #8 x 1" Slotted Screw



I275BS



I305DBS

Catalog Number	Cable Size	Color
I242BS	.242 dia. 59/u	Black
I242WS		White
I275BS	.275 dia. 6/u	Black
I275WS		White
I300BS	.300" dia. RG6 Quad Shield	Black
I300WS		White
I395BS	RG11 (.395" dia.)	Black
I395WS		White


NOTE: All staples above are packed in boxes of 100 pieces with shipper quantities of 1,000 pieces.

Cable Size: RG6 Dual (.305" x .594")

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
I305DBS	Gray	Box of 50	500
I305DWS	Tan	Box of 50	500

Insulated Plastic Staples


- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability
- INS501 comes with screw for installation into metal studs



Non-Metallic Sheathed Cable Staples



INS50



INS501

Cable Size: For 3-wire #4 & #12 NM cable and other cable up to 13/32" wide

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
INS41	White	Box of 100	1,000

Cable Size: For 3-wire #10 NM cable and other cable up to 1/2" wide

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
INS50	White	Box of 25	500

Cable Size: For 3-wire #8 and #6 NM cable and other cable up to 21/32" wide


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
INS66	White	Box of 100	2,000

Cable Size: For 2-wire NM and UF cable up to #12 to Metal Studs


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
INS501	White	Box of 100	1,000



- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability



AC/MC Staples



IAM50

Cable Size: For Armoured Cable and Metal-Clad Cable (3/8" dia.)


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IAM375	Gray	Box of 50	500

Cable Size: For Armoured Cable and Metal-Clad Cable (1/2" dia.)


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IAM50	Gray	Box of 50	500

Insulated Plastic Staples

- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability



UF Cable Staples




IUF40

Cable Size: 3/6 UF Cable (.400" x 1.300")


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IUF40	Black	Box of 50	1,000




- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability



Data/Com Staples



IDC195



IDC50

Cable Size: 4 pair, 24 gauge, Cat 5 Cable (.195" dia.)


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IDC195	Blue	Box of 100	1,000

Cable Size: Quad Satellite Coax (1/2" dia.)


Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IDC50	Blue	Box of 100	1,000

Insulated Plastic Staples

- All staples UV stabilized for severe weather conditions
- Zinc plated nails made from high carbon steel for strength & durability.



Water Pipe Staple



IWP50

Cable Size: 1/2" Plastic Water Pipe & Copper Tubing (.625" dia.)

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IWP50	Tan	Box of 100	2,000

Cable Size: 3/4" Plastic Water Pipe & Copper Tubing (.937" dia.)

Catalog Number	Color	Pkg Qty (Pieces)	Shipper (Pieces)
IWP75	Tan	Box of 50	500



Taking the electrical industry by storm!


FREE Catalog or Product Sample!

Would you like an additional copy of our catalog or a complimentary sample of one of our products shown here? Can we add you to our mailing list for new product updates and samples, promotions and company newsletter? Phone, fax or e-mail your request. Or simply fill out the postage paid request card attached to this catalog. We look forward to hearing from you...and thank you for your interest in Minerallac.



100 Gast Road • Hampshire, IL 60140
PHONE TOLL FREE 1-877-285-2200
FAX TOLL FREE 1-800-824-8942
CustomerService@minerallac.com

Hang with Minerallac®...



MasterStrut


Building For Tomorrow



Minerallac's MasterStrut -- The Best Quality in Channel & Fittings

Over the past 100 years the Minerallac name has become synonymous with quality, innovation and value. We carry these same qualities and our commitment to excellence to bring you our newest line. Choose MasterStrut for channel, fittings, hardware and accessories. From our state-of-the-art production, finest parts, competitive pricing, and broad range of custom sizes, to our unequalled customer service, you won't find a better value.

That's the Minerallac Advantage!





Anatomy of MasterStrut Channel Part Numbering System

M 158 2 A EH 10 GRN

Profile*

136 13/16"
100 1"
138 1-3/8"
158 1-5/8"
276 2-7/16"
314 3-1/4"

Gauge

2 12 gauge
4 14 gauge

Weld Configuration

A Back-to-Back

Hole Pattern (if required)

H 9/16" dia. Hole 1-7/8" O.C.
S 13/32" x 3 Slots, 4" O.C.
EH 9/16" x 1-1/8" Elongated
Holes, 2" O.C.
KO 7/8" dia. Knockouts, 6" O.C.

Length

10' and 20' lengths
(other lengths available
upon request.)

Material/Finish

GRN Painted Green
PGL Pre-Galvanized Steel
PLN Plain (lightly oiled)
SS4 304 Stainless Steel
SS6 316 Stainless Steel
GD Gold Dichromate
HDG Hot Dip Galvanized

*Width of all
channel 1-5/8"

Made in USA



Materials

STEEL: Plain and painted green channels are formed from structural quality strip steel which conforms to the requirements of ASTM A-570, Grade 33; pre-galvanized channel to the requirements of ASTM A-653, Grade 33, steel zinc coated by Hot Dip Process.

STAINLESS STEEL: Channels are formed from AISI Type 304 or Type 316 Stainless Steel and meet the requirements of ASTM B-240.

Finishes

MasterStrut channel is available plain, painted green or in three types of zinc coatings:

Plain (PLN)

Plain finish designation means that the channel retains the oiled surface applied to the raw steel during the rolling process.

Green (GRN)

Urethane coating is applied to the channel by an electro-deposition process, (between 1.8 and 2.2 mils thick) withstanding approximately 1,000 hours of salt spray, per ASTM B117, offering the most enduring quality finish for both indoor and outdoor metal products.

Zinc Coatings:

Pre-Galvanized (PGL)

Material (strip steel) is coated with zinc by hot-dip process prior to roll-forming or press operations. The zinc coating conforms to ASTM A-525, Grade 90 General Requirement for Steel Sheet, Zinc Coated (Galvanized by Hot Dip Process).



Hot-Dip Galvanized (HDG)

Material is coated with zinc after being roll-formed or after manufacturing operations are completed, conforming to ASTM specifications No. A123 or A153.

Gold Dichromate (GD)

A .5 mil electro-galvanized zinc plate is applied to the steel base metal, in compliance with ASTM B633 standard. Yellow Dichromate is applied over the zinc giving a gold appearance which acts as a nonporous barrier sealant.

Finish	Zinc Thickness
Pre-Galvanized (PGL)	.75 mil
Hot Dip Galvanized (HDG)	2.6 mil
Gold Dichromate (GD)	.5 mil

Custom Colors

Custom colors are surprisingly affordable. Contact Customer Service for pricing, minimum order quantity and lead times.


Custom Lengths

Custom lengths, cut on the mill, are our specialty. And because of our unique roll-forming technique, there is no flaring. Cut ends match up exactly. Call Customer Service for minimum order quantities, pricing and delivery. NOTE: When required to cut from standard stock lengths of 10' or 20', customer will be charged scrap resulting from cutting.



Channel

Sizes




M1364

13/16" x 1-5/8" x 14 Ga.

M1362

13/16" x 1-5/8" x 12 Ga.


Pages 220-223



M1002

1" x 1-5/8" x 12 Ga.


Page 224-225



M1382

1-3/8" x 1-5/8" x 12 Ga.

Page 226-227




M1584

1-5/8" x 1-5/8" x 14 Ga.

M1582

1-5/8" x 1-5/8" x 12 Ga.


Page 228-231



M2762

2-7/16" x 1-5/8" x 12 Ga.

Page 232-233




M3142

3-1/4" x 1-5/8" x 12 Ga.


Page 234-235




Hole Pattern




Plain - no hole pattern
Page 236




“H” Series
9/16” dia. holes
on 1-7/8” centers
Page 237



“S” Series
13/32” x 3” slot
on 4” centers
Page 238




“EH” Series
9/16” x 1-1/8” slot
on 2” centers
Page 239




“KO” Series
7/8” dia. knockouts
on 6” centers
Page 240

Weld Configuration





“A” Series
Back-to-Back
Page 241




Channel

M1364 Channel 13/16" x 1-5/8" x 14 Ga.




M1364 Channel Plain - no hole pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M136410*	10'	500	97	485
M136420*	20'	500	97	485



M1364H Channel "H" Series 9/16" dia. hole on 1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1364H10*	10'	500	87	435
M1364H20*	20'	500	87	435



M1364S Channel "S" Series 13/32" x 3" slots on 4" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1364S10*	10'	500	87	435
M1364S20*	20'	500	87	435



Add Material/Finish to part numbers when ordering.

GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		

(NOTE: Gold Dichromate available in 10' lengths only)




9/16" x 1-1/8"
Elongated
Hole

M1364EH Channel

"EH" Series

**1-1/8" x 9/16" elongated
hole on 2" centers**

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1364EH10*	10'	500	87	435
M1364EH20*	20'	500	87	435



M1364A Channel

"A" Series



Two pieces M1364 welded Back-to-Back
Overall dimensions: 1-5/8" x 1-5/8" x 14 Ga.

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1364A10*	10'	250	194	485
M1364A20*	20'	300	194	582




Channel

M1362 Channel
13/16" x 1-5/8" x 12 Ga.




M1362 Channel
Plain -
no hole pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M136210*	10'	500	128	640
M136220*	20'	500	128	640



M1362H Channel
"H" Series
9/16" dia. hole on
1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1362H10*	10'	500	123	615
M1362H20*	20'	500	123	615



M1362S Channel
"S" Series
13/32" x 3" slots
on 4" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1362S10*	10'	500	123	615
M1362S20*	20'	500	123	615



Add Material/Finish to part numbers when ordering.

- GRN** Painted Green

PLN Plain (light oil)


PGL Pre-Galvanized

GD Gold Dichromate
- SS4** 304 Stainless Steel

SS6 316 Stainless Steel

HDG Hot Dip Galvanized


(NOTE: Gold Dichromate available in 10' lengths only)



9/16" x 1-1/8"
Elongated
Hole

M1362EH Channel
"EH" Series
1-1/8" x 9/16" elongated
hole on 2" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1362EH10*	10'	500	123	615
M1362EH20*	20'	500	123	615



1-5/8"



M1362A Channel
"A" Series
Two pieces M1362 welded Back-to-Back
Overall dimensions: 1-5/8" x 1-5/8" x 12 Ga.

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1362A10*	10'	250	265	663
M1362A20*	20'	300	265	795




Channel

M1002 Channel 1" x 1-5/8" x 12




M1002 Channel Plain - no hole pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M100210*	10'	500	141	705
M100220*	20'	500	141	705



M1002H Channel "H" Series 9/16" dia. hole on 1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1002H10*	10'	500	141	705
M1002H20*	20'	500	141	705



M1002S Channel "S" Series 13/32" x 3" slots on 4" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1002S10*	10'	500	141	705
M1002S20*	20'	500	141	705



Add Material/Finish to part numbers when ordering.

GRN Painted Green	SS4 304 Stainless Steel
PLN Plain (light oil)	SS6 316 Stainless Steel
PGL Pre-Galvanized	HDG Hot Dip Galvanized
GD Gold Dichromate	

(NOTE: Gold Dichromate available in 10' lengths only)




M1002EH Channel

"EH" Series

1-1/8" x 9/16" elongated hole on 2" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1002EH10*	10'	500	141	705
M1002EH20*	20'	500	141	705




M1002KO Channel

"KO" Series

7/8" dia. knockout on 6" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1002KO10*	10'	500	141	705
M1002KO20*	20'	500	141	705



M1002A Channel

"A" Series



**Two pieces M1002 welded Back-to-Back
Overall dimensions: 2" x 1-5/8" x 12 Ga.**

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1002A10*	10'	250	292	730
M1002A20*	20'	300	292	876




Channel

M1382 Channel 1-3/8" x 1-5/8" x 12




M1382 Channel Plain - no hole pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M138210*	10'	500	170	850
M138220*	20'	500	170	850



M1382H Channel "H" Series 9/16" dia. hole on 1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1382H10*	10'	500	165	825
M1382H20*	20'	500	165	825



M1382S Channel "S" Series 13/32" x 3" slots on 4" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1382S10*	10'	500	165	825
M1382S20*	20'	500	165	825



Add Material/Finish to part numbers when ordering.


GRN Painted Green	SS4 304 Stainless Steel
PLN Plain (light oil)	SS6 316 Stainless Steel
PGL Pre-Galvanized	HDG Hot Dip Galvanized
GD Gold Dichromate	

(NOTE: Gold Dichromate available in 10' lengths only)




M1382EH Channel
“EH” Series
 1-1/8" x 9/16" elongated
 hole on 2" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1382EH10*	10'	500	165	825
M1382EH20*	20'	500	165	825



M1382KO Channel
“KO” Series
 7/8" dia. knockout
 on 6" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1382KO10*	10'	500	170	850
M1382KO20*	20'	500	170	850





M1382A Channel
“A” Series
 Two pieces M1382 welded Back-to-Back
 Overall dimensions: 2-3/4" x 1-5/8" x 12 Ga.

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1382A10*	10'	250	292	730
M1382A20*	20'	300	292	876




Channel

M1584 Channel
1-5/8" x 1-5/8" x 14 Ga.




M1584 Channel
Plain -
no hole pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M158410*	10'	500	141	705
M158420*	20'	500	141	705



M1584H Channel
"H" Series
9/16" dia. hole
on 1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1584H10*	10'	500	137	685
M1584H20*	20'	500	137	685



M1584S Channel
"S" Series
13/32" x 3" slots
on 4" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1584S10*	10'	500	137	685
M1584S20*	20'	500	137	685



Add Material/Finish to part numbers when ordering.


GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		

(NOTE: Gold Dichromate available in 10' lengths only)




M1584EH Channel
"EH" Series
 1-1/8" x 9/16" elongated
 hole on 2" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1584EH10*	10'	500	137	685
M1584EH20*	20'	500	137	685



M1584KO Channel
"KO" Series
 7/8" dia. knockout
 on 6" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1584KO10*	10'	500	141	705
M1584KO20*	20'	500	141	705





M1584A Channel
"A" Series
 Two pieces M1584 welded Back to Back
 Overall dimensions: 3-1/4" x 1-5/8" x 12 Ga.

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1584A10*	10'	250	282	705
M1584A20*	20'	300	282	846




Channel

M1582 Channel
1-5/8" x 1-5/8" x 12 Ga.




M1582 Channel
Plain -
no hole pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M158210*	10'	500	178	890
M158220*	20'	500	178	890



M1582H Channel
"H" Series
9/16" dia. hole
on 1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1582H10*	10'	500	173	865
M1582H20*	20'	500	173	865



M1582S Channel
"S" Series
13/32" x 3" slots
on 4" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1582S10*	10'	500	173	865
M1582S20*	20'	500	173	865



Add Material/Finish to part numbers when ordering.


GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		

(NOTE: Gold Dichromate available in 10' lengths only)




M1582EH Channel
"EH" Series
 1-1/8" x 9/16" elongated
 hole on 2" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1582EH10*	10'	500	173	865
M1582EH20*	20'	500	173	865



M1582KO Channel
"KO" Series
 7/8" dia. knockout
 on 6" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1582KO10*	10'	500	178	890
M1582KO20*	20'	500	178	890





M1582A Channel
"A" Series
 Two pieces M1582 welded Back-to-Back
 Overall dimensions: 3-1/4" x 1-5/8" x 12 Ga.

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M1582A10*	10'	250	340	850
M1582A20*	20'	300	340	1,020




Channel

M2762 Channel
2-7/16" x 1-5/8" x 12 Ga.




M2762Channel
Plain - no hole
pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M276210*	10'	400	247	988
M276220*	20'	400	247	988



M2762H Channel
"H" Series
9/16" dia. hole
on 1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M2762H10*	10'	400	242	968
M2762H20*	20'	400	242	968



M2762S Channel
"S" Series
13/32" x 3" slots
on 4" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M2762S10*	10'	400	242	968
M2762S20*	20'	400	242	968



Add Material/Finish to part numbers when ordering.

GRN Painted Green	SS4 304 Stainless Steel
PLN Plain (light oil)	SS6 316 Stainless Steel
PGL Pre-Galvanized	HDG Hot Dip Galvanized
GD Gold Dichromate	

(NOTE: Gold Dichromate available in 10' lengths only)




9/16" x 1-1/8"
Elongated
Hole

M2762EH Channel **"EH" Series**

**1-1/8" x 9/16" elongated
hole on 2" centers**

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M2762EH10*	10'	400	242	968
M2762EH20*	20'	400	242	968




7/8" dia. Knockout
Hole Typical

M2762KO Channel **"KO" Series**

**7/8" dia. knockout
on 6" centers**

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M2762KO10*	10'	400	247	988
M2762KO20*	20'	400	242	988



M2762A Channel **"A" Series**

Two pieces M2762 welded Back-to-Back
Overall dimensions: 4-7/8" x 1-5/8" x 12 Ga.

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M2762A10*	10'	200	484	968
M2762A20*	20'	200	484	968





MasterStrut

Channel

M3142 Channel

3-1/4" x 1-5/8" x 12 Ga.




M3142 Channel

Plain -

no hole pattern

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M314210*	10'	300	290	870
M314220*	20'	400	290	1,160




M3142H Channel

"H" Series

9/16" dia. hole

on 1-7/8" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M3142H10*	10'	300	285	855
M3142H20*	20'	400	285	1,140



M3142S Channel

"S" Series

13/32" x 3" slots

on 4" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M3142S10*	10'	300	285	855
M3142S20*	20'	400	285	1,140



Add Material/Finish to part numbers when ordering.

GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		


(NOTE: Gold Dichromate available in 10' lengths only)



M3142EH Channel **"EH" Series**

1-1/8" x 9/16" elongated hole on 2" centers


Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M3142EH10*	10'	300	285	855
M3142EH20*	20'	400	285	1,140



M3142KO Channel **"KO" Series**

7/8" dia. knockout on 6" centers

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M3142KO10*	10'	300	290	870
M3142KO20*	20'	400	290	1,160



M3142A Channel **"A" Series**


*Two pieces M3142 welded Back-to-Back
Overall dimensions: 6-1/2" x 1-5/8" x 12 Ga.*

Catalog No. (*Add Finish)	Length (feet)	Package Qty (feet)	Weight (100 ft)	Shipper Wt (lbs)
M3142A10*	10'	150	580	870
M3142A20*	20'	200	580	1,160



Channel

Plain - No Hole Pattern



Width of all Channel 1-5/8"

Catalog No. (*Add Finish)	Length (feet)	Thickness	Height "H"	Weight (100 ft)
M136410*	10'	14 ga.	13/16"	97
M136420*	20'	14 ga.	13/16"	97
M136210*	10'	12 ga.	13/16"	128
M136220*	20'	12 ga.	13/16"	128
M100210*	10'	12 ga.	1"	146
M100220*	20'	12 ga.	1"	146
M138210*	10'	12 ga.	1-3/8"	170
M138220*	20'	12 ga.	1-3/8"	170
M158410*	10'	14 ga.	1-5/8"	141
M158420*	20'	14 ga.	1-5/8"	141
M158210*	10'	12 ga.	1-5/8"	178
M158220*	20'	12 ga.	1-5/8"	178
M276210*	10'	12 ga.	2-7/16"	247
M276220*	20'	12 ga.	2-7/16"	247
M314210*	10'	12 ga.	3-1/4"	290
M314220*	20'	12 ga.	3-1/4"	290

Dimensional charts for each size channel (profile) shown on pages 220, 222, 224, 226, 228, 230, 232 and 234 of this catalog.


Add Material/Finish to part numbers when ordering.

GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		

(NOTE: Gold Dichromate available in 10' lengths only)



“H” Series Hole Pattern



Description:
9/16" dia. hole on 1-7/8" centers

Width of all Channel 1-5/8"

Catalog No. (*Add Finish)	Length (feet)	Thickness	Height "H"	Weight (100 ft)
M1364H10*	10'	14 ga.	13/16"	87
M1364H20*	20	14 ga.	13/16"	87
M1362H10*	10'	12 ga.	13/16"	123
M1362H20*	20'	12 ga.	13/16"	123
M1002H10*	10'	12 ga.	1"	141
M1002H20*	20'	12 ga.	1"	141
M1382H10*	10'	12 ga.	1-3/8"	165
M1382H20*	20'	12 ga.	1-3/8"	165
M1584H10*	10'	14 ga.	1-5/8"	137
M1584H20*	20'	14 ga.	1-5/8"	137
M1582H10*	10'	12 ga.	1-5/8"	173
M1582H20*	20'	12 ga.	1-5/8"	173
M2762H10*	10'	12 ga.	2-7/16"	242
M2762H20*	20'	12 ga.	2-7/16"	242
M3142H10*	10'	12 ga.	3-1/4"	285
M3142H20*	20'	12 ga.	3-1/4"	285

Dimensional charts for each size channel (profile) shown on pages 220, 222, 224, 226, 228, 230, 232 and 234 of this catalog.

Add Material/Finish to part numbers when ordering.


GRN Painted Green	SS4 304 Stainless Steel
PLN Plain (light oil)	SS6 316 Stainless Steel
PGL Pre-Galvanized	HDG Hot Dip Galvanized
GD Gold Dichromate	

(NOTE: Gold Dichromate available in 10' lengths only)



Channel

"S" Series Hole Pattern



Description:

13/32" x 3" slots on 4" centers

Width of all Channel 1-5/8"

Catalog No. (*Add Finish)	Length (feet)	Thickness	Height "H"	Weight (100 ft)
M1364S10*	10'	14 ga.	13/16"	87
M1364S20*	20'	14 ga.	13/16"	87
M1362S10*	10'	12 ga.	13/16"	123
M1362S20*	20'	12 ga.	13/16"	123
M1002S10*	10'	12 ga.	1"	141
M1002S20*	20'	12 ga.	1"	141
M1382S10*	10'	12 ga.	1-3/8"	165
M1382S20*	20'	12 ga.	1-3/8"	165
M1584S10*	10'	14 ga.	1-5/8"	137
M1584S20*	20'	14 ga.	1-5/8"	137
M1582S10*	10'	12 ga.	1-5/8"	173
M1582S20*	20'	12 ga.	1-5/8"	173
M2762S10*	10'	12 ga.	2-7/16"	242
M2762S20*	20'	12 ga.	2-7/16"	242
M3142S10*	10'	12 ga.	3-1/4"	285
M3142S20*	20'	12 ga.	3-1/4"	285

Dimensional charts for each size channel (profile) shown on pages 220, 222, 224, 226, 228, 230, 232 and 234 of this catalog.


Add Material/Finish to part numbers when ordering.

GRN Painted Green	SS4 304 Stainless Steel
PLN Plain (light oil)	SS6 316 Stainless Steel
PGL Pre-Galvanized	HDG Hot Dip Galvanized
GD Gold Dichromate	

(NOTE: Gold Dichromate available in 10' lengths only)



“EH” Series Hole Pattern



Description:
1-1/8" x 9/16" Elongated Hole on 2" centers

Width of all Channel 1-5/8"

Catalog No. (*Add Finish)	Length (feet)	Thickness	Height "H"	Weight (100 ft)
M1364EH10*	10'	14 ga.	13/16"	87
M1364EH20*	20	14 ga.	13/16"	87
M1362EH10*	10'	12 ga.	13/16"	123
M1362EH20*	20'	12 ga.	13/16"	123
M1002EH10*	10'	12 ga.	1"	141
M10022EH0*	20'	12 ga.	1"	141
M1382EH10*	10'	12 ga.	1-3/8"	165
M1382EH20*	20'	12 ga.	1-3/8"	165
M1584EH10*	10'	14 ga.	1-5/8"	137
M1584EH20*	20'	14 ga.	1-5/8"	137
M1582EH10*	10'	12 ga.	1-5/8"	173
M1582EH20*	20'	12 ga.	1-5/8"	173
M2762EH10*	10'	12 ga.	2-7/16"	242
M2762EH20*	20'	12 ga.	2-7/16"	242
M3142EH10*	10'	12 ga.	3-1/4"	285
M3142EH20*	20'	12 ga.	3-1/4"	285

Dimensional charts for each size channel (profile) shown on pages 221, 223, 225, 227, 229, 231, 233 and 235 of this catalog.

Add Material/Finish to part numbers when ordering.


GRN Painted Green	SS4 304 Stainless Steel
PLN Plain (light oil)	SS6 316 Stainless Steel
PGL Pre-Galvanized	HDG Hot Dip Galvanized
GD Gold Dichromate	

(NOTE: Gold Dichromate available in 10' lengths only)



Channel

"KO" Series Hole Pattern



Description:

7/8" dia. knockout on 6" centers

Width of all Channel 1-5/8"

Catalog No. (*Add Finish)	Length (feet)	Thickness	Height "H"	Weight (100 ft)
M1002KO10*	10'	12 ga.	1"	141
M1002KO20*	20'	12 ga.	1"	141
M1382KO10*	10'	12 ga.	1-3/8"	170
M1382KO20*	20'	12 ga.	1-3/8"	170
M1584KO10*	10'	14 ga.	1-5/8"	141
M1584KO20*	20'	14 ga.	1-5/8"	141
M1582KO10*	10'	12 ga.	1-5/8"	178
M1582KO20*	20'	12 ga.	1-5/8"	178
M2762KO10*	10'	12 ga.	2-7/16"	247
M2762KO20*	20'	12 ga.	2-7/16"	247
M3142KO10*	10'	12 ga.	3-1/4"	290
M3142KO20*	20'	12 ga.	3-1/4"	290

Dimensional charts for each size channel (profile) shown on pages 225, 227, 229, 231, 233 and 235 of this catalog.


Add Material/Finish to part numbers when ordering.

GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		

(NOTE: Gold Dichromate available in 10' lengths only)



“A” Series Welding Configuration



Description:
Welded Back-to-Back

Width of all Channel 1-5/8"

Catalog No. (*Add Finish)	Length (feet)	Thickness	Height “H”	Weight (100 ft)
M1364A10*	10'	14 ga.	1-5/8"	194
M1364A20*	20	14 ga.	1-5/8"	194
M1362A10*	10'	12 ga.	1-5/8"	256
M1362A20*	20'	12 ga.	1-5/8"	256
M1002A10*	10'	12 ga.	2"	292
M1002A20*	20'	12 ga.	2"	292
M1382A10*	10'	12 ga.	2-3/4"	340
M1382A20*	20'	12 ga.	2-3/4"	340
M1584A10*	10'	14 ga.	3-1/4"	282
M1584A20*	20'	14 ga.	3-1/4"	282
M1582A10*	10'	12 ga.	3-1/4"	340
M1582A20*	20'	12 ga.	3-1/4"	340
M2762A10*	10'	12 ga.	4-7/8"	484
M2762A20*	20'	12 ga.	4-7/8"	484
M3142A10*	10'	12 ga.	6-1/2"	580
M3142A20*	20'	12 ga.	6-1/2"	580

Dimensional charts for each size channel (profile) shown on pages 225, 227, 229, 231, 233 and 235 of this catalog.

Add Material/Finish to part numbers when ordering.

GRN Painted Green	SS4 304 Stainless Steel
PLN Plain (light oil)	SS6 316 Stainless Steel
PGL Pre-Galvanized	HDG Hot Dip Galvanized
GD Gold Dichromate	

(NOTE: Gold Dichromate available in 10' lengths only)



Beam & Pipe Clamps

Pipe Clamps

- Pipe Clamps are available in four styles:
MSE - for EMT only
MSS - for GRC/IMC & standard pipe
MSU - Universal, same pipe fits EMT, GRC/IMC & standard piping
MOD - O.D. tubing clamp
- Parts are made on punch press dies from hot rolled, pickled and oiled steel which conforms to the ASTM-A366, A-575 and A-576 standards.
- Parts are zinc plated after fabrication.
- Zinc plated nut and bolt included with each part.


Universal Pipe Clamp

Catalog Number	EMT, GRC/IMC & Standard Pipe	Standard Package
MSU050EG	1/2"	100
MSU075EG	3/4"	100
MSU100EG	1"	100
MSU125EG	1-1/4"	100
MSU150EG	1-1/2"	50
MSU200EG	2"	50
MSU250EG	2-1/2"	50
MSU300EG	3"	50
MSU350EG	3-1/2"	25
MSU400EG	4"	25

Rigid Conduit/Pipe Clamp

Catalog Number	GRC/IMC & Standard Pipe	Standard Package
MSS050EG	1/2"	100
MSS075EG	3/4"	100
MSS100EG	1"	100
MSS125EG	1-1/4"	100
MSS150EG	1-1/2"	50
MSS200EG	2"	50

Other finishes and larger sizes available. Please contact Customer Service for pricing, minimum order quantities and lead times.



MSE100



MSU100

Clamp for Thinwall (EMT)

Catalog Number	EMT (Thinwall)	Standard Package
MSE050EG	1/2"	100
MSE075EG	3/4"	100
MSE100EG	1"	100
MSE125EG	1-1/4"	100
MSE150EG	1-1/2"	50
MSE200EG	2"	50

O.D. Tubing Clamps

Catalog Number	O.D. Size	Standard Package
MOD38EG	3/8"	100
MOD12EG	1/2"	100
MOD58EG	5/8"	100
MOD34EG	3/4"	100
MOD78EG	7/8"	100
MOD1EG	1"	100
MOD118EG	1-1/8"	100
MOD114EG	1-1/4"	100
MOD138EG	1-3/8"	100
MOD112EG	1-1/2"	100


Other finishes and larger sizes available. Please contact Customer Service for pricing, minimum order quantities and lead times.



Beam & Pipe Clamps

Cushion Clamp Assemblies by Hydra-Zorb™

- For refrigeration and fluid power clamping requirements.
- Yellow chromate applied to clamp after fabrication.
- Cushion part of clamp has a temperature rating from -65 degrees F to 275 degrees F.



Tube Clamp Series

Catalog Number	A	B	C	D	Tube O.D.	Std Pkg
M100025	1.11	.22	.075	.62	1/4"	25
M100031	1.24	.28	.075	.75	5/16"	25
M100037	1.24	.28	.075	.75	3/8"	25
M100050	1.36	.34	.075	.87	1/2"	25
M100062	1.50	.41	.075	1.00	5/8"	25
M100075	1.78	.53	.075	1.38	3/4"	25
M100087	1.91	.58	.075	1.45	7/8"	25
M100100	2.03	.66	.105	1.66	1"	10
M100112	2.16	.72	.105	1.79	1-1/8"	10
M100125	2.30	.72	.105	1.92	1-1/4"	10
M100137	2.75	.91	.119	2.22	1-3/8"	10
M100150	2.75	.91	.119	2.22	1-1/2"	10
M100162	3.03	1.03	.119	2.47	1-5/8"	10
M100175	3.03	1.03	.119	2.47	1-3/4"	10
M100200	3.28	1.16	.119	2.72	2"	10
M100212	3.53	1.28	.119	2.97	2-1/8"	5
M100225	3.78	1.41	.119	3.22	2-1/4"	5
M100251	4.03	1.53	.119	3.47	2-1/2"	5
M100262	4.03	1.53	.119	3.47	2-5/8"	5
M100300	4.53	1.78	.119	3.97	3"	5



Pipe Clamp Series


Catalog Number	A	B	C	D	Nom. Size	Std Pkg
M200025	1.41	.63	.075	.91	1/4"	25
M200037	1.59	.45	.075	1.07	3/8"	25
M200050	1.91	.59	.075	1.45	1/2"	25
M200075	2.16	.72	.105	1.79	3/4"	10
M200100	2.75	.91	.119	2.22	1"	10
M200125	3.03	1.03	.119	2.47	1-1/4"	10
M200150	3.28	1.16	.119	3.22	1-1/2"	10
M200200	3.78	1.41	.119	3.22	2"	5
M200250	4.27	1.66	.119	3.72	2-1/2"	5
M200300	4.91	1.97	.119	4.36	3"	5
M200350	5.53	2.28	.119	4.97	3-1/2"	5
M200400	6.03	2.53	.119	5.47	4"	5
M200500	7.03	3.03	.135	6.47	5"	5
M200600	8.03	3.53	.135	7.47	6"	5



Beam & Pipe Clamps

Parallel Pipe Clamp - MPPC Series


- Zinc plated after fabrication



Catalog Number	Size	Finish	Std Pkg
MPPC38EG	3/8"	Electro-Galv	50
MPPC12EG	1/2"	Electro-Galv	50
MPPC34EG	3/4"	Electro-Galv.	50
MPPC1EG	1"	Electro-Galv.	50
MPPC114EG	1-1/4"	Electro-Galv.	50
MPPC112EG	1-1/2"	Electro-Galv.	50
MPPC2EG	2"	Electro-Galv.	25
MPPC212EG	2-1/2"	Electro-Galv.	25
MPPC3EG	3"	Electro-Galv.	25
MPPC312EG	3-1/2"	Electro-Galv.	25
MPPC4EG	4"	Electro-Galv.	25

Grip Hanger

- Zinc plated after fabricatio




Catalog Number	Size	A Rod Size	B	Std Pkg
MGH050EG	1/2"	3/8"	2-1/4"	100
MGH075EG	3/4"	3/8"	2-5/16"	100
MGH100EG	1"	3/8"	2-7/16"	100
MGH125EG	1-1/4"	3/8"	2-5/8"	100
MGH150EG	1-1/2"	3/8"	2-3/4"	100
MGH200EG	2"	3/8"	3-1/4"	100
MGH250EG	2-1/2"	3/8"	4"	50
MGH300EG	3"	3/8"	4-3/8"	50
MGH400EG	4"	3/8"	4-11/16"	25
MGH500EG	5"	1/2"	5-5/16"	10
MGH600EG	6"	1/2"	6-7/16"	10
MGH700EG	7"	1/2"	8"	10



Swing Gate Hanger


- Zinc Plated after fabrication



Catalog Number	A Dia.	Use With	Std Pkg
MSG256EG	9/16"	1/2" Rod	20
MSG287EG	7/8"	1/2" Conduit	20

Swing Gate Hanger


- Zinc Plated after fabrication




Catalog Number	A Dia.	Use With	Std Pkg
MSG556EG	9/16"	1/2" Rod	20
MSG587EG	7/8"	1/2" Conduit	20




Beam & Pipe Clamps



MRAC Series




MPC Series



MPEC Series

Malleable Pipe Clamps - Right Angle

- Right Angle Pipe Clamps
- Material: Malleable Iron
- Hot dip galvanized



MRAC Series

Catalog Number	Pipe Size	Std Pkg
MRAC38HDG	3/8"	50
MRAC12HDG	1/2"	50
MRAC34HDG	3/4"	50
MRAC1HDG	1"	50
MRAC114HDG	1-1/4"	50
MRAC112HDG	1-1/2"	50
MRAC2HDG	2"	50
MRAC212HDG	2-1/2"	25
MRAC3HDG	3"	25
MRAC312HDG	3-1/2"	25
MRAC4HDG	4"	25



Malleable Pipe Clamps - Parallel

- Parallel Pipe Clamps
- Material: Malleable Iron
- Hot dip galvanized



MPC Series

Catalog Number	Pipe Size	Std Pk
MPC38HDG	3/8"	50
MPC12HDG	1/2"	50
MPC34HDG	3/4"	50
MPC1HDG	1"	50
MPC114HDG	1-1/4"	25
MPC112HDG	1-1/2"	25
MPC2HDG	2"	25
MPC212HDG	2-1/2"	25
MPC3HDG	3"	10
MPC312HDG	3-1/2"	10
MPC4HDG	4"	10

Malleable Pipe Clamps - Edge

- Edge Pipe Clamps
- Material: Malleable Iron
- Hot dip galvanized



MPEC Series


Catalog Number	Pipe Size	Std Pkg
MPEC12HDG	1/2"	50
MPEC34HDG	3/4"	50
MPEC1HDG	1"	25
MPEC114HDG	1-1/4"	25
MPEC112HDG	1-1/2"	25
MPEC2HDG	2"	25
MPEC212HDG	2-1/2"	10
MPEC3HDG	3"	10



Beam & Pipe Clamps

Beam Clamp

- For use with 1/4", 3/8" and 1/2" threaded rod
- Part used with M17514, M17538 and M17512
- Zinc plated after fabrication




Catalog Number	For Use With	Std Pkg
M1750EG	1/4", 3/8" & 1/2" Threaded Rod	25

Use with MasterStrut Swivel Nut for 1/4", 3/8" & 1/2" Rod (see page 144).

Wide Mouth Heavy Duty Beam Clamp

- Wide Mouth, Heavy Duty Style
- Use with 3/8" or 1/2" rod
- Zinc plated after fabrication




Catalog Number	A Rod Size	B	C	Std Pkg
M36238EG	3/8"	3/16"	1/2"	10
M36212EG	1/2"	1/4"	1/2"	10



Heavy Duty Beam Clamp


- Heavy Duty Style
- Use with 1/4", 3/8" or 1/2" rod
- Zinc plated after fabrication



Catalog Number	A Rod Size	B	C	Std Pkg
M25014EG	1/4"	1/8"	3/8"	10
M25038EG	3/8"	3/16"	1/2"	10
M25012EG	1/2"	1/4"	1/2"	10

Beam Clamp


- Zinc plated after fabrication



Catalog Number	Description	Std Pkg
M751EG	Electro-Galvanized	50

Requires #1/2-13 x 1-1/2" long Hex Head Cap Screw and #1/2-13 Channel Nut not included.


Used in Pairs



Beam & Pipe Clamps

Beam Clamp


- Zinc plated after fabrication



Catalog Number	Finish	Std Pkg
M753EG	Electro-Galvanized	25

U-Bolt Beam Clamp

- Zinc plated after fabrication




Catalog Number	A	Finish	Std Pkg
M1158EG	3-3/8"	Electro-Galv.	25
M1314EG	5"	Electro-Galv.	25



Beam Clamp

- Zinc plated after fabrication




Catalog Number	Finish	Std Pkg
M1325EG	Electro-Galvanized	20

See Minerallac's Traditional parts for other Beam Clamps suitable for strut applications, such as our 600 Universal Beam Clamp, our 700 Malleable Beam Clamp and our series of Heavy Duty 2-Hole Straps. These parts are shown on pages 64 and 71 of this catalog.



600




700




Fittings

2-Hole Splice Plate




Part No.	Finish	Std Pkg
M122EG	Electro-Galvanized	50
M122GRN	Painted Green	50

3-Hole Splice Plate



Part No.	Finish	Std Pkg
M123EG	Electro-Galvanized	25
M123GRN	Painted Green	25


4-Hole Splice Plate



Part No.	Finish	Std Pkg
M124EG	Electro-Galvanized	25
M124GRN	Painted Green	25




3-Hole 90 degree Flat Plate




Part No.	Finish	Std Pkg
M133EG	Electro-Galvanized	20
M133GRN	Painted Green	20

4-Hole 90 degree Flat Plate



Part No.	Finish	Std Pkg
M134EG	Electro-Galvanized	20
M134GRN	Painted Green	20

"T" Plate




Part No.	Finish	Std Pkg
M144EG	Electro-Galvanized	25
M144GRN	Painted Green	25




Fittings

Cross Plate




Part No.	Finish	Std Pkg
M155EG	Electro-Galvanized	10
M155GRN	Painted Green	10

90 Degree Tee-Plate



Part No.	Finish	Std Pkg
M244EG	Electro-Galvanized	20
M244GRN	Painted Green	20


Angle Cross Plate



Part No.	Finish	Std Pkg
M255EG	Electro-Galvanized	10
M255GRN	Painted Green	10




90 Degree 2-Hole Corner Angle




Part No.	Finish	Std Pkg
M212EG	Electro-Galvanized	50
M212GRN	Painted Green	50

90 Degree 2-Hole End Angle



Part No.	Finish	Std Pkg
M202EG	Electro-Galvanized	50
M202GRN	Painted Green	50

Self-Aligning 2-Hole Angle




Part No.	Finish	Std Pkg
M212DEG	Electro-Galvanized	50
M212DGRN	Painted Green	50




Fittings

3-Hole Corner Angle




Part No.	Finish	Std Pkg
M223EG	Electro-Galvanized	50
M223GRN	Painted Green	50

90 Degree 3-Hole End Angle



Part No.	Finish	Std Pkg
M213EG	Electro-Galvanized	50
M213GRN	Painted Green	50


90 Degree 3-Hole End Angle



Part No.	Finish	Std Pkg
M203EG	Electro-Galvanized	50
M203GRN	Painted Green	50




90 Degree 4-Hole Corner Angle




Part No.	Finish	Std Pkg
M204EG	Electro-Galvanized	25
M204GRN	Painted Green	25

90 Degree 4-Hole End Angle




Part No.	Finish	Std Pkg
M214EG	Electro-Galvanized	25
M214GRN	Painted Green	25

5-Hole End Angle




Part No.	Finish	Std Pkg
M205EG	Electro-Galvanized	25
M205GRN	Painted Green	25




Fittings

5-Hole End Angle




Part No.	Finish	Std Pkg
M215EG	Electro-Galvanized	25
M215GRN	Painted Green	25

4-Hole Corner Connector



Part No.	Finish	Std Pkg
M164EG	Electro-Galvanized	20
M164GRN	Painted Green	20


4-Hole Corner Connector



Part No.	Finish	Std Pkg
M225EG	Electro-Galvanized	20
M225GRN	Painted Green	20




3-Hole Corner Joint Connector




Part No.	Finish	Std Pkg
M263EG	Electro-Galvanized	25
M263GRN	Painted Green	25

4-Hole Corner Joint Connector




Part No.	Finish	Std Pkg
M264EG	Electro-Galvanized	25
M264GRN	Painted Green	25

5-Hole Corner Connector




Part No.	Finish	Std Pkg
M265EG	Electro-Galvanized	10
M265GRN	Painted Green	10




Fittings

Universal Corner Connector




Part No.	Finish	Std Pkg
M206EG	Electro-Galvanized	10
M206GRN	Painted Green	10

8-Hole Double Corner Connector



Part No.	Finish	Std Pkg
MC7208EG	Electro-Galvanized	10
MC7208GRN	Painted Green	10


4-Hole Joint Angle Connector



Part No.	Finish	Std Pkg
M624EG	Electro-Galvanized	25
M624GRN	Painted Green	25




5-Hole Corner Joint Connector




Part No.	Finish	Std Pkg
M625EG	Electro-Galvanized	10
M625GRN	Painted Green	10

5-Hole Double Angle Clevis Connector



Part No.	Finish	Std Pkg
M7105EG	Electro-Galvanized	25
M7105GRN	Painted Green	25

8-Hole Double Angle Clevis Connector




Part No.	Finish	Std Pkg
M7208EG	Electro-Galvanized	10
M7208GRN	Painted Green	10




Fittings

10-Hole Double Angle Clevis Connector




Part No.	Finish	Std Pkg
M7210EG	Electro-Galvanized	5
M7210GRN	Painted Green	5

12-Hole Triple Wing Connector



Part No.	Finish	Std Pkg
MC7312EG	Electro-Galvanized	10
MC7312GRN	Painted Green	10


4-Hole Closed Angle Fitting



Part No.	Finish	Std Pkg
M30445EG	Electro-Galvanized	10
M30445GRN	Painted Green	10




2-Hole Closed Angle Fitting




Part No.	Finish	Std Pkg
M31245EG	Electro-Galvanized	25
M31245GRN	Painted Green	25

2-Hole Open Angle Fitting



Part No.	Finish	Std Pkg
M30245EG	Electro-Galvanized	25
M30245GRN	Painted Green	25

4-Hole Open Angle




Part No.	Finish	Std Pkg
M31445EG	Electro-Galvanized	10
M31445GRN	Painted Green	10




Fittings

Slotted 90 Degree Angle




Part No.	Finish	Std Pkg
MA202EG	Electro-Galvanized	50
MA202GRN	Painted Green	50

2-Hole Slotted 90 Degree Angle



Part No.	Finish	Std Pkg
MA326EG	Electro-Galvanized	25
MA326GRN	Painted Green	25


Slotted 90 Degree Angle



Part No.	Finish	Std Pkg
MA2625EG	Electro-Galvanized	25
MA2625GRN	Painted Green	25




U-Support (13/16")




Part No.	Finish	Std Pkg
M5136EG	Electro-Galvanized	20
M5136GRN	Painted Green	20

U-Support (1-5/8")



Part No.	Finish	Std Pkg
M5158EG	Electro-Galvanized	50
M5158GRN	Painted Green	50

Column Attachment (1-5/8")




Part No.	Finish	Std Pkg
MCA158EG	Electro-Galvanized	25 pairs

Can only be used in pairs.




Fittings

Angle Cross Plate



Part No.	Finish	A	B	Std Pkg
MA262EG	Elec-Galv	6-5/8"	4"	10
MA262GRN	Green	6-5/8"	4"	10
MA282EG	Elec-Galv	8-5/8"	6"	10
MA282GRN	Green	8-5/8"	6"	10


Right or Left Angle Plate Connector



Part No.	Finish	Orientation	Std Pkg
ML203EG	Electro-Galv.	Left	25
ML203GRN	Painted Green	Left	25
MR203EG	Electro-Galv.	Right	25
MR203GRN	Painted Green	Right	25




Right or Left Angle Tee Plate



Part No.	Finish	Orientation	Std Pkg
ML214EG	Electro-Galv.	Left	25
ML214GRN	Painted Green	Left	25
MR214EG	Electro-Galv.	Right	25
MR214GRN	Painted Green	Right	25

Right or Left 4-Hole Corner Connector




Part No.	Finish	Orientation	Std Pkg
ML350EG	Electro-Galv.	Left	25
ML350GRN	Painted Green	Left	25
MR350EG	Electro-Galv.	Right	25
MR350GRN	Painted Green	Right	25




Fittings

One-Hole Angle



Part No.	Finish	A	Std Pkg
M201378EG	Electro-Galv.	3-7/8"	25
M201378GRN	Painted Green	3-7/8"	25
M201578EG	Electro-Galv.	5-7/8"	25
M201578GRN	Painted Green	5-7/8"	25
M201778EG	Electro-Galv.	7-7/8"	25
M201778GRN	Painted Green	7-7/8"	25
M201978EG	Electro-Galv.	9-7/8"	25
M201978GRN	Painted Green	9-7/8"	25


Self-Aligning 2-Hole Angle



Part No.	Finish	A	Std Pkg
M230EG	Electro-Galv.	3"	25
M230GRN	Painted Green	3"	25
M235EG	Electro-Galv.	3-1/2"	25
M235GRN	Painted Green	3-1/2"	25
M240EG	Electro-Galv.	4"	25
M240GRN	Painted Green	4"	25




Single Channel Bracket Support



Fittings

Part No.	Finish	Std Pkg
MBS587EG	Electro-Galvanized	5
MBS587GRN	Painted Green	5

Double Channel Bracket Support




Part No.	Finish	Std Pkg
MDS750EG	Electro-Galvanized	5
MDS750GRN	Painted Green	5




Fittings

Right or Left 6-Hole Corner Connector



Part No.	Finish	Orientation	Std Pkg
ML541EG	Electro-Galv.	Left	10
ML541GRN	Painted Green	Left	10
MR541EG	Electro-Galv.	Right	10
MR541GRN	Painted Green	Right	10


Right or Left 6-Hole Gussetted Corner Connector




Part No.	Finish	Orientation	Std Pkg
MLG541EG	Electro-Galv.	Left	25
MLG541GRN	Painted Green	Left	25
MRG541EG	Electro-Galv.	Right	25
MRG541GRN	Painted Green	Right	25



4-Hole Splice Clevis



M6136EG
Accommodates
13/16" channel




M6158EG
Accommodates
1-5/8" channel


Part No.	Finish	Channel Size	Std Pkg
M6136EG	Electro-Galv.	13/16"	10
M6136GRN	Painted Green	13/16"	10
M6158EG	Electro-Galv.	1-5/8"	10
M6158GRN	Painted Green	1-5/8"	10

Fittings


Internal Channel Joiners



Includes 2
Cam Screws



MIJ1362EG
Accommodates
13/16" channel




MIJ1582EG
Accommodates
1-5/8" channel

Part No.	Finish	Channel Size	Std Pkg
MIJ1362EG	Electro-Galv.	13/16"	20
MIJ1582EG	Electro-Galv.	1-5/8"	20




Fittings


Mounting Detail "A"




Mounting Detail "B"



Post Base - 6" x 6" x 1-5/8" High



See Mounting Detail A




See Mounting Detail B


Catalog Number	Finish	Mounting Detail	Std Pkg
M803EG	Electro-Galv.	B	10
M803GRN	Painted Green	B	10
M803SQEG	Electro-Galv.	A	10
M803SQGRN	Painted Green	A	10



Post Base - 6" x 6" x 3-1/2" High




See Mounting Detail A




See Mounting Detail B

Catalog Number	Finish	Mounting Detail	Std Pkg
M813EG	Electro-Galv.	B	5
M813GRN	Painted Green	B	5
M813SQEG	Electro-Galv.	A	5
M813SQGRN	Painted Green	A	5

Double Column Post Base - 6" x 6" x 3-1/2" High




See Mounting Detail A




See Mounting Detail B

Catalog Number	Finish	Mounting Detail	Std Pkg
M843EG	Electro-Galv.	B	5
M843GRN	Painted Green	B	5
M843SQEG	Electro-Galv.	A	5
M843SQGRN	Painted Green	A	5




Hardware/Accessories


Spring Nut Assembly



1. Insert spring nut into channel any place you choose. The spring holds the nut in place against grooves. This prevents slippage.




2. Place fitting over nut & insert capscrew.




3. Tighten capscrew to complete assembly.

Channel Nut w/o Spring - MCW Series



Part No.	Size	Finish	Std Pkg
MCW14EG	1/4"	Electro-Galv.	100
MCW38EG	3/8"	Electro-Galv.	100
MCW12EG	1/2"	Electro-Galv.	100


Spring Grip Channel Nut - MCT Series



Part No.	Size	Finish	Std Pkg
MCT14EG	1/4"	Electro-Galv.	100
MCT516EG	5/16"	Electro-Galv.	100
MCT38EG	3/8"	Electro-Galv.	100
MCT12EG	1/2"	Electro-Galv.	100




Channel Nut w/Long Spring - MCL Series




Part No.	Size	Finish	Std Pkg
MCL14EG	1/4"	Electro-Galv.	100
MCL38EG	3/8"	Electro-Galv.	100
MCL12EG	1/2"	Electro-Galv.	100
MCL58EG	5/8"	Electro-Galv.	100
MCL34EG	3/4"	Electro-Galv.	100

Channel Nut w/Regular Spring - MCR Series



Part No.	Size	Finish	Std Pkg
MCR14EG	1/4"	Electro-Galv.	100
MCR38EG	3/8"	Electro-Galv.	100
MCR12EG	1/2"	Electro-Galv.	100
MCR58EG	5/8"	Electro-Galv.	100

Channel Nut w/Short Spring - MCS Series




Part No.	Size	Finish	Std Pkg
MCS14EG	1/4"	Electro-Galv.	100
MCS38EG	3/8"	Electro-Galv.	100
MCS12EG	1/2"	Electro-Galv.	100



Hardware/Accessories

Square Washer

- Available Zinc Plated or Painted green
- Washers 1-5/8" square with 1/4", 3/8", 1/2", 5/8" and 3/4" hole sizes




Part No.	Bolt Size	Finish	Std Pkg
M10114EG	1/4"	Electro-Galv.	100
M10114GRN	1/4"	Painted Green	100
M10138EG	3/8"	Electro-Galv.	100
M10138GRN	3/8"	Painted Green	100
M10112EG	1/2"	Electro-Galv.	100
M10112GRN	1/2"	Painted Green	100
M10158EG	5/8"	Electro-Galv.	50
M10158GRN	5/8"	Painted Green	50
M10134EG	3/4"	Electro-Galv.	100
M10134GRN	3/4"	Painted Green	100



Guided Square Washer

- Available Zinc Plated or Painted green
- Washers 1-5/8" square with 1/4", 3/8", and 1/2" hole sizes




Part No.	Bolt Size	Finish	Std Pkg
M101D14EG	1/4"	Electro-Galv.	100
M101D14GRN	1/4"	Painted Green	100
M101D38EG	3/8"	Electro-Galv.	100
M101D38GRN	3/8"	Painted Green	100
M101D12EG	1/2"	Electro-Galv.	100
M101D12GRN	1/2"	Painted Green	100



Hardware/Accessories

Continuous Threaded Rod


- Zinc plated after fabrication
- Available in 6' and 10' lengths



Catalog Number	Description & Length	Std Pkg
CTR1/4x6EG	#1/4-20, 6 ft	50 pcs (300 ft)
CTR1/4x10EG	#1/4-20, 10 ft	50 pcs (500 ft)
CTR3/8x6EG	#3/8-16, 6 ft	25 pcs (150 ft)
CTR3/8x10EG	#3/8-16, 10 ft	25 pcs (250 ft)
CTR1/2x6EG	#1/2-13, 6 ft	12 pcs (72 ft)
CTR1/2x10EG	#1/2-13, 10 ft	12 pcs (120 ft)

Hexagon Rod Coupling

- Zinc plated after fabrication




Catalog Number	Size	Std Pkg
CTRC1/4EG	#1/4-20 x 7/8"	100
CTRC3/8EG	#3/8-16 x 1-1/8"	100
CTRC1/2EG	#1/2-13 x 1-1/4"	50



Safety End Caps - MSEC Series

- Black Plastic
- Other colors available



Catalog Number	For Use With	Std Pkg
MSEC158	1-5/8" Channel	100
MSEC1316	13/16" Channel	100

Touch-Up Paint




Catalog Number	Description	Std Pkg
MSTP010	Channel Green, 12 oz. can	1



Hardware/Accessories

Round Head Machine Screw


- Zinc Plated after fabrication.



Catalog Number	Size	Standard Package
MRH25075	1/4 x 3/4"	100
MRH25100	1/4 x 1"	100
MRH25125	1/4 x 1-1/4"	100
MRH37100	3/8 x 1"	100
MRH37125	3/8 x 1-1/4"	100
MRH37150	3/8 x 1-1/2"	100

Hex Head Cap Screw

- Zinc Plated after fabrication.




Catalog Number	Size	Standard Package
MHH25075	1/4 x 3/4"	100
MHH25100	1/4 x 1"	100
MHH25125	1/4 x 1-1/4"	100
MHH25150	1/4 x 1-1/2"	100
MHH37075	3/8 x 3/4"	100
MHH37100	3/8 x 1"	100
MHH37125	3/8 X 1-1/4"	100
MHH37150	3/8 X 1-1/2"	100
MHH37200	3/8 X 2"	100
MHH50075	1/2 X 3/4"	100
MHH50100	1/2 X 1"	100
MHH50125	1/2 X 1-1/4	100
MHH50150	1/2 X 1-1/2	100
MHH50175	1/2 X 1-3/4"	100
MHH50200	1/2 X 2"	100



Slotted Hex Head Machine Screw


- Zinc Plated after fabrication.



Catalog Number	Size	Standard Package
MSH25075	1/4 x 3/4"	100
MSH31100	5/16 x 1"	100
MSH31125	5/16 x 1-1/4"	100
MSH31150	5/16 x 1-1/2"	100
MSH37125	3/8 x 1-1/4"	100

Square Nut

- Zinc Plated after fabrication.



Catalog Number	Size	Standard Package
MSN14	1/4"	100
MSN516	5/16"	100
MSN38	3/8"	100
MSN12	1/2"	100



Hardware/Accessories

Hex Nut


- Zinc Plated after fabrication.



Catalog Number	Size	Standard Package
MHN14	1/4"	500
MHN38	3/8"	500
MHN12	1/2"	100
MHN58	5/8"	50
MHN34	3/4"	50

Swivel Nut

- Use with M1750 Beam Clamp
- Zinc Plated after fabrication.




Catalog Number	Threaded Rod Size	Standard Package
M17514	#1/4-20	50
M17538	#3/8-16	50
M17512	#1/2-13	50

MasterStrut Part No. M1750 Beam Clamp sold on page 127.



Fender Washer


- Zinc Plated after fabrication.



Catalog Number	Size	Outside Diameter	Standard Package
MFW14	1/4"	1-1/2	100
MFW38	3/8"	1-1/2"	100
MFW12	1/2"	1-1/2"	100

Lock Washer

- Zinc Plated after fabrication.




Catalog Number	Size	Standard Package
MWL14	1/4"	100
MWL38	3/8"	100
MWL12	1/2"	100



Hardware/Accessories

Flat Washer


- Zinc Plated after fabrication.



Catalog Number	Size	Outside Diameter	Standard Package
MWF14	1/4"	3/4"	200
MWF38	3/8"	1"	100
MWF12	1/2"	1-3/8"	100
MWF58	5/8"	1-3/4"	100
MWF34	3/4"	2"	100

Safety Anchor Strap


- Zinc Plated after fabrication.




Catalog Number	Length	Standard Package
MS17509	9"	100
MS175012	12"	100
MS175015	15"	100

DIMENSION CHARTS


K-Series Hangers

										
Cat No.	Rigid/IMC	EMT	A	B	Thrd	Imp	C ₁	C ₂	D	E
K0B	3/8-1/2"	1/2"	0.675-0.840	1/4	1/4-20	1/4x3/8	.625	.040		
K1B	3/4	3/4"	0.922-1.050	1/4	1/4-20	1/4x3/8	.750	.040		
K2B	1"	1"	1.163-1.315	1/4	1/4-20	1/4x3/8	.750	.040		



Conduit Hangers

								
Catalog Number	Rigid & IMC	EMT	Nom. Pipe O.D.	A	B	C	D	E
0	3/8-1/2"	1/2"	0.675-0.840	1/4	1/4	.750	.050	
1	3/4"	3/4"	0.922-1.050	1/4	1/4	.875	.050	
2	1"	1"	1.163-1.315	1/4	1/4	.875	.050	
2-1/2	---	1-1/4"	1.510	1/4	1/4	.875	.050	
3	1-1/4"	1-1/2"	1.660-1.740	1/4	1/4	.875	.050	
4	1-1/2"	---	1.883-1.900	5/16	1/4	1.000	.060	
5	2"	2"	2.197-2.375	5/16	1/4	1.250	.060	
6	2-1/2"	2-1/2"	2.857-2.875	5/16	1/4	1.250	.060	
7	3"	3"	3.476-3.500	5/16	5/16	1.250	.060	
8	3-1/2"	3-1/2"	3.971-4.000	5/16	5/16	1.250	.060	
9	4"	4"	4.466-4.500	1/2	1/2	1.750	.080	
10	5"	---	5.563	1/2	1/2	1.750	.080	

K-Series Jiffy Clips

						
Catalog Number	EMT	A	Nom. Pipe O.D.	B	Bolt C	D
K30	1/2"	.050	0.706	1/4	0.625	
K45	3/4"	.050	0.922	1/4	0.625	
K55	1"	.050	1.163	1/4	0.875	


Standard Jiffy Clips



Cat. No.	Tubing O.D.	Rigid	EMT	A	Nom. OD B	Bolt C	D	No. Ribs
102	1/8"	---	---	.035	0.125	3/16	.500	1
103	3/16"	---	---	.035	0.1875	3/16	.500	1
105	1/4"	---	---	.035	0.250	3/16	.500	1
110	5/16"	---	---	.035	0.3125	3/16	.500	1
115	3/8"	---	---	.045	0.375	3/16	.625	1
120	---	1/8"	---	.045	0.405	3/16	.625	1
*125	1/2"	1/4"	BX	.045	0.540	3/16	.625	1
130	---	3/8"	1/2"	.050	0.675-0.706	1/4	.750	1
135	3/4"	---	---	.050	0.750	1/4	.750	1
140	---	1/2"	---	.050	0.840	1/4	.875	1
145	---	---	3/4"	.050	0.922	1/4	.875	1
150	1"	3/4"	---	.050	1.000-1.050	1/4	.875	1
155	---	---	1"	.050	1.163	1/4	.875	1
160	---	1"	---	.060	1.315	1/4	1.000	2
165	1-1/2"	---	1-1/4"	.060	1.500-1.510	1/4	1.000	2
170	---	1-1/4"	---	.060	1.660	5/16	1.250	2
*121	---	---	BX	.045	0.475	3/16	.625	1


*#125 fits BX 12-3, 10-2, and 10-3. #121 fits BX 14-2, 14-3 and 12-2.

Min-E Jiffy Clips



Catalog Number	Fits			A	Nom. Pipe O.D., B	Bolt C	D
	Rigid	EMT	Flexible				
MINE28	---	---	3/8"	.074	0.560	1/4	.625
MINE30	---	1/2"	---	.074	0.706	1/4	.625
MINE40	1/2"	---	1/2"	.090	0.840	1/4	.750
MINE45	---	3/4"	---	.074	0.922	1/4	.625
MINE50	3/4"	---	3/4"	.090	1.050	1/4	.750
MINE55	---	1"	---	.090	1.163	1/4	.750



Duplex Affy Clips



Catalog Number	Cable or Tubing Dia. A	Tubing Dia. B	C	D	Bolt E	F
300A	.125	.125	.035	.500	3/16	.990
300	.250	.250	.035	.500	3/16	1.260
301	.375	.375	.035	.500	3/16	1.570
300C*	.250	.250	.035	.500	3/16	1.260
301C*	.375	.375	.035	.500	3/16	1.570
302C*	.250	.375	.035	.500	3/16	1.400

*C denotes Copper Plated part. Other parts Zinc Plated.


Duplex Slotted Affy Clips





Catalog Number	Cable or Tubing Dia. A	Tubing Dia. B	C	D	E	F
300SC	.250	.250	.035	.500	1.375	.370
301SC	.375	.375	.035	.500	1.510	.380

DIMENSION CHARTS


Two-Hole Straps

								
Cat. No.	Rigid & IMC	EMT	A	B	C	D	Bolt E	No. Ribs
225	1/4"	---	.035	.625	1.765	.360	1/8	1
228	3/8"	---	.035	.750	2.515	.495	3/16	2
230	---	1/2"	.035	.750	2.558	.478	3/16	2
240	1/2"	---	.035	.750	2.565	.450	3/16	2
245	---	3/4"	.035	.750	2.765	.510	3/16	2
250	3/4"	---	.035	.750	2.795	.470	3/16	2
255	---	1"	.035	.750	3.205	.620	3/16	2
260	1"	---	.035	.750	3.140	.520	3/16	2
265	---	1-1/4"	.050	.875	3.875	.665	1/4	2
270	1-1/4"	---	.050	.875	4.375	.810	1/4	2
275	---	1-1/2"	.050	1.000	4.300	.625	1/4	2
280	1-1/2"	---	.062	1.000	4.585	.660	1/4	1
285	---	2"	.050	1.000	5.000	.720	1/4	2
290	2"	---	.062	1.250	5.030	.630	5/16	1
292	2-1/2"	---	.062	1.250	6.125	.810	3/8	1
294	3"	---	.090	1.250	7.438	.850	3/8	1

Heavy Duty Two-Hole Straps



								
Cat. No.	Rigid & IMC	EMT	A	B	C	D	Bolt E	No. Ribs
HD260	1"	---	.090	.750	3.092	.520	.206	0
HD270	1-1/4"	---	.080	.875	4.400	.720	.281	2
HD280	1-1/2"	---	.090	1.000	4.590	.730	.281	1
HD290	2"	---	.090	1.250	5.100	.725	.344	1
HD292	2-1/2"	2-1/2"	.090	1.250	6.188	.730	.406	1
HD294	3"	3"	.120	1.250	7.125	.910	.406	1
HD295	3-1/2"	3-1/2"	.187	1.250	8.750	1.140	.656	1
HD296	14"	4"	.187	1.250	9.063	1.130	.656	1
HD297	5"	---	.250	1.250	10.680	1.400	.656	0
HD298	6"	---	.250	1.250	12.140	1.500	.656	2

One-Hole Service Entrance Straps



Catalog Number	A	B	C	D	Bolt E	F
MED2	.460	.060	.280	1.080	3/16	.500
MED3	.550	.045	.325	1.190	3/16	.625
MED5	1.050	.074	.525	2.056	1/4	.625
MED7	.835	.074	.650	2.148	1/4	.875
MED9	.970	.080	.455	2.125	1/4	.875
MED12	1.090	.080	.655	2.275	1/4	.875
MED13	1.275	.080	.685	2.665	1/4	.875
MED14	1.465	.120	.695	2.880	1/4	.875
MED16	1.675	.120	.888	3.355	1/4	1.000
H12	1.209	.120	.585	2.500	1/4	.875
H14	1.330	.120	.615	2.680	1/4	1.000
H16	1.570	.120	.645	3.060	1/4	1.000



Two-Hole Service Entrance Straps





Cat. No.	For SEU	A	B	C	D	Bolt E	No. Ribs
221	UF	.425	.035	.625	2.070	1/8	1
212	Inside dia .635"	.635	.050	.750	2.895	1/8	1
223	2	.875	.035	.750	2.690	3/16	1
2203	1,1/0,2/0	1.100	.035	.750	3.018	3/16	2
2403	3/0,4/0	1.340	.035	.750	2.990	3/16	2

DIMENSION CHARTS

Two-Hole Service Entrance Straps

							
Cat. No.	For SER & BX	A	B	C	D	Bolt E	No. Ribs
225	BX, SER8	.035	.625	1.765	.360	1/8	1
228	6	.035	.750	2.515	.495	3/16	2
230	4	.035	.750	2.558	.478	3/16	2
240	2	.035	.750	2.565	.450	3/16	2
245	1, 1/0	.035	.750	2.765	.510	3/16	2
250	2/0	.035	.750	2.795	.470	3/16	2
255	3/0	.035	.750	3.205	.620	3/16	2
260	4/0	.035	.750	3.140	.520	3/16	2

Universal Beam Clamps


				
Catalog Number	Screw Dia. A	Screw Length B	Bottom Thread C	Back Thread D
600	1/4"-20	1"	1/4"-20	1/4"-20
600-10	1/4"-20	1"	10-24	10-24
602	5/16"-18	1-3/8"	3/8"-16	none
602B	5/16"-18	1-3/8"	3/8"-16	3/8"-16

GALVANIC CORROSION COMPATABILITY OF METALS


MATERIALS	Stainless Steel	Copper Plated Steel	Zinc Plated Steel	Aluminum	Spring Steel
Stainless Steel	Yes	No	Yes	Yes	Yes
Copper Plated Steel	No	Yes	No	No	No
Zinc Plated Steel	Yes	No	Yes	Yes	Yes
Aluminum	Yes	No	Yes	Yes	Yes
Spring Steel	Yes	No	Yes	Yes	Yes

DIMENSION CHARTS



Medium Jiffy Clips

						
Catalog Number	Rigid & IMC	EMT	A	B	Bolt C	D
MED30	---	1/2"	.080	0.706	1/4	.875
MED40	1/2"	---	.080	0.840	1/4	.875
MED45	---	3/4"	.080	0.922	1/4	.875
MED50	3/4"	---	.080	1.050	1/4	.875
MED55	---	1"	.080	1.163	1/4	.875
MED60	1"	---	.080	1.315	1/4	.875
MED65	---	1-1/4"	.090	1.510	5/16	1.000
MED70	1-1/4"	---	.090	1.660	5/16	1.000
MED75	---	1-1/2"	.090	1.740	5/16	1.000
MED80	1-1/2"	---	.120	1.900	3/8	1.000
MED85	---	2"	.090	2.197	3/8	1.250
MED90	2"	---	.120	2.375	3/8	1.250

Heavy Duty Jiffy Clips

						
Catalog Number	Rigid & IMC	EMT	A	Nom. Pipe O.D. B	Bolt C	D
H30	---	1/2"	.120	0.706	1/4	.875
H40	1/2"	---	.120	0.840	1/4	.875
H45	---	3/4"	.120	0.922	1/4	.875
H50	3/4"	---	.120	1.050	1/4	.875
H55	---	1"	.120	1.163	1/4	.875
H60	1"	---	.120	1.315	1/4	.875
H65	---	1-1/4"	.120	1.510	5/16	1.000
H70	1-1/4"	---	.120	1.660	5/16	1.000
H75	---	1-1/2"	.120	1.740	5/16	1.000
H80	1-1/2"	---	.120	1.900	3/8	1.250
H85	---	2"	.120	2.197	3/8	1.250
H90	2"	---	.187	2.375	3/8	1.250
H92	2-1/2"	---	.187	2.875	5/8	1.250
H94	3"	---	.187	3.500	5/8	1.250
H95	3-1/2"	---	.250	4.000	5/8	1.250
H96	4"	---	.250	4.500	5/8	1.250
H97	5"	---	.250	5.563	5/8	1.500
H98	6"	---	.250	6.625	5/8	1.500

Malleable Beam Clamps

				
Catalog Number	Screw Dia. A	Screw Length B	Bottom Tapping C	Back Tapping D
700	1/4"-20	1,000	1/4"-20	1/4"-20
700-10	1/4"-20	1,000	10-24	10-24
701	3/8"-16	1,250	3/8"-16	3/8"-16
702	1/2"-13	1,500	3/8"-16	3/8"-16
703	5/8"-11	1,500	1/2"-13	1/2"-13

LOAD CAPACITIES

One-Hole Strap W/Rawl Spike®

	Embed. Depth	3000 PSI Concrete	4000 PSI Concrete	5000 PSI Concrete	Concrete Block
Tension Load (lbs)	1-1/4"	975	1,180	1,1450	740
Shear Load (lbs)	1-1/4"	2,250	2,425	2,600	2,090

Minerallac Part Nos. MED30RS, MED45RS and MED55RS

SIZE REFERENCE CHARTS

Rigid Steel Conduit (Heavy Wall Conduit)

Nominal Conduit Size	Outside Diameter (inches)	Nominal Inside Diameter (inches)	Min. Weight per 100 ft W/Coluplings Attached	Weight of Conduit & Conductor per 100 ft
3/8"	0.675	0.493	51.5 lbs	65.1 lbs
1/2"	0.840	0.632	79.0 lbs	101.1 lbs
3/4"	1.050	0.836	105.0 lbs	145.8 lbs
1"	1.315	1.063	153.0 lbs	219.3 lbs
1-1/4"	1.660	1.394	201.0 lbs	318.3 lbs
1-1/2"	1.900	1.624	249.0 lbs	408.8 lbs
2"	2.375	2.083	332.0 lbs	593.8 lbs
2-1/2"	2.875	2.489	527.0 lbs	901.0 lbs
3"	3.500	3.090	682.6 lbs	1259.0 lbs
3-1/2"	4.000	3.570	831.0 lbs	1604.0 lbs
4"	4.500	4.050	972.3 lbs	1967.0 lbs

Intermediate Metal Conduit

Nominal Conduit Size	Outside Diameter (inches)	Nominal Inside Diameter (inches)	Min. Weight per 100 ft W/Coluplings Attached	Weight of Conduit & Conductor per 100 ft
1/2"	0.815	0.745	60.0 lbs	82.1 lbs
3/4"	1.029	0.954	82.0 lbs	122.8 lbs
1"	1.290	1.205	116.0 lbs	182.3 lbs
1-1/4"	1.638	1.553	150.0 lbs	267.3 lbs
1-1/2"	1.883	1.793	182.0 lbs	341.8 lbs
2"	2.360	2.266	242.0 lbs	503.8 lbs
2-1/2"	2.857	2.727	401.0 lbs	775.0 lbs
3"	3.476	3.346	493.0 lbs	1069.0 lbs
3-1/2"	3.971	3.841	573.0 lbs	1346.0 lbs
4"	4.466	4.336	638.0 lbs	1632.0 lbs

SIZE REFERENCE CHARTS

Electrical Metallic Tubing (EMT) (Thin Wall Conduit)

Nominal Conduit Size	Outside Diameter (inches)	Nominal Inside Diameter (inches)	Min. Weight per 100 ft W/Coluplings Attached	Weight of Conduit & Conductor per 100 ft
3/8"	0.577	0.493	23.0 lbs	36.6 lbs
1/2"	0.706	0.622	28.5 lbs	50.6 lbs
3/4"	0.922	0.824	43.5 lbs	84.3 lbs
1"	1.163	1.049	64.0 lbs	130.3 lbs
1-1/4"	1.510	1.380	95.0 lbs	212.3 lbs
1-1/2"	1.740	1.610	110.0 lbs	269.8 lbs
2"	2.197	2.067	140.0 lbs	401.8 lbs
2-1/2"	2.875	2.731	205.0 lbs	579.0 lbs
3"	3.500	3.356	250.0 lbs	626.3 lbs
3-1/2"	4.000	3.834	325.0 lbs	1098.0 lbs
4"	4.500	4.334	370.0 lbs	1364.0 lbs

Dimensions taken from ANSI C80.3-1977.
Conduit plus weight of heaviest conductor combination as specified by the National Electrical Code.

Rigid Aluminum Conduit

Nominal Conduit Size	Outside Diameter (inches)	Nominal Inside Diameter (inches)	Min. Weight per 100 ft W/Coluplings Attached	Weight of Conduit & Conductor per 100 ft
1/2"	0.840	0.632	27.4 lbs	49.5 lbs
3/4"	1.050	0.836	36.4 lbs	84.3 lbs
1"	1.315	1.063	53.0 lbs	130.3 lbs
1-1/4"	1.660	1.394	69.6 lbs	212.3 lbs
1-1/2"	1.900	1.624	82.2 lbs	269.8 lbs
2"	2.375	2.083	115.7 lbs	401.8 lbs
2-1/2"	2.875	2.489	182.5 lbs	579.0 lbs
3"	3.500	3.090	238.9 lbs	626.3 lbs
3-1/2"	4.000	3.570	287.7 lbs	1098.0 lbs
4"	4.500	4.050	340.0 lbs	1364.0 lbs
5"	5.563	5.073	465.4 lbs	2028.0 lbs
6"	6.625	6.093	612.5 lbs	2870.0 lbs

Dimensions taken from ANSI C80.3-1977.
Conduit plus weight of heaviest conductor combination as specified by the National Electrical Code.

Schedule 40 PVC Plastic Pipe

Nominal Pipe Size	Outside Diameter (inches)	Wall Thickness (inches)	Weight of Pipe (lbs/ft)	Weight of Water (lbs/ft)
1/8"	.405	.068	.04	.02
1/4"	.540	.088	.07	.04
3/8"	.675	.091	.10	.08
1/2"	.840	.109	.15	.1
3/4"	1.050	.113	.2	.2
1"	1.315	.133	.3	.4
1-1/4"	1.660	.140	.4	.6
1-1/2"	1.900	.145	.5	.9
2"	2.375	.154	.6	1.4
2-1/2"	2.875	.203	1.0	2.1
3"	3.500	.216	1.3	3.2
3-1/2"	4.000	.226	1.6	4.3
4"	4.500	.237	1.9	5.5

All Threaded Rod (ATR)

Nominal Size and Thread	Root Area		Design Load (SF=5)	
	In. ²	cm ²	LBS	kN
1/4"-20"	0.027	0.174	240	1.07
5/16"-18"	0.045	0.290	400	1.78
3/8"-16"	0.068	0.438	610	2.71

Dimensions taken from ANSI B1.1-1982 Unified Inch Screw Threads.
All threads are UNCR series.
Tabulated loads are based on an allowable tensile stress of 12000 psi (82.7 MPa) reduced by 25% resulting in 9000 psi (62 MPa). From ANSI/MSS SP-58, Table 3.

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
NUMERIC-ALPHA						
0	10000	4.0	100	X	X	113
0A	14000	1.7	100	X		*
0B	12000	6.6	100	X		112
0C	11200	4.0	100	X		*
0S	15000	4.0	100	X		113
0SB	15200	6.6	100	X		112
1	10001	5.6	100	X	X	113
1A	14001	2.3	100			*
1B	12001	8.2	100			112
1S	15001	5.6	100			113
1SB	15201	8.2	100			112
10	10010	8.8	10	X	X	113
10B	12010	10.4	10	X		112
102	40102	0.5	100			117
102E	44102	0.6	100			*
103	40103	0.6	100			117
105	40105	0.6	100			117
105C	46105	0.6	100			*
105E	46105	0.7	100			*
105SC	47105	0.5	100			121
110	40110	0.7	100			117
1105	76105	1.1	100			127
115	40115	1.4	100			117
115C	46115	1.4	100			*
115E	44115	1.6	100			*
115SC	47115	1.3	100			121
120	40120	1.3	100			117
121	40121	1.5	100	X		117, 129
125	40125	1.9	100	X		117, 129
125C	46125	1.5	100			*
125E	44125	1.6	100			*
125SC	47125	1.4	100			121
130	40130	3.0	100		X	117, 129
135	40135	2.4	100			117
14WNW	30001	2.0	100			117, 129
140	40140	3.3	100		X	117, 129
145	40145	4.2	100		X	117, 129
150	40150	3.8	100		X	117, 129
155	40155	4.4	100		X	117, 129
160	40160	7.2	100			117, 129
165	40165	8.3	100		X	117
170	40170	11.0	100		X	117
2	10002	7.4	100	X	X	113
2A	14002	2.7	100	X		*
2B	12002	9.0	100	X		112
2S	15001	7.4	100	X		113
2SB	15202	9.0	100	X		112
2SC4	80008	11.2	100			145
2-1/2	10025	7.8	100	X		113
2-1/2B	12025	10.2	100	X		112
2-1/2S	15025	7.8	100	X		113
2-1/2SB	15225	10.2	100	X		112
212	66212	3.4	100	X		130
2203	66203	3.0	100	X		130
221	66221	1.5	100			130
223	66223	3.2	100	X		130

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
225	66225	1.7	100			125, 131
228	66228	2.8	100			125, 131
230	66230	2.7	100	X		124, 131
230SS	65230	2.7	100			124, 131
240	66240	2.7	100	X		125, 131
240SS	65240	2.7	100			125, 131
2403	66403	3.1	100	X		130
245	66245	3.0	100	X		124, 131
245SS	66245	3.0	100			124, 131
250	66250	3.2	100	X		125, 131
250SS	65250	3.2	100			125, 131
255	66255	3.6	100	X		124, 131
260	66260	3.8	100	X		125, 131
265	66265	7.6	100	X		124
270	66270	7.8	100	X		125
275	66275	9.4	100	X		124
280	66280	12.2	100	X		125
285	66285	11.0	100	X		124
290	66290	8.8	50	X		125
292	66292	10.2	50	X		124, 125
294	66294	9.2	25	X		124, 125
3	10003	8.8	100	X	X	113
3B	12003	11.0	100	X		112
3S	15003	8.8	100	X		113
3SB	15203	11.0	100	X		112
300	52300	1.0	100			122
300A	52310	0.5	100			122
300C	55300	1.0	100			*
300SC	53300	1.0	100			123
301	52301	1.1	100			122
301C	55301	1.1	100			*
301SC	53301	1.1	100			123
302C	55302	1.1	100			*
305	52305	1.5	100			122
4	10004	13.4	100	X	X	113
4B	12004	16.8	100	X		112
4S	15004	13.4	100	X		113
4SB	15204	16.8	100	X		112
410C	34420	7.6	100 ft			180
410C100	34500	7.6	100 ft			180
478C	34479	12.8	100 ft			180
5	10005	10.0	50	X	X	113
5B	12005	11.4	50	X		112
5S	15005	10.0	50	X		113
5SB	15205	11.4	50	X		112
500	25000	5.3	100			71
500100	25100	8.8	100			72
500100B	25210	8.8	100			72
50050	25050	8.3	100			72
50050B	25250	8.3	100			72
50075	25075	8.4	100			72
50075B	25275	8.4	100			72
500KC1	25301	9.9	100			73
500KC112	25312	11.0	100			73
500KC112B	25412	11.0	100			73
500KC114	25314	10.9	100			73

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
500KC114B	25414	10.9	100			73
500KC1234	25334	8.9	100			73
500KC1234B	25434	8.9	100			73
500KC1B	25401	9.9	100			73
500KC2	25302	12.1	100			73
500KC2B	25402	12.1	100			73
5035	32503	22.5	100			*
505	32505	4.6	100			*
519	32510	40.8	100			*
550	32550	57.3	50			*
560	32560	73.8	50			*
6	10006	11.6	50	X	X	113
6B	12006	14.0	50	X		112
6S	15006	11.6	50	X		113
6SB	15206	14.0	50	X		112
600	24600	6.3	50			140
60010	24601	6.4	50			140
600100	26610	15.4	100		74,	143
600100B	26001	15.4	100		74,	143
60050	26650	14.9	100		74,	143
60050B	26501	14.9	100		74,	143
60075	26675	15.0	100		74,	143
60075B	26701	15.0	100		74,	143
600KC1	26101	16.5	100		75,	144
600KC112	26112	17.6	100		75,	144
600KC112B	26212	17.6	100		75,	144
600KC114	26114	17.5	100		75,	144
600KC114B	26214	17.5	100		75,	144
600KC1234	26100	15.5	100		75,	144
600KC1234B	26200	15.5	100		75,	144
600KC1B	26201	16.5	100		75,	144
600KC2	26102	18.7	100		75,	144
600KC2B	26202	18.7	100		75,	144
602	24602	7.4	25			140
602B	24603	7.6	25			140
602BSS	24613	7.6	25			140
634R	38634	3.0	100			166
634RW	38834	3.1	100	X		167
646R	38646	8.0	100	X		166
646RS	38246	5.0	50	X		168
646RW	38846	7.8	100	X		167
646RWS	38948	6.0	50	X		168
648R	38648	9.6	100	X		166
648RS	38248	6.0	50	X		168
648RW	38848	9.4	100	X		167
648RWS	38946	6.0	50	X		168
654R	38654	8.6	50	X		166
654RS	38254	15.0	50	X		168
7	10007	7.4	25	X	X	113
7B	12007	8.6	25	X		112
7S	15007	7.4	25	X		113
7SB	15207	8.6	25	X		112
700	24700	11.5	50			141
70010	24710	11.6	50			141
701	24701	11.7	25			141
702	24702	17.2	25			141
703	24703	33.8	25			141

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
8	10008	8.0	25	X	X	113
8B	12008	9.0	25	X		112
8S	15008	8.0	25	X		113
8SB	15208	9.0	25	X		112
9	10009	7.2	10	X	X	113
9B	12009	8.4	10	X		112
9S	15009	7.2	10	X		113
9SB	15209	8.4	10	X		112
9408	84408	2.2	100			176
9408S	86508	2.2	100			176
9410	84410	2.7	100			176
9410A	88410	1.0	100			176
9410S	86510	2.5	100			176
9412	84411	3.0	100			176
9412S	86512	2.8	100			176
9816	84420	9.0	50			176
9816S	86524	1.3	25			176

ALPHA-NUMERIC - A

A0600	26600	17.4	100			142
A0600B	26630	19.6	100			142
A1600	26601	19.4	100			142
A1600B	26631	22.1	100			142
A2-1/2 600	26625	21.6	100			142
A2-1/2 600B	26636	24.3	100			142
A2600	26602	19.6	100			142
A2600B	26632	22.3	100			142
A3600	26603	22.4	100			142
A3600B	26633	25.1	100			142
A4600	26604	14.6	50			142
A4600B	26634	16.1	50			142
A5600	26605	16.6	50			142
A5600B	26635	18.1	50			142
ABC25	59125	4.4	100			82
ABC25PCTF	83902	4.8	100			104
APS	18800	2.7	100	X		54
APS100	18880	6.4	100			55
APS50	18850	4.2	100			55
APS75	18875	5.9	100			55
APSKC1	18891	7.2	100	X		55
APSKC1234	18890	6.2	100	X		55
APSPCTF	83901	3.3	100			103

ALPHA-NUMERIC - B

BA	83650	3.8	100	X		182
BA50	83450	4.8	100			86
BA75	83475	5.0	100			86
BAKC1234	83434	5.3	100	X		86
BAKC38	84548	5.0	100	X		86
BAR	30030	14.0	50			149
BBC	30025	1.8	100	X		106
BC18	18200	5.0	100	X		70
BC18100	18300	8.6	100			58
BC1850	18250	7.7	100			58
BC1875	18275	8.1	100			58
BC18KC1	18611	9.0	100	X		59
BC18KC112	18613	10.5	100	X		59
BC18KC114	18612	10.3	100	X		59

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
BC18KC1234	18600	8.7	100	X		59
BC18KC2	18614	11.4	100	X		59
BC18KC38	18610	8.1	100	X		59
BC18M	89200	5.0	100			*
BC18ST	18203	5.9	100	X		70
BC516	18201	9.4	100	X		70
BC516100	18400	9.4	100			58
BC51650	18350	8.4	100			58
BC51675	18375	8.9	100			58
BC516KC1	18621	9.9	100	X		59
BC516KC112	18623	11.4	100	X		59
BC516KC114	18622	11.2	100	X		59
BC516KC1234	18601	9.0	100	X		59
BC516KC2	18624	12.3	100	X		59
BC516KC38	18620	9.2	100	X		59
BC516M	89201	5.5	100			*
BC516ST	18204	6.3	100	X		70
BC916	18202	6.4	100	X		70
BC916100	18500	10.3	100			58
BC91650	18450	9.4	100			58
BC91675	18475	9.6	100			58
BC916KC1	18631	10.8	100	X		59
BC916KC112	18633	12.3	100	X		59
BC916KC114	18632	12.1	100	X		59
BC916KC1234	18602	9.8	100	X		59
BC916KC2	18634	13.2	100	X		59
BC916KC38	18630	9.8	100	X		59
BC916M	89202	6.4	100			*
BC916ST	18205	7.5	100	X		70
BJNP	84310	6.3	100			171
BJNPH	84311	6.3	100			171
BJNPWO	84301	6.5	100			171
BJW4	80034	6.0	50 pr			183
BJW6	80036	5.2	50 pr			183
BMB16	31000	16.5	50	X		148
BMB16D	31001	16.8	50	X		148
BMB24	31002	17.2	50	X		148
BMB24D	31003	17.4	50	X		148
BO	83655	3.8	100	X		182
BRS15	38215	2.3	100	X		168
BRS2	38200	2.3	100	X		168
BS	30050	4.0	100	X		152
BS18	30005	22.0	50	X		151
BSC	30055	2.3	100	X		106
BST	84320	7.5	100			155
BXC	30022	1.8	100	X		87

ALPHA-NUMERIC - C

C6	85000	2.5	100			137
CBS18HIC100	85100	8.2	25			133
CBS18HIC10018	85119	8.3	25			147
CBS18HIC100516	85116	10.8	25			147
CBS18HIC100APS	85120	9.2	25			135
CBS18HIC100ST	85130	8.4	25			133
CBS18HIC50	85500	8.2	25			133
CBS18HIC5018	85518	8.3	25			147
CBS18HIC50516	85516	8.3	25			147
CBS18HIC50APS	85520	8.7	25			135
CBS18HIC50ST	85530	8.3	25			133

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL CSA	Page No.
CBS18HIC75	85700	8.2	25		133
CBS18HIC7518	85718	8.3	25		147
CBS18HIC75516	85716	8.3	25		147
CBS18HIC75APS	85720	8.9	25		135
CBS18HIC75ST	85730	8.3	25		133
CBS18KC1	85200	8.6	25		132
CBS18KC118	85218	10.8	25		146
CBS18KC1234	85234	8.3	25		133
CBS18KC123418	85238	8.3	25		146
CBS18KC1234516	85236	10.8	25		146
CBS18KC1234APS	85220	9.0	25		134
CBS18KC1234ST	85230	8.5	25		132
CBS18KC1516	85416	10.8	25		146
CBS18KC1APS	85420	9.3	25		134
CBS18KC1ST	85430	8.8	25		132
CBS18KC38	85338	8.1	25		132
CBS18KC3818	85318	8.3	25		146
CBS18KC38516	85316	10.8	25		146
CBS18KC38APS	85320	8.8	25		134
CBS18KC38ST	85330	8.3	25		132

ALPHA-NUMERIC - D thru G

DLS1	41219	1.1	100	X	154
DR20	73020	3.2	50		172
DR30	73030	2.2	25		172
DR40	73040	1.2	10		172
DWC1	80030	6.8	50		162
F15XR	83815	2.5	100	X	57
F2A	83821	0.8	100	X	56
F2B	83822	0.9	100	X	56
F2C	83823	0.9	100	X	56
F2D	83824	1.0	100	X	56
F2E	83825	1.2	100	X	56
F2F	83826	1.3	100	X	56
F2G	83827	1.6	100	X	56
F4A	83841	0.8	100	X	56
F4B	83842	0.9	100	X	56
F4C	83843	1.0	100	X	56
F4D	83844	1.3	100	X	56
F4E	83845	1.3	100	X	56
F4F	83846	1.3	100	X	56
F4G	83847	1.6	100	X	56
F8A	83881	0.9	100	X	56
F8B	83882	1.0	100	X	56
F8C	83883	1.0	100	X	56
F8D	83884	1.1	100	X	56
F8E	83885	1.2	100	X	56
F8F	83886	1.4	100	X	56
F8G	83887	1.7	100	X	56
FBO23	84590	15.8	100		153
FBO234	84580	21.0	100		153
FBO6	84585	23.8	100		153
FH116	83550	2.2	100	X	83
FH532	83555	2.4	100	X	83
FS1	80051	2.0	100	X	52, 53
FS2	80052	2.5	100	X	53
FS3	80053	2.8	100		53
FS4	80054	3.0	100		53

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
FSBX	80060	1.2	100		X	52
FT	80065	2.0	100			96
G100	95100	2.1	100			169
GH3	76100	4.3	1000			139
GWC1	76101	11.0	1000			138

ALPHA-NUMERIC - H

H12	60012	8.8	100			128
H14	60014	10.4	100			128
H16	60016	12.6	100			128
H16A	63016	12.6	100			128
H30	60030	7.2	100		X	120
H40	60040	8.0	100		X	120
H45	60045	8.0	100		X	120
H50	60050	9.0	100			120
H50A	63050	3.8	100			*
H55	60055	10.2	100		X	120
H60	60060	11.8	100		X	120
H65	60065	15.6	100		X	120
H70	60070	16.0	100		X	120
H75	60075	9.2	50		X	120
H80	60080	12.6	50		X	120
H85	60085	15.0	50		X	120
H90	60090	10.6	25		X	120
H92	60092	13.8	25		X	120
H94	60094	6.8	10		X	120
H95	90095	9.6	10		X	120
H96	60096	10.8	10		X	120
H97	60097	16.4	10		X	120
H98	60098	19.0	10		X	120
HD260	70260	8.6	100		X	126
HD270	70270	13.2	100		X	126
HD280	70280	9.0	50		X	126
HD290	70290	6.8	25		X	126
HD292	70292	8.0	25		X	126
HD294	70294	5.1	10		X	126
HD295	70295	9.2	10		X	126
HD296	70296	10.0	10		X	126
HD297	70297	16.4	10		X	126
HD298	70298	18.8	10		X	126
HIC100	17100	2.8	100			48
HIC100100	18705	7.1	100			50
HIC100T	18100	2.8	100			48
HIC50	17050	2.3	100			48
HIC50100	18702	6.6	100			50
HIC5050	18700	5.3	100			50
HIC5075	18701	5.5	100			50
HIC50T	18050	2.3	100			48
HIC75	17075	2.4	100			48
HIC75100	18704	6.6	100			50
HIC7575	18703	5.7	100			50
HIC75T	18075	2.4	100			48

ALPHA-NUMERIC - J

J200	41200	18.5	50			165
J200500	41250	21.4	50			165
J200600	41260	25.4	50			165
J200ABC25	41525	20.7	50			165
J200APS	41201	20.0	50			165

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
J200B	41220	20.3	50			165
J200B500	41750	23.2	50			165
J200B600	41760	27.2	50			165
J200BBC18	41418	22.9	50			165
J200BBC516	41451	23.3	50			165
J200BBC916	41491	23.7	50			165
J200SFC18	41318	20.3	50			165
J200SFC516	41351	20.4	50			165
J200SFC916	41391	20.7	50			165
J200VBC25	41625	20.7	50			165
JC12100	30010	9.2	100 ft			178

ALPHA-NUMERIC - K thru L

K0B	11000	5.2	100			114
K1B	11001	6.7	100			114
K2B	11002	7.2	100			114
K30	11030	2.3	100			116
K45	11045	2.7	100			116
K55	11055	4.4	100			116
KC1	17104	3.9	100	X		49
KC112	17106	5.0	100	X		49
KC112KC1	17304	8.8	100	X		50
KC112T	17111	5.0	100	X		49
KC114	17105	4.8	100	X		49
KC114KC1	17303	8.8	100	X		50
KC114T	17100	4.8	100	X		49
KC1234	17101	2.9	100	X		49
KC1234KC1	17301	7.5	100	X		50
KC1234KC1234	17306	6.9	100	X		50
KC1234T	17102	2.9	100	X		49
KC1KC1	17302	8.1	100	X		50
KC1T	17109	3.9	100	X		49
KC2	17107	6.1	100	X		49
KC2KC1	17305	10.0	100	X		50
KC2T	17112	6.1	100	X		49
KC38	17103	2.8	100	X		49
KC38KC1	17300	7.5	100	X		50
KC38T	17108	2.8	100	X		49

LSBAR	30045	17.0	25			159
-------	-------	------	----	--	--	-----

ALPHA-NUMERIC - M

MO	22000	5.2	100			*
MED12	56012	5.2	100	X		128
MED12A	56012	5.9	100			128
MED13	56013	6.4	100	X		128
MED13A	56213	6.4	100			128
MED14	56014	10.2	100	X		128
MED16	56016	14.0	100	X		128
MED2	56002	1.1	100	X		128
MED3	56003	1.3	100			128
MED30	56130	5.0	100	X		119
MED30RS	57130	6.0	100			118
MED30SS	55130	5.0	100			119
MED40	56140	5.4	100	X		119
MED40SS	55140	5.4	100			119
MED45	56145	5.6	100			119
MED45RS	57145	6.6	100			118

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
MED45SS	55145	5.6	100			119
MED5	56005	3.5	100	X		128
MED50	56150	7.0	100	X		119
MED50SS	55150	7.8	100	X		119
MED55	56155	7.8	100			119
MED55RS	57155	8.8	100			118
MED55SS	55155	7.0	100			119
MED60	56160	8.4	100	X		119
MED60SS	55160	8.4	100			119
MED65	56150	12.2	100	X		119
MED7	56165	5.1	100	X		128
MED70	56170	12.0	100	X		119
MED70SS	55170	12.0	100			119
MED75	56175	7.4	50	X		119
MED80	56180	9.6	50	X		119
MED80SS	55180	9.6	50			119
MED85	56185	10.8	50	X		119
MED9	56009	5.0	100	X		128
MED90	56190	15.0	50	X		119
MED90SS	55190	15.0	50			119
MINE28	64028	2.6	100			118
MINE30	64030	3.0	100			118
MINE40	64040	5.2	100			118
MINE45	64045	3.5	100			118
MINE50	64050	6.4	100			118
MINE55	64055	6.8	100			118

ALPHA-NUMERIC - N

NB100	84200	7.0	100			62
NB50	84150	6.1	100			62
NB75	84175	6.2	100			62
NBKC1234	84110	7.0	100			62
NP12	84312	14.7	50			171
NP18	84318	23.4	50			171
NP18FHA	84380	28.1	25			171
NP3	84303	6.6	100			171
NP6	84306	6.7	50			171
NP6M	84360	6.7	50			171
NP6P	84366	6.7	50			171
NP6ST	83262	18.6	50			171
NP6STW	84363	9.6	50			171
NP8	84308	17.5	25			171
NS100	51100	2.3	100			136
NS50	51050	1.8	100			136
NS75	51075	1.8	100			136

ALPHA-NUMERIC - O thru P

OR	83007	2.0	100			156
P	59001	2.8	100	X		77
P100	59012	3.6	100			80
P50	59009	5.7	100			80
P75	59010	5.8	100			80
PBA	84301	5.7	100			182
PCTF	83900	0.7	100	X		102
PH	59000	2.8	100	X		77
PH14	59002	4.6	100	X		79
PH1438N	59006	5.9	100	X		78
PH14T	59004	5.9	100	X		78
PH38	59003	4.8	100	X		79

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
PH38T	59005	5.9	100	X		78
PKC1	59011	7.0	100	X		81
PKC114	59013	4.3	100	X		81
PKC1234	59008	6.2	100	X		81
PKC38	59007	6.2	100			81
PN14	80080	0.5	100			107
PN38	80085	0.5	100			107
PN8	80075	0.5	100			107
PS	83500	1.8	100	X		109
PS100	69100	0.4	25			173
PS125	69125	0.5	25			173
PS150	69150	0.7	25			173
PS200	69200	0.9	25			173
PS250	69250	1.7	25			173
PS300	69300	1.1	10			173
PS400	69400	1.8	10			173
PS50	69050	0.5	50			173
PS75	69075	0.6	50			173
PSF18	83510	5.3	100	X		68
PSF18R	83636	6.9	100	X		68
PSF516	83515	5.9	100	X		68
PSF516R	83540	7.5	100	X		68
PSF916	83520	8.5	100	X		68
PSF916R	83545	8.5	100	X		68
PSR	83530	3.5	100	X		109

ALPHA-NUMERIC - R

R14	83615	2.2	100	X		108
R1438N	83660	2.8	100	X		108
R14T	83714	2.8	100	X		108
R14TM	84320	2.8	100	X		108
R1814	84500	5.8	100	X		66
R181438N	84565	6.5	100	X		67
R1814T	84535	6.5	100	X		67
R1838	84520	5.6	100	X		66
R1838T	84550	6.9	100	X		67
R38	83638	2.2	100	X		109
R38T	83738	2.8	100	X		109
R38TM	89738	2.8	100			109
R51614	84510	6.3	100	X		66
R5161438N	84570	6.9	100	X		67
R51614T	84540	7.1	100	X		67
R51638	84525	6.0	100	X		66
R51638T	84555	6.9	100	X		66
R91614	84515	7.3	100	X		66
R9161438N	84575	7.9	100	X		66
R91614T	84545	8.1	100	X		66
R91638	84530	7.0	100	X		66
R91638T	84560	7.9	100	X		66
RA14	84055	6.4	100	X		64
RA1438N	84075	7.0	100	X		64
RA14T	84065	7.2	100	X		64
RA38	84060	6.1	100	X		64
RA38T	84070	7.0	100	X		64
RBAR	30035	15.0	50			149
RF11614	84000	5.0	100			84
RF1161438N	84045	5.6	100			85
RF11614T	84025	5.6	100			85
RF11638	84015	4.7	100			84

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
RF11638T	84035	5.6	100			85
RF53214	84010	5.0	100			84
RF5321438N	84050	5.6	100			85
RF53214T	84030	5.6	100			85
RF53238	84020	5.6	100			84
RF53238T	84040	5.6	100			85
RNS100	52100	11.0	100			136
RNS50	52050	6.6	100			136
RNS75	52075	9.0	100			136
RO14	84080	6.4	100	X		65
RO1438N	84100	7.0	100	X		65
RO14T	84090	7.2	100	X		65
RO38	84085	6.1	100	X		65
RO38T	84095	7.8	100	X		65
RS100	84300	7.8	100			63
RS50	84250	6.9	100			63
RS75	84275	7.1	100			63
RSKC1234	84210	7.8	100			63

ALPHA-NUMERIC - S

S	83205	5.8	100	X		93
S1900	80095	5.6	100	X		92
SB100	83100	9.2	100			94
SB12	83212	9.5	100	X		93
SB14	83214	9.3	100	X		93
SB34	83234	9.5	100	X		93
SB38	83238	9.5	100	X		93
SB50	83150	8.2	100			94
SB58	83258	9.5	100	X		93
SB75	83175	8.8	100			94
SBC	83200	9.5	100	X		93
SBKC1	83115	10.1	100	X		94
SBKC114	83120	10.7	100	X		94
SBKC1234	83110	9.2	100	X		94
SBKC38	83105	9.2	100	X		94
SBO	83210	9.5	100	X		93
SBS	83000	3.3	100	X		95
SBS2.5	83002	4.9	100	X		95
SBS3.5	83003	5.0	100	X		95
SBS4	83004	5.0	100	X		95
SBS6	83325	2.8	100	X		95
SBX	83325	2.8	100	X		88
SCH48	80048	4.8	100			160
SCT2	80013	8.4	100			181
SCT3	80014	5.5	100			97
SCX1W	80099	5.4	50			161
SCX1XL	80023	5.5	50			161
SFC18	19000	3.0	100	X		76
SFC18100	19012	6.6	100			60
SFC1850	19010	5.7	100			60
SFC1875	19011	6.1	100			60
SFC18KC1	19042	7.0	100	X		61
SFC18KC112	19044	8.5	100	X		61
SFC18KC114	19043	8.3	100	X		61
SFC18KC1234	19041	6.7	100	X		61
SFC18KC2	19045	9.4	100	X		61
SFC18KC38	19040	6.1	100	X		61
SFC18PCTF	83918	3.8	100			105
SFC516	19001	3.3	100	X		76

Catalog Number	NAED # 784610-	LBS/ Pkg	Std Pkg	UL/ cUL	CSA	Page No.
SFC516100	19022	7.2	100			60
SFC51650	19020	6.3	100			60
SFC51675	19021	6.7	100			60
SFC516KC1	19052	7.7	100	X		61
SFC516KC112	19054	9.2	100	X		61
SFC516KC114	19053	9.3	100	X		61
SFC516KC1234	19051	6.8	100	X		61
SFC516KC2	19055	10.1	100	X		61
SFC516KC38	19050	7.0	100	X		61
SFC516PCTF	83951	4.5	100			105
SFC916	84600	5.3	100	X		76
SFC916100	84615	8.2	100			60
SFC91650	84605	7.3	100			60
SFC91675	84610	7.7	100			60
SFC916KC1	84630	8.7	100	X		61
SFC916KC112	84640	10.4	100	X		61
SFC916KC114	84635	10.0	100	X		61
SFC916KC1234	84625	7.8	100	X		61
SFC916KC2	84645	11.2	100	X		61
SFC916KC38	84620	8.0	100	X		61
SFC916PCTF	83991	4.9	100			105
SH212	30015	0.5	50			89
SRING	80090	5.8	100	X		88
SROM	83320	2.8	100	X		88
SS	83300	3.4	100	X		91
SS100	83380	6.9	100			90
SS50	83350	5.9	100			90
SS75	83375	6.5	100			90
SSKC1	83340	7.8	100	X		90
SSKC1234	83335	639	100	X		90
ALPHA-NUMERIC - T						
TB	82000	4.1	100			98
TB100	82203	7.7	100			99
TB50	82201	6.8	100			99
TB75	82202	7.2	100			99
TBAR	30040	17.0	50			158
TBKC1	82103	8.0	100			99
TBKC1234	82102	7.6	100			99
TBKC38	82101	7.2	100			99
TBT	82001	4.1	100			98
TS	81000	4.8	100			98
TS100	81203	7.5	100			100
TS50	81201	6.8	100			100
TS75	81202	7.0	100			100
TSKC1	81103	8.6	100			100
TSKC1234	81102	7.6	100			100
TSKC38	81101	7.2	100			100
TST	81001	4.0	100			98
ALPHA-NUMERIC - U thru W						
UFMB16	84716	9.3	25	X		150, 175
UFMB24	84724	13.2	25	X		150, 175
UN14	80070	0.4	100			107
VBC25	59126	4.4	100			82
VBC25PCTF	83925	4.8	100			104
WBF1	84350	5.6	100			174

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Shpr	Unit Pkg	Std Shpr	Page No.
METAL STAPLES					
I10A	99726	55.1	100/Box	10,000	188
I10C	99727	54.1	500/Box	10,000	188
I10G	99728	17.0	500/Jar	3,000	188
I10M	99729	25.9	5M/Keg	5,000	188
I10N	99730	50.9	10M/Keg	10,000	188
I10R	99731	26.1	5M/Pail	5,000	188
I10T	99732	51.6	10M/Pail	10,000	188
I10HA	99733	66.5	100/Box	10,000	188
I10HC	99734	64.7	500/Box	10,000	188
I10HG	99735	18.2	500/Jar	3,000	188
I10HM	99736	27.9	5M/Keg	5,000	188
I10HN	99737	54.8	10M/Keg	10,000	188
I10HR	99738	28.1	5M/Pail	5,000	188
I10HT	99739	55.6	10M/Pail	10,000	188
I10HFA	99740	66.5	100/Box	10,000	188
I10HFC	99741	64.7	500/Box	10,000	188
I10HFG	99742	17.0	500/Jar	3,000	188
I10HFM	99743	27.9	5M/Keg	5,000	188
I10HFN	99744	54.8	10M/Keg	10,000	188
I10HFR	99745	28.1	5M/Pail	5,000	188
I10HFT	99746	55.6	10M/Pail	10,000	188
I10ZA	99771	56.1	100/Box	10,000	190
I10ZC	99772	54.1	500/Box	10,000	190
I10ZM	99773	25.9	5M/Keg	5,000	190
I10ZN	99774	50.9	10M/Keg	10,000	190
I10ZR	99775	26.1	5M/Pail	5,000	190
I10ZT	99776	51.6	10M/Pail	10,000	190
I12A	99747	42.4	100/Box	5,000	189
I12B	99748	39.7	250/Box	5,000	189
I12C	99749	38.1	500/Box	5,000	189
I12G	99750	23.0	500/Jar	3,000	189
I12M	99751	36.7	5M/Keg	5,000	189
I12R	99752	37.0	5M/Pail	5,000	189
I12S	99753	56.1	75C/Pail	7,500	189
I12FA	99754	42.4	100/Box	5,000	189
I12FB	99755	39.7	250/Box	5,000	189
I12FC	99756	38.1	500/Box	5,000	189
I12FG	99757	23.0	500/Jar	3,000	189
I12FM	99758	36.7	5M/Keg	5,000	189
I12FR	99759	37.0	5M/Pail	5,000	189
I12ZA	99777	42.4	100/Box	5,000	190
I12ZB	99778	39.7	250/Box	5,000	190
I12ZC	99779	38.1	500/Box	5,000	190
I12ZM	99780	36.7	5M/Keg	5,000	190
I12ZR	99781	37.0	5M/Pail	5,000	190
I12ZS	99782	56.1	75C/Pail	7,500	190
I13A	99760	23.0	100/Box	2,000	189
I13R	99761	53.0	5M/Pail	5,000	189
I13ZA	99783	23.0	100/Box	2,000	190

Catalog Number	NAED # 784610-	LBS/ Shpr	Unit Pkg	Std Shpr	Page No.
I13ZR	99784	53.0	5M/Pail	5,000	190
I15A	99762	27.5	100/Box	2,000	189
I15Q	99763	52.0	4M/Pail	4,000	189
I15ZA	99785	27.5	100/Box	2,000	191
I15ZQ	99786	52.0	4M/Pail	4,000	191
IPVC1HA	99809	28.0	100/Box	5,000	197
IPVC1HC	99809	27.8	500/Box	5,000	197
IPVC1HF	99810	12.0	350/Jar	2,100	197
IPVC1HR	99811	28.2	5M/Pail	5,000	197
IPVC2A	99813	37.5	100/Box	5,000	197
IPVC2C	99814	36.2	500/Box	5,000	197
IPVC2F	99815	14.9	350/Jar	2,100	197
IPVC2R	99816	35.0	5M/Pail	5,000	197
IPN1A	99789	27.0	100/Box	5,000	196
IPN1C	99790	26.8	500/Box	5,000	196
IPN1E	99791	7.5	200/Jar	1,200	196
IPN1R	99792	30.0	5M/Pail	5,000	196
IPN1HA	99793	28.0	100/Box	5,000	196
IPN1HC	99794	27.8	500/Box	5,000	196
IPN1HE	99795	7.9	200/Jar	1,200	196
IPN1HR	99796	28.0	5M/Pail	5,000	196
IPNH1HFA	99797	28.0	100/Box	5,000	196
IPNH1HFC	99798	27.8	500/Box	5,000	196
IPNH1HFE	99799	7.9	200/Jar	1,200	196
IPNH1HFR	99800	28.0	5M/Pail	5,000	196
IPN2A	99801	36.0	100/Box	5,000	196
IPN2C	99802	35.5	500/Box	5,000	196
IPN2E	99803	8.7	200/Jar	1,200	196
IPN2R	99804	36.0	5M/Pail	5,000	196
IPN2FA	99805	36.0	100/Box	5,000	196
IPN2FC	99806	35.5	500/Box	5,000	196
IPN2FE	99807	8.7	200/Jar	1,200	196
IPN2FR	99808	36.0	5M/Pail	5,000	196
ISE13A	99766	29.0	100/Box	2,000	192
ISE13ZA	99787	29.0	100/Box	2,000	193
ISE14A	99767	34.9	100/Box	2,000	98
ISE14ZA	99788	34.9	100/Box	2,000	98
I17A	99764	21.0	100/Box	2,000	191
I17R	99765	46.8	5M/Pail	5,000	191

Index by Catalog Part Number

Catalog Number	NAED # 784610-	LBS/ Shpr	Unit Pkg	Std Shpr	Page No.
-------------------	-------------------	--------------	-------------	-------------	-------------

METAL STAPLES (Con't)

ISE18U	99768	13.5	50/Box	1,000	192
ISE22U	99769	13.7	50/Box	1,000	192
ISE23U	99770	15.6	50/Box	1,000	192
IUS1025C	96902	2.5	500/Box	500	194
IUS1218C	96921	50.0	50 LBS	50 LBS	194
IUS1225C	96922	3.0	500/Box	500	194
IUS1531I	96953	6.0	500/Box	500	194
IUS2050Q	96905	2.2	100/Box	100	194
IUS2063Q	96906	2.5	100/Box	100	194
IUS3090W	96909	8.0	100/Box	100	194

PLASTIC STAPLES

I242B	99885	3.4	100/Box	1,000	204
I242BC	99907	3.8	100/Box	1,000	205
I242BP	99855	7.0	100/Box	1,000	206
I242BS	99865	9.0	100/Box	1,000	207
I242W	99886	3.4	100/Box	1,000	204
I242WC	99908	3.8	100/Box	1,000	205
I242WP	99856	7.0	100/Box	1,000	206
I242WS	99866	9.0	100/Box	1,000	207
I25DB	99893	5.0	100/Box	1,000	204
I25DBC	99915	5.3	100/Box	1,000	205
I25DW	99894	5.0	100/Box	1,000	204
I25DWC	99916	5.0	100/Box	1,000	205
I275B	99887	3.4	100/Box	1,000	204
I275BC	99909	3.8	100/Box	1,000	205
I275BP	99856	7.0	100/Box	1,000	206
I275BS	99867	9.0	100/Box	1,000	207
I275W	99888	3.4	100/Box	1,000	204
I275WC	99910	3.8	100/Box	1,000	205
I275WP	99858	7.0	100/Box	1,000	206
I275WS	99868	9.0	100/Box	1,000	207
I300B	99889	3.5	100/Box	1,000	204
I300BC	99911	3.8	100/Box	1,000	205
I300BP	99859	7.0	100/Box	1,000	206
I300BS	99869	9.0	100/Box	1,000	207
I300W	99890	3.5	100/Box	1,000	204
I300WC	99912	3.8	100/Box	1,000	205
I300WP	99860	7.0	100/Box	1,000	206
I300WS	99870	9.0	100/Box	1,000	207
I305DB	99895	5.0	100/Box	1,000	204

Catalog Number	NAED # 784610-	LBS/ Shpr	Unit Pkg	Std Shpr	Page No.
PLASTIC STAPLES (Con't)					
I305DBC	99917	5.4	100/Box	1,000	205
I305DBP	99863	5.5	50/Box	500	206
I305DBS	99873	6.0	50/Box	500	207
I305DW	99896	5.0	100/Box	1,000	204
I305DWC	99918	5.4	100/Box	1,000	205
I305DWP	99864	5.5	50/Box	500	206
I305DWS	99874	6.0	50/Box	500	207
I395B	99891	6.0	100/Box	1,000	204
I395BC	99913	6.3	100/Box	1,000	205
I395BP	99861	7.0	100/Box	1,000	206
I395BS	99871	9.0	100/Box	1,000	207
I395W	99892	6.0	100/Box	1,000	204
I395WC	99914	6.3	100/Box	1,000	205
I395WP	99862	7.0	100/Box	1,000	206
I395WS	99872	9.0	100/Box	1,000	207
IAM375	99850	3.3	50/Box	500	209
IAM50	99851	4.5	50/Box	500	209
IBT251B	99919	2.0	100/Box	1,000	202
IBT251G	99920	2.0	100/Box	1,000	202
IBT251T	99921	2.0	100/Box	1,000	202
IBT251W	99922	2.0	100/Box	1,000	202
IBT252B	99923	2.6	100/Box	1,000	202
IBT252G	99924	2.6	100/Box	1,000	202
IBT252T	99925	2.6	100/Box	1,000	202
IBT252W	99926	2.6	100/Box	1,000	202
IBT312B	99927	3.3	100/Box	1,000	204
IBT312G	99928	3.3	100/Box	1,000	205
IBT312T	99929	3.3	100/Box	1,000	204
IBT312W	99930	3.3	100/Box	1,000	205
ICS12B	99875	1.2	100/Box	1,000	204
ICS12BC	99897	1.5	100/Box	1,000	205
ICS12W	99876	1.2	100/Box	1,000	204
ICS12WC	99898	1.5	100/Box	1,000	205
ICS18B	99877	3.1	100/Box	1,000	204
ICS18BC	99899	3.4	100/Box	1,000	205
ICS18W	99878	3.1	100/Box	1,000	204
ICS18WC	99900	3.4	100/Box	1,000	205
ICS25B	99879	3.2	100/Box	1,000	204
ICS25BC	99901	3.5	100/Box	1,000	205
ICS25W	99880	3.2	100/Box	1,000	204
ICS25WC	99902	3.5	100/Box	1,000	205

Catalog Number	NAED # 784610-	LBS/ Shpr	Unit Pkg	Std Shpr	Page No.
PLASTIC STAPLES (con't)					
IPS502 BX50	97250	4.8	50/Box	500	199
IPS503 BX50	97350	5.2	50/Box	500	199
IPS504 BX50	97450	6.0	50/Box	500	199
IPS50 BX100	97510	6.3	100/Box	1,000	198
IPS50 BX500	90550	13.9	500/Box	2,500	198
IPS50 KB500	99550	12.6	500/Bag	2,500	198
IPS50 KG5M	97555	25.0	5M/Keg	5,000	198
IPS50 PB100	97551	5.3	100/Bag	1,000	198
IPS50 PB500	97505	12.4	500/Bag	2,500	198
IPS50 PL2M	97552	10.6	2M/Pail	2,000	198
IPS75 BX100	97710	5.8	100/Box	1,000	198
IPS75 BX500	90750	14.6	500/Box	2,500	198
IPS75 KB250	99725	17.2	250/Bag	2,500	198
IPS75 KG5M	90755	24.8	5M/Pail	5,000	198
IPS75 PB100	97711	5.5	100/Bag	1,000	198
IPS75 PB500	97705	13.5	500/Bag	2,500	198
IPS75 PL2M	90752	12.7	2M/Pail	2,000	198
ISER10 BX50	97150	16.4	50/Box	1,000	200
ISER20 BX25	97225	11.7	25/Box	500	200
ISER30 BX25	97325	12.0	25/Box	500	200
ISER40 BX10	97410	8.0	10/Box	200	200
ISEU50 BX50	97500	15.7	50/Box	1,000	201
ISEU60 BX50	97650	16.5	50/Box	1,000	201
ISEU70 BX25	97725	12.0	25/Box	500	201
ISEU80 BX25	97825	12.0	25/Box	500	201
ITC12G BX100	95212	3.0	100/Box	1,000	203
ITC12T BX100	95412	3.0	100/Box	1,000	203
ITC25G BX100	95225	3.3	100/Box	1,000	203
ITC25T BX100	95425	3.3	100/Box	1,000	203
ITC42G BX50	95242	3.0	50/Box	500	203
ITC42T BX50	95442	3.0	50/Box	500	203
IUF40 BX50	92240	17.2	50/Box	1,000	210
IWP50 BX100	90150	23.4	100/Box	2,000	212
IWP75 BX25	90175	11.4	25/Box	500	212

NOTE: IPS50 and IPS75 are both UL and CSA listed.

Four Good Reasons to:

Hang with
Minerallac®...

Black Claw™
Spring Steel

Strong, Swift and Efficient



Traditional
M Minerallac®
A Traditional of Quality Since 1894



IMPACT™
STAPLES



*Taking the electrical industry
by storm!*



MasterStrut

Building For Tomorrow



Index by Catalog Part Number

Catalog No. (*Add Finish)	Lbs/ 100 ft	Lbs/ Pkg	Std Pkg (feet)	Page Nos.
------------------------------	----------------	-------------	-------------------	--------------

CHANNEL

M100210*	146	730	500	224, 236
M100220*	146	730	500	224, 236
M1002A10*	292	730	250	225, 241
M1002A20*	292	876	300	225, 241
M1002EH10*	141	705	500	225, 239
M1002EH20*	141	705	500	225, 239
M1002H10*	141	705	500	224, 237
M1002H20*	141	705	500	224, 237
M1002KO10*	141	705	500	225, 240
M1002KO20*	141	705	500	225, 240
M1002S10*	141	705	500	224, 238
M1002S20*	141	705	500	224, 238

M136210*	128	640	500	222, 236
M136220*	128	640	500	222, 236
M1362A10*	256	640	250	223, 241
M1362A20*	256	768	300	223, 241
M1362EH10*	123	615	500	223, 239
M1362EH20*	123	615	500	223, 239
M1362H10*	123	615	500	222, 237
M1362H20*	123	615	500	222, 237
M1362S10*	123	615	500	222, 238
M1362S20*	123	615	500	222, 238

M136410*	97	485	500	220, 236
M136420*	97	485	500	220, 236
M1364A10*	194	485	250	221, 241
M1364A20*	194	582	300	221, 241
M1364EH10*	87	435	500	221, 239
M1364EH20*	87	435	500	221, 239
M1364H10*	87	435	500	220, 237
M1364H20*	87	435	500	220, 237
M1364S10*	87	435	500	220, 238
M1364S20*	87	435	500	220, 238

M138210*	170	850	500	226, 236
M138220*	170	850	500	226, 236
M1382A10*	292	730	250	227, 241
M1382A20*	292	876	250	227, 241
M1382EH10*	165	825	500	227, 239
M1382EH20*	165	825	500	227, 239
M1382H10*	165	825	500	226, 237
M1382H20*	165	825	500	226, 237

Add Material/Finish to part numbers when ordering.

GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		

(NOTE: Gold Dichromate available in 10' lengths only.)

Call Customr Service for NAED numbers. Give part number including length and hole pattern as well as finish.



Catalog Number	Lbs/ 100 ft	Lbs/ Pkg	Std Pkg (feet)	Page Nos.
M1382KO10*	165	825	500	227, 240
M1382KO20*	165	825	500	227, 240
M1382S10*	165	825	500	226, 238
M1382S20*	165	825	500	226, 238
M158210*	178	890	500	230, 236
M158220*	178	890	500	230, 236
M1582A10*	340	850	250	231, 241
M1582A20*	340	1020	300	231, 241
M1582EH10*	173	865	500	231, 239
M1582EH20*	173	865	500	231, 239
M1582H10*	173	865	500	230, 237
M1582H20*	173	865	500	230, 237
M1582KO10*	178	890	500	231, 240
M1582KO20*	178	890	500	231, 240
M1582S10*	173	865	500	230, 238
M1582S20*	173	865	500	230, 238
M158410*	137	685	500	228, 236
M158420*	137	685	500	228, 236
M1584A10*	282	705	250	229, 241
M1584A20*	282	846	300	229, 241
M1584EH10*	137	685	500	229, 239
M1584EH20*	137	685	500	229, 239
M1584H10*	137	685	500	228, 237
M1584H20*	137	685	500	228, 237
M1584KO10*	141	705	500	229, 240
M1584KO20*	141	705	500	229, 240
M1584S10*	137	685	500	228, 238
M1584S20*	137	685	500	228, 238
M276210*	247	988	400	232, 236
M276220*	247	988	400	232, 236
M2762A10*	484	968	200	233, 241
M2762A20*	484	968	200	233, 241
M2762EH10*	242	968	400	233, 239
M2762EH20*	242	968	400	233, 239
M2762H10*	242	968	400	232, 237
M2762H20*	242	968	400	232, 237
M2762KO10*	247	988	400	233, 240
M2762KO20*	247	988	400	233, 240
M2762S10*	242	968	400	232, 238
M2762S20*	242	968	400	232, 238

Add Material/Finish to part numbers when ordering.

GRN	Painted Green	SS4	304 Stainless Steel
PLN	Plain (light oil)	SS6	316 Stainless Steel
PGL	Pre-Galvanized	HDG	Hot Dip Galvanized
GD	Gold Dichromate		

(NOTE: Gold Dichromate available in 10' lengths only.)

Call Customr Service for NAED numbers. Give part number including length and hole pattern as well as finish.

Index by Catalog Part Number

Catalog No. (*Add Finish)	Lbs/ 100 ft	Lbs/ Pkg	Std Pkg (feet)	Page Nos.
------------------------------	----------------	-------------	-------------------	--------------

CHANNEL (con't)

M314210*	290	870	300	234, 236
M314220*	290	1160	400	234, 236
M3142A10*	580	870	150	235, 241
M3142A20*	580	1160	200	235, 241
M3142EH10*	285	855	300	235, 239
M3142EH20*	285	1140	400	235, 239
M3142H10*	285	855	300	234, 237
M3142H20*	285	1140	400	234, 237
M3142KO10*	290	870	300	235, 240
M3142KO20*	290	1160	400	235, 240
M3142S10*	285	855	300	234, 238
M3142S20*	285	1140	400	234, 238

***Add Material/Finish to part numbers when ordering.**

GRN Painted Green **SS4** 304 Stainless Steel

PLN Plain (light oil) **SS6** 316 Stainless Steel

PGL Pre-Galvanized **HDG** Hot Dip Galvanized

GD Gold Dichromate

(NOTE: Gold Dichromate available in 10' lengths only.)

Call Customr Service for NAED numbers. Give part number including length, hole pattern and finish.

Catalog Number	NAED # 784610-	Feet/ Pkg	Lbs/ Pkg	Std Pkg	Page No.
-------------------	-------------------	--------------	-------------	------------	-------------

STRUT FITTINGS

CTR1/2x10EG	23121	120	61.5	12	280
CTR1/2x6EG	23126	72	35.8	12	280
CTR1/4x10EG	23141	500	59.5	50	280
CTR1/4x6EG	23146	300	35.7	50	280
CTR3/8x10EG	23381	250	71.0	25	280
CTR3/8x6EG	23386	150	42.8	25	280

Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
-------------------	-------------------	-------------	------------	-------------

CTRC1/2EG	23012	3.7	50	280
CTRC1/4EG	23014	2.0	100	280
CTRC3/8EG	23038	3.0	100	280
M100025	36302	2.7	25	244
M100031	36303	2.8	25	244
M100037	36304	2.9	25	244
M100050	36305	3.2	25	244
M100062	36306	5.0	10	244
M100075	36307	5.2	10	244
M100087	36308	6.3	10	244
M100100	36310	2.9	10	244
M100112	36311	3.5	10	244
M100125	36312	4.0	10	244



Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
M100137	36313	4.3	10	244
M100150	36315	4.5	10	244
M100162	36316	4.7	10	244
M100175	36317	4.3	10	244
M100200	36320	5.3	10	244
M100212	36321	2.7	5	244
M100225	36322	2.7	5	244
M100251	36325	2.7	5	244
M100262	36326	3.2	5	244
M100300	36330	3.2	5	244
M10112EG	20525	17.0	100	278
M10112GRN	20526	17.0	100	278
M10114EG	20545	15.0	100	278
M10114GRN	20546	15.0	100	278
M10134EG	20535	15.0	100	278
M10134GRN	20536	15.0	100	278
M10138EG	20585	18.0	100	278
M10138GRN	20586	18.0	100	278
M10158EG	20555	8.0	50	278
M10158GRN	20556	8.0	50	278
M101D12EG	20725	17.0	100	279
M101D12GRN	20726	17.0	100	279
M101D14EG	20745	15.0	100	279
M101D14GRN	20746	15.0	100	279
M101D38EG	20785	18.0	100	279
M101D38GRN	20786	18.0	100	279
M1158EG	20158	20.8	25	252
M122EG	20122	17.5	50	254
M122GRN	21122	17.5	50	254
M123EG	20123	12.5	25	254
M123GRN	21123	12.5	25	254
M124EG	20124	19.5	25	254
M124GRN	21124	19.5	25	254
M1314EG	20314	23.0	25	252
M1325EG	20325	12.6	20	253
M133EG	20133	11.6	20	255
M133GRN	21133	11.6	20	255
M134EG	20134	15.6	20	255
M134GRN	21134	15.6	20	255
M144EG	20144	20.0	25	255
M144GRN	21144	200	25	255
M155EG	20155	10.5	10	256
M155GRN	21155	10.5	10	256
M164EG	20164	21.0	20	260
M164GRN	21164	21.0	20	260
M1750EG	20750	10.5	25	250
M17512EG	27512	1.8	50	284
M17514EG	27514	2.4	50	284
M1738EG	27538	2.0	50	284
M200025	36702	3.0	25	245
M200037	36704	3.5	25	245
M200050	36705	5.2	25	245

Index by Catalog Part Number

Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
STRUT FITTINGS (con't)				
M200075	36707	2.9	10	245
M200100	36710	4.1	10	245
M200125	36712	4.5	10	245
M200150	36715	4.9	10	245
M200200	36720	2.8	5	245
M200250	36725	3.0	5	245
M200300	36730	3.9	5	245
M200350	36735	4.9	5	245
M200400	36740	5.5	5	245
M200500	36750	6.5	5	245
M200600	36760	7.0	5	245
M201378EG	28135	15.3	25	270
M201378GRN	28136	15.3	25	270
M201578EG	28155	21.0	25	270
M201578GRN	28156	21.0	25	270
M201778EG	28175	26.8	25	270
M201778GRN	28176	26.8	25	270
M201978EG	28195	32.5	25	270
M201978GRN	28196	32.5	25	270
M202EG	20250	17.5	50	257
M202GRN	20260	17.5	50	257
M203EG	20350	17.5	50	258
M203GRN	20360	17.5	50	258
M204EG	20450	19.5	10	259
M204GRN	20460	19.5	10	259
M205EG	20566	9.4	10	259
M205GRN	20567	9.4	10	259
M206EG	20650	13.4	10	262
M206GRN	20660	13.4	10	262
M212DEG	28725	20.0	50	257
M212DGRN	28726	20.0	50	257
M212EG	21251	17.5	50	257
M212GRN	21260	17.5	50	257
M213EG	21350	17.5	50	258
M213GRN	21360	17.5	50	258
M214EG	21450	19.5	25	259
M214GRN	21460	19.5	25	259
M215EG	21550	9.4	10	260
M215GRN	21560	9.4	10	260
M223EG	28325	29.0	50	258
M223GRN	38326	29.0	50	258
M225EG	28405	20.0	15	260
M225GRN	28406	20.0	15	260
M230EG	28235	10.0	50	270
M230GRN	28236	10.0	50	270
M235EG	28255	13.5	25	270
M235GRN	28256	13.5	25	270
M240EG	28245	15.3	25	270
M240GRN	28246	15.3	25	270
M244EG	20670	14.2	20	256
M244GRN	20680	14.2	20	256



Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
M25012EG	25012	13.0	10	251
M25014EG	25014	10.5	10	251
M25038EG	25038	12.5	10	251
M255EG	28525	10.5	10	255
M255GRN	28526	10.5	10	255
M263EG	28315	17.5	25	261
M263GRN	28316	17.5	25	261
M264EG	28415	26.3	25	261
M264GRN	28416	26.3	25	261
M265EG	26515	15.4	10	261
M265GRN	26516	15.4	10	261
M30245EG	23050	14.5	25	265
M30245GRN	23060	14.5	25	265
M30445EG	30445	10.0	10	264
M30445GRN	30446	10.0	10	264
M31245EG	23150	14.5	25	265
M31245GRN	23160	14.5	25	265
M31445EG	31445	7.8	10	265
M31445GRN	31446	7.8	10	265
M36212EG	36212	19.5	10	250
M36238EG	36238	15.1	10	250
M5136EG	20302	71.0	20	267
M5136GRN	20301	71.0	20	267
M5158EG	20502	88.0	20	267
M5158GRN	20501	88.0	20	267
M6136EG	20312	176.0	10	273
M6136GRN	20311	176.0	10	273
M6158EG	20512	265.0	10	273
M6158GRN	20511	265.0	10	273
M624EG	28425	25.8	25	262
M624GRN	28426	25.8	25	262
M625EG	28545	13.5	10	263
M625GRN	28546	13.5	10	263
M7105EG	20550	21.2	25	263
M7105GRN	20560	21.2	25	263
M7208EG	37250	15.0	10	263
M7208GRN	37260	15.5	10	263
M7210EG	21050	9.1	5	264
M7210GRN	21060	9.1	5	264
M751EG	23830	14.5	50	251
M753EG	37450	22.5	25	252
M803EG	21850	31.4	10	274
M803GRN	21860	31.4	10	274
M803SQEG	21870	31.4	10	274
M803SQGRN	21880	31.4	10	274
M813EG	21950	19.6	5	275
M813GRN	21960	19.6	5	275
M813SQEG	21970	19.6	5	275
M813SQGRN	21980	19.6	5	275
M843EG	23850	20.4	5	275
M843GRN	23860	20.4	5	275
M843SQEG	23870	20.4	5	275

Index by Catalog Part Number

Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
STRUT FITTINGS (con't)				
M843SQGRN	23880	20.4	5	275
MA202EG	28815	19.0	50	266
MA202GRN	28816	19.0	50	266
MA2625EG	28825	10.5	25	266
MA2625GRN	28826	10.5	25	266
MA262EG	28265	19.0	10	268
MA262GRN	28266	19.0	10	268
MA282EG	28285	24.2	10	268
MA282GRN	28286	24.2	10	268
MA326EG	28225	16.5	25	266
MA326GRN	28226	16.5	25	266
MBS587EG	20051	23.5	10	271
MBS587GRN	20052	23.5	10	271
MC7208EG	20850	14.0	10	262
MC7208GRN	20860	14.0	10	262
MC7312EG	20870	23.0	10	264
MC7312GRN	20880	23.0	10	264
MCA158EG	36521	13.0	25 pr	267
MCL12EG	21812	12.3	100	277
MCL14EG	21814	7.5	100	277
MCL34EG	21834	14.1	100	277
MCL38EG	21838	10.2	100	277
MCL58EG	21858	15.8	100	277
MCR12EG	21612	11.9	100	277
MCR14EG	21614	7.1	100	277
MCR38EG	21638	9.9	100	277
MCR58EG	21658	11.0	100	277
MCS12EG	21412	8.8	100	277
MCS14EG	21414	6.9	100	277
MCS38EG	21438	9.6	100	277
MCT12EG	22212	13.5	100	276
MCT14EG	22214	7.5	100	276
MCT38EG	22238	10.0	100	276
MCT516EG	22256	8.8	100	276
MCW12EG	21212	11.9	100	276
MCW14EG	21214	7.1	100	276
MCW38EG	21238	9.9	100	276
MDS750EG	20071	27.3	10	271
MDS750GRN	20072	27.3	10	271
MFW12	77112	2.8	100	285
MFW14	77114	3.3	100	285
MFW38	77138	3.0	100	285
MGH050EG	22005	8.0	100	246
MGH075EG	22075	9.0	100	246
MGH100EG	22010	9.0	100	246
MGH125EG	22012	10.0	100	246
MGH150EG	22015	11.0	100	246
MGH200EG	22020	12.0	100	246
MGH250EG	22025	17.0	50	246
MGH300EG	22030	18.0	50	246
MGH400EG	22040	22.0	25	246



Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
MGH500EG	22050	9.9	10	246
MGH600EG	22060	10.6	10	246
MGH700EG	22070	12.9	10	246
MHH25075	49475	1.5	100	282
MHH25100	49401	1.8	100	282
MHH25125	49425	2.1	100	282
MHH25150	49450	2.4	100	282
MHH37075	48875	3.6	100	282
MHH37100	49801	4.2	100	282
MHH37125	49825	4.9	100	282
MHH37150	49850	5.6	100	282
MHH37200	49802	7.2	100	282
MHH50075	49275	8.1	100	282
MHH50100	48291	9.2	100	282
MHH50125	49225	10.4	100	282
MHH50150	49250	11.6	100	282
MHH50175	49215	13.0	100	282
MHH50200	49202	14.4	100	282
MHN12	87212	3.8	100	284
MHN14	87214	3.5	500	284
MHN34	87234	6.0	50	284
MHN38	87238	8.0	500	284
MHN58	87258	3.7	50	284
MIJ1362EG	31362	5.4	20	273
MIJ1582EG	31582	10.3	20	273
ML203EG	28305	13.8	25	268
ML203GRN	28306	13.8	25	268
ML214EG	28465	20.0	25	269
ML214GRN	28466	20.0	25	269
ML350EG	28435	26.3	25	269
ML350GRN	28436	26.3	25	269
ML541EG	28555	16.0	10	272
ML541GRN	28556	16.0	10	272
MLG541EG	28575	23.0	25	272
MLG541GRN	28576	23.0	25	272
MOD112EG	37112	18.0	100	243
MOD114EG	37114	16.0	100	243
MOD118EG	37118	15.0	100	243
MOD12EG	37012	9.0	100	243
MOD138EG	37138	17.0	100	243
MOD1EG	37100	14.0	100	243
MOD34EG	37034	11.0	100	243
MOD38EG	37038	8.0	100	243
MOD58EG	37058	10.0	100	243
MOD78EG	37078	12.0	100	243
MPC112HDG	37512	23.0	25	249
MPC114HDG	37514	18.0	25	249
MPC12HDG	37505	29.0	50	249
MPC1HDG	37510	35.0	50	249
MPC212HDG	37522	33.8	25	249
MPC2HDG	37520	25.0	25	249
MPC312HDG	37532	19.0	10	249

Index by Catalog Part Number

Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
STRUT FITTINGS (con't)				
MPC34HDG	37575	32.0	50	249
MPC38HDG	37538	16.0	50	249
MPC3HDG	37530	15.5	10	249
MPC4HDG	37540	20.5	10	249
MPEC112HDG	37712	28.8	25	249
MPEC114HDG	37714	22.8	25	249
MPEC12HDG	37705	33.5	50	249
MPEC1HDG	37710	21.3	25	249
MPEC212HDG	37722	18.3	10	249
MPEC2HDG	37720	33.8	25	249
MPEC34HDG	37775	35.5	50	249
MPEC3HDG	37730	23.0	10	249
MPPC112EG	22612	13.5	50	246
MPPC114EG	22614	19.0	50	246
MPPC12EG	22602	14.5	50	246
MPPC1EG	22610	15.5	50	246
MPPC212EG	22622	16.5	25	246
MPPC2EG	22620	11.8	25	246
MPPC312EG	22632	21.8	25	246
MPPC34EG	22604	15.0	50	246
MPPC38EG	22608	13.5	50	246
MPPC3EG	22630	19.5	25	246
MPPC4EG	22640	22.5	25	246
MR203EG	28335	13.8	25	268
MR203GRN	27336	13.8	25	268
MR214EG	27465	20.0	25	269
MR214GRN	27466	20.0	25	269
MR350EG	28445	26.3	25	269
MR350GRN	28446	26.3	25	269
MR541EG	28565	16.0	10	272
MR541GRN	28566	16.0	10	272
MRAC112HDG	37612	29.0	50	248
MRAC114HDG	37614	26.5	50	248
MRAC12HDG	37605	20.0	50	248
MRAC1HDG	37610	24.0	50	248
MRAC212HDG	37622	26.5	25	248
MRAC2HDG	37620	42.5	50	248
MRAC312HDG	37632	32.0	25	248
MRAC34HDG	37675	21.5	50	248
MRAC38HDG	37638	12.5	50	248
MRAC3HDG	37630	27.5	25	248
MRAC4HDG	37640	35.0	25	248
MRG541EG	28585	23.0	10	272
MRG541GRN	28586	23.0	10	272
MRH25075	79475	1.3	100	282
MRH25100	79401	1.6	100	282
MRH25125	79425	1.9	100	282
MRH37100	79801	4.4	100	282
MRH37125	79825	5.0	100	282
MRH37150	79850	5.6	100	282
MS175012	22712	48.0	100	286



Catalog Number	NAED # 784610-	Lbs/ Pkg	Std Pkg	Page No.
MS175015	22815	58.0	100	286
MS17509	22719	33.0	100	286
MSE050EG	20805	11.0	100	243
MSE075EG	20807	12.0	100	243
MSE100EG	20810	15.0	100	243
MSE125EG	20812	18.0	100	243
MSE150EG	20815	14.5	50	243
MSE200EG	20820	16.5	50	243
MSEC1316	20036	2.0	100	281
MSEC158	20058	3.0	100	281
MSG256EG	28925	5.0	20	247
MSG287EG	28928	5.0	20	247
MSG556EG	28955	6.8	20	247
MSG587EG	28958	6.8	20	247
MSH25075	39475	1.7	100	283
MSH31100	39501	2.6	100	283
MSH31125	39525	3.0	100	283
MSH31150	39550	3.4	100	283
MSH37125	39825	5.3	100	283
MSN12	87112	5.8	100	283
MSN14	87114	0.9	100	283
MSN38	87138	2.6	100	283
MSN516	87156	1.6	100	283
MSS050EG	20905	11.0	100	242
MSS075EG	20907	15.0	100	242
MSS100EG	20910	17.0	100	242
MSS125EG	20912	19.0	100	242
MSS150EG	20915	14.5	50	242
MSS200EG	20920	17.0	50	242
MSTP010	21000	12 oz.	1	281
MSU050EG	20000	9.9	100	242
MSU075EG	20001	10.9	100	242
MSU100EG	20002	12.6	100	242
MSU125EG	20003	19.2	100	242
MSU150EG	20004	10.0	50	242
MSU200EG	20005	11.5	50	242
MSU250EG	20006	19.0	50	242
MSU300EG	20007	22.2	50	242
MSU350EG	20008	15.5	25	242
MSU400EG	20009	16.9	25	242
MWF12	77212	3.9	100	286
MWF14	77214	1.4	200	286
MWF34	77234	11.0	100	286
MWF38	77238	1.5	100	286
MWF58	77258	7.7	100	286
MWL12	77312	1.5	100	285
MWL14	77314	0.3	100	285
MWL38	77338	0.7	100	285

Index by Product Name/Use

Product Name	Page No.
Beam	
Assemblies - Rod to Beam	66
Assemblies - Threaded Rod to Beam	67
Clamp (see Clamps)	70
Rod/Wire Assembly	67
Bolts	
Stove	176
Box Support	
Additional	152
Assemblies, Conduit & Box	132-135
Assemblies, Beam Mount (Box & Conduit)	146-147
Box to Stud	92-93
Far Side	154
Stabilizer	153
Support	155
Brackets	
Box Mounting	148, 151
Low Voltage Mounting	174
Metal Deck/Conduit	63
Mounting	182
Nail/Conduit	62
Rod/Wire Support	64-65
Strap (also straps)	109
Universal Front Mount	150, 175
Cable Protection (also Nail Plates)	170-171
Cable Support	
Bridle Rings	166-168
D-Rings	172
J-Hooks (also Hooks)	164-165
Chain	
Jack	178
Channel	
Internal Joiners for Strut (also Fittings)	273
Strut	218-241

Product Name	Page No.
--------------	----------

Clamps

Beam	71
Beam	
Assemblies	66-67, 142-144
Conduit Hanger Assys (also Hangers)	72-75
Flange	76
Malleable	141
Two Piece	145
Universal	140

Beam & Pipe for Strut

Beam	250-253
“C” Clamp	252
Cushion by HydraZorb™	244-245
Grip Hanger	246
Heavy Duty	251
Heavy Duty Wide Mouth	250
Malleable	248-249
O.D. Tubing	243
Parallel	246
Rigid Conduit	242
Swing Gate Hangers	247
Thinwall Conduit	243
U-Bolt	252
Universal	242

Clips

Cable	52
Conduit	48-49, 53
Conduit, Flange Mount Assemblies	58-61
Flexible Conduit/Cable	56
Flexible Conduit/Cable Adaptor	57
Ground Wire	138
Multi-Function	55
Multi-Function Assemblies	54
Multi-Purpose	138, 173
One-Hole Jiffy (also straps)	115-121
One-Hole Duplex Jiffy (also straps)	122-123
Stud Adaptor	181
T-Bar Drop Wire	162
T-Bar Scissor	161

Index by Product Name/Use

Product Name	Page No.
Fasteners	
Box to Bar	106, 149
Box to T-Bar	158
Box to Stud	91, 93
Conduit to Stud	94
Flexible Conduit/Cable	87, 88
Lighting - Troffer	96
Plastic Cable Tie	102-105
Plaster Ring to Stud	89
T-Bar	98-100
Fittings for Strut	
90 Degree	255-261, 266
Angle & Clevis Connectors	263-264, 261
Bracket Support	271
Connectors	262, 266
Corner Connectors	260, 262, 264, 269, 272
Closed Angle	264-265
Column Attachment	267
Flat Plates	254-255
Internal Channel Joiners	283
Open Angle	134
Post Bases	265
Slice Clevis	274-275
U-Support	267
Grommet	
Universal Metal Stud	169
Hangers	
Beam Clamp to Conduit	74-75
Beam Clamp to Conduit Assemblies	72-73
Conduit	112-114
Flange	82-83
Rod	108
Rod to Flange	84-85
Strap	68
Twist-On T-Bar	97
T-Bar, Two Piece	160
"Z" Purlin Assemblies	78-81
"Z" Purlin Flange	82-83
Strap (also Straps)	68

Product Name	Page No.
--------------	----------

Hardware for Strut

Channel Nuts	276-277
End Caps	281
Nuts	283-284
Rod Coupling	280
Safety Anchor Straps	286
Screws	282-283
Square Washers	278-279
Threaded Rod	280
Touch-up Paint	281
Washers	285-286

Hooks

J (also Cable Support)	164-165
S	179

Nail

Plates (cable protection)	170-171
Straps (also Straps and Strapping)	136

Nuts

Push	107
U	107

Protection

Cable (also Nail Plates)	170-171
Safety Anchor Strap (also Hardware)	286

Retainer

Outlet	156
------------------	-----

Staples


Metal

Cable	188-191
Cable, Plastic Insulator	196
Cable, PVC Dipped	196
Cable, Stacking	191
Service Entrance	192-193
Utility	194

Index by Product Name/Use

Product Name	Page No.
Staples (Con't)	
Plastic	
AC/MC	209
Bell & Thermostat	202
Cable	198
Coaxial & Sound	204-207
Data/Com	211
Non-Metallic Sheathed Cable	208
Service Entrance	200-201
Stacking	199
Telephone Cable 1-Nail	203
UF	210
Water Pipe	212
Straps and Strapping	
Bracket (also Brackets)	109
Nail (also Nail)	136
One-Hole, Duplex Jiffy (also Clips)	122-123
One-Hole, Jiffy (also Clips)	115-121
One-Hole, Service Entrance	128-129
Perforated	180
Rod/Wire Bracket (also Brackets)	64-65
Two-Hole Metal	124-126
Two-Hole Plastic	173
Two-Hole, Service Entrance	130-131
Support	
Box to Stud	92
Conduit/Cable	86
Conduit & Box Assemblies	134-135
Conduit & Box Assy, Beam Mount	146-147
Conduit & Box Fastener	132-133
Conduit to Stud	90
Lighting Assembly	159
Plaster Ring to Stud	89
Wire/Cable	137
Trapeze	
Conduit to Conduit Assemblies	50-51
Washers	
Bar Joist	183
Strut (see Hardware)	
Wing Nut	177

New Packaging



Contractor-Friendly Box Design!

New box design features easy reclosable lid. Minerallac's heavy-duty, brightly-colored red, black and white box with new label design, makes parts quickly and easily identifiable.

Minerallac's high-quality products, coupled with this new user-friendly box design, is a winning combination.

Another Minerallac Advantage!

Spring Steel Cross-Reference Caddy® to Black Claw™

Caddy®	Black Claw™	Caddy®	Black Claw™
122	PH	20M58SM	SFC516KC114
123	P	20M912	BC916KC114
350	SS	20M912SM	SFC916KC114
449	BXC	24M	KC112
515	FT	24M24	BC18KC112
708	R14	24M24SM	SFC18KC112
1124TI	PH14T	24M4I	KC112T
1226A	PH38	24M58	BC516KC112
1226T	PH1438N	24M58SM	SFC516KC112
1226TI	PH38T	24M912	BC916KC112
122708	PH14	24M912SM	SFC916KC112
1231SP	P75	2EBN	PN8
12316M	PKC1	32M	KC2
12316P	P100	32M24	BC18KC2
12320M	PKC114	32M24SM	SFC18KC2
1236M	PKC38	32M4I	KC2T
123812M	PKC1234	32M58	BC516KC2
1238P	P50	32M58SM	SFC516KC2
12P	HIC75	32M912	BC916KC2
12P12P	HIC7575	32M912SM	SFC916KC2
12P16P	HIC75100	35012P	SS75
12P24	BC1875	35016M	SSKC1
12P24SM	SFC1875	35016P	SS100
12P4I	HIC75T	350812M	SSKC1234
12P58	BC51675	3508P	SS50
12P58SM	SFC51675	4EBN	PN14
12P912	BC91675	4G16	SCT3
12P912SM	SFC91675	4H24	SFC18
12PATA	TB75	4H58	SFC516
12PATS	TS75	4H912	SFC916
12PF	SB75	4TI	R14T
1616M	KC1KC1	4TI24	R1814T
1620M	KC114KC1	4TI58	R51614T
1624M	KC112KC1	4TI912	R91614T
1632M	KC2KC1	4TIB	RA14T
166M	KC38KC1	4TIO	RO14T
16812M	KC1234KC1	4Z34	APS
16M	KC1	4Z3412P	APS75
16M24	BC18KC1	4Z3416M	APSKC1
16M24SM	SFC18KC1	4Z3416P	APS100
16M41	KC1T	4Z34812M	APSKC1234
16M58	BC516KC1	4Z348P	APS50
16M58SM	SFC516KC1	515A	FT
16M912	BC916KC1	6A	R38
16M912SM	SFC916KC1	6A24	R1838
16MATA	TBKC1	6A58	R51638
16MATS	TSKC1	6A912	R91638
16MF	SBKC1	6AB	RA38
16P	HIC100	6AO	RO38
16P16P	HIC100100	6EBM	PN38
16P24	BC18100	6M	KC38
16P24SM	SFC18100	6M24	BC18KC38
16P4I	HIC100T	6M24SM	SFC18KC38
16P58	BC516100	6M4I	KC38T
16P58SM	SFC516100	6M58	BC516KC38
16P912	BC916100	6M58SM	SFC516KC38
16P912SM	SFC916100	6M912	BC916KC38
16PATA	TB100	6M912SM	SFC916KC38
16PATS	TS100	6MATA	TBKC38
16PF	SB100	6MATS	TSKC38
20M	KC114	6MF	SBKC38
20M24	BC18KC114	6T	R1438N
20M24SM	SFC18KC114	6TA24	R181438N
20M4I	KC114T	6TA58	R5161438N
20M58	BC516KC114	6TA912	R9161438N

Caddy® is a registered trademark of Erico Inc. Black Claw™ is a trademark of Minerallac Co.
See page 338 for Traditional Line and page 340 for Strut Fittings cross-reference to Caddy®.

Caddy®	Black Claw™	Caddy®	Black Claw™
6TB	RA1438N	FB12P	BA75
6TI	R38T	FB6M	BAKC38
6TI24	R1838T	FB812M	BAKC1234
6TI58	R51638T	FB8P	BA50
6TI912	R91638T	K12	FS2
6TIB	RA38T	K16	FS3
6TIO	RO38T	K20	FS4
6TO	RO1438N	K8	FS1
70824	R1814	KX	FSBX
70858	R51614	M24	BC18
708912	R91614	M24S	BC18ST
708AB	RA14	M58	BC516
708AO	RO14	M58S	BC516ST
766A	SBS	M912	BC916
812M	KC1234	M912S	BC916ST
812M24	BC18KC1234	MF250	SB14
812M24SM	SFC18KC1234	MF375	BC38
812M41	KC1234T	MF500	SB12
812M58	BC516KC1234	MF625	SB58
812M58SM	SFC516KC1234	MF750	SB34
812M912	BC916KC1234	MFI	S
812M912SM	SFC916KC1234	MFO	SBO
812MATA	TBKC1234	MFS	SBC
812MATS	TSKC1234	MSF	S1900
812MF	SBKC1234	MSR24	PSF18R
8P	HIC50	MSR58	PSF516R
8P12P	HIC5075	MSR912	PSF916R
8P16P	HIC50100	MSS24	PSF18
8P24	BC1850	MSS58	PSF516
8P24SM	SFC1850	MSS912	PSF916
8P41	HIC50T	SC2A	F2A
8P58	BC51650	SC2B	F2B
8P58SM	SFC51650	SC2C	F2C
8P8P	HIC5050	SC2D	F2D
8P912	BC91650	SC2E	F2E
8P912SM	SFC91650	SC2F	F2F
8PATA	TB50	SC2G	F2G
8PATS	TS50	SC4A	F4A
8PF	SB50	SC4B	F4B
AOL12P	RS75	SC4C	F4C
AOL16P	RS100	SC4D	F4D
AOL8P	RS50	SC4E	F4E
ATA4I	TBT	SC4F	F4F
ATS4I	TST	SC4G	F4G
BC	500	SC8A	F8A
BC12P	50075	SC8B	F8B
BC12PSM	50075B	SC8C	F8C
BC16M	500KC1	SC 8D	F8D
BC16MSM	500KC1B	SC8E	F8E
BC16P	500100	SC8F	F8F
BC16PSM	500100B	SC8G	F8G
BC20M	500KC114	T4	UN14
BC20MSM	500KC114B	VF14	FH116
BC24M	500KC112	VF14	FH532
BC24MSM	500KC112B	VF114TI	RF11614T
BC32M	500KC2	VF114TI	RF53214T
BC32MSM	500KC2B	VF146A	RF11638
BC812M	500KC1234	VF146A	RF53238
BC812MSM	500KC1234B	VF146T	RF1161438N
BC8P	50050	VF146T	RF5321438N
BC8PSM	50050B	VF146TI	RF11638T
BHC	BBC	VF146TI	RF53238T
CNB12P	NB75	VF14708	RF11614
CNB812M	NBKC1234	VF14708	RF53214
CNB8P	NB50		

Caddy® is a registered trademark of Erico Inc. Black Claw™ is a trademark of Minerallac Co.
See page 338 for Traditional Line and page 340 for Strut Fittings cross-reference to Caddy®.

Spring Steel Cross-Reference B-Line® to Black Claw™

B-Line®	Black Claw™	B-Line®	Black Claw™
BA15	FT	BG244T	KC112T
BA416	SCT3	BG24C1	500KC112B
BA54T	TST	BG24C2	500KC112
BA64T	TBT	BG24E24	SFC18KC112
BB1	SS	BG24E58	SFC516KC112
BB27	BBC	BG24E912	SFC916KC112
BB510	SB58	BG24U24	BC18KC112
BB512	SB34	BG24U58	BC516KC112
BB54	SB14	BG24U912	BC916KC112
BB56	SB38	BG32	KC2
BB58	SB12	BG24T	KC2T
BB6	S	BG32C1	500KC2B
BB6A	SBC	BG32C2	500KC2
BB7	SBS	BG32E24	SFC18KC2
BB9	S1900	BG32E58	SFC516KC2
BC1	500	BG32E912	SFC916KC2
BE24	SFC18	BG32U24	BC18KC2
BE24CT2	SFC18PCTF	BG32U58	BC516KC2
BE58	SFC516	BG32U912	BC916KC2
BE58CT2	SFC516PCTF	BG64T	KC38T
BE912	SF916	BG6	KC38
BE912CT2	SFC916PCTF	BG6A5	TSKC38
BF1	FH116	BG6A6	TBKC38
BF1CT2	VBC25PCTF	BG6B5	SBKC38
BF12	PH	BG6E24	SFC18KC38
BF13	P	BG6E58	SFC516KC38
BF140	SBS2.5	BG6E912	SFC916KC38
BF156	SBS3.5	BG6F13	PKC38
BF164	SBS4	BG6H7	BAKC38
BF196	SBS6	BG6U24	BC18KC38
BF2	FH532	BG6U58	BC516KC38
BF2CT2	VBC25PCTF	BG6U912	BC916KC38
BG16	KC1	BG812	KC1234
BG164T	KC1T	BG8124T	KC1234T
BG16A5	TSKC1	BG812A5	TSKC1234
BG16A6	TBKC1	BG812A6	TBKC1234
BG16B1	SSKC1	BG812B1	SSKC1234
BG16B5	SBKC1	BG812B5	SBKC1234
BG16C1	500KC1B	BG812C1	500KC1234B
BG16C2	500KC1	BG812C2	500KC1234
BG16E24	SFC18KC1	BG812D3	NBKC1234
BG16E58	SFC516KC1	BG812E24	SFC18KC1234
BG16E912	SFC916KC1	BG812E58	SFC516KC1234
BG16F13	PKC1	BG812E912	SFC916KC1234
BG16G16	KC1KC1	BG812F13	PKC1234
BG16G20	KC114KC1	BG812H7	BAKC1234
BG16G24	KC112KC1	BG812U24	BC18KC1234
BG16G32	KC2KC1	BG812U58	BC516KC1234
BG16G6	KC38KC1	BG812U912	BC916KC1234
BG16G812	KC1234KC1	BG812W2	APKC1234
BG16U24	BC18KC1	BH1	R14
BG16U58	BC516KC1	BH1E24	R1814
BG16U912	BC916KC1	RH1E58	R51614
BG16W2	APSKC1	BH1E912	R91614
BG20	KC114	BH1F1	RF11614
BG204T	KC114T	BH1F12	PH14
BG20B5	SBKC114	BH1F2	RF53214
BG20C1	500KC114B	BH1H7	RA14
BG20C2	500KC114	BH1H8	RO14
BG20E24	SFC18KC114	BH2	R38
BG20E58	SFC516KC114	BH24	PSF18
BG20E912	SFC916kC114	BH24R	PSF18R
BG20F13	PKC114	BH2E24	R1838
BG20U24	BC18KC114	BH2E58	R51638
BG20U58	BC516KC114	BH2E912	R91638
BG20U912	BC916KC114	BH2F1	RF11638
BG24	KC112	BH2F12	PH38

B-Line® is a registered trademark of B-Line. Black Claw™ is a trademark of Minerallac Co.
See page 339 for Traditional Line and page 342 for Strut Fittings cross-reference to B-Line®.

B-Line®	Black Claw™	B-Line®	Black Claw™
BH2F2	RF53238	BP16E24	SFC18100
BH2H7	RA38	BP16E58	SFC516100
BH2H8	RO38	BP16E912	SFC916100
BH4	R14T	BP16F13	P100
BH4E24	R1814T	BP16P16	HIC100100
BH4E58	R51614T	BP16U24	BC18100
BH4E912	R91614T	BP16U58	BC516100
BH4F1	RF11614T	BP16U912	BC916100
BH4F12	PH14T	BP16W2	APS100
BH4F2	RF53214T	BP8	HIC50
BH4H7	RA14T	BP84T	HIC50T
BH4H8	RO14T	BP8A5	TS50
BH5	R1438N	BP8A6	TB50
BH58	PSF516	BP8B1	SS50
BH58R	PSF516R	BP8B5	SS50
BH5E24	R181438N	BP8C1	50050B
BH5E58	R5161438N	BP8C2	50050
BH5E912	R9161438N	BP8D3	NB50
BH5F12	PH1438N	BP8D4	RS50
BH5F2	RF5321438N	BP8E24	SFC1850
BH5H7	RA1438N	BP8E58	SFC51650
BH5H8	RO1438N	BP8E912	SFC91650
BH6	R38T	BP8F13	P50
BH6E24	R1838T	BP8H7	BA50
BH6E58	R51638T	BP8P12	HIC5075
BH6E912	R91638T	BP8P16	HIC50100
BH6H7	RA38T	BP8P8	HIC5050
BH6F1	RF1161438N	BP8U24	BC1850
BH6F1	RF11638T	BP8U58	BC51650
BH6F12	PH38T	BP8U912	BC91650
BH6F2	RF53238T	BP8W2	APS50
BH6H8	RO38T	BU24	BC18
BH912	PSF916	BU24S	BC18ST
BH912R	PSF916R	BU58	BC516
BN1	UN14	BU58S	BC516ST
BN2	PN8	BU912	BC916
BN4	PN14	BU912S	BC916ST
BN6	PN38	BW12	FS2
BP12	HIC75	BW16	FS3
BP124T	HIC75T	BW2	APS
BP12A5	TS75	BW2CT2	APSPCTF
BP12A6	TB75	BW20	FS4
BP12B1	SS75	BW4	FSBX
BP12B5	SB75	BW8	FS1
BP12C1	50075B	BX5	SROM
BP12C2	50075	BX5	SBX
BP12D3	NB75	BX9	BXC
BP12D4	RS75	BXL1011	F8C
BP12E24	SFC1875	BXL1214	F8D
BP12E58	SFC51675	BXL1519	F8E
BP12E912	SFC91675	BXL2024	F8F
BP12F13	P75	BXL2530	F8G
BP12H7	BA75	BXL67	F8A
BP2P12	HIC7575	BXL89	F8B
BP2P16	HIC75100	BXM1011	F4C
BP12U24	BC1875	BXM1214	F4D
BP12U58	BC51675	BXM1519	F4E
BP12U912	BC91675	BXM2024	F4F
BP12W2	APS75	BXM2530	F4G
BP16	HIC100	BXM67	F4A
BP164T	HIC100T	BXM89	F4B
BP16A5	TS100	BXS1011	F2C
BP16A6	TB100	BXS1214	F2D
BP16B1	SS100	BXS1519	F2E
BP16C1	500100B	BXS2530	F2G
BP16C2	500100	BXS67	F2A
BP16D4	RS100	BXS89	F2B

B-Line® is a registered trademark of B-Line. Black Claw™ is a trademark of Minerallac Co.
See page 339 for Traditional Line and page 342 for Strut Fittings cross-reference to B-Line®.

Caddy® Cross-Reference to Minerallac® Traditional

Caddy®	Minerallac®	Caddy®	Minerallac®
512	TBAR	CD8B	8B
520	LSBAR	CD9B	9B
708	BAR	CG4	C6
770	JC12100	CJ6	C6
771	SH212	DS12A	BST
16MB18	CBS18KC1APS	ESG1	G100
16MB1824	CBS18KC118	EBS12	BS18
16MB1858	CBS18KC1516	EBS16	BS18
16MB18A	CBS18KC1	EBS18	BS18
4BRT32	648R	H23	FBO23
4BRT32WS	648RS	H4	FBO234
4BRT64	654R	H6	FBO6
4WN	14WNW	IDS	DWC1
6MB18	CBS18KC38APS	MP1P	WBF1
6MB1824	CBS18KC3818	MPLS	WBF1
6MB1858	CBS18KC38516	RBS16	UFMB16
6MB18A	CBS18KC38	RBS24	UFMB24
812MB18	CBS18KC1234APS	RLC	OR
812MB1824	CBS18KC123418	SGB16A	BMB16
812MB1858	CBS18KC1234516	SGB16A	BMB16D
812MB18A	CBS18KC1234	SGB24A	BMB24
812MB18S	CBS18KC1234ST	SGB24A	BMB24D
766A	DLS1		
AB	BA		
AO	BO		
BC200	600		
BC200CD0B	A0600B		
BC200CD1B	A1600B		
BC200CD2.5B	A2-1/2600B		
BC200CD2B	A2600B		
BC2100CD4B	A4600B		
BC200CD58	A5600B		
BC400	602B		
BHA	FS2		
CAT3224	J200BBC18		
CAT33224SM	J200SFC18		
CAT3258	J200BBC516		
CAT3258SM	J200SFC516		
CAT326Z34	J200APS		
CAT32912	J200BBC916		
CAT32912SM	J200SFC916		
CAT32AB	J200B		
CAT32AF14	J200ABC25		
CAT32BC	J200500		
CAT32BC200	J200600		
CAT32BC200B	J200B600		
CAT32BCB	J200B500		
CAT32VF14	J200VBC25		
CD0B	K0B		
CD1B	K1B		
CD2.5B	2-1/2B		
CD2B	K2B		
CD3B	3B		
CD4B	4B		
CD5B	5B		
CD6B	6B		
CD7B	7B		

B-Line® Cross-Reference to Minerallac® Traditional

B-Line®	Minerallac®	B-Line®	Minerallac®
BA1	DWC1	BL1440C442	A4600B
BA12	TBAR	BL1450C442	A5600B
BA20	LSBAR	BL1400	K0B
BA4WN	14WNW	BL1410	K1B
BB10	WBF1	BL1420	K2B
BB18	BS18	BL1425	2-1/2B
BB216	BMB16	BL1430	3B
BB216D	BMB16D	BL1440	4B
BB224	BMB24	BL1450	5B
BB224D	BMB24D	BL1460	6B
BB26	BAR	BL1470	7B
BB32	OR	BL1480	8B
BB33	BST	BL1490	9B
BB423	FBO23	BM1	G100
BB44	FBO234	BP12S18	CBS18HIC75
BB46	FBO6	BP12S18S	CBS18HIC75ST
BB50	SBO	BP12S18U24	CBS18HIC7518
BB816	UFMB16	BP12S18U58	CBS18HIC75516
BB824	UFMB24	BP12S18W2	CBS18HIC75APS
BC442	600	BP16S18	CBS18HIC100
BCH32	J200	BP16S18S	CBS18HIC100ST
BCH32U24	J200BBC18	BP16S18U24	CBS18HIC10018
BCH32E24	J200SFC18	BP16S18U58	CBS18HIC10056
BCH32U58	J200BBC516	BP16S18W2	CBS18HIC100APS
BCH32E58	J200SFC516	BP8S18	CBS18HIC50
BCH32W2	J200APS	BP8S18S	CBS18HIC50ST
BCH32U912	J200BBC916	BP8S18U24	CBS18HIC5018
BCH32E912	J200SFC916	BP8S18U58	CBS18HIC50516
BCH32RB	J200B	BP8S18W2	CBS18HIC50APS
BCH32F4	J200ABC25	BR32T	648R
BCH32C442	J200B600	BR324W	648RS
BCH32C2	J200B500	BR64T	654R
BCH32F3	J200VBC25	BRC1	C6
BG12S18U24	CBS18KC123418	BRC2	C6
BG16S18	CBS18KC1		
BG16S18U24	CBS18KC118		
BG16S18U58	CBS18KC1516		
BG16S18W2	CBS18KC1APS		
BG6S18	CBS18KC38		
BG6S18U24	CBS18KC3818		
BG6S18U58	CBS18KC38516		
BG6S18W2	CBS18KC38APS		
BG812S18	CBS18KC1234		
BG812S18S	CBS18KC1234ST		
BG812S18U58	CBS18KC1234516		
BG812S18W2	CBS18KC1234APS		
BH7	BA		
BH8	BO		
BH9	JC12100		
BH10	SH212		
BL1400C442	A0600B		
BL1410C442	A1600B		
BL1425C442	A2-1/2600B		
BL14200C442	A2600B		
BL1430C442	A3600B		

Caddy® Cross-Reference to Minerallac's MasterStrut Fittings

Caddy®	Minerallac®	Caddy®	Minerallac®
BC09-09	MS17509	HSCR1/4x1-1/2	MHH25150
BC09-12	MS175012	HSCR1/4x1-1/4	MHH25125
BC09-15	MS175015	HSCR1/4x3/4	MHH25075
BC10	M1750	HSCR1/4x3/4	MHH37075
BC1000000	M1325	HSCR3/8x1	MHH37100
BC130025	M25014	HSCR3/8x1-1/2	MHH37150
BC130037	M25038	HSCR3/8x1-1/4	MHH37125
BC130050	M25012	HSCR3/8x2	MHH37200
BC140037	M36238	L100000	M202
BC140050	M36212	L11	M212
BC17	M1158	L11000	M216
BC17	M1314	L1230	M230
BC2000000	M751	L1235	M235
BR14	MDS750	L1240	M240
EF22C000	M6136	L15	MA202
EF24A000	M6158	L18	M223
EMTC0050	MSE050	L190000	M212D
EMTC0075	MSE075	L200000	M203
EMTC0100	MSE100	L21	MA326
EMTC0125	MSE125	L220000	M204
EMTC0150	MSE150	L25L	ML214
EMTC0200	MSE200	L28	M244
ET1	MPEC1HDG	L290387	M201378
ET1/2	MPEC12HDG	L290587	M201578
ET1-1/2	MPEC112HDG	L290787	M201778
ET1-1/4	MPEC114HDG	L290987	M201978
ET2	MPEC2HDG	L30	M225
ET2-1/2	MPEC212HDG	L33	M625
ET3/4	MPEC34HDG	L37	MA262
ET3	MPEC3HDG	L38	MA282
F090000	M122	L41	M265
F110000	M101D38	L460450	M30245
F120000	M101D12	L470450	M31245
F130000	M10114	NUT0025	MCW14
F140000	M10138	NUT0037	MCW38
F150000	M10112	NUT0050	MCW12
F160000	M10158	O.D.1	MOD1
F17	M10134	O.D.1/2	MOD12
F200000	M123	O.D.1-1/2	MOD112
F230000	M124	O.D.1-1/4	MOD114
F250000	M144	O.D.1-1/8	MOD118
F280000	M155	O.D.1-3/8	MOD138
F330000	M164	O.D.3/4	MOD34
F360000	M133	O.D.3/8	MOD38
F370000	M134	O.D.5/8	MOD58
HSCR1/2x1	MHH50100	O.D.7/8	MOD78
HSCR1/2x1-1/2	MHH50150	P100000	M803
HSCR1/2x1-1/4	MHH50125	P10SQ0000	M803SQ
HSCR1/2x1-3/4	MHH50175	P110000	M813
HSCR1/2x2	MHH50200	P11SQ0000	M813SQ
HSCR1/4x1	MHH25100	P130000	M843

Caddy®	Minerallac®	Caddy®	Minerallac®
P13SQ0000	M843SQ	SPR0050	MCL12
PAR1	MPC1HDG	SPRC0025	MCS14
PAR1/2	MPC12HDG	SPRC0037	MCS38
PAR1-1/2	MPC112HDG	SPRC0050	MCS12
PAR1-1/4	MPC114HDG	SPRD1/4	MCL14
PAR2	MPC2HDG	SPRD3/4	MCL34
PAR2-1/2	MPC212HDG	SPRD3/8	MCL38
PAR3	MPC3DG	SPRD5/8	MCL58
PAR3/4	MPC34HDG	SQNT1/2	MSN12
PAR3/8	MPC38HDG	SQNT1/4	MSN14
PAR3-1/2	MPC312HDG	SQNT3/8	MSN38
PAR4	MPC4HDG	SQNT5/16	MSN516
PCC1	M200100	TCC1	M100100
PCC1/2	M200050	TCC1/2	M100050
PCC1-1/2	M200150	TCC1/4	M100025
PCC1-1/4	M200125	TCC1-1/2	M100150
PCC2	M200200	TCC1-1/4	M100125
PCC2-1/2	M200250	TCC1-1/8	M100112
PCC3	M200300	TCC1-3/4	M100175
PCC3/4	M200075	TCC1-3/8	M100137
PCC3/8	M200037	TCC1-5/8	M100162
PCC3-1/2	M200350	TCC2	M100200
PCC4	M200400	TCC2-1/4	M100225
PCC5	M200500	TCC2-1/8	M100212
PCC6	M200600	TCC2-5/8	M100262
RA1	MRAC1HDG	TCC3/4	M100075
RA1/2	MRAC12HDG	TCC3/8	M100037
RA1-1/2	MRAC112HDG	TCC5/8	M100062
RA1-1/4	MRAC114HDG	TCC7/8	M100087
RA2	MRAC2HDG	TSNT0025	MCT14
RA2-1/2	MRAC212HDG	TSNT0037	MCT38
RA3	MRAC3HDG	TSNT0050	MCT12
RA3/4	MRAC34HDG	U10A0000	M5158
RA3/8	MRAC38HDG	U11C0000	M5136
RA3-1/2	MRAC312HDG	UNIV00950	MSU0050
RA4	MRAC4HDG	UNIV0075	MSU0075
RSCR1/4x1	MRH25100	UNIV0100	MSU100
RSCR1/4x1-1/4	MRH25125	UNIV0125	MSU125
RSCR1/4x3/4	MRH25075	UNIV0150	MSU150
RSCR3/8x1	MRH37100	UNIV0200	MSU200
RSCR3/8x1-1/2	MRH37150	UNIV0250	MSU250
RSCR3/8x1-1/4	MRH37125	UNIV0300	MSU300
SHH1/4x3/4	MSH25075	UNIV0350	MSU350
SHH3/8x1-1/4	MSH37125	UNIV0400	MSU400
SHH5/16x1	MSH31100	W14	MC7208
SHH5/16x1-1/2	MSH31150	W160000	M7105
SHH5/16x1-1/4	MSH31125	W170000	M7108
SPA0025	MCR14	W180000	M7210
SPA0037	MCR38		
SPA0050	MCR12		
SPA0062	MCR58		

B-Line® Cross-Reference to Minerallac's MasterStrut Fittings

B-Line®	Minerallac®	B-Line®	Minerallac®
1/4FW	MWF12	B142	M164
1/4HN	MHN12	B143	M134
1/2LW	MWL12	B154	M30245
1/2SQN	MSN12	B155	M31245
1/2X1-1/2HHCS	MHH50150	B167	M6136
1/2X1-1/4HHCS	MHH50125	B172	M6158
1/2X1-3/4HHCS	MHH50175	B2001	MSE050
1/2X1HHCS	MHH50100	B2002	MSE075
1/2X2HHCS	MHH50200	B2003	MSE100
1/4FW	MWF14	B2004	MSE125
1/4HN	MHN14	B2005	MSE150
14LW	MWL14	B2006	MSE200
1/4X1-1/2FFW	MFW14	B2008	MSS050
1/4X1-1/2HHCS	MHH25150	B2009	MSS075
14X1-1/4HHCS	MHH25125	B201	M10138
1/4X1-1/4RHMS	MRH25125	B2010	MSS100
1/4X1HHCS	MHH25100	B2011	MSS125
1/4X1SRMS	MRH25100	B2012	MSS150
1/4X3/4HHCS	MHH25075	B2013	MSS200
1/4X3/4SHHMS	MSH25075	B2014	MSU250
1/4X3/4SRHMS	MRH25075	B2015	MSU300
1/4X1-1/4HHCS	MHH25125	B2016	MSU350
3/4FW	MWF34	B2017	MSU400
3/4HN	MHN34	B201D	M101D38
3/8FW	MWF38	B202	M10112
3/8HN	MHN38	B202-1	M10158
3/8LW	MWL38	B202-2	M10134
3/8X1-1/2FFW	MFW38	B2024	MOD38
3/8X1-1/2HHCS	MHH37150	B2025	MOD12
3/8X1-1/2RHMS	MRH37150	B2026	MOD58
3/8X1-1/4HHCS	MHH37125	B2027	MOD34
3/8X1-1/4SHHMS	MSH37125	B2028	MOD78
3/8X1-1/4SRMS	MRH37125	B2029	MOD1
3/8X1HHCS	MHH37100	B202D	M101D12
3/8X1SRMS	MRH37100	B2030	MOD118
3/8X2HHCS	MHH37200	B2031	MOD114
3/8X3/4HHCS	MHH37075	B2032	MOD138
5/16X1-1/2SHHMS	MSH31150	B2033	MOD112
5/16X1-1/4SHHMS	MSH31125	B2070	MPPC38
5/16X1SHHMS	MSH31100	B2071	MPPC12
5/8FW	MWF58	B2072	MPPC34
5/8HN	MHN58	B2073	MPPC1
ATR1/2	CTR1/2	B2074	MPPC114
ATR1/4	CTR1/4	B2075	MPPC112
ATR3/4	CTR3/4	B2076	MPPC2
ATR3/8	CTR3/8	B2077	MPPC212
ATR5/8	CTR5/8	B2078	MPPC3
B101	M202	B2079	MPPC312
B102	M223	B2080	MPPC4
B103	M203	B211	M1325
B104	M204	B212-3/8	M753
B107	M5158	B2208	MSU050
B112	MA262	B2209	MSU075
B113	MA282	B2210	MSU100
B115	M214	B2211	MSU125
B116-52	M1536	B2212	MSU150
B118	M264	B2213	MSU200
B121	MC7208	B230	M212
B123	MC7312	B231	M212D
B125	M263	B234L	ML350
B126	M624	B234R	MR350
B127	M625	B236L	ML203
M129	M122	B236R	MR203
B132	M155	B238L	ML214
B133	M144	B238R	MR214
B140	M133	B239	M255
B141	M123	B248	M31445
		B271	M7105

B-Line®	Minerallac®	B-Line®	Minerallac®
B272	M7208	B671-1	MPEC1
B273	M7210	B671-1/2	MPEC12
B279	M803	B671-1-1/2	MPEC112
B279SQ	M803SQ	B671-1-1/4	MPEC114
B280	M813	B671-2	MPEC2
B280SQ	M813SQ	B671-2-1/2	MPEC212
B281	M843	B671-3	MPEC3
B281	M843SQ	B671-3/4	MPEC34
B303	M25014	B751	M1750
B306	M25038	B766-22	MIJ1362
B308	M25012	B766-52	MIJ1582
B312-12	MS175012	B844	M206
B312-15	MS175015	BVP025	M200025
B312-9	MS17509	BVP037	M200037
B3174-1/2	MGH050	BVP050	M200050
B3174-1	MGH100	BVP075	M200075
B3174-1-1/2	MGH150	BVP100	M200100
B3174-1-1/4	MGH125	BVP125	M200125
B3174-2	MGH200	BVP150	M200150
B3174-2-1/2	MGH250	BVP200	M200200
B3174-3/4	MGH075	BVP250	M200250
B3174-3	MGH300	BVP300	M200300
B3174-4	MGH400	BVP350	M200350
B321-2	M36212	BVP400	M200400
B341	M124	BVP500	M200500
B355	M751	BVP600	M200600
B359	M230	BVT025	M100025
B360	M235	BVT037	M100037
B361	M240	BVT050	M100050
B372	MA202	BVT062	M100062
B374	M213	BVT075	M100075
B420-378	M201378	BVT087	M100087
B420-578	M201578	BVT100	M100100
B420-778	M201778	BVT112	M100112
B420-978	M201978	BVT125	M100125
B422-1	MRAC1	BVT137	M100137
B422-1/2	MRAC12	BVT150	M100150
B422-1-1/2	MRAC112	BVT162	M100162
B422-1-1/4	MRAC114	BVT175	M100175
B422-2	MRAC2	BVT200	M100200
B422-2-1/2	MRAC212	BVT212	M100212
B422-3	MRAC3	BVT225	M100225
B422-3/4	MRAC34	BVT250	M100251
B422-3-1/2	MRAC312	BVT262	M100262
B422-4	MRAC4	BVT312	M100312
M503L	MLG541	N224	MCR14
B503R	MRG541	N224WO	MCW14
B533	M265	N225	MCR12
B558	M225	N225WO	MCW12
B616-22A-7/8	MSG587	N228	MCR38
B616-22A-9/16	MSG556	N228WO	MCW38
B616-7/8	MSG287	N255	MCR58
B616-9/16	MSG256	N524	MCS14
B655-1/2	CTRC1/2	N525	MCS12
B655-1/4	CTRC1/4	N528	MCS38
B655-3/8	CTRC3/8	N7224	MCL14
M670-1	MPC1	N725	MCL12
M670-1-1/2	MPC112	N728	MCL38
M670-1-1/4	MPC114	N755	MCL58
M670-1/2	MPC12	N775	MCL34
M670-2	MPC2	TN224	MCT14
M6702-1/2	MPC212	TN225	MCT12
B670-3	MPC3	TN228	MCT38
M670-3-1/2	MPC312		
B670-3/4	MPC34		
B670-3/8	MPC38		
B670-4	MPC4		
B671-1	MPEC1		

Insulated Staples Cross-Reference

Handy Straps®	Impact™ Staples by Minerallac®	Packaging	Page
5-424	IDC195	Box of 500	211
ACMC-10	IAM375 & IAM50	Box of 50	209
		Box of 50	209
CC-1005	ICS18B	Box of 100	204
CC-1010	I242B	Box of 100	204
CC-1012	I242BP	Box of 100	206
CC-1016	I242BS	Box of 100	207
CC-1020	I275B	Box of 100	204
CC-1022	I275BP	Box of 100	206
CC-1026	I275BS	Box of 100	207
CC-1030	I300B	Box of 100	204
CC-1032	I300BP	Box of 100	206
CC-1036	I300BS	Box of 100	207
CC-1060	I395B	Box of 100	204
CC-1062	I395BP	Box of 100	206
CC-1066	I395BS	Box of 100	207
CC-2010	I25DB	Box of 100	204
CC-2020	I305DB	Box of 100	204
CC-2022	I305DBP	Box of 50	206
CC-2026	I305DBS	Box of 100	207
MS-6088	INS501	Box of 100	208
RA-1450P	---	Polybag of 50	--
RA-1455P	IPS75H	Polybag of 100	198
RA-1470	---	Polybag of 50	--
RA-1477P	IPS50H	Polybag of 100	198
RA-1555	IPS75A	Box of 100	198
RA-1566	IPS75L	Kraft Bag of 250	198
RA-1566UV	---	Kraft Bag of 250	--
RA-1577	IPS50A	Box of 100	198
RA-1580	IPS50M	Bulk 5,000	198
RA-1582	IPS50P	Pail of 2,000	198
RA-1588	IPS50K	Kraft Bag of 500	198
RA-1588/2	IPS502	Box of 50	199
RA-1588/3	IPS503	Box of 50	199
RA-1588/4	IPS504	Box of 50	199
RA-1588UV	---	Kraft Bag of 500	--
RA-1599	IBT252T	Box of 100	202
RA-1610	INS41	Box of 100	208
RA-1620	INS50	Box of 50	208
RA-1630	INS66	Box of 100	208
RA-1710	ISER10	Box of 50	200
RA-1720	ISER20	Box of 25	200
RA-1730	ISER30	Box of 25	200
RA-1740	ISER40	Box of 10	200
RA-1750	ISEU50	Box of 50	201
RA-1760	ISEU60	Box of 50	201
RA-1765	ISEU70	Box of 25	201
RA-1770	ISEU80	Box of 25	201
RA-4250	IBT251W	Box of 100	202
TC-1104G	ITC12G	Box of 100	203
TC-1104T	ITC12T	Box of 100	203
TC-1106G	ITC25G	Box of 100	203
TC-1106T	ITC25T	Box of 100	203
TC-1125G	ITC42G	Box of 50	203
TC-1125T	ITC42T	Box of 50	203
UF-2050	IUF40	Box of 50	210
WA-1810	IWP50	Box of 100	212
WA-1820	IWP75	Box of 25	212

Metal Staples Cross-Reference

King Rigid-Hed®	Impact™ Staples by Minerallac®	Packaging	Page
<i>Cable Staples</i>			
RXR10Mcarton	ICS1050HF KG10M	Bulk, 10,000	188
RXR5Mcarton	ICS1050HF KG5M	Bulk, 5,000	188
RXR5Mpail	ICS1050HF PL5M	Pail of 5,000	188
RXR10Mpail	ICS1050HF PL10M	Pail of 10,000	188
RXRP5	ICS1050HF BX500	Box of 500	188
RXRP1	ICS1050HF BX100	Box of 100	188
RXRP25	---	Box of 25	--
BXR10Mcarton	---	Bulk, 10,000	--
BXR5Mcarton	ICS1256F KG5M	Bulk, 5,000	189
BXR5Mpail	ICS1256F PL5M	Pail of 5,000	189
BXR10Mpail	---	Pail of 10,000	--
BXR P5	ICS1256F BX500	Box of 500	189
BXR P1	ICS1256F BX100	Box of 100	189
BXR P25	---	Box of 25	--

King Heavy Duty	Impact™ Staples by Minerallac®	Packaging	Page
<i>Cable Staples</i>			
RXE10Mcarton	ICS1050H KG10M	Bulk, 10,000	188
RXE5Mcarton	ICS1050H KG5M	Bulk, 5,000	188
RXE5Mpail	ICS1050H PL5M	Pail of 5,000	188
RXE10Mpail	ICS1050H PL10M	Pail of 10,000	188
RXEP5	ICS1050H BX500	Box of 500	188
RXEP1	ICS1050H BX100	Box of 100	188
BXE10Mcarton	---	Bulk, 10,000	--
BXE5Mcarton	ICS1256 KG5M	Bulk, 5,000	189
BXE5Mpail	ICS1256 PL5M	Pail of 5,000	189
BXE10Mpail	---	Pail of 10,000	--
BXE P5	ICS1256 BX500	Box of 500	189
BXE P1	ICS1256 BX100	Box of 100	189

Cable Staples With Plastic Insulator

06021	IMPI1256 PL5M	Pail of 5,000	196
06022	IMPI1256 BX500	Box of 500	196
06023	IMPI1256 BX100	Box of 100	196
06024	---	Pail of 2,500	--
06025	---	Pail of 1,250	--

Service Entrance Staples

K-30	ISE1380 BX100*	Box of 100	192
K-35	ISE1410 BX100*	Box of 100	192
K-40	ISE1813 BX50	Box of 50	192
K-45	ISE2211 BX50	Box of 50	192
K-50	ISE2316 BX50	Box of 50	192

*Note: All King Service Entrance Staples are Zinc plated.
Impact™ Service Entrance Staples are cleaned & polished.
ISE1380 & ISE1410 are also available zinc plated.

Refer to catalog page number above for description of staple and Minerallac shipper quantity.

Rigid-Hed® is a registered trademark of King Manufacturing Co., Inc.

Metal Staples Cross-Reference

Thiel's Easy Drive Staples	Impact™ Staples by Minerallac®	Packaging	Page
<i>Cable Staples</i>			
1100-1	ICS1050H BX100	Box of 100	188
	ICS1050HF BX100	Box of 100	188
1100-5	ICS1050H BX500	Box of 500	188
	ICS1050HF BX500	Box of 500	188
1100-PB5M	ICS1050H PL5M	Pail of 5,000	188
	ICS1050HF PL5M	Pail of 5,000	188
1100-PB10M	ICS1050H PL10M	Pail of 10,000	188
	ICS1050HF PL10M	Pail of 10,000	188
1125-1	ICS1256 BX100	Box of 100	189
	ICS1256F BX100	Box of 100	189
1125-5	ICS1256 BX500	Box of 500	189
	ICS1256F BX500	Box of 500	189
1125-PB5M	ICS1256 PL5M	Pail of 5,000	189
	ICS1256F PL5M	Pail of 5,000	189
1125-PB8M	ICS1256 PL75C	Pail of 7,500	189
	(Note: Thiel Pail Quantity is 8,000)		
1150-1	ICS1375 BX100	Box of 100	189
	ICS1375 PL5M	Pail of 5,000	189
(Note: Thiel Pail Quantity is 8,000)			
1175-1	ICS1510 BX100	Box of 100	189
	ICS1510 PL5M	Pail of 5,000	189
(Note: Thiel Pail Quantity is 2,500)			
<i>PVC Dipped (insulated metal Cable Staples)</i>			
1100-IN-1	IMPD1050H BX100	Box of 100	197
1100-IN-5	IMPD1050H BX500	Box of 500	197
1100-IN-PB5M	IMPD1050H PL5M	Pail of 5,000	197
1100-IN-PB10M	---	Pail of 10,000	--
1125-IN-1	IMPD1256 BX100	Box of 100	197
1125-IN-5	IMPD1256 BX500	Box of 500	197
1125-IN-PB5M	IMPD1256 PL5M	Pail of 5,000	197
1125-IN-PB10M	---	Pail of 10,000	--

Refer to catalog page number above for description of staple and Minerallac shipper quantity.

Easy Drive Staples manufactured by Thiel Tool & Engineering Co., Inc.

Metal Staples Cross-Reference

Cross Brand	Impact™ Staples by Minerallac®	Packaging	Page
Economy Cable Staples			
200 PP 5M	ICS1050 PL5M	Pail of 5,000	188
200 PB 5M	ICS1050 KG5M	Bulk, 5,000	188
200 P5	ICS1050 BX500	Box of 500	188
200 P1	ICS1050 BX100	Box of 100	188

Zinc Plated Economy Cable Staples

200 PB 5M EG	ICS1050Z KG5M	Bulk, 5,000	190
200 P5 EG	ICS1050Z BX500	Box of 500	190
200 P1 EG	ICS1050Z BX100	Box of 100	190

Viking Brand Nob-Staples®	Impact™ Staples by Minerallac®	Packaging	Page
Cable Staples			
100 PP 5M	ICS1050HF PL5M	Pail of 5,000	188
100 PB 5M	ICS1050HF KG5M	Bulk, 5,000	188
100 PP 2.5M	---	Pail of 2,500	--
100 CP 750	---	Bag of 750	--
100 P5	ICS1050HF BX500	Box of 500	188
100 P1	ICS1050HF BX100	Box of 100	188

125 PP 5M	ICS1256F PL5M	Pail of 5,000	189
125 PB 5M	ICS1256F KG5M	Bulk, 5,000	189
125 PP 2.0M	---	Pail of 2,000	--
125 P5	ICS1256F BX500	Box of 500	189
125 P1	ICS1256F BX100	Box of 100	189

Service Entrance Staples

131	ICS1375 BX100	Box of 100	189
141	ICS1510 BX100	Box of 100	189
151	ISE2316 BX50	Box of 50*	192

*(Note: Viking box quantity is 100)

Stacking Cable Staples

LL 100 PP 3M	---	Pail of 3,000	--
LL 100 PP1	ISS1750 BX100	Box of 100	191

Cable Staples with Plastic Insulator

IN3125 PP 2.5M	*	Pail of 2,500	--
IN3125 PP 1.5M	*	Pail of 1,500	--
IN3125 CP 500	*	Bag of 500	--
IN3125 CP 175	*	Bag of 175	--

*(Impact Staples with Plastic Insulator, part number IMPI1256 are packed in boxes of 100, 500, and plastic pails of 5,000. See page 196 of our catalog.)

Refer to catalog page number above for description of staple and Minerallac shipper quantity.

Viking is a brand name & Nob Staples® a registered trademark of W.W. Cross Industries, Inc.

The Minerallac Advantage

Minerallac has been manufacturing parts since 1894. Where many fastener companies outsource the manufacture of their parts or import them from other sources, Minerallac manufactures over 90% of all the parts shown in this catalog at our facilities. We are proud to proclaim "Made in the USA."

Because we design and manufacture our own parts, we maintain control over such things as quality, consistency and design.

Well-known in the industry for the quality of it's parts, Minerallac strives to enhance this well-earned reputation.

Distribution

Minerallac has a nation-wide distribution network, located throughout the United States and Canada, stocking standard Minerallac parts. This results in quick service and delivery.

Manufacturing

Stamped, Wire-Formed & Injection-Molded

Minerallac's stamped, wire-formed and injection-molded products are manufactured on modern presses with precision tooling. All tooling design, tooling manufacture and tooling repairs are completed in-house by our staff of highly skilled tool and diemakers. Their commitment to quality and innovative design means a quality part every time.

Strut

Channel is manufactured on our state-of-the-art strut rolling mill. As a new player in the strut arena, we go that extra mile. Special cuts and custom colors, as well as that same attention to detail and quick turn-around time that marks our other lines, are seen in Minerallac's MasterStrut line.

Quality Assurance

Our Quality Control department has established comprehensive testing programs from incoming inspection of raw materials through finished goods inspection and testing. Minerallac's Q.C. team verifies raw materials conformity with AISI and Minerallac's TQM standards. Finished parts are sampled and run through visual inspection and tested for load compliance and standards conformity.

Salt spray testing to simulate parts exposure to outdoor elements by an outside testing lab is also done periodically on the different finishes and/or materials offered by Minerallac. Results are available upon request.

In addition, all products are coded with the packing date to allow tracking back to the raw materials used to produce them.

Research & Development

Minerallac's Research and Development department is continually developing new products and working with our Q.C. department to improve existing product lines. Many of our new product designs are a direct result of customer suggestions or needs.

As the electrical industry moves towards parts made from light-weight, high-quality plastic, Minerallac is on the cutting edge. Expect more innovative parts in the future.

Technical Support

Technical support is just a phone call away. Call for technical support at our toll free number 877-285-2200 with product questions.

WARRANTY

Minerallac warrants all products sold to be free and clear of all liens and encumbrances and to be free from defects in material and workmanship. In the event that any product fails to conform to such warranty, Minerallac's liability is limited solely to replacing such product without charge.

The warranties set forth above are exclusive and are in lieu of all other warranties whether statutory, expressed, or implied including warranties of merchantability and fitness for a particular purpose, and warranties arising from course of dealing

or usage of trade. The above provides remedy of replacement will be the sole and exclusive remedy of any purchaser of a product for any failure by Minerallac to comply with the warranty provision, whether claims by purchaser are based on contract or in tort including negligence, and in no event shall Minerallac be liable for loss of profits, indirect, special, consequential and other similar damages, and any economic loss resulting from any such failures.