



full line catalog 2013

EiKO PRESENTS

LITESPANTM FIXTURES



- POST-TOP
- COBRAHEAD
- WALLPACK
- PARKADE
- FLOOD

- HIGH-BAY
- AREA STREET
- CANOPY
- PLATE
DOWNLIGHT



THE LED REVOLUTION IS HERE!

Our **LitespanLED®** line offers the *most efficient LED fixtures on the market* at 95-105 LPW. The **individual LED heatsink** provides unrivaled thermal control, and the **innovative modular design** allows for scalability. **Precision optics** target light to the task. Our fixtures are **IP65** rated for weather protection, and **Design Lights Consortium™ (DLC)** qualified for high quality and energy efficiency.

Advantages include directional light emission, superior optical controls, instant-on capabilities, rapid on/off cycling, cold temperature operation, extended lifetime, and superior lumen-per-watt efficacy.



Table Of Contents

ColorMaster PRO™ Ceramic Metal Halide	1
ColorMaster PRO™ PAR Lamps	1
ColorMaster PRO™ MR16 Lamps	1
ColorMaster PRO™ Double-Ended Lamps	1
ColorMaster PRO™ Bi-pin Lamps	1
ColorMaster PRO™ EDX17 Lamps	1
PowerMaster™ Ballasts	2
LED Lamps	2
LitespanLED® GEN 3	2
LitespanLED® Linear LED Lamps	2
T-8 Linear LED	2
T-8 U-Bend LED	2
LitespanLED® PAR Lamps	2
PAR16 LED	2
PAR20 LED	2
PAR30 LED	3
PAR38 LED	3
LitespanLED® Decorative Lamps	3
A19 LED	3
B11 LED	4
G25 LED	4
LitespanLED® BR/R & MR LED Lamps	4
BR/R30 LED	4
MR16 LED	4
LitespanLED® GEN 2	4
LitespanLED® Decorative Lamps	4
LitespanLED® PAR Lamps	4
PAR20 LED	4
PAR30 LED	5
PAR38 LED	5
LitespanLED® MR16 LED Lamps	5
LitespanLED® Linear LED Refit Lamps	5
Original LitespanLED® Lamps	5
LED PAR Lamps	5
Miniature Replacement LED Lamps	5
HID Lamps	6
Metal Halide HID Lamps	6
Medium & Mogul Based Metal Halide HID Lamps	6
Pulse Start Metal Halide HID Lamps	7
Open Fixture Rated Metal Halide HID Lamps	8
Double Ended Metal Halide HID Lamps	8
Single Ended Metal Halide HID Lamps	8
High Pressure Sodium HID Lamps	9
Mercury Vapor HID Lamps	9
Fluorescent Lamps	9
T5ES Retrofit Kit	9
CFLi Lamps	9
High Watt CFLi	9
Spiral Shaped CFLi Lamps	10
Medium Based Spiral CFLi Lamps	10
Dimmable CFLi Lamps	10
Mogul Based Spiral CFLi Lamps	11
GU24 Based Spiral CFLi Lamps	11
PAR CFLi Lamps	11
R-Shaped CFLi Lamps	12
Decorative CFLi Lamps	12
A Shaped Decorative CFLi Lamps	12
B10 Decorative CFLi Lamps	13
B13 Decorative CFLi Lamps	13
G25 Decorative CFLi Lamps	13
Compact Fluorescent Lamps	13
Duo-Tube CFL Lamps	13
Quad-Tube CFL Lamps	14
Triple-Tube CFL Lamps	15
FML CFL Lamps	15
4-Pin Based Spiral CFL Lamps	15
Linear Fluorescent Lamps	15
T5 Linear Fluorescent Lamps	15
Programmed Start T5 Lamps	15
Preheat T5 Lamps	16
Blacklight T5 Lamps	16
T8 Linear Fluorescent Lamps	16
Long Life T8 Lamps	16

CEE Specified T8 Lamps	16
High Lumen T8 Lamps	17
Energy Saving T8 Lamps	17
Programmed Start T8 Lamps	17
Preheat T8 Lamps	17
Blacklight T8 Lamps	17
T8 U-Bend Fluorescent Lamps	18
Circular Fluorescent Lamps	18
Fluorescent Starters	18
Halogen Lamps	18
A-Line Halogen Lamps	18
EiKON Energy Efficient Halogen Lamps	18
Classic BT15 Halogen Lamps	18
MR8 Halogen Lamps	18
MR8 Supreme Halogen Lamps	19
MR11 Halogen Lamps	19
MR16 Halogen Lamps	19
MR16 Screw Base Halogen Lamps	20
MR16 Line Voltage Halogen Lamps	20
Aluminized Reflector Lamps	20
37mm Diameter Aluminized Reflector Lamps	20
56mm Diameter Aluminized Reflector Lamps	20
Single Ended Halogen Lamps	20
Double Ended Halogen Lamps	21
Double Ended Short Halogen Lamps	21
G4 Base 2-pin Halogen Lamps	21
G6.35 Base 2-pin Halogen Lamps	22
Bi-pin Line Voltage Halogen Lamps	22
Halogen Heat Lamps	22
SoLux Halogen Lamps	22
SoLux MR16 3500K Lamps	22
SoLux MR16 4100K Lamps	23
SoLux MR16 4700K Lamps	23
SoLux PAR 3500K Lamps	23
Incandescent Lamps	23
A Shaped Incandescent Lamps	23
Rough Service Lamps	23
C Shaped Lamps	24
R & BR Incandescent Lamps	24
S Shaped Lamps	24
T Shaped Lamps	25
Miniature & Automotive Lamps	25
Miniature Lamps (Alphanumeric)	25
Automotive Forward Lighting	39
High Performance Forward Lighting	39
ClearVision™ Supreme	39
ClearVision™ XL	39
PowerVision™ PRO	39
9000 Series Halogen Forward Lighting	40
800 Series Halogen Lamps	41
H1 Series Halogen Lamps	41
H2 Series Halogen Lamps	41
H3 Series Halogen Lamps	42
H4 Series Halogen Lamps	42
H7 Series Halogen Lamps	42
H8-H13 Halogen Lamps	42
HID - OE Replacement Lamps	43
Motorcycle and Snowmobile Lamps	43
Automotive Cabinets	44
Sealed Beam Lamps	44
Incandescent Sealed Beam Lamps	44
Halogen Sealed Beam Lamps	45
ANSI Coded Lamps	45
Photographic & SSTV Lamps	50
Enlarger Lamps	50
Flashtubes	50
Modeling Lamps	50
Photoflood Lamps	51

HPL Lamps	51
ANSI Coded SSTV Lamps	51
ArcMaster SSTV Discharge Lamps	53
ColorMaster Digital Imaging Lamps	54
Germicidal Lamps	54
Healthcare, Medical & Scientific Lamps	54
LitespanLED® Fixtures	56
Flood Light Fixture	56
30W Flood Light Fixture	56
50W Flood Light Fixture	56
80W Flood Light Fixture	57
100W Flood Light Fixture	57
120W Flood Light Fixture	57
160W Flood Light Fixture	57
200W Flood Light Fixture	58
240W Flood Light Fixture	58
High Bay Fixture	58
120W High Bay Fixture	58
90W High Bay Fixture	59
130W High Bay Fixture	59
160W High Bay Fixture	59
180W High Bay Fixture	59
240W High Bay Fixture	59
Canopy Light Fixture	60
HC Series - Scottsdale Design	60
RF Series - Slim Design	60
KC Series - Richmond Design	60
Parkade Light Fixture	60
40W Parkade Light Fixture	60
50W Parkade Light Fixture	60
80W Parkade Light Fixture	61
Wallpack Light Fixture	61
30W Wallpack Light Fixture	61
40W Wallpack Light Fixture	61
48W Wallpack Light Fixture	61
Post-Top LED Replacement Lamp	62
30W Post-Top LED Replacement Lamp	62
45W Post-Top LED Replacement Lamp	62

Cross Referencing for Automotive Miniatures and General Lighting

General Overview

Cross referencing a light bulb (technically called a “lamp”) can be done in two ways:

- By matching the known part number of your lamp to a part number of another manufacturer known to have the same specifications.
- By matching the specifications of your lamp to the specifications of a known part number.

Step 1: What is the lamp type?

1) Do you have an Automotive Miniature or a General Lighting lamp?


- **Miniatures** are usually just that: small, miniature lamps. They are typically designed to provide light for instrument panels or for other focused-light uses.
- **General Lighting** lamps are larger in size and designed to light larger areas.

For Automotive Miniatures:

Step 2: What is the bulb shape?

1) Identify the shape of the bulb.

- “Bulb” refers to the glass portion of the lamp.
- Refer to the diagram for common bulb shapes.



Step 3: What is the base type?

1) Identify the base type - see page 5.

- The base supports the lamp in the socket and conducts electricity to the filament.
- Refer to the diagrams on the facing page for common base types.


























































Step 4: What is the voltage and wattage?

1) Determine the voltage.

2) Determine the wattage.

- This information can usually be found stamped on the base of the bulb.
- If only given amps, remember this conversion: **Amps x Volts = Watts**.


Common Miniature Base Types

  Axial Prefocus	  BA7S	  BA9s - Miniature Bay	  BA15s - SC Bayonet	  BA20d	  BA20s	  BAY15d - DC Bayonet Indexed
 D.F. Wedge	 End Cap  Fuse Cap SF6/6	 European Bayonet BA55	 European Bayonet BA7S	 Festoon Cap	 Glass Wedge T1 3/4	 Glass Wedge T3 4
 Glass Wedge T5	 HB1/HB5 Axial Prefocus	 HB2 P43t-38 H4 P43t	 HB3 Right Angle Prefocus	 HB4 Right Angle Prefocus	 Knurled Screw	 Micro-Midget Flanged T 3/4
 Midget Flanged T1 3/4	 Midget Grooved T1 3/4	 Midget Screw E5	 Miniature Bayonet BA9S	 Miniature Flanged P13.5s (HPR)	 Miniature Screw E10	 Miniature Wedge
 P14.5s	 P15-3 Double P15D-3	 P15-3 Single P15S-3	 P15D	 P15S	 P36t	 P43t
 P45t	 PK22s	 PX43t	 Right Angle Prefocus	 Rigid Loop	 S.F. Wedge	 Special-Midget Flanged T1 3/4
 Special Screw	 Sub-Midget Flanged T1	 T 3/4 Bi-Pin	 T1 Bi-Pin	 T1 1/4 Bi-Pin	 T1 3/4 Bi-Pin	 X511

► **For General Lighting:**

Step 2: What is the lamp family and sub-family?


1) Use the chart below to determine to which family your lamp belongs.



Step 3: What is the bulb shape?

1) Identify the shape of the bulb.

- “Bulb” refers to the glass portion of the lamp.
- Refer to the diagram for common bulb shapes.



Step 4: What is the base type?

1) Identify the base type - see page 7.












































- The base supports the lamp in the socket and conducts electricity to the filament.
- Refer to the diagrams on the facing page for common base types.

Step 5: What is the voltage and wattage?

- 1) Determine the voltage.
- 2) Determine the wattage.

- This information can usually be found stamped on the base of the bulb.
- If only given amps, remember this conversion: **Amps x Volts = Watts.**

Common General Lighting Base Types

						
Candelabra Screw E12	DC Bayonet BA15D	DC Bayonet - Indexed BAY15D	DC European Bayonet BA22D	DC Prefocus	European Screw E14	Festoon Cap
						
G4	G6.35	Glass Wedge T1 3/4	Glass Wedge T3 1/4	Glass Wedge T5	Intermediate Screw E17	Medium Screw E26
						
Miniature Screw E10	Mogul Screw E39	Rigid Loop	SC Bayonet BA15S	SC Bayonet - Indexed BAY15S	SC Prefocus	Slide #1
						
Slide #2	Slide #3	Slide #5	Slide #6	T1 Bi-Pin	T1 1/4 Bi-Pin	T1 3/4 Bi-Pin
						
G-23	GX23	GX23-2	G24d-1	G24d-2	G24d-3	GX32d-2
						
GX32d-3	G24q-1	G24q-2	G24q-3	GX24q-2	GX24q-3	GX24q-4
						
2G11						

Step 6: What is the color temperature (fluorescents, SoLux)?

1) Determine the color temperature at which the lamp burns.

- Usually represented in one of three ways:

1) Descriptive

- Warm White (WW), Cool White (CW), Daylight (D)

2) Degrees Kelvin (by hundreds)

- 27, 41, 65, etc. (27=2700 degrees Kelvin)

3) Color Rendering Index (CRI) + degrees Kelvin

- 735, 841 (735 = a CRI of approx. 75% and a color temp of 3500 degrees Kelvin)

Step 7: What is the beam spread (MR8, MR11, MR16)?

1) Determine the beam spread (light pattern) of the lamp.

Narrow Spot	NSP - 10 degrees
Spot	SP - 17 degrees
Narrow Flood	NFL - 24 degrees
Medium Flood	MFL - 26 degrees
Flood	FL - 36 degrees
Wide Flood	WFL - 55 degrees

Finding EIKO's Part Number

The easiest way to see if EIKO carries a lamp matching your description is to visit our website and conduct a short, simple search.


Visit us at www.eiko-ltd.com.

- 1) Place your pointer over the "Search" link at the top quick link bar and select "Advanced Search" from the pull down menu.
- 2) Enter as much of the description as you have and click "Search."

A list of lamps matching your description will result. Clicking on an individual item number will give you a more detailed description of each lamp.

If you have another manufacturer's part number...

- 1) Select "Basic Search" from the Search pull down menu on the website.
- 2) Enter the part number and check the "Cross Reference Part Number:"
 - If we have a match already entered in our system, the EIKO part number will be displayed. This database is updated and maintained by EIKO employees on a regular basis and will become more complete over time.
- 3) If a match cannot be found, look up the part number in the other manufacturer's catalogue (either online or hardcopy) and find the lamp specifications.
 - Using the specifications, cross the lamp to an EIKO part number using the above instructions.



Sizing your Lamp

Maximum Overall Diameter (MOD) is given in eighths of an inch (1/8") or 3.2 mm.

For example:
 a PAR20 lamp is 20 eighths of an inch or 2 1/2" (53 mm) in diameter at its maximum dimension.

ColorMaster PRO™ PAR Lamps



Ordering Code	Bar Code	Watts	MOL	Life Hours	Approx Initial Max Beam CP	Approx Initial Lumens	Approx Mean Lumens	CT deg K	CRI	Beam Angle	ANSI Ballast
CMP20/PAR20/FL	07172	20	3.74/95	9000	3500	1200	900	3000	85+	30	M156/O
CMP20/PAR20/SP	07165	20	3.74/95	9000	15000	1200	900	3000	85+	10	M156/O
CMP20/PAR30LN/FL	07174	20	4.92/125	9000	4000	1200	900	3000	85+	30	M156/O
CMP20/PAR30LN/SP	07173	20	4.92/125	9000	24000	1200	900	3000	85+	10	M156/O
CMP35/PAR20/FL	06774	35	3.74/95	10000	5000	2000	1660	3000	85+	30	M130/O
CMP35/PAR20/SP	06773	35	3.74/95	10000	23000	2000	1660	3000	85+	10	M130/O
CMP35/PAR30LN/FL	06776	35	4.92/125	10000	7500	2400	1990	3000	85+	30	M130/O
CMP35/PAR30LN/FL/842	07829	35	4.92/125	10000	7500	2400	1990	4200	85+	30	M130/O
CMP35/PAR30LN/SP	06775	35	4.92/125	10000	44000	2400	1990	3000	85+	10	M130/O
CMP70/PAR30LN/FL	07166	70	4.92/125	10000	10500	4850	3640	3000	85+	40	M139/M98/M143/O
CMP70/PAR30LN/SP	07175	70	4.92/125	10000	68000	4850	3640	3000	85+	10	M139/M98/M143/O
CMP70/PAR38/FL	07177	70	5.43/138	10000	20000	4800	3600	3000	85+	25	M139/M98/M143/O
CMP70/PAR38/SP	07176	70	5.43/138	10000	53000	4800	3600	3000	85+	15	M139/M98/M143/O

ColorMaster PRO™ MR16 Lamps



Ordering Code	Bar Code	Watts	MOL	Life Hours	Approx Initial Max Beam CP	Approx Initial Lumens	Approx Mean Lumens	CT deg K	CRI	Beam Angle	ANSI Ballast
CMP-MR16/20W/NFL/830	07178	20	2.56/65	9000	2900	1200	900	3000	85+	25	M156/O
CMP-MR16/20W/SP/830	07171	20	2.56/65	9000	9000	1200	900	3000	85+	12	M156/O

ColorMaster PRO™ Double-Ended Lamps



Ordering Code	Bar Code	Watts	MOL	Life Hours	Approx Initial Lumens	Approx Mean Lumens	CT deg K	CRI	ANSI Ballast
CMP70/TD/930	07169	70	4.69/119	12000	6500	4875	3000	90	M139/M98/M143/E
CMP70/TD/942	06732	70	4.72/120	15000	7100	5890	4200	90+	M139/M98/M143/E

ColorMaster PRO™ Bi-pin Lamps



Ordering Code	Bar Code	Watts	MOL	Life Hours	Approx Initial Lumens	Approx Mean Lumens	CT deg K	CRI	ANSI Ballast
CMP20/TC/930	07164	20	3.15/80	10000	1750	1320	3000	90	M156/E
CMP20/TM/930	07167	20	2.05/52	10000	1750	1320	3000	90	M156/E
CMP35/T6/930	06630	35	4.33/110	12000	3700	3070	3000	90	M130/E
CMP35/T6/942	06777	35	4.33/110	12000	3700	3070	4200	90+	M130/E
CMP35/TC/930	06955	35	3.15/80	12000	3700	3070	3000	90	M130/E
CMP70/T6/930	06632	70	4.33/110	12000	7200	5980	3000	90	M139/M98/M143/E
CMP70/T6/942	06633	70	4.33/110	12000	7100	5890	4200	90+	M139/M98/M143/E
CMP70/TC/930	06634	70	3.15/80	12000	7200	5980	3000	90	M139/M98/M143/E
CMP150/T6/930	06629	150	4.33/110	12000	15000	12450	3000	90+	M142/E
CMP150/T6/942	07168	150	4.33/110	10000	13000	9750	4000	95	M142/E

ColorMaster PRO™ EDX17 Lamps



Ordering Code	Bar Code	Watts	Shape	Base	MOL	Life Hours
CMP70/C/MP/3K	07281	70	EDX-17	Medium Screw (E26)	5.43/138	16,000
CMP70/C/MP/4K	07284	70	EDX-17	Medium Screw (E26)	5.43/138	20,000
CMP70/MP/3K	07278	70	EDX-17	Medium Screw (E26)	5.43/138	16,000
CMP70/MP/4K	07277	70	EDX-17	Medium Screw (E26)	5.43/138	20,000
CMP100/C/MP/3K	07280	100	EDX-17	Medium Screw (E26)	5.43/138	16,000
CMP100/C/MP/4K	07283	100	EDX-17	Medium Screw (E26)	5.43/138	20,000
CMP100/MP/3K	07279	100	EDX-17	Medium Screw (E26)	5.43/138	16,000
CMP100/MP/4K	07276	100	EDX-17	Medium Screw (E26)	5.43/138	20,000
CMP150/MP/3K	07285	150	EDX-17	Medium Screw (E26)	5.43/138	16,000
CMP150/MP/4K	07282	150	EDX-17	Medium Screw (E26)	5.43/138	20,000

METAL HALIDE & MERCURY VAPOR HID LAMPS



WARNING:

These lamps can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available.

PowerMaster™ Ballasts



Ordering Code	Bar Code	Volts
PM-2X32T8-UNV-IS	07825	120-277VAC
PM-2X32T8-UNV-IS-H	07873	120-277VAC
PM-2X32T8-UNV-IS-L	07872	120-277VAC
PM-2X54T5-UNV-PS	07827	120-277VAC
PM-3X32T8-UNV-IS	07868	120-277VAC
PM-3X32T8-UNV-IS-H	07875	120-277VAC
PM-3X32T8-UNV-IS-L	07874	120-277VAC
PM-4X32T8-UNV-IS	07826	120-277VAC
PM-4X32T8-UNV-IS-L	07876	120-277VAC
PM-4X54T5-UNV-PS	07828	120-277VAC

LED Lamps

LitespanLED® GEN 3

LitespanLED® Linear LED Lamps

T-8 Linear LED

LED Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-9T8/24/41K	07895	9	120-277VAC	T-8	G13	850	23.81/605	1.10/28	50000
LEDP-9T8/24/50K	07896	9	120-277VAC	T-8	G13	850	23.81/605	1.10/28	50000
LEDP-14T8/36/41K	07897	14	120-277VAC	T-8	G13	1100	35.74/908	1.10/28	50000
LEDP-14T8/36/50K	07898	14	120-277VAC	T-8	G13	1100	35.74/908	1.10/28	50000
LEDP-18T8/48/30K	07899	18	120-277VAC	T-8	G13	1700	47.75/1213	1.10/28	50000
LEDP-18T8/48/41K	07900	18	120-277VAC	T-8	G13	1700	47.75/1213	1.10/28	50000
LEDP-18T8/48/50K	07901	18	120-277VAC	T-8	G13	1700	47.75/1213	1.10/28	50000
LEDP-22T8/60/41K	07902	22	120-277VAC	T-8	G13	2100	59.55/1513	1.10/28	50000
LEDP-22T8/60/50K	07903	22	120-277VAC	T-8	G13	2100	59.55/1513	1.10/28	50000
LEDP-24T8/72/41K	07904	24	120-277VAC	T-8	G13	2300	71.37/1813	1.10/28	50000
LEDP-24T8/72/50K	07905	24	120-277VAC	T-8	G13	2300	71.37/1813	1.10/28	50000

T-8 U-Bend LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-18T8U6/41K	07906	18	120-277VAC	T-8	G13	1700	22.00/560	1.10/28	50000
LEDP-18T8U6/50K	07907	18	120-277VAC	T-8	G13	1700	22.00/560	1.10/28	50000

LitespanLED® PAR Lamps

PAR16 LED

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-6WPAR16/FL/830-DIM	07908	6	120	PAR 16	Medium Screw (E26)	370	3.27/83	1.97/50	35,000
LEDP-6WPAR16/FL/841-DIM	07909	6	120	PAR 16	Medium Screw (E26)	385	3.27/83	1.97/50	35,000

PAR20 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-7WPAR20/FL/827-DIM	07910	7	120	PAR 20	Medium Screw (E26)	340	3.34/85	2.48/63	40,000
LEDP-7WPAR20/FL/830-DIM	07886	7	120	PAR 20	Medium Screw (E26)	400	3.34/85	2.48/63	40,000
LEDP-7WPAR20/FL/841-DIM	07911	7	120	PAR 20	Medium Screw (E26)	400	3.34/85	2.48/63	40,000
LEDP-7WPAR20/NFL/827-DIM	07912	7	120	PAR 20	Medium Screw (E26)	320	3.34/85	2.48/63	40,000
LEDP-7WPAR20/NFL/830-DIM	07887	7	120	PAR 20	Medium Screw (E26)	350	3.34/85	2.48/63	40,000
LEDP-7WPAR20/NFL/841-DIM	07913	7	120	PAR 20	Medium Screw (E26)	350	3.34/85	2.48/63	40,000
LEDP-8WPAR20/FL/827-DIM	07952	8	120	PAR 20	Medium Screw (E26)	365	3.42/87	2.48/63	35,000
LEDP-8WPAR20/FL/830-DIM	07953	8	120	PAR 20	Medium Screw (E26)	380	3.42/87	2.48/63	35,000

LED Lamps

LitespanLED® GEN 3

LitespanLED® PAR Lamps

PAR20 LED

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-8WPAR20/FL/841-DIM	07954	8	120	PAR 20	Medium Screw (E26)	395	3.42/87	2.48/63	35,000
LEDP-8WPAR20/NFL/827-DIM	07955	8	120	PAR 20	Medium Screw (E26)	365	3.42/87	2.48/63	35,000
LEDP-8WPAR20/NFL/830-DIM	07956	8	120	PAR 20	Medium Screw (E26)	380	3.42/87	2.48/63	35,000
LEDP-8WPAR20/NFL/841-DIM	07957	8	120	PAR 20	Medium Screw (E26)	395	3.42/87	2.48/63	35,000

PAR30 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-13WPAR30/FL/827-DIM	07958	13	120	PAR 30	Medium Screw (E26)	680	4.45/113	3.74/95	35,000
LEDP-13WPAR30/FL/830-DIM	07959	13	120	PAR 30	Medium Screw (E26)	700	4.45/113	3.74/95	25,000
LEDP-13WPAR30/FL/841-DIM	07960	13	120	PAR 30	Medium Screw (E26)	730	4.45/113	3.74/95	35,000
LEDP-13WPAR30/NFL/827-DIM	07961	13	120	PAR 30	Medium Screw (E26)	680	4.45/113	3.74/95	35,000
LEDP-13WPAR30/NFL/830-DIM	07962	13	120	PAR 30	Medium Screw (E26)	700	4.45/113	3.74/95	35,000
LEDP-13WPAR30/NFL/841-DIM	07963	13	120	PAR 30	Medium Screw (E26)	730	4.45/113	3.74/95	35,000
LEDP-15WPAR30/FL/827-DIM	07916	15	120	PAR 30	Medium Screw (E26)	780	4.65/118	3.74/95	25,000
LEDP-15WPAR30/FL/830-DIM	07889	15	120	PAR 30	Medium Screw (E26)	800	4.65/118	3.74/95	25,000
LEDP-15WPAR30/FL/841-DIM	07920	15	120	PAR 30	Medium Screw (E26)	810	4.65/118	3.74/95	25,000
LEDP-15WPAR30/NFL/827-DIM	07914	15	120	PAR 30	Medium Screw (E26)	730	4.65/118	3.74/95	25,000
LEDP-15WPAR30/NFL/830-DIM	07888	15	120	PAR 30	Medium Screw (E26)	750	4.65/118	3.74/95	25,000
LEDP-15WPAR30/NFL/841-DIM	07915	15	120	PAR 30	Medium Screw (E26)	760	4.65/118	3.74/95	25,000

PAR38 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-20WPAR38/FL/827-DIM	07921	20	120	PAR 38	Medium Screw (E26)	1050	5.12/130	4.72/120	25,000
LEDP-20WPAR38/FL/830-DIM	07891	20	120	PAR 38	Medium Screw (E26)	1100	5.12/130	4.72/120	25,000
LEDP-20WPAR38/FL/841-DIM	07922	20	120	PAR 38	Medium Screw (E26)	1250	5.00/127	4.76/121	35,000
LEDP-20WPAR38/NFL/827-DIM	07923	20	120	PAR 38	Medium Screw (E26)	1150	5.12/130	4.72/120	25,000
LEDP-20WPAR38/NFL/830-DIM	07890	20	120	PAR 38	Medium Screw (E26)	1200	5.12/130	4.72/120	25,000
LEDP-20WPAR38/NFL/841-DIM	07924	20	120	PAR 38	Medium Screw (E26)	1250	5.12/130	4.72/120	25,000

LitespanLED® Decorative Lamps

A19 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-8WA19/827-DIM3	07964	8	120	A-19	Medium Screw (E26)	435	4.25/108	2.28/58	25,000
LEDP-8WA19/830-DIM3	07965	8	120	A-19	Medium Screw (E26)	450	4.25/108	2.28/58	25,000
LEDP-8WA19/841-DIM3	07966	8	120	A-19	Medium Screw (E26)	470	4.25/108	2.28/58	25,000
LEDP-12WA19/827-DIM	07917	12	120	A-19	Medium Screw (E26)	800	4.65/118	2.36/60	25,000
LEDP-12WA19/830-DIM	07918	12	120	A-19	Medium Screw (E26)	800	4.65/118	2.36/60	25,000

LED Lamps

LitespanLED® GEN 3

LitespanLED® Decorative Lamps

B11 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-3.5WB11/827-DIM	07946	3.5	120	B-11	Candelabra Screw (E12)	175	3.78/96	1.374/34.9	25,000
LEDP-3.5WB11/830-DIM	07947	3.5	120	B-11	Candelabra Screw (E12)	180	3.78/96	1.374/34.9	25,000
LEDP-5WB11/827-DIM	07925	5	120	B-11	Candelabra Screw (E12)	300	4.21/107	1.38/35	25,000
LEDP-5WB11/830-DIM	07893	5	120	B-11	Candelabra Screw (E12)	300	4.21/107	1.38/35	25,000

G25 LED

LED Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-8WG25/827-DIM	07929	8	120	G-25	Medium Screw (E26)	480	4.72/120	3.11/79	40,000
LEDP-8WG25/830-DIM	07894	8	120	G-25	Medium Screw (E26)	500	4.72/120	3.11/79	40,000

LitespanLED® BR/R & MR LED Lamps

BR/R30 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-11WR30/827-DIM	07948	11	120	R-30	Medium Screw (E26)	730	5.12/130	3.74/95	35,000
LEDP-11WR30/830-DIM	07949	11	120	R-30	Medium Screw (E26)	750	5.12/130	3.74/95	35,000
LEDP-11WR30/GU24/827-DIM	07950	11	120	R-30	GU24	730	4.49/114	3.74/95	35,000
LEDP-11WR30/GU24/830-DIM	07951	11	120	R-30	GU24	750	4.49/114	3.74/95	35,000
LEDP-15WBR30/827-DIM	07919	15	120	BR-30	Medium Screw (E26)	865	5.28/134	3.74/95	40,000
LEDP-15WBR30/830-DIM	07892	15	120	BR-30	Medium Screw (E26)	865	5.28/134	3.74/95	40,000

MR16 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-6WGU10/830-DIM	07926	6	120	MR16	GU10	320	2.24/57	1.95/50	40,000
LEDP-6WMR16/827-DIM	07943	6	12V AC/DC	MR16	GU5.3	340	2.40/61	1.97/50	35,000
LEDP-6WMR16/830-DIM	07927	6	12	MR16	GU5.3	320	1.95/50	1.95/50	40,000

LitespanLED® GEN 2

LitespanLED® Decorative Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-2.5G25/830	07700	2.5	120	G-25	Medium Screw (E26)	80	3.78/96	2.56/65	40,000
LEDP-2B11/830	07698	2	120	B-11	Candelabra Screw (E12)	60	3.94/100	1.38/35	40,000
LEDP-2G16.5/830	07699	2	120	G-16.5	Medium Screw (E26)	75	2.95/75	1.97/50	40,000
LEDP-8WA19/830-DIM	07075	7.5	120	A-19	Medium Screw (E26)	410	4.13/105	2.36/60	40,000
LEDP-8WA19/840-DIM	07079	7.5	120	A-19	Medium Screw (E26)	440	4.13/105	2.36/60	40,000

LitespanLED® PAR Lamps

PAR20 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-5PAR20/FL/830-DIM	07695	5.5	120	PAR 20	Medium Screw (E26)	235	3.35/85	2.48/63	40,000
LEDP-5PAR20/FL/840-DIM	07697	5.5	120	PAR 20	Medium Screw (E26)	255	3.35/85	2.48/63	40,000
LEDP-5PAR20/SP/830-DIM	07694	5.5	120	PAR 20	Medium Screw (E26)	235	3.35/85	2.48/63	40,000
LEDP-5PAR20/SP/840-DIM	07696	5.5	120	PAR 20	Medium Screw (E26)	255	3.35/85	2.48/63	40,000

LED Lamps

LitespanLED® GEN 2

LitespanLED® PAR Lamps

PAR30 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-9WPAR30/FL/830-DIM	07088	9	120	PAR 30	Medium Screw (E26)	480	4.65/118	3.74/95	40,000
LEDP-9WPAR30/FL/840-DIM	07092	9	120	PAR 30	Medium Screw (E26)	530	4.65/118	3.74/95	40,000
LEDP-9WPAR30/SP/830-DIM	07080	9	120	PAR 30	Medium Screw (E26)	480	4.65/118	3.74/95	40,000
LEDP-9WPAR30/SP/840-DIM	07091	9	120	PAR 30	Medium Screw (E26)	530	4.65/118	3.74/95	40,000

PAR38 LED



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-11WPAR38/FL/830-DIM	07098	11	120	PAR 38	Medium Screw (E26)	610	5.12/130	4.72/120	40,000
LEDP-11WPAR38/FL/840-DIM	07101	11	120	PAR 38	Medium Screw (E26)	680	5.12/130	4.72/120	40,000
LEDP-11WPAR38/SP/830-DIM	07094	11	120	PAR 38	Medium Screw (E26)	610	5.12/130	4.72/120	40,000
LEDP-11WPAR38/SP/840-DIM	07100	11	120	PAR 38	Medium Screw (E26)	680	5.12/130	4.72/120	40,000

LitespanLED® MR16 LED Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-3W/MR16/830	07067	3.5	12V AC/DC	MR16	GU5.3	170	1.97/50	1.97/50	40,000
LEDP-4W/GU10/FL/830	01047	3.5	120	MR16	GU10	170	2.17/55	1.97/50	25,000

LitespanLED® Linear LED Refit Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-T848-SS15AC-30K	06792	15	AC85V-165V	T-8	G13	1400	48/1219	1.0/26	40,000
LEDP-T848-SS15AC-41K	06722	15	AC85V-165V	T-8	G13	1600	48/1219	1.0/26	40,000

Original LitespanLED® Lamps

LED PAR Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	MOL	MOD	Life Hours
LEDP-7x2WPAR30/15D/41K/C/DIM	06628	12	120	PAR 30	Medium Screw (E26)	501	3.94/100	3.74/95	30,000
LEDP-9x3WPAR38/15D/30K/C/DIM	06623	15	120	PAR 38	Medium Screw (E26)	876	4.83/122.7	4.8/122	30,000
LEDP-9x3WPAR38/15D/41K/C/DIM	06624	15	120	PAR 38	Medium Screw (E26)	730	4.83/122.7	4.8/122	30,000
LEDP-9x3WPAR38/45D/41K/C/DIM	06620	15	120	PAR 38	Medium Screw (E26)	886	4.83/122.7	4.8/122	30,000
LEDP/PAR30LN-SP-30K	05775	12	120-240VAC	PAR 30LN	Medium Screw (E26)	260	4.76/121	3.54/90	50,000

Miniature Replacement LED Lamps



Ordering Code	Bar Code	Shape	Base	Life Hours	Emitted Color	Replaces
LED-6-BA9S-W	05742	T-3 1/4	Miniature Bayonet (BA9s)	30,000	White	6MB, 44, 47, 238, 755, 1810, 1847, 1866
LED-6-T1.75 WEDGE-W	02715	T-1 3/4	Sub-Miniature Wedge (W2.1x4.6d)	30,000	White	56, 79, 84, 86
LED-6-T1.75 WEDGE-Y	02716	T-1 3/4	Sub-Miniature Wedge (W2.1x4.6d)	30,000	Yellow	56, 79, 84, 86
LED-12-DCBAY-R	05378	S-8	DC Index Bayonet (BAY15d)	10,000	Red	DC Index Bayonet Base 12V S8 Lamps
LED-12-DCBAY-W	05379	S-8	DC Index Bayonet (BAY15d)	10,000	White	DC Index Bayonet Base 12V S8 Lamps

LED Lamps

Miniature Replacement LED Lamps

Ordering Code	Bar Code	Shape	Base	Life Hours	Emitted Color	Replaces
LED-12-FESTOON-W	05385	Festoon 10mm	SV8.5mm	30,000	White	10 x 44 Xenon Festoons
LED-12-SCBAY-R	05391	S-8	SC Bayonet (BA15s)	10,000	Red	SC Bayonet Base 12V S8 Lamps
LED-12-SCBAY-W	05394	S-8	SC Bayonet (BA15s)	10,000	White	SC Bayonet Base 12V S8 Lamps
LED-14-BA9S-G	02687	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Green	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893
LED-14-BA9S-R	02688	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Red	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893
LED-14-BA9S-W	02689	T-3 1/4	Miniature Bayonet (BA9s)	30,000	White	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893
LED-14-T1.75 WEDGE-W	02691	T-1 3/4	Sub-Miniature Wedge (W2.1x4.6d)	30,000	White	18, 37, 70, 73, 74
LED-24-BA9S-G	02693	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Green	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1829, 1843, 1864, 1873
LED-24-BA9S-R	02694	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Red	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1829, 1843, 1864, 1873
LED-24-BA9S-W	02695	T-3 1/4	Miniature Bayonet (BA9s)	30,000	White	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1843, 1829, 1864, 1873
LED-24-BA9S-Y	02696	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Yellow	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1843, 1829, 1864, 1873
LED-24-FESTOON-W	05377	Festoon 10mm	SV8.5mm	30,000	White	10 x 44 Xenon Festoons
LED-24-MF-R	02697	T-1 3/4	Midget Flanged (SX6s)	30,000	Red	327, 376, 385, 387, 7341
LED-24-MF-W	02698	T-1 3/4	Midget Flanged (SX6s)	30,000	White	327, 376, 385, 387, 7341
LED-24-MF-Y	02699	T-1 3/4	Midget Flanged (SX6s)	30,000	Yellow	327, 376, 385, 387, 7341
LED-24-MG-R	02701	T-1 3/4	Midget Grooved (S5.7s)	30,000	Red	276, 334, 388
LED-24-MG-W	02702	T-1 3/4	Midget Grooved (S5.7s)	30,000	White	276, 334, 388
LED-24-MG-Y	02703	T-1 3/4	Midget Grooved (S5.7s)	30,000	Yellow	276, 334, 388
LED-24-PSB-G	02704	T-2	Slide Base 5 (TS5)	30,000	Green	24PSB5, 28PSB5
LED-24-PSB-R	02705	T-2	Slide Base 5 (TS5)	30,000	Red	24PSB5, 28PSB5
LED-24-PSB-W	02706	T-2	Slide Base 5 (TS5)	30,000	White	24PSB5, 28PSB5
LED-24-PSB-Y	02707	T-2	Slide Base 5 (TS5)	30,000	Yellow	24PSB5, 28PSB5
LED-24-T1.75 WEDGE-G	02708	T-1 3/4	Sub-Miniature Wedge (W2.1x4.6d)	30,000	Green	17, 85
LED-24-T1.75 WEDGE-R	02709	T-1 3/4	Sub-Miniature Wedge (W2.1x4.6d)	30,000	Red	17, 85
LED-24-T1.75 WEDGE-W	02711	T-1 3/4	Sub-Miniature Wedge (W2.1x4.6d)	30,000	White	17, 85
LED-24-T1.75 WEDGE-Y	02712	T-1 3/4	Sub-Miniature Wedge (W2.1x4.6d)	30,000	Yellow	17, 85
LED-120-MB-G	02678	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Green	120MB, 120MB-6, 130MB, 8-3995, 949, 967
LED-120-MB-R	02679	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Red	120MB, 120MB-6, 130MB, 8-3995, 949, 967
LED-120-MB-W	02681	T-3 1/4	Miniature Bayonet (BA9s)	30,000	White	120MB, 120MB-6, 130MB, 8-3995, 949, 967
LED-120-MB-Y	02682	T-3 1/4	Miniature Bayonet (BA9s)	30,000	Yellow	120MB, 120MB-6, 130MB, 8-3995, 949, 967
LED-120-PSB-G	02683	T-2	Slide Base 5 (TS5)	30,000	Green	120PSB5, 120PSB-Neon
LED-120-PSB-R	02684	T-2	Slide Base 5 (TS5)	30,000	Red	120PSB5, 120PSB-Neon
LED-120-PSB-W	02685	T-2	Slide Base 5 (TS5)	30,000	White	120PSB5, 120PSB-Neon
LED-120-PSB-Y	02686	T-2	Slide Base 5 (TS5)	30,000	Yellow	120PSB5, 120PSB-Neon
LED-194-R	00346	T-3 1/4	Miniature Wedge (W2.1x9.5d)	30,000	Red	T3-1/4 Min Wedge Based Lamps 12/14V
LED-194-W	00345	T-3 1/4	Miniature Wedge (W2.1x9.5d)	30,000	White	T3-1/4 Min Wedge Based Lamps 12/14V
LEDP-1383/30K	07797	MR11	SC Bayonet (BA15s)	30,000	Warm White	
LEDP-1383/41K	07798	MR11	SC Bayonet (BA15s)	30,000	Cool White	

HID Lamps

HID Lamps

Metal Halide HID Lamps

Medium & Mogul Based Metal Halide HID Lamps



Ordering Code	Bar Code	Shape	Base	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
MH50/C/U/MED	49187	ED-17	Medium Screw (E26)	50	5.50/139.7	3700	10000	M110	3000
MH50/U/MED	49188	ED-17	Medium Screw (E26)	50	5.50/139.7	4000	10000	M110	3400
MH70/C/U/MED	49189	ED-17	Medium Screw (E26)	70	5.50/139.7	3700	15000	M98	5300
MH70/U/MED	15410	ED-17	Medium Screw (E26)	70	5.50/139.7	4000	15000	M98	5600
MH100/C/U/MED	49190	ED-17	Medium Screw (E26)	100	5.50/139.7	3700	15000	M90	8500
MH100/U/MED	15411	ED-17	Medium Screw (E26)	100	5.50/139.7	4000	15000	M90	9000
MH150/C/U/MED	49191	ED-17	Medium Screw (E26)	150	5.50/139.7	3700	15000	M102	13300
MH150/U/MED	15413	ED-17	Medium Screw (E26)	150	5.50/139.7	4000	15000	M102	14000
MH175/C/U	49194	ED-28	Mogul Screw (E39)	175	8.3/211.2	3700	10000	M57	13300
MH175/C/U/MED	49192	ED-17	Medium Screw (E26)	175	5.50/139.7	3700	10000	M57	13300
MH175/U	49193	ED-28	Mogul Screw (E39)	175	8.3/211.2	4000	10000	M57	14000
MH175/U/MED	15414	ED-17	Medium Screw (E26)	175	5.50/139.7	4000	10000	M57	14000

HID Lamps

Metal Halide HID Lamps

Medium & Mogul Based Metal Halide HID Lamps

Ordering Code	Bar Code	Shape	Base	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
MH200/C/U	49530	ED-28	Mogul Screw (E39)	200	8.3/211.2	3700	15000	M136	20000
MH200/U	49529	ED-28	Mogul Screw (E39)	200	8.3/211.2	4000	15000	M136	21000
MH250/C/U	49196	ED-28	Mogul Screw (E39)	250	8.3/211.2	3700	10000	M58	20000
MH250/U	49195	ED-28	Mogul Screw (E39)	250	8.3/211.2	4000	10000	M58	21000
MH250/U/T15	49531	T-15	Mogul Screw (E39)	250	9.75/247.7	4000	10000	M58	21000
MH320/U	81052	ED-28	Mogul Screw (E39)	320	8.3/211.2	4000	20000	M154/M132/E	31000
MH350/HOR	49532	ED-28	Mogul Screw (E39)	350	8.3/211.2	4000	20000	M131	33000
MH400/C/U	49198	ED-37	Mogul Screw (E39)	400	11.5/292.1	3700	20000	M59	34000
MH400/C/U/ED28	49556	ED-28	Mogul Screw (E39)	400	8.3/211.2	3700	20000	M59	34000
MH400/U	49197	ED-37	Mogul Screw (E39)	400	11.5/292.1	4000	20000	M59	36000
MH400/U/ED28	49463	ED-28	Mogul Screw (E39)	400	8.3/211.2	4000	20000	M59	36000
MH400/U/T15	49534	T-15	Mogul Screw (E39)	400	9.75/247.7	4000	15000	M59	36000
MH1000/C/U	49200	BT-56	Mogul Screw (E39)	1000	15.5/393.7	3700	12000	M47	105000
MH1000/U	49199	BT-56	Mogul Screw (E39)	1000	15.5/393.7	4000	12000	M47	110000
MH1000/U/BT37	49557	BT-37	Mogul Screw (E39)	1000	11.5/292.1	4000	12000	M47	110000
MH1500/U	49201	BT-56	Mogul Screw (E39)	1500	15.5/393.7	4000	3500	M48	155000

Pulse Start Metal Halide HID Lamps



Ordering Code	Bar Code	Shape	Base	Special Desc	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
MH-DE70/TD/UVS/3K	15406	T-6	Recessed Single Contact (R7s)	Pulse Start & UV Shielded	70	4.50/114.3	3000	10000	M85/M98	5200
MH-DE70/TD/UVS/4K	15407	T-6	Recessed Single Contact (R7s)	Pulse Start & UV Shielded	70	4.50/114.3	4200	10000	M85/M98	5500
MH-DE150/TD/UVS/3K	15408	T-7	Recessed Single Contact (R7s)	Pulse Start & UV Shielded	150	5.19/131.8	3000	10000	M81/M102	11250
MH-DE150/TD/UVS/4K	15409	T-7	Recessed Single Contact (R7s)	Pulse Start & UV Shielded	150	5.19/131.8	4200	10000	M81/M102	11250
MH-SE70/UVS/3K	49183	T-7	G12	Pulse Start & UV Shielded	70	4.25/108.0	3000	10000	M85/M98	5600
MH-SE150/UVS/3K	49185	T-7	G12	Pulse Start & UV Shielded	150	4.25/108.0	3000	10000	M81/M102	14000
MH-SE150/UVS/4K	49186	T-7	G12	Pulse Start & UV Shielded	150	4.25/108.0	4000	10000	M81/M102	14000
MH50/C/U/MED	49187	ED-17	Medium Screw (E26)	Pulse Start	50	5.50/139.7	3700	10000	M110	3000
MH50/U/MED	49188	ED-17	Medium Screw (E26)	Pulse Start	50	5.50/139.7	4000	10000	M110	3400
MH70/C/U/MED	49189	ED-17	Medium Screw (E26)	Pulse Start	70	5.50/139.7	3700	15000	M98	5300
MH70/U/MED	15410	ED-17	Medium Screw (E26)	Pulse Start	70	5.50/139.7	4000	15000	M98	5600
MH100/C/U/MED	49190	ED-17	Medium Screw (E26)	Pulse Start	100	5.50/139.7	3700	15000	M90	8500
MH100/U/MED	15411	ED-17	Medium Screw (E26)	Pulse Start	100	5.50/139.7	4000	15000	M90	9000
MH150/C/U/MED	49191	ED-17	Medium Screw (E26)	Pulse Start	150	5.50/139.7	3700	15000	M102	13300
MH150/U/MED	15413	ED-17	Medium Screw (E26)	Pulse Start	150	5.50/139.7	4000	15000	M102	14000
MH200/C/U	49530	ED-28	Mogul Screw (E39)	Pulse Start	200	8.3/211.2	3700	15000	M136	20000
MH200/U	49529	ED-28	Mogul Screw (E39)	Pulse Start	200	8.3/211.2	4000	15000	M136	21000
MH250/BU/PS	06745	ED-28	Mogul Screw (E39)	Pulse Start	250	8.3/211.2	4000	12000	M153/M138/E	25000
MH320/U	81052	ED-28	Mogul Screw (E39)	Pulse Start	320	8.3/211.2	4000	20000	M154/M132/E	31000
MH350/C/HOR	49533	ED-28	Mogul Screw (E39)	Pulse Start	350	8.3/211.2	3700	20000	M131	31000
MH350/HOR	49532	ED-28	Mogul Screw (E39)	Pulse Start	350	8.3/211.2	4000	20000	M131	33000
MH400/BU/PS	06746	ED-37	Mogul Screw (E39)	Pulse Start	400	11.5/292.1	4000	20000	M155/M128/M135/E	41000
MH400/C/BU/PS	06747	ED-37	Mogul Screw (E39)	Pulse Start	400	11.5/292.1	3700	20000	M155/M128/M135/E	41000
MP50/U/MED/3K	44501	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	50	5.5/139.7	3200	10000	M110	3200
MP70/C/U/MED/3K	49506	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	70	5.5/139.7	3200	15000	M98	5000
MP70/C/U/MED/4K	49508	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	70	5.5/139.7	3700	15000	M98	5000
MP70/U/MED/4K	49509	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	70	5.5/139.7	4000	15000	M98	5300
MP100/C/U/MED/3K	49511	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	100	5.5/139.7	3200	15000	M90	8100
MP100/C/U/MED/4K	49513	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	100	5.5/139.7	3700	15000	M90	8100

HID Lamps

Metal Halide HID Lamps

Pulse Start Metal Halide HID Lamps

Ordering Code	Bar Code	Shape	Base	Special Desc	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
MP100/U/MED/3K	49512	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	100	5.5/139.7	3200	15000	M90	8500
MP100/U/MED/4K	49514	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	100	5.5/139.7	4000	15000	M90	8500
MP150/C/U/MED/3K	49516	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	150	5.5/139.7	3200	15000	M102	12600
MP150/C/U/MED/4K	49518	EDX-17	Medium Screw (E26)	Pulse Start & UV Shielded	150	5.5/139.7	3700	15000	M102	12600
MP250/BU/P	06683	ED-28	Mogul Screw with Long Prong (EX39)	Pulse Start & UV Shielded	250	8.3/211.2	4000	12000	M153/M138/O	25000
MP320/BU	81053	ED-28	Mogul Screw with Long Prong (EX39)	Pulse Start & UV Shielded	320	8.3/211.2	4000	20000	M154/M132/O	31000
MP350/BU	49538	ED-28	Mogul Screw with Long Prong (EX39)	Pulse Start & UV Shielded	350	8.3/211.2	4000	20000	M131	35000
MP400/BU/ED28/P	06479	ED-28	Mogul Screw with Long Prong (EX39)	Pulse Start & UV Shielded	400	8.86/225	4000	20000	M155/M128/M135/O	41000
MP400/BU/P	06276	ED-37	Mogul Screw with Long Prong (EX39)	Pulse Start & UV Shielded	400	11.73/296	4000	20000	M155/M128/M135/O	41000

Open Fixture Rated Metal Halide HID Lamps



Ordering Code	Bar Code	Shape	Base	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
MP50/U/MED/3K	44501	EDX-17	Medium Screw (E26)	50	5.5/139.7	3200	10000	M110	3200
MP70/C/U/MED/3K	49506	EDX-17	Medium Screw (E26)	70	5.5/139.7	3200	15000	M98	5000
MP70/C/U/MED/4K	49508	EDX-17	Medium Screw (E26)	70	5.5/139.7	3700	15000	M98	5000
MP70/U/MED/3K	49507	EDX-17	Medium Screw (E26)	70	5.5/139.7	3200	15000	M98	5300
MP70/U/MED/4K	49509	EDX-17	Medium Screw (E26)	70	5.5/139.7	4000	15000	M98	5300
MP100/C/U/MED/3K	49511	EDX-17	Medium Screw (E26)	100	5.5/139.7	3200	15000	M90	8100
MP100/C/U/MED/4K	49513	EDX-17	Medium Screw (E26)	100	5.5/139.7	3700	15000	M90	8100
MP100/U/MED/3K	49512	EDX-17	Medium Screw (E26)	100	5.5/139.7	3200	15000	M90	8500
MP100/U/MED/4K	49514	EDX-17	Medium Screw (E26)	100	5.5/139.7	4000	15000	M90	8500
MP150/C/U/MED/3K	49516	EDX-17	Medium Screw (E26)	150	5.5/139.7	3200	15000	M102	12600
MP150/C/U/MED/4K	49518	EDX-17	Medium Screw (E26)	150	5.5/139.7	3700	15000	M102	12600
MP150/U/MED/3K	49517	EDX-17	Medium Screw (E26)	150	5.5/139.7	3200	15000	M102	13300
MP150/U/MED/4K	49519	EDX-17	Medium Screw (E26)	150	5.5/139.7	4000	15000	M102	13300
MP250/BU/P	06683	ED-28	Mogul Screw with Long Prong (EX39)	250	8.3/211.2	4000	12000	M153/M138/O	25000
MP320/BU	81053	ED-28	Mogul Screw with Long Prong (EX39)	320	8.3/211.2	4000	20000	M154/M132/O	31000
MP350/BU	49538	ED-28	Mogul Screw with Long Prong (EX39)	350	8.3/211.2	4000	20000	M131	35000
MP400/BU/ED28/P	06479	ED-28	Mogul Screw with Long Prong (EX39)	400	8.86/225	4000	20000	M155/M128/M135/O	41000
MP400/BU/P	06276	ED-37	Mogul Screw with Long Prong (EX39)	400	11.73/296	4000	20000	M155/M128/M135/O	41000

Double Ended Metal Halide HID Lamps



Ordering Code	Bar Code	Shape	Base	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
MH-DE70/TD/UVS/3K	15406	T-6	Recessed Single Contact (R7s)	70	4.50/114.3	3000	10000	M85/M98	5200
MH-DE70/TD/UVS/4K	15407	T-6	Recessed Single Contact (R7s)	70	4.50/114.3	4200	10000	M85/M98	5500
MH-DE150/TD/UVS/3K	15408	T-7	Recessed Single Contact (R7s)	150	5.19/131.8	3000	10000	M81/M102	11250
MH-DE150/TD/UVS/4K	15409	T-7	Recessed Single Contact (R7s)	150	5.19/131.8	4200	10000	M81/M102	11250

Single Ended Metal Halide HID Lamps



Ordering Code	Bar Code	Shape	Base	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
MH-SE70/UVS/3K	49183	T-7	G12	70	4.25/108.0	3000	10000	M85/M98	5600
MH-SE150/UVS/3K	49185	T-7	G12	150	4.25/108.0	3000	10000	M81/M102	14000
MH-SE150/UVS/4K	49186	T-7	G12	150	4.25/108.0	4000	10000	M81/M102	14000

HID Lamps

High Pressure Sodium HID Lamps



Ordering Code	Bar Code	Shape	Base	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
LU35/MED	15300	ED-17	Medium Screw (E26)	35	5.44/138.0	2100	16000	S76	2250
LU50	15304	ED-23.5	Mogul Screw (E39)	50	7.75/196.9	2100	24000	S68	4000
LU50/MED	15302	ED-17	Medium Screw (E26)	50	5.44/138.0	2100	24000	S68	4000
LU70	15308	ED-23.5	Mogul Screw (E39)	70	7.75/196.9	2100	24000	S62	6300
LU70/D/MED	49157	ED-17	Medium Screw (E26)	70	5.44/138.0	2100	24000	S62	5860
LU70/MED	15306	ED-17	Medium Screw (E26)	70	5.44/138.0	2100	24000	S62	6300
LU100	15312	ED-23.5	Mogul Screw (E39)	100	7.75/196.9	2100	24000	S54	9500
LU100/MED	15310	ED-17	Medium Screw (E26)	100	5.44/138.0	2100	24000	S54	9500
LU150/55	15316	ED-23.5	Mogul Screw (E39)	150	7.75/196.9	2100	24000	S55	16000
LU150/55/D/MED	49161	ED-17	Medium Screw (E26)	150	5.44/138.0	2100	24000	S55	15000
LU150/55/MED	15314	ED-17	Medium Screw (E26)	150	5.44/138.0	2100	24000	S55	16000
LU150/100	15318	ED-28	Mogul Screw (E39)	150	8.31/211.1	2100	24000	S56	16000
LU200	15319	ED-18	Mogul Screw (E39)	200	9.75/247.6	2100	24000	S66	22000
LU250	15320	ED-18	Mogul Screw (E39)	250	9.75/247.6	2100	24000	S50	28500
LU250/D	49164	ED-28	Mogul Screw (E39)	250	8.31/211.1	2100	24000	S50	26000
LU400	15322	ED-18	Mogul Screw (E39)	400	9.75/247.6	2100	24000	S51	50000
LU600	49167	T-14.5	Mogul Screw (E39)	600	11.13/282.6	2100	24000	S106	90000
LU1000	15324	E-25	Mogul Screw (E39)	1000	15.06/382.6	2100	24000	S52	140000

Mercury Vapor HID Lamps



Ordering Code	Bar Code	Shape	Base	Watts	MOL	CT deg K	Life Hours	ANSI Ballast	Approx Initial Lumens
H33CD-400	15360	ED-37	Mogul Screw (E39)	400	11.50/292.1	6500	18000	H33	21000
H33GL-400/DX	15359	ED-37	Mogul Screw (E39)	400	11.50/292.1	3700	18000	H33	22050
H37KB-250	15358	ED-28	Mogul Screw (E39)	250	8.31/211.1	6700	18000	H37	11000
H37KC-250/DX	15357	ED-28	Mogul Screw (E39)	250	8.31/211.1	3700	18000	H37	11550
H38AV-100/DX	00332	ED-17	Medium Screw (E26)	100	5.44/138.0	3900	12000	H38	4000
H38JA-100/DX	15353	ED-23.5	Mogul Screw (E39)	100	7.50/190.5	3200	12000	H38	4100
H38MP-100/DX	49168	A-23	Medium Screw (E26)	100	5.44/138.0	3700	12000	H38	4000
H39KB-175	15356	ED-28	Mogul Screw (E39)	175	8.31/211.1	6800	12000	H39	7350
H39KC-175/DX	15355	ED-28	Mogul Screw (E39)	175	8.31/211.1	3700	12000	H39	7665
H43AV-75/DX	49564	ED-17	Medium Screw (E26)	75	5.44/138.0	3200	10000	H43	2700
H46DL-40/50/DX	15350	ED-17	Medium Screw (E26)	40/50	5.12/130.0	3200	8000	H45/46	1570

HID Lamps

METAL HALIDE & MERCURY VAPOR HID LAMPS



WARNING:

These lamps can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available.

Fluorescent Lamps

T5ES Retrofit Kit

Ordering Code	Bar Code	Watts	Shape	Base	MOL	Life 3hr Start	Life 12hr Start
T5ES-28115/835	07745	28	T-5	G13	1.85/47	25000	35000
T5ES-28115/841	07746	28	T-5	G13	1.85/47	25000	35000
T5ES-28115/850	07747	28	T-5	G13	1.85/47	25000	35000

CFLi Lamps

High Watt CFLi

Ordering Code	Bar Code	Approvals	mg Hg	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP65/41/MED	05293	UL/CSA, TCLP Compliant	4.8	120	65	Medium Screw (E26)	9.45/240	4100	10000	>80	4300
SP65/50/MED	06659	UL/CSA, TCLP Compliant	4.8	120	65	Medium Screw (E26)	9.45/240	5000	10000	>80	4000
SP85/41/MED	81183	UL/CSA, TCLP Compliant	4.8	120	85	Medium Screw (E26)	9.96/253	4100	10000	>80	5700
SP85/50/MED	81181	UL/CSA, TCLP Compliant	4.8	120	85	Medium Screw (E26)	9.96/253	5000	10000	>80	5350
SP105/41/MED	81184	UL/CSA, TCLP Compliant	4	120	105	Medium Screw (E26)	11.5/292	4100	8000	82	6900
SP105/41/MOG	81185	UL/CSA, TCLP Compliant	4.8	120	105	Mogul Screw (E39)	11.26/286	4100	10000	>80	7000
SP105/41/MOG-277V	04412	TCLP Compliant	4	277	105	Mogul Screw (E39)	12/305	4100	8000	82	6900
SP105/50/MED	81180	UL/CSA, TCLP Compliant	4	120	105	Medium Screw (E26)	11.5/292	5000	8000	82	6900
SP180/41/MOG	07822	UL/CSA, TCLP Compliant	9.2	120	180	Mogul Screw (E39)	14.3/364	4100	10,000	80	11,100
SP180/50/MOG	07823	UL/CSA, TCLP Compliant	9.2	120	180	Mogul Screw (E39)	14.3/364	5000	10,000	80	10,400

Fluorescent Lamps

CFLi Lamps

Spiral Shaped CFLi Lamps

Medium Based Spiral CFLi Lamps



Ordering Code	Bar Code	Approvals	mg Hg	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP13/27K	00031	UL/CSA, Energy Star, TCLP Compliant	2.5	120	13	Medium Screw (E26)	4.50/114	2700	10000	82	900
SP13/35K	00032	UL/CSA, TCLP Compliant	2.5	120	13	Medium Screw (E26)	4.10/104	3500	8000	82	800
SP13/41K	00033	UL/CSA, Energy Star, TCLP Compliant	2.5	120	13	Medium Screw (E26)	4.10/104	4100	10000	82	800
SP13/50K	05667	UL/CSA, TCLP Compliant	2.5	120	13	Medium Screw (E26)	4.10/104	5000	10000	82	800
SP13/65K	06131	UL/CSA, TCLP Compliant	2.5	120	13	Medium Screw (E26)	4.10/104	6500	10000	82	900
SP19/27K	00034	UL/CSA, Energy Star, TCLP Compliant	<4	120	20	Medium Screw (E26)	4.73/120	2700	10000	82	1381
SP19/35K	00035	UL/CSA, TCLP Compliant	<4	120	19	Medium Screw (E26)	4.73/120	3500	10000	82	1200
SP19/41K	00036	UL/CSA, TCLP Compliant	<4	120	20	Medium Screw (E26)	4.73/120	4100	10000	82	1350
SP19/50K	05668	UL/CSA, Energy Star, TCLP Compliant	<4	120	20	Medium Screw (E26)	4.73/120	5000	10000	82	1350
SP19/65K	49324	UL/CSA, TCLP Compliant	<4	120	20	Medium Screw (E26)	5.25/133	6500	8000	82	1150
SP23/27K	49325	UL/CSA, TCLP Compliant	<4	120	23	Medium Screw (E26)	4.96/126	2700	10000	82	1600
SP23/35K	81171	UL/CSA, TCLP Compliant	<4	120	23	Medium Screw (E26)	4.96/126	3500	10000	82	1536
SP23/41K	49326	UL/CSA, TCLP Compliant	<4	120	23	Medium Screw (E26)	4.96/126	4100	10000	82	1472
SP23/50K	81172	UL/CSA, TCLP Compliant	<4	120	23	Medium Screw (E26)	4.96/126	5000	10000	82	1570
SP23/65K	49327	UL/CSA, TCLP Compliant	<4	120	23	Medium Screw (E26)	4.96/126	6500	10,000	82	1600
SP27/27K	05412		1.6		26	Medium Screw (E26)	5.079/129	2700	10000	80	1700
SP27/35K	05413	UL/CSA, TCLP Compliant	<5	120	27	Medium Screw (E26)	5.47/139	3500	10000	80	1700
SP27/41K	05414	UL/CSA, TCLP Compliant	<5	120	26	Medium Screw (E26)	5.47/139	4100	10000	80	1650
SP27/50K	05415		1.6		26	Medium Screw (E26)	5.079/129	5000	10000	80	1700
SP32/27K	05416	UL/CSA, TCLP Compliant	<5	120	31	Medium Screw (E26)	5.63/143	2700	8000	80	1920
SP32/35K	05417	UL/CSA, TCLP Compliant	<5	120	32	Medium Screw (E26)	5.63/143	3500	8000	80	2050
SP32/41K	05418	UL/CSA, TCLP Compliant	<5	120	32	Medium Screw (E26)	5.63/143	4100	8000	80	2050
SP32/50K	05419	UL/CSA, TCLP Compliant	<5	120	32	Medium Screw (E26)	5.63/143	5000	8000	80	2000
SP42/27K	05420	UL/CSA, TCLP Compliant	<5	120	42	Medium Screw (E26)	7.13/181	2700	12000	80	2800
SP42/35K	05421	UL/CSA, TCLP Compliant	<5	120	42	Medium Screw (E26)	7.13/181	3500	10000	80	2750
SP42/41K	05422	UL/CSA, TCLP Compliant	<5	120	42	Medium Screw (E26)	7.13/181	4100	10000	80	2750
SP42/50K	05423	UL/CSA, TCLP Compliant	<5	120	42	Medium Screw (E26)	7.13/181	5000	10000	80	2650
SP65/41/MED	05293	UL/CSA, TCLP Compliant	4.8	120	65	Medium Screw (E26)	9.45/240	4100	10000	>80	4300
SP65/50/MED	06659	UL/CSA, TCLP Compliant	4.8	120	65	Medium Screw (E26)	9.45/240	5000	10000	>80	4000
SP85/41/MED	81183	UL/CSA, TCLP Compliant	4.8	120	85	Medium Screw (E26)	9.96/253	4100	10000	>80	5700
SP85/50/MED	81181	UL/CSA, TCLP Compliant	4.8	120	85	Medium Screw (E26)	9.96/253	5000	10000	>80	5350
SP105/41/MED	81184	UL/CSA, TCLP Compliant	4	120	105	Medium Screw (E26)	11.5/292	4100	8000	82	6900
SP105/50/MED	81180	UL/CSA, TCLP Compliant	4	120	105	Medium Screw (E26)	11.5/292	5000	8000	82	6900

Fluorescent Lamps

Dimmable CFLi Lamps



Ordering Code	Bar Code	Volts	Watts	mg Hg	Special Desc	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP13/27K-DIM	06392	120	13	3.5	Dimmable down to 8%. Use only dimmers rated 600W or lower, made after 1995.	Medium Screw (E26)	4.92/125	2700	8000	80	900
SP13/41K-DIM	06393	120	13	3.5	Dimmable down to 8%. Use only dimmers rated 600W or lower, made after 1995.	Medium Screw (E26)	4.92/125	4100	8000	80	850
SP15/R30/27K-DIM	07879	120	15			Medium Screw (E26)	6.102/155	2700	10000		680

Fluorescent Lamps

CFLi Lamps

Spiral Shaped CFLi Lamps

Dimmable CFLi Lamps

Ordering Code	Bar Code	Volts	Watts	mg Hg	Special Desc	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP15/R30/41K-DIM	07880	120	15			Medium Screw (E26)	6.102/155	4100	10000		680
SP15/R30/50K-DIM	07881	120	15			Medium Screw (E26)	6.102/155	5000	10000		680
SP15/R30/65K-DIM	07882	120	15			Medium Screw (E26)	6.102/155	6500	10000		640
SP19/27K-DIM	06394	120	20	3.5	Dimmable down to 8%. Use only dimmers rated 600W or lower, made after 1995.	Medium Screw (E26)	5.12/130	2700	8000	80	1350
SP19/41K-DIM	06395	120	20	3.5	Dimmable down to 8%. Use only dimmers rated 600W or lower, made after 1995.	Medium Screw (E26)	5.12/130	4100	8000	80	1300
SP23/27K-DIM	06396	120	23	4	Dimmable down to 8%. Use only dimmers rated 600W or lower, made after 1995.	Medium Screw (E26)	5.47/139	2700	8000	80	1550
SP23/41K-DIM	06397	120	23	4	Dimmable down to 8%. Use only dimmers rated 600W or lower, made after 1995.	Medium Screw (E26)	5.47/139	4100	8000	80	1500

Mogul Based Spiral CFLi Lamps



Ordering Code	Bar Code	Volts	Watts	mg Hg	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP105/41/MOG	81185	120	105	4.8	Mogul Screw (E39)	11.26/286	4100	10000	>80	7000
SP105/41/MOG-277V	04412	277	105	4	Mogul Screw (E39)	12/305	4100	8000	82	6900
SP180/41/MOG	07822	120	180	9.2	Mogul Screw (E39)	14.3/364	4100	10,000	80	11,100
SP180/50/MOG	07823	120	180	9.2	Mogul Screw (E39)	14.3/364	5000	10,000	80	10,400

GU24 Based Spiral CFLi Lamps



Ordering Code	Bar Code	Volts	Watts	mg Hg	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP13/27-GU24	05255	120	13	3	GU24	3.74/95	2700	10000	82	900
SP13/27K-GU24-DIM	07701	120	13	1.6	GU24	3.94/100	2700	10000	82	800
SP13/41-GU24	07749	120	13	3	GU24	3.74/95	4100	10000	82	900
SP18/27-GU24	05256	120	18	4	GU24	4.33/110	2700	10000	82	1100
SP18/27K-GU24-DIM	07702	120	18	1.6	GU24	4.37/111	2700	10,000	82	1200
SP18/41-GU24	07750	120	18	4	GU24	4.33/110	4100	10000	82	1100
SP23/27-GU24	07751		23	1.6	GU24	4.409/112	2700	10000	80	1600
SP23/27K-GU24-DIM	07703	120	23	1.6	GU24	4.84/123	2700	10,000	82	1600
SP23/41-GU24	07752	120	23	4	GU24	4.17/106	4100	10000	82	1600
SP26/27-GU24	05258	120	23	4	GU24	4.73/123	2700	10000	82	1900

PAR CFLi Lamps



Ordering Code	Bar Code	Approvals	mg Hg	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
PAR20/9/30K	06281	UL/CSA, Energy Star, TCLP Compliant	1.5	120	9	Medium Screw (E26)	3.82/97	3000	8000	>80	280
PAR20/9/35K	01519	UL/CSA, TCLP Compliant	1.5	120	9	Medium Screw (E26)	3.82/97	3500	8000	>80	272
PAR20/9/41K	06282	UL/CSA, Energy Star, TCLP Compliant	1.5	120	9	Medium Screw (E26)	3.82/97	4100	8000	>80	270
PAR20/9/50K	01521	UL/CSA, TCLP Compliant	1.5	120	9	Medium Screw (E26)	3.82/97	5000	8000	>80	258
PAR30LN/15/30K	06279	UL/CSA, TCLP Compliant	2.5	120	15	Medium Screw (E26)	5.12/130	3000	8000	>80	750
PAR30LN/15/35K	01522	UL/CSA, Energy Star, TCLP Compliant	2.5	120	15	Medium Screw (E26)	5.12/130	3500	8000	>80	728
PAR30LN/15/41K	06280	UL/CSA, Energy Star, TCLP Compliant	2.5	120	15	Medium Screw (E26)	5.12/130	4100	8000	>80	725

Fluorescent Lamps

CFLi Lamps

PAR CFLi Lamps

Ordering Code	Bar Code	Approvals	mg Hg	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
PAR30LN/15/50K	01523	UL/CSA, Energy Star, TCLP Compliant	2.5	120	15	Medium Screw (E26)	5.12/130	5000	8000	>80	745
PAR38/23/27K	01046	UL/CSA, TCLP Compliant	2.5	120	23	Medium Screw (E26)	5.51/140	2700	8000	>80	1250
PAR38/23/30	06277	UL/CSA, Energy Star, TCLP Compliant	2.5	120	23	Medium Screw (E26)	5.51/140	3000	8000	>80	1200
PAR38/23/35K	01526	UL/CSA, TCLP Compliant	2.5	120	23	Medium Screw (E26)	5.51/140	3500	8000	>80	1200
PAR38/23/41K	06278	UL/CSA, Energy Star, TCLP Compliant	2.5	120	23	Medium Screw (E26)	5.51/140	4100	8000	>80	1210
PAR38/23/50K	01531	UL/CSA, Energy Star, TCLP Compliant	2.5	120	23	Medium Screw (E26)	5.51/140	5000	8000	>80	1200

R-Shaped CFLi Lamps



Ordering Code	Bar Code	Volts	Watts	mg Hg	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP14/R20/27K	06390	120	14	3.5	Medium Screw (E26)	4.88/124	2700	10,000	82	500
SP14/R20/41K	06391	120	14	3.5	Medium Screw (E26)	4.88/124	4100	8000	82	450
SP15/R30/27K	49365	120	15	2.5	Medium Screw (E26)	5.47/139	2700	10000	82	750
SP15/R30/27K-DIM	07879	120	15		Medium Screw (E26)	6.102/155	2700	10000		680
SP15/R30/27K-GU24	07733	120	15	1.6	GU24	4.45/113	2700	10,000	>80	690
SP15/R30/41K	49366	120	15	1.6	Medium Screw (E26)	5.394/137	4100	10000	80	700
SP15/R30/41K-DIM	07880	120	15		Medium Screw (E26)	6.102/155	4100	10000		680
SP15/R30/50K-DIM	07881	120	15		Medium Screw (E26)	6.102/155	5000	10000		680
SP15/R30/65K	49367	120	15	2.5	Medium Screw (E26)	5.47/139	6500	8000	82	700
SP15/R30/65K-DIM	07882	120	15		Medium Screw (E26)	6.102/155	6500	10000		640
SP23/R40/27K	49371	120	23	2.5	Medium Screw (E26)	6.6/167	2700	8000	82	1200
SP23/R40/27K-DIM	07704	120	23	1.6	Medium Screw (E26)	7.01/178	2700	10000		1090
SP23/R40/41K	49372	120	23	2.5	Medium Screw (E26)	6.6/167	4100	8000	82	1150
SP23/R40/41K-DIM	07705	120	23	1.6	Medium Screw (E26)	7.01/178	4100	10000		1090
SP23/R40/50K-DIM	07706	120	23	1.6	Medium Screw (E26)	7.01/178	5000	10000		1050
SP23/R40/65K	49373	120	23	2.5	Medium Screw (E26)	6.6/167	6500	8000	82	1100

Fluorescent Lamps

Decorative CFLi Lamps

A Shaped Decorative CFLi Lamps



Ordering Code	Bar Code	Approvals	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP9A19/27K	06445	UL/CSA, TCLP Compliant	120	9	Medium Screw (E26)	4.10/104	2700	10000	>80	500
SP9A19/41K	06446	UL/CSA, TCLP Compliant	120	9	Medium Screw (E26)	4.10/104	4100	10000	>80	500
SP11A/27K-GU24	07732	UL/CSA, Energy Star, TCLP Compliant	120	11	GU24	3.82/97	2700	10000	>80	600
SP13A19/27K	06447	UL/CSA, Energy Star, TCLP Compliant	120	13	Medium Screw (E26)	4.84/123	2700	10000	>80	800
SP13A19/41K	06448	UL/CSA, TCLP Compliant	120	13	Medium Screw (E26)	4.84/123	4100	10000	>80	800
SP15A/27K-GU24	07710	UL/CSA, Energy Star, TCLP Compliant	120	13	GU24	4.45/113	2700	10000	>80	800

Fluorescent Lamps

CFLi Lamps

Decorative CFLi Lamps

B10 Decorative CFLi Lamps



Ordering Code	Bar Code	Approvals	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP5B10/E12/27K	06435	UL/CSA, TCLP Compliant	120	5	Candelabra Screw (E12)	4.33/110	2700	10,000	>80	200
SP5B10/E12/41K	06437	UL/CSA, TCLP Compliant	120	5	Candelabra Screw (E12)	4.33/110	4100	10,000	>80	200
SP7B10/E12/27K	06442	UL/CSA, TCLP Compliant	120	7	Candelabra Screw (E12)	4.84/123	2700	10,000	>80	300
SP7B10/E12/41K	06449	UL/CSA, TCLP Compliant	120	7	Candelabra Screw (E12)	4.84/123	4100	10,000	>80	315

B13 Decorative CFLi Lamps



Ordering Code	Bar Code	Approvals	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP5B13/E26/27K	06452	UL/CSA, TCLP Compliant	120	5	Medium Screw (E26)	4.84/123	2700	10,000	>80	200
SP5B13/E26/41K	06453	UL/CSA, TCLP Compliant	120	5	Medium Screw (E26)	4.84/123	4100	10,000	>80	200

G25 Decorative CFLi Lamps



Ordering Code	Bar Code	Approvals	Volts	Watts	Base	MOL	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP9G25/27K	06550	UL/CSA, TCLP Compliant	120	9	Medium Screw (E26)	4.3/109	2700	10000	80	500
SP9G25/41K	06551	UL/CSA, TCLP Compliant	120	9	Medium Screw (E26)	4.3/109	4100	10000	80	500
SP13G25/27K	06552	UL/CSA, TCLP Compliant	120	13	Medium Screw (E26)	4.3/109	2700	10000	80	800
SP13G25/41K	06553	UL/CSA, Energy Star, TCLP Compliant	120	13	Medium Screw (E26)	4.3/109	4100	10000	80	800
SP15G25/27K	07870	UL/CSA, Energy Star, TCLP Compliant	120	15	Medium Screw (E26)	4.724/120	2700	10000	80	820
SP15G25/27K-GU24	07734	UL/CSA, Energy Star, TCLP Compliant	120	15	GU24	4.45/113	2700	10000	>80	740
SP15G25/41K	07871	UL/CSA, TCLP Compliant	120	15	Medium Screw (E26)	4.724/120	4100	10000	80	820

Compact Fluorescent Lamps

Duo-Tube CFL Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
DT5/27	15554	G23	4.2/107	<4	5	2700	10000	82	250	210
DT5/35	49204	G23	4.2/107	<4	5	3500	10000	82	250	210
DT5/41	49205	G23	4.2/107	<4	5	4100	10000	82	250	210
DT5/50	49206	G23	4.2/107	<4	5	5000	10000	82	250	210
DT5/65	49207	G23	4.2/107	<4	5	6500	10000	82	250	210
DT7/27	15556	G23	5.3/135	<4	7	2700	10000	82	400	330
DT7/35	49208	G23	5.3/135	<4	7	3500	10000	82	400	330
DT7/41	49209	G23	5.3/135	<4	7	4100	10000	82	400	330
DT7/50	49210	G23	5.3/135	<4	7	5000	10000	82	400	330
DT7/65	49211	G23	5.3/135	<4	7	6500	10000	82	400	330
DT9/27	15558	G23	6.6/168	<4	9	2700	10000	82	600	500
DT9/35	49212	G23	6.6/168	<4	9	3500	10000	82	600	500
DT9/41	49213	G23	6.6/168	<4	9	4100	10000	82	600	500
DT9/50	49214	G23	6.6/168	<4	9	5000	10000	82	600	500
DT9/65	49215	G23	6.6/168	<4	9	6500	10000	82	600	500
DT13/27	15560	GX23	7.3/185	<4	13	2700	10000	82	825	710
DT13/30	49216	GX23	7.3/185	<4	13	3000	10000	82	825	710
DT13/35	15575	GX23	7.3/185	<4	13	3500	10000	82	825	710
DT13/41	49217	GX23	7.3/185	<4	13	4100	10000	82	825	710
DT13/50	49218	GX23	7.3/185	<4	13	5000	10000	82	825	710
DT13/65	49219	GX23	7.3/185	<4	13	6500	10000	82	825	710
DT18/30/RS	49283	2G11	9.0/229	<4	18	3000	20000	82	1250	1130
DT18/35/RS	49284	2G11	9.0/229	<4	18	3500	20000	82	1250	1130
DT18/41/RS	49285	2G11	9.0/229	<4	18	4100	20000	82	1250	1130
DT18/50/RS	49286	2G11	9.0/229	<4	18	5000	20000	82	1250	1130
DT24/30/RS	49288	2G11	12.9/328	<4	24	3000	20000	82	1800	1620
DT24/35/RS	49289	2G11	12.9/328	<4	24	3500	20000	82	1800	1620

Fluorescent Lamps

Compact Fluorescent Lamps

Duo-Tube CFL Lamps

Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
DT24/41/RS	49290	2G11	12.9/328	<4	24	4100	20000	82	1800	1620
DT24/50/RS	49291	2G11	12.9/328	<4	24	5000	20000	82	1800	1620
DT24/65/RS	49292	2G11	12.9/328	<4	24	6500	20000	82	1800	1620
DT36/30/RS	49293	2G11	16.6/422	<4	36	3000	20000	82	2900	2610
DT36/35/RS	49294	2G11	16.6/422	<4	36	3500	20000	82	2900	2610
DT36/41/RS	49295	2G11	16.6/422	<4	36	4100	20000	82	2900	2610
DT36/50/RS	49296	2G11	16.6/422	<4	36	5000	20000	82	2900	2610
DT36/65/RS	49297	2G11	16.6/422	<4	36	6500	20000	82	2900	2610
DT40/30/RS	49298	2G11	22.5/572	<4	40	3000	20000	82	3300	2970
DT40/35/RS	49299	2G11	22.5/572	<4	40	3500	20000	82	3300	2970
DT40/41/RS	49300	2G11	22.5/572	<4	40	4100	20000	82	3300	2970
DT40/50/RS	49301	2G11	22.5/572	<4	40	5000	20000	82	3300	2970
DT40/65/RS	49302	2G11	22.5/572	<4	40	6500	20000	82	3300	2970
DT50/30/RS	49303	2G11	22.5/572	<4	50	3000	18000	82	4300	3870
DT50/35/RS	49304	2G11	22.5/572	<4	50	3500	18000	82	4300	3870
DT50/41/RS	49305	2G11	22.5/572	<4	50	4100	18000	82	4300	3870
DT50/50/RS	49306	2G11	22.5/572	<4	50	5000	18000	82	4300	3870
DT50/65/RS	49307	2G11	22.5/572	<4	50	6500	18000	82	4300	3870
DT55/30/RS	49308	2G11	21.5/546	<4	55	3000	18000	82	4800	4320
DT55/35/RS	49309	2G11	21.5/546	<4	55	3500	18000	82	4800	4320
DT55/41/RS	49310	2G11	21.5/546	<4	55	4100	18000	82	4800	4320
DT55/50/RS	49311	2G11	21.5/546	<4	55	5000	18000	82	4800	4320
DT55/65/RS	49312	2G11	21.5/546	<4	55	6500	18000	82	4800	4320

Quad-Tube CFL Lamps

Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
QT9/27	15562	G23-2	4.3/109	4	9	2700	10000	82	550	470
QT9/35	49221	G23-2	4.3/109	4	9	3500	10000	82	550	470
QT9/41	49558	G23-2	4.3/109	4	9	4100	10000	82	550	470
QT13/27	15564	GX23-2	4.6/117	<4	13	2700	10000	82	810	685
QT13/27-4P	49241	G24q-1	5/127	3.5	13	2700	10000	82	900	765
QT13/30	49222	GX23-2	4.6/117	<4	13	3000	10000	82	810	685
QT13/30-4P	49242	G24q-1	5/127	3.5	13	3000	10000	82	900	765
QT13/35	15576	GX23-2	4.6/117	<4	13	3500	10000	82	810	685
QT13/35-4P	49243	G24q-1	5/127	3.5	13	3500	10000	82	900	765
QT13/41	49084	GX23-2	4.6/117	<4	13	4100	10000	82	810	685
QT13/41-4P	49244	G24q-1	5/127	3.5	13	4100	10000	82	900	765
QT13/50	49223	GX23-2	4.6/117	<4	13	5000	10000	82	810	685
QT13/50-4P	49245	G24q-1	5/127	3.5	13	5000	10000	82	900	765
QT13/65	49224	GX23-2	4.6/117	<4	13	6500	10000	82	810	685
QT13/65-4P	49246	G24q-1	5/127	3.5	13	6500	10000	82	900	765
QT13/G24D1/30	49226	G24d-1	5.5/140	3	13	3000	10000	82	900	765
QT13/G24D1/35	49227	G24d-1	5.5/140	3	13	3500	10000	82	900	765
QT13/G24D1/50	49229	G24d-1	5.5/140	3	13	5000	10000	82	900	765
QT13/G24D1/65	49230	G24d-1	5.5/140	3	13	6500	10000	82	900	765
QT18/27	15566	G24d-2	5.9/150	<4	18	2700	10000	82	1150	980
QT18/27-4P	49247	G24q-2	5.8/147	3.5	18	2700	10000	82	1150	980
QT18/30	49231	G24d-2	5.9/150	<4	18	3000	10000	82	1150	980
QT18/30-4P	49248	G24q-2	5.8/147	3.5	18	3000	10000	82	1150	980
QT18/35	49232	G24d-2	5.9/150	<4	18	3500	10000	82	1150	980
QT18/35-4P	49249	G24q-2	5.8/147	3.5	18	3500	10000	82	1150	980
QT18/41	49233	G24d-2	5.9/150	<4	18	4100	10000	82	1150	980
QT18/41-4P	49250	G24q-2	5.8/147	3.5	18	4100	10000	82	1150	980
QT18/50	49234	G24d-2	5.9/150	<4	18	5000	10000	82	1150	980
QT18/50-4P	49251	G24q-2	5.8/147	3.5	18	5000	10000	82	1150	980
QT26/27	15568	G24d-3	6.7/170	<4	26	2700	10000	82	1710	1460
QT26/27-4P	49253	G24q-3	6.4/163	4	26	2700	10000	82	1710	1460
QT26/30	49236	G24d-3	6.7/170	<4	26	3000	10000	82	1710	1460
QT26/30-4P	49254	G24q-3	6.4/163	4	26	3000	10000	82	1710	1460
QT26/35	49237	G24d-3	6.7/170	<4	26	3500	10000	82	1710	1460
QT26/35-4P	49255	G24q-3	6.4/163	4	26	3500	10000	82	1710	1460
QT26/41	49238	G24d-3	6.7/170	<4	26	4100	10000	82	1710	1460
QT26/41-4P	49256	G24q-3	6.4/163	4	26	4100	10000	82	1710	1460
QT26/50	49239	G24d-3	6.7/170	<4	26	5000	10000	82	1710	1460
QT26/50-4P	49257	G24q-3	6.4/163	4	26	5000	10000	82	1710	1460
QT26/65	49240	G24d-3	6.7/170	<4	26	6500	10000	82	1710	1460
QT26/65-4P	49258	G24q-3	6.4/163	4	26	6500	10000	82	1710	1460

Fluorescent Lamps



Fluorescent Lamps

Compact Fluorescent Lamps

Triple-Tube CFL Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
TT18/27	49259	GX24q-2	4.8/122	3.5	18	2700	10000	82	1200	1020
TT18/30	49260	GX24q-2	4.8/122	3.5	18	3000	10000	82	1200	1020
TT18/35	49261	GX24q-2	4.8/122	3.5	18	3500	10000	82	1200	1020
TT18/41	49262	GX24q-2	4.8/122	3.5	18	4100	10000	82	1200	1020
TT18/65	49264	GX24q-2	4.8/122	3.5	18	6500	10000	82	1200	1020
TT26/27	49265	GX24q-3	5.2/132	4	26	2700	10000	82	1800	1530
TT26/30	49266	GX24q-3	5.2/132	4	26	3000	10000	82	1800	1530
TT26/35	49267	GX24q-3	5.2/132	4	26	3500	10000	82	1800	1530
TT26/41	49268	GX24q-3	5.2/132	4	26	4100	10000	82	1800	1530
TT26/50	49269	GX24q-3	5.2/132	4	26	5000	10000	82	1800	1530
TT26/65	49270	GX24q-3	5.2/132	4	26	6500	10000	82	1800	1530
TT32/27	49271	GX24q-3	5.8/147	4	32	2700	10000	82	2200	1870
TT32/30	49272	GX24q-3	5.8/147	4	32	3000	10000	82	2200	1870
TT32/35	49273	GX24q-3	5.8/147	4	32	3500	10000	82	2200	1870
TT32/41	49274	GX24q-3	5.8/147	4	32	4100	10000	82	2200	1870
TT32/50	49275	GX24q-3	5.8/147	4	32	5000	10000	82	2200	1870
TT32/65	49276	GX24q-3	5.8/147	4	32	6500	10000	82	2200	1870
TT42/27	49277	GX24q-4	6.4/163	4	42	2700	10000	82	3200	2720
TT42/30	49278	GX24q-4	6.4/163	4	42	3000	10000	82	3200	2720
TT42/35	49279	GX24q-4	6.4/163	4	42	3500	10000	82	3200	2720
TT42/41	49280	GX24q-4	6.4/163	4	42	4100	10000	82	3200	2720
TT42/50	49281	GX24q-4	6.4/163	4	42	5000	10000	82	3200	2720
TT42/65	49282	GX24q-4	6.4/163	4	42	6500	10000	82	3200	2720

FML CFL Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
FML18/65	05148	GX10q-4	5.1/129	5	18	6500	10000	82	1080	1042
FML27/27	49313	GX10q-4	5.7/145	5	27	2700	10000	82	1400	1260
FML27/41	49314	GX10q-4	5.7/145	5	27	4100	10000	82	1400	1260
FML27/65	49315	GX10q-4	5.7/145	5	27	6500	10000	82	1400	1260

4-Pin Based Spiral CFL Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens
SP13/27-4P	05251	G24q-1	3.74/95	4	13	2700	10000	80	900
SP18/27-4P	05250	GX24q-2	4.41/112	4	18	2700	10000	82	1100
SP26/27-4P	05252	GX24q-3	4.72/120	4	26	2700	10000	82	1800

Linear Fluorescent Lamps

T5 Linear Fluorescent Lamps

Programmed Start T5 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life 3hr Start	Life 12hr Start	CRI	Approx Initial Lumens	Approx Mean Lumens
F14T5/835	81147	G5	22/559	<4	14	3500	25,000	35,000	85	1350	1256
F14T5/841	81148	G5	22/559	<3	14	4000	25,000	35,000	85	1200	
F14T5/865	07151	G5	22/559	<4	14	6500	25,000	35,000	85	1300	1210
F21T5/835	81149	G5	34/864	<4	21	3500	25,000	35,000	85	2100	1953
F21T5/841	81150	G5	34/864	<3	21	4000	25,000	35,000	85	1900	
F24T5/HO/835	81154	G5	22/559	3.5	24	3500	25,000	35,000	85	2000	1860
F24T5/HO/841	81155	G5	22/559	<3	24	4000	25,000	35,000	85	1750	
F25T8/830K	49581	G13	36.0/915	3.5	25	3000	20,000	25,000	83	2225	2050
F25T8/835K	49582	G13	36.0/915	3.5	25	3500	20,000	25,000	83	2225	2050
F25T8/841K	49583	G13	36.0/915	3.5	25	4100	20,000	25,000	83	2225	2050
F28T5/835	81151	G5	46/1169	<3	28	3000	25,000	35,000	85	2600	
F28T5/841	81152	G5	46/1169	<3	28	4000	25,000	35,000	85	2600	
F28T5/850	81153	G5	46/1169	<3	28	5000	25,000	35,000	85	2400	
F28T5/865	07150	G5	46/1169	<4	28	6500	25,000	35,000	85	2850	2650
F35T5/830	04727	G5	57/1463	<3	35	3000	25,000	35,000	85	3300	
F39T5/HO/835	81156	G5	34/864	4	39	3500	25,000	35,000	85	3500	3255
F39T5/HO/841	81157	G5	34/864	4	39	4100	25,000	35,000	85	3500	3255
F49T5/HO/835	00973	G5	46/1169	3.5	49	3500	25,000	35,000	85	4900	4750
F49T5/HO/841	00976	G5	46/1169	3.5	49	4100	25,000	35,000	85	4900	4750
F49T5/HO/841	00976	G5	46/1169	<3	49	4000	25,000	35,000	85	4900	4750
F49T5/HO/850	00981	G5	46/1169	<3	49	5000	25,000	35,000	85	4800	4625
F49T5/HO/865	00982	G5	46/1169	3.5	49	6500	25,000	35,000	85	4800	4625

Visit our website for the most current specs: <http://www.eiko.com>

Fluorescent Lamps

Linear Fluorescent Lamps

T5 Linear Fluorescent Lamps

Programmed Start T5 Lamps

Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life 3hr Start	Life 12hr Start	CRI	Approx Initial Lumens	Approx Mean Lumens
F54T5/HO/830	07376	G5	46/1169	3.5	54	3000	25,000	35,000	85	5000	4650
F54T5/HO/835	81158	G5	46/1169	3.5	54	3500	25,000	35,000	85	5000	4650
F54T5/HO/841	81159	G5	46/1169	3.5	54	4100	25,000	35,000	85	5000	4650
F54T5/HO/850	81160	G5	46/1169	3.5	54	5000	25,000	35,000	85	4850	4500
F54T5/HO/865	06854	G5	46/1169	3.5	54	6500	25,000	35,000	85	4850	4500

Preheat T5 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
F4T5/CW	15500	G5	6.0/152	5	4	4100	6000	60	135	100
F4T5/D	15501	G5	6.0/152	5	4	6500	6000	75	115	92
F6T5/CW	15505	G5	9.0/229	5	6	4100	7500	60	295	235
F6T5/D	15506	G5	9.0/229	5	6	6500	7500	75	230	185
F6T5/WW	15507	G5	9.0/229	5	6	3000	7500	52	275	220
F8T5/CW	15510	G5	12.0/305	5	8	4100	7500	60	400	320
F8T5/D	15511	G5	12.0/305	5	8	6500	7500	75	330	265
F8T5/W	15513	G5	12.0/305	5	8	3500	7500	55	400	320
F8T5/WW	15512	G5	12.0/305	5	8	3000	7500	52	410	330
F13T5/CW	15517	G5	21.0/533	5	13	4100	7500	60	850	705
F13T5/D	15531	G5	21.0/533	5	13	6500	7500	75	700	460
F13T5/WW	15518	G5	21.0/533	5	13	3000	7500	60	870	720

Blacklight T5 Lamps



Ordering Code	Bar Code	Watts	Shape	Base	MOL	MOD	Life Hours
F4T5/BL	15503	4	T-5	G5	6.0/152	0.63/16	6000
F4T5/BLB	15504	4	T-5	G5	6.0/152	0.63/16	6000
F6T5/BL	15528	6	T-5	G5	9.0/229	0.63/16	7500
F6T5/BLB	15509	6	T-5	G5	9.0/229	0.63/16	7500
F8T5/BL	15515	8	T-5	G5	12.0/305	0.63/16	7500
F8T5/BLB	15516	8	T-5	G5	12.0/305	0.63/16	7500

T8 Linear Fluorescent Lamps

Long Life T8 Lamps

Ordering Code	Bar Code	Watts	Shape	Base	MOL	Life 3hr Start	Life 12hr Start
F32T8/830K/XL	07437	32	T-8	G13	48.0/1219	44,000	55,000
F32T8/835K/XL	07833	32	T-8	G13	48.0/1213	44,000	55,000
F32T8/841K/XL	07789	32	T-8	G13	48.0/1219	44,000	55,000
F32T8/850K/XL	07476	32	T-8	G13	48.0/1219	44,000	55,000
F32T8/865K/XL	07592	32	T-8	G13	48.0/1219	44,000	55,000

CEE Specified T8 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life 3hr Start	Life 12hr Start	CRI	Approx Initial Lumens	Approx Mean Lumens
F28T8/830/ES	06603	G13	48.0/1219	3.5	28	3000	24,000	30,000	83	2800	2635
F28T8/835/ES	06604	G13	48.0/1219	3.5	28	3500	24,000	30,000	83	2800	2635
F28T8/841/ES	06605	G13	48.0/1219	3.5	28	4100	24,000	30,000	83	2800	2635
F28T8/850/ES	06606	G13	48.0/1219	3.5	28	5000	24,000	30,000	83	2800	2635
F28T8/865/ES	07146	G13	48.0/1219	3.5	28	6500	24,000	30,000	83	2750	2585
F32T8/830/ES/25W	06748	G13	48.0/1219	3.5	25	3000	24,000	30,000	83	2400	2260
F32T8/830K/HL	06568	G13	48.0/1219	3.5	32	3000	24,000	30,000	83	3100	2915
F32T8/835/ES/25W	06749	G13	48.0/1219	3.5	25	3500	24,000	30,000	83	2400	2260
F32T8/865K/HL	06569	G13	48.0/1219		32	3500	24,000	30,000	83	3100	2915
F32T8/841/ES/25W	06750	G13	48.0/1219	3.5	25	4100	24,000	30,000	83	2400	2260
F32T8/841K/HL	06570	G13	48.0/1219	3.5	32	4100	24,000	30,000	83	3100	2915
F32T8/850/ES/25W	06751	G13	48.0/1219	3.5	25	5000	24,000	30,000	83	2350	2200
F32T8/850K/HL	06571	G13	48.0/1219	3.5	32	5000	24,000	30,000	83	3000	2820
F32T8/850K/XL	07476	G13	48.0/1219	2.7	32	5000	44,000	55,000	83	2950	2810
F32T8/865/ES/25W	07149	G13	48.0/1219	3.5	25	6500	24,000	30,000	83	2350	2200
F32T8/865K/HL	07148	G13	48.0/1219	3.5	32	6500	24,000	30,000	83	3000	2820

Linear Fluorescent Lamps

T8 Linear Fluorescent Lamps

High Lumen T8 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life 3hr Start	Life 12hr Start	CRI	Approx Initial Lumens	Approx Mean Lumens
F32T8/830K/HL	06568	G13	48.0/1219	3.5	32	3000	24,000	30,000	83	3100	2915
F32T8/835K/HL	06569	G13	48.0/1219		32	3500	24,000	30,000	83	3100	2915
F32T8/841K/HL	06570	G13	48.0/1219	3.5	32	4100	24,000	30,000	83	3100	2915
F32T8/850K/HL	06571	G13	48.0/1219	3.5	32	5000	24,000	30,000	83	3000	2820
F32T8/865K/HL	07148	G13	48.0/1219	3.5	32	6500	24,000	30,000	83	3000	2820

Energy Saving T8 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life 3hr Start	Life 12hr Start	CRI	Approx Initial Lumens	Approx Mean Lumens
F28T8/830/ES	06603	G13	48.0/1219	3.5	28	3000	24,000	30,000	83	2800	2635
F28T8/835/ES	06604	G13	48.0/1219	3.5	28	3500	24,000	30,000	83	2800	2635
F28T8/841/ES	06605	G13	48.0/1219	3.5	28	4100	24,000	30,000	83	2800	2635
F28T8/850/ES	06606	G13	48.0/1219	3.5	28	5000	24,000	30,000	83	2800	2635
F28T8/865/ES	07146	G13	48.0/1219	3.5	28	6500	24,000	30,000	83	2750	2585
F32T8/830/ES/25W	06748	G13	48.0/1219	3.5	25	3000	24,000	30,000	83	2400	2260
F32T8/835/ES/25W	06749	G13	48.0/1219	3.5	25	3500	24,000	30,000	83	2400	2260
F32T8/841/ES/25W	06750	G13	48.0/1219	3.5	25	4100	24,000	30,000	83	2400	2260
F32T8/850/ES/25W	06751	G13	48.0/1219	3.5	25	5000	24,000	30,000	83	2350	2200
F32T8/865/ES/25W	07149	G13	48.0/1219	3.5	25	6500	24,000	30,000	83	2350	2200

Programmed Start T8 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life 3hr Start	Life 12hr Start	CRI	Approx Initial Lumens	Approx Mean Lumens
F17T8/730K	49572	G13	24.0/610	9	17	3000	20,000	25,000	73	1325	1200
F17T8/735K	49573	G13	24.0/610	9	17	3500	20,000	25,000	73	1325	1200
F17T8/741K	49574	G13	24.0/610	9	17	4100	20,000	25,000	73	1325	1200
F17T8/830K	49575	G13	24.0/610	3.5	17	3000	20,000	25,000	83	1400	1300
F17T8/835K	49576	G13	24.0/610	3.5	17	3500	20,000	25,000	83	1400	1300
F17T8/841K	49577	G13	24.0/610	3.5	17	4100	20,000	25,000	83	1400	1300
F17T8/850K	48055	G13	24.0/610	3.5	17	5000	20,000	25,000	83	1400	1300
F25T8/830K	49581	G13	36.0/915	3.5	25	3000	20,000	25,000	83	2225	2050
F25T8/835K	49582	G13	36.0/915	3.5	25	3500	20,000	25,000	83	2225	2050
F25T8/841K	49583	G13	36.0/915	3.5	25	4100	20,000	25,000	83	2225	2050
F32T8/735K	49585	G13	48.0/1219	9	32	3500	20,000	25,000	75	2850	2705
F32T8/741K	49586	G13	48.0/1219	9	32	4100	20,000	25,000	75	2850	2705
F32T8/830K	49587	G13	48.0/1219	3.5	32	3000	20,000	25,000	83	2950	2800
F32T8/835K	49588	G13	48.0/1219	3.5	32	3500	20,000	25,000	83	2950	2800
F32T8/841K	49589	G13	48.0/1219	3.5	32	4100	20,000	25,000	83	2950	2800
F32T8/850K	81174	G13	48.0/1219	3.5	32	5000	20,000	25,000	83	2950	2800
F32T8/865K	07147	G13	48.0/1219	3.5	32	6500	20,000	25,000	83	2900	2725

Preheat T8 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
F10T8/CW	15524	G13	13.6/346	5	10	4100	7500	60	480	425
F13T8/CW	15545	G13	12.0/305	5	13	4100	7500	60	565	480
F14T8/CW	15519	G13	15.0/381	5	14	4100	7500	60	685	580
F14T8/D	15520	G13	15.0/381	5	14	6500	7500	75	645	545
F15T8/CW	15521	G13	18.0/457	5	15	4100	7500	60	825	725
F15T8/D	15522	G13	18.0/457	5	15	6500	7500	75	700	615
F15T8/W	15525	G13	18.0/457	5	15	3500	7500	55	800	725
F15T8/WW	15523	G13	18.0/457	5	15	3000	7500	52	845	745

Blacklight T8 Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Special Desc	Watts	Life Hours
F15T8/BL	15526	G13	18.0/457	5	Blacklight (350nm), Preheat	15	7500
F15T8/BLB	15527	G13	18.0/457	5	Blacklight Blue (365nm), Preheat	15	7500

Fluorescent Lamps

Linear Fluorescent Lamps

T8 U-Bend Fluorescent Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Special Desc	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
F31T8/830/U	05287	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	3000	20000	84	2750	2475
F31T8/835/U	05288	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	3500	20000	84	2750	2475
F31T8/841/U	05289	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	4100	20000	84	2750	2475
F31T8/850/U	05290	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	5000	20000	84	2625	2365
F32T8/835K/U6	02403	G13	22.5/571	9	U-Bend 6 inch centers, Universal Start	32	3500	20000	85	2800	2535
F32T8/841K/U6	02404	G13	22.5/571	9	U-Bend 6 inch centers, Universal Start	32	4100	20000	85	2800	2535
F32T8/850K/U6	02405	G13	22.5/571	9	U-Bend 6 inch centers, Universal Start	32	5000	20000	85	2750	2500

Circular Fluorescent Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
FC8T9/CW	15604	G10q	8.25/215	8	22	4100	12000	60	1100	825
FC8T9/D	15532	G10q	8.25/215	8	22	6500	12000	75	925	690
FC12T9/CW	15606	G10q	12.0/305	8	32	4100	12000	60	1950	1460
FC12T9/D	15533	G10q	12.0/305	8	32	6500	12000	75	1675	1260
FC16T9/CW	15534	G10q	16.0/406	8	40	4100	12000	60	2700	2030
FC16T9/D	15535	G10q	16.0/406	8	40	6500	12000	75	2250	1690

Fluorescent Starters



Ordering Code	Bar Code	Description
FS-2	49550	14 15 20W 120V Aluminum Case UL
FS-4	49551	30 40W 120V Aluminum Case
FS-5	49552	4 6 8W 120V Aluminum Case UL
FS-U-120V	49554	4 - 30W 120V Aluminum Case UL

Halogen Lamps

A-Line Halogen Lamps

EiKON Energy Efficient Halogen Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
29A/CL/H-120V	07757	29	120	A-19	Medium Screw (E26)	CC-8	430	4.25/108	2.36/60	1000
43A/CL/H-120V	07758	43	120	A-19	Medium Screw (E26)	CC-8	750	4.25/108	2.36/60	1000
53A/CL/H-120V	07759	53	120	A-19	Medium Screw (E26)	CC-8	1050	4.25/108	2.36/60	1000
72A/CL/H-120V	07760	72	120	A-19	Medium Screw (E26)	CC-8	1490	4.25/108	2.36/60	1000

Classic BT15 Halogen Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
60BT15/H/CL	81138	60	120	BT-15	Medium Screw (E26)	CC-8	900	4.0/101	1.9/48.3	3000
60BT15/H/W	81137	60	120	BT-15	Medium Screw (E26)	CC-8	840	4.0/101	1.9/48.3	3000
75BT15/H/W	81139	75	120	BT-15	Medium Screw (E26)	CC-8	1120	4.0/101	1.9/48.3	3000
150BT15/H/W	81141	150	120	BT-15	Medium Screw (E26)	CC-8	2850	4.0/101	1.9/48.3	1500

MR8 Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
Q10MR8/NSP/CG	06240	10	6	GU4	C-8	1.56/39.5	0.99/25.2	2000	10
Q20MR8/NFL/CG	05042	20	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	20
Q20MR8/NSP/CG	04977	20	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	10
Q35MR8/NFL/CG	06242	35	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	20
Q35MR8/NSP/CG	06241	35	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	10

Halogen Lamps

Halogen Lamps

MR8 Supreme Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
49407	49407	20	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	10
49408	49408	20	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	23

MR11 Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
FTA	15115	12	12	GU4	C-8	1.38/35.0	1.39/35.3	2000	10
FTB	15120	20	12	GU4	C-8	1.38/35.0	1.39/35.3	2000	10
FTB-FG	15140	20	12	GU4	C-8	1.56/39.5	1.41/35.8	2000	10
FTC	15122	20	12	GU4	C-8	1.38/35.0	1.39/35.3	2000	20
FTC-FG	15142	20	12	GU4	C-8	1.56/39.5	1.41/35.8	2000	20
FTD	15124	20	12	GU4	C-8	1.38/35.0	1.39/35.3	2000	30
FTD-FG	15144	20	12	GU4	C-8	1.56/39.5	1.41/35.8	2000	30
FTE	15126	35	12	GU4	C-8	1.38/35.0	1.39/35.3	2000	10
FTE-FG	15146	35	12	GU4	C-8	1.56/39.5	1.41/35.8	2000	10
FTF	15128	35	12	GU4	C-8	1.38/35.0	1.39/35.3	2000	20
FTF-FG	15148	35	12	GU4	C-8	1.56/39.5	1.41/35.8	2000	20
FTH	15130	35	12	GU4	C-8	1.38/35.0	1.39/35.3	2000	30
FTH-FG	15150	35	12	GU4	C-8	1.56/39.5	1.41/35.8	2000	30

MR16 Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
BAB	15030	20	12	GU5.3	C-8	1.81/46.0	2.00/50.8	3000	38
BAB-BLACK	81109	20	12	GU5.3	C-8	1.81/46.0	2.00/50.8	3000	38
BAB-FG	15070	20	12	GU5.3	C-8	1.99/50.5	2.00/50.8	3000	38
BAB-SILVER	81108	20	12	GU5.3	C-8	1.81/46.0	2.00/50.8	3000	38
ENL	15040	50	12	GU5.3	C-8	1.75/44.5	2.00/50.8	4000	24
ESX	15032	20	12	GU5.3	C-8	1.75/44.5	2.00/50.8	3000	12
ESX-FG	15072	20	12	GU5.3	C-8	1.99/50.5	2.00/50.8	3000	12
EXN	15042	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	4000	38
EXN-BLACK	81115	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	4000	38
EXN-FG	15080	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	38
EXN-FG-24V	49565	50	24	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	38
EXN-SILVER	81114	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	4000	38
EXT	15044	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	4000	12
EXT-FG	15082	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
EXT-FG-24V	49566	50	24	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
EXZ	15046	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	4000	24
EXZ-BLACK	81113	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	4000	24
EXZ-FG	15084	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	24
EXZ-SILVER	81112	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	4000	24
EYC	15062	75	12	GU5.3	C-8	1.75/44.5	2.00/50.8	4000	38
EYC-FG	15092	75	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	38
EYF	15064	75	12	GU5.3	C-8	1.75/44.5	2.00/50.8	4000	12
EYF-FG	15094	75	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
EYJ	15066	75	12	GU5.3	C-8	1.75/44.5	2.00/50.8	4000	24
EYJ-FG	15096	75	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	24
EYP	15034	42	12	GU5.3	C-8	1.75/44.5	2.00/50.8	4000	38
EYP-FG	15074	42	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	38
EYR	15036	42	12	GU5.3	C-8	1.75/44.5	2.00/50.8	4000	12
EYR-FG	15076	42	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
EYS	15038	42	12	GU5.3	C-8	1.75/44.5	2.00/50.8	4000	24
EYS-FG	15078	42	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	24
FMT	15047	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	12
FMT-FG	15053	35	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
FMV	15049	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	24
FMV-FG	15055	35	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	24
FMW	15051	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	38
FMW-BLACK	81111	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	38
FMW-FG	15057	35	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	38
FMW-SILVER	81110	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	38
FNC-FG	15048	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
FND-FG	15050	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
FNE-FG	15052	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
FNF-FG	15054	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
FNV	00296	50	12	GU5.3	C-8	1.75/44.5	2.00/50.8	3000	60
FNV-FG	00297	50	12	GU5.3	C-8	1.75/44.5	2.00/50.8	3000	60
FPA	15056	65	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	12
FPA-FG	15086	65	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	12
FPB	15058	65	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	38
FPB-FG	15088	65	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	38
FPC	15060	65	12	GU5.3	C-8	1.81/46.0	2.00/50.8	4000	24

Halogen Lamps

MR16 Halogen Lamps

Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
FPC-FG	15090	65	12	GU5.3	C-8	1.85/47.0	2.00/50.8	4000	24
FRA-FG	49433	35	12	GU5.3	C-8	1.99/50.5	2.00/50.8	4000	18

MR16 Screw Base Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
FSA	15100	75	120	Intermediate Screw (E17)	CC-8	2.75/69.9	2.00/50.8	2000	12
FSB	15102	75	120	Intermediate Screw (E17)	CC-8	2.75/69.9	2.00/50.8	2000	20
FSC	15104	100	120	Intermediate Screw (E17)	CC-8	2.75/69.9	2.00/50.8	2000	12
FSD	15106	75	120	Intermediate Screw (E17)	CC-8	2.75/69.9	2.00/50.8	2000	30
FSE	15108	100	120	Intermediate Screw (E17)	CC-8	2.75/69.9	2.00/50.8	2000	20
FSF	15110	100	120	Intermediate Screw (E17)	CC-8	2.75/69.9	2.00/50.8	2000	30
JDR75/FL	10453	75	120	Medium Screw (E26)	CC-8	2.84/72.0	2.00/50.8	2000	30
JDR75/MF	10452	75	120	Medium Screw (E26)	CC-8	2.84/72.0	2.00/50.8	2000	20
JDR75/SP	10451	75	120	Medium Screw (E26)	CC-8	2.84/72.0	2.00/50.8	2000	12
JDR100/FL	05426	100	120	Medium Screw (E26)	CC-8	2.84/72.0	2.00/50.8	1500	30
JDR100/MF	05425	100	120	Medium Screw (E26)	CC-8	2.84/72.0	2.00/50.8	1500	20
JDR130V50W	00211	50	130	Medium Screw (E26)	C-6Z	2.84/72.0	2.00/50.8	2000	30

MR16 Line Voltage Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
BAB-FG-GU10-120V	05373	20	120	GU10	8-Style	2.20/56	2.00/51	3000	38
EXN-FG-GU10-130V	00305	50	130	GU10	8-Style	2.20/56	2.20/50.8	3500	38
FMW-FG-GU10-130V	00009	35	130	GU10	8-Style	2.20/56	2.20/50.8	2000	38

Aluminized Reflector Lamps

37mm Diameter Aluminized Reflector Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
GBD	49861	20	12	DC Bayonet (BA15d)	C-8	1.63/41.4	1.39/35.3	2000
GBE	49862	20	12	DC Bayonet (BA15d)	C-8	1.63/41.4	1.39/35.3	2000
GBF	49664	20	12	DC Bayonet (BA15d)	C-8	1.63/41.4	1.39/35.3	2000
GBF-FR	49665	20	12	DC Bayonet (BA15d)	C-8	1.63/41.4	1.39/35.3	2000

56mm Diameter Aluminized Reflector Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
GBJ	49863	50	12	DC Bayonet (BA15d)	C-8	2.25/57.2	2.25/57.2	2000
GBK	49864	50	12	DC Bayonet (BA15d)	C-8	2.25/57.2	2.25/57.2	2000

Single Ended Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
Q50CL/DC-130V	00212	50	130	T-4	DC Bayonet (BA15d)	CC-8	2.18/55.4	0.52/13.0	2000
Q50CL/MC-130V	00213	50	130	T-4	Miniature Candelabra Screw (E11)	CC-8	2.56/65.0	0.52/13.0	2000
Q75CL-120V	15215	75	120	T-3 1/2	Miniature Candelabra Screw (E11)	CC-8	2.50/63.5	0.44/11.0	2000
Q75CL-130V	49567	75	130	T-3 1/2	Miniature Candelabra Screw (E11)	CC-8	2.50/63.5	0.44/11.0	2000
Q75CL/DC-120V	15217	75	120	T-3 1/2	DC Bayonet (BA15d)	CC-8	2.38/60.3	0.47/12.0	2000
Q75MC-120V	15287	75	120	T-4	Miniature Candelabra Screw (E11)	C-8	2.56/65.0	0.52/13.0	1000
Q100/DC-120V	15220	100	120	T-4	DC Bayonet (BA15d)	CC-8	2.44/61.9	0.52/13.0	2000
Q100/MC-120V	15234	100	120	T-4	Miniature Candelabra Screw (E11)	CC-8	2.84/72.0	0.52/13.0	2000
Q100CL/DC-120V	15219	100	120	T-4	DC Bayonet (BA15d)	CC-8	2.44/61.9	0.52/13.0	2000
Q100CL/DC/2V-120V	49600	100	120	T-4 1/4	DC Bayonet (BA15d)	CC-2V	2.44/61.9	0.55/14.0	1000
Q100CL/DC/2V-130V	15230	100	130	T-4	DC Bayonet (BA15d)	CC-2V	2.44/61.9	0.52/13.0	2000
Q100CL/MC-120V	15232	100	120	T-4	Miniature Candelabra Screw (E11)	CC-8	2.84/72.0	0.52/13.0	2000
Q100CL/MC/2V-120V	49598	100	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	2.76/70.0	0.52/13.0	750
Q100CL/MC/2V-130V	15236	100	130	T-4	Miniature Candelabra Screw (E11)	CC-2V	2.84/72.0	0.52/13.0	2000
Q100DC/2V-120V	49596	100	120	T-4	DC Bayonet (BA15d)	CC-2V	2.44/61.9	0.52/13.0	2000
Q100MC/2V-120V	49599	100	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	2.76/70.0	0.52/13.0	750
Q150CL/DC-120V	49604	150	120	T-4	DC Bayonet (BA15d)	CC-8	2.44/61.9	0.52/13.0	2000
Q150CL/DC-130V	15250	150	130	T-4	DC Bayonet (BA15d)	CC-8	2.44/61.9	0.52/13.0	2000
Q150CL/MC-120V	49601	150	120	T-4 1/4	Miniature Candelabra Screw (E11)	CC-8	3.00/76.2	0.55/14.0	2000
Q150CL/MC-130V	15239	150	130	T-4 1/4	Miniature Candelabra Screw (E11)	CC-8	3.00/76.2	0.55/14.0	2000
Q150CL/MC/2V-130V	15252	150	130	T-4	Miniature Candelabra Screw (E11)	CC-2V	2.84/72.0	0.52/13.0	1000
Q150DC-120V	49602	150	120	T-4	DC Bayonet (BA15d)	CC-8	2.68/68.0	0.52/13.0	2000
Q150MC-120V	49603	150	120	T-4 1/4	Miniature Candelabra Screw (E11)	CC-8	3.00/76.2	0.55/14.0	2000
Q250CL/DC-120V	49610	250	120	T-4 1/4	DC Bayonet (BA15d)	CC-8	3.15/80.0	0.55/14.0	2000

Halogen Lamps

Halogen Lamps

Single Ended Halogen Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
Q250CL/DC-130V	15264	250	130	T-4	DC Bayonet (BA15d)	CC-8	3.00/76.2	0.52/13.0	2000
Q250CL/MC-120V	49609	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.15/80.0	0.52/13.0	2000
Q250CL/MC-130V	15268	250	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.15/80.0	0.52/13.0	2000
Q250DC-120V	49607	250	120	T-4 1/4	DC Bayonet (BA15d)	CC-8	3.15/80.0	0.55/14.0	2000
Q250DC-130V	15266	250	130	T-4	DC Bayonet (BA15d)	CC-8	3.00/76.2	0.52/13.0	2000
Q250MC-120V	49608	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.19/81.0	0.52/13.0	2000
Q250MC-130V	15270	250	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.19/81.0	0.52/13.0	2000
Q500/MC-120V	49612	500	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.52/13.0	1700
Q500/MC-130V	49614	500	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.52/13.0	1700
Q500CL/DC-120V	15282	500	120	T-4	DC Bayonet (BA15d)	CC-8	3.75/95.3	0.59/15.0	1700
Q500CL/MC-120V	49613	500	120	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.55/14.0	1700
Q500CL/MC-130V	49615	500	130	T-4	Miniature Candelabra Screw (E11)	CC-8	3.75/95.3	0.52/13.0	1700
Q500DC-120V	15284	500	120	T-4	DC Bayonet (BA15d)	CC-8	3.75/95.3	0.59/15.0	1700

Double Ended Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
Q100T3/CL/120V	15159	100	120	T-3	Recessed Single Contact (R7s)	CC-8	4.69/119.1	0.40/10.0	2000
Q150T3/CL/120V	15161	150	120	T-3	Recessed Single Contact (R7s)	CC-8	4.69/119.1	0.40/10.0	2000
Q250T3/CL/120V	15162	250	120	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/120V	15164	300	120	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/130V	15166	300	130	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/220V	15168	300	220	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q300T3/CL/240V	00196	300	240	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/120V	15170	500	120	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/130V	15172	500	130	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/220V	15174	500	220	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q500T3/CL/240V	15176	500	240	T-3	Recessed Single Contact (R7s)	C-8	4.69/119.1	0.40/10.0	2000
Q750T3/CL/120V	49568	750	120	T-3	Recessed Single Contact (R7s)	C-8	7.50/190.5	0.40/10.0	2000
Q750T3/CL/240V	15180	750	240	T-3	Recessed Single Contact (R7s)	C-8	7.50/190.5	0.40/10.0	2000
Q1000T3/CL/120V	49569	1000	120	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1000T3/CL/220V	15182	1000	220	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1000T3/CL/240V	15184	1000	240	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1000T3/CL/277V	15186	1000	277	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/120V	49570	1500	120	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/208V	15188	1500	208	T-3	Recessed Single Contact (R7s)	C-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/220V	15190	1500	220	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/240V	15192	1500	240	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000
Q1500T3/CL/277V	15194	1500	277	T-3	Recessed Single Contact (R7s)	CC-8	10.06/255.6	0.40/10.0	2000

Double Ended Short Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
Q100W/S120V	15200	100	120	T-2 1/2	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.315/8.0	2000
Q100W/S130V	15202	100	130	T-2 1/2	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.315/8.0	2000
Q150W/S120V	15206	150	120	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q150W/S130V	15208	150	130	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q200W/S120V	15211	200	120	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q200W/S130V	15213	200	130	T-2 3/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.344/8.74	2000
Q200W/S220V	15209	200	220	T-2 3/4	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.344/8.74	2000
Q250W/S120V	49571	250	120	T-2 7/8	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.360/9.13	2000
Q300W/S120V	00019	300	120	T-2 7/8	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.360/9.13	2000
Q300W/S130V	15216	300	130	T-2 7/8	Recessed Single Contact (R7s)	CC-8	3.15/80.0	0.360/9.13	2000
Q400W/S130V	15221	400	130	T-3 1/4	Recessed Single Contact (R7s)	C-8	3.15/80.0	0.406/10.32	2000

G4 Base 2-pin Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
JC12V5W-FR	81120	5	12	T-3	G4 (Sub-Miniature 2-Pin)	C-6	1.38/35.0	0.36/9.0	2000
JC12V20W	03510	20	12	T-3	G4 (Sub-Miniature 2-Pin)	C-6	1.38/35.0	0.36/9.0	50
JC12V30W	03520	30	12	T-3	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	50
JCD6V10WH20	15001	10	6	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD6V20WH20	15003	20	6	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD12V5WH20	15005	5	12	T-2 1/2	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.32/8.2	2000
JCD12V10WH20	15007	10	12	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD12V20WH20	15009	20	12	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	1.22/31.0	0.36/9.0	2000
JCD12V35WH20	49561	35	12	T-3 1/2	G4 (Sub-Miniature 2-Pin)	CC-6	1.22/31.0	0.36/9.0	2000
JCD24V20WH20	15011	20	24	T-3 1/4	G4 (Sub-Miniature 2-Pin)	CC-6	1.22/31.0	0.44/11.0	2000

Halogen Lamps

G6.35 Base 2-pin Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
JC12V100WH20	15023	100	12	T-3 1/2	G6.35	C-6	1.73/44.0	0.51/13.0	1200
JC12V20WH20	15013	20	12	T-3	G6.35	C-6	1.73/44.0	0.46/11.5	2000
JC12V30WH20	15015	30	12	T-3 1/2	G6.35	C-6	1.73/44.0	0.46/11.5	2000
JC12V35WH20	15017	35	12	T-3 1/2	G6.35	C-6	1.73/44.0	0.46/11.5	2000
JC12V50WH20	15019	50	12	T-3 1/2	G6.35	C-8	1.73/44.0	0.46/11.5	2000
JC12V75WH20	15021	75	12	T-3 1/4	G6.35	C-6	1.73/44.0	0.46/11.5	2000

Bi-pin Line Voltage Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
JCD130V20WG6.35	00307	20	130	T-4	G6.35	CC-6V	1.44/36.5	0.52/13	1500
JCD130V20WG8	00314	20	130	T-4	G8	CC-6V	1.44/36.5	0.52/13	1500
JCD130V25WG6.35	00308	25	130	T-4	G6.35	CC-6V	1.44/36.5	0.52/13	1500
JCD130V25WG8	00315	25	130	T-4	G8	CC-6V	1.44/36.5	0.52/13	1500
JCD130V25WG9	00321	25	130	T-4	G9	4-Style	1.81/46	0.52/13	2000
JCD130V25WG9/F	00326	25	130	T-4	G9	4-Style	1.81/46	0.52/13	2000
JCD130V35WG6.35	00309	35	130	T-4	G6.35	CC-6V	1.77/45	0.52/13	2000
JCD130V35WG8	00316	35	130	T-4	G8	CC-6V	1.77/45	0.52/13	2000
JCD130V40WG9	00322	40	130	T-4	G9	4-Style	1.81/46	0.52/13	2000
JCD130V40WG9/F	00327	40	130	T-4	G9	4-Style	1.81/46	0.52/13	2000
JCD130V50WG6.35	00311	50	130	T-4	G6.35	CC-2V	1.77/45	0.52/13	2000
JCD130V50WG8	00317	50	130	T-4	G8	CC-2V	1.77/45	0.52/13	2000
JCD130V50WG9	00323	50	130	T-4	G9	4-Style	1.81/46	0.52/13	2000
JCD130V50WG9/F	00328	50	130	T-4	G9	4-Style	1.81/46	0.52/13	2000
JCD130V60WG9	00324	60	130	T-4	G9	4-Style	1.93/49	0.52/13	1500
JCD130V60WG9/F	00329	60	130	T-4	G9	4-Style	1.93/49	0.52/13	1500
JCD130V75WG6.35	00312	75	130	T-4	G6.35	CC-7A	1.77/45	0.52/13	2000
JCD130V75WG8	00318	75	130	T-4	G8	CC-7A	1.77/45	0.52/13	2000
JCD130V75WG9	00325	75	130	T-4	G9	4-Style	1.93/49	0.52/13	1500
JCD130V75WG9/F	00331	75	130	T-4	G9	4-Style	1.93/49	0.52/13	1500
JCD130V100WG8	00319	100	130	T-4	G8	CC-7A	1.97/50	0.53/13.5	1500

Halogen Heat Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	MOL	MOD	Life Hours
17002	17002	375	115-125	T-3	6 in Leads	C-8	8.82/224.0	0.40/10.0	5000
17004	17004	375	115-125	T-3	Recessed Single Contact (R7s)	C-8	8.70/221.0	0.40/10.0	5000
17006	17006	500	115-125	T-3	6 in Leads	C-8	8.82/224.0	0.40/10.0	5000
17008	17008	500	115-125	T-3	6 in Leads	C-8	8.82/224.0	0.40/10.0	5000
17010	17010	500	115-125	T-3	Recessed Single Contact (R7s)	C-8	8.70/221.0	0.40/10.0	5000
17012	17012	1000	200-220	T-3	6 in Leads	C-8	13.78/350.0	0.40/10.0	5000
17014	17014	1000	230-250	T-3	6 in Leads	C-8	13.78/350.0	0.40/10.0	5000
17016	17016	1000	230-250	T-3	6 in Leads	C-8	11.89/302.0	0.40/10.0	5000
17018	17018	1000	230-250	T-3	6 in Leads	C-8	13.78/350.0	0.40/10.0	5000
17022	17022	1200	144	T-3	6 in Leads	C-8	8.82/224.0	0.40/10.0	5000
17024	17024	1600	200-220	T-3	6 in Leads	C-8	19.80/503.0	0.40/10.0	5000
17026	17026	1600	230-250	T-3	6 in Leads	C-8	19.80/503.0	0.40/10.0	5000
17028	17028	1600	277	T-3	6 in Leads	C-8	19.80/503.0	0.40/10.0	5000
17030	17030	1600	230-250	T-3	6 in Leads	C-8	19.80/503.0	0.40/10.0	5000
17032	17032	1600	200-220	T-3	Recessed Single Contact (R7s)	C-8	19.63/498.5	0.40/10.0	5000
17034	17034	1600	230-250	T-3	Recessed Single Contact (R7s)	C-8	19.63/498.5	0.40/10.0	5000
17040	17040	2000	230-250	T-3	6 in Leads	C-8	13.78/350.0	0.40/10.0	5000
17042	17042	2500	460-500	T-3	6 in Leads	C-8	28.82/732	0.40/10.0	5000
17044	17044	2500	460-500	T-3	Recessed Single Contact (R7s)	C-8	28.62/727	0.40/10.0	5000
17046	17046	2500	460-500	T-3	6 in Leads	C-8	28.82/732	0.40/10.0	5000
17048	17048	3650	480	T-3	6 in Leads	C-8	41.6/1057	0.40/10.0	5000
17050	17050	3800	550-600	T-3	6 in Leads	C-8	41.8/1062	0.40/10.0	5000
17052	17052	3800	550-600	T-3	6 in Leads	C-8	41.8/1062	0.40/10.0	5000

SoLux Halogen Lamps

SoLux Halogen Lamps

SoLux MR16 3500K Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	CRI	Beam Angle
18006	18006	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	10
18007	18007	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	17
18008	18008	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	36
18009	18009	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	24
35006	35006	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	10
35007	35007	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	17
35008	35008	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	36
35009	35009	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	24

SoLux Halogen Lamps

SoLux MR16 4100K Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	CRI	Beam Angle
18011	18011	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	10
18012	18012	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	17
18013	18013	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	36
18014	18014	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	24
35011	35011	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	10
35012	35012	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	17
35013	35013	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	36
35014	35014	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	98+	24

SoLux MR16 4700K Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	CRI	Beam Angle
18001	18001	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	10
18002	18002	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	17
18003	18003	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	36
18004	18004	50	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	24
35001	35001	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	10
35002	35002	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	17
35003	35003	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	36
35004	35004	35	12	GU5.3	C-8	1.77/45	1.97/50	4000	99+	24

SoLux PAR 3500K Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Lumens	Life Hours	CRI	Beam Angle
50PAR20/FL30/3500K	06983	50	120	PAR 20	Medium Screw (E26)	275	2500	90	30
50PAR20/SP10/3500K	07074	50	120	PAR 20	Medium Screw (E26)	275	2500	90	10
75PAR30/FL30/3500K	07119	75	120	PAR 30	Medium Screw (E26)	600	2500	90	30
75PAR30/SP10/3500K	07023	75	120	PAR 30	Medium Screw (E26)	600	2500	90	10
90PAR38/FL30/3500K	07041	90	120	PAR 38	Medium Screw (E26)	800	2500	90	30
90PAR38/SP10/3500K	06858	90	120	PAR 38	Medium Screw (E26)	800	2500	90	10
90PAR38/WFL50/3500K	07000	90	120	PAR 38	Medium Screw (E26)	800	2500	90	50

Incandescent Lamps

A Shaped Incandescent Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
40A-130V	49819	40	130	A-19	Medium Screw (E26)	CC-6	380	4.44/112.7	2.38/60.6	2000
40A/CL-130V	49846	40	130	A-19	Medium Screw (E26)	CC-6	390	4.44/112.7	2.38/60.6	2000
40A15-130V	44390	40	130	A-15	Medium Screw (E26)	C-2V	435	3.5/89	1.9/48	1500
40A15-230/250V	44394	40	230-250	A-15	Medium Screw (E26)	C-2F	435	3.5/89	1.9/48	1500
40A15/F-130V	44392	40	130	A-15	Medium Screw (E26)	C-2V	435	3.5/89	1.9/48	1500
40A15/F-230/250V	44396	40	230-250	A-15	Medium Screw (E26)	C-2F	435	3.5/89	1.9/48	1500
60A-130V	49823	60	130	A-19	Medium Screw (E26)	CC-6	690	4.44/112.7	2.38/60.6	2000
60A/CL-130V	49848	60	130	A-19	Medium Screw (E26)	CC-6	700	4.44/112.7	2.38/60.6	2000
75A-130V	49825	75	130	A-19	Medium Screw (E26)	CC-6	890	4.44/112.7	2.38/60.6	2000
75A/CL-130V	49850	75	130	A-19	Medium Screw (E26)	CC-6	900	4.44/112.7	2.38/60.6	2000
75A/SW-130V	49851	75	130	A-19	Medium Screw (E26)	CC-6	850	4.44/112.7	2.38/60.6	2000

Rough Service Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
50A/RS	15800	50	130	A-19	Medium Screw (E26)	C-9	380	4.44/112.8	2.38/60.3	5000
50A/RS-12V	15812	50	12	A-19	Medium Screw (E26)	C-6	500	4.44/112.8	2.38/60.3	2500
50A/RS/TF	15806	50	130	A-19	Medium Screw (E26)	C-9	350	4.44/112.8	2.38/60.3	5000
75A/RS	15802	75	130	A-19	Medium Screw (E26)	C-9	700	4.44/112.8	2.38/60.3	5000
75A/RS-12V	15814	75	12	A-19	Medium Screw (E26)	C-6	750	4.44/112.8	2.38/60.3	2500
75A/RS/TF	15808	75	130	A-19	Medium Screw (E26)	C-9	660	4.44/112.8	2.38/60.3	5000
100A/RS	15804	100	130	A-19	Medium Screw (E26)	C-9	1050	4.44/112.8	2.38/60.3	5000
100A/RS-12V	15816	100	12	A-19	Medium Screw (E26)	C-6	1100	4.44/112.8	2.38/60.3	2500
100A/RS/TF	15810	100	130	A-19	Medium Screw (E26)	C-9	1000	4.44/112.8	2.38/60.3	5000
150A/RS	00008	150	130	A-21	Medium Screw (E26)	C-9	1650	4.96/126	2.63/66.7	5000
150A/RS/TF	01863	150	130	A-21	Medium Screw (E26)	C-9	1650	4.96/126	2.63/66.7	5000

Incandescent Lamps

Incandescent Lamps

C Shaped Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
4C7/120V	40353	4	120	C-7	Candelabra Screw (E12)	C-7A	20	2.30/58.4	0.88/22.3	3000
4C7/130V	40351	4	130	C-7	Candelabra Screw (E12)	C-7A	15	2.30/58.4	0.88/22.3	3000
7C7/120V	40874	7	120	C-7	Candelabra Screw (E12)	C-7A	37	2.30/58.4	0.88/22.3	3000
7C7/130V	40875	7	130	C-7	Candelabra Screw (E12)	C-7A	35	2.30/58.4	0.88/22.3	3000
7C7/130V-W	44318	7	130	C-7	Candelabra Screw (E12)	C-7A	n/a	2.30/58.4	0.88/22.3	3000
10C7/120V	40073	10	120	C-7	Candelabra Screw (E12)	C-7A	64	2.30/58.4	0.88/22.3	5000+
10C7DC/120V	40154	10	120	C-7	DC Bayonet (BA15d)	C-7A	64	2.13/54.1	0.88/22.3	5000+

R & BR Incandescent Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
30R20/FL-120V	49791	30	120	R-20	Medium Screw (E26)	CC-6	245	3.94/100		2000
30R20/FL-130V	49792	30	130	R-20	Medium Screw (E26)	CC-6	245	3.94/100		5000 Hrs at 120v
45BR30/FL-120V	49797	45	120	BR-30	Medium Screw (E26)	CC-6	390	5.38/136.7		2000
45R20/FL-120V	05986	45	120	R-20	Medium Screw (E26)	CC-6	360	3.94/100		2000
45R20/FL-130V	05987	45	130	R-20	Medium Screw (E26)	CC-6	340	3.94/100		5000 Hrs at 120v
65BR30/FL-120V	49798	65	120	BR-30	Medium Screw (E26)	CC-6	620	5.38/136.7		2000
65BR30/FL-130V	49799	65	130	BR-30	Medium Screw (E26)	CC-6	620	5.38/136.7		5000 Hrs at 120v
65BR30/SP-120V	49811	65	120	BR-30	Medium Screw (E26)	CC-6	620	5.38/136.7		2000
65BR30/SP-130V	49800	65	130	BR-30	Medium Screw (E26)	CC-6	620	5.38/136.7		5000 Hrs at 120v
65BR40/FL-120V	49801	65	120	BR-40	Medium Screw (E26)	CC-6	620	6.56/166.6		2000
65BR40/FL-130V	49802	65	130	BR-40	Medium Screw (E26)	CC-6	620	6.56/166.6		5000 Hrs at 120v

S Shaped Lamps



Ordering Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
3S6/5-120V	3	120	S-6	Candelabra Screw (E12)	C-7A	11.31	1.88/47.8	0.75/19.1	1500
3S6/5-130V	3	130	S-6	Candelabra Screw (E12)	C-7A	11.31	1.88/47.8	0.75/19.1	1500
3S6/5DC-120V	3	120	S-6	DC Bayonet (BA15d)	C-7A	11.31	1.82/46.2	0.75/19.1	3000
6S6/120V	6	120	S-6	Candelabra Screw (E12)	C-7A	39	1.88/47.8	0.75/19.1	1500
6S6/12V	6	12	S-6	Candelabra Screw (E12)	C-6	48	1.88/47.8	0.75/19.1	1500
6S6/130V	6	130	S-6	Candelabra Screw (E12)	C-7A	38	1.88/47.8	0.75/19.1	1500
6S6/145V	6	145	S-6	Candelabra Screw (E12)	C-7A	17.60	1.88/47.8	0.75/19.1	1500
6S6/155V	6	155	S-6	Candelabra Screw (E12)	C-7A	33	1.88/47.8	0.75/19.1	1500
6S6/18V	6	18	S-6	Candelabra Screw (E12)	C-6	50	1.88/47.8	0.75/19.1	1500
6S6/230V	6	230	S-6	Candelabra Screw (E12)	C-7A	11.31	1.88/47.8	0.75/19.1	1500
6S6/24V	6	24	S-6	Candelabra Screw (E12)	C-6	53	1.88/47.8	0.75/19.1	1500
6S6/30V	6	30	S-6	Candelabra Screw (E12)	C-6	52	1.88/47.8	0.75/19.1	1500
6S6/48V	6	48	S-6	Candelabra Screw (E12)	C-6	47	1.88/47.8	0.75/19.1	1500
6S6/60V	6	60	S-6	Candelabra Screw (E12)	C-7A	43	1.88/47.8	0.75/19.1	1500
6S6/6V	6	6	S-6	Candelabra Screw (E12)	C-6	54	1.88/47.8	0.75/19.1	1500
6S6DC/120V	6	120	S-6	DC Bayonet (BA15d)	C-7A	39	1.82/46.2	0.75/19.1	1500
6S6DC/12V	6	12	S-6	DC Bayonet (BA15d)	C-6	48	1.82/46.2	0.75/19.1	1500
6S6DC/130V	6	130	S-6	DC Bayonet (BA15d)	C-7A	38	1.82/46.2	0.75/19.1	1500
6S6DC/145V	6	145	S-6	DC Bayonet (BA15d)	C-7A	17.60	1.82/46.2	0.75/19.1	1500
6S6DC/24V	6	24	S-6	DC Bayonet (BA15d)	C-6	53	1.82/46.2	0.75/19.1	1500
6S6DC/30V	6	30	S-6	DC Bayonet (BA15d)	C-6	52	1.82/46.2	0.75/19.1	1500
6S6DC/32V	6	32	S-6	DC Bayonet (BA15d)	C-6	50	1.82/46.2	0.75/19.1	1500
6S6DC/48V	6	48	S-6	DC Bayonet (BA15d)	C-6	47	1.82/46.2	0.75/19.1	1500
6S6DC/60V	6	60	S-6	DC Bayonet (BA15d)	C-7A	43	1.82/46.2	0.75/19.1	1500
6S6DC/6V	6	6	S-6	DC Bayonet (BA15d)	C-6	54	1.82/46.2	0.75/19.1	1500
10S6/120V	10	120	S-6	Candelabra Screw (E12)	C-7A	60	1.88/47.8	0.75/19.1	1500
10S6/230V	10	230	S-6	Candelabra Screw (E12)	C-7A	60	1.88/47.8	0.75/19.1	1500
10S6/250V	10	250	S-6	Candelabra Screw (E12)	C-7A	60	1.88/47.8	0.75/19.1	1500
10S6DC/250V	10	250	S-6	DC Bayonet (BA15d)	C-7A	60	1.82/46.2	0.75/19.1	1500
40S11N	40	130	S-11	Intermediate Screw (E17)	C-2V		2.45/62	1.42/36	3500 at 120V

Incandescent Lamps

T Shaped Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
15T4C-130V	16017	15	130	T-4	Candelabra Screw (E12)	C-7A	90	1.97/50.0	0.54/39.1	1500
15T6C-120V	81134	15	120	T-6	Candelabra Screw (E12)	C-7A	90	3.06/77.7	0.77/19.6	2000
15T6C-130V	43000	15	130	T-6	Candelabra Screw (E12)	C-7A	90	3.06/77.7	0.77/19.6	2000
15T6C-145V	43002	15	145	T-6	Candelabra Screw (E12)	C-7A	90	3.06/77.7	0.77/19.6	2000, (7500 @ 120V)
15T7C-130V	43006	15	130	T-7	Candelabra Screw (E12)	C-7A	90	2.25/57.2	0.89/22.6	1500
15T7DC-130V	43008	15	130	T-7	DC Bayonet (BA15d)	C-7A	90	2.25/57.2	0.89/22.6	1500
15T7N-130V	43004	15	130	T-7	Intermediate Screw (E17)	C-7A	90	2.25/57.2	0.89/22.6	1500
20T6.5DC/F-130V	43016	20	130	T-6 1/2	DC Bayonet (BA15d)	C-8	170	5.56/141.2	0.83/21.1	3000
20T6-1/2DC-130V	43014	20	130	T-6 1/2	DC Bayonet (BA15d)	C-8	180	5.56/141.2	0.83/21.1	3000
20T6-1/2F-130V	43012	20	130	T-6 1/2	Intermediate Screw (E17)	C-8	170	5.5/139.7	0.83/21.1	3000
20T6-1/2N-130V	43010	20	130	T-6 1/2	Intermediate Screw (E17)	C-8	180	5.5/139.7	0.83/21.1	3000
20T6-1/2N-145V	44402	20	145	T-6 1/2	Intermediate Screw (E17)	C-8	170	5.5/139.7	0.83/21.1	3000
25T6.5DC/F-130V	43026	25	130	T-6 1/2	DC Bayonet (BA15d)	C-8	200	5.56/141.2	0.83/21.1	3000
25T6.5N/F-130V	43022	25	130	T-6 1/2	Intermediate Screw (E17)	C-8	200	5.5/139.7	0.83/21.1	3000
25T6-1/2DC-130V	43024	25	130	T-6 1/2	DC Bayonet (BA15d)	C-8	210	5.5/139.7	0.83/21.1	3000
25T6-1/2N-130V	43020	25	130	T-6 1/2	Intermediate Screw (E17)	C-8	210	5.5/139.7	0.83/21.1	3000
25T6C-120V	43018	25	120	T-6	Candelabra Screw (E12)	C-7A	190	3.06/77.7	0.77/19.6	2000
25T8C-120V	43028	25	120	T-8	Candelabra Screw (E12)	C-7A	180	2.63/66.8	1.04/26.4	1500
25T8DC-120V	49563	25	120	T-8	DC Bayonet (BA15d)	C-7A	180	2.63/66.8	1.04/26.4	1500
25T8DC-130V	43032	25	130	T-8	DC Bayonet (BA15d)	C-7A	180	2.63/66.8	1.04/26.4	1500
25T8N-130V	43030	25	130	T-8	Intermediate Screw (E17)	C-7A	180	2.63/66.8	1.04/26.4	1500
25T10-130V	43034	25	130	T-10	Medium Screw (E26)	C-8	210	5.19/131.8	1.25/31.8	1500
25T10/F-130V	43036	25	130	T-10	Medium Screw (E26)	C-8	200	5.19/131.8	1.25/31.8	1500
25T10/IF-120	41522	25	120	T-10	Medium Screw (E26)	C-8		5.19/131.8	1.25/31.8	1500
40T6-1/2N-130V	43038	40	130	T-6 1/2	Intermediate Screw (E17)	C-8	330	5.5/139.7	0.83/21.1	1500
40T10-130V	43042	40	130	T-10	Medium Screw (E26)	C-8	320	5.19/131.8	1.25/31.8	1500
40T10/F-130V	43044	40	130	T-10	Medium Screw (E26)	C-8	310	5.19/131.8	1.25/31.8	1500

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
1A/27W	00403	2.11	12.8	G7.1	C-6	2.5/63.5	0.5/13	300
1A/50W	00734	3.91	12.8	G7.1	C-6	2.5/63.5	0.5/13	300
2	40446	0.021	5	Wire Leads (WL)	C-2R	0.20/5.1	0.09/2.3	10000
3S6/5-120V	40552	0.025	120	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
3S6/5-130V	40554	0.023	130	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
3S6/5DC-120V	40556	0.025	120	DC Bayonet (BA15d)	C-7A	1.82/46.2	0.75/19.1	3000
4C7/120V	40353	0.033	120	Candelabra Screw (E12)	C-7A	2.30/58.4	0.88/22.3	3000
4C7/130V	40351	0.031	130	Candelabra Screw (E12)	C-7A	2.30/58.4	0.88/22.3	3000
6MB	40777	0.14	6	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.33/8.4	20000
6PSB5	40778	0.14	6	Slide Base 5 (TS5)	C-2V	1.11/28.2	0.27/6.9	20000
6S6/120V	40786	0.05	120	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
6S6/12V	40784	0.50	12	Candelabra Screw (E12)	C-6	1.88/47.8	0.75/19.1	1500
6S6/130V	40788	0.046	130	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
6S6/145V	40789	0.041	145	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
6S6/155V	40790	0.039	155	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
6S6/18V	49717	0.33	18	Candelabra Screw (E12)	C-6	1.88/47.8	0.75/19.1	1500
6S6/230V	40791	0.026	230	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
6S6/24V	40792	0.25	24	Candelabra Screw (E12)	C-6	1.88/47.8	0.75/19.1	1500
6S6/30V	40794	0.20	30	Candelabra Screw (E12)	C-6	1.88/47.8	0.75/19.1	1500
6S6/48V	40796	0.125	48	Candelabra Screw (E12)	C-6	1.88/47.8	0.75/19.1	1500
6S6/60V	40800	0.10	60	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
6S6/6V	40798	1	6	Candelabra Screw (E12)	C-6	1.88/47.8	0.75/19.1	1500
6S6DC/12V	40802	0.50	12	DC Bayonet (BA15d)	C-6	1.82/46.2	0.75/19.1	1500
6S6DC/130V	40806	0.046	130	DC Bayonet (BA15d)	C-7A	1.82/46.2	0.75/19.1	1500
6S6DC/145V	40807	0.041	145	DC Bayonet (BA15d)	C-7A	1.82/46.2	0.75/19.1	1500
6S6DC/24V	40808	0.25	24	DC Bayonet (BA15d)	C-6	1.82/46.2	0.75/19.1	1500
6S6DC/30V	40810	0.20	30	DC Bayonet (BA15d)	C-6	1.82/46.2	0.75/19.1	1500
6S6DC/32V	40811	0.1875	32	DC Bayonet (BA15d)	C-6	1.82/46.2	0.75/19.1	1500
6S6DC/48V	40812	0.125	48	DC Bayonet (BA15d)	C-6	1.82/46.2	0.75/19.1	1500
6S6DC/60V	40816	0.10	60	DC Bayonet (BA15d)	C-7A	1.82/46.2	0.75/19.1	1500
6S6DC/6V	40814	1	6	DC Bayonet (BA15d)	C-6	1.82/46.2	0.75/19.1	1500
7C7/120V	40874	0.0583	120	Candelabra Screw (E12)	C-7A	2.30/58.4	0.88/22.3	3000
7C7/130V	40875	0.0538	130	Candelabra Screw (E12)	C-7A	2.30/58.4	0.88/22.3	3000
7C7/130V-W	44318	0.0538	130	Candelabra Screw (E12)	C-7A	2.30/58.4	0.88/22.3	3000
8-3995	44300	0.025	120	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.43/10.9	7500
10C7DC/120V	40154	0.083	120	DC Bayonet (BA15d)	C-7A	2.13/54.1	0.88/22.3	5000+
10ESB5	44014	0.035	10	Slide Base 5 (TS5)	C-6	0.92/23.4	0.27/6.9	10000
10S6/230V	42446	0.043	230	Candelabra Screw (E12)	C-7A	1.88/47.8	0.75/19.1	1500
10S6DC/250V	40149	0.04	250	DC Bayonet (BA15d)	C-7A	1.82/46.2	0.75/19.1	1500
12ESB5	40218	0.04	12	Slide Base 5 (TS5)	C-2V	0.92/23.4	0.27/6.9	7500
12MB	40220	0.17	12	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.33/8.4	12000
12PSB5	40222	0.17	12	Slide Base 5 (TS5)	C-2F	1.11/28.2	0.27/6.9	12000
12RB	44016	0.17	12	Miniature Bayonet (BA9s)	C-2F	1.16/29.5	0.91/23.1	12000

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
12RC	40223	0.17	12	Candelabra Screw (E12)	C-2F	1.22/31.0	0.91/23.1	12000
13	40247	0.3	3.7	Miniature Screw (E10)	C-2R	0.94/23.9	0.43/11.0	15
14	40264	0.3	2.47	Miniature Screw (E10)	C-2R	0.94/23.9	0.43/11.0	15
14-BP	40265	0.3	2.47	Miniature Screw (E10)	C-2R	0.94/23.9	0.43/11.0	15
15T6C-130V	43000	0.12	130	Candelabra Screw (E12)	C-7A	3.06/77.7	0.77/19.6	2000
15T6C-145V	43002	0.10	145	Candelabra Screw (E12)	C-7A	3.06/77.7	0.77/19.6	2000, (7500 @ 120V)
15T7C-130V	43006	0.12	130	Candelabra Screw (E12)	C-7A	2.25/57.2	0.89/22.6	1500
15T7DC-130V	43008	0.12	130	DC Bayonet (BA15d)	C-7A	2.25/57.2	0.89/22.6	1500
15T7N-130V	43004	0.12	130	Intermediate Screw (E17)	C-7A	2.25/57.2	0.89/22.6	1500
16ESB5	40291	0.04	16	Slide Base 5 (TS5)	C-2F	0.92/23.4	0.27/6.9	7500
17	44322	0.065	28	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	5000
18	40350	0.04	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	5000
20-99	16024	1.08	13.0	SC Bayonet (BA15s)	C-6	3.00/76.2	2.12/53.9	1000
20-99F	16025	1.08	13.0	SC Bayonet (BA15s)	C-6	3.00/76.2	2.12/53.9	1000
20T6.5DC/F-130V	43016	0.15	130	DC Bayonet (BA15d)	C-8	5.56/141.2	0.83/21.1	3000
20T6-1/2DC-130V	43014	0.15	130	DC Bayonet (BA15d)	C-8	5.56/141.2	0.83/21.1	3000
20T6-1/2F-130V	43012	0.15	130	Intermediate Screw (E17)	C-8	5.5/139.7	0.83/21.1	3000
20T6-1/2N-130V	43010	0.15	130	Intermediate Screw (E17)	C-8	5.5/139.7	0.83/21.1	3000
20T6-1/2N-145V	44402	0.14	145	Intermediate Screw (E17)	C-8	5.5/139.7	0.83/21.1	3000
24	42240	0.24	14	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.91/23.1	0.34/8.7	1500
24-BP	42010	0.24	14	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.91/23.1	0.34/8.7	1500
24A	42244	0.24	14	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.91/23.1	0.34/8.7	1500
24CSB	40513	0.017	24	Slide Base 5 (TS5)	C-2F	0.92/23.4	0.27/6.9	15000
24E1	44017	0.035	24	Slide Base 1 (TS1)	C-2F	1.69/42.9	0.27/6.9	10000
24E2	44018	0.035	24	Slide Base 2 (TS2)	C-2F	1.69/42.9	0.27/6.9	7000
24E3	40509	0.035	24	Slide Base 3 (TS3)	C-2F	1.69/42.9	0.27/6.9	7000
24ESB5	40507	0.04	24	Slide Base 5 (TS5)	C-2F	0.92/23.4	0.27/6.9	8000
24EX	44020	0.035	24	Slide Base 2 (TS2)	C-2F	1.69/42.9	0.27/6.9	8000
24MB	40510	0.073	24	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.33/8.4	10000
24PSB5	40512	0.073	24	Slide Base 5 (TS5)	C-2F	1.11/28.2	0.27/6.9	10000
24RC	40515	0.073	24	Candelabra Screw (E12)	C-2F	1.22/31.0	0.91/23.1	10000
24X	40516	0.035	24	Slide Base 2 (TS2)	C-2F	1.69/42.9	0.27/6.9	8000
25T6.5DC/F-130V	43026	0.19	130	DC Bayonet (BA15d)	C-8	5.56/141.2	0.83/21.1	3000
25T6.5N/F-130V	43022	0.19	130	Intermediate Screw (E17)	C-8	5.5/139.7	0.83/21.1	3000
25T6-1/2DC-130V	43024	0.19	130	DC Bayonet (BA15d)	C-8	5.5/139.7	0.83/21.1	3000
25T6-1/2N-130V	43020	0.19	130	Intermediate Screw (E17)	C-8	5.5/139.7	0.83/21.1	3000
25T6C-120V	43018	0.21	120	Candelabra Screw (E12)	C-7A	3.06/77.7	0.77/19.6	2000
25T8C-120V	43028	0.21	120	Candelabra Screw (E12)	C-7A	2.63/66.8	1.04/26.4	1500
25T8DC-120V	49563	0.21	120	DC Bayonet (BA15d)	C-7A	2.63/66.8	1.04/26.4	1500
25T8DC-130V	43032	0.19	130	DC Bayonet (BA15d)	C-7A	2.63/66.8	1.04/26.4	1500
25T8N-130V	43030	0.19	130	Intermediate Screw (E17)	C-7A	2.63/66.8	1.04/26.4	1500
25T10-130V	43034	0.19	130	Medium Screw (E26)	C-8	5.19/131.8	1.25/31.8	1500
25T10/F-130V	43036	0.19	130	Medium Screw (E26)	C-8	5.19/131.8	1.25/31.8	1500
25T10/IF-120	41522	0.21	120	Medium Screw (E26)	C-8	5.19/131.8	1.25/31.8	1500
27	40539	0.3	4.9	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	30
27.0H1	00408	2.11	12.8	GY6.35	C-6	1.33/33.8	0.42/10.7	220
28ESB5	40544	0.04	28	Slide Base 5 (TS5)	C-2F	0.92/23.4	0.27/6.9	6000
28MB	40546	0.04	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.33/8.4	5000
28PSB5	40548	0.04	28	Slide Base 5 (TS5)	C-2F	1.11/28.2	0.27/6.9	5000
28RC	40549	0.4	28	Candelabra Screw (E12)	C-2F	1.22/31.0	0.91/23.1	5000
31	40574	0.3	6.15	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	15
35A2	49460	0.040	35	Slide Base 2 (TS2)	C-2F	1.69/42.9	0.27/6.9	7500
37	40648	0.09	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	2500
37-BP	42014	0.09	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	2500
37.5H1	00446	2.93	12.8	GY6.35	C-6	1.33/33.8	0.42/10.7	200
40	40694	0.15	6.3	Miniature Screw (E10)	C-2R	1.19/30.2	0.43/11.0	3000
40T6-1/2N-130V	43038	0.31	130	Intermediate Screw (E17)	C-8	5.5/139.7	0.83/21.1	1500
40T10-130V	43042	0.31	130	Medium Screw (E26)	C-8	5.19/131.8	1.25/31.8	1500
40T10/F-130V	43044	0.31	130	Medium Screw (E26)	C-8	5.19/131.8	1.25/31.8	1500
41	40700	0.5	2.5	Miniature Screw (E10)	C-2R	1.19/30.2	0.43/11.0	3000
41-BP	81133	0.5	2.5	Miniature Screw (E10)	C-2R	1.19/30.2	0.43/11.0	3000
43	40706	0.5	2.5	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44	40716	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44-A	05198	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44-B	01347	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44-BP	49419	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44-G	01349	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44-P	05204	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44-R	01351	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
44-Y	01353	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
46	40726	0.25	6.3	Miniature Screw (E10)	C-2R	1.19/30.2	0.43/11.0	3000
46-BP	42330	0.25	6.3	Miniature Screw (E10)	C-2R	1.19/30.2	0.43/11.0	3000
47	40730	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
47-A	05202	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
47-B	00025	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
47-BP	49420	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
47-G	00026	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
47-P	05200	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
47-R	00027	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
47-Y	00028	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
48	40732	0.06	2	Miniature Screw (E10)	S-2	1.19/30.2	0.43/11.0	1000
48C2	49549	0.035	48	Slide Base 2 (TS2)	C-2F	1.69/42.9	0.27/6.9	10,000
48ESB5	40738	0.04	48	Slide Base 5 (TS5)	CC-2F	0.92/23.4	0.27/6.9	5000
48MB	40740	0.05	48	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.33/8.4	10000
48PSB5	40742	0.05	48	Slide Base 5 (TS5)	C-7A	1.11/28.2	0.27/6.9	10000
48RC	40743	0.05	48	Candelabra Screw (E12)	C-2F	1.22/31.0	0.91/23.1	10000
49	40744	0.06	2	Miniature Bayonet (BA9s)	C-6	1.19/30.2	0.43/11.0	1000
50	40746	0.22	7.5	Miniature Screw (E10)	C-2R	0.94/23.9	0.43/11.0	1000
51	40756	0.22	7.5	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	1000
51-BP	42016	0.22	7.5	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	1000
51A	01408	0.035	10	Slide Base 6 (TS6)	C-2F	0.92/23.4	0.27/6.9	8000
52	40760	0.1	14.4	Miniature Screw (E10)	C-2V	0.94/23.9	0.43/11.0	1000
52A	44324	0.03	24	Slide Base 6 (TS6)	C-2F	0.92/23.4	0.27/6.9	8000
53	40761	0.12	14.4	Miniature Bayonet (BA9s)	C-2V	0.94/23.9	0.43/11.0	1000
53-BP	40762	0.12	14.4	Miniature Bayonet (BA9s)	C-2V	0.94/23.9	0.43/11.0	1000
55	40766	0.41	7	Miniature Bayonet (BA9s)	C-2R	1.07/27.2	0.59/15.0	200
55-BP	40767	0.41	7	Miniature Bayonet (BA9s)	C-2R	1.07/27.2	0.59/15.0	200
55A/S8	41702	0.55	12	Single Contact Prefocus Flanged (P15s30)	C-8S	2.09/53.1	1.04/26.4	500
55C2	40765	0.050	55	Slide Base 2 (TS2)	C-2F	1.69/42.9	0.27/6.9	5000
55C3	40768	0.05	55	Slide Base 3 (TS3)	CC-2F	1.69/42.9	0.27/6.9	5000
56	44326	0.115	5	Sub-Miniature Wedge (W2.1x4.9d)	C-2R	0.80/20.3	0.23/5.9	20000
57	40771	0.24	14	Miniature Bayonet (BA9s)	C-2V	1.07/27.2	0.59/15.0	500
57-BP	40772	0.24	14	Miniature Bayonet (BA9s)	C-2V	1.07/27.2	0.59/15.0	500
60MB	40820	0.05	60	Miniature Bayonet (BA9s)	CC-2F	1.19/30.2	0.33/8.4	7500
60PSB5	40822	0.05	60	Slide Base 5 (TS5)	CC-2F	1.11/28.2	0.27/6.9	7500
60RB	40821	0.05	60	Miniature Bayonet (BA9s)	CC-7A	1.16/29.5	0.91/23.1	7500
63	40830	0.63	7	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	1000
63-BP	40831	0.63	7	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	1000
63-R	81186	0.63	7	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	1000
64	40835	0.63	7	DC Bayonet (BA15d)	C-6	1.44/36.6	0.75/19.1	1000
67	40845	0.59	13.5	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	5000
67-BP	40846	0.59	13.5	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	5000
67K	49711	0.59	13.5	Candelabra Screw (E12)	C-2R	1.38/35.1	0.75/19.1	5000
68	40850	0.59	13.5	DC Bayonet (BA15d)	C-6	1.44/36.6	0.75/19.1	5000
68-BP	42018	0.59	13.5	DC Bayonet (BA15d)	C-6	1.44/36.6	0.75/19.1	5000
70	40876	0.15	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	100
73	40898	0.08	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	15000
73-BP	42020	0.08	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	15000
74	40928	0.1	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	1000
74-BP	42022	0.1	14	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	1000
77A/S8	41704	0.77	12	Single Contact Prefocus Flanged (P15s30)	C-8S	2.09/53.1	1.04/26.4	500
79	44328	0.2	6	Sub-Miniature Wedge (W2.1x4.9d)	C-2R	0.80/20.3	0.23/5.9	1000
81	40958	1.02	6.5	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	500
82	40964	1.02	6.5	DC Bayonet (BA15d)	C-6	1.44/36.6	0.75/19.1	500
84	40968	0.04	6.3	Sub-Miniature Wedge (W2.1x4.9d)	C-2R	0.80/20.3	0.23/5.9	20000
85	40972	0.04	28	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	7000
86	40974	0.2	6.3	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	20000
86G	00361	0.2	6.3	Sub-Miniature Wedge (W2.1x4.9d)	C-2F	0.80/20.3	0.23/5.9	20000
87	40986	1.91	6.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	300
88	40992	1.91	6.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	300
89	40995	0.58	13	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	750
89-BP	40996	0.58	13	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	750
89K	01785	0.58	13	Candelabra Screw (E12)	C-2R	1.38/35.1	0.75/19.1	750
90	41005	0.58	13	DC Bayonet (BA15d)	C-6	1.44/36.6	0.75/19.1	750
90-BP	41006	0.58	13	DC Bayonet (BA15d)	C-6	1.44/36.6	0.75/19.1	750
90MB	40886	0.03	90	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.33/8.4	5000
93	41033	1.04	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	700
93-BP	41034	1.04	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	700
94	41037	1.04	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	700
96	41041	0.69	13.5	DC Bayonet (BA15d)	C-2V	1.44/36.6	0.75/19.1	5000
97	41043	0.69	13.5	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	5000
97-BP	41044	0.69	13.5	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	5000
97A	41046	0.69	13.5	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	5000
98	41048	0.62	13	SC Bayonet (BA15s)	C-6	1.44/36.6	0.75/19.1	800
105	40163	1.0	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	500
105-BP	42026	1.0	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	500
112	40168	0.25	1.2	Miniature Screw (E10)	S-2	0.93/23.6	0.38/9.6	5
120MB	40226	0.025	120	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.33/8.4	10000
120MB-Neon	40225	0.004	120	Miniature Bayonet (BA9s)	Neon	1.19/30.2	0.38/9.6	10000
120MB/6	44022	0.052	120	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.33/8.4	3000
120PSB5	40230	0.025	120	Slide Base 5 (TS5)	CC-7A	1.11/28.2	0.27/6.9	10000
120PSB5-Neon	40229	0.0035	120	Slide Base 5 (TS5)	Neon	1.12/28.5	0.27/6.9	10000

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
120RB	40231	0.025	120	Miniature Bayonet (BA9s)	CC-7A	1.16/29.5	0.91/23.1	7500
120RC	40253	0.025	120	Candelabra Screw (E12)	CC-7A	1.22/31.0	0.91/23.1	7500
120RC-Neon	40297	0.0035	120	Candelabra Screw (E12)	Neon	1.22/31.0	0.91/23.1	10000
123	40237	0.3	1.25	Miniature Screw (E10)	S-2	0.94/23.9	0.43/11.0	10
124	40238	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	5000
124-BP	42028	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	5000
130	49671	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	5000
130MB	40249	0.025	130	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.33/8.4	10000
131	40252	0.1	1.3	Miniature Screw (E10)	S-2	0.94/23.9	0.43/11.0	50
147	40278	0.43	7	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	1500
155MB	40296	0.025	155	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.33/8.4	10000
155PSB5	40298	0.025	155	Slide Base 5 (TS5)	CC-7A	1.11/28.2	0.27/6.9	10000
158	40300	0.24	14	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	500
158-BP	40301	0.24	14	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	500
159	40303	0.15	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	5000
161	40304	0.19	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	4000
161-BP	42030	0.19	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	4000
168	40317	0.35	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	1500
168-BP	40318	0.35	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	1500
168LL-BP	40337	0.35	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	3000
168NA	00227	0.35	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	1500
168NA-BP	00228	0.35	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	1500
192	40424	0.33	13	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	1000
192-BP	42344	0.33	13	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	1000
193	40426	0.33	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	15000
194	40427	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194-BP	40428	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194A	40430	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194A-BP	40431	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194B	42438	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194B-BP	42440	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194G	00794	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194G-BP	49830	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194LL	42504	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	5000
194LL-BP	40335	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	5000
194NA	40432	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194NA-BP	40433	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194R	42442	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
194R-BP	42444	0.27	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
198	40443	2.25/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
198-BP	42032	2.25/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
198LL	42508	2.25/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
198LL-BP	40331	2.25/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
199	40445	2.25	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
200	00805	0.85	4.0	DC Bayonet (BA15d)	C-6	1.44/36.6	0.75/19.1	50
210	40454	1.78	6.5	DC Bayonet (BA15d)	C-6	1.75/44.5	0.79/20.1	100
211-2	40480	0.97	12.8	Double End Cap	C-8	1.72/43.7	0.38/9.6	1000
211-2-BP	40481	0.97	12.8	Double End Cap	C-8	1.72/43.7	0.38/9.6	1000
211-2/F	42312	0.97	12.8	SV8.5mm	C-8	1.72/43.7	0.42/10.54	1000
211-2/F-BP	42238	0.97	12.8	SV8.5mm	C-8	1.72/43.7	0.42/10.54	1000
211-2B	00837	0.37	12.8	Double End Cap	C-8	1.72/43.7	0.43/11.0	1000
211-2B	00837	0.37	12.8	Double End Cap	C-8	1.72/43.7	0.43/11.0	1000
211-2B-BP	00838	0.37	12.8	Double End Cap	C-8	1.72/43.7	0.43/11.0	1000
211-2R-BP	00841	0.37	12.8	Double End Cap	C-8	1.72/43.7	0.43/11.0	1000
212-2	42256	0.74	13.5	Double End Cap	C-8	1.72/43.7	0.38/9.6	2000
212-2-BP	42036	0.74	13.5	Double End Cap	C-8	1.72/43.7	0.38/9.6	2000
214-2	42040	0.52	13.5	Double End Cap	C-8	1.72/43.7	0.38/9.6	1000
219	49701	0.25	6.3	Miniature Bayonet (BA9s)	C-2V	0.94/23.9	0.43/11.0	5000
222	40492	0.25	2.25	Miniature Screw (E10)	C-2R	0.93/23.6	0.38/9.6	5
222-BP	40493	0.25	2.25	Miniature Screw (E10)	C-2R	0.93/23.6	0.38/9.6	5
233	49702	0.27	2.33	Miniature Screw (E10)	C-2R	0.94/23.9	0.43/11.0	10
238	49704	0.5	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	2000
239	00929	0.36	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	5000+
243	40520	0.27	2.33	Miniature Screw (E10)	C-6	0.93/23.6	0.38/9.6	10
245	49703	0.5	2.46	Miniature Screw (E10)	C-2R	0.94/23.9	0.43/11.0	15
251	40524	0.3	2.47	Midget Flanged (SX6s)	C-2R	0.63/16.0	0.23/5.9	30
257	49674	0.27	14	Miniature Bayonet (BA9s)	C-2R	1.07/27.2	0.59/15.0	500
258	49706	0.27	14	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	500
259	40534	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	5000
265	49707	0.08	28	Miniature Bayonet (BA9s)	C-2F	0.94/23.9	0.43/11.0	5000
267	01034	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	5000
293	40550	0.33	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	5000
293-BP	42044	0.33	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	5000
301	49448	0.17	28	SC Bayonet (BA15s)	C-2F	1.38/35.1	0.62/15.8	500
301-R	07632	0.17	28	SC Bayonet (BA15s)	C-2F	1.38/35.1	0.62/15.8	500

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
303	40562	0.3	28	SC Bayonet (BA15s)	CC-6	1.44/36.6	0.75/19.1	500
304	49103	0.3	28	DC Bayonet (BA15d)	C-2F	1.44/36.6	0.75/19.1	500
306	40566	0.51	28	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	300
307	40568	0.67	28	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	300
308	40570	0.67	28	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	300
311	40576	1.29	28	SC Bayonet (BA15s)	CC-2V	2.38/60.5	1.35/34.3	300
312	01125	1.29	28	DC Bayonet (BA15d)	C-2V	2.38/60.45	1.42/36	300
313	40578	0.17	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	500
313-BP	81130	0.17	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	500
313-R	01132	0.17	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	500
315	40580	0.9	28	SC Bayonet (BA15s)	CC-6	2.00/50.8	1.04/26.4	300
327	40596	0.04	28	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	4000
328	40598	0.2	6	Midget Flanged (SX6s)	C-2R	0.63/16.0	0.23/5.9	1000
330	40599	0.08	14	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	1500
334	40606	0.04	28	Midget Grooved (S5.7s)	C-2F	0.63/16.0	0.23/5.9	4000
335	40607	0.04	28	Midget Screw (E5)	C-2F	0.72/18.3	0.23/5.9	4000
336	49631	0.08	14	Midget Grooved (S5.7s)	C-2F	0.63/16.0	0.23/5.9	1500
337	40616	0.2	6.3	Midget Grooved (S5.7s)	C-2R	0.63/16.0	0.23/5.9	1000
338	01183	0.06	2.7	Midget Flanged (SX6s)	C-2R	0.63/16.0	0.23/5.9	6000
342	01185	0.04	6	Midget Screw (E5)	C-2R	0.63/16.0	0.23/5.9	10000
344	40622	0.014	10	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	50000
345	40624	0.04	6	Midget Flanged (SX6s)	C-2V	0.63/16.0	0.23/5.9	10000
356	40636	0.17	28	Miniature Bayonet (BA9s)	C-2V	0.94/23.9	0.43/11.0	500
359	49787	0.06	1.35	Miniature Screw (E10)	S-2	0.94/23.9	0.43/11.0	50
363	40640	0.2	14	Miniature Bayonet (BA9s)	C-2V	0.94/23.9	0.43/11.0	250
367	49709	0.04	10	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	5000
370	40650	0.04	18	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	10000
373	40654	0.08	14	Midget Screw (E5)	C-2F	0.72/18.3	0.23/5.9	1500
375	01215	0.015	3.0	Midget Flanged (SX6s)	C-2R	0.63/16.0	0.23/5.9	10000
376	40658	0.06	28	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	25000
377	40660	0.075	6.3	Midget Flanged (SX6s)	C-2R	0.63/16.0	0.23/5.9	1000
378	40662	0.2	6.3	Midget Screw (E5)	C-2F	0.72/18.3	0.23/5.9	20000
379	40664	0.2	6.3	Midget Grooved (S5.7s)	C-2F	0.63/16.0	0.23/5.9	20000
380	40666	0.04	6.3	Midget Flanged (SX6s)	C-2V	0.63/16.0	0.23/5.9	20000
381	40668	0.2	6.3	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	20000
382	40670	0.08	14	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	15000
385	40672	0.04	28	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	10000
386	40674	0.08	14	Midget Grooved (S5.7s)	C-2F	0.63/16.0	0.23/5.9	40000
387	40678	0.04	28	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	10000
388	40680	0.04	28	Midget Grooved (S5.7s)	C-2F	0.63/16.0	0.23/5.9	25000
394	40686	0.04	12	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	20000
398	49632	0.2	6.3	Midget Grooved (S5.7s)	C-2R	0.63/16.0	0.23/5.9	5000
399	40692	0.04	28	Midget Screw (E5)	C-2F	0.72/18.3	0.23/5.9	7000
400	40696	0.1	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	1000
407	40698	0.3	4.9	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	50
425	40702	0.5	5	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	15
428	40704	0.25	12.5	Miniature Screw (E10)	C-2V	1.07/27.2	0.59/15.0	250
432	49726	0.25	18	Miniature Screw (E10)	C-2V	1.07/27.2	0.59/15.0	250
455	40720	0.5	6.5	Miniature Bayonet (BA9s)	C-2R	1.07/27.2	0.59/15.0	500
456	49634	0.17	28	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	5000
464	40728	0.17	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	1500
502	40750	0.15	5.1	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	100
502-BP	16041	0.15	5.1	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	100
503	40752	0.15	5.1	Miniature Bayonet (BA9s)	C-2R	1.07/27.2	0.59/15.0	100
509K	40754	0.18	24	Candelabra Screw (E12)	C-2F	1.38/35.1	0.75/19.1	1000
555	40783	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	3000
555-A	05199	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	3000
555-B	16043	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	3000
555-G	16044	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	3000
555-P	05203	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	3000
555-R	16045	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	3000
555-Y	16046	0.25	6.3	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	3000
558	40769	0.33	13	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	500
558-BP	42048	0.33	13	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	500
561	40775	0.97	12.8	Rigid Loop (RGLP)	C-8	1.72/43.7	0.39/9.9	1000
561-BP	40776	0.97	12.8	Rigid Loop (RGLP)	C-8	1.72/43.7	0.39/9.9	1000
562	42052	0.74	13.5	Rigid Loop (RGLP)	C-8	1.72/43.7	0.39/9.9	2000
562-BP	42050	0.74	13.5	Rigid Loop (RGLP)	C-8	1.72/43.7	0.39/9.9	2000
563	42058	0.52	13.5	Rigid Loop (RGLP)	C-8	1.72/43.7	0.39/9.9	1000
564	42070	0.44	14	Rigid Loop (RGLP)	C-8	1.72/43.7	0.39/9.9	2000
577	42082	1.4	12.8	Double End Cap	C-8	1.72/43.7	0.62/15.8	1000
577-BP	42080	1.4	12.8	Double End Cap	C-8	1.72/43.7	0.62/15.8	1000
578	06699	0.97	12.8	Double End Cap	C-8	1.72/43.7	0.38/9.6	1000
578-BP	06700	0.97	12.8	Double End Cap	C-8	1.72/43.7	0.38/9.6	1000
579	06702	0.80	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	200
579-BP	06703	0.80	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	200
585	40759	0.04	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	7000
605	40826	0.5	6.15	Miniature Screw (E10)	C-2R	1.07/27.2	0.59/15.0	15

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
623	40828	0.37	28	SC Bayonet (BA15s)	2C-6	1.44/36.6	0.75/19.1	1000
624	40829	0.37	28	DC Bayonet (BA15d)	2C-6	1.44/36.6	0.75/19.1	1000
631	40832	0.63	14	SC Bayonet (BA15s)	C-6/C-6	1.44/36.6	0.75/19.1	1000
631-BP	40833	0.63	14	SC Bayonet (BA15s)	C-6/C-6	1.44/36.6	0.75/19.1	1000
655	49620	0.20	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	7000
656	40836	0.06	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	2500
657	40837	0.08	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	15000
658	42272	0.08	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	15000
658-BP	42086	0.08	14	Miniature Wedge (W2.1x9.5d)	C-2F	1.06/26.9	0.40/10.2	15000
680	40852	0.06	5	Wire Leads (WL)	C-2R	0.25/6.4	0.13/3.2	60000
683	40856	0.06	5	Wire Leads (WL)	C-2R	0.25/6.4	0.13/3.2	25000
685	40872	0.06	5	Sub-Midget Flanged (SX4s)	C-2R	0.38/9.7	0.13/3.2	25000
715	40884	0.115	5	Wire Leads (WL)	C-2R	0.25/6.4	0.13/3.2	40000
718	81173	0.115	5	Sub-Midget Flanged (SX4s)	C-2R	0.38/9.7	0.13/3.2	40000
755	40932	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	20000
755-BP	16052	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	20000
756	40934	0.08	14	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	15000
757	40936	0.08	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.40/10.2	15000
757-BP	42362	0.08	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.40/10.2	15000
778	41400	3.33	6	G4 (Sub-Miniature 2-Pin)	C-6	1.05/26.7	0.38/9.6	100
787	41402	1.67	6	G4 (Sub-Miniature 2-Pin)	C-6	1.00/25.4	0.30/7.6	100
788	41404	3.33	6	G4 (Sub-Miniature 2-Pin)	C-6	1.00/25.4	0.30/7.6	100
789	41406	1.17	12	G4 (Sub-Miniature 2-Pin)	C-6	1.05/26.7	0.38/9.6	200
795	44019	3.91	12.8	SC Bayonet (BA15s)	C-6	2.50/63.5	0.48/12.2	200
795X	44021	3.91	12.8	SC Bayonet (BA15s)	C-8	2.50/63.5	0.48/12.2	200
796	44023	2.73	12.8	SC Bayonet (BA15s)	C-6	2.50/63.5	0.48/12.2	300
797	00447	3.91	12.8	G7.1	C-6	1.9/48.3	0.5/13	200
882	42100	0.35	12.8	Printed Circuit socket (B10d)	C-6	1.18/30.0	0.72/18.3	2000
891	42116	0.625	12.8	G4 (Sub-Miniature 2-Pin)	C-6	1.20/30.5	0.32/8.1	500
895	41004	0.53	40	DC Bayonet (BA15d)	CC-6	2.00/50.8	1.04/26.4	3800
901	42141	0.31	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
901-BP	42143	0.31	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
901A	43201	0.31	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
901B	43204	0.31	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
901G	43207	0.31	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
901R	43210	0.31	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
904	41010	0.69	13.5	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	5000
904-BP	42206	0.69	13.5	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	5000
906	41012	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
906-BP	42142	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
906A	01814	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
906B	00358	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
906G	00356	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
906P	06011	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
906R	00357	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
906Y	00359	0.69	13	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1000
908	41014	1.5	6	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	50
909	41016	0.62	6	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	50
912	41017	1.0	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	1000
912-BP	41018	1.0	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	1000
912LL	42510	1.0	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	2000
914	41020	0.9	4	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	50
915	41021	0.75	12	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	50
916	41022	0.54	13.5	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	10000
916-BP	42152	0.54	13.5	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	10000
916NA	42150	0.54	13.5	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	10000
916NA-BP	42146	0.54	13.5	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	10000
917	41024	1.2	12.0	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1200
918	41025	0.56	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
918-BP	43300	0.56	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
918A	43302	0.56	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
918B	43305	0.56	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
918G	43308	0.56	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
918R	43311	0.56	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
920	42157	1.2	12.8	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	1200
921	41026	1.4	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	1000
921-BP	41027	1.4	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	1000
921-FR	49562	1.4	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	1000
921LL	42512	1.4	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	2000
921LL-BP	40349	1.4	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	2000
921X	50046	1.4	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.53/38.9	0.62/15.8	3000
921X	50046	1.4	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.53/38.9	0.62/15.8	3000
922	41029	0.98	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	200
922-BP	42156	0.98	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	200
923	41031	0.91	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
923-BP	43400	0.91	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
923G	43408	0.91	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500
923R	43411	0.91	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	500

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
927	49682	1.2	6	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	50
928	41032	0.3	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	500
939	49683	0.9	6	Miniature Wedge (W2.1x9.5d)	C-6	1.49/37.9	0.62/15.8	75
949	49621	0.022	130	Miniature Bayonet (BA9s)	2C-2F	1.19/30.2	0.43/11.0	7000
957	41040	0.5	9.84	Miniature Bayonet (BA9s)	C-2R	1.38/35.1	0.59/15.0	200
967	49622	0.025	120	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.43/11.0	7500
1003	40155	0.94	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	100
1003-BP	40156	0.94	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	100
1003LL-BP	00201	0.94	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	200
1004	40158	0.94	12.8	DC Bayonet (BA15d)	C-6	1.75/44.5	0.79/20.1	200
1004-BP	40159	0.94	12.8	DC Bayonet (BA15d)	C-6	1.75/44.5	0.79/20.1	200
1016	40166	1.34/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1000
1016-BP	48083	1.34/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1000
1034	40161	1.8/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 5000
1034-BP	49690	1.8/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 5000
1047	16012	2.7	26.0	SC Bayonet (BA15s)	2CC6	2.25/57.2	1.42/36.1	25
1062	49618	0.92	40	DC Bayonet (BA15d)	C-2V	2.25/57.2	1.42/36.1	100
1073	40165	1.8	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1073-BP	49691	1.8	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1076	40167	1.8	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	200
1076-BP	81031	1.8	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	200
1093	49684	1.19	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1000
1105	05147	5.72	6.2	SC Bayonet (BA15s)	C-2V	2.25/57.2	1.42/36.1	125
1129	40170	2.63	6.4	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1129-BP	40103	2.63	6.4	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1130	40172	2.63	6.4	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	200
1133	40174	3.91	6.2	SC Bayonet (BA15s)	C-6	2.25/57.2	1.42/36.1	200
1134	49619	3.91	6.2	DC Bayonet (BA15d)	C-2R	2.25/57.2	1.42/36.1	200
1139IF	00487	1.04	12.8	SC Bayonet (BA15s)	C-6	2.25/57.2	1.42/36.1	700
1141	40176	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1500
1141-BP	41066	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1500
1141IF	40115	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1000
1141LL	42514	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2000
1141LL-BP	40327	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2000
1142	40178	1.6	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	1000
1142-BP	42164	1.6	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	1000
1143	49635	1.98	12.5	SC Bayonet (BA15s)	C-2R	2.25/57.2	1.42/36.1	400
1143IF	49636	1.98	12.5	SC Bayonet (BA15s)	C-2R	2.25/57.2	1.42/36.1	400
1144	49637	1.98	12.5	DC Bayonet (BA15d)	C-2R	2.25/57.2	1.42/36.1	400
1152	40184	1.34	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	500
1154	40186	2.63/0.75	6.4/7	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1154-BP	40121	2.63/0.75	6.4/7	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1155	40188	0.59	13.5	SC Bayonet (BA15s)	C-6/C-6	1.44/36.6	0.75/19.1	5000
1155-BP	40189	0.59	13.5	SC Bayonet (BA15s)	C-6/C-6	1.44/36.6	0.75/19.1	5000
1156	40190	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156-BP	40191	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156A	44030	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156A-BP	40215	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156B	00354	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156DC	44334	2.1	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	1200
1156G	00352	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156LL		2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2400
1156LL-BP	40323	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2400
1156NA	40193	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156NA-BP	44034	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156P	00355	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156R	00351	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156Y	00353	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1157	40194	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157-BP	40195	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157A	40197	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157A-BP	40198	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157LL	42518	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
1157LL-BP	40321	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
1157NA	40199	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157NA-BP	40200	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157NALL-BP	40339	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
1158	40202	2.63/0.75	6.4/7	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1158-BP	42166	2.63/0.75	6.4/7	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1176	40204	1.34/0.59	12.8/14	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1500
1176-BP	40205	1.34/0.59	12.8/14	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1500

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
1178	49091	0.69	13.5	DC Bayonet (BA15d)	C-2V	1.44/36.6	0.75/19.1	5000
1195	40210	3.0	12.5	SC Bayonet (BA15s)	C-2V	2.25/57.2	1.42/36.1	300
1196	40213	3.0	12.5	DC Bayonet (BA15d)	C-2V	2.25/57.2	1.42/36.1	300
1203	40232	0.71	28	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	400
1204	49080	0.71	28	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	400
1210X	49015	0.833	12	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	2000
1211X	49017	0.917	12	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	5000
1224	40234	0.16	32	DC Bayonet (BA15d)	C-2F	1.44/36.6	0.75/19.1	200
1224K	49692	0.16	32	Candelabra Screw (E12)	C-2F	1.38/35.1	0.75/19.1	200
1228	49693	0.45	32	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	150
1236X	49013	0.3	12	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	20000
1236X-BP	49719	0.3	12	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	20000
1250X	49019	0.37	13.5	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	500
1250X-2	49023	0.37	13.5	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	2000
1250X-5	49025	0.37	13.5	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	5000
1251	40242	0.23	28	SC Bayonet (BA15s)	C-6/C-6	1.44/36.6	0.75/19.1	2000
1252	40244	0.23	28	DC Bayonet (BA15d)	C-6/C-6	1.44/36.6	0.75/19.1	2000
1295	40246	3.0	12.5	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1295NA	42172	3.0	12.5	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	300
1295NA-BP	42170	3.0	12.5	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	300
1309	40250	0.52	28	SC Bayonet (BA15s)	2C-6	1.75/44.5	0.79/20.1	300
1383	40258	1.5	13	SC Bayonet (BA15s)	C-8	2.63/66.8	1.55/39.4	300
1383TF	40259	1.5	13	SC Bayonet (BA15s)	CC-8	2.63/66.8	1.55/39.4	300
1385	40262	0.72	28	SC Bayonet (BA15s)	CC-8	2.63/66.8	1.55/39.4	300
1408	40268	0.13	10	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	250
1414	49695	0.46	14	Miniature Bayonet (BA9s)	C-2R	1.38/35.0	0.59/15.0	500
1416	44340	0.8	12.8	Miniature Bayonet (BA9s)	C-2R	1.38/35.1	0.59/15.0	1000
1434	49623	2.75	3.7	SC Bayonet (BA15s)	C-6	1.75/44.5	0.65/16.5	100
1437	00611	0.06	24	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	20
1445	40271	0.135	14.4	Miniature Bayonet (BA9s)	C-2V	0.94/23.9	0.43/11.0	2000
1445-BP	40272	0.135	14.4	Miniature Bayonet (BA9s)	C-2V	0.94/23.9	0.43/11.0	2000
1446	00613	0.2	12	Miniature Screw (E10)	C-2V	0.94/23.9	0.43/11.0	250
1447	49696	0.15	18	Miniature Screw (E10)	C-2V	0.94/23.9	0.43/11.0	250
1449	40276	0.2	14	Miniature Screw (E10)	C-2V	0.94/23.9	0.43/11.0	250
1449-BP	81121	0.2	14	Miniature Screw (E10)	C-2V	0.94/23.9	0.43/11.0	250
1450	49624	0.035	24	Miniature Bayonet (BA9s)	C-2F	0.94/23.9	0.43/11.0	3000
1450X	49031	0.357	14	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	5000
1464	49697	0.25	22	Miniature Bayonet (BA9s)	C-6	1.19/30.2	0.62/15.8	250
1477	40282	0.17	24	Miniature Screw (E10)	C-2V	1.25/31.8	0.40/10.2	250
1480	00618	0.17	18	Candelabra Screw (E12)	C-7A	1.97/50.0	0.54/39.1	1500
1487	40284	0.2	14	Miniature Screw (E10)	C-2V	1.19/30.2	0.43/11.0	3000
1489	40407	2.75	6.5	SC Bayonet (BA15s)	C-6U	1.75/44.5	0.65/16.5	125
1490	40286	0.16	3.2	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
1493	40701	2.75	6.4	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	100
1495	40703	0.3	28	Miniature Bayonet (BA9s)	C-2F	1.38/35.1	0.59/15.0	500
1524X	50050	0.3	24	Miniature Wedge (W2.1x9.5d)	C-2F	1.53/38.9	0.62/15.8	2500
1591	40305	0.61	28	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1000
1619	49626	1.9	6.7	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	500
1638	00647	1.02	28	DC Bayonet (BA15d)	2C-6	2.00/50.8	1.04/26.4	500
1651	40316	0.6	5	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	20
1662	42382	0.93/0.34	28/28	DC Index Bayonet (BAY15d)	CC-6/C-6	2.00/50.8	1.04/26.4	400 / 1000
1680	49627	4.1	6	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	300
1683	40322	1.02	28	SC Bayonet (BA15s)	2C-6	2.00/50.8	1.04/26.4	500
1691	40324	0.61	28	SC Bayonet (BA15s)	2C-6	2.00/50.8	1.04/26.4	1000
1692	40326	0.61	28	DC Bayonet (BA15d)	2C-6	2.00/50.8	1.04/26.4	1000
1768	40342	0.2	6	Midget Screw (E5)	C-2R	0.63/16.0	0.23/5.9	1000
1769	40344	0.2	2.5	Midget Screw (E5)	C-2R	0.72/18.3	0.23/5.9	500
1775	40346	0.075	6.3	Midget Screw (E5)	C-2R	0.63/16.0	0.23/5.9	1000
1804	40352	0.06	4	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	1000
1810	40356	0.4	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	3000
1813	40358	0.1	14.4	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	1000
1813-BP	81123	0.1	14.4	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	1000
1815	40360	0.2	14	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	3000
1815-BP	42176	0.2	14	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	3000
1816	40362	0.33	13	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	1000
1816-BP	42178	0.33	13	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	1000
1818	40364	0.17	24	Miniature Bayonet (BA9s)	C-2V	1.19/30.2	0.43/11.0	250
1819	40366	0.04	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	2500
1819-BP	16021	0.04	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	2500
1820	40368	0.1	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1820-BP	81124	0.1	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1820BTS	49790	0.1	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1820R	00723	0.1	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1821	40370	0.17	28	Miniature Screw (E10)	C-2F	1.19/30.2	0.43/11.0	500
1822	40372	0.1	36	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1828	40380	0.05	37.5	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	3000
1829	40382	0.07	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1829-BP	81126	0.07	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
1835	40386	0.05	55	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	5000
1843	40707	0.022	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	3000
1847	40390	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	5000
1847-BP	49100	0.15	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	5000
1850	40394	0.09	5	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	1500
1864	40398	0.17	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1500
1866	40400	0.25	6.3	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	5000
1873	40404	0.2	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	7000
1873-BP	81129	0.2	28	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	7000
1876	49699	2.5	3.5	SC Bayonet (BA15s)	C-6	1.75/44.5	0.65/16.5	2000
1888	40406	0.5	7	Miniature Bayonet (BA9s)	C-2R	1.19/30.2	0.43/11.0	1500
1889	40408	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	2000
1889-BP	49689	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	2000
1891	40409	0.24	14	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	500
1891-BP	40410	0.24	14	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	500
1892	40412	0.12	14.4	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1892-BP	42180	0.12	14.4	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	1000
1893	40413	0.33	14	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	7500
1893-BP	40414	0.33	14	Miniature Bayonet (BA9s)	C-2F	1.19/30.2	0.43/11.0	7500
1895	40416	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	2000
1895-BP	40417	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	2000
1895A	40419	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	2000
1895B	40719	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	2000
1895B-BP	40721	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	2000
1895G	00754	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	2000
1895R	40725	0.27	14	Miniature Bayonet (BA9s)	C-2F	1.07/27.2	0.59/15.0	2000
1906	40422	0.07	5	Miniature Bayonet (BA9s)	C-6	1.19/30.2	0.43/11.0	1000
2040	42470	0.625	12.8	Sub-Miniature Wedge (W2x4.6d)	CC-6	1.29/32.8	0.38/9.6	500
2040-BP	42182	0.625	12.8	Sub-Miniature Wedge (W2x4.6d)	CC-6	1.29/32.8	0.38/9.6	500
2057	40448	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
2057-BP	40449	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
2057A	42262	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
2057A-BP	42062	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
2057LL	42522	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
2057LL-BP	40325	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
2057NA	40455	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
2057NA-BP	40456	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
2057NALL	42524	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
2057NALL-BP	40341	2.1/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
2102	16026	0.04	18	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	10000
2114	40464	0.06	6	Wire Leads (WL)	C-2R	0.46/11.7	0.17/4.3	3000
2162	40468	0.1	14	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	10000
2174	40470	0.04	12	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	10000
2176	40472	0.05	24	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	1000
2181	49106	0.2	6.3	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	20000
2182	40478	0.08	14	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	40000
2185	00226	0.04	28	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	10000
2187	40484	0.04	28	Wire Leads (WL)	C-2F	0.52/13.2	0.23/5.9	10000
2200	40488	0.06	5	Wire Leads (WL)	C-2R	0.52/13.2	0.23/5.9	25000
2232	42384	0.643	28	SC Bayonet (BA15s)	CC-8	2.00/50.8	1.04/26.4	2000
2233	42386	0.766	28	SC Bayonet (BA15s)	CC-8	2.00/50.8	1.04/26.4	2000
2357	40498	2.23/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 5000
2357-BP	40499	2.23/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 5000
2357A	42304	2.23/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 5000
2357A-BP	42234	2.23/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 5000
2357LL-BP	40329	2.23/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	800 / 10000
2357NA	40501	2.23/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 5000
2357NA-BP	40502	2.23/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 5000
2396	40504	2.23	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	400
2396-BP	40633	2.23	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	400
2397	42229	2.23/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 2000
2397-BP	42230	2.23/0.48	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	400 / 2000
2410X-1	50038	0.417	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	10000
2410X-1	50038	0.417	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	10000
2410X-2	50054	0.417	24	Miniature Wedge (W2.1x9.5d)	C-2F	1.53/38.9	0.62/15.8	3000
2410X-2	50054	0.417	24	Miniature Wedge (W2.1x9.5d)	C-2F	1.53/38.9	0.62/15.8	3000
2450X	50030	0.208	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	500
2450X	50030	0.208	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	500
2470X	50032	0.3	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	12000

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
2470X	50032	0.3	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	12000
2475X-1	50036	0.313	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	10000
2475X-1	50036	0.313	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	10000
2504	07861	2.00	12	PGU20-7	C-8Z	1.42/36	.71/18	750
2721	42231	0.1	12	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.80/20.3	0.20/5.1	1000
2721-BP	40635	0.1	12	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.80/20.3	0.20/5.1	1000
2721MF	05259	0.1	12	MF Series (B8.5d)	C-2V	0.925/23.5	0.20/5.1	1000
2721MF-BP	49831	0.1	12	MF Series (B8.5d)	C-2V	0.925/23.5	0.20/5.1	1000
2723	01044	0.19	12	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.80/20.3	0.20/5.1	1100
2723-BP	40638	0.19	12	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.80/20.3	0.20/5.1	1100
2741	42223	0.05	24	Sub-Miniature Wedge (W2x4.6d)	C-2V	0.80/20.3	0.20/5.1	1000
2741MF	00198	0.05	24	MF Series (B8.5d)	C-2V	0.925/23.5	0.20/5.1	1000
2821	42232	0.25	12	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	1000
2821-BP	42233	0.25	12	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	1000
2825	40637	0.4	12	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	300
2825-BP	42235	0.4	12	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	300
2827	06379	0.4	12	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	300
2827-BP	06380	0.4	12	Miniature Wedge (W2.1x9.5d)	C-2R	1.06/26.9	0.40/10.2	300
2841	49053	0.125	24	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	1000
2860X	50042	0.214	28	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	1000
2860X	50042	0.214	28	Miniature Wedge (W2.1x9.5d)	C-2V	1.06/26.9	0.40/10.2	1000
3011	01084	1.29	28	SC Bayonet (BA15s)	CC-6	2.38/60.5	1.35/34.3	1000
3047K	06383	1.59/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	2000 /10,000
3047K-BP	06384	1.59/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	2000 /10,000
3057	40600	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3057-BP	40601	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3057A	42621	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200/5000
3057A-BP	42622	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200/5000
3057K	42600	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	2000 / 10000
3057K-BP	42601	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	2000 / 10000
3057NA	40603	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3057NA-BP	40604	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3155	42288	1.6	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	1500
3155-BP	42186	1.6	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	1500
3155K	49718	1.44	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	2000
3156	42292	2.1	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	1200
3156-BP	42188	2.1	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	1200
3156A	49035	2.1	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	1200
3156K	42603	2.1	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	2000
3156K-BP	42604	2.1	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	2000
3157	40610	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3157-BP	40611	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3157A	42624	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200/5000
3157A-BP	42625	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200/5000
3157K	42606	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	2000 / 10000
3157K-BP	42607	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	2000 / 10000
3157NA	40613	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3157NA-BP	40614	2.1/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200 / 5000
3357	42189	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3357-BP	49720	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3357A	49037	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3357NA	42195	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3357NA-BP	49833	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
3456K	05467	2.1	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	800
3456K-BP	06654	2.1	12.8	Plastic Wedge Single Filament (W2.5x16d)	C-6	2.09/53.1	1.04/26.4	800
3457/3357	42192	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3457/3357-BP	42190	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3457A	16033	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3457NA/3357NA	42198	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3457NA/3357NA-BP	42196	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	400 / 5000
3496	40641	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	0.79/20.1	600 / 5000
3496-BP	40627	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	0.79/20.1	600 / 5000
3497	40645	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	0.79/20.1	600
3497-BP	40629	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	0.79/20.1	600
3652	40655	0.37	13.5	Miniature Wedge (W2.1x9.5d)	C-6	1.06/26.9	0.40/10.2	700
3652-BP	40653	0.37	13.5	Miniature Wedge (W2.1x9.5d)	C-6	1.06/26.9	0.40/10.2	700
3757NAK	00183	2.1/0.59	12.8/14	Plastic Wedge w/ Offset Key Double Filament (WX2.5)	C-6/C-6	2.09/53.1	1.04/26.4	2000 / 10000
3757NAK-BP	00184	2.1/0.59	12.8/14	Plastic Wedge w/ Offset Key Double Filament (WX2.5)	C-6/C-6	2.09/53.1	1.04/26.4	2000 / 10000
3893	40659	0.33	12	Miniature Bayonet (BA9s)	C-2R	1.06/27	0.38/9.6	300
3893-BP	40661	0.33	12	Miniature Bayonet (BA9s)	C-2R	1.06/27	0.38/9.6	300
3898	16037	0.17	12	European Bayonet (BA7s)	C-2V	0.82/20.8	0.27/6.9	200
4057K	05390	2.23/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000 / 10000
4057K-BP	05375	2.1/0.48	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000 / 10000
4114K	00181	2.23/0.59	14/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000/10000
4114K-BP	00182	2.23/0.59	14/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000/10000
4157K	81143	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000 / 10000
4157K-BP	81047	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000 / 10000
4157NAK	81136	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000 / 10000
4157NAK-BP	81182	2.23/0.59	12.8/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	4000 / 10000
4745-BP	57044	3.52/3.52	12.8/12.8	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.63/92.1	0.67/17.0	120/250
5007	40647	0.42	12	SC Bayonet (BA15s)	C-2R	1.44/36.6	0.75/19.1	200
5007-BP	40639	0.42	12	SC Bayonet (BA15s)	C-2R	1.44/36.6	0.75/19.1	200
5008	40663	0.83	12	SC Bayonet (BA15s)	C-2R	1.44/36.6	0.75/19.1	200
5008-BP	40665	0.83	12	SC Bayonet (BA15s)	C-2R	1.44/36.6	0.75/19.1	200
5200	07862	2.00	12	PGU20-4	C-8Z	1.42/36	.71/18	1200
5201	07864	1.58	12	PG20-1	C-8Z	1.42/36	.71/18	1000
5202	06153	1.78	13.5	PG20/3	C-8Z	1.42/36	0.73/18.5	1500
5702NAK	06145	1.92/0.59	14/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200/5000
5702NAK-BP	06146	1.92/0.59	14/14	Plastic Wedge Double Filament (W2.5x16q)	C-6/C-6	2.09/53.1	1.04/26.4	1200/5000
6022	40824	0.02	5	Wire Leads (WL)	C-2R	0.25/6.4	0.13/3.2	10000
6253	40667	0.5	12	Miniature Bayonet (BA9s)	C-2V	1.07/27.2	0.59/15.0	200
6361-BP	57027	4.68/4.30	12.8/12.8	Axial Prefocus, H4 (P45t41)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
6365-BP	48094	7.81/6.25	12.8/12.8	Axial Prefocus, H4 (P45t41)	C-8/C-8	3.63/92.1	0.67/17.0	100/200
6411	40671	0.83	12	SV8.5mm	C-8	1.61/40.9	0.43/11.0	200
6411-BP	40673	0.83	12	SV8.5mm	C-8	1.61/40.9	0.43/11.0	200
6418	40675	0.4	12	SV8.5mm	C-8	1.38/35.1	0.43/11.0	300
6418-BP	40677	0.4	12	SV8.5mm	C-8	1.38/35.1	0.43/11.0	300
6610F	40840	0.055	12	Double End Cap (SF6/6)	C-8	1.26/32.0	0.24/6.1	5000
6612F	40841	0.25	12	Double End Cap (SF6/6)	C-8	1.26/32.0	0.24/6.1	5000
6614F	05833	0.05	14	Double End Cap (SF6/6)	C-8	1.26/32.0	0.24/6.1	10000
6614F-BP	49724	0.05	14	Double End Cap (SF6/6)	C-8	1.26/32.0	0.24/6.1	10000
6615F	40844	0.08	14	Double End Cap (SF6/6)	C-8	1.26/32.0	0.24/6.1	10000
6833	40864	0.06	5	Wire Leads (WL)	C-2R	0.20/5.1	0.09/2.3	25000
6838	40866	0.024	28	Wire Leads (WL)	CC-2F	0.25/6.4	0.13/3.2	16000
6839	40868	0.024	28	Sub-Midget Flanged (SX4s)	CC-2F	0.38/9.7	0.13/3.2	16000
6848	49098	0.025	48	Midget Flanged (SX6s)	CC-2F	0.63/16.0	0.23/5.9	5000
7010	07858	1.19	13.5	PU20d-1	C-8Z	1.42/36	.71/18	3000
7012	07859	1.41	13.5	PU20d-3	C-8Z	1.42/36	.71/18	2000
7014	07860	1.78	13.5	PU20d-6	C-8Z	1.42/36	.71/18	
7219	42390	0.06	12	Wire Leads (WL)	C-2F	0.25/6.4	0.13/3.2	10000
7225	42237	1.852/0.370	13.5	DC Index Bayonet Offset (BAZ15d)	C-6/C-6	2.00/50.8	1.04/26.4	150 / 1500
7225-BP	42239	1.852/0.370	13.5	DC Index Bayonet Offset (BAZ15d)	C-6/C-6	2.00/50.8	1.04/26.4	150 / 1500
7327	40896	0.04	28	Bi-Pin .125 (G3.17)	C-2F	0.60/15.2	0.23/5.9	4000
7328	42400	0.2	6	Bi-Pin .125 (G3.17)	C-2R	0.63/16.0	0.23/5.9	1000

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
7330	40902	0.08	14	Bi-Pin .125 (G3.17)	C-2F	0.63/16.0	0.23/5.9	1500
7333	81145	0.06	5	Midget Flanged (SX6s)	C-2R	0.63/16.0	0.23/5.9	25000
7349	42408	0.2	6.3	Bi-Pin .125 (G3.17)	C-2R	0.63/16.0	0.23/5.9	5000
7362	49503	0.115	5	Bi-Pin .125 (G3.17)	C-2R	0.63/16.0	0.23/5.9	40000
7370	00333	0.04	18	Bi-Pin .125 (G3.17)	C-2F	0.63/16.0	0.23/5.9	10000
7371	40910	0.04	12	Bi-Pin .125 (G3.17)	C-2F	0.63/16.0	0.23/5.9	10000
7373	40912	0.1	14	Bi-Pin .125 (G3.17)	C-2F	0.63/16.0	0.23/5.9	10000
7374	49712	0.04	28	Bi-Pin .125 (G3.17)	C-2F	0.60/15.2	0.23/5.9	10000
7377	49056	0.075	6.3	Bi-Pin .125 (G3.17)	C-2R	0.60/15.2	0.23/5.9	1000
7380	01662	0.04	6.3	Bi-Pin .125 (G3.17)	C-2F	0.60/15.2	0.23/5.9	20000
7381	40920	0.2	6.3	Bi-Pin .125 (G3.17)	C-2F	0.63/16.0	0.23/5.9	20000
7382	40922	0.08	14	Bi-Pin .125 (G3.17)	C-2F	0.63/16.0	0.23/5.9	40000
7387	40926	0.04	28	Bi-Pin .125 (G3.17)	C-2F	0.63/16.0	0.23/5.9	25000
7440	40931	1.85	13.5	Maxi Wedge Single Filament (W3x16d)	C-6	1.75/44.5	0.79/20.1	300
7440-BP	40925	1.85	13.5	Maxi Wedge Single Filament (W3x16d)	C-6	1.75/44.5	0.79/20.1	300
7440NA	00178	1.85	13.5	Maxi Wedge Single Filament (W3x16d)	C-6	1.75/44.5	0.79/20.1	300
7440NA-BP	00199	1.85	13.5	Maxi Wedge Single Filament (W3x16d)	C-6	1.75/44.5	0.79/20.1	300
7441	00849	2.1	12.8	Maxi Wedge Single Filament (W3x16d)	C-6	1.75/44.5	0.79/20.1	1200
7441-BP	07819	2.1	12.8	Maxi Wedge Single Filament (W3x16d)	C-6	1.75/44.5	0.79/20.1	1200
7443	40935	1.85/0.44	13.5/13.5	Maxi Wedge Double Filament (W3x16q)	C-6/C-6	1.75/44.5	0.79/20.1	500 / 1000
7443-BP	40927	1.85/0.44	13.5/13.5	Maxi Wedge Double Filament (W3x16q)	C-6/C-6	1.75/44.5	0.79/20.1	500 / 1000
7444NA	06409	1.85/0.44	13.5/13.5	Maxi Wedge Double Filament (W3x16q)	C-6/C-6	1.75/44.5	0.79/20.1	500 / 1000
7444NA-BP	06463	1.85/0.44	13.5/13.5	Maxi Wedge Double Filament (W3x16q)	C-6/C-6	1.75/44.5	0.79/20.1	500 / 1000
7506	42241	1.86	13.5	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	350
7506-BP	42242	1.86	13.5	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	350
7507NA	05594	1.85	13.5	SC Bayonet Offset (BAU15s)	C-6	2.00/50.8	1.04/26.4	150
7507NA-BP	42225	1.85	13.5	SC Bayonet Offset (BAU15s)	C-6	2.00/50.8	1.04/26.4	150
7511	00233	1.00	28	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	350
7528	42245	1.86/0.44	13.5/13.5	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	300/2000
7528-BP	42247	1.86/0.44	13.5/13.5	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	300/2000
7537	00234	1.00/0.36	28/28	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	300/2000
7632	40938	0.04	28	Bi-Pin .100 (G2.54)	C-2F	0.60/15.2	0.17/4.3	1000
7646	49713	0.08	14	Bi-Pin .100 (G2.54)	C-2R	0.60/15.2	0.17/4.3	1000
7683	40944	0.06	5	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	25000
7683	40944	0.06	5	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	25000
7714	40946	0.075	5	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	25000
7714	40946	0.075	5	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	25000
7715	40948	0.115	5	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	40000
7715	40948	0.115	5	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	40000
7839	40950	0.024	28	Bi-Pin .050 (G1.27)	CC-2F	0.38/9.7	0.13/3.2	40000
7839	40950	0.024	28	Bi-Pin .050 (G1.27)	CC-2F	0.38/9.7	0.13/3.2	40000
7876	40954	0.06	28	Bi-Pin .125 (G3.17)	C-2F	0.60/15.2	0.23/5.9	25000
8111	40960	0.065	14	Wire Leads (WL)	C-2F	0.25/6.4	0.13/3.2	10000
8362	42418	0.08	14	Midget Screw (E5)	C-2F	0.69/17.5	0.23/5.9	15000
8610	40976	0.2	6.3	Wire Leads (WL)	C-2R	0.46/11.7	0.17/4.3	5000
8627	40978	0.04	28	Wire Leads (WL)	C-2F	0.46/11.7	0.17/4.3	1000
8640	40982	0.08	14	Wire Leads (WL)	C-2F	0.46/11.7	0.17/4.3	1000
8666	40984	0.08	5	Wire Leads (WL)	C-2R	0.20/5.1	0.09/2.3	15000
8918	41002	0.1	14	Midget Flanged (SX6s)	C-2F	0.63/16.0	0.23/5.9	10000
16120X	50044	1.35	12.8	Miniature Wedge (W2.1x9.5d)	C-2R	1.53/38.9	0.62/15.8	10000
42000	42000	0.32	1.35	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	5
42002	42002	0.32	2.7	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	5
42003	42003	0.32	2.7	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	5
42005	42005	0.32	1.35	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	5
42005	42005	0.32	1.35	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	5
42006	42006	0.32	2.7	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	5
42006	42006	0.32	2.7	Bi-Pin .050 (G1.27)	C-2R	0.38/9.7	0.13/3.2	5
45675	49462	0.046	14	Bi-Pin .100 (G2.54)	C-2F	0.60/15.2	0.17/4.3	
45685	05223	0.06	14	Bi-Pin .100 (G2.54)	C-2F	0.60/15.2	0.19/4.8	
64111	40689	0.416	12	Miniature Bayonet (BA9s)	C-6	1.29/32.8	0.38/9.6	240
64111-BP	40691	0.416	12	Miniature Bayonet (BA9s)	C-6	1.29/32.8	0.38/9.6	240
A-62	48000	0.49	6.75	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	
A-62-BP	48001	0.49	6.75	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	
A-72	48002	0.29	13.5	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	4000
A-72-BP	48003	0.29	13.5	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	4000
A-1272-BP	48007	0.17	12	European Bayonet (BA7s)	C-2R	0.91/23.0	0.27/6.9	200
A-3598H-BP	57029	2.31/2.31	6.5/6.5	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	-
A-3603-BP	48009	2.08/2.08	12/12	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	100/100
A-3625-BP	48011	3.85/3.85	6.5/6.5	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	150/150
A-4513-BP	48015	2.66	6.4	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
A-4527-BP	48017	1.80	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
A-4813-BP	48021	2.66/0.71	6.4/7	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200/1000
A-4829-BP	57031	2.11/0.57	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200/5000
A-5659-BP	48025	5.38/5.38	6.5/6.5	Double Contact Prefocus Flanged (P15d30)	C-6/C-2V	2.20/56.0	1.26/32.0	100/100

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
A1A	40000	0.0006	110	Wire Leads (WL) (1.25" Leads)	Neon	1.00/25.4	0.25/6.4	25000
A1B	40002	0.0003	110	Wire Leads (WL) (1" Leads)	Neon	0.50/12.7	0.25/6.4	25000
A1C	40004	0.0012	110	Wire Leads (WL) (1.25" Leads)	Neon	0.50/12.7	0.25/6.4	25000
A1H	40006	0.0012	110	Midget Flanged (SX6s)	Neon	0.63/16	0.23/5.9	25000
A2B	40010	0.0007	110	Wire Leads (WL) (2" Leads)	Neon	0.75/19.1	0.25/6.4	25000
A3C	40012	0.0018	110	Wire Leads (WL) (2" Leads)	Neon	0.75/19.1	0.25/6.4	25000
A9A	40014	0.007	110	Wire Leads (WL) (2" Leads)	Neon	1.00/25.4	0.25/6.4	25000
B1A	40016	0.003	110	Miniature Bayonet (BA9s)	Neon	1.19/30.2	0.38/9.6	25000
B2A	40018	0.0012	110	Miniature Bayonet (BA9s)	Neon	1.19/30.2	0.38/9.6	25000
B7A	40020	0.002	110	Candelabra Screw (E12)	Neon	1.38/35.0	0.50/12.7	7500
C2A	40024	0.0018	110	Wire Leads (WL) (1.25" Leads)	Neon	0.75/19.1	0.25/6.4	25000
C7A	40029	0.007	110	Midget Flanged (SX6s)	Neon	0.94/23.9	0.23/5.9	25000
C9A	40030	0.0018	110	Midget Flanged (SX6s)	Neon	0.94/23.9	0.23/5.9	25000
DE3021	42216	0.24	14	SV7mm	C-8	1.10/28.0	0.32/8.0	1000
DE3021-BP	42214	0.24	14	SV7mm	C-8	1.10/28.0	0.32/8.0	1000
DE3022	42308	0.38	13	SV7mm	C-8	1.15/29.2	0.32/8.0	1000
DE3022-BP	42236	0.38	13	SV7mm	C-8	1.15/29.2	0.32/8.0	1000
DE3175	42298	0.77	13	SV8.5mm	C-8	1.23/31.3	0.40/10.0	400
DE3175-BP	42204	0.77	13	SV8.5mm	C-8	1.23/31.3	0.40/10.0	400
DE3423	42222	0.39	13	SV8.5mm	C-8	1.46/37.1	0.43/11.0	150
DE3423-BP	42220	0.39	13	SV8.5mm	C-8	1.46/37.1	0.43/11.0	150
DE3425	42424	0.77	13	SV8.5mm	C-8	1.46/37.1	0.43/11.0	400
DE3425-BP	42420	0.77	13	SV8.5mm	C-8	1.46/37.1	0.43/11.0	400
E37	49453	0.09	14	Sub-Miniature Wedge (W2x4.6d)	C-2F	0.80/20.3	0.20/5.1	2500
E73	49454	0.08	14	Sub-Miniature Wedge (W2x4.6d)	C-2F	0.80/20.3	0.20/5.1	15000
E85	49458	0.04	28	Sub-Miniature Wedge (W2x4.6d)	C-2F	0.80/20.3	0.20/5.1	7000
E86	49459	0.2	6.3	Sub-Miniature Wedge (W2x4.6d)	C-2F	0.80/20.3	0.20/5.1	20000
H21W	01727	1.75	12	BAY9s	C-6	1.29/32.8	0.38/9.6	200
H1156	44038	3.91	12.8	SC Bayonet (BA15s)	C-6	2.08/53	0.50/12.7	250
H1156-BP2	81179	3.91	12.8	SC Bayonet (BA15s)	C-6	2.08/53	0.50/12.7	250
H1157	44040	3.91/1.17	12.8/12.8	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	0.5/13.0	250/400
HPR36	40031	1.0	5.5	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	40
HPR40	44000	0.67	6	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	50
HPR44	40034	1.0	4	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	300
HPR50	40040	0.85	5.2	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	25
HPR51	40046	0.7	6.5	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	25
HPR51-BP	40048	0.7	6.5	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	25
HPR52	40052	0.85	2.8	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	10
HPR53	40058	0.85	4	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	25
HPR55	40070	0.5	5.2	SC Miniature Flanged (P13.5s)	C-6	1.25/31.8	0.38/9.6	15
JF02XE	50114	0.833	6	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	20000
JF03XE	50118	0.417	12	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	3000
JF07XE	50124	0.833	12	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	20000
JF13XE	50132	0.208	24	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	3000
JF14XE	50134	0.208	24	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	20000
JF14XE/F	16065	0.208	24	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	20000
JF17XE	50138	0.417	24	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	20000
JF135100XE	50098	0.74	13.5	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	15000
JF260050XE	50100	0.192	26	Rigid Loop (RGLP)	C-8	1.72/43.7	0.40/10.0	15000
K12	40059	0.7	5.95	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
K15	40061	0.7	4.8	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
K222	40063	0.6	2.33	Miniature Screw (E10)	C-2R	0.93/23.6	0.38/9.6	5
KK10XE	50056	0.37	13.5	SV8.5mm	C-8	1.22/31.0	0.40/10.0	5000
KL20XE	50072	0.192	26	SV8.5mm	C-8	1.45/37.0	0.40/10.0	5000
KL23XE	50074	0.385	26	SV8.5mm	C-8	1.45/37.0	0.40/10.0	3000
KO10XE	50086	0.37	13.5	SV8.5mm	C-8	1.73/44.0	0.40/10.0	5000
KO10XE/F	05584	0.37	13.5	SV8.5mm	C-8	1.73/44.0	0.40/10.0	5000
KO16XE	50090	0.74	13.5	SV8.5mm	C-8	1.73/44.0	0.40/10.0	5000
KO16XE/F	05586	0.74	13.5	SV8.5mm	C-8	1.73/44.0	0.40/10.0	5000
KO20XE	50092	0.192	26	SV8.5mm	C-8	1.73/44.0	0.40/10.0	5000
KO20XE/F	05588	0.192	26	SV8.5mm	C-8	1.73/44.0	0.40/10.0	5000
KO23XE	50094	0.385	26	SV8.5mm	C-8	1.73/44.0	0.40/10.0	3000
KO23XE/F	05590	0.385	26	SV8.5mm	C-8	1.73/44.0	0.40/10.0	3000
KPR2	40041	0.5	2.38	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
KPR2-BP	44001	0.5	2.38	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
KPR3	40043	0.91	3.6	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	30
KPR4	44003	0.47	2.2	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
KPR13	40045	0.5	4.75	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	10
KPR102	40047	0.7	2.4	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
KPR103	40049	0.75	3.6	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
KPR118	40051	0.55	7.2	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	20
NE51-R	40074	0.0003	110	Miniature Bayonet (BA9s)	Neon	1.19/30.2	0.38/9.6	25000
NE51H-R	40076	0.0012	110	Miniature Bayonet (BA9s)	Neon	1.19/30.2	0.38/9.6	25000
P21/5W	44011	1.86/0.44	13.5/13.5	DC Index Bayonet (BAY15d)	C-6/C-6	2.06/52.5	1.05/26.5	300/2000
P25-1	40082	1.86	13.5	SC Bayonet (BA15s)	C-6	2.06/52.5	1.05/26.5	350
PC37	06431	0.09	14	Printed Circuit socket (P8.25d)	C-2F	0.82/20.8	0.23/5.9	2500
PC37-BP	06464	0.09	14	Printed Circuit socket (P8.25d)	C-2F	0.82/20.8	0.23/5.9	2500
PC74	06432	0.10	14	Printed Circuit socket (P8.25d)	C-2F	0.82/20.8	0.23/5.9	1000

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
PC74-BP	06465	0.10	14	Printed Circuit socket (P8.25d)	C-2F	0.82/20.8	0.23/5.9	1000
PC119	07753	0.15	14	Printed Circuit socket (P8.25d)	C-2V	2.28/58	0.28/7.14	3000
PC168	00231	0.35	14	Printed Circuit socket (P12.4d also PCT3 1/4)	C-2F	1.11/28.2	0.40/10.2	1500
PC168-BP	00232	0.35	14	Printed Circuit socket (P12.4d also PCT3 1/4)	C-2F	1.11/28.2	0.40/10.2	1500
PC194	00229	0.27	14	Printed Circuit socket (P12.4d also PCT3 1/4)	C-2F	1.11/28.2	0.40/10.2	2500
PC194-BP	00230	0.27	14	Printed Circuit socket (P12.4d also PCT3 1/4)	C-2F	1.11/28.2	0.40/10.2	2500
PR2	40100	0.5	2.38	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR2-BP	40101	0.5	2.38	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR3	40104	0.5	3.57	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR3-BP	40105	0.5	3.57	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR4	40108	0.27	2.33	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	10
PR6	40112	0.3	2.47	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	30
PR7	40114	0.3	3.7	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	30
PR9	40116	0.15	2.7	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	45
PR12	40084	0.5	5.95	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR12-BP	40085	0.5	5.95	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR13	40086	0.5	4.75	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR13-BP	40087	0.5	4.75	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR15	40090	0.5	4.82	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	30
PR16	40092	0.25	12.5	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	50
PR18	40096	0.55	7.2	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	3
PR20	40102	0.5	8.63	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	15
PR30	40106	0.86	3.75	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	40
PS13W	07865	1.08	12	PG18.5d-1	C-8Z	1.42/36	.71/18	4000
PSX26W	07866	2.17	12	PG18.5d-3	C-8Z	1.42/36	.71/18	1500
PSY24WSV	07863	2.00	12	PG20-4	C-8Z	1.42/36	.71/18	1000
PSY24WY	07867	2.00	12	PG20-4	C-8Z	1.42/36	.71/18	1200
SE1274	40117	0.12	14.4	European Bayonet (BA7s)	C-2F	0.80/20.3	0.23/5.9	500
SE1274-BP	42208	0.12	14.4	European Bayonet (BA7s)	C-2F	0.80/20.3	0.23/5.9	500
XPR3	06028	0.91	3.6	SC Miniature Flanged (P13.5s)	C-2R	1.25/31.8	0.45/11.5	30

Automotive Forward Lighting

High Performance Forward Lighting

ClearVision™ Supreme

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
880CVSU-BP	07021	27	12.8	T-3 1/4	Axial Prefocus (PG13)	C-6		2.68/68.1	0.42/10.7	300
881CVSU-BP	07033	27	12.8	T-3 1/4	Right-Angle Prefocus, (PGJ13)	C-6		2.68/68.1	0.42/10.7	300
885CVSU-BP	07013	50	12.8	T-3 1/4	Axial Prefocus (PG13)	C-6	1320	2.68/68.1	0.42/10.7	200
889CVSU-BP	07018	27	12.8	T-3 1/4	Right-Angle Prefocus, (PGJ13)	C-6		2.68/68.1	0.42/10.7	300
893CVSU-BP	07035	37.5	12.8	T-3 1/4	Axial Prefocus (PG13)	C-6		2.68/68.1	0.42/10.7	200
894CVSU-BP	07043	37.5	12.8	T-3 1/4	Right-Angle Prefocus, (PGJ13)	C-6		2.68/68.1	0.42/10.7	200
896CVSU-BP	07001	37.5	12.8	T-3 1/4	Right-Angle Prefocus, (PGJ13)	C-6		2.68/68.1	0.42/10.7	200
899CVSU-BP	01206	37.5	12.8	T-3 1/4	Axial Prefocus (PG13)	C-6		2.68/68.1	0.42/10.7	300
9003/H4CVSU-BP	07675	60/55	12.8/12.8	T-5	Axial Prefocus, HB2 (P43t38)	C-8/C-8	1545/955	3.62/92.0	0.65/16.5	150/800
9003/H4CVSU2	01881	60/55	12.8/12.8	T-5	Axial Prefocus, HB2 (P43t38)	C-8/C-8	1545/955	3.62/92.0	0.65/16.5	150/800
9004CVSU-BP	07676	65/45	12.8/12.8	T-4 3/4	Axial Prefocus, HB1 (P29t)	C-6/C-6	1195/690	4.17/106	1.33/33.8	150/320
9004CVSU2	02262	65/45	12.8/12.8	T-4 3/4	Axial Prefocus, HB1 (P29t)	C-6/C-6	1195/690	4.17/106	1.33/33.8	150/320
9005CVSU-BP	07672	65	12.8	T-3 1/4	Right Angle Prefocus, HB3 (P20d)	C-8	1695	3.09/78.0	0.42/10.7	150
9005CVSU2	02277	65	12.8	T-3 1/4	Right Angle Prefocus, HB3 (P20d)	C-8	1695	3.09/78.0	0.42/10.7	150
9005XSCVSU-BP	07686	65	12.8	T-3 1/4	Axial Prefocus, HB3A (P20d)	C-8	1695	2.59/65.9	0.42/10.7	150
9005XSCVSU2	07671	65	12.8	T-3 1/4	Axial Prefocus, HB3A (P20d)	C-8	1695		0.42/10.7	150
9006CVSU-BP	07677	55	12.8	T-3 1/4	Right Angle Prefocus, HB4 (P22d)	C-8	1005	3.09/78.0	0.42/10.7	320
9006CVSU2	02434	55	12.8	T-3 1/4	Right Angle Prefocus, HB4 (P22d)	C-8	1005	3.09/78.0	0.42/10.7	320
9006XSCVSU-BP	07674	55	12.8	T-3 1/4	Axial Prefocus, HB4A (P22d)	C-8	1005	2.61/66.2	0.42/10.7	320
9006XSCVSU2	07673	55	12.8	T-3 1/4	Axial Prefocus, HB4A (P22d)	C-8	1005	2.61/66.2	0.42/10.7	320
9007CVSU-BP	07678	65/55	12.8/12.8	T-4 3/4	Axial Prefocus, HB5 (Px29t)	C-8/C-8	1345/1105	4.17/106	1.33/33.8	150/320
9007CVSU2	03497	65/55	12.8/12.8	T-4 3/4	Axial Prefocus, HB5 (Px29t)	C-8/C-8	1345/1105	4.17/106	1.33/33.8	150/320
9008CVSU-BP	07679	65/55	12.8/12.8	T-5	Axial Prefocus, H13 (P26.4t)	C-8/C-8	1510/1005	3.68/93.6	0.63/16.0	150/500
9008CVSU2	03790	65/55	12.8/12.8	T-5	Axial Prefocus, H13 (P26.4t)	C-8/C-8	1510/1005	3.68/93.6	0.63/16.0	150/500
H11BCVSU-BP	07682	55	13.2	T-3 1/4	Right Angle Prefocus, H11B (PGJY19-2)	CC-8	1345	2.63/66.8	0.43/10.8	550
H11BCVSU2	07010	55	13.2	T-3 1/4	Right Angle Prefocus, H11B (PGJY19-2)	CC-8	1345	2.63/66.8	0.43/10.8	550
H155CVSU-BP	07683	55	12	T-3 1/2	H1 Type (P14.5s)	C-8	1545	2.65/67.3	0.33/8.4	225
H155CVSU2	03791	55	12	T-3 1/2	H1 Type (P14.5s)	C-8	1545	2.65/67.3	0.33/8.4	225
H355CVSU-BP	07684	55	12	T-3 1/2	Prefocus Flanged, H3 (PK22s)	CC-6	1445	1.65/41.9	0.46/11.5	320
H355CVSU2	03853	55	12	T-3 1/2	Prefocus Flanged, H3 (PK22s)	CC-6	1445	1.65/41.9	0.46/11.5	320
H755CVSU-BP	07685	55	12.8	T-3 1/2	Axial Prefocus, H7 (PX26d)	C-8	1510	2.36/60.0	0.49/12.5	320
H755CVSU2	04054	55	12.8	T-3 1/2	Axial Prefocus, H7 (PX26d)	C-8	1510	2.36/60.0	0.49/12.5	320
H1042CVSU-BP	07680	42	13.2	T-4	Right Angle Prefocus, H10 (PY20d)	CC-8	840	3.17/80.5	0.47/11.8	775
H1042CVSU2	07062	42	13.2	T-4	Right Angle Prefocus, H10 (PY20d)	CC-8	840	3.17/80.5	0.47/11.8	775
H1155CVSU-BP	07681	55	13.2	T-3 1/4	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	1345	2.64/67	0.43/10.8	550
H1155CVSU2	07008	55	13.2	T-3 1/4	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	1345	2.64/67	0.43/10.8	550

Automotive Forward Lighting

ClearVision™ XL

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
9003/H4CVXL-BP	07657	60/55	12.8/12.8	T-5	Axial Prefocus, HB2 (P43t38)	C-8/C-8	1545/955	3.62/92.0	0.65/16.5	150/800
9003/H4CVXL2	01870	60/55	12.8/12.8	T-5	Axial Prefocus, HB2 (P43t38)	C-8/C-8	1545/955	3.62/92.0	0.65/16.5	150/800
9004CVXL-BP	07658	65/45	12.8/12.8	T-4 3/4	Axial Prefocus, HB1 (P29t)	C-6/C-6	1195/690	4.17/106	1.33/33.8	150/320
9004CVXL2	01883	65/45	12.8/12.8	T-4 3/4	Axial Prefocus, HB1 (P29t)	C-6/C-6	1195/690	4.17/106	1.33/33.8	150/320
9005CVXL-BP	07659	65	12.8	T-3 1/4	Right Angle Prefocus, HB3 (P20d)	C-8	1695	3.09/78.0	0.42/10.7	150
9005CVXL2	02276	65	12.8	T-3 1/4	Right Angle Prefocus, HB3 (P20d)	C-8	1695	3.09/78.0	0.42/10.7	150
9006CVXL-BP	07660	55	12.8	T-3 1/4	Right Angle Prefocus, HB4 (P22d)	C-8	1005	3.09/78.0	0.42/10.7	320
9006CVXL2	02433	55	12.8	T-3 1/4	Right Angle Prefocus, HB4 (P22d)	C-8	1005	3.09/78.0	0.42/10.7	320
9007CVXL-BP	07661	65/55	12.8/12.8	T-4 3/4	Axial Prefocus, HB5 (Px29t)	C-8/C-8	1345/1105	4.17/106	1.33/33.8	150/320
9007CVXL2	03494	65/55	12.8/12.8	T-4 3/4	Axial Prefocus, HB5 (Px29t)	C-8/C-8	1345/1105	4.17/106	1.33/33.8	150/320
9008CVXL-BP	07662	65/55	12.8/12.8	T-5	Axial Prefocus, H13 (P26.4t)	C-8/C-8	1510/1005	3.68/93.6	0.63/16.0	150/500
9008CVXL2	03789	65/55	12.8/12.8	T-5	Axial Prefocus, H13 (P26.4t)	C-8/C-8	1510/1005	3.68/93.6	0.63/16.0	150/500
H755CVXL-BP	07664	55	12.8	T-3 1/2	Axial Prefocus, H7 (PX26d)	C-8	1510	2.36/60.0	0.49/12.5	320
H755CVXL2	03855	55	12.8	T-3 1/2	Axial Prefocus, H7 (PX26d)	C-8	1510	2.36/60.0	0.49/12.5	320
H1155CVXL-BP	07663	55	13.2	T-3 1/4	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	1345	2.64/67	0.43/10.8	550
H1155CVXL2	07005	55	13.2	T-3 1/4	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	1345	2.64/67	0.43/10.8	550
H4651CVXL	07668	50	12.8	Rec 100x165	2 Contact Lugs	C-6		4.8/121		200
H6024CVXL	07667	65/35	12.8	PAR 56	3 Contact Lugs	C-6/C-6		5.0/127	7.0/178	150/450

Automotive Forward Lighting

High Performance Forward Lighting

PowerVision™ PRO

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
9003/H4PVP-BP	07633	60/55	12.8/12.8	T-5	Axial Prefocus, HB2 (P43t38)	C-8/C-8	1545/955	3.62/92.0	0.65/16.5	150/800
9003/H4PVP2	01868	60/55	12.8/12.8	T-5	Axial Prefocus, HB2 (P43t38)	C-8/C-8	1545/955	3.62/92.0	0.65/16.5	150/800
9004PVP-BP	07634	65/45	12.8/12.8	T-4 3/4	Axial Prefocus, HB1 (P29t)	C-6/C-6	1195/690	4.17/106	1.33/33.8	150/320
9004PVP2	02267	65/45	12.8/12.8	T-4 3/4	Axial Prefocus, HB1 (P29t)	C-6/C-6	1195/690	4.17/106	1.33/33.8	150/320
9005PVP-BP	07635	65	12.8	T-3 1/4	Right Angle Prefocus, HB3 (P20d)	C-8	1695	3.09/78.0	0.42/10.7	150
9005PVP2	02268	65	12.8	T-3 1/4	Right Angle Prefocus, HB3 (P20d)	C-8	1695	3.09/78.0	0.42/10.7	150
9005XSPVP-BP	07650	65	12.8	T-3 1/4	Axial Prefocus, HB3A (P20d)	C-8	1695	2.59/65.9	0.42/10.7	150
9005XSPVP2	07649	65	12.8	T-3 1/4	Axial Prefocus, HB3A (P20d)	C-8	1695	2.59/65.9	0.42/10.7	150
9006PVP-BP	07636	55	12.8	T-3 1/4	Right Angle Prefocus, HB4 (P22d)	C-8	1005	3.09/78.0	0.42/10.7	320
9006PVP2	02431	55	12.8	T-3 1/4	Right Angle Prefocus, HB4 (P22d)	C-8	1005	3.09/78.0	0.42/10.7	320
9006XSPVP-BP	07652	55	12.8	T-3 1/4	Axial Prefocus, HB4A (P22d)	C-8	1005	2.61/66.2 9	0.42/10.7	320
9006XSPVP2	07651	55	12.8	T-3 1/4	Axial Prefocus, HB4A (P22d)	C-8	1005	2.61/66.2 9	0.42/10.7	320
9007PVP-BP	07637	65/55	12.8/12.8	T-4 3/4	Axial Prefocus, HB5 (Px29t)	C-8/C-8	1345/110 5	4.17/106	1.33/33.8	150/320
9007PVP2	03207	65/55	12.8/12.8	T-4 3/4	Axial Prefocus, HB5 (Px29t)	C-8/C-8	1345/110 5	4.17/106	1.33/33.8	150/320
9008PVP-BP	07638	65/55	12.8/12.8	T-5	Axial Prefocus, H13 (P26.4t)	C-8/C-8	1510/100 5	3.68/93.6	0.63/16.0	150/500
9008PVP2	03788	65/55	12.8/12.8	T-5	Axial Prefocus, H13 (P26.4t)	C-8/C-8	1510/100 5	3.68/93.6	0.63/16.0	150/500
H11BPVP-BP	07646	55	13.2	T-3 1/4	Right Angle Prefocus, H11B (PGJY19-2)	CC-8	1345	2.63/66.8	0.43/10.8	550
H11BPVP2	07645	55	13.2	T-3 1/4	Right Angle Prefocus, H11B (PGJY19-2)	CC-8	1345	2.63/66.8	0.43/10.8	550
H155PVP-BP	07642	55	12	T-3 1/2	H1 Type (P14.5s)	C-8	1545	2.65/67.3	0.33/8.4	225
H155PVP2	07641	55	12	T-3 1/2	H1 Type (P14.5s)	C-8	1545	2.65/67.3	0.33/8.4	225
H355PVP-BP	07644	55	12	T-3 1/2	Prefocus Flanged, H3 (PK22s)	CC-6	1445	1.65/41.9	0.46/11.5	320
H355PVP2	07643	55	12	T-3 1/2	Prefocus Flanged, H3 (PK22s)	CC-6	1445	1.65/41.9	0.46/11.5	320
H755PVP-BP	07640	55	12.8	T-3 1/2	Axial Prefocus, H7 (PX26d)	C-8	1510	2.36/60.0	0.49/12.5	320
H755PVP2	03854	55	12.8	T-3 1/2	Axial Prefocus, H7 (PX26d)	C-8	1510	2.36/60.0	0.49/12.5	320
H1042PVP-BP	07648	42	13.2	T-4	Right Angle Prefocus, H10 (PY20d)	CC-8	840	3.17/80.5	0.47/11.8	775
H1042PVP2	07647	42	13.2	T-4	Right Angle Prefocus, H10 (PY20d)	CC-8	840	3.17/80.5	0.47/11.8	775
H1155PVP-BP	07639	55	13.2	T-3 1/4	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	1345	2.64/67	0.43/10.8	550
H1155PVP2	07003	55	13.2	T-3 1/4	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	1345	2.64/67	0.43/10.8	550
H4656PVP	07655	35/35	12.8	Rec 100x165	3 Contact Lugs	C-6/C-6		4.8/121		200/320
H6024PVP	07654	65/35	12.8	PAR 56	3 Contact Lugs	C-6/C-6		5.0/127	7.0/178	150/450
H6054PVP	07653	65/35	12.8	Rec 142x200	3 Contact Lugs	C-6/C-6		5.44/138		150/320

Automotive Forward Lighting

9000 Series Halogen Forward Lighting



Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
9003	42268	E13	60/55	12.8/12.8	Axial Prefocus, HB2 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/800
9003-BP	42064	E13	60/55	12.8/12.8	Axial Prefocus, HB2 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/800
9004	41008		65/45	12.8/12.8	Axial Prefocus, HB1 (P29t)	C-6/C-6	4.17/106	1.33/33.8	150/320
9004-BP	41009		65/45	12.8/12.8	Axial Prefocus, HB1 (P29t)	C-6/C-6	4.17/106	1.33/33.8	150/320
9004HW	43504		100/80	12.8/12.8	Axial Prefocus, HB1 (P29t)	C-6/C-6	4.17/106	1.33/33.8	100/250
9004LL	41063		65/45	12.8/12.8	Axial Prefocus, HB1 (P29t)	C-6/C-6	4.17/106	1.33/33.8	250/850
9004LL-BP	41062		65/45	12.8/12.8	Axial Prefocus, HB1 (P29t)	C-6/C-6	4.17/106	1.33/33.8	250/850
9005	41052	E11	65	12.8	Right Angle Prefocus, HB3 (P20d)	C-8	3.09/78.0	0.42/10.7	150
9005-BP	41053	E11	65	12.8	Right Angle Prefocus, HB3 (P20d)	C-8	3.09/78.0	0.42/10.7	150
9005XS	49413		65	12.8	Axial Prefocus, HB3A (P20d)	C-8	2.59/65.9	0.42/10.7	150
9005XS-BP	49414		65	12.8	Axial Prefocus, HB3A (P20d)	C-8	2.59/65.9	0.42/10.7	150
9005XSLL	00236		65	12.8	Axial Prefocus, HB3A (P20d)	C-8	2.59/65.9	0.42/10.7	600
9006	41055	E11	55	12.8	Right Angle Prefocus, HB4 (P22d)	C-8	3.09/78.0	0.42/10.7	320
9006-BP	41056	E11	55	12.8	Right Angle Prefocus, HB4 (P22d)	C-8	3.09/78.0	0.42/10.7	320
9006HW	43564		80	12.8	Right Angle Prefocus, HB4 (P22d)	C-8	3.09/78.0	0.42/10.7	150
9006LL	44170	E11	55	12.8	Right Angle Prefocus, HB4 (P22d)	C-8	3.09/78.0	0.42/10.7	800
9006LL-BP	44172	E11	55	12.8	Right Angle Prefocus, HB4 (P22d)	C-8	3.09/78.0	0.42/10.7	800
9006XS	49416		55	12.8	Axial Prefocus, HB4A (P22d)	C-8	2.61/66.2 9	0.42/10.7	320
9006XS-BP	49417		55	12.8	Axial Prefocus, HB4A (P22d)	C-8	2.61/66.2 9	0.42/10.7	320
9006XSLL	00237		55	12.8	Axial Prefocus, HB4A (P22d)	C-8	2.61/66.2 9	0.42/10.7	600
9006XSLL-BP	05356		55	12.8	Axial Prefocus, HB4A (P22d)	C-8	2.61/66.2 9	0.42/10.7	600
9007	42426		65/55	12.8/12.8	Axial Prefocus, HB5 (Px29t)	C-8/C-8	4.17/106	1.33/33.8	150/320
9007-BP	42124		65/55	12.8/12.8	Axial Prefocus, HB5 (Px29t)	C-8/C-8	4.17/106	1.33/33.8	150/320
9007HW	43517		100/80	12.8/12.8	Axial Prefocus, HB5 (Px29t)	C-8/C-8	4.17/106	1.33/33.8	100/150

9000 Series Halogen Forward Lighting

Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
9007LL	44176		65/55	12.8/12.8	Axial Prefocus, HB5 (Px29t)	C-8/C-8	4.17/106	1.33/33.8	150/1450
9007LL-BP	44178		65/55	12.8/12.8	Axial Prefocus, HB5 (Px29t)	C-8/C-8	4.17/106	1.33/33.8	150/1450
9008	49865		65/55	12.8/12.8	Axial Prefocus, H13 (P26.4t)	C-8/C-8	3.68/93.6	0.63/16.0	150/500
9008-BP	49867		65/55	12.8/12.8	Axial Prefocus, H13 (P26.4t)	C-8/C-8	3.68/93.6	0.63/16.0	150/500
9011	00711		65	12.8	PX20d	C-8	3.09/78.5	0.5/12.5	150 at 14V
9012LL	00732		60	12.8	PX22d	C-8	3.09/78.5	0.43/11.0	1000 at 14V
9040	16070		40	12.8	Right Angle Prefocus (P20d/40t)	C-6	3.17/80.5	0.5/12.4	1500
9040-BP	16056		40	12.8	Right Angle Prefocus (P20d/40t)	C-6	3.17/80.5	0.5/12.4	1500
9045	06427		45	12.8	Right Angle Prefocus (P20d/45t)	C-6	3.17/80.5	0.5/12.4	1000
9140	06428		40	12.8	Right Angle Prefocus (P20d/40a)	C-8	3.17/80.5	0.5/12.4	1500
9155	06429		55	12.8	Right Angle Prefocus (P20d/55a)	C-8	3.17/80.5	0.5/12.4	1200

800 Series Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD in/mm	Life Hours
862	00043	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	2000
880	42450	27	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	300
880-BP	42088	27	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	300
880SW-BP	49435	27	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	300
881	42452	27	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	300
881-BP	42094	27	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	300
881SW-BP	49436	27	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	300
882	42100	4.5	12.8	Printed Circuit socket (B10d)	C-6	1.18/30.0	0.72/18.3	2000
882-BP	42096	4.5	12.8	Printed Circuit socket (B10d)	C-6	1.18/30.0	0.72/18.3	2000
885	42456	50	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	200
885-BP	48082	50	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	200
885SW-BP	49438	50	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	200
886	42458	50	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
886-BP	42130	50	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
889	42460	27	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	300
889-BP	42106	27	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	300
889SW-BP	49440	27	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	300
890	42462	27	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	300
890-BP	42110	27	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	300
891	42116	8	12.8	G4 (Sub-Miniature 2-Pin)	C-6	1.20/30.5	0.32/8.1	500
891-BP	42114	8	12.8	G4 (Sub-Miniature 2-Pin)	C-6	1.20/30.5	0.32/8.1	500
893	42464	37.5	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	200
893-BP	42120	37.5	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	200
893SW-BP	49443	37.5	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	200
894	42466	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
894-BP	42134	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
894SW-BP	49444	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
896	42468	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
896-BP	42138	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
896SW-BP	49445	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	200
898	49678	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	1900
898-BP	49679	37.5	12.8	Right-Angle Prefocus, (PGJ13)	C-6	2.68/68.1	0.42/10.7	1900
899	44330	37.5	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	1900
899-BP	44331	37.5	12.8	Axial Prefocus (PG13)	C-6	2.68/68.1	0.42/10.7	1900

H1 Series Halogen Lamps



Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
01000	40122		55	6	H1 Type (P14.5s)	C-8	2.65/67.3	0.33/8.4	150
01003	40124	E1,E13	55	12	H1 Type (P14.5s)	C-8	2.65/67.3	0.33/8.4	225
01003-BP	40129	E1,E13	55	12	H1 Type (P14.5s)	C-8	2.65/67.3	0.33/8.4	225
01004	40126		100	12	H1 Type (P14.5s)	C-8	2.65/67.3	0.33/8.4	100
01004-BP	40135		100	12	H1 Type (P14.5s)	C-8	2.65/67.3	0.33/8.4	100
01027	40150	E1,E13	70	24	H1 Type (P14.5s)	CC-8	2.65/67.3	0.33/8.4	150

H2 Series Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
01005	40128	55	12	H2 Prefocus Type (X511)	C-8	1.22/31.0	0.33/8.4	225
01005-BP	42226	55	12	H2 Prefocus Type (X511)	C-8	1.22/31.0	0.33/8.4	225
01023	40148	100	12	H2 Prefocus Type (X511)	C-8	1.22/31.0	0.33/8.4	100

Automotive Forward Lighting

H3 Series Halogen Lamps



Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
01006	40130		55	6	Prefocus Flanged, H3 (PK22s)	C-6	1.65/41.9	0.45/11.5	150
01007	40132	E1,E13	55	12	Prefocus Flanged, H3 (PK22s)	CC-6	1.65/41.9	0.46/11.5	320
01007-Blue	44348		55	12	Prefocus Flanged, H3 (PK22s)	CC-6	1.65/41.9	0.46/11.5	150
01007-BP	40133	E1,E13	55	12	Prefocus Flanged, H3 (PK22s)	CC-6	1.65/41.9	0.46/11.5	320
01008	40134	E1,E13	70	24	Prefocus Flanged, H3 (PK22s)	CC-6	1.65/41.9	0.45/11.5	150
01008-BP	49834	E1,E13	70	24	Prefocus Flanged, H3 (PK22s)	CC-6	1.65/41.9	0.45/11.5	150
01015	40140		100	12	Prefocus Flanged, H3 (PK22s)	C-6	1.65/41.9	0.45/11.5	100
01015-BP	40141		100	12	Prefocus Flanged, H3 (PK22s)	C-6	1.65/41.9	0.45/11.5	100
01031	40153		35	12	Prefocus Flanged, H3 (PK22s)	C-6	1.65/41.9	0.45/11.5	200
01031-BP	49839		35	12	Prefocus Flanged, H3 (PK22s)	C-6	1.65/41.9	0.45/11.5	200
H3C	05620		55	12	Prefocus Flanged, H3C	CC-6	2.48/63	0.43/10.8	320

H4 Series Halogen Lamps



Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
01009	40136	E1,E13	60/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
01009-Blue	44364	E13	60/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
01009-Blue-BP	44366	E13	60/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
01009-BP	42228	E1,E13	60/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
01010	40138	E1,E13	75/70	24/24	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
01019	40144		100/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
01019-BP	40145		100/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
01021	40146		100/80	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
01021-BP	40143		100/80	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
4745	57045		45/45	12.8/12.8	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.63/92.1	0.67/17.0	120/250
48220-BP	57043		35/35	12.8/12.8	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.63/92.1	0.67/17.0	120/300

H7 Series Halogen Lamps



Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
H7/70W/24V	01532		70	24	Axial Prefocus, H7 (PX26d)	CC-8	2.24/57	0.43/10.9	250
H755	44074	E1,E13	55	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	320
H755-BP	44076	E1,E13	55	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	320
H755LL	00266		55	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	1000
H755LL-BP	05357		55	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	1000
H755SWTX	44158		55	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	320
H7100	44082		100	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	150
H7100-BP	44084		100	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	150
H7100-Super White	44086		100	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	150
H7100-SUPER WHITE-BP	44088		100	12.8	Axial Prefocus, H7 (PX26d)	C-8	2.36/60.0	0.49/12.5	150

H8-H13 Halogen Lamps



Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
9008	49865		65/55	12.8/12.8	Axial Prefocus, H13 (P26.4t)	C-8/C-8	3.68/93.6	0.63/16.0	150/500
9040	16070		40	12.8	Right Angle Prefocus (P20d/40t)	C-6	3.17/80.5	0.5/12.4	1500
9040-BP	16056		40	12.8	Right Angle Prefocus (P20d/40t)	C-6	3.17/80.5	0.5/12.4	1500
9155	06429		55	12.8	Right Angle Prefocus (P20d/55a)	C-8	3.17/80.5	0.5/12.4	1200
H11B	06716		55	13.2	Right Angle Prefocus, H11B (PGJY19-2)	CC-8	2.63/66.8	0.43/10.8	550
H11B-BP	06715		55	13.2	Right Angle Prefocus, H11B (PGJY19-2)	CC-8	2.63/66.8	0.43/10.8	550
H835	81162	E11	35	13.2	Right Angle Prefocus, H8 (PGJ19-1)	CC-8	2.64/67	0.43/10.8	320
H835-BP	05427	E11	35	13.2	Right Angle Prefocus, H8 (PGJ19-1)	CC-8	2.64/67	0.43/10.8	320
H965	81161	E11	65	13.2	Right Angle Prefocus, H9 (PGJ19-5)	CC-8	2.64/67	0.43/10.8	120
H965-BP	05428	E11	65	13.2	Right Angle Prefocus, H9 (PGJ19-5)	CC-8	2.64/67	0.43/10.8	120
H1042	81163		42	13.2	Right Angle Prefocus, H10 (PY20d)	CC-8	3.17/80.5	0.47/11.8	775
H1042-BP	00042		42	13.2	Right Angle Prefocus, H10 (PY20d)	CC-8	3.17/80.5	0.47/11.8	775
H1155	81164	E11,E13	55	13.2	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	2.64/67	0.43/10.8	550
H1155-BP	05429	E11,E13	55	13.2	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	2.64/67	0.43/10.8	550
H1155LL	00267	E11,E13	55	13.2	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	2.64/67	0.43/10.8	1000
H1155LL-BP	05355		55	13.2	Right Angle Prefocus, H11 (PGJ19-2)	CC-8	2.64/67	0.43/10.8	1000
H1156	44038		50	12.8	SC Bayonet (BA15s)	C-6	2.08/53	0.50/12.7	250
H1156-BP2	81179		50	12.8	SC Bayonet (BA15s)	C-6	2.08/53	0.50/12.7	250

H8-H13 Halogen Lamps

Ordering Code	Bar Code	Approvals	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
H1157	44040	E11,E13	50/15	12.8/12.8	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	0.5/13.0	250/400
H1157-BP	49685	E11,E13	50/15	12.8/12.8	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	0.5/13.0	250/400
H1253	81165		53	13.2	Right Angle Prefocus, H12 (PZ20d)	CC-6	3.17/80.5	0.47/11.8	950
H1253-BP	05430		53	13.2	Right Angle Prefocus, H12 (PZ20d)	CC-6	3.17/80.5	0.47/11.8	950

HID - OE Replacement Lamps



Ordering Code	Bar Code	Watts	Base	Lumens	Life Hours
D1R	04403	35	PK32 d3	2800	3000
D1S	04402	35	PK32 d2	3200	3000
D2R	00362	35	P32 d-3	2800	2000
D2S	00363	35	P32 d-2	3200	2000
D3R	06904	35	PK32d-6	2800	3000
D3S	07103	35	PK32d-5	3200	3000
D4R	06381	35	P32d-6	2800	2500
D4S	06382	35	P32d-5	3200	2500

Motorcycle and Snowmobile Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
625J	48044	25	12.8	Single Contact Prefocus Flanged (P15s30)	C-6	2.30/58.4	1.38/35.0	100
635B	48052	35	12.8	SC Bayonet European (BA20s)	C-6	2.60/66.0	1.42/36.0	100
635J	48046	35	12.8	Single Contact Prefocus Flanged (P15s-3)	C-6	2.25/57.2	1.25/32.0	100
660B	48054	60	12.8	SC Bayonet European (BA20s)	C-6	2.60/66.0	1.42/36.0	75
4745-BP	57044	45/45	12.8/12.8	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.63/92.1	0.67/17.0	120/250
6235B	48056	35/35	12.8/12.8	DC Bayonet European (BA20d)	C-8/C-2R	2.60/66.0	1.42/36.0	100/100
6235B-BP	48057	35/35	12.8/12.8	DC Bayonet European (BA20d)	C-8/C-2R	2.60/66.0	1.42/36.0	100/100
6235J	48038	35/35	12.8/12.8	Double Contact Prefocus Flanged (P15d-3)	C-6/C-6	2.25/57.2	1.25/32.0	100/100
6235J-BP	57033	35/35	12.8/12.8	Double Contact Prefocus Flanged (P15d-3)	C-6/C-6	2.25/57.2	1.25/32.0	100/100
6235Y	48028	35/35	12.8/12.8	Double Contact Prefocus Flanged (P15d30)	C-6/C-6	2.30/58.4	1.38/35.0	100/100
6235Y-BP	57032	35/35	12.8/12.8	Double Contact Prefocus Flanged (P15d30)	C-6/C-6	2.30/58.4	1.38/35.0	100/100
6245B	48058	45/45	12.8/12.8	DC Bayonet European (BA20d)	C-8/C-2R	2.60/66.0	1.42/36.0	100/100
6245B-BP	48059	45/45	12.8/12.8	DC Bayonet European (BA20d)	C-8/C-2R	2.60/66.0	1.42/36.0	100/100
6245BA	48062	45/45	12.8/12.8	Axial Prefocus (P45t41)	C-8/C-2R	3.00/76.2	1.61/41.0	100/100
6245BA-BP	48063	45/45	12.8/12.8	Axial Prefocus (P45t41)	C-8/C-2R	3.00/76.2	1.61/41.0	100/100
6245J-BP	48041	45/45	12.8/12.8	Double Contact Prefocus Flanged (P15d-3)	C-6/C-2V	2.25/57.2	1.25/32.0	100/100
6245Y-BP	48031	45/45	12.8/12.8	Double Contact Prefocus Flanged (P15d30)	C-6/C-6	2.30/58.4	1.38/35.0	100/100
6253	40667	6	12	Miniature Bayonet (BA9s)	C-2V	1.07/27.2	0.59/15.0	200
6253-BP	40669	6	12	Miniature Bayonet (BA9s)	C-2V	1.07/27.2	0.59/15.0	200
6255BAH-BP	48067	60/55	12.8/12.8	Axial Prefocus, H4 (P45t41)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
6255BAHP-BP	48069	100/55	12.8/12.8	Axial Prefocus, H4 (P45t41)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
6260B-BP	48061	60/60	12.8/12.8	DC Bayonet European (BA20d)	C-8/C-2R	2.60/66.0	1.42/36.0	75
6260BA	48064	60/60	12.8/12.8	Axial Prefocus (P45t41)	C-8/C-2R	3.00/76.2	1.61/41.0	75/75
6260BA-BP	48065	60/60	12.8/12.8	Axial Prefocus (P45t41)	C-8/C-2R	3.00/76.2	1.61/41.0	75/75
6260H-BP	48071	60/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
6260HD-BP	48097	60/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
6260HP-BP	48073	100/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
6260J	48042	60/60	12.8/12.8	Double Contact Prefocus Flanged (P15d-3)	C-6/C-2V	2.25/57.2	1.25/32.0	75/75
6260J-BP	48043	60/60	12.8/12.8	Double Contact Prefocus Flanged (P15d-3)	C-6/C-2V	2.25/57.2	1.25/32.0	75/75
6260S	48036	60/60	12.8/12.8	Prefocus Flanged (P36t)	C-6/C-6	3.00/76.2	1.42/36.0	75/75
6260S-BP	48037	60/60	12.8/12.8	Prefocus Flanged (P36t)	C-6/C-6	3.00/76.2	1.42/36.0	75/75
6260SA-BP	48035	60/60	12.8/12.8	Axial Prefocus, H4 (P43t38)	C-8/C-2R	3.00/76.2	1.42/36.0	75/75
6263-BP	48096	100/55	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
6265-BP	48095	100/80	12/12	Axial Prefocus, H4 (P43t38)	C-8/C-8	3.62/92.0	0.65/16.5	100/200
6361-BP	57027	60/55	12.8/12.8	Axial Prefocus, H4 (P45t41)	C-8/C-8	3.62/92.0	0.65/16.5	150/300
6365	48093	100/80	12.8/12.8	Axial Prefocus, H4 (P45t41)	C-8/C-8	3.63/92.1	0.67/17.0	100/200
6365-BP	48094	100/80	12.8/12.8	Axial Prefocus, H4 (P45t41)	C-8/C-8	3.63/92.1	0.67/17.0	100/200
A-62	48000	3	6.75	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	
A-62-BP	48001	3	6.75	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	
A-72	48002	4	13.5	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	4000
A-72-BP	48003	4	13.5	Miniature Bayonet (BA9s)	C-2R	0.94/23.9	0.43/11.0	4000
A-1262	48004	1.2	6	European Bayonet (BA7s)	C-2R	0.91/23.0	0.27/6.9	200
A-1272	48006	2	12	European Bayonet (BA7s)	C-2R	0.91/23.0	0.27/6.9	200
A-1272-BP	48007	2	12	European Bayonet (BA7s)	C-2R	0.91/23.0	0.27/6.9	200
A-3598H	48012	15/15	6.5/6.5	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	-
A-3598H-BP	57029	15/15	6.5/6.5	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	-

Automotive Forward Lighting

Motorcycle and Snowmobile Lamps

Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours
A-3603	48008	25/25	12/12	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	100/100
A-3603-BP	48009	25/25	12/12	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	100/100
A-3625	48010	25/25	6.5/6.5	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	150/150
A-3625-BP	48011	25/25	6.5/6.5	Double Contact Flanged (PX15d)	C-2V/C-2V	1.85/47.0	0.79/20.1	150/150
A-4513	48014	17	6.4	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
A-4513-BP	48015	17	6.4	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
A-4527	48016	23	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
A-4527-BP	48017	23	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
A-4813	48020	17/5	6.4/7	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200/1000
A-4813-BP	48021	17/5	6.4/7	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200/1000
A-4829-BP	57031	27/8	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200/5000
A-5659	48024	35/35	6.5/6.5	Double Contact Prefocus Flanged (P15d30)	C-6/C-2V	2.20/56.0	1.26/32.0	100/100
A-5659-BP	48025	35/35	6.5/6.5	Double Contact Prefocus Flanged (P15d30)	C-6/C-2V	2.20/56.0	1.26/32.0	100/100
A-7025-BP	48027	35/25	13/13	Double Contact Prefocus Flanged (P15d-3)	C-6/C-2V	2.20/56.0	1.38/35.0	100/100
HM201	00385	30/30	12.8/12.8	Double Contact Prefocus Flanged (PX15d25-1)	C-6/C-6	1.63/41.3	0.40/10.2	300/320
HM202	00402	36.5/35	12.8/12.8	Double Contact Prefocus Flanged (PX15d25-2)	C-6/C-6	1.63/41.3	0.40/10.2	200/300

Automotive Cabinets



Ordering Code	Bar Code
44250	44250
44500	44500
CVSUKIT	07777

Sealed Beam Lamps

Incandescent Sealed Beam Lamps



Ordering Code	Bar Code	Volts	Watts	Shape	Base	Filament	MOL	MOD in/mm	Life Hours
4007	46002	13	100/100	PAR 46	MP (Slip-On and Screw)	C-6/C-6	3.75/95	5.75/146	25/25
4044	46008	12	12	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	150
4049	46010	13	150	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	15
4340	46012	48	80	PAR 36	MP (Slip-On and Screw)	C-2V	2.75/70	4.5/114.3	400
4350	46014	36	60	PAR 36	MP (Slip-On and Screw)	C-2V	2.75/70	4.5/114.3	400
4405	46016	12.8	30	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	100
4406	46018	12.8	35	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300 @ 14V
4411	46020	12.8	35	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300 @ 14V
4412	46022	12.8	35	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	300
4412A	46024	12.8	35	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	300
4413	46026	12.8	35	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	300 @ 14V
4414	46028	12.8	18	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
4415	46032	12.8	35	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
4415A	46034	12.8	35	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
4416	46036	12.8	30	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
4416R	46038	12.8	30	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
4419	46040	12.8	35	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	300 @ 14V
4435	46044	12.8	30	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	100 @ 14V
4436	46046	12.8	35	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	300
4446	46048	12.8	25	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
4461	46050	12.8	60	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300 @ 14V
4478	46052	13	60	PAR 46	2 Contact Lugs	2C-6	4.0/102	5.75/146	800 @ 14V
4502	46054	28	50	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	400
4505	46056	28	50	PAR 36	MP (Slip-On and Screw)	CC-6	2.75/70	4.5/114.3	400
4509	46057	13	100	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	25
4510	46058	6.4	25	PAR 36	Screw terminals (2ST)	C-6	2.75/70	4.5/114.3	300
4511	46060	6.2	30	PAR 36	Screw terminals (2ST)	C-6	2.75/70	4.5/114.3	300 @ 7V
4515	46062	6.4	30	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	100
4537	46066	13	100	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	25
4543	46068	12.5	100	PAR 56	Screw terminals (2ST)	C-6	4.5/114	7.0/178	50
4545	46070	12.0	100	PAR 56	Screw terminals (2ST)	C-6	4.5/114	7.0/178	100
4546	46072	4.7	2.35	PAR 36	Screw terminals (2ST)	C-2R	2.75/70	4.5/114.3	100
4570	46076	28	150	PAR 46	Screw terminals (2ST)	CC-6	3.75/95	5.75/146	300
4571	01359	28	150	PAR 46	Screw terminals (2ST)	CC-6	3.75/95	5.75/146	300
4578	46078	28	60	PAR 46	2 Contact Lugs	2C-6	4.0/102	5.75/146	800
4579	46080	28/28	80/60	PAR 46	3 Contact Lugs	CC-6/CC-6	4.0/102	5.75/146	400/400
4581	46082	28	450	PAR 46	MP (Slip-On and Screw)	CC-8	3.75/95	5.75/146	10
4589	46084	28	50	PAR 36	MP (Slip-On and Screw)	CC-6	2.75/70	4.5/114.3	400
4596	46085	28	250	PAR 36	Screw terminals (2ST)	CC-8	2.75/70	4.5/114.3	25

Sealed Beam Lamps

Incandescent Sealed Beam Lamps

Ordering Code	Bar Code	Volts	Watts	Shape	Base	Filament	MOL	MOD in/mm	Life Hours
4626	46086	28	150	PAR 36	MP (Slip-On and Screw)	CC-6	2.75/70	4.5/114.3	300
4636	91031	14	80	PAR 46	MP (Slip-On and Screw)	2CC6	3.75/95	5.75/146	200
4651	46090	12.8	50	Rec 100x165	2 Contact Lugs	C-6	4.8/121		200
4652	46092	12.8	40/60	Rec 100x165	3 Contact Lugs	C-6/C-6	4.8/121		200/320
4700	01373	13	100/100	PAR 36	Screw Terminals (3ST)	C-6/C-6	2.75/70	4.5/114.3	25/25
4880	01380	28	60	PAR 46	2 Contact Lugs	2C-6	4.0/102	5.75/146	800
6014	46098	12.8	60/50	PAR 56	3 Contact Lugs	C-6/C-6	5.0/127	7.0/178	200/320
6015	46100	12.8	60/50	PAR 56	3 Contact Lugs	C-6/C-6	5.0/127	7.0/178	300/500
6052	46102	12.8	65/55	Rec 142x200	3 Contact Lugs	C-6/C-6	5.44/138		150/320
7400	46106	12.8	35	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
7613	46108	6	7.4	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	50
7672-1	01689	6	7.2	PAR 36	Slip-On Terminals	C-6	2.75/70	4.5/114.3	50

Halogen Sealed Beam Lamps



Ordering Code	Bar Code	Volts	Watts	Shape	Base	Filament	MOL	MOD in/mm	Life Hours
36PAR36/CAP/WFL32	81166	12	36	PAR 36	MP (Slip-On and Screw)	C-6	2.36/60	4.5/114.3	4000
H4351	46107	12.8	55	Rec 55x135	Right Angle, Plastic	C-8	4.0/102		500
H4352	46109	12.8	65	Rec 55x135	Right Angle, Plastic	C-8	4.0/102		150
H4651	46110	12.8	50	Rec 100x165	2 Contact Lugs	C-6	4.8/121		200
H4656	46112	12.8	35/35	Rec 100x165	3 Contact Lugs	C-6/C-6	4.8/121		200/320
H4656C VXL	07669	12.8	35/35	Rec 100x165	3 Contact Lugs	C-6/C-6	4.8/121		200/320
H4656P VP	07655	12.8	35/35	Rec 100x165	3 Contact Lugs	C-6/C-6	4.8/121		200/320
H4666	46117	12.8	65/45	Rec 100x165	3 Contact Lugs	C-8/C-8	4.8/121		150/320
H4666C VXL	07755	12.8	65/45	Rec 100x165	3 Contact Lugs	C-8/C-8	4.8/121		150/320
H4666P VP	07756	12.8	65/45	Rec 100x165	3 Contact Lugs	C-8/C-8	4.8/121		150/320
H4701	91095	12.8	65	Rec 92x150	2 Contact Lugs	C-8	3.35/85		150
H4703	91094	12.8	55	Rec 92x150	2 Contact Lugs	C-8	3.35/85		320
H5001	46114	12.8	50	PAR 46	2 Contact Lugs	C-6	4.0/102	5.75/146	200
H5006	46116	12.8	35/35	PAR 46	3 Contact Lugs	C-6/C-6	4.0/102	5.75/146	200/320
H6024	46118	12.8	65/35	PAR 56	3 Contact Lugs	C-6/C-6	5.0/127	7.0/178	150/450
H6054	46120	12.8	65/35	Rec 142x200	3 Contact Lugs	C-6/C-6	5.44/138		150/320
H6054C VXL	07666	12.8	65/35	Rec 142x200	3 Contact Lugs	C-6/C-6	5.315/136		150/320
H6054H O/H655 4	46123	12.8	65/55	Rec 142x200	3 Contact Lugs	C-8/C-8	5.44/138		150/700
H6054P VP	07653	12.8	65/35	Rec 142x200	3 Contact Lugs	C-6/C-6	5.44/138		150/320
H7550	91074	6	8	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	50
H7600	91072	12.8	37.5	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
H7604	91070	12.8	50	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	100
H7606	02464	12.8	50	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	400 @ 14V
H7609	91077	12.8	50	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	400 @ 14V
H7610	91069	12.8	50	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	400 @ 14V
H7614	91071	12.8	50	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	100
H7616	91073	12.8	37.5	PAR 36	MP (Slip-On and Screw)	C-6	2.75/70	4.5/114.3	300
H7619	91078	12.8	50	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	400 @ 14V
H7635	46122	12.8	50	PAR 46	MP (Slip-On and Screw)	C-6	3.75/95	5.75/146	100
H7921-1	91088	12.8	50	Rec 100x165	MP (Slip-On and Screw)	C-6	4.53/115		200 @ 14V
H7935-1	91089	12.8	50	Rec 100x165	MP (Slip-On and Screw)	C-6	4.53/115		100
H9405	91100	12.8	50	Rec 92x150	2 Rt Angle Lugs	C-6	3.0/76		100
H9406	91096	12.8	50	Rec 92x150	2 Rt Angle Lugs	C-6	3.0/76		400 at 14V
H9411	91098	12.8	50	Rec 92x150	2 Rt Angle Lugs	C-6	3.0/76		400 at 14V
H9414	91101	12.8	50	Rec 92x150	2 Rt Angle Lugs	C-6	3.0/76		400 at 14V
H9415	91099	12.8	37.5	Rec 92x150	2 Rt Angle Lugs	C-6	3.0/76		200 at 14V
H9420	91102	12.8	50	Rec 92x150	2 Rt Angle Lugs	C-6	3.0/76		200 at 14V
H9421	91097	12.8	50	Rec 92x150	2 Rt Angle Lugs	C-6	3.0/76		200 at 14V

ANSI Coded Lamps

ANSI Coded Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
25T8/DC	03750	25	120	T-8	DC Bayonet (BA15d)	C-7A	195	2.63/66.7	0.99/25.0	200
100T8/1SC	49638	100	20	T-8	SC Bayonet (BA15s)	CC-6	2600	3.00/76.2	0.99/25.0	50
125T10P	03666	125	120	T-10	Medium Prefocus Flanged Single Contact (P28s)	C-13B	1740	5.75/146.1	1.26/32.0	500
150T10/H/F	00251	150	120	T-10	Medium Screw (E26)	CC-8	2850	4.0/101	1.25/31.8	1500
250T10/H/F	00197	250	120	T-10	Medium Screw (E26)	CC-8	4600	4.0/101	1.25/31.8	1500
64514	03655	300	120	T-6	GX6.35	CC-2F	7700	2.26/57.5	0.74/18.8	75

ANSI Coded Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
BBA	00040	250	120	A-21	Medium Screw (E26)	C-9	8500	4.77/121.2	2.68/68.0	3
BBA-LN	06959	250	120	A-21	Medium Screw (E26)	C-9	8700	4.88/124	2.68/68.0	4
BCA	00050	250	120	A-21	Medium Screw (E26)	C-9	5000	4.94/125.4	2.68/68.0	3
BCK	00060	500	120	T-6	G17t	C-13D P.R.		3.22/82.0	0.77/19.5	50
BFE	00090	750	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	17000	5.75/146.1	2.52/64.0	200
BFK/BFL	00100	750	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	13500	5.75/146.1	2.52/64.0	200
BKV	00140	30	120	S-11	SC Bayonet (BA15s)	CC-2V	400	2.38/60.3	1.40/35.5	50
BLC	10020	30	120	S-11	DC Bayonet (BA15d)	CC-2V	400	2.38/60.3	1.40/35.5	50
BLR	00170	50	120	S-11	SC Bayonet (BA15s)	CC-2V	780	2.38/60.3	1.40/35.5	50
BNF	00220	75	120	S-11	DC Bayonet (BA15d)	CC-2V	1300	2.38/60.3	1.40/35.5	25
BRH	00250	1000	120	T-5	Recessed Single Contact (R7s)	CC-8	30000	3.75/95.3	0.63/16.0	75
BRL	10033	50	12	T-3 1/2	G6.35	C BAR 6	1400	1.73/44.0	0.46/11.5	50
BTG	00380	1200	120	T-7	G17t	C-13D	38200	3.75/95.3	0.91/23.0	20
BTL	00390	500	120	T-6	Medium Prefocus Flanged Single Contact (P28s)	C-13D	11000	5.00/127.0	0.77/19.5	500
BTN	00410	750	120	T-7	Medium Prefocus Flanged Single Contact (P28s)	C-13D	17000	5.00/127.0	0.91/23.0	500
BTP	00420	750	120	T-7	Medium Prefocus Flanged Single Contact (P28s)	C-13D	20000	5.00/127.0	0.91/23.0	200
BTR	00430	1000	120	T-7	Medium Prefocus Flanged Single Contact (P28s)	C-13D	27500	5.00/127.0	0.91/23.0	200
BVT	00500	1000	120	T-7	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	23000	7.00/178.0	0.91/23.0	500
BVV	00510	1000	120	T-7	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	28500	7.00/178.0	0.91/23.0	200
BVW	00520	2000	120	T-11	Single Contact Mogul Prefocus Flanged (P40s)	C-13	59000	8.00/203.2	1.38/35.0	200
BWA	00530	2000	120	T-8	Mogul Bi-Pin Post (G38)	CC-8	54000	8.00/203.2	0.99/25.0	500
BWF	00540	2000	120	T-9	Mogul Screw (E39)	CC-8	54000	7.50/190.5	0.99/25.0	500
BWM	00550	750	120	T-7	G9.5	C-13D	21000	4.50/114.3	0.81/20.5	200
BWN	00560	1000	120	T-7	G9.5	C-13D	28500	4.50/114.3	0.81/20.5	250
BXE	00580	75	10	T-8	SC Bayonet (BA15s)	C-8	1700	3.13/79.4	0.99/25.0	100
CBA	00690	500	120	T-6	G17q	C-13D P.R.		3.63/92.1	0.77/19.5	50
CBX/CBS	00720	75	120	T-8	DC Bayonet (BA15d)	CC-13	1200	3.13/79.4	0.99/25.0	50
CDJ	00740	100	120	T-8	DC Bayonet (BA15d)	CC-2V	2000	3.13/79.4	0.99/25.0	50
CDS/CDX	00750	100	120	T-8	SC Bayonet (BA15s)	CC-13	1800	3.13/79.4	0.99/25.0	50
CEA/CEB/CDK	00760	100	120	T-8	DC Bayonet (BA15d)	CC-13	2000	3.13/79.4	0.99/25.0	50
CEM	00770	120	120	T-8	SC Bayonet (BA15s)	CC-2V	1950	3.13/79.4	0.99/25.0	200
CEW/CFC	00800	150	120	T-8	SC Bayonet (BA15s)	2CC-8	3500	3.63/92.1	0.99/25.0	25
CHK	00820	150	120	T-8	SC Bayonet (BA15s)	CC-13	2995	3.63/92.1	0.99/25.0	500
CLS/CLG	00830	300	120	T-8 1/2	SC Bayonet (BA15s)	C-13	7600	4.12/104.8	1.06/27.0	25
CMV/CMT	00850	300	120	T-8 1/2	SC Bayonet (BA15s)	C-13D	7300	4.12/104.8	1.06/27.0	25
CVX/CVS	00880	200	120	T-10	Medium Prefocus Flanged Single Contact (P28s)	CC-13	4250	5.31/135.0	1.26/32.0	50
CWZ	01010	1500	120	T-8	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	38500	7.50/190.5	1.38/35.0	325
CXK	01030	300	120	T-10	Medium Prefocus Flanged Single Contact (P28s)	C-13	7500	5.75/146.1	1.26/32.0	25
CXL/CXR	01040	50	8	T-9 1/2	Single Contact Prefocus Flanged (P15s30)	C-6		3.78/96.0	1.69/43.0	25
CXZ	01060	1500	120	T-8	Mogul Bi-Pin Post (G38)	C-13D	38500	8.00/203.2	1.38/35.0	325
CYC	01070	300	120	T-10	SC Bayonet (BA15s)	C-13	7400	3.19/81.0	1.14/29.0	25
CYV	01080	1000	120	T-7	Mogul Bi-Pin Post (G38)	C-13D	27500	7.87/200.0	0.91/23.0	200
CZX/DAB	01130	500	120	T-10	Medium Prefocus Flanged Single Contact (P28s)	C-13D	12500	5.75/146.1	1.26/32.0	25
DAY/DAK	01160	500	120	T-10	G17q	C-13D	12500	4.06/103.0	1.26/32.0	30
DCH/DJA/DFP	01190	150	120	T-12	G17q	CC-6		3.56/90.5	1.50/38.0	15
DDJ/DZZ	01230	80	10	T-3	GY9.5	C BAR 6	1700	2.00/50.8	0.44/11.0	1000
DDK	01240	80	19	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
DDL	10146	150	20	MR16	GX5.3	C-8		1.75/44.5	2.00/50.8	500
DDM	01250	80	19	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
DDS	01290	80	21	MR16	GX5.3	CC-6	165	1.75/44.5	2.00/50.8	1000
DFN/DFC	01390	150	120	T-12	G17q	CC-8		3.19/81.0	1.50/38.0	15
DJL	01430	150	120	T-14	G17q	CC-8		3.50/89.0	1.77/45.0	15
DLD/DFZ	01444	80	30	T-14	GX17q	CC-6		3.50/89.0	1.77/45.0	15
DLG/DLS/DHX	01450	150	21.5	T-14	GX17q	CC-6		3.50/89.0	1.77/45.0	10
DMX	01470	500	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	13200	5.75/146.1	2.52/64.0	50
DNE	01480	150	120	MR16	G7.9	CC-8		2.00/50.8	2.25/57.2	12
DNF	01490	150	21	MR16	GX7.9	C-6		2.00/50.8	2.25/57.2	25

ANSI Coded Lamps

ANSI Coded Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
DNS/FMC	01500	500	120	T-12	Medium Prefocus Flanged Single Contact (P28s)	C-13D	11000	6.12/155.5	1.50/38.0	200
DNW	01530	500	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	10000	5.75/146.1	2.52/64.0	500
DPT	01550	1000	120	T-20	Mogul Screw (E39)	C-13	28000	9.06/230.2	2.52/64.0	50
DPW	01560	1000	120	T-20	Single Contact Mogul Prefocus Flanged (P40s)	C-13	28000	9.50/241.3	2.52/64.0	50
DPY	01570	5000	120	T-17	Mogul Bi-Pin Post (G38)	C-13	145000	11.00/279.4	2.38/60.5	500
DRA	01580	300	120	T-5	G6.35	CC-6	6900	1.97/50.0	0.63/16.0	300
DRB/DRC	01600	1000	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	28000	5.75/146.1	2.52/64.0	25
DRS	01620	1000	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13D	29000	5.75/146.1	2.52/64.0	25
DRW	01640	1000	120	T-20	Mogul Screw (E39)	C-13D	27400	9.06/230.2	2.52/64.0	25
DTA	01660	1500	120	T-8	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	39000	8.00/203.2	0.99/25.0	100
DTJ	01670	1500	120	T-20	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	42500	9.50/241.3	2.52/64.0	25
DVS	01690	500	130	T-3	Recessed Single Contact (R7s)	CC-8	10000	4.71/119.6	0.40/10.0	2000
DVY	01700	650	120	G-6	G5.3	CC-6	20000	2.48/63.0	0.79/20.0	25
DWT	01720	1000	120	T-6	Recessed Single Contact (R7s)	CC-8	23400	5.67/144.1	0.75/19.1	2000
DXW	01760	1000	120	T-5	Recessed Single Contact (R7s)	CC-8	28000	3.75/95.3	0.71/18.0	150
DXX	01770	800	240	T-4	Recessed Single Contact (R7s)	CC-8	20500	3.17/80.6	0.55/14.0	75
DYH	01800	600	120	G-7	G5.3	CC-6	17000	2.50/63.5	0.87/22.0	75
DYR	01840	650	220	G-7	GZ9.5	2CC-8	16500	2.50/63.5	0.95/24.0	50
DYS/DYV/BHC	01850	600	120	T-6	GZ9.5	CC-6	17000	2.50/63.5	0.87/22.0	75
DYS/DYV/BHC/5	01860	600	120	T-6	GZ9.5	CC-6	17000	2.50/63.5	0.87/22.0	150
DYY/EGH	01880	500	120	T-6	G17t	C-13D	14000	3.22/82.0	0.77/19.5	50
DZA	01890	30	10.8	T-3 1/2	G5.3	C-6	800	2.00/50.8	0.46/11.5	400
DZE/FDS	49451	150	24	T-4	GY9.5	C BAR 6	4600	2.25/57.2	0.55/14.0	100
EAJ	01930	35 / 25	12 / 12	T-6 1/2	DC Bayonet (BA15d)	C-6/C-6	620 / 420	3.97/100.8	0.83/21.0	300 / 300
EBV	01950	500	120	PS-25	Medium Screw (E26)	C-9	17000	6.10/155	3.15/80.0	6
EBV-LN	06940	500	120	PS-25	Medium Screw (E26)	C-9	17800	6.85/174	3.15/80.0	8
EBW	01960	500	120	PS-25	Medium Screw (E26)	C-9	10500	6.10/155	3.15/80.0	6
ECA	01970	250	120	A-23	Medium Screw (E26)	C-9	6500	5.52/140.2	2.76/70.0	20
ECA-LN	07015	250	120	A-23	Medium Screw (E26)	C-9	6500	5.87/149	2.76/70.0	20
ECT	01980	500	120	PS-25	Medium Screw (E26)	C-9	13650	6.10/155	3.15/80.0	60
ECT-LN	06906	500	120	PS-25	Medium Screw (E26)	C-9	13650	6.85/174	3.15/80.0	60
EFM	01990	50	8	MR16	GZ6.35	C-6		1.65/42.0	1.97/50.0	50
EFN	10234	75	12	MR16	GZ6.35	C-8		1.65/42.0	1.97/50.0	50
EFP	10235	100	12	MR16	GZ6.35	C-8		1.65/42.0	1.97/50.0	50
EFR	10236	150	15	MR16	GZ6.35	C-8		1.65/42.0	1.97/50.0	50
EGC	02000	500	120	T-4	Medium Prefocus Flanged Single Contact (P28s)	CC-8	13000	6.00/152.4	0.55/14.0	300
EGE	02010	500	120	T-4 1/2	Medium Prefocus Flanged Single Contact (P28s)	CC-8	10000	6.00/152.4	0.55/14.0	2000
EGF	02020	750	120	T-5	Medium Prefocus Flanged Single Contact (P28s)	CC-8	20000	6.00/152.4	0.63/16.0	250
EGG	02030	750	120	T-5	Medium Prefocus Flanged Single Contact (P28s)	CC-8	15000	6.00/152.4	0.63/16.0	2000
EGJ	02040	1000	120	T-6	Medium Prefocus Flanged Single Contact (P28s)	CC-8	27500	6.00/152.4	0.77/19.5	400
EGK	02050	1000	120	T-6	Medium Prefocus Flanged Single Contact (P28s)	CC-8	26500	6.00/152.4	0.77/19.5	400
EGN	02070	500	120	T-6	Medium Bi-Post (G22)	C-13D	13000	5.50/139.7	0.77/19.5	100
EGR	02080	750	120	T-7	Medium Bi-Post (G22)	C-13D	20000	5.50/139.7	0.91/23.0	200
EGT	02090	1000	120	T-7	Medium Bi-Post (G22)	C-13D	27500	5.50/139.7	0.91/23.0	200
EHA	02120	500	120	T-6	GY9.5	C-13 P.R.		3.00/76.2	0.77/19.5	50
EHC/EHB	02140	500	120	T-4	G9.5	CC-8	13000	3.75/95.3	0.55/14.0	300
EHD	02150	500	120	T-5	G9.5	CC-8	10000	4.00/101.6	0.55/14.0	2000
EHF	02160	750	120	T-5	G9.5	CC-8	20400	4.12/104.8	0.73/18.5	300
EHG	02170	750	120	T-5	G9.5	CC-8	15000	4.12/104.8	0.73/18.5	2000
EHJ	10257	250	24	T-4	G6.35	C BAR 6	8000	2.16/55.0	0.53/13.5	50
EHM	02180	300	120	T-3	Recessed Single Contact (R7s)	C-8	6000	4.72/119.9	0.40/10.0	2000
EHP	15214	300	120	T-4	Recessed Single Contact (R7s)	CC-8	5000	3.17/80.6	0.52/13.0	2000
EHR	15218	400	120	T-4	Recessed Single Contact (R7s)	CC-8	7750	3.17/80.6	0.52/13.0	2000
EHT	15256	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	5000	3.15/80.0	0.52/13.0	2000
EHZ	02230	300	120	T-3	Recessed Single Contact (R7s)	C-8	6000	4.72/119.9	0.36/9.0	2000
EJA	10264	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40

ANSI Coded Lamps

ANSI Coded Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
EJG	02250	750	120	T-3	Recessed Single Contact (R7s)	C-8	20600	4.72/119.9	0.48/12.0	400
EJL	02260	200	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
EJM	02280	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
EJV	02290	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
EJY	10272	80	19	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25
EKB	02300	420	120	G-7	GZ9.5	CC-6	11000	2.50/63.5	0.87/22.0	75
EKD	02310	650	120	G-6	GZ9.5	CC-6	20000	2.60/66.0	0.78/19.9	25
EKE	10275	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	200
EKP/ENA	02350	80	30	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25
EKZ	02370	30	10.8	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	200
ELB	02390	80	30	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	15
ELC	02400	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
ELC/5	02410	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	100
ELC/5H	49423	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	500
ELC/E	02420	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
ELD/EJN	02430	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
ELE	02440	80	30	MR14	GX7.9	CC-6		1.60/40.7	1.75/44.5	20
ELH	02450	300	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	35
ELH/5	02460	300	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	70
EMD	02520	750	120	T-3	Recessed Single Contact (R7s)	C-8	19500	4.72/119.9	0.44/11.0	400
EMM/EKS	02530	250	24	MR14	GX7.9	CC-6		1.87/47.5	1.75/44.5	50
ENG	02550	300	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	15
ENH	02570	250	120	MR16	GY5.3	CC-8	15000	1.75/44.5	2.00/50.8	175
ENX	02600	360	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	75
ENX/5	02610	360	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	150
ENZ	02620	50	30	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25
EPN	02660	35	12	MR16	GX5.3	C-6		1.75/44.5	2.00/50.8	50
EPT	02680	42	10.8	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	8000
EPZ	02720	50	13.8	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	1000
ESD	02750	150	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	12
ESH	02760	85	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	250
ESJ	02770	85	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	40
ESL	15240	150	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	2800	2.80/71.0	0.52/13.0	1000
ESM	15258	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	4800	3.19/81.0	0.52/13.0	2000
ESN	15222	100	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	1900	2.80/71.0	0.52/13.0	750
ESP	15246	150	120	T-4	DC Bayonet (BA15d)	CC-2V	2400	2.44/61.9	0.55/14.0	1000
ESR	15226	100	120	T-4	DC Bayonet (BA15d)	CC-2V	1900	2.44/61.9	0.55/14.0	1000
ESS	15260	250	120	T-4	DC Bayonet (BA15d)	CC-8	5000	3.15/80.0	0.55/14.0	2000
ESY	02780	150	120	T-4	G6.35	CC-6	3300	1.97/50.0	0.53/13.5	200
ETB	15262	250	120	T-4	DC Bayonet (BA15d)	CC-8	4700	3.15/80.0	0.55/14.0	2000
ETC	15244	150	120	T-4	DC Bayonet (BA15d)	CC-8	2800	2.44/61.9	0.52/13.0	2000
ETD	15228	100	120	T-4	DC Bayonet (BA15d)	CC-2V	1750	2.44/61.9	0.52/13.0	750
ETE	15224	100	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	1750	2.80/71.0	0.52/13.0	750
ETF	15248	150	120	T-4	DC Bayonet (BA15d)	CC-8	2700	2.68/68.0	0.52/13.0	2000
ETG	15238	150	120	T-4	Miniature Candelabra Screw (E11)	CC-8	2600	3.00/76.2	0.55/14.0	2000
ETH	15242	150	120	T-4	Miniature Candelabra Screw (E11)	CC-8	2700	3.00/76.2	0.55/14.0	2000
ETJ	02790	250	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	175
EVC/FGX	02800	250	24	T-4	G6.35	C BAR 6	8400	2.25/57.2	0.57/14.5	200
EVD	02810	400	36	T-6	G6.35	C BAR 6	14500	2.38/60.3	0.75/19.1	50
EVR	15278	500	120	T-4	Miniature Candelabra Screw (E11)	CC-8	10000	3.75/95.3	0.55/14.0	2000
EVW	02820	250	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
EXR	02850	300	82	MR13	GX5.3	CC-8		1.75/44.5	1.66/42.1	35
EXR/5	02860	300	82	MR13	GX5.3	CC-8		1.75/44.5	1.66/42.1	70
EXV	02880	100	12	MR16	GX5.3	CC-6	3300	1.75/44.5	2.00/50.8	50
EXY	02920	250	82	MR13	GX5.3	CC-8		1.75/44.5	1.66/42.1	200
EYA	02940	200	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
EYB	02950	360	82	T-3 1/2	G5.3	CC-8	10000	2.25/57.2	0.46/11.5	75
EYB/5	02960	360	82	T-3 1/2	G5.3	CC-8	10000	2.25/57.2	0.46/11.5	150
EYH/FKT	02970	250	120	G-6	G5.3	CC-6	5400	2.48/63.0	0.87/22.0	200
EYK	02980	300	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	60
EYV	15276	500	130	T-4	Miniature Candelabra Screw (E11)	CC-8	10000	3.75/95.3	0.52/13.0	2000
EYW	15280	500	130	T-4	Miniature Candelabra Screw (E11)	CC-8	10000	3.75/95.3	0.52/13.0	2000
EYX	15274	500	120	T-4	Miniature Candelabra Screw (E11)	CC-8	10000	3.75/95.3	0.52/13.0	2000
EZE	03000	150	82	MR13	GX5.3	CC-8	350	1.75/44.5	1.66/42.1	150
FAD	03010	650	120	T-4	Recessed Single Contact (R7s)	CC-8	16500	3.17/80.6	0.55/14.0	100
FAL	03020	420	120	T-4	Recessed Single Contact (R7s)	CC-8	11000	2.63/66.7	0.55/14.0	90
FBG/FBD	03040	500	120	G-6	G5.3	CC-6	13200	3.00/76.2	0.87/22.0	50
FCB	03100	600	120	T-4	Recessed Single Contact (R7s)	CC-8	16500	3.75/95.3	0.55/14.0	75
FCL	03130	500	120	T-3	Recessed Single Contact (R7s)	C-8	10000	4.72/119.9	0.44/11.0	2000
FCM	03140	1000	120	T-3	Recessed Single Contact (R7s)	C-8	27000	4.72/119.9	0.44/11.0	300
FCR	10403	100	12	T-3 1/2	GY6.35	C BAR 6	2900	1.73/44.0	0.46/11.5	50
FCS	10404	150	24	T-4	G6.35	C BAR 6	4500	1.97/50.0	0.53/13.5	50
FCZ	03160	500	120	T-3	Recessed Single Contact (R7s)	C-8	10800	4.72/119.9	0.44/11.0	2000
FDB	03180	1500	120	T-4	Recessed Single Contact (R7s)	C-8	40000	6.61/167.9	0.44/11.0	400

ANSI Coded Lamps

ANSI Coded Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
FDF	03190	500	120	T-3	Recessed Single Contact (R7s)	C-8	13250	4.72/119.9	0.44/11.0	400
FDN	03200	500	120	T-3	Recessed Single Contact (R7s)	C-8	12500	4.72/119.9	0.44/11.0	400
FDT	03220	100	12	T-3 1/4	GZ9.5	C BAR 6	2900	2.25/57.2	0.44/11.0	50
FDV	03230	150	24	T-4	G6.35	C BAR 6	4300	2.00/50.8	0.55/14.0	100
FEL	03240	1000	120	T-6	G9.5	CC-8	27000	4.00/101.6	0.77/19.5	300
FEP	03250	1000	220	T-6	G9.5	CC-8	26500	4.00/101.6	0.77/19.5	150
FEV	15254	200	120	T-4	DC Bayonet (BA15d)	CC-2V	5500	2.44/61.9	0.55/14.0	50
FEY	03280	2000	120	T-8	Recessed Single Contact (R7s)	CC-8	57000	5.62/142.8	1.10/28.0	300
FFJ	03290	600	120	T-4	Recessed Single Contact (R7s)	CC-8	16500	2.63/66.7	0.55/14.0	75
FFN	03320	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	11000	6.03/153.0	8.35/212.0	800
FFP	03330	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	12000	6.03/153.0	8.35/212.0	800
FFR	03340	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	14000	6.03/153.0	8.35/212.0	800
FFS	03350	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	19000	6.03/153.0	8.35/212.0	800
FFT	03360	1000	120	T-3 1/4	Recessed Single Contact (R7s)	C-8	26400	6.61/167.9	0.44/11.0	300
FHM	03400	1000	120	T-3	Recessed Single Contact (R7s)	C-8	26000	4.72/119.9	0.44/11.0	300
FHS	03420	300	82	MR13	GX5.3	CC-8		1.75/44.5	1.66/42.1	70
FKW	03455	300	120	T-6	GY9.5	C-13	7800	3.54/90.0	0.75/19.1	200
FLK	03475	575	120	T-6	G9.5	CC-8	16500	3.97/100.8	0.75/19.1	300
FLT	03470	28	13.8	MR11	GU4	CC-6		1.50/38.0	1.41/35.8	500
FLW	03480	300	24	T-4	GY6.35 w/ Ceramic Seal Cover	C BAR 6	10200	2.16/55.0	0.55/14.0	50
FNT	03500	275	24	T-4	G6.35	C BAR 6	10000	2.16/55.0	0.55/14.0	75
FRK	15095	650	120	T-7	GY9.5	C-13	16900	3.54/90.0	0.87/22.0	200
FTK	15097	500	120	T-6	GY9.5	CC-6	13500	2.57/65.3	0.75/19.1	200
FXL	03501	410	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
FXL/5	49116	410	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	100
GCA	03503	250	120	T-3 1/2	G5.3	CC-8	6000	2.25/57.2	0.46/11.5	200
GDA	03507	500	120	T-4	Recessed Single Contact (R7s)	C-8	11000	5.25/133.3	0.48/12.0	100
GLA	10418	575	115	T-7	G9.5	C-13D	13000	4.00/101.6	0.87/22.0	1500
GLC	10419	575	115	T-7	G9.5	C-13D	15500	4.00/101.6	0.87/22.0	400
HPL375/115V	05913	375	115	T-6	G9.5 w/ Heatsink	4-C8	10540	3.86/98	0.72/18.4	300
HPL375LL/115V	05914	375	115	T-6	G9.5 w/ Heatsink	4-C8	8000	3.86/98	0.72/18.4	1000
HPL550/77V	05641	550	77	T-6	G9.5 w/ Heatsink	4-C8	16170	3.86/98	0.72/18.4	300
HPL550LL/77V	05915	550	77	T-6	G9.5 w/ Heatsink	4-C8	12160	3.86/98	0.72/18.4	2000
HPL575/115V	10415	575	115	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300
HPL575/120V	05152	575	120	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300
HPL575/230V	05916	575	230	T-6	G9.5 w/ Heatsink	6-C8	14900	3.86/98	0.72/18.4	400
HPL575/240V	05917	575	240	T-6	G9.5 w/ Heatsink	6-C8	14900	3.86/98	0.72/18.4	400
HPL575LL/115V	10416	575	115	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2000
HPL575LL/120V	05918	575	120	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2000
HPL575LL/230V	05919	575	230	T-6	G9.5 w/ Heatsink	6-C8	11780	3.86/98	0.72/18.4	1500
HPL575LL/240V	05920	575	240	T-6	G9.5 w/ Heatsink	6-C8	11780	4.09/104	0.72/18.4	1500
HPL750/77V	05642	750	77	T-6	G9.5 w/ Heatsink	4-C8	22950	3.86/98	0.72/18.4	300
HPL750/115V	10417	750	115	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300
HPL750/120V	05921	750	120	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300
HPL750/230V	05922	750	230	T-6	G9.5 w/ Heatsink	6-C8	19750	4.09/104	0.72/18.4	300
HPL750/240V	05923	750	240	T-6	G9.5 w/ Heatsink	6-C8	19750	4.09/104	0.72/18.4	300
HPL750LL/115V	05924	750	115	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	1500
HPL750LL/120V	05925	750	120	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	2000
HPL750LL/230V	05926	750	230	T-6	G9.5 w/ Heatsink	6-C8	15600	4.09/104	0.72/18.4	1500
HPL750LL/240V	05927	750	240	T-6	G9.5 w/ Heatsink	6-C8	15600	4.09/104	0.72/18.4	1500
JC24V300W	03530	300	24	T-4 1/2	G6.35	C-6	9900	2.16/55.0	0.55/14.0	50
JCR/M12V100W	03624	100	12	MR11	G5.3-4.8	C-8		1.46/37.0	1.41/35.8	50
JCR/M12V75W	03623	75	12	MR11	G5.3-4.8	C-8	300	1.46/37.0	1.41/35.8	50
JCR/M14V35W	03625	35	14	MR11	GZ4	CC-8		1.65/42.0	1.50/38.0	50
JCR120V150WB	03640	150	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	100
ML-2100	05411	100	120	R-19	Medium Screw (E26)	CC-6	1450	4.06/103	2.36/60	750
PH/111A	03650	75	120	S-11	SC Bayonet (BA15s)	CC-2V	1120	2.38/60.3	1.38/35.0	25
PH/140	03662	75	120	S-14	Medium Screw (E26)	CC-2V	1150	3.38/86.0	1.73/44.0	50
PH/211	03663	75	115-125	A-21	Medium Screw (E26)	CC-2V	1000	4.94/125.4	2.60/66.0	100
PH/212	03664	150	115-125	A-21	Medium Screw (E26)	CC-2V	2300	4.94/125.4	2.60/66.0	100
Q75CL-28V	15210	75	28	T-3 1/2	Miniature Screw w/ Ceramic Seal (E210)	CC-6	1200	2.50/63.5	0.44/11.0	2000
Q75CL/DC-28V	15212	75	28	T-3 1/2	DC Bayonet (BA15d)	CC-6	1300	2.38/60.3	0.44/11.0	2000
Q150T4/CL/25	15204	150	25	T-4	Recessed Single Contact (R7s)	C-8	2700	2.48/63.0	0.52/13.0	3000
WK76	80150	400	600-1000							
WK76-UV	80160	400	600-1000							

ANSI Coded Lamps

ANSI Coded Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
WK92	80100	1000	800							
WK92-UV	80110	1000	800							
WK93	80120	200	400							
WK94	80080	400	800							
WK95	80130	400	400							
WK96	80060	2000	900							
WK96-UV	80070	2000	900							
WK98	80190	3200	600-1200							
WK98-UV	80200	3200	600-1200							
WK101	80205	600-1000	450-900							
WK120HD	80020	400	450							
WK120HD-UV	80030	400	450							
WK140HD	80040	400	450-500							
WK140HD-UV	80050	400	450-500							

Photographic & SSTV Lamps

Enlarger Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
EJL	02260	200	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
EJV	02290	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
ELC	02400	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
ELC/E	02420	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
ELH	02450	300	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	35
ENH	02570	250	120	MR16	GY5.3	CC-8	15000	1.75/44.5	2.00/50.8	175
ESD	02750	150	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	12
ESJ	02770	85	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	40
EVW	02820	250	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
EYA	02940	200	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
FAL	03020	420	120	T-4	Recessed Single Contact (R7s)	CC-8	11000	2.63/66.7	0.55/14.0	90
FFJ	03290	600	120	T-4	Recessed Single Contact (R7s)	CC-8	16500	2.63/66.7	0.55/14.0	75
PH/111A	03650	75	120	S-11	SC Bayonet (BA15s)	CC-2V	1120	2.38/60.3	1.38/35.0	25
PH/140	03662	75	120	S-14	Medium Screw (E26)	CC-2V	1150	3.38/86.0	1.73/44.0	50
PH/211	03663	75	115-125	A-21	Medium Screw (E26)	CC-2V	1000	4.94/125.4	2.60/66.0	100
PH/212	03664	150	115-125	A-21	Medium Screw (E26)	CC-2V	2300	4.94/125.4	2.60/66.0	100

Flashtubes

Ordering Code	Bar Code	Watts	Volts
WK76	80150	400	600-1000
WK76-UV	80160	400	600-1000
WK92	80100	1000	800
WK92-UV	80110	1000	800
WK93	80120	200	400
WK94	80080	400	800
WK95	80130	400	400
WK96	80060	2000	900
WK96-UV	80070	2000	900
WK98	80190	3200	600-1200
WK98-UV	80200	3200	600-1200
WK101	80205	600-1000	450-900
WK120HD	80020	400	450
WK120HD-UV	80030	400	450
WK140HD	80040	400	450-500
WK140HD-UV	80050	400	450-500

Modeling Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
25T8/DC	03750	25	120	T-8	DC Bayonet (BA15d)	C-7A	195	2.63/66.7	0.99/25.0	200
150T10/H/F	00251	150	120	T-10	Medium Screw (E26)	CC-8	2850	4.0/101.8	1.25/31.8	1500
250T10/H/F	00197	250	120	T-10	Medium Screw (E26)	CC-8	4600	4.0/101.8	1.25/31.8	1500
500T46/MOG-120V	06783	500	120	T-13	Mogul Screw (E39)	CC-8	10000	7.87/200.0	1.81/46.0	1500
EAJ	01930	35 / 25	12 / 12	T-6 1/2	DC Bayonet (BA15d)	C-6/C-6	620 / 420	3.97/10.8	0.83/21.0	300 / 300
EHT	15256	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	5000	3.15/80.0	0.52/13.0	2000
ESL	15240	150	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	2800	2.80/71.0	0.52/13.0	1000
ESM	15258	250	120	T-4	Miniature Candelabra Screw (E11)	CC-8	4800	3.19/81.0	0.52/13.0	2000

Photographic & SSTV Lamps

Modeling Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
ESN	15222	100	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	1900	2.80/71.0	0.52/13.0	750
ESP	15246	150	120	T-4	DC Bayonet (BA15d)	CC-2V	2400	2.44/61.9	0.55/14.0	1000
ESR	15226	100	120	T-4	DC Bayonet (BA15d)	CC-2V	1900	2.44/61.9	0.55/14.0	1000
ESS	15260	250	120	T-4	DC Bayonet (BA15d)	CC-8	5000	3.15/80.0	0.55/14.0	2000
ETB	15262	250	120	T-4	DC Bayonet (BA15d)	CC-8	4700	3.15/80.0	0.55/14.0	2000
ETC	15244	150	120	T-4	DC Bayonet (BA15d)	CC-8	2800	2.44/61.9	0.52/13.0	2000
ETD	15228	100	120	T-4	DC Bayonet (BA15d)	CC-2V	1750	2.44/61.9	0.52/13.0	750
ETE	15224	100	120	T-4	Miniature Candelabra Screw (E11)	CC-2V	1750	2.80/71.0	0.52/13.0	750
ETF	15248	150	120	T-4	DC Bayonet (BA15d)	CC-8	2700	2.68/68.0	0.52/13.0	2000
ETG	15238	150	120	T-4	Miniature Candelabra Screw (E11)	CC-8	2600	3.00/76.2	0.55/14.0	2000
ETH	15242	150	120	T-4	Miniature Candelabra Screw (E11)	CC-8	2700	3.00/76.2	0.55/14.0	2000
EVR	15278	500	120	T-4	Miniature Candelabra Screw (E11)	CC-8	10000	3.75/95.3	0.55/14.0	2000
ML-2100	05411	100	120	R-19	Medium Screw (E26)	CC-6	1450	4.06/103	2.36/60	750

Photoflood Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
BBA	00040	250	120	A-21	Medium Screw (E26)	C-9	8500	4.77/121.2	2.68/68.0	3
BBA-LN	06959	250	120	A-21	Medium Screw (E26)	C-9	8700	4.88/124	2.68/68.0	4
BCA	00050	250	120	A-21	Medium Screw (E26)	C-9	5000	4.94/125.4	2.68/68.0	3
EBV	01950	500	120	PS-25	Medium Screw (E26)	C-9	17000	6.10/155	3.15/80.0	6
EBV-LN	06940	500	120	PS-25	Medium Screw (E26)	C-9	17800	6.85/174	3.15/80.0	8
EBW	01960	500	120	PS-25	Medium Screw (E26)	C-9	10500	6.10/155	3.15/80.0	6
ECA	01970	250	120	A-23	Medium Screw (E26)	C-9	6500	5.52/140.2	2.76/70.0	20
ECA-LN	07015	250	120	A-23	Medium Screw (E26)	C-9	6500	5.87/149	2.76/70.0	20
ECT	01980	500	120	PS-25	Medium Screw (E26)	C-9	13650	6.10/155	3.15/80.0	60
ECT-LN	06906	500	120	PS-25	Medium Screw (E26)	C-9	13650	6.85/174	3.15/80.0	60

HPL Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
HPL375/115V	05913	375	115	T-6	G9.5 w/ Heatsink	4-C8	10540	3.86/98	0.72/18.4	300
HPL375LL/115V	05914	375	115	T-6	G9.5 w/ Heatsink	4-C8	8000	3.86/98	0.72/18.4	1000
HPL550/77V	05641	550	77	T-6	G9.5 w/ Heatsink	4-C8	16170	3.86/98	0.72/18.4	300
HPL550LL/77V	05915	550	77	T-6	G9.5 w/ Heatsink	4-C8	12160	3.86/98	0.72/18.4	2000
HPL575/115V	10415	575	115	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300
HPL575/120V	05152	575	120	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300
HPL575/230V	05916	575	230	T-6	G9.5 w/ Heatsink	6-C8	14900	3.86/98	0.72/18.4	400
HPL575/240V	05917	575	240	T-6	G9.5 w/ Heatsink	6-C8	14900	3.86/98	0.72/18.4	400
HPL575LL/115V	10416	575	115	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2000
HPL575LL/120V	05918	575	120	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2000
HPL575LL/230V	05919	575	230	T-6	G9.5 w/ Heatsink	6-C8	11780	3.86/98	0.72/18.4	1500
HPL575LL/240V	05920	575	240	T-6	G9.5 w/ Heatsink	6-C8	11780	4.09/104	0.72/18.4	1500
HPL750/77V	05642	750	77	T-6	G9.5 w/ Heatsink	4-C8	22950	3.86/98	0.72/18.4	300
HPL750/115V	10417	750	115	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300
HPL750/120V	05921	750	120	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300
HPL750/230V	05922	750	230	T-6	G9.5 w/ Heatsink	6-C8	19750	4.09/104	0.72/18.4	300
HPL750/240V	05923	750	240	T-6	G9.5 w/ Heatsink	6-C8	19750	4.09/104	0.72/18.4	300
HPL750LL/115V	05924	750	115	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	1500
HPL750LL/120V	05925	750	120	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	2000
HPL750LL/230V	05926	750	230	T-6	G9.5 w/ Heatsink	6-C8	15600	4.09/104	0.72/18.4	1500
HPL750LL/240V	05927	750	240	T-6	G9.5 w/ Heatsink	6-C8	15600	4.09/104	0.72/18.4	1500

Photographic & SSTV Lamps

ANSI Coded SSTV Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
BFE	00090	750	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	17000	5.75/146.1	2.52/64.0	200
BFK/BFL	00100	750	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	13500	5.75/146.1	2.52/64.0	200
BRH	00250	1000	120	T-5	Recessed Single Contact (R7s)	CC-8	30000	3.75/95.3	0.63/16.0	75
BTL	00390	500	120	T-6	Medium Prefocus Flanged Single Contact (P28s)	C-13D	11000	5.00/127.0	0.77/19.5	500
BTN	00410	750	120	T-7	Medium Prefocus Flanged Single Contact (P28s)	C-13D	17000	5.00/127.0	0.91/23.0	500
BTP	00420	750	120	T-7	Medium Prefocus Flanged Single Contact (P28s)	C-13D	20000	5.00/127.0	0.91/23.0	200
BTR	00430	1000	120	T-7	Medium Prefocus Flanged Single Contact (P28s)	C-13D	27500	5.00/127.0	0.91/23.0	200
BVT	00500	1000	120	T-7	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	23000	7.00/178.0	0.91/23.0	500
BVV	00510	1000	120	T-7	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	28500	7.00/178.0	0.91/23.0	200
BVW	00520	2000	120	T-11	Single Contact Mogul Prefocus Flanged (P40s)	C-13	59000	8.00/203.2	1.38/35.0	200
BWA	00530	2000	120	T-8	Mogul Bi-Pin Post (G38)	CC-8	54000	8.00/203.2	0.99/25.0	500
BWF	00540	2000	120	T-9	Mogul Screw (E39)	CC-8	54000	7.50/190.5	0.99/25.0	500
BWM	00550	750	120	T-7	G9.5	C-13D	21000	4.50/114.3	0.81/20.5	200
BWN	00560	1000	120	T-7	G9.5	C-13D	28500	4.50/114.3	0.81/20.5	250
CWZ	01010	1500	120	T-8	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	38500	7.50/190.5	1.38/35.0	325
CXZ	01060	1500	120	T-8	Mogul Bi-Pin Post (G38)	C-13D	38500	8.00/203.2	1.38/35.0	325
CYV	01080	1000	120	T-7	Mogul Bi-Pin Post (G38)	C-13D	27500	7.87/200.0	0.91/23.0	200
DMX	01470	500	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	13200	5.75/146.1	2.52/64.0	50
DNS/FMC	01500	500	120	T-12	Medium Prefocus Flanged Single Contact (P28s)	C-13D	11000	6.12/155.5	1.50/38.0	200
DNW	01530	500	120	T-20	Medium Prefocus Flanged Single Contact (P28s)	C-13	10000	5.75/146.1	2.52/64.0	500
DPT	01550	1000	120	T-20	Mogul Screw (E39)	C-13	28000	9.06/230.2	2.52/64.0	50
DPW	01560	1000	120	T-20	Single Contact Mogul Prefocus Flanged (P40s)	C-13	28000	9.50/241.3	2.52/64.0	50
DPY	01570	5000	120	T-17	Mogul Bi-Pin Post (G38)	C-13	145000	11.00/279.4	2.38/60.5	500
DRW	01640	1000	120	T-20	Mogul Screw (E39)	C-13D	27400	9.06/230.2	2.52/64.0	25
DTA	01660	1500	120	T-8	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	39000	8.00/203.2	0.99/25.0	100
DTJ	01670	1500	120	T-20	Single Contact Mogul Prefocus Flanged (P40s)	C-13D	42500	9.50/241.3	2.52/64.0	25
DVS	01690	500	130	T-3	Recessed Single Contact (R7s)	CC-8	10000	4.71/119.6	0.40/10.0	2000
DWT	01720	1000	120	T-6	Recessed Single Contact (R7s)	CC-8	23400	5.67/144.1	0.75/19.1	2000
DXW	01760	1000	120	T-5	Recessed Single Contact (R7s)	CC-8	28000	3.75/95.3	0.71/18.0	150
DXX	01770	800	240	T-4	Recessed Single Contact (R7s)	CC-8	20500	3.17/80.6	0.55/14.0	75
EGC	02000	500	120	T-4	Medium Prefocus Flanged Single Contact (P28s)	CC-8	13000	6.00/152.4	0.55/14.0	300
EGE	02010	500	120	T-4 1/2	Medium Prefocus Flanged Single Contact (P28s)	CC-8	10000	6.00/152.4	0.55/14.0	2000
EGF	02020	750	120	T-5	Medium Prefocus Flanged Single Contact (P28s)	CC-8	20000	6.00/152.4	0.63/16.0	250
EGG	02030	750	120	T-5	Medium Prefocus Flanged Single Contact (P28s)	CC-8	15000	6.00/152.4	0.63/16.0	2000
EGJ	02040	1000	120	T-6	Medium Prefocus Flanged Single Contact (P28s)	CC-8	27500	6.00/152.4	0.77/19.5	400
EGK	02050	1000	120	T-6	Medium Prefocus Flanged Single Contact (P28s)	CC-8	26500	6.00/152.4	0.77/19.5	400
EGN	02070	500	120	T-6	Medium Bi-Post (G22)	C-13D	13000	5.50/139.7	0.77/19.5	100
EGR	02080	750	120	T-7	Medium Bi-Post (G22)	C-13D	20000	5.50/139.7	0.91/23.0	200
EGT	02090	1000	120	T-7	Medium Bi-Post (G22)	C-13D	27500	5.50/139.7	0.91/23.0	200
EHC/EHB	02140	500	120	T-4	G9.5	CC-8	13000	3.75/95.3	0.55/14.0	300
EHD	02150	500	120	T-5	G9.5	CC-8	10000	4.00/101.6	0.55/14.0	2000
EHF	02160	750	120	T-5	G9.5	CC-8	20400	4.12/104.8	0.73/18.5	300
EHG	02170	750	120	T-5	G9.5	CC-8	15000	4.12/104.8	0.73/18.5	2000
EHM	02180	300	120	T-3	Recessed Single Contact (R7s)	C-8	6000	4.72/119.9	0.40/10.0	2000
EHP	15214	300	120	T-4	Recessed Single Contact (R7s)	CC-8	5000	3.17/80.6	0.52/13.0	2000
EHR	15218	400	120	T-4	Recessed Single Contact (R7s)	CC-8	7750	3.17/80.6	0.52/13.0	2000

ANSI Coded SSTV Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
EHZ	02230	300	120	T-3	Recessed Single Contact (R7s)	C-8	6000	4.72/119.9	0.36/9.0	2000
EJG	02250	750	120	T-3	Recessed Single Contact (R7s)	C-8	20600	4.72/119.9	0.48/12.0	400
EKB	02300	420	120	G-7	GZ9.5	CC-6	11000	2.50/63.5	0.87/22.0	75
EKD	02310	650	120	G-6	GZ9.5	CC-6	20000	2.60/66.0	0.78/19.9	25
ELC/5H	49423	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	500
EMD	02520	750	120	T-3	Recessed Single Contact (R7s)	C-8	19500	4.72/119.9	0.44/11.0	400
FAD	03010	650	120	T-4	Recessed Single Contact (R7s)	CC-8	16500	3.17/80.6	0.55/14.0	100
FCL	03130	500	120	T-3	Recessed Single Contact (R7s)	C-8	10000	4.72/119.9	0.44/11.0	2000
FCM	03140	1000	120	T-3	Recessed Single Contact (R7s)	C-8	27000	4.72/119.9	0.44/11.0	300
FCZ	03160	500	120	T-3	Recessed Single Contact (R7s)	C-8	10800	4.72/119.9	0.44/11.0	2000
FDB	03180	1500	120	T-4	Recessed Single Contact (R7s)	C-8	40000	6.61/167.9	0.44/11.0	400
FDF	03190	500	120	T-3	Recessed Single Contact (R7s)	C-8	13250	4.72/119.9	0.44/11.0	400
FDN	03200	500	120	T-3	Recessed Single Contact (R7s)	C-8	12500	4.72/119.9	0.44/11.0	400
FEL	03240	1000	120	T-6	G9.5	CC-8	27000	4.00/101.6	0.77/19.5	300
FEP	03250	1000	220	T-6	G9.5	CC-8	26500	4.00/101.6	0.77/19.5	150
FEY	03280	2000	120	T-8	Recessed Single Contact (R7s)	CC-8	57000	5.62/142.8	1.10/28.0	300
FFN	03320	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	11000	6.03/153.1	8.35/212.0	800
FFP	03330	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	12000	6.03/153.1	8.35/212.0	800
FFR	03340	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	14000	6.03/153.1	8.35/212.0	800
FFS	03350	1000	120	PAR 64	Mogul End Prong (GX16d)	CC-6	19000	6.03/153.1	8.35/212.0	800
FFT	03360	1000	120	T-3 1/4	Recessed Single Contact (R7s)	C-8	26400	6.61/167.9	0.44/11.0	300
FHM	03400	1000	120	T-3	Recessed Single Contact (R7s)	C-8	26000	4.72/119.9	0.44/11.0	300
FKW	03455	300	120	T-6	GY9.5	C-13	7800	3.54/90.0	0.75/19.1	200
FLK	03475	575	120	T-6	G9.5	CC-8	16500	3.97/100.8	0.75/19.1	300
FRK	15095	650	120	T-7	GY9.5	C-13	16900	3.54/90.0	0.87/22.0	200
FTK	15097	500	120	T-6	GY9.5	CC-6	13500	2.57/65.3	0.75/19.1	200
GDA	03507	500	120	T-4	Recessed Single Contact (R7s)	C-8	11000	5.25/133.3	0.48/12.0	100
GLA	10418	575	115	T-7	G9.5	C-13D	13000	4.00/101.6	0.87/22.0	1500
GLC	10419	575	115	T-7	G9.5	C-13D	15500	4.00/101.6	0.87/22.0	400

ArcMaster SSTV Discharge Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Lumens	MOL	MOD	Life Hours
ESD200-SE-D	04005	200	70	GY9.5	13700	4.25/108	0.91/23	2000
ESD250-SE-D	04006	250	95	GY9.5	18800	4.25/108	0.91/23	2000
ESD250/2-SE-D8.5	04008	250	95	GY9.5	18000	4.25/108	0.91/23	2000
ESD575-SE-D	04007	575	95	GX9.5	49000	4.92/125	1.18/30	2000
ESD575/2-SE-D7.2	04009	575	95	GX9.5	45000	4.92/125	1.18/30	1000
ESD575/2-SE-D8.5	04010	575	95	GX9.5	44000	4.92/125	1.18/30	1000
ESI575-DE	04017	575	95	SFc 10-4	49000	5.35/136	0.83/21	750
ESI1200-DE	04018	1200	100	SFc 15.5-6	110000	8.66/220	1.1/28	750
ESI1200-DE-S	04019	1200	100	SFa 10-4	95000	5.35/136	0.83/21	750
ESI2500-DE	04020	2500	115	SFa 21-12	240000	13.98/355	1.26/32	500
ESI4000-DE	04021	4000	200	SFa 21-12	380000	15.94/405	1.57/40	500
ESI6000-DE	04022	6000	123	S25.5x60	570000	17.72/450	2.05/52	350
ESI12000-DE	04023	12000	160	S30x70	1100000	18.5/470	2.56/65	500
ESR200-SE-HR	04011	200	70	GZY9.5	15000	3.15/80	0.79/20	200
ESR400-SE-HR	04012	400	67	GZZ9.5	33000	4.33/110	0.91/23	650
ESR400-SE-NHR	04000	400	67	GX9.5	33000	4.41/112	0.91/23	650
ESR575-SE-HR	04013	575	95	Medium Bi-Post (G22)	49000	5.71/145	1.18/30	750
ESR575-SE-NHR	04001	575	95	GX9.5	49000	4.92/125	1.18/30	750
ESR800-SE-HR	04014	800	95	Medium Bi-Post (G22)	64000	5.71/145	1.22/31	1000
ESR1200-SE-HR	04015	1200	100	Mogul Bi-Pin Post (G38)	110000	7.87/200	1.57/40	750
ESR1200-SE-NHR	04003	1200	100	Medium Bi-Post (G22)	110000	6.89/175	1.57/40	750
ESR2500-SE-HR	04016	2500	115	Mogul Bi-Pin Post (G38)	240000	9.45/240	2.36/60	500

ColorMaster Digital Imaging Lamps



Ordering Code	Bar Code	Watts	Volts	Shape	Base	MOL	MOD	Life Hours
SP30/955K	48045	30	120	T-4	Medium Screw (E26)	6.3/160	2.76/70	10000
SP50/955K	05622	50	120	T-4	Medium Screw (E26)	9.06/230	2.80/71	10000

Germicidal Lamps



Ordering Code	Bar Code	Shape	Base	MOL	Special Desc	UV Output Watts	Life Hours
G4T5	41300	T-5	G5	5.3/134.5	Germicidal (254nm), Preheat, Ozoneless	0.8	6000
G6T5	41302	T-5	G5	8.3/210.5	Germicidal (254nm), Preheat, Ozoneless	1.7	6000
G8T5	41384	T-5	G5	11.3/287.0	Germicidal (254nm), Preheat, Ozoneless	2.5	6000
G10T5/4P	00216	T-5	4 Pin	14/357	Germicidal (254nm), Preheat, Ozoneless	5.3	9000
G10T5L	00205	T-5	Single Pin 7.9mm	14/357	Germicidal (254nm), Preheat, Ozoneless	5.3	9000
G10T8	41386	T-8	G13	13/330	Germicidal (254nm), Preheat, Ozoneless	2.7	6000
G11T5	00217	T-5	G5	8.3/210.5	Germicidal (254nm), Preheat, Ozoneless	2.2	8000
G14T5/4P	00219	T-5	4 Pin	11.3/287	Germicidal (254nm), Preheat, Ozoneless	3	8000
G15T8	41388	T-8	G13	17.2/436	Germicidal (254nm), Preheat, Ozoneless	4.9	8000
G16T5	00221	T-5	G5	11.3/287	Germicidal (254nm), Preheat, Ozoneless	3.2	8000
G20T5	00222	T-5	G5	15.8/400	Germicidal (254nm), Preheat, Ozoneless	5.5	8000
G20T10	00202	T-10	G13	23.2/588.5	Germicidal (254nm), Preheat, Ozoneless	7.5	8000
G25T8	00203	T-8	G13	17.2/436	Germicidal (254nm), Preheat, Ozoneless	6.9	8000
G30T8	00204	T-8	G13	35.2/893	Germicidal (254nm), Preheat, Ozoneless	13.4	8000
G36T5/4P	00223	T-5	4 Pin	33.2/842	Germicidal (254nm), Preheat, Ozoneless	12	9000
G36T5L	00206	T-5	Single Pin 7.9mm	33.2/842	Germicidal (254nm), Preheat, Ozoneless	12	9000
G40T10	00214	T-10	G13	47.2/1198	Germicidal (254nm), Preheat, Ozoneless	19.8	8000
G55T8	00224	T-8	G13	35.2/893	Germicidal (254nm), Preheat, Ozoneless	18	8000
G64T5/4P	00225	T-5	4 Pin	61.2/1554	Germicidal (254nm), Preheat, Ozoneless	25	9000
G64T5L	00207	T-5	Single Pin 7.9mm	61.2/1554	Germicidal (254nm), Preheat, Ozoneless	25	9000
GTL-2	02449	T-6	Intermediate Screw (E17)	2.2/55	Germicidal (254nm), Preheat, Ozoneless	0.12	2000
GTL-3	41568	T-6	Intermediate Screw (E17)	2.5/63	Germicidal (254nm), Preheat, Ozoneless	0.18	2000

Healthcare, Medical & Scientific Lamps

Healthcare, Medical & Scientific Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
10S11N	41528	10	120	S-11	Intermediate Screw (E17)	C-5A	80	2.31/58.7	1.36/34.4	1500
10S11NF	41530	10	120	S-11	Intermediate Screw (E17)	C-7A	79	2.31/58.7	1.36/34.4	1500
15S11-13	41516	15	120	S-11	Candelabra Screw (E12)	C-7A	137	2.28/58	1.38/35	750
15S11-14	41514	15	120	S-11	Candelabra Screw (E12)	C-7A	150	2.28/58	1.38/35	200
15S11-87	41532	15	120	S-11	Intermediate Screw (E17)	C-7A		2.28/58	1.38/35	750
15S11-F	41512	15	120	S-11	Candelabra Screw (E12)	C-7A	137	2.28/58	1.38/35	250
15S11/102CL	41099	15	120	S-11	Medium Screw (E26)	C-5	150	2.20/56.0	1.38/35.0	500
15S11/102IF	04411	15	120	S-11	Medium Screw (E26)	C-5		2.20/56.0	1.38/35.0	500
25S11-2C	41520	25	120	S-11	Candelabra Screw (E12)	C-7A	200	2.28/58	1.38/35	500
25S11-5C	41518	25	120	S-11	Candelabra Screw (E12)	C-7A	190	2.28/58	1.38/35	500
80-A	41508	7	60	T-4	4 Pin		40	1.32/33.5	3.23/82	3000
80-B	41510	7	60	T-4	4 Pin		40	4.09/104	3.23/82	3000
150P25/10	81118	150	120	P-25	Medium Screw (E26)	C-7A	2100	4.75/120.7	3.13/79.4	200
778	41400	20	6	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	400	1.05/26.7	0.38/9.6	100
787	41402	10	6	T-2 1/4	G4 (Sub-Miniature 2-Pin)	C-6	16	1.00/25.4	0.30/7.6	100
788	41404	20	6	T-2 1/4	G4 (Sub-Miniature 2-Pin)	C-6	32	1.00/25.4	0.30/7.6	100
789	41406	14	12	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	22	1.05/26.7	0.38/9.6	200
1096	40401	27	6	S-8	DC Prefocus S (P30d)	C-2R	30	2.00/50.8	1.04/26.4	500
1096X	40403	27	6	S-8	DC Prefocus S (P30d)	C-2R	375	2.00/50.8	1.04/26.4	500
1460	40279	18	6.5	S-8	DC Prefocus S (P30d)	C-6	289	2.00/50.8	1.04/26.4	100
1460X	40281	18	6.5	S-8	DC Prefocus S (P30d)	C-6	289	2.00/50.8	1.04/26.4	100
1468X	40405	27	6	S-8	DC Prefocus S (P30d)	C-2R	375	2.00/50.8	1.04/26.4	500
1489	40407	18	6.5	T-5	SC Bayonet (BA15s)	C-6U	300	1.75/44.5	0.65/16.5	125
1507	40294	37.5	12.5	RP-11	Single Contact Prefocus Flanged (P15s30)	C-2V	625	2.2/56	1.42/36	300

Healthcare, Medical & Scientific Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
1630	40311	18	6.5	S-8	DC Prefocus S (P30d)	C-6	289	2.00/50.8	1.04/26.4	100
1631X	40312	18	6.5	S-8	DC Prefocus S (P30d)	C-6	289	2.00/50.8	1.04/26.4	100
1634	40313	20	20	S-8	DC Prefocus S (P30d)	CC-6	302	2.00/50.8	1.04/26.4	200
1649	40705	18	6.5	S-8	DC Prefocus S (P30d)	FC-6Z	23	2.00/50.8	1.04/26.4	100
01800	41412	1.125	2.5	T-2 1/2	Thread	CC-6		0.98/25.0	0.34/8.7	
02500	41210		6	G-6	Miniature Screw (E10)	C-2R	8.1	1.20/30.5	0.75/19	50
03000	41216	2.5	3.5	T-1 1/2	Flange		2.7	0.88/22.3	0.25/6.35	15
03100	41218	2.5	3.5	TL-1 1/2	48 Grooves/Inch	C-2R		0.75/19.1	0.19/4.8	20
03600	41224		2.5	TL-2	Miniature Screw (E10)	C-2R	600	0.95/24.1	1.38/35	2000
03900	41228		2.5							
04100	41230	33	14.5	TL-3 1/2	Thread	CC-6		1.35/34.3	0.37/9.5	100
04200	41232	35	12	MR16	GX5.3	CC-6		1.75/44.5	2.01/51	50
04900	41240	2.5	3.5	TL-1 1/2	Flange	C-2R		0.90/22.9	0.31/7.9	20
06300	41248	20	12	T-3	G4 (Sub-Miniature 2-Pin)	C-6			0.51/13	2000
06500	07352	2.73	3.5	TL-1 1/2					0.19/4.75	15
07600	41252		2.5	TL-2	Thread	C-6		0.90/22.9		
07800	41254	4.26	6	TL-1 1/2	Thread	C-6		1.12/28.4	0.19/4.8	75
8001	41084	26.1	6	S-35mm	European Screw (E14)	C-6	410	2.56/65.0	1.38/35.0	100
8013	41085	10	6	G-25mm	DC Bayonet (BA15d)	C-6	150	1.81/46.0	0.99/25.0	200
8014	41086	10	6	G-25mm	SC Bayonet (BA15s)	C-6	100	1.81/46.0	0.99/25.0	600
8017	41087	15	6	T-19mm	DC Bayonet (BA15d)	C BAR 6	145	2.12/54.0	0.75/19.1	1000
8018	41088	15	6	T-19mm	DC Bayonet (BA15d)	C BAR 6	210	2.05/52.0	0.75/19.1	100
8022	41090	50	12	S-35mm	DC Bayonet European (BA20d)	CC-6	1000	2.71/69.0	1.38/35.0	50
8100	41089	30	6	S-35mm	European Screw (E14)	C-6	260	2.56/65.0	1.38/35.0	600
08200	41258		3.5	TL-2	Flange	C-6		0.80/20.3	0.22/5.5	
11143	41540	20	6	T-2 1/2	G4 (Sub-Miniature 2-Pin)	C-6	570	1.1/28	0.35/9	2000
16073	16073	80	12	MR11	G5.3-4.8	CC-8		1.46/37.0	1.41/35.8	50
41304	41304	15	120	S-11	Intermediate Screw (E17)	C-5	100	2.36/60	1.38/35	600
41306	41306	30	6	T-8	DC Bayonet (BA15d)	C-6Z	230	2.2/56	1/25	200
41308	41308	15	6	T-6	DC Prefocus w/ Triangle Flange (P25d)	C-6Z	130	2.13/54	0.75/19	100
41310	41310	15	6	G-6	DC Bayonet (BA15d)	C-8Z	130	1.46/37	0.75/19	100
41312	41312	35	7	S-8	DC Bayonet (BA15d)	C-8Z	460	2/50	1/25	100
41314	41314	2.4	6	G-4 1/2	Miniature Screw (E10)	C-2R	12	1.1/28	0.57/14.5	200
41316	41316	15	6	G-8	SC Bayonet (BA15s)	C-6	130	1.69/43	1/25	150
41318	41318	27	6	G-12 1/2	E14 w/ Special Flange (P44s)	C-6	360	2.64/67	1.57/40	100
41320	41320	3	6	G-3 1/2	Miniature Screw (E10)	C-2R	15	0.94/24	0.43/11	300
41324	41324	5	6	G-6	DC Bayonet (BA15d)	C-2R	70	1.38/35	0.75/19	600
41326	41326	33	6	S-8	SC Bayonet Prefocus w/ Triangle Flange	C-8Z	430	2/50	1/25	80
41328	41328	27	6	S-11	E14 w/ Special Prefocus Flange	C-6U	300	2.64/67	1.38/35	100
41332	41332	35	7	S-8	DC Prefocus S (P30d)	C-8Z	460	2/50	1/25	100
41334	41334	30	12	T-3 1/4	G6.35	C-6	570	1.73/44	0.43/11	1000
41336	41336	1.5	3	T-2 1/2	9 x 17 (M5 x 0.75)	S-2F	18	1.02/26	0.31/8	10
41338	41338	1.2	6	T-1 1/2	5.5 x 15 (M4.5 x 0.5)	C-2R	9	1/25	0.2/5	500
41340	41340	27	6	S-11	E14 w/ Special Flange (P44s)	C-6	360	2.52/64	1.38/35	100
41344	41344	25	6	T-7	DC Bayonet European w/ Special Flange (BA20d/26)	C-8	330	2.36/60	0.88/22	100
41346	41346	25	120	S-11	Intermediate Screw (E17)	C-5	150	2.32/59	1.38/35	600
41348	41348	15	120	G-11	Medium Screw (E26)	C-5	100	2.2/56	1.38/35	600
41350	41350	15	120	G-11	Medium Screw (E26)	C-10	100	2.2/56	1.38/35	600
41352	41352	0.95	2.5	T-1 1/4	Special Screw	C-2R	10	0.59/15.0	0.24/6	10
41354	41354	1.08	2.7	T-2 1/2	Special Screw	S-2F	11	0.79/20	0.28/7	20
41358	41358	50.4	12	T-3 1/4	E14 w/ Special Flange (P44s)	C BAR 6	1400	2.6/66		30
41360	41360	15	110	G-11	Medium Screw (E26)	C-5	150	2.2/56	1.38/35	500
41362	41362	50	120	T-8	DC Bayonet (BA15d)	CC-13	775	3.13/79.4	1.00/25.4	50
41364	41364	10	6	T-2 1/2	Special Base	C-6	200	1.06/27	0.31/8	100
41366	41366	33	6	T-8	DC w/ Special Flange	C-8Z	430	3/75	1/25	80
41368	41368	20	6	T-2 1/2	Sub-Miniature 2-Pin w/ Special Flange (G4)	C-6	475	1.22/31	0.35/9	100
41374	41374	3.6	4	T-2 1/2	Special Base	S-2F	45	1.02/26	0.31/8	10
41376	41376	60	12.5	G-11	Single Contact Prefocus Flanged (P15s30)	C BAR 6	1300	2.2/56	1.38/35	25
41382	41382	25	6	T-8	Single Contact Prefocus Flanged (P15s30)	C-8	450	3.11/79	1/25	50
64260	41546	30	12	T-3	Prefocus Flanged (PG22d-b)	C BAR 6	800	1.57/40	0.35/9	50
71818	41095	70	10	G-50mm	Medium Prefocus Flanged Single Contact (P28s)	C BAR 6	1100	3.31/84.1	1.97/50.0	100
76907	41092	15	6	G-19mm	DC Bayonet (BA15d)	C BAR 6	150	1.40/35.6	0.75/19.1	100
77903	41100	15	6	T-19mm	DC Prefocus (P15d30)	C BAR 6	130	2.16/55.0	0.75/19	200
77904	41093	30	6	T-25	DC Bayonet (BA15d)	C BAR 6	250	2.16/55.0	0.99/25.0	200
77910	41094	18	6	G-18mm	DC Bayonet w/ Triangle Flange (P25d)	C BAR 6	180	1.40/35.6	0.75/19.1	50
56016164	41432	25	24	G-13	DC Bayonet (BA15d)	C-6		2.52/64.0	1.57/40	700
56018366	41550	75	22.8	T-3 1/2	Recessed Single Contact (R7s)	CC-8	1400	2.50/63.4	0.43/11	800
56018550	41434	40	24	G-13	DC Bayonet (BA15d)	CC-8		2.56/65.0		700
56018566	41552	50	22.8	T-3 1/2	G6.35	CC-6	1000	1.73/44.0		1000
56018769	41554	40	22.8	T-3 1/2	G6.35	CC-6	760	1.73/44.0	0.43/11	1000
A1-010-28	41556	40	24	T-4	Miniature Candelabra Screw (E11)	CC-6	720	2.36/60.0	0.51/13	600
A1-420-10	41558	60	24	T-4	Miniature Screw (E10)	CC-6	1100	2.36/60.0	0.51/13	800
A1-510-01	41560	50	24	T-4	Miniature Candelabra Screw (E11)	CC-6	800	2.36/60.0	0.51/13	800

Healthcare, Medical & Scientific Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
B1-010-28	41390	50	24	T-4 1/2	G8	C BAR 6	1100	2.20/56.0	0.51/13	100
B5-011-32	41562	100	24	T-4 1/2	G8	C BAR 6	2700	2.20/56.0	0.51/13	100
BFM	10012	25	120	T-8	European Screw (E14)	C-5	300	2.16/55.0	1.03/26.0	500
BZW	00602	50	120	T-8	SC Bayonet (BA15s)	CC-2V	850	3.13/79.4	0.99/25.0	50
CAX	00780	50	120	T-8	DC Bayonet (BA15d)	CC-13	775	3.13/79.4	1.00/25.4	50
CAX-130V	00790	50	130	T-8	DC Bayonet (BA15d)	CC-13	775	3.13/79.4	1.00/25.4	50
CAX-130V-HAL	06312	50	130	T-4	DC Bayonet (BA15d)	C-2V	800	2.36/60	0.53/13.5	500
CDD	00730	100	120	T-8	SC Bayonet (BA15s)	CC-2V	2000	3.13/79.4	1.00/25.4	50
EI-77Z	41091	15	6	T-6	DC w/ Special Flange	C BAR 6	130	2.05/52.0	0.75/19.1	100
EI-722	41079	30	120	S-9 1/2	DC Bayonet (BA15d)	C-5	250	2.08/53.0	1.18/30.0	500
EI-737	41080	18	6	S-9 1/2	DC Bayonet (BA15d)	C-6	176	2.08/53.0	1.18/30.0	100
EI-738	41081	30	6	T-25	DC Bayonet (BA15d)	C BAR 6	250	2.16/55.0	0.99/25.0	100
EI-886	41083	20	120	G-9 1/2	DC Bayonet (BA15d)	CC-7A	150	2.08/53.0	1.18/30.0	400
EI-2201	41082	20	115	S-9 1/2	DC Bayonet (BA15d)	C-5	150	2.08/53.0	1.18/30.0	500
EI-74000	41394	120	24	T-4 1/2	X514	CC-6	3000	1.81/46.0		200
EI-B153	41096	20	120	S-11	DC Bayonet (BA15d)	CC-2V	150	2.36/60.0	1.38/35.0	300
EI-M102	41097	6 - 12	3 - 6	G-6	SC Bayonet (BA15s)	C BAR 6	125	1.40/35.6	0.75/19.1	100
EI-M103	41098	12 - 18	6 - 9	G-6	SC Bayonet (BA15s)	C BAR 6	200	1.40/35.6	0.75/19.1	100
EJY	10272	80	19	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25
EL-1B	41075	54	13.5	S-7 3/4	SC Bayonet (BA15s)	C BAR 6	1000	1.97/50.0	0.99/25.0	100
EL-2B	41076	12	8	G-5 1/2	Miniature Bayonet (BA9s)	C-2R	160	1.25/32.0	0.71/18.0	100
EL-3B	41077	12	8	G-5 1/2	Miniature Bayonet (BA9s)	C-2R	160	1.25/32.0	0.71/18.0	100
EL-12B	41078	15	6	G-5 1/2	Miniature Bayonet (BA9s)	C BAR 6	180	1.25/32.0	0.71/18.0	100
EL-38	49680	15	8	G-5 1/2	Miniature Bayonet (BA9s)	C BAR 6	140	1.25/32.0	0.71/18.0	200
ESA/FHD	10329	10	6	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	200	1.18/30.0	0.36/9.0	100
ESB/FHE	10330	20	6	T-2 3/4	G4 (Sub-Miniature 2-Pin)	C-6	450	1.18/30.0	0.36/9.0	100
EVA	10348	100	12	T-3 1/2	GY6.35	C BAR 6	2400	1.73/44.0	0.46/11.5	1000
EVB/BRJ	10349	150	15	T-3 1/2	G6.35	C BAR 6	5000	1.73/44.0	0.46/11.5	50
FCR	10403	100	12	T-3 1/2	GY6.35	C BAR 6	2900	1.73/44.0	0.46/11.5	50
FCS	10404	150	24	T-4	G6.35	C BAR 6	4500	1.97/50.0	0.53/13.5	50
GTL-3	41568	3	10.5	T-6	Intermediate Screw (E17)			2.5/63	0.79/20	2000
P129362-228	41564	220	22.8	T-4	GY9.5	CC-6	4300	2.44/62.0	0.51/13	500
Q235T4/3-33V	41392	235	33	T-4	GY9.5	CC-6	5000	2.44/62.0	0.51/13	500

LitespanLED® Fixtures

Flood Light Fixture

30W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-30W-40K-N31-BL-N-N	93081	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-40K-N31-BL-P-N	93082	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-40K-N31-BR-N-N	93083	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-40K-N31-BR-P-N	93084	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-40K-N31-S-N-N	93085	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-40K-N31-S-P-N	93086	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-40K-N31-W-N-N	93087	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-40K-N31-W-P-N	93088	30	120-277 VAC	2970	-40C - 55C
C0820-FL-30W-50K-N31-BL-N-N	93089	30	120-277 VAC	3150	-40C - 55C
C0820-FL-30W-50K-N31-BL-P-N	93090	30	120-277 VAC	3150	-40C - 55C
C0820-FL-30W-50K-N31-BR-N-N	93091	30	120-277 VAC	3150	-40C - 55C
C0820-FL-30W-50K-N31-BR-P-N	93092	30	120-277 VAC	3150	-40C - 55C
C0820-FL-30W-50K-N31-S-N-N	93093	30	120-277 VAC	3150	-40C - 55C
C0820-FL-30W-50K-N31-S-P-N	93094	30	120-277 VAC	3150	-40C - 55C
C0820-FL-30W-50K-N31-W-N-N	93095	30	120-277 VAC	3150	-40C - 55C
C0820-FL-30W-50K-N31-W-P-N	93096	30	120-277 VAC	3150	-40C - 55C

50W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-50W-40K-N31-BL-N-N	93097	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-40K-N31-BL-P-N	93098	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-40K-N31-BR-N-N	93099	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-40K-N31-BR-P-N	93100	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-40K-N31-S-N-N	93101	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-40K-N31-S-P-N	93102	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-40K-N31-W-N-N	93103	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-40K-N31-W-P-N	93104	50	120-277 VAC	4950	-40C - 55C
C0820-FL-50W-50K-N31-BL-N-N	93105	50	120-277 VAC	5250	-40C - 55C
C0820-FL-50W-50K-N31-BL-P-N	93106	50	120-277 VAC	5250	-40C - 55C
C0820-FL-50W-50K-N31-BR-N-N	93107	50	120-277 VAC	5250	-40C - 55C
C0820-FL-50W-50K-N31-BR-P-N	93108	50	120-277 VAC	5250	-40C - 55C
C0820-FL-50W-50K-N31-S-N-N	93109	50	120-277 VAC	5250	-40C - 55C
C0820-FL-50W-50K-N31-S-P-N	93110	50	120-277 VAC	5250	-40C - 55C
C0820-FL-50W-50K-N31-W-N-N	93111	50	120-277 VAC	5250	-40C - 55C

Flood Light Fixture

50W Flood Light Fixture

Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-50W-50K-N31-W-P-N	93112	50	120-277 VAC	5250	-40C - 55C

80W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-80W-40K-N31-BL-N-N	93113	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-40K-N31-BL-P-N	93114	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-40K-N31-BR-N-N	93115	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-40K-N31-BR-P-N	93116	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-40K-N31-S-N-N	93117	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-40K-N31-S-P-N	93118	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-40K-N31-W-N-N	93119	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-40K-N31-W-P-N	93120	80	120-277 VAC	7920	-40C - 55C
C0820-FL-80W-50K-N31-BL-N-N	93121	80	120-277 VAC	8400	-40C - 55C
C0820-FL-80W-50K-N31-BL-P-N	93122	80	120-277 VAC	8400	-40C - 55C
C0820-FL-80W-50K-N31-BR-N-N	93123	80	120-277 VAC	8400	-40C - 55C
C0820-FL-80W-50K-N31-BR-P-N	93124	80	120-277 VAC	8400	-40C - 55C
C0820-FL-80W-50K-N31-S-N-N	93125	80	120-277 VAC	8400	-40C - 55C
C0820-FL-80W-50K-N31-S-P-N	93126	80	120-277 VAC	8400	-40C - 55C
C0820-FL-80W-50K-N31-W-N-N	93127	80	120-277 VAC	8400	-40C - 55C
C0820-FL-80W-50K-N31-W-P-N	93128	80	120-277 VAC	8400	-40C - 55C

100W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-100W-40K-N31-BL-N-N	93001	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-40K-N31-BL-P-N	93002	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-40K-N31-BR-N-N	93003	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-40K-N31-BR-P-N	93004	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-40K-N31-S-N-N	93005	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-40K-N31-S-P-N	93006	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-40K-N31-W-N-N	93007	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-40K-N31-W-P-N	93008	100	120-277 VAC	9900	-40C - 55C
C0820-FL-100W-50K-N31-BL-N-N	93009	100	120-277 VAC	10500	-40C - 55C
C0820-FL-100W-50K-N31-BL-P-N	93010	100	120-277 VAC	10500	-40C - 55C
C0820-FL-100W-50K-N31-BR-N-N	93011	100	120-277 VAC	10500	-40C - 55C
C0820-FL-100W-50K-N31-BR-P-N	93012	100	120-277 VAC	10500	-40C - 55C
C0820-FL-100W-50K-N31-S-N-N	93013	100	120-277 VAC	10500	-40C - 55C
C0820-FL-100W-50K-N31-S-P-N	93014	100	120-277 VAC	10500	-40C - 55C
C0820-FL-100W-50K-N31-W-N-N	93015	100	120-277 VAC	10500	-40C - 55C
C0820-FL-100W-50K-N31-W-P-N	93016	100	120-277 VAC	10500	-40C - 55C

120W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-120W-40K-N31-BL-N-N	93017	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-40K-N31-BL-P-N	93018	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-40K-N31-BR-N-N	93019	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-40K-N31-BR-P-N	93020	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-40K-N31-S-N-N	93021	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-40K-N31-S-P-N	93022	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-40K-N31-W-N-N	93023	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-40K-N31-W-P-N	93024	120	120-277 VAC	11340	-40C - 55C
C0820-FL-120W-50K-N31-BL-N-N	93025	120	120-277 VAC	12600	-40C - 55C
C0820-FL-120W-50K-N31-BL-P-N	93026	120	120-277 VAC	12600	-40C - 55C
C0820-FL-120W-50K-N31-BR-N-N	93027	120	120-277 VAC	12600	-40C - 55C
C0820-FL-120W-50K-N31-BR-P-N	93028	120	120-277 VAC	12600	-40C - 55C
C0820-FL-120W-50K-N31-S-N-N	93029	120	120-277 VAC	12600	-40C - 55C
C0820-FL-120W-50K-N31-S-P-N	93030	120	120-277 VAC	12600	-40C - 55C
C0820-FL-120W-50K-N31-W-N-N	93031	120	120-277 VAC	12600	-40C - 55C
C0820-FL-120W-50K-N31-W-P-N	93032	120	120-277 VAC	12600	-40C - 55C

160W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-160W-40K-N31-BL-N-N	93033	160	120-277 VAC	15840	-40C - 55C
C0820-FL-160W-40K-N31-BL-P-N	93034	160	120-277 VAC	15840	-40C - 55C
C0820-FL-160W-40K-N31-BR-N-N	93035	160	120-277 VAC	15840	-40C - 55C
C0820-FL-160W-40K-N31-BR-P-N	93036	160	120-277 VAC	15840	-40C - 55C
C0820-FL-160W-40K-N31-S-N-N	93037	160	120-277 VAC	15840	-40C - 55C

Flood Light Fixture

160W Flood Light Fixture

Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-160W-40K-N31-S-P-N	93038	160	120-277 VAC	15840	-40C - 55C
C0820-FL-160W-40K-N31-W-N-N	93039	160	120-277 VAC	15840	-40C - 55C
C0820-FL-160W-40K-N31-W-P-N	93040	160	120-277 VAC	15840	-40C - 55C
C0820-FL-160W-50K-N31-BL-N-N	93041	160	120-277 VAC	16800	-40C - 55C
C0820-FL-160W-50K-N31-BL-P-N	93042	160	120-277 VAC	16800	-40C - 55C
C0820-FL-160W-50K-N31-BR-N-N	93043	160	120-277 VAC	16800	-40C - 55C
C0820-FL-160W-50K-N31-BR-P-N	93044	160	120-277 VAC	16800	-40C - 55C
C0820-FL-160W-50K-N31-S-N-N	93045	160	120-277 VAC	16800	-40C - 55C
C0820-FL-160W-50K-N31-S-P-N	93046	160	120-277 VAC	16800	-40C - 55C
C0820-FL-160W-50K-N31-W-N-N	93047	160	120-277 VAC	16800	-40C - 55C
C0820-FL-160W-50K-N31-W-P-N	93048	160	120-277 VAC	16800	-40C - 55C

200W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-200W-40K-N31-BL-N-N	93049	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-40K-N31-BL-P-N	93050	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-40K-N31-BR-N-N	93051	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-40K-N31-BR-P-N	93052	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-40K-N31-S-N-N	93053	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-40K-N31-S-P-N	93054	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-40K-N31-W-N-N	93055	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-40K-N31-W-P-N	93056	200	120-277 VAC	16193	-40C - 55C
C0820-FL-200W-50K-N31-BL-N-N	93057	200	120-277 VAC	21000	-40C - 55C
C0820-FL-200W-50K-N31-BL-P-N	93058	200	120-277 VAC	21000	-40C - 55C
C0820-FL-200W-50K-N31-BR-N-N	93059	200	120-277 VAC	21000	-40C - 55C
C0820-FL-200W-50K-N31-BR-P-N	93060	200	120-277 VAC	21000	-40C - 55C
C0820-FL-200W-50K-N31-S-N-N	93061	200	120-277 VAC	21000	-40C - 55C
C0820-FL-200W-50K-N31-S-P-N	93062	200	120-277 VAC	21000	-40C - 55C
C0820-FL-200W-50K-N31-W-N-N	93063	200	120-277 VAC	21000	-40C - 55C
C0820-FL-200W-50K-N31-W-P-N	93064	200	120-277 VAC	21000	-40C - 55C

240W Flood Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-FL-240W-40K-N31-BL-N-N	93065	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-40K-N31-BL-P-N	93066	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-40K-N31-BR-N-N	93067	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-40K-N31-BR-P-N	93068	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-40K-N31-S-N-N	93069	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-40K-N31-S-P-N	93070	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-40K-N31-W-N-N	93071	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-40K-N31-W-P-N	93072	240	120-277 VAC	22680	-40C - 55C
C0820-FL-240W-50K-N31-BL-N-N	93073	240	120-277 VAC	25200	-40C - 55C
C0820-FL-240W-50K-N31-BL-P-N	93074	240	120-277 VAC	25200	-40C - 55C
C0820-FL-240W-50K-N31-BR-N-N	93075	240	120-277 VAC	25200	-40C - 55C
C0820-FL-240W-50K-N31-BR-P-N	93076	240	120-277 VAC	25200	-40C - 55C
C0820-FL-240W-50K-N31-S-N-N	93077	240	120-277 VAC	25200	-40C - 55C
C0820-FL-240W-50K-N31-S-P-N	93078	240	120-277 VAC	25200	-40C - 55C
C0820-FL-240W-50K-N31-W-N-N	93079	240	120-277 VAC	25200	-40C - 55C
C0820-FL-240W-50K-N31-W-P-N	93080	240	120-277 VAC	25200	-40C - 55C

High Bay Fixture

120W High Bay Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HB-120W-40K-N39-BR-N-N	93129	120	120-277 VAC	10170	-40C - 55C
C0820-HB-120W-40K-N39-S-N-N	93130	120	120-277 VAC	10170	-40C - 55C
C0820-HB-120W-40K-N39-W-N-N	93131	120	120-277 VAC	10170	-40C - 55C
C0820-HB-120W-40K-N40-BR-N-N	93132	120	120-277 VAC	10162	-40C - 55C
C0820-HB-120W-40K-N40-S-N-N	93133	120	120-277 VAC	10162	-40C - 55C
C0820-HB-120W-40K-N40-W-N-N	93134	120	120-277 VAC	10162	-40C - 55C
C0820-HB-120W-50K-N39-BR-N-N	93135	120	120-277 VAC	10936	-40C - 55C
C0820-HB-120W-50K-N39-S-N-N	93136	120	120-277 VAC	10936	-40C - 55C
C0820-HB-120W-50K-N39-W-N-N	93137	120	120-277 VAC	10936	-40C - 55C
C0820-HB-120W-50K-N40-BR-N-N	93138	120	120-277 VAC	10927	-40C - 55C
C0820-HB-120W-50K-N40-S-N-N	93139	120	120-277 VAC	10927	-40C - 55C
C0820-HB-120W-50K-N40-W-N-N	93140	120	120-277 VAC	10927	-40C - 55C

LitespanLED® Fixtures

High Bay Fixture

90W High Bay Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HB-90W-40K-N39-BR-N-N	93189	90	120-277 VAC	7882	-40C - 55C
C0820-HB-90W-40K-N39-S-N-N	93190	90	120-277 VAC	7882	-40C - 55C
C0820-HB-90W-40K-N39-W-N-N	93191	90	120-277 VAC	7882	-40C - 55C
C0820-HB-90W-40K-N40-BR-N-N	93192	90	120-277 VAC	7872	-40C - 55C
C0820-HB-90W-40K-N40-S-N-N	93193	90	120-277 VAC	7872	-40C - 55C
C0820-HB-90W-40K-N40-W-N-N	93194	90	120-277 VAC	7872	-40C - 55C
C0820-HB-90W-50K-N39-BR-N-N	93195	90	120-277 VAC	8475	-40C - 55C
C0820-HB-90W-50K-N39-S-N-N	93196	90	120-277 VAC	8475	-40C - 55C
C0820-HB-90W-50K-N39-W-N-N	93197	90	120-277 VAC	8475	-40C - 55C
C0820-HB-90W-50K-N40-BR-N-N	93198	90	120-277 VAC	8464	-40C - 55C
C0820-HB-90W-50K-N40-S-N-N	93199	90	120-277 VAC	8464	-40C - 55C
C0820-HB-90W-50K-N40-W-N-N	93200	90	120-277 VAC	8464	-40C - 55C

130W High Bay Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HB-130W-40K-N39-BR-N-N	93141	130	120-277 VAC	12870	-40C - 55C
C0820-HB-130W-40K-N39-S-N-N	93142	130	120-277 VAC	12870	-40C - 55C
C0820-HB-130W-40K-N39-W-N-N	93143	130	120-277 VAC	12870	-40C - 55C
C0820-HB-130W-40K-N40-BR-N-N	93144	130	120-277 VAC	12870	-40C - 55C
C0820-HB-130W-40K-N40-S-N-N	93145	130	120-277 VAC	12870	-40C - 55C
C0820-HB-130W-40K-N40-W-N-N	93146	130	120-277 VAC	12870	-40C - 55C
C0820-HB-130W-50K-N39-BR-N-N	93147	130	120-277 VAC	13650	-40C - 55C
C0820-HB-130W-50K-N39-S-N-N	93148	130	120-277 VAC	13650	-40C - 55C
C0820-HB-130W-50K-N39-W-N-N	93149	130	120-277 VAC	13650	-40C - 55C
C0820-HB-130W-50K-N40-BR-N-N	93150	130	120-277 VAC	13650	-40C - 55C
C0820-HB-130W-50K-N40-S-N-N	93151	130	120-277 VAC	13650	-40C - 55C
C0820-HB-130W-50K-N40-W-N-N	93152	130	120-277 VAC	13650	-40C - 55C

160W High Bay Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HB-160W-40K-N39-BR-N-N	93153	160	120-277 VAC	13484	-40C - 55C
C0820-HB-160W-40K-N39-S-N-N	93154	160	120-277 VAC	13484	-40C - 55C
C0820-HB-160W-40K-N39-W-N-N	93155	160	120-277 VAC	13484	-40C - 55C
C0820-HB-160W-40K-N40-BR-N-N	93156	160	120-277 VAC	13474	-40C - 55C
C0820-HB-160W-40K-N40-S-N-N	93157	160	120-277 VAC	13474	-40C - 55C
C0820-HB-160W-40K-N40-W-N-N	93158	160	120-277 VAC	13474	-40C - 55C
C0820-HB-160W-50K-N39-BR-N-N	93159	160	120-277 VAC	14499	-40C - 55C
C0820-HB-160W-50K-N39-S-N-N	93160	160	120-277 VAC	14499	-40C - 55C
C0820-HB-160W-50K-N39-W-N-N	93161	160	120-277 VAC	14499	-40C - 55C
C0820-HB-160W-50K-N40-BR-N-N	93162	160	120-277 VAC	14488	-40C - 55C
C0820-HB-160W-50K-N40-S-N-N	93163	160	120-277 VAC	14488	-40C - 55C
C0820-HB-160W-50K-N40-W-N-N	93164	160	120-277 VAC	14488	-40C - 55C

180W High Bay Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HB-180W-40K-N39-BR-N-N	93165	180	120-277 VAC	15887	-40C - 55C
C0820-HB-180W-40K-N39-S-N-N	93166	180	120-277 VAC	15887	-40C - 55C
C0820-HB-180W-40K-N39-W-N-N	93167	180	120-277 VAC	15887	-40C - 55C
C0820-HB-180W-40K-N40-BR-N-N	93168	180	120-277 VAC	15865	-40C - 55C
C0820-HB-180W-40K-N40-S-N-N	93169	180	120-277 VAC	15865	-40C - 55C
C0820-HB-180W-40K-N40-W-N-N	93170	180	120-277 VAC	15865	-40C - 55C
C0820-HB-180W-50K-N39-BR-N-N	93171	180	120-277 VAC	17083	-40C - 55C
C0820-HB-180W-50K-N39-S-N-N	93172	180	120-277 VAC	17083	-40C - 55C
C0820-HB-180W-50K-N39-W-N-N	93173	180	120-277 VAC	17083	-40C - 55C
C0820-HB-180W-50K-N40-BR-N-N	93174	180	120-277 VAC	17060	-40C - 55C
C0820-HB-180W-50K-N40-S-N-N	93175	180	120-277 VAC	17060	-40C - 55C
C0820-HB-180W-50K-N40-W-N-N	93176	180	120-277 VAC	17060	-40C - 55C

240W High Bay Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HB-240W-40K-N39-BR-N-N	93177	240	120-277 VAC	20400	-40C - 55C
C0820-HB-240W-40K-N39-S-N-N	93178	240	120-277 VAC	20400	-40C - 55C
C0820-HB-240W-40K-N39-W-N-N	93179	240	120-277 VAC	20400	-40C - 55C
C0820-HB-240W-40K-N40-BR-N-N	93180	240	120-277 VAC	20376	-40C - 55C
C0820-HB-240W-40K-N40-S-N-N	93181	240	120-277 VAC	20376	-40C - 55C
C0820-HB-240W-40K-N40-W-N-N	93182	240	120-277 VAC	20376	-40C - 55C

High Bay Fixture

240W High Bay Fixture

Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HB-240W-50K-N39-BR-N-N	93183	240	120-277 VAC	21935	-40C - 55C
C0820-HB-240W-50K-N39-S-N-N	93184	240	120-277 VAC	21935	-40C - 55C
C0820-HB-240W-50K-N39-W-N-N	93185	240	120-277 VAC	21935	-40C - 55C
C0820-HB-240W-50K-N40-BR-N-N	93186	240	120-277 VAC	21910	-40C - 55C
C0820-HB-240W-50K-N40-S-N-N	93187	240	120-277 VAC	21910	-40C - 55C
C0820-HB-240W-50K-N40-W-N-N	93188	240	120-277 VAC	21910	-40C - 55C

Canopy Light Fixture

HC Series - Scottsdale Design



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-HC-100W-40K-N39-W-N-N	93201	100	120-277 VAC	8856	-40C - 55C
C0820-HC-100W-50K-N39-W-N-N	93202	100	120-277 VAC	9840	-40C - 55C
C0820-HC-120W-40K-N39-W-N-N	93203	120	120-277 VAC	10628	-40C - 55C
C0820-HC-120W-50K-N39-W-N-N	93204	120	120-277 VAC	11808	-40C - 55C
C0820-HC-80W-40K-N38-W-N-N	93205	80	120-277 VAC	7083	-40C - 55C
C0820-HC-80W-40K-N39-W-N-N	93206	80	120-277 VAC	7085	-40C - 55C
C0820-HC-80W-50K-N38-W-N-N	93207	80	120-277 VAC	7870	-40C - 55C
C0820-HC-80W-50K-N39-W-N-N	93208	80	120-277 VAC	7872	-40C - 55C

RF Series - Slim Design



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-RF-100W-40K-N39-W-N-N	93251	100	120-277 VAC	8856	-40C - 55C
C0820-RF-100W-50K-N39-W-N-N	93252	100	120-277 VAC	9840	-40C - 55C
C0820-RF-120W-40K-N39-W-N-N	93253	120	120-277 VAC	10628	-40C - 55C
C0820-RF-120W-50K-N39-W-N-N	93254	120	120-277 VAC	11808	-40C - 55C
C0820-RF-80W-40K-N39-W-N-N	93255	80	120-277 VAC	7085	-40C - 55C
C0820-RF-80W-50K-N39-W-N-N	93256	80	120-277 VAC	7872	-40C - 55C

KC Series - Richmond Design



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-KC-100W-40K-N39-W-N-N	93209	100	120-277 VAC	8856	-40C - 55C
C0820-KC-100W-50K-N39-W-N-N	93210	100	120-277 VAC	9840	-40C - 55C
C0820-KC-120W-40K-N39-W-N-N	93211	120	120-277 VAC	10628	-40C - 55C
C0820-KC-120W-50K-N39-W-N-N	93212	120	120-277 VAC	11808	-40C - 55C
C0820-KC-80W-40K-N39-W-N-N	93213	80	120-277 VAC	7085	-40C - 55C
C0820-KC-80W-50K-N38-W-N-N	93214	80	120-277 VAC	7870	-40C - 55C
C0820-KC-80W-50K-N39-W-N-N	93215	80	120-277 VAC	7872	-40C - 55C

Parkade Light Fixture

40W Parkade Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-PK-40W-27K-N18-BR-N-N	93216	40	120-277 VAC	3640	-40C - 55C
C0820-PK-40W-27K-N18-S-N-N	93217	40	120-277 VAC	3640	-40C - 55C
C0820-PK-40W-27K-N18-W-N-N	93218	40	120-277 VAC	3640	-40C - 55C
C0820-PK-40W-40K-N18-BR-N-N	93219	40	120-277 VAC	3960	-40C - 55C
C0820-PK-40W-40K-N18-S-N-N	93220	40	120-277 VAC	3960	-40C - 55C
C0820-PK-40W-40K-N18-W-N-N	93221	40	120-277 VAC	3960	-40C - 55C
C0820-PK-40W-50K-N18-BR-N-N	93222	40	120-277 VAC	4200	-40C - 55C
C0820-PK-40W-50K-N18-S-N-N	93223	40	120-277 VAC	4200	-40C - 55C
C0820-PK-40W-50K-N18-W-N-N	93224	40	120-277 VAC	4200	-40C - 55C

50W Parkade Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-PK-50W-27K-N18-BR-N-N	93225	50	120-277 VAC	4550	-40C - 55C
C0820-PK-50W-27K-N18-S-N-N	93226	50	120-277 VAC	4550	-40C - 55C
C0820-PK-50W-27K-N18-W-N-N	93227	50	120-277 VAC	4550	-40C - 55C
C0820-PK-50W-40K-N18-BR-N-N	93228	50	120-277 VAC	4428	-40C - 55C
C0820-PK-50W-40K-N18-S-N-N	93229	50	120-277 VAC	4428	-40C - 55C
C0820-PK-50W-40K-N18-W-N-N	93230	50	120-277 VAC	4428	-40C - 55C
C0820-PK-50W-50K-N18-BR-N-N	93231	50	120-277 VAC	5250	-40C - 55C
C0820-PK-50W-50K-N18-S-N-N	93232	50	120-277 VAC	5250	-40C - 55C

LitespanLED® Fixtures

Parkade Light Fixture

50W Parkade Light Fixture

Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-PK-50W-50K-N18-W-N-N	93233	50	120-277 VAC	5250	-40C - 55C

80W Parkade Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-PK-80W-27K-N18-BR-N-N	93234	80	120-277 VAC	7820	-40C - 55C
C0820-PK-80W-27K-N18-S-N-N	93235	80	120-277 VAC	7820	-40C - 55C
C0820-PK-80W-27K-N18-W-N-N	93236	80	120-277 VAC	7820	-40C - 55C
C0820-PK-80W-40K-N18-BR-N-N	93237	80	120-277 VAC	7085	-40C - 55C
C0820-PK-80W-40K-N18-S-N-N	93238	80	120-277 VAC	7085	-40C - 55C
C0820-PK-80W-40K-N18-W-N-N	93239	80	120-277 VAC	7085	-40C - 55C
C0820-PK-80W-50K-N18-BR-N-N	93240	80	120-277 VAC	8400	-40C - 55C
C0820-PK-80W-50K-N18-S-N-N	93241	80	120-277 VAC	8400	-40C - 55C
C0820-PK-80W-50K-N18-W-N-N	93242	80	120-277 VAC	8400	-40C - 55C

Wallpack Light Fixture

30W Wallpack Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-WP-30W-40K-N19-BL-N-N	93273	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-40K-N19-BL-P-N	93274	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-40K-N19-BR-N-N	93275	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-40K-N19-BR-P-N	93276	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-40K-N19-S-N-N	93277	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-40K-N19-S-P-N	93278	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-40K-N19-W-N-N	93279	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-40K-N19-W-P-N	93280	30	120-277 VAC	2657	-40C - 55C
C0820-WP-30W-50K-N19-BL-N-N	93281	30	120-277 VAC	2952	-40C - 55C
C0820-WP-30W-50K-N19-BL-P-N	93282	30	120-277 VAC	2952	-40C - 55C
C0820-WP-30W-50K-N19-BR-N-N	93283	30	120-277 VAC	2952	-40C - 55C
C0820-WP-30W-50K-N19-BR-P-N	93284	30	120-277 VAC	2952	-40C - 55C
C0820-WP-30W-50K-N19-S-N-N	93285	30	120-277 VAC	2952	-40C - 55C
C0820-WP-30W-50K-N19-S-P-N	93286	30	120-277 VAC	2952	-40C - 55C
C0820-WP-30W-50K-N19-W-N-N	93287	30	120-277 VAC	2952	-40C - 55C
C0820-WP-30W-50K-N19-W-P-N	93288	30	120-277 VAC	2952	-40C - 55C

40W Wallpack Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-WP-40W-40K-N19-BL-N-N	93289	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-40K-N19-BL-P-N	93290	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-40K-N19-BR-N-N	93291	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-40K-N19-BR-P-N	93292	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-40K-N19-S-N-N	93293	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-40K-N19-S-P-N	93294	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-40K-N19-W-N-N	93295	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-40K-N19-W-P-N	93296	40	120-277 VAC	3283	-40C - 55C
C0820-WP-40W-50K-N19-BL-N-N	93297	40	120-277 VAC	3936	-40C - 55C
C0820-WP-40W-50K-N19-BL-P-N	93298	40	120-277 VAC	3936	-40C - 55C
C0820-WP-40W-50K-N19-BR-N-N	93299	40	120-277 VAC	3936	-40C - 55C
C0820-WP-40W-50K-N19-BR-P-N	93300	40	120-277 VAC	3936	-40C - 55C
C0820-WP-40W-50K-N19-S-N-N	93301	40	120-277 VAC	3936	-40C - 55C
C0820-WP-40W-50K-N19-S-P-N	93302	40	120-277 VAC	3936	-40C - 55C
C0820-WP-40W-50K-N19-W-N-N	93303	40	120-277 VAC	3936	-40C - 55C
C0820-WP-40W-50K-N19-W-P-N	93304	40	120-277 VAC	3936	-40C - 55C

48W Wallpack Light Fixture



Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-WP-48W-40K-N19-BL-N-N	93305	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-40K-N19-BL-P-N	93306	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-40K-N19-BR-N-N	93307	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-40K-N19-BR-P-N	93308	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-40K-N19-S-N-N	93309	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-40K-N19-S-P-N	93310	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-40K-N19-W-N-N	93311	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-40K-N19-W-P-N	93312	48	120-277 VAC	4250	-40C - 55C
C0820-WP-48W-50K-N19-BL-N-N	93313	48	120-277 VAC	4723	-40C - 55C
C0820-WP-48W-50K-N19-BL-P-N	93314	48	120-277 VAC	4723	-40C - 55C

Wallpack Light Fixture

48W Wallpack Light Fixture

Ordering Code	Bar Code	Watts	Volts	Lumens	Operating Temp
C0820-WP-48W-50K-N19-BR-N-N	93315	48	120-277 VAC	4723	-40C - 55C
C0820-WP-48W-50K-N19-BR-P-N	93316	48	120-277 VAC	4723	-40C - 55C
C0820-WP-48W-50K-N19-S-N-N	93317	48	120-277 VAC	4723	-40C - 55C
C0820-WP-48W-50K-N19-S-P-N	93318	48	120-277 VAC	4723	-40C - 55C
C0820-WP-48W-50K-N19-W-N-N	93319	48	120-277 VAC	4723	-40C - 55C
C0820-WP-48W-50K-N19-W-P-N	93320	48	120-277 VAC	4723	-40C - 55C

Post-Top LED Replacement Lamp

30W Post-Top LED Replacement Lamp

Ordering Code	Bar Code	Watts	Volts	Lumens
C0820-PT-30W-27K-W	93243	30	120-277 VAC	2730
C0820-PT-30W-30K-W	93244	30	120-277 VAC	2775
C0820-PT-30W-40K-W	93245	30	120-277 VAC	2970
C0820-PT-30W-50K-W	93246	30	120-277 VAC	3150

45W Post-Top LED Replacement Lamp

Ordering Code	Bar Code	Watts	Volts	Lumens
C0820-PT-45W-27K-W	93247	45	120-277 VAC	4095
C0820-PT-45W-30K-W	93248	45	120-277 VAC	4275
C0820-PT-45W-40K-W	93249	45	120-277 VAC	4455
C0820-PT-45W-50K-W	93250	45	120-277 VAC	4725

Part Number Index

0		
01000	41	
01003	41	
01003-BP	41	
01004	41	
01004-BP	41	
01005	41	
01005-BP	41	
01006	42	
01007	42	
01007-BLUE	42	
01007-BP	42	
01008	42	
01008-BP	42	
01009	42	
01009-BLUE	42	
01009-BLUE-BP	42	
01009-BP	42	
01010	42	
01015	42	
01015-BP	42	
01019	42	
01019-BP	42	
01021	42	
01021-BP	42	
01023	41	
01027	41	
01031	42	
01031-BP	42	
01800	55	
02500	55	
03000	55	
03100	55	
03600	55	
03900	55	
04100	55	
04200	55	
04900	55	
06300	55	
06500	55	
07600	55	
07800	55	
08200	55	
1		
1003	31	
1003-BP	31	
1003LL-BP	31	
1004	31	
1004-BP	31	
100A/RS	23	
100A/RS/TF	23	
100A/RS-12V	23	
100T8/1SC	45	
1016	31	
1016-BP	31	
1034	31	
1034-BP	31	
1047	31	
105	27	
105-BP	27	
1062	31	
1073	31	
1073-BP	31	
1076	31	
1076-BP	31	
1093	31	
1096	54	
1096X	54	
10C7/120V	24	
10C7DC/120V	24,25	
10ESB5	25	
10S11N	54	
10S11NF	54	
10S6/120V	24	
10S6/230V	24,25	
10S6/250V	24	
10S6DC/250V	24,25	
1105	31	
11143	55	
112	27	
1129	31	
1129-BP	31	
1130	31	
1133	31	
1134	31	
1139IF	31	
1141	31	
1141-BP	31	
1141IF	31	
1141LL	31	
1141LL-BP	31	
1142	31	
1142-BP	31	
1143	31	
1143IF	31	
1144	31	
1152	31	
1154	31	
1154-BP	31	
1155	31	
1155-BP	31	
1156	31	
1156A	31	
1156A-BP	31	
1156B	31	
1156-BP	31	
1156DC	31	
1156G	31	
1156LL	31	
1156LL-BP	31	
1156NA	31	
1156NA-BP	31	
1156P	31	
1156R	31	
1156Y	31	
1157	31	
1157A	31	
1157A-BP	31	
1157-BP	31	
1157LL	31	
1157LL-BP	31	
1157NA	31	
1157NA-BP	31	
1157NALL-BP	31	
1158	31	
1158-BP	31	
1176	31	
1176-BP	31	
1178	32	
1195	32	
1196	32	
1203	32	
1204	32	
120MB	27	
120MB/6	27	
120MB-NEON	27	
120PSB5	27	
120PSB5-NEON	27	
120RB	28	
120RC	28	
120RC-NEON	28	
1210X	32	
1211X	32	
1224	32	
1224K	32	
1228	32	
123	28	
1236X	32	
1236X-BP	32	
124	28	
124-BP	28	
1250X	32	
1250X-2	32	
1250X-5	32	
1251	32	
1252	32	
125T10P	45	
1295	32	
1295NA	32	
1295NA-BP	32	
12ESB5	25	
12MB	25	
12PSB5	25	
12RB	25	
12RC	26	
13	26	
130	28	
1309	32	
130MB	28	
131	28	
1383	32	
1383TF	32	
1385	32	
14	26	
1408	32	
1414	32	
1416	32	
1434	32	
1437	32	
1445	32	
1445-BP	32	
1446	32	
1447	32	
1449	32	
1449-BP	32	
1450	32	
1450X	32	
1460	54	
1460X	54	
1464	32	
1468X	54	
147	28	
1477	32	
1480	32	
1487	32	
1489	32,54	
1490	32	
1493	32	
1495	32	
14-BP	26	
1507	54	
150A/RS	23	
150A/RS/TF	23	
150BT15/H/W	18	
150P25/10	54	
150T10/H/F	45,50	
1524X	32	
155MB	28	
155PSB5	28	
158	28	
158-BP	28	
159	28	
1591	32	
15S11/102CL	54	
15S11/102IF	54	
15S11-13	54	
15S11-14	54	
15S11-87	54	
15S11-F	54	
15T4C-130V	25	
15T6C-120V	25	
15T6C-130V	25,26	
15T6C-145V	25,26	
15T7C-130V	25,26	
15T7DC-130V	25,26	
15T7N-130V	25,26	
16073	55	
161	28	
16120X	36	
1619	32	
161-BP	28	
1630	55	
1631X	55	
1634	55	
1638	32	
1649	55	
1651	32	
1662	32	
168	28	

1680	32	1891-BP	33	2232	33
1683	32	1892	33	2233	33
168-BP	28	1892-BP	33	233	28
168LL-BP	28	1893	33	2357	33
168NA	28	1893-BP	33	2357A	33
168NA-BP	28	1895	33	2357A-BP	33
1691	32	1895A	33	2357-BP	33
1692	32	1895B	33	2357LL-BP	33
16ESB5	26	1895B-BP	33	2357NA	33
17	26	1895-BP	33	2357NA-BP	33
17002	22	1895G	33	238	28
17004	22	1895R	33	239	28
17006	22	1906	33	2396	33
17008	22	192	28	2396-BP	33
17010	22	192-BP	28	2397	33
17012	22	193	28	2397-BP	33
17014	22	194	28	24	26
17016	22	194A	28	2410X-1	33
17018	22	194A-BP	28	2410X-2	33
17022	22	194B	28	243	28
17024	22	194B-BP	28	245	28
17026	22	194-BP	28	2450X	33
17028	22	194G	28	2470X	33,34
17030	22	194G-BP	28	2475X-1	34
17032	22	194LL	28	24A	26
17034	22	194LL-BP	28	24-BP	26
17040	22	194NA	28	24CSB	26
17042	22	194NA-BP	28	24E1	26
17044	22	194R	28	24E2	26
17046	22	194R-BP	28	24E3	26
17048	22	198	28	24ESB5	26
17050	22	198-BP	28	24EX	26
17052	22	198LL	28	24MB	26
1768	32	198LL-BP	28	24PSB5	26
1769	32	199	28	24RC	26
1775	32	1A/27W	25	24X	26
18	26	1A/50W	25	2504	34
18001	23	2		250T10/H/F	45,50
18002	23	2	25	251	28
18003	23	200	28	257	28
18004	23	2040	33	258	28
18006	22	2040-BP	33	259	28
18007	22	2057	33	25S11-2C	54
18008	22	2057A	33	25S11-5C	54
18009	22	2057A-BP	33	25T10/F-130V	25,26
18011	23	2057-BP	33	25T10/IF-120	25,26
18012	23	2057LL	33	25T10-130V	25,26
18013	23	2057LL-BP	33	25T6.5DC/F-130V	25,26
18014	23	2057NA	33	25T6.5N/F-130V	25,26
1804	32	2057NA-BP	33	25T6-1/2DC-130V	25,26
1810	32	2057NALL	33	25T6-1/2N-130V	25,26
1813	32	2057NALL-BP	33	25T6C-120V	25,26
1813-BP	32	20-99	26	25T8/DC	45,50
1815	32	20-99F	26	25T8C-120V	25,26
1815-BP	32	20T6.5DC/F-130V	25,26	25T8DC-120V	25,26
1816	32	20T6-1/2DC-130V	25,26	25T8DC-130V	25,26
1816-BP	32	20T6-1/2F-130V	25,26	25T8N-130V	25,26
1818	32	20T6-1/2N-130V	25,26	265	28
1819	32	20T6-1/2N-145V	25,26	267	28
1819-BP	32	210	28	27	26
1820	32	2102	33	27.0H1	26
1820-BP	32	211-2	28	2721	34
1820BTS	32	211-2/F	28	2721-BP	34
1820R	32	211-2/F-BP	28	2721MF	34
1821	32	211-2B	28	2721MF-BP	34
1822	32	211-2B-BP	28	2723	34
1828	32	211-2-BP	28	2723-BP	34
1829	32	211-2R-BP	28	2741	34
1829-BP	32	2114	33	2741MF	34
1835	33	212-2	28	2821	34
1843	33	212-2-BP	28	2821-BP	34
1847	33	214-2	28	2825	34
1847-BP	33	2162	33	2825-BP	34
1850	33	2174	33	2827	34
1864	33	2176	33	2827-BP	34
1866	33	2181	33	2841	34
1873	33	2182	33	2860X	34
1873-BP	33	2185	33	28ESB5	26
1876	33	2187	33	28MB	26
1888	33	219	28	28PSB5	26
1889	33	2200	33	28RC	26
1889-BP	33	222	28	293	28
1891	33	222-BP	28	293-BP	28

29A/CL/H-120V	18	35014	23	41360	55
3		356	29	41362	55
301	28	359	29	41364	55
3011	34	35A2	26	41366	55
301-R	28	363	29	41368	55
303	29	3652	35	41374	55
304	29	3652-BP	35	41376	55
3047K	34	367	29	41382	55
3047K-BP	34	36PAR36/CAP/WFL32	45	4157K	35
3057	34	37	26	4157K-BP	35
3057A	34	37.5H1	26	4157NAK	35
3057A-BP	34	370	29	4157NAK-BP	35
3057-BP	34	373	29	41-BP	26
3057K	34	375	29	42000	36
3057K-BP	34	3757NAK	35	42002	36
3057NA	34	3757NAK-BP	35	42003	36
3057NA-BP	34	376	29	42005	36
306	29	377	29	42006	36
307	29	378	29	425	29
308	29	379	29	428	29
30R20/FL-120V	24	37-BP	26	43	26
30R20/FL-130V	24	380	29	432	29
31	26	381	29	4340	44
311	29	382	29	4350	44
312	29	385	29	43A/CL/H-120V	18
313	29	386	29	44	26
313-BP	29	387	29	4405	44
313-R	29	388	29	4406	44
315	29	3893	35	4411	44
3155	34	3893-BP	35	4412	44
3155-BP	34	3898	35	4412A	44
3155K	34	394	29	4413	44
3156	34	398	29	4414	44
3156A	34	399	29	4415	44
3156-BP	34	3S6/5-120V	24,25	4415A	44
3156K	34	3S6/5-130V	24,25	4416	44
3156K-BP	34	3S6/5DC-120V	24,25	4416R	44
3157	34	4		4419	44
3157A	34	40	26	44250	44
3157A-BP	34	400	29	4435	44
3157-BP	34	4007	44	4436	44
3157K	34	4044	44	4446	44
3157K-BP	34	4049	44	44500	44
3157NA	34	4057K	35	4461	44
3157NA-BP	34	4057K-BP	35	4478	44
327	29	407	29	44-A	26
328	29	40A/CL-130V	23	44-B	26
330	29	40A-130V	23	44-BP	26
334	29	40A15/F-130V	23	44-G	26
335	29	40A15/F-230/250V	23	44-P	26
3357	34	40A15-130V	23	44-R	26
3357A	34	40A15-230/250V	23	44-Y	26
3357-BP	34	40S11N	24	4502	44
3357NA	34	40T10/F-130V	25,26	4505	44
3357NA-BP	34	40T10-130V	25,26	4509	44
336	29	40T6-1/2N-130V	25,26	4510	44
337	29	41	26	4511	44
338	29	4114K	35	4515	44
342	29	4114K-BP	35	4537	44
344	29	41304	55	4543	44
345	29	41306	55	4545	44
3456K	35	41308	55	4546	44
3456K-BP	35	41310	55	455	29
3457/3357	35	41312	55	456	29
3457/3357-BP	35	41314	55	45675	36
3457A	35	41316	55	45685	36
3457NA/3357NA	35	41318	55	4570	44
3457NA/3357NA-BP	35	41320	55	4571	44
3496	35	41324	55	4578	44
3496-BP	35	41326	55	4579	44
3497	35	41328	55	4581	44
3497-BP	35	41332	55	4589	44
35001	23	41334	55	4596	44
35002	23	41336	55	45BR30/FL-120V	24
35003	23	41338	55	45R20/FL-120V	24
35004	23	41340	55	45R20/FL-130V	24
35006	22	41344	55	46	26
35007	22	41346	55	4626	45
35008	22	41348	55	4636	45
35009	22	41350	55	464	29
35011	23	41352	55	4651	45
35012	23	41354	55	4652	45
35013	23	41358	55	46-BP	26

47	26	578-BP	29	6614F	35
4700	45	579	29	6614F-BP	35
4745	42	579-BP	29	6615F	35
4745-BP	35,43	57-BP	27	67	27
47-A	26	585	29	67-BP	27
47-B	26	6		67K	27
47-BP	26	6014	45	68	27
47-G	27	6015	45	680	30
47-P	27	6022	35	683	30
47-R	27	605	29	6833	35
47-Y	27	6052	45	6838	35
48	27	60A/CL-130V	23	6839	35
48220-BP	42	60A-130V	23	6848	35
4880	45	60BT15/H/CL	18	685	30
48C2	27	60BT15/H/W	18	68-BP	27
48ESB5	27	60MB	27	6MB	25
48MB	27	60PSB5	27	6PSB5	25
48PSB5	27	60RB	27	6S6/120V	24,25
48RC	27	623	30	6S6/12V	24,25
49	27	6235B	43	6S6/130V	24,25
49407	19	6235B-BP	43	6S6/145V	24,25
49408	19	6235J	43	6S6/155V	24,25
4C7/120V	24,25	6235J-BP	43	6S6/18V	24,25
4C7/130V	24,25	6235Y	43	6S6/230V	24,25
5		6235Y-BP	43	6S6/24V	24,25
50	27	624	30	6S6/30V	24,25
5007	35	6245B	43	6S6/48V	24,25
5007-BP	35	6245BA	43	6S6/60V	24,25
5008	35	6245BA-BP	43	6S6/6V	24,25
5008-BP	35	6245B-BP	43	6S6DC/120V	24
500T46/MOG-120V	50	6245J-BP	43	6S6DC/12V	24,25
502	29	6245Y-BP	43	6S6DC/130V	24,25
502-BP	29	6253	35,43	6S6DC/145V	24,25
503	29	6253-BP	43	6S6DC/24V	24,25
509K	29	6255BAH-BP	43	6S6DC/30V	24,25
50A/RS	23	6255BAHP-BP	43	6S6DC/32V	24,25
50A/RS/TF	23	625J	43	6S6DC/48V	24,25
50A/RS-12V	23	6260BA	43	6S6DC/60V	24,25
50PAR20/FL30/3500K	23	6260BA-BP	43	6S6DC/6V	24,25
50PAR20/SP10/3500K	23	6260B-BP	43	7	
51	27	6260H-BP	43	70	27
51A	27	6260HD-BP	43	7010	35
51-BP	27	6260HP-BP	43	7012	35
52	27	6260J	43	7014	35
5200	35	6260J-BP	43	715	30
5201	35	6260S	43	718	30
5202	35	6260SA-BP	43	71818	55
52A	27	6260S-BP	43	7219	35
53	27	6263-BP	43	7225	35
53A/CL/H-120V	18	6265-BP	43	7225-BP	35
53-BP	27	63	27	72A/CL/H-120V	18
55	27	631	30	73	27
555	29	631-BP	30	7327	35
555-A	29	635B	43	7328	35
555-B	29	635J	43	7330	36
555-G	29	6361-BP	35,43	7333	36
555-P	29	6365	43	7349	36
555-R	29	6365-BP	35,43	7362	36
555-Y	29	63-BP	27	7370	36
558	29	63-R	27	7371	36
558-BP	29	64	27	7373	36
55A/S8	27	6411	35	7374	36
55-BP	27	64111	36	7377	36
55C2	27	64111-BP	36	7380	36
55C3	27	6411-BP	35	7381	36
56	27	6418	35	7382	36
56016164	55	6418-BP	35	7387	36
56018366	55	64260	55	73-BP	27
56018550	55	64514	45	74	27
56018566	55	655	30	7400	45
56018769	55	656	30	7440	36
561	29	657	30	7440-BP	36
561-BP	29	658	30	7440NA	36
562	29	658-BP	30	7440NA-BP	36
562-BP	29	65BR30/FL-120V	24	7441	36
563	29	65BR30/FL-130V	24	7441-BP	36
564	29	65BR30/SP-120V	24	7443	36
57	27	65BR30/SP-130V	24	7443-BP	36
5702NAK	35	65BR40/FL-120V	24	7444NA	36
5702NAK-BP	35	65BR40/FL-130V	24	7444NA-BP	36
577	29	660B	43	74-BP	27
577-BP	29	6610F	35	7506	36
578	29	6612F	35	7506-BP	36

7507NA	36	885-BP	41	9006XS-BP	40
7507NA-BP	36	885CVSU-BP	39	9006XSCVSU2	39
7511	36	885SW-BP	41	9006XSCVSU-BP	39
7528	36	886	41	9006XSLL	40
7528-BP	36	886-BP	41	9006XSLL-BP	40
7537	36	889	41	9006XSPVP2	40
755	30	889-BP	41	9006XSPVP-BP	40
755-BP	30	889CVSU-BP	39	9007	40
756	30	889SW-BP	41	9007-BP	40
757	30	89	27	9007CVSU2	39
757-BP	30	890	41	9007CVSU-BP	39
75A/CL-130V	23	890-BP	41	9007CVXL2	39
75A/RS	23	891	30,41	9007CVXL-BP	39
75A/RS/TF	23	8918	36	9007HW	40
75A/RS-12V	23	891-BP	41	9007LL	41
75A/SW-130V	23	893	41	9007LL-BP	41
75A-130V	23	893-BP	41	9007PVP2	40
75BT15/H/W	18	893CVSU-BP	39	9007PVP-BP	40
75PAR30/FL30/3500K	23	893SW-BP	41	9008	41,42
75PAR30/SP10/3500K	23	894	41	9008-BP	41
7613	45	894-BP	41	9008CVSU2	39
7632	36	894CVSU-BP	39	9008CVSU-BP	39
7646	36	894SW-BP	41	9008CVXL2	39
7672-1	45	895	30	9008CVXL-BP	39
7683	36	896	41	9008PVP2	40
76907	55	896-BP	41	9008PVP-BP	40
7714	36	896CVSU-BP	39	901	30
7715	36	896SW-BP	41	9011	41
778	30,54	898	41	9012LL	41
77903	55	898-BP	41	901A	30
77904	55	899	41	901B	30
77910	55	899-BP	41	901-BP	30
77A/58	27	899CVSU-BP	39	901G	30
7839	36	89-BP	27	901R	30
787	30,54	89K	27	904	30
7876	36	9		9040	41,42
788	30,54	90	27	9040-BP	41,42
789	30,54	9003	40	9045	41
79	27	9003/H4CVSU2	39	904-BP	30
795	30	9003/H4CVSU-BP	39	906	30
795X	30	9003/H4CVXL2	39	906A	30
796	30	9003/H4CVXL-BP	39	906B	30
797	30	9003/H4PVP2	40	906-BP	30
7C7/120V	24,25	9003/H4PVP-BP	40	906G	30
7C7/130V	24,25	9003-BP	40	906P	30
7C7/130V-W	24,25	9004	40	906R	30
8		9004-BP	40	906Y	30
8001	55	9004CVSU2	39	908	30
8013	55	9004CVSU-BP	39	909	30
8014	55	9004CVXL2	39	90-BP	27
8017	55	9004CVXL-BP	39	90MB	27
8018	55	9004HW	40	90PAR38/FL30/3500K	23
8022	55	9004LL	40	90PAR38/SP10/3500K	23
80-A	54	9004LL-BP	40	90PAR38/WFL50/3500K	23
80-B	54	9004PVP2	40	912	30
81	27	9004PVP-BP	40	912-BP	30
8100	55	9005	40	912LL	30
8111	36	9005-BP	40	914	30
82	27	9005CVSU2	39	9140	41
8362	36	9005CVSU-BP	39	915	30
8-3995	25	9005CVXL2	39	9155	41,42
84	27	9005CVXL-BP	39	916	30
85	27	9005PVP2	40	916-BP	30
86	27	9005PVP-BP	40	916NA	30
8610	36	9005XS	40	916NA-BP	30
862	41	9005XS-BP	40	917	30
8627	36	9005XSCVSU2	39	918	30
8640	36	9005XSCVSU-BP	39	918A	30
8666	36	9005XSLL	40	918B	30
86G	27	9005XSPVP2	40	918-BP	30
87	27	9005XSPVP-BP	40	918G	30
88	27	9006	40	918R	30
880	41	9006-BP	40	920	30
880-BP	41	9006CVSU2	39	921	30
880CVSU-BP	39	9006CVSU-BP	39	921-BP	30
880SW-BP	41	9006CVXL2	39	921-FR	30
881	41	9006CVXL-BP	39	921LL	30
881-BP	41	9006HW	40	921LL-BP	30
881CVSU-BP	39	9006LL	40	921X	30
881SW-BP	41	9006LL-BP	40	922	30
882	30,41	9006PVP2	40	922-BP	30
882-BP	41	9006PVP-BP	40	923	30
885	41	9006XS	40	923-BP	30

923G	30
923R	30
927	31
928	31
93	27
939	31
93-BP	27
94	27
949	31
957	31
96	27
967	31
97	27
97A	27
97-BP	27
98	27

A

A1-010-28	55
A-1262	43
A-1272	43
A-1272-BP	36,43
A1-420-10	55
A1-510-01	55
A1A	37
A1B	37
A1C	37
A1H	37
A2B	37
A-3598H	43
A-3598H-BP	36,43
A-3603	44
A-3603-BP	36,44
A-3625	44
A-3625-BP	36,44
A3C	37
A-4513	44
A-4513-BP	36,44
A-4527	44
A-4527-BP	36,44
A-4813	44
A-4813-BP	36,44
A-4829-BP	36,44
A-5659	44
A-5659-BP	36,44
A-62	36,43
A-62-BP	36,43
A-7025-BP	44
A-72	36,43
A-72-BP	36,43
A9A	37

B

B1-010-28	56
B1A	37
B2A	37
B5-011-32	56
B7A	37
BAB	19
BAB-BLACK	19
BAB-FG	19
BAB-FG-GU10-120V	20
BAB-SILVER	19
BBA	46,51
BBA-LN	46,51
BCA	46,51
BCK	46
BFE	46,52
BFK/BFL	46,52
BFM	56
BKV	46
BLC	46
BLR	46
BNF	46
BRH	46,52
BRL	46
BTG	46
BTL	46,52
BTN	46,52
BTP	46,52
BTR	46,52
BVT	46,52
BVV	46,52
BVW	46,52

BWA	46,52
BWF	46,52
BWM	46,52
BWN	46,52
BXE	46
BZW	56

C

C0820-FL-100W-40K-N31-BL-N-N	57
C0820-FL-100W-40K-N31-BL-P-N	57
C0820-FL-100W-40K-N31-BR-N-N	57
C0820-FL-100W-40K-N31-BR-P-N	57
C0820-FL-100W-40K-N31-S-N-N	57
C0820-FL-100W-40K-N31-S-P-N	57
C0820-FL-100W-40K-N31-W-N-N	57
C0820-FL-100W-40K-N31-W-P-N	57
C0820-FL-100W-50K-N31-BL-N-N	57
C0820-FL-100W-50K-N31-BL-P-N	57
C0820-FL-100W-50K-N31-BR-N-N	57
C0820-FL-100W-50K-N31-BR-P-N	57
C0820-FL-100W-50K-N31-S-N-N	57
C0820-FL-100W-50K-N31-S-P-N	57
C0820-FL-100W-50K-N31-W-N-N	57
C0820-FL-100W-50K-N31-W-P-N	57
C0820-FL-120W-40K-N31-BL-N-N	57
C0820-FL-120W-40K-N31-BL-P-N	57
C0820-FL-120W-40K-N31-BR-N-N	57
C0820-FL-120W-40K-N31-BR-P-N	57
C0820-FL-120W-40K-N31-S-N-N	57
C0820-FL-120W-40K-N31-S-P-N	57
C0820-FL-120W-40K-N31-W-N-N	57
C0820-FL-120W-40K-N31-W-P-N	57
C0820-FL-120W-50K-N31-BL-N-N	57
C0820-FL-120W-50K-N31-BL-P-N	57
C0820-FL-120W-50K-N31-BR-N-N	57
C0820-FL-120W-50K-N31-BR-P-N	57
C0820-FL-120W-50K-N31-S-N-N	57
C0820-FL-120W-50K-N31-S-P-N	57
C0820-FL-120W-50K-N31-W-N-N	57
C0820-FL-120W-50K-N31-W-P-N	57
C0820-FL-160W-40K-N31-BL-N-N	57
C0820-FL-160W-40K-N31-BL-P-N	57
C0820-FL-160W-40K-N31-BR-N-N	57
C0820-FL-160W-40K-N31-BR-P-N	57
C0820-FL-160W-40K-N31-S-N-N	57
C0820-FL-160W-40K-N31-S-P-N	58
C0820-FL-160W-40K-N31-W-N-N	58
C0820-FL-160W-40K-N31-W-P-N	58
C0820-FL-160W-50K-N31-BL-N-N	58
C0820-FL-160W-50K-N31-BL-P-N	58
C0820-FL-160W-50K-N31-BR-N-N	58
C0820-FL-160W-50K-N31-BR-P-N	58
C0820-FL-160W-50K-N31-S-N-N	58
C0820-FL-160W-50K-N31-S-P-N	58
C0820-FL-160W-50K-N31-W-N-N	58
C0820-FL-160W-50K-N31-W-P-N	58
C0820-FL-200W-40K-N31-BL-N-N	58
C0820-FL-200W-40K-N31-BL-P-N	58
C0820-FL-200W-40K-N31-BR-N-N	58
C0820-FL-200W-40K-N31-BR-P-N	58
C0820-FL-200W-40K-N31-S-N-N	58
C0820-FL-200W-40K-N31-S-P-N	58
C0820-FL-200W-40K-N31-W-N-N	58
C0820-FL-200W-40K-N31-W-P-N	58
C0820-FL-240W-40K-N31-BL-N-N	58
C0820-FL-240W-40K-N31-BL-P-N	58
C0820-FL-240W-40K-N31-BR-N-N	58
C0820-FL-240W-40K-N31-BR-P-N	58
C0820-FL-240W-40K-N31-S-N-N	58
C0820-FL-240W-40K-N31-S-P-N	58
C0820-FL-240W-40K-N31-W-N-N	58
C0820-FL-240W-40K-N31-W-P-N	58
C0820-FL-240W-50K-N31-BL-N-N	58
C0820-FL-240W-50K-N31-BL-P-N	58
C0820-FL-240W-50K-N31-BR-N-N	58
C0820-FL-240W-50K-N31-BR-P-N	58
C0820-FL-240W-50K-N31-S-N-N	58
C0820-FL-240W-50K-N31-S-P-N	58
C0820-FL-240W-50K-N31-W-N-N	58
C0820-FL-240W-50K-N31-W-P-N	58
C0820-FL-30W-40K-N31-BL-N-N	56
C0820-FL-30W-40K-N31-BL-P-N	56
C0820-FL-30W-40K-N31-BR-N-N	56
C0820-FL-30W-40K-N31-BR-P-N	56
C0820-FL-30W-40K-N31-S-N-N	56
C0820-FL-30W-40K-N31-S-P-N	56
C0820-FL-30W-40K-N31-W-N-N	56
C0820-FL-30W-40K-N31-W-P-N	56
C0820-FL-30W-50K-N31-BL-N-N	56

C0820-FL-160W-50K-N31-BR-N-N	58
C0820-FL-160W-50K-N31-BR-P-N	58
C0820-FL-160W-50K-N31-S-N-N	58
C0820-FL-160W-50K-N31-S-P-N	58
C0820-FL-160W-50K-N31-W-N-N	58
C0820-FL-160W-50K-N31-W-P-N	58
C0820-FL-200W-40K-N31-BL-N-N	58
C0820-FL-200W-40K-N31-BL-P-N	58
C0820-FL-200W-40K-N31-BR-N-N	58
C0820-FL-200W-40K-N31-BR-P-N	58
C0820-FL-200W-40K-N31-S-N-N	58
C0820-FL-200W-40K-N31-S-P-N	58
C0820-FL-200W-40K-N31-W-N-N	58
C0820-FL-200W-40K-N31-W-P-N	58
C0820-FL-200W-50K-N31-BL-N-N	58
C0820-FL-200W-50K-N31-BL-P-N	58
C0820-FL-200W-50K-N31-BR-N-N	58
C0820-FL-200W-50K-N31-BR-P-N	58
C0820-FL-200W-50K-N31-S-N-N	58
C0820-FL-200W-50K-N31-S-P-N	58
C0820-FL-200W-50K-N31-W-N-N	58
C0820-FL-200W-50K-N31-W-P-N	58
C0820-FL-240W-40K-N31-BL-N-N	58
C0820-FL-240W-40K-N31-BL-P-N	58
C0820-FL-240W-40K-N31-BR-N-N	58
C0820-FL-240W-40K-N31-BR-P-N	58
C0820-FL-240W-40K-N31-S-N-N	58
C0820-FL-240W-40K-N31-S-P-N	58
C0820-FL-240W-40K-N31-W-N-N	58
C0820-FL-240W-40K-N31-W-P-N	58
C0820-FL-240W-50K-N31-BL-N-N	58
C0820-FL-240W-50K-N31-BL-P-N	58
C0820-FL-240W-50K-N31-BR-N-N	58
C0820-FL-240W-50K-N31-BR-P-N	58
C0820-FL-240W-50K-N31-S-N-N	58
C0820-FL-240W-50K-N31-S-P-N	58
C0820-FL-240W-50K-N31-W-N-N	58
C0820-FL-240W-50K-N31-W-P-N	58
C0820-FL-30W-40K-N31-BL-N-N	56
C0820-FL-30W-40K-N31-BL-P-N	56
C0820-FL-30W-40K-N31-BR-N-N	56
C0820-FL-30W-40K-N31-BR-P-N	56
C0820-FL-30W-40K-N31-S-N-N	56
C0820-FL-30W-40K-N31-S-P-N	56
C0820-FL-30W-40K-N31-W-N-N	56
C0820-FL-30W-40K-N31-W-P-N	56
C0820-FL-30W-50K-N31-BL-N-N	56

C0820-FL-30W-50K-N31-BL-P-N	56	C0820-HB-120W-50K-N39-W-N-N	58	C0820-HB-240W-50K-N39-S-N-N	60
C0820-FL-30W-50K-N31-BR-N-N	56	C0820-HB-120W-50K-N40-BR-N-N	58	C0820-HB-240W-50K-N39-W-N-N	60
C0820-FL-30W-50K-N31-BR-P-N	56	C0820-HB-120W-50K-N40-S-N-N	58	C0820-HB-240W-50K-N40-BR-N-N	60
C0820-FL-30W-50K-N31-S-N-N	56	C0820-HB-120W-50K-N40-W-N-N	58	C0820-HB-240W-50K-N40-S-N-N	60
C0820-FL-30W-50K-N31-S-P-N	56	C0820-HB-130W-40K-N39-BR-N-N	59	C0820-HB-240W-50K-N40-W-N-N	60
C0820-FL-30W-50K-N31-W-N-N	56	C0820-HB-130W-40K-N39-S-N-N	59	C0820-HB-90W-40K-N39-BR-N-N	59
C0820-FL-30W-50K-N31-W-P-N	56	C0820-HB-130W-40K-N39-W-N-N	59	C0820-HB-90W-40K-N39-S-N-N	59
C0820-FL-50W-40K-N31-BL-N-N	56	C0820-HB-130W-40K-N40-BR-N-N	59	C0820-HB-90W-40K-N39-W-N-N	59
C0820-FL-50W-40K-N31-BL-P-N	56	C0820-HB-130W-40K-N40-S-N-N	59	C0820-HB-90W-40K-N40-BR-N-N	59
C0820-FL-50W-40K-N31-BR-N-N	56	C0820-HB-130W-40K-N40-W-N-N	59	C0820-HB-90W-40K-N40-S-N-N	59
C0820-FL-50W-40K-N31-BR-P-N	56	C0820-HB-130W-50K-N39-BR-N-N	59	C0820-HB-90W-40K-N40-W-N-N	59
C0820-FL-50W-40K-N31-S-N-N	56	C0820-HB-130W-50K-N39-S-N-N	59	C0820-HB-90W-50K-N39-BR-N-N	59
C0820-FL-50W-40K-N31-S-P-N	56	C0820-HB-130W-50K-N39-W-N-N	59	C0820-HB-90W-50K-N39-S-N-N	59
C0820-FL-50W-40K-N31-W-N-N	56	C0820-HB-130W-50K-N40-BR-N-N	59	C0820-HB-90W-50K-N39-W-N-N	59
C0820-FL-50W-40K-N31-W-P-N	56	C0820-HB-130W-50K-N40-S-N-N	59	C0820-HB-90W-50K-N40-BR-N-N	59
C0820-FL-50W-50K-N31-BL-N-N	56	C0820-HB-130W-50K-N40-W-N-N	59	C0820-HB-90W-50K-N40-S-N-N	59
C0820-FL-50W-50K-N31-BL-P-N	56	C0820-HB-160W-40K-N39-BR-N-N	59	C0820-HB-90W-50K-N40-W-N-N	59
C0820-FL-50W-50K-N31-BR-N-N	56	C0820-HB-160W-40K-N39-S-N-N	59	C0820-HC-100W-40K-N39-W-N-N	60
C0820-FL-50W-50K-N31-BR-P-N	56	C0820-HB-160W-40K-N39-W-N-N	59	C0820-HC-100W-50K-N39-W-N-N	60
C0820-FL-50W-50K-N31-S-N-N	56	C0820-HB-160W-40K-N40-BR-N-N	59	C0820-HC-120W-40K-N39-W-N-N	60
C0820-FL-50W-50K-N31-S-P-N	56	C0820-HB-160W-40K-N40-S-N-N	59	C0820-HC-120W-50K-N39-W-N-N	60
C0820-FL-50W-50K-N31-W-N-N	56	C0820-HB-160W-40K-N40-W-N-N	59	C0820-HC-80W-40K-N38-W-N-N	60
C0820-FL-50W-50K-N31-W-P-N	57	C0820-HB-160W-50K-N39-BR-N-N	59	C0820-HC-80W-40K-N39-W-N-N	60
C0820-FL-80W-40K-N31-BL-N-N	57	C0820-HB-160W-50K-N39-S-N-N	59	C0820-HC-80W-50K-N38-W-N-N	60
C0820-FL-80W-40K-N31-BL-P-N	57	C0820-HB-160W-50K-N39-W-N-N	59	C0820-HC-80W-50K-N39-W-N-N	60
C0820-FL-80W-40K-N31-BR-N-N	57	C0820-HB-160W-50K-N40-BR-N-N	59	C0820-KC-100W-40K-N39-W-N-N	60
C0820-FL-80W-40K-N31-BR-P-N	57	C0820-HB-160W-50K-N40-S-N-N	59	C0820-KC-100W-50K-N39-W-N-N	60
C0820-FL-80W-40K-N31-S-N-N	57	C0820-HB-160W-50K-N40-W-N-N	59	C0820-KC-120W-40K-N39-W-N-N	60
C0820-FL-80W-40K-N31-S-P-N	57	C0820-HB-180W-40K-N39-BR-N-N	59	C0820-KC-120W-50K-N39-W-N-N	60
C0820-FL-80W-40K-N31-W-N-N	57	C0820-HB-180W-40K-N39-S-N-N	59	C0820-KC-80W-40K-N39-W-N-N	60
C0820-FL-80W-40K-N31-W-P-N	57	C0820-HB-180W-40K-N40-BR-N-N	59	C0820-KC-80W-50K-N38-W-N-N	60
C0820-FL-80W-50K-N31-BL-N-N	57	C0820-HB-180W-40K-N40-S-N-N	59	C0820-KC-80W-50K-N39-W-N-N	60
C0820-FL-80W-50K-N31-BL-P-N	57	C0820-HB-180W-40K-N40-W-N-N	59	C0820-PK-40W-27K-N18-BR-N-N	60
C0820-FL-80W-50K-N31-BR-N-N	57	C0820-HB-180W-50K-N39-BR-N-N	59	C0820-PK-40W-27K-N18-S-N-N	60
C0820-FL-80W-50K-N31-BR-P-N	57	C0820-HB-180W-50K-N39-S-N-N	59	C0820-PK-40W-27K-N18-W-N-N	60
C0820-FL-80W-50K-N31-S-N-N	57	C0820-HB-180W-50K-N39-W-N-N	59	C0820-PK-40W-40K-N18-BR-N-N	60
C0820-FL-80W-50K-N31-S-P-N	57	C0820-HB-180W-50K-N40-BR-N-N	59	C0820-PK-40W-40K-N18-S-N-N	60
C0820-FL-80W-50K-N31-W-N-N	57	C0820-HB-180W-50K-N40-S-N-N	59	C0820-PK-40W-40K-N18-W-N-N	60
C0820-FL-80W-50K-N31-W-P-N	57	C0820-HB-180W-50K-N40-W-N-N	59	C0820-PK-40W-50K-N18-BR-N-N	60
C0820-HB-120W-40K-N39-BR-N-N	58	C0820-HB-180W-50K-N40-W-N-N	59	C0820-PK-40W-50K-N18-S-N-N	60
C0820-HB-120W-40K-N39-S-N-N	58	C0820-HB-240W-40K-N39-BR-N-N	59	C0820-PK-40W-50K-N18-W-N-N	60
C0820-HB-120W-40K-N39-W-N-N	58	C0820-HB-240W-40K-N39-S-N-N	59	C0820-PK-50W-27K-N18-BR-N-N	60
C0820-HB-120W-40K-N40-BR-N-N	58	C0820-HB-240W-40K-N39-W-N-N	59	C0820-PK-50W-27K-N18-S-N-N	60
C0820-HB-120W-40K-N40-S-N-N	58	C0820-HB-240W-40K-N40-BR-N-N	59	C0820-PK-50W-27K-N18-W-N-N	60
C0820-HB-120W-40K-N40-W-N-N	58	C0820-HB-240W-40K-N40-S-N-N	59	C0820-PK-50W-40K-N18-BR-N-N	60
C0820-HB-120W-50K-N39-BR-N-N	58	C0820-HB-240W-40K-N40-W-N-N	59	C0820-PK-50W-40K-N18-S-N-N	60
C0820-HB-120W-50K-N39-S-N-N	58	C0820-HB-240W-50K-N39-BR-N-N	60	C0820-PK-50W-40K-N18-W-N-N	60

C0820-PK-50W-50K-N18-BR-N-N	60	C0820-WP-40W-50K-N19-BL-N-N	61	CMP70/MP/3K	1
C0820-PK-50W-50K-N18-S-N-N	60	C0820-WP-40W-50K-N19-BL-P-N	61	CMP70/MP/4K	1
C0820-PK-50W-50K-N18-W-N-N	61	C0820-WP-40W-50K-N19-BR-N-N	61	CMP70/PAR30LN/FL	1
C0820-PK-80W-27K-N18-BR-N-N	61	C0820-WP-40W-50K-N19-BR-P-N	61	CMP70/PAR30LN/SP	1
C0820-PK-80W-27K-N18-S-N-N	61	C0820-WP-40W-50K-N19-S-N-N	61	CMP70/PAR38/FL	1
C0820-PK-80W-27K-N18-W-N-N	61	C0820-WP-40W-50K-N19-S-P-N	61	CMP70/PAR38/SP	1
C0820-PK-80W-40K-N18-BR-N-N	61	C0820-WP-40W-50K-N19-W-N-N	61	CMP70/T6/930	1
C0820-PK-80W-40K-N18-S-N-N	61	C0820-WP-40W-50K-N19-W-P-N	61	CMP70/T6/942	1
C0820-PK-80W-40K-N18-W-N-N	61	C0820-WP-48W-40K-N19-BL-N-N	61	CMP70/TC/930	1
C0820-PK-80W-50K-N18-BR-N-N	61	C0820-WP-48W-40K-N19-BL-P-N	61	CMP70/TD/930	1
C0820-PK-80W-50K-N18-S-N-N	61	C0820-WP-48W-40K-N19-BR-N-N	61	CMP70/TD/942	1
C0820-PK-80W-50K-N18-W-N-N	61	C0820-WP-48W-40K-N19-S-N-N	61	CMP-MR16/20W/NFL/830	1
C0820-PT-30W-27K-W	62	C0820-WP-48W-40K-N19-S-P-N	61	CMP-MR16/20W/SP/830	1
C0820-PT-30W-30K-W	62	C0820-WP-48W-40K-N19-S-N-N	61	CMV/CMT	46
C0820-PT-30W-40K-W	62	C0820-WP-48W-40K-N19-S-P-N	61	CVSUKIT	44
C0820-PT-30W-50K-W	62	C0820-WP-48W-50K-N19-BL-N-N	61	CVX/CSV	46
C0820-PT-45W-27K-W	62	C0820-WP-48W-50K-N19-BL-P-N	61	CWZ	46,52
C0820-PT-45W-30K-W	62	C0820-WP-48W-50K-N19-W-P-N	61	CXK	46
C0820-PT-45W-40K-W	62	C0820-WP-48W-50K-N19-W-N-N	61	CXL/CXR	46
C0820-PT-45W-50K-W	62	C0820-WP-48W-50K-N19-W-P-N	61	CXZ	46,52
C0820-RF-100W-40K-N39-W-N-N	60	C0820-WP-48W-50K-N19-S-N-N	61	CYC	46
C0820-RF-100W-50K-N39-W-N-N	60	C0820-WP-48W-50K-N19-S-P-N	61	CYV	46,52
C0820-RF-120W-40K-N39-W-N-N	60	C0820-WP-48W-50K-N19-W-N-N	61	CZX/DAB	46
C0820-RF-120W-50K-N39-W-N-N	60	C0820-WP-48W-50K-N19-W-P-N	61	D	
C0820-RF-80W-40K-N39-W-N-N	60	C0820-WP-48W-50K-N19-W-N-N	61	D1R	43
C0820-RF-80W-50K-N39-W-N-N	60	C0820-WP-48W-50K-N19-W-P-N	61	D1S	43
C0820-WP-30W-40K-N19-BL-N-N	61	C0820-WP-48W-50K-N19-W-N-N	61	D2R	43
C0820-WP-30W-40K-N19-BL-P-N	61	C0820-WP-48W-50K-N19-W-P-N	61	D2S	43
C0820-WP-30W-40K-N19-BR-N-N	61	C0820-WP-48W-50K-N19-W-N-N	61	D3R	43
C0820-WP-30W-40K-N19-BR-P-N	61	C0820-WP-48W-50K-N19-W-P-N	61	D3S	43
C0820-WP-30W-40K-N19-S-N-N	61	C0820-WP-48W-50K-N19-S-N-N	61	D4R	43
C0820-WP-30W-40K-N19-S-P-N	61	C0820-WP-48W-50K-N19-S-P-N	61	D4S	43
C0820-WP-30W-40K-N19-W-N-N	61	C0820-WP-48W-50K-N19-W-N-N	61	DAY/DAK	46
C0820-WP-30W-50K-N19-BL-N-N	61	C0820-WP-48W-50K-N19-W-P-N	61	DCH/DJA/DFP	46
C0820-WP-30W-50K-N19-BL-P-N	61	C0820-WP-48W-50K-N19-W-N-N	61	DDJ/DZZ	46
C0820-WP-30W-50K-N19-BR-N-N	61	C0820-WP-48W-50K-N19-W-P-N	61	DDK	46
C0820-WP-30W-50K-N19-BR-P-N	61	C0820-WP-48W-50K-N19-S-N-N	61	DDL	46
C0820-WP-30W-50K-N19-S-N-N	61	C0820-WP-48W-50K-N19-S-P-N	61	DDM	46
C0820-WP-30W-50K-N19-S-P-N	61	C0820-WP-48W-50K-N19-W-N-N	61	DDS	46
C0820-WP-30W-50K-N19-W-N-N	61	C0820-WP-48W-50K-N19-W-P-N	61	DE3021	37
C0820-WP-40W-40K-N19-BL-N-N	61	C2A	37	DE3021-BP	37
C0820-WP-40W-40K-N19-BL-P-N	61	C7A	37	DE3022	37
C0820-WP-40W-40K-N19-BR-N-N	61	C9A	37	DE3022-BP	37
C0820-WP-40W-40K-N19-BR-P-N	61	CAX	56	DE3175	37
C0820-WP-40W-40K-N19-S-N-N	61	CAX-130V	56	DE3175-BP	37
C0820-WP-40W-40K-N19-S-P-N	61	CAX-130V-HAL	56	DE3423	37
C0820-WP-40W-40K-N19-W-N-N	61	CBA	46	DE3423-BP	37
C0820-WP-40W-40K-N19-W-P-N	61	CBX/CBS	46	DE3425	37
C0820-WP-40W-50K-N19-BL-N-N	61	CDD	56	DE3425-BP	37
C0820-WP-40W-50K-N19-BL-P-N	61	CDJ	46	DFN/DFC	46
C0820-WP-40W-50K-N19-BR-N-N	61	CDS/CDX	46	DJL	46
C0820-WP-40W-50K-N19-BR-P-N	61	CEA/CEB/CDK	46	DLD/DFZ	46
C0820-WP-40W-50K-N19-S-N-N	61	CEM	46	DLG/DLS/DHX	46
C0820-WP-40W-50K-N19-S-P-N	61	CEW/CFC	46	DMX	46,52
C0820-WP-40W-50K-N19-W-N-N	61	CHK	46	DNE	46
C0820-WP-40W-50K-N19-W-P-N	61	CLS/CLG	46	DNF	46
C0820-WP-40W-40K-N19-BL-N-N	61	CMP100/C/MP/3K	1	DNS/FMC	47,52
C0820-WP-40W-40K-N19-BL-P-N	61	CMP100/C/MP/4K	1	DNW	47,52
C0820-WP-40W-40K-N19-BR-N-N	61	CMP100/MP/3K	1	DPT	47,52
C0820-WP-40W-40K-N19-BR-P-N	61	CMP100/MP/4K	1	DPW	47,52
C0820-WP-40W-40K-N19-S-N-N	61	CMP150/MP/3K	1	DPY	47,52
C0820-WP-40W-40K-N19-S-P-N	61	CMP150/MP/4K	1	DRA	47
C0820-WP-40W-40K-N19-W-N-N	61	CMP150/T6/930	1	DRB/DRC	47
C0820-WP-40W-40K-N19-W-P-N	61	CMP150/T6/942	1	DRS	47
C0820-WP-40W-50K-N19-BL-N-N	61	CMP20/PAR20/FL	1	DRW	47,52
C0820-WP-40W-50K-N19-BL-P-N	61	CMP20/PAR20/SP	1	DT13/27	13
C0820-WP-40W-50K-N19-BR-N-N	61	CMP20/PAR30LN/FL	1	DT13/30	13
C0820-WP-40W-50K-N19-BR-P-N	61	CMP20/PAR30LN/SP	1	DT13/35	13
C0820-WP-40W-50K-N19-S-N-N	61	CMP20/TC/930	1	DT13/41	13
C0820-WP-40W-50K-N19-S-P-N	61	CMP20/TM/930	1	DT13/50	13
C0820-WP-40W-50K-N19-W-N-N	61	CMP35/PAR20/FL	1	DT13/65	13
C0820-WP-40W-50K-N19-W-P-N	61	CMP35/PAR20/SP	1	DT18/30/RS	13
C0820-WP-40W-40K-N19-BL-N-N	61	CMP35/PAR30LN/FL	1	DT18/35/RS	13
C0820-WP-40W-40K-N19-BL-P-N	61	CMP35/PAR30LN/SP	1	DT18/41/RS	13
C0820-WP-40W-40K-N19-BR-N-N	61	CMP35/T6/930	1	DT18/50/RS	13
C0820-WP-40W-40K-N19-BR-P-N	61	CMP35/T6/942	1	DT24/30/RS	13
C0820-WP-40W-40K-N19-S-N-N	61	CMP35/TC/930	1	DT24/35/RS	13
C0820-WP-40W-40K-N19-S-P-N	61	CMP70/C/MP/3K	1	DT24/41/RS	14
C0820-WP-40W-40K-N19-W-N-N	61	CMP70/C/MP/4K	1	DT24/50/RS	14
C0820-WP-40W-40K-N19-W-P-N	61			DT24/65/RS	14
				DT36/30/RS	14
				DT36/35/RS	14
				DT36/41/RS	14

DT36/50/RS	14	EI-2201	56	ETC	48,51
DT36/65/RS	14	EI-722	56	ETD	48,51
DT40/30/RS	14	EI-737	56	ETE	48,51
DT40/35/RS	14	EI-738	56	ETF	48,51
DT40/41/RS	14	EI-74000	56	ETG	48,51
DT40/50/RS	14	EI-77Z	56	ETH	48,51
DT40/65/RS	14	EI-886	56	ETJ	48
DT5/27	13	EI-B153	56	EVA	56
DT5/35	13	EI-M102	56	EVB/BRJ	56
DT5/41	13	EI-M103	56	EVC/FGX	48
DT5/50	13	EJA	47	EVD	48
DT5/65	13	EJG	48,53	EVR	48,51
DT50/30/RS	14	EJL	48,50	EVW	48,50
DT50/35/RS	14	EJM	48	EXN	19
DT50/41/RS	14	EJV	48,50	EXN-BLACK	19
DT50/50/RS	14	EJY	48,56	EXN-FG	19
DT50/65/RS	14	EKB	48,53	EXN-FG-24V	19
DT55/30/RS	14	EKD	48,53	EXN-FG-GU10-130V	20
DT55/35/RS	14	EKE	48	EXN-SILVER	19
DT55/41/RS	14	EKP/ENA	48	EXR	48
DT55/50/RS	14	EKZ	48	EXR/5	48
DT55/65/RS	14	EL-12B	56	EXT	19
DT7/27	13	EL-1B	56	EXT-FG	19
DT7/35	13	EL-2B	56	EXT-FG-24V	19
DT7/41	13	EL-38	56	EXV	48
DT7/50	13	EL-3B	56	EXY	48
DT7/65	13	ELB	48	EXZ	19
DT9/27	13	ELC	48,50	EXZ-BLACK	19
DT9/35	13	ELC/5	48	EXZ-FG	19
DT9/41	13	ELC/5H	48,53	EXZ-SILVER	19
DT9/50	13	ELC/E	48,50	EYA	48,50
DT9/65	13	ELD/EJN	48	EYB	48
DTA	47,52	ELE	48	EYB/5	48
DTJ	47,52	ELH	48,50	EYC	19
DVS	47,52	ELH/5	48	EYC-FG	19
DVY	47	EMD	48,53	EYF	19
DWT	47,52	EMM/EKS	48	EYF-FG	19
DXW	47,52	ENG	48	EYH/FKT	48
DXX	47,52	ENH	48,50	EYJ	19
DYH	47	ENL	19	EYJ-FG	19
DYR	47	ENX	48	EYK	48
DYS/DYV/BHC	47	ENX/5	48	EYP	19
DYS/DYV/BHC/5	47	ENZ	48	EYP-FG	19
DYY/EGH	47	EPN	48	EYR	19
DZA	47	EPT	48	EYR-FG	19
DZE/FDS	47	EPZ	48	EYS	19
E		ESA/FHD	56	EYS-FG	19
E37	37	ESB/FHE	56	EYV	48
E73	37	ESD	48,50	EYW	48
E85	37	ESD200-SE-D	53	EYX	48
E86	37	ESD250/2-SE-D8.5	53	EZE	48
EAJ	47,50	ESD250-SE-D	53	F	
EBV	47,51	ESD575/2-SE-D7.2	53	F10T8/CW	17
EBV-LN	47,51	ESD575/2-SE-D8.5	53	F13T5/CW	16
EBW	47,51	ESD575-SE-D	53	F13T5/D	16
ECA	47,51	ESH	48	F13T5/WW	16
ECA-LN	47,51	ESI12000-DE	53	F13T8/CW	17
ECT	47,51	ESI1200-DE	53	F14T5/835	15
ECT-LN	47,51	ESI1200-DE-S	53	F14T5/841	15
EFM	47	ESI2500-DE	53	F14T5/865	15
EFN	47	ESI4000-DE	53	F14T8/CW	17
EFP	47	ESI575-DE	53	F14T8/D	17
EFR	47	ESI6000-DE	53	F15T8/BL	17
EGC	47,52	ESJ	48,50	F15T8/BLB	17
EGE	47,52	ESL	48,50	F15T8/CW	17
EGF	47,52	ESM	48,50	F15T8/D	17
EGG	47,52	ESN	48,51	F15T8/W	17
EGJ	47,52	ESP	48,51	F15T8/WW	17
EGK	47,52	ESR	48,51	F17T8/730K	17
EGN	47,52	ESR1200-SE-HR	53	F17T8/735K	17
EGR	47,52	ESR1200-SE-NHR	53	F17T8/741K	17
EGT	47,52	ESR200-SE-HR	53	F17T8/830K	17
EHA	47	ESR2500-SE-HR	53	F17T8/835K	17
EHC/EHB	47,52	ESR400-SE-HR	53	F17T8/841K	17
EHD	47,52	ESR400-SE-NHR	53	F17T8/850K	17
EHF	47,52	ESR575-SE-HR	53	F21T5/835	15
EHG	47,52	ESR575-SE-NHR	53	F21T5/841	15
EHJ	47	ESR800-SE-HR	53	F24T5/HO/835	15
EHM	47,52	ESS	48,51	F24T5/HO/841	15
EHP	47,52	ESX	19	F25T8/830K	15,17
EHR	47,52	ESX-FG	19	F25T8/835K	15,17
EHT	47,50	ESY	48	F25T8/841K	15,17
EHZ	47,53	ETB	48,51	F28T5/835	15

F28T5/841	15	FDV	49	G36T5/4P	54
F28T5/850	15	FEL	49,53	G36T5L	54
F28T5/865	15	FEP	49,53	G40T10	54
F28T8/830/ES	16,17	FEV	49	G4T5	54
F28T8/835/ES	16,17	FEY	49,53	G55T8	54
F28T8/841/ES	16,17	FFJ	49,50	G64T5/4P	54
F28T8/850/ES	16,17	FFN	49,53	G64T5L	54
F28T8/865/ES	16,17	FFP	49,53	G6T5	54
F31T8/830/U	18	FFR	49,53	G8T5	54
F31T8/835/U	18	FFS	49,53	GBD	20
F31T8/841/U	18	FFT	49,53	GBE	20
F31T8/850/U	18	FHM	49,53	GBF	20
F32T8/735K	17	FHS	49	GBF-FR	20
F32T8/741K	17	FKW	49,53	GBJ	20
F32T8/830/ES/25W	16,17	FLK	49,53	GBK	20
F32T8/830K	17	FLT	49	GCA	49
F32T8/830K/HL	16,17	FLW	49	GDA	49,53
F32T8/830K/XL	16	FML18/65	15	GLA	49,53
F32T8/835/ES/25W	16,17	FML27/27	15	GLC	49,53
F32T8/835K	17	FML27/41	15	GTL-2	54
F32T8/835K/HL	16,17	FML27/65	15	GTL-3	54,56
F32T8/835K/U6	18	FMT	19	H	
F32T8/835K/XL	16	FMT-FG	19	H1042	42
F32T8/841/ES/25W	16,17	FMV	19	H1042-BP	42
F32T8/841K	17	FMV-FG	19	H1042CVSU2	39
F32T8/841K/HL	16,17	FMW	19	H1042CVSU-BP	39
F32T8/841K/U6	18	FMW-BLACK	19	H1042PVP2	40
F32T8/841K/XL	16	FMW-FG	19	H1042PVP-BP	40
F32T8/850/ES/25W	16,17	FMW-FG-GU10-130V	20	H1155	42
F32T8/850K	17	FMW-SILVER	19	H1155-BP	42
F32T8/850K/HL	16,17	FNC-FG	19	H1155CVSU2	39
F32T8/850K/U6	18	FND-FG	19	H1155CVSU-BP	39
F32T8/850K/XL	16	FNE-FG	19	H1155CVXL2	39
F32T8/865/ES/25W	16,17	FNF-FG	19	H1155CVXL-BP	39
F32T8/865K	17	FNT	49	H1155LL	42
F32T8/865K/HL	16,17	FNV	19	H1155LL-BP	42
F32T8/865K/XL	16	FNV-FG	19	H1155PVP2	40
F35T5/830	15	FPA	19	H1155PVP-BP	40
F39T5/HO/835	15	FPA-FG	19	H1156	37,42
F39T5/HO/841	15	FPB	19	H1156-BP2	37,42
F49T5/HO/835	15	FPB-FG	19	H1157	37,43
F49T5/HO/841	15	FPC	19	H1157-BP	43
F49T5/HO/850	15	FPC-FG	20	H11B	42
F49T5/HO/865	15	FRA-FG	20	H11B-BP	42
F4T5/BL	16	FRK	49,53	H11BCVSU2	39
F4T5/BLB	16	FS-2	18	H11BCVSU-BP	39
F4T5/CW	16	FS-4	18	H11BPVP2	40
F4T5/D	16	FS-5	18	H11BPVP-BP	40
F54T5/HO/830	16	FSA	20	H1253	43
F54T5/HO/835	16	FSB	20	H1253-BP	43
F54T5/HO/841	16	FSC	20	H155CVSU2	39
F54T5/HO/850	16	FSD	20	H155CVSU-BP	39
F54T5/HO/865	16	FSE	20	H155PVP2	40
F6T5/BL	16	FSF	20	H155PVP-BP	40
F6T5/BLB	16	FS-U-120V	18	H21W	37
F6T5/CW	16	FTA	19	H33CD-400	9
F6T5/D	16	FTB	19	H33GL-400/DX	9
F6T5/WW	16	FTB-FG	19	H355CVSU2	39
F8T5/BL	16	FTC	19	H355CVSU-BP	39
F8T5/BLB	16	FTC-FG	19	H355PVP2	40
F8T5/CW	16	FTD	19	H355PVP-BP	40
F8T5/D	16	FTD-FG	19	H37KB-250	9
F8T5/W	16	FTE	19	H37KC-250/DX	9
F8T5/WW	16	FTE-FG	19	H38AV-100/DX	9
FAD	48,53	FTF	19	H38JA-100/DX	9
FAL	48,50	FTF-FG	19	H38MP-100/DX	9
FBG/FBD	48	FTH	19	H39KB-175	9
FC12T9/CW	18	FTH-FG	19	H39KC-175/DX	9
FC12T9/D	18	FTK	49,53	H3C	42
FC16T9/CW	18	FXL	49	H4351	45
FC16T9/D	18	FXL/5	49	H4352	45
FC8T9/CW	18	G		H43AV-75/DX	9
FC8T9/D	18	G10T5/4P	54	H4651	45
FCB	48	G10T5L	54	H4651CVXL	39
FCL	48,53	G10T8	54	H4656	45
FCM	48,53	G11T5	54	H4656CVXL	45
FCR	48,56	G14T5/4P	54	H4656PVP	40,45
FCS	48,56	G15T8	54	H4666	45
FCZ	48,53	G16T5	54	H4666CVXL	45
FDB	48,53	G20T10	54	H4666PVP	45
FDG	49,53	G20T5	54	H46DL-40/50/DX	9
FDN	49,53	G25T8	54	H4701	45
FDT	49	G30T8	54	H4703	45

H5001	45	JC12V20WH20	22	LED-120-MB-Y	6
H5006	45	JC12V30W	21	LED-120-PSB-G	6
H6024	45	JC12V30WH20	22	LED-120-PSB-R	6
H6024CVXL	39	JC12V35WH20	22	LED-120-PSB-W	6
H6024PVP	40	JC12V50WH20	22	LED-120-PSB-Y	6
H6054	45	JC12V5W-FR	21	LED-12-DCBAY-R	5
H6054CVXL	45	JC12V75WH20	22	LED-12-DCBAY-W	5
H6054HO/H6554	45	JC24V300W	49	LED-12-FESTOON-W	6
H6054PVP	40,45	JCD12V10WH20	21	LED-12-SCBAY-R	6
H7/70W/24V	42	JCD12V20WH20	21	LED-12-SCBAY-W	6
H7100	42	JCD12V35WH20	21	LED-14-BA9S-G	6
H7100-BP	42	JCD12V5WH20	21	LED-14-BA9S-R	6
H7100-SUPER WHITE	42	JCD130V100WG8	22	LED-14-BA9S-W	6
H7100-SUPER WHITE-BP	42	JCD130V20WG6.35	22	LED-14-T1.75 WEDGE-W	6
H755	42	JCD130V20WG8	22	LED-194-R	6
H7550	45	JCD130V25WG6.35	22	LED-194-W	6
H755-BP	42	JCD130V25WG8	22	LED-24-BA9S-G	6
H755CVSU2	39	JCD130V25WG9	22	LED-24-BA9S-R	6
H755CVSU-BP	39	JCD130V25WG9/F	22	LED-24-BA9S-W	6
H755CVXL2	39	JCD130V35WG6.35	22	LED-24-BA9S-Y	6
H755CVXL-BP	39	JCD130V35WG8	22	LED-24-FESTOON-W	6
H755LL	42	JCD130V40WG9	22	LED-24-MF-R	6
H755LL-BP	42	JCD130V40WG9/F	22	LED-24-MF-W	6
H755PVP2	40	JCD130V50WG6.35	22	LED-24-MF-Y	6
H755PVP-BP	40	JCD130V50WG8	22	LED-24-MG-R	6
H755SWTX	42	JCD130V50WG9	22	LED-24-MG-W	6
H7600	45	JCD130V50WG9/F	22	LED-24-MG-Y	6
H7604	45	JCD130V60WG9	22	LED-24-PSB-G	6
H7606	45	JCD130V60WG9/F	22	LED-24-PSB-R	6
H7609	45	JCD130V75WG6.35	22	LED-24-PSB-W	6
H7610	45	JCD130V75WG8	22	LED-24-PSB-Y	6
H7614	45	JCD130V75WG9	22	LED-24-T1.75 WEDGE-G	6
H7616	45	JCD130V75WG9/F	22	LED-24-T1.75 WEDGE-R	6
H7619	45	JCD24V20WH20	21	LED-24-T1.75 WEDGE-W	6
H7635	45	JCD6V10WH20	21	LED-24-T1.75 WEDGE-Y	6
H7921-1	45	JCD6V20WH20	21	LED-6-BA9S-W	5
H7935-1	45	JCR/M12V100W	49	LED-6-T1.75 WEDGE-Y	5
H835	42	JCR/M12V75W	49	LED-6-T1.75 WEDGE-Y	5
H835-BP	42	JCR/M14V35W	49	LEDP/PAR30LN-SP-30K	5
H9405	45	JCR120V150WB	49	LEDP-11WPAR38/FL/830-DIM	5
H9406	45	JDR100/FL	20	LEDP-11WPAR38/FL/840-DIM	5
H9411	45	JDR100/MF	20	LEDP-11WPAR38/SP/830-DIM	5
H9414	45	JDR130V50W	20	LEDP-11WPAR38/SP/840-DIM	5
H9415	45	JDR75/FL	20	LEDP-11WR30/827-DIM	4
H9420	45	JDR75/MF	20	LEDP-11WR30/830-DIM	4
H9421	45	JDR75/SP	20	LEDP-11WR30/GU24/827-DIM	4
H965	42	JF02XE	37	LEDP-11WR30/GU24/830-DIM	3
H965-BP	42	JF03XE	37	LEDP-12WA19/827-DIM	3
HM201	44	JF07XE	37	LEDP-12WA19/830-DIM	3
HM202	44	JF135100XE	37	LEDP-1383/30K	6
HPL375/115V	49,51	JF13XE	37	LEDP-1383/41K	6
HPL375LL/115V	49,51	JF14XE	37	LEDP-13WPAR30/FL/827-DIM	3
HPL550/77V	49,51	JF14XE/F	37	LEDP-13WPAR30/FL/830-DIM	3
HPL550LL/77V	49,51	JF17XE	37	LEDP-13WPAR30/FL/841-DIM	3
HPL575/115V	49,51	JF260050XE	37	LEDP-13WPAR30/NFL/827-DIM	3
HPL575/120V	49,51	K		LEDP-13WPAR30/NFL/830-DIM	3
HPL575/230V	49,51	K12	37	LEDP-13WPAR30/NFL/841-DIM	3
HPL575/240V	49,51	K15	37	LEDP-13WPAR30/NFL/841-DIM	3
HPL575LL/115V	49,51	K222	37	LEDP-14T8/36/41K	2
HPL575LL/120V	49,51	KK10XE	37	LEDP-14T8/36/50K	2
HPL575LL/230V	49,51	KL20XE	37	LEDP-15WBR30/827-DIM	4
HPL575LL/240V	49,51	KL23XE	37	LEDP-15WBR30/830-DIM	4
HPL750/115V	49,51	KO10XE	37	LEDP-15WPAR30/FL/827-DIM	3
HPL750/120V	49,51	KO10XE/F	37	LEDP-15WPAR30/FL/830-DIM	3
HPL750/230V	49,51	KO16XE	37	LEDP-15WPAR30/FL/841-DIM	3
HPL750/240V	49,51	KO16XE/F	37	LEDP-15WPAR30/NFL/827-DIM	3
HPL750/77V	49,51	KO20XE	37	LEDP-15WPAR30/NFL/841-DIM	3
HPL750LL/115V	49,51	KO20XE/F	37	LEDP-18T8/36/41K	2
HPL750LL/120V	49,51	KO23XE	37	LEDP-18T8/36/50K	2
HPL750LL/230V	49,51	KO23XE/F	37	LEDP-15WBR30/827-DIM	4
HPL750LL/240V	49,51	KPR102	37	LEDP-15WBR30/830-DIM	4
HPR36	37	KPR103	37	LEDP-15WPAR30/FL/827-DIM	3
HPR40	37	KPR118	37	LEDP-15WPAR30/FL/830-DIM	3
HPR44	37	KPR13	37	LEDP-15WPAR30/FL/841-DIM	3
HPR50	37	KPR2	37	LEDP-15WPAR30/NFL/827-DIM	3
HPR51	37	KPR2-BP	37	LEDP-15WPAR30/NFL/830-DIM	3
HPR51-BP	37	KPR3	37	LEDP-15WPAR30/NFL/841-DIM	3
HPR52	37	KPR4	37	LEDP-18T8/48/30K	2
HPR53	37	L		LEDP-18T8/48/41K	2
HPR55	37	LED-120-MB-G	6		
J		LED-120-MB-R	6		
JC12V100WH20	22	LED-120-MB-W	6		
JC12V20W	21				

LEDP-18T8/48/50K	2	LEDP-9X3WPAR38/15D/41K/C/DIM	5	MP70/U/MED/4K	7,8
LEDP-18T8U6/41K	2	LEDP-9X3WPAR38/45D/41K/C/DIM	5	N	
LEDP-18T8U6/50K	2	LEDP-T848-SS15AC-30K	5	NE51H-R	37
LEDP-2.5G25/830	4	LEDP-T848-SS15AC-41K	5	NE51-R	37
LEDP-20WPAR38/FL/827-DIM	3	LU100	9	P	
LEDP-20WPAR38/FL/830-DIM	3	LU100/MED	9	P129362-228	56
LEDP-20WPAR38/FL/841-DIM	3	LU1000	9	P21/5W	37
LEDP-20WPAR38/NFL/827-DIM	3	LU150/100	9	P25-1	37
LEDP-20WPAR38/NFL/830-DIM	3	LU150/55	9	PAR20/9/30K	11
LEDP-20WPAR38/NFL/841-DIM	3	LU150/55/D/MED	9	PAR20/9/35K	11
LEDP-22T8/60/41K	2	LU150/55/MED	9	PAR20/9/41K	11
LEDP-22T8/60/50K	2	LU200	9	PAR20/9/50K	11
LEDP-24T8/72/41K	2	LU250	9	PAR30LN/15/30K	11
LEDP-24T8/72/50K	2	LU250/D	9	PAR30LN/15/35K	11
LEDP-2B11/830	4	LU35/MED	9	PAR30LN/15/41K	11
LEDP-2G16.5/830	4	LU400	9	PAR30LN/15/50K	12
LEDP-3.5WB11/827-DIM	4	LU50	9	PAR38/23/27K	12
LEDP-3.5WB11/830-DIM	4	LU50/MED	9	PAR38/23/30	12
LEDP-3W/MR16/830	5	LU600	9	PAR38/23/35K	12
LEDP-4W/GU10/FL/830	5	LU70	9	PAR38/23/41K	12
LEDP-5PAR20/FL/830-DIM	4	LU70/D/MED	9	PAR38/23/50K	12
LEDP-5PAR20/FL/840-DIM	4	LU70/MED	9	PC119	38
LEDP-5PAR20/SP/830-DIM	4	M		PC168	38
LEDP-5PAR20/SP/840-DIM	4	MH100/C/U/MED	6,7	PC168-BP	38
LEDP-5WB11/827-DIM	4	MH100/U/MED	6,7	PC194	38
LEDP-5WB11/830-DIM	4	MH1000/C/U	7	PC194-BP	38
LEDP-6WGU10/830-DIM	4	MH1000/U	7	PC37	37
LEDP-6WMMR16/827-DIM	4	MH1000/UTBT37	7	PC37-BP	37
LEDP-6WMMR16/830-DIM	4	MH150/C/U/MED	6,7	PC74	37
LEDP-6WPAR16/FL/830-DIM	2	MH150/U/MED	6,7	PC74-BP	38
LEDP-6WPAR16/FL/841-DIM	2	MH1500/U	7	PH/111A	49,50
LEDP-7WPAR20/FL/827-DIM	2	MH175/C/U	6	PH/140	49,50
LEDP-7WPAR20/FL/830-DIM	2	MH175/C/U/MED	6	PH/211	49,50
LEDP-7WPAR20/FL/841-DIM	2	MH175/U	6	PH/212	49,50
LEDP-7WPAR20/NFL/827-DIM	2	MH175/U/MED	6	PM-2X32T8-UNV-IS	2
LEDP-7WPAR20/NFL/830-DIM	2	MH200/C/U	7	PM-2X32T8-UNV-IS-H	2
LEDP-7WPAR20/NFL/841-DIM	2	MH200/U	7	PM-2X32T8-UNV-IS-L	2
LEDP-7WPAR20/NFL/827-DIM	2	MH250/BU/PS	7	PM-2X54T5-UNV-PS	2
LEDP-7WPAR20/NFL/830-DIM	2	MH250/C/U	7	PM-3X32T8-UNV-IS	2
LEDP-7WPAR20/NFL/841-DIM	2	MH250/U	7	PM-3X32T8-UNV-IS-H	2
LEDP-7WPAR20/NFL/827-DIM	2	MH250/U/T15	7	PM-3X32T8-UNV-IS-L	2
LEDP-7WPAR20/NFL/830-DIM	2	MH320/U	7	PM-4X32T8-UNV-IS	2
LEDP-7WPAR20/NFL/841-DIM	2	MH350/C/HOR	7	PM-4X32T8-UNV-IS-L	2
LEDP-7WPAR20/NFL/827-DIM	2	MH350/HOR	7	PM-4X54T5-UNV-PS	2
LEDP-7WPAR20/NFL/830-DIM	2	MH400/BU/PS	7	PR12	38
LEDP-7WPAR20/NFL/841-DIM	2	MH400/C/BU/PS	7	PR12-BP	38
LEDP-7X2WPAR30/15D/41K/C/DIM	5	MH400/C/U	7	PR13	38
LEDP-8WA19/827-DIM3	3	MH400/C/U/ED28	7	PR13-BP	38
LEDP-8WA19/830-DIM	4	MH400/U	7	PR15	38
LEDP-8WA19/830-DIM3	3	MH400/U/ED28	7	PR16	38
LEDP-8WA19/840-DIM	4	MH400/U/T15	7	PR18	38
LEDP-8WA19/841-DIM3	3	MH50/C/U/MED	6,7	PR2	38
LEDP-8WG25/827-DIM	4	MH50/U/MED	6,7	PR20	38
LEDP-8WG25/830-DIM	4	MH70/C/U/MED	6,7	PR2-BP	38
LEDP-8WPAR20/FL/827-DIM	2	MH70/U/MED	6,7	PR3	38
LEDP-8WPAR20/FL/830-DIM	2	MH-DE150/TD/UVS/3K	7,8	PR30	38
LEDP-8WPAR20/FL/841-DIM	3	MH-DE150/TD/UVS/4K	7,8	PR3-BP	38
LEDP-8WPAR20/NFL/827-DIM	3	MH-DE70/TD/UVS/3K	7,8	PR4	38
LEDP-8WPAR20/NFL/830-DIM	3	MH-DE70/TD/UVS/4K	7,8	PR6	38
LEDP-8WPAR20/NFL/841-DIM	3	MH-SE150/UVS/3K	7,8	PR7	38
LEDP-8WPAR20/NFL/827-DIM	3	MH-SE150/UVS/4K	7,8	PR9	38
LEDP-8WPAR20/NFL/830-DIM	3	MH-SE70/UVS/3K	7,8	PS13W	38
LEDP-8WPAR20/NFL/841-DIM	3	ML-2100	49,51	PSX26W	38
LEDP-8WPAR20/NFL/827-DIM	3	MP100/C/U/MED/3K	7,8	PSY24WSV	38
LEDP-8WPAR20/NFL/830-DIM	3	MP100/C/U/MED/4K	7,8	PSY24WY	38
LEDP-8WPAR20/NFL/841-DIM	3	MP100/U/MED/3K	8	Q	
LEDP-8WPAR20/NFL/827-DIM	3	MP100/U/MED/4K	8	Q100/DC-120V	20
LEDP-9T8/24/41K	2	MP150/C/U/MED/3K	8	Q100/MC-120V	20
LEDP-9T8/24/50K	2	MP150/C/U/MED/4K	8	Q1000T3/CL/120V	21
LEDP-9WPAR30/FL/830-DIM	5	MP150/U/MED/3K	8	Q1000T3/CL/220V	21
LEDP-9WPAR30/FL/840-DIM	5	MP150/U/MED/4K	8	Q1000T3/CL/240V	21
LEDP-9WPAR30/SP/830-DIM	5	MP250/BU/P	8	Q1000T3/CL/277V	21
LEDP-9WPAR30/SP/840-DIM	5	MP320/BU	8	Q100CL/DC/2V-120V	20
LEDP-9X3WPAR38/15D/30K/C/DIM	5	MP350/BU	8	Q100CL/DC/2V-130V	20
		MP400/BU/ED28/P	8	Q100CL/MC/2V-120V	20
		MP400/BU/P	8	Q100CL/MC/2V-130V	20
		MP50/U/MED/3K	7,8	Q100CL/MC-120V	20
		MP70/C/U/MED/3K	7,8	Q100DC/2V-120V	20
		MP70/C/U/MED/4K	7,8	Q100MC/2V-120V	20
		MP70/U/MED/3K	8	Q100T3/CL/120V	21
				Q100W/S120V	21

Q100W/S130V	21	QT18/35	14	SP23/R40/41K	12
Q10MR8/NSP/CG	18	QT18/35-4P	14	SP23/R40/41K-DIM	12
Q1500T3/CL/120V	21	QT18/41	14	SP23/R40/50K-DIM	12
Q1500T3/CL/208V	21	QT18/41-4P	14	SP23/R40/65K	12
Q1500T3/CL/220V	21	QT18/50	14	SP26/27-4P	15
Q1500T3/CL/240V	21	QT18/50-4P	14	SP26/27-GU24	11
Q1500T3/CL/277V	21	QT26/27	14	SP27/27K	10
Q150CL/DC-120V	20	QT26/27-4P	14	SP27/35K	10
Q150CL/DC-130V	20	QT26/30	14	SP27/41K	10
Q150CL/MC/2V-130V	20	QT26/30-4P	14	SP27/50K	10
Q150CL/MC-120V	20	QT26/35	14	SP30/955K	54
Q150CL/MC-130V	20	QT26/35-4P	14	SP32/27K	10
Q150DC-120V	20	QT26/41	14	SP32/35K	10
Q150MC-120V	20	QT26/41-4P	14	SP32/41K	10
Q150T3/CL/120V	21	QT26/50	14	SP32/50K	10
Q150T4/CL/25	49	QT26/50-4P	14	SP42/27K	10
Q150W/S120V	21	QT26/65	14	SP42/35K	10
Q150W/S130V	21	QT26/65-4P	14	SP42/41K	10
Q200W/S120V	21	QT9/27	14	SP42/50K	10
Q200W/S130V	21	QT9/35	14	SP50/955K	54
Q200W/S220V	21	QT9/41	14	SP5B10/E12/27K	13
Q20MR8/NFL/CG	18			SP5B10/E12/41K	13
Q20MR8/NSP/CG	18	S		SP5B13/E26/27K	13
Q235T4/3-33V	56	SE1274	38	SP5B13/E26/41K	13
Q250CL/DC-120V	20	SE1274-BP	38	SP65/41/MED	9,10
Q250CL/DC-130V	21	SP105/41/MED	9,10	SP65/50/MED	9,10
Q250CL/MC-120V	21	SP105/41/MOG	9,11	SP7B10/E12/27K	13
Q250CL/MC-130V	21	SP105/41/MOG-277V	9,11	SP7B10/E12/41K	13
Q250DC-120V	21	SP105/50/MED	9,10	SP85/41/MED	9,10
Q250DC-130V	21	SP11A/27K-GU24	12	SP85/50/MED	9,10
Q250MC-120V	21	SP13/27-4P	15	SP9A19/27K	12
Q250MC-130V	21	SP13/27-GU24	11	SP9A19/41K	12
Q250T3/CL/120V	21	SP13/27K	10	SP9G25/27K	13
Q250W/S120V	21	SP13/27K-DIM	10	SP9G25/41K	13
Q300T3/CL/120V	21	SP13/27K-GU24-DIM	11		
Q300T3/CL/130V	21	SP13/35K	10	T	
Q300T3/CL/220V	21	SP13/41-GU24	11	T5ES-28115/835	9
Q300T3/CL/240V	21	SP13/41K	10	T5ES-28115/841	9
Q300W/S120V	21	SP13/41K-DIM	10	T5ES-28115/850	9
Q300W/S130V	21	SP13/50K	10	TT18/27	15
Q35MR8/NFL/CG	18	SP13/65K	10	TT18/30	15
Q35MR8/NSP/CG	18	SP13A19/27K	12	TT18/35	15
Q400W/S130V	21	SP13A19/41K	12	TT18/41	15
Q500/MC-120V	21	SP13G25/27K	13	TT18/65	15
Q500/MC-130V	21	SP13G25/41K	13	TT26/27	15
Q500CL/DC-120V	21	SP14/R20/27K	12	TT26/30	15
Q500CL/DC-130V	21	SP14/R20/41K	12	TT26/35	15
Q500CL/MC-120V	21	SP15/R30/27K	12	TT26/41	15
Q500CL/MC-130V	21	SP15/R30/27K-DIM	10,12	TT26/50	15
Q500DC-120V	21	SP15/R30/27K-GU24	12	TT26/65	15
Q500T3/CL/120V	21	SP15/R30/41K	12	TT32/27	15
Q500T3/CL/130V	21	SP15/R30/41K-DIM	11,12	TT32/30	15
Q500T3/CL/220V	21	SP15/R30/50K-DIM	11,12	TT32/35	15
Q500T3/CL/240V	21	SP15/R30/65K	12	TT32/41	15
Q50CL/DC-130V	20	SP15/R30/65K-DIM	11,12	TT32/50	15
Q50CL/MC-130V	20	SP15A/27K-GU24	12	TT32/65	15
Q750T3/CL/120V	21	SP15G25/27K	13	TT42/27	15
Q750T3/CL/240V	21	SP15G25/27K-GU24	13	TT42/30	15
Q75CL/DC-120V	20	SP15G25/41K	13	TT42/35	15
Q75CL/DC-28V	49	SP18/27-4P	15	TT42/41	15
Q75CL-120V	20	SP18/27-GU24	11	TT42/50	15
Q75CL-130V	20	SP18/27K-GU24-DIM	11	TT42/65	15
Q75CL-28V	49	SP18/41-GU24	11		
Q75MC-120V	20	SP180/41/MOG	9,11	W	
QT13/27	14	SP180/50/MOG	9,11	WK101	50
QT13/27-4P	14	SP19/27K	10	WK120HD	50
QT13/30	14	SP19/27K-DIM	11	WK120HD-UV	50
QT13/30-4P	14	SP19/35K	10	WK140HD	50
QT13/35	14	SP19/41K	10	WK140HD-UV	50
QT13/35-4P	14	SP19/41K-DIM	11	WK76	49,50
QT13/41	14	SP19/50K	10	WK76-UV	49,50
QT13/41-4P	14	SP19/65K	10	WK92	50
QT13/50	14	SP23/27-GU24	11	WK92-UV	50
QT13/50-4P	14	SP23/27K	10	WK93	50
QT13/65	14	SP23/27K-DIM	11	WK94	50
QT13/65-4P	14	SP23/27K-GU24-DIM	11	WK95	50
QT13/G24D1/30	14	SP23/35K	10	WK96	50
QT13/G24D1/35	14	SP23/41-GU24	11	WK96-UV	50
QT13/G24D1/50	14	SP23/41K	10	WK98	50
QT13/G24D1/65	14	SP23/41K-DIM	11	WK98-UV	50
QT18/27	14	SP23/50K	10		
QT18/27-4P	14	SP23/65K	10	X	
QT18/30	14	SP23/R40/27K	12	XPR3	38
QT18/30-4P	14	SP23/R40/27K-DIM	12		

TERMS, CONDITIONS & SHIPPING PROCEDURES

Effective: January 15th, 2013.

Supersedes all past terms and conditions of Price books and Sales Supplements.

Prices: As Shown and subject to change without notice.

Distributor Status: Distributors must purchase a minimum of \$2500 annually in order to maintain distributor status.

Small Order Charge: Orders under \$150.00 will be assessed a \$10.00 small order charge (SOC).

Payment Terms: Net 30 days, from date of shipment as it appears on invoice. Postmark date on envelope will determine if payment has been made within terms. All orders received are subject to review and approval by our credit department. Orders received from customers with delinquent accounts may be subject to shipping delays, so please keep your account current.

Freight: NOTE: SoLux and EiKO products may be combined to meet prepaid freight requirements. EiKO Ltd. will select the carrier of its choice.

1. All orders of \$750.00 or more will be shipped FREE FREIGHT F.O.B. destination via regular ground UPS, FedEx or USPS within the continental United States. Orders less than \$750.00 will be shipped F.O.B. origin.
2. UPS Second Day Air Blue – At the request of the distributor, orders will be billed at the UPS Second Day Air Rate.
3. UPS Next Day Air Red Label – At the request of the distributors, orders will be billed at the UPS Red Label Air rate.
4. Shipments made at the choice of the distributors, other than above, will be shipped F.O.B. shipping point.
5. Additional charges will apply for residential delivery.
6. **Alaska, Hawaii and Puerto Rico** – Orders of \$1,000.00 or more will be shipped free freight F.O.B. to a freight forwarder.
7. EiKO will no longer ship freight collect using the customer's account number.

We will cover the above items under normal Continental United States Policy. Therefore, you can achieve free freight to a border destination and then pick up the expense of forwarding the freight to your destination in Alaska, Hawaii or Puerto Rico. As an example, if you are a customer in Hawaii, you can have the goods for orders over \$1000.00 shipped free freight to a freight forwarder. It would then be your responsibility to cover the freight to Hawaii.

Return Authorization:

1. You must contact EiKO, Ltd. for authorization to return defective products and shipment errors.
 2. Return authorization will not be issued unless the distributor provides a **valid invoice number** showing when goods were purchased. A copy of this invoice must be included with the return.
 3. **Goods must be less than one year old to be eligible for return.**
 4. Where the request for return is neither defective merchandise nor error made by EiKO, Ltd., the following policy will apply: A restocking charge of 20% will be charged on all authorized and acceptable goods. If goods are not returned in resalable condition they will be returned to the sender at the expense of the sender and no credit will be issued.
- NOTE: All returns must have a return number on the outside of the box or they will be refused.

Shipment Discrepancies: All shipment discrepancies, damage, etc, must be reported within 10 days of the shipment date shown on the invoice.

General: We reserve the right to, at any time and without notice, discontinue or substitute brands.

Minimum Order Requirements for Linear Fluorescent Lamps: In order to avoid breakage, the minimum order quantity for T8 & T12 linear fluorescent lamps four feet or longer is 360. The minimum order quantity for programmed start T5 linear fluorescent lamps is 100. Mixing SKUs to meet the minimum order is allowed. Orders under \$750 will be charged \$70 LTL freight.

***Important Note About Minimum Advertised Pricing (MAPP):** In order to avoid predatory pricing and to maintain the integrity of the products, SoLux products purchased through EiKO, Ltd. may not be advertised for sale (Internet, electronic, print media, mailings or otherwise) by you, a sub-distributor or any other agent, below the minimum advertised price established in the current Distributor Net Price Schedule. This minimum advertised price will be known as and referred to as the MAPP price. Failure to comply with MAPP pricing requirements will result in the loss of your access to SoLux products.

EiKO Ltd: 23220 W. 84TH St., Shawnee, KS 66227 • Ph: 1.800.852.2217 • Fax: 1.913.441.6679 • Email: eiko@eiko.com
EiKO CANADA: 81 King St., Barrie, Ontario L4N 6B5, Canada • Ph: 1.705.721.5189 • Fax: 1.705.721.7855

www.eiko.com

GENERAL LIGHTING LIMITED WARRANTY.

EiKO brand lamps are warranted to be free of defective materials and workmanship for the period listed below. EiKO will replace or credit the distributor only for the cost of any lamp that fails under normal operating conditions and the use and operation conditions below due to defective materials or workmanship.

This warranty is limited to the replacement or credit of the lamp itself. This is buyer's exclusive remedy. Any other warranty, express or implied, including any warranty of merchantability or fitness for a particular purpose, is excluded and disclaimed. EiKO shall not be liable for any special, incidental or consequential damage including labor, loss of use, lost profits or injury to persons or property.

EiKO reserves the right to examine all lamps prior to the determination of warranty status. All lamps must be retained for warranty claims. The warranty period starts on the date of installation. If the date of installation is unknown or undetermined the warranty period will start at the wholesale purchase date.

Lamp Category	Warranty Period
Metal Halide, High-Pressure Sodium, Mercury Vapor	15 months
Compact Fluorescent	12 months
Self Ballasted Compact Fluorescent	12 months
Linear Fluorescent (below 14 watt)	12 months
Linear Fluorescent (14 watt and above)	24 months
LED	36 months
LCD	120 days
LitespanLED® Fixtures	60 months
LitespanLED® Replacement Lamps	60 months

Use and Operating Conditions: Lamps must be used in UL approved fixtures with UL approved ballasts and installed according to local and national codes and standards. Use of occupancy sensors, dimmers or programmable systems with the lamp may void the warranty.

HID Lamps: Warranty is based on 5,000 hours per year maximum operation with a minimum of 8 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.

Fluorescent Lamps: Warranty is based on 4,000 hours per year maximum operation with a minimum of 3 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.

Large Lamps: Warranty is in effect for sales and installations on and after January 1, 2006.

LED: Warranty is in effect for sales and installations on and after November 1, 2008.

LCD: Warranty is in effect for sales and installations on and after July 1, 2009.



EiKO Ltd: 23220 W. 84TH St., Shawnee, KS 66227 • Ph: 1.800.852.2217 • Fax: 1.913.441.6679 • Email: eiko@eiko.com
EiKO CANADA: 81 King St., Barrie, Ontario L4N 6B5, Canada • Ph: 1.705.721.5189 • Fax: 1.705.721.7855

www.eiko.com

HIGH PERFORMANCE FORWARD LIGHTING



CLEAR VISION™ Supreme

+80% Brighter!
+50% Whiter!

Clear Vision Supreme™ premium halogen headlamps feature SoLux™ Technology that produces up to **80% brighter and 50% whiter light**, as well as the longest beam of any DOT legal headlamp.

CLEAR VISION™ XL

+65% Brighter!
+25% Whiter!

Clear Vision XL™ halogen headlamps feature a proprietary coating technology that produces up to **65% brighter and 25% whiter light** for increased depth perception and contrast.



POWER VISION™ PRO

+50% Brighter!
+10% Whiter!

PowerVision PRO™ halogen headlamps feature a high performance tungsten filament that produces up to **50% brighter and 10% whiter light** than the average lamp without sacrificing life.



LITESPANLED®

LED REPLACEMENT LAMPS



LINEAR



PAR



DECORATIVE



R/BR & MR

EiKO's line of **LITESPANLED®** Replacement Lamps represents the next generation in LED lighting, saving you time, energy and money with ultra-high efficiency lighting options!



Global Headquarters

23220 W. 84th Street • Shawnee, KS • 66227
phone: 913-441-8500 • toll-free: 1-800-852-2217
fax: 913-441-6679 • toll-free: 1-800-492-8975
eiko@eiko.com

EiKO Canada

81 King Street • Barrie, Ontario L4N 6B5 • Canada
phone: [1] 705-721-5189
fax: [1] 705-721-7855
orderdesk@eiko.com

EiKO Pacific

Main Office - Taiwan
25F, No. 29-1, Sec. 2 • Zhongzheng E Rd • Danshuei Jen
Taipei, Taiwan ROC
phone: [886] 2-8809-9966
fax: [886] 2-8809-8372
eiko@eiko-ltd.com.tw

Suzhou Office

Room C-915, International Conference Center
No. 1296, Ganjang W. Road • Suzhou, China
Phone: [86]512-6863-9964
Fax: [86]512-6863-9947

EiKO Europe

Mittelwegring 20/23 • 76751 Jockgrim • Germany
phone: [49] 0 7271-7607-0
fax: [49] 0 7271-7607-29
info@eiko-europe.de

EiKO Korea

708-2 Gojan-dong • Danwon-gu, Sam Young Town #606
Ansan City, Gyeonggi Province • Republic of Korea
phone: [82] 31-486-6001
fax: [82] 31-486-4002
eiko@eiko-korea.co.kr

eiko.com