
CATALOG

Floor Boxes

Wire & cable management



**Thomas & Betts is now ABB
Installation Products, but our long
legacy of quality products and
innovation remains the same. From
connectors that wire buildings on
Earth to cable ties that help put
machines in space, we continue to
work every day to make, market,
design and sell products that
provide a smarter, safer and more
reliable flow of electricity, from
source to socket.**

Table of contents

004–012	Overview
013–019	Concrete applications – On grade floors / recessed service
020–031	Concrete applications – On grade floors / flush service
032–038	Concrete applications – On or above grade floors / recessed service
039–053	Concrete applications – On or above grade floors / flush service
054–068	Concrete applications – Above grade floors / recessed service
069–078	Concrete applications – Above grade floors / flush service
079–091	Concrete applications – Fire-rated poke-through
092–097	Concrete applications – Fire-rated poke-through / furniture feed
098–107	Access floor module applications
108–114	Wood floor applications – recessed service
115–127	Wood floor applications – flush service
128–132	Others and accessories
135–141	Index

Floor boxes

The aesthetic and technical needs of today's buildings are as diverse as the equipment that fills them. Small wonder, then, that floor boxes can continue to solve the needs of today and the future as they did in the early 1900s when they were invented. They are still a contemporary, capable and cost-effective wire management system. Steel City®, a pioneer in both the design and applications of floor boxes since 1904, invites you to discover or rediscover the possibilities.


Visit www.tnb.com/floorboxselect to use our online floor box selection tool to quickly and easily identify an appropriate in-floor solution for your needs.



Concrete application – On grade floors


Recessed service

- Material: Cast iron
- Covers: MopTite® 664-CST Series



664-CI (2-gang) - See page 14

- Material: Stamped steel/cast iron
- Covers: MopTite® 665-CST Series



665-CI (2-gang) - See page 17

Concrete application – On grade floors

Flush service

- Material: Cast iron
- Covers: MopTite® P60 Series




600 Series - See page 22

- Material: Stamped steel/cast iron
- Covers: MopTite® P90 Series




78 Series - See page 25

- Material: Cast iron
- Covers: MopTite® P64 Series



640 Series (1-, 2-, 3- & 4-Gang) - See page 29

- Material: Stamped steel/cast iron
- Covers: MopTite® P64 Series



840 Series (1-, 2- & 3-Gang) - See page 29

Concrete application – On or above grade floors


Flush service

- Material: Non-metallic
- Covers: MopTite® P60 & P68 Series



68-P Series - See page 43

- Material: Non-metallic
- Covers: 68-HP Series



68-HP Series - See page 47

- Material: Non-metallic
- Covers: 640HP Series activations with MopTite® P64 Series covers




640P Series (1-, 2- & 3-Gang) - See page 51

Concrete application – On or above grade floors

Recessed service

- Material: Stamped steel
- Covers: P62 and P60 Series



663-SC (2-gang) - See page 55

- Material: Stamped steel
- Covers: MopTite® 664-CST SW Series




664-SC/664-S (2-gang) - See page 57

- Material: Stamped steel/cast iron
- Covers: MopTite® 665-CST-SW Series




665-SC/665-AV2 (4-gang) - See page 60

- Material: Stamped steel
- Covers: MopTite® 667-CST-SW Series



667-SC (8-gang) - See page 64

- Material: Stamped steel
- Covers: MopTite® 668-CST



668-S (4-gang) - See page 66

Concrete application – Above grade floors


Flush service

- Material: Stamped steel
- Covers: MopTite® P60 Series



68 Series - See page 71

- Material: Stamped steel
- Covers: 640P Series activations with MopTite® P64 Series covers



740 Series (1-, 2- & 3-Gang) - See page 74

- Stamped steel
- Covers: MopTite® P90 Series



88 Series - See page 78

Concrete application – On or above grade floors

Poke-through and furniture feed



Flush service - See page 82




Recessed service - See page 89



Furniture feed - See page 93

Access floor module application

- Material: Stamped steel
- Covers: MopTite® covers, assembled



Access floor modules - See page 99

Floor box cover selection guide

Cat. No.	Service capabilities			Floor box body material			Minimum depth of pour					Adjustability					
	Receptacles			Multiple service capabilities	Cast Iron	Stamped Steel	Non-metallic	2"	2½"	3"	3½"	4"	4½"	Wood Floor	Adjustability		
	Single	Duplex	GFCI												Fully-	Semi-	Non-
600-SC							
601-SC							
602-SC								
603-SC								
604-SC			
61-W				
62-W		.	.	2 duplexes, 2 com./data or 1 duplex with com./data		.								.			13/16" adjustment after installation
641	.	.	.	1-gang; 1 service per gang	.							.					.
641P	.	.	.	1-gang; 1 service per gang	.		.										.
642	.	.	.	2-gang; 1 service per gang	.							.					.
642P	.	.	.	2-gang; 1 service per gang	.		.										.
643	.	.	.	3-gang; 1 service per gang	.							.					.
643P	.	.	.	3-gang; 1 service per gang	.		.										.
663-SC	
664-CI		.	.	Two duplexes, two communications/data or one duplex with com./ data	.							.					.
664-S	
664-SC	
665		.	.	Up to 4 devices or any combination of pwr. com./data		.					.						.
665-CI		.	.	Up to 4 devices or any combination of power data	.						.						.
667-SC		.	.	Up to 8 devices or any combination of pwr. com./data		.						.					.
668-S		.	.	Up to 4 devices or any combination of power data		.			.								.
671-SC
672
68-D
68-P	.	.		1 duplex, up to 8 data jacks			.										.
68-S
71-W	
78-S	.								.								.
78-SC	.								.								.
841-SC	.	.	.	1-gang; 1 service per gang	.			.									.
842-SC	.	.	.	2-gang; 1 service per gang	.			.									.
843-SC	.	.	.	3-gang; 1 service per gang	.			.									.
88-S
GAB-8-s								6"			.

Floor box cover selection guide

Floor Box Cat. No.	Description	Cover plates	Carpet activations			Tile activation			Non- metallic
			Brass	Aluminum	Non-metallic	Brass	Aluminum		
663-SC	Concealed service – Steel	P60 Series	P60-CP	P60-CPL	P62-CP	P62-TAR	SP-P62-TAR-A	N/A	
664-SC	Concealed service – Steel	664-CST-M Series	N/A	N/A	664-CST-W Series	N/A	N/A	N/A	
664-S	Shallow concealed service – Steel	664-CST-M Series	N/A	N/A	664-CST-W Series	N/A	N/A	N/A	
664-CI	Concealed service – Cast Iron	664-CST-M Series	N/A	N/A	664-CST-W Series	N/A	N/A	N/A	
68-S	Flush service – Steel	P60 Series	P60-CP P60-CACP	P60-CPAL P60-CACPAL	P60-LCP	*	**	—	
68-D	Flush service – Steel	P60 Series	P60-CP P60-CACP	P60-CPAL P60-CACPAL	P60-LCP	*	**	—	
68-P	Flush service – Non-metallic	P60 Series	P60-CP P60-CACP	P60-CPAL P60-CACPAL	P68-SRC Color P68-DRC-Color P68-ECC-Color	68-PAR-W/ 600-4-FL	68-PAR-W/ 600-4-FL-AL	—	
600-SC Series	Flush service – Cast Iron	P60 Series	P60-CP P60-CACP	C60-CPAL P60-CACPAL	N/A	*	**	—	
601-SC Series	Flush service – Cast Iron	P60 Series	P60-CP P60-CACP	C60-CPAL P60-CACPAL	N/A	*	**	—	
602-SC Series	Flush service – Cast Iron	P60 Series	P60-CP P60-CACP	C60-CPAL P60-CACPAL	N/A	*	**	—	
603-SC Series	Flush service – Cast Iron	P60 Series	P60-CP P60-CACP	C60-CPAL P60-CACPAL	N/A	*	**	—	
604-SC Series	Flush service – Cast Iron	P60 Series	P60-CP P60-CACP	C60-CPAL P60-CACPAL	N/A	*	**	—	
641	Flush service – Cast Iron	P64 Series	P64-CP	P64-CPAL	P64-CP Series P-64-LCP	*	**	N/A	
641P	Flush service – Non-metallic	P64 Series P64P Series	641P-CACB	641P-CACA	641P-CAC Series	641P-TACB	641P-TACA	641P-TAC- Series	
642	Flush service – Cast Iron	P64 Series	P64-2GCP	P64-2GCPAL	P64P-2GCP Series P64-2LCP	*	**	N/A	
642P	Flush service – Non-metallic	P64 Series P64P Series	642P-CACB	642P-CACA	642P-CAC Series	642P-TACB	642P-TACA	642P-TAC Series	
643	Flush service – Cast Iron	P64 Series	P64-3GCP	P64-3GCPAL	P64P-3GCP Series P64-3LCP	*	**	N/A	
643P	Flush service – Non-metallic	P64 Series P64P Series	643P-CACB	643P-CACA	643P-CAC Series	633P-TACB	643P-TACA	643P-TAC Series	
841-SC	Shallow flush service – Cast Iron	P64 Series	P64-CP	P64CPAL	P64P-CP Series P64-LCP	*	**	N/A	
842-SC	Shallow flush service – Cast Iron	P64 Series	P64-2GCP	P64-2GCPAL	P64P-2GCP Series P64-2LCP	*	**	—	
843-SC	Shallow flush service – Cast Iron	P64 Series	P64-3GCP	P64-3GCPA	P64-3GCP Series P64-3LCP	*	**	N/A	
78-SC	Flush service – Cast Iron	P90 Series	P90-CP	P90-CPAL	N/A	*	**	N/A	
78S	Flush service – Cast Iron	P90 Series	P90-CP	P90-CPAL	N/A	*	**	N/A	
671	Flush service – Cast Iron	P67 Series	P90-CP	P90-CPAL	N/A	—	**	N/A	
672	Flush service – Cast Iron	P67 Series	P90-CP	P90-CPAL	N/A	*	**	N/A	
88S	Flush service – Steel	P90 Series	P90-CP	P90-CPAL	N/A	*	**	N/A	
665-SC	Concealed service	665-CST Series	N/A	N/A	665-CST Series	—	—	—	
667	Concealed service	667-M CST Series	N/A	N/A	667-CST-W Series	—	—	—	
61W	Flush service – Steel	P64 Series	P64-CP	P64-CPAL	P64-CP Series	N/A	N/A	N/A	
62W	Flush service – Steel	P64 Series	P64-2GCP	P64-2GCPAL	P64-2GCP Series	N/A	N/A	N/A	

* Supplied standard with box.
 ** Supplied standard with -AL suffix box.
 N/A Not Available.

Floor box cover selection guide

Cover Series	Cover Cat. No.	Description	Standard Finish	
P60 4" Dia.	P-60-1/2	½" N.P.S. plug	Brushed Brass	
	P-60-1/2-AL	½" N.P.S. plug	Brushed Aluminum	
	P-60-3/4	¾" N.P.S. plug	Brushed Brass	
	P-60-3/4-AL	¾" N.P.S. plug	Brushed Aluminum	
	P-60-1	1" N.P.S. plug	Brushed Brass	
	P-60-1-AL	1" N.P.S. plug	Brushed Aluminum	
	P-60-1 1/4	1¼" N.P.S. plug	Brushed Brass	
	P-60-1 1/4-AL	1¼" N.P.S. plug	Brushed Aluminum	
	P-60-2	2" dia. plug	Brushed Brass	
	P-60-2-AL	2" dia. plug	Brushed Aluminum	
	P-60-2 5/8	2⅝" dia. plug	Brushed Brass	
	P-60-2 5/8-AL	2⅝" dia. plug	Brushed Aluminum	
	P-60-1/2-2	½" N.P.S. & 2" dia. plugs	Brushed Brass	
	P-60-1/2-2-AL	½" N.P.S. & 2" dia. plugs	Brushed Aluminum	
	P-60-3/4-2	¾" N.P.S. & 2" dia. plugs	Brushed Brass	
	P-60-3/4-2-AL	¾" N.P.S. & 2" dia. plugs	Brushed Aluminum	
	P-60-DU	Two 1⅞" dia. plugs	Brushed Brass	
	P-60-DU-AL	Two 1⅞" dia. plugs	Brushed Aluminum	
	P-60-DS	Two hinged lift lids	Brushed Brass	
	P-60-DS-AL	Two hinged lift lids	Brushed Aluminum	
	P-60-DR	Single hinged lift lid	Brushed Brass	
		Single hinged lift lid	Brushed Aluminum	
		P-60-GFCI	GFCI hinged lift lid	Brushed Brass
	P60-CACP One-Piece 5½" Dia.	P-60-CACP	One-piece carpet plate with two hinged lift lids for duplex	Brushed Brass
		P-60-CACP-AL	One-piece carpet plate with two hinged lift lids for duplex	Brushed Aluminum
		P-60-CACP-GFCI	One-piece carpet plate with two GFCI hinged lift lids	Brushed Brass
P-60-3/4-2-CACP		One-piece carpet plate with 3⅞" ¾" N.P.S. & 2" Dia. plug	Brushed Brass	
P-60-3/4-2-CACP-AL		One-piece carpet plate with ¾" & 2" N.P.S. plugs	—	
P67 3½" Dia.	P-67-1/2	½" N.P.S. plug	Brushed Brass	
	P-67-3/4	¾" N.P.S. plug	Brushed Brass	
	P-67-3/4-AL	¾" N.P.S. plug	Brushed Aluminum	
	P-67-1	1" N.P.S. plug	Brushed Brass	
	P-67-1AL	1" N.P.S. plug	Brushed Aluminum	
	P-67-1 1/4	1¼" N.P.S. plug	Brushed Brass	
	P-67-2	2" dia. plug	Brushed Brass	
	P-67-2AL	2" dia. plug	Brushed Aluminum	
	P-67-1/2-2	½" N.P.S. & 2" dia. plugs	Brushed Brass	
	P-67-3/4-2	¾" N.P.S. & dia. plugs	Brushed Brass	
P64 3" x 4 ½" Rectangular	P-64-1/2	½" N.P.S. plug	Polished Brass	
	P-64-3/4	¾" N.P.S. plug	Polished Brass	
	P-64-3/4AL	¾" N.P.S. plug	Brushed Aluminum	
	P-64-1	1" N.P.S. plug	Polished Brass	
	P-64-1AL	1" N.P.S. plug	Brushed Aluminum	
	P-64-1 1/4	1¼" N.P.S. plug	Polished Brass	
	P-64-1 1/4AL	1¼" N.P.S. plug	Brushed Aluminum	
	P-64-2	2" N.P.S. plug	Polished Brass	
	P-64-2-AL	2" N.P.S. plug	Brushed Aluminum	
	P-64-1/2-2	½" & 2" N.P.S. plug	Polished Brass	
	P-64-1/2-2AL	½" & 2" N.P.S. plug	Brushed Aluminum	
	P-64-3/4-2	¾" & 2" N.P.S. plug	Polished Brass	
	P-64-3/4-2AL	¾" & 2" N.P.S. plug	Brushed Aluminum	
	P-64-2-5/8	2⅝" N.P.S. plug	Polished Brass	
	P-64-2-5/8AL	2⅝" N.P.S. plug	Brushed Aluminum	
	P-64-DU	Two 1⅞" dia. plugs	Polished Brass	
	P-64-DUAL	Two 1⅞" dia. plugs	Brushed Aluminum	
	P-64-D8	Two Hinged Lift Lids	Polished Brass	
	P-64-GFCI	GFCI Hinged Lift Lid	Polished Brass	
	P64P	P-64P-BP	Blank Plate	Non-metallic
		P-64P-URC	Universal Cover	Non-metallic
		P-90-3/4AL	¾" N.P.S. plug	Brushed Aluminum
		P-90-1AL	1" N.P.S. plug	Brushed Aluminum
		P-90-1 1/4AL	1¼" N.P.S. plug	Brushed Aluminum
	P68 6" Dia.	P-90-2AL	2" dia. plug	Brushed Aluminum
		P-90-1/2-2	½" N.P.S. & 2" dia. plugs	Polished Brass
P-90-3/4-2		¾" N.P.S. & 2" dia. plugs	Polished Brass	
P-90-3/4-2AL		¾" N.P.S. & 2" dia. plugs	Brushed Aluminum	
P-68-SRC-GRY		Carpet & cover plate for single receptacle	Non-metallic Gray	
P-68-SRC-BRN		Carpet & cover plate for single receptacle	Non-metallic Brown	
P-68-SRC-BGE		Carpet & cover plate for single receptacle	Non-metallic Beige	
P-68-FSC-GRY		Carpet & cover plate with 1" N.P.S. plug	Non-metallic Gray	
P-68-FSC-BRN		Carpet & cover plate with 1" N.P.S. plug	Non-metallic Brown	
P-68-FSC-BGE		Carpet & cover plate with 1" N.P.S. plug	Non-metallic Beige	
P-68-DRC-GRY	Carpet & cover plate for duplex receptacle	Non-metallic Gray		
P-68-DRC-BRN	Carpet & cover plate for duplex receptacle	Non-metallic Brown		
P-68-DRC-BGE	Carpet & cover plate for duplex receptacle	Non-metallic Beige		

Standard specification

Flush floor boxes

Cast iron formed steel

Considerations when writing specifications:

Floor boxes are manufactured in various sizes, configurations and materials. The specifier should determine the most suitable product for his application. Refer to the ABB floor box catalog and select the appropriate paragraphs listed below. Plans should supply wiring capacity, conduit sizes, adjustability and floor finish. Construction Specifications Institute (CSI) references sections: 16132 Floor Boxes; 16141 Wiring Devices; Part 2-206 Floor Mounted Service Fittings; and 16741 Telephone Raceway Systems, Part 2-201 G Floor Boxes. Section 16132 Floor Boxes is preferable.

Part 2: Products

2.01 Acceptable manufacturers – Floor boxes

A. Shall be as manufactured by ABB, Memphis, TN

2.02 Materials – Floor boxes

2.02.1

A. Shall be cast iron, painted inside and out with weatherproof paint intended for use on metal as indicated on the plans.

2.02.1

B. Shall be formed steel with a zinc plating at least .0005 in. thick on the outside and .00015 in. thick on the inside as indicated on the plans.

2.02.2

A. Construction shall be as required by UL 514A.

2.02.2

B. Carpet or tile frame shall be (brass, aluminum, polycarbonate, nylon).

2.02.2

C. Cover assembly shall protect against the ingress of water or foreign material with a gasket and shall be UL Listed as moptight.

2.03 General design – Floor boxes

A. Shall deliver electric power from receptacles installed at the surface of the floor or from service fittings (Reference 16141 as shown on the plans).

B. 640/840 Series shall deliver power and telephone/data cable without interference from electric power delivery (see Section 16741).

C. Cubic inch capacity shall be as shown on the plans.

D. Boxes shall accept conduit sizes as required on the plans.

E. Shall be listed by Underwriters Laboratories.

Part 3: Execution

3.01 General

A. Locate position for floor boxes and runs of conduit as shown on the plans.

3.02 Installation

A. Position floor boxes and conduit runs.

B. After concrete pour, pull wires and install devices according to manufacturers recommendations.

C. Activate in accordance with the National Electrical Code®.

D. Coordinate with floor covering contractor to complete installation.

Standard specification

Concealed service

Service floor outlet multiple service, power and communications

Considerations when writing specifications:

The 664 Concealed Service Floor Box provides both electric power and telephone (data) services from the same device for economy of space and cost, as well as affording a flush delivery (no above floor service fitting). For these reasons, your specification may reference this product in three sections: Floor Boxes, Wiring Devices and Telephone Raceway Systems. Construction Specifications Institute (CSI) references them in: 16132 Floor Boxes; 16141 Wiring Devices; Part 2 – 2.06 Floor Mounted Service Fittings; and 16741 Telephone Raceway Systems, Part 2 – 2.01 G Floor Boxes. Section 16132 Floor Boxes is preferable. For clarification include a reference in 16141, Part 2, 2.06 Floor Mounted Service Fittings as follows: Surface type service fittings are not acceptable.

Part 2: Products

2.01 Acceptable manufacturers – Floor boxes, multiple service

A. Shall be series 664 concealed service floor box as manufactured by ABB.

2.02 Materials – Floor boxes, multiple service

A. Shall be electrogalvanized, 14 gauge sheet steel. (Alternate A shall be cast iron).

B. Construction shall be as required by UL 514A.

C. Carpet frame shall be nylon UL Recognized Component QMFZ2.

D. Hinged outer cover shall be reinforced with a 5/32" steel plate.

2.03 General design – Floor boxes, multiple service

A. Shall deliver electric power from one or two duplex receptacles installed below the surface of the floor.

B. Shall deliver telephone or data cable without interference from the electric power delivery.

C. Shall protect delivery of both services by a hinged cover with a retractable opening and foam plastomer dust seal.

D. Hinged cover shall accept carpet or tile to match floor covering and be 180 degrees reversible.

E. Shall have 90 cubic inch total capacity with 24 cubic inch power chambers.

F. Shall accept conduit sizes up to 1¼ inches.

G. Shall afford 18 square inches of access with cover open.

H. Box shall be listed by Underwriters Laboratories.

I. When hinged cover is closed and no services in place, device shall have no obstructions above surface of floor.

Part 3: Execution

3.01 General

A. Locate position for floor boxes and runs of conduit as shown on the plans.

3.02 Installation

A. Position floor boxes and conduit runs.

B. After concrete pour, pull wires and install devices according to manufacturers recommendations.

C. Activate in accordance with the National Electrical Code®.

D. Coordinate with floor covering contractor to complete installation.

Standard specification

Above-floor service

Service floor outlet multiple service, power and communications

Considerations when writing specifications:

The 664 Concealed Service Floor Box provides both electric power and telephone (data) services from the same device for economy of space and cost, as well as affording a flush delivery (no above floor service fitting). For these reasons, your specification may reference this product in three sections: Floor Boxes, Wiring Devices and Telephone Raceway Systems. Construction Specifications Institute (CSI) references them in: 16132 Floor Boxes; 16141 Wiring Devices; Part 2 — 2.06 Floor Mounted Service Fittings; and 16741 Telephone Raceway Systems, Part 2 — 2.01 G Floor Boxes. Section 16132 Floor Boxes is preferable. For clarification include a reference in 16141, Part 2, 2.06 Floor Mounted Service Fittings as follows: Surface type service fittings are not acceptable.

Part 2: Products

2.01 Acceptable manufacturers – Floor boxes, multiple service

A. Shall be series 664 concealed service floor box as manufactured by ABB.

2.02 Materials – Floor boxes, multiple service

- A. Shall be electrogalvanized, 14 gauge sheet steel. (Alternate A shall be cast iron).
- B. Construction shall be as required by UL 514A.
- C. Carpet frame shall be nylon UL Recognized Component QMFZ2.
- D. Hinged outer cover shall be reinforced with a $\frac{5}{32}$ " steel plate.

2.03 General design – Floor boxes, multiple service

- A. Shall deliver electric power from one or two duplex receptacles installed below the surface of the floor.
- B. Shall deliver telephone or data cable without interference from the electric power delivery.
- C. Shall protect delivery of both services by a hinged cover with a retractable opening and foam plastomer dust seal.
- D. Hinged cover shall accept carpet or tile to match floor covering and be 180 degrees reversible.
- E. Shall have 90 cubic inch total capacity with 24 cubic inch power chambers.
- F. Shall accept conduit sizes up to $1\frac{3}{4}$ inches.
- G. Shall afford 18 square inches of access with cover open.
- H. Box shall be listed by Underwriters Laboratories.
- I. When hinged cover is closed and no services in place, device shall have no obstructions above surface of floor.

Part 3: Execution

3.01 General

A. Locate position for floor boxes and runs of conduit as shown on the plans.

3.02 Installation

- A. Position floor boxes and conduit runs.
- B. After concrete pour, pull wires and install devices according to manufacturers recommendations.
- C. Activate in accordance with the National Electrical Code®.
- D. Coordinate with floor covering contractor to complete installation.

CONCRETE APPLICATIONS

On grade floors
recessed service






Cast iron for slab-on-grade applications

664 Series

Features and benefits:

Multiple-service floor boxes deliver power, communications and data from standard conduit with no exposed service fittings. Result: Open office planning flexibility. Ideal for the modern office with workstations that have power, communications and data equipment. Power receptacles and low-voltage connections can be enclosed underfloor in either steel or cast-iron bodies. Galvanized 14-gauge steel boxes are provided with knockouts from 3/4" to 1 1/4" (see engineering data). Cast-iron bodies have threaded openings for 3/4" and 1" conduit.

- Two-compartment box is available in three configurations: stamped steel (664-SC), shallow (664-S) (see page 57) and cast iron (664-CI)
- Durable non-metallic covers include a steel reinforcement plate for added strength
- Metallic covers in solid brass, aluminum and aluminum black powder-coated provide aesthetics and durability
- Cover flange self-levels with the finished floor for easy installation



Cat. No.	Description	Std. Ctn.
664-CI	Cast-iron box which accepts two plates, with one duplex 664-RP provided	1

Note: When ordering a 664 Series box, the cover must be ordered separately. See page 15.
For communications accessories, see page 130.

Engineering data for 664 Series




Cat. No.	Dimensions (in.)			Before Pour Adj. (in.)	After Pour Adj. (in.)	Maximum capacity (cu. in.)	Conduit Hubs	Conduit KOs		
	A	B	C					Sides	Bottom	Covers
664-CI	3 3/4	5 3/32	9 15/16	2 1/2	3/4	24 per gang, 90 total	(4) 3/4" (4) 1"	—	—	664-CST Series

CAUTION: When using the center side KOs, Cat. No. 664-RP must be assembled to the box prior to installing the conduit.

Non-metallic covers

664 Series floor boxes

Covers for all boxes



664-CST-SW

MopTite® covers meet UL/CSA scrubwater exclusion requirements for carpet, tile and wood.



Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
664-CST-SW-GRY	Gray cover	1,500	1
664-CST-SW-BRN	Brown cover	1,500	1
664-CST-SW-BGE	Beige cover	1,500	1
664-CST-SW-BLK	Black cover	1,500	1

Metallic covers


664 Series floor boxes



664-CST-M-BRS
Solid brass

664-CST-M-ALM
Solid aluminum

664-CST-M-BLK
Solid aluminum cover, black powder coated




MopTite® covers meet UL/CSA scrubwater exclusion requirements for carpet, tile and wood.



Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
664-CST-M-BRS	Solid brass cover for 664 Series floor boxes	2,250	1
664-CST-M-ALM	Solid aluminum cover for 664 Series floor boxes	2,250	1
664-CST-M-BLK	Solid aluminum cover, black powder coated for 664 Series floor boxes	2,250	1

Wire tunnel

664 Series



664-WT


- Wire tunnel for protecting electrical connections between the two receptacles when the box is used for power/power application



Cat. No.	Description	Std. Ctn.
664-WT	For use with 664 and 664-CI floor boxes	4

Device plates

664-SC & 664-CI



664-RP

664-GP

664-BP

664-2-MAAP

- Receptacle face plate for 664 Series floor box for additional power service
- Does not include receptacle. Can be placed at either end of floor box



Cat. No.	Description	Std. Ctn.
664-RP	For use with 664 and 664-CI floor boxes	4
664-BP	Blank plate for use with 664 & 664-CI floor boxes	4
664-GP	GFCI receptacle plate	4
664-2-MAAP	Device panel, accepts 2 Extron MAAP plates	4

CAUTION: When using the center side KOs, all 664 plates must be assembled to the box prior to installing the conduit.


Cast iron for slab-on-grade applications

665 Series - 665-CI

The Steel City® 665 cast iron floor box provides a high-capacity power and data solution for ground-floor installations. This 4-gang recessed service floor box is ideal for slab-on-grade applications. Removable voltage dividers enable users to customize wiring configurations by feeding two or more adjacent compartments with a single conduit. Aesthetic covers feature a recess to accept floor covering to match the surrounding floor.


Features and benefits:

- 4-gang, recessed service for a high-capacity aesthetic floor-box solution
- Removable voltage dividers between compartments enable a single conduit to feed two or more adjacent compartments heavy duty, non-metallic covers with steel reinforcement plates are available in a wide variety of colors to match any decor (black, gray, brown and beige)
- Metallic covers
- Separate cord door in the cover latches firmly in the open position to prevent damage to cables
- MopTite® covers meet UL/CSA scrubwater exclusion requirements for carpet, tile and wood
- Largest cubic-inch capacity of any cast iron recessed 4-gang floor box
- Inline 1 1/4" hubs allow high-capacity straight runs for communicator wiring
- Custom device panels and hub sizes are available. Contact technical service about these offerings



Cat. No.	Description	Device compartments (in.)						Std. Ctn.
		Length	Width	Height	Area	Device Access Area		
665-CI	Cast iron box	5 3/4	3 1/2	2 1/4	45 cu. in.	126 cu. in.	1	

665-CI floor box does not include device plates or cover. Order separately. (See page 18 and 19)
 For communications accessories, see page 130.




Metallic covers

665 Series floor boxes





665-CST-M-BRS
Solid brass



665-CST-M-ALM
Solid aluminum



665-CST-M-BLK
Solid aluminum, black powder coated




Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
665-CST-M-BRS	Solid brass cover for 665 Series floor boxes	1,500	1
665-CST-M-ALM	Solid aluminum cover for 665 Series floor boxes	1,500	1
665-CST-M-BLK	Solid aluminum cover, black powder coated for 665 Series floor boxes	1,500	1

Non-metallic covers




665 Series floor boxes



665-CST-SW-BLK
Black non-metallic cover



5/32" Steel top plate on lid, carpet or tile can be glued to top plate.



Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
665-CST-SW-BLK	Non-metallic cover for 665 Series floor boxes, black	750	1
665-CST-SW-GRY	Non-metallic cover for 665 Series floor boxes, gray	750	1
665-CST-SW-BGE	Non-metallic cover for 665 Series floor boxes, beige	750	1
665-CST-SW-BRN	Non-metallic cover for 665 Series floor boxes, brown	750	1


Furnished with (4) #8-32 x 5/8" mounting screws.
Contact ABB Technical Service for Color Chip samples.

Device plates and accessories

665 Series floor boxes



665-RP
Duplex plate



665-GP
GFCI plate



665-BP
Blank plate



665-6RJ
Data plate for 6 keystone jacks









665-WT
Wire tunnel feeds multiple compartments from a single conduit (one included with each 665-AV2 and 665-SC)



Cat. No.	Description	Std. Ctn.
665-RP	Duplex plate for 665 Series floor boxes	4
665-GP	GFCI plate for 665 Series floor boxes	4
665-BP	Blank plate for 665 Series floor boxes	4
665-6RJ	Data plate for 665 Series floor boxes, accepts 6 keystone jacks	4
665-STEL	Telephone data plate for 665 Series floor boxes	4
665-WT	Replacement wire tunnel for 665-SC, 665-CI & 665-AV2 floor boxes	4

Each box requires (4) device plates.






CONCRETE APPLICATIONS

On grade floors
flush service

Round floor boxes for power or communications


600 Series



Features – 600 Series

- Cast iron, watertight body, fully adjustable
- Painted silver enamel inside and out for additional corrosion resistance
- Interior and exterior leveling screws permit adjustment to meet finished floor
- Shipped complete with expendable cap to prevent ingress of concrete during pour
- 3/4" threaded conduit openings are standard
- Uses P60 Series MopTite® covers and carpet plate, see page 23

600-SC



601

602

603

604



Cat. No.	Description	Std. Ctn.
600-SC	Cast-iron floor box 3/4" conduit tapping	4
600-AL-SC	Cast-iron floor box 3/4" conduit tapping with aluminum trim ring	4
600-1-SC	Cast-iron floor box 1" conduit tapping	4
600-2-SC	Cast-iron floor box 2" conduit tapping	4
601-1/2-SC	Cast-iron floor box 1/2" conduit tapping	4
601-AL-SC	Cast-iron floor box 3/4" conduit tapping with aluminum trim ring	4
601-SC	Cast-iron floor box 3/4" conduit tapping	4
601-1	Cast-iron floor box 1" conduit tapping	4
601-1-1/4	Cast-iron floor box 1 1/4" conduit tapping	4
602-SC	Cast-iron floor box 3/4" conduit tapping	4
602-AL-SC	Cast-iron floor box 3/4" conduit tapping with aluminum trim ring	4
602-1	Cast-iron floor box 1" conduit tapping	4
603-SC	Cast-iron floor box 3/4" conduit tapping	4
603-AL-SC	Cast-iron floor box 3/4" conduit tapping with aluminum trim ring	4
604-SC	Cast-iron floor box 3/4" conduit tapping	4
604-AL-SC	Cast-iron floor box 3/4" conduit tapping with aluminum trim ring	4
600-4-FL	Trim ring brass	4
600-4-FL-AL	Trim ring aluminum	4

P-60 Covers sold separately.

Round floor boxes for power or communications

600 Series



Features – 600 Series



- Cast iron, watertight body, fully adjustable
- Painted silver enamel inside and out for additional corrosion resistance
- Interior and exterior leveling screws permit adjustment to meet finished floor
- Shipped complete with expendant cap to prevent ingress of concrete during pour
- 3/4" threaded conduit openings are standard
- Uses P60 Series MopTite® covers and carpet plate, see page 23

Engineering data



Cat. No.	Dimensions (in.)			Before pour adj. (in.)	After pour adj. (in.)	Maximum capacity kos (cu. in.)	Conduit hubs	Conduit KOs (in.)	
	A	B	C					Sides	Bottom
600-SC	4 1/4	4 1/4	5 1/8	2 1/2	1 5/16	64	3/4	—	—
600-1-SC	4 1/4	4 1/4	5 1/8	2 1/2	1 5/16	64	1	—	—
600-11/4	4 1/4	4 1/4	5 1/8	2 1/2	1 5/16	64	1 1/4	—	—
600-2-SC	4 1/4	4 1/4	5 1/8	2 1/2	1 5/16	64	2	—	—
601-SC	4 1/4	3 9/16	5 1/8	2 1/2	1 5/16	56	3/4	—	—
601-1	4 1/4	3 9/16	5 1/8	2 1/2	1 5/16	56	1	—	—
601-11/4	4 1/4	3 9/16	5 1/8	2 1/2	1 5/16	56	1 1/4	—	—
602-SC	4 1/4	3 1/32	4	2 1/2	1 5/16	36	3/4	—	—
602-1	4 1/4	3 1/32	4	2 1/2	1 5/16	36	3/4	—	—
603-SC	4 1/4	2 1/2	4	2 1/2	1 1/16	27	3/4	—	—
604-SC	4 1/4	2	4	1 1/2	—	15	3/4	—	—

Use P-60 Series covers and carpet plates.
Wiring Device: Duplex, single or voice/data plates.



MopTite® carpet plates

600 Series

- 01 P-60-3/4-2-CACP
- Polished brass finish
 - Integrated carpet plate and 3/4"-2" floor plate in one unit
 - Furnished complete with sealing gasket and 8-32 x 1" brass screws
 - 5 3/4" outside diameter



01

- 02 P-60-CP
- Polished brass finish
 - Furnished complete with 8-32 x 1" brass screws
 - For brushed aluminum, add AL after catalog number



02




03

- 03 P-60-LCP
- Translucent polycarbonate
 - Textured finish



04

- 04 P-60-CACP
- Polished-brass finish
 - Integrated carpet plate and duplex floor plate in one unit




05

- 05 P-60-CACP-GFCI
- Furnished complete with sealing gasket and 8-32 x 1" brass screws
 - 5 3/4" outside diameter



Cat. No.	Description	Std. Ctn.
P-60-CP	Brass carpet plate, 5 11/16" diameter	4
P-60-CPAL	Aluminum carpet plate	4
P-60-LCP	Polycarbonate carpet plate, 5 3/8" diameter	4
P-60-CACP	Brass one-piece carpet cover plate	4
P-60-CACP-AL	Aluminum one-piece carpet	4
P-60-3/4-2-CACP	Brass one-piece carpet plate with 3/4"-2" plugs	4
P60-3/4-2-CACP-AL	Aluminum one-piece carpet plate with 3/4"-2" plugs	4
P60-CACP-GFCI	Brass one-piece carpet plate for GFCI devices	4
P60-CACP-GFCI-AL	Aluminum one-piece carpet plate for GFCI devices	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.



MopTite® cover plates

600 Series

Features and benefits:

- Polished finish
- Furnished complete with sealing gasket and 8-32 x 7/16" screws
- 4" outside diameter



P-60-1/2
1/2" N.P.S. plug size



P-60-3/4
3/4" N.P.S. plug size



P-60-1
1" N.P.S. plug size




P-60-1-1/4




P-60-2*
2" dia. plug size



P-60-2-5/8*
2 5/8" dia. plug size



P-60-1/2-2*
1/2" & 2" dia. plug size



P-60-3/4-2*
3/4" & 2" dia. plug size




P-60-DR*
Duplex lift lid




P-60-DU*
Duplex 1 7/16" plugs



P-60-DS*
Hinged lift lids



P-60-GFCI*



Cat. No.	Description	Std. Ctn.
P-60-1/2	Brass cover plate 1/2" NPS plug size	4
P-60-1/2-AL	Aluminum cover plate 1/2" NPS plug size	4
P-60-3/4	Brass cover plate 3/4" NPS plug size	4
P-60-3/4-AL	Aluminum cover plate 3/4" NPS plug size	4
P-60-1	Brass cover plate 1" NPS plug size	4
P-60-1-AL	Aluminum cover plate 1" NPS plug size	4
P-60-1-1/4	Brass cover plate 1 1/4" NPS plug size	4
P-60-1-1/4-AL	Aluminum cover plate 1 1/4" NPS plug size	4
P-60-2	Brass cover plate 2" diameter plug size	4
P-60-2-AL	Aluminum cover plate 2" diameter plug size	4
P-60-2-5/8	Brass cover plate 2 5/8" diameter plug size	4
P-60-2-5/8-AL	Aluminum cover plate 2 5/8" diameter plug size	4
P-60-1/2-2	Brass cover plate 1/2"-2" diameter plug size	4
P-60-1/2-2-AL	Aluminum cover plate 1/2"-2" diameter plug size	4
P-60-3/4-2	Brass cover plate 3/4"-2" diameter plug size	4
P-60-3/4-2-AL	Aluminum cover plate 3/4"-2" diameter plug size	4
P-60-DR	Brass cover with duplex lift lid	4
P-60-DS	Brass cover for duplex with individual lift lids	4
P-60-DS-AL	Aluminum cover for duplex with individual lift lids	4
P-60-DU	Brass cover plate with two 1 7/16" plugs for duplex	4
P-60-DU-AL	Aluminum cover with two 1 7/16" plugs for duplex	4
P-60-GFCI	Brass cover plate for GFCI devices	4
P-60-GFCI-AL	Aluminum cover plate for GFCI devices	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.

Floor boxes for single short-strap receptacles or communications


78 Series

Service fitting application

78 Series Floor Boxes provide flush service for power or communications and data. They can be used for either carpet or tile applications.

78 Series – features and benefits:

- Cast iron, watertight body, semi-adjustable
- Painted silver enamel inside and out for additional corrosion resistance
- Exterior leveling screws and threaded vertical adjusting ring permit adjustment to meet finish floor
- Shipped complete with expandable cap to prevent ingress of concrete during pour
- 3/4" threaded conduit openings
- Uses P90 Series MopTite® covers



78 Series



Cat. No.	Description	Std. Ctn.
78SC	Cast-iron single-gang floor box with 3/4" conduit tapping	4
78-S	Cast-iron single-gang floor box (shallow)	4

Engineering Data




Cat. No.	Dimensions (in.)			Before pour adj. (in.)	After pour adj. (in.)	Maximum capacity (cu. in.)	Standard conduit tapping (in.)
	A	B	C				
78SC	3	2 ¹³ / ₁₆	3 ⁷ / ₈	2 ¹ / ₂	3/4	24	3/4
78-S	3	2 ⁵ / ₈	3 ⁷ / ₈	1 ¹ / ₂	3/4	20	3/4


Cat. No.	Maximum conduit tapping (in.)		Conduit KOs (in.)		Covers and Carpet Plates	Wiring device
	w/bushing	w/o bushing	Sides	Bottom		
78SC	3/4	1	—	—	P90 series	Sing. short, strap rec.
78-S	3/4	1	—	—	P90 series	Sing. short, strap rec.

MopTite® cover plates

78 Series



P-90-3/4-AL
3/4" N.P.S. plug



P-90-1-AL
1" N.P.S. plug




P-90-1-1/4
1 1/4" N.P.S. plug




P-90-2-AL*
2" dia. plug



P-90-1/2-2*
1/2" & 2" dia.



P-90-3/4-2*
3/4" & 2" dia. plugs



Features and benefits:

- Polished-brass finish
- Furnished complete with sealing gasket and 6-32 x 1/2" screws
- 2 13/16" outside diameter



Cat. No.	Description	Finish	Std. Ctn.
P-90-3/4-AL	Cover plate 3/4" NPS plug	Aluminum	4
P-90-1-AL	Cover plate 1" NPS plug	Aluminum	4

MopTite® Covers exceed UL/CSA watertight requirements.
*Also includes steel seating plates for receptacles.

Cat. No.	Description	Finish	Std. Ctn.
P-90-1-1/4-AL	Cover plate 1 1/4" NPS plug	Aluminum	4
P-90-2-AL	Cover plate 2" UN plug	Aluminum	4
P-90-1/2-2	Cover plate 1/2" & 2" plug	Brass	4
P-90-3/4-2	Cover plate 3/4" & 2" plug	Brass	4
P-90-3/4-2-AL	Cover plate 3/4" & 2" plug	Aluminum	4

Accessories

78 Series floor boxes

- 15-Amp, 125-Volt, NEMA grounding type
- Mounted on steel seating plate
- For use with 2" diameter-opening floor plate



478-G-12




Cat. No.	Description	Std. Ctn.
478-G-12	15-Amp 125-Volt NEMA grounding receptacle	4

Carpet plate

78 Series floor boxes

- Polished-brass finish
- Furnished complete with 6-32 x 1" brass flathead screws and gasket
- Threaded 2-20UN-2B to accept 694 plug
- 3 3/8" O.D. with 5/8" flange



Cat. No.	Description	Finish	Std. Ctn.
P-90-CP	Carpet plate	Brass	4

Will not accept P90 covers. Will accept 694 threaded plug, see page 132.

Floor boxes for single short-strap receptacles or communications

671 and 672 Series

671 and 672 Series floor boxes provide flush service for power or communications and data. They can be used in either wood or concrete floors and are suitable for carpet, tile or wood applications.

Features and benefits:



- Cast iron, watertight, non-adjustable
- Painted silver enamel inside and out for additional corrosion resistance
- **For use in wood or concrete floors**
- 1/2" and 3/4" threaded conduit openings; uses P67 Series covers
- Cat. No. 672 is the 671 floor box with factory-mounted 15-ampere, 125-volt, NEMA grounding receptacle and P67-2 MopTite® cover plate



671SC



672



Cat. No.	Dimensions (in.)			Maximum capacity (cu. in.)	Standard conduit tapping	Maximum conduit tapping (in.)			Conduit KOs (in.)				Covers/ carpet plates	Wiring Device	Std. Ctn.
	A	B	C			w/bushing	w/o bushing	Sides	Bottom	Sides	Bottom				
671SC	3 1/2	3	2 31/32	13	(2)-3/4"	3/4	3/4	(2) 1/2	(2) 1/2	(2) 3/4	—	P67 Series	Sing. short strap rec	4	
672	3 1/2	3 3/16	2 31/32	13	(4)-1/2"	3/4	3/4	(2) 1/2	(2) 1/2	(2) 3/4	—	P67 Series	Sing. short strap rec	4	

MopTite® Covers exceed UL/CSA watertight requirements.

MopTite® Plates

671 and 672 Series



P-67-1/2
1/2" N.P.S. plug



P-67-3/4
3/4" N.P.S. plug



P-67-1
1" N.P.S. plug




P-67-1-1/4*
1 1/4" N.P.S. plug




P-67-2
2" dia. plug



P-67-1/2-2*
1/2" & 2" dia. plugs



P-67-3/4-2*
3/4" & 2" dia. plugs



- Polished brass finish
- Furnished complete with sealing gasket and 6-32 x 1/2" screws
- 3 1/2" outside diameter

*Also includes seating plate for receptacle.




Cat. No.	Description	Finish	Std. Ctn.
P-67-1/2	Cover plate with 1/2" NPS plug	Brass	4
P-67-3/4	Cover plate with 3/4" NPS plug	Brass	4
P-67-3/4-AL	Cover plate with 3/4" NPS plug	Aluminum	4
P-67-1	Cover plate with 1" NPS plug	Brass	4
P-67-1-AL	Cover plate with 1" NPS plug	Aluminum	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements. For plug replacement, see page 132.

Cat. No.	Description	Finish	Std. Ctn.
P-67-1-1/4	Cover plate with 1 1/4" NPS plug	Brass	4
P-67-2	Cover plate with 2" UN thread plug	Brass	4
P-67-2-AL	Cover plate with 2" UN thread plug	Aluminum	4
P-67-1/2-2	Cover plate with 1/2" & 2" plug	Brass	4
P-67-3/4-2	Cover plate with 3/4" & 2" plug	Brass	4

Carpet plates

671 and 672 Series



694 Plug

Features and benefits:

- Polished-brass finish
- Furnished complete with 6-32 x 1"-long brass flathead screws and gasket
- 3³/₈" outside diameter



Cat. No.	Description	Std. Ctn.
P-90-CP	Carpet plate – Brass	4


Will not accept P-67 covers, will accept threaded plug, see page 132.

Accessories

671 and 672 floor boxes



P-67-F
Edge ring



478-G-12
Short strap receptacle

Features and benefits:

- Use brass edge ring for neat appearance when non-adjustable floor box is installed in concrete
- Edge ring has 3³/₄" OD and adds 3³/₈" to floor box height
- 15-amp, 125-volt, NEMA grounding type
- Mounted on steel seating plate
- For use with 2" diameter opening floor plate



Cat. No.	Description	Std. Ctn.
P-67-F	Brass edge ring for concrete	4
478-G-12	15-Amp, 125-Volt NEMA grounding receptacle	4

Multiple-gang floor boxes for power and communications

640 and 840SC Series

640 and 840 Series floor boxes provide flush service for power, communications and data. Multiple-gang boxes enable the user to place high- and low-voltage in a single floor box.

Floor boxes up to four-gangs are available.


640 and 840 Series boxes can be used for either carpet or tile applications.

640 Series – features and benefits:



- Cast iron, watertight body, fully adjustable
- Painted silver enamel inside and out for additional corrosion resistance
- Interior and exterior leveling screws permit adjustment to finished floor
- Removable partitions for large capacity requirements on 2-, 3- and 4-gang
- Shipped complete with expendable cap to prevent ingress of concrete during pour
- 3/4" threaded conduit openings are standard
- Uses P64 Series MopTite® covers (one cover per gang)

840SC Series – features and benefits

- Cast iron, watertight body, semi-adjustable
- Painted silver enamel inside and out for additional corrosion resistance
- Exterior leveling screws for adjustment to finished floor
- Removable partitions for large capacity requirements on 2- and 3-gang
- Shipped complete with expendable cap to prevent ingress of concrete during pour
- 3/4" threaded conduit openings are standard
- Uses P64 Series MopTite® covers (one cover per gang)



Trim ring SP-641-FL is the replacement part number (1 brass trim ring is included).




Features and benefits:

- Polished brass finish
- Furnished complete with sealing gasket and 8-32 x 1" screws
- 3" x 4 1/2" outside dimension
- All covers meet MopTite® requirements

Multiple-gang floor boxes for power and communications

640 and 840SC Series



Engineering data

Cat. No.	Dimensions (in.)			Before pour adj. (in.)	After pour adj. (in.)
	A	B	C		
641	3 ⁵ / ₈	4	5 ¹ / ₂	2 ¹ / ₂	5 ⁵ / ₈
642	3 ⁵ / ₈	7	5 ¹ / ₂	2 ¹ / ₂	5 ⁵ / ₈
643	3 ⁵ / ₈	10	5 ¹ / ₂	2 ¹ / ₂	5 ⁵ / ₈
841-SC	2	4	5 ¹ / ₂	1 ¹ / ₂	—
842-SC	2	7	5 ¹ / ₂	1 ¹ / ₂	—
843-SC	2	10	5 ¹ / ₂	1 ¹ / ₂	—

Cat. No.	Number of gangs	Maximum capacity (cu. in.)	Conduit hubs (in.)
641	1	35	3/4
642	2	37 per gang	3/4
643	3	37 per gang	3/4
841-SC	1	15	3/4
842-SC	2	16.5 per gang	3/4
843-SC	3	16.5 per gang	3/4


Use P64 Series covers and carpet plates.

*Additional hub sizes available — see next page.



Floor boxes

640 and 840SC Series













Cat. No.	Description	Std. Ctn.
641	Cast-iron single-gang floor box with 3/4" conduit hubs	4
641-AL	Cast-iron single-gang floor box with 3/4" conduit hubs & aluminum trim	4
641-1	Cast-iron single-gang floor box with 1" conduit hubs	4
SP-641-1-AL	Cast-iron single-gang floor box with 1" conduit hubs & aluminum trim	4
642	Cast-iron two-gang floor box with 3/4" conduit hubs	2
642-AL	Cast-iron two-gang floor box with 3/4" conduit hubs & aluminum trim	2
642-1	Cast-iron two-gang floor box with 1" conduit hubs	2
SP-642-1-AL	Cast-iron two-gang floor box with 1" conduit hubs & aluminum trim	2
643	Cast-iron three-gang floor box with 3/4" conduit hubs	1
643-AL	Cast-iron three-gang floor box with 3/4" conduit hubs & aluminum trim	1
SP-643-1	Cast-iron three-gang floor box with 1" conduit hubs	1
SP-643-1-AL	Cast-iron three-gang floor box with 1" conduit hubs & aluminum trim	1
841-SC	Shallow cast-iron single-gang floor box with 3/4" conduit hubs	4
841-AL	Shallow cast-iron single-gang floor box with 3/4" conduit hubs & aluminum trim	4
842-SC	Shallow cast-iron two-gang floor box with 3/4" conduit hubs	2
842-AL-SC	Shallow cast-iron two-gang floor box with 3/4" conduit hubs & aluminum trim	2
843-SC	Shallow cast-iron three-gang floor box with 3/4" conduit hubs	1
843-AL-SC	Shallow cast-iron three-gang floor box with 3/4" conduit hubs & aluminum trim	1

Boxes supplied with brass tile trim unless otherwise specified.



MopTite® cover plates

640 and 840 Series



*Also includes seating plate for receptacle like others.






Cat. No.	Description	Finish	Std. Ctn.
P-64-1/2	Cover plate 1/2" NPS plug	Brass	4
P-64-3/4	Cover plate 3/4" NPS plug	Brass	4
P-64-3/4-AL	Cover plate 3/4" NPS plug	Aluminum	4
P-64-1	Cover plate 1" NPS plug	Brass	4
P-64-1-AL	Cover plate 1" NPS plug	Aluminum	4
P-64-1-1/4	Cover plate 1 1/4" NPS plug	Brass	4
P-64-1-1/4-AL	Cover plate 1 1/4" NPS plug	Aluminum	4
P-64-2	Cover plate 2" UN plug	Brass	4
P-64-2-AL	Cover plate 2" UN plug	Aluminum	4
P-64-1/2-2	Cover plate 1/2" & 2" UN plug	Brass	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.
For replacement plug see page 127.

Cat. No.	Description	Finish	Std. Ctn.
P-64-1/2-2-AL	Cover plate 1/2" & 2" UN plug	Aluminum	4
P-64-3/4-2	Cover plate 3/4" & 2" UN plug	Brass	4
P-64-3/4-2-AL	Cover plate 3/4" & 2" UN plug	Aluminum	4
P-64-DS	Cover plate duplex Lift lids	Brass	4
P-64-DS-AL	Cover plate duplex Lift lids	Aluminum	4
P-64-2-5/8	Cover plate 2 5/8" UN plug	Brass	4
P-64-2-5/8-AL	Cover plate 2 5/8" UN plug	Aluminum	4
P-64-DU	Cover plate duplex 1 7/16" plugs	Brass	4
P-64-DU-AL	Cover plate duplex 1 7/16" plugs	Aluminum	4
P-64-GFCI	Cover plate GFCI flip lid	Brass	4
P-64-GFCI-AL	Cover plate GFCI flip lid	Aluminum	4

Metallic carpet plates

640 and 840 Series



Cat. No.	Number of gangs	Outside Dimension (in.)	Material	Std. Ctn.
P64-CP	1	4 5/8 x 6 1/8	Brass	4
P64-CP-AL	1	4 5/8 x 6 1/8	Aluminum	4
P64-2G-CP	2	7 5/8 x 6 1/8	Brass	4
P64-2G-CP-AL	2	7 5/8 x 6 1/8	Aluminum	4
P64-3G-CP	3	10 5/8 x 6 1/8	Brass	4
P64-3G-CP-AL	3	10 5/8 x 6 1/8	Aluminum	4

Gaskets

Floor plate assemblies



Cat. No.	For use with	Std. Ctn.
SP650	P-64 Series floor plate assemblies	4
SP651	P-64-DU floor plate assemblies	10
SP-P64-DS-P2	P-64-DS floor plate assembly	4

CONCRETE APPLICATIONS

On or above grade floors
recessed service



1-, 2- and 3-Gang


Rectangular floor box

Carlton® rectangular floor box systems – three-way power, data and communications plus easy double- or triple-gang, too.

Compared to metal boxes, Carlton® rectangular floor boxes cost less and install faster to save you money on every job. Three-in-one power, data and communications capability cuts installation time and cost even more, while simple two- and three-gang modularity gives you the flexibility, installation ease and cost-savings no other non-metallic boxes can match. The covers attach without the use of fasteners, providing a professional, clean installation as well as preserving the aesthetic life of the product. Take a closer look at all that our rectangular floor box systems offer you.

Features and benefits:

- Covers require no adjusting collar – two screws ensure a flush, secure installation
- Non-metallic PVC construction, watertight gasket and corrosion-resistant hardware ensure long life and reliable performance, even in harsh and/or corrosive environments
- One consistent box depth simplifies ordering time and reduces inventory
- Saves time and money on installations with simple saw cut to floor level
- Concrete tight and suitable for any on-grade/below-grade application; concrete or wood subfloor construction approved
- Convenient cubic inch capacity markings on inside enable easy inspection
- PVC-molded ports and reducer plugs included
- Accepts ½", ¾" and 1" conduit, tubing or raceway
- Rectangular sides are drillable
- Suitable for tile and carpet applications
- Cover options include solid brass, stainless steel and non-metallic (brown, slate and caramel)
- UL/CSA scrubwater tested, approved for all types of finish flooring



Gangable rectangular

Floor box




Features and benefits:

With our rectangular boxes, one SKU is all you ever need. Simply remove appropriate sides and slide boxes together to create two- or three-gang boxes for on-the-job flexibility no competitor offers.

For wood floor applications, box must be supported from below.



Cat. No.	Material	Size	Internal volume (cu. in.)	Min. concrete depth	Hubs (In.)	Reducer plugs (In.)	Std. Ctn.	Std. Wt. (lbs.)
E976RFB	PVC	1-Gang	97.4 (16.8 per inch of depth)	3½	(2) 1	(2) 1 x ¾ (2) ¾ x ½	3	6.92



Activation

Kit



Activation kit provides components to accommodate all standard power, data and communications devices, plus a divider to separate power from data and communications – all in a single SKU. Device yokes can be adjusted to store excess cord in the box.

Requires one kit per gang.



Cat. No.	Material	Std. Ctn.	Std. Wt. (lbs.)
E976AK2	PVC	3	2.47



1-, 2- and 3-gang non-metallic Floor box covers

On-the-job flexibility extends to our rectangular box covers. Each one-, two- or three-gang cover is suitable for any wiring application and can be used with any floor surface. Non-metallic covers are even field-reversible for tile or carpet. Double-door feature enables easy access to the device and helps keep stray cords organized.


Features and benefits:

- High-impact resistant thermoplastic
- Field reversible for tile or carpet
- Gasketed for a watertight seal
- Double-door design
- For tile and carpet applications
- UL/CSA scrubwater tested

Carlon® Rectangular Floor Box Covers do not require a separate carpet flange. The carpet flange is part of the cover and may be removed for tile application.



Cat. No.	Size	Color	Carpet flange	Dimensions (w x L) (In.)	Std. Ctn.	Std. Wt. (lbs.)
E9761B	One-Gang	Brown	Included	7.13 x 5.00	3	1.7
E9762B	Two-Gang	Brown	Included	7.13 x 8.25	9	8.5
E9763B	Three-Gang	Brown	Included	7.13 x 11.50	6	7.5
E9761C	One-Gang	Caramel	Included	7.13 x 5.00	3	1.7
E9762C	Two-Gang	Caramel	Included	7.13 x 8.25	9	8.5
E9763C	Three-Gang	Caramel	Included	7.13 x 11.50	6	7.5
E9761S	One-Gang	Slate	Included	7.13 x 5.00	3	1.7
E9762S	Two-Gang	Slate	Included	7.13 x 8.25	9	8.5
E9763S	Three-Gang	Slate	Included	7.13 x 11.50	6	7.5





1-, 2- and 3-gang solid brass and Stainless steel floor box covers


Carlton® brass and stainless steel rectangular floor box covers add a classic touch to all floor box installations, and are particularly suited for use in high-traffic areas because of the resistance to wear. The gasket gives a watertight seal, and the light lacquer finish provides extra protection.

Features and benefits:


- Rugged construction
- Coated with a light lacquer finish for extra protection
- Covers include a cord door
- Gasketed for watertight applications
- Accepts single, duplex, GFCI and low-voltage receptacles
- For tile and carpet applications
- UL/CSA scrubwater tested




Cat. No.	Size	Color	Dimensions (in.)	Std. Ctn.	Std. Wt. (lbs.)
E9761BR	One-gang	Brass	7.13 x 5	3	6.8
E9762BR	Two-gang	Brass	7.13 x 8.25	3	9.9
E9763BR	Three-gang	Brass	7.13 x 11.5	3	12.1
E9761SS	One-gang	Stainless steel	7.13 x 5	3	7.4
E9762SS	Two-gang	Stainless steel	7.13 x 8.25	3	11.6
E9763SS	Three-gang	Stainless steel	7.13 x 11.5	3	17.2



One-gang



Two-gang



Three-gang

Recessed service box

68R Series for use with 68-P floor box

— 01 Use a Steel City® round PVC floor box, catalog number 68-P (purchased separately) See page 43

— 02 Concrete applications

— 03 Lid closes flush with the floor, even with cords plugged in

Plug in power and communication cords, and then close the lid to hide unsightly plugs and receptacles below the floor.

Features and benefits:

- Unique cover provides aesthetic recessed service with cost-effective box options for concrete, wood sub-floor and raised-floor applications
- Lid can be rotated to expose a small opening for cords, enabling the lid to close flush with the floor while in use

- Cover accepts one duplex or GFCI receptacle – no special device plates required (receptacle purchased separately)
- Cover accepts up to two communications jacks – includes one 2-port keystone data plate and one blank data plate for custom cut-outs or power-only applications (communications jacks purchased separately)
- Non-metallic covers are available in black, gray, beige and brown. Black covers are available with an optional brass or aluminum flange
- Two set screws lock the cover in place – no gluing required



— 01



— 02




— 03



— 04

Recessed covers

68R Series




Features and benefits:

- Cover assembly
- Receptacle mounting plate
- Duplex receptacle insert
- 2-port keystone data plate
- Blank data plate
- Voltage divider



Device not included. Cover is 6³/₄ in. dia.





Important application note:

When using the 68R recessed cover with the 68-P floor box for concrete applications, the entire box depth (6") is required. Prior to concrete pour, level the top of the box with the screed line of the concrete.



Cat. No.	Description	Std. Ctn.
68R-CST-BLK	Non-metallic recessed floor box cover kit, black	4
68R-CST-GRY	Non-metallic recessed floor box cover kit, gray	4
68R-CST-BGE	Non-metallic recessed floor box cover kit, beige	4
68R-CST-BRN	Non-metallic recessed floor box cover kit, brown	4
68R-CST-BRS	Non-metallic recessed floor box cover kit, black with brass flange	4
68R-CST-ALM	Non-metallic recessed floor box cover kit, black with aluminum flange	4
68-P	Round PVC floor box for concrete applications	8



CONCRETE APPLICATIONS


On or above grade floors
flush service



Carlton® round floor box systems

Three-way versatility for power, data and communications

Carlton® round floor boxes give you the same cost-saving advantages over metal boxes as our rectangular boxes. By combining power, data and communications in the same box, you can dramatically reduce your installation time and cost compared to other non-metallic boxes. In addition, multi-use covers mean fewer SKUs to deal with and greater jobsite flexibility to increase your savings further. Take a closer look at all their advantages.





Features and benefits:

- Non-metallic PVC construction, watertight gasket and corrosion-resistant hardware ensure long life and reliable performance, even in harsh and/or corrosive environments
- Covers are available for a variety of applications
- The same box depth simplifies ordering and reduces inventory
- Suitable for tile and carpet applications
- Cover options include: brass, stainless steel and non-metallic (ivory, caramel, taupe, slate and brown)
- Concrete tight and suitable for any on-grade/ below-grade application; concrete or wood floor construction approved
- Y-connector (E972Y) enables you to feed parallel runs of ¾" conduit or to feed in/out from the same side for increased wiring flexibility and faster installation
- PVC-molded ports and reducer plugs included
- Accepts ½", ¾" and 1" conduit, tubing or raceway
- UL/CSA scrubwater tested, approved for all types of finish flooring

Round floor box - Carlton® round floor boxes enable various thicknesses of concrete pours. Trim out is easy – just use a handsaw to cut off box at desired height to accommodate carpet, tile or other flooring. Carlton® leveling ring guarantees a level top every time, even if the box is tipped slightly during the pouring process.



Cat. No.	Internal volume (cu. in.)	Min. concrete depth (in.)	Hubs (in.)	Reducer plugs (in.)	Std. Ctn.	Std. Wt. (lbs.)
E971FB	90.0 (15.5 per inch of depth)	3½	(2) 1 and (2) ¾	(2) 1 x ¾ and (2) ¾ x ½	10	15.6




Brass and stainless steel covers

For round floor boxes




Features and benefits:

- Screws concealed under doors
- Rugged construction
- Coated with a light lacquer finish for extra protection
- Resistance to wear – suited for high-traffic areas
- Gasketed for watertight applications
- Available in four styles – single door, two door, NPS opening and two-door dual service
- For tile and carpet applications
- UL/CSA scrubwater tested
- Cover diameter: 5½"




Two-door dual service (divider kit included)

Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BR2D	Brass	Duplex and two data ports	5	9.2
E97SS2D	Stainless steel	Duplex and two data ports	5	9.1




NPS opening

Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BRg	Brass	1¼" outlet and single receptacle	5	7.5
E97SSg	Stainless steel	1¼" outlet and single receptacle	5	8.1



Two door


Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BR2	Brass	Duplex	5	7
E97SS2	Stainless steel	Duplex	5	7.7



Cover adapter ring for use with metal covers

Cat. No.	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97ABR2	One-piece metal cover adapter	5	9.2

Note: Carlon® metal cover adapter ring (E97ABR2) is required with these covers (sold separately).




Single door

Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BR	Brass	GFCI and duplex	5	7
E97SS	Stainless steel	GFCI and duplex	5	7.9

Accessories

The multi-service divider kit for separate power, data and communications compartments provides unbeatable flexibility and money-saving installation speed. For use with non-metallic boxes only.




Multi-service divider kit

Cat. No.	Std. Ctn.	Std. Wt. (lbs.)
E973K	10	3

Features and benefits:

- High impact-resistant thermoplastic
- Compatible with standard NEMA Duplex and 1 1/4" NPS receptacles
- Drill points (3/8") provided for low-voltage cable pass throughs
- 1 1/4" NPS plugs may be modified to accept smaller fittings (3/8", 1/2" and 3/4")
- For tile and carpet applications
- UL/CSA scrubwater tested, approved for all types of finish flooring
- Cover diameter: 5.7"




Caramel

Slate

Ivory

Taupe

Brown



The 3/4" Y fitting provides for in-and-out service from a single 1" port, and provides two 3/4" parallel conduit runs to adapt into a single-conduit body port



3/4" Y fitting

Cat. No.	Std. Ctn.	Std. Wt. (lbs.)
E972Y	10	2.1



Duplex covers

Cat. No.	Color	Description	Std. Ctn.	Std. Wt. (lbs.)
E97DSI	Ivory	Duplex cover	10	5.2
E97DSC	Caramel	Duplex cover	10	5.7
E97DST	Taupe	Duplex cover	10	5.7
E97DSS	Slate	Duplex cover	10	5.6
E97DSB	Brown	Duplex cover	10	5.8



Reducer plugs

Cat. No.	Size (In.)	Std. Ctn.	Std. Wt. (lbs.)
E971C	3/4 x 1/2	100	2.1
E971D	1 x 3/4	100	3.2



1 1/4" NPS covers



Cat. No.	Color	Description	Std. Ctn.	Std. Wt. (lbs.)
E97SSRB	Brown	NPS cover	10	3.8
E97SSRC	Caramel	NPS cover	10	3.8
E97SSRS	Slate	NPS cover	10	3.8

Clear cover carpet ring

Cat. No.	Color	Std. Ctn.	Std. Wt. (lbs.)
E97CCR	Clear	10	1.2

Round non-metallic floor box

68-P Series



The 68-P floor box provides flush service for power or communications and data. The non-metallic floor box is used in concrete floors and is suitable for carpet, tile or wood applications.

Features and benefits:

- High-strength rigid PVC construction, non-corrosive
- Easy installation with no leveling required – just cut the box level with the concrete after the pour
- Compatible with standard-schedule PVC conduit Pre-packaged with concrete cap and six hub plugs
- Includes four (4) 3/4 to 1/2" reducing bushings
- Includes four (2) 1 to 3/4" reducing bushings




Cat. No.	Dimensions (in.)			After pour adj.	Maximum capacity (cu. in.)	Standard conduit tapping	Covers and carpet plates	Wiring device	Std. Ctn.
	A	B	C						
68-P	5 5/32	6	6 3/8	None	100	(4) 3/4" (2) 1"	P60 P68 series	Single duplex or data/voice	8



Minimum pour 3 inches. Cubic in. capacity is 17 cubic inches per inch of box height. **Note:** Must use 68-PAR to attach cover plates to 68-P floor box.

Adjusting ring

for 68-P floor box



Features and benefits:

- Non-metallic adjusting ring includes pigtail and clips



Cat. No.	Description	Std. Ctn.
68-PAR	Non-Metallic Adjusting Ring	8

Required to mount P60 and P68 Series covers to 68P floor box (not needed for dual-voltage kits).

Metallic tile trims

for 68-P floor box



Features and benefits:

- Tile trim rings are available in brass or aluminum for flush installation of metallic plates in linoleum, tile, wood or carpeted floors. Must be used to mount P60 series plates. (Not required for P-68 covers, P60-CACP or P60-3/4-2-CACP)



Cat. No.	Description	Std. Ctn.
68P-FL	Tile trim ring, brass	4
68P-FL-AL	Tile trim ring, aluminum	4

Required to attach P60 Series cover plates to 68-P floor box.

Dual-Voltage kits

68-P Series



Features and benefits:

- Voltage divider has easy-cut score lines to accommodate concrete depths of 3 to 6 inches
- Faceplate has removable data plates and can accommodate GFCI or standard duplex receptacles
- Kit comes equipped with 4 standard keystone-size openings in the data plates. Other styles available include openings sized for Ortronics, Avaya, Panduit and Hubbell
- MopTite® cover uses a “snap-lock” to close the lid. No screws to turn... just push down the lid and it snaps in place. The cover uses a factory-installed gasket and exceeds all UL/CSA scrubwater exclusion requirements for carpet, wood and tile floors
- MopTite® cover available in solid brass, black powder paint aluminum or aluminum
- Includes everything required for a standard installation (68P floor box, data jacks and receptacles not included)



Cat. No.	Description	Std. Ctn.
68P-DV-KIT-BRS	Dual-voltage divider kit with MopTite® brass cover	1
68P-DV-KIT-AL	Dual-voltage divider kit with MopTite® aluminum cover	1
68P-DV-KIT-BLK	Dual-voltage divider kit with MopTite® black cover	1
68P-DV-DP-ORT	Ortronics data plate to accommodate 2 jacks	10
68P-DV-DP	Standard data plate to accommodate 4 keystonejacks	10

*Keystone data plates come standard with the kit. Other style data plates are available from ABB and can be ordered separately.



MopTite® metallic carpet plates

68-P Series



P60-CACP



P60-3/4-2-CACP



P60-CACP-GFCI



P60-CP

Features and benefits:

- Polished brass or brushed aluminum finish
- Furnished complete with 8-32 x 1" brass screws



Cat. No.	Description	Finish	Std. Ctn.
P60-CACP	One-piece duplex cover and carpet flange	Brass	4
P60-CACP-AL	One-piece duplex cover and carpet flange	Aluminum	4
P60-3/4-2-CACP	One-piece cover and carpet flange with 3/4" and 2" plugs	Brass	4
P60-3/4-2-CACP-AL	One-piece cover and carpet flange with 3/4" and 2" plugs	Aluminum	4
P60-CACP-GFCI*	One-piece GFCI cover and carpet flange	Brass	4
P60-CACP-GFCI-AL*	One-piece GFCI cover and carpet flange	Aluminum	4
P60-CP*	Carpet flange	Brass	4
P60-CP-AL*	Carpet flange	Aluminum	4

*Requires 68-PAR and 68P-FL or 68P-FL-AL to attach cover to 68-P floor box. MopTite® Covers exceed UL/CSA watertight requirements.


MopTite® non-metallic carpet plates

68-P Series

05 Non-metallic, single receptacle plate (SRC) with matching carpet plate and cover. 6" O.D.

06 Non-metallic floor service cover (FSC) with 1" NPS screw plug accommodates most above-floor service fittings with matching carpet plate. 6" O.D.

07 Non-metallic, duplex/voice data receptacle plates (DRC) with matching carpet plate and cover. 6" O.D.



Cat. No.	Color	Description	Std. Ctn.	Cat. No.	Color	Description	Std. Ctn.
P-68-SRC-GRY	Gray	Non-metallic carpet plate and cover for single receptacle	4	P-68-FSC-BGE	Beige	Non-metallic carpet plate and cover with 1" NPS screw plug	4
P-68-SRC-BRN	Brown	Non-metallic carpet plate and cover for single receptacle	4	P-68-FSC-BLK	Black	Non-metallic carpet plate and cover with 1" NPS screw plug	4
P-68-SRC-BGE	Beige	Non-metallic carpet plate and cover for single receptacle	4	P-68-DRC-GRY	Gray	Non-metallic carpet plate and cover for duplex receptacle	4
P-68-SRC-BLK	Black	Non-metallic carpet plate and cover for single receptacle	4	P-68-DRC-BRN	Brown	Non-metallic carpet plate and cover for duplex receptacle	4
P-68-FSC-GRY	Gray	Non-metallic carpet plate and cover with 1" NPS screw plug	4	P-68-DRC-BGE	Beige	Non-metallic carpet plate and cover for duplex receptacle	4
P-68-FSC-BRN	Brown	Non-metallic carpet plate and cover with 1" NPS screw plug	4	P-68-DRC-BLK	Black	Non-metallic carpet plate and cover for duplex receptacle	4

*Requires 68-PAR to attach cover to 68-P floor box. MopTite® Covers exceed UL/CSA watertight requirements.

MopTite® metallic cover plates

for 68-P Series

Features and benefits:

- Polished finish
- Furnished complete with sealing gasket and 8-32 x 7/16" brass screws
- 4" outside diameter
- For brushed aluminum, add AL after catalog number
- When not using the P60-CP, then use 68P-FL



P-60-1/2
1/2" N.P.S. Plug Size



P-60-3/4
3/4" N.P.S. Plug Size



P-60-1
1" N.P.S. Plug Size




P-60-1-1/4
1 1/4" N.P.S. Plug Size




P-60-2*
2" dia. Plug Size



P-60-2-5/8*
2 5/8" dia. Plug Size



P-60-1/2-2*
1/2" & 2" dia. Plug Size



P-60-3/4-2*
3/4" & 2" dia. Plug Size




P-60-DR*
Duplex Lift Lid



P-60-DS*
Hinged Lift Lids



P-60-DU*
Duplex 17/16" Plugs



P-60-GFCI*
12 P-60-GFCI*


* Also includes steel seating plate for receptacles.



Cat. No.	Description	Std. Ctn.
P-60-1/2	Brass cover plate 1/2" NPS plug size	4
P-60-1/2-AL	Aluminum cover plate 1/2" NPS plug size	4
P-60-3/4	Brass cover plate 3/4" NPS plug size	4
P-60-3/4-AL	Aluminum cover plate 3/4" NPS plug size	4
P-60-1	Brass cover plate 1" NPS plug size	4
P-60-1-AL	Aluminum cover plate 1" NPS plug size	4
P-60-1-1/4	Brass cover plate 1 1/4" NPS plug size	4
P-60-1-1/4-AL	Aluminum cover plate 1 1/4" NPS plug size	4
P-60-2	Brass cover plate 2" diameter plug size	4
P-60-2-AL	Aluminum cover plate 2" diameter plug size	4
P-60-2-5/8	Brass cover plate 2 5/8" diameter plug size	4
P-60-2-5/8-AL	Aluminum cover plate 2 5/8" diameter plug size	4

Cat. No.	Description	Std. Ctn.
P-60-1/2-2	Brass cover plate 1/2"-2" diameter plug size	4
P-60-1/2-2-AL	Aluminum cover plate 1/2"-2" diameter plug size	4
P-60-3/4-2	Brass cover plate 3/4"-2" diameter plug size	4
P-60-3/4-2-AL	Aluminum cover plate 3/4"-2" diameter plug size	4
P-60-DR	Brass cover with duplex lift lid	4
P-60-DS	Brass cover for duplex with individual lift lids	4
P-60-DS-AL	Aluminum cover for duplex with individual lift lids	4
P-60-DU	Brass cover plate with two 1 1/16" plugs for duplex	4
P-60-DU-AL	Aluminum cover with two 1 1/16" plugs for duplex	4
P-60-GFCI	Brass cover plate for GFCI devices	4
P-60-GFCI-AL	Aluminum cover plate for GFCI devices	4

*Requires 68-PAR and 68P-FL or 68P-FL-AL to attach cover to 68-P floor box.
MopTite® Covers exceed UL/CSA watertight requirements.



Round floor boxes for power and communications

68-HP Series

Innovative 3-Gang round floor box for power, data and AV



Unmatched flexibility to configure any combination of power and communications devices

- Accepts standard devices from any manufacturer, including duplex, GFCI, locking, hospital grade or isolated ground receptacles
- Accommodates a wide variety of multi-media devices through the use of rectangular adapters

Combines the capacity of a 3-gang box with the affordability of a round non-metallic floor box

- 6" diameter round non-metallic floor box – the largest in the industry
- Large inline hubs for power and data wiring: 1" for power, 1½" for data



No leveling, gluing or aligning for an easy installation


- No wasted time leveling the box before the concrete is poured – simply cut the box at the appropriate height after the pour
- No gluing – stainless steel retention bars secure the mounting frame to the box
- Round design – no need to align the box with walls during installation

Easy-to-use covers made of durable solid brass and aluminum

- Stands up to heavy carts, cleaning equipment, and general floor traffic
- Convenient slide latch provides tool-less access to devices
- Lid lies flat while in use to minimize obstructions above floor level



Stainless steel bars



Slide latch for tool-less access



Lid lies flat against the floor while in use



1" Hub for Power, 1½" Hub for Data



Furniture-feed and cast iron options for a comprehensive floor box solution

- Dual-voltage furniture-feed covers transition power and communications wiring from the floor into modular furniture
- Cast iron box with a non-metallic collar for slab-on-grade or metallic conduit applications

Round floor boxes for power and communications

68-HP Series




68-HP

68-HP-CI

These include two 1 1/2 to 1" reducing bushings. It also comes with two 1 to 3/4" reducing bushings




Cat. No.	Description	Minimum concrete depth		Std. Ctn.
		Flush	Furniture feed	
68-HP	6" round non-metallic floor box	4"	3 1/2"	4
68-HP-CI	Cast iron floor box with 6" round non-metallic collar	4 1/2"	4"	1



Flush covers


68-HP Series



- Slide latch for tool-less access to devices
- Lid lies flat when box is in use




Cat. No.	Description	Std. Ctn.
68-HP-FC-ALM	Flush cover – solid aluminum with brushed finish, 1,000 lb. load rating	4
68-HP-FC-BRS	Flush cover – solid brass with brushed finish, 1,500 lb. load rating	4
68-HP-FC-BLK	Flush cover – solid aluminum with black powder-coated finish, 1,000 lb. load rating	4



Flush mounting kit and accessories

68-HP Series




Features and benefits:

- Flush mounting kit required in order to mount devices and covers to the 68-HP Series floor box
- Stainless steel barbs – no gluing required
- Includes (3) compartments for standard devices
- Voltage dividers allow any combination of power and communications devices
- Each compartment includes (1) knockout for power and (1) knockout for data for access to either power or communications wiring

Kit Includes:


- Mounting frame
- Voltage divider
- (3) Device plates
 - (1) Center plate: GFCI/rectangular
 - (2) side plates: Rectangular
- (3) Duplex inserts



68-HP-FMK
Flush mounting kit


Optional accessories

Device plates




68-HP-DPC-GFCI 68-HP-DPS-DEC 68-HP-DPC-R 68-HP-DPC-2MAAP 68-HP-DPS-2MAAP

Regular Inserts




68-HP-BI 68-HP-DI OPODEC6-WH**

Extron® AV Plate



68-HP-DPAV-EXT
(Low voltage only)



Divider



Cat. No.	Description	Std. Ctn.
68-HP-FMK	Mounting kit for flush covers	4
68-HP-DPC-GFCI	Center device plate – GFCI/rectangular receptacle	10
68-HP-DPS-DEC	Side device plate – rectangular receptacle	10
68-HP-DPC-R	Center device plate — Single round receptacle, 1 5/8" opening	10
68-HP-DPC-2MAAP	Center device plate – 2 Extron® MAAP plates*	10
68-HP-DPS-2MAAP	Side device plate – 2 Extron® MAAP plates*	10
68-HP-BI	Rectangular insert — blank (for unused compartments)	10
68-HP-DI	Rectangular insert – duplex receptacle	10
OPODEC6-WH	Rectangular adapter for GFCI/rectangular device plate – 6-port data, keystone, white**	5
68-HP-DPAV-EXT	Extron® AV plate – 3 AAP plates, 2 MAAP plates*	1

* Extron® MAAP plates purchased from an authorized Extron® distributor. Extron® is a registered trademark of RGB Systems, Incorporated.
 ** Additional rectangular adapters available for low voltage applications – see Communications Accessories on page 130.

Round floor boxes for power and communications

68-HP Series

Features and benefits:

- Dual-voltage covers for feeding power and communications wiring to modular furniture
- Furniture feed mounting kit required to mount covers to 68-HP Series floor box




68-HP-FFC-ALM



68-HP-FFC-BRS




68-HP-FFC-BLK



68-HP-FFMK




Cat. No.	Description	Std. Ctn.
68-HP-FFC-ALM	Furniture feed cover – solid aluminum with brushed finish	4
68-HP-FFC-BRS	Furniture feed cover – solid brass with brushed finish	4
68-HP-FFC-BLK	Furniture feed cover – solid aluminum with black powder-coated finish	4
68-HP-FFMK	Mounting kit for furniture feed cover	4



Multiple-gang floor boxes for power and communications

640P Series



Features and benefits:

- Significant savings over metal boxes
- Die-cast adjusting ring with unique “snap-on” feature which eliminates gluing
- Reduced installation time; no leveling required
- Compatibility with standard-schedule PVC conduit; 1", 3/4" and 1/2"
- Removable adjusting ring accepts wide variety of service accessories
- One-piece housing unit with premolded conduit holes
- Molded from a high-grade polymer material which is fully compatible with standard- schedule PVC conduit
- 640P Series floor boxes utilize both plastic and brass carpet (P64 series) plates and covers
- Available in one-, two- and three-gang versions. Two- and three-gang boxes provided with partitions in corresponding activation kits
- Min. concrete pour 2 1/2"



Cat. No.	Description	Dimensions (in.)			Max. Volume	Std. Ctn.
		Length	Width	Height		
641P	One-gang box	4	5 3/8	6	85.0 cu. in.	1
642P	Two-gang box	7	5 3/8	6	171.0 cu. in.	1
643P	Three-gang box	10 3/8	5 3/8	6	256.5 cu. in.	1


Carpet activations

640P Series



Cat. No.	Description	Finish	Std. Ctn.
641P-CACA	One-gang carpet trim	Aluminum	4
641P-CACB	One-gang carpet trim	Brass	4
641P-CAC-BGE	One-gang carpet trim	Non-metallic beige	4
641P-CAC-BLK	One-gang carpet trim	Non-metallic black	4
641P-CAC-GRY	One-gang carpet trim	Non-metallic gray	4
642P-CACA	Two-gang carpet trim	Aluminum	4
642P-CACB	Two-gang carpet trim	Brass	4
642P-CAC-BGE	Two-gang carpet trim	Non-metallic beige	4

Cat. No.	Description	Finish	Std. Ctn.
642P-CAC-BLK	Two-gang carpet trim	Non-metallic black	4
642P-CAC-GRY	Two-gang carpet trim	Non-metallic gray	4
643P-CACA	Three-gang carpet trim	Aluminum	4
643P-CACB	Three-gang carpet trim	Brass	4
643P-CAC-BGE	Three-gang carpet trim	Non-metallic beige	4
643P-CAC-BLK	Three-gang carpet trim	Non-metallic black	4
643P-CAC-GRY	Three-gang carpet trim	Non-metallic gray	4




Tile activations

640P Series



Cat. No.	Description	Finish	Std. Ctn.
641P-TACA	One-gang tile trim	Aluminum	4
641P-TACB	One-gang tile trim	Brass	4
641P-TAC-BGE	Non-metallic	Beige	4
641P-TAC-BLK	Non-metallic	Black	4
641P-TAC-GRY	Non-metallic	Gray	4
642P-TACA	Two-gang tile trim	Aluminum	4
642P-TACB	Two-gang tile trim	Brass	4
642P-TAC-BGE	Non-metallic	Beige	4

Cat. No.	Description	Finish	Std. Ctn.
642P-TAC-BLK	Non-metallic	Black	4
642P-TAC-GRY	Non-metallic	Gray	4
643P-TACA	Three-gang tile trim	Aluminum	4
643P-TACB	Three-gang tile trim	Brass	4
643P-TAC-BGE	Non-metallic	Beige	4
643P-TAC-BLK	Non-metallic	Black	4
643P-TAC-GRY	Non-metallic	Gray	4



MopTite® cover plates

640 Series




Plate Dimensions



P-64-DU*




P-64-GFCI



P-64-1/2



P-64-3/4



P-64-3/4-2*




P-64-2-5/8*



P-64-DS*



P-64-1



P-64-1-1/4



P-64-2*



P-64-1/2-2*




Cat. No.	Description	Finish	Std. Ctn.
P-64-1/2	Cover plate 1/2" NPS plug	Brass	4
P-64-3/4	Cover plate 3/4" NPS plug	Brass	4
P-64-3/4-AL	Cover plate 3/4" NPS plug	Aluminum	4
P-64-1	Cover plate 1" NPS plug	Brass	4
P-64-1-AL	Cover plate 1" NPS plug	Aluminum	4
P-64-1-1/4	Cover plate 1 1/4" NPS plug	Brass	4
P-64-1-1/4-AL	Cover plate 1 1/4" NPS plug	Aluminum	4
P-64-2	Cover plate 2" UN plug	Brass	4
P-64-2-AL	Cover plate 2" UN plug	Aluminum	4
P-64-1/2-2	Cover plate 1/2" & 2" UN plug	Brass	4

MopTite® Covers exceed UL/CSA Scrubwater exclusion requirements. For replacement plug, see page 132.

Cat. No.	Description	Finish	Std. Ctn.
P-64-1/2-2-AL	Cover plate 1/2" & 2" UN plug	Aluminum	4
P-64-3/4-2	Cover plate 3/4" & 2" UN plug	Brass	4
P-64-3/4-2-AL	Cover plate 3/4" & 2" UN plug	Aluminum	4
P-64-2-5/8	Cover plate 2 5/8" UN plug	Brass	4
P-64-2-5/8-AL	Cover plate 2 5/8" UN plug	Aluminum	4
P-64-DU	Cover plate duplex 1 1/16" plugs	Brass	4
P-64-DU-AL	Cover plate duplex 1 1/16" plugs	Aluminum	4
P-64-DS	Cover plate duplex lift lids	Brass	4
P-64-DS-AL	Cover plate duplex lift lids	Aluminum	4
P-64-GFCI	Cover plate GFCI flip lid	Brass	4
P-64-GFCI-AL	Cover plate GFCI flip lid	Aluminum	4

MopTite® non-metallic covers

640P Series



Features and benefits:

- Furnished complete with sealing gasket and 8-32 x 1" screws
- 3" x 4½" outside dimension
- All covers meet MopTite® requirements



Cat. No.	Description	Color	Std. Ctn.
P64P-URC-BLK	Universal cover *	Black	4
P64P-URC-GRY	Universal cover *	Gray	4
P64P-URC-BGE	Universal cover *	Beige	4
P64P-BP-BLK	Blank cover	Black	4
P64P-BP-GRY	Blank cover	Gray	4
P64P-BP-BGE	Blank cover	Beige	4

MopTite® Covers exceed UL/CSA Scrubwater exclusion requirements.
 * 5 pieces included, see picture above

Non-metallic carpet plates

640 Series



Features and benefits:

- Polycarbonate material
- Textured finish



Cat. No.	Number of gangs	Description	Finish	Std. Ctn.
P64P-CP-BLK	1	Single-gang carpet plate	Black	4
P64P-CP-GRY	1	Single-gang carpet plate	Gray	4
P64P-CP-BGE	1	Single-gang carpet plate	Beige	4
P64P-2G-CP-BLK	2	Two-gang carpet plate	Black	4
P64P-2G-CP-GRY	2	Single-gang carpet plate	Gray	4
P64P-2G-CP-BGE	2	Two-gang carpet plate	Beige	4
P64P-3G-CP-BLK	3	Three-gang carpet plate	Black	4
P64P-3G-CP-GRY	3	Three-gang carpet plate	Gray	4
P64P-3G-CP-BGE	3	Three-gang carpet plate	Beige	4

MopTite® Covers exceed UL/CSA Scrubwater exclusion requirements.

CONCRETE APPLICATIONS

Above grade floors
recessed service





Floor box

663-SC Series

Features and benefits:

- Multiple service floor box that delivers power, communications and data from standard conduit with no exposed service fittings
- Result: open office planning flexibility
- Ideal for workstations that require power, communications and data service
- Stamped steel, concrete-tight, semi-adjustable
- Galvanized body and hardware
- Shipped complete with expendable cap to prevent ingress of concrete
- Blank- and duplex-face plates can be mounted at either end of the box
- **Does not include duplex faceplate**
- Uses P-62 and P-60 Series covers*



Engineering data for 663 Series floor box





Cat. No.	Dimensions (In.)			Before Pour Adj.	After Pour Adj.	Maximum Capacity (cu. in.)	Conduit KOs	
	A	B	C				Sides	Bottom
663-SC	3 ⁵ / ₈	4 ¹¹ / ₁₆	8 ¹³ / ₁₆	None	3/4"	25 per gang 90 Total	(2) 1-1/4" (4) 3/4"	None



Cat. No.	Covers and carpet plates	Wiring device	Std. Ctn.
663-SC	P-62 Series P-60* Series	Duplex and/or data/voice	4

*P-62-TAR is required when using P-60 series covers.
Caution: To abandon 663 you must use a P-60 series brass cover plate.



Covers, carpet plates and adjusting rings

663 Series



P-60-3B

- Polished brass finish with non-metallic bronze insert
- Plastic insert has one $\frac{7}{8}$ " cutout and two $\frac{1}{2}$ " cutouts
- Furnished complete with sealing gasket, 8-32 x $\frac{1}{2}$ " brass screws and one P-60-Q device plate
- Split cover sections have access notch for screw-driver lift

P-62-CP

- High-strength polycarbonate
- Furnished with one $\frac{7}{8}$ " cutout and two $\frac{1}{2}$ " cutouts and P-60-Q device plate
- 5 $\frac{5}{8}$ " outside diameter

P-62-TAR

- Gives $\frac{3}{4}$ " adjustment when mounted on 663 floor box
- Accepts P-60-3B, P-60-CP and all P-60 Series cover plates (see page 46)

P-60-CP

- Polished-brass finish
- P-62-TAR is required when used on 663 floor box
- 5 $\frac{1}{16}$ " outside diameter



Cat. No.	Description	Std. Ctn.
P-60-3B*	Brass cover plate — Includes 1 P60Q	4
P-62-CP-AS* ²	Polycarbonate cover and carpet plate (charcoal) — Includes 1 P60Q	4
P-62-CP-BRN* ²	Polycarbonate cover and carpet plate (brown) — Includes 1 P60Q	4
P-62-CP-G* ²	Polycarbonate cover and carpet plate (gold) — Includes 1 P60Q	4
P-60-CP	Carpet plate (polished brass)	4
P-60-CP-AL	Carpet plate (aluminum)	4
P-62-TAR	Flange and adjusting ring for 663 Box (brass)	4
P-62-TAR-AL	Flange and adjusting ring for 663 Box (aluminum)	4
P-60-Q	Duplex receptacle plate for 663 floor box	4
P-60-QB	Blank plate for 663 floor box	4
P-60-Q-GFCI	GFCI plate for 663 floor box	4

* For use as cover only when box is in service.

² When not in use, the P-62-CP Series Cover should be replaced by P-60-CP, P-60 and P-62 TAR Series Covers.




Caution: These covers are not to be used in high traffic areas.
For communications accessories, see page 132.

Multiple-service floor boxes for power, communications and data: 664 Series

Features and benefits:

Multiple-service floor boxes deliver power, communications and data from standard conduit with no exposed service fittings. Result: Open office planning flexibility. Ideal for the modern office with workstations that have power, communications and data equipment. Power receptacles and low-voltage connections can be enclosed underfloor in either steel or cast-iron bodies. Galvanized 14-gauge steel boxes are provided with knockouts from 3/8" to 1 1/2" (see engineering data). Cast-iron bodies have threaded openings for 3/4" and 1" conduit.

- Two-compartment box is available in three configurations: stamped steel (664-SC), shallow (664-S) and cast iron (664-CI)
- Durable non-metallic covers include a steel reinforcement plate for added strength
- Metallic covers in solid brass, aluminum and aluminum black powder-coated provide aesthetics and durability
- Cover flange self-levels with the finished floor for easy installation



664-SC

664-S

Cat. No.	Description	Std. Ctn.
664-SC	Stamped-steel box which accepts two plates, with one duplex 664-RP provided	4
664-S	Shallow stamped-steel box which accepts two plates, with one duplex 664-S-RP provided	4

Note: When ordering a 664 Series box, the cover must be ordered separately. See page 15. For communications accessories, see page 130.

Engineering data for 664 Series




Cat. No.	Dimensions (in.)			Before Pour Adj. (in.)	After Pour Adj. (in.)	Maximum capacity (cu. in.)	Conduit Hubs	Conduit KOs		
	A	B	C					Sides	Bottom	Covers
664-SC	3 3/4	4 11/16	10 1/4	2 1/2	3/4	24 per gang, 90 total	—	(4) 1"–1 1/4" (4) 3/4"	None	664-CST Series
664-S	2 7/8	4 11/16	10 1/4	1 1/2	3/4	16.5 per gang, 70 total	—	(6) 3/4"	None	664-CST Series

CAUTION: When using the center side KOs, Cat. No. 664-RP must be assembled to the box prior to installing the conduit.

Non-metallic covers

664 Series floor boxes

Covers for all boxes



664-CST-SW

MopTite® covers meet UL/CSA scrubwater exclusion requirements for carpet, tile and wood.



Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
664-CST-SW-GRY	Gray cover	1,500	1
664-CST-SW-BRN	Brown cover	1,500	1
664-CST-SW-BGE	Beige cover	1,500	1
664-CST-SW-BLK	Black cover	1,500	1

Metallic covers


664 Series floor boxes



664-CST-M-BRS
Solid brass

664-CST-M-ALM
Solid aluminum

664-CST-M-BLK
Solid aluminum cover, black powder coated




MopTite® covers meet UL/CSA scrubwater exclusion requirements for carpet, tile and wood.




Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
664-CST-M-BRS	Solid brass cover for 664 Series floor boxes	2,250	1
664-CST-M-ALM	Solid aluminum cover for 664 Series floor boxes	2,250	1
664-CST-M-BLK	Solid aluminum cover, black powder coated for 664 Series floor boxes	2,250	1

Non-metallic covers

664 Series floor boxes



664-S-RP




664-S-BP




Cat. No.	Description	Std. Ctn.
664-S-RP	Receptacle plate for use with 664-S floor box	4
664-S-BP	Blank plate for use with 664-S floor box	4

Wire tunnel

664 Series



664-WT



664-S-WT


- Wire tunnel for protecting electrical connections between the two receptacles when the box is used for power/power application




Cat. No.	Description	Std. Ctn.
664-WT	For use with 664 and 664-CI floor boxes	4
664-S-WT	For use with 664-S floor box	4

Device plates


664-SC & 664-CI Series




664-RP



664-GP



664-BP



664-2-MAAP

- Receptacle face plate for 664 Series floor box for additional power service
- Does not include receptacle. Can be placed at either end of floor box



Cat. No.	Description	Std. Ctn.
664-RP	For use with 664 and 664-CI floor boxes	4
664-BP	Blank plate for use with 664 & 664-CI floor boxes	4
664-GP	GFCI receptacle plate	4
664-2-MAAP	Device panel, accepts 2 Extron MAAP plates	4




CAUTION: When using the center side KO's, all 664 plates must be assembled to the box prior to installing the conduit.

Stamped steel above grade applications


665-SC Series

Features and benefits:


- Four (4) device compartments can accommodate any combination of devices.
For example: (3) duplex power devices and (1) duplex telephone device, or (2) voice and data connectors and (1) GFCI device and (1) blank, etc.
- Overall height of 3 1/2" allows for shallow pours when needed
- High-strength polycarbonate cover with a 5/32" steel plate assures structural integrity
- Metallic Covers also available in solid brass and aluminum and black
- Four-side feed-through allows installer to feed through power or data/comm service from any orientation
- Non-metallic wire tunnels aesthetically clean. Full-width tunnel provides maximum feed-through capacity; non-metallic material prevents conductor damage
- Total access area of 126 cu. in. allows for friendly installation of workstation cables
- Contains 28 knockouts (16-1 1/4" and 12 3/4" KOs) that provide increased flexibility when installed
- The 665 line is an extension of the 664 Series; our concealed service line now allows the customer to install up to four device panels in one box
- Through the use of a unique non-metallic wire tunnel, the installer can easily partition the power, voice/data requirements
- This UL/CSA Listed, stamped steel floor box can be installed with ABB voice and data connector products
- Four 2 1/2" levelling screws provided with all boxes
- **Device plate and box cover must be ordered separately**



Top View



Bottom Plate



Cat. No.	Description	Length	Width	Device Compartments (IN.)		Device Access Area	Std. Ctn.
				Height	Area		
665-SC	Stamped steel box	5 3/4	2 3/4	2 1/2	40 cu. in.	126 cu. in.	1


Material: Pre-galvanized steel.
For communication accessories, see page 130.

2" KOs for audio visual applications

665 Series - 665-AV2

Features and benefits:

- 2" KOs enable pre-terminated AV cables and connectors to be pulled directly through the conduit
- Accepts standard 665 Series covers and device plates for power, voice, data and audio visual connections
- Rectangular adapters allow voice, data and AV connectors to be mounted in a standard GFCI device plate
- Keystone style voice, data and AV connectors meet a wide range of low-voltage applications.
- All connectors are recessed for flush mounting in floor box applications
- Device plates are available that accept Extron®
- MAAP plates to accommodate any AV requirements (Extron® MAAP plates purchased from an authorized Extron distributor)
- Metallic covers provide a durable, aesthetic installation, including solid brass covers, aluminum and black powder painted aluminum
- **Device plate and box cover must be ordered separately**




Rectangular adapters and Keystone Inserts for GFCI Device Plates (see page 131)



Cat. No.	Description	Std. Ctn.
665-AV2	4-Compartment recessed service floor Box with 2" KOs for AV applications	1

Extron® is a registered trademark of RGB Systems, Inc.
For communication accessories, see page 130.

Engineering Information



665-AV2 Floor box engineering data




Cat. No.	Before Pour Adj. (in.)	After Pour Adj. (in.)	Length (in.)	Compartment size & capacity (qty = 4)			Conduit KOs (in.)	
				Width (in.)	Height (in.)	Volume	Sides	Bottom
665-AV2	2 1/2	3/4	(2) 5 3/4	3 3/4	3 3/8	72 cu. in.	(4) 2	(2) 2
			(2) 5 3/4	2 3/4	3 3/8	52 cu. in.	(8) 1 1/4	(2) 1 1/4
							(8) 3/4	(4) 3/4

Metallic covers

665 Series floor boxes





665-CST-M-BRS
Solid brass



665-CST-M-ALM
Solid aluminum



665-CST-M-BLK
Solid aluminum, black powder coated




Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
665-CST-M-BRS	Solid brass cover for 665 Series floor boxes	1,500	1
665-CST-M-ALM	Solid aluminum cover for 665 Series floor boxes	1,500	1
665-CST-M-BLK	Solid aluminum cover, black powder coated for 665 Series floor boxes	1,500	1

Non-metallic covers

665 Series floor boxes



665-CST-SW-BLK
Black non-metallic cover



Cat. No.	Description	Load Rating (lbs.)	Std. Ctn.
665-CST-SW-BLK	Non-metallic cover for 665 Series floor boxes, black	750	1
665-CST-SW-GRY	Non-metallic cover for 665 Series floor boxes, gray	750	1
665-CST-SW-BGE	Non-metallic cover for 665 Series floor boxes, beige	750	1
665-CST-SW-BRN	Non-metallic cover for 665 Series floor boxes, brown	750	1


Furnished with (4) #8-32 x 3/8" mounting screws.
Contact ABB Technical Service for Color Chip samples.

Device plates and accessories


665 Series floor boxes



665-RP
Duplex plate



665-GP
GFCI plate



665-BP
Blank plate



665-6RJ
Data plate for 6 keystone jacks









665-WT
Wire tunnel feeds multiple compartments from a single conduit (one included with each 665-AV2 and 665-SC)



Cat. No.	Description	Std. Ctn.
665-RP	Duplex plate for 665 Series floor boxes	4
665-GP	GFCI plate for 665 Series floor boxes	4
665-BP	Blank plate for 665 Series floor boxes	4
665-6RJ	Data plate for 665 Series floor boxes, accepts 6 keystone jacks	4
665-STEL	Telephone data plate for 665 Series floor boxes	4
665-WT	Replacement wire tunnel for 665-SC, 665-CI & 665-AV2 floor boxes	4

Each box requires (4) device plates. Material: Pre-galvanized steel.





Floor box



667-SC Series

Features and benefits:


- Large capacity concealed-service floor box
 - Four “double-gangs” allow for two receptacles per gang, for a total of eight receptacles per box
 - Each gang has 40 cu. in. of capacity
 - Box interior has 128 cu. in. of capacity
- Standard box configuration is for up to eight power and/or low-voltage devices
 - Box design allows for feed-through cabling for power and low-voltage conductors
- Shallow design
 - 3" overall height is ideal for renovations and upper level floor installations
- Full line of low-profile covers
 - Utilizes same quality cover as AFM-8 Access Floor Module
 - High-strength polycarbonate
 - Steel reinforced for added durability
 - Two retractable cable exit ports
 - 64 sq. in. opening provides easy access to device panels
 - 1/4" recess for carpet/tile insert
 - Available in gray, black, brown and beige
- Box is manufactured with (1) 3/4", (3) 1" and (1) 1 1/4" KOs per gang
 - This includes a 1" and 1 1/4" KO located in the bottom
- Full complement of device panels
 - Device panels available with one or two duplex openings, one or two GFI openings, six standard “keystone” with Omni 110 bezels and blanks
- Provided with leveling legs and base feet
 - Base feet can be attached to form, preventing box movement during concrete pour
 - Leveling legs provide up to 1 1/2" pre-pour adjustment
- Manufactured from 14-gauge pre-galvanized steel
 - Quality construction provides added durability and rust protection
 - MopTite® covers meet UL/CSA scrubwater exclusion requirements for carpet, tile and wood



Floor Box Bottom



Floor Box Top




Cat. No.	Description	Std. Ctn.
667-SC	Four-gang recessed floor box	1

Supplied with (1) 667-2RP for 2 duplex receptacles and (1) 667-BP blank plate. For covers and other device plates, see page 66.
For communications accessories, see page 130.

Covers and device plates

667-SC Series

For brass and aluminum covers, use 668 series



Device plates




Cat. No.	Description	Std. Ctn.
667-BP	Blank device panel	4
667-RP	Single duplex receptacle Plate	4
667-2RP	Device panel for 2 duplex receptacles with duplex KOs	4
667-1G	Device panel for 1 GFCI receptacle	4
667-2G	Device panel for 2 GFCI receptacles	4
667-6RJ*	Device panel for 6 Keystone data jacks	4

Covers

Cat. No.	Description	Std. Ctn.
667-CST-SW-GRY	Cover and flange – gray	4
667-CST-SW-BLK	Cover and flange – black	4
667-CST-SW-BRN	Cover and flange – brown	4
667-CST-SW-BGE	Cover and flange – beige	4

*For data connectors and adapters, see page 130.
MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.



667-CST-SW-XXX


Ultra-shallow box

668-S Series


The 668-S ultra-shallow floor box from ABB provides a high-capacity power and data solution for shallow concrete floors. The low-profile 4-gang box is constructed of galvanized stamped steel. Removable voltage dividers enable users to customize wiring configurations by feeding two or more adjacent compartments with a single conduit. Metallic covers with durable powder-coat finish are designed to match any decor, while optional trim rings enable covers to be mounted completely flush with the floor in tile or wood floor applications.

Features and benefits:


- Low profile (2½" height) for shallow concrete pours
- 4-gang, recessed service for a high-capacity, aesthetic floor box solution
- Stamped-steel box construction
- Removable voltage dividers between compartments enable a single conduit to feed two or more adjacent compartments
- Metallic covers feature durable powder-coat paint to match any decor (black, gray, brown and beige)
- Heavy-duty cord door in the cover latches firmly in the open position to prevent damage to cables
- Optional tile trim enables flush mounting for tile and wood floor applications
- MopTite® covers meet UL/CSA scrubwater exclusion requirements for carpet, tile and wood
- Largest cubic-inch capacity of any shallow, recessed 4-gang floor box
- Additional KOs (up to 2") on the bottom of the box enable installation flexibility
- Custom device panels are available – contact technical service about these offerings



Top view - compartment layout
Note: Shown with top plate removed



Top view



Side view



Cat. No.	Description	Std. Ctn.
668-S	Shallow, concealed service floor box	1


For covers and device plates, see page 67.
For communications accessories, see page 130.

Covers and tile trims

668-S floor box

01 Per terrazzo floors, polish and grind against floor box trim.


02 Flush mounting configuration: Optional trim ring allows cover to be mounted flush with tile, wood floors and concrete.




01

02

Cover



Section A-A



Trim rings




Cat. No.	Description	Std. Ctn.
668-CST-ALM	668-S metal cover – aluminum powdercoat	1
668-CST-BRS	668-S Metal Cover – brass powdercoat	1
668-CST-BLK	668-S metal cover – black powdercoat	1
668-CST-BRN	668-S metal cover – brown powdercoat	1
668-CST-BGE	668-S metal cover – beige powdercoat	1
668-TRIM-ALM*	668-S trim ring – aluminum powdercoat	4
668-TRIM-BRS *	668-S trim ring – brass powdercoat	4
668-TRIM-BLK*	668-S trim ring – black powdercoat	4
668-TRIM-BRN*	668-S trim ring – brown powdercoat	4
668-TRIM-BGE*	668-S trim ring – beige powdercoat	4

Contact technical service for color samples.


* Trim for flush mounting




668-S-1RP



668-S-1G



668-S-BP




668-S-6AVA

Device plates




Cat. No.	Description	Std. Ctn.
668-S-1RP	668-S single-gang duplex plate	1
668-S-1G	668-S single-gang GFCI plate	1
668-S-BP	668-S blank plate	1
668-S-6RJ	668-S data plate – 6 Keystone jacks	1
668-S-6PAN	668-S data plate – 6 Panduit® jacks	1
668-S-6ORT	668-S data plate – 6 Ortonics® jacks	4
668-S-6AVA	668-S data plate – 6 Avaya® jacks	4

Concrete Inserts



GAB-8-S




GAB-8-S with AFM-8

- The only box that can be installed in this insert is the AFM-8 (see page 107)

Cat. No.	Dimensions (In.)			Maximum capacity (cu. in.)	Standard conduit tapping	Maximum conduit tapping	Afm Insert	Std. Ctn.
	A	B	C					
GAB-8-S	5 $\frac{7}{8}$	9 $\frac{3}{4}$	16 $\frac{3}{8}$	325	2- $\frac{3}{4}$ " 2-1 $\frac{1}{4}$ "	—	AFM-8	1

*Required for installation of an AFM-8 in concrete pours only.




CONCRETE APPLICATIONS

Above grade floors flush service



Round floor boxes for power or communications

68 Series



- Stamped steel, concrete-tight, fully adjustable
- Electro-galvanized body and hardware
- Interior and exterior leveling screws permit adjustment to meet finished floor
- Shipped complete with expendable cap to prevent ingress of concrete during pour 1/2", 3/4" and 1" knockouts – all bottom knockouts are accessible
- Uses P60 Series MopTite® covers and carpet plate





Cat. No.	Description	Std. Ctn.
68-D	Stamped-steel floor box, deep	4
68-D-AL	Stamped-steel with aluminum trim ring, deep	4
68-S	Stamped-steel floor box, shallow	4
68-S-AL	Stamped-steel with aluminum trim ring, shallow	4
600-4-FL	Trim ring brass	4
600-4-FL-AL	Trim ring aluminum	4

Engineering data – 68 Series



Cat. No.	Dimensions (in.)			Before pour adj. (in.)	After pour adj. (in.)	Maximum capacity kos (cu. in.)	Conduit hubs	Conduit KOs (in.)	
	A	B	C					Sides	Bottom
68-D	4 1/4	3 5/8	4 11/16	2 1/2	1 1/2	60	—	(4) 3/4	(2) 1/2
68-S	4 1/4	2 3/4	4 11/16	1 1/2	1 1/2	47	—	(4) 1	(2) 3/4



MopTite® carpet plates


68 Series

- 01 P-60-3/4-2-CACP
- Polished brass finish
- Integrated carpet plate and 3/4"-2" floor plate in one unit
- Furnished complete with sealing gasket and 8-32 x 1" brass screws
- 5 3/4" outside diameter



01

- 02 P-60-CP
- Polished brass finish
- Furnished complete with 8-32 x 1" brass screws
- For brushed aluminum, add AL after catalog number



02




03

- 03 P-60-LCP
- Translucent polycarbonate
- Textured finish



04

- 04 P-60-CACP
- Polished-brass finish
- Integrated carpet plate and duplex floor plate in one unit




05

- 05 P-60-CACP-GFCI
- Furnished complete with sealing gasket and 8-32 x 1" brass screws
- 5 3/4" outside diameter



Cat. No.	Description	Std. Ctn.
P-60-CP	Brass carpet plate, 5 11/16" diameter	4
P-60-CPAL	Aluminum carpet plate	4
P-60-LCP	Polycarbonate carpet plate, 5 3/8" diameter	4
P-60-CACP	Brass one-piece carpet cover plate	4
P-60-CACP-AL	Aluminum one-piece carpet	4
P-60-3/4-2-CACP	Brass one-piece carpet plate with 3/4"-2" plugs	4
P60-3/4-2-CACP-AL	Aluminum one-piece carpet plate with 3/4"-2" plugs	4
P60-CACP-GFCI	Brass one-piece carpet plate for GFCI devices	4
P60-CACP-GFCI-AL	Aluminum one-piece carpet plate for GFCI devices	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.



P-60-CACP

MopTite® cover plates

68 Series

Features and benefits:

- Polished finish
- Furnished complete with sealing gasket and 8-32 x $\frac{7}{16}$ " screws
- 4" outside diameter

* Also includes steel seating plate for receptacles



P-60-1/2
½" N.P.S. plug size



P-60-3/4
¾" N.P.S. plug size




P-60-1
1" N.P.S. plug size




P-60-1-1/4




P-60-2*
2" dia. plug size



P-60-2-5/8*
2½" dia. plug size



P-60-1/2-2*
½" & 2" dia. plug size



P-60-3/4-2*
¾" & 2" dia. plug size




P-60-DR*
Duplex liftlid



P-60-DU*
Duplex 17/16" plugs



P-60-DS*
Hinged lift lids



P-60-GFCI*



	Cat. No.	Description	Std. Ctn.
	P-60-1/2	Brass cover plate ½" NPS plug size	4
	P-60-1/2-AL	Aluminum cover plate ½" NPS plug size	4
	P-60-3/4	Brass cover plate ¾" NPS plug size	4
	P-60-3/4-AL	Aluminum cover plate ¾" NPS plug size	4
	P-60-1	Brass cover plate 1" NPS plug size	4
	P-60-1-AL	Aluminum cover plate 1" NPS plug size	4
	P-60-1-1/4	Brass cover plate 1¼" NPS plug size	4
	P-60-1-1/4-AL	Aluminum cover plate 1¼" NPS plug size	4
	P-60-2	Brass cover plate 2" diameter plug size	4
	P-60-2-AL	Aluminum cover plate 2" diameter plug size	4
	P-60-2-5/8	Brass cover plate 2½" diameter plug size	4
	P-60-2-5/8-AL	Aluminum cover plate 2½" diameter plug size	4
	P-60-1/2-2	Brass cover plate ½"-2" diameter plug size	4
	P-60-1/2-2-AL	Aluminum cover plate ½"-2" diameter plug size	4
	P-60-3/4-2	Brass cover plate ¾"-2" diameter plug size	4
	P-60-3/4-2-AL	Aluminum cover plate ¾"-2" diameter plug size	4
	P-60-DR	Brass cover with duplex lift lid	4
	P-60-DS	Brass cover for duplex with individual lift lids	4
	P-60-DS-AL	Aluminum cover for duplex with individual lift lids	4
	P-60-DU	Brass cover plate with two 17/16" plugs for duplex	4
	P-60-DU-AL	Aluminum cover with two 17/16" plugs for duplex	4
	P-60-GFCI	Brass cover plate for GFCI devices	4
P-60-GFCI-AL	Aluminum cover plate for GFCI devices	4	

68P-FL or 68P-FL-AL required to attach cover plates to 68-P floor box.
MopTite® Covers exceed UL/CSA watertight requirements for 514A, 514C.



Multiple-gang floor boxes for power and communications

740 Series

The 740 Series line of stamped-steel floor boxes are an extension of ABB's 640 and 840 series cast-iron floor boxes. The boxes provide flush service for power, communications and data. Multiple-gang boxes allow the user to place high- and low-voltage in a single floor box. The 740 series can be used for carpet or tile applications.

Features and benefits:

- Available in shallow (2⁵/₈"") and deep (3⁵/₈"") versions
- Available in one-, two- and three-gang versions
- **Two- and three-gang boxes are supplied with customer-installed dividers**
- 16 ga. pre-galvanized steel construction
- Adjustable with four exterior leveling legs capable of 2" pre-pour adjustment and an interior leveling ring capable of 1¹/₄" after-pour adjustment
- Made with a variety of KOs ranging from 1/2" to 1¹/₄"
- Boxes utilize the 640P series metallic and non-metallic floor box accessories with the unique one-step installation method
- Shipped with expendable steel cap to prevent ingress of concrete at installation



Cat. No.	Description	Std. Ctn.
741-S	Shallow one-gang steel floor box for concrete construction	4
742-S	Shallow two-gang steel floor box for concrete construction	1
743-S	Shallow three-gang steel floor box for concrete construction	1
741-D	Deep one-gang steel floor box for concrete construction	4
742-D	Deep two-gang steel floor box for concrete construction	1
743-D	Deep three-gang steel floor box for concrete construction	1


Engineering Data for 740 Series



Cat. No.	Dimensions (in.)			Adjustment (in.)		Capacity per gang	Sides	Ends	Bottom
	A	B	C	Before pour	After pour				
741-S	4	5 ¹ / ₂	2 ⁵ / ₈	2	1 ¹ / ₂	29 cu. in.	(2) 3/4	(2) 1/2	(1) 1/2 & (1) 3/4
742-S	7 ¹ / ₄	5 ¹ / ₂	2 ⁵ / ₈	2	1 ¹ / ₂	26 cu. in.	(4) 3/4	(2) 1/2	(2) 1/2 & (2) 3/4
743-S	10 ¹ / ₄	5 ¹ / ₂	2 ⁵ / ₈	2	1 ¹ / ₂	26 cu. in.	(6) 3/4	(2) 1/2	(3) 1/2 & (3) 3/4
741-D	4	5 ¹ / ₂	3 ⁵ / ₈	2	1 ¹ / ₂	48 cu. in.	(2) 3/4	(2) 1 ¹ / ₄	(1) 1/2 & (1) 3/4
742-D	7 ¹ / ₄	5 ¹ / ₂	3 ⁵ / ₈	2	1 ¹ / ₂	41 cu. in.	(2) 1/2 & (2) 3/4	(2) 1 ¹ / ₄	(2) 1/2 & (2) 3/4
743-D	10 ¹ / ₄	5 ¹ / ₂	3 ⁵ / ₈	2	1 ¹ / ₂	41 cu. in.	(3) 1/2 & (3) 3/4	(3) 1 ¹ / ₄	(3) 1/2 & (3) 3/4

MopTite® cover plates

740 Series



Carpet activations for 740 Series




Cat. No.	Description	Finish	Std. Ctn.
641P-CACA	One-gang carpet trim	Aluminum	4
641P-CACB	One-gang carpet trim	Brass	4
641P-CAC-BGE	One-gang carpet trim	Non-metallic beige	4
641P-CAC-BLK	One-gang carpet trim	Non-metallic black	4
641P-CAC-GRY	One-gang carpet trim	Non-metallic gray	4
642P-CACA	Two-gang carpet trim	Aluminum	4
642P-CACB	Two-gang carpet trim	Brass	4
642P-CAC-BGE	Two-gang carpet trim	Non-metallic beige	4
642P-CAC-BLK	Two-gang carpet trim	Non-metallic black	4
642P-CAC-GRY	Two-gang carpet trim	Non-metallic gray	4
643P-CACA	Three-gang carpet trim	Aluminum	4
643P-CACB	Three-gang carpet trim	Brass	4
643P-CAC-BGE	Three-gang carpet trim	Non-metallic beige	4
643P-CAC-BLK	Three-gang carpet trim	Non-metallic black	4
643P-CAC-GRY	Three-gang carpet trim	Non-metallic gray	4


Tile activations for 740 Series



Cat. No.	Description	Finish	Std. Ctn.
641P-TACA	One-gang tile trim	Aluminum	4
641P-TACB	One-gang tile trim	Brass	4
641P-TAC-BGE	One-gang tile trim	Non-metallic beige	4
641P-TAC-BLK	One-gang tile trim	Non-metallic black	4
641P-TAC-GRY	One-gang tile trim	Non-metallic gray	4
642P-TACA	Two-gang tile trim	Aluminum	4
642P-TACB	Two-gang tile trim	Brass	4
642P-TAC-BGE	Two-gang tile trim	Non-metallic beige	4
642P-TAC-BLK	Two-gang tile trim	Non-metallic black	4
642P-TAC-GRY	Two-gang tile trim	Non-metallic gray	4
643P-TACA	Three-gang tile trim	Aluminum	4
643P-TACB	Three-gang tile trim	Brass	4
643P-TAC-BGE	Three-gang tile trim	Non-metallic beige	4
643P-TAC-BLK	Three-gang tile trim	Non-metallic black	4
643P-TAC-GRY	Three-gang tile trim	Non-metallic gray	4




Carpet activation kit




Tile activation kit

MopTite® cover plates

740 Series



P-64-DS*
Duplex Lift lids



P-64-2-5/8*
2 5/8" dia. plug




P-64-3/4-2*
3/4" & 2" dia. plug



P-64-DU*
Duplex 1 7/16" plugs



P-64-GFCI




P-64-1/2
1/2" N.P.S. plug




P-64-3/4
3/4" N.P.S. plug



P-64-1
1" N.P.S. plug



P-64-1-1/4
1 1/4" N.P.S. plug



P-64-2*
2" dia. plug




P-64-1/2-2*
1/2" & 2" dia. plug

*Also includes seating plate for receptacle like others.




Cat. No.	Description	Finish	Std. Ctn.
P-64-1/2	Cover plate 1/2" NPS plug	Brass	4
P-64-3/4	Cover plate 3/4" NPS plug	Brass	4
P-64-3/4-AL	Cover plate 3/4" NPS plug	Aluminum	4
P-64-1	Cover plate 1" NPS plug	Brass	4
P-64-1-AL	Cover plate 1" NPS plug	Aluminum	4
P-64-1-1/4	Cover plate 1 1/4" NPS plug	Brass	4
P-64-1-1/4-AL	Cover plate 1 1/4" NPS plug	Aluminum	4
P-64-2	Cover plate 2" UN plug	Brass	4
P-64-2-AL	Cover plate 2" UN plug	Aluminum	4
P-64-1/2-2	Cover plate 1/2" & 2" UN plug	Brass	4
P-64-1/2-2-AL	Cover plate 1/2" & 2" UN plug	Aluminum	4
P-64-3/4-2	Cover plate 3/4" & 2" UN plug	Brass	4
P-64-3/4-2-AL	Cover plate 3/4" & 2" UN plug	Aluminum	4
P-64-2-5/8	Cover plate 2 5/8" UN plug	Brass	4
P-64-2-5/8-AL	Cover plate 2 5/8" UN plug	Aluminum	4
P-64-DU	Cover plate duplex 1 7/16" plugs	Brass	4
P-64-DU-AL	Cover plate duplex 1 7/16" plugs	Aluminum	4
P-64-DS	Cover plate duplex lift lids	Brass	4
P-64-DS-AL	Cover plate duplex lift lids	Aluminum	4
P-64-GFCI	Cover plate GFCI Flip lid	Brass	4
P-64-GFCI-AL	Cover plate GFCI Flip lid	Aluminum	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.
For replacement plug, see page 132.



MopTite® non-metallic cover plates

740 Series



Features and benefits:

- Furnished complete with sealing gasket and 8-32 x 1" screws
- 3" x 4½" outside dimension
- All covers meet MopTite® requirements




Cat. No.	Description	Finish	Std. Ctn.
P64P-URC-BLK	Universal cover	Black	4
P64P-URC-GRY	Universal cover	Gray	4
P64P-URC-BGE	Universal cover	Beige	4
P64P-URC-BRN	Universal cover	Brown	4
P64P-BP-BLK	Blank cover	Black	4
P64P-BP-GRY	Blank cover	Gray	4
P64P-BP-BGE	Blank cover	Beige	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.

* 5 pieces included, see picture above.

Non-metallic carpet plates

740 Series



Features and benefits:

- Polycarbonate material
- Textured finish



Cat. No.	Number of gangs	Description	Finish	Std. Ctn.
P64P-CP-BLK	1	Single-gang carpet plate	Black	4
P64P-CP-GRY	1	Single-gang carpet plate	Gray	4
P64P-CP-BGE	1	Single-gang carpet plate	Beige	4
P64P-2G-CP-BLK	2	Two-gang carpet plate	Black	4
P64P-2G-CP-GRY	2	Single-gang carpet plate	Gray	4
P64P-2G-CP-BGE	2	Two-gang carpet plate	Beige	4
P64P-3G-CP-BLK	3	Three-gang carpet plate	Black	4
P64P-3G-CP-GRY	3	Three-gang carpet plate	Gray	4
P64P-3G-CP-BGE	3	Three-gang carpet plate	Beige	4

MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.

Floor boxes for single short-strap receptacles or communications

88 S Series

Service fitting application

88 Series Floor Boxes provide flush service for power or communications and data. They can be used for either carpet or tile applications.



88 Series

88 Series – features and benefits

- Stamped steel, concrete-tight, semi-adjustable
- Electro-galvanized body and hardware
- Exterior leveling screws and threaded vertical adjusting ring permit adjustment to meet finish floor
- Shipped complete with expandable cap to prevent ingress of concrete during pour
- 1/2" and 3/4" knockouts – all bottom knockouts accessible
- Uses P90 Series MopTite® covers




Cat. No.	Description	Std. Ctn.
88-S	Shallow version stamped steel	4

Engineering Data




Cat. No.	Dimensions (in.)			Before pour adj. (in.)	After pour adj. (in.)	Maximum capacity (cu. in.)	Standard conduit tapping (in.)
	A	B	C				
88-S	3	2 3/4	5 3/4	1 1/2	3/4	23	—

Cat. No.	Maximum conduit tapping (in.)		Conduit KOs (in.)		Covers and Carpet Plates	Wiring device
	w/bushing	w/o bushing	Sides	Bottom		
88-S	—	—	(2) 1/2 (2) 3/4	(3) 1/2 (2) 3/4	P90 series	Sing. short strap rec.




MopTite® cover plates

88 Series




P-90-3/4-AL
3/4" N.P.S. plug




P-90-1-AL
1" N.P.S. plug




P-90-1-1/4
1 1/4" N.P.S. plug




P-90-2-AL*
2" dia. plug



P-90-1/2-2*
1/2" & 2" dia. plugs



P-90-3/4-2*
3/4" & 2" dia. plugs



Features and benefits:

- Polished-brass finish
- Furnished complete with sealing gasket and 6-32 x 1/2" screws
- 2 13/16" outside diameter



Cat. No.	Description	Finish	Std. Ctn.
P-90-3/4-AL	Cover plate 3/4" NPS plug	Aluminum	4
P-90-1-AL	Cover plate 1" NPS plug	Aluminum	4


MopTite® Covers exceed UL/CSA scrubwater exclusion requirements.
*Also includes steel seating plates for receptacles.

Cat. No.	Description	Finish	Std. Ctn.
P-90-1-1/4-AL	Cover plate 1 1/4" NPS plug	Aluminum	4
P-90-2-AL	Cover plate 2" UN plug	Aluminum	4
P-90-1/2-2	Cover plate 1/2" & 2" plug	Brass	4
P-90-3/4-2	Cover plate 3/4" & 2" plug	Brass	4
P-90-3/4-2-AL	Cover plate 3/4" & 2" plug	Aluminum	4

Accessories

88 Series floor boxes

- Seven cubic inch capacity
- 15-Amp, 125-Volt, NEMA grounding type
- Mounted on steel seating plate
- For use with 2" diameter-opening floor plate



478-G-12




Cat. No.	Description	Std. Ctn.
478-G-12	15-Amp 125-Volt NEMA grounding receptacle	4

Carpet plate

88 Series floor boxes

- Polished-brass finish
- Furnished complete with 6-32 x 1" brass flathead screws and gasket
- Threaded 2-20UN-2B to accept 694 plug
- 3 3/8" O.D. with 5/8" flange



Cat. No.	Description	Finish	Std. Ctn.
P-90-CP	Carpet plate	Brass	4

CONCRETE APPLICATIONS

Fire rated poke-through



Fire-Rated Poke-through systems

Capacity, durability, flexibility – everything you've been looking for in a Poke-through



FPT3 Series

- Accommodates 1 duplex receptacle and 2 data jacks



FFPT3 Series

- Concentric 2" and 1¹/₄" hub for power or communications
- Core drill size: 3"



FPT Flush Series

- Accepts 1 duplex receptacle
- Core drill size: 3"



FPT furniture feed Series

- 3 conduit hubs: (2) 1¹/₂" and (1) 3³/₄" for power and communications
- Core drill size: 3"

Flush power & communications



FPT4 Series

- Maximum capacity and flexibility for flush-mounted power and communications devices, including the popular "4 x 4" configuration (4 power outlets, 4 communications devices)
- Core drill size: 4"

Furniture feed



FFPT4 Series

- 2 Conduit hubs: 3³/₄" for power and 1¹/₄" for communications
- Core drill size: 4"



Above floor pedestals



FPT Above-floor pedestals

- Available in 2 compartment and 4 compartment for power and communications
- Core drill size: 3"

FPT Flush Series



The Steel City® FPT Poke-through Series provides an economical solution for installing a duplex receptacle in an existing floor – right where you need it.

Features and benefits:

- Capacity: 1 duplex receptacle
- Core drill size: 3"
- Brushed brass and aluminum covers provide superior aesthetics and durability
- Non-metallic covers are available in black, gray, beige and brown
- Non-metallic covers include openings for 3 communications cables
- Integral junction box features (5) 1/2" and (5) 3/4" knockouts (27 cubic inch capacity)
- Assembled units include (1) 20A duplex receptacle, pre-wired with pigtail ends in junction box
- **For use on carpet floors only**

Poke-through: 2 power



Cat. No.	Description	Std. Ctn.
FPT-449	FPT Flush Poke-through assembly: base unit with solid-brass cover	1
FPT-450	FPT Flush Poke-through assembly: base unit with solid-aluminum cover	1
FPT-445-SW-BLK	FPT Flush Poke-through assembly: base unit with black non-metallic cover	1
FPT-445-SW-GRY	FPT Flush Poke-through assembly: base unit with gray non-metallic cover	1
FPT-445-SW-BRN	FPT Flush Poke-through assembly: base unit with brown non-metallic cover	1
FPT-445-SW-BRS	FPT Flush Poke-through assembly: base unit with non-metallic brass cover	1
FPT-400B	FPT Poke-through base unit only (no duplex): cover purchased separately	1


- Non-metallic covers feature 3 openings for communications cables

Brushed metal finishes



FPT-CACP FPT-CACP-AL

Non-metallic colors and finishes



FPT-441-SW-BLK FPT-441-SW-GRY FPT-441-SW-BRS FPT-441-SW-BRN


Poke-through covers



Cat. No.	Description	Std. Ctn.
FPT-CACP	Solid brass, brushed finish, 5 3/4" diameter	10
FPT-CACP-AL	Solid aluminum, brushed finish, 5 3/4" diameter	10
FPT-441-SW-BLK	Black, non-metallic, 7" diameter	10
FPT-441-SW-GRY	Gray, non-metallic, 7" diameter	10
FPT-441-SW-BRS	Brass, non-metallic, 7" diameter	10
FPT-441-SW-BRN	Brown, non-metallic, 7" diameter	10

FPT3 Series


This aesthetic, easy-to-use Poke-through provides an ideal power and data solution – great for new construction or upgrading existing 3" core installations.



* If 1/2" EMT conduit stubs are required for communications cabling, use "City of Chicago" base unit, catalog # FPT3-2P-2C-C (see page 88).

Features and benefits:

- Capacity: 1 duplex receptacle and 2 data jacks (included)
- Core drill size: 3"
- Durable solid brass or aluminum covers protect devices from damage and debris when not in use – no exposed plastic components
- Powder-coated aluminum covers are available in black, gray, brown and beige to match any décor
- Brushed brass and aluminum finishes provide superior aesthetics
- Slide latches enable tool-less access to individual receptacles – eliminates the need for hard-to-use locking screws
- Accepts Keystone, Leviton® or Hubbell® data jacks
- Junction box features (3) 1/2" and (4) 3/4" knockouts (13 cubic inch capacity)
- Includes (1) 20A duplex receptacle, pre-wired, pigtail ends in junction box
- Includes (2) Leviton® CAT5e data jacks



Poke-through: 2 power and 2 communications



Cat. No.	Description	Std. Ctn.
FPT3-2P-2C-BRS	FPT3 Series Poke-through assembly: base unit with brushed-brass cover	1
FPT3-2P-2C-ALM	FPT3 Series Poke-through assembly: base unit with brushed-aluminum cover	1
FPT3-2P-2C-BLK	FPT3 Series Poke-through assembly: base unit with black powder-coat cover	1
FPT3-2P-2C	FPT3 Series Poke-through base unit only: cover purchased separately (see below)	1

See page 81 to view typical brushed metal and powder coat finishes.

Poke-through covers



Cat. No.	Description	Std. Ctn.
FPT3-CVR-BRS	Cover, FPT3 Series Poke-through – solid brass, brushed finish	4
FPT3-CVR-ALM	Cover, FPT3 Series Poke-through – solid aluminum, brushed finish	4
FPT3-CVR-BLK	Cover, FPT3 Series Poke-through – aluminum with black powder-coat finish	4
FPT3-CVR-GRY	Cover, FPT3 Series Poke-through – aluminum with gray powder-coat finish	4
FPT3-CVR-BGE	Cover, FPT3 Series Poke-through – aluminum with beige powder-coat finish	4
FPT3-CVR-BRN	Cover, FPT3 Series Poke-through – aluminum with brown powder-coat finish	4

FPT4
Series

The FPT4 Series provides everything you look for in a flush Poke-through – capacity, durability, flexibility, accessibility and aesthetics.

Capacity:

- Four standard configurations:
 - 4 power receptacles + 4 communications devices (4 x 4)
 - 2 power receptacles + 6 communications devices
 - 8 communications devices
 - 1 locking receptacle + 2 communications devices
- Core drill size: 4"

Durability:

- Solid brass or aluminum covers protect devices from damage and debris when not in use – no exposed plastic components
- Unique latching lid eliminates easily damaged, hard-to-use locking screws

Accessibility:

- Full access to communications compartment through the cover without exposing power compartments – even after it’s installed in the floor
- “Straight-through” wiring of communications cabling for easy installation and changes

Flexibility:

- Configurable design to meet any project requirements:
 - 4 standard configurations for power and communications devices
 - 20A receptacles can be wired as isolated ground (orange labels provided)
 - Communications plates available to accommodate data jacks from many manufacturers
 - Accepts Extron MAAP plates for A/V components
- Threaded conduit hubs enable all communications cabling to be enclosed in a single conduit
 - Integral 1" hub on the 4 x 4 – no extra parts needed
 - Optional hubs available for other configurations
- Junction box features (5) 1/2" and (5) 3/4" knockouts (27 cubic inch capacity)

Aesthetics:

- The only 4" core Poke-through for power and communications with the entire cover made of solid brass – features an aesthetic brushed finish
- Solid aluminum covers also available with brushed finish or powder-coated finishes in black, gray, brown and beige to match any décor



- 01 4 power + 4 communications, page 84.
- 02 2 power + 6 communications, page 85
- 03 8 communications, page 85
- 04 1 locking receptacle + 2 communications, page 86



01



02




03



04

FPT4

Series (continued)




Features and benefits:

- Four 20A receptacles, two circuits, six 12 AWG wires, prewired, pigtail ends in junction box (can be wired as isolated ground, labels provided)
- Keystone communications device plate with four keystone category 5e data jacks – see page 87 for optional communications device plates for compartment A
- Integral 1" threaded conduit hub for communication wiring (cast iron)

Poke-through: 4 power and 4 communications



Cat. No.	Description	Std. Ctn.
FPT4-4P-4C-TBRS	Poke-through assembly: base with brass cover	1
FPT4-4P-4C-TALM	Poke-through assembly: base with aluminum cover	1
FPT4-4P-4C-TBLK	Poke-through assembly: base with black cover	1
FPT4-4P-4C	Poke-through base (cover purchased separately)	1



Brass



Aluminum




Black

1/2" measured rise

Poke-through: Covers



Cat. No.	Description	Std. Ctn.
FPT4-CVR-TBRS	Cover, FPT4 Series Poke-through – brushed brass	4
FPT4-CVR-TALM	Cover, FPT4 Series Poke-through – brushed aluminum	4
FPT4-CVR-TBLK	Cover, FPT4 Series Poke-through – aluminum with black powder coat finish	4
FPT4-CVR-TBGE	Cover, FPT4 Series Poke-through – aluminum with beige powder coat finish	4
FPT4-CVR-TBRN	Cover, FPT4 Series Poke-through – aluminum with brown powder coat finish	4



FPT4

Series (continued)






(Cover purchased separately)



FPT4-CCH-6C
Communications conduit
hub (optional)

1" threaded
Hub



Poke-through: 2 power and 6 communications



Cat. No.	Description	Std. Ctn.
FPT4-2P-6C	Poke-through base unit only (cover purchased separately)	1
FPT4-CCH-6C	Optional 1" threaded conduit hub for communications wiring (cast iron)	1

Two 20A receptacles, one circuit, three 12 AWG wires, prewired, pigtail ends in junction box (can be wired as isolated ground, labels provided). Includes keystone communications device plates with six keystone category 5e data jacks – see page 87 for optional communications device plates for compartment A and compartment B.






(Cover purchased separately)



FPT4-CCH-8C
Communications conduit
hub (optional)

1 1/4" threaded
hub



• Features and benefits:

- Keystone communications device plates with eight keystone category 5e data jacks – see page 87 for optional communications device plates for compartment A and compartment B

Poke-through: 8 communications



Cat. No.	Description	Std. Ctn.
FPT4-8C	Poke-through base (cover purchased separately)	1
FPT4-CCH-8C	Optional 1 1/4" threaded conduit hub for communications wiring (cast iron)	4

FPT4

Series (continued)




(Cover purchased separately)



FPT4-CCH-2P
Communications conduit
hub (optional)


½" threaded
hub

Device layout



Compartment B

Cable entry



½" threaded hub
for power
¾" thru-hole for
communications


Features and benefits:

- 20A receptacle: pre-wired, three 12 AWG wires, pigtail ends in junction box
- 30A receptacle: pre-wired, three 10 AWG wires, pigtail ends in junction box
- Cover purchased separately
- Includes keystone communications device
- plates with two keystone category 5e data jacks – see page 87 for optional
- communications device plates for compartment B

Poke-through: 1 locking receptacle and 2 communications




Cat. No.	Description	Std. Ctn.
FPT4-1TL21-2C	Poke-through base, NEMA L5-20R, 20A/125V locking receptacle, 2 communications receptacles	1
FPT4-1TL22-2C	Poke-through base, NEMA L6-20R, 20A/250V locking receptacle, 2 communications receptacles	1
FPT4-1TL31-2C	Poke-through base, NEMA L5-30R, 30A/125V locking receptacle, 2 communications receptacles	1
FPT4-1TL32-2C	Poke-through base, NEMA L6-30R, 30A/250V locking receptacle, 2 communications receptacles	1
FPT4-CCH-2P	Optional ½" threaded conduit hub for communications wiring (cast iron)	4



Optional communications


Device plates





Features and benefits:

- Device plate only — no jacks included

Compartment A Plates



Compartment B plates



Optional communications – Device plates



Cat. No.	Description	Std. Ctn.
FPT4-CPA-4KEY*	For 4 Keystone jacks – compartment A	4
FPT4-CPA-4SYS	For 4 Systemax [®] jacks – compartment A	4
FPT4-CPA-3PAN**	For 3 Panduit jacks – compartment A	4
FPT4-CPA-1MAAP	For Extron [®] MAAP plate, single space – compartment A	4
FPT4-CPA-4ORT	For 4 Ortronics [®] jacks – compartment A	4
FPT4-CPA-BLANK	Blank – compartment A	4
FPT4-CPB-2KEY*	For 4 Keystone jacks – compartment B	4
FPT4-CPB-2SYS	For 4 Systemax [®] jacks – compartment B	4
FPT4-CPB-2PAN**	For 2 Panduit jacks – compartment B	4
FPT4-CPB-1MAAP	For Extron [®] MAAP plate, single space – compartment B	4
FPT4-CPB-2ORT	For 4 Ortronics [®] jacks – compartment B	4
FPT4-CPB-BLANK	blank – compartment B	4
FPT4-CPAB-2MAAP***	For Extron [®] MAAP plate, double space – compartment A-B	4

* Keystone plates also accept Leviton[®] and Hubbell[®] devices.

** Requires CMNZABL-X adapter from Panduit[®] to mount Panduit[®] MiniCom jacks.

*** For use with FPT4-2P-6C and FPT4-8C Series only; replaces one compartment A plate and one compartment B plate.

Features and benefits:

- For use with FPT4-4P-4C and FPT4-2P-6C Series Poke-through Systems



Replacement power insert – 2 receptacles



Cat. No.	Description	Std. Ctn.
FPT4-2P-RPL	Replacement power insert with 18" wire whip – two 20A receptacles	4

City of Chicago approved

Base units



(Cover purchased separately)

Features and benefits:

- Covers purchased separately, see page 84
- All base units include appropriate communications conduit hub
- All base units include appropriate Keystone Communications device plate and Category 5e Keystone data jacks, see page 87 for additional device plates
- Power junction box not included – use City of Chicago approved box
- See page 83 for additional details on FPT4 Series

FPT4 Poke-through



Cat. No.	Description	Std. Ctn.
FPT4-4P-4C-C	FPT4 Poke-through base unit only, (4) 20A power receptacles, (4) communications devices	1
FPT4-2P-6C-C	FPT4 Poke-through base unit only, (2) 20A power receptacles, (6) communications devices	1
FPT4-8C-C	FPT4 Poke-through base unit only, (8) communications devices	1
FPT4-1TL21-2C-C	FPT4 Poke-through base unit only, 20A/125V twist lock receptacle, NEMA L5-20R (2) communications devices	1
FPT4-1TL22-2C-C	FPT4 Poke-through base unit only, 20A/250V twist lock receptacle, NEMA L6-20R (2) communications devices	1
FPT4-1TL31-2C-C	FPT4 Poke-through base unit only, 30A/125V twist lock receptacle, NEMA L5-30R (2) communications devices	1
FPT4-1TL32-2C-C	FPT4 Poke-through base unit only, 30A/250V twist lock receptacle, NEMA L6-30R (2) communications devices	1



(Cover purchased separately)

Features and benefits:

- Covers purchased separately, see page 82
- Includes (1) 20A duplex receptacle, pre-wired
- Includes (2) CAT5e data jacks
- Power junction box not included – use City of Chicago approved box
- See page 82 for additional details on FPT3 Series

FPT3 Poke-through



Cat. No.	Description	Std. Ctn.
FPT3-2P-2C-C	FPT3 Poke-through base unit only, (1) 20A duplex receptacle, (2) communications devices	1

Recessed Poke-through boxes


RPT6 Series

Given the limitations on the number of holes that can be drilled in a floor, it is important to maximize the capacity of each location.

The RPT6 series offers a configurable solution that provides high capacity for both power wiring and communications cabling in a single-core drill location.

Features and benefits:

- Greater capacity than typical 3 in. and 4 in. core poke-throughs
- Core drill size: 6 in.
- Solid brass, black and brushed aluminum finishes provide superior aesthetics and durability
- Toolless cover entry. Cover rotates 180° to while-in-use position. No hinges which can mechanically fail.
- Customer can use off-the-shelf wiring devices
- Center compartment can accept GFCIs and is also rated for 30 amp devices
- Recessed service conceals devices below floor level
- Configurable compartment bottom junction box includes a cover with 1-1/4 in., 1-1/2 in. or 2 in. knockouts
- UL 263 – 2-hour fire test



Shown without cover
3 gang recessed compartment. Note: power and data devices are not furnished

RPT6 Series – Recessed Poke-through

Cat. No.	Description	Std. Ctn.
RPT6-3G-BRS	RPT6 series Poke-through Assembly: Base unit with solid brass cover	1
RPT6-3G-BLK	RPT6 series Poke-through Assembly: Base unit with black cover	1
RPT6-3G-ALM	RPT6 series Poke-through Assembly: Base unit with brushed aluminum cover	1



RPT6 Series – Recessed Poke-through covers



Cat. No.	Description	Std. Ctn.
RPT6-CVR-BRS	Solid brass cover	1
RPT6-CVR-BLK	Black cover	1
RPT6-CVR-ALM	Brushed aluminum cover	1

Moptite® covers meet UL/CSA scrub-water exclusion requirements for carpet, tile and wood.

RPT6 Series – RPT6 Series – Optional accessories



Cat. No.	Description	Std. Ctn.
RPT6-DPC-GFCI	Center plate for GFCI device	1
RPT6-DPC-R	Center plate for GFCI device 1 -9/16 round receptacle	1
RPT6-DPC-2MAAP*	Center plate for 2 Extron MAAP device	1
RPT6-DPS-DEC	Side plate for duplex or rectangular device	1
RPT6-DPS-2MAAP*	Side plate for 2 Extron MAAP device	1
RPT6-JB-CVR-2G	Junction box cover 2-G with 1-1/2" KO	1
RPT6-JB-CVR-3G	Junction box cover 3-G with 2" KO	1


* CSA and UL not applicable

Recessed Poke-through boxes

RPT8 Series

5-gang Poke-through designed to fit in 8" holes in the second floor and above in commercial buildings.

The RPT8 Series offers a configurable solution that provides high capacity for both power wiring and communications cabling – in a single-core drill location.



Features and benefits:

- Floor box, cover, abandonment cover, kit for device adaptors, and supplemental junction box
- Core drill size: 8"
- Greater capacity than typical 3", 4" and 6" core poke-throughs adaptor included with every unit
- 20, 30, & 50 amp rated center compartment Solid brass, black, brushed aluminum and NEW satin nickel finishes provide superior aesthetics and durability
- Temporary abandonment cover included
- Customer can use off-the-shelf wiring devices
- Recessed service conceals devices below floor level
- Bottom compartment can be configured for separate emergency power
- Configurable compartment bottom junction box includes a cover with 1-1/4", 1-1/2", or 2 in. knockouts
- UL 263–2-hour Fire Test and UL 514A /CSA C22.2 No18.1 Scrub Water compliant

RPT8 Series – Recessed Poke-through




Cat. No.	Description	Std. Ctn.
RPT8-5G-BRS	RPT8 series Poke-through assembly: Base unit with solid brass cover	1
RPT8-5G-BLK	RPT8 series Poke-through assembly: Base unit with black cover	1
RPT8-5G-ALM	RPT8 series Poke-through assembly: Base unit with brushed aluminum cover	1
RPT8-5G-SN	RPT8 series Poke-through assembly: Base unit with satin nickel cover	1

RPT8 Series – Optional accessories



Cat. No.	Description	Std. Ctn.
RPT8-CDP-MAAP	Center device plate for Extron MAAP	5
RPT8-SDP-Keystone	Side device plate for keystone	5
RPT8-ODP-Keystone	Outer device plate for keystone	5
RPT8-CDP-30A	Center device plate for 30A receptacle	5
RPT8-CDP-50A	Center device plate for 50A receptacle	5
RPT8-CDP-Keystone	Center device plate for keystone	5
RPT8-SDP-MAAP	Side device plate for Extron MAAP	5
RPT8-INSERT-WHITE	White duplex insert	5
RPT8-INSERT-BLANK	Blank insert	5

Pedestal
FPT Series



By mounting all outlets above floor level and at a 90° angle to the floor, the FPT Pedestal Series protects power receptacles and communications devices from dirt and debris. An overhanging housing provides additional protection for the outlets.

Features and benefits:


- Pedestals available in 2 compartment and 4 compartment for power and communications applications
- Core drill size: 3"
- Housings and device plates feature a brushed-aluminum finish
- Integral junction box features (5) 1/2" and (5) 3/4" knockouts (27 cubic inch capacity)



FPT-421



FPT-401A




Poke-through



Cat. No.	Description	Std. Ctn.
FPT-401A	FPT pedestal, accepts 2 device plates, Poke-through base unit purchased separately , (2 5/8" high x 4" wide x 4 7/8" deep)	10
FPT-421	FPT pedestal, accepts 4 device plates, Poke-through base unit purchased separately , (2 5/8" high x 4" wide x 4 7/8" deep)	5
FPT-400B	FPT Poke-through base unit only	1

Device plates & accessories



OPOD4-WH

Cat. No.	Description	Std. Ctn.
FPT-424	Duplex device plate, aluminum with anodized finish	50
FPT-425	Blank device plate, aluminum with anodized finish	50
OPOD4-WH	4-Port "106" duplex adapter for keystone jacks (for use with FPT-424 plate)	100
FPT-408A	Voltage divider for FPT-401A pedestal	10
FPT-422A	Voltage divider for FPT-421 pedestal	10


CONCRETE APPLICATIONS

Fire rated poke-through furniture feed



Furniture feed


FPT Series



With three conduit hubs for power and communications and an integral junction box, the FPT Series provides a flexible, cost-effective furniture feed solution.

Features and benefits:



- Capacity: (2) 1/2" hubs and (1) 3/4" hub for power and data (plugs included)
- Core drill size: 3"
- Non-metallic covers are available in black, gray, beige and brown
- Provided with Steel City® die cast fittings for flexible metal conduit: (2) 1/2" and (1) 3/4"
- Integral junction box features (5) 1/2" and (5) 3/4" knockouts (27 cubic inch capacity)



Poke-through



Cat. No.	Description	Std. Ctn.
FPT-448-SW-BLK	FPT Furniture feed Poke-through assembly: base unit with black non-metallic cover	1
FPT-448-SW-GRY	FPT Furniture feed Poke-through assembly: base unit with gray non-metallic cover	1
FPT-448-SW-BGE	FPT Furniture feed Poke-through assembly: base unit with beige non-metallic cover	1
FPT-448-SW-BRN	FPT Furniture feed Poke-through assembly: base unit with brown non-metallic cover	1
FPT-448-SW-BRS	FPT Furniture feed Poke-through assembly: base unit with brass non-metallic cover	1
FPT-400B	FPT Poke-through base unit only: cover purchased separately (see below)	1



Poke-through covers



Cat. No.	Description	Std. Ctn.
FPT-442-SW-BLK	Black, non-metallic, 7" diameter	10
FPT-442-SW-GRY	Gray, non-metallic, 7" diameter	10
FPT-442-SW-BGE	Beige, non-metallic, 7" diameter	10
FPT-442-SW-BRN	Brown, non-metallic, 7" diameter	10
FPT-442-SW-BRS	Brass, non-metallic, 7" diameter	10
FPT-3/4-2-CACP	Brass, metallic, 5 3/4" diameter	10

See page 81 to view typical non-metallic cover colors and finishes.


FFPT3
Series



When feeding large bundles of communications cables through a fire-rated floor, the FFPT3 Series provides a high-capacity, straight-through wiring solution. It can also be used for power wiring.

Features and benefits:

- Capacity: Concentric 1 1/4" and 2" hub for power or communications wiring (plugs included)
- Core drill size: 3"
- Solid brass and aluminum finishes provide superior aesthetics and durability
- Powder-coated aluminum covers are available in black, gray, brown and beige to match any décor – the most colors in the industry
- Junction box not included



Poke-through



Cat. No.	Description	Std. Ctn.
FFPT3-BRS	FFPT3 Series Poke-through assembly: base unit with brushed-brass cover	1
FFPT3-ALM	FFPT3 Series Poke-through assembly: base unit with brushed-aluminum cover	1
FFPT3-BLK	FFPT3 Series Poke-through assembly: base unit with black powder-coat cover	1
FFPT3	FFPT3 Series Poke-through base unit only: cover purchased separately (see below)	1


Poke-through covers



Cat. No.	Description	Std. Ctn.
FFPT3-CVR-BRS	Solid brass, brushed finish	4
FFPT3-CVR-ALM	Solid aluminum, brushed finish	4
FFPT3-CVR-BLK	Aluminum with black powder-coat finish	4
FFPT3-CVR-GRY	Aluminum with gray powder-coat finish	4
FFPT3-CVR-BGE	Aluminum with beige powder-coat finish	4
FFPT3-CVR-BRN	Aluminum with brown powder-coat finish	4

See page 81 to view typical brushed metal and powder coat colors and finishes.



FFPT4
Series



With limitations on the number of holes that can be drilled in a floor, it is important to maximize the capacity of each location. The FFPT4 Series provides high capacity for both power wiring and communications cabling when feeding modular furniture – in a single-core drill location.

Features and benefits:

- Capacity: 3/4" hub for power wiring and 1 1/4" hub for communications cabling (plugs included)
- Core drill size: 4"
- Solid brass and aluminum finishes provide superior aesthetics and durability
- Powder-coated aluminum covers are available in black, gray, brown and beige to match any décor
- Integral junction box features (5) 1/2" and (5) 3/4" knockouts (27 cubic inch capacity)



Poke-through



Cat. No.	Description	Std. Ctn.
FFPT4-BRS	FFPT4 Series Poke-through assembly: base unit with brushed-brass cover	1
FFPT4-ALM	FFPT4 Series Poke-through assembly: base unit with brushed-aluminum cover	1
FFPT4-BLK	FFPT4 Series Poke-through assembly: base unit with black powder-coat cover	1
FFPT4	FFPT4 Series Poke-through base unit only: cover purchased separately (see page A-179)	1


Poke-through covers



Cat. No.	Description	Std. Ctn.
FFPT4-CVR-BRS	Solid brass, brushed finish	4
FFPT4-CVR-ALM	Solid aluminum, brushed finish	4
FFPT4-CVR-BLK	Aluminum with black powder-coat finish	4
FFPT4-CVR-GRY	Aluminum with gray powder-coat finish	4
FFPT4-CVR-BGE	Aluminum with beige powder-coat finish	4
FFPT4-CVR-BRN	Aluminum with brown powder-coat finish	4

See page 81 to view typical brushed metal and powder coat colors and finishes.

FFPT6
Series



Given the limitations on the number of holes that can be drilled in a floor, it is important to maximize the capacity of each location.

The FFPT6 series provides high capacity for both power wiring and communications cabling when feeding modular furniture in a single-core drill location.

Features and benefits:

- Power and/or communication connections: 3/4 in., 1-1/4 in. or 2 in. threaded hubs
- Core drill size: 6 in.
- Solid brass, black and brushed aluminum cover finishes provide superior aesthetics and durability
- Integral junction box features five 1/2 in and five 3/4 in. knockouts, with 27 in.³ capacity (443 cm³)
- UL 263 – 2-hour fire test

FFPT6 Series – Furniture Feed Poke-through



Cat. No.	Description	Std. Ctn.
FFPT6-BRS	FFPT6 series poke-through assembly: Base unit with solid brass cover	1
FFPT6-BLK	FFPT6 series poke-through assembly: Base unit with black cover	1
FFPT6-ALM	FFPT6 series poke-through assembly: Base unit with brushed aluminum cover	1



FFPT6 Series – Furniture Feed Poke-through covers



Cat. No.	Description	Std. Ctn.
FFPT6-CVR-BRS	Solid brass cover	1
FFPT6-CVR-BLK	Black cover	1
FFPT6-CVR-ALM	Brushed aluminum cover	1

City of Chicago approved
FFPT4 Poke-through base unit



(Cover purchased separately)

Features and benefits:

- Covers purchased separately, see page 95
- Power junction box not included — use City of Chicago approved box
- See page 95 for additional details on FFPT4 Series

FFPT4 Poke-through



Cat. No.	Description	Std. Ctn.
FFPT4-C	FFPT4 Poke-through base unit only	1

City of Chicago approved
FFPT3 Poke-through base unit



(Cover purchased separately)

FFPT3 Poke-through

- Covers purchased separately, see page 94
- Power junction box not included – use City of Chicago approved box
- See page 94 for additional details on FFPT3 Series

FFPT3 Poke-through



Cat. No.	Description	Std. Ctn.
FFPT3	FFPT3 Poke-through base unit only	1

—
Access floor module
applications



Access floor modules



Steel City® access floor modules from ABB eliminate the clutter of power, voice and data lines by keeping everything out of sight but conveniently close at hand. Our easy-to-install access floor modules are designed to blend with any decor, while providing the durability and versatility you need to meet the growing demands of today's high-tech offices.

You can use our access floor modules with virtually any type of raised floor. Our system is designed to provide a simple, strong and adaptable solution to even the most demanding wire-management needs.

Range of box sizes designed to meet the needs of any application. Now and later.


With five sizes to choose from, our access floor modules handle a broad range of wiring needs, from single power lines to complex data and voice systems. In fact, our largest unit offers 325 cu. in. of space. And, because our modules are easy to install and relocate, you can easily change box sizes or reposition modules as office configurations change.

New, low-profile box fits right in with shallower raised floors.

For installations where shallower raised floors are needed, ABB has developed a low-profile access floor modules to provide the same accessibility and convenience where space is at a premium. Just 2½-inches deep, it can still accommodate a variety of power, voice and data connections.

Wide variety of interchangeable power and data panels adapt to changing demands.

Our extensive line of panels and connection devices maximizes the versatility of our access floor modules. All our panels are designed to be easy to connect, disconnect and rearrange to reduce on-site installation time. And ABB is continually developing new configurations to meet the requirements of virtually any installation, especially for the fast-growing needs of voice and data communication.



Durable, solid steel covers support heavy loads to protect important connections.

We've reinforced the resilient nylon covers of our modules with a ½" steel plate to prevent buckling under heavy furniture and equipment. The beveled sides enable quick and unobstructed installation in the raised floor.

In addition, our retractable exit not only helps prevent tripping, but protects cable connections by sealing out dust and debris. And, as with all ABB products, our access floor modules are constructed to meet your high standards for durability, safety and reliability.

Steel City® access floor modules provide outstanding performance without standing out.

The hinged service top on our modules sits flush with the floor and provides complete access to the connections within. The nylon frame comes in gray, brown, beige and black.






Our access floor modules keep wire connections close at hand but not under foot. The wide variety of box sizes, panels and devices provides exceptional versatility for changing office needs.

Look below the surface and see how Steel City® Access floor modules can manage all your power, voice and data connections – today and tomorrow.

AFM-2 Series access floor module

Non-metallic covers included



AFM	Power panels	
AFM-2- BLK AFM-2- GRY AFM-2- BRN AFM-2- BGE	AFP-2A* Single duplex	AFP-2B Single duplex
		
Data panel	Accessories	
AFD-2 3RJ 3 T&B Omnijacks or Keystone-style jacks	AFT-2 Power tunnel	
	AFR-2** Mounting trim	

* (1) supplied with box.

** Used to correct opening in floor. Not required for all installations.

AFM-2 Access floor module



Access floor module size	AFM-2
AFM depth	4"
Access floor cut-out	7 ¹ / ₈ " x 4 ¹ / ₈ "
AFM cover size	6 ³ / ₄ " x 3 ⁷ / ₈ "
AFM cover access area	17 sq. in.
Box volume (less panels)	75 cu in.
Device compartment volume – 45° power	16.2 cu in.
Base opening	—

* Special panels available — consult factory.

** Devices not included.

Replacement covers: see 664 series covers on page 15.

Access floor module size	AFM-2
Power panel included**	AFP-2A
Closure panel included	—
Cover/carpet flange material	Polycarbonate
Body material	14-ga. galvanized steel
Prewiring available	Yes*
Max. no. of device panels	2



AFM-2
Shown with supplied power panel and optional panel (sold separately).

AFM-2 Series access floor module

Metallic covers included



AFM-2 Access floor module






Access floor module size	AFM-2
AFM depth	4"
Access floor cut-out	7 $\frac{1}{8}$ " x 4 $\frac{1}{8}$ "
AFM cover size	6 $\frac{3}{4}$ " x 3 $\frac{7}{8}$ "
AFM cover access area	17 sq. in.
Box volume (less panels)	75 cu in.
Device compartment volume	16.2 cu in.
Base opening	—

Access floor module size	AFM-2
Power panel included**	AFP-2A
Closure panel included	—
Cover/carpet flange material	Brass, Aluminum
Body material	14-ga. galvanized steel
Prewiring available	Yes*
Max. no. of device panels	2

* Special panels available — consult factory.

** See previous page for device plates and accessories.

Replacement covers: see 664 Series covers on page 15




AFM-2 Series raised floor boxes

Cat. No.	Description	Std. Ctn.
AFM-2-BRS	AFM-2 raised floor box, 2 compartment, solid brass cover	1
AFM-2-ALM	AFM-2 raised floor box, 2 compartment, solid aluminum cover	1
AFM-2-MBLK	AFM-2 raised floor box, 2 compartment, black powder-coat finish	1

For additional device plate options see previous page.

AFM-4 Series access floor module

Non-metallic covers included



AFM	Power panels		
AFM-4- BLK	AFP-4A*	AFP-4A60	4GFCI
AFM-4- GRY	Single duplex - 45°	Single duplex - 60°	Single GFCI - 60°
AFM-4- BRN			
AFM-4- BGE	AFP-4B	AFP-4B60	AFP-4-GFCI-45
	Blank - 45°	Blank - 60°	Single GFCI - 45°

* (1) supplied with box.

Data panels		Accessories	
AFD-4A	AFD-4B	AFT-46	AFR-4**
Single duplex data	Blank	Power tunnel	Trim flange
	AFD-4 4RJ	AFC-N	AFM-4EX
	Keystone style jacks	Grommeted closure panel	Extension collar

** Used to correct opening in floor. Not required for all installations.

AFM-4 Access floor module - non metallic covers

Access floor module size		AFM-4
AFM depth		4"
Access floor cut-out		7 ¹⁵ / ₁₆ " x 7 ¹⁵ / ₁₆ "
AFM cover size		7 ⁵ / ₈ " x 7 ⁵ / ₈ "
AFM cover access area		39 sq. in.
Box volume (less panels)		150 cu in.
Device	45° power	27.3 cu in.
Compartment	60° power	25.2 cu in.
Volume	Center data	20.6 cu in.



* Special panels available – consult factory.

** Devices not included.

Replacement covers: see 665 Series covers on page 18.



Access floor module size		AFM-4
Base opening		2" x 2 ⁷ / ₈ "
Power panel included**		AFP-4A
Closure panel included		AFC-C
Cover/carpet flange material		Polycarbonate
Body material		14-ga. galvanized steel
Prewiring available		Yes*
Max. no. of device panels		3



45° Angle plates
Shown with applied power panel and optional data panel and 45° power panel (sold separately).

60° Angle plates
Shown with optional 60° panels (sold separately).

AFM-4 Series access floor module

Metallic covers



AFM-4 Access floor module - metallic covers



Access floor module size	AFM-4
AFM depth	4"
Access floor cut-out	7 ¹⁵ / ₁₆ " x 7 ¹⁵ / ₁₆ "
AFM cover size	7 ⁵ / ₈ " x 7 ⁵ / ₈ "
AFM cover access area	39 sq. in.
Box volume (less panels)	150 cu in.
Device compartment volume	27.3 cu in.
	25.2 cu in.
	20.6 cu in.


Access floor module size	AFM-4
Base opening	2" x 2 ⁷ / ₈ "
Power panel included**	AFP-4A
Closure panel included	AFC-C
Cover/carpet flange material	Brass, Aluminum
Body material	14-ga. galvanized steel
Prewiring available	Yes*
Max. no. of device panels	3

* Special panels available – consult factory.



** Devices not included.

See previous page for device plates and accessories.

Replacement covers: see 665 Series covers on page 18




One duplex plate included



AFM-2 Series raised floor boxes

Cat. No.	Description	Std. Ctn.
AFM-4-BRS	AFM-4 raised floor box, 3 compartment, solid brass cover	1
AFM-4-ALM	AFM-4 raised floor box, 3 compartment, solid aluminum cover	1
AFM-4-MBLK	AFM-4 raised floor box, 3 compartment, 1 black powder-coat finish cover	1

AFM-6 Series access floor module



AFM	Power Panels		
AFM-6- BLK AFM-6- GRY AFM-6- BRN AFM-6- BGE	AFP-6Q* Double duplex - 45°	AFP-6B Blank 45°	AFP-6A Single duplex - 45°
	AFP-6B60 Blank - 60°	AFP-6R60 Double duplex - 60°	AFP-6-GFCI Double GFCI - 60°
	AFP-6A60 Single duplex - 60°	AFP-6-GFCI-45 Double GFCI - 45°	


Data Panels		Accessories	
AFD-6Q Double duplex data	AFD-6B Blank	AFT-46 Power tunnel	AFR-6** Trim flange
AFD-6 6RJ T&B Omni jacks or Keystone style jacks	AFD-6A Single duplex	AFC-N Grommeted Closure panel	AFM-6EX Extension collar

* (1) supplied with box.
** Used to correct opening in floor. Not required for all installations.


AFM-6 Access floor module

Access floor module size	AFM-6
AFM depth	4
Access floor cut-out	7 ¹⁵ / ₁₆ " x 10"
AFM cover size	7 ⁵ / ₈ " x 9 ³ / ₄ "
AFM cover access area	60 sq. in.
Box volume (less panels)	225 cu. in.
	45° power 41.5 cu. in.
	60° power 38.3 cu. in.
Device compartment volume	Center data 31.3 cu. in.

* Special panels available – consult factory.
** Devices not included.
Replacement cover: AFM-6-CST-SW black (-BLK), brown (-BRN), beige (-BGE) or gray (-GRY) cover flange.




45° angle plates shown with supplied power panel and optional data panel and 45° power panel (sold separately).



60° angle plates shown with optional 60° panels (sold separately).



Access floor module size	AFM-6
Base opening	2" x 2 ⁷ / ₈ "
Power panel included**	AFP-6Q
Closure panel included	AFC-C
Cover/carpet flange material	Polycarbonate
Body material	14-ga. galvanized steel
Prewiring available	Yes*
Max. no. of device panels	3



AFM-6S2 Series access floor module



AFM	Power Panels	
AFM-6S- BLK AFM-6S- GRY AFM-6S- BRN AFM-6S- BGE	AFP-6S2-R (-L)* Single duplex R-right side; L-left side)	AFP-6S2-GR (-GL) Single GFCI
	AFP-6S2-BR (-BL) Blank	

Data Panels	Accessories
AFD-6S2-2RJ T&B Omni jacks or Keystone-style jacks	AFP-6S2-BR Blank
	AFR-6** Mounting flange

* (1) AFP-6S2-R & (1) AFP-6S2-L supplied with box.
** Used to correct opening in floor. Not required for all installations.



AFM-6S2 Access floor module

Access floor module size	AFM-6S
AFM depth	2½"
Access floor cut-out	7 ¹⁵ / ₁₆ " x 10"
AFM cover size	7 ⁵ / ₈ " x 9 ³ / ₄ "
AFM cover access area	60 sq. in.
Box volume (less panels)	172 cu. in.
Device compartment volume	Power 13.1 cu. in. Data 6.6 cu. in.

* Special panels available – consult factory.
** Devices not included.
Replacement cover: AFM-6-CST-SW black (-BLK), brown (-BRN), beige (-BGE) or gray (-GRY) cover flange.





Access floor module size	AFM-6S
Base opening	—
Power panel included**	AFP-6S2-L, AFP-6S2-R
Wire tunnel included	—
Cover/carpet flange material	Polycarbonate
Body material	14-ga. galvanized steel
Prewiring available	Yes*
Max. no. of device panels	4



AFM-6S2
Shown with supplied power panels and optional data panels (sold separately).

AFM-6V Series access floor module







AFM-6
Shown with supplied power panels and optional panels
(sold separately)

AFM-6V Access floor module

Access floor module size	AFM-6V	
AFM depth	4.70 in.	
Access floor cut-out	7 ¹⁵ / ₁₆ " x 10"	
AFM cover size	7 ⁵ / ₈ " x 9 ³ / ₄ "	
AFM cover access area	60 sq. in.	
Box volume (less panels)	201 cu in.	
Device compartment volume	45° power	—
	60° power	—
	Center Data	—
	Power	51 cu in.
	Data	51 cu in.

Devices not included. Cover flange available in Black, Grey, Brown or Beige.
Replacement cover: AFM-6-CST-SW black (-BLK), brown (-BRN), beige (-BGE) or gray (-GRY) cover flange.

AFM	Power panels	
AFM-6V- BLK AFM-6V- GRY AFM-6V- BRN AFM-6V- BGE	AFP-6V-3D* Three duplex	AFP-6V-3G* Three GFCI
		



Data Panels	Accessories
AFD-6V-2F* Two single gang data face plates	AFR-6** Mounting flange
	

- * Not CSA Certified.
- (1) AFP-6V-3D and (1) AFD-6V-2F supplied with box
- ** Used to correct opening in floor. Not required for all installations.








Access floor module size	AFM-6V
Base opening	1.72 in. x 5.28 in.
Data panel included	AFD-6V-2F
Power panel included	AFP-6V-3D
Closure panel included	Yes
Cover/carpet flange material	Nylon-6
Body Material	14 gauge galvanized steel
Max. no. of device panels	2

AFM-8 Series access floor module



AFM-8
Shown with optional power panels (sold separately). Accepts 10 device panels.
Each compartment can accept voltage dividers for any combination of power and data (included with device panels).

AFM	Power panels	
AFM-8- BLK	AFP-8A* Single duplex	AFP-8G* Single GFCI
AFM-8- GRY		
AFM-8- BRN	AFP-8B Blank	
AFM-8- BGE		

Data Panels	Accessories
AFD-8-3RJ Keystone	AFR-8** Mounting flange
	

* Power panels include a voltage partition for use between power and data panels.
** Used to correct opening in floor. Not required for all installations.

AFM-8 Access floor module

Access floor module size	AFM-8
AFM depth	5 5/8"
Access floor cut-out	9 5/8" x 9 5/8"
AFM cover size	9 3/8" x 9 3/8"
AFM cover access area	74 sq. in.
Box volume (less panels)	325 cu in.
Device compartment volume	45° power 60° power Power or data
	15.75 cu in.

* Special panels available – consult factory.
Replacement covers: see 667 Series covers on page 65

Access floor module size	AFM-8
Base opening	—
Power panel included	—
Closure panel included	—
Cover/carpet flange material	Polycarbonate
Body material	14-ga. galvanized steel
Prewiring available	Yes*
Max. no. of device panels	10





—
Wood floor applications
recessed service

Recessed service box

68R Series

—
01 Use an appropriate Steel City® 3" x 2" metal switch box with mounting ears (purchased separately).

—
02 Wood sub-floor/raised floor applications

—
03 Lid closes flush with the floor, even with cords plugged in


—
04 Power and communications wood sub-floor/raised floor applications

Plug in power and communication cords, and then close the lid to hide unsightly plugs and receptacles below the floor.

Features and benefits:

- Unique cover provides aesthetic recessed service with cost-effective box options for concrete, wood sub-floor and raised-floor applications
- Lid can be rotated to expose a small opening for cords, enabling the lid to close flush with the floor while in use

- Cover accepts one duplex or GFCI receptacle – no special device plates required (receptacle purchased separately)
- Cover accepts up to two communications jacks – includes one 2-port keystone data plate and one blank data plate for custom cut-outs or power-only applications (communications jacks purchased separately)
- Non-metallic covers are available in black, gray, beige and brown. Black covers are available with an optional brass or aluminum flange
- Two set screws lock the cover in place – no gluing required



—
01



—
02




—
03



—
04

Recessed covers

68R Series



Cover kit includes:



- Cover assembly
- Receptacle mounting plate
- Duplex receptacle insert
- 2-port keystone data plate
- Blank data plate
- Voltage divider



Device not included. Cover is 6³/₄in. dia.



Cat. No.	Description	Std. Ctn.
68R-CST-BLK	Non-metallic recessed floor box cover kit, black	4
68R-CST-GRY	Non-metallic recessed floor box cover kit, gray	4
68R-CST-BGE	Non-metallic recessed floor box cover kit, beige	4
68R-CST-BRN	Non-metallic recessed floor box cover kit, brown	4
68R-CST-BRS	Non-metallic recessed floor box cover kit, black with brass flange	4
68R-CST-ALM	Non-metallic recessed floor box cover kit, black with aluminum flange	4
CXWOW	3" x 2" metal switch box, 3 ¹ / ₂ " deep, for non-metallic sheathed cable, wood subfloors	25
CY 1/2	3" x 2" metal switch box, 3 ¹ / ₂ " deep, 1/2" KOs	25



Rectangular floor box

1-, 2- and 3-gang

Carlton® rectangular floor box systems – three-way power, data and communications plus easy double- or triple-gang, too.

Compared to metal boxes, Carlton® rectangular floor boxes cost less and install faster to save you money on every job. Three-in-one power, data and communications capability cuts installation time and cost even more, while simple two- and three-gang modularity gives you the flexibility, installation ease and cost-savings no other non-metallic boxes can match. The covers attach without the use of fasteners, providing a professional, clean installation as well as preserving the aesthetic life of the product. Take a closer look at all that our rectangular floor box systems offer you.

Features and benefits:

- Covers require no adjusting collar – two screws ensure a flush, secure installation
- Non-metallic PVC construction, watertight gasket and corrosion-resistant hardware ensure long life and reliable performance, even in harsh and/or corrosive environments
- One consistent box depth simplifies ordering time and reduces inventory
- Saves time and money on installations with simple saw cut to floor level
- Concrete tight and suitable for any on-grade/below-grade application; concrete or wood subfloor construction approved
- Convenient cubic inch capacity markings on inside enable easy inspection
- PVC-molded ports and reducer plugs included
- Accepts ½", ¾" and 1" conduit, tubing or raceway
- Rectangular sides are drillable
- Suitable for tile and carpet applications
- Cover options include solid brass, stainless steel and non-metallic (brown, slate and caramel)
- UL/CSA scrubwater tested, approved for all types of finish flooring



Gangable rectangular Floor box




Features and benefits:

With our rectangular boxes, one SKU is all you ever need. Simply remove appropriate sides and slide boxes together to create two- or three-gang boxes for on-the-job flexibility no competitor offers.

For wood floor applications, box must be supported from below.



Cat. No.	Material	Size	Internal volume (cu. in.)	Min. concrete depth	Hubs (In.)	Reducer plugs (In.)	Std. Ctn.	Std. Wt. (lbs.)
E976RFB	PVC	1-Gang	97.4 (16.8 per inch of depth)	3½	(2) 1	(2) 1 x ¾ (2) ¾ x ½	3	6.92



Activation

Kit



Activation kit provides components to accommodate all standard power, data and communications devices, plus a divider to separate power from data and communications – all in a single SKU. Device yokes can be adjusted to store excess cord in the box.

One kit per gang.



Cat. No.	Material	Std. Ctn.	Std. Wt. (lbs.)
E976AK2	PVC	3	2.47

1-, 2- and 3-gang non-metallic


Floor box covers

On-the-job flexibility extends to our rectangular box covers. Each one-, two- or three-gang cover is suitable for any wiring application and can be used with any floor surface. Non-metallic covers are even field-reversible for tile or carpet. Double-door feature enables easy access to the device and helps keep stray cords organized.


Carlon® Rectangular Floor Box Covers do not require a separate carpet flange. The carpet flange is part of the cover and may be removed for tile application.

Features and benefits:

- High-impact resistant thermoplastic
- Field reversible for tile or carpet
- Gasketed for a watertight seal
- Double-door design
- For tile and carpet applications
- UL/CSA scrubwater tested



Cat. No.	Size	Color	Carpet flange	Dimensions (w x L) (In.)	Std. Ctn.	Std. Wt. (lbs.)
E9761B	One-Gang	Brown	Included	7.13 x 5.00	3	1.7
E9762B	Two-Gang	Brown	Included	7.13 x 8.25	9	8.5
E9763B	Three-Gang	Brown	Included	7.13 x 11.50	6	7.5
E9761C	One-Gang	Caramel	Included	7.13 x 5.00	3	1.7
E9762C	Two-Gang	Caramel	Included	7.13 x 8.25	9	8.5
E9763C	Three-Gang	Caramel	Included	7.13 x 11.50	6	7.5
E9761S	One-Gang	Slate	Included	7.13 x 5.00	3	1.7
E9762S	Two-Gang	Slate	Included	7.13 x 8.25	9	8.5
E9763S	Three-Gang	Slate	Included	7.13 x 11.50	6	7.5





Solid brass and stainless steel floor box covers

1-, 2- and 3-gang


Carlton® brass and stainless steel rectangular floor box covers add a classic touch to all floor box installations, and are particularly suited for use in high-traffic areas because of the resistance to wear. The gasket gives a watertight seal, and the light lacquer finish provides extra protection.

Features and benefits:


- Rugged construction
- Coated with a light lacquer finish for extra protection
- Covers include a cord door
- Gasketed for watertight applications
- Accepts single, duplex, GFCI and low-voltage receptacles
- For tile and carpet applications
- UL/CSA scrubwater tested




Cat. No.	Size	Color	Dimensions (in.)	Std. Ctn.	Std. Wt. (lbs.)
E9761BR	One-gang	Brass	7.13 x 5	3	6.8
E9762BR	Two-gang	Brass	7.13 x 8.25	3	9.9
E9763BR	Three-gang	Brass	7.13 x 11.5	3	12.1
E9761SS	One-gang	Stainless steel	7.13 x 5	3	7.4
E9762SS	Two-gang	Stainless steel	7.13 x 8.25	3	11.6
E9763SS	Three-gang	Stainless steel	7.13 x 11.5	3	17.2
Rectangular floor box activation kit					
E976AK2	—	—	—	3	1.3



One-gang



Two-gang



Three-gang

—
Wood floor applications
flush service



Adjust-A-Box® adjustable residential floor boxes

1- and 2-gang

Carlton® Adjust-A-Box® Floor Boxes make installing floor outlets fast and easy by providing maximum installation flexibility. The box features an adjustment screw designed to adjust the box from 0" to 1¾" by simply turning the screw clockwise or counterclockwise, providing a flushmount every time.

Covers are available in three types: non-metallic, brass and stainless steel. They feature two hinged doors to protect unused devices and to keep out dust and scrubwater. Because the doors are attached, they won't get lost or misplaced while the outlet is in use.

The Adjust-A-Box® is available in two sizes, single-gang and double-gang. The single-gang box has a 20 cubic inch capacity and includes a duplex receptacle, and the double-gang box has a 34 cubic inch capacity, and comes with a divider for dual-voltage capabilities.

Carlton® Adjust-A-Box® residential floor boxes are ideal for residential and home office applications and provide a clean, aesthetically pleasing floor outlet anywhere you need it.


Features and benefits:

- Listed floor boxes in accordance to section 314.27(B) of the NEC®
- Adjustment screw adjusts depth (from 0" to 1¾")
- Cover options include: non-metallic, brass and stainless-steel covers
- Covers have two (non-removable) hinged doors
- Solid brushed-brass and stainless-steel covers with a light lacquer finish for extra protection
- Non-metallic covers are available in white and ivory (single-gang box only)
- Two-gang version features dual-service capabilities (requires use of dual-service divider)
- Integral cable clamps
- Ideal for new work and retrofit applications
- UL® Listed
- UL/CSA scrubwater tested
- Single-gang only has a 2-hour fire rating

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

—
01 Double-Gang
*Devices not included

—
02 Single-Gang



—
01



—
02

Adjust-A-Box® installation

1- and 2-Gang


- 01 Install clip over subfloor
- 02 Screw in to adjust
- 03 Beautiful flush fit every time!



01



02



03

04 Double-gang

Kits include:

Single-Gang

Ivory/white cover:

- Two (2) 6-32 x 1 flat head machine screws
- Four (4) #6 1¼ self-tapping flat head screws
- Two (2) #6 1½ drywall screws
- One (1) cover plug
- One (1) new work bracket
- One (1) old work bracket
- One (1) 20 cubic in. UL Listed floor box
- One (1) UL Listed floor cover
- One (1) short shank receptacle (tamper proof)
- One (1) tube dow corning #4 sealant
- Installation instructions

Single-Gang

Brass & Stainless Steel Covers::

- Two (2) 6-32 x 1 plated flat head machine screws
- Four (4) #6 1¼ self-tapping flat head screws
- Two (2) #6 1½ drywall screws
- One (1) new work bracket
- One (1) old work bracket
- One (1) 20 cubic in. UL Listed floor box
- One (1) UL Listed floor cover
- One (1) short shank receptacle
- Green ground wire
- Installation instructions

Double-Gang

- One (1) new work bracket
- One (1) old work bracket
- One (1) 34 cubic in. UL Listed floor box
- One (1) dual-voltage divider
- One (1) UL Listed floor cover
- Four (4) #6-32 x 1" flat head machine screws
- Four (4) #6 x 1¼" flat head self-tapping screws
- Two (2) #6 x 1½" square drive trim head screws
- Green ground wire
- Installation instructions



04

*Devices not included



E11461

Cat. No.	Size	Cover	Cubic in.	Std. Ctn.	Std. Wt. (lbs.)
Non-metallic					
B121BFRW	One-gang	White	20	8	7.1
B121BFBR	One-gang	Ivory	20	8	6.9
Brass					
B121BFBB	One-gang	Brass	20	8	15.0
B234BFBB	Two-gang	Brass	34	4	10.7
Stainless steel					
B121BFSS	One-gang	Stainless steel	20	8	13.7
B234BFSS	Two-gang	Stainless steel	34	4	9.8

Low-voltage adjustable floor bracket with cover

Carlton® structured cable management systems...your total systems solution!

—
01 Install clip
over subfloor.
Screw in to adjust.
Beautiful flush fit
every time!

The Carlton® low-voltage adjustable floor bracket is specifically designed for the low-voltage, structured cabling market...the floor bracket is industry-standard orange to identify low-voltage applications, the open design provides the space needed for low-voltage bend-radius requirements and the Leviton QuickPort® Quad 106® Insert provides up to four low-voltage outlet ports. The Carlton® low-voltage adjustable floor bracket is ideal for any residential or commercial low-voltage application.

The floor bracket also features a unique screw design, enabling it to be adjusted to most finished floor heights by simply turning the screw clockwise or counterclockwise and adjusting flush to the floor.

The floor bracket kit comes complete with a non-metallic (white or ivory) or brass cover, a Leviton QuickPort® Quad 106® Insert, new work and old work metal mounting brackets and mounting screws.


Features and benefits:

- White, ivory or brass cover
- Orange – identifies low-voltage installations
- Open design floor bracket – accommodates low-voltage bend-radius requirements
- Adjustable screw – bracket adjusts to most finished floor depths
- Leviton QuickPort® Quad 106® insert – install up to 4 low-voltage inserts
- Two-door design

Installation



01



E216492

Cat. No.	Cover	Std. Ctn.	Std. Wt. (lbs.)
SC100FBWC	Non-metallic – White	8	5.62
SC100FBVC	Non-metallic – Ivory	8	5.62
SC100FBBC	Brass	8	13.78

Floor box kit for wood floors

Single-gang residential


— 01 Brass finish with duplex receptacle

— 02 Nickel finish with GFCI receptacle

Tired of tripping over extension cords? Look no further than the Steel City® single-gang residential floor box kit from ABB. This affordable and conveniently packaged kit for the residential market provides power right where you need it most.

Features and benefits:

- Kit includes switch box, cover, flange and receptacle
- Durable metallic covers and flanges are available in aesthetic brass or nickel finishes
- Available with duplex or GFCI receptacle MopTite® covers meet UL® scrubwater requirements for wood, tile and carpet
- 3" x 2" switch box is 3½" deep with 18 cu. in. capacity
- Box includes integral non-metallic sheathed cable clamps



— 01



— 02

Steel City® single-gang residential floor box kit



Cat. No.	Description	Std. Ctn.
71W-DS	1-Gang residential floor box – duplex recp., brass finish	4
71W-DS-N	1-Gang residential floor box – duplex recp., nickel finish	4
71W-GFCI	1-Gang residential floor box – GFCI recp., brass finish	4
71W-GFCI-N	1-Gang residential floor box – GFCI recp., nickel finish	4

Drop-in floor box

Carlton®

The Carlton® Drop-in floor box with brass cover combines many of the same features of our existing floor box line with the strength, durability and style necessary to accommodate today's residential electrical/ telecommunication needs.

The Carlton® Drop-in floor box is the fastest, easiest way for contractors to put a floor socket anywhere they need it! It's designed to accommodate high- and low-voltage applications and comes complete with everything needed for installation – floor box, brass cover, hole saw, wired receptacle, two-hole low-voltage plate, blank plate, mounting screws and wire nuts.

Features and benefits:

- Single hole installation
- Fast, easy installation
- Cover options include: Brass and Aluminum
- Accommodates high- and low-voltage applications
- Includes single-gang grounded receptacle, low-voltage telephone/cable plate (data jacks not included) and blank plate for custom installations
- Tamper-resistant receptacle
- Available with or without a hole saw
- 11.8 inch cubic capacity
- Suitable for wood floor installations
- Ideal for residential and home offices
- Eliminates the need for extension cords
- Superior aesthetics – ideal for home offices and entertainment rooms
- 2.25" installation hole diameter



Drop-in floor box installation:

Note: Turn power off before installation.

01 Cut 2³/₈" hole through carpeting before using hole saw.



01

02 Drill hole in floor using hole saw.




02

03 Pull Romex™/Loomex™ through floor.



03

04 Connect receptacle wires to Romex™/Loomex™. Be sure to match wire color(s).




04

05 Secure wire clamp on bottom of tube.




05

06 Cover snaps into place. Use a small screwdriver to pry open cover to plug in appliance.



06

07 Align the three latches on the low-voltage plate with the three latch holes in the round floor box tube.





07



08

08 Remove receptacle by pressing three tabs located on side of tube. * 15A, 120V tamper proof receptacle.

Installed




Cat. No.	Cover	Description	Std. Ctn.	Std. Wt. (lbs.)
E971FBDI-2	Brass	Drop-in floor box with hole saw	5	6.5
E971FBDIB-2	Brass	Drop-in floor box without hole saw	20	17.6
E971FADI-2	Aluminum	Drop-in floor box with hole saw	5	5.1
E971FADIB-2	Aluminum	Drop-in floor box without hole saw	20	12.0

For wood subfloors

60W Series


Steel City® 60W Series Floor Boxes provide single- and multi-gang solutions for wood subfloor applications.




Features and benefits:

- Up to three-gang configuration for high-capacity, multi-service installations
- Large KOs ($\frac{3}{4}$ " and 1") on gang for application flexibility
- Adjustable mounting brackets allow for various finished floor-material heights (hardwoods, tile or carpet - $\frac{3}{4}$ " max)
- Ideal for open-layout residential applications, school lay-out auditoriums or commercial office space
- Voltage dividers are included with multi-gang boxes to accommodate power, voice and data services in the same floor box
- Full range of metallic and non-metallic cover and flange options


New construction (new work) applications



Retrofit construction (old work) application




Cat. No.	Dimension	A (in.)	Capacity	Std. Ctn.
61W	1-Gang floor box for wood subfloors $3\frac{11}{16}$ " Ends: (2) $\frac{1}{2}$ ", (2) $\frac{3}{4}$ " Bottom: (1) $\frac{1}{2}$ ", (1) 1"	$3\frac{11}{16}$	31 cu. in.	1
62W	2-Gang floor box for wood subfloors $7\frac{1}{16}$ " Ends: (4) $\frac{1}{2}$ ", (4) $\frac{3}{4}$ " Bottom: (2) $\frac{1}{2}$ ", (2) 1"	$7\frac{1}{16}$	60 cu. in.	1
63W	3-Gang floor box for wood subfloors $10\frac{1}{4}$ " Ends: (6) $\frac{1}{2}$ ", (6) $\frac{3}{4}$ " Bottom: (3) $\frac{1}{2}$ ", (3) 1"	$10\frac{1}{4}$	90 cu. in.	1




Metallic carpet plates


60W Series



P-64-CP



P-64-2G-CP




P-64-3G-CP




Cat. No.	Number of gangs	Outside Dimension (in.)	Material	Std. Ctn.
P64-CP	1	4 ⁵ / ₈ x 6 ¹ / ₈	Brass	4
P64-CP-AL	1	4 ⁵ / ₈ x 6 ¹ / ₈	Aluminum	4
P64-2G-CP	2	7 ⁵ / ₈ x 6 ¹ / ₈	Brass	4
P64-2G-CP-AL	2	7 ⁵ / ₈ x 6 ¹ / ₈	Aluminum	4
P64-3G-CP	3	10 ⁵ / ₈ x 6 ¹ / ₈	Brass	4
P64-3G-CP-AL	3	10 ⁵ / ₈ x 6 ¹ / ₈	Aluminum	4

Non-metallic carpet plates

60W Series




P64P-CP



P64P-2G-CP

Features and benefits:


- Translucent polycarbonate material
- Textured finish
- To install LCP Series plates, remove trim ring and place inside. Replace trim ring on box



P64P-3G-CP



P64P-2LCP



P64P-2LCP



P64P-3LCP




Cat. No.	Number of gangs	Description	Finish	Std. Ctn.
P64P-CP-BLK	1	Single-gang carpet plate	Black	4
P64P-CP-GRY	1	Single-gang carpet plate	Gray	4
P64P-CP-BGE	1	Single-gang carpet plate	Beige	4
P64P-2G-CP-BLK	2	Two-gang carpet plate	Black	4
P64P-2G-CP-GRY	2	Single-gang carpet plate	Gray	4
P64P-2G-CP-BGE	2	Two-gang carpet plate	Beige	4
P64P-3G-CP-BLK	3	Three-gang carpet plate	Black	4
P64P-3G-CP-GRY	3	Three-gang carpet plate	Gray	4
P64P-3G-CP-BGE	3	Three-gang carpet plate	Beige	4
P64P-LCP	1	Single gang carpet plate	Clear	4
P64P-2LCP	2	Two gang carpet plate		
P64P-3LCP	3	Three gang carpet plate		

MopTite™ Covers exceed UL/CSA Scrubwater exclusion requirements.

MopTite® carpet plates

60W Series



Features and benefits:

- Polished brass finish
- Furnished complete with sealing gasket and #8-32 x 7/16" screws
- 3" x 4-1/2" outside dimension



Cat. No.	Description	Finish	Std. Ctn.
P-64-1/2	Cover plate 1/2" NPS plug	Brass	4
P-64-3/4	Cover plate 3/4" NPS plug	Brass	4
P-64-3/4-AL	Cover plate 3/4" NPS plug	Aluminum	4
P-64-1	Cover plate 1" NPS plug	Brass	4
P-64-1-AL	Cover plate 1" NPS plug	Aluminum	4
P-64-1-1/4	Cover plate 1 1/4" NPS plug	Brass	4
P-64-1-1/4-AL	Cover plate 1 1/4" NPS plug	Aluminum	4
P-64-2	Cover plate 2" UN plug	Brass	4
P-64-2-AL	Cover plate 2" UN plug	Aluminum	4
P-64-1/2-2	Cover plate 1/2" & 2" UN plug	Brass	4

MopTite® Covers exceed UL/CSA Scrubwater exclusion requirements. For replacement plug, see page 132.

Cat. No.	Description	Finish	Std. Ctn.
P-64-1/2-2-AL	Cover plate 1/2" & 2" UN plug	Aluminum	4
P-64-3/4-2	Cover plate 3/4" & 2" UN plug	Brass	4
P-64-3/4-2-AL	Cover plate 3/4" & 2" UN plug	Aluminum	4
P-64-2-5/8	Cover plate 2 5/8" UN plug	Brass	4
P-64-2-5/8-AL	Cover plate 2 5/8" UN plug	Aluminum	4
P-64-DU	Cover plate duplex 1 7/16" plugs	Brass	4
P-64-DU-AL	Cover plate duplex 1 7/16" plugs	Aluminum	4
P-64-DS	Cover plate duplex lift lids	Brass	4
P-64-DS-AL	Cover plate duplex lift lids	Aluminum	4
P-64-GFCI	Cover plate GFCI flip lid	Brass	4
P-64-GFCI-AL	Cover plate GFCI flip lid	Aluminum	4

MopTite® non-metallic covers

60W Series



Features and benefits:

- Furnished complete with sealing gasket and #8-32 x 1" screws
- 3" x 4-1/2" outside dimension




Cat. No.	Description	Color	Std. Ctn.
P64P-URC-BLK	Universal cover *	Black	4
P64P-URC-GRY	Universal cover *	Gray	4
P64P-URC-BGE	Universal cover *	Beige	4
P64P-BP-BLK	Blank cover	Black	4
P64P-BP-GRY	Blank cover	Gray	4
P64P-BP-BGE	Blank cover	Beige	4

MopTite® Covers exceed UL/CSA Scrubwater exclusion requirements. * 5 pieces included, see picture above

Carlton® round floor box systems

Three-way versatility for power, data and communications

Carlton® round floor boxes give you the same cost-saving advantages over metal boxes as our rectangular boxes. By combining power, data and communications in the same box, you can dramatically reduce your installation time and cost compared to other non-metallic boxes. In addition, multi-use covers mean fewer SKUs to deal with and greater jobsite flexibility to increase your savings further. Take a closer look at all their advantages.





Features and benefits:

- Non-metallic PVC construction, watertight gasket and corrosion-resistant hardware ensure long life and reliable performance, even in harsh and/or corrosive environments
- Covers are available for a variety of applications
- The same box depth simplifies ordering and reduces inventory
- Suitable for tile and carpet applications
- Cover options include: brass, stainless steel and non-metallic (ivory, caramel, taupe, slate and brown)
- Concrete tight and suitable for any on-grade/ below-grade application; concrete or wood floor construction approved
- Y-connector (E972Y) enables you to feed parallel runs of 3/4" conduit or to feed in/out from the same side for increased wiring flexibility and faster installation
- PVC-molded ports and reducer plugs included
- Accepts 1/2", 3/4" and 1" conduit, tubing or raceway
- UL/CSA scrubwater tested, approved for all types of finish flooring

Round floor box - Carlton® round floor boxes enable various thicknesses of concrete pours. Trim out is easy – just use a handsaw to cut off box at desired height to accommodate carpet, tile or other flooring. Carlton® leveling ring guarantees a level top every time, even if the box is tipped slightly during the pouring process.



Cat. No.	Internal volume (cu. in.)	Min. concrete depth (in.)	Hubs (in.)	Reducer plugs (in.)	Std. Ctn.	Std. Wt. (lbs.)
E971FB	90.0 (15.5 per inch of depth)	3 1/2	(2) 1 and (2) 3/4	(2) 1 x 3/4 and (2) 3/4 x 1/2	10	15.6




Brass and stainless steel covers

For round floor boxes




Features and benefits:

- Screws concealed under doors
- Rugged construction
- Coated with a light lacquer finish for extra protection
- Resistance to wear – suited for high-traffic areas
- Gasketed for watertight applications
- Available in four styles – single door, two door, NPS opening and two-door dual service
- For tile and carpet applications
- UL/CSA scrubwater tested
- Cover diameter: 5½"




Two-door dual service (divider kit included)

Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BR2D	Brass	Duplex and two data ports	5	9.2
E97SS2D	Stainless steel	Duplex and two data ports	5	9.1




NPS opening

Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BRg	Brass	1¼" outlet and single receptacle	5	7.5
E97SSg	Stainless steel	1¼" outlet and single receptacle	5	8.1



Two door


Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BR2	Brass	Duplex	5	7
E97SS2	Stainless steel	Duplex	5	7.7



Cover adapter ring for use with metal covers

Cat. No.	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97ABR2	One-piece metal cover adapter	5	9.2

Note: Carlon® metal cover adapter ring (E97ABR2) is required with these covers (sold separately).




Single door

Cat. No.	Cover	Devices	Std. Ctn.	Std. Wt. (lbs.)
E97BR	Brass	GFCI and duplex	5	7
E97SS	Stainless steel	GFCI and duplex	5	7.9

Accessories

For round floor boxes

The multi-service divider kit for separate power, data and communications compartments provides unbeatable flexibility and money-saving installation speed. For use with non-metallic boxes only.




Multi-service divider kit



Cat. No.	Std. Ctn.	Std. Wt. (lbs.)
E973K	10	3

Features and benefits:

- High impact-resistant thermoplastic
- Compatible with standard NEMA Duplex and 1 1/4" NPS receptacles
- Drill points (3/8") provided for low-voltage cable pass throughs
- 1 1/4" NPS plugs may be modified to accept smaller fittings (3/8", 1/2" and 3/4")
- For tile and carpet applications
- UL/CSA scrubwater tested, approved for all types of finish flooring
- Cover diameter: 5.7"



Duplex covers



Cat. No.	Color	Description	Std. Ctn.	Std. Wt. (lbs.)
E97DSI	Ivory	Duplex cover	10	5.2
E97DSC	Caramel	Dulpex cover	10	5.7
E97DST	Taupe	Duplex cover	10	5.7
E97DSS	Slate	Duplex cover	10	5.6
E97DSB	Brown	Duplex cover	10	5.8

The 3/4" Y fitting provides for in-and-out service from a single 1" port, and provides two 3/4" parallel conduit runs to adapt into a single-conduit body port



3/4" Y fitting



Cat. No.	Std. Ctn.	Std. Wt. (lbs.)
E972Y	10	2.1

1 1/4" NPS covers



Cat. No.	Color	Description	Std. Ctn.	Std. Wt. (lbs.)
E97SSRB	Brown	NPS cover	10	3.8
E97SSRC	Caramel	NPS cover	10	3.8
E97SSRS	Slate	NPS cover	10	3.8



Reducer plugs



Cat. No.	Size (In.)	Std. Ctn.	Std. Wt. (lbs.)
E971C	3/4 x 1/2	100	2.1
E971D	1 x 3/4	100	3.2

Clear cover carpet ring

Cat. No.	Color	Std. Ctn.	Std. Wt. (lbs.)
E97CCR	Clear	10	1.2

Others and accessories



Retractable work surface receptacle

Concealed receptacle provides safe and convenient desktop power

With the variety of electronics and powered devices today, convenient power outlets in the home and office are critical. While phone chargers, laptops, appliances and other devices are typically located on work surfaces, outlets are often located underneath the work surface, along the wall or on the floor. Repeatedly accessing these outlets is an inconvenience and poses safety hazards.

The Carlon® retractable work surface receptacle provides a convenient outlet right where you need it. A hole saw is included that attaches to your power drill to quickly mount the receptacle in a counter, desk or similar work surface. A 6-ft. cord connects to an existing wall or floor outlet, so no wiring is required. Simply pull up the receptacle's cover to raise the unit above the work surface and plug in a device. When not in use, push the cover down to store the receptacle below the work surface. The non-metallic cover is black to complement most home or office decor.

Features and benefits:

- Provides easy access to a power outlet – simply pull up the receptacle to plug in a device
- 6-ft. cord plugs into an existing floor or wall outlet
- Receptacle remains hidden below work surface when not in use
- Compact design occupies minimal space both when recessed and while in use
- Rotated receptacle orientation accommodates oversized power adapters
- Hole saw included
- cULus Listed, File Number E340129 (per UL® 962A, Furniture Power Distribution Units)



Cat. No.	Description	Std. Pkg. Qty.
RWSR	Recessed pull-up receptacle, black, 6 ft. cord with three-prong plug	1

Communication accessories

Rectangular/Duplex adapters



OPODEC1-WH



OPODEC2-WH



OPODEC3-WH



OPODEC4-WH*



OPODEC6-WH*



OPOD4-WH



OPODEC-XLRF-WH



OPODEC-XLRM-WH



OPODEC-VGA-WH

Rectangular/duplex adapters for use with standard floor box device plates

Cat. No.	Description	Std. Ctn.
OPODEC1-WH	Rectangular adapters for GFCI device plate, 1-port, keystone, white	5
OPODEC2-WH	Rectangular adapters for GFCI device plate, 2-port, keystone, white	5
OPODEC3-WH	Rectangular adapters for GFCI device plate, 3-port, keystone, white	5
OPODEC4-WH*	Rectangular adapters for GFCI device plate, 4-port, keystone, white	5
OPODEC6-WH*	Rectangular adapters for GFCI device plate, 6-port, keystone, white	5
OPOD4-WH	Duplex adapter, 4-port, keystone, white	10
OPODEC-XLRF-WH	Rectangular adapters, female XLR microphone jack, solder leads, white	5
OPODEC-XLRM-WH	Rectangular adapters, male XLR microphone jack, solder leads, white	5
OPODEC-VGA-WH	Rectangular adapters, VGA connector, female-to-female, white	5

* Special installation note: When using these AV connectors with OPODEC4-WH & OPODEC6-WH rectangular adapters, only a blank insert (OPAB-WH) can be used in the same horizontal row. Trim the ears off one side of the Blank Insert and install prior to installing the AV connector in the row.

Keystone

Inserts




OPJDU5EL-WH




OPJDU6L-WH




OPJV6C-WH



OPARCAW*



OPARCAR*



OPARCAW*



OPAS-WH*



OPAB-WH

Keystone inserts for data, voice and audio visual applications

Cat. No.	Description	Std. Ctn.
OPJDU5EL-WH	CAT5e data jack, keystone, white	5
OPJDU6L-WH	CAT6 data jack, keystone, white	5
OPJV6CL-WH	Phone jack, 6-conductor, keystone, white	5
OPARCAW*	RCA connector – white, recessed, keystone, female-to-female	5
OPARCAR*	RCA connector – red, recessed, keystone, female-to-female	5
OPARCAW*	RCA connector – yellow, recessed, keystone, female-to-female	5
OPAS-WH	S-Video connector, 4-Pin, recessed, keystone, female-to-female, white	5
OPAB-WH	Blank insert, keystone, white	25

* Special Installation Note: When using these AV connectors with OPODEC4-WH & OPODEC6-WH Rectangular Adapters, only a Blank Insert (OPABL-WH) can be used in the same horizontal row. Trim the ears off one side of the Blank Insert and install prior to installing the AV connector in the row.

Keystone


Data accessories

Keystone Category 5e Jacks



Cat. No.	Description	Std. Ctn.
OPJNUD	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, black	25
OPJNUD-IV	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, ivory	25
OPJNUDBL	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, blue	25
OPJNUDOW	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, off white	25
OPJNUDWH	CAT5e Slim-Line UTP Jack, 568A/568B Wiring, Dual 110/Krone IDC, white	25


Keystone RJ11 Voice Jacks



Cat. No.	Description	Std. Ctn.
OPJ6CVBK	6 Wire RJ11/RJ12 Voice Jack, black	25
OPJ6CVIV	6 Wire RJ11/RJ12 Voice Jack, ivory	25
OPJ6CVWH	6 Wire RJ11/RJ12 Voice Jack, white	25

Replacement parts & accessories for 68, 600, 640, 740 and 840 Series

1-, 2-, 3-Gang



Floor plate plug inserts



Cat. No.	Size or description	Std. Ctn.
690-SC	1/2"-14" NPS thread	4
691-SC	3/4"-14" NPS thread	4
692-SC	1"-11 1/2" NPS thread	4
692-AL	1"-11 1/2" NPS thread	4
693-SC	1 1/4"-11 1/2" NPS thread	4
694	2"-20" UN thread	4
694-AL	2"-20" UN thread	4
695	1/2"-2"	4
695-AL	1/2"-2"	4
696-SC	3/4"-2"	4
697*	2 5/8"-20" UN 2A thread	4
697-AL	2 5/8"-20" UN 2A thread	4
698*	1 1/16" for duplex P-60-DU	4
698-AL	1 1/16" for duplex P-60-DU	4

* CSA Not applicable.



Gaskets for floor plate assemblies



Cat. No.	Description for use with:	Std. Ctn.
630-SC	P-60 Series floor plate assemblies	4
631	(except duplex) P-60-DR, P-60-DU, P-60-DC-AL floor plate assemblies	4
SP-60-DS-P3	P-60-DS floor plate assembly	1



Seating plates for receptacles – steel



Cat. No.	Description for use with:	Std. Ctn.
SP-620-MA	P-60-2, P-60-1/2-2, P-60-3/4-2 floor plate assemblies	1
SP-621	P-60-DR, P-60-DU, P-60-DC-AL and P-60-DS floor plate assemblies	1



Tile trims



Cat. No.	Description	Std. Ctn.
600-4-FL-AL	Aluminum	4
600-4-FL	Brass	4



Gaskets for floor plate assemblies



Cat. No.	Description for use with:	Std. Ctn.
SP650	P-64 Series floor plate assemblies	4
SP651	P-64-DU floor plate assemblies	10
SPP-64-DS-P2	P-64-DS floor plate assemblies	4




Seating plates for receptacles – steel



Cat. No.	Description for use with:	Std. Ctn.
640	P-64-2, P-64-1/2-2, P-64-3/4-2 floor plate assemblies	4
638	P-64-DS and P-64-DU floor plate assemblies	1



8803



8818

Floor plate plug inserts



Cat. No.	Description for use with:	Std. Ctn.
8803	Threaded steel body cover for 98 Series	4
8818	Metal protective cap	4

* CSA Not applicable.
2-5/8 in. – 20 in. UN 2A Thread



Plate for short strap receptacle



Cat. No.	Description for use with:	Std. Ctn.
889	Series 671 and 672 Boxes	4



489-MA 1-1/4 in. dia.




Plate for short strap receptacle



Cat. No.	Description for use with:	Std. Ctn.
489-MA	27-gauge galvanized steel with 1-1/4 in. dia. Opening for standard microphone jacks: for Steel City® Floor Box Serie 671	4

Index & useful information

Order code classification

Part No.	Page No.	Part No.	Page No.	Part No.	Page No.
631	127	602-SC	22	642P-TAC-BLK	52
638	127	603-AL-SC	21	642P-TAC-BLK	74
640	127	603-SC	21	642P-TAC-GRY	52
641	30	603-SC	22	642P-TAC-GRY	74
641	30	604-AL-SC	21	642P-TACA	52
641	30	604-SC	21	642P-TACA	74
642	30	604-SC	22	642P-TACB	52
642	30	61W	117	642P-TACB	74
642	30	62W	117	643-AL	30
643	30	630-SC	127	643P	51
643	30	63W	117	643P-CAC-BGE	51
643	30	641-1	30	643P-CAC-BGE	74
672	27	641-AL	30	643P-CAC-BLK	51
694	127	641P	51	643P-CAC-BLK	74
695	127	641P-CAC-BGE	51	643P-CAC-GRY	51
889	127	641P-CAC-BGE	74	643P-CAC-GRY	74
8803	127	641P-CAC-BLK	51	643P-CACA	51
8818	127	641P-CAC-BLK	74	643P-CACA	74
478-G-12	26	641P-CAC-GRY	51	643P-CACB	51
478-G-12	28	641P-CAC-GRY	74	643P-CACB	74
478-G-12	78	641P-CACA	51	643P-TAC-BGE	52
489-MA	127	641P-CACA	74	643P-TAC-BGE	74
4GFCI	100	641P-CACB	51	643P-TAC-BLK	52
600-1-SC	21	641P-CACB	74	643P-TAC-BLK	74
600-1-SC	22	641P-TAC-BGE	52	643P-TAC-GRY	52
600-11/4	22	641P-TAC-BGE	74	643P-TAC-GRY	74
600-2-SC	21	641P-TAC-BLK	52	643P-TACA	52
600-2-SC	22	641P-TAC-BLK	74	643P-TACA	74
600-4-FL	21	641P-TAC-GRY	52	643P-TACB	52
600-4-FL	70	641P-TAC-GRY	74	643P-TACB	74
600-4-FL	127	641P-TACA	52	663-SC	55
600-4-FL-AL	21	641P-TACA	74	663-SC	55
600-4-FL-AL	70	641P-TACB	52	664-2-MAAP	16
600-4-FL-AL	127	641P-TACB	74	664-2-MAAP	59
600-AL-SC	21	642-1	30	664-BP	16
600-SC	21	642-AL	30	664-BP	59
600-SC	22	642P	51	664-CI	14
601-1	21	642P-CAC-BGE	51	664-CI	14
601-1	22	642P-CAC-BGE	74	664-CST-M-ALM	58
601-1-1/4	21	642P-CAC-BLK	51	664-CST-M-BLK	58
601-1/2-SC	21	642P-CAC-BLK	74	664-CST-M-BRS	58
601-11/4	22	642P-CAC-GRY	51	664-CST-SW-BGE	15
601-AL-SC	21	642P-CAC-GRY	74	664-CST-SW-BGE	58
601-SC	21	642P-CACA	51	664-CST-SW-BLK	15
601-SC	22	642P-CACA	74	664-CST-SW-BLK	58
602-1	21	642P-CACB	51	664-CST-SW-BRN	15
602-1	22	642P-CACB	74	664-CST-SW-BRN	58
602-AL-SC	21	642P-TAC-BGE	52	664-CST-SW-GRY	15
602-SC	21	642P-TAC-BGE	74	664-CST-SW-GRY	58

Index & useful information

Order code classification

Part No.	Page No.	Part No.	Page No.	Part No.	Page No.
664-GP	16	667-RP	65	68P-DV-KIT-BLK	44
664-GP	59	667-SC	64	68P-DV-KIT-BRS	44
664-RP	16	668-CST-BGE	67	68P-FL	43
664-RP	59	668-CST-ALM	67	68P-FL-AL	43
664-S	57	668-CST-BLK	67	68R-CST-ALM	38
664-S-BP	59	668-CST-BRN	67	68R-CST-ALM	108
664-S-RP	59	668-CST-BRS	67	68R-CST-BGE	38
664-S-WT	59	668-S	66	68R-CST-BGE	108
664-SC	57	668-S-1G	67	68R-CST-BLK	38
664-WT	16	668-S-1RP	67	68R-CST-BLK	108
664-WT	59	668-S-6AVA	67	68R-CST-BRN	38
665-6RJ	19	668-S-6ORT	67	68R-CST-BRN	108
665-6RJ	63	668-S-6PAN	67	68R-CST-BRS	38
665-AV2	61	668-S-6RJ	67	68R-CST-BRS	108
665-BP	19	668-S-BP	67	68R-CST-GRY	38
665-BP	63	668-TRIM-ALM*	67	68R-CST-GRY	108
665-CI	17	668-TRIM-BGE*	67	690-SC	127
665-CST-M-ALM	18	668-TRIM-BLK*	67	691-SC	127
665-CST-M-ALM	62	668-TRIM-BRN*	67	692-AL	127
665-CST-M-BLK	18	668-TRIM-BRS *	67	692-SC	127
665-CST-M-BLK	62	671SC	27	693-SC	127
665-CST-M-BRS	18	68-D	70	694-AL	127
665-CST-M-BRS	62	68-D-AL	70	695-AL	127
665-CST-SW-BGE	18	68-HP	48	696-SC	127
665-CST-SW-BGE	62	68-HP-BI	49	697-AL	127
665-CST-SW-BLK	18	68-HP-CI	48	697*	127
665-CST-SW-BLK	62	68-HP-DI	49	698-AL	127
665-CST-SW-BRN	18	68-HP-DPAV-EXT	49	698*	127
665-CST-SW-BRN	62	68-HP-DPC-2MAAP	49	71W-DS -C	114
665-CST-SW-GRY	18	68-HP-DPC-GFCI	49	71W-DS-N -C	114
665-CST-SW-GRY	62	68-HP-DPC-R	49	71W-GFCI -C	114
665-GP	19	68-HP-DPS-2MAAP	49	71W-GFCI-N -C	114
665-GP	63	68-HP-DPS-DEC	49	741-D	73
665-RP	19	68-HP-FC-ALM	48	741-D	73
665-RP	63	68-HP-FC-BLK	48	741-S	73
665-SC	60	68-HP-FC-BRS	48	741-S	73
665-STEL	19	68-HP-FFC-ALM	50	742-D	73
665-STEL	63	68-HP-FFC-BLK	50	742-D	73
665-WT	19	68-HP-FFC-BRS	50	742-S	73
665-WT	63	68-HP-FFMK	50	742-S	73
667-1G	65	68-HP-FMK	49	743-D	73
667-2G	65	68-P	38	743-D	73
667-2RP	65	68-P	43	743-S	73
667-6RJ*	65	68-PAR	43	743-S	73
667-BP	65	68-S	70	78-S	25
667-CST-SW-BGE	65	68-S-AL	70	78-S	25
667-CST-SW-BLK	65	68P-DV-DP	44	78-S	25
667-CST-SW-BRN	65	68P-DV-DP-ORT	44	78SC	25
667-CST-SW-GRY	65	68P-DV-KIT-AL	44	78SC	25

Index & useful information

Order code classification

Part No.	Page No.	Part No.	Page No.	Part No.	Page No.
78SC	25	AFM-6S- BRN	103	E971FADIB-2	116
841-AL	30	AFM-6S- GRY	103	E971FB	40
841-SC	30	AFM-6V- BGE	104	E971FB	120
841-SC	30	AFM-6V- BLK	104	E971FBDI-2	116
841-SC	30	AFM-6V- BRN	104	E971FBDIB-2	116
842-AL-SC	30	AFM-6V- GRY	104	E972Y	42
842-SC	30	AFM-8- BGE	105	E972Y	122
842-SC	30	AFM-8- BRN	105	E973K	42
842-SC	30	AFM-8- GRY	105	E973K	122
843-AL-SC	30	AFP-2A	98	E9761B	35
843-SC	30	AFP-2B	98	E9761B	111
843-SC	30	AFP-4-GFCI-45	100	E9761BR	36
843-SC	30	AFP-4A	100	E9761BR	112
88-S	77	AFP-4A60	100	E9761C	35
AFC-N	100	AFP-4B	100	E9761C	111
AFC-N	102	AFP-4B60	100	E9761S	35
AFD-2 3RJ	98	AFP-6- GFCI	102	E9761S	111
AFD-4 4RJ	100	AFP-6- GFCI-45	102	E9761SS	36
AFD-4A	100	AFP-6A	102	E9761SS	112
AFD-4B	100	AFP-6A60	102	E9762B	35
AFD-6 6RJ	102	AFP-6B	102	E9762B	111
AFD-6A	102	AFP-6B60	102	E9762BR	36
AFD-6B	102	AFP-6Q	102	E9762BR	112
AFD-6Q	102	AFP-6R60	102	E9762C	35
AFD-6S2-2RJ	103	AFP-6S2-BR	103	E9762C	111
AFD-6V-2F	104	AFP-6S2-BR (-BL)	103	E9762S	35
AFD-8-3RJ	105	AFP-6S2-GR (-GL)	103	E9762S	111
AFM-2- BGE	98	AFP-6S2-R (-L)	103	E9762SS	36
AFM-2- BLK	98	AFP-6V-3D•	104	E9762SS	112
AFM-2- BRN	98	AFP-6V-3G	104	E9763B	35
AFM-2- GRY	98	AFP-8A	105	E9763B	111
AFM-2-ALM	99	AFP-8B	105	E9763BR	36
AFM-2-BRS	99	AFP-8G	105	E9763BR	112
AFM-2-MBLK	99	AFR-2	98	E9763C	35
AFM-4- BGE	100	AFR-4	100	E9763C	111
AFM-4- BLK	100	AFR-6	102	E9763S	35
AFM-4- BRN	100	AFR-6	103	E9763S	111
AFM-4- GRY	100	AFR-6	104	E9763SS	36
AFM-4-ALM	101	AFR-8	105	E9763SS	112
AFM-4-BRS	101	AFT-2	98	E976AK2	34
AFM-4-MBLK	101	AFT-46	100	E976AK2	111
AFM-4EX	100	AFT-46	102	E976AK2	112
AFM-6- BGE	102	CXWOWP-CN	108	E976RFB	34
AFM-6- BLK	102	CY12CN	108	E976RFB	111
AFM-6- BRN	102	E971C	42	E97ABR2	41
AFM-6- GRY	102	E971C	122	E97ABR2	121
AFM-6EX	102	E971D	42	E97BR	41
AFM-6S- BGE	103	E971D	122	E97BR	121
AFM-6S- BLK	103	E971FADI-2	116	E97BR2	41

Index & useful information

Order code classification

Part No.	Page No.	Part No.	Page No.	Part No.	Page No.
E97BR2	121	FFPT4-CVR-BRS	94	FPT3-CVR-BRS	82
E97BR2D	41	FFPT4-CVR-GRY	94	FPT3-CVR-GRY	82
E97BR2D	121	FFPT6-ALM	95	FPT4-1TL21-2C	86
E97BRg	41	FFPT6-BLK	95	FPT4-1TL22-2C	86
E97BRg	121	FFPT6-BRS	95	FPT4-1TL31-2C	86
E97Ccr	42	FFPT6-CVR-ALM	95	FPT4-1TL32-2C	86
E97Ccr	122	FFPT6-CVR-BLK	95	FPT4-2P-6C	85
E97DSB	42	FFPT6-CVR-BRS	95	FPT4-2P-RPL	87
E97DSB	122	FM-8- BLK	105	FPT4-4P-4C	84
E97DSC	42	FPT-3/4-2-CACP	92	FPT4-4P-4C-TALM	84
E97DSC	122	FPT-400B	81	FPT4-4P-4C-TBLK	84
E97DSI	42	FPT-400B	90	FPT4-4P-4C-TBRS	84
E97DSI	122	FPT-400B	92	FPT4-8C	85
E97DSS	42	FPT-401A	90	FPT4-CCH-2P	86
E97DSS	122	FPT-408A	90	FPT4-CCH-6C	85
E97DST	42	FPT-421	90	FPT4-CCH-8C	85
E97DST	122	FPT-422A	90	FPT4-CPA-1MAAP	87
E97SS	41	FPT-424	90	FPT4-CPA-3PAN**	87
E97SS	121	FPT-425	90	FPT4-CPA-4KEY*	87
E97SS2	41	FPT-441-SW-BLK	81	FPT4-CPA-4ORT	87
E97SS2	121	FPT-441-SW-BRN	81	FPT4-CPA-4SYS	87
E97SS2D	41	FPT-441-SW-BRS	81	FPT4-CPA-BLANK	87
E97SS2D	121	FPT-441-SW-GRY	81	FPT4-CPAB-2MAAP***	87
E97SSg	41	FPT-442-SW-BGE	92	FPT4-CPB-1MAAP	87
E97SSg	121	FPT-442-SW-BLK	92	FPT4-CPB-2KEY*	87
E97SSRB	42	FPT-442-SW-BRN	92	FPT4-CPB-2ORT	87
E97SSRB	122	FPT-442-SW-BRS	92	FPT4-CPB-2PAN**	87
E97SSRC	42	FPT-442-SW-GRY	92	FPT4-CPB-2SYS	87
E97SSRC	122	FPT-445-SW-BLK	81	FPT4-CPB-BLANK	87
E97SSRS	42	FPT-445-SW-BRN	81	FPT4-CVR-TALM	84
E97SSRS	122	FPT-445-SW-BRS	81	FPT4-CVR-TBGE	84
FFPT3	93	FPT-445-SW-GRY	81	FPT4-CVR-TBLK	84
FFPT3-ALM	93	FPT-448-SW-BGE	92	FPT4-CVR-TBRN	84
FFPT3-BLK	93	FPT-448-SW-BLK	92	FPT4-CVR-TBRS	84
FFPT3-BRS	93	FPT-448-SW-BRN	92	GAB-8-S	68
FFPT3-CVR-ALM	93	FPT-448-SW-BRS	92	OPAB-WH	126
FFPT3-CVR-BGE	93	FPT-448-SW-GRY	92	OPARCAR*	126
FFPT3-CVR-BLK	93	FPT-449	81	OPARCAW*	126
FFPT3-CVR-BRN	93	FPT-450	81	OPARCAY*	126
FFPT3-CVR-BRS	93	FPT-CACP	81	OPAS-WH	126
FFPT3-CVR-GRY	93	FPT-CACP-AL	81	OPJ6CVBK	126
FFPT4	94	FPT3-2P-2C	82	OPJ6CVIV	126
FFPT4-ALM	94	FPT3-2P-2C-ALM	82	OPJ6CVWH	126
FFPT4-BLK	94	FPT3-2P-2C-BLK	82	OPJDU5EL-WH	126
FFPT4-BRS	94	FPT3-2P-2C-BRS	82	OPJDU6L-WH	126
FFPT4-CVR-ALM	94	FPT3-CVR-ALM	82	OPJNUD	126
FFPT4-CVR-BGE	94	FPT3-CVR-BGE	82	OPJNUD-IV	126
FFPT4-CVR-BLK	94	FPT3-CVR-BLK	82	OPJNUDBL	126
FFPT4-CVR-BRN	94	FPT3-CVR-BRN	82	OPJNUDOW	126

Index & useful information

Order code classification

Part No.	Page No.	Part No.	Page No.	Part No.	Page No.
OPJNUDWH	126	P-60-3/4	24	P-60-Q-GFCI	56
OPJV6CL-WH	126	P-60-3/4	46	P-60-QB	56
OPOD4-WH	90	P-60-3/4	72	P-62-CP-AS*2	56
OPOD4-WH	125	P-60-3/4-2	24	P-62-CP-BRN*2	56
OPODEC-VGA-WH	125	P-60-3/4-2	46	P-62-CP-G*2	56
OPODEC-XLRF-WH	125	P-60-3/4-2	72	P-62-TAR	56
OPODEC-XLRM-WH	125	P-60-3/4-2-AL	24	P-62-TAR-AL	56
OPODEC1-WH	125	P-60-3/4-2-AL	46	P-64-1	31
OPODEC2-WH	125	P-60-3/4-2-AL	72	P-64-1	52
OPODEC3-WH	125	P-60-3/4-2-CACP	23	P-64-1	75
OPODEC4-WH*	125	P-60-3/4-2-CACP	71	P-64-1	119
OPODEC6-WH	49	P-60-3/4-AL	24	P-64-1-1/4	31
OPODEC6-WH*	125	P-60-3/4-AL	46	P-64-1-1/4	52
P-60-1	24	P-60-3/4-AL	72	P-64-1-1/4	75
P-60-1	46	P-60-3B*	56	P-64-1-1/4	119
P-60-1	72	P-60-CACP	23	P-64-1-1/4-AL	31
P-60-1-1/4	24	P-60-CACP	71	P-64-1-1/4-AL	52
P-60-1-1/4	46	P-60-CACP-AL	23	P-64-1-1/4-AL	75
P-60-1-1/4	72	P-60-CACP-AL	71	P-64-1-1/4-AL	119
P-60-1-1/4-AL	24	P-60-CP	23	P-64-1-AL	31
P-60-1-1/4-AL	46	P-60-CP	56	P-64-1-AL	52
P-60-1-1/4-AL	72	P-60-CP	71	P-64-1-AL	75
P-60-1-AL	24	P-60-CP-AL	56	P-64-1-AL	119
P-60-1-AL	46	P-60-CPAL	23	P-64-1/2	52
P-60-1-AL	72	P-60-CPAL	71	P-64-1/2	75
P-60-1/2	24	P-60-DR	24	P-64-1/2	119
P-60-1/2	46	P-60-DR	46	P-64-1/2-2	31
P-60-1/2	72	P-60-DR	72	P-64-1/2-2	52
P-60-1/2-2	24	P-60-DS	24	P-64-1/2-2	75
P-60-1/2-2	46	P-60-DS	46	P-64-1/2-2	119
P-60-1/2-2	72	P-60-DS	72	P-64-1/2-2-AL	31
P-60-1/2-2-AL	24	P-60-DS-AL	24	P-64-1/2-2-AL	52
P-60-1/2-2-AL	46	P-60-DS-AL	46	P-64-1/2-2-AL	75
P-60-1/2-2-AL	72	P-60-DS-AL	72	P-64-1/2-2-AL	119
P-60-1/2-AL	24	P-60-DU	24	P-64-1/2-AL	31
P-60-1/2-AL	46	P-60-DU	46	P-64-2	31
P-60-1/2-AL	72	P-60-DU	72	P-64-2	52
P-60-2	24	P-60-DU-AL	24	P-64-2	75
P-60-2	46	P-60-DU-AL	46	P-64-2	119
P-60-2	72	P-60-DU-AL	72	P-64-2-5/8	31
P-60-2-5/8	24	P-60-GFCI	24	P-64-2-5/8	52
P-60-2-5/8	46	P-60-GFCI	46	P-64-2-5/8	75
P-60-2-5/8	72	P-60-GFCI	72	P-64-2-5/8	119
P-60-2-5/8-AL	24	P-60-GFCI-AL	24	P-64-2-5/8-AL	31
P-60-2-5/8-AL	46	P-60-GFCI-AL	46	P-64-2-5/8-AL	52
P-60-2-5/8-AL	72	P-60-GFCI-AL	72	P-64-2-5/8-AL	75
P-60-2-AL	24	P-60-LCP	23	P-64-2-5/8-AL	119
P-60-2-AL	46	P-60-LCP	71	P-64-2-AL	31
P-60-2-AL	72	P-60-Q	56	P-64-2-AL	52

Index & useful information

Order code classification

Part No.	Page No.	Part No.	Page No.	Part No.	Page No.
P-64-2-AL	75	P-67-3/4	27	P64-2G-CP-AL	31
P-64-2-AL	119	P-67-3/4-2	27	P64-2G-CP-AL	118
P-64-3/4	31	P-67-3/4-AL	27	P64P-2LCP	118
P-64-3/4	52	P-67-F	28	P64-3G-CP	31
P-64-3/4	75	P-68-DRC-BGE	45	P64-3G-CP	118
P-64-3/4	119	P-68-DRC-BLK	45	P64-3G-CP-AL	31
P-64-3/4-2	31	P-68-DRC-BRN	45	P64-3G-CP-AL	118
P-64-3/4-2	52	P-68-DRC-GRY	45	P64P-3LCP	118
P-64-3/4-2	75	P-68-FSC-BGE	45	P64-CP	31
P-64-3/4-2	119	P-68-FSC-BLK	45	P64-CP	118
P-64-3/4-2-AL	31	P-68-FSC-BRN	45	P64-CP-AL	31
P-64-3/4-2-AL	52	P-68-FSC-GRY	45	P64-CP-AL	118
P-64-3/4-2-AL	75	P-68-SRC-BGE	45	P64P-LCP	118
P-64-3/4-2-AL	119	P-68-SRC-BLK	45	P64P-2G-CP-BGE	53
P-64-3/4-AL	31	P-68-SRC-BRN	45	P64P-2G-CP-BGE	76
P-64-3/4-AL	52	P-68-SRC-GRY	45	P64P-2G-CP-BGE	118
P-64-3/4-AL	75	P-90-1-1/4-AL	26	P64P-2G-CP-BLK	53
P-64-3/4-AL	119	P-90-1-1/4-AL	78	P64P-2G-CP-BLK	76
P-64-DS	31	P-90-1-AL	26	P64P-2G-CP-BLK	118
P-64-DS	52	P-90-1-AL	78	P64P-2G-CP-GRY	53
P-64-DS	75	P-90-1/2-2	26	P64P-2G-CP-GRY	76
P-64-DS	119	P-90-1/2-2	78	P64P-2G-CP-GRY	118
P-64-DS-AL	31	P-90-2-AL	26	P64P-3G-CP-BGE	53
P-64-DS-AL	52	P-90-2-AL	78	P64P-3G-CP-BGE	76
P-64-DS-AL	75	P-90-3/4-2	26	P64P-3G-CP-BGE	118
P-64-DS-AL	119	P-90-3/4-2	78	P64P-3G-CP-BLK	53
P-64-DU	31	P-90-3/4-2-AL	26	P64P-3G-CP-BLK	76
P-64-DU	52	P-90-3/4-2-AL	78	P64P-3G-CP-BLK	118
P-64-DU	75	P-90-3/4-AL	26	P64P-3G-CP-GRY	53
P-64-DU	119	P-90-3/4-AL	78	P64P-3G-CP-GRY	76
P-64-DU-AL	31	P-90-CP	26	P64P-3G-CP-GRY	118
P-64-DU-AL	52	P-90-CP	28	P64P-BP-BGE	53
P-64-DU-AL	75	P-90-CP	78	P64P-BP-BGE	76
P-64-DU-AL	119	P60-3/4-2-CACP	45	P64P-BP-BGE	119
P-64-GFCI	31	P60-3/4-2-CACP-AL	23	P64P-BP-BLK	53
P-64-GFCI	52	P60-3/4-2-CACP-AL	45	P64P-BP-BLK	76
P-64-GFCI	75	P60-3/4-2-CACP-AL	71	P64P-BP-BLK	119
P-64-GFCI	119	P60-CACP	45	P64P-BP-GRY	53
P-64-GFCI-AL	31	P60-CACP-AL	45	P64P-BP-GRY	76
P-64-GFCI-AL	52	P60-CACP-GFCI	23	P64P-BP-GRY	119
P-64-GFCI-AL	75	P60-CACP-GFCI	71	P64P-CP-BGE	53
P-64-GFCI-AL	119	P60-CACP-GFCI-AL	23	P64P-CP-BGE	76
P-67-1	27	P60-CACP-GFCI-AL	71	P64P-CP-BGE	118
P-67-1-1/4	27	P60-CACP-GFCI-AL*	45	P64P-CP-BLK	53
P-67-1-AL	27	P60-CACP-GFCI*	45	P64P-CP-BLK	76
P-67-1/2	27	P60-CP-AL*	45	P64P-CP-BLK	118
P-67-1/2-2	27	P60-CP*	45	P64P-CP-GRY	53
P-67-2	27	P64-2G-CP	31	P64P-CP-GRY	76
P-67-2-AL	27	P64-2G-CP	118	P64P-CP-GRY	118

Index & useful information

Order code classification

Part No.	Page No.	Part No.	Page No.
P64P-URC-BGE	53	SPP-64-DS-P2	127
P64P-URC-BGE	76		
P64P-URC-BGE	119		
P64P-URC-BLK	53		
P64P-URC-BLK	76		
P64P-URC-BLK	119		
P64P-URC-BRN	76		
P64P-URC-GRY	53		
P64P-URC-GRY	76		
P64P-URC-GRY	119		
RPT6-3G-ALM	88		
RPT6-3G-BLK	88		
RPT6-3G-BRS	88		
RPT6-CVR-ALM	88		
RPT6-CVR-BLK	88		
RPT6-CVR-BRS	88		
RPT6-DPC-2MAAP*	88		
RPT6-DPC-GFCI	88		
RPT6-DPC-R	88		
RPT6-DPS-2MAAP*	88		
RPT6-DPS-DEC	88		
RPT6-JB-CVR-2G	88		
RPT6-JB-CVR-3G	88		
RPT8-5G-ALM	89		
RPT8-5G-BLK	89		
RPT8-5G-BRS	89		
RPT8-5G-SN	89		
RPT8-CDP-30A	89		
RPT8-CDP-50A	89		
RPT8-CDP-Keystone	89		
RPT8-CDP-MAAP	89		
RPT8-INSERT-BLANK	89		
RPT8-INSERT-WHITE	89		
RPT8-ODP-Keystone	89		
RPT8-SDP-Keystone	89		
RPT8-SDP-MAAP	89		
RWSR	124		
SP-60-DS-P3	127		
SP-620-MA	127		
SP-621	127		
SP-641-1-AL	30		
SP-642-1-AL	30		
SP-643-1	30		
SP-643-1-AL	30		
SP-P64-DS-P2	31		
SP650	31		
SP650	127		
SP651	31		
SP651	127		

Additional information

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.





—
US

ABB Installation Products
Electrification Products division
860 Ridge Lake Blvd.
Memphis, TN 38120
+1 901-252-5000

tnb.abb.com