



FITTINGS & STAMPINGS





FITTINGS & STAMPINGS



Staples PC 5020, 5025



- 12 Gauge Steel
- Rust Inhibitor
- Finger Friendly
- Boxed or in Pails
- Caution! Always Wear Eye Protection

Staples are used to attach NMC (non metallic cable) or BX (armored) cable to wooden studs. The RX Series is used for Romex® and the BX Series is used for Romex® and BX. The SEU staple is used for service entrance cable and is available in 100 pack. For electro galvanized specify G (i.e.; RXG50, BXG or SEU63G). Plastic Insulated staples are used for coaxial cable, bell wire, thermostat wire, telephone wire and Romex®.





| CAT NO | UPC | CABLE SIZE | SIZE (W X L) | GAUGE | STD | MSTR | WT/STD | UNIT |
|--|-------|---------------------|----------------|-------|-------|-------------|--------|------|
| 1/2" - 2 Conductor (#12 & #14) Romex® and other type NM Cable - PC 5020 | | | | | | | | |
| RX501 | 30710 | 14-2, 12-2 | 1/2 x 1" | 12 GA | 100 | 5000 | 0.57# | M |
| RX505 | 30715 | 14-2, 12-2 | 1/2 x 1" | 12 GA | 500 | 5000 | 2.75# | M |
| RX50B | 30720 | 14-2, 12-2 | 1/2 x 1" | 12 GA | 5000 | 5000 | 28.12# | M |
| RX503P | 30725 | 14-2, 12-2 | 1/2 x 1" | 12 GA | 10000 | 10000(Pail) | 56.60# | M |
| 9/16" - 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other Cable - PC 5020 | | | | | | | | |
| BX1001 | 27010 | 14-3, 12-3, 10-3 | 9/16 x 1-3/16" | 12 GA | 100 | 5000 | 0.69# | M |
| BX1005 | 27015 | 14-3, 12-3, 10-3 | 9/16 x 1-3/16" | 12 GA | 500 | 5000 | 3.38# | M |
| BX100B | 27020 | 14-3, 12-3, 10-3 | 9/16 x 1-3/16" | 12 GA | 5000 | 5000 | 34.50# | M |
| BX3P | 27025 | 14-3, 12-3, 10-3 | 9/16 x 1-3/16" | 12 GA | 7500 | 7500(Pail) | 51.64# | M |
| SEU - PC 5025 | | | | | | | | |
| SEU63 | 27130 | 6/3 SEU Cable | 13/16 x 1-3/8" | 12 GA | 100 | 1000 | 1.09# | M |
| SEU43 | 27135 | 4/3 & 2/3 SEU Cable | 1-1/8 x 1-1/2" | 12 GA | 100 | 1000 | 1.30# | M |

Staples - Electro Galvanized PC 5022, 5024



| CAT NO | UPC | CABLE SIZE | SIZE (W X L) | GAUGE | STD | MSTR | WT/STD | UNIT |
|--|-------|---------------------|----------------|-------|-------|-------------|--------|------|
| 1/2" - 2 Conductor (#12 & #14) Romex® and other type NM Cable - PC 5022 | | | | | | | | |
| RXG501 | 10530 | 14-2, 12-2, 10-2 | 1/2 x 1" | 12 GA | 100 | 5000 | 0.60# | M |
| RXG505 | 10531 | 14-2, 12-2, 10-2 | 1/2 x 1" | 12 GA | 500 | 5000 | 2.85# | M |
| RXG503P | 10532 | 14-2, 12-2, 10-2 | 1/2 x 1" | 12 GA | 10000 | 10000(Pail) | 59.50# | M |
| 9/16" - 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other Cable - PC 5022 | | | | | | | | |
| BXG1001 | 10533 | 14-3, 12-3, 10-3 | 9/16 x 1-3/16" | 12 GA | 100 | 5000 | 0.70# | M |
| BXG1005 | 10534 | 14-3, 12-3, 10-3 | 9/16 x 1-3/16" | 12 GA | 500 | 5000 | 3.50# | M |
| BXG3P | 10535 | 14-3, 12-3, 10-3 | 9/16 x 1-3/16" | 12 GA | 7500 | 7500(Pail) | 52.50# | M |
| SEU - PC 5024 | | | | | | | | |
| SEU63G | 27131 | 6/3 SEU Cable | 13/16 x 1-3/8" | 12 GA | 100 | 1000 | 1.09# | M |
| SEU43G | 27136 | 4/3 & 2/3 SEU Cable | 1-1/8 x 1-1/2" | 12 GA | 100 | 1000 | 1.32# | M |

Staples - Plastic Insulated PC 5026

| CAT NO | UPC | CABLE SIZE | SIZE | COLOR | STD | MSTR | WT/STD | UNIT |
|--|-------|--|------------|-----------|------|------------|--------|------|
| 1/2" - 2 Conductor (#12 & #14) Romex® and other type NM Cable | | | | | | | | |
| PLX501 | 27140 | 14-2, 12-2 | 1/2" | White | 100 | 5000 | 0.57# | M |
| PLX505 | 27142 | 14-2, 12-2 | 1/2" | White | 500 | 5000 | 2.44# | M |
| PLX50P | 27144 | 14-2, 12-2 | 1/2" | White | 4000 | 4000(Pail) | 22.80# | M |
| 9/16" - 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other Cable | | | | | | | | |
| PLX751 | 27146 | 14-3, 12-3, 10-3 | 3/4" | White | 100 | 5000 | 0.62# | M |
| PLX755 | 27148 | 14-3, 12-3, 10-3 | 3/4" | White | 500 | 5000 | 2.53# | M |
| PLX75P | 27150 | 14-3, 12-3, 10-3 | 3/4" | White | 3000 | 3000(Pail) | 15.60# | M |
| Co-Axial Straps (Use Co-Axial RG-6 & RG-59U) | | | | | | | | |
| PLX250W | 10523 | Tuff Pack  | 1/4" | White | 500 | 3000 | 1.16# | M |
| PLX250B | 10539 | Tuff Pack  | 1/4" | Black(UV) | 500 | 3000 | 1.16# | M |
| Bell, Telephone & Thermostat Wire Straps | | | | | | | | |
| PLX18W | 10540 | Tuff Pack  | 1/4 x 1/8" | White | 500 | 3000 | 1.08# | M |
| PLX18B | 10541 | Tuff Pack  | 1/4 x 1/8" | Black(UV) | 500 | 3000 | 1.08# | M |



Safety Plates PC 5050, 5060

Steel safety plates are affixed to the face of 2" x 4" members to protect utility pipes and to prevent nails from penetrating into hidden live wires (NMC cable) which may be running through notches or through the drilled holes in the stud.

- 16 Gauge Steel
- 20 Gauge Steel
- Nail Sharp Points
- Easy to Install
- Available in Boxes Or Pails
- Caution! Always Wear Eye Protection

| CAT NO | UPC | SIZE | GAUGE | STD | MSTR | WT/STD | UNIT |
|----------------|-------|----------------|-------|-----------|-----------|--------|------|
| PC 5050 | | | | | | | |
| 411 | 14100 | 1-1/2 x 2-3/4" | 16 | 100 | 1000 | 7.00# | C |
| 415 | 14105 | 1-1/2 x 2-3/4" | 16 | 500 | 500 | 35.00# | C |
| 41P | 14116 | 1-1/2 x 2-3/4" | 16 | 500(Pail) | 500(Pail) | 35.00# | C |
| PC 5060 | | | | | | | |
| 2516 | 14110 | 1-3/4 x 5" | 16 | 100 | 100 | 16.00# | C |
| 2520 | 14115 | 1-3/4 x 5" | 20 | 100 | 100 | 10.00# | C |
| 3516 | 14120 | 3 x 5" | 16 | 100 | 100 | 26.80# | C |

Dottie guarantees these plates to be 16 ga (.0538 to .0658) as required by some codes. Dottie makes no warranty that these plates cannot be pierced by powder actuated / gas powered nail guns.

Plate Straps PC 5150

Plate straps are nailed across studs to restrain pipe between studs; installed over utility pipes & electrical wire that pass through framing members to prevent piercing.

- 12 Gauge Steel
- 16 Gauge Steel
- Various Lengths
- Caution! Always Wear Eye Protection

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------------------|-----|------|--------|------|
| PS129 | 60010 | 1-1/2 x 9" | 50 | 50 | 16.66# | C |
| PS1212 | 60012 | 1-1/2 x 12" | 50 | 50 | 23.50# | C |
| PS1218 | 60014 | 12 Gauge 1-1/2 x 18" | 50 | 50 | 36.00# | C |
| PS1224 | 60016 | 1-1/2 x 24" | 50 | 50 | 41.20# | C |
| PS169 | 60018 | 1-1/2 x 9" | 50 | 50 | 9.14# | C |
| PS1612 | 60020 | 1-1/2 x 12" | 50 | 50 | 15.40# | C |
| PS1618 | 60022 | 16 Gauge 1-1/2 x 18" | 50 | 50 | 19.58# | C |
| PS1624 | 60024 | 1-1/2 x 24" | 50 | 50 | 28.50# | C |



Nail Straps PC 5070, 5080, 5090

Nail Straps are a stamped steel strap (J hook) which is nailed into studs to support tubing, pipe or E.M.T. Available in zinc or copper plated, and in copper plated with the top plastic coated.

- 12 Gauge Steel
- Copper Plated With Plastic Coating
- Zinc or Copper Plated
- Caution! Always Wear Eye Protection

| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|---|-------|--------|----------------|-------------|-------------|--------|------|
| Zinc Plated - PC 5070 | | | | | | | |
| D1 | 27655 | 1/2" | Pipe | 100 | 1000 | 1.94# | M |
| D1P | 27658 | 1/2" | Pipe | 2000 (Pail) | 2000 (Pail) | 39.90# | M |
| D2 | 27660 | 3/4" | Pipe | 100 | 1000 | 2.32# | M |
| D3 | 27665 | 1" | Pipe | 100 | 1000 | 2.63# | M |
| D11 | 27670 | 1/2" | E.M.T. | 100 | 1000 | 1.53# | M |
| D12 | 27675 | 3/4" | E.M.T. | 100 | 1000 | 1.99# | M |
| D13 | 27680 | 1" | E.M.T. | 100 | 1000 | 2.30# | M |
| Copper Plated - PC 5080 | | | | | | | |
| K1 | 27100 | 1/2" | Tube | 100 | 1000 | 1.60# | M |
| K2 | 27102 | 3/4" | Tube | 100 | 1000 | 1.86# | M |
| K3 | 27104 | 1" | Tube | 100 | 1000 | 2.36# | M |
| K4 | 27106 | 1-1/4" | Tube | 100 | 1000 | 2.36# | M |
| Copper Plated w/ Plastic Coating - PC 5090 | | | | | | | |
| PL10 | 27107 | 1/2" | Tube 3/8" Iron | 100 | 1000 | 1.72# | M |
| PL20 | 27108 | 3/4" | Tube 1/2" Iron | 100 | 1000 | 2.04# | M |
| PL30 | 27110 | 1" | Tube 3/4" Iron | 50 | 500 | 1.30# | M |
| PL40 | 27112 | 1-1/4" | Tube 1" Iron | 50 | 500 | 1.55# | M |



Wire Hangers PC 5100

- 10 Gauge Steel
- Plain (Uncoated)
- Plastic Coated

- Caution! Always Wear Eye Protection

Wire Hangers are used to secure pipe or tubing transversing wood beams.



| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------------|-------|----------|-----|------|--------|------|
| Plain | | | | | | |
| WH124 | 27200 | 1/2 x 4" | 100 | 500 | 4.38# | M |
| WH126 | 27202 | 1/2 x 6" | 100 | 500 | 6.22# | M |
| WH344 | 27204 | 3/4 x 4" | 100 | 500 | 4.36# | M |
| WH346 | 27206 | 3/4 x 6" | 100 | 500 | 7.40# | M |

| | | | | | | |
|-----------------------|-------|----------|-----|-----|-------|---|
| Plastic Coated | | | | | | |
| PC124 | 27208 | 1/2 x 4" | 100 | 500 | 4.52# | M |
| PC126 | 27210 | 1/2 x 6" | 100 | 500 | 6.20# | M |
| PC344 | 27212 | 3/4 x 4" | 100 | 500 | 4.60# | M |
| PC346 | 27214 | 3/4 x 6" | 100 | 500 | 6.30# | M |

Hook on Clips · Hook on Straps PC 5110, 5120

- Hook on Clips & Straps
- Formed Wire
- Supplied With Insulator
- Caution! Always Wear Eye Protection

Hook on Straps & Clips are used to secure pipe or tubing running parallel with studs. The hook on straps are nailed across two studs. The hook on clips with insulator snap into holes in the strap and tubing or pipe is then secured perpendicular to the strap.



| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|---------------------------|-------|------------|-----|------|--------|------|
| 14 Gauge - PC 5110 | | | | | | |
| HC50 | 27220 | 1/2" Pipe | 100 | 1000 | 1.66# | M |
| HC75 | 27225 | 3/4" Pipe | 100 | 1000 | 1.75# | M |
| 12 Gauge - PC 5120 | | | | | | |
| 5818 | 27230 | 18" Length | 100 | 100 | 21.08# | C |
| 5826 | 27235 | 26" Length | 100 | 100 | 30.58# | C |

Plumber's Tape PC 5130, 5140

- Galvanized Steel
- Solid Copper

Plumber's Tape is 3/4" wide and is perforated with alternating size holes to accommodate nails or bolts. It is used to strap or support pipe, ducts & other fastening applications. Copper strap also used for grounding.



| CAT NO | UPC | LENGTH | GAUGE | STD | MSTR | WT/STD | UNIT |
|-----------------------------------|-------|-----------|-------|-----|------|--------|------|
| Galvanized Steel - PC 5130 | | | | | | | |
| PT28 | 30945 | 3/4 x 10' | 28 | 100 | 100 | 35.16# | Ea |
| PT26 | 30940 | 3/4 x 10' | 26 | 100 | 100 | 46.24# | Ea |
| PT22 | 30935 | 3/4 x 10' | 22 | 50 | 50 | 37.64# | Ea |
| Solid Copper - PC 5140 | | | | | | | |
| CU10 | 27550 | 3/4 x 10' | 23 | 1 | 10 | 0.58# | Ea |
| CU25 | 27555 | 3/4 x 25' | 23 | 1 | 6 | 1.48# | Ea |
| CU50 | 27560 | 3/4 x 50' | 23 | 1 | 6 | 2.97# | Ea |



One Hole Straps PC 5160

One Hole Straps are used to secure cables, tubing, pipe or E.M.T. to a surface

- Zinc Plated Steel (After Fabrication)
- Inverted Rib For Strength
- For E.M.T. / Pipe

| CAT NO | UPC | TYPE | SIZE | GAUGE | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------------|--------|-------|-----|------|--------|------|
| TW14 | 27745 | Coaxial | 1/4" | 18 GA | 100 | 1000 | 0.57# | C |
| TW38 | 27750 | BX * | 3/8" | 18 GA | 100 | 1000 | 1.15# | C |
| TW501 | 27700 | | 1/2" | 18 GA | 100 | 1000 | 2.22# | C |
| TW75 | 27705 | | 3/4" | 18 GA | 100 | 1000 | 3.12# | C |
| TW100 | 27710 | E.M.T. | 1" | 18 GA | 100 | 1000 | 3.45# | C |
| TW125 | 27715 | | 1-1/4" | 15 GA | 100 | 500 | 5.49# | C |
| TW150 | 27720 | | 1-1/2" | 15 GA | 50 | 500 | 3.86# | C |
| TW200 | 27725 | | 2" | 13 GA | 50 | 500 | 7.10# | C |
| TW250 | 27726 | | 2-1/2" | 9 GA | 25 | 100 | 10.13# | C |
| TW300 | 27727 | | 3" | 9 GA | 25 | 100 | 13.38# | C |
| TW350 | 27728 | E.M.T. / Pipe | 3-1/2" | 7 GA | 25 | 100 | 16.61# | C |
| TW400 | 27729 | | 4" | 7 GA | 25 | 100 | 19.02# | C |
| MTW50 | 27730 | E.M.T. | 1/2" | 14 GA | 100 | 1000 | 3.62# | C |
| MTW75 | 27735 | Medium | 3/4" | 14 GA | 100 | 1000 | 4.17# | C |
| MTW100 | 27740 | Weight | 1" | 14 GA | 100 | 500 | 5.45# | C |
| HW50 | 27800 | | 1/2" | 18 GA | 100 | 1000 | 2.53# | C |
| HW75 | 27805 | | 3/4" | 18 GA | 100 | 1000 | 3.19# | C |
| HW100 | 27810 | Pipe | 1" | 14 GA | 100 | 1000 | 6.66# | C |
| HW125 | 27815 | | 1-1/4" | 13 GA | 50 | 500 | 5.49# | C |
| HW150 | 27820 | | 1-1/2" | 11 GA | 50 | 500 | 8.36# | C |
| HW200 | 27825 | | 2" | 11 GA | 50 | 500 | 10.66# | C |
| MHW50 | 27830 | Pipe | 1/2" | 14 GA | 100 | 1000 | 3.82# | C |
| MHW75 | 27835 | Medium | 3/4" | 14 GA | 100 | 1000 | 5.00# | C |
| MHW100 | 27840 | Weight | 1" | 14 GA | 100 | 1000 | 6.71# | C |

* Accommodates 12-2, 12-3, 10-2, 10-3 BX



Two Hole Straps PC 5200

Two hole straps are used to secure cables, tubing, pipe or E.M.T. to a surface

- Zinc Plated Steel (After Fabrication)
- Inverted Rib For Strength
- For E.M.T. / Pipe

| CAT NO | UPC | TYPE | SIZE | GAUGE | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------------|--------|-------|-----|------|--------|------|
| TW301 | 27300 | | 1/2" | 22 GA | 250 | 1000 | 4.13# | C |
| TW302 | 27305 | | 3/4" | 22 GA | 250 | 1000 | 4.67# | C |
| TW303 | 27310 | | 1" | 22 GA | 250 | 1000 | 8.24# | C |
| TW304 | 27315 | E.M.T. | 1-1/4" | 20 GA | 100 | 500 | 4.45# | C |
| TW305 | 27320 | | 1-1/2" | 20 GA | 100 | 500 | 4.83# | C |
| TW306 | 27325 | | 2" | 20 GA | 50 | 250 | 3.11# | C |
| HW400 | 27900 | | 3/8" | 22 GA | 250 | 1000 | 4.64# | C |
| HW401 | 27905 | | 1/2" | 22 GA | 250 | 1000 | 4.70# | C |
| HW402 | 27910 | | 3/4" | 22 GA | 250 | 1000 | 5.33# | C |
| HW403 | 27915 | | 1" | 20 GA | 100 | 1000 | 3.82# | C |
| HW404 | 27920 | | 1-1/4" | 20 GA | 100 | 500 | 4.74# | C |
| HW405 | 27925 | Pipe | 1-1/2" | 20 GA | 100 | 500 | 5.30# | C |
| HW406 | 27930 | | 2" | 18 GA | 50 | 500 | 4.32# | C |
| HW407 | 27935 | | 2-1/2" | 15 GA | 25 | 250 | 4.96# | C |
| HW408 | 27940 | | 3" | 15 GA | 25 | 250 | 5.64# | C |
| HW409 | 27945 | | 3-1/2" | 15 GA | 10 | 50 | 3.44# | C |
| HW410 | 27950 | | 4" | 15 GA | 10 | 50 | 3.72# | C |





- Zinc Plated Steel (After Fabrication)
- Assembled With Combo Round Head Screws and Hex Nuts
- For E.M.T. & Pipe

Conduit hangers are used for supporting conduit or PVC from overhead applications.

| CAT NO | UPC | PIPE | E.M.T. | GAUGE | BOLT SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|--------|-------|-----------------|-----|------|--------|------|
| PH50B | 28320 | 3/8 -1/2" | 1/2" | 18 GA | 1/4-20 x 1" | 100 | 100 | 4.33# | C |
| PH75B | 28322 | 3/4" | 3/4" | 18 GA | 1/4-20 x 1-1/4" | 100 | 100 | 6.12# | C |
| PH100B | 28324 | 1" | 1" | 18 GA | 1/4-20 x 1-1/4" | 100 | 100 | 6.71# | C |
| PH110B | 28326 | - | 1-1/4" | 18 GA | 1/4-20 x 1-1/4" | 100 | 100 | 1.91# | C |
| PH125B | 28328 | 1-1/4" | 1-1/2" | 18 GA | 1/4-20 x 1-1/2" | 100 | 100 | 9.18# | C |
| PH150B | 28330 | 1-1/2" | - | 16 GA | 1/4-20 x 1-1/2" | 100 | 100 | 13.88# | C |
| PH200B | 28332 | 2" | 2" | 16 GA | 1/4-20 x 1-1/2" | 50 | 50 | 11.39# | C |
| PH250B | 28334 | 2-1/2" | 2-1/2" | 16 GA | 1/4-20 x 1-1/2" | 50 | 50 | 12.07# | C |
| PH300B | 28336 | 3" | 3" | 16 GA | 1/4-20 x 1-1/2" | 25 | 25 | 7.45# | C |
| PH350B | 28337 | 3-1/2" | - | 16 GA | 1/4-20 x 2" | 25 | 25 | 8.95# | C |
| PH400B | 28338 | 4" | - | 16 GA | 1/4-20 x 2" | 25 | 25 | 9.80# | C |

**Conduit Hangers - Stainless Steel with
Stainless Steel Bolt - PC 5221**



- 301 Stainless Steel
- stainless Steel Bolts and Nuts
- For EMT & Pipe

Conduit hangers are used for supporting conduit or PVC from overhead applications. Stainless Steel dramatically improves corrosion resistance.

| CAT NO | UPC | PIPE | E.M.T. | GAUGE | BOLT SIZE | STD | MSTR | WT/STD | UNIT |
|----------|-------|-----------|--------|-------|-----------------|-----|------|--------|------|
| PH50BSS | 81497 | 3/8 -1/2" | 1/2" | 18 GA | 1/4-20 x 1" | 10 | 100 | 0.43# | C |
| PH75BSS | 81498 | 3/4" | 3/4" | 18 GA | 1/4-20 x 1-1/4" | 5 | 50 | 0.36# | C |
| PH100BSS | 81499 | 1" | 1" | 18 GA | 1/4-20 x 1-1/4" | 5 | 50 | 0.33# | C |
| PH110BSS | 81500 | - | 1-1/4" | 18 GA | 1/4-20 x 1-1/4" | 2 | 20 | 0.38# | C |
| PH125BSS | 81501 | 1-1/4" | 1-1/2" | 18 GA | 1/4-20 x 1-1/2" | 2 | 20 | 0.48# | C |
| PH150BSS | 81502 | 1-1/2" | - | 16 GA | 1/4-20 x 1-1/2" | 2 | 20 | 0.27# | C |
| PH200BSS | 81503 | 2" | 2" | 16 GA | 1/4-20 x 1-1/2" | 2 | 20 | 0.45# | C |
| PH250BSS | 81504 | 2-1/2" | 2-1/2" | 16 GA | 1/4-20 x 1-1/2" | 2 | 20 | 0.48# | C |
| PH300BSS | 81505 | 3" | 3" | 16 GA | 1/4-20 x 1-1/2" | 2 | 20 | 0.59# | C |
| PH350BSS | 81506 | 3-1/2" | - | 16 GA | 1/4-20 x 2" | 2 | 20 | 0.72# | C |
| PH400BSS | 81507 | 4" | - | 16 GA | 1/4-20 x 2" | 2 | 20 | 0.78# | C |

TECH TALK



ZINC CHROMATE Plating is the most widely used plating. Zinc is popular as a fastener coating because it is the least expensive and can be applied to a broad range of thicknesses. It has good to excellent corrosion resistance and is relatively non toxic.

STAINLESS STEEL Is a family of ferrous alloys, each with a minimum chromium content of 12 percent. Chromium is a non-corrodible element; consequently, all stainless steels have a high degree of corrosion resistance. Generally, the higher the chromium content, the better the corrosion resistance.



Universal Strut Clamps PC 5391

One tool is all you need with our Universal Strut Clamps thanks to the **welded stud** that allows for a quick and easy installation. Includes keps nut, and the clamps come assembled to make sure you never lose any parts. Electrogalvanized is the standard finish.

| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|------------------------|-----|------|--------|------|
| SC50U | 81707 | 1/2" | Universal Strut Clamps | 50 | 50 | 5.5# | C |
| SC75U | 81708 | 3/4" | Universal Strut Clamps | 50 | 50 | 6.0# | C |
| SC100U | 81709 | 1" | Universal Strut Clamps | 50 | 50 | 7.5# | C |
| SC125U | 81710 | 1-1/4" | Universal Strut Clamps | 50 | 50 | 9.0# | C |
| SC150U | 81711 | 1-1/2" | Universal Strut Clamps | 50 | 50 | 10.0# | C |
| SC200U | 81712 | 2" | Universal Strut Clamps | 50 | 50 | 11.0# | C |

E.M.T. Strut Clamps come assembled with a keps nut and slotted hex head bolt to make sure you never lose a part. Electrogalvanized is the standard finish.

| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|---------------------|-----|------|--------|------|
| SC50E | 81713 | 1/2" | E.M.T. Strut Clamps | 100 | 100 | 11.0# | C |
| SC75E | 81714 | 3/4" | E.M.T. Strut Clamps | 100 | 100 | 12.0# | C |
| SC100E | 81715 | 1" | E.M.T. Strut Clamps | 100 | 100 | 15.0# | C |
| SC125E | 81716 | 1-1/4" | E.M.T. Strut Clamps | 50 | 50 | 7.5# | C |
| SC150E | 81717 | 1-1/2" | E.M.T. Strut Clamps | 50 | 50 | 14.5# | C |
| SC200E | 81718 | 2" | E.M.T. Strut Clamps | 50 | 50 | 16.5# | C |

Rigid Strut Clamps come assembled with a keps nut and slotted hex head bolt to make sure you never lose a part. Electrogalvanized is the standard finish. Also available are Stainless Steel Ridge Strut Clamps Type 304 or 316, quoted upon request.

| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|--------------------|-----|------|--------|------|
| SC50R | 81719 | 1/2" | Rigid Strut Clamps | 100 | 100 | 11.0# | C |
| SC75R | 81720 | 3/4" | Rigid Strut Clamps | 100 | 100 | 15.0# | C |
| SC100R | 81721 | 1" | Rigid Strut Clamps | 100 | 100 | 17.0# | C |
| SC125R | 81722 | 1-1/4" | Rigid Strut Clamps | 50 | 50 | 9.5# | C |
| SC150R | 81723 | 1-1/2" | Rigid Strut Clamps | 50 | 50 | 14.5# | C |
| SC200R | 81724 | 2" | Rigid Strut Clamps | 50 | 50 | 17.0# | C |
| SC250R | 81725 | 2-1/2" | Rigid Strut Clamps | 25 | 25 | 10.0# | C |
| SC300R | 81726 | 3" | Rigid Strut Clamps | 25 | 25 | 11.8# | C |
| SC350R | 81727 | 3-1/2" | Rigid Strut Clamps | 50 | 50 | 31.0# | C |
| SC400R | 81728 | 4" | Rigid Strut Clamps | 50 | 50 | 33.5# | C |
| SC500R | 81729 | 5" | Rigid Strut Clamps | 25 | 25 | 20.0# | C |
| SC600R | 81730 | 6" | Rigid Strut Clamps | 25 | 25 | 25.2# | C |



Channel Nuts & U-Bolt Beam Clamps PC 5392

Channel Nuts are formed or stamped from steel bar stock and are case hardened after all forming and tapping operations have been completed. The nuts are then coated with zinc for an electrogalvanize finish. Sizes are also available in type 316 stainless steel, quoted upon request.

| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|----------------------------|-----|------|--------|------|
| SSN25 | 81731 | 1/4" | Standard Spring Nut | 100 | 100 | 7.5# | C |
| SSN38 | 81732 | 3/8" | Standard Spring Nut | 100 | 100 | 10.0# | C |
| SSN50 | 81733 | 1/2" | Standard Spring Nut | 100 | 100 | 11.5# | C |
| SSN25S | 81734 | 1/4" | Short Spring Nut | 100 | 100 | 7.5# | C |
| SSN38S | 81735 | 3/8" | Short Spring Nut | 100 | 100 | 9.0# | C |
| SSN50S | 81736 | 1/2" | Short Spring Nut | 100 | 100 | 8.2# | C |
| SCN25 | 81737 | 1/4" | Channel Nut Without Spring | 100 | 100 | 6.5# | C |
| SCN38 | 81738 | 3/8" | Channel Nut Without Spring | 100 | 100 | 9.0# | C |
| SCN50 | 81739 | 1/2" | Channel Nut Without Spring | 100 | 100 | 10.6# | C |

U-Bolt Beam clamps are made from cold formed steel and conform to all tolerances listed in section 5.3 of the metal framing standards publication.


| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------|-----------------------------|-----|------|--------|------|
| SUB158 | 81767 | 1-5/8" x 1-5/8" | U-Bolt Beam Clamp for Strut | 25 | 25 | 20.5# | C |
| SUB325 | 81768 | 1-5/8" x 3-1/4" | U-Bolt Beam Clamp for Strut | 25 | 25 | 23.0# | C |



Flat Plate Fittings PC 5393




Flat Plate Strut Fittings are made from cold formed steel and conform to all tolerances listed in section 5.3 of Metal Framing Standards Publication No. MFMA-1. Standard finish is electrogalvanized. Stainless steel types 304 and 316, quoted upon request.



| CAT NO | UPC | SIZE/TYPE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|----------------------|-----|------|--------|------|
| SQW516 | 81740 | 5/16" | Square Washer | 100 | 100 | 18.0# | C |
| SQW38 | 81741 | 3/8" | Square Washer | 100 | 100 | 18.0# | C |
| SQW50 | 81742 | 1/2" | Square Washer | 100 | 100 | 18.0# | C |
| SQW58 | 81743 | 5/8" | Square Washer | 100 | 100 | 17.0# | C |
| SFP2 | 81744 | 2 Hole | Flat Plate Fitting | 50 | 50 | 19.0# | C |
| SFP3 | 81745 | 3 Hole | Flat Plate Fitting | 50 | 50 | 29.0# | C |
| SFP4 | 81746 | 4 Hole | Flat Plate Fitting | 25 | 25 | 19.5# | C |
| SFPL3 | 81747 | 3 Hole | Flat L Plate Fitting | 50 | 50 | 31.0# | C |
| SFPT4 | 81748 | 4 Hole | Flat T Plate Fitting | 25 | 25 | 20.0# | C |
| SFPC5 | 81749 | 5 Hole | Cross Plate Fitting | 15 | 15 | 14.2# | C |

Angle Fittings PC 5394


Angle Strut Fittings are made from cold formed steel and conform to all tolerances listed in section 5.3 of Metal Framing Standards Publication No. MFMA-1. Standard finish is electrogalvanized. Stainless steel types 304 and 316, quoted upon request.



| CAT NO | UPC | TYPE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|---------|-------|--------|-------------------------------|-----|------|--------|------|
| SAF290 | 81750 | 2 Hole | Bent 90° Angle Fitting | 50 | 50 | 19.0# | C |
| SAF390 | 81751 | 3 Hole | Bent 90° Angle Fitting | 50 | 50 | 29.0# | C |
| SAF490 | 81752 | 4 Hole | Bent 90° Angle Fitting | 25 | 25 | 19.5# | C |
| SAFU690 | 81753 | 6 Hole | Universal 90° Angle Fitting | 15 | 15 | 21.9# | C |
| SAF245 | 81754 | 2 Hole | Bent 45° Open Angle Fitting | 50 | 50 | 25.0# | C |
| SAF245C | 81755 | 2 Hole | Bent 45° Closed Angle Fitting | 25 | 25 | 14.5# | C |
| SAF445 | 81756 | 4 Hole | Bent 45° Open Angle Fitting | 25 | 25 | 15.0# | C |
| SAF445C | 81757 | 4 Hole | Bent 45° Closed Angle Fitting | 15 | 15 | 19.5# | C |

Zee Fittings & U Fittings and Post Bases - PC 5395


Zee and U-shaped fittings, Post Bases are made from cold formed steel and conform to all tolerances listed in section 5.3 of Metal Framing Standards Publication No. MFMA-1. Standard finish is electrogalvanized. Stainless steel types 304 and 316, quoted upon request.



| CAT NO | UPC | SIZE/TYPE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|------------------------------------|-------|-----------|-----------------------------------|-----|------|--------|------|
| Zee Fittings and U Fittings | | | | | | | |
| SZFDS | 81758 | - | Zee Fitting Deep Strut | 50 | 50 | 27.5# | C |
| SZFSS | 81759 | - | Zee Fitting Shallow Strut | 50 | 50 | 23.5# | C |
| SUFDS | 81760 | - | U Fitting Deep Strut | 15 | 15 | 13.2# | C |
| SUFSS | 81761 | - | U Fitting Shallow Strut | 25 | 25 | 17.7# | C |
| Post Bases | | | | | | | |
| SPB890 | 81762 | 8 Hole | Single Channel Tall Clevis | 10 | 10 | 28.7# | C |
| SPB1045 | 81763 | 10 Hole | Single Channel Tall Clevis | 10 | 10 | 37.2# | C |
| SPB1090 | 81764 | 10 Hole | Single Channel Tall Clevis Square | 10 | 10 | 37.2# | C |
| SPB1245 | 81765 | 12 Hole | Double Channel Tall Clevis | 10 | 10 | 40.0# | C |
| SPB1290 | 81766 | 12 Hole | Double Channel Tall Clevis Square | 10 | 10 | 40.0# | C |

FITTINGS & STAMPINGS > FLAT PLATE, ANGLE, ZEE & U FITTINGS > POST BASES






Standard - Roof Jacks PC 5230

Roof Jacks are applied to the roof to form a water-tight seal. They add additional support between the roof line and service entrance conduit or ventilation pipe.

- 28 Gauge
- Galvanized Steel

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT | |
|--------|-------|-----------------|--------|------|--------|--------|----|
| RJ50 | 69600 | Standard | 1/2" | 24 | 24 | 24.08# | Ea |
| RJ75 | 69605 | | 3/4" | 24 | 24 | 23.92# | Ea |
| RJ100 | 69610 | | 1" | 24 | 24 | 23.06# | Ea |
| RJ125 | 69615 | | 1-1/4" | 24 | 24 | 23.13# | Ea |
| RJ150 | 69620 | | 1-1/2" | 24 | 24 | 22.87# | Ea |
| RJ200 | 69625 | | 2" | 24 | 24 | 21.82# | Ea |
| RJ300 | 69630 | | 3" | 12 | 12 | 15.22# | Ea |
| RJ400 | 69635 | | 4" | 12 | 12 | 19.39# | Ea |



3 in 1 Roof Jacks PC 5250

Roof Jacks are applied to the roof to form a water-tight seal. They add additional support between the roof line and service entrance conduit or ventilation pipe.

- 24 Gauge
- Elastomer Collar

| CAT NO | UPC | PIPE SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|-----|------|--------|------|
| RN3 | 10350 | Pipe Sizes: 1/2", 3/4", 1" * Base Size: 8-3/4", 12-1/2" | 12 | 12 | 11.95# | Ea |
| RN4 | 10352 | Pipe Sizes: 1-1/2", 2", 2-1/2", 3" Base Size: 10-3/4" x 12-1/2" | 12 | 12 | 18.82# | Ea |

*Can be modified to fit 1-1/4" pipe

Fits any roof pitch - from flat to 45°

Tested for ultraviolet, ozone, and weather resistance.



Steel / Galvanized - Tie Wire PC 5030 - 5035

Tie wire is used for many purposes, among them tying down PVC conduit in trenches before pouring concrete, as well as drop ceiling applications.

- 16 1/2 Gauge
- 400 Ft. (3 1/2#)
- Black Annealed or Galvanized

| CAT NO | UPC | STD | MSTR | WT/STD | UNIT |
|---------------------------------|-------|-----|------|--------|------|
| Black Annealed - PC 5030 | | | | | |
| TY164 | 28170 | 20 | 20 | 71.10# | Ea |
| Galvanized - PC 5035 | | | | | |
| VTYG | 28180 | 20 | 20 | 68.35# | Ea |



Tie Wire Dispenser PC 5040

The tie wire dispenser stores and dispenses tie wire.

- High Impact Plastic
- Mounts On Tool Belt

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------------------|-----|------|--------|------|
| TYD | 28175 | Tie Wire Dispenser | 1 | 6 | 1.10# | Ea |



Beam Clamps - Steel PC 5260, 5265




- Zinc Plated Steel or High Strength Malleable Iron
- Case Hardened Steel Bolt
- Tapped Threads Back & Bottom

Beam Clamps when secured to an I-beam, girder or other structural member, provide a mounting base for the attachment of conduit hangers, either directly or by using threaded rod.

| CAT NO | UPC | SIZE | TYPE | STD | MSTR | WT/STD | UNIT |
|------------------------|-------|--------|-------|-----|------|--------|------|
| Steel - PC 5260 | | | | | | | |
| BK14 | 10090 | 1/4-20 | Steel | 50 | 250 | 6.03# | C |
| BK38 | 10095 | 3/8-16 | Steel | 25 | 100 | 6.62# | C |

| | | | | | | | |
|----------------------------|-------|--------|-----------|----|-----|--------|---|
| Malleable - PC 5265 | | | | | | | |
| BK14M | 10092 | 1/4-20 | Malleable | 50 | 250 | 11.44# | C |
| BK38M | 10097 | 3/8-16 | Malleable | 25 | 100 | 18.22# | C |
| BK50M | 10099 | 1/2-13 | Malleable | 10 | 50 | 12.96# | C |



| | A | B | C | D | E* |
|--------|------|-------|---------------|------|--------|
| BK-14 | 1.39 | .672 | 1/4 x 1" | .695 | 1/4-20 |
| BK-14M | 1.39 | .750 | 5/16 x 1" | .625 | 1/4-20 |
| BK-38 | 1.95 | .781 | 5/16 x 1 3/8" | .979 | 3/8-16 |
| BK-38M | 1.75 | .875 | 3/8 x 1 1/4" | .625 | 3/8-16 |
| BK-50M | 2.47 | 1.109 | 3/8 x 1 1/2" | .812 | 1/2-13 |

* Bottom & Back

Floor Flanges PC 5270

- High Strength Malleable Iron
- Zinc Plated

Floor flanges are secured to floors or walls and threaded conduit is then inserted as a post or divider.



| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| FF50 | 60350 | 1/2" | 25 | 25 | 6.79# | C |
| FF75 | 60351 | 3/4" | 25 | 25 | 7.64# | C |
| FF100 | 60352 | 1" | 10 | 10 | 4.50# | C |
| FF125 | 60353 | 1-1/4" | 5 | 5 | 3.15# | C |
| FF150 | 60354 | 1-1/2" | 5 | 5 | 3.85# | C |
| FF200 | 60355 | 2" | 5 | 5 | 6.46# | C |

Switch Box Supports PC 5290

- Quick Installation
- Supports Box, No Stud Needed
- Prevents Box Pull Out
- Galvanized Steel

Switch box supports are used in pairs in old work. The tongues are bent over the lip of the box and the bar is inserted into the opening to prevent the box from falling back out of the opening. The ears of the box keep it from falling into the opening.



| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------------|----------|----------|--------|----------|
| SBS165 | 59850 | Galvanized Box Support | 100 Pair | 500 Pair | 5.30# | 100 Pair |

Ceiling Cover Plate PC 5280

- Steel
- White
- Adjustable Strap For 3" or 4" Boxes

Ceiling cover plates, 5 1/4" canopy with adjustable strap and screws for 3" or 4" outlet boxes. White color blends with most installations. Temporary or permanent.



| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----------------------------|-----|------|--------|------|
| CP5 | 27545 | 5-1/4" | White Universal Cover Plate | 10 | 50 | 7.11# | C |



Reducing Bushings PC 5430

Reducing bushings are used with rigid /IMC conduit to reduce the size of a threaded opening to accept a smaller size conduit.

- Zinc Plated Steel
- High Strength Malleable Iron

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------|-----|------|--------|------|
| R351 | 30500 | 1/2 x 3/8" | 100 | 500 | 2.40# | C |
| R352 | 30505 | 3/4 x 1/2" | 100 | 500 | 5.00# | C |
| R353 | 30510 | 1 x 1/2" | 50 | 250 | 5.88# | C |
| R354 | 30515 | 1 x 3/4" | 50 | 250 | 6.77# | C |
| R355 | 30520 | 1-1/4 x 1/2" | 25 | 125 | 3.44# | C |
| R356 | 30525 | 1-1/4 x 3/4" | 25 | 125 | 5.33# | C |
| R357 | 30530 | 1-1/4 x 1" | 25 | 125 | 3.70# | C |
| R358 | 30535 | 1-1/2 x 1/2" | 25 | 125 | 10.06# | C |
| R359 | 30540 | 1-1/2 x 3/4" | 25 | 125 | 8.25# | C |
| R360 | 30545 | 1-1/2 x 1" | 25 | 125 | 6.45# | C |
| R361 | 30550 | 1-1/2 x 1-1/4" | 25 | 125 | 2.78# | C |
| R362 | 30555 | 2 x 1/2" | 10 | 50 | 8.18# | C |
| R363 | 30560 | 2 x 3/4" | 10 | 50 | 7.34# | C |
| R364 | 30565 | 2 x 1" | 10 | 50 | 6.50# | C |
| R365 | 30570 | 2 x 1-1/4" | 10 | 50 | 4.81# | C |
| R366 | 30575 | 2 x 1-1/2" | 10 | 50 | 3.27# | C |
| R367 | 30576 | 2-1/2 x 2" | 1 | 10 | 0.60# | C |
| R368 | 30577 | 3 x 2" | 1 | 10 | 1.04# | C |
| R369 | 30578 | 3 x 2-1/2" | 1 | 10 | 1.22# | C |
| R370 | 30579 | 3-1/2 x 2" | 1 | 10 | 1.39# | C |
| R371 | 30580 | 3-1/2 x 2-1/2" | 1 | 10 | 1.48# | C |
| R372 | 30581 | 3-1/2 x 3" | 1 | 10 | 1.17# | C |
| R373 | 30582 | 4 x 2" | 1 | 10 | 3.62# | C |
| R374 | 30583 | 4 x 2-1/2" | 1 | 10 | 1.95# | C |
| R375 | 30584 | 4 x 3" | 1 | 10 | 1.64# | C |
| R376 | 30585 | 4 x 3-1/2" | 1 | 10 | 1.28# | C |



Plastic Bushings PC 5670

Plastic bushings are threaded onto the end of conduit and are used to protect wires coming through the conduit.

- UL Listed
- Thermoplastic
- 105° C
- Fits Rigid Conduit

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| PB50 | 10100 | 1/2" | 100 | 1000 | 0.49# | C |
| PB75 | 10105 | 3/4" | 100 | 1000 | 0.64# | C |
| PB100 | 10110 | 1" | 50 | 500 | 0.58# | C |
| PB125 | 10115 | 1-1/4" | 25 | 250 | 0.44# | C |
| PB150 | 10120 | 1-1/2" | 25 | 250 | 0.50# | C |
| PB200 | 10125 | 2" | 25 | 250 | 0.74# | C |
| PB250 | 10130 | 2-1/2" | 25 | 100 | 1.32# | C |
| PB300 | 10135 | 3" | 25 | 100 | 1.55# | C |
| PB350 | 10140 | 3-1/2" | 10 | 50 | 0.85# | C |
| PB400 | 10145 | 4" | 10 | 20 | 0.98# | C |
| PB500 | 10150 | 5" | 10 | 10 | 2.93# | C |
| PB600 | 10155 | 6" | 10 | 10 | 3.85# | C |



EMT Bushings PC 5675

EMT Insulating Bushings protect cables from abrasion. Use where nonmetallic low voltage cabling is installed in EMT.

- Stay-In-Place Design
- Engineered Plastic
- Color: White

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|---------|-------|--------|-----|------|--------|------|
| EMTB50 | 81613 | 1/2" | 100 | 1000 | 0.40# | C |
| EMTB75 | 81614 | 3/4" | 50 | 500 | 0.25# | C |
| EMTB100 | 81615 | 1" | 25 | 250 | 0.23# | C |
| EMTB125 | 81616 | 1-1/4" | 25 | 250 | 0.27# | C |
| EMTB150 | 81617 | 1-1/2" | 25 | 100 | 0.35# | C |
| EMTB200 | 81618 | 2" | 25 | 100 | 0.55# | C |
| EMTB250 | 81619 | 2-1/2" | 25 | 100 | 1.40# | C |
| EMTB300 | 81620 | 3" | 25 | 100 | 1.30# | C |
| EMTB350 | 81621 | 3-1/2" | 25 | 100 | 2.10# | C |
| EMTB400 | 81622 | 4" | 25 | 100 | 3.20# | C |

Nylon KO Bushings PC 6100



- 105° C
- Snap In
- Reusable

Nylon KO bushings are snapped into punched holes in panels to protect wires from the rough edges.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| 1210D | 12100 | 1/2" | 100 | 1000 | 0.45# | C |
| 1211D | 12110 | 3/4" | 100 | 1000 | 0.66# | C |
| 1212D | 12120 | 1" | 100 | 1000 | 0.99# | C |
| 1213D | 12130 | 1-1/4" | 50 | 500 | 0.70# | C |
| 1214D | 12140 | 1-1/2" | 25 | 250 | 0.46# | C |
| 1215D | 12150 | 2" | 25 | 250 | 0.93# | C |
| 1216D | 12160 | 2-1/2" | 25 | 250 | 1.20# | C |

Anti-Short Bushings PC 5680



- Plastic
- Fits Armored Cable
- Prevents Shorts

Anti-Short bushings are used to protect wire insulation from the jagged or sharp cut edges of BX or flex. Priced per 100 pieces.

| CAT NO | UPC | FLEX | CABLE SIZE | PKG | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------|-------------------------|-----|------|------|--------|------|
| 0 | 11600 | 5/16" | 14/2, 14/3, 12/2 | 100 | 1000 | 1000 | 0.75# | C |
| 1 | 11601 | 3/8" | 14/4, 6/1,4/1, 12/3 | 100 | 1000 | 1000 | 0.30# | C |
| 2 | 11602 | 7/16" | 12/4, 10/2, 10/3, 2/1 | 50 | 500 | 500 | 0.35# | C |
| 3 | 11603 | 1/2" | 10/4, 8/2, 8/3, 1/1 | 50 | 500 | 500 | 0.40# | C |
| 4 | 11604 | 3/4" | 8/4, 6/2, 6/3, 4/2, 4/3 | 50 | 500 | 500 | 0.40# | C |

K.O. Seals PC 5440



- Snap In
- Steel
- Zinc Plated

Snap in K.O. seals are used to seal up holes punched in panels or knockouts from outlet boxes. They are held in place by spring tension. Available in sizes from 1/2" thru 2".

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| KO50 | 16000 | 1/2" | 100 | 1000 | 1.44# | C |
| KO75 | 16010 | 3/4" | 100 | 1000 | 1.62# | C |
| KO100 | 16020 | 1" | 100 | 500 | 2.10# | C |
| KO125 | 16030 | 1-1/4" | 50 | 100 | 1.45# | C |
| KO150 | 16040 | 1-1/2" | 50 | 50 | 2.14# | C |
| KO200 | 16050 | 2" | 25 | 25 | 1.44# | C |

Three Piece K.O. Seals PC 5450



- Assembled*
- Includes Screw and Threaded Strap
- Steel
- Zinc Plated

Three piece K.O. seals are used to seal up holes punched in panels or knockouts from outlet boxes. They are held in place by a screw inserted through the seal into a threaded strap on the opposite side of the opening. Available in sizes from 1/2" thru 6". Three piece K.O. seals are embossed to centralize in knockout. Installs from the inside or outside of any box without rearranging wires. One screw secures unit. Size is stamped into seal.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| D10S* | 10240 | 1/2" | 100 | 100 | 2.62# | C |
| D20S* | 10242 | 3/4" | 50 | 50 | 1.73# | C |
| D30S* | 10244 | 1" | 25 | 25 | 1.33# | C |
| D40S | 10246 | 1-1/4" | 25 | 25 | 1.74# | C |
| D50S | 10248 | 1-1/2" | 10 | 10 | 1.03# | C |
| D60S | 10250 | 2" | 10 | 10 | 1.46# | C |
| D70S | 10252 | 2-1/2" | 10 | 10 | 2.16# | C |
| D80S | 10254 | 3" | 10 | 10 | 3.11# | C |
| D90S | 10256 | 3-1/2" | 10 | 10 | 3.97# | C |
| D100S | 10258 | 4" | 10 | 10 | 5.81# | C |
| D110S | 10260 | 4-1/2" | 10 | 10 | 10.45# | C |
| D120S | 10262 | 5" | 10 | 10 | 13.33# | C |
| D130S | 10264 | 6" | 10 | 10 | 14.10# | C |



Reducing Washers PC 5455

Reducing washers are used to reduce the size of a knockout on a sheet metal box, enclosure or cabinet.

- Steel
- Zinc Plated
- Stamped With Size

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------|-----|------|--------|------|
| RW21 | 30103 | 3/4 x 1/2" | 100 | 1000 | 0.98# | C |
| RW31 | 30106 | 1 x 1/2" | 100 | 1000 | 1.90# | C |
| RW32 | 30109 | 1 x 3/4" | 100 | 1000 | 1.37# | C |
| RW41 | 30112 | 1-1/4 x 1/2" | 50 | 500 | 1.33# | C |
| RW42 | 30115 | 1-1/4 x 3/4" | 50 | 500 | 1.24# | C |
| RW43 | 30118 | 1-1/4 x 1" | 50 | 500 | 0.95# | C |
| RW51 | 30121 | 1-1/2 x 1/2" | 50 | 500 | 1.93# | C |
| RW52 | 30124 | 1-1/2 x 3/4" | 50 | 500 | 1.78# | C |
| RW53 | 30127 | 1-1/2 x 1" | 50 | 500 | 1.54# | C |
| RW54 | 30130 | 1-1/2 x 1-1/4" | 50 | 500 | 1.15# | C |
| RW61 | 30133 | 2 x 1/2" | 25 | 250 | 1.56# | C |
| RW62 | 30136 | 2 x 3/4" | 25 | 250 | 1.49# | C |
| RW63 | 30139 | 2 x 1" | 25 | 250 | 1.37# | C |
| RW64 | 30142 | 2 x 1-1/4" | 25 | 250 | 1.17# | C |
| RW65 | 30145 | 2 x 1-1/2" | 25 | 250 | 0.99# | C |
| RW71 | 30148 | 2-1/2 x 1/2" | 25 | 50 | 2.49# | C |
| RW72 | 30151 | 2-1/2 x 3/4" | 25 | 50 | 2.37# | C |
| RW73 | 30154 | 2-1/2 x 1" | 25 | 50 | 2.26# | C |
| RW74 | 30157 | 2-1/2 x 1-1/4" | 25 | 50 | 2.04# | C |
| RW75 | 30160 | 2-1/2 x 1-1/2" | 25 | 50 | 1.82# | C |
| RW76 | 30163 | 2-1/2 x 2" | 25 | 50 | 1.37# | C |
| RW81 | 30166 | 3 x 1/2" | 10 | 30 | 1.45# | C |
| RW82 | 30169 | 3 x 3/4" | 10 | 30 | 1.43# | C |
| RW83 | 30172 | 3 x 1" | 10 | 30 | 1.32# | C |
| RW84 | 30175 | 3 x 1-1/4" | 10 | 30 | 1.28# | C |
| RW85 | 30178 | 3 x 1-1/2" | 10 | 30 | 1.11# | C |
| RW86 | 30181 | 3 x 2" | 10 | 30 | 1.01# | C |
| RW87 | 30184 | 3 x 2-1/2" | 10 | 30 | 0.78# | C |
| RW91 | 30170 | 3-1/2 x 1/2" | 10 | 10 | 2.08# | C |
| RW92 | 30171 | 3-1/2 x 3/4" | 10 | 10 | 2.74# | C |
| RW93 | 30173 | 3-1/2 x 1" | 10 | 10 | 2.57# | C |
| RW94 | 30185 | 3-1/2 x 1-1/4" | 10 | 10 | 2.70# | C |
| RW95 | 30186 | 3-1/2 x 1-1/2" | 10 | 10 | 2.29# | C |
| RW96 | 30188 | 3-1/2 x 2" | 10 | 10 | 2.04# | C |
| RW97 | 30190 | 3-1/2 x 2-1/2" | 10 | 10 | 2.33# | C |
| RW98 | 30192 | 3-1/2 x 3" | 10 | 10 | 1.19# | C |
| RW101 | 30189 | 4 x 1/2" | 10 | 10 | 3.47# | C |
| RW102 | 30191 | 4 x 3/4" | 10 | 10 | 3.40# | C |
| RW103 | 30193 | 4 x 1" | 10 | 10 | 3.32# | C |
| RW104 | 30195 | 4 x 1-1/4" | 10 | 10 | 3.42# | C |
| RW105 | 30197 | 4 x 1-1/2" | 10 | 10 | 3.06# | C |
| RW106 | 30194 | 4 x 2" | 10 | 10 | 2.70# | C |
| RW107 | 30196 | 4 x 2-1/2" | 10 | 10 | 2.35# | C |
| RW108 | 30198 | 4 x 3" | 10 | 10 | 1.84# | C |
| RW109 | 30200 | 4 x 3-1/2" | 10 | 10 | 1.39# | C |





- UL Listed
- Allow Cables To Pull Easily, Prevent Hang-ups
- Snaps Securely Into Metal Studs
- 24 to 12 Gauge

Universal Plastic Stud Bushings are used to protect wires from abrasion in metal studs. Due to their molded high-strength, non-conductive polypropylene construction, the USB allows for the installation of multiple cables through a single opening while providing a smooth wire pulling surface. Dottie's USB's can be used with power cabling, low voltage datacom, video and voice cables. Fits all standard pre-punched and field punched holes.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|-----|------|--------|------|
| USB | 81031 | 3/8" | 25 | 500 | 0.34# | C |

Locknuts PC 5660



- Steel
- Zinc Plated

Locknuts are used to secure conduit by running or threading conduit into a box or panel and attaching the locknut and cinching up until tight.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| LN38* | 12300 | 3/8" | 100 | 1000 | 3.02# | C |
| LN50 | 12301 | 1/2" | 100 | 1000 | 1.34# | C |
| LN75 | 12302 | 3/4" | 100 | 1000 | 2.05# | C |
| LN100 | 12303 | 1" | 100 | 500 | 2.78# | C |
| LN125 | 12304 | 1-1/4" | 50 | 250 | 2.08# | C |
| LN150 | 12305 | 1-1/2" | 50 | 250 | 2.95# | C |
| LN200 | 12306 | 2" | 50 | 100 | 3.22# | C |
| LN250 | 12307 | 2-1/2" | 25 | 100 | 3.30# | C |
| LN300 | 12308 | 3" | 25 | 100 | 3.94# | C |
| LN350 | 12309 | 3-1/2" | 25 | 50 | 5.00# | C |
| LN400 | 12310 | 4" | 25 | 50 | 6.06# | C |
| LN500 | 12311 | 5" | 10 | 10 | 8.95# | C |
| LN600 | 12312 | 6" | 10 | 10 | 9.90# | C |

* LN38 Square Fixture Locknut

Sealing Locknuts PC 5665 Rated: NEMA FB1



- UL Listed
- Steel Locknut
- PVC Sealing Ring
- Zinc Plated

Used wherever a liquid tight application is needed when fastening threaded conduit to an unthreaded opening in a box or enclosure.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| LNS50 | 12330 | 1/2" | 100 | 1000 | 1.34# | C |
| LNS75 | 12331 | 3/4" | 100 | 1000 | 2.05# | C |
| LNS100 | 12332 | 1" | 100 | 500 | 2.78# | C |
| LNS125 | 12333 | 1-1/4" | 50 | 250 | 2.08# | C |
| LNS150 | 12334 | 1-1/2" | 50 | 250 | 2.95# | C |
| LNS200 | 12336 | 2" | 50 | 100 | 3.22# | C |
| LNS250 | 12338 | 2-1/2" | 25 | 100 | 3.30# | C |
| LNS300 | 12340 | 3" | 25 | 100 | 3.94# | C |
| LNS350 | 12342 | 3-1/2" | 25 | 50 | 5.00# | C |
| LNS400 | 12344 | 4" | 25 | 50 | 6.06# | C |

FITTINGS & STAMPINGS > UNIVERSAL PLASTIC STUD BUSHING > LOCKNUTS > SEALING LOCKNUTS



Non Metallic Cable Connectors PC 6081

DRC 50 & 75 are smaller and easily installed in confined and tight areas. No tools required. Snap in and you're done. Easily removed from knockouts and easy removal of Romex from connectors. A labor saving connector with 60 pound test pull!

- UL/CSA Listed
- Thermoplastic
- Easily Installed / No Tools Required
- 60 Pound Test Pull

| CAT NO | UPC | CABLE SIZE | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|------|-----|------|--------|------|
| DRC50 | 50507 | Single Cable 14/2 - 10/3 Two Cables 14/2, 12/2, 14/3 | 1/2" | 100 | 4000 | 1.06# | C |
| DRC75 | 50508 | Single Cable 8/3 - 6/3 Two Cables 14/2 - 8/2 | 3/4" | 50 | 2400 | 0.72# | C |



Non Metallic Cable Connectors PC 6070

The NMC50 connector for Romex is a snap to install. Molded in a one piece plastic construction, this push in design has a captive locking wedge. The cable will be securely retained and no locknut is required. They provide excellent strain relief and are designed to accommodate 14/2 minimum to 10/3 maximum cables, and one or more .300 to .600 diameter cords.

- UL Listed
- One or Two Cables
- Installs Quickly
- Excellent Strain Relief
- All Plastic Design; Resists Corrosion

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|-----|------|--------|------|
| NMC50 | 10160 | 1/2" | 100 | 1000 | 1.14# | C |



Cat-A-Pillar Wiring Device Spacer PC 6230

Cat-A-Pillar is a non conductive, low density polyethylene spacer strip consisting of 8 foldable segments. Each segment allows for 1/8" of spacing. It's easy to calculate. Determine the depth of the box to the surface and tear or cut the number of 1/8" segments needed. Snap over screw (no need to remove) and rotate a Cat-A-Pillar so that the slot faces away from the device. Installs quickly on single or multi-gang boxes. Reusable and can be used as a shim or a plastic washer to straighten crooked devices.

- Low Density Polyethylene
- Non Conductive
- Reusable
- Sold Per Ea Pack

| CAT NO | UPC | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----|------|--------|---------|
| CA25 | 16170 | 25 | 250 | 0.18# | Ea Pack |
| CA100 | 16171 | 100 | 1000 | 0.65# | Ea Pack |

CAT-A-PILLARS are not intended to be used in lieu of standard means of support under normal circumstances or when in conflict with governing electrical codes.



Wall Plate Insulation Gaskets PC 6240

Energy saving gaskets prevent the loss of heat and cold through outlets and switches located on outside walls. Constructed of UL Rated #94HFI listed cross link close cell polyethylene insulating foam. New one piece design fits: regular toggle or duplex receptacle and Decora Type Toggle and duplex receptacles.

- Polyethylene Insulating Foam
- Flame Retardant
- Energy Saving
- One Size Fits All
- Sold Per Ea Pack

| CAT NO | UPC | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----|------|--------|---------|
| WPI25 | 16180 | 25 | 500 | 0.05# | Ea Pack |
| WPI100 | 16182 | 100 | 1000 | 0.40# | Ea Pack |



Strain Relief Connectors - Nylon PC 5510



- UL Listed
- Liquid Tight to 70PSI
- Excellent Pullout Resistance
- Extended Cable Range

Nylon strain relief connectors grip portable cord to relieve strain on cord and prevent wires from being pulled out of connecting screws.
Note: Wire ranges vary from the steel strain relief connectors.
Locknut not supplied.

| CAT NO | UPC | SIZE | CABLE RANGE | STD | MSTR | WT/STD | UNIT |
|---------|-------|------|--------------|-----|------|--------|------|
| NSR38L | 36020 | 3/8" | .197 to .394 | 25 | 100 | 0.71# | C |
| NSR12L | 36024 | 1/2" | .394 to .551 | 25 | 100 | 0.96# | C |
| NSR34L | 36028 | 3/4" | .354 to .551 | 10 | 50 | 0.62# | C |
| NSR100L | 36032 | 1" | .709 to .984 | 10 | 50 | 1.02# | C |

Strain Relief Connectors - Steel PC 5520



- UL Listed
- Excellent Pullout Resistance
- Extended Cable Range
- Zinc Plated Steel

Steel strain relief connectors grip portable cord to relieve strain on cord and prevent wires from being pulled out of connecting screws.
Note: Wire ranges vary from the nylon strain relief connectors.

| CAT NO | UPC | SIZE | CABLE RANGE | COLOR | STD | MSTR | WT/STD | UNIT |
|------------|-------|------|---------------|--------|-----|------|--------|------|
| SR50A250 | 36050 | 1/2" | .150 to .250 | Red | 25 | 125 | 2.61# | C |
| SR50A350 | 36052 | 1/2" | .250 to .350 | White | 25 | 125 | 2.58# | C |
| SR50A450 | 36054 | 1/2" | .350 to .450 | Blue | 25 | 125 | 2.55# | C |
| SR50A560 | 36056 | 1/2" | .450 to .560 | Green | 25 | 125 | 2.50# | C |
| SR50A650 | 36058 | 1/2" | .550 to .650 | Brown | 25 | 125 | 2.43# | C |
| SR75A250 | 36060 | 3/4" | .150 to .250 | Red | 10 | 50 | 1.67# | C |
| SR75A350 | 36062 | 3/4" | .250 to .350 | White | 10 | 50 | 1.71# | C |
| SR75A450 | 36064 | 3/4" | .350 to .450 | Blue | 10 | 50 | 1.66# | C |
| SR75A560 | 36066 | 3/4" | .450 to .560 | Green | 10 | 50 | 1.62# | C |
| SR75A650 | 36068 | 3/4" | .550 to .650 | Brown | 10 | 50 | 1.57# | C |
| SR75B750 | 36070 | 3/4" | .650 to .750 | Yellow | 10 | 50 | 1.44# | C |
| SR75B850 | 36072 | 3/4" | .750 to .850 | Purple | 10 | 50 | 1.45# | C |
| SR100B750 | 36074 | 1" | .650 to .750 | Yellow | 5 | 25 | 1.44# | C |
| SR100B850 | 36076 | 1" | .750 to .850 | Purple | 5 | 25 | 1.44# | C |
| SR100C950 | 36078 | 1" | .850 to .950 | Gray | 5 | 25 | 1.43# | C |
| SR100C1050 | 36080 | 1" | .950 to 1.050 | Black | 5 | 25 | 1.41# | C |

Steel Combo Couplings PC 5470



- UL Listed
- Steel
- Zinc Plated

Steel combo couplings are used to connect liquid tight conduit to E.M.T.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------------------|-----|------|--------|------|
| CF1 | 40750 | 1/2" Flex to E.M.T. | 25 | 125 | 3.39# | C |
| CF2 | 40755 | 3/4" Flex to E.M.T. | 10 | 50 | 2.16# | C |
| CF3 | 40760 | 1" Flex to E.M.T. | 10 | 20 | 3.49# | C |

FITTINGS & STAMPINGS > STRAIN RELIEF CONNECTORS > STEEL COMBO COUPLINGS



Die Cast Liquid Tite Connectors PC 5460

Die cast liquid tite connectors are used to connect metallic & non-metallic liquid tite conduit into an enclosure.

- UL Listed
- Zinc Die Cast
- Straight & 90°
- Insulated & Non Insulated

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|----------|-------|-------------------------|-----|------|--------|------|
| LT38 | 11000 | 3/8" | 25 | 250 | 3.22# | C |
| LT50 | 11005 | 1/2" | 25 | 250 | 3.65# | C |
| LT75 | 11010 | 3/4" | 10 | 100 | 2.19# | C |
| LT100 | 11015 | Straight 1" | 5 | 50 | 1.74# | C |
| LT125 | 11020 | 1-1/4" | 5 | 50 | 2.69# | C |
| LT150 | 11025 | 1-1/2" | 2 | 20 | 1.26# | C |
| LT200 | 11030 | 2" | 2 | 20 | 1.60# | C |
| LT9038 | 11200 | 3/8" | 10 | 100 | 2.17# | C |
| LT9050 | 11205 | 1/2" | 10 | 100 | 2.97# | C |
| LT9075 | 11210 | 3/4" | 10 | 100 | 2.73# | C |
| LT90100 | 11215 | 90° 1" | 5 | 50 | 2.26# | C |
| LT90125 | 11220 | 1-1/4" | 5 | 50 | 3.92# | C |
| LT90150 | 11225 | 1-1/2" | 2 | 20 | 2.12# | C |
| LT90200 | 11230 | 2" | 2 | 20 | 2.62# | C |
| LT38I | 11100 | 3/8" | 25 | 250 | 3.86# | C |
| LT50I | 11105 | 1/2" | 25 | 250 | 3.32# | C |
| LT75I | 11110 | 3/4" | 10 | 100 | 2.37# | C |
| LT100I | 11115 | 1" | 5 | 50 | 1.84# | C |
| LT125I | 11120 | Straight 1-1/4" | 5 | 50 | 2.66# | C |
| LT150I | 11125 | Insulated 1-1/2" | 2 | 20 | 1.24# | C |
| LT200I | 11130 | 2" | 2 | 20 | 1.64# | C |
| LT250I | 11135 | 2-1/2" | 1 | 1 | 1.74# | C |
| LT300I | 11140 | 3" | 1 | 1 | 2.68# | C |
| LT350I | 11145 | 3-1/2" | 1 | 1 | 3.45# | C |
| LT400I | 11150 | 4" | 1 | 1 | 3.87# | C |
| LT9038I | 11300 | 3/8" | 10 | 100 | 2.28# | C |
| LT9050I | 11305 | 1/2" | 10 | 100 | 1.98# | C |
| LT9075I | 11310 | 3/4" | 10 | 100 | 2.77# | C |
| LT90100I | 11315 | 1" | 5 | 50 | 2.26# | C |
| LT90125I | 11320 | 90° 1-1/4" | 5 | 50 | 4.09# | C |
| LT90150I | 11325 | Insulated 1-1/2" | 2 | 20 | 2.06# | C |
| LT90200I | 11330 | 2" | 2 | 20 | 2.81# | C |
| LT90250I | 11235 | 2-1/2" | 1 | 1 | 3.43# | C |
| LT90300I | 11240 | 3" | 1 | 1 | 4.72# | C |
| LT90350I | 11245 | 3-1/2" | 1 | 1 | 7.33# | C |
| LT90400I | 11250 | 4" | 1 | 1 | 8.03# | C |



PVC Liquid Tite Connectors PC 5490

PVC liquid tite connectors are used to connect non metallic liquid tite conduit & flexible non-metallic tubing to enclosures. UV rated plastic.

- UL Listed
- PVC With Polypropylene Sealing Ring
- Straight & 90°

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|----------|-------|--------------------|-----|------|--------|------|
| NLT38 | 36000 | 3/8" | 25 | 100 | 1.92# | C |
| NLT50 | 36002 | 1/2" | 25 | 100 | 1.34# | C |
| NLT75 | 36004 | 3/4" | 25 | 100 | 2.38# | C |
| NLT100 | 36006 | Straight 1" | 25 | 100 | 2.68# | C |
| NLT125 | 36007 | 1-1/4" | 5 | 25 | 1.40# | C |
| NLT150 | 36009 | 1-1/2" | 5 | 25 | 1.42# | C |
| NLT200 | 36011 | 2" | 5 | 25 | 2.13# | C |
| NLT9038 | 36008 | 3/8" | 10 | 50 | 0.89# | C |
| NLT9050 | 36010 | 1/2" | 10 | 50 | 0.76# | C |
| NLT9075 | 36012 | 3/4" | 10 | 50 | 1.07# | C |
| NLT90100 | 36014 | 90° 1" | 5 | 25 | 1.00# | C |
| NLT90125 | 36013 | 1-1/4" | 5 | 25 | 1.72# | C |
| NLT90150 | 36015 | 1-1/2" | 5 | 25 | 2.43# | C |
| NLT90200 | 36016 | 2" | 5 | 25 | 3.41# | C |

Steel Liquid Tite Connectors PC 5480

- UL Listed
- Zinc Plated Steel
- Malleable Iron

- Straight, 45° & 90°
- Insulated & Non Insulated

Steel liquid tite connectors are used to connect liquid tite conduit into an enclosure.



FITTINGS & STAMPINGS > STEEL LIQUID TITE CONNECTORS

| CAT NO | UPC | | SIZE | STD | MSTR | WT/STD | UNIT |
|----------|-------|---------------------------|--------|-----|------|--------|------|
| SL38 | 66701 | | 3/8" | 25 | 125 | 2.88# | C |
| SL50 | 66700 | | 1/2" | 25 | 125 | 3.22# | C |
| SL75 | 66702 | Straight | 3/4" | 10 | 50 | 1.80# | C |
| SL100 | 66704 | | 1" | 5 | 25 | 1.49# | C |
| SL125 | 66736 | | 1-1/4" | 5 | 25 | 2.35# | C |
| SL150 | 66738 | | 1-1/2" | 5 | 5 | 3.01# | C |
| SL200 | 66740 | | 2" | 5 | 5 | 4.25# | C |
| SL4538 | 66705 | | 3/8" | 10 | 50 | 1.99# | C |
| SL4550 | 66706 | | 1/2" | 10 | 50 | 2.19# | C |
| SL4575 | 66708 | 45° | 3/4" | 10 | 50 | 3.06# | C |
| SL45100 | 66710 | | 1" | 5 | 25 | 2.61# | C |
| SL45125 | 66711 | | 1-1/4" | 5 | 5 | 3.43# | C |
| SL45150 | 66713 | | 1-1/2" | 2 | 2 | 2.04# | C |
| SL45200 | 66715 | | 2" | 2 | 2 | 2.92# | C |
| SL9038 | 66709 | | 3/8" | 10 | 50 | 2.22# | C |
| SL9050 | 66712 | | 1/2" | 10 | 50 | 2.35# | C |
| SL9075 | 66714 | 90° | 3/4" | 10 | 50 | 3.54# | C |
| SL90100 | 66716 | | 1" | 5 | 25 | 2.93# | C |
| SL90125 | 66742 | | 1-1/4" | 5 | 5 | 4.10# | C |
| SL90150 | 66743 | | 1-1/2" | 2 | 2 | 2.36# | C |
| SL90200 | 66745 | | 2" | 2 | 2 | 3.48# | C |
| SL38I | 66717 | | 3/8" | 25 | 125 | 2.93# | C |
| SL50I | 66718 | | 1/2" | 25 | 125 | 3.09# | C |
| SL75I | 66720 | Straight Insulated | 3/4" | 10 | 50 | 2.08# | C |
| SL100I | 66722 | | 1" | 5 | 25 | 1.47# | C |
| SL125I | 66744 | | 1-1/4" | 5 | 25 | 2.33# | C |
| SL150I | 66746 | | 1-1/2" | 5 | 5 | 2.93# | C |
| SL200I | 66748 | | 2" | 5 | 5 | 4.25# | C |
| SL250I | 81623 | | 2-1/2" | 1 | 1 | 2.60# | C |
| SL300I | 81624 | | 3" | 1 | 1 | 3.60# | C |
| SL350I | 81625 | | 3-1/2" | 1 | 1 | 4.45# | C |
| SL400I | 81626 | | 4" | 1 | 1 | 5.20# | C |
| SL4538I | 66723 | | 3/8" | 10 | 50 | 1.99# | C |
| SL4550I | 66724 | | 1/2" | 10 | 50 | 2.23# | C |
| SL4575I | 66726 | 45° Insulated | 3/4" | 10 | 50 | 3.08# | C |
| SL45100I | 66728 | | 1" | 5 | 25 | 2.67# | C |
| SL45125I | 66729 | | 1-1/4" | 5 | 5 | 3.27# | C |
| SL45150I | 66731 | | 1-1/2" | 2 | 2 | 1.79# | C |
| SL45200I | 66733 | | 2" | 2 | 2 | 2.92# | C |
| SL45250I | 81627 | | 2-1/2" | 1 | 1 | 4.78# | C |
| SL45300I | 81628 | | 3" | 1 | 1 | 7.75# | C |
| SL45350I | 81629 | | 3-1/2" | 1 | 1 | 8.80# | C |
| SL45400I | 81630 | | 4" | 1 | 1 | 10.00# | C |
| SL9038I | 66735 | | 3/8" | 10 | 50 | 2.37# | C |
| SL9050I | 66730 | | 1/2" | 10 | 50 | 2.37# | C |
| SL9075I | 66732 | 90° Insulated | 3/4" | 10 | 50 | 3.62# | C |
| SL90100I | 66734 | | 1" | 5 | 25 | 3.37# | C |
| SL90125I | 66749 | | 1-1/4" | 5 | 5 | 4.42# | C |
| SL90150I | 66747 | | 1-1/2" | 2 | 2 | 2.00# | C |
| SL90200I | 66751 | | 2" | 2 | 2 | 3.65# | C |
| SL90250I | 81631 | | 2-1/2" | 1 | 1 | 6.25# | C |
| SL90300I | 81632 | | 3" | 1 | 1 | 9.00# | C |
| SL90350I | 81633 | | 3-1/2" | 1 | 1 | 10.00# | C |
| SL90400I | 81634 | | 4" | 1 | 1 | 15.00# | C |

NEW

NEW

NEW



Weathertight Hubs PC 5462

Weathertight hubs are used to terminate rigid conduit or IMC into an enclosure.

- UL Listed
- Die Cast From High Strength Zinc Alloy
- With or Without Lugs
- Sealing Ring
- 105° Rated Throat Insulator

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| WTH50 | 60255 | 1/2" | 10 | 100 | 1.85# | C |
| WTH75 | 60256 | 3/4" | 10 | 100 | 2.62# | C |
| WTH100 | 60257 | 1" | 10 | 100 | 3.96# | C |
| WTH125 | 60258 | 1-1/4" | 5 | 50 | 2.72# | C |
| WTH150 | 60259 | 1-1/2" | 5 | 50 | 3.62# | C |
| WTH200 | 60260 | 2" | 2 | 20 | 1.94# | C |
| WTH250 | 60261 | 2-1/2" | 1 | 5 | 1.79# | C |
| WTH300 | 60262 | 3" | 1 | 5 | 2.23# | C |
| WTH350 | 60263 | 3-1/2" | 1 | 5 | 2.74# | C |
| WTH400 | 60264 | 4" | 1 | 5 | 2.80# | C |

Grounding Lug

| | | | | | | |
|----------|-------|--------|----|-----|-------|---|
| WTHGL50 | 60270 | 1/2" | 10 | 100 | 2.02# | C |
| WTHGL75 | 60271 | 3/4" | 10 | 100 | 2.78# | C |
| WTHGL100 | 60272 | 1" | 10 | 100 | 4.00# | C |
| WTHGL125 | 60273 | 1-1/4" | 5 | 50 | 2.68# | C |
| WTHGL150 | 60274 | 1-1/2" | 5 | 50 | 3.65# | C |
| WTHGL200 | 60275 | 2" | 2 | 20 | 2.02# | C |
| WTHGL250 | 60276 | 2-1/2" | 1 | 5 | 1.79# | C |
| WTHGL300 | 60277 | 3" | 1 | 5 | 2.26# | C |
| WTHGL350 | 60278 | 3-1/2" | 1 | 5 | 2.74# | C |
| WTHGL400 | 60279 | 4" | 1 | 5 | 2.80# | C |



No Thread Connectors & Couplings PC 5530

No thread connectors are used to connect rigid conduit to an enclosure. The connectors and couplings are raintite and approved for direct burial.

- UL-CSA Listed
- Zinc Plated Steel
- For Rigid Conduit
- Non Insulated & Insulated

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|-------------------|-------|--------|-----|------|--------|------|
| Connectors | | | | | | |
| NT50 | 66750 | 1/2" | 25 | 125 | 2.95# | C |
| NT75 | 66752 | 3/4" | 25 | 125 | 4.49# | C |
| NT100 | 66754 | 1" | 10 | 50 | 3.06# | C |
| NT125 | 66756 | 1-1/4" | 10 | 50 | 4.22# | C |
| NT150 | 66758 | 1-1/2" | 5 | 25 | 2.83# | C |
| NT200 | 66780 | 2" | 5 | 25 | 3.54# | C |

| | | | | | | |
|--------|-------|--------|----|-----|--------|---|
| NT50I | 66760 | 1/2" | 25 | 125 | 3.09# | C |
| NT75I | 66762 | 3/4" | 25 | 125 | 4.54# | C |
| NT100I | 66764 | 1" | 10 | 50 | 3.08# | C |
| NT125I | 66766 | 1-1/4" | 10 | 50 | 4.36# | C |
| NT150I | 66768 | 1-1/2" | 5 | 25 | 2.87# | C |
| NT200I | 66782 | 2" | 5 | 25 | 3.87# | C |
| NT250I | 81635 | 2-1/2" | 5 | 5 | 12.10# | C |
| NT300I | 81636 | 3" | 3 | 3 | 9.21# | C |
| NT350I | 81637 | 3-1/2" | 2 | 2 | 11.70# | C |
| NT400I | 61638 | 4" | 2 | 2 | 9.84# | C |

Couplings

| | | | | | | |
|--------|-------|--------|----|-----|--------|---|
| NTC50 | 66770 | 1/2" | 25 | 125 | 3.82# | C |
| NTC75 | 66772 | 3/4" | 25 | 125 | 6.00# | C |
| NTC100 | 66774 | 1" | 15 | 75 | 5.52# | C |
| NTC125 | 66776 | 1-1/4" | 5 | 25 | 2.72# | C |
| NTC150 | 66778 | 1-1/2" | 5 | 25 | 3.46# | C |
| NTC200 | 66784 | 2" | 5 | 25 | 4.43# | C |
| NTC250 | 81639 | 2-1/2" | 5 | 5 | 18.00# | C |
| NTC300 | 81640 | 3" | 3 | 3 | 12.15# | C |
| NTC350 | 81641 | 3-1/2" | 2 | 2 | 10.90# | C |
| NTC400 | 81642 | 4" | 2 | 2 | 12.70# | C |

NEW

NEW

Insulated Ground Bushings - Feed Through Lugs PC 5590



- Insulated Ground Bushings
- UL Listed
- Die Cast
- Feed Through
- Cu/Al (Copper/Aluminum)

Ground bushings with feed through lugs are used to terminate threaded rigid conduit or IMC to an enclosure. A 90° C Cu/Al dual rated feed through lug is provided for grounding jumper to neutral bus bar.

| CAT NO | UPC | SIZE | RANGE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-------------------|-----|------|--------|------|
| GB50 | 10300 | 1/2" | 14 Sol to 4 Str | 25 | 250 | 1.68# | C |
| GB75 | 10305 | 3/4" | 14 Sol to 4 Str | 25 | 250 | 1.99# | C |
| GB100 | 10310 | 1" | 14 Sol to 4 Str | 25 | 250 | 2.50# | C |
| GB125 | 10315 | 1-1/4" | 14 Sol to 4 Str | 25 | 250 | 2.97# | C |
| GB150 | 10320 | 1-1/2" | 14 Sol to 2 Str | 25 | 250 | 3.63# | C |
| GB200 | 10325 | 2" | 14 Sol to 2 Str | 10 | 100 | 1.81# | C |
| GB250 | 10330 | 2-1/2" | 14 Sol to 1/0 Str | 5 | 50 | 1.69# | C |
| GB300 | 10335 | 3" | 14 Sol to 1/0 Str | 5 | 50 | 2.00# | C |
| GB350 | 10340 | 3-1/2" | 14 Sol to 2/0 Str | 2 | 20 | 2.40# | C |
| GB400 | 10345 | 4" | 14 Sol to 2/0 Str | 2 | 20 | 2.78# | C |

Insulated Ground Bushings - Lay In Lugs PC 5600



- Insulated Ground Bushings
- UL Listed
- Die Cast
- Lay in Lug
- Cu/Al (Copper/Aluminum)

Ground bushings with lay-in lugs are used to terminate threaded rigid conduit or IMC to an enclosure. A 90° C Cu/Al dual rated lay in lug is provided for grounding jumper to neutral bus bar.

| CAT NO | UPC | SIZE | RANGE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-------------------|-----|------|--------|------|
| GBL50 | 10400 | 1/2" | 14 Sol to 4 Str | 25 | 250 | 1.87# | C |
| GBL75 | 10405 | 3/4" | 14 Sol to 4 Str | 25 | 250 | 2.11# | C |
| GBL100 | 10410 | 1" | 14 Sol to 4 Str | 25 | 250 | 2.48# | C |
| GBL125 | 10415 | 1-1/4" | 14 Sol to 4 Str | 25 | 250 | 3.09# | C |
| GBL150 | 10420 | 1-1/2" | 14 Sol to 2 Str | 25 | 250 | 4.12# | C |
| GBL200 | 10425 | 2" | 14 Sol to 2 Str | 10 | 100 | 1.94# | C |
| GBL250 | 10430 | 2-1/2" | 14 Sol to 1/0 Str | 5 | 50 | 1.86# | C |
| GBL300 | 10435 | 3" | 14 Sol to 1/0 Str | 5 | 50 | 2.19# | C |
| GBL350 | 10440 | 3-1/2" | 14 Sol to 1/0 Str | 2 | 20 | 1.09# | C |
| GBL400 | 10445 | 4" | 14 Sol to 1/0 Str | 2 | 20 | 1.17# | C |

Ground Rods (Copper Bonded) PC 5610



- UL Listed
- Copper Bonded
- Caution! Always Wear Eye Protection

Ground rods are available in 1/2", 5/8" and 3/4" diameters and in 8' and 10' lengths. The copper exterior is molecularly bonded to nickel sealed, high strength steel cores. Copper jacket plating thickness exceeds UL & ANSI specs of .010".

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|-----|------|--------|------|
| GR1208 | 35005 | 1/2 x 8' | 10 | 100 | 50.00# | Ea |
| GR1210 | 35010 | 1/2 x 10' | 10 | 100 | 63.00# | Ea |
| GR5808 | 35015 | 5/8 x 8' | 10 | 100 | 69.50# | Ea |
| GR5810 | 35020 | 5/8 x 10' | 10 | 100 | 86.00# | Ea |
| GR3408 | 35025 | 3/4 x 8' | 5 | 50 | 49.75# | Ea |
| GR3410 | 35030 | 3/4 x 10' | 5 | 50 | 63.75# | Ea |

Ground Rod Driver PC 6550



- No Need For Ladders Or Sledge Hammers!
- Caution! Always Wear Eye Protection

Install ground rod from ground level. Sliding action drives rod without need of hammer. Driver will not deform end of rod. Heavy duty construction provides maximum driving forces, while soft rubber ergonomic grip provides user comfort.

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------------------|-------|---|-----|------|--------|------|
| GRD58 | 24101 | 5' Driver with insert for 5/8" Ground Rod | 1 | 1 | 22.34# | Ea |
| GRD34 | 24102 | 5' Driver with insert for 3/4" Ground Rod | 1 | 1 | 22.13# | Ea |
| Insert Only | | | | | | |
| GRDI58 | 24103 | Insert only for 5/8" Ground Rod | 1 | 1 | 5.73# | Ea |
| GRDI34 | 24104 | Insert only for 3/4" Ground Rod | 1 | 1 | 5.63# | Ea |

See new products at Ihdottie.com

Dottie

C19

FITTINGS & STAMPINGS > INSULATED GROUND BUSHINGS > GROUND RODS > GROUND ROD DRIVER



Bare Ground Clamps PC 5560

Bare ground clamps are used to connect bare copper wire to water pipe, rebar, ground rod or copper water tubing for grounding. Fittings are UL listed and cast from high strength, highly conductive copper alloy with steel, brass or bronze screws.

- UL Listed
- Pressure Cast or Bronze
- Bonding or Grounding
- With Steel, Stainless Steel, Brass or Bronze Screws

| CAT NO | UPC | WIRE RANGE | DESCRIPTION | SCREW TYPE | PIPE SIZE | STD | MSTR | WT/STD | UNIT |
|--|-------|-----------------|-------------------------------------|-----------------|-------------|-----|------|--------|------|
| 20B* | 10005 | 8 Sol to 2 Str | Prsr Cast Brs Plated | Steel | 1/2 to 1" | 25 | 250 | 3.83# | C |
| 20M | 10010 | 8 Sol to 2 Str | Prsr Cast Mlbl Finish | Steel | 1/2 to 1" | 25 | 250 | 4.40# | C |
| 25 | 10015 | 10 Sol to 2 Str | Bronze | Steel | 1/2 to 1" | 25 | 250 | 4.48# | C |
| DB25 | 67500 | 10 Sol to 2 Str | Bronze Direct Burial | Bronze | 1/2 to 1" | 25 | 250 | 4.79# | C |
| DLI25 | 28090 | 10 Sol to 2 Str | Bronze Direct Burial Lay in Feature | Stainless Steel | 1/2 to 1" | 25 | 250 | 4.79# | C |
| DB25 and DLI25 Approved For Steel 4/6/8 Rebar | | | | | | | | | |
| DB2538 | 67503 | 10 Sol to 2 Str | Bronze Direct Burial | Bronze | 1/2 to 1" | 25 | 250 | 4.45# | C |
| DB2538 Dual Rated Suitable For Pipe or Steel Rebar 3/8 to 1" (#3 - #8). Accommodates Steel Rebar Without Disassembly | | | | | | | | | |
| PL25 | 56470 | 10 Sol to 2 Str | Bronze | Brass | 1/2 to 1" | 25 | 250 | 4.85# | C |
| 27 | 10025 | 10 Sol to 2 Str | Bronze | Steel | 1-1/4 to 2" | 5 | 50 | 2.18# | C |
| DB27 | 67502 | 10 Sol to 2 Str | Bronze Direct Burial | Bronze | 1-1/4 to 2" | 5 | 50 | 2.13# | C |
| DLI27 | 28092 | 10 Sol to 2 Str | Bronze Direct Burial Lay in Feature | Stainless Steel | 1-1/4 to 2" | 5 | 50 | 2.13# | C |
| 1001 | 10027 | 10 Sol to 2 Str | Bronze | Steel | 2-1/2 to 4" | 5 | 5 | 5.07# | C |
| 1002 | 10028 | 10 Sol to 2 Str | Bronze | Steel | 4-1/2 to 6" | 5 | 5 | 9.12# | C |

* Non UL Approved



Armored Ground Clamps PC 5560

Used to connect armored cable to water pipe for grounding. Special pressure bar grips armored cable insulation to decrease chances of grounding conductor being pulled out. Cast from high strength, highly conductive copper alloy.

- UL Listed
- Pressure Cast or Bronze
- Bonding or Grounding
- With Steel or Stainless Steel Screws

| CAT NO | UPC | WIRE RANGE | DESCRIPTION | SCREW TYPE | PIPE SIZE | STD | MSTR | WT/STD | UNIT |
|--|-------|-----------------|-----------------------|-----------------|-------------|-----|------|--------|------|
| 21B* | 10030 | 8 Sol to 4 Str | Prsr Cast Brs Plated | Steel | 1/2 to 1" | 25 | 250 | 5.09# | C |
| 21M | 10035 | 8 Sol to 4 Str | Prsr Cast Mlbl Finish | Steel | 1/2 to 1" | 25 | 250 | 5.09# | C |
| 26 | 10040 | 8 Sol to 4 Str | Bronze | Steel | 1/2 to 1" | 25 | 250 | 5.83# | C |
| DLI26 | 28091 | 8 Sol to 4 Str | Bronze Lay in Feature | Stainless Steel | 1/2 to 1" | 25 | 250 | 5.63# | C |
| 26SWV | 10042 | 10 Sol to 6 Str | Bronze Swivel Type | Steel | 1/2 to 1" | 25 | 125 | 9.33# | C |
| 26SWV Includes a pressure bar that swings 360° for easy adjustment | | | | | | | | | |
| 28 | 10045 | 8 Sol to 4 Str | Bronze | Steel | 1-1/4 to 2" | 25 | 250 | 11.63# | C |
| 28SWV | 10046 | 10 Sol to 6 Str | Bronze swivel Type | Steel | 1-1/4 to 2" | 5 | 5 | 3.05# | C |
| 28SWV Includes a pressure bar that swings 360° for easy adjustment | | | | | | | | | |
| 1102* | 10047 | 8 Sol to 4 Str | Bronze | Steel | 2-1/2 to 4" | 5 | 5 | 6.60# | C |
| 1103* | 11048 | 8 Sol to 4 Str | Bronze | Steel | 4-5-6" | 5 | 5 | 9.92# | C |


* Non UL Approved



Ground Clamps With Hubs PC 5560

- UL Listed
- Bronze
- With 1/2", 3/4" or 1" Hubs

Ground clamps with hubs are used to connect grounding conductor in conduit to water pipe for grounding. Cast from high strength, highly conductive copper alloy with steel or bronze screws.



| CAT NO | UPC | PHOTO | WIRE RANGE | HUB SIZE | PIPE SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------|------------|----------|-------------|-----|------|--------|------|
| 29L | 10051 | E | 10-6 | 1/2" | 1/2 to 1" | 25 | 125 | 9.80# | C |
| 29BRZ | 10054 | E | 10-6 | 1/2" | 1/2 to 1" | 25 | 125 | 10.06# | C |
| 30L | 10053 | D | 10-2/0 | 3/4" | 1/2 to 1" | 25 | 125 | 11.35# | C |
| 31L | 10056 | D | 10-3/0 | 1" | 1/2 to 1" | 25 | 125 | 12.33# | C |
| 270L | 10057 | E | 10-6 | 1/2" | 1-1/4 to 2" | 25 | 25 | 14.87# | C |
| 271L | 10059 | D | 10-2/0 | 3/4" | 1-1/4 to 2" | 25 | 25 | 16.63# | C |
| 272L | 10061 | D | 10-3/0 | 1" | 1-1/4 to 2" | 25 | 25 | 17.44# | C |
| 280L | 10063 | E | 10-6 | 1/2" | 2-1/2 to 4" | 5 | 5 | 6.23# | C |
| 281L | 10064 | D | 10-2/0 | 3/4" | 2-1/2 to 4" | 5 | 5 | 6.63# | C |
| 282L | 10066 | D | 10-3/0 | 1" | 2-1/2 to 4" | 5 | 5 | 6.64# | C |

All clamps provided with steel screws except 29BRZ (bronze screws)

Ground Rod Clamps PC 5570

- UL Listed
- Direct Burial
- Bronze
- With Bronze Hex Head Bolt

Ground rod clamps are used to connect conductor to a driven ground rod. Cast from high strength, highly conductive copper alloy, they are approved for direct burial in ground and concrete and are assembled with a bronze hex head bolt.



| CAT NO | UPC | SIZE | GROUND WIRE | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|-----------------|-----|------|--------|------|
| GR12 | 10500 | 1/2" | 10 Sol to 2 Str | 50 | 250 | 8.83# | C |
| GR58 | 10505 | 5/8" | 10 Sol to 2 Str | 50 | 250 | 4.65# | C |
| GR34 | 10510 | 3/4" | 10 Sol to 2 Str | 25 | 100 | 2.96# | C |

Ground Rod Clamps - Universal PC 5570

- UL Listed
- Direct Burial
- Stainless Steel
- One Size Fits All

Universal Ground Rod Clamp is UL Listed for all sizes of Ground Rods and Rebar. Constructed of Stainless Steel Alloy and a High Performance Stainless Steel Bolt. For direct Burial in Earth or Concrete.




| CAT NO | UPC | ROD SIZES | WIRE RANGE | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|------------------|-----|------|--------|------|
| UGRCS | 83180 | 3/8" | 10 Sol - 1/0 Str | 50 | 250 | 4.65# | C |
| | | 1/2" | 10 Sol - 1/0 Str | | | | |
| | | 5/8" | 10 Sol - 1/0 Str | | | | |
| | | 3/4" | 8 Sol - 1/0 Str | | | | |



Hubs PC 5580

- UL Listed
- Bronze

Hubs are used with ground clamps to connect rigid conduit to water pipe for grounding. 360° swing type hub provides flexibility. They are cast from high strength, highly conductive copper alloy with zinc plated screws.



| CAT NO | UPC | SIZE | PHOTO | GROUND WIRE | STD | MSTR | WT/STD | UNIT |
|---------|-------|------|-------|-------------------|-----|------|--------|------|
| HUB50L | 10171 | 1/2" | F | 10 Sol to 6 Str | 25 | 250 | 5.04# | C |
| HUB75L | 10176 | 3/4" | G | 10 Sol to 2/0 Str | 25 | 250 | 7.23# | C |
| HUB100L | 10181 | 1" | G | 10 Sol to 3/0 Str | 10 | 100 | 3.00# | C |



Now With Multi-Drive

Ground Screws PC 5620

Ground screws are plated green for identification purposes and are used for grounding pigtails or wire. They have either a 1/4" or 5/16" head with Hex/Slotted/Phillips/Square drive. The 1/4" (1032G & 1032GTP) has a leader point; the 5/16" (1032TC & 1032TCTP) has a thread cutting point.

- Steel
- Green Zinc Plated
- 1/4" or 5/16" Head
- Leader or Thread Cutting Point
- Hex/Slotted/Phillips/Square

| CAT NO | UPC | DESCRIPTION | HEX SIZE | SCREW SIZE | STD | MSTR | WT/STD | UNIT |
|----------|-------|---|----------|--------------|-----|------|--------|------|
| 1032G | 14107 | Leader Point Hex/Slotted/Phillips/Square | 1/4" | 10-32 x 3/8" | 100 | 1000 | 0.44# | C |
| 1032GTP | 14108 | Tuff Pack | 1/4" | 10-32 x 3/8" | 500 | 3000 | 4.20# | C |
| 1032TC | 14109 | Thread Cutting Pt. Hex/Slotted/Phillips/Square | 5/16" | 10-32 x 3/8" | 100 | 1000 | 0.50# | C |
| 1032TCTP | 14111 | Tuff Pack | 5/16" | 10-32 x 3/8" | 500 | 3000 | 4.86# | C |



Now With Multi-Drive

Ground Pigtails PC 5630

Ground pigtails are used for grounding receptacles to steel boxes.

- Green Zinc Plated Ground Screw
- UL Listed Wire
- Green #12 Ga. Solid Copper Wire
- 7-1/2", 10-1/2" or 12-1/2" Lengths
- 1/4" Hex/Slotted/Phillips/Square with (Leader Point)

| CAT NO | UPC | SIZE | GAUGE | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------|-------|-----|------|--------|------|
| GP650 | 16100 | 7-1/2" | 12 Ga | 250 | 2000 | 4.90# | C |
| GP1050 | 16102 | 10-1/2" | 12 Ga | 250 | 2000 | 6.56# | C |
| GP1250 | 16103 | 12-1/2" | 12 Ga | 250 | 1000 | 7.44# | C |



Ground Clips PC 5640

Ground Clips are intended to be pressed on the top edge of a box to hold a No.10, 12, or 14AWG copper or No.10, or 12AWG aluminum grounding conductor against the side wall. This clip may be used for connecting the grounding conductor of nonmetallic sheathed cable to outlet boxes or for connecting the grounding jumper from a receptacle to an outlet.

- UL Listed
- Zinc Plated
- Holds 10, 12, or 14 Ga. Copper Wire
- Holds 10, or 12 Ga. Aluminum Wire

| CAT NO | UPC | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------|------|--------|-------|
| GC | 27050 | 100 | 1000 | 0.38# | C |
| GCTP | 27051 | Tuff Pack | 500 | 3000 | 1.90# |



Copper Crimp Sleeves PC 5650

Copper Crimp Sleeves are used to group and terminate copper wires and provide a vibration resistant connection. Copper requires crimping pressure and resists corrosion.

- UL Listed
- Solid Copper
- 18 to 10 Ga. Wire
- 18 to 8 Ga. Wire

| CAT NO | UPC | WIRE GAUGE | STD | MSTR | WT/STD | UNIT |
|---------|-------|------------------|-----|------|--------|------|
| CS410 | 27755 | 18-10 AWG | 100 | 1000 | 0.24# | C |
| CS410TP | 27756 | Tuff Pack | 500 | 3000 | 1.15# | C |
| CS411 | 27760 | 18-8 AWG | 50 | 500 | 0.24# | C |

Entrance Caps PC 5690



- UL Listed
- Die Cast Copper Free Aluminum
- Phenolic Insulator
- Clamp On Style
- Weather Resistant

Clamp on service entrance caps permit a weather resistant entrance for type SE cable on rigid, IMC or EMT for pulling service drop conductors. They are assembled with an electrical grade Phenolic insulator with multiple holes.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| EC50 | 40005 | 1/2" | 25 | 25 | 6.21# | C |
| EC75 | 40010 | 3/4" | 25 | 25 | 7.18# | C |
| EC100 | 40015 | 1" | 25 | 25 | 8.97# | C |
| EC125 | 40020 | 1-1/4" | 10 | 10 | 4.89# | C |
| EC150 | 40025 | 1-1/2" | 10 | 10 | 7.56# | C |
| EC200 | 40030 | 2" | 5 | 5 | 6.09# | C |
| EC250 | 40035 | 2-1/2" | 1 | 1 | 3.83# | C |
| EC300 | 40040 | 3" | 1 | 1 | 5.43# | C |
| EC350 | 40045 | 3-1/2" | 1 | 1 | 6.47# | C |
| EC400 | 40050 | 4" | 1 | 1 | 6.78# | C |

Entrance Ells (SLB) PC 5700



- UL Listed
- Die Cast Copper Free Aluminum
- Assembled with Fiber Gasket & Aluminum Cover
- Weather Resistant

Service Entrance Ells are used with threaded rigid conduit or IMC for providing access to the interior of a conduit system for pulling, splicing, inspection and maintenance.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| SLB50 | 40100 | 1/2" | 10 | 100 | 2.01# | C |
| SLB75 | 40105 | 3/4" | 10 | 100 | 2.60# | C |
| SLB100 | 40110 | 1" | 5 | 50 | 2.15# | C |
| SLB125 | 40115 | 1-1/4" | 5 | 50 | 3.76# | C |
| SLB150 | 40120 | 1-1/2" | 2 | 20 | 1.83# | C |
| SLB200 | 40125 | 2" | 2 | 10 | 2.69# | C |

Pulling Ells PC 5710



- UL Listed
- Die Cast
- High Strength Zinc Alloy
- Removable Aluminum Cover & Neoprene Gasket

Pulling Ells are used to connect two lengths of threaded rigid conduit or IMC to form a 90° bend and provide access for wire pulling.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|-----|------|--------|------|
| PE1 | 40130 | 1/2" | 10 | 100 | 1.89# | C |
| PE2 | 40135 | 3/4" | 10 | 100 | 2.69# | C |
| PE3 | 40140 | 1" | 5 | 25 | 2.50# | C |



Threaded Conduit Bodies PC 5730

Threaded Conduit Bodies are used with rigid conduit to provide access to the interior of a conduit system. They are available as bodies only, or as bodies assembled with covers and gaskets. The flat back design allows the unit to be mounted close to the wall. They are die cast from high strength, copper free aluminum.

- UL Listed
- Die Cast Copper Free Aluminum
- Without Covers
- Without Gaskets

| CAT NO | UPC | | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|--------|-----|------|--------|------|
| LB50 | 40400 | | 1/2" | 10 | 100 | 2.98# | C |
| LB75 | 40405 | | 3/4" | 10 | 50 | 4.41# | C |
| LB100 | 40410 | | 1" | 5 | 25 | 3.15# | C |
| LB125 | 40415 | | 1-1/4" | 2 | 10 | 2.63# | C |
| LB150 | 40420 | | 1-1/2" | 2 | 10 | 2.94# | C |
| LB200 | 40425 | LB | 2" | 1 | 5 | 2.46# | C |
| LB250 | 40430 | | 2-1/2" | 1 | 1 | 4.71# | C |
| LB300 | 40435 | | 3" | 1 | 1 | 5.40# | C |
| LB350 | 40440 | | 3-1/2" | 1 | 1 | 8.32# | C |
| LB400 | 40445 | | 4" | 1 | 1 | 8.50# | C |
| LR50 | 40600 | | 1/2" | 10 | 100 | 2.52# | C |
| LR75 | 40605 | | 3/4" | 10 | 50 | 4.58# | C |
| LR100 | 40610 | | 1" | 5 | 25 | 3.12# | C |
| LR125 | 40615 | | 1-1/4" | 2 | 10 | 2.89# | C |
| LR150 | 40620 | | 1-1/2" | 2 | 10 | 3.15# | C |
| LR200 | 40625 | LR | 2" | 1 | 5 | 2.59# | C |
| LR250 | 40630 | | 2-1/2" | 1 | 1 | 6.13# | C |
| LR300 | 40635 | | 3" | 1 | 1 | 9.02# | C |
| LR350 | 40640 | | 3-1/2" | 1 | 1 | 10.24# | C |
| LR400 | 40645 | | 4" | 1 | 1 | 9.60# | C |
| LL50 | 40550 | | 1/2" | 10 | 100 | 2.48# | C |
| LL75 | 40555 | | 3/4" | 10 | 50 | 4.50# | C |
| LL100 | 40560 | | 1" | 5 | 25 | 3.13# | C |
| LL125 | 40565 | | 1-1/4" | 2 | 10 | 2.47# | C |
| LL150 | 40570 | | 1-1/2" | 2 | 10 | 2.98# | C |
| LL200 | 40575 | LL | 2" | 1 | 5 | 2.61# | C |
| LL250 | 40580 | | 2-1/2" | 1 | 1 | 4.69# | C |
| LL300 | 40585 | | 3" | 1 | 1 | 6.44# | C |
| LL350 | 40590 | | 3-1/2" | 1 | 1 | 9.13# | C |
| LL400 | 40595 | | 4" | 1 | 1 | 9.22# | C |
| C50 | 40700 | | 1/2" | 10 | 100 | 2.44# | C |
| C75 | 40705 | | 3/4" | 10 | 50 | 4.17# | C |
| C100 | 40710 | | 1" | 5 | 25 | 2.42# | C |
| C125 | 40715 | | 1-1/4" | 2 | 10 | 3.16# | C |
| C150 | 40720 | | 1-1/2" | 2 | 10 | 2.84# | C |
| C200 | 40725 | C | 2" | 1 | 5 | 2.55# | C |
| C250 | 40730 | | 2-1/2" | 1 | 1 | 5.25# | C |
| C300 | 40735 | | 3" | 1 | 1 | 5.72# | C |
| C350 | 40740 | | 3-1/2" | 1 | 1 | 9.51# | C |
| C400 | 40745 | | 4" | 1 | 1 | 9.00# | C |
| T50 | 40800 | | 1/2" | 10 | 100 | 2.99# | C |
| T75 | 40805 | | 3/4" | 10 | 50 | 4.43# | C |
| T100 | 40810 | | 1" | 5 | 25 | 3.27# | C |
| T125 | 40815 | | 1-1/4" | 2 | 10 | 3.76# | C |
| T150 | 40820 | | 1-1/2" | 2 | 10 | 3.29# | C |
| T200 | 40825 | T | 2" | 2 | 2 | 5.38# | C |
| T250 | 40830 | | 2-1/2" | 1 | 1 | 5.77# | C |
| T300 | 40835 | | 3" | 1 | 1 | 6.35# | C |
| T350 | 40840 | | 3-1/2" | 1 | 1 | 11.30# | C |
| T400 | 40845 | | 4" | 1 | 1 | 9.70# | C |





- UL Listed
- Die Cast Copper Free Aluminum
- With Covers
- With Neoprene Gaskets

Threaded Conduit Bodies with cover and gasket are used with rigid conduit to provide access to the interior of a conduit system. They are available as bodies only, or as bodies assembled with covers and gaskets. The flat back design allows the unit to be mounted close to the wall. They are die cast from high strength, copper free aluminum.

| CAT NO | UPC | | SIZE | STD | MSTR | WT/STD | UNIT |
|---------|-------|-----------|--------|-----|------|--------|------|
| LB50CG | 10722 | | 1/2" | 10 | 100 | 2.93# | C |
| LB75CG | 10724 | | 3/4" | 10 | 50 | 4.10# | C |
| LB100CG | 10726 | | 1" | 5 | 25 | 3.58# | C |
| LB125CG | 10728 | | 1-1/4" | 2 | 10 | 2.96# | C |
| LB150CG | 10730 | | 1-1/2" | 2 | 10 | 3.25# | C |
| LB200CG | 10732 | LB | 2" | 1 | 5 | 2.80# | C |
| LB250CG | 10734 | | 2-1/2" | 1 | 1 | 5.10# | C |
| LB300CG | 10736 | | 3" | 1 | 1 | 6.20# | C |
| LB350CG | 10738 | | 3-1/2" | 1 | 1 | 9.54# | C |
| LB400CG | 10740 | | 4" | 1 | 1 | 10.09# | C |
| LR50CG | 10762 | | 1/2" | 10 | 100 | 2.98# | C |
| LR75CG | 10764 | | 3/4" | 10 | 50 | 5.21# | C |
| LR100CG | 10766 | | 1" | 5 | 25 | 3.62# | C |
| LR125CG | 10768 | | 1-1/4" | 2 | 10 | 3.06# | C |
| LR150CG | 10770 | | 1-1/2" | 2 | 10 | 3.33# | C |
| LR200CG | 10772 | LR | 2" | 1 | 5 | 2.80# | C |
| LR250CG | 10774 | | 2-1/2" | 1 | 1 | 6.43# | C |
| LR300CG | 10776 | | 3" | 1 | 1 | 9.60# | C |
| LR350CG | 10778 | | 3-1/2" | 1 | 1 | 11.39# | C |
| LR400CG | 10780 | | 4" | 1 | 1 | 12.00# | C |
| LL50CG | 10742 | | 1/2" | 10 | 100 | 3.00# | C |
| LL75CG | 10744 | | 3/4" | 10 | 50 | 5.17# | C |
| LL100CG | 10746 | | 1" | 5 | 25 | 3.52# | C |
| LL125CG | 10748 | | 1-1/4" | 2 | 10 | 2.93# | C |
| LL150CG | 10750 | | 1-1/2" | 2 | 10 | 3.22# | C |
| LL200CG | 10752 | LL | 2" | 1 | 5 | 2.84# | C |
| LL250CG | 10754 | | 2-1/2" | 1 | 1 | 5.26# | C |
| LL300CG | 10756 | | 3" | 1 | 1 | 7.02# | C |
| LL350CG | 10758 | | 3-1/2" | 1 | 1 | 10.35# | C |
| LL400CG | 10760 | | 4" | 1 | 1 | 10.80# | C |
| C50CG | 10702 | | 1/2" | 10 | 100 | 2.82# | C |
| C75CG | 10704 | | 3/4" | 10 | 50 | 4.79# | C |
| C100CG | 10706 | | 1" | 5 | 25 | 2.87# | C |
| C125CG | 10708 | | 1-1/4" | 2 | 10 | 2.88# | C |
| C150CG | 10710 | | 1-1/2" | 2 | 10 | 2.90# | C |
| C200CG | 10712 | C | 2" | 1 | 5 | 2.65# | C |
| C250CG | 10714 | | 2-1/2" | 1 | 1 | 5.67# | C |
| C300CG | 10716 | | 3" | 1 | 1 | 6.28# | C |
| C350CG | 10718 | | 3-1/2" | 1 | 1 | 9.90# | C |
| C400CG | 10720 | | 4" | 1 | 1 | 10.35# | C |
| T50CG | 10782 | | 1/2" | 10 | 100 | 3.80# | C |
| T75CG | 10784 | | 3/4" | 10 | 50 | 4.25# | C |
| T100CG | 10786 | | 1" | 5 | 25 | 3.63# | C |
| T125CG | 10788 | | 1-1/4" | 2 | 10 | 4.03# | C |
| T150CG | 10790 | | 1-1/2" | 2 | 10 | 3.55# | C |
| T200CG | 10792 | T | 2" | 2 | 2 | 5.85# | C |
| T250CG | 10794 | | 2-1/2" | 1 | 1 | 7.06# | C |
| T300CG | 10796 | | 3" | 1 | 1 | 7.63# | C |
| T350CG | 10798 | | 3-1/2" | 1 | 1 | 12.52# | C |
| T400CG | 10802 | | 4" | 1 | 1 | 10.95# | C |
| TB50CG | 81526 | | 1/2" | 10 | 100 | 3.80# | C |
| TB75CG | 81527 | | 3/4" | 10 | 50 | 4.25# | C |
| TB100CG | 81528 | TB | 1" | 5 | 25 | 3.63# | C |
| TB125CG | 81529 | | 1-1/4" | 2 | 10 | 4.03# | C |
| TB150CG | 81530 | | 1-1/2" | 2 | 10 | 3.55# | C |
| TB200CG | 81531 | | 2" | 2 | 2 | 5.85# | C |
| X50CG | 81532 | | 1/2" | 10 | 100 | 3.80# | C |
| X75CG | 81533 | | 3/4" | 10 | 50 | 4.25# | C |
| X100CG | 81534 | X | 1" | 5 | 25 | 3.63# | C |
| X125CG | 81535 | | 1-1/4" | 2 | 10 | 4.03# | C |
| X150CG | 81536 | | 1-1/2" | 2 | 10 | 3.55# | C |
| X200CG | 81537 | | 2" | 2 | 2 | 5.85# | C |





Malleable Conduit Bodies PC 5731

- Tapered Thread
- Suitable For Use In Concrete
- Zinc Plated Aluminum Enameled

Malleable Threaded Conduit bodies are used with rigid conduit to provide access to the interior of a conduit system.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------|-----|------|--------|------|
| LB50M | 81538 | 1/2" | 10 | 100 | 7.06# | C |
| LB75M | 81539 | 3/4" | 10 | 50 | 9.67# | C |
| LB100M | 81540 | 1" | 5 | 25 | 7.13# | C |
| LB125M | 81541 | 1-1/4" | 2 | 10 | 5.75# | C |
| LB150M | 81542 | 1-1/2" | 2 | 10 | 6.63# | C |
| LB200M | 81543 | LB 2" | 1 | 5 | 5.34# | C |
| LB250M | 81544 | 2-1/2" | 1 | 1 | 11.05# | C |
| LB300M | 81545 | 3" | 1 | 1 | 11.60# | C |
| LB350M | 81546 | 3-1/2" | 1 | 1 | 19.89# | C |
| LB400M | 81547 | 4" | 1 | 1 | 20.99# | C |
| LR50M | 81568 | 1/2" | 10 | 100 | 7.63# | C |
| LR75M | 81569 | 3/4" | 10 | 50 | 9.74# | C |
| LR100M | 81570 | 1" | 5 | 25 | 6.90# | C |
| LR125M | 81571 | 1-1/4" | 2 | 10 | 6.18# | C |
| LR150M | 81572 | 1-1/2" | 2 | 10 | 6.63# | C |
| LR200M | 81573 | LR 2" | 1 | 5 | 4.97# | C |
| LR250M | 81574 | 2-1/2" | 1 | 1 | 11.05# | C |
| LR300M | 81575 | 3" | 1 | 1 | 14.36# | C |
| LR350M | 81576 | 3-1/2" | 1 | 1 | 23.20# | C |
| LR400M | 81577 | 4" | 1 | 1 | 24.31# | C |
| LL50M | 81558 | 1/2" | 10 | 100 | 7.63# | C |
| LL75M | 81559 | 3/4" | 10 | 50 | 9.74# | C |
| LL100M | 81560 | 1" | 5 | 25 | 6.90# | C |
| LL125M | 81561 | 1-1/4" | 2 | 10 | 6.18# | C |
| LL150M | 81562 | 1-1/2" | 2 | 10 | 6.63# | C |
| LL200M | 81563 | LL 2" | 1 | 5 | 4.97# | C |
| LL250M | 81564 | 2-1/2" | 1 | 1 | 11.05# | C |
| LL300M | 81565 | 3" | 1 | 1 | 14.36# | C |
| LL350M | 81566 | 3-1/2" | 1 | 1 | 23.20# | C |
| LL400M | 81567 | 4" | 1 | 1 | 24.31# | C |
| C50M | 81548 | 1/2" | 10 | 100 | 9.82# | C |
| C75M | 81549 | 3/4" | 10 | 50 | 11.84# | C |
| C100M | 81550 | 1" | 5 | 25 | 8.48# | C |
| C125M | 81551 | 1-1/4" | 2 | 10 | 6.18# | C |
| C150M | 81552 | 1-1/2" | 2 | 10 | 7.36# | C |
| C200M | 81553 | C 2" | 1 | 5 | 5.52# | C |
| C250M | 81554 | 2-1/2" | 1 | 1 | 12.15# | C |
| C300M | 81555 | 3" | 1 | 1 | 14.36# | C |
| C350M | 81556 | 3-1/2" | 1 | 1 | 22.10# | C |
| C400M | 81557 | 4" | 1 | 1 | 23.20# | C |
| T50M | 81578 | 1/2" | 10 | 100 | 11.15# | C |
| T75M | 81579 | 3/4" | 10 | 50 | 13.70# | C |
| T100M | 81580 | 1" | 5 | 25 | 9.82# | C |
| T125M | 81581 | 1-1/4" | 2 | 10 | 6.63# | C |
| T150M | 81582 | 1-1/2" | 2 | 10 | 7.36# | C |
| T200M | 81583 | T 2" | 1 | 5 | 6.63# | C |
| T250M | 81584 | 2-1/2" | 1 | 1 | 12.70# | C |
| T300M | 81585 | 3" | 1 | 1 | 15.47# | C |
| T350M | 81586 | 3-1/2" | 1 | 1 | 25.41# | C |
| T400M | 81587 | 4" | 1 | 1 | 25.41# | C |
| TB50M | 81607 | 1/2" | 10 | 100 | 8.84# | C |
| TB75M | 81608 | 3/4" | 10 | 50 | 11.97# | C |
| TB100M | 81609 | 1" | 5 | 25 | 9.86# | C |
| TB125M | 81610 | TB 1-1/4" | 2 | 10 | 3.96# | C |
| TB150M | 81611 | 1-1/2" | 2 | 10 | 6.85# | C |
| TB200M | 81612 | 2" | 1 | 5 | 6.90# | C |
| X50M | 81588 | 1/2" | 10 | 100 | 8.84# | C |
| X75M | 81589 | 3/4" | 5 | 50 | 11.97# | C |
| X100M | 81590 | 1" | 2 | 20 | 9.86# | C |
| X125M | 81591 | X 1-1/4" | 2 | 10 | 3.96# | C |
| X150M | 81592 | 1-1/2" | 2 | 10 | 6.85# | C |
| X200M | 81593 | 2" | 1 | 5 | 6.90# | C |





- Fiber
- Neoprene

Gaskets are available in fiber or neoprene and are used to make a conduit body weather resistant.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------------------------------|-------|----------------|-----|------|--------|------|
| Fiber Gaskets - PC 5790 | | | | | | |
| G50 | 40200 | 1/2" | 50 | 500 | 0.36# | C |
| G75 | 40205 | 3/4" | 50 | 500 | 0.48# | C |
| G100 | 40210 | 1" | 50 | 250 | 0.64# | C |
| G125/150 | 40215 | 1-1/4 & 1-1/2" | 50 | 100 | 1.31# | C |
| G200 | 40220 | 2" | 25 | 50 | 0.98# | C |
| G250/300 | 40225 | 2-1/2 & 3" | 25 | 50 | 2.30# | C |
| G350/400 | 40230 | 3-1/2 & 4" | 25 | 50 | 3.10# | C |

Neoprene Gaskets - PC 5800

| | | | | | | |
|-----------|-------|----------------|----|-----|-------|---|
| GN50 | 40250 | 1/2" | 50 | 500 | 0.58# | C |
| GN75 | 40255 | 3/4" | 50 | 500 | 0.78# | C |
| GN100 | 40260 | 1" | 50 | 250 | 1.00# | C |
| GN125/150 | 40265 | 1-1/4 & 1-1/2" | 50 | 100 | 2.21# | C |
| GN200 | 40270 | 2" | 25 | 50 | 1.84# | C |
| GN250/300 | 40275 | 2-1/2 & 3" | 25 | 50 | 4.60# | C |
| GN350/400 | 40280 | 3-1/2 & 4" | 25 | 50 | 6.25# | C |

**Aluminum Covers
PC 5760**



- UL Listed
- Captive Plated Screws

Aluminum covers are stamped from high strength aluminum and are used with all styles of aluminum conduit bodies.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|-----------|-------|----------------|-----|------|--------|------|
| BC50 | 40300 | 1/2" | 50 | 50 | 2.40# | C |
| BC75 | 40305 | 3/4" | 50 | 50 | 3.13# | C |
| BC100 | 40310 | 1" | 25 | 25 | 2.22# | C |
| BC125/150 | 40315 | 1-1/4 & 1-1/2" | 10 | 10 | 1.67# | C |
| BC200 | 40320 | 2" | 5 | 5 | 1.42# | C |
| BC250/300 | 40325 | 2-1/2 & 3" | 5 | 5 | 4.03# | C |
| BC350/400 | 40330 | 3-1/2 & 4" | 5 | 5 | 4.12# | C |

**Steel Covers
PC 5761**



- Raised Dome
- Captive Stainless Steel Screws
- Zinc Plated

Raised Dome Steel Conduit Body covers are stamped from high strength steel and are used with all style of malleable conduit bodies.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|-----------|-------|----------------|-----|------|--------|------|
| SC50 | 81598 | 1/2" | 50 | 50 | 4.70# | C |
| SC75 | 81599 | 3/4" | 50 | 50 | 6.25# | C |
| SC100 | 81600 | 1" | 25 | 25 | 4.70# | C |
| SC125/150 | 81601 | 1-1/4 & 1-1/2" | 10 | 10 | 3.13# | C |
| SC200 | 81602 | 2" | 5 | 5 | 2.50# | C |
| SC250/300 | 81603 | 2-1/2 & 3" | 5 | 5 | 4.69# | C |
| SC350/400 | 81604 | 3-1/2 & 4" | 5 | 5 | 6.87# | C |

FITTINGS & STAMPINGS > FIBER & NEOPRENE GASKETS > ALUMINUM COVERS > STEEL COVERS



Spider Plate PC 5910

Spider plates are a universal mounting plate which allows mounting fixtures to a 3" or 4" round box regardless of screw hole location.

- Steel
- Universal

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------------------------|-----|------|--------|------|
| SP34 | 42090 | Adapts 3-1/4" to 4" boxes | 20 | 20 | 3.00# | C |



Closure Plugs PC 5910

Closure Plugs are used to seal unused holes in weatherproof boxes.

- Weatherproof
- Die Cast

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------------------|-----|------|--------|------|
| TP50 | 42070 | 1/2" Threaded Plug | 100 | 1000 | 0.10# | C |
| TP75 | 42075 | 3/4" Threaded Plug | 100 | 1000 | 0.20# | C |



Blank Covers PC 5910

Industrial design provides a durable enclosure for weatherproof box.

- Weatherproof
- Die Cast

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|----------------------------------|-------|-----------------------|-----|------|--------|------|
| Blank Covers | | | | | | |
| BLC1 | 42120 | With gaskets & Screws | 25 | 250 | 2.25# | C |
| Two Gang Blank Box Covers | | | | | | |
| BLC2 | 43060 | With gaskets & Screws | 10 | 100 | 0.90# | C |



Bend Saver - EMT Coupling System PC 6253

Never Bend 1/2" & 3/4" EMT again when running EMT into a junction box, standoff design eliminates conduit bending and provides automatic alignment with electrical box knockouts.

- UL Listed
- Steel and Die Cast
- No Offset Required
- Time Saver

| CAT NO | UPC | SIZE | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|-----------------------|-----|------|--------|------|
| BSCS50 | 16460 | 1/2" | Steel Conduit Strap | 50 | 500 | 1.88# | C |
| BSCS75 | 16461 | 3/4" | Steel Conduit Strap | 50 | 500 | 2.20# | C |
| BSDC50 | 16462 | 1/2" | Die Cast EMT Coupling | 50 | 500 | 2.15# | C |
| BSDC75 | 16463 | 3/4" | Die Cast EMT Coupling | 50 | 500 | 3.45# | C |



Bend Saver Installed

Quicklock Type Connectors Insulated Throat - PC 5715



QL50 QL75 QL50DUP

- UL Listed
- Tubular Steel
- Combo Screw
- No Locknut Required
- Single or Double
- Zinc Plated

Single unit construction eliminates loose component parts, integral green plastic insulated throat bushing provides maximum protection for insulated wires. For connecting MC, AC, and Flex Cable.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|---------|-------|-------------|-----|------|--------|------|
| QL50 | 11977 | 1/2" Single | 25 | 250 | 1.88# | C |
| QL75 | 11978 | 3/4" Single | 25 | 250 | 3.63# | C |
| QL50DUP | 11979 | 1/2" Double | 20 | 200 | 1.02# | C |

| CABLE TYPE | QL-50 1/2" KO | | | QL-75 3/4" KO | | QL-50DUP** 1/2 KO DUPLEX | | |
|-------------------------|------------------|----------------|----------------|------------------|--------------|-----------------------------|--------------|--------------|
| AC Steel | 14/2 12/2 | 14/3 12/3 | 14/4 12/4 | 10/4 8/3 | 10/5 8/4 | 14/2 12/2 | 14/3 12/3 | 14/4 12/4 |
| | 10/2 10/3 | | 6/3 | | | | | |
| AC Aluminum Interlocked | 14/2 12/2 | 14/3 12/3 | 14/4 12/4 | 8/3 | 10/4 8/4 | 14/2 12/2 | 14/3 12/3 | 14/4 12/4 |
| MC Steel | 14/2* 12/2* | 14/3* 12/3* | 14/4* 12/4* | 10/3* 8/2* | 10/4 8/3* | 14/2 12/2 | 14/3 12/3 | 14/4 12/4 |
| | 10/2 10/3 | | 6/2* | | 10/2 | | | |
| MC Aluminum Interlocked | 14/2 12/2 | 14/3 12/3 | 14/4 12/4 | 10/3 8/2 | 10/4 | 14/2 12/2 | 14/3 12/3 | 14/4 12/4 |
| MC Aluminum | 12/2* | 14/3 12/3* | 14/4 12/4 | - | - | - | - | - |
| | 10/2 10/3 | | | | | | | |
| MC Aluminum Flat | 12/3 | | | - | | - | | |
| Flex RW | 3/8 Steel & Al. | | | 1/2 Steel | | - | | |

* Concrete tight when taped and used with PVC jacketed cord. ** Accepts 2 cables of each size listed.

Offset Nipples PC 5540



- UL Listed
- Die Cast
- High Strength Zinc Alloy

Offset Nipples are used to offset the axis of raceways.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| ON50 | 10600 | 1/2" | 25 | 250 | 2.33# | C |
| ON75 | 10605 | 3/4" | 20 | 200 | 2.48# | C |
| ON100 | 10610 | 1" | 10 | 100 | 2.11# | C |
| ON125 | 10615 | 1-1/4" | 10 | 100 | 2.79# | C |
| ON150 | 10620 | 1-1/2" | 2 | 20 | 0.80# | C |
| ON200 | 10625 | 2" | 2 | 20 | 1.18# | C |

Conduit Nipples PC 5550



- UL Listed
- Die Cast
- High Strength Zinc Alloy

Conduit Nipples are used with a locknut to serve as a short raceway between enclosures.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| CN50 | 10200 | 1/2" | 100 | 500 | 2.97# | C |
| CN75 | 10205 | 3/4" | 100 | 500 | 5.60# | C |
| CN100 | 10210 | 1" | 100 | 500 | 7.66# | C |
| CN125 | 10215 | 1-1/4" | 25 | 125 | 2.77# | C |
| CN150 | 10220 | 1-1/2" | 25 | 125 | 3.99# | C |
| CN200 | 10225 | 2" | 25 | 125 | 5.70# | C |
| CN250 | 67700 | 2-1/2" | 5 | 5 | 2.19# | C |
| CN300 | 67702 | 3" | 5 | 5 | 2.41# | C |
| CN350 | 67704 | 3-1/2" | 5 | 5 | 3.71# | C |
| CN400 | 67706 | 4" | 5 | 5 | 4.02# | C |




Multi-Guard Covers PC 5912

"While In-use" weatherproof receptacle cover meets NEC 410-57(b) code. Protection from rain, sleet and snow with cord set plugged in for unattended receptacles. Designed to meet NEC 210-60(b) code.

- UL Listed
- Single & Double Gang
- Weatherproof
- Mounts Vertically or Horizontally

| CAT NO | UPC | DESCRIPTION | DEPTH | STD | MSTR | WT/STD | UNIT |
|--------------------|-------|----------------------|--------|-----|------|--------|------|
| Single Gang | | | | | | | |
| FG1100C | 10901 | Standard Depth Cover | 2-1/4" | 1 | 10 | 0.45# | Ea |
| FG1110C | 10902 | Deep Cover | 3-1/8" | 1 | 10 | 0.49# | Ea |


14 Configurations, One Cover
 Single Gang Vertical or Horizontal.
 Includes 3 Patented Inserts
 4 Rounds; Toggle; Duplex;
 GFCI 1-3/8"; 1-5/8"; 1-3/4"; 2-1/8"



Mounts Vertically or Horizontally
 Plug and Outlet Protection for any Single Gang Application. The standard Depth Cover recommended for 16 gauge or lighter cord sets for vending machines, holiday lighting, landscape lighting and portable signs.

| CAT NO | UPC | DESCRIPTION | DEPTH | STD | MSTR | WT/STD | UNIT |
|--------------------|-------|----------------------|--------|-----|------|--------|------|
| Double Gang | | | | | | | |
| FG1220C | 10911 | Standard Depth Cover | 2-1/4" | 1 | 10 | 0.55# | Ea |

70 Configurations, One Cover
 Any Two Gang Application.
 Includes 6 Snap Together Patented Inserts.



Mounts Vertically or Horizontally
 Plug and Outlet Protection for any Two Gang Application. The standard Depth Cover recommended for 16 gauge or lighter cord sets for vending machines, holiday lighting, landscape lighting and portable signs.

TECH TALK

Plastic In-Use Covers

Flexible and easy to install, "While in Use" Covers are ideal for single-gang, double-gang, horizontal and vertical outdoor applications in a wet location.

- Ensure compliance with Article 406.8(B)(1) of the National Electronic Code which states that 15 and 20 Ampere, 125 and 250 volt receptacles installed in a wet location shall have an enclosure that is weatherproof whether or not the attachment plug cap is inserted.
- Meets UL and CSA Cold Impact Testing at -60°F (-51°C)
- Clear UV Stabilized Polycarbonate Covers for long life in high abuse outdoor installations
- All Covers are shipped with gasket, mounting screws, base and cover assembly and two inserts
- Patented inserts for all wiring devices

