



PASS & SEYMOUR® UL Hospital Grade USB Chargers 15 & 20A, 125V

TR8200HUSB, TR8300HUSB

Charge ahead with the UL Hospital Grade USB duplex receptacle.

Pass & Seymour® Hospital Grade Tamper-Resistant Duplex Receptacles with USB Charging capabilities are designed with strength and durability in mind. They were designed for the healthcare market, and are capable of withstanding heavy use due to their UL Hospital Grade certification. This product features an improved overall 3.1A USB charging capability, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy.



FEATURES & BENEFITS

Overall 3.1A USB charging capability

Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices

AC receptacles available in 15 and 20 Amp, 125V

AC receptacles are tamper-resistant as standard - patented shutter system prevents improper insertion of foreign objects



TR8300HUSBW

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

Stainless steel auto-ground clips assure positive ground

FIELD USES/VERTICAL MARKETS

- Healthcare
- Education
- Institutional




PASS & SEYMOUR®

UL Hospital Grade USB Chargers

15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rating A	V	Color	NEMA Configuration No.
Duplex Tamper-Resistant Receptacle with USB Charger				
TR8200HUSB	15A	125V	Brown	5-15R
TR8200HUSBW	15A	125V	White	5-15R
TR8200HUSBLA	15A	125V	Light Almond	5-15R
TR8200HUSBI	15A	125V	Ivory	5-15R
TR8200HUSBBK	15A	125V	Black	5-15R
TR8200HUSBGRY	15A	125V	Gray	5-15R
TR8200HUSBRED	15A	125V	Red	5-15R
TR8200HUSBNI	15A	125V	Nickel-Plated	5-15R
TR8300HUSB	20A	125V	Brown	5-20R
TR8300HUSBW	20A	125V	White	5-20R
TR8300HUSBLA	20A	125V	Light Almond	5-20R
TR8300HUSBI	20A	125V	Ivory	5-20R
TR8300HUSBBK	20A	125V	Black	5-20R
TR8300HUSBGRY	20A	125V	Gray	5-20R
TR8300HUSBRED	20A	125V	Red	5-20R
TR8300HUSBNI	20A	125V	Nickel-Plated	5-20R



For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®

UL Hospital Grade USB Chargers

15 & 20A, 125V



TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, UL Fed Spec Listed
Complies with test requirements UL 498, UL 1310, Fed Spec WC596, CSA C22.2 No. 42, CSA C22.2 No. 223

Performance

Electrical


Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)

Mechanical

Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.
Product Identification	Ratings are permanent part of the device

Environmental

Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



Materials


Face	Polycarbonate
Body	Nylon
Contacts	CDA 260 Brass
Mounting Strap	.046" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate For Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel
Auto-Ground Clip	Stainless Steel

Warranty

1 Year


For more information on these and other P&S products refer to our Catalog or visit our web site.

COMPLEMENTARY DEVICES & ACCESSORIES




PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade



DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



GFCIs

- Specification Grade



WALL PLATES

- TradeMaster Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

ALSO AVAILABLE...

- | | | | |
|--------------------------------------|-------------------------------------|-------------------------------|----------------------------|
| ■ Hospital Grade Devices | ■ Straight Blade Plugs & Connectors | ■ Weatherproof Boxes & Covers | ■ Flexcor® Wire Mesh Grips |
| ■ SPD & Isolated Ground Devices | ■ Turnlok® Locking Devices | ■ IEC 309 Industrial Products | ■ Bulk Solutions |
| ■ Ground Continuity Monitoring (GCM) | | | |



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195
www.legrand.ca

