

■ TURNLOK® LOCKING DEVICES

Pass & Seymour

legrand®

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.

Clear thermoplastic terminal chamber for clear view of terminals and wire connections.

Exclusive external neoprene dust cover on 20 and 30A devices seals cable entry; optional weatherproof boots seal connection. (Sold separately, Cat.# DC-1.)

Exclusive, rugged integral cord grip accepts a wide range of cord widths, no external parts to snag or break off.

NEMA configurations always visible for fast I.D. without disconnecting.

L620-C and L620-P

Recessed cord-grip screw reduces screwdriver slippage, improves safety. Compatible with wire mesh strain reliefs.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Index

Receptacles, Connectors, Plugs, Inlets & Outlets

	Rating	Page Number
NEMA Configurations		H-4
Ground Continuity Monitoring	15, 20 & 30A, 125, 250, 277, 347 & 125/250V	H-5
2 Wire Non-Grounding	15A, 125V & 20A, 250V	H-6
3 Wire Grounding	15A, 125 & 250V, 277VAC	H-7, H-8
3 Wire Grounding	20A, 125 & 250V, 277VAC	H-9
3 Wire Grounding	20A, 347, 480 & 600V	H-10
3 Wire Grounding	30A, 125 & 250V, 277VAC	H-11
3 Wire Grounding	30A, 480 & 600V	H-12
3 Wire Grounding & Non-Grounding	10 & 15A, 125 & 250V; 20 & 30A, 125/250 & 250V	H-13
3 Wire Non-Grounding	20A, 125/250V; 3ø, 250 & 480V	H-14
3 Wire Non-Grounding	30A, 125/250V; 3ø, 250, 480 & 600V	H-15
4 Wire Grounding	20A, 125/250V; 3ø, 250 & 480V	H-16
4 Wire Grounding	30A, 125/250V; 3ø, 250, 480 & 600V	H-17
4 Wire Non-Grounding	20 & 30A, 3øY, 120/208VAC	H-18
4 Wire Non-Grounding	20A, 3øY, 120/208, 277/480 & 347/600V	H-19
4 Wire Non-Grounding	30A, 3øY, 120/208, 277/480 & 347/600V	H-20
5 Wire Grounding	20A, 3øY, 120/208, 277/480 & 347/600V	H-21
5 Wire Grounding	30A, 3øY, 120/208, 277/480 & 347/600V	H-22
Angle Devices	15A, 125 & 250V, 277VAC	H-23
Rubber & Watertight	15A, 125V, 277V	H-24
3 Wire Grounding	50A, 125, 250 & 480V; 250VDC, 600VAC	H-25
4 Wire Grounding	50A, 125/250V; 3ø, 250 & 480V; 250VDC, 600VAC	H-26
Midget 2 & 3 Wire Non-Grounding & 2 Wire Grounding	15A, 125 & 125/250V	H-27
3 Wire Power Interrupting	20A, 125V; 20A, 125V, 10A, 250VDC, 480VAC	H-28
4 Wire Power Interrupting	30A 480V; 30A, 600VAC, 20A, 250VDC; 60A, 600V	H-29
5 Wire Power Interrupting	30A, 600VAC, 20A, 250VDC; 60A, 600V	H-30
Accessories		H-31, H-32
Product Specifications & Performance, Horsepower Ratings		H-33 – H-39

Pass & Seymour



Turnlok® Locking Devices

High-strength, brass alloy blades resist heat rise; provide excellent conductivity.

Tri-drive assembly screws conveniently accept slotted, Phillips & Robertson screwdrivers.

Comes disassembled and ready-to-wire for quick installation.

Clear, high-impact-resistant thermoplastic terminal chamber for clear view of connection.

Double-wipe power contacts withstand work-site abuse and ensure lasting blade retention.


All-nylon exterior parts resist chemicals and impacts.

Rugged external two-piece cord grip provides uniform pressure for superior retention of conductors.

Keyed back body for quicker assembly.

Easy-grip contour molded into back body prevents hand slippage.

Internal dust shield to maintain contaminant-free terminations.




PSL515-P and PSL515-C

Interior components constructed of high-grade brass material for physical and electrical integrity.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

High-impact thermoplastic housing withstands on-the-job abuse.



4716-SS and 4715-SS

Turnlok® Locking Devices

Pass & Seymour



Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

Clearly marked NEMA configuration, rating, and third party listing on each unit's face.

One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Side and external screw-pressure-plate back wire capability.
Accepts #14 - #10 AWG.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

L620-R

2002 National Electrical Code® Section 406.3(F) Noninterchangeability. Receptacles, cord connectors, and attachment plugs shall be constructed so that receptacle or cord connectors will not accept an attachment plug with a different voltage or current rating than that for which the device is intended; however, a 20-ampere T-slot receptacle or cord connector shall be permitted to accept a 15-ampere attachment plug of the same voltage rating. Nongrounding-type receptacles and connectors shall not accept grounding-type attachment plugs.

Section 430.109(F): (Disconnecting Means) For a cord and plug connected motor, a horsepower rated attachment plug and receptacle having ratings no less than the motor ratings shall be permitted to serve as the disconnecting means.


Midget – Locking

		15 AMPERE	
		RECEPTACLE	PLUG
2 Pole, 2 Wire Non-Grounding			
125V	ML1		
125V		ML-1R	ML-1P
2 Pole, 3 Wire Grounding			
125V	ML2		
125V		ML-2R	ML-2P
3 Pole, 3 Wire Non-Grounding			
125/250V	ML3		
125/250V		ML-3R	ML-3P

Labels & Their Meaning

X, Y, Z	Hot Lead
W	Neutral Lead
G	Grounding Lead

Open Slots
Indicate receptacle configurations (female).



Closed Slots
Indicate plug blade configurations (male).




Locking Plugs & Receptacles

		15 AMPERE		20 AMPERE		30 AMPERE	
		RECEPTACLE	PLUG	RECEPTACLE	PLUG	RECEPTACLE	PLUG
2 Pole, 2 Wire Non-Grounding							
125V	L1						
125V		L1-15R	L1-15P				
250V	L2						
250V				L2-20R	L2-20P		
2 Pole, 3 Wire Grounding							
125V	L5						
125V		L5-15R	L5-15P	L5-20R	L5-20P	L5-30R	L5-30P
250V	L6						
250V		L6-15R	L6-15P	L6-20R	L6-20P	L6-30R	L6-30P
277VAC	L7						
277VAC		L7-15R	L7-15P	L7-20R	L7-20P	L7-30R	L7-30P
347VAC	L24						
347VAC				L24-20R	L24-20P		
480VAC	L8						
480VAC				L8-20R	L8-20P	L8-30R	L8-30P
600VAC	L9						
600VAC				L9-20R	L9-20P	L9-30R	L9-30P
3 Pole, 3 Wire Non-Grounding							
125/250V	L10						
125/250V				L10-20R	L10-20P	L10-30R	L10-30P
3ø250V	L11						
3ø250V				L11-20R	L11-20P	L11-30R	L11-30P
3ø480V	L12						
3ø480V				L12-20R	L12-20P	L12-30R	L12-30P
3ø600V	L13						
3ø600V						L13-30R	L13-30P
3 Pole, 4 Wire Grounding							
125/250V	L14						
125/250V				L14-20R	L14-20P	L14-30R	L14-30P
3ø250V	L15						
3ø250V				L15-20R	L15-20P	L15-30R	L15-30P
3ø480V	L16						
3ø480V				L16-20R	L16-20P	L16-30R	L16-30P
3ø600V	L17						
3ø600V						L17-30R	L17-30P
4 Pole, 4 Wire Non-Grounding							
3øY 120/208V	L18						
3øY 120/208V				L18-20R	L18-20P	L18-30R	L18-30P
3øY 277/480V	L19						
3øY 277/480V				L19-20R	L19-20P	L19-30R	L19-30P
3øY 347/600V	L20						
3øY 347/600V				L20-20R	L20-20P	L20-30R	L20-30P
4 Pole, 5 Wire Grounding							
3øY 120/208V	L21						
3øY 120/208V				L21-20R	L21-20P	L21-30R	L21-30P
3øY 277/480V	L22						
3øY 277/480V				L22-20R	L22-20P	L22-30R	L22-30P
3øY 347/600V	L23						
3øY 347/600V				L23-20R	L23-20P	L23-30R	L23-30P

Turnlok® Locking Devices Heavy-Duty Ground Continuity Monitoring (GCM) Plugs & Connectors

2 Pole, 3 Wire Grounding 15, 20 & 30A; 125, 250, 277 & 347V
3 Pole, 4 Wire Grounding 20 & 30A, 125/250V


Pass & Seymour



PSL15-PGCM






PSL15-CGCM



L620-PGCM



L620-CGCM



Features – Heavy-Duty Turnlok GCM

- Integral indication of ground continuity and power status. Continuous monitoring enhances personnel safety and adds convenience.
- Dual, bright LED indicators with 360° visibility. Green LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross. For 250V configurations: Hot to ground cross will be indicated by a green and red LED.
- NEMA configurations always visible for fast identification without disconnecting.
- Exclusive neoprene dust cover on devices seals cable entry. Optional weatherproof boots (sold separately).
- Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.
- Exclusive, rugged two-piece cord grip (15 Amp only) accepts a wide range of cord widths. Provides uniform pressure for superior retention of conductors.
- Recessed cord-grip screw reduces screwdriver slippage, improves safety. Quick-thread tri-drive assembly and cord-grip screws come backed-out and ready-to-wire.
- Color-coded terminal screws are backed-out for fast installation.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Catalog Number	Rating A. V.	Description	Cord Diameter	NEMA Config. No.	3rd Party Compliance	
					cULus	FSUL WC596
2 Pole, 3 Wire Grounding						
NEW PSL15-PGCM	15 125	Plug, Black & White	.230"-.720"	L5-15P	•	•
NEW PSL15-PGCMAN	15 125	Angled Plug, Black & White	.320"-.655"	L5-15P	•	•
NEW PSL15-CGCM	15 125	Connector, Black & White	.230"-.720"	L5-15R	•	•
L520-PGCM	20 125	Plug, Black & White	.385"-1.15"	L5-20P	•	•
L520-CGCM	20 125	Connector, Black & White	.385"-1.15"	L5-20R	•	•
L530-PGCM	30 125	Plug, Black & White	.385"-1.15"	L5-30P	•	•
L530-CGCM	30 125	Connector, Black & White	.385"-1.15"	L5-30R	•	•
NEW PSL615-PGCM	15 250	Plug, Black & White	.230"-.720"	L6-15P	•	•
NEW PSL615-PGCMAN	15 250	Angled Plug, Black & White	.320"-.655"	L6-15P	•	•
NEW PSL615-CGCM	15 250	Connector, Black & White	.230"-.720"	L6-15R	•	•
L620-PGCM	20 250	Plug, Black & White	.385"-1.15"	L6-20P	•	•
L620-CGCM	20 250	Connector, Black & White	.385"-1.15"	L6-20R	•	•
L630-PGCM	30 250	Plug, Black & White	.385"-1.15"	L6-30P	•	•
L630-CGCM	30 250	Connector, Black & White	.385"-1.15"	L6-30R	•	•
NEW PSL715-PGCM	15 277*	Plug, Black & White	.230"-.720"	L7-15P	•	•
NEW PSL715-PGCMAN	15 277*	Angled Plug, Black & White	.320"-.655"	L7-15P	•	•
NEW PSL715-CGCM	15 277*	Connector, Black & White	.230"-.720"	L7-15R	•	•
L720-PGCM	20 277*	Plug, Black & White	.385"-1.15"	L7-20P	•	•
L720-CGCM	20 277*	Connector, Black & White	.385"-1.15"	L7-20R	•	•
L730-PGCM	30 277*	Plug, Black & White	.385"-1.15"	L7-30P	•	•
L730-CGCM	30 277*	Connector, Black & White	.385"-1.15"	L7-30R	•	•
L3720-PGCM	20 347	Plug, Black & White	.385"-1.15"	L24-20P	•	•
L3720-CGCM	20 347	Connector, Black & White	.385"-1.15"	L24-20R	•	•
3 Pole, 4 Wire Grounding						
L1420-PGCM	20 125/250	Plug, Black & White	.385"-1.15"	L14-20P	•	•
L1420-CGCM	20 125/250	Connector, Black & White	.385"-1.15"	L14-20R	•	•
L1430-PGCM	30 125/250	Plug, Black & White	.385"-1.15"	L14-30P	•	•
L1430-CGCM	30 125/250	Connector, Black & White	.385"-1.15"	L14-30R	•	•

*AC only.



All devices listed on this page conform to NEMA WD-1 and WD-6.

H-5


Pass & Seymour




Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets


2 Wire Non-Grounding 15A, 125V & 20A, 250V




7535



7210



L0116




7526




7506



7101



7547-DF




7102

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
7535	15 125	Single Receptacle		L1-15R			•
L0116	15 125	Duplex Receptacle		L1-15R			•
7210	20 250	Single Receptacle		L2-20R			•
Connectors							
7506*	15 125	Black	.296"-.562"	L1-15R			•
7101*	20 250	Black Back, White Front Body	.296"-.562"	L2-20R			•
Plugs							
7547-DF	15 125	Black	.296"-.625"	L1-15P			•
7102*	20 250	Black Back, White Front Body	.296"-.562"	L2-20P			•
Flanged Inlets & Outlets							
L0115	15 125	Flanged Inlet		L1-15P			•
7526	15 125	Flanged Outlet		L1-15R			•

* For replacement use only.
Reference Pages H-31 and H-32 for Accessories.

2 Pole, 2 Wire



Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets

3 Wire Grounding 15A, 125V



Pass & Seymour




Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets


Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL UL498	FSUL WC596	CSA
Receptacles							
4710	15 125	Single Receptacle		L5-15R	•	•	•
IG4710	15 125	Single Receptacle, Orange		L5-15R	•	•	•
4700	15 125	Duplex Receptacle		L5-15R	•	•	•
IG4700	15 125	Duplex Receptacle, Orange		L5-15R	•	•	•
4792	15 125	Combination Straight Blade and Locking		5-15R and L5-15R	•	•	•
Connectors IP20 Suitability							
NEW PSL515-C	15 125	Black Back, White Front Body	.230"-.720"	L5-15R	•	•	•
CRL515-C	15 125	Corrosion Resistant Yellow Back, White Front Body	.230"-.720"	L5-15R	•	•	•
Plugs IP20 Suitability							
NEW PSL515-P	15 125	Black Back, White Front Body	.230"-.720"	L5-15P	•	•	•
CRL515-P	15 125	Corrosion Resistant, Yellow Back, White Front Body	.230"-.720"	L5-15P	•	•	•
4720-SSAN	15 125	Angled Plug, Black Back, White Front Body	.320"-.655"	L5-15P	•	•	•
Flanged Inlets & Outlets							
4716-SS	15 125	Flanged Inlet		L5-15P	•	•	•
4715-SS	15 125	Flanged Outlet		L5-15R	•	•	•
Straight Blade/Locking Adapters							
44829	15 125	High-Visibility Yellow		L5-15R/5-15P			
44859	15 125	High-Visibility Yellow		5-15R/L5-15P			




15A Connector



4715-SS



15A Plug



4716-SS

2 Pole, 3 Wire



NEMA L5-15R



NEMA L5-15P



NEMA 5-15R



NEMA 5-15P


All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour




Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


3 Wire Grounding 15A, 250V & 277VAC




4560



4550



4760



4750

NEW


NEW

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
4560	15 250	Single Receptacle		L6-15R	•		
4550†	15 250	Duplex Receptacle		L6-15R	•		
4760	15 277*	Single Receptacle		L7-15R	•		•
IG4760	15 277*	Single Receptacle, Orange		L7-15R	•		•
4750	15 277*	Duplex Receptacle		L7-15R	•		•
Connectors IP20 Suitability							
PSL615-C	15 250	Black Back, White Front Body	.230"-.720"	L6-15R	•	•	•
PSL715-C	15 277*	Black Back, White Front Body	.230"-.720"	L7-15R	•	•	•
Plugs IP20 Suitability							
PSL615-P	15 250	Black Back, White Front Body	.230"-.720"	L6-15P	•	•	•
PSL615-PAN	15 250	Angled Plug, Black Back, White Front Body	.320"-.655"	L6-15P	•		
PSL715-P	15 277*	Black Back, White Front Body	.230"-.720"	L7-15P	•	•	•
PSL715-PAN	15 277*	Angled Plug, Black Back, White Front Body	.320"-.655"	L7-15P	•		
Flanged Inlets & Outlets							
615	15 250	Flanged Inlet, Gray		L6-15P			
614	15 250	Flanged Outlet, Gray		L6-15R			
L0715	15 277*	Flanged Inlet, Gray		L7-15P			
L0714	15 277*	Flanged Outlet, Gray		L7-15R			


*AC only.

†Not designed for split circuits.

Reference Pages H-31 and H-32 for Accessories.



15A Connector



15A Plug

2 Pole, 3 Wire



NEMA L6-15R



NEMA L6-15P



NEMA L7-15R



NEMA L7-15P

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

3 Wire Grounding 20A, 125 & 250V, 277VAC

Pass & Seymour



Turnlok® Locking Devices



Receptacles, Connectors, Plugs, Inlets, Outlets

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L520-R	20 125	Single Receptacle		L5-20R	•	•	•
IGL520-R	20 125	Single Receptacle, Orange		L5-20R	•	•	•
CRL520-R	20 125	Single Receptacle, Corrosion-Resistant		L5-20R	•	•	•
L620-R	20 250	Single Receptacle		L6-20R	•	•	•
IGL620-R	20 250	Single Receptacle, Orange		L6-20R	•	•	•
L720-R	20 277*	Single Receptacle		L7-20R	•	•	•
IGL720-R	20 277*	Single Receptacle, Orange		L7-20R	•	•	•
Connectors IP20 Suitability							
L520-C	20 125	Black Back, White Front Body	.385"-1.150"	L5-20R	•	•	•
L520-CBK	20 125	Black Back, Black Front Body	.385"-1.150"	L5-20R	•	•	•
CRL520-C	20 125	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L5-20R	•	•	•
L620-C	20 250	Black Back, White Front Body	.385"-1.150"	L6-20R	•	•	•
CRL620-C	20 250	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L6-20R	•	•	•
L720-C	20 277*	Black Back, White Front Body	.385"-1.150"	L7-20R	•	•	•
Plugs IP20 Suitability							
L520-P	20 125	Black Back, White Front Body	.385"-1.150"	L5-20P	•	•	•
L520-PBK	20 125	Black Back, Black Front Body	.385"-1.150"	L5-20P	•	•	•
CRL520-P	20 125	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L5-20P	•	•	•
L620-P	20 250	Black Back, White Front Body	.385"-1.150"	L6-20P	•	•	•
CRL620-P	20 250	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L6-20P	•	•	•
L720-P	20 277*	Black Back, White Front Body	.385"-1.150"	L7-20P	•	•	•
Flanged Inlets & Outlets							
L520-FI	20 125	Gray Inlet		L5-20P	•	•	•
L520-FO	20 125	Gray Outlet		L5-20R	•	•	•
L620-FI	20 250	Gray Inlet		L6-20P	•	•	•
L620-FO	20 250	Gray Outlet		L6-20R	•	•	•
L720-FI	20 277*	Gray Inlet		L7-20P	•	•	•
L720-FO	20 277*	Gray Outlet		L7-20R	•	•	•


*AC only.

Reference Pages H-31 and H-32 for Accessories.


2 Pole, 3 Wire




20A Receptacle




20A Connector



20A Plug



L520, L620, L720-FI




L520, L620, L720-FO


All devices listed on this page conform to NEMA WD-1 and WD-6.

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


3 Wire Grounding 20A, 347, 480 & 600V




20A Receptacle




20A Connector



20A Plug



L820, L920-FI



L820, L920-FO

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L820-R	20 480	Single Receptacle		L8-20R	•	•	
IgL820-R	20 480	Single Receptacle, Orange		L8-20R	•	•	
L920-R	20 600	Single Receptacle		L9-20R	•	•	
L3720-R	20 347	Single Receptacle		L24-20R	•	•	
Connectors IP20 Suitability							
L820-C	20 480	Black Back, White Front Body	.385"-1.150"	L8-20R	•	•	
L920-C	20 600	Black Back, White Front Body	.385"-1.150"	L9-20R	•	•	
L3720-C	20 347	Black Back, White Front Body	.385"-1.150"	L24-20R	•	•	
Plugs IP20 Suitability							
L820-P	20 480	Black Back, White Front Body	.385"-1.150"	L8-20P	•	•	
L920-P	20 600	Black Back, White Front Body	.385"-1.150"	L9-20P	•	•	
L3720-P	20 347	Black Back, White Front Body	.385"-1.150"	L24-20P	•	•	
Flanged Inlets & Outlets							
L820-FI	20 480	Gray Inlet		L8-20P	•	•	
L820-FO	20 480	Gray Outlet		L8-20R	•	•	
L920-FI	20 600	Gray Inlet		L9-20P	•	•	
L920-FO	20 600	Gray Outlet		L9-20R	•	•	
L3720-FO	20 347	Gray Outlet		L24-20R	•	•	

Reference Pages H-31 and H-32 for Accessories.

2 Pole, 3 Wire



Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets

3 Wire Grounding 30A, 125 & 250V, 277VAC

Pass & Seymour





Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets


Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L530-R	30 125	Single Receptacle		L5-30R	•	•	•
IGL530-R	30 125	Single Receptacle, Orange		L5-30R	•	•	•
CRL530-R	30 125	Single Receptacle, Corrosion-Resistant		L5-30R	•	•	•
L630-R	30 250	Single Receptacle		L6-30R	•	•	•
IGL630-R	30 250	Single Receptacle, Orange		L6-30R	•	•	•
L730-R	30 277*	Single Receptacle		L7-30R	•	•	•
Connectors IP20 Suitability							
L530-C	30 125	Black Back, White Front Body	.385"-1.150"	L5-30R	•	•	•
L530-CBK	30 125	Black Back, Black Front Body	.385"-1.150"	L5-30R	•	•	•
CRL530-C	30 125	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L5-30R	•	•	•
L630-C	30 250	Black Back, White Front Body	.385"-1.150"	L6-30R	•	•	•
CRL630-C	30 250	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L6-30R	•	•	•
L730-C	30 277*	Black Back, White Front Body	.385"-1.150"	L7-30R	•	•	•
Plugs IP20 Suitability							
L530-P	30 125	Black Back, White Front Body	.385"-1.150"	L5-30P	•	•	•
L530-PBK	30 125	Black Back, Black Front Body	.385"-1.150"	L5-30P	•	•	•
CRL530-P	30 125	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L5-30P	•	•	•
L630-P	30 250	Black Back, White Front Body	.385"-1.150"	L6-30P	•	•	•
CRL630-P	30 250	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L6-30P	•	•	•
L730-P	30 277*	Black Back, White Front Body	.385"-1.150"	L7-30P	•	•	•
Flanged Inlets & Outlets							
L530-FI	30 125	Gray Inlet		L5-30P	•	•	•
L530-FO	30 125	Gray Outlet		L5-30R	•	•	•
L630-FI	30 250	Gray Inlet		L6-30P	•	•	•
L630-FO	30 250	Gray Outlet		L6-30R	•	•	•
L730-FI	30 277*	Gray Inlet		L7-30P	•	•	•
L730-FO	30 277*	Gray Outlet		L7-30R	•	•	•

*AC only.


Reference Pages H-31 and H-32 for Accessories.




30A Receptacle




30A Connector



30A Plug



L530, L630, L730-FI




L530, L630, L730-FO


All devices listed on this page conform to NEMA WD-1 and WD-6.

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


3 Wire Grounding 30A, 480 & 600V




30A Receptacle




30A Connector



30A Plug



L830, L930-FI




L830, L930-FO

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L830-R	30 480	Single Receptacle		L8-30R	•	•	•
L930-R	30 600	Single Receptacle		L9-30R	•	•	•
Connectors IP20 Suitability							
L830-C	30 480	Black Back, White Front Body	.385"-1.150"	L8-30R	•	•	•
L930-C	30 600	Black Back, White Front Body	.385"-1.150"	L9-30R	•	•	•
Plugs IP20 Suitability							
L830-P	30 480	Black Back, White Front Body,	.385"-1.150"	L8-30P	•	•	•
L930-P	30 600	Black Back, White Front Body	.385"-1.150"	L9-30P	•	•	•
Flanged Inlets & Outlets							
L830-FI	30 480	Gray Inlet		L8-30P	•		•
L830-FO	30 480	Gray Outlet		L8-30R	•		•
L930-FI	30 600	Gray Inlet		L9-30P	•		•
L930-FO	30 600	Gray Outlet		L9-30R	•		•

Reference Pages H-31 and H-32 for Accessories.

2 Pole, 3 Wire



NEMA L8-30R

NEMA L8-30P

NEMA L9-30R

NEMA L9-30P

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

3 Wire Grounding & Non-Grounding
10 & 15A, 125 & 250V; 20 & 30A, 125/250 & 250V

Pass & Seymour




Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets


Catalog Number	Rating		Description/Color	Cord Diameter	3rd Party Compliance		
	A.	V.			UL UL498	FSUL WC596	CSA
Receptacles							
7582*	15	125	Single Receptacle				
7580	15	125	Duplex Receptacle				
7580-G	15	125	Duplex Receptacle, Grounding				
7310*	20	125/250	Single Receptacle				
3330	30	125/250	Single Receptacle				
3330-G	30	125/250	Single Receptacle, Grounding				
Connectors IP20 Suitability							
7555-SS*	15	125	Yellow	.296"-.625"			
7555-G	15	125	High-Visibility Yellow	.280"-.710"			
7313-SS	20	125/250	Black Back, White Front Body	.385"-1.150"	•	•	•
7313-SSBK	20	125/250	Black Back, Black Front Body	.385"-1.150"	•	•	•
3333-SS	30	125/250	Black Back, White Front Body	.385"-1.150"	•	•	•
Plugs IP20 Suitability							
S2348-DF	14	125-480	Black Back, White Front Body				
7554-SS*	15	125	Yellow	.296"-.625"			
7572-G	15	125	High-Visibility Yellow, Grounding	.280"-.710"			
7311-SS	20	125/250	Black Back, White Front Body	.385"-1.150"	•	•	•
7311-SSBK	20	125/250	Black Back, Black Front Body	.385"-1.150"	•	•	•
7311-G	20	250	High-Visibility Yellow, Grounding	.410"-1.060"			
3331-SS	30	125/250	Black Back, White Front Body	.385"-1.150"	•	•	•
3331-G	30	250	High-Visibility Yellow, Grounding	.410"-1.060"			
Flanged Inlets & Outlets							
S2347	14	125-480	Outlet				
7556-SS*	15	125	Gray Inlet				
7557-SS*	15	125	Gray Outlet				
3334-SS	30	125/250	Gray Inlet		•		
3335-SS	30	125/250	Gray Outlet		•		

*For replacement use only.


Reference Pages H-31 and H-32 for Accessories.




7582





7580-G




7555-SS



7554-SS



7556-SS




7557-SS


All devices listed on this page conform to NEMA WD-1 and WD-6.

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


3 Wire Non-Grounding 20A, 125/250V; 3ø, 250 & 480V




20A Receptacle




20A Connector



20A Plug



L1020, L1120, L1220-FI




L1020, L1120, L1220-FO

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L1020-R	20 125/250	Single Receptacle		L10-20R	•	•	
L1120-R	20 3ø, 250	Single Receptacle		L11-20R	•	•	
L1220-R	20 3ø, 480	Single Receptacle		L12-20R	•	•	
Connectors IP20 Suitability							
L1020-C	20 125/250	Black Back, White Front Body	.385"-1.150"	L10-20R	•	•	•
L1120-C	20 3ø, 250	Black Back, White Front Body	.385"-1.150"	L11-20R	•	•	•
L1220-C	20 3ø, 480	Black Back, White Front Body	.385"-1.150"	L12-20R	•	•	•
Plugs IP20 Suitability							
L1020-P	20 125/250	Black Back, White Front Body	.385"-1.150"	L10-20P	•	•	•
L1120-P	20 3ø, 250	Black Back, White Front Body	.385"-1.150"	L11-20P	•	•	•
L1220-P	20 3ø, 480	Black Back, White Front Body	.385"-1.150"	L12-20P	•	•	•
Flanged Inlets & Outlets							
L1020-FI	20 125/250	Gray Inlet		L10-20P	•		•
L1020-FO	20 125/250	Gray Outlet		L10-20R	•		
L1120-FI	20 3ø, 250	Gray Inlet		L11-20P	•		•
L1120-FO	20 3ø, 250	Gray Outlet		L11-20R	•		
L1220-FI	20 3ø, 480	Gray Inlet		L12-20P	•		•
L1220-FO	20 3ø, 480	Gray Outlet		L12-20R	•		

Reference Pages H-31 and H-32 for Accessories.

3 Pole, 3 Wire



Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

3 Wire Non-Grounding 30A, 125/250V; 3ø, 250, 480 & 600V

Pass & Seymour





Turnlok® Locking Devices


Receptacles, Connectors, Plugs, Inlets, Outlets

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L1030-R	30 125/250	Single Receptacle		L10-30R	•	•	
L1130-R	30 3ø, 250	Single Receptacle		L11-30R	•	•	
L1230-R	30 3ø, 480	Single Receptacle		L12-30R	•	•	
L1330-R	30 3ø, 600	Single Receptacle		L13-30R	•	•	
Connectors IP20 Suitability							
L1030-C	30 125/250	Black Back, White Front Body	.385"-1.150"	L10-30R	•	•	
L1130-C	30 3ø, 250	Black Back, White Front Body	.385"-1.150"	L11-30R	•	•	•
L1230-C	30 3ø, 480	Black Back, White Front Body	.385"-1.150"	L12-30R	•	•	•
L1330-C	30 3ø, 600	Black Back, White Front Body	.385"-1.150"	L13-30R	•	•	•
Plugs IP20 Suitability							
L1030-P	30 125/250	Black Back, White Front Body	.385"-1.150"	L10-30P	•	•	
L1130-P	30 3ø, 250	Black Back, White Front Body	.385"-1.150"	L11-30P	•	•	•
L1230-P	30 3ø, 480	Black Back, White Front Body	.385"-1.150"	L12-30P	•	•	•
L1330-P	30 3ø, 600	Black Back, White Front Body	.385"-1.150"	L13-30P	•	•	•
Flanged Inlets and Outlets							
L1030-FI	30 125/250	Gray Inlet		L10-30P	•		
L1030-FO	30 125/250	Gray Outlet		L10-30R	•		
L1130-FI	30 3ø, 250	Gray Inlet		L11-30P	•		
L1130-FO	30 3ø, 250	Gray Outlet		L11-30R	•		
L1230-FI	30 3ø, 480	Gray Inlet		L12-30P	•		
L1230-FO	30 3ø, 480	Gray Outlet		L12-30R	•		
L1330-FI	30 3ø, 600	Gray Inlet		L13-30P	•		
L1330-FO	30 3ø, 600	Gray Outlet		L13-30R	•		


Reference Pages H-31 and H-32 for Accessories.




30A Receptacle




30A Connector



30A Plug



L1030, L1130, L1230
L1330-FI



L1030, L1130, L1230
L1330-FO


All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour




Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


4 Wire Grounding 20A, 125/250V; 3ø, 250 & 480V




20A Receptacle




20A Connector



20A Plug



L1420, L1520, L1620-FI



L1420, L1520, L1620-FO

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L1420-R	20 125/250	Single Receptacle		L14-20R	•	•	•
IGL1420-R	20 125/250	Single Receptacle, Orange		L14-20R	•		•
L1520-R	20 3ø, 250	Single Receptacle		L15-20R	•	•	•
IGL1520-R	20 3ø, 250	Single Receptacle, Orange		L15-20R	•		•
L1620-R	20 3ø, 480	Single Receptacle		L16-20R	•	•	•
IGL1620-R	20 3ø, 480	Single Receptacle, Orange		L16-20R	•		•
Connectors IP20 Suitability							
L1420-C	20 125/250	Black Back, White Front Body	.385"-1.150"	L14-20R	•	•	•
CRL1420-C	20 125/250	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L14-20R	•	•	•
L1520-C	20 3ø, 250	Black Back, White Front Body	.385"-1.150"	L15-20R	•	•	•
L1520-CBK	20 3ø, 250	Black Back, Black Front Body	.385"-1.150"	L15-20R	•	•	•
L1620-C	20 3ø, 480	Black Back, White Front Body	.385"-1.150"	L16-20R	•	•	•
Plugs IP20 Suitability							
L1420-P	20 125/250	Black Back, White Front Body,	.385"-1.150"	L14-20P	•	•	•
CRL1420-P	20 125/250	Corrosion-Resistant Yellow Back, White Front Body	.385"-1.150"	L14-20P	•	•	•
L1520-P	20 3ø, 250	Black Back, White Front Body	.385"-1.150"	L15-20P	•	•	•
L1520-PBK	20 3ø, 250	Black Back, Black Front Body	.385"-1.150"	L15-20P	•	•	•
L1620-P	20 3ø, 480	Black Back, White Front Body	.385"-1.150"	L16-20P	•	•	•
Flanged Inlets & Outlets							
L1420-FI	20 125/250	Gray Inlet		L14-20P	•		•
L1420-FO	20 125/250	Gray Outlet		L14-20R	•		•
L1520-FI	20 3ø, 250	Gray Inlet		L15-20P	•		•
L1520-FIBK	20 3ø, 250	Black Inlet		L15-20P	•		•
L1520-FO	20 3ø, 250	Gray Outlet		L15-20R	•		•
L1520-FOBK	20 3ø, 250	Black Outlet		L15-20R	•		•
L1620-FI	20 3ø, 480	Gray Inlet		L16-20P	•		•
L1620-FO	20 3ø, 480	Gray Outlet		L16-20R	•		•

Reference Pages H-31 and H-32 for Accessories.

3 Pole, 4 Wire



NEMA L14-20R



NEMA L14-20P



NEMA L15-20R



NEMA L15-20P



NEMA L16-20R



NEMA L16-20P

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

4 Wire Grounding 30A, 125/250V; 3ø, 250, 480 & 600V

Pass & Seymour





Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets


Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L1430-R	30 125/250	Single Receptacle		L14-30R	•	•	•
IGL1430-R	30 125/250	Single Receptacle, Orange		L14-30R	•	•	•
L1530-R	30 3ø, 250	Single Receptacle		L15-30R	•	•	•
IGL1530-R	30 3ø, 250	Single Receptacle, Orange		L15-30R	•	•	•
L1630-R	30 3ø, 480	Single Receptacle		L16-30R	•	•	•
L1730-R	30 3ø, 600	Single Receptacle		L17-30R	•	•	•
Connectors IP20 Suitability							
L1430-C	30 125/250	Black Back, White Front Body	.385"-1.150"	L14-30R	•	•	•
CRL1430-C	30 125/250	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L14-30R	•	•	•
L1530-C	30 3ø, 250	Black Back, White Front Body	.385"-1.150"	L15-30R	•	•	•
L1530-CBK	30 3ø, 250	Black Back, Black Front Body	.385"-1.150"	L15-30R	•	•	•
L1630-C	30 3ø, 480	Black Back, White Front Body	.385"-1.150"	L16-30R	•	•	•
L1730-C	30 3ø, 600	Black Back, White Front Body	.385"-1.150"	L17-30R	•	•	•
Plugs IP20 Suitability							
L1430-P	30 125/250	Black Back, White Front Body	.385"-1.150"	L14-30P	•	•	•
CRL1430-P	30 125/250	Corrosion-Resistant, Yellow Back, White Front Body	.385"-1.150"	L14-30P	•	•	•
L1530-P	30 3ø, 250	Black Back, White Front Body	.385"-1.150"	L15-30P	•	•	•
L1530-PBK	30 3ø, 250	Black Back, Black Front Body	.385"-1.150"	L15-30P	•	•	•
L1630-P	30 3ø, 480	Black Back, White Front Body	.385"-1.150"	L16-30P	•	•	•
L1730-P	30 3ø, 600	Black Back, White Front Body	.385"-1.150"	L17-30P	•	•	•
Flanged Inlets & Outlets							
L1430-FI	30 125/250	Gray Inlet		L14-30P	•	•	•
L1430-FO	30 125/250	Gray Outlet		L14-30R	•	•	•
L1530-FI	30 3ø, 250	Gray Inlet		L15-30P	•	•	•
L1530-FIBK	30 3ø, 250	Black Inlet		L15-30P	•	•	•
L1530-FO	30 3ø, 250	Gray Outlet		L15-30R	•	•	•
L1530-FOBK	30 3ø, 250	Black Outlet		L15-30R	•	•	•
L1630-FI	30 3ø, 480	Gray Inlet		L16-30P	•	•	•
L1630-FO	30 3ø, 480	Gray Outlet		L16-30R	•	•	•
L1730-FI	30 3ø, 600	Gray Inlet		L17-30P	•	•	•
L1730-FO	30 3ø, 600	Gray Outlet		L17-30R	•	•	•

Reference Pages H-31 and H-32 for Accessories.


3 Pole, 4 Wire




30A Receptacle




30A Connector



30A Plug




L1430, L1530, L1630
L1730-FI



L1430, L1530, L1630
L1730-FO

All devices listed on this page conform to NEMA WD-1 and WD-6.


Pass & Seymour




7410 Series
3430 Series




20 & 30A Connector



20 & 30A Plug



7408-SS
3434-SS



7409-SS
3435-SS

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

4 Pole, 4 Wire Non-Grounding 20 & 30A, 3øY 120/208V

3 Pole, 4 Wire Grounding 20 & 30A, 3øY, 250V; 10 & 30A, 600V

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	3rd Party Compliance		
				UL498	FSUL WC596	CSA
Receptacles						
7410	20 3øY, 120/208	Single Receptacle		•	•	
7410-G*	20 3øY, 250 10 600	Single Receptacle, Grounded				•
3430	30 3øY, 120/208	Single Receptacle		•	•	
3430-G*	30 3øY, 250 10 600	Single Receptacle, Grounded				•
Connectors IP20 Suitability						
7413-SS	20 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	•	•	
7413-G*	20 3øY, 250 10 600	High-Visibility Yellow	.333"-1.060"			
3433-SS	30 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	•	•	
Plugs IP20 Suitability						
7411-SS	20 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	•	•	
7411-G*	20 3øY, 250 10 600	High-Visibility Yellow	.333"-1.060"			
3431-SS	30 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	•	•	
3431-G*	30 3øY, 250 30 600	High-Visibility Yellow	.333"-1.060"			
Flanged Inlets & Outlets						
7408-SS	20 3øY, 120/208	Gray Inlet				•
7409-SS	20 3øY, 120/208	Gray Outlet				•
3434-SS	30 3øY, 120/208	Gray Inlet				•
3435-SS	30 3øY, 120/208	Gray Outlet				•

*For replacement use only.
Reference Pages H-31 and H-32 for Accessories.

4 Pole, 4 Wire



NON-NEMA
7409-SS, 7410
7413-SS



NON-NEMA
7408-SS
7411-SS



NON-NEMA
3430, 3433-SS
3435-SS



NON-NEMA
3431-SS
3434-SS

3 Pole, 4 Wire



NON-NEMA
7410-G
7413-G



NON-NEMA
7411-G



NON-NEMA
3430-G
3433-G



NON-NEMA
3431-G

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

4 Wire Non-Grounding 20A, 3øY, 120/208, 277/480 & 347/600V

Pass & Seymour





Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets


Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL UL498	FSUL WC596	CSA
Receptacles							
L1820-R	20 3øY, 120/208	Single Receptacle		L18-20R	•	•	
L1920-R	20 3øY, 277/480	Single Receptacle		L19-20R	•	•	
L2020-R	20 3øY, 347/600	Single Receptacle		L20-20R	•	•	
Connectors IP20 Suitability							
L1820-C	20 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L18-20R	•	•	•
L1920-C	20 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L19-20R	•	•	•
L2020-C	20 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L20-20R	•	•	•
Plugs IP20 Suitability							
L1820-P	20 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L18-20P	•	•	•
L1920-P	20 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L19-20P	•	•	•
L2020-P	20 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L20-20P	•	•	•
Flanged Inlets & Outlets							
L1820-FI	20 3øY, 120/208	Gray Inlet		L18-20P	•	•	•
L1820-FO	20 3øY, 120/208	Gray Outlet		L18-20R	•	•	•
L1920-FI	20 3øY, 277/480	Gray Inlet		L19-20P	•	•	•
L1920-FO	20 3øY, 277/480	Gray Outlet		L19-20R	•	•	•
L2020-FI	20 3øY, 347/600	Gray Inlet		L20-20P	•	•	•
L2020-FO	20 3øY, 347/600	Gray Outlet		L20-20R	•	•	•

Reference Pages H-31 and H-32 for Accessories.


4 Pole, 4 Wire




20A Receptacle




20A Connector



20A Plug



L1820, L1920, L2020-FI




L1820, L1920, L2020-FO

All devices listed on this page conform to NEMA WD-1 and WD-6.

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


4 Wire Non-Grounding 30A, 3øY, 120/208, 277/480 & 347/600V




30A Receptacle




30A Connector



30A Plug



L1830, L1930, L2030-FI



L1830, L1930, L2030-FO

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L1830-R	30 3øY, 120/208	Single Receptacle		L18-30R	•		
L1930-R	30 3øY, 277/480	Single Receptacle		L19-30R	•		
L2030-R	30 3øY, 347/600	Single Receptacle		L20-30R	•		
Connectors IP20 Suitability							
L1830-C	30 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L18-30R	•		
L1930-C	30 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L19-30R	•		
L2030-C	30 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L20-30R	•		
Plugs IP20 Suitability							
L1830-P	30 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L18-30P	•		
L1930-P	30 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L19-30P	•		
L2030-P	30 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L20-30P	•		
Flanged Inlets & Outlets							
L1830-FI	30 3øY, 120/208	Gray Inlet		L18-30P	•		
L1830-FO	30 3øY, 120/208	Gray Outlet		L18-30R	•		
L1930-FI	30 3øY, 277/480	Gray Inlet		L19-30P	•		
L1930-FO	30 3øY, 277/480	Gray Outlet		L19-30R	•		
L2030-FI	30 3øY, 347/600	Gray Inlet		L20-30P	•		
L2030-FO	30 3øY, 347/600	Gray Outlet		L20-30R	•		

Reference Pages H-31 and H-32 for Accessories.

4 Pole, 4 Wire



NEMA L18-30R



NEMA L18-30P



NEMA L19-30R



NEMA L19-30P



NEMA L20-30R



NEMA L20-30P

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

5 Wire Grounding 20A, 3øY, 120/208, 277/480 & 347/600V

Pass & Seymour





Turnlok® Locking Devices


Receptacles, Connectors, Plugs, Inlets, Outlets

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	CSA
Receptacles							
L2120-R	20 3øY, 120/208	Single Receptacle		L21-20R	•	•	•
IGL2120-R	20 3øY, 120/208	Single Receptacle, Orange		L21-20R	•	•	•
L2220-R	20 3øY, 277/480	Single Receptacle		L22-20R	•	•	•
IGL2220-R	20 3øY, 277/480	Single Receptacle, Orange		L21-20R	•	•	•
L2320-R	20 3øY, 347/600	Single Receptacle		L23-20R	•	•	•
IGL2320-R	20 3øY, 347/600	Single Receptacle, Orange		L23-20R	•	•	•
Connectors IP20 Suitability							
L2120-C	20 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L21-20R	•	•	•
L2220-C	20 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L22-20R	•	•	•
L2220-CBK	20 3øY, 277/480	Black Back, Black Front Body	.385"-1.150"	L22-20R	•	•	•
L2320-C	20 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L23-20R	•	•	•
Plugs IP20 Suitability							
L2120-P	20 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L21-20P	•	•	•
L2220-P	20 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L22-20P	•	•	•
L2220-PBK	20 3øY, 277/480	Black Back, Black Front Body	.385"-1.150"	L22-20P	•	•	•
L2320-P	20 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L23-20P	•	•	•
Flanged Inlets & Outlets							
L2120-FI	20 3øY, 120/208	Gray Inlet		L21-20P	•	•	•
L2120-FO	20 3øY, 120/208	Gray Outlet		L21-20R	•	•	•
L2220-FI	20 3øY, 277/480	Gray Inlet		L22-20P	•	•	•
L2220-FIBK	20 3øY, 277/480	Black Inlet		L22-20P	•	•	•
L2220-FO	20 3øY, 277/480	Gray Outlet		L22-20R	•	•	•
L2220-FOBK	20 3øY, 277/480	Black Outlet		L22-20R	•	•	•
L2320-FI	20 3øY, 347/600	Gray Inlet		L23-20P	•	•	•
L2320-FO	20 3øY, 347/600	Gray Outlet		L23-20R	•	•	•


Reference Pages H-31 and H-32 for Accessories.




20A Receptacle




20A Connector



20A Plug



L2120, L2220, L2320-FI



L2120, L2220, L2320-FO


All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


5 Wire Grounding 30A, 3øY, 120/208, 277/480 & 347/600V




30A Receptacle




30A Connector



30A Plug



L2130, L2230, L2330-FI



L2130, L2230, L2330-FO

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL UL498	FSUL WC596	CSA
Receptacles							
L2130-R	30 3øY, 120/208	Single Receptacle		L21-30R	•	•	•
IGL2130-R	30 3øY, 120/208	Single Receptacle, Orange		L21-30R	•		•
L2230-R	30 3øY, 277/480	Single Receptacle		L22-30R	•	•	•
IGL2230-R	30 3øY, 277/480	Single Receptacle, Orange		L22-30R	•		•
L2330-R	30 3øY, 347/600	Single Receptacle		L23-30R	•	•	•
IGL2330-R	30 3øY, 347/600	Single Receptacle, Orange		L23-30R	•		•
Connectors IP20 Suitability							
L2130-C	30 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L21-30R	•	•	•
L2230-C	30 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L22-30R	•	•	•
L2230-CBK	30 3øY, 277/480	Black Back, Black Front Body	.385"-1.150"	L22-30R	•	•	•
L2330-C	30 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L23-30R	•	•	•
Plugs IP20 Suitability							
L2130-P	30 3øY, 120/208	Black Back, White Front Body	.385"-1.150"	L21-30P	•	•	•
L2230-P	30 3øY, 277/480	Black Back, White Front Body	.385"-1.150"	L22-30P	•	•	•
L2230-PBK	30 3øY, 277/480	Black Back, Black Front Body	.385"-1.150"	L22-30P	•	•	•
L2330-P	30 3øY, 347/600	Black Back, White Front Body	.385"-1.150"	L23-30P	•	•	•
Flanged Inlets & Outlets							
L2130-FI	30 3øY, 120/208	Gray Inlet		L21-30P	•		•
L2130-FO	30 3øY, 120/208	Gray Outlet		L21-30R	•		•
L2230-FI	30 3øY, 277/480	Gray Inlet		L22-30P	•		•
L2230-FIBK	30 3øY, 277/480	Black Inlet		L22-30P	•		•
L2230-FO	30 3øY, 277/480	Gray Outlet		L22-30R	•		•
L2230-FOBK	30 3øY, 277/480	Black Outlet		L22-30R	•		•
L2330-FI	30 3øY, 347/600	Gray Inlet		L23-30P	•		•
L2330-FO	30 3øY, 347/600	Gray Outlet		L23-30R	•		•

Reference Pages H-31 and H-32 for Accessories.

4 Pole, 5 Wire



NEMA
L21-30R



NEMA
L21-30P



NEMA
L22-30R



NEMA
L22-30P



NEMA
L23-30R



NEMA
L23-30P

Turnlok® Locking Devices Angle Devices


3 Wire 15A, 125 & 250V, 277VAC
3, 4 & 5 Wire 15, 20 & 30A Adapters

Pass & Seymour




Features


- Angle plugs and adapters both allow for 4-position face rotation. 20/30A 3 Wire Turnlok® Right Angle Adapters are adjustable up to 8 positions.
- Angle adapters (sold separately) will accommodate all P&S Turnlok style plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.
- Tri-drive assembly and cord-grip screws are standard on all angle plugs and adapters.
- Angle plugs and adapters have the same wide cord diameter range (.230"-1.150") that is present on all Turnlok plugs and connectors.




15 Amp
Angle Plug



L15-AN



L20303-AN



L203045-AN

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance	
					UL UL498	FSUL WC596
Plugs						
PS4720-SSAN	15 125	Black Back Body, White Front Body	.230"-.655"	L5-15P	•	•
PSL615-PAN	15 250	Black Back Body, White Front Body	.230"-.690"	L6-15P	•	•
PSL715-PAN	15 277	Black Back Body, White Front Body	.230"-.690"	L7-15P	•	•



NEMA
L5-15P



NEMA
L6-15P



NEMA
L7-15P

Catalog Number	Description
Accessories	
L15-AN	15A Turnlok Right Angle Adapter
L20303-AN	20/30A 3 Wire Turnlok Right Angle Adapter
L203045-AN	20/30A 4 and 5 Wire Turnlok Right Angle Adapter

Pass & Seymour



Turnlok® Locking Devices Rubber & Watertight Plugs & Connectors


2 Pole, 3 Wire Grounding 15A, 125V, 277VAC

IP20


Suitability

Features


- Rubber body construction stands up to impacts, oil, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts and reduce stress on blades and contacts.
- Neoprene grommet keeps out contaminants at cord entrance.
- Terminal screws come backed-out – ready-to-wire.
- Nickel-plated blades and connectors provide an extra measure of corrosion resistance.
- Closure cap on watertight model forms a seal to keep out contaminants when connector is not in use.
- Multiple seals between plug and connector on watertight version protects electrical connection from contaminants.




2447



2547



24W47



25W47

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance	
				UL UL498	CSA C22.2 42M
Rubber					
2447	15 125	Rubber Locking Plug	L5-15P	•	•
2547	15 125	Rubber Locking Connector	L5-15R	•	•
2434	15 277	Rubber Locking Plug	L7-15P	•	•
2534	15 277	Rubber Locking Connector	L7-15R	•	•
NEMA 4X – Watertight Devices					
24W47	15 125	NEMA 4X Locking Plug	L5-15P	•	•
25W47	15 125	NEMA 4X Locking Connector	L5-15R	•	•
24W34	15 277	NEMA 4X Locking Plug	L7-15P	•	•
25W34	15 277	NEMA 4X Locking Connector	L7-15R	•	•

Catalog Number	Description	NEMA Config. No.	3rd Party Compliance	
			UL UL498	CSA C22.2 42M
Caps – Watertight Only				
14WPS	Male Cap	All	•	•
50W50PS	Female Replacement Cap	All	•	•

NEMA
L5-15RNEMA
L5-15PNEMA
L7-15RNEMA
L7-15P

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets

3 Wire Grounding 50A, 125, 250 & 480V; 250VDC, 600VAC

Pass & Seymour




Turnlok® Locking Devices


Catalog Number	Rating A. V.	Description	Cord Diameter	3rd Party Compliance		
				UL498	FSUL WC596	CSA
Receptacles						
CR6370	50 125	Corrosion-Resistant		•		•
CS6370	50 125	California Standard		•		•
CS8269	50 250	California Standard		•		•
CS8469	50 480	California Standard		•		•
3771	50 250VDC, 600VAC	Corrosion-Resistant		•		•
Connectors						
CR6360	50 125	Corrosion-Resistant	.680"-1.125"	•		•
CS6360	50 125	California Standard	.680"-1.125"	•		•
CS8264	50 250	California Standard	.680"-1.125"	•		•
CS8464	50 480	California Standard	.680"-1.125"	•		•
3762	50 250VDC, 600VAC	Corrosion-Resistant	.680"-1.125"	•		•
Plugs						
CR6361	50 125	Corrosion-Resistant	.680"-1.125"	•		•
CS6361	50 125	California Standard	.680"-1.125"	•		•
CS8265	50 250	California Standard	.680"-1.125"	•		•
CS8465	50 480	California Standard	.680"-1.125"	•		•
3763-M	50 250VDC, 600VAC	Corrosion-Resistant	.680"-1.125"	•		•
Flanged Inlets						
CR6377	50 125	Corrosion-Resistant		•		•
CS6377	50 125	California Standard		•		•
CS8275	50 250	California Standard		•		•
CS8475	50 480	California Standard		•		•
3777	50 250VDC, 600VAC	Corrosion-Resistant		•		•

Reference Pages H-31 and H-32 for Accessories.


Catalog Number	Description
Accessories	
7770	Weatherproof Cover for 50A Locking Receptacles, Thermoplastic Note: 7770 covers not to be used with flanged devices.
CR7716-N	Weatherproof Boot, 50A Locking Connector
CR7717-N	Weatherproof Boot, 50A Locking Plug
PSLD	Lockout Device




California Standard Receptacle



California Standard Connector



California Standard Plug



California Standard Flanged Inlet

Non-NEMA CR6370 CR6360	Non-NEMA CS6370 CS6360	Non-NEMA CS8269 CS8265	Non-NEMA CS8469 CS8464	Non-NEMA 3771 3762	Non-NEMA CR6361 CR6377	Non-NEMA CS6361 CS6377	Non-NEMA CS8265 CS8275	Non-NEMA CS8465 CS8475	Non-NEMA 3763 3777	Non-NEMA 3763 3777

All devices listed on this page conform to NEMA WD-1 and WD-6.


Receptacles, Connectors, Plugs, Inlets

Pass & Seymour



Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets


4 Wire Grounding 50A, 125/250V; 3Ø, 250 & 480V; 250VDC, 600VAC




Corrosion-Resistant Receptacle



Corrosion-Resistant Connector



Corrosion-Resistant Plug




Corrosion-Resistant Flanged Inlet

All devices listed on this page conform to NEMA WD-1 and WD-6.

Catalog Number	Rating A. V.	Description	Cord Diameter	3rd Party Compliance		
				UL498	FSUL WC596	CSA
Receptacles						
CR6369	50 125/250	Corrosion-Resistant		•		•
CS6369	50 125/250	California Standard		•		•
CS8369	50 3Ø, 250	California Standard		•		•
CS8169	50 3Ø, 480	California Standard		•		•
3769	50 250VDC, 600VAC	Corrosion-Resistant		•		•
7379*	50 250VDC, 600VAC	Corrosion-Resistant		•		•
Connectors						
CR6364	50 125/250	Corrosion-Resistant	.680"-1.125"	•		•
CS6364	50 125/250	California Standard	.680"-1.125"	•		•
CS8364	50 3Ø, 250	California Standard	.680"-1.125"	•		•
CS8164	50 3Ø, 480	California Standard	.680"-1.125"	•		•
3764	50 250VDC, 600VAC	Corrosion-Resistant	.680"-1.125"	•		•
7764*	50 250VDC, 600VAC	Corrosion-Resistant	.680"-1.125"	•		•
Plugs						
CR6365	50 125/250	Corrosion-Resistant	.680"-1.125"	•		•
CS6365	50 125/250	California Standard	.680"-1.125"	•		•
CS8365	50 3Ø, 250	California Standard	.680"-1.125"	•		•
CS8165	50 3Ø, 480	California Standard	.680"-1.125"	•		•
3765	50 250VDC, 600VAC	Corrosion-Resistant	.680"-1.125"	•		•
7765*	50 250VDC, 600VAC	Corrosion-Resistant	.680"-1.125"	•		•
Flanged Inlets						
CR6375	50 125/250	Corrosion-Resistant		•		•
CS6375	50 125/250	California Standard		•		•
CS8375	50 3Ø, 250	California Standard		•		•
CS8175	50 3Ø, 480	California Standard		•		•
CS8177	50 3Ø, 480	California Standard with Flip Lid		•		•
3775	50 250VDC, 600VAC	Corrosion-Resistant		•		•
7958*	50 250VDC, 600VAC	Corrosion-Resistant		•		•

*Devices for replacement use only in existing installations. Reference Pages H-31 and H-32 for Accessories.

Catalog Number	Description
Accessories	
7770	Weatherproof Cover for 50A Locking Receptacles, Thermoplastic Note: 7770 covers not to be used with flanged devices.
CR7716-N	Weatherproof Boot, 50A Locking Connector
CR7717-N	Weatherproof Boot, 50A Locking Plug
PSLD	Lockout Device



Turnlok® Locking Devices Midget Connectors, Plugs, Inlets, Outlets

2 Pole, 2 Wire Non-Grounding 15A, 125V
2 Pole, 2 Wire Grounding 15A, 125V
3 Pole, 3 Wire Non-Grounding 15A, 125/250V









Pass & Seymour



Turnlok® Locking Devices


Midget Connectors, Plugs, Inlets, Outlets

Catalog Number	Rating A. V.	Description	Cord Diameter	NEMA Config. No.	3rd Party Compliance
					UL498
Connectors					
7427	15 125	Black	.312"-.50"	ML1-15R	•
ML1133	15 125	Black	.10"-.35"	ML1-15R	•
ML2133	15 125	Black	.18"-.52"	ML2-15R	•
ML3133	15 125/250	Black	.18"-.52"	ML3-15R	•
Plugs					
ML1113	15 125	Black	.10"-.35"	ML1-15P	•
ML2113	15 125	Black	.18"-.52"	ML2-15P	•
ML3113	15 125/250	Black	.18"-.52"	ML3-15P	•
Flanged Inlets & Outlets					
ML115	15 125	Flanged Inlet, Black Face Gray Flange		ML1-15P	•
ML114	15 125	Flanged Outlet, Black Face Gray Flange		ML1-15R	•
ML215	15 125	Flanged Inlet, Black Face Gray Flange		ML2-15P	•
ML214	15 125	Flanged Outlet, Black Face Gray Flange		ML2-15R	•
ML315	15 125/250	Flanged Inlet, Black Face Gray Flange		ML3-15P	•
ML314	15 125/250	Flanged Outlet, Black Face Gray Flange		ML3-15R	•




Turnlok® Locking Devices Receptacles, Connectors & Plugs


3 Wire Power Interrupting Devices 20A, 125V Hospital Use
20A, 125V & 20A, 125V; 10A, 250VDC, 480VAC




23000-HG



23030



23000



23005-N



23056-N
23035-N



23002-N



23054-N

Catalog Number	Rating A. V.	Description	Cord Diameter	3rd Party Compliance
				UL498
Receptacles				
23000-HG	20 125	Hospital Use, Non-Metallic		•
23050	20 125	Hospital Use, Black Bakelite		•
23030	20 125	Non-Metallic		•
23000-G	20 125; 10 250VDC, 480VAC	Grounding, Non-Metallic		•
23000	20 125; 10 250VDC, 480VAC	Non-Grounding, Non-Metallic		•
Connectors				
23054-N	20 125	Hospital Use, Non-Metallic	.250"-.656"	•
23002-N	20 125; 10 250VDC, 480VAC	Non-Metallic	.250"-.656"	•
Plugs				
23056-N	20 125	Hospital Use, Non-Metallic	.250"-.656"	•
23035-N	20 125	Non-Metallic	.250"-.656"	•
23005-N	20 125; 10 250VDC, 480VAC	Non-Metallic	.250"-.656"	•

Configuration Descriptions

Hospital Use	2 Pole, 3 Wire	2 Pole, 3 Wire
2 Pole, 3 Wire	20A 125V	20A 125V
20A 125V		10A 480VAC 250VDC

Catalog Number	Description
Accessories	
PSLD	Lockout Device
23007	Aluminum Receptacle Cover with Gasket

Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets

4 Wire Power Interrupting Devices

30A, 480V & 30A, 600VAC; 20A, 250VDC & 60A, 600V


Pass & Seymour




Turnlok® Locking Devices

Receptacles, Connectors, Plugs, Inlets, Outlets


Catalog Number	Rating A. V.	Description	Cord Diameter	3rd Party Compliance
				UL UL498
Receptacles				
20443-N	30 480	Non-Metallic		•
20403-N	30, 600VAC; 20, 250VDC	Non-Metallic		
21420	30, 600VAC; 20, 250VDC	Angled, 3/4" Tap for Conduit, Die-Cast		
26420	60 600	Die-Cast with Lift Lid Enclosure		•
Connectors				
20444-N	30 480	Non-Metallic	.400"-1.062"	•
20414	30, 600VAC; 20, 250VDC	Metallic	.562"-1.000"	
20414-N	30, 600VAC; 20, 250VDC	Non-Metallic	.400"-1.062"	
21414	30, 600VAC; 20, 250VDC	Metallic with Rubber Cord Grip	.360"-0.484"	•
26414	60 600	Metallic	.750"-1.250"	
26427	60 600	Metallic	.750"-1.250"	
Plugs				
20445-N	30 480	Non-Metallic	.400"-1.062"	•
20415	30, 600VAC; 20, 250VDC	Metallic	.562"-1.000"	
20415-N	30, 600VAC; 20, 250VDC	Non-Metallic	.400"-1.062"	
21415	30, 600VAC; 20, 250VDC	Metallic with Rubber Cord Grip	.360"-0.484"	•
21426	30, 600VAC; 20, 250VDC	Metallic with Rubber Cord Grip	.484"-0.750"	
21426S	30, 600VAC; 20, 250VDC	Metallic with Tab with Rubber Cord Grip	.484"-0.750"	
26415	60 600	Metallic	.750"-1.250"	•
26426	60 600	Metallic	.750"-1.250"	
Flanged Inlets & Outlets				
20418	30, 600VAC; 20, 250VDC	Inlet, Die-Cast for FS and FD Box		•
26415-A	60 600	Inlet, Die-Cast		
26414-A	60 600	Outlet, Die-Cast		



20443-N




26420



26415



26414




20418

Configuration Descriptions


3 Pole, 4 Wire, 30A 480V

3 Pole, 4 Wire, 30A 600VAC;
20A 250VDC

3 Pole, 4 Wire, 60A 600V



26415-A




26414-A


Catalog Number	Description
Accessories	
WPG-1	Weatherproof Cover for 20403N
26400	Box and Plate for 26420
26401	Box only for 26404 Angle Adapter
26402	Mounting Plate only for 26401 Box
26404	45° Angle Adapter
20446N	Red Nylon Cover and Gasket for 20443N
20416N	Nylon Cover and Gasket for 20403N
20417N	Aluminum Cover (No Gasket) for 20403N




26426



20445-N, 20415-N



26427



20444-N, 20414-N





All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



Turnlok® Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets






5 Wire Power Interrupting Devices
30A, 600VAC; 20A, 250VDC & 60A, 600V



Catalog Number	Rating		Description	Cord Diameter	3rd Party Compliance
	A.	V.			UL498
Receptacles					
25250	30	600VAC; 20	250VDC	Die-Cast with Lift Lid Enclosure	
26520	60	600		Die-Cast with Lift Lid Enclosure	•
Connectors					
25414-N	30	600VAC; 20	250VDC	Non-Metallic	.625"-1.000" .725"-1.250"
25414	30	600VAC; 20	250VDC	Metallic	.625"-1.000"
26514	60	600		Metallic	.750"-1.250"
26527	60	600		Metallic with Rubber Cord Grip	.750"-1.250"
Plugs					
25415-N	30	600VAC; 20	250VDC	Non-Metallic	.625"-1.000" .725"-1.250"
25415	30	600VAC; 20	250VDC	Metallic	.625"-1.000"
26515	60	600		Metallic	.750"-1.250"
26526	60	600		Metallic with Rubber Cord Grip	.750"-1.250"
Flanged Inlets & Outlets					
26515-A	60	600		Inlet, Die-Cast	•
26514-A	60	600		Outlet, Die-Cast	•

Configuration Descriptions
4 Pole, 5 Wire 30A 600VAC; 20A 250VDC 4 Pole, 5 Wire 60A 600V

Catalog Number	Description	Catalog Number	Description
Accessories			
26400	Box and Plate for 26520	26404	45° Angle Adapter
26401	Box only for 26404 Angle Adapter	25424	Rubber Cover for 25414 Connector and 25415 Plug
26402	Mounting Plate only for 26401 Box		



All devices listed on this page conform to NEMA WD-1 and WD-6.







Turnlok® Locking Devices Accessories

Pass & Seymour




Turnlok® Locking Devices

Catalog Number	Description	Color
Weatherproof Boots		
L15-RBC	Boot for 15A Locking Connector	Black
L15-RBP	Boot for 15A Locking Plug	Black
L2030-RBC	Boot for 20/30A Locking Connector	Black
L2030-RBP	Boot for 20/30A Locking Plug	Black
Corrosion-Resistant Boots		
CRL2030-RBC	Boot for 20/30A Locking Connector	Yellow
CRL2030-RBP	Boot for 20/30A Locking Plug	Yellow
CR7716-N	Boot for 50A Locking Connector	Yellow
CR7717-N	Boot for 50A Locking Plug	Yellow
Protective Boots		
BOOT15	Rubber Boot for 15 and 20A Gator Grip Plug and Connectors	Yellow
BOOT20	Rubber Boot for 20A Gator Grip Plug and Connectors	Yellow
BOOT50	Rubber Boot for 50A Gator Grip Plug and Connectors	Yellow
Lockout Devices		
PSLD	Lockout Device 15, 20, 30, 50A Turnlok Plug and Connector	Yellow
Dust Covers		
DC1	20 and 30A Plug and Connector Replacement Cover	Black




Turnlok® Locking Devices Accessories




WPG-1




WPG-2




7770



L15-AN



L20303-AN



L203045-AN

Catalog Number	Description	Color
Weatherproof Covers		
WPG-1	Cover for 15A Turnlok Flanged Inlets and Outlets	Gray
WPG-2	Cover for 20 and 30A Turnlok Flanged Inlets and Outlets	Gray
7770	Cover for 50A Locking Receptacle, Thermoplastic	Yellow
3720-FS	Clear Cover for Single Receptacle, Thermoplastic	Gray
3710-FS	Clear Cover for Duplex Receptacle, Thermoplastic	Gray
3722-FS	Clear Cover for Power Outlet, Thermoplastic	Gray
3760	Cover for Single Receptacle	Gray
Stainless Steel Plates		
SS7	Plate for Single Receptacle	S/S
SS8	Plate for Duplex Receptacle	S/S
SS720	Plate for Locking Receptacle	S/S
WP7	Dustproof Cover for Single Receptacle	S/S
WP8	Dustproof Cover for Duplex Receptacle	S/S
Strain Relief Grips		
FC22-GL	Strain Relief Grip – .220"-.320"	
FC30-GL	Strain Relief Grip – .300"-.430"	
FC40-GL	Strain Relief Grip – .400"-.560"	
FC52-GL	Strain Relief Grip – .520"-.730"	
FC70-GL	Strain Relief Grip – .700"-.940"	
FC94-GL	Strain Relief Grip – .940"-1.250"	
Turnlok Right Angle Adapter		
L15-AN	15A Turnlok Right Angle Adapter	Black
L20303-AN	20 and 30A 3 Wire Turnlok Right Angle Adapter	Black
L203045-AN	20 and 30A 4 and 5 Wire Turnlok Right Angle Adapter	Black

Turnlok® Locking Devices Ground Continuity Monitoring Plugs & Connectors

Product Specifications & Performance

Pass & Seymour



15, 20 & 30 Amp Turnlok GCM Plugs & Connectors

Plugs	
Back Body	Nylon
Front Body	Nylon
Terminal Chamber	Polycarbonate
Cord Clamp	Nylon
Insert	Nylon
Dust Cover*	Neoprene
Blades	Brass
Terminal Clamp	15A = Zinc-Plated Steel, 20A = Nickel-Plated Steel, 30A = Brass
Terminal Screws	15A = Nickel- or Brass-Plated Steel, 20 & 30A = Brass
Ground Screws	15A = Nickel-Plated Steel, 20 & 30A = Brass
Cord Clamp Screws	Nickel-Plated Steel
Assembly Screws	Nickel-Plated Steel
Connectors	
Back Body	Nylon
Front Body	Nylon
Terminal Chamber	Polycarbonate
Cord Clamp	Nylon
Insert	Nylon
Dust Cover*	Neoprene
Contacts	Brass
Terminal Clamp	15A = Zinc-Plated Steel, 20A = Nickel-Plated Steel, 30A = Brass
Terminal Screws	15A = Nickel- or Brass-Plated Steel, 20 & 30A = Brass
Ground Screws	15A = Nickel-Plated Steel, 20 & 30A = Brass
Cord Clamp Screws	Nickel-Plated Steel
Assembly Screws	Nickel-Plated Steel
Performance	
Electrical	
Dielectric Withstand Voltage	15A = 1600V minimum, 20 & 30A = 2200V minimum
Maximum Working Voltage	15A = 277VAC, 20 & 30A = 600VAC
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C maximum after 50 cycles at 150% rated current
Mechanical	
Cord Accommodations	Round portable service cords of diameters in accordance with the device rating as defined in UL62
Cord Grip Accommodations	15A = .230"-.720" diameter, 20 & 30A = .385"-1.15" diameter
Terminal Identification	15A = Green = Ground, White = Neutral, Brass = Hot 20 & 30A = "GR" and Green color = Ground, "WH" and White color = Neutral, "X", "Y", "Z" = Hot
Terminal Accommodation	15A = #18 AWG min. - #10 AWG max. 20A = #18 AWG min. - #8 AWG max. 30A = #18 AWG min. - #6 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration hot stamped onto device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous: +75°C Minimum: -40°C without impact

*Dust Cover for 20 & 30 Amp Plugs & Connectors.

Turnlok® Locking Devices Plugs & Connectors Product Specifications & Performance

15 Amp Turnlok Plugs & Connectors

	Standard Product	Corrosion-Resistant
Plugs		
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Polycarbonate	Polycarbonate
Cord Clamp	Nylon	Nylon
Insert	Nylon	Nylon
Blades	Brass	Nickel-Plated Brass
Terminal Clamp	Zinc-Plated Steel	Nickel-Plated Steel
Terminal Screws	Nickel- or Brass-Plated Steel	Nickel-Plated Steel
Ground Screws	Nickel-Plated Steel	Nickel-Plated Steel
Cord Clamp Screws	Nickel-Plated Steel	Nickel-Plated Steel
Assembly Screws	Nickel-Plated Steel	Nickel-Plated Steel
Connectors		
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Polycarbonate	Polycarbonate
Cord Clamp	Nylon	Nylon
Insert	Nylon	Nylon
Contacts	Brass	Nickel-Plated Brass
Terminal Clamp	Zinc-Plated Steel	Nickel-Plated Steel
Terminal Screws	Nickel- or Brass-Plated Steel	Nickel-Plated Steel
Ground Screws	Nickel-Plated Steel	Nickel-Plated Steel
Cord Clamp Screws	Nickel-Plated Steel	Nickel-Plated Steel
Assembly Screws	Nickel-Plated Steel	Nickel-Plated Steel
Performance		
Electrical		
Dielectric Withstand Voltage	1600V minimum	
Maximum Working Voltage	277VAC	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	30°C maximum after 50 cycles at 150% rated current	
Mechanical		
Cord Accommodations	Round portable service cords of diameters in accordance with the device rating as defined in UL62	
Cord Grip Accommodations	.230"-.720" diameter	
Terminal Identification	Green = Ground, White = Neutral, Brass = Hot	
Terminal Accommodation	#18 AWG min. – #10 AWG max.	
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration	
Environmental		
Flammability	UL94 V2	
Operating Temperature	Maximum continuous: +75°C Minimum: -40°C without impact	

Turnlok® Locking Devices Receptacles Product Specifications & Performance

Pass & Seymour



15, 20 & 30 Amp Turnlok Receptacles

	Standard	Corrosion-Resistant
Receptacles		
Front Body	Nylon	Nylon
Back Body	Nylon	Nylon
Mounting Strap	15A = Steel; 20 & 30A = Brass	Nickel-Plated Brass
Pressure Plate	Brass	Nickel-Plated Brass
Contacts	Brass	Nickel-Plated Brass
Terminal Clamps	Brass	Nickel-Plated Brass
Terminal Screws	Brass	Brass
Mounting Screws	Zinc-Plated Steel	Stainless Steel
Performance		
Electrical		
Dielectric Withstand Voltage	2000V minimum	
Maximum Working Voltage	600VAC	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	30°C maximum after 50 cycles at 150% rated current	
Mechanical		
Terminal Accommodation	15A = #18 AWG min. – #10 AWG max. 20 & 30A = #14 AWG min. – #10 AWG max.	
Product Identification	Amperage, Voltage, NEMA Configuration molded into face	
Environmental		
Flammability	UL94 V2	
Operating Temperature	Maximum continuous: +75°C Minimum: -40°C without impact	

50 Amp Turnlok Receptacles

	Corrosion-Resistant	California Standard
Receptacles		
Front Body	Glass-Filled Nylon	Glass-Filled Nylon
Back Body	Glass-Filled Nylon	Glass-Filled Nylon
Mounting Strap	Nickel-Plated Brass	Nickel-Plated Brass
Contacts	Nickel-Plated Brass	Brass
Terminal Clamps	Brass	Brass
Ground Shunt	Brass	Brass
Mounting Screws	Stainless Steel	Zinc-Plated Steel
Performance		
Electrical		
Dielectric Withstand Voltage	3000V minimum	
Maximum Working Voltage	600VAC	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	30°C maximum after 50 cycles at 150% rated current	
Mechanical		
Terminal Accommodation	#10 AWG min. – #6 AWG max.	
Product Identification	Amperage, Voltage molded into face	
Environmental		
Flammability	UL94 V0	
Operating Temperature	Maximum continuous: +115°C Minimum: -40°C without impact	

Turnlok® Locking Devices Plugs & Connectors Product Specifications & Performance

20 & 30 Amp Turnlok Plugs & Connectors

	Standard	Corrosion-Resistant
Plugs		
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Polycarbonate	Polycarbonate
Cord Clamp	Nylon	Nylon
Insert	Nylon	Nylon
Dust Cover	Neoprene	Neoprene
Blades	Brass	20A = Nickel-Plated Brass 30A = Tin-Plated Brass
Terminal Clamp	20A = Nickel-Plated Steel 30A = Brass	20A = Nickel-Plated Steel 30A = Nickel-Plated Brass
Terminal Screws	Brass	Nickel-Plated Brass
Ground Screws	Brass	Nickel-Plated Brass
Cord Clamp Screws	Nickel-Plated Steel	Nickel-Plated Steel
Assembly Screws	Nickel-Plated Steel	Nickel-Plated Steel
Connectors		
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Polycarbonate	Polycarbonate
Cord Clamp	Nylon	Nylon
Insert	Nylon	Nylon
Dust Cover	Neoprene	Neoprene
Contacts	Brass	20A = Nickel-Plated Brass 30A = Tin-Plated Brass
Terminal Clamp	20A = Nickel-Plated Steel 30A = Brass	20A = Nickel-Plated Steel 30A = Nickel-Plated Brass
Terminal Screws	Brass	Nickel-Plated Brass
Ground Screws	Brass	Nickel-Plated Brass
Cord Clamp Screws	Nickel-Plated Steel	Nickel-Plated Steel
Assembly Screws	Nickel-Plated Steel	Nickel-Plated Steel
Performance		
Electrical		
Dielectric Withstand Voltage	2200V minimum	
Maximum Working Voltage	600VAC	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	30°C maximum after 50 cycles at 150% rated current	
Mechanical		
Cord Accommodations	Round portable service cords of diameters in accordance with the device rating as defined in UL62	
Cord Grip Accommodations	.385"-1.15" diameter	
Terminal Identification	"GR" and Green color = Ground, "WH" and White color = Neutral, "X", "Y", "Z" = Hot	
Terminal Accommodation	#18 AWG min. – #8 AWG max.	
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration hot stamped onto device	
Environmental		
Flammability	UL94 V2	
Operating Temperature	Maximum continuous: +75°C Minimum: -40°C without impact	

Turnlok® Locking Devices Plugs & Connectors Product Specifications & Performance

Pass & Seymour



50 Amp Turnlok Plugs & Connectors

	Corrosion-Resistant	California Standard
Plugs		
Plug Shroud	Zytel Supertough Nylon	Zytel Supertough Nylon
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Nylon	Nylon
Cord Clamp	Nylon	Nylon
Blades	Nickel-Plated Brass	Brass
Terminal Clamp	Nickel-Plated Brass	Brass
Terminal Screws	Nickel-Plated Brass	Brass
Ground Screw	Nickel-Plated Brass	Brass
Assembly Screws	Stainless Steel	Stainless Steel
Connectors		
Back Body	Nylon	Nylon
Front Body	Nylon	Nylon
Terminal Chamber	Nylon	Nylon
Cord Clamp	Nylon	Nylon
Contacts	Nickel-Plated Brass	Brass
Terminal Clamp	Nickel-Plated Brass	Brass
Terminal Screws	Nickel-Plated Brass	Brass
Ground Screw	Nickel-Plated Brass	Brass
Assembly Screws	Stainless Steel	Stainless Steel
Performance		
Electrical		
Dielectric Withstand Voltage	3000V minimum	
Maximum Working Voltage	600VAC	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	30°C maximum after 50 cycles at 150% rated current	
Mechanical		
Cord Accommodations	Round portable service cords of diameters in accordance with the device rating as defined in UL62	
Cord Grip Accommodations	.680"-1.125" diameter	
Terminal Identification	Color Coded Terminal Screws	
Terminal Accommodation	#10 AWG min. – #4 AWG max.	
Product Identification	Amperage, Voltage hot stamped on device	
Environmental		
Flammability	UL94 HB or better	
Operating Temperature	Maximum continuous: +75°C Minimum: -40°C without impact	

Turnlok® Locking Devices Inlets & Outlets Product Specifications & Performance

15, 20 & 30 Amp Turnlok Inlets & Outlets

	15 Amp	20 Amp	30 Amp
Flanged Inlets			
Flanged Casing	Polycarbonate	Polycarbonate	Polycarbonate
Blade Holder	Polycarbonate	Polycarbonate	Nylon
Blades	Nickel-Plated Brass	Brass	Tin-Plated Stresscon
Terminal Clamp	Zinc-Plated Steel	Zinc-Plated Steel	Brass
Terminal Screws	Zinc- or Brass-Plated Steel	Zinc- or Brass-Plated Steel	Brass
Ground Screws	Zinc-Plated Steel	Zinc-Plated Steel	Brass
Assembly Screws	Zinc-Plated Steel	Zinc-Plated Steel	Zinc-Plated Steel
Flanged Outlets			
Flanged Casing	Polycarbonate	Polycarbonate	Polycarbonate
Contact Carrier	Polycarbonate	Polycarbonate	Nylon
Contacts	Brass	Brass	Tin-Plated Brass
Terminal Clamp	Zinc-Plated Steel	Zinc-Plated Steel	Brass- or Nickel-Plated Steel
Terminal Screws	Zinc- or Brass-Plated Steel	Zinc- or Brass-Plated Steel	Brass- or Nickel-Plated Steel
Ground Screws	Zinc-Plated Steel	Zinc-Plated Steel	Nickel-Plated Brass
Assembly Screws	Zinc-Plated Steel	Zinc-Plated Steel	Zinc-Plated Steel
Performance			
Electrical			
Dielectric Withstand Voltage	15A = 2000V minimum, 20 & 30A = 3000V minimum		
Maximum Working Voltage	15A = 277VAC, 20 & 30A = 600VAC		
Current Interrupting	Certified for current interrupting at full-rated current		
Temperature Rise	30°C maximum after 50 cycles at 150% rated current		
Mechanical			
Terminal Identification	Green = Ground, White = Neutral, Brass = Hot		
Terminal Accommodation	15A = #18 AWG min. – #10 AWG max., 20 & 30A = #12 AWG min. – #8 AWG max.		
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration		
Environmental			
Flammability	UL94 V2		
Operating Temperature	Maximum continuous: 15 & 20A = +115°C, 30A = +75°C Minimum: -40°C without impact		

Turnlok® Locking Devices Inlets Product Specifications & Performance & Horsepower Rating Chart

Pass & Seymour



50 Amp Inlet

Inlets	
Flanged Casing	Nylon
Contact Carrier	Nylon
Blades	Brass
Terminal Clamps	Brass
Terminal Screws	Brass
Assembly Screws	Nickel-Plated Steel
Performance	
Electrical	
Dielectric Withstand Voltage	3000V minimum
Maximum Working Voltage	600VAC
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C maximum after 50 cycles at 150% rated current
Mechanical	
Terminal Accommodation	#10 AWG min. – #4 AWG max.
Product Identification	Amperage, Voltage hot stamped onto face
Environmental	
Flammability	UL94 V0
Operating Temperature	Maximum continuous: +75°C Minimum: -40°C without impact

Turnlok Horsepower Rating for NEMA Configuration Attachment Plugs & Receptacles

NEMA Configuration	AC HP Rating	NEMA Configuration	AC HP Rating
L1-15	1/2	L21-20	2
L5-15	1/2	L22-20	5
L6-15	1 1/2*	L5-30	2
L7-15	2	L6-30	2*
L2-20	2*	L7-30	3
L5-20	1	L8-30	5
L6-20	2*	L10-30	2 Line to Line*
L7-20	2		2 Line to Neutral
L8-20	3	L11-30	3
L10-20	2 Line to Line*	L12-30	10
	1 Line to Neutral	L14-30	2 Line to Line*
L11-20	3	L15-30	3
L12-20	5	L16-30	10
L14-20	2 Line to Line*	L18-30	3
L15-20	3	L19-30	10
L16-20	5	L21-30	3
L18-20	2	L22-30	10
L19-20	5		

*Suitable for 208V motor applications at the HP rating specified.