

JULY 2016

MaxLite®

A NEW WAVE OF LIGHT



Online Version Updated: 9/15/16

Our Vision:

Transform the way people experience light

MaxLite has 25 years of experience providing certified energy-efficient lighting solutions to the commercial building and residential markets. One of the first movers into LED technology in the industry, MaxLite offers an extensive line of state-of-the-art indoor and outdoor LED lamps and luminaires. We are a four-time recipient of the prestigious ENERGY STAR® Partner of the Year Award for our industry leadership and continue to be at the forefront of energy efficient technologies through the innovative research and development capabilities of our New Jersey headquarters and California facility.



West Caldwell, NJ

Our Mission:

To advance our leadership position as a trustworthy lighting solutions provider that connects and empowers our customers. We will leverage our efficiency, scale and capabilities in lighting and controls to create and respond to real market opportunities, ahead of the curve. Our purpose is to create innovative lighting; our passion is in providing superior service and support.



Anaheim, CA

Our Products:

MaxLite supports its products with the highest standards of quality assurance and customer support. Most MaxLite LED products are certified by ENERGY STAR® and DesignLights Consortium® (DLC), rendering them eligible for utility rebate programs. MaxLite also offers a large selection of lamps and luminaires that meet California Title 24 requirements. We keep our products in stock and available for immediate purchase and delivery, shipping within the United States in one to three business days on standard orders.



Our Services:

We work with our customers to ensure that our products meet the needs of their installation by providing a full range of complimentary services, including:

- Facility audits
- Lighting layouts
- ROI calculations
- Utility rebate assistance
- Local representation
- Lifetime product support



PARTNER OF THE YEAR
Sustained Excellence



Recent Accolades:

As a result of our commitment to innovation, MaxLite has received numerous honors, including:

2016:

- Environmental Protection Agency ENERGY STAR® Partner of the Year - Sustained Excellence Award
- EC&M Product of the Year Category Winner for *QuadroMAX*
- Architectural SSL Product Innovation Awards for *LED Lightsbars* and *QuadroMAX*
- ADEX Platinum Award winners: *QuadroMAX*, *Architectural Security Light*, *Filament Lamps*, *Traditional Omni A-Lamp* and *DirectFit PL Lamps*

2015:

- Environmental Protection Agency ENERGY STAR® Partner of the Year
- Design Journal Best of 2015 Products for *LED Filament Lamps*
- BUILDINGS Money-Saving Product winner for *LED Faux Can*
- Lighting for Tomorrow Honorable mention for *LED Warm-on-Dim Downlight Retrofit*
- Lighting for Tomorrow Special Recognition *LED Filament Lamps*
- IES Progress Report recognition for *Puck Lamp*

INDOOR LED FIXTURES

LED Flat Panel Direct Lit Economical Series	>1-2	NEW LED Acrylic Highbay Pendant	>28
FlatMAX [®] Edge Lit LED Flat Panels	>3-4	BayMAX [™] LED Linear High Bays	>29
ECO-T [™] Recessed Troffers	>5-6	LED T8 Lamp Ready Fixtures	>30
LED Lensed Retrofit Kits	>7-8	NEW LED Cooler/Freezer Lamps	>31
ArcMAX [™] Volumetric LED Panels	>9-11	& Cooler Door Fixtures	
LED Commercial Downlight Retrofits	>12-13	NEW LED Polygon [™] Linear Fixtures	>32
LED Commercial Downlight Retrofits	>14	LED Utility Wrap Fixtures	>33-34
Economical Series		LED Vapor Tight Linear Fixtures	>35-36
LED Recessed Downlight Retrofits	>15-18	Plug-and-Play Lightbars	>37-40
Architectural Series		NEW L-Form Linear LED Luminaire	>41
LED Commercial Recessed Downlight Fixtures	>19-21	NEW LED Shop Light	>42
LED Adjustable Recessed Downlight Retrofits	>22	LED Flush Mounts	>43
LED Recessed Downlight Retrofits	>23-24	NEW LED Flush Mount Retrofits	>44
LED Recessed Downlight Fixtures	>25	& Torchieres	
LED Faux Cans	>26	LED Semi Flush Mount, Vanity Bar	>45
BayMAX [™] LED Pendant High Bays	>27	& Wall Sconce	

OUTDOOR LED FIXTURES

QuadroMAX	>46-49	StaxMAX [™] LED High Output Floods	>61
LED Area Luminaires	>50	StaxMAX [™] Accessories	>62
LED Area & Barn Luminaires	>51	LED Post Top Luminaires	>63
LED Wall Packs	>52	LED Parking Luminaires	>64
LED Wall Packs & Medium Flood Lights	>53	LED Canopy Luminaires	>65-66
LED Adjustable Wall Packs	>54	StaxMAX [™] LED Flood Lights	>67
LED Security Lights	>55	for Hazardous Locations	
NEW LED Bullet Floods	>56	NEW HLRMax Hazardous Location	>68
LED Small Floods	>57	LED Vapor Proof Jelly Jars	>69
LED Architectural Floods	>58	LED Recessed Gas Station Canopy	>70
LED Medium Floods	>59	LED Lanterns	>71
NEW ModMax High Output Flood	>60		

GENERAL PURPOSE LAMPS

LED Vintage Filament Lamps	>72	LED BR Lamps	>80
LED Marquee, Candelabra & Globe Lamps	>73	LED PL, T8 UBend & T8/T5 Linear	>81
LED G4 & G9 Retrofit Lamps	>74	Direct Fit Lamps	
LED Omni-Directional A Lamps	>75	LED PL Retrofit Lamps	>82
Traditional Shape		LED Linear T8 Internal Driver	>83-84
LED Omni-Directional A Lamps	>76	High Efficiency LED Linear T8	>85
LED Omni-Directional Enclosed Rated,	>77	Internal Driver	
3-Way A Lamps & Non-Dimmable A19		LED Puck Lamps	>86
LED MR16 Lamps	>78	Specialty LED Retrofit Lamps	>87
LED PAR Lamps	>79		

LED Flat Panel Direct Lit Economical Series

1' x 4' MODEL



MODEL NUMBER	MLFP14DE3535 (EM)	MLFP14DE3541 (EM)	MLFP14DE3550 (EM)
Input Wattage	35W	35W	35W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2770 lm	2930 lm	3010 lm
Efficacy (lm/W)	84 lm/W	89 lm/W	94 lm/W
Color Rendering Index (CRI)	81	81	81
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC

1'x4' models available only on special order basis and will not support inventory. Please call MaxLite for additional details. For available accessories, see maxlite.com.

2' x 2' MODEL



MODEL NUMBER	MLFP22DE3535 (EM)	MLFP22DE3541 (EM)	MLFP22DE3550 (EM)
Input Wattage	35W	35W	35W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2870 lm	3000 lm	3020 lm
Efficacy (lm/W)	86 lm/W	91 lm/W	94 lm/W
Color Rendering Index (CRI)	81	81	81
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC

For available accessories, see maxlite.com.

LED Flat Panel Direct Lit Economical Series



2' x 4' MODEL



MLFP24DE4535 (EM)	MLFP24DE4541 (EM)	MLFP24DE4550 (EM)	MODEL NUMBER
45W	45W	45W	Input Wattage
120-277V	120-277V	120-277V	Voltage
4480 lm	4500 lm	4680 lm	Delivered Lumens (lm)
96 lm/W	100 lm/W	105 lm/W	Efficacy (lm/W)
81	81	81	Color Rendering Index (CRI)
3500K	4100K	5000K	Color Temperature (CCT)
0-10V	0-10V	0-10V	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC	CERTIFICATIONS

For available accessories, see maxlite.com.



Direct Hit!

MaxLite's LED Direct Lit Flat Panels - Economical Series

MaxLite
A NEW WAVE OF LIGHT

FlatMAX® Edge Lit LED Flat Panels

1' x 4' MODEL



MODEL NUMBER	MLFP14EP3635-215 (EM)	MLFP14EP3641-215 (EM)	MLFP14EP3650-215 (EM)
Input Wattage	36W	36W	36W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	3490 lm	3550 lm	3650 lm
Efficacy (lm/W)	99 lm/W	101 lm/W	103 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, DLC, FCC	cULus, DLC, FCC	cULus, DLC, FCC

1'x4' models available only on special order basis and will not support inventory. Please call MaxLite for additional details. For available accessories, see maxlite.com.

2' x 2' MODEL




MODEL NUMBER	MLFP22EP4035* (EM)	MLFP22EP4041* (EM)	MLFP22EP4050 (EM)
Input Wattage	40W	40W	40W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	4120 lm	4180 lm	4320 lm
Efficacy (lm/W)	102 lm/W	105 lm/W	108 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Longevity (Life Hours) L70	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, DLC, FCC	cULus, DLC, FCC	cULus, DLC Premium, FCC

***DLC Standard only**

For available accessories, see maxlite.com.

FlatMAX[®] Edge Lit LED Flat Panels



2' x 4' MODEL



MLFP24EP5035 (EM)	MLFP24EP5041 (EM)	MLFP24EP5050 (EM)	MODEL NUMBER
50W	50W	50W	Input Wattage
120-277V	120-277V	120-277V	Voltage
5870 lm	5920 lm	6060 lm	Delivered Lumens (lm)
117 lm/W	118 lm/W	121 lm/W	Efficacy (lm/W)
80	80	80	Color Rendering Index (CRI)
3500K	4100K	5000K	Color Temperature (CCT)
0-10V	0-10V	0-10V	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cULus, DLC Premium, FCC	cULus, DLC Premium, FCC	cULus, DLC Premium, FCC	CERTIFICATIONS

For available accessories, see maxlite.com.

INTENSITY (CANDLES/FEET)	SUMMARY	OUTPUT LUMENS
1099		
1091		
1072		
1041		
998		
946		
888		
811		
740		
680		
620		
560		
500		
440		
380		
320		
260		
200		
140		
80		
20		

MaxLite
A NEW WAVE OF LIGHT

On The Cutting EDGE!
LED Edge Lit Performance Series Flat Panels

ZONE	LUMENS	LUMINAIRE
0-30	866	27.02
0-40	1435	44.45
0-60	2520	78.60
0-80	3806	118.90

ECO-T™ Recessed Troffers

2' x 2' MODEL



MODEL NUMBER	MLRT22D3535	MLRT22D3541	MLRT22D3550
Input Wattage	35W	35W	35W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2990 lm	3220 lm	3380 lm
Efficacy (lm/W)	85 lm/W	92 lm/W	96 lm/W
Color Rendering Index (CRI)	83	83	83
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	85,000 hours	85,000 hours	85,000 hours
CERTIFICATIONS	cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC

For available accessories, see maxlite.com.

2' x 2' MODEL



MODEL NUMBER	MLRT22D2535	MLRT22D2550	MLRT22D2350-150
Input Wattage	25W	25W	23W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2203 lm	2243 lm	1970 lm
Efficacy (lm/W)	99 lm/W	100 lm/W	92 lm/W
Color Rendering Index (CRI)	82	83	80
Color Temperature (CCT)	3500K	5000K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	150,000 hours	150,000 hours	50,000 hours
CERTIFICATIONS	cETLus, DLC, FCC, NSF	cETLus, DLC, FCC, NSF	cETLus, DLC, FCC

For available accessories, see maxlite.com.

ECO-T™ Recessed Troffers



2' x 4' MODEL



MLRT24D4535	MLRT24D4541	MLRT24D4550	MODEL NUMBER
45W	45W	45W	Input Wattage
120-277V	120-277V	120-277V	Voltage
4270 lm	4400 lm	4530 lm	Delivered Lumens (lm)
95 lm/W	98 lm/W	101 lm/W	Efficacy (lm/W)
80	80	80	Color Rendering Index (CRI)
3500K	4100K	5000K	Color Temperature (CCT)
0-10V	0-10V	0-10V	Dimming Compatible
85,000 hours	85,000 hours	85,000 hours	Lumen Maintenance (L70)
cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC	CERTIFICATIONS

For available accessories, see maxlite.com.



2' x 4' MODEL



MLRT24D3535	MLRT24D3550	MLRT24D3750-150	MODEL NUMBER
35W	35W	37W	Input Wattage
120-277V	120-277V	120-277V	Voltage
3283 lm	3375 lm	3490 lm	Delivered Lumens (lm)
100 lm/W	100 lm/W	101 lm/W	Efficacy (lm/W)
82	83	80	Color Rendering Index (CRI)
3500K	4100K	5000K	Color Temperature (CCT)
0-10V	0-10V	0-10V	Dimming Compatible
150,000 hours	150,000 hours	50,000 hours	Lumen Maintenance (L70)
cETLus, DLC, FCC, NSF	cETLus, DLC, FCC, NSF	cETLus, DLC, FCC	CERTIFICATIONS

For available accessories, see maxlite.com.

LED Lensed Retrofit Kits

2' x 2' MODEL



MODEL NUMBER	LRK22D2335* (EM)	LRK22D2341* (EM)
Input Wattage	23W	23W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	2460 lm	2540 lm
Efficacy (lm/W)	101 lm/W	103 lm/W
Color Rendering Index (CRI)	83	83
Color Temperature (CCT)	3500K	4100K
Dimming Compatible	0-10V	0-10V
Lumen Maintenance (L70)	103,000 hours	103,000 hours
CERTIFICATIONS	cULus, FCC, DLC	cULus, FCC, DLC

***DLC Standard only**

2' x 2' MODEL



MODEL NUMBER	LRK22D2350 (EM)
Input Wattage	23W
Voltage	120-277V
Delivered Lumens (lm)	2660 lm
Efficacy (lm/W)	109 lm/W
Color Rendering Index (CRI)	83
Color Temperature (CCT)	5000K
Dimming Compatible	0-10V
Lumen Maintenance (L70)	103,000 hours
CERTIFICATIONS	cULus, FCC, DLC Premium

LED Lensed Retrofit Kits



2' x 4' MODEL



LRK24D3535* (EM)

35W	MODEL NUMBER
120-277V	Input Wattage
3670 lm	Voltage
106 lm/W	Delivered Lumens (lm)
83	Efficacy (lm/W)
3500K	Color Rendering Index (CRI)
0-10V	Color Temperature (CCT)
103,000 hours	Dimming Compatible
cULus, FCC, DLC	Lumen Maintenance (L70)
	CERTIFICATIONS

*DLC Standard only



2' x 4' MODEL



LRK24D3541 (EM)

LRK24D3550 (EM)

LRK24D3541 (EM)	LRK24D3550 (EM)	MODEL NUMBER
35W	35W	Input Wattage
120-277V	120-277V	Voltage
3860 lm	4010 lm	Delivered Lumens (lm)
111 lm/W	115 lm/W	Efficacy (lm/W)
83	83	Color Rendering Index (CRI)
4100K	5000K	Color Temperature (CCT)
0-10V	0-10V	Dimming Compatible
103,000 hours	103,000 hours	Lumen Maintenance (L70)
cULus, FCC, DLC Premium	cULus, FCC, DLC Premium	CERTIFICATIONS

ArcMAX™ Volumetric LED Panels

1' x 4' MODEL



MODEL NUMBER	MLVT14D4235 (EM)	MLVT14D4241 (EM)	MLVT14D4250 (EM)
Input Wattage	42W	42W	42W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	3400 lm	3640 lm	3750 lm
Efficacy (lm/W)	86 lm/W	86 lm/W	89 lm/W
Color Rendering Index (CRI)	82	82	87
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC

1'x4' models available only on special order basis and will not support inventory. Please call MaxLite for additional details. For available accessories, see maxlite.com.

2' x 2' MODEL



MODEL NUMBER	MLVT22D3541 (EM)	MLVT22D3550 (EM)
Input Wattage	32W	32W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	3270 lm	3430 lm
Efficacy (lm/W)	100 lm/W	106 lm/W
Color Rendering Index (CRI)	84	84
Color Temperature (CCT)	4100K	5000K
Dimming Compatible	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, DLC, FCC	cETLus, DLC, FCC

For available accessories, see maxlite.com.

ArcMAX™ Volumetric LED Panels



2' x 4' MODEL

**MLVT24D4541 (EM)****MODEL NUMBER**

42W

Input Wattage

120-277V

Voltage

3990 lm

Delivered Lumens (lm)

93 lm/W

Efficacy (lm/W)

84

Color Rendering Index (CRI)

4100K

Color Temperature (CCT)

0-10V

Dimming Compatible

50,000 hours

Lumen Maintenance (L70)

cETLus, DLC, FCC

CERTIFICATIONSFor available accessories, see maxlite.com.

Smooth
Operator

ArcMAX™ Volumetric LED Panel

MaxLite
A NEW WAVE OF LIGHT

ArcMAX™ Volumetric LED Panels

2' x 2' MODEL



MODEL NUMBER	MLVT22D3535/SB (EM)	MLVT22D3541/SB (EM)	MLVT22D3550/SB (EM)
Input Wattage	35W	35W	35W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	3000 lm	3100 lm	3200 lm
Efficacy (lm/W)	91 lm/W	91 lm/W	91 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC

For available accessories, see maxlite.com.

2' x 4' MODEL



MODEL NUMBER	MLVT24D4235/SB (EM)	MLVT24D4241/SB (EM)	MLVT24D4250/SB (EM)
Input Wattage	42W	42W	42W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	4200 lm	4300 lm	4400 lm
Efficacy (lm/W)	99 lm/W	100 lm/W	100 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3500K	4100K	5000K
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, DLC, FCC	cETLus, DLC, FCC	cETLus, DLC, FCC

For available accessories, see maxlite.com.

LED Commercial Downlight Retrofits



4" MODEL



RR41530W/V2	RR41540W/V2	RR42330W	RR42340W	
14W	14W	23W	23W	MODEL NUMBER
120-277V	120-277V	120-277V	120-277V	Input Wattage
790 lm	880 lm	1640 lm	1690 lm	Voltage
56 lm/W	63 lm/W	71 lm/W	74 lm/W	Delivered Lumens (lm)
85	85	80	80	Efficacy (lm/W)
3000K	4000K	3000K	4000K	Color Rendering Index (CRI)
Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Color Temperature (CCT)
50,000 hours	50,000 hours	50,000 hours	50,000 hours	Dimming Compatible
cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	Lumen Maintenance (L70)
				CERTIFICATIONS

ACCESSORIES: Brushed Nickel Trim Ring available Model: RR4-BNRING



6" MODEL



RR61530W/V2	RR61540W/V2	RR62330W	RR62340W	RR63030W	RR63040W	
14W	14W	23W	23W	30W	30W	MODEL NUMBER
120-277V	120-277V	120-277V	120-277V	120-277V	120-277V	Input Wattage
830 lm	910 lm	1400 lm	1790 lm	2250 lm	2530 lm	Voltage
59 lm/W	65 lm/W	61 lm/W	78 lm/W	75 lm/W	84 lm/W	Delivered Lumens (lm)
85	85	85	80	80	80	Efficacy (lm/W)
3000K	4000K	3000K	4000K	3000K	4000K	Color Rendering Index (CRI)
Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Color Temperature (CCT)
50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	Dimming Compatible
cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	Lumen Maintenance (L70)
						CERTIFICATIONS

ACCESSORIES: Extended Trim Ring available Model: RR6-XWHTRING
Brushed Nickel Trim Ring available Model: RR6-BNRING

LED Commercial Downlight Retrofits



8" MODEL



MODEL NUMBER	RR81530W/V2	RR81540W/V2	RR82330W	RR82340W	RR83030W	RR83040W
Input Wattage	14W	14W	23W	23W	30W	30W
Voltage	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	840 lm	920 lm	1670 lm	1750 lm	2220 lm	2510 lm
Efficacy (lm/W)	60 lm/W	66 lm/W	73 lm/W	76 lm/W	74 lm/W	84 lm/W
Color Rendering Index (CRI)	85	85	80	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®

ACCESSORIES: Extended Trim Ring available Model: RR8-XWHTRING
Brushed Nickel Trim Ring available Model: RR8-BNRING



9" MODEL



MODEL NUMBER	RR92330W	RR92340W	RR93030W	RR93040W
Input Wattage	23W	23W	30W	30W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	1710 lm	1770 lm	2260 lm	2560 lm
Efficacy (lm/W)	74 lm/W	77 lm/W	76 lm/W	86 lm/W
Color Rendering Index (CRI)	80	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®

LED Commercial Downlight Retrofits Economical Series



6" MODEL



RRECO61830W	RRECO61840W	RRECO62730W	RRECO62740W	MODEL NUMBER
18W	18W	27W	27W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
1500 lm	1500 lm	2000 lm	2100 lm	Delivered Lumens (lm)
84 lm/W	84 lm/W	75 lm/W	80 lm/W	Efficacy (lm/W)
80	80	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	Color Temperature (CCT)
0-10V	0-10V	0-10V	0-10V	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

Additional CCT available, contact MaxLite for info.



8" MODEL



RRECO82330W	RRECO82340W	RRECO84030W	RRECO84040W	MODEL NUMBER
23W	23W	40W	40W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
1700 lm	1750 lm	3100 lm	3300 lm	Delivered Lumens (lm)
78 lm/W	78 lm/W	83 lm/W	85 lm/W	Efficacy (lm/W)
80	80	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	Color Temperature (CCT)
0-10V	0-10V	0-10V	0-10V	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

Additional CCT available, contact MaxLite for info.

LED Recessed Downlight Retrofits Architectural Series

4" MODEL



MODEL NUMBER	DLR41030	DLR41040
Input Wattage	11W	11W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	1130 lm	1100 lm
Efficacy (lm/W)	98 lm/W	100 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	4000K
Dimming Compatible	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V
Lumen Maintenance (L70)	100,000 hours	100,000 hours
CERTIFICATIONS	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®

4" MODEL



MODEL NUMBER	DLR41530	DLR41540	DLR42030	DLR42040
Input Wattage	20W	20W	28W	28W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	1840 lm	1800 lm	2360 lm	2300 lm
Efficacy (lm/W)	90 lm/W	90 lm/W	90 lm/W	82 lm/W
Color Rendering Index (CRI)	80	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V
Lumen Maintenance (L70)	100,000 hours	100,000 hours	100,000 hours	100,000 hours
CERTIFICATIONS	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®

LED Recessed Downlight Retrofits Architectural Series



6" MODEL



DLR61030	DLR61040	DLR61530	DLR61540	MODEL NUMBER
11W	11W	20W	20W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
1160 lm	1100 lm	1830 lm	1930 lm	Delivered Lumens (lm)
104 lm/W	100 lm/W	91 lm/W	96 lm/W	Efficacy (lm/W)
80	80	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	Color Temperature (CCT)
Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Dimming Compatible
100,000 hours	100,000 hours	100,000 hours	100,000 hours	Lumen Maintenance (L70)
cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS



6" MODEL



DLR62030	DLR62040	DLR63030	DLR63040	MODEL NUMBER
28W	28W	38W	38W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
2450 lm	2540 lm	3100 lm	3200 lm	Delivered Lumens (lm)
84 lm/W	86 lm/W	82 lm/W	84 lm/W	Efficacy (lm/W)
80	80	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	Color Temperature (CCT)
Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Dimming Compatible
100,000 hours	100,000 hours	100,000 hours	100,000 hours	Lumen Maintenance (L70)
cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

LED Recessed Downlight Retrofits Architectural Series

8" MODEL



MODEL NUMBER	DLR81030	DLR81040	DLR81530	DLR81540
Input Wattage	11W	11W	20W	20W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	1210 lm	1220 lm	1910 lm	1990 lm
Efficacy (lm/W)	110 lm/W	96 lm/W	96 lm/W	100 lm/W
Color Rendering Index (CRI)	80	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V
Lumen Maintenance (L70)	100,000 hours	100,000 hours	100,000 hours	100,000 hours
CERTIFICATIONS	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®

8" MODEL



MODEL NUMBER	DLR82030	DLR82040	DLR83030	DLR83040	DLR85030	DLR85040
Input Wattage	28W	28W	38W	38W	60W	60W
Voltage	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2550 lm	2740 lm	3240 lm	3470 lm	5530 lm	5880 lm
Efficacy (lm/W)	87 lm/W	94 lm/W	94 lm/W	87 lm/W	85 lm/W	87 lm/W
Color Rendering Index (CRI)	80	80	80	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	0-10V	0-10V
Lumen Maintenance (L70)	100,000 hours	100,000 hours	100,000 hours	100,000 hours	100,000 hours	100,000 hours
CERTIFICATIONS	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®

LED Recessed Downlight Retrofits Architectural Series



9" MODEL



DLR91030	DLR91040	DLR91530	DLR91540	MODEL NUMBER
11W	11W	20W	20W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
1180 lm	1250 lm	1860 lm	1940 lm	Delivered Lumens (lm)
107 lm/W	114 lm/W	92 lm/W	97 lm/W	Efficacy (lm/W)
80	80	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	Color Temperature (CCT)
Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Dimming Compatible
100,000 hours	100,000 hours	100,000 hours	100,000 hours	Lumen Maintenance (L70)
cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS



9" MODEL



DLR92030	DLR92040	DLR93030	DLR93040	DLR95030	DLR95040	MODEL NUMBER
28W	28W	38W	38W	60W	60W	Input Wattage
120-277V	120-277V	120-277V	120-277V	120-277V	120-277V	Voltage
2540 lm	2580 lm	3400 lm	3300 lm	5560 lm	5560 lm	Delivered Lumens (lm)
85 lm/W	88 lm/W	84 lm/W	87 lm/W	85 lm/W	87 lm/W	Efficacy (lm/W)
80	80	80	80	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	3000K	4000K	Color Temperature (CCT)
Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	Triac (120V only) and 0-10V	0-10V	0-10V	Dimming Compatible
100,000 hours	100,000 hours	100,000 hours	100,000 hours	100,000 hours	100,000 hours	Lumen Maintenance (L70)
cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	cULus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

LED Commercial Recessed Downlight Fixtures

4" MODEL



MODEL NUMBER	RAF41530W/V2	RAF41540W/V2	RAF42330W	RAF42340W
Input Wattage	15W	15W	23W	23W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	790 lm	880 lm	1640 lm	1700 lm
Efficacy (lm/W)	56 lm/W	63 lm/W	71 lm/W	74 lm/W
Color Rendering Index (CRI)	85	85	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®

ACCESSORIES: Brushed Nickel Trim Ring available Model: RR4-BNRING

6" MODEL



MODEL NUMBER	RAF61530W/V2	RAF61540W/V2	RAF62330W	RAF62340W	RAF63030W	RAF63040W
Input Wattage	15W	15W	23W	23W	30W	30W
Voltage	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	830 lm	910 lm	1730 lm	1790 lm	2250 lm	2530 lm
Efficacy (lm/W)	59 lm/W	65 lm/W	75 lm/W	78 lm/W	75 lm/W	84 lm/W
Color Rendering Index (CRI)	85	85	80	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®

ACCESSORIES: Extended Trim Ring available Model: RR6-XWHTRING; Brushed Nickel Trim Ring available Model: RR6-BNRING

LED Commercial Recessed Downlight Fixtures



8" MODEL



RAF81530W/V2	RAF81540W/V2	RAF82330W	RAF82340W	RAF83030W	RAF83040W	MODEL NUMBER
15W	15W	23W	23W	30W	30W	Input Wattage
120-277V	120-277V	120-277V	120-277V	120-277V	120-277V	Voltage
880 lm	920 lm	1670 lm	1750 lm	2220 lm	2510 lm	Delivered Lumens (lm)
63 lm/W	66 lm/W	73 lm/W	76 lm/W	74 lm/W	84 lm/W	Efficacy (lm/W)
85	85	80	80	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	3000K	4000K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

ACCESSORIES: Extended Trim Ring available Model: RR8-XWHTRING; Brushed Nickel Trim Ring available Model: RR8-BNRING



4" MODEL



RCF41530W/V2	RCF41540W/V2	RCF42330W	RCF42340W	MODEL NUMBER
15W	15W	23W	23W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
790 lm	880 lm	1640 lm	1700 lm	Delivered Lumens (lm)
56 lm/W	63 lm/W	71 lm/W	74 lm/W	Efficacy (lm/W)
85	85	80	80	Color Rendering Index (CRI)
3000K	4000K	3000K	4000K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

ACCESSORIES: Brushed Nickel Trim Ring available Model: RR4-BNRING

LED Commercial Recessed Downlight Fixtures

6" MODEL



MODEL NUMBER	RCF61530W/V2	RCF61540W/V2	RCF62330W	RCF62340W	RCF63030W	RCF63040W
Input Wattage	15W	15W	23W	23W	30W	30W
Voltage	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	880 lm	920 lm	1400 lm	1790 lm	2250 lm	2530 lm
Efficacy (lm/W)	63 lm/W	66 lm/W	61 lm/W	78 lm/W	75 lm/W	84 lm/W
Color Rendering Index (CRI)	85	85	85	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®

ACCESSORIES: Extended Trim Ring available Model: RR6-XWHTRING

8" MODEL



MODEL NUMBER	RCF81530W/V2	RCF81540W/V2	RCF82330W	RCF82340W	RCF83030W	RCF83040W
Input Wattage	15W	15W	23W	23W	30W	30W
Voltage	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	880 lm	920 lm	1670 lm	1750 lm	2220 lm	2510 lm
Efficacy (lm/W)	63 lm/W	66 lm/W	73 lm/W	76 lm/W	74 lm/W	84 lm/W
Color Rendering Index (CRI)	85	85	80	80	80	80
Color Temperature (CCT)	3000K	4000K	3000K	4000K	3000K	4000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®	cETLus, RoHS, FCC, ENERGY STAR®

ACCESSORIES: Extended Trim Ring available Model: RR8-XWHTRING; Brushed Nickel Trim Ring available Model: RR8-BNRING

LED Adjustable Recessed Downlight Retrofits



6" MODEL



RRA61030W	RRA61041W	MODEL NUMBER
10W	10W	Input Wattage
120V	120V	Voltage
875 lm	875 lm	Delivered Lumens (lm)
88 lm/W	88 lm/W	Efficacy (lm/W)
80	80	Color Rendering Index (CRI)
3000K	4100K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Dimming Compatible
35,000 hours	35,000 hours	Lumen Maintenance (L70)
cULus (Damp Listed), RoHS, FCC	cULus (Damp Listed), RoHS, FCC	CERTIFICATIONS



WARM-ON-DIM

6" MODEL



RRA610SSW	MODEL NUMBER
10W	Input Wattage
120V	Voltage
645 lm	Delivered Lumens (lm)
64 lm/W	Efficacy (lm/W)
80	Color Rendering Index (CRI)
2000K-3000K	Color Temperature (CCT)
Triac (120V only)	Dimming Compatible
35,000 hours	Lumen Maintenance (L70)
cULus (Damp Listed), RoHS, FCC, ENERGY STAR® (Pending)	CERTIFICATIONS

LED Recessed Downlight Retrofits



5" & 6" MODEL
DAMP & WET LISTED
SUITABLE FOR SHOWER APPLICATIONS

MODEL NUMBER	RR61430W	RR61441W	RR61450W
Input Wattage	14W	14W	14W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	900 lm	950 lm	1000 lm
Efficacy (lm/W)	64 lm/W	68 lm/W	71 lm/W
Color Rendering Index (CRI)	85	85	80
Color Temperature (CCT)	3000K	4100K	5000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Damp & Wet Listed), RoHS, FCC, ENERGY STAR®	cETLus (Damp & Wet Listed), RoHS, FCC, ENERGY STAR®	cETLus (Damp & Wet Listed), FCC, ENERGY STAR®

4" MODEL



MODEL NUMBER	RR41127W-L4	RR41227WC-L4
Input Wattage	11W	12W
Voltage	120V	120V
Delivered Lumens (lm)	760 lm	760 lm
Efficacy (lm/W)	72 lm/W	65 lm/W
Color Rendering Index (CRI)	80	90
Color Temperature (CCT)	2700K	2700K
Dimming Compatible	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	35,000 hours	35,000 hours
CERTIFICATIONS	cULus (Wet Listed), RoHS, FCC, ENERGY STAR®	cULus (Wet Listed), RoHS, FCC, ENERGY STAR®, CA Title 24

LED Recessed Downlight Retrofits



6" MODEL



RR61227W-L4	RR61227WC-L4	MODEL NUMBER
12W	12W	Input Wattage
120V	120V	Voltage
940 lm	880 lm	Delivered Lumens (lm)
78 lm/W	73 lm/W	Efficacy (lm/W)
80	90	Color Rendering Index (CRI)
2700K	2700K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Dimming Compatible
35,000 hours	35,000 hours	Lumen Maintenance (L70)
cULus (Wet Listed), RoHS, FCC, ENERGY STAR®	cULus (Wet Listed), RoHS, FCC, CA Title 24, ENERGY STAR®	CERTIFICATIONS



6" MODEL



RR61827W-L4	RR61927WC-L4	MODEL NUMBER
18W	20W	Input Wattage
120V	120V	Voltage
1380 lm	1420 lm	Delivered Lumens (lm)
79 lm/W	72 lm/W	Efficacy (lm/W)
82	90	Color Rendering Index (CRI)
2700K	2700K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Dimming Compatible
35,000 hours	35,000 hours	Lumen Maintenance (L70)
cULus (Wet Listed), RoHS, FCC, ENERGY STAR®	cULus (Wet Listed), RoHS, FCC, CA Title 24, ENERGY STAR®	CERTIFICATIONS

LED Recessed Downlight Fixtures

REMODEL PRODUCTS



6" MODEL

MODEL NUMBER	RFR614ICAT30W	RFR614ICAT50W
Input Wattage	14W	14W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	900 lm	1000 lm
Efficacy (lm/W)	64 lm/W	71 lm/W
Color Rendering Index (CRI)	80	85
Color Temperature (CCT)	3000K	5000K
Dimming Compatible	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Damp & Wet Listed), IC & AT Rated, FCC	cETLus (Damp & Wet Listed), IC & AT Rated, FCC

NEW CONSTRUCTION PRODUCTS



6" MODEL

MODEL NUMBER	RF614ICAT30W	RF614ICAT50W
Input Wattage	14W	14W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	900 lm	1000 lm
Efficacy (lm/W)	64 lm/W	71 lm/W
Color Rendering Index (CRI)	80	85
Color Temperature (CCT)	3000K	5000K
Dimming Compatible	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Damp & Wet Listed), IC & AT Rated, FCC	cETLus (Damp & Wet Listed), IC & AT Rated, FCC

LED Faux Cans



4" MODEL



LFC41327W/V2*	LFC41330W/V2*	LFC41341W/V2*	MODEL NUMBER
12W	12W	12W	Input Wattage
120V	120V	120V	Voltage
540 lm	570 lm	630 lm	Delivered Lumens (lm)
45 lm/W	46 lm/W	47 lm/W	Efficacy (lm/W)
90	90	90	Color Rendering Index (CRI)
2700K	3000K	4100K	Color Temperature (CCT)
Triac	Triac	Triac	Dimming Compatible
30,000 hours	30,000 hours	30,000 hours	Lumen Maintenance (L70)
CSA (Wet Listed), RoHS, FCC, ENERGY STAR®	CSA (Wet Listed), RoHS, FCC, ENERGY STAR®	CSA (Wet Listed), RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

*Use with junction box.



6" MODEL



LFC61527W/V2*	LFC61530W/V2*	LFC61541W/V2*	MODEL NUMBER
15W	15W	15W	Input Wattage
120V	120V	120V	Voltage
920 lm	940 lm	988 lm	Delivered Lumens (lm)
63 lm/W	63 lm/W	63 lm/W	Efficacy (lm/W)
90	90	90	Color Rendering Index (CRI)
2700K	3000K	4100K	Color Temperature (CCT)
Triac	Triac	Triac	Dimming Compatible
30,000 hours	30,000 hours	30,000 hours	Lumen Maintenance (L70)
CSA (Wet Listed), RoHS, FCC, ENERGY STAR®	CSA (Wet Listed), RoHS, FCC, ENERGY STAR®	CSA (Wet Listed), RoHS, FCC, ENERGY STAR®	CERTIFICATIONS

*Use with junction box.

BayMAX™ LED Pendant High Bays

NARROW MODEL



MODEL NUMBER	MLLHP100USD12/N (EM)(MS)	MLLHP125USD12/N (EM)(MS)	MLLHP150USD12/N (EM)(MS)
Input Wattage	100W	124W	155W
Voltage	120-277V, 480V (OPT)	120-277V, 480V (OPT)	120-277V, 480V (OPT)
Delivered Lumens (lm)	11,660 lm	14,400 lm	14,970 lm
Efficacy (lm/W)	117 lm/W	116 lm/W	97 lm/W
Color Rendering Index (CRI)	87	87	87
Color Temperature (CCT)	5000K	5000K	5000K
Metal Halide Replacement	250W MH	250W MH	400W MH
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), DLC, FCC	cULus (Damp Listed), DLC, FCC	cULus (Damp Listed), DLC, FCC

125W models available only on special order basis and will not support inventory. Please call MaxLite for additional details.

12" diameter and weighs only 7.5 lbs.

For available options/accessories, see maxlite.com.

WIDE MODEL



MODEL NUMBER	MLLHP100USD12/W (EM)(MS)	MLLHP125USD12/W (EM)(MS)	MLLHP150USD12/W (EM)(MS)
Input Wattage	100W	124W	153W
Voltage	120-277V, 480V (OPT)	120-277V, 480V (OPT)	120-277V, 480V (OPT)
Delivered Lumens (lm)	12,550 lm	15,100 lm	16,640 lm
Efficacy (lm/W)	125 lm/W	122 lm/W	109 lm/W
Color Rendering Index (CRI)	87	87	87
Color Temperature (CCT)	5000K	5000K	5000K
Metal Halide Replacement	250W MH	250W MH	400W MH
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), DLC, FCC	cULus (Damp Listed), DLC, FCC	cULus (Damp Listed), DLC, FCC

125W models available only on special order basis and will not support inventory. Please call MaxLite for additional details.

12" diameter and weighs only 7.5 lbs.

For available options/accessories, see maxlite.com.

NEW**LED Acrylic Highbay Pendant****HP-080UVA-00H-500**

80W
120-277V
11,600 lm
141 lm/W
85
5000K
200W MH
0-10V
100,000 hours
cULus (Damp Listed), DLC Premium, FCC

MODEL NUMBER

Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Metal Halide Replacement
Dimming Compatible
Lumen Maintenance (L70)

CERTIFICATIONS

For available options/accessories, see maxlite.com.

**HP-120UVA-00H-500****HP-155UVA-00H-500**

120W	155W
120-277V	120-277V
16,800 lm	22,200 lm
140 lm/W	141 lm/W
85	85
5000K	5000K
400W MH	600W MH
0-10V	0-10V
100,000 hours	100,000 hours
cULus (Damp Listed), DLC Premium, FCC	cULus (Damp Listed), DLC Premium, FCC

MODEL NUMBER

Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Metal Halide Replacement
Dimming Compatible
Lumen Maintenance (L70)

CERTIFICATIONS

For available options/accessories, see maxlite.com.

BayMAX™ LED Linear High Bays



MODEL NUMBER	BLHT115USD4810 (MS)(EM)	BLHT150USD4815 (MS)(EM)	BLHT235USD4820 (MS)(EM)
Input Wattage	115W	150W	237W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	12,430 lm	17,130 lm	25,300 lm
Efficacy (lm/W)	118 lm/W	114 lm/W	106 lm/W
Color Rendering Index (CRI)	83	83	84
Color Temperature (CCT)	5000K	5000K	5000K
Metal Halide Replacement	250W MH	400W MH	400W MH
T8 Replacement	3X54T5HO; 4X32T8	4x54T5HO; 6x32T8	6x545HO; 8x32T8
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	85,000 hours	107,000 hours	110,000 hours
CERTIFICATIONS	cULus (Damp Listed), DLC, FCC	cULus (Damp Listed), DLC, FCC	cULus (Damp Listed), DLC, FCC

For available options/accessories, see maxlite.com.

High Performance High Bay

BayMAX™ LED Linear High Bay Fixture

- 115W = 250W MH
- 150W = 400W MH @ 15-25' ht.
- 235W = 400W MH @ 20-35' ht.
- Up to 25,000 lumens
- Quick connects for easy wiring
- Dimming
- Diffusers, doors, guards, and sensor options available
- Aisle and general lighting in warehouses

When a 400W metal halide is replaced with the 150W BayMAX, facilities can save \$2,335 in energy and maintenance over the lifetime of the fixture.

www.maxlite.com

ASSEMBLED IN THE
US
AND CANADA

MaxLite
A NEW WAVE OF LIGHT

LED T8 Lamp Ready Fixtures



4'
LAMP READY HIGH BAY



BLHT4XT8USE4810	BLHT6XT8USE4815	BLHT8XT8USE4820	MODEL NUMBER
4x T8 LED*	6x T8 LED*	8x T8 LED*	Number of Lamps
120-277V	120-277V	120-277V	Voltage
22W Per Lamp	22W Per Lamp	22W Per Lamp	Max Wattage
cULus (Damp Listed)	cULus (Damp Listed)	cULus (Damp Listed)	CERTIFICATIONS

Lamps not included. See Pages 83-85 for compatible T8 lamps.



4'
LAMP READY VAPOR TIGHT



LSV2XT8USE4806	LSV3XT8USE4806	MODEL NUMBER
2x T8 LED*	3x T8 LED*	Number of Lamps
120-277V	120-277V	Voltage
22W Per Lamp	22W Per Lamp	Max Wattage
cULus (Damp Listed)	cULus (Damp Listed)	CERTIFICATIONS

Lamps not included. See Pages 83-85 for compatible T8 lamps.



4'
LAMP READY LINEAR UTILITY STRIP



4'
LAMP READY UTILITY WRAP



LSS1XT8USE4802	LSS2XT8USE4803	LSU2XT8USE4806	LSU3XT8USE4806	MODEL NUMBER
1x T8 LED*	2x T8 LED*	2x T8 LED*	3x T8 LED*	Number of Lamps
120-277V	120-277V	120-277V	120-277V	Voltage
22W Per Lamp	22W Per Lamp	22W Per Lamp	22W Per Lamp	Max Wattage
cULus (Damp Listed)	cULus (Damp Listed)	cULus (Damp Listed)	cULus (Damp Listed)	CERTIFICATIONS

Lamps not included. See Pages 83-85 for compatible T8 lamps.

LED Cooler/Freezer Lamps & Cooler Door Fixtures **NEW**

48"

60"

72"

MODEL NUMBER	48RL1841	60RL2241	72RL3041
Input Wattage	19W	23W	29W
Voltage	24Vdc	24Vdc	24Vdc
Delivered Lumens (lm)	1450 lm	1820 lm	2220 lm
Efficacy (lm/W)	74 lm/W*	79 lm/W*	76 lm/W*
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	4100K	4100K	4100K
Dimming Compatible	Driver Dependent	Driver Dependent	Driver Dependent
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), DLC	cULus (Damp Listed), DLC	cULus (Damp Listed), DLC

*Using 100W driver.



36"

48"

60"

72"



MODEL NUMBER	36RDL41	48RDL41	60RDL41	72RDL41
Input Wattage	9W	12W	15W	18W
Voltage	24Vdc	24Vdc	24Vdc	24Vdc
Delivered Lumens (lm)	1043 lm	1390 lm	1567 lm	2033 lm
Efficacy (lm/W)	114 lm/W	115 lm/W	104 lm/W	112 lm/W
Color Rendering Index (CRI)	84	84	84	84
Color Temperature (CCT)	4100K	4100K	4100K	4100K
Dimming Compatible	Driver Dependent	Driver Dependent	Driver Dependent	Driver Dependent
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed)	cULus (Damp Listed)	cULus (Damp Listed)	cULus (Damp Listed)

NEW LED Polygon™ Linear Fixtures



4' MODEL



LSP4805UU44DV35 LSP4805UU44DV50		MODEL NUMBER
40W		Input Wattage
120-277V		Voltage
4633-4670 lm		Delivered Lumens (lm)
119 lm/W		Efficacy (lm/W)
84		Color Rendering Index (CRI)
3500K, 5000K		Color Temperature (CCT)
Very Wide Flood		Distribution
(2) F32T8		Fluorescent Equivalency
0-10V		Dimming Compatible
50,000 hours		Lumen Maintenance (L70)
cULus (Damp Listed)		CERTIFICATIONS

For available options/accessories, see maxlite.com.



8' MODEL



LSP9605UU55DV35 LSP9605UU55DV50		LSP9605UU80DV35 LSP9605UU80DV50		MODEL NUMBER
60W		80W		Input Wattage
120-277V		120-277V		Voltage
7423-7859 lm		9417-9880 lm		Delivered Lumens (lm)
128-132 lm/W		121-126 lm/W		Efficacy (lm/W)
84,85		84,85		Color Rendering Index (CRI)
3500K, 5000K		3500K, 5000K		Color Temperature (CCT)
Very Wide Flood		Very Wide Flood		Distribution
(3) F32T8, (1) F96T12		(4) F32T8, (2) F96T12		Fluorescent Equivalency
0-10V		0-10V		Dimming Compatible
50,000 hours		50,000 hours		Lumen Maintenance (L70)
cULus (Damp Listed)		cULus (Damp Listed)		CERTIFICATIONS

For available options/accessories, see maxlite.com.

LED Utility Wrap Fixtures

LENGTH: 24"



MODEL NUMBER	LSU2406SU30DV40 (MS)	LSU2406SU30DV50 (MS)
Input Wattage	32W	32W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	2900 lm	3020 lm
Efficacy (lm/W)	90 lm/W	92 lm/W
Color Rendering Index (CRI)	83	83
Color Temperature (CCT)	4000K	5000K
Distribution	Very Wide Flood	Very Wide Flood
Fluorescent Equivalency	(2) F17T8	(2) F17T8
Dimming Compatible	0-10V	0-10V
Lumen Maintenance (L70)	54,000 hours	54,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, DLC	cULus (Damp Listed), FCC, DLC

For available options/accessories, see maxlite.com.

LENGTH: 48"



MODEL NUMBER	LSU4806SU20DV40 (MS)(EM)	LSU4806SU20DV50 (MS)(EM)	LSU4806SU30DV40 (MS)(EM)	LSU4806SU30DV50 (MS)(EM)
Input Wattage	20W	20W	31W	31W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2190 lm	2170 lm	3580 lm	3230 lm
Efficacy (lm/W)	107 lm/W	107 lm/W	103 lm/W	103 lm/W
Color Rendering Index (CRI)	83	83	83	83
Color Temperature (CCT)	4000K	5000K	4000K	5000K
Distribution	Very Wide Flood	Very Wide Flood	Very Wide Flood	Very Wide Flood
Fluorescent Equivalency	(1-2) F32T8	(1-2) F32T8	(2) F32T8, (1) F54T5	(2) F32T8, (1) F54T5
Dimming Compatible	0-10V	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	76,000 hours	76,000 hours	76,000 hours	76,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, DLC	cULus (Damp Listed), FCC, DLC	cULus (Damp Listed), FCC, DLC	cULus (Damp Listed), FCC, DLC

For available options/accessories, see maxlite.com.

LED Utility Wrap Fixtures



LENGTH: 48"



LSU4806SU50DV40 (MS)(EM)	LSU4806SU50DV50 (MS)(EM)	MODEL NUMBER
48W	48W	Input Wattage
120-277V	120-277V	Voltage
4630 lm	4920 lm	Delivered Lumens (lm)
97 lm/W	97 lm/W	Efficacy (lm/W)
83	83	Color Rendering Index (CRI)
4000K	5000K	Color Temperature (CCT)
Very Wide Flood	Very Wide Flood	Distribution
(3-4) F32T8, (2) F54T5	(3-4) F32T8, (2) F54T5	Fluorescent Equivalency
0-10V	0-10V	Dimming Compatible
59,000 hours	59,000 hours	Lumen Maintenance (L70)
cULus (Damp Listed), FCC, DLC	cULus (Damp Listed), FCC, DLC	CERTIFICATIONS

For available options/accessories, see maxlite.com.

LED Utility Wraps are a cost-effective, energy-efficient lighting solution that meets the latest building and safety codes for high-occupancy dwellings, parking garages, stairwells and other commercial utility applications. Engineered with thermal- and lumen-balanced LED engines, Utility Wraps consume less power than fluorescent wrap-around fixtures while delivering high efficacy of up to 99 lumens per watt.



LED Vapor Tight Linear Fixtures



LENGTH: 24"



MODEL NUMBER	LSV2406SU30DV40 (MS)	LSV2406SU30DV50 (MS)
Input Wattage	32W	32W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	3080 lm	3110 lm
Efficacy (lm/W)	95 lm/W	95 lm/W
Color Rendering Index (CRI)	83	83
Color Temperature (CCT)	4000K	5000K
Distribution	Medium Flood	Medium Flood
Fluorescent Equivalency	(3) F17T8, (2) F24T5	(3) F17T8, (2) F24T5
Dimming Compatible	0-10V	0-10V
Lumen Maintenance (L70)	56,000 hours	56,000 hours
CERTIFICATIONS	cULus (Wet Listed), FCC, DLC	cULus (Wet Listed), FCC, DLC

Comes standard with clear lens. For translucent lens, add "TS" to the end of model number.
For available options/accessories, see maxlite.com.



LENGTH: 50"



MODEL NUMBER	LSV4806SU50DV50PKG	LSV4806SU50DV50PKGMS
Input Wattage	48W	48W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	4200 lm	4200 lm
Efficacy (lm/W)	89 lm/W	89 lm/W
Color Rendering Index (CRI)	81	81
Color Temperature (CCT)	5000K	5000K
Distribution	Parking Distribution	Parking Distribution
Fluorescent Equivalency	(3) F32T8	(3) F32T8
Dimming Compatible	0-10V	0-10V
Lumen Maintenance (L70)	54,000 hours	54,000 hours
CERTIFICATIONS	cULus (Wet Listed), FCC, DLC	cULus (Wet Listed), FCC, DLC

**PARKING GARAGE
W/ OCCUPANCY SENSOR**

Comes standard with clear lens. Not compatible with translucent lens.
For available options/accessories, see maxlite.com.

LED Vapor Tight Linear Fixtures



LENGTH: 50"



LSV4806SU30DV40 (MS)(EM)	LSV4806SU30DV50 (MS)(EM)	MODEL NUMBER
32W	32W	Input Wattage
120-277V	120-277V	Voltage
3940 lm	3510 lm	Delivered Lumens (lm)
112 lm/W	112 lm/W	Efficacy (lm/W)
83	83	Color Rendering Index (CRI)
4000K	5000K	Color Temperature (CCT)
Medium Flood	Medium Flood	Distribution
(3) F32T8, (2) F54T5	(3) F32T8, (2) F54T5	Fluorescent Equivalency
0-10V	0-10V	Dimming Compatible
76,000 hours	76,000 hours	Lumen Maintenance (L70)
cULus (Wet Listed), FCC, DLC	cULus (Wet Listed), FCC, DLC	CERTIFICATIONS

Comes standard with clear lens. For translucent lens, add "TS" to the end of model number (TS lens option pictured).
For available options/accessories, see maxlite.com.



LENGTH: 50"



LSV4806SU50DV40 (MS)(EM)	LSV4806SU50DV50 (MS)(EM)	MODEL NUMBER
48W	48W	Input Wattage
120-277V	120-277V	Voltage
5000 lm	5040 lm	Delivered Lumens (lm)
104 lm/W	104 lm/W	Efficacy (lm/W)
83	83	Color Rendering Index (CRI)
4000K	5000K	Color Temperature (CCT)
Medium Flood	Medium Flood	Distribution
(4) F32T8	(4) F32T8	Fluorescent Equivalency
0-10V	0-10V	Dimming Compatible
54,000 hours	54,000 hours	Lumen Maintenance (L70)
cULus (Wet Listed), FCC, DLC	cULus (Wet Listed), FCC, DLC	CERTIFICATIONS

Comes standard with clear lens. For translucent lens, add "TS" to the end of model number (TS lens option pictured).
For available options/accessories, see maxlite.com.

Plug-and-Play Lightbars



LENGTH: 6"




MODEL NUMBER	6LB27	6LB35	6LB50
Input Wattage	3W	3W	3W
Voltage	120V	120V	120V
Delivered Lumens (lm)	150 lm	150 lm	150 lm
Efficacy (lm/W)	51 lm/W	51 lm/W	51 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	2700K	3500K	5000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®

ACCESSORIES: See Page 40



LENGTH: 12"



**AMBIENT OUTPUT
w/ DIFFUSER**

MODEL NUMBER	12LB27AO	12LB35AO	12LB50AO
Input Wattage	5W	5W	5W
Voltage	120V	120V	120V
Delivered Lumens (lm)	250 lm	250 lm	250 lm
Efficacy (lm/W)	58 lm/W	58 lm/W	58 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	2700K	3500K	5000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®

ACCESSORIES: See Page 40

Plug-and-Play Lightbars



LENGTH: 12"



12LB27	12LB35	12LB50	MODEL NUMBER
7W	7W	7W	Input Wattage
120V	120V	120V	Voltage
370 lm	370 lm	370 lm	Delivered Lumens (lm)
58 lm/W	58 lm/W	58 lm/W	Efficacy (lm/W)
80	80	80	Color Rendering Index (CRI)
2700K	3500K	5000K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Triac (120V only)	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	CERTIFICATIONS

ACCESSORIES: See Page 40



**HIGH OUTPUT
w/ DIFFUSER**

LENGTH: 12"



12LB27HO	12LB35HO	12LB50HO	MODEL NUMBER
10W	10W	10W	Input Wattage
120V	120V	120V	Voltage
650 lm	650 lm	650 lm	Delivered Lumens (lm)
60 lm/W	60 lm/W	60 lm/W	Efficacy (lm/W)
80	80	80	Color Rendering Index (CRI)
2700K	3500K	5000K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Triac (120V only)	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	CERTIFICATIONS

ACCESSORIES: See Page 40

Plug-and-Play Lightbars



LENGTH: 24"



MODEL NUMBER	24LB27	24LB35	24LB50
Input Wattage	11W	11W	11W
Voltage	120V	120V	120V
Delivered Lumens (lm)	650 lm	650 lm	650 lm
Efficacy (lm/W)	60 lm/W	60 lm/W	60 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	2700K	3500K	5000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®

ACCESSORIES: See Page 40



LENGTH: 48"



MODEL NUMBER	48LB27	48LB35	48LB50
Input Wattage	24W	24W	24W
Voltage	120V	120V	120V
Delivered Lumens (lm)	1380 lm	1380 lm	1380 lm
Efficacy (lm/W)	59 lm/W	59 lm/W	59 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	2700K	3500K	5000K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®	cETLus (Damp Listed), NSF, DLC, ENERGY STAR®

ACCESSORIES: See Page 40

Plug-and-Play Lightbars



LENGTH: 72"



72LB27	72LB35	72LB50	MODEL NUMBER
36W	36W	36W	Input Wattage
120V	120V	120V	Voltage
1980 lm	1980 lm	1980 lm	Delivered Lumens (lm)
56 lm/W	56 lm/W	56 lm/W	Efficacy (lm/W)
80	80	80	Color Rendering Index (CRI)
2700K	3500K	5000K	Color Temperature (CCT)
Triac (120V only)	Triac (120V only)	Triac (120V only)	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	Lumen Maintenance (L70)
cETLus, NSF, DLC, ENERGY STAR®	cETLus, NSF, DLC, ENERGY STAR®	cETLus, NSF, DLC, ENERGY STAR®	CERTIFICATIONS

72" models available only on special order basis and will not support inventory

ACCESSORIES INCLUDED:



4" corner joiner for continuous runs



Quick-clip mounting bracket and screws



Bar-to-bar joiner



Alternative mounting option double-sided tape

OPTIONAL ACCESSORIES:



71219 - MLSDLBJL40G
Joiner lead 40"



71225 - MLSDLBLC48G
Line cord 48" w/ molded plug to demonstrate lightbars



71221 - MLSDLBJL70G
Hardwired lead 70"



72139 - MLSDLBJL12G
Joiner lead 12"



74085 - MLSDLB-CBOX
Lightbar connector box



74230 - MLSDLB-DBOX
Lightbar distribution box



71631- MLSDLBCONN S
Lightbar connection box - Unpainted



71645- MLSDLBCONN SW
Lightbar connection box - Painted

L-Form Linear LED Luminaire **NEW**

LENGTH: 48"



MODEL NUMBER

LF-4836U-40

Input Wattage	36W
Voltage	120-277V
Delivered Lumens (lm)	4500 lm
Efficacy (lm/W)	125 lm/W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	4100K
Fluorescent Equivalency	1 x 54W T5
Dimming Compatible	0-10V
Lumen Maintenance (L70)	100,000 hours
CERTIFICATIONS	cULus, DLC Premium, FCC

LENGTH: 48"



MODEL NUMBER

LF-4849U-40

Input Wattage	49W
Voltage	120-277V
Delivered Lumens (lm)	6100 lm
Efficacy (lm/W)	124 lm/W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	4100K
Fluorescent Equivalency	2 x 54W T5
Dimming Compatible	0-10V
Lumen Maintenance (L70)	100,000 hours
CERTIFICATIONS	cULus, DLC Premium, FCC

NEW LED Shop Light

LENGTH: 48"

**LS-4848U-50****MODEL NUMBER**

48W

Input Wattage

120-277V

Voltage

4000 lm

Delivered Lumens (lm)

83 lm/W

Efficacy (lm/W)

80

Color Rendering Index (CRI)

5000K

Color Temperature (CCT)

2 x 32W T8

Fluorescent Equivalency

0-10V

Dimming Compatible

50,000 hours

Lumen Maintenance (L70)

cULus, ENERGY STAR®, FCC

CERTIFICATIONS

The MaxLite Shop Light is designed to replace traditional fluorescent fixtures in both residential and commercial applications. Developed with a built in on/off chain and uniform light distribution, it is ideally suited for workshops, garages, and utility rooms.



LED Flush Mounts



TRADITIONAL SERIES



ARCHITECTURAL SERIES



TRANSITIONAL SERIES

MODEL NUMBER	ML2LA17MTRBNI927** ML2LA23LTRBNI827*** ML2LA23LTRBNI927**	ML2LA17MABNIP927** ML2LA23LABNIP927***	ML2LA17MTNBNI927** ML2LA17MTNORB927** ML2LA17MTNWH927**
Input Wattage	17W or 23W	17W or 23W	17W
Voltage	120V	120V	120V
Delivered Lumens (lm)	1000-1700 lm	1200-1800 lm	1104 lm
Efficacy (lm/W)	60-73 lm/W	66-78 lm/W	64 lm/W
Color Rendering Index (CRI)	80 or 90	80 or 90	90
Color Temperature (CCT)	2700K	2700K	2700K
Equivalent Wattage	40-60W	40-60W	75W
Dimming Compatible	Yes, ELV	Yes, ELV	Yes, ELV
Lumen Maintenance (L70)	35,000 hours	35,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, ENERGY STAR®	cULus (Damp Listed), FCC, ENERGY STAR®	cULus (Damp Listed), FCC, ENERGY STAR®

*Small **Medium ***Large
For additional finishes, see maxlite.com.



ALABASTER SERIES



PEARL SERIES




MUSHROOM SERIES

MODEL NUMBER	ML2LA17MALBNI927**	ML2LA23LPRBNIP927***	ML2LS12XSMBN927* ML2LS12XSMOR927*
Input Wattage	17W	23W	12W
Voltage	120V	120V	120V
Delivered Lumens (lm)	1000-1100 lm	1600-1700 lm	695 lm
Efficacy (lm/W)	60-65 lm/W	70-75 lm/W	57 lm/W
Color Rendering Index (CRI)	90	90	90
Color Temperature (CCT)	2700K	2700K	2700K
Equivalent Wattage	75W	125W	40W
Dimming Compatible	Yes, ELV	Yes, ELV	Yes, ELV
Lumen Maintenance (L70)	35,000 hours	35,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, ENERGY STAR®	cULus (Damp Listed), FCC, ENERGY STAR®	cULus (Damp Listed), FCC, ENERGY STAR®

*Small **Medium ***Large
For additional finishes, see maxlite.com.

LED Flush Mount Retrofits & Torchieres



NEW

7.5"



NEW

9"



FRK17X7.5-927	FRK23X9-927	MODEL NUMBER
17W	23W	Input Wattage
120V	120V	Voltage
1349 lm	1607 lm	Delivered Lumens (lm)
79 lm/W	70 lm/W	Efficacy (lm/W)
91	91	Color Rendering Index (CRI)
2700K	2700K	Color Temperature (CCT)
AC Driver on Board	AC Driver on Board	Engine Technology
Yes	Yes	Dimming Compatible
50,000 hours	50,000 hours	Lumen Maintenance (L70)
UL Classified	UL Classified	CERTIFICATIONS



BLACK



WHITE



ML1L112GU514ARB	ML1L112GU514ARW	MODEL NUMBER
12W	12W	Input Wattage
120V	120V	Voltage
1162 lm	1162 lm	Source Lumens (lm)
95 lm/W	95 lm/W	Efficacy (lm/W)
82	82	Color Rendering Index (CRI)
2700K	2700K	Color Temperature (CCT)
Omni	Omni	Beam Type
60W	60W	Equivalent Wattage
Yes, Rotary Knob	Yes, Rotary Knob	Dimming Compatible
25,000 hours	25,000 hours	Lumen Maintenance (L70)
ETL, ENERGY STAR®	ETL, ENERGY STAR®	CERTIFICATIONS

LED Semi Flush Mount, Vanity Bar & Wall Sconce



ALABASTER SERIES



VANITY BAR

MODEL NUMBER	ML3LA23MALBNI927***	ML8LS2ORBNI927
Input Wattage	23W	20W
Voltage	120V	120-277V
Delivered Lumens (lm)	1586 lm	1500 lm
Efficacy (lm/W)	67 lm/W	77 lm/W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	2700K
Equivalent Wattage	75W	75W
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, FCC, ENERGY STAR®	cULus (Damp Listed), FCC, ENERGY STAR®

*Small **Medium ***Large

For additional finishes, see maxlite.com.



WALL SCONCE

MODEL NUMBER	ML9LA17LCNBNI927	ML9LA23LCNBNI927
Input Wattage	17W	24W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	1550 lm	2075 lm
Efficacy (lm/W)	88 lm/W	85 lm/W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	2700K
Equivalent Wattage	75W	125W
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, ENERGY STAR®	cULus (Damp Listed), FCC, ENERGY STAR®

For additional finishes, see maxlite.com.

QuadroMAX[®]

UNIVERSAL, SCALABLE OUTDOOR LIGHTING FIXTURE



8

**Mounting
Options**

5

**Wattage
Configurations**

4

**Categories
of Lighting**

1

**Sleek
Body**

CONSULTING - SPECIFYING
engineer.
2016
**PRODUCT
OF THE YEAR**
FINALISTS



EC&M CATEGORY WINNER
PRODUCT OF THE YEAR 16



UNIVERSAL APPEAL

Meet QuadroMAX, a single fixture that can be scaled across four main categories of outdoor lighting (Area, Flood, Wall Pack, Canopy) and multiple applications. Using eight different mounting arms, the fixture can be customized into virtually any type of outdoor fixture.



MaxLite poles coming soon. Contact your local MaxLite sales rep for more info.



Area Light



Wall Pack




Flood Light



Canopy


BROAD LUMEN OUTPUT RANGE



5,700 Lumens

20,000 Lumens

COMPLETE PHOTOMETRIC DISTRIBUTION




Type II

Type III

Type IV

Type V

WARM TO COOL COLOR TEMPS



3000K

4000K

5000K

THREE FINISHES



Bronze

White

Black

20kV SURGE SUPPRESSOR



20kV Surge Suppressor

10-YEAR WARRANTY



10 YEAR WARRANTY

DLC PREMIUM LISTED



DLC PREMIUM LISTED

WIDE RANGE OF EQUIVALENCIES



175W MH

400W+ MH

MaxLite gives you one convenient way to order your QuadroMAX with two easy steps.



Light Engine
QM-5AU7T350N-B-BPC

Bracket
QM-SK-B

Full Fixture & Bracket

1 Choose Your Light Engine and Optional Sensor

The QuadroMAX fixture can be scaled up or down according to your project needs, so you receive a fixture that is sized right for the wattage, the application and your budget.

55W

80W

110W

135W

160W & 185W



6,090 lm

Equivalent to:
150W HID

9,060 lm

Equivalent to:
250W HID

12,290 lm

Equivalent to:
320W-400W HID

15,255 lm

Equivalent to:
400W HID

20,000 lm

Equivalent to:
400W HIDOrder Example: **QM-5AU7T350N-B-BPC**

FAMILY	LED ENGINES	DRIVER	DRIVER	DISTRIB.	CCT	MOUNT OPTIONS	FINISH	OCCUPANCY & PHOTOCELL OPTIONS
QM=	2A= 24 LEDs (55W) 6000-6300 lm 3A= 36 LEDs (80W) 9000-9300 lm 4A= 48 LEDs (110W) 12,000-12,600 lm 5A= 60 LEDs (135W) 14,800-15,500 lm 6A= 72 LEDs (160W or 185W)* 17,800-20,000 lm	U= 120-277V H= 347-480V**	7= 700mA 8= 800mA**	T2= Type II T3= Type III T4= Type IV T5= Type V	30= 3000K 40= 4000K 50= 5000K	N= None C= Canopy	B= Bronze W= White L= Black	(OMIT)= None MS4= Sensor (Hi/Low/Off) RPC= NEMA Rotatable Photocell Receptacle (std.) PR5= Photocell Receptacle 5-Pin PR7= Photocell Receptacle 7-Pin BPC= Button Photocontrol

*Depends on Drive Current
**5-Year Limited Warranty

2 Choose Your Mounting Options



Rigid Pole Mount



Slipfitter Knuckle



Slipfitter Fixed



Fixed Surface



Knuckle Surface



Trunnion Swivel



Wall Pack



Canopy Mount

Order Example: **QM-SK-B**

FAMILY	MOUNTING	FINISH
QM=	PM= Rigid Pole Mount SK= Slipfitter Knuckle SF= Slipfitter Fixed FS= Fixed Surface KS= Knuckle Surface TS= Trunnion Swivel WP= Wall Pack	B= Bronze W= White L= Black

Canopy mount included with fixture if selected.
Not sold separately.

Church Converts to Energy Saving Benefits of LED Lighting from MaxLite

The First Baptist Church of Bethalto, Illinois was looking to update its facility with improved lighting that provided energy savings. The 25,000-square-foot building and exterior were lit by an aging system of fluorescent and metal halide fixtures that had become prohibitively expensive and labor intensive to maintain. Converting to LED was the ideal solution because of its lower energy consumption and longevity. Working with local representative agency Cool City Lights, the church replaced the lighting throughout the property with MaxLite LED lamps and fixtures.

The most dramatic transformation occurred on the exterior of the building, where many of the fixtures were no longer functional. Six 400-watt metal halide pole-top fixtures in the parking lot were replaced with QuadroMAX, MaxLite's universal and scalable outdoor luminaire, in a 160-watt, 5000K configuration. Delivering exceptional efficacy of 110 lumens per watt, QuadroMAX can be customized for virtually any type of outdoor lighting application by applying one of eight different mounting arms to a universal body to create a canopy, area, flood or wall pack luminaire.



Photos by Scott Evers



"We were very pleased with the lighting upgrades. The biggest improvement was in the parking lot. Previous dark spots have been eliminated, and the safety of those coming and going from the Church has improved."

- Tom Howland, Trustee, First Baptist Church

Use QuadroMAX for virtually any type of outdoor lighting application.



Area Light



Wall Pack



Flood Light



Canopy



Quickest Turnarounds
We keep the QuadroMAX in stock and just add the mounting part you need. This means customers can order a specification-grade, customizable fixture that ships in the same amount of time as a standard product.



Best-In-Class Protection
The QuadroMAX is engineered with state-of-the-art LEDs and 20KV surge suppression to protect the fixture from power surges. A maintenance-free lifetime of 100,000 hours, limited ten-year warranty and lifetime customer support make the QuadroMAX the smart choice for converting lighting systems to the energy- and cost saving benefits of LED.

LED Area Luminaires



ARX25UT550BOAO	ARX25UT550BOKO	MODEL NUMBER
252W	252W	Input Wattage
120-277V	120-277V	Voltage
28,980 lm	28,980 lm	Delivered Lumens (lm)
115 lm/W	115 lm/W	Efficacy (lm/W)
75	75	Color Rendering Index (CRI)
5000K	5000K	Color Temperature (CCT)
Type V	Type V	Distribution
Yes	Yes	Dimming Compatible
100,000 hours	100,000 hours	Longevity (Life Hours) L85
4" Square Pole Arm	2 3/8" Slipfitter	Mounting
cULus, DLC Premium	cULus, DLC Premium	CERTIFICATIONS



MELR300U350**	MODEL NUMBER
318W	Input Wattage
120-277V*	Voltage
37,200 lm	Delivered Lumens (lm)
117 lm/W	Efficacy (lm/W)
75	Color Rendering Index (CRI)
5000K	Color Temperature (CCT)
Type III	Distribution
No	Dimming Compatible
118,000 hours	Longevity (Life Hours) L70
Slipfitter	Mounting
cULus, DLC	CERTIFICATIONS

*347-480V Models Available

**All models also available in Type I and Type II

For additional optic versions, see maxlite.com.

LED Area & Barn Luminaires



Available in Bronze & White



MODEL NUMBER	MAL55AU7T550B	MAL80AU7T550B	MAL105AU7T550B
Input Wattage	55W	80W	105W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	5770 lm	8435 lm	11,315 lm
Efficacy (lm/W)	105 lm/W	104 lm/W	102 lm/W
Color Rendering Index (CRI)	70	70	70
Color Temperature (CCT)	5000K	5000K	5000K
Distribution	Type V	Type V	Type V
Dimming Compatible	0-10V	0-10V	0-10V
Replacement Wattage	250W	320W	400W
Longevity (Life Hours) L70	200,000 hours	200,000 hours	200,000 hours
CERTIFICATIONS	cULus, DLC Premium	cULus, DLC Premium	cULus, DLC

Available in high volatage. Available in 4000K.
 For available optic versions, see maxlite.com.
 Patent pending MaxFOCUS™ light collimator



MODEL NUMBER	BP35AUT550BPMO	BP45AUT550BPMO
Input Wattage	34 W	45W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	3325 lm	5005 lm
Efficacy (lm/W)	99 lm/W	113 lm/W
Color Rendering Index (CRI)	78	70
Color Temperature (CCT)	5000K	5000K
Distribution	Type V	Type V
Dimming Compatible	No	No
Replacement Wattage	150W HPS	175W MH
Longevity (Life Hours) L70	100,000 hours	100,000 hours
CERTIFICATIONS	cULus, DLC	cULus, DLC

LED Wall Packs



Available in
Bronze & White

**WPS30AU50B**

26W	MODEL NUMBER
120-277V	Input Wattage
2195 lm	Voltage
85 lm/W	Delivered Lumens (lm)
82	Efficacy (lm/W)
5000K	Color Rendering Index (CRI)
Type IV	Color Temperature (CCT)
0-10V	Distribution
150W MH	Dimming Compatible
145,000 hours	Replacement Wattage
cULus, DLC	Longevity (Life Hours) L70
	CERTIFICATIONS

For available options/accessories, see maxlite.com.



NEW



Available in
Bronze & White

**WPL40AU50B****WPL55AU50B****WPL80AU50B**

WPL40AU50B	WPL55AU50B	WPL80AU50B	MODEL NUMBER
38W	53W	77W	Input Wattage
120-277V	120-277V	120-277V	Voltage
3480 lm	4775 lm	8600 lm	Delivered Lumens (lm)
91 lm/W	90 lm/W	113 lm/W	Efficacy (lm/W)
84	82	80	Color Rendering Index (CRI)
5000K	5000K	5000K	Color Temperature (CCT)
Type IV	Type IV	Type IV	Distribution
0-10V	0-10V	0-10V	Dimming Compatible
175W MH	250W MH	400W MH	Replacement Wattage
145,000 hours	145,000 hours	145,000 hours	Longevity (Life Hours) L70
cULus, DLC	cULus, DLC	cULus, DLC	CERTIFICATIONS

For available options/accessories, see maxlite.com.

LED Wall Packs & Medium Flood Lights



Available in
Bronze & White



MODEL NUMBER	WPCS20AU50B	WPCS30AU50B
Input Wattage	19W	26W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	2195 lm	3025 lm
Efficacy (lm/W)	116 lm/W	117 lm/W
Color Rendering Index (CRI)	80	82
Color Temperature (CCT)	5000K	5000K
Distribution	Type V	Type V
Dimming Compatible	0-10V	0-10V
Replacement Wattage	100W	150W
Longevity (Life Hours) L70	145,000 hours	145,000 hours
CERTIFICATIONS	cULus, DLC Premium	cULus, DLC Premium

For available options/accessories, see maxlite.com.



Available in
Bronze & White



MODEL NUMBER	WPCL40AU50B	WPCL55AU50B
Input Wattage	39W	53W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	4475 lm	6120 lm
Efficacy (lm/W)	116 lm/W	116 lm/W
Color Rendering Index (CRI)	83	82
Color Temperature (CCT)	5000K	5000K
Distribution	Type V	Type V
Dimming Compatible	0-10V	0-10V
Replacement Wattage	175W	250W
Longevity (Life Hours) L70	145,000 hours	145,000 hours
CERTIFICATIONS	cULus, DLC Premium	cULus, DLC Premium

LED Adjustable Wall Packs



SAW SERIES



SAW13U50B	SAW26U50B	MODEL NUMBER
14W	29W	Input Wattage
120-277V	120-277V	Voltage
1165 lm	2345 lm	Delivered Lumens (lm)
82 lm/W	81 lm/W	Efficacy (lm/W)
70	70	Color Rendering Index (CRI)
5000K	5000K	Color Temperature (CCT)
No	No	Dimming Compatible
100W	175W	Replacement Wattage
120,000 hours	120,000 hours	Longevity (Life Hours) L70
IP66, cULus, DLC	IP66, cULus, DLC	CERTIFICATIONS

SS = 10kA Surge Suppression Available

Adjustable from 0-90°

For available options/accessories, see maxlite.com.



LAW SERIES

4" Pole Adapter
for LAW LAWPA

LAW74U50B	MODEL NUMBER
74W	Input Wattage
120-277V	Voltage
6230 lm	Delivered Lumens (lm)
85 lm/W	Efficacy (lm/W)
70	Color Rendering Index (CRI)
5000K	Color Temperature (CCT)
No	Dimming Compatible
250W	Replacement Wattage
120,000 hours	Longevity (Life Hours) L70
IP66, cULus, DLC	CERTIFICATIONS

SS = 10kA Surge Suppression Available

Adjustable from 0-90°

For available options/accessories, see maxlite.com.

LED Security Lights



Available in
Bronze & White



BATTERY BACKUP



MODEL NUMBER	SECL15U50BPCITEM	SECA15U50BPC12
Input Wattage	13W	15W
Voltage	120-277V	120V
Delivered Lumens (lm)	1050 lm	1450 lm
Efficacy (lm/W)	82 lm/W	97 lm/W
Color Rendering Index (CRI)	70	80
Color Temperature (CCT)	5000K	5000K
Dimming Compatible	No	No
Replacement Wattage	30-42W CFL	30-42W CFL
Longevity (Life Hours) L70	120,000 hours	120,000 hours
CERTIFICATIONS	cULus, DLC	cULus, DLC

For available options/accessories, see maxlite.com.



MODEL NUMBER	SEC12U50BPC12	SEC12U50BPC27
Input Wattage	12W	12W
Voltage	120V	208-277V
Delivered Lumens (lm)	1300 lm	1225 lm
Efficacy (lm/W)	107 lm/W	97 lm/W
Color Rendering Index (CRI)	83	83
Color Temperature (CCT)	5000K	5000K
Dimming Compatible	No	No
Replacement Wattage	100W	100W
Longevity (Life Hours) L70	135,000 hours	135,000 hours
CERTIFICATIONS	cETLus, ENERGY STAR®	cETLus

For available options/accessories, see maxlite.com.

NEW LED Bullet Floods

Shroud Accessory available.
Sold separately.



BF12AUDT30B000*	BF12AUDN30B000*	BF12AUDM30B000*	BF12AUDW30B000	MODEL NUMBER
11W	11W	11W	11W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
1175 lm	1165 lm	1150 lm	1200 lm	Delivered Lumens (lm)
108 lm/W	107 lm/W	106 lm/W	111 lm/W	Efficacy (lm/W)
72	72	72	72	Color Rendering Index (CRI)
3000K, 5000K	3000K, 5000K	3000K, 5000K	3000K, 5000K	Color Temperature (CCT)
25° Tight	30° Narrow	35° Medium	60° Wide	Beam Angle
No	No	No	No	Dimming Compatible
50W QH	50W QH	50W QH	50W QH	Replacement Wattage
100,000 hours	100,000 hours	100,000 hours	100,000 hours	Longevity (Life Hours) L70
cULus, DLC Premium	cULus, DLC Premium	cULus, DLC Premium	cULus, DLC Premium	CERTIFICATIONS

***Made-to-order items**

For available options/accessories, see maxlite.com.



Shroud Accessory available.
Sold separately.



BF30AUDT30B000*	BF30AUDN30B000*	BF30AUDM30B000*	BF30AUDW30B000	MODEL NUMBER
28W	28W	28W	28W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
3225 lm	3250 lm	3060 lm	3120 lm	Delivered Lumens (lm)
118 lm/W	118 lm/W	111 lm/W	114 lm/W	Efficacy (lm/W)
72	72	72	72	Color Rendering Index (CRI)
3000K, 5000K	3000K, 5000K	3000K, 5000K	3000K, 5000K	Color Temperature (CCT)
10° Tight	20° Narrow	35° Medium	60° Wide	Beam Angle
No	No	No	No	Dimming Compatible
150W MH	150W MH	150W MH	150W MH	Replacement Wattage
100,000 hours	100,000 hours	100,000 hours	100,000 hours	Longevity (Life Hours) L70
cULus, DLC Premium	cULus, DLC Premium	cULus, DLC Premium	cULus, DLC Premium	CERTIFICATIONS

***Made-to-order items**

For available options/accessories, see maxlite.com.

LED Small Floods



Available in
Bronze & White



LANDSCAPE



MODEL NUMBER	FLS15U50B	FLS20U50B
Input Wattage	14W	19W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	1260 lm	1985 lm
Efficacy (lm/W)	95 lm/W	109 lm/W
Color Rendering Index (CRI)	82	82
Color Temperature (CCT)	5000K	5000K
Beam Angles	97°	101°
Dimming Compatible	No	No
Replacement Wattage	100W QH	150W MH
Longevity (Life Hours) L70	210,000 hours	210,000 hours
CERTIFICATIONS	cULus, DLC	cULus, DLC

Also available in 4000K
For available options/accessories, see maxlite.com.



Available in
Bronze & White



FLOOD



MODEL NUMBER	FLS40U50B	FLS50U50B
Input Wattage	36W	49W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	4010 lm	5290 lm
Efficacy (lm/W)	112 lm/W	108 lm/W
Color Rendering Index (CRI)	84	74
Color Temperature (CCT)	5000K	5000K
Beam Angles	104°	108°
Dimming Compatible	No	No
Replacement Wattage	175W MH	250W MH
Longevity (Life Hours) L70	55,000 hours	55,000 hours
CERTIFICATIONS	cULus, DLC	cULus, DLC

Also available in 4000K
For available options/accessories, see maxlite.com.

LED Architectural Floods



AFB50U641KSB	AFC80U641KLB	MODEL NUMBER
52W	76W	Input Wattage
120-277V	120-277V	Voltage
5660 lm	8070 lm	Delivered Lumens (lm)
115 lm/W	107 lm/W	Efficacy (lm/W)
70	70	Color Rendering Index (CRI)
4000K	4000K	Color Temperature (CCT)
NEMA 6x6	NEMA 6x6	Beam Angles
No	No	Dimming Compatible
175W	250W	Replacement Wattage
100,000 hours	100,000 hours	Longevity (Life Hours) L70
IP65, cULus, DLC	IP65, cULus, DLC	CERTIFICATIONS

SS = 10kA Surge Suppression Available

For available options/accessories, see maxlite.com.



AFD110U641KLB	AFD150U341KLB	MODEL NUMBER
114W	152W	Input Wattage
120-277V	120-277V	Voltage
12,010 lm	13,990 lm	Delivered Lumens (lm)
105 lm/W	93 lm/W	Efficacy (lm/W)
70	70	Color Rendering Index (CRI)
4000K	4000K	Color Temperature (CCT)
NEMA 6x6	NEMA 3x3	Beam Angles
No	No	Dimming Compatible
400W	400W	Replacement Wattage
100,000 hours	100,000 hours	Longevity (Life Hours) L70
IP65, cULus, DLC	IP65, cULus, DLC	CERTIFICATIONS


SS = 10kA Surge Suppression Available

For available options/accessories, see maxlite.com.

LED Medium Floods



Available in Bronze & White



MODEL NUMBER	MFL55AU7T550B
Input Wattage	55W
Voltage	120-277V
Delivered Lumens (lm)	5772 lm
Efficacy (lm/W)	105 lm/W
Color Rendering Index (CRI)	70
Color Temperature (CCT)	5000K
Distribution	Type V
Dimming Compatible	0-10V
Replacement Wattage	250W
Longevity (Life Hours) L70	200,000 hours
CERTIFICATIONS	cULus, DLC Premium

Available in high volatage. Available in 4000K.
For available optic versions, see maxlite.com.
Patent pending MaxFOCUS™ light collimator



Available in Bronze & White



MODEL NUMBER	MFL80AU7T550B	MFL105AU7T550B
Input Wattage	80W	105W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	8435 lm	11,315 lm
Efficacy (lm/W)	104 lm/W	102 lm/W
Color Rendering Index (CRI)	70	70
Color Temperature (CCT)	5000K	5000K
Distribution	Type V	Type V
Dimming Compatible	0-10V	0-10V
Replacement Wattage	320W	400W
Longevity (Life Hours) L70	200,000 hours	200,000 hours
CERTIFICATIONS	cULus, DLC Premium	cULus, DLC

Available in high volatage. Available in 4000K.
For available optic versions, see maxlite.com.
Patent pending MaxFOCUS™ light collimator

NEW ModMax High Output Flood

MM210UW50FDG	MM420UWW50FDG	MODEL NUMBER
218W	445W	Input Wattage
120-277V	120-277V	Voltage
19,545 lm	38,440 lm	Delivered Lumens (lm)
89 lm/W	86 lm/W	Efficacy (lm/W)
85	85	Color Rendering Index (CRI)
5000K	5000K	Color Temperature (CCT)
57°	57°	Beam Angle
No	No	Dimming Compatible
400W	1000W	Replacement Wattage
200,000 hours	200,000 hours	Longevity (Life Hours) L70
cULus	cULus	CERTIFICATIONS



MM630UWW50FDG	MODEL NUMBER
663W	Input Wattage
120-277V	Voltage
56,355 lm	Delivered Lumens (lm)
90 lm/W	Efficacy (lm/W)
85	Color Rendering Index (CRI)
5000K	Color Temperature (CCT)
57°	Beam Angle
No	Dimming Compatible
1500W	Replacement Wattage
200,000 hours	Longevity (Life Hours) L70
cULus	CERTIFICATIONS

StaxMAX™ LED High Output Floods



MODEL NUMBER	ELLF180DW50	ELLF360DW50
Input Wattage	178W	356W
Voltage	120-277V*	120-277V*
Delivered Lumens (lm)	18,970 lm	37,940 lm
Efficacy (lm/W)	104 lm/W	104 lm/W
Color Rendering Index (CRI)	75	75
Color Temperature (CCT)	5700K	5700K
Beam Angle	18°/58°/111°	18°/58°/111°
Dimming Compatible	0-10V	0-10V
Replacement Wattage	400W	1000W
Longevity (Life Hours) L70	75,000 hours	75,000 hours
CERTIFICATIONS	IP66, DLC, cULus	IP66, DLC, cULus

ACCESSORIES: See Page 62

***347-480V Models Available: ELLF1354N50, ELLF1354M50, ELLF1354W50**

For available accessories such as PTMB & HBMB mounting brackets, see maxlite.com.



MODEL NUMBER	ELLF540DW50
Input Wattage	534W
Voltage	120-277V*
Delivered Lumens (lm)	56,910 lm
Efficacy (lm/W)	104 lm/W
Color Rendering Index (CRI)	75
Color Temperature (CCT)	5700K
Beam Angle	18°/58°/111°
Dimming Compatible	0-10V
Replacement Wattage	1000W
Longevity (Life Hours) L70	75,000 hours
CERTIFICATIONS	IP66, DLC, cULus

ACCESSORIES: See Page 62

***347-480V Models Available: ELLF2704N50, ELLF2704M50, ELLF2704W50, ELLF2704C50**

For available accessories such as PTMB & HBMB mounting brackets, see maxlite.com.

StaxMAX™ Accessories



HBMB
bracket



AYMB
bracket

ELLF540D
with medium & narrow
optics*

*Each StaxMAX™ flood fixture module can be configured with either narrow, medium or wide optics.

ACCESSORIES:



PTMB
POLE TENON MOUNT BRACKET
To be used with
HBMB bracket only



PTMBC
CAP FOR POLE TENON
MOUNT BRACKET

ORDERING MODEL LOGIC: Typical Order Example: ELLF180DW50***

SERIES	TECH	TYPE	WATTAGE	VOLTAGE	DISTRIBUTION	CCT	BRACKET
EL = High Output Flood	L = LED	F = Flood	180 = 180W; 18,000 lm 360 = 360W; 36,000 lm 540 = 540W; 54,000 lm	D = 120-277V 4* = 387-480V	N = Narrow 22° M = Medium 55° W = Wide 120° C** = Custom	50 = 5000K	Blank = AYMB H = HBMB

*For 347V and 480V use wattage: 135, 270 or 405

**Item ordering is typically by common beam type; contact MaxLite for applications with mixed beam angles (custom) on same carriages.

LED Post Top Luminaires



MODEL NUMBER	PTD80UT541SMB
Input Wattage	82W
Voltage	120-277V
Delivered Lumens (lm)	6755 lm
Efficacy (lm/W)	82 lm/W
Color Rendering Index (CRI)	70
Color Temperature (CCT)	4000K
Distribution	Type V
Dimming Compatible	No
Replacement Wattage	250W MH
Longevity (Life Hours) L70	50,000 hours
CERTIFICATIONS	cULus, DLC

SS = 10kA Surge Suppression Available
Also available in Type III



MODEL NUMBER	PTD100UT541SMB
Input Wattage	116W
Voltage	120-277V
Delivered Lumens (lm)	9360 lm
Efficacy (lm/W)	81 lm/W
Color Rendering Index (CRI)	70
Color Temperature (CCT)	4000K
Distribution	Type V
Dimming Compatible	No
Replacement Wattage	400W MH
Longevity (Life Hours) L70	50,000 hours
CERTIFICATIONS	cULus, DLC

SS = 10kA Surge Suppression Available
Also available in Type III

LED Parking Luminaires



NEW

CPL40AUP50B000

41W	MODEL NUMBER
120-277V	Input Wattage
3965 lm	Voltage
96 lm/W	Delivered Lumens (lm)
80	Efficacy (lm/W)
5000K	Color Rendering Index (CRI)
Parking Garage	Color Temperature (CCT)
0-10V	Distribution
175W	Dimming Compatible
50,000 hours	Replacement Wattage
cULus, FCC	Longevity (Life Hours) L70
	CERTIFICATIONS



NEW

**CP25AUP50B000****CP40AUP50B000****CP55AUP50B000**

CP25AUP50B000	CP40AUP50B000	CP55AUP50B000	MODEL NUMBER
25W	39W	52W	Input Wattage
120-277V	120-277V	120-277V	Voltage
2650 lm	4015 lm	4990 lm	Delivered Lumens (lm)
106 lm/W	100 lm/W	95 lm/W	Efficacy (lm/W)
80	80	80	Color Rendering Index (CRI)
5000K	5000K	5000K	Color Temperature (CCT)
Parking Garage	Parking Garage	Parking Garage	Distribution
0-10V	0-10V	0-10V	Dimming Compatible
150W	175W	250W	Replacement Wattage
100,000 hours	100,000 hours	100,000 hours	Longevity (Life Hours) L70
cETLus, FCC, DLC Premium	cETLus, FCC, DLC Premium	cETLus, FCC, DLC Premium	CERTIFICATIONS

LED Canopy Luminaires



NEW



NEW

MOTION SENSOR



MODEL NUMBER	PKGS45UT550	PKGS45UT550MS
Input Wattage	46W	46W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	4770 lm	4930 lm
Efficacy (lm/W)	105 lm/W	108 lm/W
Color Rendering Index (CRI)	75	74
Color Temperature (CCT)	5000K	5000K
Distribution	Type V	Type V
Dimming Compatible	0-10V	0-10V
Replacement Wattage	250W	250W
Longevity (Life Hours) L70	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, FCC, DLC	cULus, FCC, DLC

All models available in 347-480V.
For available options/accessories, see maxlite.com.



MODEL NUMBER	CD40UT550CMB	CD60UT550CMB
Input Wattage	40W	60W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	3929 lm	6112 lm
Efficacy (lm/W)	97 lm/W	101 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	5000K	5000K
Distribution	Type V	Type V
Dimming Compatible	No	No
Replacement Wattage	175W	250W
Longevity (Life Hours) L70	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, DLC	cULus, DLC

SS = 10kA Surge Suppression Available
For available options/accessories, see maxlite.com.

LED Canopy Luminaires



CAN20U50B		CP25AUTC50B000		MODEL NUMBER
21W		25W		Input Wattage
120-277V		120-277V		Voltage
2475 lm		2795 lm		Delivered Lumens (lm)
118 lm/W		111 lm/W		Efficacy (lm/W)
75		80		Color Rendering Index (CRI)
5000K		5000K		Color Temperature (CCT)
Canopy		Canopy		Distribution
No		0-10V		Dimming Compatible
100W		150W		Replacement Wattage
160,000 hours		100,000 hours		Longevity (Life Hours) L70
cULus, DLC		cETLus, FCC, DLC Premium		CERTIFICATIONS

For available options/accessories, see maxlite.com.



CP40AUTC50B000		CP55AUTC50B000		MODEL NUMBER
39W		52W		Input Wattage
120-277V		120-277V		Voltage
4290 lm		5290 lm		Delivered Lumens (lm)
110 lm/W		101 lm/W		Efficacy (lm/W)
80		80		Color Rendering Index (CRI)
5000K		5000K		Color Temperature (CCT)
Canopy		Canopy		Distribution
0-10V		0-10V		Dimming Compatible
175W		250W		Replacement Wattage
100,000 hours		100,000 hours		Longevity (Life Hours) L70
cETLus, FCC, DLC Premium		cETLus, FCC, DLC Premium		CERTIFICATIONS

For available options/accessories, see maxlite.com.

StaxMAX™ LED Flood Lights for Hazardous Locations



MODEL NUMBER	ELLF135UW50AGSH12	ELLF270UW50AGSH12
Input Wattage	135W	270W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	15,830 lm	31,660 lm
Efficacy (lm/W)	112 lm/W	112 lm/W
Color Rendering Index (CRI)	75	75
Color Temperature (CCT)	5000K	5000K
Beam Angle	120°	120°
Dimming Compatible	0-10V	0-10V
Replacement Wattage	320-400W	700-720W
Longevity (Life Hours) L70	80,000 hours	80,000 hours
CERTIFICATIONS	IP65, DLC, cULus 1598 & 844	IP65, DLC, cULus 1598 & 844

Available in 18° & 58° beam angle. **ACCESSORIES:** See Page 62
 For available accessories such as PTMB & HBMB mounting brackets, see maxlite.com.



MODEL NUMBER	ELLF405UW50AGSH12
Input Wattage	405W
Voltage	120-277V
Delivered Lumens (lm)	47,490 lm
Efficacy (lm/W)	112 lm/W
Color Rendering Index (CRI)	75
Color Temperature (CCT)	5000K
Beam Angle	120°
Dimming Compatible	0-10V
Replacement Wattage	1000W
Longevity (Life Hours) L70	80,000 hours
CERTIFICATIONS	IP65, DLC, cULus 1598 & 844

Available in 18° & 58° beam angle. **ACCESSORIES:** See Page 62
 For available accessories such as PTMB & HBMB mounting brackets, see maxlite.com.

NEW HLRMax Hazardous Location

HLR80UW50xCG	HLR110UW50xCG	HLR140UW50xCG	HLR170UW50xCG	MODEL NUMBER
80W	110W	140W	170W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
9100 lm	12,525 lm	14,730 lm	17,895 lm	Delivered Lumens (lm)
110 lm/W	111 lm/W	106 lm/W	105 lm/W	Efficacy (lm/W)
74	74	74	74	Color Rendering Index (CRI)
5000K	5000K	5000K	5000K	Color Temperature (CCT)
120°	120°	120°	120°	Beam Angle
175-250W	400W	400W	400-600W	Replacement Wattage
50,000 hours	50,000 hours	50,000 hours	50,000 hours	Longevity (Life Hours) L70
cULus, FCC	cULus, FCC	cULus, FCC	cULus, FCC	CERTIFICATIONS

All models available in 347-480V.

For available options/accessories, see maxlite.com.

MOUNTING ACCESSORIES:

Wall 40°
HLRW40G



Wall 90°
HLRW90G



Stanchion 25°
HLRS22G



Stanchion 90°
HLRS92G



Swivel Clamp
HLRSCG



Swivel Surface
HLRSSG



Ceiling Mount
HLRCMG



Pendant

Pendant Mount: Accessory included with fixture when the "P" mounting option is ordered. Not sold separately.


LED Vapor Proof Jelly Jars



**Wire Guard
MLVPC14LED50CP**



MODEL NUMBER	MLVPC14LED50CP
Input Wattage	14W
Voltage	120-277V
Delivered Lumens (lm)	1125 lm
Efficacy (lm/W)	83 lm/W
Color Rendering Index (CRI)	66
Color Temperature (CCT)	5000K
Dimming Compatible	No
Replacement Wattage	100W INC
Longevity (Life Hours) L70	50,000 hours
CERTIFICATIONS	cULus



**Wire Guard
MLVPC14LED50CP**



MODEL NUMBER	MLVPC14LED50CP
Input Wattage	14W
Voltage	120-277V
Delivered Lumens (lm)	1120 lm
Efficacy (lm/W)	83 lm/W
Color Rendering Index (CRI)	66
Color Temperature (CCT)	5000K
Dimming Compatible	No
Replacement Wattage	100W INC
Longevity (Life Hours) L70	50,000 hours
CERTIFICATIONS	cULus

LED Recessed Gas Station Canopy



10YR WARRANTY



RC94U118LED50W

RC94U118LED50W		MODEL NUMBER
94W		Input Wattage
120-277V		Voltage
11,795 lm		Delivered Lumens (lm)
126 lm/W		Efficacy (lm/W)
80		Color Rendering Index (CRI)
5000K		Color Temperature (CCT)
No		Dimming Compatible
400W HID		Replacement Wattage
120,000 hours		Longevity (Life Hours) L70
cETLus, DLC		CERTIFICATIONS



RCX120AU50W000

RCX120AU50W000		MODEL NUMBER
126W		Input Wattage
120-277V		Voltage
15,765 lm		Delivered Lumens (lm)
123 lm/W		Efficacy (lm/W)
80		Color Rendering Index (CRI)
5000K		Color Temperature (CCT)
0-10V		Dimming Compatible
400W HID		Replacement Wattage
100,000 hours		Longevity (Life Hours) L70
cETLus, DLC Premium		CERTIFICATIONS



LED Lanterns



Available in Black & White



MEDIUM COACH LANTERN



MEDIUM LANTERN

MODEL NUMBER	ML4LS10MCLBK827	ML4LS12MOLW ML4LS12MOLB
Input Wattage	10W	12W
Voltage	120V	120V
Delivered Lumens (lm)	565 lm	511 lm
Efficacy (lm/W)	56 lm/W	41 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Replacement Wattage	40W	40W
Longevity (Life Hours) L70	35,000 hours	35,000 hours
CERTIFICATIONS	cULus (Wet Listed), FCC, ENERGY STAR®	cULus (Wet Listed), FCC, ENERGY STAR®

For available options/accessories, see maxlite.com.



Available in Black & White



RANCH LANTERN



SMALL LANTERN

MODEL NUMBER	ML4LS12SRLBK827	ML4LS10SOLB ML4LS10SOLW
Input Wattage	12W	10W
Voltage	120V	120V
Delivered Lumens (lm)	751 lm	552 lm
Efficacy (lm/W)	62 lm/W	55 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Replacement Wattage	40W	40W
Longevity (Life Hours) L70	35,000 hours	35,000 hours
CERTIFICATIONS	cULus (Wet Listed), FCC, ENERGY STAR®	cULus (Wet Listed), FCC, ENERGY STAR®

For available options/accessories, see maxlite.com.

LED Vintage Filament Lamps



SILVER BOWL A19
E26 BASE



TORPEDO
E12 BASE



TORPEDO
E26 BASE



SB6.5A19DLED27	V2.5B11DLED22	V2.5B11DLED22E	MODEL NUMBER
6.5W	2.5W	2.5W	Input Wattage
120V	120V	120V	Voltage
700 lm	250 lm	250 lm	Delivered Lumens (lm)
108 lm/W	100 lm/W	100 lm/W	Efficacy (lm/W)
80	80	80	Color Rendering Index (CRI)
2700K	2200K	2200K	Color Temperature (CCT)
60W	25W	25W	Equivalent Wattage
Yes	Yes	Yes	Dimming Compatible
15,000 hours	15,000 hours	15,000 hours	Longevity (Life Hours) L70
cULus	cULus	cULus	CERTIFICATIONS



VINTAGE A19
E26 BASE



VINTAGE T14
E26 BASE



VINTAGE ST18
E26 BASE



VINTAGE G30
E26 BASE



V4.5A19DLED22	V4.5T14DLED22	V6.5ST18DLED22	V6.5G30DLED22	MODEL NUMBER
4.5W	4.5W	6.5W	6.5W	Input Wattage
120V	120V	120V	120V	Voltage
400 lm	400 lm	620 lm	620 lm	Delivered Lumens (lm)
89 lm/W	89 lm/W	95 lm/W	95 lm/W	Efficacy (lm/W)
80	80	80	80	Color Rendering Index (CRI)
2200K	2200K	2200K	2200K	Color Temperature (CCT)
40W	40W	60W	60W	Equivalent Wattage
Yes	Yes	Yes	Yes	Dimming Compatible
15,000 hours	15,000 hours	15,000 hours	15,000 hours	Longevity (Life Hours) L70
cULus	cULus	cULus	cULus	CERTIFICATIONS

LED Marquee, Candelabra & Globe Lamps

CLEAR
E12 BASECLEAR
E26 BASEFROSTED
E26 BASE

MODEL NUMBER	SKBC2.0CDLED27	SKBC2.5DLED27	SKBF2.5DLED27
Input Wattage	2.0W	2.5W	2.5W
Voltage	120V	120V	120V
Delivered Lumens (lm)	75 lm	125 lm	125 lm
Efficacy (lm/W)	38 lm/W	50 lm/W	50 lm/W
Color Rendering Index (CRI)	81	80	80
Equivalent Wattage	10-15W	10-15W	10-15W
Color Temperature (CCT)	2700K	2700K	2700K
Dimming Compatible	No	No	No
Longevity (Life Hours) L70	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus	cETLus (Wet Listed)	cETLus (Wet Listed)



E12 BASE



E26 BASE



E26 BASE



MODEL NUMBER	5B11DLED27*	6G25DLED27*	14G40DLED30*
Input Wattage	5W	6W	14W
Voltage	120V	120V	120V
Delivered Lumens (lm)	325 lm	450 lm	1300 lm
Efficacy (lm/W)	65 lm/W	75 lm/W	93 lm/W
Color Rendering Index (CRI)	82	82	82
Equivalent Wattage	40W	40W	150W
Color Temperature (CCT)	2700K	2700K	3000K
Dimming Compatible	Yes	Yes	Yes
Longevity (Life Hours) L70	15,000 hours	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®	cULus, ENERGY STAR®	ETL, ENERGY STAR®

*ENERGY STAR® for these models only

LED G4 & G9 Retrofit Lamps



**12V
BI-PIN BASE**



**12V
WEDGE BASE**

2.5G4LED27

2.5W

12V AC/DC

180 lm

72 lm/W

80

20W

2700K

No

25,000 hours

TUV

2.5WDGLED27

2.5W

12V AC/DC

180 lm

72 lm/W

80

20W

2700K

No

25,000 hours

TUV

MODEL NUMBER

Input Wattage

Voltage

Delivered Lumens (lm)

Efficacy (lm/W)

Color Rendering Index (CRI)

Equivalent Wattage

Color Temperature (CCT)

Dimming Compatible

Longevity (Life Hours) L70

CERTIFICATIONS

**SKG0903LED27
SKG0903DLED27 (DIM)**

3W

120V

275 lm, 220 lm

92 lm/W, 73 lm/W

80

25W

2700K

No, Yes

25,000 hours

TUV



**SKG0905LED27
SKG0905DLED27 (DIM)**

5W

120V

430 lm, 350 lm

86 lm/W, 70 lm/W

80

40W

2700K

No, Yes

25,000 hours

TUV

MODEL NUMBER

Input Wattage

Voltage

Delivered Lumens (lm)

Efficacy (lm/W)

Color Rendering Index (CRI)

Equivalent Wattage

Color Temperature (CCT)

Dimming Compatible

Longevity (Life Hours) L70

CERTIFICATIONS

LED Omni-Directional A Lamps Traditional Shape

E26 BASE



A19



A19



A19
90+ CRI



A19



A21

MODEL NUMBER

6A19DLED27/G2*	9A19DLED27*	9.5A19DLED927*	11A19DLED27/G2*	15A21DLED27/G2*
6A19DLED30/G2*	9A19DLED30*	9.5A19DLED930*	11A19DLED30/G2*	15A21DLED30/G2*
6A19DLED40/G2	9A19DLED40*		11A19DLED40/G2*	15A21DLED40/G2*

Input Wattage	6W	9W	9.5W	11W	15W
Voltage	120V	120V	120V	120V	120V
Delivered Lumens (lm)	470 lm	800 lm	800 lm	1100 lm	1600 lm
Efficacy (lm/W)	78 lm/W	89 lm/W	84 lm/W	100 lm/W	107 lm/W
Color Rendering Index (CRI)	82	82	91-92	82	82
Equivalent Wattage	40W	60W	60W	75W	100W
Color Temperature (CCT)	2700K, 3000K, 4000K	2700K, 3000K, 4000K	2700K, 3000K	2700K, 3000K, 4000K	2700K, 3000K, 4000K
Dimming Compatible	Yes	Yes	Yes	Yes	Yes
Longevity (Life Hours) L70	25,000 hours	25,000 hours	25,000 hours	25,000 hours	25,000 hours

CERTIFICATIONS

cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, CA Title 24 ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®
---------------------	---------------------	---------------------------------	---------------------	---------------------

*ENERGY STAR® for these models only

GU24 BASE



A19



A19



A19
90+ CRI



A19



A21

MODEL NUMBER

6A19GUDLED27/G2*	9A19GUDLED27/G2*	9.5A19GUDLED930/G2*	11A19GUDLED27/G2*	15A21GUDLED27/G2*
6A19GUDLED30/G2*	9A19GUDLED30/G2*		11A19GUDLED30/G2*	15A21GUDLED30/G2*
6A19GUDLED40/G2	9A19GUDLED40/G2*		11A19GUDLED40/G2*	15A21GUDLED40/G2*

Input Wattage	6W	9W	9.5W	11W	15W
Voltage	120V	120V	120V	120V	120V
Delivered Lumens (lm)	470 lm	800 lm	800 lm	1100 lm	1600 lm
Efficacy (lm/W)	78 lm/W	89 lm/W	84 lm/W	100 lm/W	107 lm/W
Color Rendering Index (CRI)	82	82	91-92	82	82
Equivalent Wattage	40W	60W	60W	75W	100W
Color Temperature (CCT)	2700K, 3000K, 4000K	2700K, 3000K, 4000K	3000K	2700K, 3000K, 4000K	2700K, 3000K, 4000K
Dimming Compatible	Yes	Yes	Yes	Yes	Yes
Longevity (Life Hours) L70	25,000 hours	25,000 hours	25,000 hours	25,000 hours	25,000 hours

CERTIFICATIONS

cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, CA Title 24 ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®
---------------------	---------------------	---------------------------------	---------------------	---------------------

*ENERGY STAR® for these models only

LED Omni-Directional A Lamps



A19



A19

E26 BASE



11A19DLED30*	12A19DLED30-141*	MODEL NUMBER
11W	12W	Input Wattage
120V	120V	Voltage
800 lm	800 lm	Delivered Lumens (lm)
73 lm/W	67 lm/W	Efficacy (lm/W)
82	81	Color Rendering Index (CRI)
60W	60W	Equivalent Wattage
3000K	3000K	Color Temperature (CCT)
Yes	Yes	Dimming Compatible
25,000 hours	25,000 hours	Longevity (Life Hours) L70
cULus, ENERGY STAR®	cULus, ENERGY STAR®	CERTIFICATIONS

*ENERGY STAR® for these models only

A19
90+ CRI E26 BASEA19
90+ CRI GU24 BASEA19
E26 BASE

12A19DLED930*	12A19GUDLED930*	12A19DLED27* 12A19DLED30* 12A19DLED41*	MODEL NUMBER
12W	12W	12W	Input Wattage
120V	120V	120V	Voltage
800 lm	800 lm	1100 lm	Delivered Lumens (lm)
67 lm/W	67 lm/W	92 lm/W	Efficacy (lm/W)
95	95	82	Color Rendering Index (CRI)
60W	60W	75W	Equivalent Wattage
3000K	3000K	2700K, 3000K, 4100K	Color Temperature (CCT)
Yes	Yes	Yes	Dimming Compatible
25,000 hours	25,000 hours	25,000 hours	Longevity (Life Hours) L70
cULus, CA Title 24 ENERGY STAR®	cULus, CA Title 24 ENERGY STAR®	cULus, ENERGY STAR®	CERTIFICATIONS

*ENERGY STAR® for these models only

LED Omni-Directional Enclosed Rated, 3-Way A Lamps & Non-Dimmable A19



NEW



**A19
E26 BASE**



NEW



**A19
GU24 BASE**

MODEL NUMBER	E9A19DLED27* E9A19DLED30*	E9A19GUDLED27* E9A19GUDLED30*
Input Wattage	9W	9W
Voltage	120V	120V
Delivered Lumens (lm)	800 lm	800 lm
Efficacy (lm/W)	89 lm/W	89 lm/W
Color Rendering Index (CRI)	82	82
Equivalent Wattage	60W	60W
Color Temperature (CCT)	2700K, 3000K	2700K, 3000K
Dimming Compatible	Yes	Yes
Longevity (Life Hours) L70	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®	cULus, ENERGY STAR®

***ENERGY STAR® for these models only**



NEW

**A21 3-WAY
E26 BASE**



NEW

**A19 NON-DIMMABLE
E26 BASE**

MODEL NUMBER	17A21/3WLED27* 17A21/3WLED30*	9A19LED27/G4*
Input Wattage	5/10/17W	9.5W
Voltage	120V	120V
Delivered Lumens (lm)	450/800/1600 lm	800 lm
Efficacy (lm/W)	94 lm/W	94 lm/W
Color Rendering Index (CRI)	82	82
Equivalent Wattage	40/60/100W	60W
Color Temperature (CCT)	2700K, 3000K	2700K
Dimming Compatible	Yes	No
Longevity (Life Hours) L70	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®	cULus, ENERGY STAR®

***ENERGY STAR® for these models only**

LED MR16 Lamps



GU5.3 BASE



GU10 BASE



7MR16LED30FL*	7MR16GUDLED30FL	MODEL NUMBER
7W	7W	Input Wattage
12V	120V	Voltage
400 lm	450 lm	Delivered Lumens (lm)
57 lm/W	64 lm/W	Efficacy (lm/W)
81	80	Color Rendering Index (CRI)
42W	42W	Equivalent Wattage
3000K	3000K	Color Temperature (CCT)
No	Yes	Dimming Compatible
25,000 hours	25,000 hours	Longevity (Life Hours) L70
cULus, ENERGY STAR®	cULus	CERTIFICATIONS

*ENERGY STAR® for these models only



GU5.3 BASE



GU10 BASE

GU10 BASE
90+ CRI

6.5MR16DLED27FL 6.5MR16DLED30FL	6.5MR16GUDLED27FL 6.5MR16GUDLED30FL	6MR16GUDLED930FL	MODEL NUMBER
6.5W	6.5W	6W	Input Wattage
12V	12V	120V	Voltage
500 lm	500 lm	400 lm	Delivered Lumens (lm)
77 lm/W	77 lm/W	67 lm/W	Efficacy (lm/W)
82	82	90	Color Rendering Index (CRI)
42-50W	42-50W	50W	Equivalent Wattage
2700K, 3000K	2700K, 3000K	3000K	Color Temperature (CCT)
Yes	Yes	Yes	Dimming Compatible
25,000 hours	25,000 hours	40,000 hours	Longevity (Life Hours) L70
cULus	cULus	cULus, CA Title 24	CERTIFICATIONS

*ENERGY STAR® for these models only

LED PAR Lamps

NEW



PAR20



**PAR30
SHORT NECK**



**PAR30
LONG NECK**



**277V PAR30
LONG NECK**



MODEL NUMBER	7P20DLED27NF/G2* 7P20DLED27FL/G2* 7P20DLED30NF* 7P20DLED30FL/G2* 7P20DLED40NF/G2 7P20DLED40FL/G2*	12P30DLED27NF* 12P30DLED27FL* 12P30DLED30NF* 12P30DLED30FL* 12P30DLED41NF 12P30DLED41FL	12P30LNDLED27NF/G2* 12P30LNDLED27FL/G2* 12P30LNDLED30NF/G2* 12P30LNDLED30FL/G2* 12P30LNDLED40NF/G2 12P30LNDLED40FL/G2*	13P30LNLED230FL 13P30LNLED240FL
---------------------	--	--	---	------------------------------------

Input Wattage	7W	12W	12W	13W
Voltage	120V	120V	120V	277V
Delivered Lumens (lm)	470 lm	850 lm	850 lm	1000-1200 lm
Efficacy (lm/W)	67 lm/W	71 lm/W	71 lm/W	77-92 lm/W
Color Rendering Index (CRI)	82	80	80	82
Equivalent Wattage	50W	75W	75W	90W
Color Temperature (CCT)	2700K, 3000K, 4000K	2700K, 3000K, 4100K	2700K, 3000K, 4000K	3000K, 4000K
Dimming Compatible	Yes	Yes	Yes	No
Longevity (Life Hours) L70	25,000 hours	25,000 hours	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®	cRUus

***ENERGY STAR® for these models only**



PAR38



**PAR38
WET LISTED**



277V PAR38



MODEL NUMBER	15P38DLED27NF/G2* 15P38DLED27FL/G2* 15P38DLED30NF/G2* 15P38DLED30FL/G2* 15P38DLED40NF/G2 15P38DLED40FL/G2*	17P38DLED27FL* 17P38DLED30FL* 17P38DLED41FL 17P38DLED50FL	17P38LED230FL 17P38LED240FL
---------------------	---	--	--------------------------------

Input Wattage	15W	17W	17W
Voltage	120V	120V	277V
Delivered Lumens (lm)	1050 lm	1300 lm	1700-1800 lm
Efficacy (lm/W)	70 lm/W	76 lm/W	100-106 lm/W
Color Rendering Index (CRI)	80	80	82
Equivalent Wattage	120W	150W	90W
Color Temperature (CCT)	2700K, 3000K, 4000K	2700K, 3000K, 4100K, 5000K	3000K, 4000K
Dimming Compatible	Yes	Yes	No
Longevity (Life Hours) L70	25,000 hours	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®	cULus (Wet Listed)	cRUus

***ENERGY STAR® for these models only**

LED BR Lamps

NEW**BR20****BR30****BR30****BR30
90+ CRI**


7BR20DLED27/G2* 7BR20DLED30/G2* 7BR20DLED40/G2*	8BR30DLED27/G2* 8BR30DLED30/G2* 8BR30DLED40/G2*	11BR30DLED27/G2* 11BR30DLED30/G2* 11BR30DLED40/G2*	12BR30DLED927/G2* 12BR30DLED930/G2*	MODEL NUMBER
7W	8W	11W	12W	Input Wattage
120V	120V	120V	120V	Voltage
550 lm	650 lm	850 lm	800 lm	Delivered Lumens (lm)
79 lm/W	81 lm/W	77 lm/W	67 lm/W	Efficacy (lm/W)
82	82	82	94	Color Rendering Index (CRI)
50W	65W	65W	65W	Equivalent Wattage
2700K, 3000K, 4000K	2700K, 3000K, 4000K	2700K, 3000K, 4000K	2700K, 3000K	Color Temperature (CCT)
Yes	Yes	Yes	Yes	Dimming Compatible
25,000 hours	25,000 hours	25,000 hours	25,000 hours	Longevity (Life Hours) L70
cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, CA Title 24, ENERGY STAR®	CERTIFICATIONS

***ENERGY STAR® for these models only****BR40
90+ CRI****BR40**

14BR40DLED930/G2*	17BR40DLED27/G2* 17BR40DLED30/G2* 17BR40DLED40/G2*	MODEL NUMBER
14W	17W	Input Wattage
120V	120V	Voltage
1000 lm	1400 lm	Delivered Lumens (lm)
71 lm/W	82 lm/W	Efficacy (lm/W)
93	80	Color Rendering Index (CRI)
75W	100W	Equivalent Wattage
3000K	2700K, 3000K, 4000K	Color Temperature (CCT)
Yes	Yes	Dimming Compatible
25,000 hours	25,000 hours	Longevity (Life Hours) L70
cULus, CA Title 24, ENERGY STAR®	cULus, ENERGY STAR®	CERTIFICATIONS

***ENERGY STAR® for these models only**

LED PL, T8 UBend & T8/T5 Linear Direct Fit Lamps



**T8 UBEND
BALLAST COMPATIBLE**

**HORIZONTAL MOUNT PL
BALLAST COMPATIBLE**

**VERTICAL MOUNT PL
BALLAST COMPATIBLE**

	U16T8DF235 U16T8DF240 U16T8DF250	13PLG24QHLED27 13PLG24QHLED35 13PLG24QHLED41	13PLG24QVLED27 13PLG24QVLED35 13PLG24QVLED41
MODEL NUMBER			
Input Wattage	16W (Bare Lamp)	13W	13W
Voltage	(Ballast Dependent)	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	1800 lm	850-900 lm	850-900 lm
Color Rendering Index (CRI)	85	84	84
Equivalent Wattage	32W Fluorescent	26-42W	26-42W
Color Temperature (CCT)	3500K, 4000K, 5000K	2700K, 3500K, 4100K	2700K, 3500K, 4100K
Dimming Compatible	No	No	No
Longevity (Life Hours) L70	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus	UL Classified	UL Classified

NEW



**T8 4'
GLASS**

**T8 4'
COATED GLASS**

**T5 4'
COATED GLASS**



	L14T8DF435-G L14T8DF440-G L14T8DF450-G	L15T8DF435-CG L15T8DF440-CG L15T8DF450-CG	L27T5DF435-CG L27T5DF440-CG L27T5DF450-CG
MODEL NUMBER			
Input Wattage	14W (Bare Lamp)	15W (Bare Lamp)	27W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	1800 lm	1850-2000 lm	3100-3400 lm
Color Rendering Index (CRI)	85	83	83
Equivalent Wattage	32W Fluorescent	32W Fluorescent	54W HO Fluorescent
Color Temperature (CCT)	3500K, 4000K, 5000K	3500K, 4000K, 5000K	3500K, 4000K, 5000K
Dimming Compatible	No	Yes (Ballast Dependent)	No
Longevity (Life Hours) L70	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	DLC, cULus, NSF	DLC, cULus, ETL Sanitation	DLC, cULus, ETL Sanitation

LED PL Retrofit Lamps



E26 BASE




G24Q BASE



GU24 BASE



GX23 BASE



6PLE26LED27 6PLE26LED30	6PLG24QLED27 6PLG24QLED30 6PLG24QLED35 6PLG24QLED40 6PLG24QLED50	6PLGU24LED27 6PLGU24LED30 6PLGU24LED40	6PLGX23LED27 6PLGX23LED35 6PLGX23LED40 6PLGX23LED50	MODEL NUMBER
6W	6W	6W	6W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
500 lm	500-525 lm	500-525 lm	500-525 lm	Delivered Lumens (lm)
83 lm/W	83-88 lm/W	83-88 lm/W	83-88 lm/W	Efficacy (lm/W)
85	85	85	85	Color Rendering Index (CRI)
13W CFL	13W CFL	13W CFL	13W CFL	Equivalent Wattage
2700K, 3000K	2700K, 3000K, 3500K, 4000K, 5000K	2700K, 3000K, 4000K	2700K, 3500K, 4000K, 5000K	Color Temperature (CCT)
No	No	No	No	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	50,000 hours	Longevity (Life Hours) L70
cULus	UL Classified	cULus	UL Classified	CERTIFICATIONS



E26 BASE




G24Q BASE



GU24 BASE



GX23 BASE



8PLE26LED27 8PLE26LED30	8PLG24QLED27 8PLG24QLED30 8PLG24QLED35 8PLG24QLED40 8PLG24QLED50	8PLGU24LED27 8PLGU24LED30 8PLGU24LED40	8PLGX23LED27 8PLGX23LED35 8PLGX23LED40 8PLGX23LED50	MODEL NUMBER
8W	8W	8W	8W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
675 lm	675-725 lm	675-725 lm	675-725 lm	Delivered Lumens (lm)
84 lm/W	84-91 lm/W	84-91 lm/W	84-91 lm/W	Efficacy (lm/W)
85	85	85	85	Color Rendering Index (CRI)
18W CFL	18W CFL	18W CFL	18W CFL	Equivalent Wattage
2700K, 3000K	2700K, 3000K, 3500K, 4000K, 5000K	2700K, 3000K, 4000K	2700K, 3500K, 4000K, 5000K	Color Temperature (CCT)
No	No	No	No	Dimming Compatible
50,000 hours	50,000 hours	50,000 hours	50,000 hours	Longevity (Life Hours) L70
cULus	UL Classified	cULus	UL Classified	CERTIFICATIONS

LED Linear T8 Internal Driver



2'

MODEL NUMBER	L10T8SE235* L10T8SE241 L10T8SE250
Input Wattage	10W
Voltage	120-277V
Delivered Lumens (lm)	1050 lm
Efficacy (lm/W)	105 lm/W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3500K, 4100K, 5000K
Dimming Compatible	No
Replacement Wattage	17W Fluorescent
Longevity (Life Hours) L70	50,000 hours
CERTIFICATIONS	DLC, UL Classified

*Special Order Only



3'

MODEL NUMBER	L10T8SE341
Input Wattage	10W
Voltage	120-277V
Delivered Lumens (lm)	1080 lm
Efficacy (lm/W)	108 lm/W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	4100K
Dimming Compatible	No
Replacement Wattage	25W Fluorescent
Longevity (Life Hours) L70	50,000 hours
CERTIFICATIONS	UL Classified

LED Linear T8 Internal Driver

4'
GLASS4'
GLASS

L15T8SE435-G
L15T8SE440-G
L15T8SE450-G
L15T8SE465-G*

L18T8SE435-G
L18T8SE440-G
L18T8SE450-G

		MODEL NUMBER
	15W	18W
	120-277V	120-277V
	1800 lm	2200 lm
	120 lm/W	122 lm/W
	85	85
	3500K, 4000K, 5000K, 6500K	3500K, 4000K, 5000K
	No	No
	32W Fluorescent	32W Fluorescent
	50,000 hours	50,000 hours
	DLC, UL Classified	DLC, UL Classified
		CERTIFICATIONS



*6500K is not DLC Certified

NEW

5'



6'

		MODEL NUMBER
	L19T8SE540-G	L31T8SE641
	19W	31W
	120-277V	120-277V
	2500 lm	3250 lm
	131 lm/W	105 lm/W
	82	82
	4000K	4100K
	No	No
	40W Fluorescent	70W Fluorescent
	50,000 hours	50,000 hours
	UL Classified	UL Classified
		CERTIFICATIONS

High Efficiency LED Linear T8 Internal Driver


10
YEAR
WARRANTY

NEW
4'
GLASS

4'
GLASS - 10YR WARRANTY

MODEL NUMBER	L12.5T8SE435-G* L12.5T8SE440-G L12.5T8SE450-G	L12.5T8SE440-G10 L12.5T8SE450-G10
Input Wattage	12.5W	12.5W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	1800 lm	1800 lm
Efficacy (lm/W)	144 lm/W	144 lm/W
Color Rendering Index (CRI)	85	85
Color Temperature (CCT)	3500K, 4000K, 5000K	4000K, 5000K
Dimming Compatible	No	No
Replacement Wattage	32W Fluorescent	32W Fluorescent
Longevity (Life Hours) L70	50,000 hours	100,000 hours
CERTIFICATIONS	DLC, UL Classified	DLC, UL Classified

*Special Order Only


10
YEAR
WARRANTY

NEW
4'
GLASS

4'
GLASS - 10YR WARRANTY

MODEL NUMBER	L16.5T8SE435-G* L16.5T8SE440-G L16.5T8SE450-G	L16.5T8SE440-G10* L16.5T8SE450-G10*
Input Wattage	16.5W	16.5W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	2200 lm	2200 lm
Efficacy (lm/W)	133 lm/W	133 lm/W
Color Rendering Index (CRI)	85	85
Color Temperature (CCT)	3500K, 4000K, 5000K	4000K, 5000K
Dimming Compatible	No	No
Replacement Wattage	32W Fluorescent	32W Fluorescent
Longevity (Life Hours) L70	50,000 hours	100,000 hours
CERTIFICATIONS	DLC, UL Classified	DLC, UL Classified

*Special Order Only

LED Puck Lamps



E26 BASE
(SUITABLE FOR
ENCLOSED FIXTURE)



E26 BASE
(SUITABLE FOR
ENCLOSED FIXTURE)



GU24 BASE
(SUITABLE FOR
ENCLOSED FIXTURE)



LEPM03A0927	9PUADLED27 9PUADLED30	9PUAGULED27 9PUAGULED30	MODEL NUMBER
9W	9W	9W	Input Wattage
120V	120V	120V	Voltage
800 lm	800-850 lm	800-850 lm	Delivered Lumens (lm)
89 lm/W	89-94 lm/W	89-94 lm/W	Efficacy (lm/W)
82	80	80	Color Rendering Index (CRI)
60W	60W	60W	Equivalent Wattage
2700K	2700K, 3000K	2700K, 3000K	Color Temperature (CCT)
Yes	Yes	Yes	Dimming Compatible
25,000 hours	25,000 hours	25,000 hours	Longevity (Life Hours) L70
cULus	cULus (Wet Listed)	cULus (Wet Listed)	CERTIFICATIONS



NON-DIMMABLE
E26 BASE
(SUITABLE FOR
ENCLOSED FIXTURE)



NON-DIMMABLE
GU24 BASE
(SUITABLE FOR
ENCLOSED FIXTURE)



NON-DIMMABLE
**COMPACT
E26 BASE**
(SUITABLE FOR
ENCLOSED FIXTURE)



NON-DIMMABLE
**COMPACT
GU24 BASE**
(SUITABLE FOR
ENCLOSED FIXTURE)



10PUALED27 10PUALED30	10PUAGULED27 10PUAGULED30	10CPALED27 10CPALED30	10CPUGULED27 10CPUGULED30	MODEL NUMBER
10W	10W	10W	10W	Input Wattage
120-277V	120-277V	120-277V	120-277V	Voltage
850-900 lm	850-900 lm	900-1000 lm	900-1000 lm	Delivered Lumens (lm)
85-90 lm/W	85-90 lm/W	90-100 lm/W	90-100 lm/W	Efficacy (lm/W)
80	80	80	80	Color Rendering Index (CRI)
60W	60W	60W	60W	Equivalent Wattage
2700K, 3000K	2700K, 3000K	2700K, 3000K	2700K, 3000K	Color Temperature (CCT)
No	No	No	No	Dimming Compatible
25,000 hours	25,000 hours	25,000 hours	25,000 hours	Longevity (Life Hours) L70
cULus (Wet Listed - 120V)	cULus (Wet Listed - 120V)	cULus (Wet Listed - 120V)	cULus (Wet Listed - 120V)	CERTIFICATIONS

Specialty LED Retrofit Lamps



E39 BASE



E39 BASE

MODEL NUMBER	BLHR43UN27B	BLHR43UN50B
Input Wattage	43W	43W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	3900 lm	4300 lm
Efficacy (lm/W)	91 lm/W	100 lm/W
Color Rendering Index (CRI)	73	73
Color Temperature (CCT)	2700K	5000K
MH Replacement Wattage	100W	100W
Longevity (Life Hours) L70	50,000 hours	50,000 hours
CERTIFICATIONS	cULus	cULus



E26 BASE



E26 BASE



E39 BASE




E39 BASE



MODEL NUMBER	SKPT12LEDU30E26 SKPT12LEDU50E26	SKPT20LEDU30E26 SKPT20LEDU50E26	SKPT30LEDU30E39 SKPT30LEDU50E39	SKPT50LEDU30E39 SKPT50LEDU50E39
Input Wattage	12W	20W	30W	50W
Voltage	120V-277V	120V-277V	120V-277V	120V-277V
Delivered Lumens (lm)	1100 lm	1800 lm	3000-3300 lm	5000-5800 lm
Efficacy (lm/W)	92 lm/W	90 lm/W	100 lm/W	100 lm/W
Color Rendering Index (CRI)	82	82	80	80
Color Temperature (CCT)	3000K, 5100K	3000K, 5100K	3000K, 5000K	3000K, 5000K
MH Replacement Wattage	50W	75W	125W	175W
Longevity (Life Hours) L70	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus	cULus	DLC, cULus	DLC, cULus

MaxLite Tools & Resources

YouTube Channel (MaxLiteNewsRoom)



[Product Training Videos](#) | [Installation Videos](#)

Social Media (Follow us on...)



[LinkedIn](#)



[Twitter @MaxLite](#)



[Facebook](#)

MaxLite.com



[Product Datasheets](#) | [Case Studies](#) | [Catalogs & Brochures](#) | [ROI Calculator](#) | [Utility Rebate Finder](#) | [ENERGY STAR](#)

MaxLiteUniversity.com



[Free online lighting degree program](#) | [Eligible for ALA Credit Hours](#)

QuadroMAX.com



[Product videos, specs and ordering information](#)

Find, like and follow us on social media.




MaxLite®

A NEW WAVE OF LIGHT

www.maxlite.com



Item # LEDGENCATQ316
Ord. Code: 101745



Corporate Headquarters

12 York Ave.
West Caldwell, NJ 07006
T: 1-800-555-5629
F: 973-244-7333

California Facility

1148 North Ocean Circle
Anaheim, CA 92806
T: 1-800-793-1212
F: 714-678-5096