

One-piece nickel-plated steel strap with integral ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Cam control and spring actuator for positive "makes and breaks".



Auto-ground clip assures positive ground.

Shallow design for easier installation.

Glass-reinforced nylon back body for superior durability and strength.

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 – #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure-plate back wire.

PS20AC1-LA

Readily installed in the plant or at the office — you can rely on all of our switches for years of quiet, trouble-free operation.


HP Conversion Table – Switches

15 Amp	1/2 Horsepower at 120VAC 2 Horsepower at 240VAC
20 Amp	1 Horsepower at 120VAC 2 Horsepower at 240VAC
30 Amp	2 Horsepower at 120VAC 2 Horsepower at 240VAC


Index

Device	Rating	Page Number
Horsepower Rating Chart		A-1
Industrial Extra Heavy-Duty Spec. Grade Switches	15, 20 & 30A, 120, 277 & 120/277VAC	A-2
Lock Switch Keys		A-2
Extra Heavy-Duty Spec. Grade & Security Switches	15 & 20A, 347VAC; 20A, 120/277VAC	A-3
Hard Use & Commercial Specification Grade Switches	15 & 20A, 120/277VAC	A-4
Manual Controllers	30 & 40A 1Ø & 3Ø; 15, 20 & 30A, 120/277VAC; 60A NEMA 3R; 20 & 30A 1Ø	A-5 – A-9
TradeMaster® Grounding Toggle Switches	15A, 120VAC	A-10
TradeMaster® Non-Grounding Toggle Switches	15A, 120VAC	A-11
Grounding Combination Switches	15 & 20A, 120/277VAC; 15A, 120/125VAC; 20A, 120VAC	A-12
Non-Grounding Combination Switches	15 & 20A, 120/277VAC; 15A, 120/125VAC	A-13
Specification Grade Decorator Switches	15 & 20A, 120/277 & 347VAC; 20A, 120VAC	A-14
TradeMaster® Decorator Switches	15A, 120 & 120/277VAC	A-15
Momentary & Maintained Contact Switches	15A, 120 & 120/277VAC	A-16
Spec. Grade Decorator Combination Switches	20A, 277VAC	A-17
TradeMaster® Decorator Combination Switches	15A, 120/125 & 120/277VAC	A-18 – A-20
Decorator Combination Switch/GFCI Receptacles	15A, 125VAC	A-21
Canopy Switches & 911 Locator	15A, 120 & 250VAC; 15A, 120VAC	A-22


Pass & Seymour



15 & 20 Amp*



15 & 20 Amp Lighted & Pilot Lighted*




Locking*

*30AC series is 1.437" wide

Lock Switch Replacement Keys

(One key furnished with each switch)



All devices listed on this page conform to NEMA WD-1 and WD-6.

Switches

Industrial Extra Heavy-Duty Specification Grade Switches

15, 20 & 30A, 120, 277 & 120/277VAC

Features

- External screw-pressure-plate back and side wired. Accepts #14 – #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast “make” and positive “break” to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.

Catalog Number				Rating A. VAC	Color	3rd Party Compliance		
Single Pole	Double Pole	Three-Way	Four-Way			UL20	FSUL WS896	CS C22.2 111
Toggle Switches Back & Side Wire								
PS15AC1-I PS15AC1-W PS15AC1 PS15AC1-GRY PS15AC1-LA	PS15AC2-I PS15AC2-W PS15AC2 PS15AC2-GRY PS15AC2-LA	PS15AC3-I PS15AC3-W PS15AC3 PS15AC3-GRY PS15AC3-LA	PS15AC4-I PS15AC4-W PS15AC4 PS15AC4-GRY PS15AC4-LA	15 120/277 15 120/277 15 120/277 15 120/277 15 120/277	Ivory White Brown Gray Light Almond	• • • • •	• • • • •	• • • • •
PS20AC1-I PS20AC1-W PS20AC1 PS20AC1-GRY PS20AC1-BK PS20AC1-RED PS20AC1-LA	PS20AC2-I PS20AC2-W PS20AC2 PS20AC2-GRY PS20AC2-BK PS20AC2-RED PS20AC2-LA	PS20AC3-I PS20AC3-W PS20AC3 PS20AC3-GRY PS20AC3-BK PS20AC3-RED PS20AC3-LA	PS20AC4-I PS20AC4-W PS20AC4 PS20AC4-GRY PS20AC4-BK PS20AC4-RED PS20AC4-LA	20 120/277 20 120/277 20 120/277 20 120/277 20 120/277 20 120/277 20 120/277	Ivory White Brown Gray Black Red Light Almond	• • • • • • •	• • • • • • •	• • • • • • •
PS30AC1-I PS30AC1	PS30AC2-I PS30AC2-W PS30AC2	PS30AC3-I PS30AC3		30 120/277 30 120/277 30 120/277	Ivory White Brown	• • •	• • •	• • •
Lighted Toggle Switches (Lighted when OFF) Back & Side Wire								
PS15AC1-CSL PS15AC1-ISL PS15AC1-WSL		PS15AC3-CSL PS15AC3-ISL PS15AC3-WSL		15 120/277 15 120/277 15 120/277	Clear Ivory White	• • •	• • •	• • •
PS20AC1-CSL PS20AC1-ISL PS20AC1-WSL PS20AC1-LASL		PS20AC3-CSL PS20AC3-ISL PS20AC3-WSL PS20AC3-LASL		20 120/277 20 120/277 20 120/277 20 120/277	Clear Ivory White Light Almond	• • • •	• • • •	• • • •
Pilot Lighted Switches (Lighted when ON) Back & Side Wire								
PS15AC1-CPL PS15AC1-RPL		PS15AC3-CPL PS15AC3-RPL		15 120 15 120	Clear Red	• •	• •	• •
PS20AC1-CPL PS20AC1-CPL7 PS20AC1-RPL PS20AC1-RPL7		PS20AC3-CPL7 PS20AC3-RPL PS20AC3-RPL7		20 120 20 277 20 120 20 277	Clear Clear Red Red	• • • •	• • • •	• • • •
	PS20AC2-CPL PS20AC2-RPL			20 120/277 20 120/277	Clear Red	• •	• •	• •
PS30AC1-RPL	PS30AC2-RPL	PS30AC3-RPL		30 120 30 120/277	Red Red	• •	• •	• •
Lock Switches (Key can be removed in both positions) Back & Side Wire								
PS15AC1-L PS20AC1-L PS20AC1-IL PS20AC1-WL PS20AC1-LAL	PS20AC2-L	PS15AC3-L PS20AC3-L PS20AC3-IL PS20AC3-WL PS20AC3-LAL	PS20AC4-L	15 120/277 20 120/277 20 120/277 20 120/277 20 120/277	Gray Gray Ivory White Light Almond	• • • • •	• • • • •	• • • • •


Switches Extra Heavy-Duty Specification Grade & Security Switches

15 & 20A, 347VAC; 20A, 120/277VAC

Pass & Seymour



Features	
<ul style="list-style-type: none"> ■ External screw-pressure-plate back and side wired. Accepts #14 – #10 AWG copper or copper-clad conductors. ■ Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce. ■ Cam controls fast “make” and positive “break” to minimize arcing. ■ Heavy-duty bumper pads for quiet operation. ■ High strength thermoplastic polycarbonate toggle. 	<ul style="list-style-type: none"> ■ Back body made of glass-reinforced nylon. ■ Locking support provides resistance to face and back body separation. ■ Oversized silver alloy contacts for long life and better heat dissipation. ■ Grounding terminal is standard. ■ Shallow design for ease of installation. ■ Strap nickel-plated steel with integral ground.




15 & 20 Amp
Canadian 347VAC

Catalog Number		Rating		Color	3rd Party Compliance
Single Pole	Three-Way	A.	VAC		C22.2 111
347VAC Toggle Switches Back & Side Wire					
★ PS371510-I	★ PS371530-I	15	347	Ivory	•
★ PS371510-W	★ PS371530-W	15	347	White	•
★ PS371510	★ PS371530	15	347	Brown	•
★ PS371510-GRY	★ PS371530-GRY	15	347	Gray	•
★ PS371510-BK	★ PS371530-BK	15	347	Black	•
★ PS371510-RED	★ PS371530-RED	15	347	Red	•
★ PS372010-I	★ PS372030-I	20	347	Ivory	•
★ PS372010-W	★ PS372030-W	20	347	White	•
★ PS372010	★ PS372030	20	347	Brown	•
★ PS372010-GRY	★ PS372030-GRY	20	347	Gray	•
★ PS372010-BK	★ PS372030-BK	20	347	Black	•
★ PS372010-RED	★ PS372030-RED	20	347	Red	•
★ PS372010-LA	★ PS372030-LA	20	347	Light Almond	•
★ PS372010-L	★ PS372030-L	20	347	Gray, Locking	•
★ Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.					

Features	
<ul style="list-style-type: none"> ■ Back and side wired. Accepts #14 – #10 AWG. ■ Operated by cam lock for maximum security in critical areas. ■ Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. 	<ul style="list-style-type: none"> ■ Uses same key as Cat.# 4600 cast enclosure. ■ Key can be removed in both positions.

Catalog Number				Rating		3rd Party Compliance		
Single Pole	Double Pole	Three-Way	Four-Way	A.	VAC	UL	FSUL	C22.2 55
Security Switches Back & Side Wire								
PS20AC1-KL	PS20AC2-KL	PS20AC3-KL	PS20AC4-KL	20	120/277	•	•	•
★ PS372010-KL		★ PS372030-KL		20	347	•		
★ Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.								




Security Switch

Stainless Steel Plate for PS20AC-KL Switches Single Gang – SS717, Double Gang – SS727.
 For custom combinations specify opening Style No. 302.
 Catalog Number 4609 Security Switch Replacement Keys for PS20AC-KL Switches (2 keys furnished with each switch).

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



15 & 20 Amp

Switches

Hard Use & Commercial Specification Grade Switches

15 & 20A, 120/277VAC


Features

- One-piece brass alloy contact arm for reliable electrical performance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Strap steel with integral ground, for corrosion resistance.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 – #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.

Catalog Number				Rating A. VAC	Color	3rd Party Compliance		
Single Pole	Double Pole	Three-Way	Four-Way			UL UL20	FSUL WS896	CS C22.2 111
Hard Use Specification Grade Back & Side Wire								
CSB15AC1-I	CSB15AC2-I	CSB15AC3-I	CSB15AC4-I	15 120/277	Ivory	•	•	•
CSB15AC1-W	CSB15AC2-W	CSB15AC3-W	CSB15AC4-W	15 120/277	White	•	•	•
CSB15AC1	CSB15AC2	CSB15AC3	CSB15AC4	15 120/277	Brown	•	•	•
CSB15AC1-GRY	CSB15AC2-GRY	CSB15AC3-GRY	CSB15AC4-GRY	15 120/277	Gray	•	•	•
CSB15AC1-LA	CSB15AC2-LA	CSB15AC3-LA	CSB15AC4-LA	15 120/277	Light Almond	•	•	•
CSB20AC1-I	CSB20AC2-I	CSB20AC3-I	CSB20AC4-I	20 120/277	Ivory	•	•	•
CSB20AC1-W	CSB20AC2-W	CSB20AC3-W	CSB20AC4-W	20 120/277	White	•	•	•
CSB20AC1	CSB20AC2	CSB20AC3	CSB20AC4	20 120/277	Brown	•	•	•
CSB20AC1-GRY	CSB20AC2-GRY	CSB20AC3-GRY	CSB20AC4-GRY	20 120/277	Gray	•	•	•
CSB20AC1-LA	CSB20AC2-LA	CSB20AC3-LA	CSB20AC4-LA	20 120/277	Light Almond	•	•	•

Catalog Number		Rating A. VAC	Color	3rd Party Compliance		
Single Pole	Three-Way			UL UL20	FSUL WS896	CS C22.2 111
Commercial Specification Grade Side Wire						
CS15AC1-I	CS15AC3-I	15 120/277	Ivory	•	•	•
CS15AC1-W	CS15AC3-W	15 120/277	White	•	•	•
CS15AC1	CS15AC3	15 120/277	Brown	•	•	•
CS15AC1-GRY	CS15AC3-GRY	15 120/277	Gray	•	•	•
CS15AC1-LA	CS15AC3-LA	15 120/277	Light Almond	•	•	•
CS20AC1-I	CS20AC3-I	20 120/277	Ivory	•	•	•
CS20AC1-W	CS20AC3-W	20 120/277	White	•	•	•
CS20AC1	CS20AC3	20 120/277	Brown	•	•	•
CS20AC1-GRY	CS20AC3-GRY	20 120/277	Gray	•	•	•
CS20AC1-LA	CS20AC3-LA	20 120/277	Light Almond	•	•	•

For Configurable Solutions, see Page U-1.



NEMA Type Enclosures

NEMA Type 1 Enclosures – Intended for indoor use primarily to provide a degree of protection against limited amounts of falling dirt in locations where unusual service conditions do not exist.

NEMA Type 7 Enclosures – Intended for indoor use in locations classified as Class 1, Group A, B, C, or D, as defined in the National Electrical Code. They shall be capable of withstanding the pressures resulting from an internal explosion of specified gases, and contain such an explosion sufficient that an explosive gas-air mixture existing in the atmosphere surrounding the enclosure will not be ignited. Enclosed heat generating devices shall not cause external surfaces to reach temperatures capable of igniting explosive gas-air mixtures in the surrounding atmosphere. Enclosures shall meet explosion, hydrostatic, and temperature design tests.

NEMA Type 3R Enclosures – Intended for outdoor use primarily to provide a degree of protection against rain and sleet; and to be undamaged by the formation of ice on the enclosure. They are not intended to provide protection against conditions such as internal condensation, or internal icing.


NEMA Type 9 Enclosures – Intended for indoor use in locations classified as Class II, Groups E, F, or G, as defined in the National Electrical Code. They shall be capable of preventing the entrance of dust. Enclosed heat generating devices shall not cause external surfaces to reach temperatures capable of igniting or discoloring dust on the enclosure or igniting dust-air mixtures in the surrounding atmosphere. Enclosures shall meet dust penetration and temperature design tests, and aging of gaskets (if used).

Pass & Seymour



Switches


Manual Controllers

30A 1 ϕ , & 3 ϕ 


7802
7803



7812-P
7813-P



7812-EX
7813-EX



7832
7833

Features — 7802 & 7803

- High horsepower rating of 20HP.
- Compact design.
- Gull-wing shaped brass terminal pressure clamps.
- Constructed of glass-reinforced thermoplastic.
- Two-point contact arms.
- One-piece contact carrier.
- UL508 and cULus Listing of individual device and assembled device within enclosure.
- Heavy-duty zinc-plated steel strap.
- Two brass rivets secure strap to housing.
- External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals.
- Oversized silver alloy contacts.
- 2-3/4" hubs (7812-EX and 7813-EX).
- 2-1/2" knockouts on back and 2-1/2"-3/4" knockouts on top and bottom (7812-P, 7813-P, 7806P).
- 2-1/2" knockouts on bottom and back (7832 and 7833).

Catalog Number	Description	Rating			
		A.	VAC	HP	VAC
Double Pole, Single Phase					
7802	Double Pole, Single Phase AC Manual Motor Controller (No overload protection)	General Use 30	600 max.	2 3 7.5 10	120 240 480 600
7802-MD	7802, See Footnote 1	Same as 7802			
7812-P	7802 in a NEMA 1 Enclosure	Same as 7802			
7812-PMD	7812-P, See Footnote 1	Same as 7802			
7812-EX	7802 in a NEMA 7 and 9 Enclosure for Hazardous Locations Class I - Groups C, D; Class II - Groups E, F, G	Same as 7802			
7832	7802 in a NEMA 3R Enclosure	Same as 7802			
7832-MD	7832, See Footnote 1	Same as 7802			
Three Pole, Three Phase					
7803	Three Pole, Three Phase AC Manual Motor Controller (No overload protection)	General Use 30	600 max.	3 7.5 10 20	120 240 480 600
7803-MD	7803, See Footnote 1	Same as 7803			
7813-P	7803 in a NEMA 1 Enclosure	Same as 7803			
7813-PMD	7813-P, See Footnote 1	Same as 7803			
7813-EX	7803 in a NEMA 7 & 9 Enclosure for Hazardous Locations Class I - Groups C, D; Class II - Groups E, F, G	Same as 7803			
7833	7803 in a NEMA 3R Enclosure	Same as 7803			
7833-MD	7833, See Footnote 1	Same as 7803			

7806-P NEMA 1 Black Nylon Enclosure with 1/2" and 3/4" knockouts at each end.

7801-P Handle Locking Guard has opening for padlock to secure control in either ON or OFF position.

7830 NEMA 3R Aluminum Enclosure.

All Industrial Control Equipment is suitable for use in a circuit capable of deliverable not more than 5,000 rms amperes at 600VAC maximum or equivalent.

Footnote:

1. Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.

Switches Manual Controllers


40A 1 ϕ & 3 ϕ

Pass & Seymour



Features — 7842 & 7843

- High horsepower rating of 20HP.
- Compact design.
- Gull-wing shaped brass terminal pressure clamps.
- Constructed of glass-reinforced thermoplastic.
- Two-point contact arms.
- One-piece contact carrier.
- Heavy-duty yellow chromate plated steel strap.
- Two brass rivets secure strap to housing.
- External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals.
- Oversized silver alloy contacts.
- UL508 and cULus Listing of individual device and assembled device within enclosure.



Catalog Number	Description	Rating			
		A.	VAC	HP	VAC
Double Pole, Single Phase					
7842	Double Pole, Single Phase AC Manual Motor Controller (No overload protection)	40	600 max.	2 5 10 15	120 240 480 600
7842-MD	7842, See Footnote 2	same as 7842			
Three Pole, Three Phase					
7843	Three Pole, Three Phase AC Manual Motor Controller (No overload protection)	40	600 max.	3 7.5 15 20	120 240 480 600
7843-MD	7843, See Footnote 2	same as 7843			


All Industrial Control Equipment is suitable for use in a circuit capable of deliverable not more than 5,000 rms amperes at 600VAC maximum or equivalent.

Footnote:

2. Suitable as Motor Disconnect - 10KA @ 600VAC, 60A max. Class J Fuse or 100A max. Ferraz Shawmut HSJ Fuse.

RATINGS

CATALOG NO.	PHASE	POLE
7802 or 7842	1	2
7803 or 7843	3	3



RESISTANCE				
7802 / 7803		30 AMP	600 VAC MAX.	
7842 / 7843		40 AMP	600 VAC MAX.	
MANUAL MOTOR CONTROLLER				
VAC	30A		40A	
	1 PHASE HP	3 PHASE HP	1 PHASE HP	3 PHASE HP
120	2	3	2	3
240	3	7.5	5	7.5
480	7.5	10	10	15
600	10	20	15	20

USE 60 / 75°C WIRING
TORQUE TERMINAL SCREWS
TO 16 IN. LBS.



Pass & Seymour



7863R

Switches



Manual Controllers

60A NEMA 3R Manual Controller
20 & 30A 1Ø

Features

- High horsepower rating, up to 3 HP for heavy duty applications.
- Compact design provides ease of installation.
- Box lug terminals.
- Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life.
- Made in USA.
- Wire pockets and thick wall arc barriers.
- Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements.
- Type 3R enclosure has 2-1/2", 3/4" and 1" concentric knockouts on bottom.
- Accepts #4 AWG.
- cULus listed.

Catalog Number	Description	Rating			
		A.	VAC	HP	VAC
Double Pole Manual Motor Controller					
7862R	Double Pole AC Manual Motor Controller in a NEMA 3R Enclosure	60	600 max.	3 5 15 15	120 240 480 600
7862	Double Pole AC Manual Motor Controller	60	600 max.	Same as 7862R	
Three Pole Manual Motor Controller					
7863R	Three Pole AC Manual Motor Controller in a NEMA 3R Enclosure	60	600 max.	5 10 20 30	120 240 480 600
7863	Three Pole AC Manual Motor Controller	60	600 max.	Same as 7863R	
NEMA 3R Enclosure					
7860	NEMA 3R Enclosure for 7862 & 7863				



PS20AC2-HP
PS30AC2-HP

All devices listed on this page conform to NEMA WD-1 and WD-6.

Features

- Oversize silver contacts for long life and better heat dissipation.
- Single phase switches are side wired with #14 - #10 AWG copper or copper-clad conductors.
- Shallow design for ease of installation.
- 2-3/4" hubs (HP30-EX).

Catalog Number	Description	Rating			
		A.	VAC	HP	VAC
Double Pole, Single Phase					
PS20AC2-HP	Double Pole, Single Phase AC Manual Motor Starting Switch (No overload protection)	20	120/277	1 2	120 240
PS30AC2-HP	Double Pole, Single Phase AC Manual Motor Starting Switch (No overload protection)	30	120/277	2 2	120 240
HP30-EX	PS30AC2-HP in a NEMA 7 & 9 Enclosure for Hazardous Locations Class I - Groups C, D; Class II - Groups E, F, G	Same as PS30AC2-HP			

Switches Manual Controllers

15, 20 & 30A, 120/277VAC – Maintained Contact
15, 20 & 30A, 120/277VAC – Momentary Contact

Pass & Seymour




Applications

For ON-OFF control of motors on small machine tools, pumps, fans and air conditioning equipment that require heavy-duty AC Double Throw Center OFF controls.


Features

- Oversized silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 – #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers and toggles molded of durable nylon.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Locking Switches supplied with one 1498-NT key.
- Normally open.



Fiber Insulator

Maintained and Momentary Contact



Fiber Insulator

Locking

Catalog Number		Rating A.	VAC	Color
S.P.D.T.	D.P.D.T.			
Maintained Contact Three Position – Two Circuit, Center Off				
1221-I	1222-I	15	120/277	Ivory
1221-W	1222-W	15	120/277	White
1221	1222	15	120/277	Brown
1221-L	1222-L	15	120/277	Locking
1225-I	1226-I	20	120/277	Ivory
1225-W	1226-W	20	120/277	White
1225	1226	20	120/277	Brown
1225-LA		20	120/277	Light Almond
1225-L	1226-L	20	120/277	Locking
1227-I	1228-I	30	120/277	Ivory
1227	1228	30	120/277	Brown
Maintained Contact Either Direction Two Position, No Center Off				
1275	1276	30	120/277	Brown
Momentary Contact Either Direction Three Position, Center Off				
1250-I		15	120/277	Ivory
1250-W		15	120/277	White
1250		15	120/277	Brown
1250-GRY		15	120/277	Gray
1250-L		15	120/277	Locking
1251-I		20	120/277	Ivory
1251		20	120/277	Brown
1251-LA		20	120/277	Light Almond
1251-L		20	120/277	Locking
1255	1256	30	120/277	Brown
1255-L	1256-L	30	120/277	Locking

Catalog Number	Description
Lock Switch Replacement Keys	
1498	Fits switches manufactured before 1976.
1498-NT	Fits switches manufactured between 1976-present.

HP Conversion Table

1221 Series		1250 Series	
15 Amp	1/2 Horsepower at 120VAC 2 Horsepower at 240VAC	15 Amp	1/2 Horsepower at 120VAC 2 Horsepower at 240VAC
20 Amp	1 Horsepower at 120VAC 2 Horsepower at 240VAC	20 Amp	1 Horsepower at 120VAC 2 Horsepower at 240VAC
30 Amp	2 Horsepower at 120VAC 2 Horsepower at 240VAC		

UL Listed.
CSA Certified.
All devices listed on this page
conform to NEMA WD-1 and WD-6.


Switches

TradeMaster® Grounding Toggle Switches

15A, 120VAC

Features

- Thermoplastic toggle and frame.
- Extra-long strap.
- High-impact resistant construction.
- Side wire #12 and #14 AWG.
- Push wire #14 AWG.
- Tri-drive ground, terminal and mounting screws.
- Easy-access green hex head ground screw.
- Smooth, quiet toggle action.

660-IG
663-IG

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL [®] UL20	CSA C22.2 111
Single Pole Toggle Switches Grounding				
660-IG*	15 120	Ivory	•	•
660-WG*	15 120	White	•	•
660-G*	15 120	Brown	•	•
660-BKG	15 120	Black	•	•
660-LAG*	15 120	Light Almond	•	•
Single Pole Toggle Switches Grounding (Without Ears)				
660-IGMH	15 120	Ivory	•	•
660-WGMH	15 120	White	•	•
660-GMH	15 120	Brown	•	•
Single Pole Illuminated Toggle Switches Grounding (Lighted when OFF)				
660-ISLG	15 120	Ivory	•	•
660-WSLG	15 120	White	•	•
660-LASLG	15 120	Light Almond	•	•
Three-Way Toggle Switches Grounding				
663-IG**	15 120	Ivory	•	•
663-WG**	15 120	White	•	•
663-G**	15 120	Brown	•	•
663-BKG	15 120	Black	•	•
663-LAG**	15 120	Light Almond	•	•
Three-Way Toggle Switches Grounding (Without Ears)				
663-IGMH	15 120	Ivory	•	•
663-GMH	15 120	Brown	•	•
Three-Way Illuminated Toggle Switches Grounding (Lighted when OFF)				
663-ISLG	15 120	Ivory	•	•
663-WSLG	15 120	White	•	•
663-LASLG	15 120	Light Almond	•	•
Four-Way Toggle Switches Grounding				
664-IG	15 120	Ivory	•	•
664-WG	15 120	White	•	•
664-G	15 120	Brown	•	•
664-BKG	15 120	Black	•	•
664-LAG	15 120	Light Almond	•	•
🍁 664-ICN	15 120	Ivory	•	•
🍁 664-WCN	15 120	White	•	•
🍁 Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.				

*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example: 660-WGU.

**Available in bulk packs of 90. Add "U" to end of Catalog Number. Example: 663-WGU.

Switches TradeMaster® Non-Grounding Toggle Switches

15A, 120VAC


Pass & Seymour



Features

- Thermoplastic toggle and frame.
- Extra-long strap.
- High-impact resistant construction.
- Side wire #12 and #14 AWG.
- Push wire #14 AWG.
- Tri-drive ground, terminal and mounting screws.
- Easy-access green hex head ground screw.
- Smooth, quiet toggle action.

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL20	C22.2 111
Single Pole Toggle Switches Non-grounding				
660-I	15 120	Ivory	•	•
660-W	15 120	White	•	•
660	15 120	Brown	•	•
660-LA	15 120	Light Almond	•	•
🍁 660-ICN	15 120	Ivory		•
🍁 660-WCN	15 120	White		•
🍁 660-CN	15 120	Brown		•
🍁 660-LACN	15 120	Light Almond		•
Three-Way Toggle Switches Non-grounding				
663-I	15 120	Ivory	•	•
663-W	15 120	White	•	•
663	15 120	Brown	•	•
663-LA	15 120	Light Almond	•	•
🍁 663-ICN	15 120	Ivory		•
🍁 663-WCN	15 120	White		•
🍁 663-CN	15 120	Brown		•
🍁 663-LACN	15 120	Light Almond		•
🍁 Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.				



660-I
663-I

Pass & Seymour




Switches

Grounding Combination Switches


15 & 20A, 120/277VAC; 15A, 120/125VAC; 20A, 120VAC

Features

- Available in ten switch, receptacle and pilot light combinations.
- Easily accessible break-off for separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.



Standard Combination



Decorator Combination

NEMA
5-15RNEMA
5-20R

All devices listed on this page conform to NEMA WD-1 and WD-6.

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance	
				UL UL20	UL UL498
Standard: Two Single Pole Switches Side Wire, Grounding					
690-IG	15 120/277	Ivory		•	
690-WG	15 120/277	White		•	
690-G	15 120/277	Brown		•	
690-LAG	15 120/277	Light Almond		•	
670-IG	20 120/277	Ivory		•	
670-WG	20 120/277	White		•	
670-G	20 120/277	Brown		•	
670-LAG	20 120/277	Light Almond		•	
Single Pole & Three-Way Switch Side Wire, Grounding					
696-IG	15 120/277	Ivory		•	
696-WG	15 120/277	White		•	
696-G	15 120/277	Brown		•	
696-LAG	15 120/277	Light Almond		•	
Two Three-Way Switches Side Wire, Grounding					
693-IG	15 120/277	Ivory		•	
693-WG	15 120/277	White		•	
693-G	15 120/277	Brown		•	
693-LAG	15 120/277	Light Almond		•	
Single Pole Switch & Single Receptacle Side Wire, Grounding					
691-I	15 120/125	Ivory	5-15R	•	•
691-W	15 120/125	White	5-15R	•	•
691	15 120/125	Brown	5-15R	•	•
691-LA	15 120/125	Light Almond	5-15R	•	•
671-I	20 120	Ivory	5-20R	•	•
671-W	20 120	White	5-20R	•	•
671	20 120	Brown	5-20R	•	•
671-LA	20 120	Light Almond	5-20R	•	•
Single Pole Switch & Pilot Light Side Wire, Grounding					
692-IG	15 120/125	Ivory		•	
692-WG	15 120/125	White		•	
692-G	15 120/125	Brown		•	
692-LAG	15 120/125	Light Almond		•	
Three-Way Switch & Pilot Light Side Wire, Grounding					
695-IG	15 120/125	Ivory		•	
695-WG	15 120/125	White		•	
695-G	15 120/125	Brown		•	
695-LAG	15 120/125	Light Almond		•	
Decorator: Two Single Pole Switches Side Wire, Grounding					
680-IG	15 120/277	Ivory		•	
680-WG	15 120/277	White		•	
680-LAG	15 120/277	Light Almond		•	
Single Pole Switch & Single Receptacle Side Wire, Grounding					
681-I	15 120/125	Ivory	5-15R	•	•
681-W	15 120/125	White	5-15R	•	•
681-LA	15 120/125	Light Almond	5-15R	•	•

Switches

Non-Grounding Combination Switches


15 & 20A, 120/277VAC; 15A, 120/125VAC

Pass & Seymour




Features	
<ul style="list-style-type: none"> Available in seven switch, receptacle and pilot light combinations. Easily accessible break-off for separate or common feed. 	<ul style="list-style-type: none"> Long-life red neon lamp in pilot light rated 1/25 Watt, 125V. Side wire #12 and #14 AWG. Two devices fit into the space of one.

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL20	UL498
Standard: Two Single Pole Switches Side Wire, Non-Grounding				
690-I	15 120/277	Ivory	•	•
690-W	15 120/277	White	•	•
690	15 120/277	Brown	•	•
670-I	20 120/277	Ivory	•	•
670-W	20 120/277	White	•	•
670	20 120/277	Brown	•	•
Single Pole & Three-Way Switch Side Wire, Non-Grounding				
696-I	15 120/277	Ivory	•	•
696-W	15 120/277	White	•	•
696	15 120/277	Brown	•	•
696-LA	15 120/277	Light Almond	•	•
Two Three-Way Switches Side Wire, Non-Grounding				
693-I	15 120/277	Ivory	•	•
693-W	15 120/277	White	•	•
693	15 120/277	Brown	•	•
693-LA	15 120/277	Light Almond	•	•
Single Pole Switch & Pilot Light Side Wire, Non-Grounding				
692-I	15 120/125	Ivory	•	•
692-W	15 120/125	White	•	•
692	15 120/125	Brown	•	•
692-LA	15 120/125	Light Almond	•	•
Three-Way Switch & Pilot Light Side Wire, Non-Grounding				
695-I	15 120/125	Ivory	•	•
695-W	15 120/125	White	•	•
695	15 120/125	Brown	•	•
695-LA	15 120/125	Light Almond	•	•
Decorator: Two Single Pole Switches Side Wire, Non-Grounding				
680-I	15 120/277	Ivory	•	•
680-W	15 120/277	White	•	•
680-LA	15 120/277	Light Almond	•	•




Standard Combination



Decorator Combination

See our full range of Decorator Combination Devices on Pages D-6 – D-10, D-17, D-19, D-25, and D-26.



NEMA 5-15R

NEMA 5-20R


Switches

Specification Grade Decorator Switches


15 & 20A, 120/277 & 347VAC; 20A, 120VAC

Features


- Impact-resistant polycarb back body and frame.
- Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
- Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.
- Internal screw-pressure-plate back and side wire capability for easy installation with #14 – #10 stranded or solid copper/copper clad wire. Terminals made of high conductivity brass and serrated for maximum wire gripping.
- Color-coded back bodies for positive identification of switch rating.
- Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
- Integral auto-ground clip for positive ground to metal boxes.
- Tri-drive ground, terminal and mounting screws. All terminal screws backed out, ready-to-install.



2601



2625, 2626, 2629



2601347

Catalog Number				Rating A. VAC	Color	3rd Party Compliance	
Single Pole	Double Pole	Three-Way	Four-Way			UL20	C22.2 111
Specification Grade Decorator Switches Back & Side Wire*							
2601-I		2603-I	2604-I	15	120/277	Ivory	• •
2601-W		2603-W	2604-W	15	120/277	White	• •
2601-GRY		2603-GRY		15	120/277	Gray	• •
2601-BK		2603-BK		15	120/277	Black	• •
2601-LA		2603-LA	2604-LA	15	120/277	Light Almond	• •
2621-I	2622-I	2623-I	2624-I	20	120/277	Ivory	• •
2621-W	2622-W	2623-W	2624-W	20	120/277	White	• •
2621	2622	2623	2624	20	120/277	Brown	• •
2621-GRY	2622-GRY	2623-GRY	2624-GRY	20	120/277	Gray	• •
2621-BK	2622-BK	2623-BK	2624-BK	20	120/277	Black	• •
2621-RED	2622-RED	2623-RED	2624-RED	20	120/277	Red	• •
2621-LA	2622-LA	2623-LA	2624-LA	20	120/277	Light Almond	• •
Illuminated Decorator Switches (Lighted when OFF) Back & Side Wire*							
2625-I		2626-I	2628-I	20	120	Ivory	• •
2625-W		2626-W	2628-W	20	120	White	• •
2625-LA		2626-LA	2628-LA	20	120	Light Almond	• •
Pilot Lighted Decorator Switches (Lighted when ON) Back & Side Wire*							
2629-I				20	120	Ivory	• •
2629-W				20	120	White	• •
2629-LA				20	120	Light Almond	• •

*For Configurable Solutions, see Page U-1.

Catalog Number				Rating A. VAC	Color	3rd Party Compliance	
Single Pole	Three-Way	Four-Way				UL20	C22.2 111
Specification Grade Decorator Switches Back & Side Wire							
2601347-I	2603347-I			15	347	Ivory	• •
2601347-W	2603347-W			15	347	White	• •
2601347-GRY	2603347-GRY			15	347	Gray	• •
2601347-LA	2603347-LA			15	347	Light Almond	• •
2621347-I	2623347-I	2624347-I		20	347	Ivory	• •
2621347-W	2623347-W	2624347-W		20	347	White	• •
2621347-GRY	2623347-GRY	2624347-GRY		20	347	Gray	• •
2621347-BK	2623347-BK	2624347-BK		20	347	Black	• •
2621347-RED	2623347-RED	2624347-RED		20	347	Red	• •
2621347-LA	2623347-LA	2624347-LA		20	347	Light Almond	• •
* Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.							

Switches


TradeMaster® Decorator Switches

15A, 120 & 120/277VAC


Pass & Seymour




Features	
<ul style="list-style-type: none"> Designer-style satin-finish rocker. High-impact resistant thermoplastic construction. External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG. Push wire #14 AWG. Narrow back body leaves more room for wires in the box. 	<ul style="list-style-type: none"> Extra-long, through-body strap eliminates floating installations and imperfect applications. Smooth, quiet paddle action. Easy-access green hex head ground screw. Tri-drive ground, terminal and mounting screws. ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.




TM870-LA



TM870-LAON



TM873-LA



TM874-LA

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL UL20	CS C22.2 111
Single Pole Decorator Switches Grounding*				
TM870-I	15 120/277	Ivory	•	•
TM870-W	15 120/277	White	•	•
TM870	15 120/277	Brown	•	•
TM870-GRY	15 120/277	Gray	•	•
TM870-BK	15 120/277	Black	•	•
TM870-LA	15 120/277	Light Almond	•	•
Single Pole Decorator Switches Grounding with ON-OFF Indication				
TM870-ION	15 120/277	Ivory	•	•
TM870-WON	15 120/277	White	•	•
TM870-BKON	15 120/277	Black	•	•
TM870-LAON	15 120/277	Light Almond	•	•
Single Pole Illuminated Decorator Switches Grounding (Lighted when OFF)				
TM870-ISL	15 120/277	Ivory	•	•
TM870-WSL	15 120/277	White	•	•
TM870-LASL	15 120/277	Light Almond	•	•
Three-Way Decorator Switches Grounding*				
TM873-I	15 120/277	Ivory	•	•
TM873-W	15 120/277	White	•	•
TM873	15 120/277	Brown	•	•
TM873-GRY	15 120/277	Gray	•	•
TM873-BK	15 120/277	Black	•	•
TM873-LA	15 120/277	Light Almond	•	•
Three-Way Illuminated Decorator Switches Grounding (Lighted when OFF)				
TM873-ISL	15 120	Ivory	•	•
TM873-WSL	15 120	White	•	•
TM873-LASL	15 120	Light Almond	•	•
Four-Way Decorator Switches Grounding				
TM874-I	15 120/277	Ivory	•	•
TM874-W	15 120/277	White	•	•
TM874	15 120/277	Brown	•	•
TM874-BK	15 120/277	Black	•	•
TM874-LA	15 120/277	Light Almond	•	•

*For Configurable Solutions, see Page U-1.


Pass & Seymour



Switches

Decorator & Specification Grade Combination Momentary & Maintained Contact Switches

15A, 120 & 120/277VAC



TM870-STMLACC

Features



- Designer-style satin-finish rocker.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.
- Extra-long, through-body strap eliminates floating installations and imperfect applications.
- Smooth, quiet paddle action.
- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL UL20	SP C22.2 111
Single Pole Decorator Momentary Contact Switches				
TM870-STMICC	15 120/277	Ivory	•	•
TM870-STMWCC	15 120/277	White	•	•
TM870-STMLACC	15 120/277	Light Almond	•	•
TM870-STMBKCC	15 120/277	Black	•	•



Features

- Unique "Up/Down" switches match the look and feel of standard decorator switches.
- Impact-resistant face and body.
- Side and external screw-pressure-plate back wire accepts #12 and #14 AWG.
- All screws are tri-drive.
- Full wraparound heavy-gauge steel strap is plated for corrosion resistance and features lock-in tabs.
- Patent-pending split circuit tab — easily accessible, and can be reinstalled without a tool.

Momentary
ContactMaintained
Contact

Catalog Number	Rating A. VAC	Color	3rd Party Compliance		
			cULus cULus	UL UL20	UL UL508
NEW Specification Grade Double Throw Momentary Contact Switches					
TM811-DTMOI	15 120	Ivory	•	•	•
TM811-DTMOW	15 120	White	•	•	•
TM811-DTMOLA	15 120	Light Almond	•	•	•
NEW Specification Grade Double Throw Maintained Contact Switches					
TM811-DTMAI	15 120	Ivory	•	•	•
TM811-DTMAW	15 120	White	•	•	•
TM811-DTMALA	15 120	Light Almond	•	•	•

Switches Specification Grade Decorator Combination Switches


20A, 277VAC

Pass & Seymour

legrand



Features	
<ul style="list-style-type: none"> Unique "Up/Down" switches match the look and feel of standard decorator switches. Impact-resistant face and body. Side and external screw-pressure-plate back wire accepts #12 and #14 AWG. All screws are tri-drive. Full wraparound heavy-gauge steel strap is plated for corrosion resistance and features lock-in tabs. 	<ul style="list-style-type: none"> Patent-pending split circuit tab — easily accessible, and can be reinstalled without a tool. Patent-pending snap-in light module (sold separately) transforms a combination switch into an illuminated switch. Identification modules (sold separately) identifies each switch — light, fan, heat lamp. See Page A-20 for details.



15 & 20 Amp

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			cULus	UL20
NEW Two Single Pole Switches				
PS811-20I	20 277	Ivory	•	•
PS811-20W	20 277	White	•	•
PS811-20LA	20 277	Light Almond	•	•
NEW Three Single Pole Switches				
PS8111-20I	20 277	Ivory	•	•
PS8111-20W	20 277	White	•	•
PS8111-20LA	20 277	Light Almond	•	•
NEW Snap-In Light Module*				
PS8LM	— —	Clear		

*For use with PS811-20 and PS8111-20 only.

Pass & Seymour



Switches TradeMaster® Decorator Combination Switches




Unique "Up/Down" switches match the look and feel of standard Decorator switches.

Easy-to-use oversized main switch for primary load.

Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds. See Page A-20 for details.

Identification modules (sold separately) identifies each switch — light, fan, heat lamp. See Page A-20 for details.



TM8113-WCC
Shown with Snap-In Light Module TM8LMCC.

Fully rounded back body protects wires from being damaged by sharp edges.

Ground screw position under the end of the strap minimizes the risk of contact.

Impact-resistant face and body.

Full wraparound metal strap, commercial grade with lock-in tabs.




All screws are tri-drive.

Patented split circuit tab — easily accessible, and can be reinstalled without a tool.

External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.

Adding a Snap-In Light Module



Switches TradeMaster® Decorator Combination Switches

15A, 120VAC


Pass & Seymour




Features

- Impact-resistant face and body.
- Fully rounded back body protects wires from being damaged by sharp edges.
- Clear identification of circuits.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Full wraparound metal strap with lock-in tabs.
- Patented split circuit tab – easily accessible, and can be reinstalled without a tool.
- Unique “Up/Down” switches match the look and feel of standard Decorator switches.
- Largest breadth of 15 amp offering.
- All screws are tri-drive.
- Patented Snap-In Light and Identification Modules (sold separately). See Page A-20 for details.


Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL ₂₀	cUL _{us}
Two Single Pole Switches				
TM811-ICC	15 120	Ivory	•	•
TM811-WCC	15 120	White	•	•
TM811-CC	15 120	Brown	•	•
TM811-BKCC	15 120	Black	•	•
TM811-LACC	15 120	Light Almond	•	•
Two Single Pole Switches with Pilot Light				
TM811-PLICC	15 120	Ivory	•	•
TM811-PLWCC	15 120	White	•	•
TM811-PLBKCC	15 120	Black	•	•
TM811-PLLACC	15 120	Light Almond	•	•
Single Pole Switch & Three-Way Switch				
TM813-ICC	15 120	Ivory	•	•
TM813-WCC	15 120	White	•	•
TM813-CC	15 120	Brown	•	•
TM813-BKCC	15 120	Black	•	•
TM813-LACC	15 120	Light Almond	•	•
Single Pole Switch with Pilot Light & Three-Way Switch				
TM813-PLICC	15 120	Ivory	•	•
TM813-PLWCC	15 120	White	•	•
TM813-PLBKCC	15 120	Black	•	•
TM813-PLLACC	15 120	Light Almond	•	•
Two Three-Way Switches				
TM833-ICC	15 120	Ivory	•	•
TM833-WCC	15 120	White	•	•
TM833-CC	15 120	Brown	•	•
TM833-BKCC	15 120	Black	•	•
TM833-LACC	15 120	Light Almond	•	•
Three Single Pole Switches				
TM8111-ICC	15 120	Ivory	•	•
TM8111-WCC	15 120	White	•	•
TM8111-CC	15 120	Brown	•	•
TM8111-BKCC	15 120	Black	•	•
TM8111-LACC	15 120	Light Almond	•	•
Two Single Pole Switches & Three-Way Switch				
TM8113-ICC	15 120	Ivory	•	•
TM8113-WCC	15 120	White	•	•
TM8113-CC	15 120	Brown	•	•
TM8113-BKCC	15 120	Black	•	•
TM8113-LACC	15 120	Light Almond	•	•
Four Single Pole Switches				
TM81111-ICC	15 120	Ivory	•	•
TM81111-WCC	15 120	White	•	•
TM81111-CC	15 120	Brown	•	•
TM81111-BKCC	15 120	Black	•	•
TM81111-LACC	15 120	Light Almond	•	•



TM811-WCC




TM8111-WCC




TM81111-WCC

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



TM818-WCC



TM8118-WCC



TM8LMCC



TM8ID-WCC

Switches

TradeMaster® Decorator Combination Switches

15A, 120/125VAC

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL20	UL498	cULus
Single Pole Switch & Single Receptacle						
TM818-ICC	15 120/125	Ivory	5-15R	•	•	•
TM818-WCC	15 120/125	White	5-15R	•	•	•
TM818-CC	15 120/125	Brown	5-15R	•	•	•
TM818-BKCC	15 120/125	Black	5-15R	•	•	•
TM818-LACC	15 120/125	Light Almond	5-15R	•	•	•
Single Pole Switch & Single Receptacle with Pilot Light						
TM818-PLICC	15 120/125	Ivory	5-15R	•	•	•
TM818-PLWCC	15 120/125	White	5-15R	•	•	•
TM818-PLBKCC	15 120/125	Black	5-15R	•	•	•
TM818-PLLACC	15 120/125	Light Almond	5-15R	•	•	•
Three-Way Switch & Single Receptacle						
TM838-ICC	15 120/125	Ivory	5-15R	•	•	•
TM838-WCC	15 120/125	White	5-15R	•	•	•
TM838-CC	15 120/125	Brown	5-15R	•	•	•
TM838-BKCC	15 120/125	Black	5-15R	•	•	•
TM838-LACC	15 120/125	Light Almond	5-15R	•	•	•
Two Single Pole Switches & Single Receptacle						
TM8118-ICC	15 120/125	Ivory	5-15R	•	•	•
TM8118-WCC	15 120/125	White	5-15R	•	•	•
TM8118-CC	15 120/125	Brown	5-15R	•	•	•
TM8118-BKCC	15 120/125	Black	5-15R	•	•	•
TM8118-LACC	15 120/125	Light Almond	5-15R	•	•	•
Single Pole Switch & Pilot Light						
TM81-PLICC	15 120/125	Ivory		•	•	•
TM81-PLWCC	15 120/125	White		•	•	•
TM81-PLBKCC	15 120/125	Black		•	•	•
TM81-PLLACC	15 120/125	Light Almond		•	•	•
Three-Way Switch & Pilot Light						
TM83-PLICC	15 120/125	Ivory		•	•	•
TM83-PLWCC	15 120/125	White		•	•	•
TM83-PLBKCC	15 120/125	Black		•	•	•
TM83-PLLACC	15 120/125	Light Almond		•	•	•

Features

- Module simply snaps-in for easy installation.
 - Can be installed with the following devices: TM811, TM813, TM833, TM818, TM838, TM8111, TM8113, TM81111, TM8118 and the LS Series of Dimmers & Fan Speed Controls (see Pages M-8 and M-17).
- Snap-In Light Module:**
- Lights when OFF.
 - Uses energy-efficient 1/4 watt LED light.
 - LED light will not generate heat and will last on average 47 years.

Catalog Number	Rating A. VAC	Color	3rd Party Compliance
			cULus
Snap-In Light Module			
TM8LMCC	15 120/125	Clear	•
Identification Modules			
TM8ID-ICC	— —	Ivory	
TM8ID-WCC	— —	White	
TM8ID-CC	— —	Brown	
TM8ID-BKCC	— —	Black	
TM8ID-LACC	— —	Light Almond	


For Decorator Hallway Lights and Combination Devices, see Pages D-14, D-17, and D-19.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Switches Decorator Combination Switch/GFCI Receptacles

15A, 125VAC

Pass & Seymour



1595-SWTWCC4



1595-2SWTWCC4



NEMA
5-15R

Features

- Meets 2006 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Up-down switching.
- 15 Amp single pole switch rated for 1/2 HP motor loads – perfect for bath or kitchen vents and garbage disposals.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red lamp).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Switch Rating A. VAC	Receptacle Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	UL20 C22.2 No. 111
NEW Combination Single Pole Switch/GFCI							
1595-SWTICC4	15 120	15 125	Ivory	5-15R	•	•	•
1595-SWTWCC4	15 120	15 125	White	5-15R	•	•	•
1595-SWTBKCC4	15 120	15 125	Black	5-15R	•	•	•
1595-SWTLACC4	15 120	15 125	Light Almond	5-15R	•	•	•
NEW Combination Two Single Pole Switches/GFCI							
1595-2SWTICC4	15 120	15 125	Ivory	5-15R	•	•	•
1595-2SWTWCC4	15 120	15 125	White	5-15R	•	•	•
1595-2SWTBKCC4	15 120	15 125	Black	5-15R	•	•	•
1595-2SWTLACC4	15 120	15 125	Light Almond	5-15R	•	•	•

Available Spring 2006.


Pass & Seymour



Switches

Canopy Switches & 911 Locator

15A, 120 & 250VAC; 15A, 120VAC

1200
1201

Features

- Equipped with wire leads.
- 1200 and 1201 complete with metal box and plate.
- Only 14 oz. pressure actuates switch.
- Back box cold rolled steel.
- Plate is steel with a bronze coating.

Catalog Number		Rating AC	
Light On Door Open	Light On Door Closed	120VAC	250VAC
Pressure Sensitive Door & Canopy Switches			
1200	1201	15A	15A
Interiors Only, with Leads & Plunger			
1205	1206	15A	15A
Interiors Only, with Leads, Plunger & Face Plate			
1205-A	1206-A	15A	15A

911 Locator Switch

Application

The 911 Locator should be used in place of a standard single-pole switch to turn outdoor house or porch lights ON and OFF. In the 911 "flashing" position, the light becomes a house locator for police, medical personnel, emergency utility service, foul weather deliveries, etc.


- Illuminated toggle when switch is off.
- Toggle and attached load flashes when toggle in center position (in 911 mode).

Helps Emergency Personnel Locate Address

Used in conjunction with your call for assistance, the 911 Locator solves the problem of night time house identification for emergency personnel. After you have placed your call for help, simply flick the switch toggle to the "911" position and your outdoor light will flash on and off continuously, cutting response time to insure effective action.

Features

- Functions as a standard ON/OFF switch.
- Installs in minutes. Replaces any standard single-pole switch.
- 5" pre-stripped wire leads.
- All wire nuts and mounting hardware included.
- Transparent wall plate sticker included.
- UL20 Listed.



911LOCATOR


Catalog Number	Description	Rating
Single Pole, Double Throw		
911LOCATOR	Emergency Flasher Switch	600 Watts, 120VAC

Devices & Wall Plates Color Selection Chart


Pass & Seymour



Devices & Plastic Wall Plate Colors



Ivory Light Almond White



Black Blue Brown Gray Orange Red

See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates



Metal Finish Aluminum Brass (Brushed) Polished Brass Stainless Steel Brushed Bronze Chrome

Custom Metal Wall Plates Paint Finish Colors



Paint Color Light Blue Orange Navy Peach Hunter Green Gray Yellow



Paint Color Glossy Black Brown Burgundy White Primer Red



Paint Color Beige Pink Flat Black Ivory Light Almond Medium Blue

To order custom metal wall plates, see Pages S-40 - S-43.