

WAC LIGHTING

2016 January New Products

Table of Contents

InvisiLED®		
Recessed Symmetrical Channel	New	2
Recessed Asymmetrical Channel	New	3
Recessed Indirect Channel	New	4
InvisiLED® Pro 3	New	5
InvisiLED® Pro 2	New	6
<hr/>		
LED Recessed		
Duo	New	8
Aether	New	10
Summit 2.0	New	11
Tesla		13
Precision Multiples		21
Mini Multiple Spots	New	24
<hr/>		
LED Track		
W Track Current Limiter		25
W Track Quick Connect™ Adapter		26
H Track Current Limiter	New	27
Paloma		28
Exterminator II		29
Exterminator		32
Summit		33
Precision		35
LED Track Luminaires		36
<hr/>		
LED Task		
InvisiLED® Lite	New	37
InvisiLED® Pro2	New	38
InvisiLED® Pro3	New	39
InvisiLED® Mounting Accessories	New	40
Touch and Occupancy Control Kit		41
LED90 Edge Lit Button Light	New	42
LINE		43
Light Bars		45
<hr/>		
LED Exterior		
Endurance™	New	47
Tube		55
Scoop		59
Rubix		60
<hr/>		
LED Decorative		
Disc	New	63
Flo	New	64
Glo		65
Blo	New	66
Vector		67
Monterrey		69
Sublime	New	71
<hr/>		
Dweled	New	73-132



Symmetrical Recessed Channel



- Linear channel can be field cut
- Accommodates either one or two runs of InvisiLED® indoor tape
- Includes a translucent white acrylic diffuser
- Dense foam insert for spackling



8 ft linear channel

LED-T-RCH1-WT


Includes an end cap and diffuser



Power feed

LED-T-RBOX1-WT



*Includes a wiring box, two hanger bars, two five-pin InvisiLED® adapters, an end cap and diffuser
The end cap may be placed on either side or be removed
Hanger bars may install on any side of the wiring box*



Lateral corner

LED-T-CTC1-WT


Includes diffuser



Perpendicular corner

LED-T-WTC1-WT


*Transitions between walls or wall to ceiling
Includes diffuser*



Outside corner


LED-T-WTW1-WT

*Transitions around columns, bump outs, or soffits
Includes diffuser*



Asymmetrical Recessed Channel


- Linear channel can be field cut
- Accomodates one run of InvisiLED® indoor tape
- Dense foam insert for spackling



InvisiLED® indoor tape

8 ft linear channel
Includes an end cap



LED-T-RCH2-WT



Power feed



LED-T-RBOX2-WT

Includes a wiring box, two hanger bars, a five-pin InvisiLED® adapter, and two end caps
The end cap may be placed on either side or be removed
Hanger bars may install on any side of the wiring box




Indirect Recessed Channel

- Linear channel can be field cut
- Accommodates up to two runs of InvisiLED® indoor tapes
- Dense foam insert for spackling



8ft linear channel
Includes an end cap


LED-T-RCH3-WT



Power feed

LED-T-RBOX3-WT

Includes a wiring box, two hanger bars, two five-pin InvisiLED® adapters, and one end cap
The end cap may be placed on either side or be removed
Hanger bars may install on any side of the wiring box



Pro3 InvisiLED®

New Product


Power: 5W / ft
Lumens: Up to 475 lm / ft
CRI: 90
Rated Life: 70,000 hours

- Can be put inside a recessed channel to be used as cove, wallwash, and downlight
- Brightest InvisiLED® system available
- Laterally bendable design
- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap and a male to male connector with each tape section
- ELV dimming - see specification sheet for list of tested dimmers

Curve clip **LED-T-CL1** shown
 (see page 40 for detail)

Longitudinally bendable
 over marked signs

Field-cutable
 every 6"
 at the end of a run



Tape Selections

System	Color Temp	CRI	Length	Qty	Finish
LED-TE24	27 2700K	95	6IN 6 inches	1	WT White
	30 3000K	95	1 1 foot	1	
	35 3500K	90	5 5 feet	1	
	45 4500K	90	1-40 1 foot	40	

Example: **LED-TE2435-6IN-WT**

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	20 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	20 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	20 feet	Yes

Accessories

For mounting accessories, please see page 40



Lead Wire	LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies
Extension Cable	LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section
Low Voltage Wiring Box With Feed	LED-TC-B-2 L: 1½ in W: ¾ in H: 7/8 in	Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box	LED-T-B L: 1½ in W: ¾ in H: 7/8 in	Neatly houses up to two wires
Wiring Box With Switch	TB-S L: 6¼ in W: 1½ in H: 1¼ in	Use when spanning a large gap in a system layout without leaving exposed wiring
Joiner Cable	LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
3-Way "Y" Connector	LED-TC-Y	Connects tape sections
4-Way "X" Connector	LED-TC-X	Connects tape sections
"L" Connector	LED-TC-L	Connects tape sections
End cap	LED-TC-EC	1 cut end cap 1 male end cap

Pro2 InvisiLED®

New 2200K Color Temperature

Power: 4W / ft
Lumens: Up to 330 lm / ft
CRI: 90
Rated Life: 80,000 hours

- Can be put inside a recessed channel to be used as accent, indicator or wayfinding light
- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	Length	Qty	Finish
LED-TX24	22 2200K	6IN 6 inches	1	WT White
	27 2700K		1	
	30 3000K		1	
	35 3500K		1	
	45 4500K		40	

Example: **LED-TX2435-6IN-WT**

"L" Connector

System	Color Temp	Finish
LED-TX24	22 2200K	5L-WT White
	27 2700K	
	30 3000K	
	35 3500K	
	45 4500K	

Example: **LED-TX2435-5L-WT**
 Each "L" connector consumes 2 watt

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	25 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	25 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	25 feet	Yes


Accessories

For mounting accessories, please see page 40


Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box		LED-T-B	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires
Wiring Box With Switch		TB-S	L: 6 1/4 in W: 1 5/8 in H: 1 1/4 in Use when spanning a large gap in a system layout without leaving exposed wiring
Joiner Cable		LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
3-Way "Y" Connector		LED-TC-Y	Connects tape sections
4-Way "X" Connector		LED-TC-X	Connects tape sections
"L" Connector		LED-TC-L	Connects tape sections
End cap		LED-TC-EC	1 cut end cap 1 male end cap

Set the right atmosphere

Depending on the activity, the lighting theme can change from bright to dim, crisp white to warmer tone, and from spot to ambient distribution all in one luminaire, just by adjusting your regular dimmer. Specify in multi-functional residential or commercial spaces, television rooms, or areas with heavy visual display usage.





Spot light distribution
High brightness
Crisp white light color



Ambient light distribution
Lower brightness
Warm white color

Adjust
dimmer


A white double-headed arrow pointing left and right, indicating the range of adjustment for the dimmer.

3" Duo™ New Product

Glare Reducing Dual-source LED Downlight



A spot light at the maximum light output for task becomes a wide distribution ambient light source as it dims down



Input: 120V
Power: 15W
Rated Life: 50,000 hours

- Reduces overhead glare in the aperture with a warm dimming mixing chamber
- Offered in two warm dimming CCT ranges from 2700K to 2200K and 3000K to 2200K
- 52° cut-off angle
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

		At the brightest output				At the lowest output			
		Color Temp	Lumen	Beam Spread	CRI	Color Temp	Lumen	Beam Spread	CRI
	HR3D-RO92722S-WT	2700K	810	20°	90+	2200K	15	120°	90+
	HR3D-RO93022S-WT	3000K	890	20°	90+	2200K	15	120°	90+

Housings (Required)

	Model	Input	Notes
	HR3D-2015-NICA New Construction IC-Rated, Airtight	120V	Ceiling thickness: 1/2"–1"
	HR3D-2015-RA Remodel Non-IC, Airtight	120V	Ceiling thickness: 1/2"–1"




3.5"

Fits in tight plenums

with complex HVAC ducts, sprinkler pipes and conduit runs



Aether™
3.5" Shallow IC
LED Downlight



Aether™ Now available as IC standard









3.5" Shallow IC LED Downlight

Power: 22.5W
Delivered Lumens: Up to 1375
Comparable to: 75W MR16
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours





Designed to fit in tight plenum

- Narrow IC Housing
- Energy Star® rated
- Wet location listed
- 3.5" trim aperture and 3.5" housing height
- 35° cut-off angle
- Universal input voltage (120V-220V-277V)
- Ceiling thickness: ½" - 1½"
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

		HR-3LED-T120-WT <i>Round</i>
		HR-3LED-T720-WT <i>Square</i>
		HR-3LED-TL220-WT <i>Round Trimless</i>
		HR-3LED-TL820-WT <i>Square Trimless</i>

Housings

	Beam	Max CBCP	Max Lumen	Color Temp	CRI
 	HR-3LED-H20A <i>New Construction IC-rated, Airtight</i>				
	N 25°	4480	1375	927 2700K	90
 	HR-3LED-H20AC <i>New Construction IC-rated, Airtight Chicago Plenum</i>				
	F 40°	2555	1315	27 2700K	85
				930 3000K	90
				30 3000K	85
			35 3500K	85	
			40 4000K	85	

Example: **HR-3LED-H20A-F-930**



Summit™ 2.0 3.5" LED IC-Rated New Product

Power:	14.5W	<ul style="list-style-type: none"> ACLED IC-rated downlight Integral housing and trim, no driver needed Single spot light source 30° Visual cutoff angle for glare control Ceiling thickness: ½" - ¾" ELV dimming - see specification sheet for list of tested dimmers 	<ul style="list-style-type: none"> Energy Star® rated Title 24 Compliant ETL&cETL wet location listed
Comparable to:	50W MR16		
ELV Dimming:	100%-10%		
Input:	120V		
Beam Angle:	45°		
Rated Life:	50,000 hours		

Trims and Housing

		Lumen	Color Temp	CRI	
		<p>HR35-ICR30F-WT Round Trim <i>New Construction</i> <i>IC-Rated, Airtight</i></p>	910	3000K	90
		<p>HR35-ICS30F-WT Square Trim <i>New Construction</i> <i>IC-Rated, Airtight</i></p>	895	3000K	90



Summit™ 2.0 3.5" LED Non-IC New Product

Power:	14.5W	<ul style="list-style-type: none"> ACLED non-IC downlight Configurable for both new construction and remodel Integral housing and trim, no driver needed Single spot light source 30° Visual cutoff angle for glare control Ceiling thickness: ½" - ¾" ELV dimming - see specification sheet for list of tested dimmers 	<ul style="list-style-type: none"> Energy Star® rated Title 24 Compliant ETL&cETL wet location listed
Comparable to:	50W MR16		
ELV Dimming:	100%-10%		
Input:	120V		
Beam Angle:	45°		
Rated Life:	50,000 hours		

Trims and Housing

		Lumen	Color Temp	CRI	
		<p>HR35-R30F-WT <i>Round Trim</i> New Construction and Remodel Non-IC, Airtight</p>	910	3000K	90
		<p>HR35-S30F-WT <i>Square Trim</i> New Construction and Remodel Non-IC, Airtight</p>	895	3000K	90

Tesla Pro 2" LED

















Delivered Lumens: Up to 1090
Comparable to: 50W MR16
Power: 14.5W
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours

High Output LED

- Wet and damp location listed
- Energy Star® rated
- CEC Title 24 Compliant (see website for list of models)
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- Universal input voltage (120V-220V-277V)
- 2" aperture
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

Trims (Order Housing Separately)		Beam	Color Temp	CRI	Finish
		HR2LD-ET109P High Brightness Wet Location Listed Energy Star® 9° visual cutoff	N 30° F 55°		
		HR2LEDT109P Open Reflector Energy Star®	N 27° F 40°		
		HR2LEDT309P 0°- 30° Adjustable Energy Star®	N 27° F 40°		
		HR2LEDT409P 30°- 45° Adjustable Energy Star®	N 27° F 40°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85	BN Brushed Nickel CB Copper Bronze WT White
		HR2LEDT209P Shower Light Wet Location Listed Energy Star®	N 27°		
		HR2LEDT709P Open Reflector Energy Star®	N 30° F 45°		
		HR2LEDT509P 0°- 30° Adjustable Energy Star®	N 30° F 45°		

Example: **HR2LEDT109PF835BN**

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Narrow Flood **SL-REF-BL10-1-N**
 Flood **SL-REF-BL10-1-F**

LED

2700K 85 CRI **BXRC-27E1000-B-03**
 2700K 90 CRI **BXRC-27G1000-B-03**
 3000K 85 CRI **BXRC-30E1000-B-03**
 3000K 90 CRI **BXRC-30G1000-B-03**
 3500K 85 CRI **BXRC-35E1000-B-03**
 4000K 85 CRI **BXRC-40E1000-B-03**

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket

Tesla Pro 2" Housing

Housings (Required)	Model	Input	Notes
<p><i>Adjustable New Construction</i></p>	<p>HR-2LED-H09D-ICA <i>IC-Rated, Airtight</i></p>	120V-277V	<p>Allows adjustment in any direction when used with adjustable trims</p>
<p><i>Remodel</i></p>	<p>HR-2LED-R09D-A <i>Non-IC, Airtight</i></p>	120V-277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2"–1"</p> <p>Does not accommodate adjustments</p>
<p><i>Adjustable Remodel</i></p>	<p>HR-2LED-R14D <i>Non-IC</i></p>	120V-277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2"-5/8"</p>

















Tesla 2" LED



Delivered Lumens: Up to 730
Comparable to: 50W MR16
Power: 14.5W
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 90,000 hours

- Universal input voltage (120V-220V-277V)
- Wet and damp location listed
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- 2" aperture
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

Trims (Order Housing Separately)		Beam	Color Temp	CRI	Finish
		HR-2LD-ET109 <i>Wet Location Listed</i> <i>Energy Star®</i> <i>9° visual cutoff</i>	S 16.5° N 30° F 53°		
		HR-2LED-T109 <i>Open Reflector</i>			
		HR-2LED-T309 <i>0°-30° Adjustable</i>	S 15° N 26° F 45°		
		HR-2LED-T409 <i>30°-45° Adjustable</i>	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85		BN Brushed Nickel CB Copper Bronze WT White
		HR-2LED-T209 <i>Shower Light</i> <i>Wet Location Listed</i>	N 26°		
		HR-2LED-T709 <i>Open Reflector</i>	S 15° N 26° F 45°		
		HR-2LED-T509 <i>0°-30° Adjustable</i>			

Example: **HR-2LD-ET109F-9W-BN**

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Spot	SL-REF-LUX10-S
Narrow Flood	SL-REF-LUX10-N
Flood	SL-REF-LUX10-F




LED

2700K	85 CRI	LXS8-PW27
3000K	90 CRI	LXS9-PW30
3000K	85 CRI	LXS8-PW30
3500K	85 CRI	LXS8-PW35
4000K	85 CRI	LXS8-PW40

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket

Tesla 2" Housing

Housings (Required)	Model	Input	Notes
<p><i>Adjustable New Construction</i></p> 	<p>HR-2LED-H09D-ICA <i>IC-Rated, Airtight</i></p>	<p>120V-277V</p>	<p><i>Allows adjustment in any direction when used with adjustable trims</i></p>
<p><i>Remodel</i></p> 	<p>HR-2LED-R09D-A <i>Non-IC, Airtight</i></p>	<p>120V-277V</p>	<p><i>Requires 3" of clearance from insulation on all sides</i></p> <p><i>Ceiling thickness: 1/2"-1"</i></p> <p><i>Does not accommodate adjustments</i></p>
<p><i>Adjustable Remodel</i></p> 	<p>HR-2LED-R14D <i>Non-IC</i></p>	<p>120V-277V</p>	<p><i>Allows adjustment in any direction when used with adjustable trims</i></p> <p><i>Requires 3" of clearance from insulation on all sides</i></p> <p><i>Ceiling thickness: 1/2"-5/8"</i></p>



Tesla Pro 3.5" LED



















Power: 22W
Delivered Lumens: Up to 1460
Comparable to: 75W MR16
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours

High Output LED






- Universal input voltage (120V-220V-277V)
- All Energy Star® rated
- Wet and Damp location listed
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- 3.5" aperture
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

	Beam	Color Temp	CRI	Finish	Reflector/Trim
  <p>HR3LD-ET118P High Brightness Wet Location Listed Energy Star® 9° visual cutoff</p>	F 48°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85		BN Brushed Nickel CB Copper Bronze WT White	
  <p>HR3LEDT118P Downlight Energy Star®</p>	N 30° F 55°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85		HBN Haze/Brushed Nickel HCB Haze/Copper Bronze HWT Haze/White BBN Specular Black/Brushed Nickel BCB Specular Black/Copper Bronze BWT Specular Black/White BN Brushed Nickel CB Copper Bronze WT White	
  <p>HR3LEDT318P 0°- 30° Adjustable Energy Star®</p>	N 30° F 55°				
  <p>HR3LEDT418P 30°- 45° Adjustable Energy Star®</p>	N 26° F 38°				
  <p>HR3LEDT218P Shower Light Wet Location Listed Energy Star®</p>	N 30°				
  <p>HR3LEDT718P Open Reflector Energy Star®</p>	N 30° F 52°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85		BN Brushed Nickel CB Copper Bronze WT White	
  <p>HR3LEDT518P 0°- 30° Adjustable Energy Star®</p>	N 30° F 52°				
  <p>HR3LEDT918P 30°- 45° Adjustable Energy Star®</p>	N 26° F 38°				
  <p>HR3LEDT818P Shower Light Wet Location Listed Energy Star®</p>	N 30°				

Example: **HR3LD-ET118PF930BN**

Tesla Pro 3.5" Housing

Housings (Required)	Model	Input	Notes
<p><i>Narrow New Construction</i></p> 	<p>HR-3LED-H18D1-ICA IC-Rated, Airtight</p>	120V -277V	<p>Allows adjustment in one direction when used with HR3LEDT918P</p> <p>Does not accommodate HR3LEDT418P</p> <p>Ceiling thickness: ½"–¾"</p>
	<p>HR-3LED-H18D1-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V -277V	
<p><i>Adjustable New Construction</i></p> 	<p>HR-3LED-H18D-ICA IC-Rated, Airtight</p>	120V -277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Ceiling thickness: ½"–¾"</p>
	<p>HR-3LED-H18D-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V -277V	
	<p>HR-3LED-H18D-EMICA IC-Rated, Airtight Emergency Backup Battery</p>	120V	
<p>HR-3LED-H18D-EMICAF IC-Rated, Airtight Emergency Backup Battery</p>	277V		
<p><i>New Construction</i></p> 	<p>HR-3LED-H18D-A Non-IC, Airtight</p>	120V -277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: ½"–1"</p> <p>Does not accommodate adjustments</p>
<p><i>Remodel</i></p> 	<p>HR-3LED-R18D-A Non-IC, Airtight</p>	120V -277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: ½"–1"</p> <p>Does not accommodate adjustments</p>
<p><i>Adjustable Remodel</i></p> 	<p>HR-3LED-R22D Non-IC</p>	120V-277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: ½"-5/8"</p>

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Narrow Flood	SL-REF-BL10-1-N
Flood	SL-REF-BL10-1-F

LED

2700K	85 CRI	BXRC-27E1000-B-03
2700K	90 CRI	BXRC-27G1000-B-03
3000K	85 CRI	BXRC-30E1000-B-03
3000K	90 CRI	BXRC-30G1000-B-03
3500K	85 CRI	BXRC-35E1000-B-03
4000K	85 CRI	BXRC-40E1000-B-03

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket

Tesla 3.5" LED



Power: 21.5W
Delivered Lumens: Up to 1070
Comparable to: 75W MR16
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours






- Damp location listed (Shower Light is wet location listed)
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- Universal driver (120V-220V-277V)
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

Trims (Order Housing Separately)		Beam	Color Temp	CRI	Finish	Reflector/Trim
		HR-3LD-ET118 Round Downlight Energy Star® 9° visual cutoff	F 40°	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85	BN Brushed Nickel/Brushed Nickel CB Copper Bronze/Copper Bronze WT White/White	
		HR-3LED-T118 Round Downlight	S 15° N 28° F 50°	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85	HZ/BN Haze/Brushed Nickel HZ/CB Haze/Copper Bronze HZ/WT Haze/White SB/BN Specular Black/Brushed Nickel SB/CB Specular Black/Copper Bronze SB/WT Specular Black/White BN Brushed Nickel/Brushed Nickel CB Copper Bronze/Copper Bronze WT White/White	
		HR-3LED-T318 Round 0°- 30° Adjustable				
		HR-3LED-T618 Round Pin Hole, 0°- 30° Adjustable				
		HR-3LED-T418 Round 30°- 45° Adjustable	S 15° N 28° F 41°	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85	BN Brushed Nickel/Brushed Nickel CB Copper Bronze/Copper Bronze WT White/White	
		HR-3LED-T218 Round Shower Light Wet Location Listed				
		HR-3LED-T718 Square Downlight				
		HR-3LED-T818 Square Shower Light Wet Location Listed	S 15° N 28° F 50°	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85	BN Brushed Nickel/Brushed Nickel CB Copper Bronze/Copper Bronze WT White/White	
		HR-3LED-T518 Square 0°- 30° Adjustable				
		HR-3LED-T918 Square 30°- 45° Adjustable				

Example: **HR-3LED-T918F-W-CB**

Tesla 3.5" Housing

Housings (Required)	Model	Input	Notes
<p><i>Narrow New Construction</i></p> 	<p>HR-3LED-H18D1-ICA IC-Rated, Airtight</p>	120V-277V	<p>Allows adjustment in one direction when used with HR3LEDT918</p>
	<p>HR-3LED-H18D1-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V-277V	<p>Does not accommodate HR3LEDT418</p> <p>Ceiling thickness: ½"–¾"</p>
<p><i>Adjustable New Construction</i></p> 	<p>HR-3LED-H18D-ICA IC-Rated, Airtight</p>	120V-277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Ceiling thickness: ½"–¾"</p>
	<p>HR-3LED-H18D-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V-277V	
	<p>HR-3LED-H18D-EMICA IC-Rated, Airtight Emergency Backup Battery</p>	120V	
<p>HR-3LED-H18D-EMICAF IC-Rated, Airtight Emergency Backup Battery</p>	277V		
<p><i>New Construction</i></p> 	<p>HR-3LED-H18D-A Non-IC, Airtight</p>	120V-277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: ½"–1"</p> <p>Does not accommodate adjustments</p>
<p><i>Remodel</i></p> 	<p>HR-3LED-R18D-A Non-IC, Airtight</p>	120V-277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: ½"–1"</p> <p>Does not accommodate adjustments</p>
<p><i>Adjustable Remodel</i></p> 	<p>HR-3LED-R22D Non-IC</p>	120V-277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: ½"–5/8"</p>

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Spot	SL-REF-LUX10-S
Narrow Flood	SL-REF-LUX10-N
Flood	SL-REF-LUX10-F

LED

2700K	85 CRI	LXS8-PW27
3000K	90 CRI	LXS9-PW30
3000K	85 CRI	LXS8-PW30
3500K	85 CRI	LXS8-PW35
4000K	85 CRI	LXS8-PW40

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket

Precision Multiples 4" LED with ELV or 0-10V dimming options



Black trim shown





Comparable to: 75W MR16
 Rated Life: 50,000 hours

Retractable Spot Lights

- ELV and 0-10V dimming options - see specification sheet for list of tested dimmers
- Black, white, or Invisible Trim™ option
- Energy Star® rated
- CEC Title 24 Compliant
- Fully retractable from housing
- 355° horizontal rotation and 180° vertical aiming
- Accepts 1 replacement lens


1 Light

Trims

		MT-4LD116T Trim	WT White BK Black
		MT-4LD116TL-WT Invisible Trim™	

Example: **MT-4LD116T-WT**





Housings

Housings	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD116N 0-10V dimming Non-IC, 120V-277V input	16.5W	S 20° 1100 F 40° 1080	5370 2390	27 2700K 927 2700K 30 3000K 930 3000K 35 3500K 40 4000K	85	BK Black
	MT4LD116NE ELV dimming Non-IC, 120V input	16.5W	S 20° 1005 F 40° 990	4700 2115			
	MT4LD111NE ELV dimming IC-Rated, 120V input	11.5W	S 20° 890 F 40° 885	3925 1820			

Example: **MT4LD111NE-F930-BK**


2 Lights

Trims

		MT-4LD216T Trim	WT White BK Black
		MT-4LD216TL-WT Invisible Trim™	


Example: **MT-4LD216T-WT**

Housings

Housings	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD216N 0-10V dimming Non-IC, 120V-277V input	33W	S 20° 2200 F 40° 2160	5370x2 2390x2	27 2700K 927 2700K 30 3000K 930 3000K 35 3500K 40 4000K	85	BK Black
	MT4LD216NE ELV dimming Non-IC, 120V input	33W	S 20° 2010 F 40° 1980	4700x2 2115x2			
	MT4LD211NE ELV dimming IC-Rated, 120V input	23W	S 20° 1785 F 40° 1765	3928x2 1820x2			

Example: **MT-4LD216N-S927-BK**





Replacement Lens

Amber	LENS-16-AMB	
Blue	LENS-16-BLU	
Green	LENS-16-GRN	
Red	LENS-16-RED	
Yellow	LENS-16-YEL	

UV Filter	LENS-16-UVF	
Frosted	LENS-16-FR	
Spread	LENS-16-SPR	
Beam Elongator	LENS-16-BEL	


3 Lights

Trims

		MT-4LD316T Trim	WT White BK Black
		MT-4LD316TL-WT Invisible Trim™	

Example: **MT-4LD316T-WT**





Housings

Housings	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD316N 0-10V dimming Non-IC, 120V-277V input	49.5W	S 20° F 40°	3300 3240	5370x3 2390x3	27 2700K 927 2700K	BK Black
	MT4LD316NE ELV dimming Non-IC, 120V input	49.5W	S 20° F 40°	3015 2970	4700x3 2115x3	30 3000K 930 3000K	
	MT4LD311NE ELV dimming IC-Rated, 120V input	34.5W	S 20° F 40°	2680 2650	3925x3 1820x3	35 3500K 40 4000K	

Example: **MT4LD311NE-S30-BK**


4 Lights

Trims

		MT-4LD416T Trim	WT White BK Black
		MT-4LD416TL-WT Invisible Trim™	

Example: **MT-4LD416T-WT**





Housings

Housings	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD416N 0-10V dimming Non-IC, 120V-277V input	66W	S 20° F 40°	4400 4320	5370x4 2390x4	27 2700K 927 2700K	BK Black
	MT4LD416NE ELV dimming Non-IC, 120V input	66W	S 20° F 40°	4020 3960	4700x4 2115x4	30 3000K 930 3000K	
	MT4LD411NE ELV dimming IC-Rated, 120V input	46W	S 20° F 40°	3570 3535	3925x4 1820x4	35 3500K 40 4000K	

Example: **MT-4LD416N-S927-BK**


4 Lights (2x2)

Trims

		MT-4LD226T Trim	WT White BK Black
		MT-4LD226TL-WT Invisible Trim™	

Example: **MT-4LD226T-WT**

Housings

Housings	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD226N 0-10V dimming Non-IC, 120V-277V input	66W	S 20° F 40°	4400 4320	5370x4 2390x4	27 2700K 927 2700K	BK Black
	MT4LD226NE ELV dimming Non-IC, 120V input	66W	S 20° F 40°	4020 3960	4700x4 2115x4	30 3000K 930 3000K	
	MT4LD221NE ELV dimming IC-Rated, 120V input	46W	S 20° F 40°	3570 3535	3925x4 1820x4	35 3500K 40 4000K	

Example: **MT4LD226NE-S930-BK**



Mini LED Multiple Spots


New Color Temperature options

Comparable: 50W MR16
Dimming: 100 - 10%
Rated Life: 50,000 hours
Input Voltage: 120V

- Integral housing and trim**
- Energy Star®
 - Individually adjustable luminaires
 - Complete unit includes housing & trim
 - 30° visual cutoff for glare control
 - ELV dimming - see specification sheet for list of tested dimmers




1 Light



		Power	Beam	Max Lumens	Max CBCP	Color Temp	CRI	Finish			
	MT-3LD111NA <i>New Construction</i> <i>Non-IC, Airtight</i>	11W	F 25°	805	2224	927 2700K 90	930 3000K 90	BK White trim with black interior			
			W 45°	795	1042						
	MT-3LD111R <i>Remodel</i> <i>Non-IC</i>	11W	F 25°	805	2224				935 3500K 90	940 4000K 90	WT White trim with white interior
			W 45°	795	1042						

Example: **MT-3LD111NA-F927-WT**

2 Lights



		Power	Beam	Max Lumens	Max CBCP	Color Temp	CRI	Finish			
	MT-3LD211NA <i>New Construction</i> <i>Non-IC, Airtight</i>	22W	F 25°	805x2	2224x2	927 2700K 90	930 3000K 90	BK White trim with black interior			
			W 45°	795x2	1042x2						
	MT-3LD211R <i>Remodel</i> <i>Non-IC</i>	22W	F 25°	805x2	2224x2				935 3500K 90	940 4000K 90	WT White trim with white interior
			W 45°	795x2	1042x2						

Example: **MT-3LD211R-F927-WT**

3 Lights



		Power	Beam	Max Lumens	Max CBCP	Color Temp	CRI	Finish			
	MT-3LD311NA <i>New Construction</i> <i>Non-IC, Airtight</i>	33W	F 25°	805x3	2224x3	927 2700K 90	930 3000K 90	BK White trim with black interior			
			W 45°	795x3	1042x3						
	MT-3LD311R <i>Remodel</i> <i>Non-IC</i>	33W	F 25°	805x3	2224x3				935 3500K 90	940 4000K 90	WT White trim with white interior
			W 45°	795x3	1042x3						

Example: **MT-3LD311R-F927-WT**

Driver hidden inside
W track

Twist to adjust beam angle



Use with a track cover for a seamless installation



8 foot W track cover: **W8-COV-WT**
Can be field-cut and painted




Paloma Adjustable Beam LED

Power: 24W
Delivered Lumens: Up to 1600
CBCP: Up to 7650
Comparable to: 20W HID
Rated Life: 50,000 hours

Museum-quality LED luminaire with adjustable beam angle

- Adjustable beam angle between 15° - 60°
- Die-cast aluminum construction
- 365° horizontal rotation and 180° vertical aiming
- Smooth and continuous ELV dimming for 120V
- ELV dimming - see specification sheet for list of tested dimmers





Track	Model	Color Temp	CRI	Max Lumens	Max CBCP	Finish	
W Track	WTK 120V WHK 277V	LED523	27 2700K	85	1340	6840	BK Black PT Platinum WT White
			927 2700K	90	1260	6515	
			30 3000K	85	1500	7595	
			930 3000K	90	1350	6635	
			35 3500K	85	1495	7280	
		40 4000K	85	1600	7650		

Example: **WTK-LED523-927-WT**

Adjustable Beam Angle


Adjustable between 15° - 60°



W Track Quick Connect™ Adapter



Transformer hidden inside W track



See website www.waclighting.com for all other pendant options

The Quick Connect™ collection includes a wide array of pendants and fixtures with different mounting options.



The threaded male adapter makes inter-system compatibility a snap. Simply insert the metal fitting into the system adapter and hand tighten the collar.

Order one per Quick Connect™ fixture or pendant used.

Use with a track cover for a seamless installation




8 foot W track cover: **W8-COV-WT**
Can be field-cut and painted


System Adapter	Specifications	Model	Finish
W Track 120V 	<ul style="list-style-type: none"> • Recessed transformer within W track • Allows all Quick Connect™ elements to be used with the W track 120V systems • 1W minimum load transformer • Smooth and continuous ELV dimming 	EN-WQ50AR	BK Black PT Platinum WT White 

Example: **EN-WQ50AR-WT**


W Track Current Limiter



Surface Mount










Recessed Flanged










Recessed Flangeless

120V W Track

	Model	Rating	Circuit Breaker	Max Wattage	Finish
Single Live end (Left)	 WEDL Surface Mount	1/5A 1/2A 1A 2A 5A 7A 10A 12A	2 X 0.2Amp 2 X 0.5Amp 2 X 1 Amp 2 X 2.5Amp 2 X 5 Amp 2 X 7.5Amp 2 X 10Amp 2 X 12Amp	2 X 24W 2 X 60W 2 X 120W 2 X 300W 2 X 600W 2 X 900W 2 X 1200W 2 X 1440W	BK Black PT Platinum WT White 
	 WEDL-RT Recessed Flanged				
	 WEDL-RTL Recessed Flangeless				
Single Live end (Right)	 WEDR Surface Mount				
	 WEDR-RT Recessed Flanged				
	 WEDR-RTL Recessed Flangeless				

Example: **WEDL-1/5A-BK**











277V W Track

	Model	Rating	Circuit Breaker	Max Wattage	Finish
Single Live end (Left)	 WHEDL Surface Mount	1A 2A 5A 7A 10A 12A	2 X 1 Amp 2 X 2.5Amp 2 X 5 Amp 2 X 7.5Amp 2 X 10Amp 2 X 12Amp	2 X 277W 2 X 692W 2 X 1385W 2 X 2077W 2 X 2770W 2 X 3324W	BK Black PT Platinum WT White 
	 WHEDL-RT Recessed Flanged				
	 WHEDL-RTL Recessed Flangeless				
Single Live end (Right)	 WHEDR Surface Mount				
	 WHEDR-RT Recessed Flanged				
	 WHEDR-RTL Recessed Flangeless				


Example: **WHEDL-1A-BK**

H Track Current Limiter

- Slim single live end nearly matches the width and height of the H track stem
- Small capacity current limiters allow further energy saving

	Model	Circuit Breaker	Max Wattage	Finish
 <p>New Product</p> <p><i>Slim Single Live End</i></p>  <p>THL-HLES</p>				
 <p><i>Single Live End</i></p>  <p>THL-HLE</p>	1/5A 1/2A 1A 2A 5A 7A 10A	200mA 500mA 1A 2.5A 5A 7.5A 10A	24W 60W 120W 300W 600W 900W 1200W	
 <p><i>Double Live End</i></p>  <p>THL-HI</p>				
 <p><i>Double Live End (Left)</i></p>  <p>THL-LEFT</p>	1-1/2A 2-1/2A 1-1A 2-1A 1-2A 2-2A 1-5A 2-5A 1-7A 2-7A	500mA 500mA per end 1A 1A per end 2.5A 2.5A per end 5A 5A per end 7.5A 7.5A per end	60W 60W per end 120W 120W per end 300W 300W per end 600W 600W per end 900W 900W per end	
 <p><i>Double Live End (Right)</i></p>  <p>THL-RIGHT</p>	1-10A 2-10A	10A 10A per end	1200W 1200W per end	

BK Black
BN Brushed Nickel
DB Dark Bronze
WT White



Example: **THL-LEFT-1-1/5A-WT**



52W Exterminator II

Comparable: 70W HID
 ELV Dimming: 100% - 1%
 Rated Life: 80,000 hours

- Energy Star® rated
- Accommodates one lens accessory and one glare control accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Max Lumens	Max CBCP	Color Temp	CRI	Finish
<p>WTK 120V WHK 277V</p>	1052 52W	N 25° 4237 F 55° 3910	15970 1640	827 2700K 85	85	BK Black PT Platinum WT White
				927 2700K 90		
				830 3000K 85		
				930 3000K 90		
				835 3500K 85		
				840 4000K 85		
<p>H H TRACK L L TRACK J J/J2 TRACK</p>	1052 52W	N 25° 4237 F 55° 3910	15970 4640	827 2700K 85	85	BN Brushed Nickel BK Black WT White
				927 2700K 90		
				830 3000K 85		
				930 3000K 90		
				835 3500K 85		
				840 4000K 85		

Example: **WTK-1052N-930-WT**

LENS ACCESSORIES

Amber	LENS-25-AMB
Blue	LENS-25-BLU
Green	LENS-25-GRN
Red	LENS-25-RED
Yellow	LENS-25-YEL
UV Filter	LENS-25-UVF
Frosted	LENS-25-FR
Spread	LENS-25-SPR
Beam Elongating	LENS-25-BEL

REFLECTORS

25°	SL-REF-LUX1208-N
55°	SL-REF-LUX1208-F

GLARE CONTROL ACCESSORIES

Cross Louver	LENS-25-CRL
Snoot	LENS-25-SNOOT

LED MODULES

2700K	CRI 85	LHC1-2780-1208-W
2700K	CRI 90	LHC1-2790-1208-W
3000K	CRI 85	LHC1-3080-1208-W
3000K	CRI 90	LHC1-3090-1208-W
3500K	CRI 85	LHC1-3580-1208-W
4000K	CRI 85	LHC1-4080-1208-W



35W Exterminator II

Comparable: 50W HID
 ELV Dimming: 100% - 5%
 Rated Life: 60,000 hours

- Energy Star® rated
- CEC Title 24 Compliant
- Accommodates one lens accessory and one glare control accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Max Lumens	Max CBCP	Color Temp	CRI	Finish
<p>WTK 120V WHK 277V</p>	1035 35W	N 25° 2795 F 55° 2828	9748 3886	827 2700K 85	85	BK Black PT Platinum WT White
				927 2700K 90		
				830 3000K 85		
				930 3000K 90		
				835 3500K 85		
				840 4000K 85		
<p>H L J TRACK</p>	1035 35W	N 25° 2795 F 55° 2828	9748 3886	827 2700K 85	85	BN Brushed Nickel BK Black WT White
				927 2700K 90		
				830 3000K 85		
				930 3000K 90		
				835 3500K 85		
				840 4000K 85		

Example: **WHK-1035F-830-BK**

LENS ACCESSORIES

Amber	LENS-20-AMB
Blue	LENS-20-BLU
Green	LENS-20-GRN
Red	LENS-20-RED
Yellow	LENS-20-YEL
UV Filter	LENS-20-UVF
Frosted	LENS-20-FR
Spread	LENS-20-SPR
Beam Elongating	LENS-20-BEL

REFLECTORS

25°	SL-REF-BL18-N
55°	SL-REF-BL18-F

GLARE CONTROL ACCESSORIES

Cross Louver	LENS-20-CRL
Snoot	LENS-20-SNOOT

LED MODULES

2700K	CRI 85	BXRC-27E4000-F-23
2700K	CRI 90	BXRC-27G4000-F-23
3000K	CRI 85	BXRC-30E4000-F-23
3000K	CRI 90	BXRC-30G4000-F-23
3500K	CRI 85	BXRC-35E4000-F-23
4000K	CRI 85	BXRC-40E4000-F-23



14W Exterminator II

Comparable: 20W HID
ELV Dimming: 100% - 1%
Rated Life: 100,000 hours

- Energy Star® rated
- CEC Title 24 Compliant
- Accommodates one lens accessory and one glare control accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model		Max Lumens	Max CBCP	Color Temp	CRI	Finish
<p>WTK 120V</p>	1014 14W	N	20°	965	4585	827 2700K 85	BK Black PT Platinum WT White
			40°	980	2117	927 2700K 90	
		F	830 3000K 85				
			930 3000K 90				
			835 3500K 85				
			840 4000K 85				
<p>H H TRACK L L TRACK J J/J2 TRACK</p>	1014 14W	N	20°	965	4585	827 2700K 85	BN Brushed Nickel BK Black WT White
			40°	980	2117	927 2700K 90	
		F	830 3000K 85				
			930 3000K 90				
			835 3500K 85				
			840 4000K 85				

Example: **WTK-1014N-927-WT**

LENS ACCESSORIES

Amber	LENS-11-AMB
Blue	LENS-11-BLU
Green	LENS-11-GRN
Red	LENS-11-RED
Yellow	LENS-11-YEL
UV Filter	LENS-11-UVF
Frosted	LENS-11-FR
Spread	LENS-11-SPR
Beam Elongating	LENS-11-BEL

REFLECTORS

20°	SL-REF-CXA1310-N
40°	SL-REF-CXA1310-F

GLARE CONTROL ACCESSORIES

Cross Louver	LENS-11-CRL
Snoot	LENS-11-SNOOT

LED MODULES

2700K	CRI 85	CXA1310-00J227H-W
2700K	CRI 90	CXA1310-0YG227H-W
3000K	CRI 85	CXA1310-00J430H-W
3000K	CRI 90	CXA1310-0YG430H-W
3500K	CRI 85	CXA1310-00J435H-W
4000K	CRI 85	CXA1310-0HK240H-W



23W Exterminator

Comparable: 39W HID
ELV Dimming: 100% - 10%
Rated Life: 60,000 hours

- Recessed Driver
- Energy Star® Rated
- Accommodates one lens accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Max Lumens	Max CBCP	Color Temp	CRI	Finish
<p>WTK 120V WHK 277V</p>	LED20 23W	S 20° 1450 F 40° 1390	6772 2928	27 2700K 85	85	BK Black PT Platinum WT White
				927 2700K 90		
				30 3000K 85		
				930 3000K 90		
				35 3500K 85		
40 4000K 85						
<p>H H TRACK L L TRACK J J/J2 TRACK</p>	LED20 23W	S 20° 1450 F 40° 1390	6772 2928	27 2700K 85	85	BN Brushed Nickel BK Black WT White
				927 2700K 90		
				30 3000K 85		
				930 3000K 90		
				35 3500K 85		
40 4000K 85						

Example: **WTK-LED20F-30-PT**

LENS ACCESSORIES

Amber	LENS-16-AMB
Blue	LENS-16-BLU
Green	LENS-16-GRN
Red	LENS-16-RED
Yellow	LENS-16-YEL
UV Filter	LENS-16-UVF
Frosted	LENS-16-FR
Spread	LENS-16-SPR
Beam Elongating	LENS-16-BEL

REFLECTORS

20°	RF-S
40°	RF-F

LED MODULES

2700K	CRI 85	BXRC-27E1000
2700K	CRI 90	BXRC-27G1000
3000K	CRI 85	BXRC-30E1000
3000K	CRI 90	BXRC-30G1000
3500K	CRI 85	BXRC-35E1000
4000K	CRI 85	BXRC-40E1000



LED207





LED201

Summit LED

Power: 15W
Comparable: 50W MR16
CRI: 85
ELV Dimming: 100% - 10%
Input: 120V
Rated Life: 50,000 hours

Compact driverless LED track luminaire

- Energy Star® rated
- 120VAC - no driver needed
- Beamshift™ enables in-field change of beam angle (patent pending)
- Die-cast aluminum construction
- ELV dimming - see specification sheet for list of tested dimmers


Track	Model	Color Temp	Beam*	Lumens	CBCP	Finish
H H TRACK L L TRACK J J/J2 TRACK	 LED207-30	3000K	25° 40°	540 660	1275 1030	BK Black WT White
	 LED201-30	3000K	25° 40°	540 660	1275 1030	BK Black WT White

Example: **H-LED207-30-WT**


*All Summit LED track luminaires come with Flood (40°) beam setting by default, which may be reconfigured to Narrow(25°) in field.

BeamShift™

All Summit series track luminaires come with BeamShift™, allowing in-field change of beam angle simply by changing the location of the lens



Flood Configuration
Lens located at the back



Spot Configuration
Lens located in the front



LED202







LED208

Summit LED

Power: 15W
Comparable: 50W MR16
CRI: 85
ELV Dimming: 100% - 10%
Input: 120V
Rated Life: 50,000 hours

Compact driverless LED track luminaire

- Energy Star® rated
- 120VAC - no driver needed
- Beamshift™ enables in-field change of beam angle (patent pending)
- Die-cast aluminum construction
- ELV dimming - see specification sheet for list of tested dimmers

Track		Model	Color Temp	Beam*	Lumens	CBCP	Finish
H L J	H TRACK L TRACK J/J2 TRACK	 LED202-30	3000K	25° 40°	540 660	1275 1030	BK Black WT White
		 LED208-30	3000K	25° 40°	540 660	1275 1030	AB Antique Bronze
HM1	FLEXRAIL 1™	 LED202-30	3000K	25° 40°	540 660	1275 1030	PT Platinum
		 LED208-30	3000K	25° 40°	540 660	1275 1030	DB Dark Bronze

Example: H-LED202-30-BK

* All Summit LED track luminaires come with Flood (40°) beam setting by default, which may be reconfigured to Narrow(25°) in field.



Precision LED

Power: 14.5W
Delivered Lumens: Up to 975
CBCP: Up to 4500
Comparable to: 65W MR16
ELV Dimming: 100%-10%
Rated Life: 70,000 hours

Compact single diode LED

- CEC Title24 Compliant
- Die-cast aluminum construction
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Beam	Color Temp	CRI	Finish
H H TRACK L L TRACK J J/J2 TRACK	 LED160	S 20° F 40°	927 2700K	90	BK Black WT White
			27 2700K	85	
			930 3000K	90	
			30 3000K	85	
			35 3500K	85	
			40 4000K	85	

Example: **H-LED160S-927-BK**

Replacement Lenses

Amber	LENS-16-AMB	
Blue	LENS-16-BLU	
Green	LENS-16-GRN	
Red	LENS-16-RED	
Yellow	LENS-16-YEL	


UV Filter	LENS-16-UVF	
Frosted	LENS-16-FR	
Spread	LENS-16-SPR	
Beam Elongator	LENS-16-BEL	

LED Track Luminaires MR16 Replacement - Now with 1W-60W Transformer

Power: 8W
Lumens: 450
CBCP: 850
Color Temp: 3000K
CRI: 85
ELV Dimming: 100% - 10%
Input: 120V
Rated Life: 25,000 hours

- 1 W to 60 W load transformer
- Fixtures specifically designed to ensure proper lamp fit
- LED lamp included
- ELV dimming - see specification sheet for list of tested dimmers

System	Model	Finish
 HHT LHT JHT	164LED	BK WT <i>Black White</i>
 HHT LHT JHT	886LED	AB <i>Antique Bronze</i>
 HHT LHT JHT	874LED	AB <i>Antique Bronze</i>
 HHT LHT JHT	856LED	AB BK BN WT <i>Antique Bronze Black Brushed Nickel White</i>
 HHT LHT JHT	817LED	BK PT/BK PT/WT WT <i>Black Platinum/Black Platinum/White White</i>
 HHT LHT JHT	826LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	816LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	808LED	BK DB WT <i>Black Dark Bronze White</i>

System	Model	Finish
 HHT LHT JHT	160LED	BK WT <i>Black White</i>
 HHT LHT JHT	180LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	809LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	802LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	846LED	BK WT <i>Black White</i>
 HHT LHT JHT	204LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	801LED	BK WT <i>Black White</i>
 HHT LHT JHT	007LED	BK BN WT <i>Black Brushed Nickel White</i>

Example: HHT-808LED-DB

Power: 2W / ft
Lumens: Up to 175 lm / ft
CRI: 85
Rated Life: 50,000 hours

- UL listed for damp location
- May be field cut every 2 inches at the end of a run
- Includes an end cap
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	Length	Qty	Finish
LED-T24	27L 2700K 30L 3000K	2IN 2 inches	1	WT White
		2IN10 2 inches	10	
		1 1 foot	1	
		5 5 feet	1	
		1-40 1 foot	40	

Example: **LED-T2427L-5-WT**

"L" Connector

System	Color Temp	Finish
LED-T24	27L 2700K 30L 3000K	3L-WT White

Example: **LED-T2427L-3L-WT**

Each "L" connector consumes 0.7 watt

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	30 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	40 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	40 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	30 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	40 feet	Yes

Accessories

For mounting accessories, please see page 40



Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box		LED-T-B	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires
Wiring Box With Switch		TB-S	L: 6 1/4 in W: 1 5/8 in H: 1 1/4 in Use when spanning a large gap in a system layout without leaving exposed wiring
Joiner Cable		LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
3-Way "Y" Connector		LED-TC-Y	Connects tape sections
4-Way "X" Connector		LED-TC-X	Connects tape sections
"L" Connector		LED-TC-L	Connects tape sections
End cap		LED-TC-EC	1 cut end cap 1 male end cap

Pro2 InvisiLED®

New 2200K Color Temperature

Power: 4W / ft
Lumens: Up to 330 lm / ft
CRI: 90
Rated Life: 80,000 hours

- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	Length	Qty	Finish
LED-TX24	22 2200K	6IN 6 inches	1	WT White
	27 2700K		1	
	30 3000K		1	
	35 3500K		1	
	45 4500K		40	

Example: **LED-TX2435-6IN-WT**

"L" Connector

System	Color Temp	Finish
LED-TX24	22 2200K	5L-WT White
	27 2700K	
	30 3000K	
	35 3500K	
	45 4500K	

Example: **LED-TX2435-5L-WT**
 Each "L" connector consumes 2 watt

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	25 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	25 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	25 feet	Yes

Accessories

For mounting accessories, please see page 40


Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box		LED-T-B	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires
Wiring Box With Switch		TB-S	L: 6 1/4 in W: 1 5/8 in H: 1 1/4 in Use when spanning a large gap in a system layout without leaving exposed wiring
Joiner Cable		LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
3-Way "Y" Connector		LED-TC-Y	Connects tape sections
4-Way "X" Connector		LED-TC-X	Connects tape sections
"L" Connector		LED-TC-L	Connects tape sections
End cap		LED-TC-EC	1 cut end cap 1 male end cap

Pro3 InvisiLED®

New Product

Power: 5W / ft
Lumens: Up to 475 lm / ft
CRI: 90
Rated Life: 70,000 hours

- Brightest InvisiLED® system available
- Laterally bendable design
- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap and a male to male connector with each tape section
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	CRI	Length	Qty	Finish
LED-TE24	27 2700K	95	6IN 6 inches	1	WT White
	30 3000K	95	1 1 foot	1	
	35 3500K	90	5 5 feet	1	
	45 4500K	90	1-40 1 foot	40	

Example: **LED-TE2435-6IN-WT**

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	20 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	20 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	20 feet	Yes



Accessories

For mounting accessories, please see page 40

Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies		
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section	Joiner Cable	 LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in Connects tape sections
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1½ in W: ¾ in H: 7/8 in Neatly houses up to two wires with 2" female feed	3-Way "Y" Connector	 LED-TC-Y Connects tape sections
Low Voltage Wiring Box		LED-T-B	L: 1½ in W: ¾ in H: 7/8 in Neatly houses up to two wires	4-Way "X" Connector	 LED-TC-X Connects tape sections
Wiring Box With Switch		TB-S	L: 6¼ in W: 1½ in H: 1¼ in Use when spanning a large gap in a system layout without leaving exposed wiring	"L" Connector	 LED-TC-L Connects tape sections
				End cap	 LED-TC-EC 1 cut end cap 1 male end cap


Mounting accessories

Compatible with InvisiLED® Pro, Pro2, Pro3, LITE, Classic, Daylight to Sunset, and Palette

Aluminum Channel

LED-T-CH

5 feet



Includes a diffuser, two end caps, and five screws

Deep Aluminum Channel

LED-T-CH1

5 feet




Includes a diffuser, two end caps, and five screws

45° Angled Aluminum Channel

LED-T-CH2

5 feet



Includes a diffuser, two end caps, and five screws

Fixed Angle Channel Clip

LED-T-CL3-PT

2 pcs




Used to mount any aluminum channel
Includes 2 pieces, 4 screws

Adjustable Channel Clip

LED-T-CL2-PT

2 pcs




Used to mount any aluminum channel
Adjusts 50° from center either way
Includes 2 pieces, 4 screws

Retrofit Channel

LED-T-RC

3 feet




Can be bent to create fixed curves

Clip

LED-T-CL

10 pcs



Holds the tape from the underside
Includes 10 pieces, 10 screws

New Product


Curve Clip

LED-T-CL1


10 pcs



Runs over the tape to secure the angled tape
Includes 10 pieces, 10 screws



Touch and Occupancy Control Kit For Low Voltage Systems



CT-6A-R2


Includes a Touch Panel, an Occupancy Sensor, and a Controller
AC/DC input at 12V(60W Max) or 24V(96W Max)
Connect on secondary side of driver/transformer

Three custom settings of lighting control


Touch and Sensor: Touch panel turns the luminaire on/off manually while the motion sensor turns it off when the space is vacant

Touch: Touch panel turns the luminaire on/off manually

Sensor: Motion sensor turns the luminaire on/off autonomously



Surface mounted



Recessed

LED90 Edge Lit Button Light New Dark Bronze Finish



Power: 24V, 5W
CRI: 90
ELV Dimming: 100% – 5%
Rated Life: 100,000 hours
Cutout: 3 3/4" for recessed applications

- Energy Star® rated
- CEC Title24 Compliant
- Can be surface mounted or recessed
- Super thin profile at 1/2"
- Edge-lit LEDs reduce glare and assure even light distribution
- Anti-microbial white paint
- ELV dimming - see specification sheet for list of tested dimmers

Model	Color Temp	Lumens	Finish
HR-LED90	27 2700K	200	BN <i>Brushed Nickel</i>
	30 3000K	200	BK <i>Black</i>
			DB <i>Dark Bronze</i>
			WT <i>White</i>

Example: **HR-LED90-30-WT**
 Includes 6 foot lead wire

Class 2 enclosed electronic transformers (Required)

Model	Input	Output	Min Load	Max Fixture Run	L	W	H	
 EN-2460-RB2 EN-24100-RB2	120V	24V, 60W	1W	7	6 1/2"	1 5/8"	1 1/4"	<i>Fits through small openings</i>
	120V	24V, 96W	1W	10	6 1/2"	1 5/8"	1 1/4"	
 EN-2460-P-AR	120V	24V, 60W	1W	7	2 3/4"	1 5/8"	1 3/4"	<i>Plug-in power supply with on/off switch and 6' detachable cord</i>

- Secondary wiring for Class 2 transformers does not require conduit sheathed cable or clamp wiring techniques
- Intrinsically safe, Class 2 transformers permit no greater than a 5 amp current to be drawn
- Non-metallic sheathed cable may be used for secondary wiring in walls and ceilings
- Power consumption may vary depending on the efficiency of the power supply being used



LINE™ 2.0 LED Undercabinet

Fixed Light Panel

- Energy Star® rated
- Diffused light source reduces glare, eliminates hard shadows
- Asymmetrical forward throw for optimal light distribution
- Anti-microbial paint (white only)
- Connections made at the center of each fixture
- ELV dimming - see specification sheet for list of tested dimmers

CRI: 90+

ELV Dimming: 100% - 10% (120V only)

Rated Life: 100,000 hours

	Length	Watt	Max Lumens	Max Fixture Run		Color Temp	Finish
				60 W	96 W		
	LN-LED06P	6.5W	265	6	11	27 2700K 30 3000K	AL Brushed Aluminum WT White
	LN-LED12P	10.5W	515	3	6		
	LN-LED18P	16W	875	2	4		
	LN-LED24P	20W	1160	2	3		
	LN-LED30P	23.5W	1345	1	2		

Example: **LN-LED18P-30-WT**



LINE™ LED Undercabinet

Detachable light panel for maintenance

- Energy Star® rated
- Diffused light source reduces glare, eliminates hard shadows
- Asymmetrical forward throw for optimal light distribution
- ELV dimming - see specification sheet for list of tested dimmers

CRI: 90+

ELV Dimming: 100% - 10% (120V only)

100% / 50% high/low settings on board



Rated Life: 80,000 hours

	Length	Watt	Max Lumens	Max Fixture Run		Color Temp	Finish
				60 W	96 W		
	LN-LED06	7.0W	275	8	13	27 2700K 30 3000K	AL Brushed Aluminum
	LN-LED12	12.5W	600	4	7		
	LN-LED18	19.0W	955	3	5		
	LN-LED24	23.0W	1245	2	4		
	LN-LED30	26.0W	1345	2	3		


Example: **LN-LED18-27-AL**

"I" connector included with each luminaire





Class 2 Power Supply for LINE™ and LINE™ 2.0 (Required)

Type		Model	Output	Input	Dim	Dimensions
Remote		EN-2460-RB2-S EN-24100-RB2-S	60W (24V) 96W (24V)	120V	Yes	6½" × 1⅝" × 1¼"
Plug-In		EN-2460-P-AR-S EN-24100-P-AR-S	60W (24V) 96W (24V)	120V	Yes	2¾" × 1⅝" × 1¾" 4⅝" × 2" × 1⅝"






Control Accessory

Touch Panel and Motion Sensor		CT-6A-R2	Includes a Touch Panel, an Occupancy Sensor, and a Controller AC/DC input at 12V(60W Max) or 24V(96W Max) Connect on secondary side of driver/transformer			
-------------------------------	---	-----------------	---	--	--	--

Power Supply Accessories

Wiring Box with On/Off Switch option		TB-S		6¼" × 1⅝" × 1¼"	Use when spanning a large gap in a system layout without leaving exposed wiring (i.e. lighting kitchen cabinets on either side of a sink or window).
Multiple Terminal Block		MTB-08	8 outputs	4⅞" × 1⅝" × ¾"	Easily wire multiple output connections for a neat installation without the use of open splices. One power supply input and 8 outputs. 5A capacity. Three mounting screws included.
12' Extension Cable		SL-EXT-144		Wire: 144" Connector: 1⅝"	Use to extend the distance between power supply or wiring box (TB-S) to a LINE™ section.
Wire Clip (10 Pack)		SL-WC-1		½" × ⅜"	Use to tack power cords or joiner cables neatly to a surface.

Connection Accessories


Joiner Cables		SL-IC-06 SL-IC-12 SL-IC-24 SL-IC-36		6" 12" 24" 36"	Connects two sections of LINE™.
Custom Cable Extenders		SL-IF		Ø3/8" × 3⅝"	Two female ends. Connects two joiner cables to create custom lengths.
4-way "X" Connector		SL-X		Wires: 4" each Connectors: 1⅝" each	"X" connector has four male connectors and can be used to easily customize your design layout.
3-way "Y" Connector		SL-Y		Wires: 4" each Connectors: 1⅝" each	"Y" connector has three male connectors and can be used to easily customize your design layout.
"I" Connector		SL-I		Ø¼" × ⅞"	For end-to-end connection of LINE™ sections.



Minimal space between luminaires

New Brushed Aluminum Finish


Shown: **BA-ACLED12-AL**



Uniform light

Using a 98% efficient reflector, light from the LED sources inside the housing diffuse inside the mixing chamber in order to create evenly distributed illumination. Energy Star® compliant.


- May be hard-wired with 120V power or used with a plug-in power cord
- Subsequent fixtures may be powered with an "I" Connector or Interconnect Cable carrying 120V
- May be individually switched and/or wired to a wall box switch/dimmer



Power Cord

Model	WT	Length
BA-PC6	White	6'
	Black	


Supplies power in any application.



"I" Connector

Model	Max Fixture Run
BA-I-WT	6

Interconnection for seamless end to end transitions. Each light bar includes one.




Interconnect Cable

Model	Length	Max Fixture Run	WT	BK
BA-IC12	12"	4	White	
BA-IC24	24"	4		Black
BA-IC36	36"	3		

Example: **BA-IC12-WT**

Links two light bars using a single power connection.



Light Bars LEDme® Pro

Color Temp: 2700K, 3000K
CRI: 90+
Dimming: 100% – 10% *smooth and continuous ELV dimming*
Rated Life: 90,000 hours

- Uniform Light
- Energy Star® Rated
- CEC Title24 Compliant
- 120VAC - no driver needed
- Diffused light source reduces glare
- 1 inch Profile
- Extruded aluminum construction for optimal thermal management
- Multiple knock outs for ease of wiring
- ELV dimming - see specification sheet for list of tested dimmers

	Model	Length	Watt	Lumens	Color Temp	Finish
	BA-ACLED8	8"	5.5W	255	927 2700K 930 3000K	BZ Bronze AL Brushed Aluminum WT White
	BA-ACLED12	12"	8.0W	365		
	BA-ACLED18	18"	10.0W	450		
	BA-ACLED24	24"	15.0W	705		
	BA-ACLED30	30"	17.0W	785		

Example: **BA-ACLED12-927-WT**



Light Bars LEDme®

Color Temp: 2700K, 3000K
CRI: 85
Dimming: 100% – 10% *smooth and continuous ELV dimming*
Rated Life: 70,000 hours

- Integral drivers
- 1 inch Profile
- Extruded aluminum construction for optimal thermal management
- Multiple knock outs for ease of wiring
- ELV dimming - see specification sheet for list of tested dimmers

	Model	Length	Watt	Lumens	Color Temp	Finish
	BA-LED2	8"	3.5W	150	27 2700K 3000K	BB Bronze SN Satin Nickel WT White
	BA-LED4	12"	6W	285		
	BA-LED6	18"	8.6W	465		
	BA-LED8	24"	10.9W	585		
	BA-LED10	30"	13.4W	695		

Example: **BA-LED4-27-BB** for 2700K
BA-LED4-BB for 3000K

Endurance™

WAC LIGHTING

LED technology offers superior alternatives to conventional Halogen and HID sources. With factory sealed die-cast aluminum housings. Endurance™ provides lasting performance for years.

Patent pending design for a water and dust proof, IP66 rated luminaire. Thermal engineering for up to 100,000 hours of rated life, eliminating the need for maintenance once installed. Thoughtful details include a built-in level and factory sealed light engine.



Energy Star® Rated



Factory-Sealed Fixture Housing
Protects LEDs From
Environmental Factors



Dark Sky Friendly



IP66, WET

IP 66 Rated
Dust Tight, Waterproof



Motion and Photosensor Ready



LED Performs Efficiently
In Cold Weather With Added Lifespan



ETL & cETL Listed



Aluminum

Durable Die-Cast Aluminum



5
Year
Warranty

5 Year WAC Product Warranty


Sensors for Endurance™ Series

	Motion Sensor	MS-120-BZ	Bronze
	(120V)	MS-120-GY	Gray
		MS-120-WT	White


	Photosensor	PC-120-BZ	Bronze
	(120V)	PC-120-GY	Gray
		PC-120-WT	White

Endurance™ Flood

New Graphite Finish



Heavy Duty 1/2" Threaded Mounting Arm




360° Horizontal Rotation
90° Vertical Aiming


CRI: 85
Rated Life: 60,000 hours

- Waterproof breathable technology to maintain stable atmospheric pressure
- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® rated
- Die-Cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- Photo/Motion Sensor Sold Separately - see page 47
- ELV dimming - see specification sheet for list of tested dimmers

1/2" Threaded Heavy Duty Mounting Arm


Also Includes Two Canopy Accessories for use with Surface Mount or Recessed Junction Boxes



		Power	Comparable	Max Delivered Lumens	Color Temp	Finish
	WP-LED335	35W	100W HID	2070	30 3000K	aBZ Architectural Bronze
					50 5000K	aGH Architectural Graphite
						aWT Architectural White


Example: **WP-LED335-30-aBZ**


Endurance™ Single Spot New Product



CRI: 85
Rated Life: 43,000 hours


- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® rated
- Die-Cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- Photo/Motion Sensor Sold Separately - see page 47
- ELV dimming - see specification sheet for list of tested dimmers



		Power	Comparable	Color Temp	Delivered Lumens	Finish
	WP-LED415	15W	75W Halogen	30 3000K	965	aBZ Architectural Bronze
				50 5000K	1030	aGH Architectural Graphite
						aWT Architectural White


Example: **WP-LED415-30-aBZ**


Endurance™ Double Spot New Product



CRI: 85
Rated Life: 43,000 hours

- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® rated
- Die-Cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- Photo/Motion Sensor Sold Separately - see page 47
- ELV dimming - see specification sheet for list of tested dimmers



	Power	Comparable	Color Temp	Delivered Lumens	Finish
	WP-LED430 30W	150W Halogen	30 3000K	965 x2	aBZ Architectural Bronze
			50 5000K	1030 x2	aGH Architectural Graphite
					aWT Architectural White

Example: **WP-LED430-30-aWT**



Endurance™ Fin




3 Outputs
2 Color Temperatures
1 Size

Tempered Prismatic Glass
Reduces glare while optimizing light distribution

CRI: 85
Rated Life: 100,000 hours

- Waterproof breathable technology to maintain stable atmospheric pressure
- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® and DLC rated
- Die-Cast Aluminum Construction
- 20° Forward Throw Illumination
- Built-in Level For Easy Adjustment
- Photo/Motion Sensor Sold Separately
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



	Power	Comparable	Max Delivered Lumens	Color Temp	Finish	
	WP-LED119	19W	39W HID	1460	30 3000K 50 5000K	aBZ Architectural Bronze aGH Architectural Graphite aWT Architectural White
	WP-LED127	27W	70W HID	2135		
	WP-LED135	35W	100W HID	2825		

Example: **WP-LED119-30-aWT**



Endurance™ Hawk

Also Includes a Box Sleeve when used with existing Surface Mount Junction Boxes



Shown with the Box Sleeve over an existing Surface Mount Junction Box



Tempered Prismatic Glass
Reduces glare while optimizing light distribution



Mounts In Any Orientation For Direct and Indirect Illumination




CRI: 85
Rated Life: 100,000 hours

- Waterproof breathable technology to maintain stable atmospheric pressure
- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® and DLC rated
- Die-Cast Aluminum Construction
- 20° Forward Throw Illumination
- Photo/Motion Sensor Sold Separately
- Built-in Level For Easy Adjustment
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers

Also Includes a Box Sleeve when used with existing Surface Mount Junction Boxes



		Power	Comparable	Max Delivered Lumens	Color Temp	Finish	
	WP-LED219	19W	39W HID	1435	30	3000K	aBZ Architectural Bronze
	WP-LED227	27W	70W HID	2095	50	5000K	aGH Architectural Graphite
							aWT Architectural White


Example: **WP-LED219-30-aBZ**




Tube Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours




- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- ADA Compliant
- Mounts up or down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W2609



WS-W2610

Distribution		Beam	Voltage	Watt	Lumens	Finish	
	Single Light	WS-W2609 Dark Sky Friendly Energy Star®	70°	120V - 277V	16W	825	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
	Double Light	WS-W2610	70°	120V - 277V	30W	1525	


Example: **WS-W2609-WT**




Tube Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours




- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- Mounts up or down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers




WS-W2605



WS-W2604

Distribution	Beam	Voltage	Watt	Lumens	Finish
 Single Light WS-W2605 <i>Dark Sky Friendly</i> <i>Energy Star®</i>	33°	120V - 277V	16W	800	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White 
 Double Light WS-W2604	33°	120V - 277V	30W	1750	


Example: **WS-W2604-BZ**



Tube Ceiling Mount




Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- CEC Title 24 Compliant
- Ceiling Mount
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



FM-W2612

FM-W2605

	Distribution		Beam	Voltage	Watt	Lumens	Finish
	Down	FM-W2612	91°	120V - 277V	30W	1740	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
	Down	FM-W2605	33°	120V - 277V	16W	800	


Example: **FM-W2612-GH**




Tube Pendant Mount


Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- CEC Title 24 Compliant
- Die-Cast Aluminum Construction
- Hang Straight Swivel
- Three 12" and one 6" down rods included
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



Distribution	Beam	Voltage	Watt	Lumens	Finish
 Down	33°	120V - 277V	16W	800	AL Brushed Aluminum
					BK Black
					BZ Bronze
					GH Graphite
					WT White


Example: **PD-W2605-BK**




Scoop Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours


- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- Mounts Up or Down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- ADA Compliant
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W20506

Distribution	Beam	Voltage	Watt	Lumens	Finish
 Single Light	86°	120V - 277V	16W	805	AL Brushed Aluminum
					BK Black
					BZ Bronze
					GH Graphite
					WT White


Example: **WS-W20506-BZ**




Rubix Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours



- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- ADA Compliant
- Mounts Up or Down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W2509



WS-W2510

Distribution	Beam	Voltage	Watt	Lumens	Finish
 Single Light	WS-W2509 Dark Sky Friendly Energy Star®	86°	120V - 277V	16W	805
 Double Light	WS-W2510	86°	120V - 277V	30W	1385
					AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White




Example: **WS-W2510-GH**





Rubix Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- Mounts up or down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W2504, WS-W2505

Distribution		Beam	Voltage	Watt	Lumens	Finish
 <i>Single Light</i>	WS-W2504 <i>Dark Sky Friendly Energy Star®</i>	86°	120V - 277V	16W	750	AL <i>Brushed Aluminum</i> BK <i>Black</i> BZ <i>Bronze</i> GH <i>Graphite</i> WT <i>White</i>
 <i>Double Light</i>	WS-W2505	86°	120V - 277V	30W	1400	


Example: **WS-W2504-GH**



Rubix Ceiling Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- CEC Title 24 Compliant
- Ceiling Mount
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



	Distribution	Beam	Voltage	Watt	Lumens	Finish	
	Down	FM-W2505	86°	120V - 277V	16W	750	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
	Down	FM-W2510	95°	120V - 277V	30W	1875	

Example: **FM-W2510-WT**



New 4 inch model and 6 inch 4000K Color Temperature

Disc LED Ceiling and Wall

Dimming: 100% - 10%
Rated Life: 35,000 hours

- Energy Star® rated
- Wet Location Listed
- CEC Title 24 Compliant
- ADA compliant
- Wall or Ceiling Mount
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers



Install over a junction box



Retrofit over a 4", 5" or 6" recessed can

	Watt	Color Temp	CRI	LED Lumens	Delivered Lumens	Finish
FM-304	12W	930 3000K	90	670	570	BN Brushed nickel BZ Bronze WT White
FM-306	15W	930 3000K	90	1110	865	
		940 4000K	90	1165	905	








Example: **FM-306-930-WT**



Flo LED Ceiling and Wall New Product

CRI: 85
Dimming: 100% - 10%
Rated Life: 35,000 hours

- Energy Star® rated
- Wall or Ceiling Mount, closet rated
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers

				Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
		WS-224 24"	20.5W	27 2700K	1670	1190	WT White 	
				35 3500K	1870	1340		
		WS-236 36"	31W	27 2700K	2570	1785		
				35 3500K	2865	2005		
		WS-248 48"	40.5W	27 2700K	3280	2325		
				35 3500K	3555	2685		








Example: **WS-236-35-WT**



Glo LED Ceiling and Wall

CRI: 85
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Energy Star® rated
- ADA compliant for FM-211 and FM-214
- Wall or Ceiling Mount
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers

				Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
		FM-211	11"	15W	27 2700K 35 3500K	1355 1465	1015 1100	WT White 
		FM-214	14"	24W	27 2700K 35 3500K	1915 2175	1435 1630	
		FM-216	16"	33.5W	27 2700K 35 3500K	2815 3015	2110 2260	

Example: **FM-214-35-WT**








Blo LED Ceiling and Wall

New Product

CRI: 85
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Energy Star® rated
- ADA compliant
- Wall or Ceiling Mount
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers

			Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
		FM-113	13" 22W	27 2700K	1695	1395	WT White 
				35 3500K	1770	1510	
		FM-115	15" 33W	27 2700K	2475	2060	
				35 3500K	2595	2150	



Example: **FM-115-35-WT**



Vector Fixed Rail

Color Temp: 3000K
CRI: 90
Rated Life: 60,000 hours

- Energy Star® rated
- Individually Adjustable Heads
- ETL & cETL Damp Location Listed
- Wall or Ceiling Mount
- Aluminum Construction
- Universal Voltage Input (120V - 277V)
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 0-10V and ELV dimming - see specification sheet for list of tested dimmers



Brushed Nickel

Brushed Brass

Chrome

		Watt	LED Lumens	Delivered Lumens	Finish
	TK-49534	33W	1500	1465	BN Brushed Nickel BR Brushed Brass CH Chrome

Example: **TK-49534-CH**





Vector Monopoint

Color Temp: 3000K
 CRI: 90
 Rated Life: 60,000 hours

- Energy Star® rated
- Adjustable Head
- ETL & cETL Damp Location Listed
- Wall or Ceiling Mount
- Aluminum Construction
- Universal Voltage Input (120V - 277V)
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 0-10V and ELV dimming - see specification sheet for list of tested dimmers



		Watt	LED Lumens	Delivered Lumens	Finish	
	MO-495	9W	441	438	BN <i>Brushed Nickel</i> BR <i>Brushed Brass</i> CH <i>Chrome</i>	


Example: **MO-495-BR**



Monterrey Fixed Rail

Color Temp: 3000K
CRI: 90
Rated Life: 60,000 hours

- Individually Adjustable Heads
- CEC Title 24 Compliant
- ETL & cETL Damp Location Listed
- Wall or Ceiling Mount
- Universal Voltage Input (120V - 277V)
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 0-10V and ELV dimming - see specification sheet for list of tested dimmers





Antique Bronze

Antique Nickel

Burnished Brass

Polished Nickel

		Watt	LED Lumens	Delivered Lumens	Finish
	TK-48536	33W	1972	1905	AB <i>Antique Bronze</i> AN <i>Antique Nickel</i> BB <i>Burnished Brass</i> PN <i>Polished Nickel</i>



Example: **TK-48536-AB**






Sublime LED Pendants

Color Temp: 3500K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 55,000 hours

- Hand cut clear crystal
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- 10' of wire included
- 3-12" and 1-6" downrods included
- Hang straight swivel
- Driver located in canopy
- Universal driver (120V-220V-277V)





			Watt	LED Lumens	Delivered Lumens	Finish
	8"	PD-88608	11W	690	546	PN Polished Nickel 
	6"	PD-93611	11W	690	546	

Example: **PD-88608-PN / PD-93611-PN**

dweLED

by WAC Lighting

[dweL-E-D]

LED technology becomes accessible for decorative luminaires, with transitional styling and 2700K warm white light for even the most demanding applications.

dweLED decorative LED luminaires are designed to integrate within a variety of spaces ranging from multi-family residential to commercial and healthcare. Options include ADA compliance, ELV dimming, 277 volt power, wet location, and a variety of sizes and finishes.

The dweLED collection incorporates indoor and outdoor sconces, vanities, swing-arm reading lights, ceiling-mount lights, picture lights, and chandeliers, all engineered optimally for energy efficient LEDs.

Consult the factory to take advantage of our custom capabilities in large quantities.



Slice	75	Aviator	100
Dice	77, 87	Prohibition	101
Niveous	79, 119	Empire	102
Compass	80, 88, 129	Delano	103
Level	81, 113	Corbusier	105
Brink	82, 114	Float	106
Bliss	83, 107	Coco	108
Rondelle	84	Bric	109
Soho	85	Blok	110
Greta	89	Mythical	111
Elementum	90, 117	Laced	115
Kube	91	Mod	120
Ashton	93	Funnel	121
Dunhill	94, 104	Zulu	123
Roswell	95	Folsom	124
Palais	97	Arch	125
Havana	98	Steampunk	127
Moderne	99	Flip	131
















Slice LED Ceiling and Wall

CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Etched 3/4" thick pressed glass diffuser with interior ceramic glaze
- Mount as a ceiling fixture or wall sconce
- ADA compliant when mounted on wall
- FM-4115 is IP44
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- Transformer located in J box
- 277V available (special order)





		Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
	FM-4114-27	2700K	31W	1323	595	BN <i>Brushed Nickel</i> 
	FM-4114-30	3000K	31W	1356	670	
	FM-4109-27	2700K	27W	1356	750	
	FM-4109-30	3000K	27W	1392	770	
	FM-4111-27	2700K	31W	1593	915	BN <i>Brushed Nickel</i>  BZ <i>Bronze</i>  CH <i>Chrome</i> 
	FM-4111-30	3000K	31W	1635	940	
	FM-4115-27	2700K	25W	2130	950	
	FM-4115-30	3000K	25W	2355	1050	

Example: **FM-4111-27-BZ**





For 277V special order, add an "F" before the color temperature: **FM-4111F-27-BZ**













Dice LED Ceiling and Wall

CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Etched $\frac{3}{4}$ " thick pressed glass diffuser with interior ceramic glaze
- Mount as a ceiling fixture or wall sconce
- ADA compliant when mounted on wall
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- Transformer located in J box
- 277V available (special order)





		Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
	FM-4014-27	2700K	31W	1323	610	BN <i>Brushed Nickel</i> 
	FM-4014-30	3000K	31W	1356	640	
	FM-4006-27	2700K	17.5W	779	355	BN <i>Brushed Nickel</i> 
	FM-4006-30	3000K	17.5W	800	365	
	FM-4009-27	2700K	27W	1341	885	BZ <i>Bronze</i>  CH <i>Chrome</i> 
	FM-4009-30	3000K	27W	1376	910	
	FM-4012-27	2700K	25W	1990	890	BZ <i>Bronze</i>  CH <i>Chrome</i> 
	FM-4012-30	3000K	25W	2200	985	

Example: **FM-4009-30-CH**

For 277V special order, add an "F" before the color temperature: **FM-4009F-30-CH**







Niveous LED Ceiling and Wall

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ETL & cETL Wet location, IP65 rated

- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	6"	FM-W52306	9.5W	800	680	WT White 
	9"	FM-W52309	18W	1600	1428	

Example: **FM-W52306-WT**

For 277V, add an "F" before the finish: **FM-W52306F-WT**




Compass LED Indoor/Outdoor Ceiling & Wall


Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ELV dimming - see specification sheet for list of tested dimmers





- ADA compliant, low profile design
- ETL & cETL wet location listed, IP65
- Also rated for installation in closets
- No transformer or driver required
- 277V available (special order)



33612



33616

			Watt	LED Lumens	Delivered Lumens	Finish
	12"	FM-W33612	19W	1647	1147	AL Brushed Aluminum  BZ Bronze 
	16"	FM-W33616	35W	3112	1668	

Example: **FM-W33616-AL**

For 277V, add an "F" before the finish: **FM-W33612F-AL**










Level LED Vanities & Sconces

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Acrylic lens
- CEC Title 24 compliant
- Vertical or horizontal mount
- Adjustable backplate
- ETL & cETL damp location listed
- WS-85618 is ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	19"	WS-85618	15.5W	1300	865	AL Brushed Aluminum 
	25"	WS-85624	20.5W	1735	1255	
	37"	WS-85636	30W	2561	1800	


Example: **WS-85618-AL**







Brink LED Vanities & Sconces:

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Adjustable backplate
- Co-extruded clear and white acrylic provides substance, luminosity and optical efficacy
- Vertical or horizontal mount
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



				Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-77618	15.5W	1300	1095		
	24"	WS-77624	20.5W	1735	1460	AL Brushed Aluminum 	
	36"	WS-77636	30W	2561	2130		

Example: **WS-77618-AL**







Bliss LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- White mitered glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-79622	25W	2390	1646	PN Polished Nickel 
	2 Lights	WS-79636	38.5W	3472	2540	

Example: **WS-79622-PN**




For 277V special order, add an "F" before the finish: **WS-79636F-PN**







Rondelle LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 60,000 hours

- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in J box
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-42505	8.5W	230	220	
	2 Lights	WS-42514	16W	518	490	PN Polished Nickel 
	3 Lights	WS-42524	24.5W	865	805	

Example: **WS-42524-PN**


For 277V special order, add an "F" before the finish: **WS-42524F-PN**







Soho LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant
- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4 inch Jbox included
- Transformer located in J box
- 277V available (special order)





			Watt	LED Lumens	Delivered Lumens	Finish
	11"	WS-6111	16W	700	520	
	17"	WS-6117	25W	1170	860	BN <i>Brushed Nickel</i> CH <i>Chrome</i> GL <i>Gold Plated</i> 
	23"	WS-6123	33.5W	1597	1245	

Example: **WS-6117-GL**

For 277V special order, add an "F" before the finish: **WS-6117F-GL**
 For alternate color temperature, special order adding -30 or -35: **WS-6117-30-GL**





Dice LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- No transformer or driver required



			Watt	LED Lumens	Delivered Lumens	Finish
	2 Light	WS-20624	24W	1972	1247	
	3 Lights	WS-20635	36W	2898	1672	BN Brushed Nickel 
	4 Lights	WS-20646	48W	3850	2507	

Example: **WS-20624-BN**








Compass LED Vanities & Sconces

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 45,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-21611	12W	900	495	
	2 Lights	WS-21622	24W	1840	1055	AL Brushed Aluminum 
	3 Lights	WS-21633	35.5W	2665	1675	

Example: **WS-21622-AL**






Greta LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 40,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed

- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver needed



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-82609	10W	679	505	
	2 Lights	WS-82620	20W	1450	970	SN <i>Satin Nickel</i> 
	3 Lights	WS-82631	30.5W	2049	1386	




Example: **WS-82609-SN**







Elementum LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours

- Mouth blown etched opal glass
- Luminaire may be rotated 180° when mounting
- Up & down light
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



		Watt	LED Lumens	Delivered Lumens	Finish
	1 Light WS-76608	8W	468	422	
	2 Lights WS-76612	15W	949	804	SN <i>Satin Nickel</i> 
	3 Lights WS-76622	22W	1335	1110	

Example: **WS-76622-SN**




Kube LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 60,000 hours

- Each light also contains a powerful downlight
- ETL & cETL damp location listed
- ADA compliant for WS-44505
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 277V available for WS-44505 and WS-44512 (special order)
- WS-44522 has Universal Voltage Input (120V-277V)



44505



44512





44522



		Watt	LED Lumens	Delivered Lumens	Finish
	1 Light WS-44505	18W	675	605	
	2 Lights WS-44512	32W	1554	1355	CH Chrome 
	3 Lights WS-44522 (120V-277V Input)	47.5W	2346	2210	

Example: **WS-44505-CH**

For 277V special order, add an "F" before the finish: **WS-44505F-CH**



Ashton LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL Wet Location listed
- ADA compliant
- Transformer located in J box

- ELV dimming - see specification sheet for list of tested dimmers
- WS-39513 emits downlight as well as ambient light
- 277V available (special order)

			Watt	LED Lumens	Delivered Lumens	Finish
	13"	WS-39513	25.5W	1093	770	
	22"	WS-39522	30W	1373	990	
	28"	WS-39528	41W	1512	1320	
						AB Antique Bronze AN Antique Nickel BB Burnished Brass PN Polished Nickel 

Example: **WS-39513-BB**

For 277V special order, add an "F" before the finish: **WS-39513F-BB**
 For alternate color temperature, special order adding -30 or -35: **WS-39513-35-BB**






Dunhill LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant
- Conversion plate included


- ELV dimming - see specification sheet for list of tested dimmers
- Transformer located in J box
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	20"	WS-40520	27W	1125	770	
	26"	WS-40526	33.5W	1551	935	
	38"	WS-40538	50W	2437	1330	
						AB <i>Antique Bronze</i> AN <i>Antique Nickel</i> BB <i>Burnished Brass</i> PN <i>Polished Nickel</i> 

Example: **WS-40520-PN**




For 277V special order, add an "F" before the finish: **WS-40520F-PN**
 For alternate color temperature, special order adding -30 or -35: **WS-40520-30-PN**







Roswell LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- Luminaire may be rotated 180° when mounting
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)





			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-84611	8.5W	400	355	
	2 Lights	WS-84616	16W	930	815	NR Natural Iron 
	3 Lights	WS-84624	23W	1385	1180	

Example: **WS-84611-NR**






Palais LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-49618	11W	708	424	SN Satin Nickel 

Example: **WS-49618-SN**






Havana LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	17"	WS-47617	16W	967	522	SN <i>Satin Nickel</i> 

Example: **WS-47617-SN**






Moderne LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- Driver located in outlet box
- ELV dimming - see specification sheet for list of tested dimmers
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	15"	WS-40615	20W	1482	887	SN Satin Nickel 

Example: **WS-40615-SN**






Aviator LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-43613	16W	1134	761	SN Satin Nickel 

Example: **WS-43613-SN**






Prohibition LED Sconce

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



	Height	Watt	LED Lumens	Delivered Lumens	Finish	
	20"	WS-45620	18W	1377	817	SN Satin Nickel 

Example: **WS-45620-SN**






Empire LED Sconce

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- Driver located in outlet box
- ELV dimming - see specification sheet for list of tested dimmers
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-41618	15.5W	1207	870	SN Satin Nickel 

Example: **WS-41618-SN**






Delano LED Sconce

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 85,000 hours

- White mitered glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-87618	25W	1625	1165	SN Satin Nickel 

Example: **WS-87618-SN**




Dunhill LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours


- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- ADA compliant
- Conversion plate included
- Transformer located in J box
- 277V available (special order)




40520



40526



40538

			Watt	LED Lumens	Delivered Lumens	Finish
	20"	WS-40520	27W	1125	770	
	26"	WS-40526	33.5W	1551	935	
	38"	WS-40538	50W	2437	1330	
						AB <i>Antique Bronze</i> AN <i>Antique Nickel</i> BB <i>Burnished Brass</i> PN <i>Polished Nickel</i>

Example: **WS-40520-PN**


For 277V special order, add an "F" before the finish: **WS-40520F-PN**
 For alternate color temperature, special order adding -30 or -35: **WS-40520-30-PN**





Corbusier LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Super white mitered ceramic glazed glass
- CEC Title 24 compliance
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	15"	WS-42618	20W	1476	827	SN Satin Nickel 

Example: **WS-42618-SN**




Float LED Sconce


Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 85,000 hours

- No visible mounting hardware
- Super white mitered ceramic glazed glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed




- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



7312



7318

			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-7312	15W	1125	615	BN <i>Brushed Nickel</i> CH <i>Chrome</i> 
	18"	WS-7318	20.5W	1555	890	

Example: **WS-7318-BN**







Bliss LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- White mitered glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-79622	25W	2390	1646	PN Polished Nickel 
	2 Lights	WS-79636	38.5W	3472	2540	

Example: **WS-79622-PN**

For 277V special order, add an "F" before the finish: **WS-79636F-PN**






Coco LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours


- Mouth blown etched opal glass
- CEC Title 24 compliant
- ELV dimming - see specification sheet for list of tested dimmers

- ETL & cETL damp location listed
- Driver located in outlet box
- Universal driver (120V-220V-277V)



	Height	Watt	LED Lumens	Delivered Lumens	Finish
	10"	WS-46609 21W	1377	873	SN <i>Satin Nickel</i> 

Example: **WS-46609-SN**




New Brushed Bronze Finish


Bric LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Sconce may be rotated 180° when mounting
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- CEĈ Title 24 compliant

- Mounts on a 4" x 2" horizontal switch box
- Conversion plate for 4" J box included
- Replaceable LED module
- Approved wiring compartment is also within fixture



			Watt	LED Lumens	Delivered Lumens	Finish
	7"	WS-11807	9W	800	660	BN <i>Brushed Nickel</i> WT <i>White</i> BO <i>Brushed Bronze</i>

Example: **WS-11807-BO**





Blok LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours

- Up & down light
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers

- Driver located inside the fixture
- Universal driver (120V-220V-277V)
- Emergency battery back up option (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-25612	29W	1479	1162	SN Satin Nickel WT Textured White

Example: **WS-25612-SN**

For emergency battery, add -EM after the finish: **WS-25612-SN-EM**






Mythical LED Sconce

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 80,000 hours




- Clear seeded glass
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers

- Up & down light
- CEC Title 24 compliant
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-12712	16W	772	559	PN Polished Nickel 

Example: **WS-12712-PN**







Mythical LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Clear seeded glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- No driver or transformer needed
- 277V available (special order)

		Height		Watt	LED Lumens	Delivered Lumens	Finish
	Small	13"	WS-12713	5.5W	415	70	PN Polished Nickel 
	Medium	18"	WS-12718	10.5W	830	140	
	Large	24"	WS-12724	10.5W	830	160	

Example: **WS-12718-PN**
 For 277V, add an "F" before the finish: **WS-12718F-PN**










Level LED Vanities & Sconces

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Acrylic lens
- CEC Title 24 compliant
- Vertical or horizontal mount
- Adjustable backplate
- ETL & cETL damp location listed
- WS-85618 is ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	19"	WS-85618	15.5W	1300	865	AL Brushed Aluminum 
	25"	WS-85624	20.5W	1735	1255	
	37"	WS-85636	30W	2561	1800	


Example: **WS-85618-AL**







Brink LED Vanities & Sconces

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Adjustable backplate
- Co-extruded clear and white acrylic provides substance, luminosity and optical efficacy.
- Vertical or horizontal mount
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-77618	15.5W	1300	1095	
	24"	WS-77624	20.5W	1735	1460	AL Brushed Aluminum 
	36"	WS-77636	30W	2561	2130	


Example: **WS-77618-AL**






Laced LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 65,000 hours




- Mouth blown etched opal glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)





			Watt	LED Lumens	Delivered Lumens	Finish
	21"	WS-32621	15.5W	1030	557	BN <i>Brushed Nickel</i> 

Example: **WS-32621-BN**





Elementum LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours


- Mouth blown etched opal glass
- Luminaire may be rotated 180° when mounting
- ETL & cETL damp location listed
- Up & down light

- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)

		Watt	LED Lumens	Delivered Lumens	Finish
	1 Light WS-76608	8W	468	422	
	2 Lights WS-76612	15W	949	804	SN <i>Satin Nickel</i> 
	3 Lights WS-76622	22W	1335	1110	

Example: **WS-76622-SN**





Elementum LED Pendant

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 65,000 hours

- Mouth blown etched opal glass
- Twist lock glass attachment
- CEC Title 24 compliant
- ETL & cETL damp location listed
- Universal driver (120V-220V-277V)
- Driver located in outlet box

- ELV dimming - see specification sheet for list of tested dimmers
- Hang straight swivel
- 10' of wire included
- 1-6" and 3-12" downrods included

			Watt	LED Lumens	Delivered Lumens	Finish
	11"	PD-26611	15W	1187	858	SN <i>Satin Nickel</i>
	16"	PD-26616	20W	1769	1363	

Example: **PD-26616-SN**




Niveous LED Ceiling and Wall

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ETL & cETL Wet location, IP65 rated

- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	6"	FM-W52306	9.5W	800	680	WT <i>White</i> 
	9"	FM-W52309	18W	1600	1428	

Example: **FM-W52306-WT**

For 277V, add an "F" before the finish: **FM-W52306F-WT**




Mod LED Outdoor Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours

- Diecast aluminum construction
- Dark Sky friendly
- Luminaire may be rotated 180° when mounting
- ETL & cETL wet location listed, IP65

- ADA compliant
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located inside the fixture
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	6"	WS-W65607	16.5W	1165	850	BZ Bronze GH Graphite



Example: **WS-W65607-GH**




Funnel LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 75,000 hours



- Up & down light
- Vertical or horizontal mount (WS-W37617)
- Energy Star® rated
- CEC Title 24 compliant
- ETL & cETL Wet location listed, IP65 rated
- ELV and 0-10V dimming - see specification sheet for list of tested dimmers
- Driver located inside the fixture
- Universal driver (120V-220V-277V)





			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-W37612	21W	1546	997	BZ Bronze 
	17"	WS-W37617	21W	1546	960	

Example: **WS-W37617-BZ**




Zulu LED Outdoor Sconce

Color Temp: 3000K
CRI: 90
Dimming: 90% - 10%
Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL wet location listed, IP65
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required
- 277V available (special order)

			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-W67612	12W	875	336	BZ Bronze TT Texture Titanium <div style="display: flex; align-items: center; margin-top: 5px;"> <div style="width: 20px; height: 10px; background-color: #444; margin-right: 5px;"></div> <div style="width: 20px; height: 10px; background-color: #888; margin-right: 5px;"></div> </div>
	16"	WS-W67616	18W	1471	579	

Example: **WS-W67612-BZ**



For 277V, add an "F" before the finish: **WS-W67612F-BZ**





Folsom LED Outdoor Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- UV rated acrylic, aluminum construction
- Vertical or horizontal mount
- CEC Title 24 compliant
- ETL & cETL Wet Location listed, IP65 rated
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	10"	WS-W23610	6.5W	630	120	BZ Bronze GH Graphite
	14"	WS-W23614	12W	965	120	

Example: **WS-W23610-GH**


For 277V special order, add an "F" before the finish: **WS-W23610F-GH**



Arch LED Outdoor

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours



- Mounts vertical or horizontal
- ADA compliant
- Die-cast aluminum construction
- ETL & cETL wet location listed, IP65 rated
- ELV dimming - see specification sheet for list of tested dimmers
- 277V available (special order)



26513

26518



			Watt	LED Lumens	Delivered Lumens	Finish
	13"	WS-W26513	5W	154	120	BZ Bronze GH Graphite
	18"	WS-W26518	9.5W	398	225	

Example: **WS-W26518-BZ**


For 277V special order, add an "F" before the finish: **WS-W26518F-BZ**




Steampunk LED Outdoor

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 80,000 hours


- Clear hammered seeded mouth blown glass
- ETL & cETL wet location listed, IP65 rated
- Die-cast Aluminum Construction
- ELV dimming - see specification sheet for list of tested dimmers
- 277V available (special order)




			Watt	LED Lumens	Delivered Lumens	Finish
	9"	WS-W24509	10W	624	365	BZ Bronze GH Graphite
	13"	WS-W24513	10W	657	440	

Example: **WS-W24513-BZ**

For 277V special order, add an "F" before the finish: **WS-W24513F-BZ**




Pivot hinge on canopy allows installation on sloped ceiling



Steampunk LED Outdoor Pendant

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Clear hammered seeded mouth blown glass
- ETL & cETL wet location listed, IP65 rated
- Die-cast Aluminum Construction
- ELV dimming - see specification sheet for list of tested dimmers
- 277V available (special order)

		Watt	LED Lumens	Delivered Lumens	Finish
	13" PD-W24513	10W	750	470	BZ Bronze GH Graphite

Example: **PD-W24513-GH**

For 277V special order, add an "F" before the finish: **PD-W24513F-GH**




Compass LED Indoor/Outdoor Pendant



Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 35,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- 1-6" and 3-12" downrods included
- 10' of wire included
- Hang straight swivel

- ETL & cETL Wet location listed, IP65 rated
- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required
- 277V available (special order)



Watt	LED Lumens	Delivered Lumens	Finish
------	------------	------------------	--------

	20"	PD-W33620	35W	3200	1890	AL Brushed Aluminum BZ Bronze	
---	-----	------------------	-----	------	------	--	---

Example: **PD-W33620-AL**


For 277V, add an "F" before the finish: **PD-W33620F-AL**







Compass LED Indoor/Outdoor Ceiling & Wall

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours


- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ELV dimming - see specification sheet for list of tested dimmers
- ADA compliant, low profile design
- ETL & cETL wet location listed, IP65
- Also rated for installation in closets
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	FM-W33612	19W	1647	1147	AL Brushed Aluminum  BZ Bronze 
	16"	FM-W33616	35W	3112	1668	

Example: **FM-W33616-AL**

For 277V, add an "F" before the finish: **FM-W33612F-AL**



Flip LED Floor

Color Temp: 3000K

CRI: 85

Dimming: 100% - 10% (Integral dimmer)

Rated Life: 70,000 hours

- Fingertip touch dimmer
- Smooth arm swivel
- ETL & cETL damp location listed
- Driver located at the plug

	Watt	LED Lumens	Delivered Lumens	Finish
FL-1350	8W	490	430	BZ <i>Bronze</i> TT <i>Titanium</i>

Example: **FL-1350-BZ**



Flip LED Task


Color Temp: 3000K

CRI: 85

Dimming: 100% - 10% (Integral dimmer)

Rated Life: 70,000 hours

- Fingertip touch dimmer
- Smooth arm swivel
- ETL & cETL damp location listed
- Driver located at the plug



	Watt	LED Lumens	Delivered Lumens	Finish
TL-1310	8W	490	430	BZ Bronze TT Titanium

Example: **TL-1310-BZ**

WAC LIGHTING
Responsible Lighting®