



Shown actual size: Skylark dimmer and 1-gang Claro wallplate in White (WH).

Product family features

- Rocker switch returns light to your favorite light level
- Slide up to brighten, down to dim (adjust light to suit any activity)
- **eco-dim®** model available
- 1000 W preset dimmers have voltage compensation which maintains stable light levels, despite line voltage variations
- 100% factory tested
- Coordinating Claro® and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates, see pg. 155

Control types

 Single-pole (one location)

 3-way or 4-way (two or more locations)

Direct load type compatibility

-  Incandescent/halogen lighting
-  Magnetic low-voltage lighting
-  Electronic low-voltage lighting
-  Fluorescent lighting
-  LED lighting
-  Dimmable compact fluorescent
-  Ceiling fans
-  Ceiling fan/lights

Load type requiring load interface

 Neon/cold cathode lighting

Lighting load interfaces may be applicable for some additional load type, voltage and capacity combinations.

For additional information, see pg. 174.

Available finishes

Use **BOLD** color code in model number (Example: S-600P-**GR**)

Gloss finishes*



WH
White



LA
Light Almond



AL
Almond



IV
Ivory



GR
Gray



BR
Brown



BL
Black



SS
Stainless Steel

*Coordinating wallplates only available separately. For wallplate information, see pg. 160.

Stainless Steel wallplate includes black plastic trim/adaptor, visible from side. Match with separate Black (BL) controls.

Dimmers

Slide-to-off dimmers



- Slide up to on/brighten; down to dim/off

Dimmers with on/off switch and locator light



- Rocker switch turns on/off
- Slide up to brighten; down to dim
- Includes amber locator light

Dimmers with on/off switch



- Rocker switch turns on/off
- Slide up to brighten; down to dim
- **eco-dim®** model guarantees at least 15% energy savings compared to a standard switch

Fan and fan/light controls

Slide-to-off fan controls



- Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to prevent motor hum
- Fully variable model also available

Dual devices

Dual slide-to-off dimmers (two loads)



Dimmers (left/right)

- Slide up to on/brighten; down to dim/off

Slide-to-off fan controls with on/off light switch



Fan control (top)

- Slide up to on/increase fan speed; down to decrease fan speed/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to prevent motor hum

Switch (bottom)

- Rocker switch turns light on/off

Dual slide-to-off fan control and dimmer



Fan control (left)


- Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- Quiet 3-speed designed to prevent motor hum
- Fully variable available for use with multiple paddle or exhaust fans

Dimmer (right)

- Slide up to on/brighten; down to dim/off



Connections overview

Load connections*



Control types (for 2 or more locations)

Dim from one location, switch from the others



For more information on ballasts, visit www.lutron.com/ballasts.

For more information on LED drivers, visit www.lutron.com/LED.

***For illustration purposes only.** Consult model number pages for specific voltage and capacity information.

Dimmer model numbers



Incandescent/halogen dimmers

Dimmers with on/off switch

Single-pole 120V 600W	S-600P- CC ³
Single-pole 120V 1000W	S-10P- CC ³
3-way 120V 600W	S-603P- CC ³
3-way 120V 1000W	S-103P- CC ³

eco-dim® dimmer with on/off switch

3-way/single-pole 120V 600W	S-603PG- EE ²
--------------------------------	---------------------------------

eco-dim model guarantees at least 15% energy savings compared to a standard switch.

Dimmers with on/off switch and locator light

Single-pole 120V 600W	S-600PNL- CC ³
Single-pole 120V 1000W	S-10PNL- CC ³
3-way 120V 600W	S-603PNL- CC ³
3-way 120V 1000W	S-103PNL- CC ³

Slide-to-off dimmers

Single-pole 120V 600W	S-600- CC ³
Single-pole 120V 1000W	S-1000- CC ³

For dual slide-to-off dimmers (two loads), see page 111.



Magnetic low-voltage dimmers

Dimmers with on/off switch

Single-pole 120V 600 VA (450W)	SLV-600P- CC ³
3-way 120V 600 VA (450W)	SLV-603P- CC ³

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load. The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.



Electronic low-voltage dimmers*

Dimmers with on/off switch

Single-pole 120V 300W	SELV-300P- CC ³
3-way 120V 300W	SELV-303P- CC ³

Certain LED drivers are dimmable using an ELV dimmer, for more information, visit www.lutron.com/LED.

CC³: Gloss color codes, see pg. 105

EE²: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA) (Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

*Requires neutral wire connection.

Dimmer model numbers

3-wire fluorescent dimmers*

Dimmers with on/off switch

Single-pole 120V 8A	SF-10P- CC ³
Single-pole 277V 6A	SF-12P-277- CC ³
3-way 120V 8A	SF-103P- CC ³
3-way 277V 6A	SF-12P-277-3- CC ³

For use with Hi-lume®, Hi-lume® Compact SE, Hi-lume® 3D, Eco-10®, EcoSystem® ballasts.

No derating required if ganged.

Adjustable low-end trim.

Hi-lume® LED drivers: 3-wire fluorescent dimmers*

Dimmers with on/off switch

Single-pole 120V 8A	SF-10P- CC ³
Single-pole 277V 6A	SF-12P-277- CC ³
3-way 120V 8A	SF-103P- CC ³
3-way 277V 6A	SF-12P-277-3- CC ³

For use with Hi-lume LED driver only.

For more information on Hi-lume LED drivers, visit www.lutron.com/HilumeLED.

No derating required if ganged.

Adjustable low-end trim.

Tu-Wire® fluorescent dimmers

Dimmers with on/off switch

3-way/single-pole 120V 5A	SFTU-5A3P- CC ³
------------------------------	-----------------------------------

Also compatible with Advance Mark X ballasts, for further information, visit www.lutron.com/advance.

For information on use with Universal and OSRAM ballasts, contact Technical Support at 1.800.523.9466.

CC³: Gloss color codes, see pg. 105
(Wallplates not included, order separately, see pg. 160)

For more information on ballasts, visit www.lutron.com/ballasts.

All models must be derated if ganged unless otherwise noted, see pg. 170.

*Requires neutral wire connection.

Fan control model numbers

Fan controls

Slide-to-off fan controls—quiet 3-speed

Single-pole	SFSQ-F- CC ³
120V 1.5A	

Single-pole	SFSQ-F-HO- CC ³
120V 2.0A	

For use with only one ceiling paddle fan.

SFSQ-F-HO- for use with Hunter Original Series.

Slide-to-off fan control—fully variable

Single-pole	SFS-5E- CC ³
120V 5A	

For use with multiple ceiling paddle fans or exhaust fans.

Fan/light controls

Fan control—quiet 3-speed and dimmer

Single-pole fan control	S2-LFSQ- CC ³
120V 1.5A (left)	

120V single-pole dimmer 300W (right)

For use with only one ceiling paddle fan.

Fan control—fully variable and dimmer

Single-pole fan control	S2-LF- CC ³
120V 2.5A (left)	

120V single-pole dimmer 300W (right)

For use with multiple ceiling paddle fans.

Fan control/light switch

Fan control—quiet 3-speed and switch

Single-pole fan control	SFSQ-LF- CC ³
120V 1.5A (top)	

120V single-pole switch 360W (bottom) (incandescent/halogen loads only)
--

CC³: Gloss color codes, see pg. 105
(Wallplates not included, order separately,
see pg. 160)

All models must be derated if ganged unless
otherwise noted, see pg. 170.

***Requires neutral wire connection.**

Dual device model numbers

 Incandescent/halogen and
Incandescent/halogen dimmers

Dual slide-to-off dimmers (two loads)

Single-pole	S2-L- CC ³
120 V 300 W light (left) incandescent/halogen	
120 V 300 W light (right) incandescent/halogen	

Replacement knob model numbers

 Knobs

Single-pole	SK- EE ²
Standard knob	
Split knobs	contact customer service

CC³: Gloss color codes, see pg. 105
(Wallplates not included, order separately,
see pg. 160)
EE²: Available in White (WH), Ivory (IV),
Almond (AL) and Light Almond (LA)

All models must be derated if ganged unless
otherwise noted, see pg. 170.

Accessories

Wallplates



Shown actual size:
2-gang Claro® wallplate
in White (WH).

For more information
about Designer wallplates,
see pg. 160.

Coordinated electrical devices



Tamper resistant
GFCI receptacle




Customizable
6-port frame



Cable jack

For more information
about coordinated
Designer electrical
devices, see pg. 163.



Shown actual size:
Maestro dimmers
and 2-gang Claro
wallplate in White (WH).

Product family features

- Can be used in conjunction with the following dimmer(s) and switch(es): Maestro®, Maestro IR®, Maestro Wireless®, Pico™ wireless control, Spacer System®, Diva®, Lyneo® Lx, Skylark®, Skylark Contour™
- All Lutron® wallplates are screwless, seamless and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- Full line of wiring devices in designer style opening
- Blank inserts available for Gloss colors (DV-BI-) and Satin colors (SC-BI-)
- Customize your designer wallplate with engraving, contact customer service to get started at 1.888.LUTRON1


Ganging and derating

- Designer wallplates use standard ganging
- Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging), see pg. 170
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pg. 172

Available finishes

Use **BOLD** color code in model number (Example: SC-1-**PL**)

Gloss finishes



Satin finishes



*Stainless Steel finish wallplates include black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Wallplates for Maestro®, Maestro IR®, Maestro Wireless®, Pico™ wireless control, Spacer System®, Diva®, Lyneo® Lx, Skylark® and Skylark Contour™



1-gang*

CW-1-**CC**²
SC-1-**CC**⁴


W: 2.94 in (75 mm); H: 4.69 in (119 mm)
D: .30 in (7.6 mm)



4-gang*

CW-4-**CC**²
SC-4-**CC**⁴

W: 8.37 in (213 mm); H: 4.69 in (119 mm);
D: .30 in (7.6 mm)



2-gang*

CW-2-**CC**²
SC-2-**CC**⁴

W: 4.75 in (121 mm); H: 4.69 in (119 mm);
D: .30 in (7.6 mm)



5-gang*

CW-5-**CC**²
SC-5-**CC**⁴

W: 10.18 in (259 mm); H: 4.69 in (119 mm);
D: .30 in (7.6 mm)



3-gang*

CW-3-**CC**²
SC-3-**CC**⁴

W: 6.56 in (167 mm); H: 4.69 in (119 mm);
D: .30 in (7.6 mm)

Multiple devices with line and low-voltage can be mounted behind a common wallplate using a standard barrier backbox, see Application Note #213 (Combining Low-Voltage and Line Voltage Wiring Devices in a Multi-Gang Box) at www.lutron.com/applicationnotes.

CC²: Gloss and Stainless Steel color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

Multi-gang dimmer installations may require derating, see pg. 170.

*Stainless Steel finish wallplates include black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Receptacles



6-gang*

CW-6-**CC**²

SC-6-**CC**⁴

W: 12.00in (305mm); H: 4.69in (119mm);
D: .30in (7.6mm)



Tamper resistant receptacles

15 A, 125V*	CARS-15-TR- CC ³
	SCRS-15-TR- CC ⁴
20 A, 125V*	SCRS-20-TR- CC ⁴

Cable jacks



- F-style, 75-Ohm coaxial cable

Single cable jack*

CA-CJH-**CC**³

SC-CJ-**CC**⁴

Receptacles

15 A, 125V*	CAR-15H- CC ³
	SCR-15- CC ⁴
20 A, 125V*	SCR-20- CC ⁴

GFCI Receptacles



- Press test button to confirm LED indicator status
- Press reset button to reset GFCI after circuit interruption

Telephone jacks



- 6-conductor telephone jack, RJ11

Single telephone jack*

CA-PJH-**CC**³

SC-PJ-**CC**⁴

Tamper resistant GFCI receptacles

15 A, 125V*	GFCI	CAR-15-GFTR- CC ³
		SCR-15-GFTR- CC ⁴
20 A, 125V*	GFCI	SCR-20-GFTR- CC ⁴

CC²: Gloss and Stainless Steel color codes, see pg. 161

CC³: Gloss color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

*Stainless Steel finish only available as separate wallplate. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use

Duplex for dimming use

15 A	120/125 V*	CAR-15-DFDU- CC ²
15 A	120/125 V*	SCR-15-DFDU- CC ⁴
20 A	120/125 V*	CAR-20-DFDU- CC ²
20 A	120/125 V*	SCR-20-DFDU- CC ⁴

Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs

Split duplex (half for dimming use)

15 A	120/125 V*	CAR-15-HFDU- CC ²
15 A	120/125 V*	SCR-15-HFDU- CC ⁴
20 A	120/125 V*	CAR-20-HFDU- CC ²
20 A	120/125 V*	SCR-20-HFDU- CC ⁴

Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use
- 15 A model shown
- Tamper resistant shutter mechanism

Dual dimming tamper resistant

15 A	120/125 V*	CAR-15-DDTR- CC ²
15 A	120/125 V*	SCR-15-DDTR- CC ⁴
20 A	120/125 V*	CAR-20-DDTR- CC ²
20 A	120/125 V*	SCR-20-DDTR- CC ⁴

Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs
- 15 A model shown
- Tamper resistant shutter mechanism

Half dimming tamper resistant

15 A	120/125 V*	CAR-15-HDTR- CC ²
15 A	120/125 V*	SCR-15-HDTR- CC ⁴
20 A	120/125 V*	CAR-20-HDTR- CC ²
20 A	120/125 V*	SCR-20-HDTR- CC ⁴

CC²: Gloss color code and Stainless Steel, see pg. 161

CC⁴: Satin color codes, see pg. 161

*Stainless Steel finish only available as separate wallplate. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Replacement plug for dimming
(use with receptacles on left)



- This plug required for use with Lutron® receptacles for dimming use—plug will work in standard receptacle
- Easily replaces the existing plugs on lamps

120/125 V White	RP-FDU-10-WH
120/125 V Brown	RP-FDU-10-BR

UL/CSA/NOM regulatory approvals.

Important notes

- If the hot and dimmed hot feeds to the split duplex HFDU are supplied from different circuits or split-wired with separate switch-legs, a means to simultaneously disconnect these circuits must be provided at the panel board where they originate (NEC 210.7(C) 2002 Edition). A 2-pole circuit breaker or two single-pole circuit breakers with an approved handle tie can be used to accomplish this simultaneous disconnect. Feed-through dimming panels, which are those without breakers, are recommended when using the HFDU.
- Receptacles and plugs for dimming use are UL listed for use with all Lutron® wallbox dimmers included in this catalog.
- If there is only one electrical feed to the receptacle, then the duplex DFDU must be used.
- For detailed information, see Application Notes #91 (Guide to Dimming Table Lamps) and #109 (Guide to Dimming Portable Lamps via Receptacles) at www.lutron.com/applicationnotes.

CC²: Gloss color code and Stainless Steel, see pg. 161
CC⁴: Satin color codes, see pg. 161

*Stainless Steel finish only available as separate wallplate. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Field customizable 6-port frame



- Shipped with six blanks in matching colors
- Connectors and wallplate sold separately
- Connectors snap in (no tools required)
- Connectors available in White (WH), unless noted

6-port frame*	CA-6PF- CC ³ SC-6PF- CC ⁴
---------------	--

Connectors for 6-port frame

Telephone/network jacks



8-conductor, RJ45 category 3	CON-1P-C3- EE ⁴
---------------------------------	-----------------------------------

8-conductor, RJ45 category 5e	CON-1P-C5E- EE ⁴
----------------------------------	------------------------------------

8-conductor, RJ45 category 6	CON-1P-C6- EE ⁴
---------------------------------	-----------------------------------

Fiber jacks



MT-RJ feed through	CON-1F-MTRJ-WH
--------------------	----------------



SC simplex	CON-1F-SC-WH
------------	--------------



LC non-flush mount	CON-1F-LC-WH
--------------------	--------------



ST style	CON-1F-ST-WH
----------	--------------

Cable jack



F-style, 75-Ohm coaxial cable	CON-1C- EE ⁴
----------------------------------	--------------------------------

BNC jack



BNC connector, 50-Ohm	CON-1B-WH
-----------------------	-----------

Connectors only for use with 6-port frame.

Switches



- Paddle turns on/off
- Use with any 15A load
- General purpose switching of all sources and motor loads
- No derating if ganged

General purpose switches (120/277 V)

Single-pole	15A*	CA-1PSH- CC ³ SC-1PS- CC ⁴
3-way	15A*	CA-3PSH- CC ³ SC-3PS- CC ⁴
4-way	15A*	CA-4PSH- CC ³ SC-4PS- CC ⁴

General purpose switch with locator light (120V only)

Single-pole	15A*	CA-1PSNL- EE ² SC-1PSNL- EE ¹⁰
3-way	15A*	CA-3PSNL- EE ² SC-3PSNL- EE ¹⁰
4-way	15A*	CA-4PSNL- EE ² SC-4PSNL- EE ¹⁰

CC³: Gloss color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

EE²: Only available in Almond (AL), Ivory (IV), Light Almond (LA) and White (WH)

EE⁴: Only available in White (WH) and Black (BL)

EE¹⁰: Available in Biscuit (BI), Eggshell (ES), Goldstone (GS), Limestone (LS), Sea Glass (SG) and Snow (SW)

*Stainless Steel finish only available as separate wallplate. Match with separate Black (BL) or Midnight (MN) controls and accessories.

How to understand ganging and derating

Standard ganging

Ganging is the side-by-side mounting of two or more dimmers or accessory devices under a multi-gang wallplate.

Standard multi-gang installation:

- Uses standard multi-gang electrical backboxes
- Uses standard multi-gang wallplates
- Requires fins to be removed from dimmers for proper spacing (“Fins Broken” ganging)
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pgs. 172–173


Custom ganging for Architectural style controls

For Architectural style dimmers and switches, it is possible to retain the maximum capacity of dimmers in multi-gang applications via custom architectural multi-gang:

- May require customized, wider-than-standard wallplates
- May require wider-than-standard electrical backboxes
- Allows full capacity (“No Fins Broken”) ganging
- Required for Nova® dimmers and for larger width (high capacity) architectural controls
- Visit www.lutron.com/customganging for additional information


Standard ganging for dimmers, switches and accessories

New Architectural




pg. 148

Architectural




pg. 152

Designer




pg. 160


Traditional




pg. 166




Vierti®



Vareo®
Nova T☆®



Maestro®
Maestro IR®
Maestro Wireless®
Spacer System®
Diva®
Lyneo® Lx
Skylark®
Skylark Contour™



Abella®
Ceana®
Ariadni®
Glyder®
Rotary


Derating Table 1
pg. 172

Derating Table 2
pg. 173


Derating Table 1
pg. 172

Derating Table 1
pg. 172

Standard ganging and fins broken derating examples:



Custom Architectural ganging example:



For further information on ganging and derating, visit www.lutron.com/multigang.

*The fins are scored and designed to be removed easily.

Derating Table 1

New Architectural | Verti®

Designer | Maestro®, Maestro IR®, Maestro Wireless®, Spacer System®, Diva®, Lyneo® Lx, Skylark Contour™, Skylark®

Traditional | Abella®, Ceana®, Ariadni®, Glyder®, Rotary



No fins broken



1 fin broken



2 fins broken

Incandescent			
Dimmers	600W	500W	400W
	1000W	800W	650W
Dual dimmers	300W	250W	200W
	300W	250W	200W
Magnetic low-voltage			
Dimmers	600VA/450W	500VA/400W	400VA/300W
	1000VA/800W	800VA/650W	650VA/500W
Electronic low-voltage			
Dimmers	300W	250W	200W
	500W	450W	400W
	600W	500W	400W
Fluorescent			
Hi-lume®/Hi-lume® Compact SE/Eco-10®/EcoSystem®			
Verti	60 ballasts/6 A	50 ballasts/5 A	35 ballasts/3.5 A
Maestro/Spacer System	20 ballasts/6 A	20 ballasts/5 A	20 ballasts/3.5 A
Diva, Skylark, Lyneo Lx and Ariadni	no derating	no derating	no derating
Tu-Wire®: Spacer System, Diva, Skylark	5 A	4 A	3.3 A
Fan controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5 A	1.5 A	1.5 A
Fully variable	5 A	4 A	3 A
Fan/light controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5 A/300W	1.5 A/300W	1.5 A/300W
	1.5 A/360W	1.5 A/360W	1.5 A/360W
Fully variable	2.5 A/300W	2.1 A/250W	1.7 A/200W
Electronic switches			
Verti	6A/3A	5A/3A	3.5A/3A
Maestro (light/fan)	8A/3A	6.5A/3A	5A/3A
Abella (light/fan)	6A/3A	5A/3A	3.5A/3A

Derating Table 2

Architectural | Vareo®, Nova T☆®

	 No fins broken	 1 fin broken	 2 fins broken
Incandescent			
Dimmers	600W	500W	300W
	1000W	900W	700W
	1500W	1250W	1000W
	1950W	—	—
Magnetic low-voltage			
Dimmers	600 VA/450 W	500 VA/400 W	300 VA/250 W
	1000 VA/800 W	900 VA/750 W	700 VA/500 W
	1500 VA/1200 W	1250 VA/1000 W	1000 VA/800 W
Electronic low-voltage			
Dimmers	300W	300W	250W
	600W	500W	400W
Fluorescent			
Hi-lume®/Hi-lume® Compact SE/Eco-10®/EcoSystem®			
Vareo	20 ballasts / 8 A	20 ballasts / 6 A	20 ballasts / 4.5 A
Nova T☆	6 A	no derating	no derating
	8 A	no derating	no derating
	16 A	no derating	no derating
0-10 VDC control ¹	30 mA ballasts	no derating	no derating
Tu-Wire®	5 A	4 A	3.3 A
Fan controls			
Quiet 3-speed	1.5 A	no derating	no derating
Fully variable	6 A	4.2 A	2.5 A
Fully variable	12 A	10 A	8.3 A
Electronic tapswitches²			
VETS-1000-	1000W	800W	650W
VETS-1000-SL-	1000W	900W	700W
VETN-1000-	1000 VA	700 VA	550 VA

For further information on ganging Nova®, visit www.lutron.com/customganging.

¹PowerPack required for line voltage switching.

²VETS-R-Auxiliary electronic tapswitches do not require derating.

Dimmer capabilities and interface requirements

M Multi-location—true dimming from each location

E eco-model available

 Compatible dimmer (no interface)

WBX **TVI** **3F** **PA** Requires interface, see notes below

				
Vierti®* pg. 14	Vareo® pg. 20	Nova T☆® pg. 26	Nova® pg. 34	Centurion® pg. 42
M				
		M		
		M		
	WBX			
	WBX			
	WBX			
	WBX	WBX		
	WBX		WBX	
	WBX		WBX	
	WBX			
	WBX	WBX		
	WBX		WBX	
	WBX	WBX	WBX	
	WBX	WBX		
	3F			
	3F			
	3F			
	3F	3F	3F	
	PA			
TVI	TVI			

WBX: Wallbox Phase Adaptive Power Module (PHPM-WBX-DV-WH)

3F: Fluorescent Power Module (PHPM-3F-DV-WH)

TVI: 0-10V Interface (GRX-TVI)

PA: Phase Adaptive Power Module (PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

*Consult Lutron Technical Support for information on interfaces with Vierti.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

M Multi-location—true dimming from each location

E eco-model available

 Compatible dimmer (no interface)

WBX **TVI** **3F** **PA** Requires interface, see notes below

						
		Maestro® pg. 46	Maestro IR® pg. 60	Maestro Wireless® pg. 68	Spacer System® pg. 76	Diva® pg. 86
Dimmers	capacity†	M	M	M	M	
 Incandescent/halogen 120V	600W	E				E
	1000W					
	1500W	WBX		WBX	WBX	WBX
	2000W	WBX		WBX	WBX	WBX
 Magnetic low-voltage 120V	600 VA (450W)					
	1000 VA (800W)					
	1500 VA (1200W)	WBX		WBX	WBX	WBX
	2000 VA (1600W)	WBX		WBX	WBX	WBX
 Magnetic low-voltage 277V	600 VA (450W)	WBX		WBX	WBX	WBX
	1000 VA (800W)	WBX		WBX	WBX	WBX
 Electronic low-voltage 120V	300W			WBX		
	450W			WBX		WBX
	600W			WBX		WBX
 Electronic low-voltage 277V	16A	WBX		WBX	WBX	WBX
 Neon/cold cathode				WBX		WBX
 3-wire ballasts and Hi-lume® LED driver 120V	6A					
	Hi-lume, Hi-lume Compact SE, Eco-10® and EcoSystem® ballasts	3F		3F	3F	
		3F		3F	3F	3F
 3-wire ballasts and Hi-lume LED driver 277V	6A					
	Hi-lume, Hi-lume Compact SE, Eco-10 and EcoSystem ballasts	3F		3F	3F	3F
		3F		3F	3F	3F
 Tu-Wire® ballasts 120V	5A	PA		PA		
 0-10VDC (ballasts or LED Drivers) 120/277V	16A	TVI		TVI	TVI	TVI

WBX: Wallbox Phase Adaptive Power Module (PHPM-WBX-DV-WH)

3F: Fluorescent Power Module (PHPM-3F-DV-WH)

TVI: 0-10V Interface (GRX-TVI)

PA: Phase Adaptive Power Module (PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

M Multi-location—true dimming from each location

E eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below

					
		Lyneo® Lx pg. 94	Skylark Contour™ pg. 100	Skylark® pg. 104	Abella® pg. 114
Dimmers	capacity†				M
 Incandescent/halogen 120V	600W		E	E	
	1000W				
	1500W	WBX		WBX	
	2000W	WBX		WBX	
 Magnetic low-voltage 120V	600VA (450W)				
	1000VA (800W)			WBX	
	1500VA (1200W)	WBX		WBX	
	2000VA (1600W)	WBX		WBX	
 Magnetic low-voltage 277V	600VA (450W)	WBX		WBX	
	1000VA (800W)	WBX		WBX	
 Electronic low-voltage 120V	300W				
	450W			WBX	
	600W			WBX	
 Electronic low-voltage 277V	16A	WBX		WBX	
 Neon/cold cathode		WBX		WBX	
 3-wire ballasts and Hi-lume® LED driver 120V	6A				
	Hi-lume, Hi-lume Compact SE, Eco-10® and EcoSystem® ballasts				
	8A				
 3-wire ballasts and Hi-lume LED driver 277V	6A				
	Hi-lume, Hi-lume Compact SE, Eco-10 and EcoSystem ballasts				
	8A	3F		3F	
 3-wire ballasts and Hi-lume LED driver 277V	16A	3F		3F	
	16A	3F		3F	
 Tu-Wire® ballasts 120V	5A	PA			
 0-10VDC (ballasts or LED Drivers) 120/277V	16A	TVI		TVI	

WBX: Wallbox Phase Adaptive Power Module (PHPM-WBX-DV-WH)

3F: Fluorescent Power Module (PHPM-3F-DV-WH)

TVI: 0-10V Interface (GRX-TVI)

PA: Phase Adaptive Power Module (PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

- M** Multi-location—true dimming from each location
- E** eco-model available
- Compatible dimmer (no interface)
- WBX** **TVI** **3F** **PA** Requires interface, see notes below

			
Ceana® pg. 120	Ariadni® pg. 124	Glyder® pg. 130	Rotary pg. 134

Dimmers		capacity†				
	Incandescent/halogen 120V	600W	 	E	 	E
		1000W	 		 	
		1500W		WBX		
		2000W		WBX		
	Magnetic low-voltage 120V	600VA (450W)	 	 	 	
		1000VA (800W)		 		
		1500VA (1200W)		WBX		
		2000VA (1600W)		WBX		
	Magnetic low-voltage 277V	600VA (450W)		WBX		
		1000VA (800W)		WBX		
	Electronic low-voltage 120V	300W		WBX		
		450W		WBX		
		600W		WBX		
	Electronic low-voltage 277V	16A		WBX		
	Neon/cold cathode			WBX		
	3-wire ballasts and Hi-lume® LED driver 120V	6A				
		Hi-lume, Hi-lume Compact SE, Eco-10® and EcoSystem® ballasts	8A	 		
			16A	3F		
	3-wire ballasts and Hi-lume LED driver 277V	6A		 		
		Hi-lume, Hi-lume Compact SE, Eco-10 and EcoSystem ballasts	8A	3F		
			16A	3F		
	Tu-Wire® ballasts 120V	5A		PA		
	0-10VDC (ballasts or LED Drivers) 120/277V	16A		TVI		

WBX: Wallbox Phase Adaptive Power Module (PHPM-WBX-DV-WH)

3F: Fluorescent Power Module (PHPM-3F-DV-WH)

TVI: 0-10V Interface (GRX-TVI)

PA: Phase Adaptive Power Module (PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer models/load interface compatibility

	Incandescent, magnetic and electronic low-voltage (120/277 V)		3-wire Fluorescent ballasts or Hi-lume® LED drivers (120/277 V)		0-10VDC Ballasts or LED drivers (120/277 V)	
	WBX 		3F 		TVI 	
	Wallbox Phase Adaptive Power Module* PHPM-WBX-DV-WH		Fluorescent Power Module* PHPM-3F-DV-WH		0-10V Interface GRX-TVI	
Dimmer Family	Single-pole	3-way or multi-location	Single-pole	3-way or multi-location	Single-pole	3-way or multi-location
Abella®	—	—	—	—	—	—
Ariadni®	—	AYF-103P-	—	AYF-103P-	—	AYF-103P-
Ceana®	—	—	—	—	—	—
Diva® Gloss	—	DVF-103P-	—	DVF-103P-	—	DVF-103P-
Diva Satin Colors®	—	DVSCF-103P-	—	DVSCF-103P-	—	DVSCF-103P-
Glyder®	—	—	—	—	—	—
Lyneo® Lx	—	LXF-103PL-	—	LXF-103PL-	—	LXF-103PL-
Maestro® Gloss	—	MAF-6AM-	—	MAF-6AM-	—	MAF-6AM-
Maestro® Satin Colors®	—	MSCF-6AM-	—	MSCF-6AM-	—	MSCF-6AM-
Maestro Wireless®	—	MRF2-F6AN-DV-	—	MRF2-F6AN-DV-	—	MRF2-F6AN-DV-
Nova®	NF-10-	NF-103P-	NF-10-	NF-103P-	NF-10-	NF-103P-
Nova T☆®	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-
Skylark®	SF-10P-	SF-103P-	SF-10P-	SF-103P-	SF-10P-	SF-103P-
Spacer System®	—	SPSF-6AM-	—	SPSF-6AM-	SPSF-S6A-	SPSF-6AM-
Vareo®	—	VF-10-	—	VF-10-	—	VF-10-
Vierti®	contact Lutron		contact Lutron		—	VTF-6AM-

Use only dimmer model numbers listed.

*Dual 120/277 V model given, 120V only versions are also available.
Please see Technical notes, pg. 179.

Dimmer models/load interface compatibility

	Tu-Wire® Fluorescent Ballasts (120V)		Switched Lighting (120/277V)	
	PA 		SW 	
	Phase Adaptive Power Module* PHPM-PA-DV-WH		Switching Power Module* PHPM-SW-DV-WH	
Dimmer Family	Single-pole	3-way or multi-location	Single-pole	3-way or multi-location
Abella®	–	–	–	AB-S6AM-
Ariadni®	–	AYF-103P-	–	–
Ceana®	–	–	–	–
Diva® Gloss	–	DVF-103P-	–	–
Diva Satin Colors®	–	DVSCF-103P-	–	–
Glyder®	–	–	–	–
Lyneo® Lx	–	LXF-103PL-	LX-1PSL-	LX-3PSL-
Maestro® Gloss	–	MAF-6AM-	–	MA-S8AM-
Maestro® Satin Colors®	–	MSCF-6AM-	–	MSC-S8AM-
Maestro Wireless®	–	MRF2-F6AN-DV-	–	MRF2-6ANS-
Nova®	NF-10-	NF-103P-	–	–
Nova T☆®	NTF-10-	NTF-103P-	–	–
Skylark®	SF-10P-	SF-103P-	–	–
Spacer System®	SPSF-S6A-	SPSF-6AM-	SPSF-S6A-	SPSF-S6AM-
Vareo®	–	VF-10-	–	VETN-1000-
Vierti®	contact Lutron		contact Lutron	

Technical notes

- Lighting load interfaces must be matched to load type and voltage
- All load interfaces for dimmed load are controlled by a 120V 3-wire fluorescent dimmer
- Power feed to dimmer may differ from lighting load/interface voltage
- Interfaces typically require additional power feeds
- For wiring information, consult wiring diagrams, see pgs. 193-195
- For assistance and additional solutions, consult Lutron Technical Support at 1.800.523.9466 (24 hours/7 days)


Interface mounting

- PHPM interfaces mount to 2-gang electrical backbox (W: 6.30 in x H: 5.10 in)
- GRX-TVI enclosure is surface mount only (W: 6.10 in x H: 12.50 in x D: 3.30 in)

Use only dimmer model numbers listed.

*Dual 120/277V model given, 120V only versions are also available.
Please see Technical notes, pg. 179.

Skylark Contour™



For illustration purposes only. Consult model number pages for specific voltage and capacity information.