

Guide to Green Lighting

Progress Lighting

For more than 100 years, Progress Lighting has continued to build on its reputation as a leader and trendsetter in residential decorative lighting. While we are focused on the many aspects of “green” lighting, our commitment to consumers, homeowners and homebuilders is to provide products that maximize energy savings without sacrificing aesthetic appeal.

Progress Lighting has responded to the ever-changing needs of the lighting industry with extensive research and development programs that ensure high standards of quality and innovation for green lighting in home applications.

And we’re excited to share our knowledge with you.

Progress Lighting’s *Guide to Green Lighting* offers solutions for light commercial and residential lighting with fixtures in contemporary, modern and classic designs, all of which will lower energy costs and contribute to a healthier environment.

Table of Contents

- Green Lighting Guide 2
- Shared Interior Spaces 11
- Working Interior Spaces 47
- Outdoor and Utility Spaces 61
- Concealed Lighting
for Interior Spaces 75

LEEDing by Example



LEED Headquarters

To solidify our environmental commitment, Progress Lighting (Hubbell Lighting, Inc.) moved into its LEED-certified headquarters in 2007. This building incorporates many forms of energy efficient lighting and controls, as well as daylighting and other energy efficient and sustainable elements.

Lighting Solutions Center

The first floor of the new corporate headquarters is home to the company's unique Lighting Solutions Center. This self-contained 25,000-square-foot space provides real world solutions to the most challenging and timely lighting issues. Additionally, unique teaching tools in the Lighting Solutions Center include a fixture comparison mechanism that directly compares differences in energy usage and cost savings.

Solid State Lighting Lab



What Does Green Mean?

Sustainable or green building design is the dominant subject just about everywhere you turn. Flip through your favorite magazine, watch a popular television program or surf the Internet and you'll see that everyone is "going green."

But what does that mean to you and how can you get started?

Simple changes in home lighting habits are an easy first step, resulting in less greenhouse gas emissions and significant financial savings as well.

For instance:

By replacing standard incandescent fixtures with those using green-friendly compact fluorescent bulbs, over the long run a household can save an estimated \$30 per CFL over its lifetime. Fluorescent bulbs are more expensive than incandescent, but last as much as ten times longer, and use significantly less energy over their lifetime.

The following pages contain many tips for those who are just beginning to 'go green' as well as technical information about lighting that will help you understand what 'green lighting' means.

Your Home, Your Work, Your Environment

How we light up the places where we live, work and play makes a significant difference in how we feel; it also makes a big impact on the environment. Proper and effective lighting placement and energy-efficient fixture operation is important with any lighting application. Effective lighting can increase comfort and productivity while saving energy costs and minimizing pollution.

Did You Know?

Despite various new and efficient technological advancements, lighting remains one of the least energy-efficient practices in the home. Nearly 90 percent of energy in traditional incandescent sources is lost to heat, leaving only 10 percent for light. Lighting generally accounts for nearly a tenth of a homeowner's energy bill, and is one of the least environmentally sound aspects of modern living. CFLs produce 75% less heat than incandescent sources, which is 75% less load on your HVAC system due to contributions from lighting.

This need not be the case with the lighting technology currently available. Energy efficient lighting can reduce energy consumption by as much as 75 percent. Additionally, energy-efficient sources last an average of 10 times longer than incandescent sources. The following pages contain information and resources that can help you contribute to a greener environment.

Awards for Green Product Innovation and Design



Progress Lighting is dedicated to providing beautiful, functional products that incorporate state-of-the-art features. We are very proud to have been recognized by leaders in the lighting industry, such as the Illuminating Engineering Society of North America (IESNA), Energy Star, the American Lighting Association (ALA) and others.



Award	Given By	Year(s)
Partner of the Year	ENERGY STAR	2007
Progress Report	IESNA	2007 (Copenhagen, Lakeland, Strata)
Innovation Award Winner	Home Builder Executive	2006
Best In Class	Professional Builder	2006
Best In Class	Custom Builder	2006
Lighting For Tomorrow	DOE/ALA/CEE/EPA	2007 (Strata*) 2006 (Fairview) 2006 (Lakeland) 2006 (International**)

* winner in outdoor category of Solid State Lighting products
 ** honorable mention



Green Basics

It can be a daunting task when you see unfamiliar terms and acronyms. Included in this book are some terms that relate to lighting and sustainability practices.

Green Friendly

Green friendly lighting products are less damaging to the environment than traditional lighting products, such as incandescent bulbs. They light more efficiently and reduce power consumption to contribute to a healthier living environment.



Incandescent

The standard incandescent bulb incorporates a tungsten filament. When the filament is heated it glows. Incandescent bulbs tend to have a very poor lamp life and lose most of their energy (up to 90%) to heat.



CFL

Compact fluorescent lamps (CFL) are filled with low-pressure gas. The gas emits ultraviolet light that is converted to visible light when it strikes phosphors on the glass. CFLs generate significantly more light per watt than incandescent lamps and have a far superior lamp life.



LED

LED stands for Light Emitting Diode. An LED is a semiconductor device that emits visible light when an electric current passes through it. LEDs don't burn out like traditional bulbs, they simply dim over time. They use two to five times less energy than an incandescent lamp.

ENERGY STAR

Besides saving energy, when you choose Energy Star qualified products, you help protect the environment from air pollution associated with power generation.

If just one room in every U.S. home was brightened by Energy Star qualified lighting, the change would have the pollution savings equal to removing more than 8 million cars from the road.

Energy Star is the mark of quality for energy efficient, green friendly lighting. Progress Lighting offers a wide array of Energy Star fixtures and was named the 2007 Energy Star Product Manufacturing Partner of the Year.

Most Energy Star fixtures include lamps that last more than 10,000 hours.

Energy Star fixtures are tested to meet strict energy efficiency guidelines set by the US Environmental Protection Agency (EPA) and US Department of Energy (DOE).

More Light for Less Money

A 20-watt CFL has about the same light output as a 100-watt incandescent, and uses 50-80% less energy.

CFL
Total cost of lamp + energy = **\$49.60**

Cost of energy over lamp life \$40.60

Cost of 1 bulb \$9.00

Incandescent
Total cost of lamp + energy = **\$104.05**

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Cost of energy for 1 bulb \$9.85

Cost of 1 bulb \$0.50

Progress in the Community

Progress Lighting has partnered with a number of organizations to bring sustainable concepts to communities and create a dialogue on the benefits of green lighting. Here are just a few examples of projects in which we participated.



National Homebuilder Mainstream GreenHome

The GreenHome is an educational platform for residential sustainability to bring eco-friendly construction techniques to the forefront of residential building. The home showcases numerous innovative combinations of sustainable features that make it one of the greenest homes in the country. Progress Lighting donated LEDs and CFLs to complete the house and showcase the benefits of state-of-the-art lighting techniques. Since construction, it has earned the highest eco-friendly accolades and has set many “first-of-its-kind” trends. To learn more about the project, visit www.mainstreamgreenhome.com.



Honorable Mentions

Progress Lighting also has donated decorative Energy Star qualified lanterns for PBS/ETV and New American Home projects to highlight the possibilities available with energy efficient options.



Green Lingo

Progress Lighting is a committed ENERGY STAR partner and helps to change people's lives through education and product availability. The ENERGY STAR mark identifies products that are designed to meet the highest standards of energy efficiency.


ENERGY STAR



ENERGY STAR qualified light fixtures lower the cost of lighting in your home because they use less electricity than non-qualified models. Besides saving energy, when you choose ENERGY STAR qualified fixtures, you also protect the environment from air pollution associated with power generation.

Color Temperature

Color temperature is measured in degrees Kelvin and describes the visual warmth or coolness of light. Numerically high color temperatures have visually cool (blue) appearance and vice versa.



California Title 24

Title 24 legislation was started in 1978 in response to a legislative mandate to reduce California's energy consumption. Title 24 addresses lighting in a residential building based on the room type. For each room in the house, there are specific standards that must be met to comply with Title 24.



Lamp Life

Lamp life is measured in operating hours and is determined based on "half average life method." The rated life is the number of operating hours required for half of the lamps to fail.



Incandescent lamp life: 167 days



CFL lamp life: 1,642 days (4.5 years)

LED



Light Emitting Diodes (LED) are the most recent development in residential lighting technology. Light is generated by semi-conductors and modified by tiny diode lenses. These lamps do not burn out like traditional lighting, but gradually dim over several decades.

Extreme Makeover: Home Edition



Progress Lighting donated numerous Energy Star qualified fixtures for an “Extreme Makeover: Home Edition” project in Athens, Vermont.

Progress Lighting’s donation helps the house meet the energy requirements of a 5-Star Plus, ENERGY STAR qualified home.


Since the family’s return to their new “Extreme” home, they have used a fraction of the energy typically needed for a house this size.



Progress Lighting also donated LED products for inclusion in “Extreme Makeover: Home Edition’s” green house for display at the West Coast Green Show in San Francisco, as well as the 2008 Superbowl.



Lumens vs. Watts. Why You Should Care.



You've probably heard these two terms used in discussions about green lighting.

But do you know how they are different and why (or if) this is important to you?

Lumens are a measure of light output. The more lumens, the more light.

Wattage is a measure of energy. The more watts, the more energy needed. A higher-wattage light bulb is not necessarily a brighter bulb. It is, however, more expensive to use than a lower-wattage bulb.

CFLs with light output comparable to typical incandescent light bulbs will have lower wattages for the same amount of lumens, meaning less energy is used by the CFL for the same amount of light.

As shown in the chart to the left, a 26w CFL with light output similar to that of a 100w incandescent uses much less energy. (It also lasts up to ten times as long as the incandescent bulb, saving even more in the long run.)

Green Light, Clear Sky

Replacing one incandescent light bulb with one CFL will save 150 pounds of carbon dioxide per year, which would result in reduced pollution and cleaner, blue skies.

If everyone in the U.S. used energy-efficient lighting, we could retire 90 average size power plants.



Calculate Your Savings

Calculate lamp light savings, calculate yearly savings! By visiting <http://www.energyefficientlight.com>, you can learn more about solid state lighting, ENERGY STAR benefits and other energy efficient lighting options. You can even calculate your savings by comparing energy efficient products to similar units using incandescent lamps with our energy savings calculator!

More Ways to Make a Difference



In Your Home & Office

- Clean or replace air filters at least once a month
- Lower the thermostat on your water heater to 120 degrees
- Turn off unneeded lights – even if leaving for a few minutes
- Set your refrigerator temperature to 38 degrees
- Keep your air conditioning at 78 degrees in the summer
- Keep your heat set to 68 degrees in the winter
- Work one day a week from home, and reduce commuting traffic and auto emissions
- Use a glass cup or mug rather than a disposable one
- Recycle used printer and copier cartridges



Conserve Water

- Check and fix any water leaks in your home
- Don't wash dishes with the water running continuously
- Install low-flow shower heads in your bathrooms
- Wash only full loads of laundry and dishes
- Use a broom instead of a hose to clean sidewalks and driveways



In Your Yard

- Leave grass clippings on the lawn as nutrients for the soil
- Water grass early in the morning
- Avoid using leaf blowers and other dust-producing equipment
- Install a drip irrigation system in your yard
- If you are heating an outdoor pool, keep it covered at night and when not in use



Protect the Air

- Walk, ride a bike, carpool or use public transportation whenever possible
- Use radial tires and keep them properly inflated
- Burn seasoned wood in your fireplace rather than green wood
- Support your farmer's market. Buy locally grown produce to reduce pollution associated with transporting food long distances.



Starlite LED

Brushed Nickel finish

Frosted glass

Warm light output, modern styling
with state of the art LED technology

Dimmable with 3-wire electronic low
voltage dimmer switches



P4420-09



P7101-09

Mounts up or down



P5022-09

Product No.	Finish	Description	Size	Lamp(s)
P4420-09*	Brushed Nickel	Five-light chandelier Includes two 12" and two 15" stems with 90° hang straight.	27" dia., 17-1/4" ht. Overall ht. w/stem 73"; wire 15'.	Five 3w LED (included) 3500K, CRI: 76.
P5022-09*	Brushed Nickel	One-light pendant. Includes two 12" and two 15" stems with 90° hang straight.	7-3/4" dia., 5-1/4" ht. Overall ht. w/stem 61"; wire 10'.	One 3w LED (included) 3500K, CRI: 76.
P7101-09*	Brushed Nickel	One-light wall bracket. Mounts up or down.	7-3/4" W., 11-3/4" ht. Extends 10". H/CTR 9".	One 3w LED (included) 3500K, CRI: 76.

*Includes integral dimmable power sources

EVERLUME™
LED LIGHTING

See more Everlume LED fixtures
throughout this catalog.

Copenhagen LED

Brushed Nickel and Antique Bronze finishes
 Etched white opal glass with textured design
 Modern styling with state-of-the-art LED technology
 Warm light output
 Dimmable with 3-wire electronic low voltage dimmer switches



Product No.	Finish	Description	Size	Lamp(s)
P4430-09*	Brushed Nickel	Four-light chandelier.	22" dia., 19" ht.	Four 3w LED w/frosted
P4430-20*	Antique Bronze		Overall ht. w/ chain 94"; wire 15'.	LED lamp shrouds (included). 3500K, CRI: 76.
P5031-09*	Brushed Nickel	One-light mini-pendant.	6" dia., 5-1/8" ht.	One 3w LED w/frosted
P5031-20*	Antique Bronze	Includes one 6", two 12" and one 15" stems with 90° hang straight.	Overall ht. w/stem 53"; wire 10'.	LED lamp shroud (included). 3500K, CRI: 76.

*Includes integral dimmable power sources

The Copenhagen chandelier received a 2007 Progress Report label from the Illuminating Engineering Society of North America for its innovative use of LED technology for residential illumination. Progress Report labels recognize products that have made significant advances to the art of science and lighting.







International

- Brushed Nickel finish
- Etched opal glass bowls
- Minimal linear forms
- Urban sophistication



See *Progress Lighting Catalog 128* for incandescent fixtures that match these stylish, energy-saving compact fluorescents.



Product No.	Finish	Description	Size	Ballast	Lamp(s)
P2854-09EBWB	Brushed Nickel	Three-light foyer. 13 ft. of aluminum aircraft cable included.	18-1/2" dia., 18-1/2" ht. Overall ht. w/cord 180".	120V NPF electronic	Three 26w 4-pin triple tube CFL (included). GX24q-3 base. 
P2858-09EBWB	Brushed Nickel	Three-light close-to-ceiling.	18" dia., 8-1/4" ht.	120V NPF electronic	Three 26w 4-pin triple tube CFL (included). GX24q-3 base. 



P4275-09EBWB



P3468-09EBWB

Mount directly to ceiling...

or hang from chain



P3468-09EBWB



P4276-09EBWB



P5145-09EBWB

Avalon





Brushed Nickel finish


Etched alabaster style glass

Twisted rope scrolls




See pages 23 and 48 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.

Product No.	Finish	Description	Size	Lamp(s)
P3468-09EBWB	Brushed Nickel	Two-light foyer. Chain and ceiling mounts included.	13-1/8" dia., 15" ht. Overall ht. w/chain 90"; wire 15'.	Two self-ballasted 13w spiral CFL (included). GU24 base. 
P4275-09EBWB	Brushed Nickel	Five-light chandelier.	26-1/2" dia., 23" ht. Overall ht. w/chain 98"; wire 15'.	Five self-ballasted 13w spiral CFL (included). GU24 base. 
P4276-09EBWB	Brushed Nickel	Three-light chandelier.	24-1/4" dia., 14-1/2" ht. Overall ht. w/chain 91"; wire 15'.	Three self-ballasted 13w spiral CFL (included). GU24 base. 
P5145-09EBWB P5145-33EBWB	Brushed Nickel Cobblestone	Mini-pendant.	7-3/4" dia., 6-1/2" ht. Overall ht. w/stem 63". wire 10'. Includes two 12" and two 15" stems with 90° hang straight.	One self-ballasted 13w spiral CFL (included). GU24 base. 

ENERGY STAR 

Most people are sensitive to the need to protect our environment, but many don't know where to start. Choosing ENERGY STAR qualified lighting is a simple way to save money, energy, and time, while helping to keep our planet a healthy place to live.

Visit www.energystar.gov to learn more.



Savannah

Burnished Chestnut
 Antique alabaster glass
 Pineapple symbol of hospitality
 Twisted rope details



P7209-86STRWB







P4278-86EBWB



P3488-86STRWB



P5146-86EBWB

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3488-86STRWB	Burnished Chestnut	Two-light foyer. Glass top diffuser.	17" dia., 27-1/4" ht. Overall ht. w/chain 102-1/4"; wire 15'.	120V NPF electronic	Two 18w 4-pin Quad CFL (included). G24q-2 base. 
P4278-86EBWB	Burnished Chestnut	Five-light chandelier.	26-5/8" dia., 28" ht. Overall ht. w/chain chain 103"; wire 15'.	N/A	Five self-ballasted 13w spiral CFL (included). GU24 base. 
P5146-86EBWB	Burnished Chestnut	One-light mini-pendant. Includes two 12" and two 15" stems with 90° hang straight.	8-3/4" dia., 6-7/8" ht. Overall ht. w/stem 63-1/4"; wire 10'.	N/A	One self-ballasted 13w spiral CFL (included). GU24 base. 
P7209-86STRWB	Burnished Chestnut	One-light wall sconce.	13" W., 8-3/4" ht. Extends 6-1/2".	120V NPF electronic	One 18w 4-pin Quad CFL (included). G24q-2 base. 



See pages 24 and 48 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.

P3796-09EBWB



Mount directly to ceiling...

P3796-09EBWB



or hang from chain

P3186-09EBWB



Mounts up or down

P4393-09EBWB



Bedford




Brushed Nickel finish

Etched alabaster glass

Chandeliers with distinctive center column



See page 49 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.

Product No.	Finish	Description	Size	Lamp(s)
P3186-09EBWB	Brushed Nickel	One-light wall bracket. Damp location listed.	5-5/8" W., 9-1/4" ht. Extends 7-1/2". H/CTR 3-1/16".	One self-ballasted 13w spiral CFL (included). GU24 base. 
P3796-09EBWB	Brushed Nickel	One-light foyer. Chain and ceiling mounts included.	10-1/2" dia., 14-1/2" ht. Overall ht. w/chain 54"; wire 15".	One self-ballasted 13w spiral CFL (included). GU24 base. 
P4393-09EBWB	Brushed Nickel	Five-light chandelier.	22-1/2" dia., 16" ht. Overall ht. w/chain 91"; wire 15".	Five self-ballasted 13w spiral CFL (included). GU24 base. 



LED Mini-pendants

Energy-efficient warm white (2700K) LED lamps

Integral dimmable transformer

Long lamp life (40,000 hrs)

120 lumens – light output comparable to 40w incandescent

See more Everlume LED fixtures throughout this catalog.

Product No.	Finish	Description	Size	Lamp(s)
P5148-09B	Brushed Nickel	Blue glass	4-1/8" dia., 6-3/4" ht.	One 3w LED (included). Overall ht. w/cord 129"; wire 10'.
P5148-09W	Brushed Nickel	White glass		
P5149-20T	Antique Bronze	Topaz glass	5-3/8" dia., 6-3/8" ht.	One 3w LED (included). Overall ht. w/cord 128"; wire 10'.
P5150-09PT	Brushed Nickel	Topaz tortoise glass	4-1/2" dia., 8" ht.	One 3w LED (included). Overall ht. w/cord 130"; wire 10'.
P5150-20PR	Antique Bronze	Red patterned glass		
P5150-20PT	Antique Bronze	Topaz tortoise glass		
P5151-09SW	Brushed Nickel	Swirled glass	6-5/8" dia., 6-1/4" ht.	One 3w LED (included). Overall ht. w/cord 128"; wire 10'.
P5151-20SW	Antique Bronze			
P5154-09A	Brushed Nickel	Amber glass	6-3/4" dia., 6" ht.	One 3w LED (included). Overall ht. w/cord 128"; wire 10'.
P5154-20A	Antique Bronze			



About LED


LED stands for Light Emitting Diode. An LED is a very small device that produces light through the semi-conducting properties of its metal alloys. LEDs do not have a filament that will burn out, and they don't get hot.

How long do LEDs last?


Unlike other light sources, LEDs don't typically burn out; they simply get dimmer over time. The best white LEDs have a useful life of about 35,000 hours (four years of continuous operation). A 75w incandescent bulb lasts about 1,000 hours and a comparable CFL lasts 8,000 to 10,000 hours.

Usable Light Comparison

Incandescent



LED



Surface footcandles from a 3w LED module are comparable to a 40w incandescent lamp.

Eclipse

Cobblestone with faux Tiffany art glass

Polished Brass and Brushed Steel with

satin opal glass

P3495-33EB
P7322-33EBWB



P3496-33EB
P7323-33EBWB



P3576-13EB



P3574-10EB
P7330-10EBWB



P7171-13STRWB



P7176-33EBWB

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P7171-10STRWB	Polished Brass	One-light wall sconce	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V NPF electronic	1 13w 4-pin Quad (included). G24q-1 base. ADA
P7171-13STRWB	Brushed Steel	One-light wall sconce	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V NPF electronic	1 26w 4-pin triple CFL (included). GX24q-3 base. ADA

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3495-33EB	Cobblestone	Three-light chandelier	19-3/8" dia. 17" ht.	120V/277V HPF electronic	3 26w 4-pin Quad CFL. G24q-3 base.
P3574-10EB	Polished Brass	Three-light chandelier	19-3/8" dia. 17" ht.	120V/277V HPF electronic	3 13w 4-pin Quad CFL. G24q-1 base.
P3574-13EB	Brushed Steel	Three-light chandelier	19-3/8" dia. 17" ht.	120V/277V HPF electronic	3 13w 4-pin Quad CFL. G24q-1 base.

Overall ht. w/chain 56"; wire 15".

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P7322-33EBWB	Cobblestone	Three-light chandelier	19-3/8" dia. 17" ht.	120V NPF electronic	3 26w 4-pin Quad CFL (included). G24q-3 base.
P7330-10EBWB	Polished Brass	Three-light chandelier	19-3/8" dia. 17" ht.	120V NPF electronic	3 13w 4-pin Quad CFL (included). G24q-1 base.
P7330-13EBWB	Brushed Steel	Three-light chandelier	19-3/8" dia. 17" ht.	120V NPF electronic	3 13w 4-pin Quad CFL (included). G24q-1 base.

Overall ht. w/chain 56"; wire 15".

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3496-33EB	Cobblestone	Four-light chandelier	27-3/8" dia. 24-1/8" ht.	120V/277V HPF electronic	4 26w 4-pin Quad CFL. G24q-3 base
P3576-10EB	Polished Brass	Four-light chandelier	27-3/8" dia. 24" ht.	120V/277V HPF electronic	4 13w 4-pin Quad CFL. G24q-1 base.
P3576-13EB	Brushed Steel	Four-light chandelier	27-3/8" dia. 24" ht.	120V/277V HPF electronic	4 13w 4-pin Quad CFL. G24q-1 base.
P7323-33EBWB	Cobblestone	Four-light chandelier	27-3/8" dia. 24-1/8" ht.	120V NPF electronic	4 26w 4-pin Quad CFL (included). G24q-3 base.

Overall ht. w/chain 63"; wire 15".



P3568-10EB
P7327-10EBWB



P7327-11EBWB



P3492-33EB

Product No.	Finish	Size	Ballast	Lamp(s)
P3492-33EB	Cobblestone	15-1/4" dia. 10-5/8" ht.	120V/277V HPF electronic	2 26w 4-pin Quad CFL. G24q-3 base.
P3568-10EB	Polished Brass	15-1/4" dia.	120V/277V	2 13w 4-pin Quad
P3568-13EB	Brushed Steel	10-5/8" ht.	HPF electronic	CFL. G24q-1 base.



P3493-33EB
P7319-33EBWB

Product No.	Finish	Size	Ballast	Lamp(s)
P3493-33EB	Cobblestone	19-3/8" dia. 13-1/4" ht.	120V/277V HPF electronic	3 26w 4-pin Quad CFL. G24q-3 base.
P3570-10EB	Polished Brass	19-3/8" dia.	120V/277V	3 13w 4-pin Quad
P3570-11EB	Antique Brass	13-1/4" ht.	HPF electronic	CFL. G24q-1 base.
P3570-13EB	Brushed Steel			

Product No.	Finish	Size	Ballast	Lamp(s)
P3494-33EB	Cobblestone	27-3/8" dia. 20-1/2" ht.	120V/277V HPF electronic	4 26w 4-pin Quad CFL. G24q-3 base.
P3572-10EB	Polished Brass	27-3/8" dia.	120V/277V	4 13w 4-pin Quad
P3572-13EB	Brushed Steel	20-1/2" ht.	HPF electronic	CFL. G24q-1 base.



P3570-10EB

Product No.	Finish	Size	Ballast	Lamp(s)
P7327-10EBWB	Polished Brass	15-1/4" dia.	120V NPF	2 13w 4-pin Quad
P7327-11EBWB	Antique Brass	10-5/8" ht.	electronic	CFL (included).
P7327-13EBWB	Brushed Steel			G24q-1 base.

Product No.	Finish	Size	Ballast	Lamp(s)
P7319-33EBWB	Cobblestone	19-3/8" dia. 13-1/4" ht.	120V NPF electronic	3 26w 4-pin Quad CFL (included). G24q-3 base.
P7328-13EBWB	Brushed Steel	19-3/8" dia., 13-1/4" ht.	120V NPF electronic	3 13w 4-pin Quad CFL (included). G24q-1 base.



P3572-13EB
P7329-13EBWB

Product No.	Finish	Size	Ballast	Lamp(s)
P7320-33EBWB	Cobblestone	27-3/8" dia., 20-1/2" ht.	120V NPF electronic	4 26w 4-pin Quad CFL (included). G24q-3 base.
P7329-13EBWB	Brushed Steel	27-3/8" dia., 20-1/2" ht.	120V NPF electronic	4 13w 4-pin Quad CFL (included). G24q-1 base.

Eclipse

Cobblestone with faux Tiffany art glass

Polished Brass and Brushed Steel with satin opal glass



P3490-33EB
P7316-33EBWB



P3564-10EB
P7325-10EBWB



P3566-13EB
P7326-13EBWB

Drive Smart

If you have more than one car, use the most fuel-efficient one whenever you can. You will save money and be kinder to the planet.

Combine errands into one trip instead of several— save gas, and time, too.



P3562-13EB
P7324-13EBWB





P3562-10EB
P7324-10EBWB






P3489-33EB
P7315-33EBWB

Product No.	Finish	Size	Ballast	Lamp(s)
P3489-33EB	Cobblestone	15-1/4" dia. 4-5/8" ht.	120V/277V HPF electronic	2 13w 4-pin Quad CFL. G24q-1 base.
P3562-10EB	Polished Brass	15-1/4" dia. 4-5/8" ht.	120V/277V HPF electronic	2 13w 4-pin Quad CFL. G24q-1 base.
P3562-11EB	Antique Brass			
P3562-13EB	Brushed Steel			

Product No.	Finish	Size	Ballast	Lamp(s)
P7315-33EBWB	Cobblestone	15-1/4" dia. 4-5/8" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base. 
P7324-10EBWB	Polished Brass	15-1/4" dia. 4-5/8" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base. 
P7324-13EBWB	Brushed Steel			

Product No.	Finish	Size	Ballast	Lamp(s)
P3490-33EB	Cobblestone	19-3/8" dia. 5-1/2" ht.	120V/277V HPF electronic	3 13w 4-pin Quad CFL. G24q-1 base.
P3564-10EB	Polished Brass	19-3/8" dia. 5-1/2" ht.	120V/277V HPF electronic	3 13w 4-pin Quad CFL. G24q-1 base.
P3564-13EB	Brushed Steel			

Product No.	Finish	Size	Ballast	Lamp(s)
P7316-33EBWB	Cobblestone	19-3/8" dia. 5-1/2" ht.	120V NPF electronic	3 13w 4-pin Quad CFL (included). G24q-1 base. 
P7325-10EBWB	Polished Brass	19-3/8" dia. 5-1/2" ht.	120V NPF electronic	3 13w 4-pin Quad CFL (included). G24q-1 base. 
P7325-13EBWB	Brushed Steel			

Product No.	Finish	Size	Ballast	Lamp(s)
P3491-33EB	Cobblestone	27-3/8" dia. 7-1/8" ht.	120V/277V HPF electronic	4 13w 4-pin Quad CFL. G24q-1 base.
P3566-10EB	Polished Brass	27-3/8" dia. 7-1/8" ht.	120V/277V HPF electronic	4 13w 4-pin Quad CFL. G24q-1 base.
P3566-13EB	Brushed Steel			
P7326-13EBWB	Brushed Steel	27-3/8" dia. 7-1/8" ht.	120V NPF electronic	4 13w 4-pin Quad CFL (included). G24q-1 base. 

International



Etched opal glass

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P2858-09EBWB	Brushed Nickel	Three-light	18" dia. 8-1/4" ht.	120V NPF electronic	3 26w triple tube CFL (included). GX24q-3 base.

Damp location listed.

See page 14 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.



P2858-09EBWB

Prescott

Satin-etched glass

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3748-10	Polished Brass	Three-light semi-flush	19-1/2" dia. 16" ht.	120V HPF	3 13w 2-pin twin CFL. GX23 base.



P3748-10

Avalon

Swirled alabaster style glass

Product No.	Finish	Description	Size	Lamp(s)
P3468-09EBWB	Brushed Nickel	Two-light semi-flush	13-5/8" dia., 15" ht.	2 self-ballasted 13w spiral CFL (included). GU24 base.

Chain & ceiling mounts both included.

See pages 15 and 48 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.



P3468-09EBWB

Everlume LED



6" recessed surface-mount fixture

Product No.	Finish	Description	Size	Lamp
P8024-09/35K	Brushed Nickel	3500K color temp.	2-3/8" ht. 7" O.D.	12w LED (included). CRI:76 530 lumens
P8024-30/35K	White	3500K color temp.	2-3/8" ht. 7" O.D.	12w LED (included). CRI:76 530 lumens
P8024-30	White	2700K color temp.	2-3/8" ht. 7" O.D.	12w LED (included). CRI:76 480 lumens

Includes LEDs, integral dimmable power source, frosted lens, hardware for mounting into standard ceiling junction box. Frosted lens provides 120 degree beam pattern (comparable to 18w CFL and 50-60w incandescent)

See more Everlume LED fixtures throughout this catalog.



P8024-09/35K



P8024-30
P8024-30/35K



Savannah

Antique alabaster glass

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P3497-86STRWB*	Burnished Chestnut	Two-light	13" dia., 7-1/4" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	
P3498-86STRWB*	Burnished Chestnut	Two-light	17" dia., 8-3/4" ht.	120V NPF electronic	2 18w 4-pin Quad CFL (included). G24q-2 base.	
P3499-86STRWB	Burnished Chestnut	Two-light semi-flush	13" dia., 13-1/4" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	

*Damp location listed





See pages 16 and 48 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.

Flush Mount

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P7312-10 P7312-30	Polished Brass White	Two-light. White glass	11-3/4" dia., 5-7/8" ht.	120V NPF magnetic	2 13w 2-pin twin CFL. GX23 base	
P7312-10STRWB P7312-30STRWB	Polished Brass White	Two-light. White glass	11-3/4" dia., 5-7/8" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	
P7313-10STRWB	Polished Brass	Two-light. White acrylic	11" dia., 3-1/2" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	ADA
P7313-10WB	Polished Brass	Two-light. White acrylic	11" dia., 3-1/2" ht.	120V NPF magnetic	2 13w 2-pin twin CFL (included). GX23 base.	ADA
P7353-10	Polished Brass	Two-light. Opal glass	12-1/2" dia., 7" ht.	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.	
P7359-69	White	Two-light. Opal glass w/Polished Brass accents	16" dia., 8-1/2" ht.	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.	
P7360-69EB	White	Two-light. Opal glass w/Polished Brass accents	16" dia., 8-3/4" ht.	120V HPF electronic	2 18w 4-pin biax CFL. 2G11 base.	
P7364-10	Polished Brass	Two-light. Ice glass	12-1/2" dia., 7" ht.	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.	
P7364-10STRWB	Polished Brass	Two-light. Ice glass	12-1/2" dia., 7" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	

Damp location listed.

Etched Ribbed Glass

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3761-09STRWB	Brushed Nickel	One-light	11-1/4" dia. 4/1/8" ht.	120V NPF electronic	1 13w 4-pin Quad CFL (included). G24q-1 base. 
P3762-09STRWB	Brushed Nickel	Two-light	14" dia. 4-3/4" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base. 




Damp location listed.



P3761-09STRWB

P3762-09STRWB

Etched Alabaster Style Glass

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3760-09STRWB	Brushed Nickel	Two-light	16-5/8" dia. 5-1/2" ht.	120V NPF electronic	2 18w 4-pin Quad CFL (included). G24q-2 base. 
P3760-10STRWB	Polished Brass				
P3764-09STRWB	Brushed Nickel	One-light	11-1/2" dia. 3-3/4" ht.	120V NPF electronic	1 13w 4-pin Quad CFL (included). G24q-1 base. 
P3764-10STRWB	Polished Brass				
P3765-09STRWB	Brushed Nickel	Two-light	14" dia. 4-1/2" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base. 

Damp location listed.





P3764-10STRWB

P3765-09STRWB

P3760-10STRWB

Satin Swirled Glass

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3546-30	Textured White	Two-light	11-3/8" dia. 5-3/4" ht.	120V HPF magnetic	2 13w 2-pin Quad CFL. GX23-2 base.
P3547-30STRWB	Textured White	Two-light	13-1/4" dia. 6" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base. 
P3548-30STRWB	Textured White	Three-light	15-1/2" dia. 6" ht.	120V NPF electronic	3 13w 4-pin Quad CFL (included). G24q-1 base. 

Damp location listed.



P3546-30

P3547-30STRWB

P3548-30STRWB

Unplugged

Unplug lamps, electronics, battery chargers and other equipment when not in use. Together, these small items can use as much power as a refrigerator.

Acrylic Round Clouds

Regressed chassis. Wall or ceiling mount.

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P7307-60	White	One-light	16" dia., 4" ht.	120V NPF	1 32w FC12T9 circline	ADA
P7308-60	White	Two-light	16" dia., 4" ht.	120V NPF	1 22w FC8T9 and 1 32w FC12T9 circline	HPF ADA
P7309-60	White	Two-light	20" dia., 4-3/4" ht.	120V HPF	1 32w FC12T9 and 1 40w FC16T9 circline	
P7310-60EB	White	Two-light	16" dia., 4" ht.	120V HPF electronic	2 13w 4-pin Quad CFL. G24q-1 base.	ADA
P7310-60STRWB	White	Two-light	16" dia., 4" ht.	120V NPF electronic	2 13w 4-pin Quad CFL. (included). G24q-1 base.	ADA 
P7311-60EB	White	Four-light	20" dia., 4-3/4" ht.	120V/277V HPF electronic	4 13w 4-pin Quad CFL. G24q-1 base.	MTO
P7311-60STRWB	White	Four-light	20" dia., 4-3/4" ht.	120 NPF electronic	4 13w 4-pin Quad CFL. (included). G24q-1 base.	ADA 

Acrylic Squares

White acrylic diffuser

Swing action latches on diffuser

Regressed white chassis

Wall or ceiling mount

Product No.	Finish	Description	Size	Ballast	Lamps	
P7379-30	White	Two-light	15" sq., 3-1/8" ht.	120V NPF	1 22w FC8T9 circline & 1 32w FC12T9 circline	ADA
P7380-30	White	Two-light	19" sq., 3-1/8" ht.	120V NPF	1 32w FC12T9 circline and 1 40w FC16T9 circline	ADA
P7381-30	White	Three-light	15" sq., 3" ht.	120V NPF	3 13w 2-pin twin CFL. GX23 base.	ADA
P7382-30	White	Two-light	12-1/8" sq., 3-1/8" ht.	120V NPF	2 13w 2-pin twin CFL. GX23 base.	ADA

Damp location listed.

Squares

White polycarbonate diffuser

Mounts flush on ceiling, under shelves or to wall

Low profile, impact resistant polycarbonate frame

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P7118-30	White	Two-light	12" sq., 2-1/4" ht.	120V NPF	2 13w 2-pin twin CFL. GX23 base.	ADA
P7182-30	White	Two-light	9-1/2" sq., 2" ht.	120V NPF	2 7w or 2 9w 2-pin twin CFL. G23 base.	ADA

Damp location listed.



P7307-60
P7308-60
P7310-60STRWB
P7310-60EB



P7309-60
P7311-60STRWB
P7311-60EB



P7379-30



P7380-30



P7381-30



P7382-30



P7118-30

P7182-30

Acrylic Clouds


Twist-on installation. Wall or ceiling mount.

Product No.	Finish	Description	Size	Ballast	Lamps	ADA
P7383-30	White	Two-light	14" dia., 3-5/8" ht.	120V NPF	1 22w FC8T9 circline & 1 32w FC12T9 circline	ADA
P7384-30	White	Two-light	15-1/4" dia., 4-1/8" ht.	120V NPF	1 32w FC12T9 circline & 1 40w FC16T9 circline	
P7385-30	White	One-light	10-7/8" dia., 3-1/4" ht.	120V NPF	1 22w FC8T9 circline	ADA

Damp location listed.

Round Acrylic

White acrylic

Product No.	Finish	Description	Size	Ballast	Lamp(s)	ADA
P7249-09EBWB	Brushed Nickel	One-light	10-3/8" dia., 3-1/2" ht.	120V NPF	1 22w FC8T9	ADA
P7249-174EBWB	Urban Bronze			electronic	circline (included)	

Damp location listed.

Round

White contoured acrylic clouds

Regressed chassis

Wall or ceiling mount

Product No.	Finish	Description	Size	Ballast	Lamp(s)	ADA
P7372-30	White	Two-light	13-7/8" dia., 3-1/8" ht.	120V NPF rapid start	1 22w FC8T9 and 1 32w FC12T9 circline	ADA, HPF
P7372-30STRWB	White	Two-light	13-7/8" dia., 3-1/8" ht.	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	ADA 
P7373-30	White	Two-light	19" dia., 4-1/4" ht.	120V HPF rapid start	1 32w FC12T9 and 1 40w FC16T9 circline	HPF
P7375-30 P7375-31	White Black	Two-light	8-3/4" dia., 3-1/4" ht.	120V NPF	2 7w 2-pin twin CFL. G23 base.	ADA
P7375-30STRWB	White	One-light	8-3/4" dia., 3-1/4" ht.	120V NPF electronic	1 13w 4-pin Quad CFL (included). G24q-1 base.	ADA 
P7376-30 P7376-31	White Black	Two-light	11" dia., 3-1/4" ht.	120V NPF	2 13w 2-pin twin CFL. GX23 base.	ADA, HPF
P7377-30	White	One-light	11" dia., 3" ht.	120V NPF	1 22w FC8T9 circline	ADA
P7378-30	White	Three-light	14" dia., 3-3/4" ht.	120V NPF	3 13w 2-pin twin CFL. GX23 base.	ADA

Damp location listed.






P2523-105C
Pietra Crackle with
Distressed Walnut blades



Tuscan Oak blades

Villa Cortona

P2623-105C Pietra Crackle and Weathered Bronze (-46) with reversible Tuscan Oak/Distressed Walnut blades. 30-year limited warranty. CUL. Size: 52" dia., 16-1/2" ht. CTC 13" ht. Note: use Weathered Bronze (-46) accessory downrods.



See Progress Lighting Catalog 128 for matching incandescent fixtures.




P2523-80
Forged Black with
Tuscan Oak blades



Italian Walnut blades

Canyon Ridge

P2523-80 Forged Black with reversible Tuscan Oak/Italian Walnut blades. 30-year limited warranty. CUL. Size: 52" dia., 16-1/2" ht. CTC 13" ht.



See Progress Lighting Catalog 128 for matching incandescent fixtures.

Light Kits

Alabaster Bowl

P2621-09EBWB Brushed Nickel

P2621-30EBWB White

P2621-33EBWB Cobblestone

Universal-style with quick-connect wiring. Alabaster glass.

Size: 10-3/4" dia. 6" ht.

Lamps: Two 18w CFL, included (non-dimmable).



P2621-09EBWB



P2621-33EBWB



P2621-30EBWB

Schoolhouse

P2620-30EBWB White

Indoor. Universal-style with quick-connect wiring.

Schoolhouse opal glass.

Size: 8-1/4" dia., 7-1/4" ht.

Lamp: One 18w CFL, included (non-dimmable).



P2620-30EBWB

Ceiling Fans for Greener Living

Install a ceiling fan to save on cooling bills in the summer and heating in the winter. Use a ceiling fan instead of air conditioning to save energy in the summer. Purchasing a fan with a reversible motor will enable you to push warm air down from the ceiling and save on heating costs in the winter.

Energy Policy Act of 2005 (EPACT)

The Energy Policy Act of 2005 (EPACT) established a comprehensive, long-range energy policy. It provides incentives for traditional energy production as well as newer, more efficient energy technologies and conservation.

Under EPACT, any ceiling fan with included lighting or any ceiling fan lighting accessory, beginning with products produced January 1, 2007, must:

Include an Energy Star (v3.0) screw-in compact fluorescent lamp for each medium base socket, or

Meet Energy Star (v4.0) requirements for lighting (pin-base compact fluorescent only)

For fan lights that use other lamp bases, such as candelabra, the law defers a decision until a future date, but no later than 2009

52" Performance Fan

P2503-09 Brushed Nickel with reversible Cherry/Natural Cherry blades

P2503-27 Golden Umber with reversible Teak/White Oak blades

P2503-30W White with White blades

P2503-33 Cobblestone with reversible Honey Pine/Rosewood blades

P2503-42 Seabrook with reversible Medium Oak/Light Oak blades

P2503-46 Weathered Bronze with reversible Oak/Dark Teak blades

P2503-86 Burnished Chestnut with reversible Oak/White Oak blades

Size: 52" dia., 15-1/4" ht.
CTC 10-1/2" ht.

Lifetime limited warranty
SureConnect® blade arms

14° blade pitch

45° canopy (up to 12:12 ceiling pitch)

Dual mount

Triple capacitor, 188mm x 15mm reversible motor


80" lead wires

Plywood blade construction


Light fixture adaptable


CUL



P2503-09
Brushed Nickel
with Natural
Cherry blades

Cherry blades



P2503-27
Golden Umber
with Teak blades

White Oak blades



CTC installation




P2503-30W
White with
White blades

Living Green Starts at Home


Why is it important to conserve your home's energy consumption? According to energystar.gov, the energy used in the average home can be responsible for more than twice the greenhouse gas emissions of the average car. When you use less energy at home, you reduce greenhouse gas emissions from power plants and help protect our environment from the risks of global climate change.





P2503-33
Cobblestone with
Honey Pine blades

Rosewood blades




P2503-42
Seabrook with
Light Oak blades

Medium Oak
blades



P2503-46
Weathered Bronze with
Dark Teak blades

Oak blades



P2503-86
Burnished Chestnut with
Oak blades

White Oak blades

SureConnect® System


Motor screws pre-installed in blade arms to prevent them from falling out during installation.

Special guides perfectly align blade arms to motor.

Preinstalled rubber isolation pads prevent vibration noise.



45° Canopy



Standard canopy works with sloped ceilings up to 45°. (12:12 ceiling pitch)

Outlet box mounting plate includes convenient hands-free hanger for wiring.

Oversize, textured die-cast hanger ball reduces vibrations that can cause noise and wobble.

Dual-mount for downrod or close-to-ceiling installation (on select fans)

52" Signature Fan

P2521-09 Brushed Nickel with reversible White/Natural Cherry blades

P2521-20 Antique Bronze with reversible Medium Cherry/Classic Walnut blades

P2521-33 Cobblestone with reversible Honey Pine/Medium Cherry blades

P2521-40 Millstone with reversible Medium Oak/Light Oak blades

P2521-71 Gilded Iron with reversible Classic Walnut/Dark Cherry blades

P2521-77 Forged Bronze with reversible Classic Walnut/Medium Cherry blades

P2521-81 Antique Nickel with reversible Medium Oak/Cherry blades

P2521-93 Corinthian Bronze with reversible Dark Teak/Medium Cherry blades

Size: 52" dia., 14-5/8" ht.
CTC 11-9/16" ht.

30-year limited warranty
SureConnect® blade arms
12° blade pitch

45° canopy (up to 12:12 ceiling pitch)

Dual mount

Triple capacitor, 153mm x 18mm reversible motor

80" lead wires

Plywood blade construction

Light fixture adaptable

CUL



P2521-77
Forged Bronze with Classic Walnut blades



Medium Cherry blades



P2521-33
Cobblestone with Medium Cherry blades



Honey Pine blades



P2521-71
Gilded Iron with Dark Cherry blades



Classic Walnut blades



P2521-40
Millstone with Medium Oak blades



Light Oak blades



P2521-93
Corinthian Bronze with Dark Teak blades




Medium Cherry blades



P2521-81
Antique Nickel with Cherry blades



Medium Oak blades



CTC installation

52"

Builder Fan 

P2501-04 Platinum Mist with reversible Cherry/Natural Cherry blades

P2501-09 Brushed Nickel with reversible Cherry/Natural Cherry blades

P2501-10 Polished Brass with reversible Walnut/Medium Oak blades

P2501-20 Antique Bronze with reversible Medium Cherry/Classic Walnut blades

P2501-30 White with reversible White/Washed Oak blades

P2501-30W White with all white blades

P2501-33 Cobblestone with reversible Rosewood/Honey Pine blades

P2501-44 Oxford Silver with reversible Cherry/Medium Oak blades

Size: 52" dia., 13-1/2" ht.
CTC 9-3/4" ht.

30-year limited warranty
SureConnect® blade arms
12° blade pitch
45° canopy (up to 12:12 ceiling pitch)

Dual mount
Triple capacitor, 153mm x 14.5mm reversible motor

80" lead wires
MDF blade construction
Light fixture adaptable
CUL



P2501-09
Brushed Nickel with
Cherry blades



Natural Cherry
blades



P2501-33
Cobblestone with
Rosewood blades



Honey Pine
blades



P2501-04
Platinum Mist with Natural
Cherry blades



Cherry blades



P2501-30
White with White blades



Washed Oak
blades



P2501-20
Antique Bronze with
Medium Cherry blades



Classic Walnut
blades




P2501-10
Polished Brass with
Medium Oak blades



Walnut blades

CTC installation



ENERGY STAR Glass Wall Sconces

Illuminate hallways, provide general perimeter lighting, or add a touch of decorative wall lighting. Choose from a variety of styles and finishes.



MICHAEL GRAVES
COLLECTION

P7117-09EBWB



P7102-10STRWB



P7146-11STRWB



P7090-09EBWB



P7093-09EBWB



P7092-09EBWB

Product No.	Finish	Description	Size	Ballast	Lamp(s)	ADA
P7090-09EBWB	Brushed Nickel	Satin opal glass.	10-1/4" W., 12" ht. Extends 4". H/CTR 6".	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	
P7092-09EBWB	Brushed Nickel	Etched opal glass.	8" W., 10-3/4" ht. Ext. 4". H/CTR 5-1/2".	120V NPF electronic	2 13w 4-pin triple CFL (included). GX24q-1 base.	
P7093-09EBWB	Brushed Nickel	Clear & white glass. Top cover.	11-1/4" W., 11-5/16" ht. Ext. 3-1/2". H/CTR 3".	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	
P7102-10STRWB	Polished Brass	Satin opal glass.	7-3/4" W., 11" ht. Ext. 4". H/CTR 4-1/2".	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	
P7117-09EBWB	Brushed Nickel	Michael Graves. Etched glass. Top cover.	10-5/8" W., 11-1/4" ht. Ext. 4". H/CTR 2-3/8".	120V NPF electronic	1 13w 4-pin Quad CFL (included). 2GX7 base.	
P7146-11STRWB	Antique Brass	Satin opal glass. Top cover.	8" W., 12-3/8" ht. Ext. 4". H/CTR 3-3/4".	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	



P7044-09EBWB



P7044-174EBWB



P7047-20EBWB



P7052-20EBWB







P7052-09EBWB



P7089-20EBWB



P7089-09EBWB

Product No.	Finish	Description	Size	Ballast	Lamp(s)	ADA
P7044-09EBWB P7044-174EBWB	Brushed Nickel Urban Bronze	White glass.	14-3/4" W., 9-7/8" ht. Ext. 3-7/8". H/CTR 6."	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	
P7047-20EBWB	Antique Bronze	Light satin amber glass.	4-1/2" W., 13-1/2" ht. Ext. 4". H/CTR 9-1/8".	120V NPF electronic	1 26w 4-pin Quad CFL (included). G24q-3 base.	
P7052-09EBWB P7052-20EBWB	Brushed Nickel Antique Bronze	Satin opal glass.	7" W., 14" ht. Ext. 4". H/CTR 7".	120V NPF electronic	1 26w 4-pin Quad CFL (included). G24q-3 base.	
P7089-09EBWB P7089-20EBWB	Brushed Nickel Antique Bronze	Etched glass.	6-1/8" W., 11-1/8" ht. Ext. 4". H/CTR 5-1/2".	120V NPF electronic	1 26w 4-pin triple CFL (included). GX24q-1 base.	

Bright Idea

Use wall sconces to illuminate hallways or to provide general perimeter lighting. By incorporating ENERGY STAR qualified wall sconces into your lighting scheme, you can add a touch of decorative wall lighting while saving energy in your home.

ENERGY STAR Glass Wall Sconces

Available in a variety of shapes, colors and materials, these Energy Star qualified wall sconces save energy while illuminating hallways and providing ambient lighting.



P7169-57EBWB



P7079-09EBWB



P7113-30STRWB



P7091-09EBWB



P7209-86STRWB



P7176-33EBWB














P7171-10STRWB



P7171-13STRWB



P7106-69STRWB

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P7079-09EBWB	Brushed Nickel	Alabaster glass. Includes Polished Brass, Antique Bronze and Brushed Nickel ball nuts.	12-1/4" W., 4-3/4" ht. Extends 6". H/CTR 2-3/8".	120V NPF electronic	1 18w 4-pin Quad CFL (included). G24q-2 base. 
P7091-09EBWB	Brushed Nickel	Alabaster glass.	11-3/4" W., 5-3/4" ht. Extends 6-5/8". H/CTR 6-5/8".	120V NPF electronic	1 13w 4-pin Quad CFL (included). G24q-1 base. 
P7106-69STRWB	White	Ribbed, satin etched glass. Polished Brass accents.	16" W., 8-1/8" ht. Ext. 8". H/CTR 3-1/8".	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base. 
P7113-30STRWB	White	White opal glass.	11-1/2" W., 5-3/4" ht. Ext. 5". H/CTR 2-3/8".	120V NPF electronic	1 13w 4-pin Quad CFL (included). G24q-1 base. 
P7169-57EBWB	Copper Verde	Travera. Faux Tiffany art glass.	19" W., 7-3/4" ht. Ext. 4". H/CTR 3-1/4".	120V NPF electronic	1 26w 4-pin Quad CFL (included). G24q-3 base.  
P7171-10STRWB P7171-13STRWB	Polished Brass Brushed Steel	Eclipse. Satin white glass.	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V NPF electronic	1 13w 4-pin Quad CFL (included). G24q-1 base.  
P7176-33EBWB	Cobblestone	Eclipse. Faux Tiffany art glass.	15" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V NPF electronic	1 26w 4-pin Quad CFL (included). G24q-3 base.  
P7209-86STRWB	Burnished Chestnut	Savannah. Alabaster glass. Rope details. Top cover.	13" W., 7" ht. Extends 6-1/2".	120V NPF electronic	1 18w 4-pin Quad CFL (included). G24q-2 base. 

ENERGY STAR Acrylic Wall Sconces

Acrylic sconces

UL listed for damp locations



P7085-09EBWB



P7085-174EBWB



P7083-09EBWB



P7084-09EBWB



P7249-09EBWB



P7249-174EBWB



P7190-30STRWB

Product No.	Finish	Description	Size	Ballast	Lamp(s)	ADA
P7083-09EBWB	Brushed Nickel	Acrylic alabaster swirl. Top cover.	8-7/8" W., 10-5/8" ht. Extends 3-7/8". H/CTR 5-3/4".	120V NPF electronic	1 18w 4-pin Quad CFL (included). G24q-2 base.	
P7084-09EBWB	Brushed Nickel	White acrylic. Top cover.	8-3/4" W., 10-3/4" ht. Extends 3-3/8". H/CTR 5-1/2".	120V NPF electronic	1 18w 4-pin Quad CFL (included). G24q-2 base.	
P7085-09EBWB P7085-174EBWB	Brushed Nickel Urban Bronze	White acrylic. Top cover.	9-3/8" W., 10-5/8" ht. Extends 3-7/8". H/CTR 5-1/2".	120V NPF electronic	1 26w 4-pin Quad CFL (included). G24q-3 base.	
P7190-30STRWB	White	Paintable white crown molding.	14" W., 6" ht. Extends 4". H/CTR 2-3/4".	120V NPF electronic	2 13w 4-pin Quad CFL (included). G24q-1 base.	
P7249-09EBWB P7249-174EBWB	Brushed Nickel Urban Bronze	White acrylic.	10-3/8" dia. Extends 3-1/2".	120V NPF electronic	1 22w 4-pin T-9 circline (included).	



CFL Glass
Wall Sconces



P7113-30



P7090-09



P7091-09



P7106-69



P7178-10
P7178-10EB

P7171-13
P7171-13EB

Mercury and CFLs

CFLs contain a very small amount of mercury sealed within the glass tubing – an average of 5 milligrams – about the amount that would cover the tip of a ballpoint pen. By comparison, older thermometers contain about 500 milligrams of mercury. It would take 100 CFLs to equal that amount.

Mercury currently is an essential component of CFLs and is what allows the bulb to be an efficient light source. No mercury is released when the bulbs are intact or in use.

See tip on page 42 for proper CFL care and disposal hints.

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P7090-09	Brushed Nickel	Satin opal glass.	10-1/4" W., 12" ht. Extends 4". H/CTR 6".	120V NPF magnetic	2 13w 2-pin twin CFL. GX23 base.	ADA
P7091-09	Brushed Nickel	Alabaster glass.	11-3/4" W., 5-3/4" ht. Extends 6-5/8". H/CTR 2-1/4"	120V NPF magnetic	1 13w 2-pin twin CFL. GX23 base.	
P7106-69	White	Ribbed, satin-etched glass and polished brass accents	16" W., 8-1/8" ht. Extends 8". H/CTR 2-3/4"	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.	
P7113-30	White	Satin white glass.	11-1/2" W., 5-3/4" ht. Extends 5". H/CTR 2-3/8".	120V NPF magnetic	1 13w 2-pin twin CFL. GX23 base.	HPF
P7171-13	Brushed Steel	Eclipse. White opal glass.	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V HPF magnetic	1 13w 2-pin twin CFL. GX23 base.	ADA
P7171-10EB P7171-13EB	Polished Brass Brushed Steel	Eclipse. White opal glass.	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V/277V electronic	1 26w 4-pin CFL. G24q-1 base.	ADA
P7178-10	Polished Brass	Prescott Collection. Satin-etched glass.	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V HPF magnetic	1 13w 2-pin twin CFL. GX23 base.	ADA
P7178-10EB	Polished Brass	Prescott Collection. Satin-etched glass.	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V/277V HPF electronic	1 13w 4-pin Quad CFL. G24q-1 base	ADA



P7093-09



P7164-58



P7146-11
P7146-11EB



P7102-10
P7102-10EB



P7135-01



P7092-09



P7138-46EB

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P7092-09	Brushed Nickel	Satin opal glass	8" W., 10-3/4" ht. Extends 4". H/CTR 5-1/2".	120V NPF magnetic	2 13w 2-pin twin CFL. GX23 base.	ADA
P7093-09	Brushed Nickel	Clear and white glass	11-1/4" W., 11-1/4" ht. Extends 3-1/2". H/CTR 3".	120V NPF magnetic	2 13w 2-pin twin CFL. GX23 base.	ADA
P7102-10	Polished Brass	Satin opal glass	7-3/4" W., 11" ht. Extends 4". H/CTR 4-1/2".	120V HPF electronic	2 13w 2-pin twin CFL. GX23 base.	ADA
P7102-10EB	Polished Brass	Satin opal glass	7-3/4" W., 11" ht. Extends 4". H/CTR 4-1/2".	120V/277V electronic	2 13w 4-pin Quad CFL. G24q-1 base.	ADA
P7135-01	White Glass	White distressed glass. Golden Baroque & Vintage Gold ball knobs included.	8-1/4" W., 12" ht. Extends 4". H/CTR 4-3/4".	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.	ADA
P7138-46EB	Weathered Bronze	Arts & Crafts. Light honey art glass. Vertical or horizontal mounting.	5" W., 14-1/4" ht. Extends 4". H/CTR 7-1/4".	120V/277V HPF electronic	1 26w 4-pin Quad CFL. GX24q-3 base.	ADA
P7146-11	Antique Brass	Satin white glass	8" W., 12-1/4" ht. Extends 4". H/CTR 3-3/4".	120V HPFw	2 13w 2-pin twin CFL. GX23 base.	ADA
P7146-11EB	Antique Brass	Satin white glass	8" W., 12-1/4" ht. Extends 4". H/CTR 3-3/4".	120V/277V HPF electronic	2 13w 4-pin Quad CFL. G24q-1 base.	ADA
P7164-58	Textured Slate	Etched seeded glass	13" W., 11" ht. Extends 4". H/CTR 3-3/4".	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.	ADA

Wall Pockets™

The Wall Pockets System

Step 1

Select a recessed wall box or surface mount backplate.

Step 2

Choose a diffuser option. Once installed, the cost of future renovation is greatly reduced. Simply select a new “Wall Pocket” diffuser and mount onto existing recessed wall box or backplate.



Wall Pockets™ Light Source

Surface Mount Backplate


- Provides the light source for “Wall Pocket” diffusers.
- Can be horizontally or vertically mounted.
- Covers outlet box.
- Can be mounted directly to an outlet box.

Recessed Wall Box

- Provides the light source for “Wall Pocket” diffusers
- Can be horizontally or vertically mounted, except P3-TGEM which is horizontal mount only.
- UL listed for contact with insulation and damp locations.
- Helps to eliminate lamp image in diffuser.
- An accessible internal splice compartment is included.
- Electrical components are protected inside box.
- For new construction or remodel projects.
- Optional hanger bars, P8716-01, available for ease of installation. (See Progress Catalog 128)




P3-TG




P3-TGEM



P5-TG



P7200-30/P7200-30EB



P7200-30STRWB

Product No.	Description	Size	Ballast	Lamp(s)
P3-TG	Recessed wall box*	7-5/8" L., 4-7/8" W. 3-1/2" depth	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.
P3-TGEM	Recessed wall box* with emergency	7-5/8" L., 4-7/8" W. 3-1/2" depth	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.
P5-TG	Recessed wall box*	7-5/8" L., 4-7/8" W. 3-1/2" depth	120V/277V HPF electronic	1 26, 32, or 42w 4-pin triple tube CFL. GX24q-3/4 base.
P7200-30	Surface mount backplate*	7-3/4" L., 4-3/4" W. Extends 2-1/2".	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.
P7200-30EB	Surface mount backplate*	7-3/4" L., 4-3/4" W. Extends 2-1/2".	120V/277V HPF electronic	2 13w 4-pin Quad CFL. G24q-1 base.
P7200-30STRWB	Energy Star surface mount backplate*	7-5/8" W., 4-3/4" L. 2-1/2" depth	120V NPF electronic	2 13w 4-pin Quad CFL. G24q-1 base. (included)

Mercury Facts

The Scoop on Mercury & CFLs

- CFL mercury content: <5mg
- Mercury deposited from CFL energy*: 2.4 mg
- Total mercury from CFLs: 7.4mg
- Mercury deposited from incandescent*: 10 mg

* Mercury added to the environment over a 5-year period as a result of electricity generated from a coal fired power plant.

*Backplates and Recessed Boxes must be used with Decorative Wall Pockets Diffusers.



Wall Pockets™ Diffusers

Product No.	Finish	Description	Mounting	Size
P7107-09	Brushed Nickel	Traditional wall pocket with decorative fabric shade	Horizontal	14-1/2" W., 25-1/2" ht. ADA Extends 4". H/CTR 14-1/8".
P7120-30	White	Tri-band metal louvered sconce. Provides "up/down" illumination.	Horizontal	14" W., 7" ht. ADA Extends 4". H/CTR 3-1/4".
P7121-60	Opal White	Acrylic wall pocket. Provides direct/indirect illumination.	Horizontal	16" W., 8" ht. ADA Extends 3-3/4". H/CTR 3".
P7150-10 P7150-57	Polished Brass Copper Verde	Satin opal glass wall sconce. Provides direct/indirect illumination.	Vertical	7-3/4" W., 11" ht. ADA Extends 4". H/CTR 4-1/2".
P7151-51	Faux Alabaster	Quarter sphere wall sconce. Provides direct/indirect illumination	Horizontal	17-1/4" W., 8-3/4" ht. ADA Extends 4". H/CTR 2-7/8".
P7152-47	Sandstone	Satin white acrylic wall pocket w/decorative sandstone banding.	Horizontal	19" W., 9-1/2" ht. ADA Extends 4". H/CTR 2-3/8".
P7166-10	Polished Brass	Opalescent white acrylic quarter sphere. Stepped-off wall to provide halo effect. Provides direct/indirect illumination.	Horizontal	16-1/2" W., 8-1/4" ht. ADA Extends 3-7/8". H/CTR 3".
P7195-51	Faux Alabaster	Bevel-cut diffuser. Provides direct/indirect illumination.	Horizontal	15-1/2" W., 7" ht. ADA Extends 4". H/CTR 2-7/8".



P7152-47



P7195-51



P7120-30

Wall Pockets Diffusers must be used with Surface Mount Backplate or Recessed Wall Box.

CFL Wall Sconces

Caring for CFLs


CFLs are made of glass and can break if dropped or roughly handled. Be careful when removing the bulb from its packaging, installing it, or replacing it. Always screw and unscrew the lamp by its base (not the glass).

If a CFL breaks in your home, go to energystar.gov for clean up details. Used CFLs should always be disposed of properly.

EPA recommends that consumers take advantage of available local recycling options for compact fluorescent light bulbs. EPA is working with CFL manufacturers and major U.S. retailers to expand recycling and disposal options. Consumers can contact their local municipal solid waste agency directly, or go to www.epa.gov/bulbrecycling or www.earth911.org to identify local recycling options.



P7111-30



P7110-30



P7190-30
P7190-30EB



P7104-30

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P7104-30	White	Tri-band louver. Provides illumination from top, bottom and between louvers.	14" W., 7" ht. Extends 7". H/CTR 2-1/4".	120V HPF magnetic	2 13w 2-pin twin CFL. GX23 base.	
P7110-30	White	White acrylic diffuser.	4-1/2" W., 12" ht. Extends 4". H/CTR 6-1/4".	120V NPF magnetic	1 13w 2-pin twin CFL. GX23 base.	ADA, HPF
P7111-30	White	White acrylic diffuser.	7-1/2" W., 12" ht. Extends 4". H/CTR 6-1/2".	120V NPF magnetic	2 13w 2-pin twin CFL. GX23 base.	ADA, HPF
P7190-30	White	Wood crown moulding. Paintable.	14" W., 6" ht. Extends 4". H/CTR 2-3/4".	120V NPF magnetic	2 13w 2-pin twin CFL. GX23 base.	ADA, HPF
P7190-30EB	White	Wood crown moulding. Paintable.	14" W., 6" ht. Extends 4". H/CTR 2-3/4".	120V/277V HPF electronic	2 13w 4-pin Quad CFL. G24q-1 base	ADA

LED Step & Wall Lights

P6827 and P6828 LED step/wall lights are available in a vertical or horizontal configuration for mounting into a single-gang wallbox

CUL-UL listed for dry locations

Integral dimmable power module in a compact package

Consume only 5w of power per fixture.

Lumen output comparable to 7w CFL and 25w incandescent

Warm white 2700K LED's included

CRI: 76

Beam spread: 120 degrees



P6827-09



P6828-09



P6828-30

Product No.	Finish	Description	Size	Lamp
P6827-09 P6827-30	Brushed Nickel White	Mini horizontal step/wall light	5-1/4" W. 3-1/2" ht.	5w LED (included). CRI:76
P6828-09 P6828-30	Brushed Nickel White	Mini vertical step/wall light	3-1/2" W. 5-1/4" ht.	5w LED (included). CRI:76



P6829-09



P6829-20



P6829-30



P6829-31

Product No.	Finish	Description	Size	Lamp
P6829-09 P6829-20 P6829-30 P6829-31	Brushed Nickel Antique Bronze White Black	Mini vertical step/wall light	2-7/8" W. 4-1/2" ht.	5w LED (included). CRI:76

See more Everlume LED fixtures throughout this catalog.

P6829 LED step/wall lights provide an attractive solution for a variety of illumination tasks

CUL-UL listed for outdoor as well as indoor applications

Integral dimmable power module in a compact package

Consume only 5w of power per fixture

Lumen output comparable to 7w CFL and 25w incandescent

Warm white 2700K LED's included

CRI: 76

Beam spread: 120 degrees



Step Lights

Brick Lights Outdoor & Indoor

Lighting for safety in traffic areas.




P6802-31
P6805-31

Cast aluminum housing with aluminum louver.

Three 1/2" I.P. conduit entries.

For brick, masonry, poured concrete and wood stud installations.

UL listed for wet locations.



Indoor & Protected Outdoor



P6821-30


Spring-held louver faceplate.

Metal housing has 1/2" I.P. conduit entry.

For indoor and protected outdoor use.

UL listed for damp locations.

Sheet rock or dry wall installations.



Thru-Wall Double Face



P6824-30
P6825-30

One metal housing with two shatter-resistant white acrylic faceplates for both sides of a stud wall, 3-1/2" to 4-1/2" thick.

White trim.

Reduces costs by illuminating two areas with one fluorescent light.


For indoor and protected outdoor use.

UL listed for damp locations.

Sheet rock or dry wall installations.

*Requires accessory bar hanger kit, P8716-01 for installation to wood studs.

U.S. Patent #: 6357891, 5379199



Product No.	Finish	Size	Lamp(s)
P6802-30	White	See drawing.	One 7w twin CFL.
P6802-31	Black		
P6805-31	Black	See drawing.	One 13w 4-ppin twin CFL GX24q-1 base.
P6821-30	White	See drawing.	One 7w or 9w twin CFL
P6824-30	White	See drawing. Shatter-resistant white faceplate	One 7w or 9w twin CFL
P6825-30*	White	See drawing. Two-louver faceplate	One 7w or 9w twin CFL
P6826-30	White	See drawing. Shatter-resistant white faceplate	One 7w or 9w twin CFL

Track

Compact Fluorescent Wall Washer

Specular, parabolic baffle louver with specular aluminum reflector

120V electronic HPF ballast standard

Emits a wide distribution of light on vertical space.



Product No.	Finish	Size	Lamp(s)
P9210-28	Bright White	12-1/4" L., 5" W., 7-1/4" ht.	Two 18w 4-pin CFL. 2G11 base
P9211-28	Bright White	14-1/4" L., 5" W., 7-1/4" ht.	Two 24w or 27w long 4-pin twin CFL. 2G11 base
P9212-28 P9212-31	Bright White Black	18" L., 5" W., 7-1/4" ht.	Two 36w or 39w long 4-pin twin CFL. 2G11 base

More CFL Facts

You might have heard that CFLs use a lot of energy when turning on and off. While there is a brief surge in every use when a CFL is turned on, with today's starting technology, that surge usually lasts about one tenth of a second and consumes about as much as five seconds of normal operations.

Use ENERGY STAR CFLs in fixtures that are hard to reach, such as ceiling fixtures and enclosed outdoor fixtures. Because CFLs last longer, you enjoy the convenience of buying and changes bulbs less frequently.

CFLs cost a bit more than an incandescent, but use about a quarter as much energy and last many times longer (usually around 10,000 hours). It is estimated that a CFL pays for its higher price after about 500 hours of use. Also, because CFLs release less heat, not only are they safer, but your cooling load is less in the summer.

Shop Wise

Get more at the grocery store: Buying in bulk can keep money in your pocket and can also help reduce shipping and packaging waste.

When buying packaged products, seek out those that use less packaging.

When asked "Paper or Plastic?", say "Neither." Buy a reusable, durable cloth bag instead.

Energy Saving LED Exit Signs and Emergency Fixtures

Fixtures are constructed of injection-molded plastic with soft round corners.

LED lamps provide maximum energy savings.

The included battery provides 1-1/2 hours of emergency illumination.

UL listed for damp locations.

LED Exit Sign

Integral emergency battery pack.

Includes 2nd face for unit to be used as a single or double face sign.

Top, end, or surface mount.



Product No.	Finish	Size
PE001-30	White with red letters	12-1/4" W., 5-5/8" ht. Extends 2-1/2". 120/277 VAC
PE002-30	White with green letters	



PE001-30



PE002-30

Combo LED Exit Sign/ Emergency Fixture

Integral emergency battery pack.

Includes 2nd face for unit to be used as a single or double face sign. End or surface mount.

Emergency fixture portion includes 2 x 5.4w incandescent lamps.


Product No.	Finish	Size
PE003-30	White with red letters	14-5/8" W., 13-3/8" ht. Extends 5-1/8". 120/277 VAC
PE004-30	White with green letters	



PE004-30



PE003-30



Avalon

Brushed Nickel finish
Damp location listed



P3153-09EBWB



P3154-09EBWB



P3155-09EBWB



P3156-09EBWB

Product No.	Finish	Description	Size	Lamp(s)
P3153-09EBWB	Brushed Nickel	One-light	7-3/4" W. 12" ht. Extends 8-3/4".	1 self-ballasted 13w spiral CFL (included). GU24 base
P3154-09EBWB	Brushed Nickel	Two-light	18" W., 7-1/4" ht. Extends 8-3/4".	2 self-ballasted 13w spiral CFL (included). GU24 base
P3155-09EBWB	Brushed Nickel	Three-light	24" W., 7-1/4" ht. Extends 8-3/4".	3 self-ballasted 13w spiral CFL (included). GU24 base
P3156-09EBWB	Brushed Nickel	Four-light	36" W., 7-1/4" ht. Extends 8-3/4".	4 self-ballasted 13w spiral CFL (included). GU24 base



See pages 15 and 23 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.

Savannah

Burnished Chestnut finish
Damp location listed



P3159-86EBWB



P3158-86EBWB

Product No.	Finish	Description	Size	Lamp(s)
P3158-86EBWB	Burnished Chestnut	Two-light	16-1/4" W., 9-1/8" ht. Extends 9".	2 self-ballasted 13w spiral CFL (included). GU24 base
P3159-86EBWB	Burnished Chestnut	Three-light	25-1/4" W., 9-1/8" ht. Extends 9".	3 self-ballasted 13w spiral CFL (included). GU24 base



See pages 16 and 24 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.

These fixtures mount up or down.



P3187-09EBWB






P3188-09EBWB

Bedford

Brushed Nickel finish
Etched alabaster glass
Damp location listed



P3186-09EBWB

Product No.	Finish	Description	Size	Lamp(s)
P3186-09EBWB	Brushed Nickel	One-light	5-5/8" W., 9-1/4" ht. Extends 7-5/8".	1 self-ballasted 13w spiral CFL (included). GU24 base. 
P3187-09EBWB	Brushed Nickel	Two-light	14-5/8" W., 8-3/4" ht. Extends 6-1/2".	2 self-ballasted 13w spiral CFL (included). GU24 base. 
P3188-09EBWB	Brushed Nickel	Three-light	17" W., 8-3/4" ht. Extends 9-1/2".	3 self-ballasted 13w spiral CFL (included). GU24 base. 



See page 17 of this catalog for matching CFL fixtures and Progress Lighting Catalog 128 for matching incandescent fixtures.



P7141-46EB



P7140-46EB



P7139-46EB

These fixtures are wall mount only

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P7139-46EB	Weathered Bronze	Two-light	28-1/2" W., 5" ht. Extends 4".	120V HPF electronic	2-F17T8 linear fluorescent ADA
P7140-46EB	Weathered Bronze	Two-light	40-1/2" W., 5" ht. Extends 4".	120V HPF electronic	2-F25T8 linear fluorescent ADA
P7141-46EB	Weathered Bronze	Two-light	52-1/2" W., 5" ht. Extends 4".	120V HPF electronic	2-F32T8 linear fluorescent ADA

* Can mount horizontally or vertically. Light honey glass on all sides.

Arts & Crafts

Weathered Bronze finish
Damp location listed



See Progress Lighting Catalog 128 for matching incandescent fixtures.

Bath Time

Take shorter showers and install a water-conserving showerhead. Showers are responsible for up to one-fifth of the water used in a typical household.



Melon Bath Bars

White acrylic melon diffuser.



P2896-15EBWB







P2897-15EBWB



P2898-15EBWB



P2899-15EBWB

Product No.	Finish	Size	Lamp(s)
P2896-15EBWB	Polished Chrome	12" L., 4-1/2" ht. Extends 9".	1 self-ballasted 13w spiral CFL (included). GU24 base. 
P2897-15EBWB	Polished Chrome	24" L., 4-1/2" ht. Extends 9".	2 self-ballasted 13w spiral CFL (included). GU24 base. 
P2898-15EBWB	Polished Chrome	36" L., 4-1/2" ht. Extends 9".	3 self-ballasted 13w spiral CFL (included). GU24 base. 
P2899-15EBWB	Polished Chrome	48" L., 4-1/2" ht. Extends 9".	4 self-ballasted 13w spiral CFL (included). GU24 base. 


Damp location listed.

Slim Profile

White acrylic diffuser mounts horizontally or vertically and snaps in place

White end caps


Wall mount only






P7096-30EB



P7095-30EB




P7094-30EB

Product No.	Finish	Size	Ballast	Lamp(s)
P7094-30EB	White	25-5/8" L., 4-3/4" ht. Extends 4".	120V NPF electronic	2-F17T8 ADA 
P7095-30EB	White	37-5/8" L., 4-3/4" ht. Extends 4".	120V NPF electronic	2-F25T8 ADA 
P7096-30EB	White	49-5/8" L., 4-3/4" ht. Extends 4".	120V NPF electronic	2-F32T8 ADA 

Damp location listed



P7229-09EB



P7228-09EB



P7227-88EB

Contemporary Acrylic ENERGY STAR

Metal end caps.

Product No.	Finish	Size	Ballast	Lamp(s)
P7227-09EB P7227-88EB	Brushed Nickel Heirloom	25-1/4" L., 5-1/4" ht. Extends 4-1/4".	120V NPF electronic	2-F17T8
P7228-09EB P7228-88EB	Brushed Nickel Heirloom	37-1/4" L., 5-1/4" ht. Extends 4-1/4".	120V NPF electronic	2-F25T8
P7229-09EB P7229-88EB	Brushed Nickel Heirloom	49-1/4" L., 5-1/4" ht. Extends 4-1/4".	120V NPF electronic	2-F32T8


Damp location listed.



P7235-88EB



P7234-88EB




P7233-88EB

Open Round Acrylic ENERGY STAR

Metal end caps.

Product No.	Finish	Size	Ballast	Lamp(s)
P7233-88EB	Heirloom	24-1/2" L., 5" ht. Extends 4".	120V NPF electronic	2-F17T8 ADA
P7234-88EB	Heirloom	36-1/2" L., 5" ht. Extends 4".	120V NPF electronic	2-F25T8 ADA
P7235-88EB	Heirloom	48-1/2" L., 5" ht. Extends 4".	120V NPF electronic	2-F32T8 ADA


Damp location listed.



P7232-15EB



P7231-15EB



P7230-15EB

Metal Edge Acrylic

Metal end caps.




Product No.	Finish	Size	Ballast	Lamp(s)
P7230-15EB	Polished Chrome	24-1/2" L., 5-1/4" ht. Extends 3-1/4".	120/277V HPF electronic	2-F17T8
P7231-15EB	Polished Chrome	36-1/2" L., 5-1/4" ht. Extends 3-1/4".	120/277V HPF electronic	2-F25T8
P7232-15EB	Polished Chrome	48-1/2" L., 5-1/4" ht. Extends 3-1/4".	120/277V HPF electronic	2-F32T8

Damp location listed.

Shell End Bracket

Ribbed-etched acrylic lens

Wall mount only

Product No.	Finish	Size	Ballast	Lamp(s)
P7197-30EB	Textured White	25" L., 5-1/4" ht. Extends 4-1/2".	120V HPF electronic	2-F17T8 
P7198-30EB	Textured White	37" L., 5-1/4" ht. Extends 4-1/2".	120V HPF electronic	2-F25T8 
P7199-10EB	Polished Brass	49" L., 5-1/4" ht.	120V HPF	2-F32T8 
P7199-30EB	Textured White	Extends 4-1/2".	electronic	

Damp location listed







Squared Bracket

Extruded ribbed white acrylic diffuser and white end caps

Knockout for G.C.O. and switch

Mount horizontally or vertically

Wall mount only

Product No.	Finish	Size	Ballast	Lamp(s)
P7128-30EB	White	24-3/8" L., 4-5/8" ht. Extends 4".	120V NPF electronic	1-F17T8 
P7129-30EB	White	24-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	2-F17T8 
P7130-30EB	White	36-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	1-F25T8 
P7131-30EB	White	36-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	2-F25T8 
P7132-30EB	White	48-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	1-F32T8 
P7133-30EB	White	48-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	2-F32T8 



Damp location listed

Crown Moulding


White acrylic diffuser and white trim

Provides up lighting

Wall mount only

Product No.	Size	Ballast	Lamp(s)
P7160-30EB	28-13/16" L., 5" ht. Extends 5-3/4".	120V HPF electronic	2-F17T8 
P7162-30EB	52-13/16" L., 5" ht. Extends 5-3/4".	120V HPF electronic	2-F32T8 


Damp location listed.




Toilet Tips
 Replace your old toilet with a new, low-flow model. In many communities, your local utility company offers rebates to help offset the cost of a new, water-saving toilet.
 Already used extensively outside of North America, dual-flush toilets are an innovative technology. A simple concept, dual-flush toilets use a full 1.6 gallon flush for solids and a reduced volume, 1.1 gallon flush for liquids.



P7116-60EB



P7115-60EB






P7114-60EB

Soft Clouds

White acrylic diffusers mount horizontally or vertically

Provide light out and down

Wall mount only

Product No.	Finish	Size	Ballast	Lamp(s)
P7114-60EB	White	26-3/4" L., 6" ht. Extends 4-1/4".	120V HPF electronic	2-F17T8 
P7115-60EB	White	38-3/4" L., 6" ht. Extends 4-1/4".	120V HPF electronic	2-F25T8 
P7116-60EB	White	50-3/4" L., 6" ht. Extends 4-1/4".	120V HPF electronic	2-F32T8 

Damp location listed.



PV008-30WB



PV008-74WB



PV008-09WB



PV008-15WB

Product No.	Finish	Size	Ballast	Lamp(s)
PV008-09WB	Brushed Nickel	Fan: 13-1/2" dia.	120V NPF electronic	Two 13w 4-pin spiral CFL (incl.) GX24q-1 base.
PV008-15WB	Polished Chrome	Back box: 8-1/4" L.		
PV008-30WB	White	7-3/4" W., 6-1/4" ht.		
PV008-74WB	Venetian Bronze			

Decorative Bath Fan

Decorative Bath/Exhaust Fan/Light Combination Units

Round decorative design with frosted low-profile melon glass

Smooth finish for easy cleaning

Damp location listed

Exhaust fans for residential vent fan application

70cfm fans provide general exhaust ventilation for most room sizes

Fans are shipped so that the galvanized fan housing can be installed prior to the motor/grille assembly

Fans can be ceiling or wall mounted


Sound level rating 3.5 Sones

4" duct adapter


Surface Mount Linear Fluorescent

For kitchen, bath, laundry, workshop or family area

UL listed for damp locations

Product No.	Finish	Size	Ballast	Lamp(s)
P7258-09EB	Brushed Nickel w/white acrylic	48-1/2" L.,	120V NPF	3-32w T-8
P7258-174EB	Urban Bronze w/white acrylic	11-5/8" W., Extends 4-1/2".	electronic	

Product No.	Finish	Size	Ballast	Lamp(s)
P7225-09EB	Brushed Nickel w/etched glass & nickel caps	25-5/8" L., 8-1/8" W., Extends 4-1/8".	120V NPF electronic	2-13w T-5
P7226-09EB	Brushed Nickel w/etched glass & nickel caps	37-5/16" L., 13" W., Extends 4-5/8".	120V NPF electronic	2-21w T-5



P7258-174EB



P7226-09EB



P7225-09EB

Surface Mount Circline Fluorescent

White acrylic diffuser

For kitchen, bath, laundry, workshop or family area

UL listed for damp locations

Product No.	Finish	Size	Ballast	Lamp(s)
P7249-09EBWB	Brushed Nickel	10-3/8" dia.,	120V NPF	1-22w T-9
P7249-174EBWB	Urban Bronze	3-1/2" ht.	electronic	included
P7250-09EBWB	Brushed Nickel	17-5/8" dia.,	120V NPF	1-22w T-9 &
P7250-174EBWB	Urban Bronze	4-1/2" ht.	electronic	1-32w T-9 (incl)
P7251-09EBWB	Brushed Nickel	32-1/2" L.,	120V NPF	2-32w T-9
P7251-174EBWB	Urban Bronze	18" W., 4-3/8" ht.	electronic	included
P7252-09EBWB	Brushed Nickel	31-1/4" dia.,	120V NPF	3-32w T-9
P7252-174EBWB	Urban Bronze	6-1/2" ht.	electronic	included



P7252-09EBWB



P7250-174EBWB



P7251-174EBWB



P7249-09EBWB

Emergency Battery Pack

P8698-01 Emergency fluorescent ballast accessory for remote mounting.

Operates 2' - 4' single bi-pin T8 and T12 fluorescent lamps, 17w to 40w.

Can be mounted in wireway or on top of the fixture. Includes test switch and charge indicator accessory kit.

Emergency Operating Time: 90 minutes

Input Voltage: 120/277V, 60Hz

Initial Illumination: (1) lamp up to 700 Lumens

Operating temp: 0° to 55° C

UL and CUL Listed




P8698-01

Domes


Contoured white acrylic domes with curved, textured white molding. Floats 3/4" from ceiling, creating a halo effect.



P7205-30EB



P7206-30EB



Product No.	Finish	Size	Ballast	Lamp(s)
P7205-30EB	White	36" dia. 7-1/8" ht.	120V HPF electronic	2-FB32T8
P7206-30EB	White	59" L., 21" W. 6-5/8" ht.	120V HPF electronic	4-F32T8

Soft Clouds

Contoured, white acrylic clouds. Diffuser suspended from white chassis.



P7278-60EB



P7279-60ES
P7279-60EB



P7285-60EB

Product No.	Finish	Size	Ballast	Lamp(s)
P7278-60EB	White	28" L., 18" W., 4-5/8" ht.	120V HPF electronic	4-F17T8
P7279-60EB	White	52" L., 12" W., 4-5/8" ht.	120V HPF electronic	2-F32T8
P7279-60ES	White	52" L., 12" W., 4-5/8" ht.	120V HPF electronic	2-F34T12
P7280-60EB	White	52" L., 18" W., 4-5/8" ht.	120V HPF electronic	4-F32T8
P7280-60ES	White	52" L., 18" W., 4-5/8" ht.	120V HPF electronic	4-F34T12
P7285-60EB	White	30-3/4" L., 27-1/4" W., 5" ht.	120V HPF electronic	2-FB32T8



P7186-30EB



P7183-30EB

Wrap-Arounds

Clear prismatic acrylic diffuser, squared white end caps and white chassis.

General utility fluorescents for individual or continuous run ceiling mounting.


Tube Talk

'T' lamps are commonly used for kitchen and other ceiling fixtures. The 'T' stands for the tubular shape of the lamp. The number following the T gives the diameter in eighths of an inch. Example: A T8 lamp is 8/8" or 1" in diameter.

Product No.	Finish	Size	Ballast	Lamp(s)
P7183-30	White	24" L., 7-3/4" W., 3" ht.	120V NPF electronic	2-F20T12
P7183-30EB	White	24" L., 7-3/4" W., 3" ht.	120V HPF electronic	2-F17T8
P7186-30ES	White	48" L., 7-3/4" W., 3" ht.	120V HPF magnetic	2-F34T12
P7186-30EB	White	48" L., 7-3/4" W., 3" ht.	120V HPF electronic	2-F32T8
P7196-30EB	White	48" L., 15-5/8" W., 3" ht.	120V HPF electronic	4-F32T8

Wood Frame

Square wood frame suspended from surface-mounted white chassis. White acrylic diffuser.



Trim No.	Finish	Chassis	Size	Ballast	Lamp(s)
P7273-30	White	P7213-30EB	26-1/2" L., 26" W.,	120V HPF	2-FB32T8
P7273-35	Natural Oak	P7213-30EB	4-1/4" ht.	electronic	
P7274-30	White	P7214-30EB	50-1/2" L., 15" W.,	120V HPF	2-F32T8
P7274-35	Natural Oak	P7214-30EB	4-1/4" ht.	electronic	
P7275-30	White	P7215-30EB	50-1/2" L., 18" W.,	120V HPF	4-F32T8
P7275-35	Natural Oak	P7215-30EB	4-3/4" ht.	electronic	
P7276-30	White	P7216-30EB	50-1/2" L., 26-1/2" W.,	120V HPF	4-F32T8
P7276-35	Natural Oak	P7216-30EB	4-1/4" ht.	electronic	



P7273-30



P7275-30



P7274-35

Drop Opal in Oak Frame

Natural finished oak.
Soft white acrylic diffuser.
Frame suspended from surface mounted white chassis.

Product No.	Finish	Size	Ballast	Lamp(s)
P7286-35EB	Oak	25-3/4" L., 25-1/4" W., 4-3/4" ht.	120 V HPF electronic	2-FB32T8
P7287-35EB	Oak	49-1/2" L., 11" W., 4-3/4" ht.	120V HPF electronic	2-F32T8
P7288-35EB	Oak	49-1/2" L., 17" W., 4-3/4" ht.	120V HPF electronic	4-F32T8




P7288-35EB

Oak Finish Grid

White acrylic diffuser.
Frame suspended from surface mounted white chassis. Lift and Shift Access: the diffuser grid assembly is easily removed for cleaning and lamp replacement. No need to remove the entire frame.


Product No.	Finish	Size	Ballast	Lamp(s)
P7334-35EB	Oak	49-1/2" L., 11-1/8" W., 4-3/8" ht.	120V HPF electronic	2-F32T8
P7335-35EB	Oak	25-7/8" L., 25-1/4" W., 4-3/8" ht.	120V HPF electronic	2-FB32T8
P7336-35EB	Oak	49-1/2" L., 17-1/8" W., 4-3/8" ht.	120V HPF electronic	4-F32T8



P7336-35EB

White Finish

White vinyl on metal.
White acrylic diffuser suspended from surface mounted white chassis.



Product No.	Finish	Size	Ballast	Lamp(s)
P7262-30EB	White	24-1/2" L., 24-1/2" W., 4-1/2" ht.	120V HPF electronic	2-FB32T8
P7263-30EB	White	49" L., 12-1/2" W., 4-1/2" ht.	120V HPF electronic	2-F32T8
P7264-30EB	White	49" L., 16" W., 4-1/2" ht.	120V HPF electronic	4-F32T8



P7262-30EB







P7263-30EB

Fluorescent Strips

T-8 fluorescent strips for utility, closet, garage or general lighting.






Product No.	Finish	Size	Ballast	Lamp(s)
P7265-30EB	White	24" L., 3" W. Extends 3-1/4"	120V NPF electronic	1-17w T-8 
P7266-30EB	White	24-1/4" L., 4-1/4" W. Extends 3-1/4"	120V NPF electronic	2-17w T-8 
P7267-30EB	White	48" L., 4-1/2" W. Extends 3-1/4"	120V NPF electronic	1-32w T-8 
P7268-30EB	White	48" L., 3" W. Extends 3-1/2"	120V NPF electronic	2-32w T-8 

Slim Line Wrap

Acrylic diffuser with white end caps. For kitchens, laundry rooms and work areas.



Product No.	Finish	Size	Ballast	Lamp(s)
P7137-30STR	White	26-3/4" L., 6-1/4" W., 2-1/2" ht.	120V NPF electronic	2-F17T8 
P7154-30STR	White	38-3/4" L., 6-1/4" W., 2-1/2" ht.	120V NPF electronic	2-F25T8 
P7189-30STR	White	50-5/8" L., 6-1/4" W., 2-1/2" ht.	120V NPF electronic	2-F32T8 

Closet Lights

White acrylic diffuser with white metal housing. Can be mounted directly to junction box.



Product No.	Finish	Size	Ballast	Lamp(s)
P7201-30WB	White	18-1/4" L., 4" W., 1-3/8" ht.	120V NPF magnetic	1-15w T8 (included)
P7202-30WB	White w/pull chain	18-1/4" L., 4" W., 1-3/8" ht.	120V NPF magnetic	1-15w T8 (included)

Clean and Green

Buy cleaning products in concentrated form. You will be using less packaging than with a non-concentrated version.

Buy a front-loading washer instead of a top-loading one and save both energy and water.

See page 74 for emergency battery pack

HIDE-a-Lite³

The Hide-a-Lite 3 system is the premier direct-wire linkable solution for undercabinet lighting. Utilizing a low profile direct-wire junction box (P8740) that acts as the heart of the HAL3 system, the undercabinet fixtures can easily be linked together with the Quick-Link cables (P8733-P8740) to form a complete and flexible undercabinet solution.

Linkable and **low-profile**, with high brightness T-5 lamps.

Integral on/off rocker switch, and a white acrylic diffuser.

Available in **4 lengths**, they can be linked together with the HAL3 Quick-link cables (P8735-P8738). The P8740 hardwire junction box must be used to power the HAL3 T-5 fluorescent products.

Lamping

Each fixture includes a T-5 fluorescent lamp that has a 10,000 hr. average lamp life and 3000K color temperature.

Construction





Extruded aluminum housing with a white acrylic diffuser.



Mounting and Installation

Slotted holes allow easy mounting through housing. Tool-less electrical compartment entry.

UnderCabinet T-5 Fluorescent Strips



Product No.	Finish	Description	Size	Lamp(s)	
P7020-30EBWB	White	8w T5 linkable	12" L., 3-1/4" W., 1-1/8" ht.	1-F8T5 (included)	
P7021-30EBWB	White	13w T5 linkable	21" L., 3-1/4" W., 1-1/8" ht.	1-F13T5 (included)	
P7022-30EBWB	White	8w and 13w T5 linkable	34" L., 3-1/2" W., 1-1/8" ht.	1-F8T5 and 1-F13T5 (included)	
P7023-30EBWB	White	Two 13w T5 linkable	42" L., 3-1/4" W., 1-1/8" ht.	2-F13T5 (included)	



P8733-30 White
12" Undercabinet fixture linking cable.
Size: 3/4" W., 3/8" ht. 12" L.

P8735-30 White
6" Undercabinet fixture linking cable.
Size: 3/4" W., 3/8" ht. 6" L.

P8737-30 White
18" Undercabinet fixture linking cable.
Size: 3/4" W., 3/8" ht. 18" L.

P8738-30 White
24" Undercabinet fixture linking cable.
Size: 3/4" W., 3/8" ht. 24" L.

P8740-30 White HAL3 junction box.
Size: 3-1/4" W., 7/8" ht. 3-1/2" L.

P8743-30 White
Coupling cable to connect two linking cables together.
Size: .75" W., .5" ht. 6" L.

Undercabinet Fluorescents

Trim, energy efficient fluorescents mount easily under cabinets and shelves, over a desk, in kitchens or any work area.

All have a white acrylic diffuser and white baked enamel housing.

For units wired to a wall switch, select models without a rocker switch.



P7000-30



P7017-30



P7006-30

Task Force

Use task lighting instead of brightly lighting an entire room, focus the light where you need it. For example, use fluorescent undercabinet lighting for kitchen sinks and countertops and save energy, too.

Product No.	Finish	Size	Ballast	Rocker Switch	G.C.O.	Lamp(s)
P7000-30	White	12-7/8" L., 5" W., 1-1/8" ht.	120V NPF	Yes	K.O.	1-F8T5
P7004-30	White	12-7/8" L., 5" W., 1-1/8" ht.	120V NPF	K.O.*	K.O.	1-F8T5
P7010-30	White	21-1/4" L., 5" W., 1-1/8" ht.	120V NPF	Yes	K.O.	1-F13T5
P7010-30EB	White	21-1/4" L., 5" W., 1-1/8" ht.	120V/277V HPF electronic	Yes	K.O.	1-F13T5 MTO
P7011-30	White	21-1/4" L., 5" W., 1-1/8" ht.	120V NPF	K.O.*	K.O.	1-F13T5
P7011-30EB	White	21-1/4" L., 5" W., 1-1/8" ht.	120V/277V HPF electronic	K.O.*	K.O.	1-F13T5 MTO
P7014-30	White	24-1/2" L., 5" W., 1-1/8" ht.	120V NPF	K.O.*	K.O.	2-F8T5
P7015-30	White	33-1/2" L., 5" W., 1-1/8" ht.	120V NPF	K.O.*	K.O.	1-F8 & 1-F13T5
P7016-30	White	42-3/8" L., 5" W., 1-1/8" ht.	120V NPF	K.O.*	K.O.	2-F13T5

*Knockout for rocker switch

Product No.	Finish	Size	Ballast	Rocker Switch	G.C.O.	Lamp(s)
P7017-30	White	18-3/8" L., 4" W., 1-5/8" ht.	120V NPF	Yes	K.O.	1-F15T8
P7018-30	White	18-3/8" L., 4" W., 1-5/8" ht.	120V NPF	K.O.*	K.O.	1-F15T8
P7019-30WB**	White	18-3/8" L., 4" W., 1-5/8" ht.	120V NPF	Yes	—	1-F15T8

*Knockout for on/off switch

**Includes 6 foot cord, plug and lamp.

Product No.	Finish	Size	Ballast	Rocker Switch	G.C.O.	Lamp(s)
P7006-30	White	18" L., 5-1/4" W., 1-3/4" ht.	120V NPF	K.O.*	K.O.	1-F15T12
P7007-30	White	24" L., 5-1/4" W., 1-3/4" ht.	120V NPF	K.O.*	K.O.	1-F20T12
P7007-30EB	White	24" L., 5-1/4" W., 1-3/4" ht.	120V NPF electronic	K.O.*	K.O.	1-F17T8
P7008-30	White	36" L., 5-1/4" W., 1-3/4" ht.	120V NPF	K.O.*	K.O.	1-F30T12
P7008-30EB	White	36" L., 5-1/4" W., 1-3/4" ht.	120V/277V HPF electronic	K.O.*	K.O.	1-F25T8
P7009-30	White	48" L., 5-1/4" W., 1-3/4" ht.	120V NPF	K.O.*	K.O.	1-F34T12
P7009-30EB	White	48" L., 4-1/2" W., 1-3/4" ht.	120V/277V HPF electronic	K.O.*	K.O.	1-F32T8

*Knockout for rocker switch

MTO Made to order



LED Cove Lighting

Cove lighting creates a soft indirect lighting that enhances the feel of any space by providing an additional layer of light and a sense of height and openness.

The typical applications include ledges, valences, or horizontal recessed areas on an upper wall or ceiling of a space.

See more Everlume LED fixtures throughout this catalog.

Fanciful and Practical

Most kitchens require constant illumination, so it makes sense to seek out high-efficiency solutions. Because cove lighting is designed for hard-to-reach spaces, LEDs can be the perfect solution for enhancing open spaces while experiencing the long-life advantages of LED.

Three Main Components of this Cove Lighting System



1. Track

Flexible track section available in four lengths that can be field cut or electrically linked to additional track sections. Sockets accept up to 5 **P7814-30** LED Lamps (ordered separately) per linear foot of track. Length – determined by part number

LED Cove lighting track

P7513-30 2 feet

P7514-30 4 feet

P7515-30 8 feet

P7516-30 12 feet

Dimensions: 3/4" Width



2. Lamp Modules

LED lamp modules insert into the flexible cove lighting track sections.

P7814-30 Standard LED lamp modules, 5 per pack, 1.4 total watts per lamp module, 2700K warm white, Dimensions: 1-3/4"L, 1/2"H, 1"W

3. Transformer

Transformer models for use with the Progress LED cove lighting system.

P8674-01 is a 60W max version that can NOT be dimmed and

P8675-01 is a 250W max transformer that can be dimmed with a low voltage dimmer.



P8674-01



P8675-01




ALL INTERIOR SPACES




LED Recessed Quick-Link

Housings and Trims


Using standard 6" and 4" can designs, these recessed trims combine the LED sources, trim, and power source as one unit. High-brightness warm white LED sources, integral dimmable power source, and wide distribution patterns showcase cutting-edge technology for general and functional illumination.



Quick-Link



4" LED Quick-Link Housing



P830-ATQL
 4" Recessed New Construction Housing
 Dimensions: 7-7/8" x 10-3/4"
 Ceiling opening: 4-1/2" dia.
 Plaster frame: 7-7/8" x 10-3/4"
 Recessed depth: 5-1/2"
 Pryouts: 1/2" & 3/4"
 UL and CUL listed for damp locations
 Title 24 compliant



P8027-30QL/27K White, 2700K color temp
P8027-30QL/35K White, 3500K color temp
 4" Recessed LED trim
 Tilting trim for aiming
 Dimensions: 1-7/8" ht., 5" outside dia.



P8029-30QL/27K White, 2700K color temp
P8029-30QL/35K White, 3500K color temp
 4" Recessed LED trim
 Smooth open white trim
 Dimensions: 2-1/8" ht., 5" outside dia.

6" LED Quick-Link Housing



P87-ATQL
 6" Recessed New Construction Housing
 Integral nail in bar hanger
 Dimensions: 7-7/8" x 10-3/4"
 Ceiling opening: 6-7/8" dia.
 Plaster frame: 7-7/8" x 10-3/4"
 Recessed depth: 7-1/2"
 Pryouts: 1/2" & 3/4"
 UL and CUL listed for damp locations
 Title 24 compliant



P8059-30QL/27K White, 2700K color temp
P8059-30QL/35K White, 3500K color temp
 6" Recessed LED trim
 Tilting adjustable trim for aiming
 Dimensions: 6" ht., 7-3/4" outside dia.



P8058-30QL/27K White, 2700K color temp
P8058-30QL/35K White, 3500K color temp
 6" Recessed LED trim
 Smooth open white trim
 Dimensions: 6" ht., 7-3/4" outside dia.

Note: Refer to product number for color temperature

See more Everlume LED fixtures throughout this catalog.

4" LED Trims for Progress P830/P831/P832



P8027-30 White, 2700K color temp
P8027-30/35K White, 3500K color temp
 4" Recessed LED trim
 Tilting adjustable trim for aiming
 Dimensions: 1-7/8" ht., 5" outside dia.



P8029-30 White, 2700K color temp
P8029-30/35K White, 3500K color temp
 4" Recessed LED trim
 Smooth open white trim
 Dimensions: 2-1/8" ht., 5" outside dia.

6" LED Trims for Progress P87/P187



P8058-30 White, 2700K color temp
P8058-30/35K White, 3500K color temp
 6" Recessed LED trim
 Smooth open white trim
 Dimensions: 6" ht., 7-3/4" outside dia.



P8059-30 White, 2700K color temp
P8059-30/35K White, 3500K color temp
 6" Recessed LED trim
 Tilting adjustable trim for aiming
 Dimensions: 6" ht., 7-3/4" outside dia.



P8069-30 White
P8069-30/35K White
 6" Recessed LED smooth open trim
 Smooth open white trim
 Dimensions: 3" ht., 7-3/4" outside dia.



P8070-30 White
P8070-30/35K White
 6" Recessed LED adjustable trim
 Tilting adjustable trim for aiming
 Dimensions: 2" ht., 7-3/4" outside dia.

Other available recessed housings for use with LED retrofit trims:
 6": P87-AT, P187-AT, P87-ATQC
 4": P831-AT, P830-TG, P832-TG

LED Retrofit Trims for Progress Housings



6" LED Recessed Retrofit Trims



These trims are designed and UL Classified to mount into existing standard 6" recessed housings including products by Capri®, Commercial Electric®, Emerald®, Halo®, Intense®, Juno®, Lithonia®, Nora®, WAC® and others (see factory for details on compatibility with other housings). Note the 4" LED retrofit trims are compatible with competitive housings as well.

6" Compact Fluorescent Housings & Trims – 26w

IC Trims

7-3/4" outside diameter, except where indicated

IC trims may be used as non-IC trims with same wattages.

IC Trims: Wet Location Listed

7-3/4" outside diameter

IC trims may be used as non-IC trims with same wattages.

Compact Fluorescent Lamp Matrix

For complete fixture, order housing with trim.

Trims are for use with compact fluorescent recessed fixtures listed in chart below.

Baffle



P8075-28 White

Open Splay



P8072-28 White
P8072-10 Brass

Wall Washer



P8054-31 Black

Wall Washer



P8052-28 White Baffle

Step Baffle



P8066-28 White
P8066-31 Black
P8066-09 Brushed Nickel*
P8066-14 Brushed Copper*
P8066-20 Antique Bronze
P8066-36 Chestnut
*Unpainted Flange

Cones



P8068-22A Gold Alzak®
P8068-21A Clear Alzak®
P8068-23A Black Alzak®
P8068-21 Clear Anodized
P8068-22 Gold Anodized
P8068-28 White

Cones



P8053-31 Black

Decorative Trims, lensed



P8012-86SV Burnished Chestnut
P8012-09 Brushed Nickel
P8012-10 Polished Brass
P8012-15 Polished Chrome
P8012-30 White
P8012-33 Cobblestone
P8012-46AC Weathered Bronze
P8012-71GV Gilded Iron
P8012-74 Venetian Bronze
P8081-09 Brushed Nickel

Dome Shower

Wet location listed



P8025-60 White
Polycarbonate
8-1/4" outside diameter

Drop Opal Shower

Wet location listed



P8096-60 White
Non-metallic flange

Fresnel

Wet Location listed.



P8062-28 White
Metal flange

Albalite - Metal

Wet Location listed.



P8060-28 White
Metal flange

Albalite - Plastic


Wet Location listed.



P8008-60 White
Non-metallic flange

CATALOG NO.	WATTAGE	LAMP BASE	LAMP TYPE	TRIM NO.	P8012
P83-26ICAT, P183-26EB P83-26ICATDM P183-26DM	26W	GX24q-3, 4-pin	Triple		GE F26TBX, Philips PLT26, Sylvania CF26DT, Progress P7817-01
MAX. LENGTH OF LAMP					5.7"



New Construction 
Air-Tight, IC Energy Star 26w




P83-26ICAT

Ceiling opening: 6-7/8"
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" and 3/4"

P83-26ICAT

- Quick-connects allow simple installation of 12-20 AWG wire, without the need for wire nuts
- 120V NPF electronic ballast
- Meets requirements for Energy Star
- Meets California T-24 requirements
- Not rated for through branch, but can be "daisy-chained"
- One 4-pin triple 26w compact fluorescent lamp vertically mounted
- Nail bar hangers span 24" T-bar spacing
- Can be installed in ceilings from 1/2" to 2" thick
- Includes gasket to complete air-tight installation per Washington State Energy Code

New Construction and Remodel 
Dimmable 26w




P83-26ICATDM

Ceiling opening: 6-7/8"
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" and 3/4"

P83-26ICATDM

- 120V NPF electronic dimmable ballast. Dimmable to 15% of lamp output on standard incandescent dimmers
- Meets requirements for Energy Star
- Meets California T-24 requirements
- Not rated for through branch, but can be "daisy-chained"
- One 4-pin triple 26w compact fluorescent lamp vertically mounted
- Nail bar hangers span 24" T-bar spacing
- Can be installed in ceilings from 1/2" to 2" thick
- Includes gasket to complete air-tight installation per Washington State Energy Code

Remodel IC Energy Star 26w 




P183-26EB

Ceiling opening: 6-5/8"
Recessed depth: 7-1/2"
Pryouts: 1/2"

P183-26EB

- 120V NPF electronic ballast
- Meets requirements for Energy Star
- Meets WSEC requirements for air-tight when used with accessory gasket kit P8593-01. P8587-01 accessory ceiling gasket or caulking around opening.
- Exclusive slide mounting bars permit quick and solid mounting in ceilings
- Can be installed in ceilings from 1/2" to 1-1/2" thick.
- UL and CUL listed for damp locations and through wiring
- Rated for 4 #12 90° conductors (2 in/2 out)
- Rated for 60° supply wires in end of run applications
- One 4-Pin triple 26w compact fluorescent vertically mounted

Remodel IC 26w 
Dimmable 26w



P183-26DM

Ceiling opening: 6-5/8"
Recessed depth: 7-1/2"
Pryouts: 1/2"

P183-26DM

- 120V NPF electronic dimmable ballast. Dimmable to 15% of lamp output on standard incandescent dimmers
- Meets requirements for Energy Star
- Meets WSEC requirements for air-tight when used with accessory gasket kit P8593-01. P8587-01 accessory ceiling gasket or caulking around opening.
- Exclusive slide mounting bars permit quick and solid mounting in ceilings
- Can be installed in ceilings from 1/2" to 1-1/2" thick.
- UL and CUL listed for damp locations and through wiring
- Rated for 4 #12 90° conductors (2 in/2 out)
- Rated for 60° supply wires in end of run applications
- One 4-Pin triple 26w compact fluorescent vertically mounted
- Requires P8593-01 and P8587-01 accessory gaskets for air-tight requirements

Compact Fluorescent Recessed for the Home California Title 24 Compliant

P8025

GE F26TBX, Philips PLT26, Sylvania CF26DT, Progress P7817-01

5.3"

P8052, P8053, P8054

GE F26TBX, Philips PLT26, Sylvania CF26DT, Progress P7817-01

5.5"

P8060, P8062, P8008

Sylvania CF26DT, Progress 7817-01

4.8"

P8066, P8068, P8072, P8075

GE F26TBX, Philips PLT26, Sylvania CF26DT, Progress P7817-01

5.5"

P8074, P8096

GE F26TBX, Philips PLT26, Sylvania CF26DT, Progress P7817-01

5.9"

6" Compact Fluorescent Housings & Trims – 13w and 18w

For complete fixture, order housing with trim.

Trims are for use with compact fluorescent recessed fixtures listed in chart below.

IC Trims

7-3/4" outside diameter, except where indicated



IC trims may be used as non-IC trims with same wattages.

<p>Baffle</p>  <p>P8075-28 White</p>	<p>Wall Washer</p>  <p>P8052-28 White Baffle P8052-31 Black Baffle</p>	<p>Wall Washer</p>  <p>P8054-31 Black</p>	<p>Open Splay</p>  <p>P8072-28 White P8072-10 Brass</p>
<p>Step Baffle</p>   <p>P8066-28 White P8066-31 Black P8066-09 Brushed Nickel* P8066-14 Brushed Copper* *Unpainted Flange P8066-20 Antique Bronze P8066-36 Chestnut</p>	<p>Cones</p>  <p>P8068-22A Gold Alzak® P8068-21A Clear Alzak® P8068-23A Black Alzak® P8068-21 Clear Anodized P8068-22 Gold Anodized P8068-28 White</p>	<p>Cones</p>  <p>P8053-31 Black</p>	<p>Decorative Trims, lensed</p>  <p>P8012-09 Brushed Nickel P8012-10 Polished Brass P8012-15 Polished Chrome P8012-30 White P8012-33 Cobblestone P8012-46AC Weathered Bronze P8012-71GV Gilded Iron P8012-74 Venetian Bronze P8012-86SV Burnished Chestnut P8081-09 Brushed Nickel</p>

IC Trims Wet Location Listed

7-3/4" outside diameter

IC trims may be used as non-IC trims with same wattages.

<p>Drop Opal Shower Wet location listed.</p>  <p>P8007-60 White glass Metal Flange. O.D.: 8-1/4"</p>	<p>Drop Opal Shower Wet location listed.</p>  <p>P8009-60 White Non-metallic flange</p>	<p>Dome Shower Wet location listed.</p>  <p>P8025-60 White Polycarbonate O.D.: 8-1/4"</p>	<p>Drop Opal Shower Wet location listed.</p>  <p>P8096-60 White Non-metallic flange</p>
<p>Fresnel Wet Location listed.</p>  <p>P8062-28 White Metal flange</p>	<p>Albalite Wet location listed.</p>  <p>P8060-28 White Metal flange</p>	<p>Albalite Wet location listed.</p>  <p>P8008-60 White Non-metallic flange</p>	

Compact Fluorescent Lamp Matrix


CATALOG NO.	WATTAGE	LAMP BASE	LAMP TYPE	TRIM NO.	P8007, P8009	P8012
P83-ICAT, P83-AT, P183-EB	13W	G24q-1 or GX24q-1, 4-pin	Triple or Quad		GE F13TBX, Sylvania CF13DT, Progress P7815-01	GE F13DBX, GE F13TBX, Philips PLC13, Sylvania CF13DD, Sylvania CF13DT, Progress 7815-01
P88-ICAT	18W	GX24q-2, 4-pin	Triple or Quad		Philips PLT18, Sylvania CF18DT, Progress 7816-01	GE F18DBX, GE F18TBX, Philips PLC18, Philips PLT18, Sylvania CF18DT, Progress 7816-01, Sylvania CF18DD
MAX. LENGTH OF LAMP					4.8"	5.7"



Wall Washing

Compact fluorescent wall washer fixtures, recessed fixtures that are mounted on the ceiling an equal distance away from the wall and each other, enable clean and even illumination across vertical surfaces. To make a room seem more spacious, light an entire wall with wall-washers.

New Construction

Air Tight, IC Energy Star 13w 

New Construction Air Tight, IC 13w

New Construction Air Tight, IC 18w

Remodel IC 13w



Ceiling opening: 6-7/8"
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" and 3/4"

P83-ICAT

- 120V NPF electronic ballast
- Meets requirements for Energy Star
- Meets California T-24 requirements
- Not rated for through branch, but can be "daisy-chained"
- One 4-pin quad or triple 13w compact fluorescent lamp vertically mounted
- Nail bar hangers span 24" T-bar spacing
- Can be installed in ceilings from 1/2" to 2" thick
- Meets WSEC for air-tight requirements - P8587-01 accessory ceiling gasket or caulking around plaster frame opening



Ceiling opening: 6-7/8"
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" and 3/4"

P83-AT

- 120-277V HPF electronic ballast
- FCC rated Class A ballast
- One 4-pin Quad or triple 13w compact fluorescent lamp vertically mounted
- Meets Washington State Energy Code requirements - P8587-01 Accessory Ceiling Gasket
- Integral Romex clamp
- Spans 24" T-bar spacing
- Rated for 8 #12 90° conductors (4 in/4 out)
- Can be installed in ceilings from 1/2" to 2" thick



Ceiling opening: 6-7/8"
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" and 3/4"

P88-ICAT

- 120v NPF electronic ballast
- Not rated for through branch, but can be "daisy-chained"
- One 4-pin quad or triple 18w compact fluorescent lamp vertically mounted
- Meets California T-24 requirements
- Spans 24" T-bar spacing
- Can be installed in ceilings from 1/2" to 2" thick
- Meets Washington State Energy Code for air-tight requirements - P8587-01 accessory ceiling gasket or caulking around plaster frame opening



Ceiling opening: 6-5/8"
Recessed depth: 7-1/2"
Pryouts: 1/2"

P183-EB

- 120V NPF electronic ballast
- Exclusive slide mounting bars permit quick and solid mounting in ceilings
- Meets California T-24 requirements
- Can be installed in ceilings from 1/2" to 1-1/2" thick.
- UL and CUL listed for damp locations and through wiring
- Rated for 4 #12 90° conductors (2 in/2 out)
- Rated for 60° supply wires in end of run applications
- One 4-Pin Quad or triple 13w compact fluorescent vertically mounted

P8025

GE F13DBX, GE F13TBX, Philips PLC13, Sylvania CF13DD, Sylvania CF13DT, Progress P7815-01
GE F18TBX, Philips PLT18, Sylvania CF18DT, Progress 7816-01

5.3"

P8052, P8053, P8054

GE F13DBX, GE F13TBX, Philips PLC13, Sylvania CF13DD, Sylvania CF13DT, Progress 7815-01
GE F18TBX, Philips PLT18, Sylvania CF18DT, Progress 7816-01

5.5"

P8060, P8062, P8008

GE F13DBX, GE F13TBX, Sylvania CF13DT, Progress P7815-01
GE F18TBX, Philips PLT18, Sylvania CF18DT, Progress 7816-01

4.8"

P8066, P8068, P8072, P8075

GE F13DBX, GE F13TBX, Philips PLC13, Sylvania CF13DD, Sylvania CF13DT, Progress 7815-01
GE F18TBX, Philips PLT18, Sylvania CF18DT, Progress 7816-01

5.5"

P8074, P8096

GE F13DBX, GE F13TBX, Philips PLC13, Sylvania CF13DD, Sylvania CF13DT, Progress 7815-01
GE F18DBX, GE F18TBX, Philips PLC18, Philips PLT18, Sylvania CF18DD, Sylvania CF18DT, Progress 7816-01

5.9"

4" Compact Fluorescent Housings & Trims



Trims

Baffle



P8144-20 Antique Bronze

Baffle



P8144-28 White

Baffle



P8144-31 Black

Open



P8145-28 White

Baffle



P8144-36 Chestnut

Open



P8145-21 Clear Anodized


Open



P8145-22 White Anodized

Make Yourself at Home

One of the easiest ways to make your rental property feel like home is to add a fresh coat of paint. Unfortunately, many paints contain toxins that are harmful to the environment and can be hazardous to your health. What can you do? Use a natural paint or select brands of paint with low VOCs (volatile organic compounds).

New Construction 
AT/IC/ES 18w and 13w



P830-18ICAT
P830-13ICAT

Ceiling opening: 4-1/2"
Plaster frame: 17-7/8" x 10-3/4"
Recessed depth: 5-1/2"

U.S. Patent #: 9758959, 9857766, 6004011

P830-18ICAT **P830-13ICAT**

- 120V NPF electronic ballast
- Meets requirements for Energy Star
- Meets WSEC for air-tight requirements
 - P8588-01 accessory ceiling gasket or caulking around plaster frame opening
- Exclusive slide mounting bars permit quick and solid mounting in ceilings
- Spans 24" T-bar spacing
- One 13w or 18w Gx24q triple CFL vertically mounted
- UL and CUL listed for damp locations

6" Fluorescent Firebox™

Open



P8074-28 White
OD: 8-3/4"

Open Splay



P8072-28 White
P8072-10 Brass

Wall Washer



P8052-28 White Baffle
P8052-31 Black Baffle

Wall Washer



P8054-31 Black

Step Baffle



P8066-28 White
P8066-31 Black Baffle
w/ White Flange
P8066-09 Brushed Nickel*
P8066-14 Brushed Copper*
*Unpainted Flange

Step Baffle



P8066-20 Antique Bronze

Step Baffle



P8066-36 Chestnut

Baffle



P8075-28 White
P8075-31 Black

Cone



P8068-22A Gold Alzak®
P8068-21A Clear Alzak®
P8068-21 Clear Anodized
P8068-22 Gold Anodized
P8068-28 White

Cone




P8053-31 Black

Decorative Trims, lensed



P8012-33 Cobblestone
See pg. 62 for complete listing.

Fresnel



P8062-28 White
Metal flange
Wet Location listed.

Drop Opal Shower

Wet location listed



P8096-60 White
Non-metallic flange

Dome Shower

Wet location listed



P8025-60 White
Polycarbonate
8-1/4" outside diameter

Albalite - Metal

Wet Location listed.



P8060-28 White
Metal flange

Albalite - Plastic

Wet Location listed.



P8008-60 White
Non-metallic flange

Catalog no: **P62-FB**
Wattage: 26W or 32W
Lamp base: GX24q-3, 4-pin
Lamp type: Triple

Trim no.	Lamp*	Max. Length of Lamp
P8008, P8096	Progress P7817-01, Sylvania CF26DT	4.8"
P8012	GE F32TBX, Philips PLT32	5.7"
P8025	Phillips PLT26, GE F32TBX, Sylvania CF26DT, Progress P7817-01	5.3"
P8052, P8053, P8054	GE F32TBX, Sylvania CF26DT	5.5"
P8060, P8062	Progress P7817-01, Sylvania CF26DT	4.8"
P8066, P8068, P8072	GE F32TBX	5.5"
P8074, P8075	GE F32TBX, Philips PLT32, Sylvania CF32DT	5.9"

*Partial lamp list of maximum wattages and lengths.
Consult lamp manufacturers for available lamps with M.O.L. requirements.

Trims

7-3/4" outside diameter, except where indicated

IC trims may be used as non-IC trims with same wattages.

All trims accept 26W or 32W triple tube 4-pin compact fluorescent lamps unless stated otherwise.

2-Hour Fluorescent Firebox



P62-FB

Ceiling Opening: 6-7/8"
Recessed Depth: 8-9/16"
Plaster Frame: 12-3/8" X 9-9/16"
Pryouts: 1/2" and 3/4"

- Non-IC rated*
- Air-Tight
- Fits into 2 x 10 construction
- UL classified to maintain up to a two hour fire rating in UL L500 & G531 fire rated ceiling assemblies
- All trims accept 26W or 32W triple tube or spiral 4-pin compact fluorescent lamps unless stated otherwise
- Includes hardware for mounting to furring channels

*Accessory P8555-01 IC Box required for use in IC rated applications.



Patented

6" Fluorescent Pro-Optic Firebox®



Trims for Fluorescent Pro-Optic Firebox

7-3/4" outside diameter (OD), except where indicated



Ceiling Opening: 6-7/8"
 Recessed Depth: 8-9/16"
 Plaster Frame: 12-3/8" - 9-9/16"
 Pryouts: 1/2" and 3/4"

- Non-IC rated*
- Fits into 2 x 10 construction
- UL 1598 and CUL listed for damp locations and through branch wiring
- UL classified to maintain fire ratings of 1 hour or less for UL500 series ceiling/floor designs

*Accessory P8555-01 IC Box required for use in IC rated applications.



Patented

U.S. Patent #:
 6357891, 6254527, 6838618

<p>Open Alzak®</p>  <p>P8030-21AFB Clear</p>	<p>Open Alzak®</p>  <p>P8030-22AFB Gold</p>	<p>Open Alzak®</p>  <p>P8030-61FB Straw</p>	<p>Open Alzak®</p>  <p>P8030-64FB Wheat</p>
<p>Open Alzak®</p>  <p>P8030-67FB Haze</p>	<p>Open Alzak®</p>  <p>P8030-17AFB Pewter</p>	<p>Wall Washer Alzak®</p>  <p>P8032-21FB Clear Alzak®</p>	<p>Open</p>  <p>P8030-28FB White</p>
<p>Baffle</p>  <p>P8031-31FB Black Baffle</p> <p>P8031-28FB White Baffle</p>	<p>Regressed Fresnel Wet location listed</p>  <p>P8034-83FB Regressed Fresnel</p>	<p>Flush Albalite Lens Wet location listed</p>  <p>P8033-60FB Flush Albalite</p>	<p>Regressed Prismatic Wet location listed</p>  <p>P8035-68FB Regressed Prismatic</p>
<p>Flush Fresnel Lens Wet location listed</p>  <p>P8038-83FB Flush Fresnel</p>			

Catalog Number	Ballast	Wattage	Lamp Base	Line Current (Amps)	Input (Watts)	Minimum Start Temp
P63-EBFB	120/277V Electronic	2 13w Quad 4-Pin	G24q-1	0.25/0.11	29	0
P66-EBFB	120/277V Electronic	2 26w Quad 4-Pin	G24q-3	0.42/0.21	54	-4
P68-EBFB	120/277V Electronic	2 18w Quad 4-Pin	G24q-2	0.35/0.15	42	-4

Integral emergency option not available on any Pro-Optic Firebox® housing.
 See page 74 for remote mount battery pack options.

6" Compact Fluorescent Pro-Optic™

6" Trims for P63/66/68

Open White



P8030-28 White

White Baffle



P8031-28

Black Baffle



P8031-31

Pewter Alzak®



P8030-17A

Open Clear Alzak®



P8030-21A

Open Gold Alzak®



P8030-22A

Open Straw Alzak®



P8030-61 **MTO**

Open Wheat Alzak®



P8030-64 **MTO**

Open Haze Alzak®



P8030-67 **MTO**

Wall Washer Clear Alzak®



P8032-21

Regressed Fresnel Lens
Wet Location Listed



P8034-83 White
R.D.: 5-3/4"

Regressed Prismatic Lens
Wet Location Listed



P8035-68 White
R.D.: 5-3/4"

Flush Albalite Lens
Wet Location Listed



P8033-60 Flush Albalite

6" Trims for P6132-EB

Baffle*



P8014-28 White
P8014-31 Black

Open*



P8015-21A Clear Alzak®
P8015-22A Gold Alzak®

Lensed*




P8016-68 White Prismatic
P8016-83 White Fresnel

7" outside diameter (OD) 6-3/16" aperture
Recessed Depth: 4-1/2"
(except as indicated)

U.S. Patent #: 6254257

Emergency Battery Pack

For use with 6" and 8" horizontal frames



Pro-Optic® offers the ability to conceal the test button and indicator light inside the trim and between the lamps, completely out of sight of the general public. The tops of all Pro-Optic® trims are equipped with two knockouts that can simply be removed when used with emergency battery pack housings.

All internal emergency housings are made to order. Add "EM" to end of standard catalog number.

6" Pro Optic® Housings



P63-EB shown with P8030-21A trim

Ceiling opening: 6-1/4" dia.
Plaster frame: 9-1/16" x 14"
Recessed depth: see trims
Pryouts: 1/2" and 3/4"

- 120/277v HPF electronic ballast
- Bar hangers span 24" T-bar spacing
- J-Box rated for 8 #12 90° conductors (4 in/4 out)
- UL and CSA listed for damp locations
- Accommodates 1-1/4" thick ceilings

Catalog No.	Ballast	Wattage	Lamp Base	Line Current (Amps)	Input (Watts)	Minimum Start Temp. °F
P63-EB	120/277V electronic	2 13w Quad 4-Pin	GX24q-1	0.25/0.11	29	0
P66-EB	120/277V electronic	2 26w Quad 4-Pin	GX24q-3	0.45/0.20	54	0
P66-DM	120/277V electronic dimmable	2 26w Quad 4-Pin	GX24q-3	0.46/0.19	54/52	0
P68-EB	120/277V electronic	2 18w Quad 4-Pin	GX24q-2	0.33/0.15	39	0
P6132-EB	120/277V electronic	1 26w Triple 4-Pin 1 32w	GX24q-4	0.24/0.11 0.31/0.13	29 36	0 0



8" Compact Fluorescent Pro-Optic™



8" Trims for P8213/8218/8226

9" outside diameter, 8-3/16" aperture,
Recessed Depth: 5" (except as indicated)

Open

Open Clear Alzak®



P8130-21A

Open Gold Alzak®



P8130-22A

Baffle



P8131-28 White
P8131-31 Black

Shallow Cross Louver 3-7/8" overall height

Clear Alzak®



P8170-21A

Gold Alzak®



P8170-22A

Wall Washer

Clear Alzak®



P8132-21
R.D.: 7-1/16"

Lensed Trims

Regressed Prismatic Lens Wet Location Listed



P8135-68
R.D.: 7-1/16"

8" Pro-Optic® Housings



P8226-DVEB shown with
P8130-21A trim

Ceiling opening: 8-3/16" dia.
Plaster frame: 9-1/16" x 14"
Recessed depth: see trims
Pryouts: 1/2" and 3/4"

- 120/277v HPF electronic ballast
- Bar hangers span 24" T-bar spacing
- J-Box rated for 8 #12 90° conductors (4 in/4 out)
- Accommodates 1-1/4" thick ceilings
- UL and CSA listed for damp locations

8" Trims for P8232-EB

Open*



P8115-21A Clear Alzak®
P8115-22A Gold Alzak®

Baffle*



P8114-28 White
P8114-31 Black

Lensed*



P8116-68 White Prismatic
P8116-83 White Fresnel

Wall Washer*



P8113-21A Clear Alzak®
P8113-22A Gold Alzak®

Catalog No.	Ballast	Lamp Wattage	Lamp Base	Line Current (Amps)	Input (Watts)	Minimum Start Temp. (°F)
P8213-EB	120/277V Elec.	2 13w Quad 4-Pin	GX24q-1	0.25/.11	29	0
P8218-DVEB	120/277V Elec.	2 18w Quad 4-Pin	GX24q-2	0.33/0.14	39	0
P8226-DVEB	120/277V Elec.	2 26w Quad 4-Pin	GX24q-3	0.45/0.20	54	0
P8226-DM	120/277V Elec. Dimmable	2 26w Quad 4-Pin	GX24q-3	0.46/0.19	54/52	0
P8232-EB	120/277V Elec.	2 32w Triple 4-Pin 2 42w Triple 4-Pin	GX24q-4	0.57/0.25 0.78/0.33	68 93	0 0

*For use with P8232-EB only.





6" Trimlite

26w - 42w Compact Fluorescent
Mounting Frames

Open Trim



P6621-30 White
R.D. 8-1/4", O.D. 7-7/16"
Lamp: 26w, 32w or 42w
Triple Tube CFL

Scoop Wall Washer



P6623-30 White
R.D. 8-1/4", O.D. 7-7/16"
Lamp: 26w or 32w Triple
Tube CFL

Alzak® Cone



P6692-22 Gold Alzak®
P6692-21 Clear Alzak®
R.D. 8-1/4", O.D. 7-7/16"
Lamp: 26w, 32w or 42w
Triple Tube CFL

Trims for P632-EB

For complete fixture,
order housing with trim.

Step Baffle



P6625-30 White
P6625-31 Black
R.D. 8-1/4", O.D. 7-7/16"
Lamp: 26w, 32w or 42w
Triple Tube CFL

Alzak® Multiplier Superior performance



P6715-21 Clear Alzak®
P6715-22 Gold Alzak®
R.D. 10-5/8", O.D. 7-3/4"
Lamp: 26w, 32w or 42w
Triple Tube CFL
P8627-31 Optional
snap-in black baffle

Shower Light Wet location listed



P6622-60 Acrylic
R.D. 8-1/4", O.D. 7-1/2"
Shatter-resistant, white
diffuser with gasket.
Lamp: 26w, 32w or 42w
Triple Tube CFL

Fresnel Glass Wet location listed



P6691-83
R.D. 8-1/4", O.D. 7-5/8"
Lamp: 26w or 32w Triple
Tube CFL

Technical Information

Lamp	Wattage Voltage	Line Current Amps	Min Input Watts	Start Temp.(F)
26W Triple Tube	120	0.25	28	0°
26W Triple Tube	277	0.11	28	0°
32W Triple Tube	120	0.32	36	0°
32W Triple Tube	277	0.14	36	0°
42W Triple Tube	120	0.42	48	0°
42W Triple Tube	277	0.18	48	0°

Total Harmonic Distortion	<10%
Lamp Current Crest Factor	<1.5
Power Factor	>.98
End of Lamp Life Shutdown Circuit Protection	

- Ceiling opening 6-7/8", Plaster frame 7-7/8" x 10-3/4", Recessed Depth (R.D.) - see reflector trims
- Maximum ceiling thickness: 1-1/2".
- Socket cup mounts to trim for consistent lamp positioning.
- Socket cup can be positioned in upper or lower positions for different beamsread diameters.
- Full Reflector design eliminates light leaks around trim flange.
- Slotted, interlocking bar hangers securely span 24" T-bar spacing.
- UL and CUL listed for damp locations and through wiring.
- Integral nailer and T-bar mounting clamp.
- Rated for 8 #12 90° conductors (4 in/4 out)

6" Vertical Mounted Lamp



Ceiling Opening: 6-7/8"
Plaster Frame: 7-7/8" x 10-3/4"
Recess Depth (R.D.): See trims
Pryouts: 1/2" and 3/4"

P632-EB

- 3 Lamps (26w, 32w, 42w), 2 Voltages (120/277), 1 Housing
- 120V/277V HPF electronic ballast.
- Superior visual cut off of lamp image.
- End of Lamp Life Shutdown Circuit Protection

Recessed Accessories

Green Your Most Used Spaces

At a minimum, ENERGY STAR recommends installing qualified CFLs in fixtures that are used at least 15 minutes at a time or several hours per day. The best fixtures to use qualified CFLs in are usually found in the following areas of your home:


- family and living rooms
- kitchen
- dining room
- bedrooms
- outdoors

Paper Tips

Choose recycled paper and envelopes that have been processed and colored using eco-friendly materials.

Get off mailing lists you don't want to be part of. You will save paper and the annoyance of all that junk mail.

If your copier or printer has a 2-sided feature, use it. You will use half as much paper.



P8588-01 4" ceiling gasket
P8584-01 5" ceiling gasket
P8587-01 6" ceiling gasket
P8589-01 8" ceiling gasket
 Ceiling gasket seals housing to drywall opening for Washington State Energy Code compliance.




P8511-01 Furring channel mounting clip for bar hangers.



P8593-01 Airtight Gasket Kit to convert the P86-TG, P186-TG P183-26EB to an air tight unit. When not using caulk at the ceiling line, P8587-01 may also be required.



P8700-01 Four plaster frame clips and screws for complete squares and rounds.




P8607-01 Remodel Clips
 Three plaster frame clips for use in new construction frames in finished ceilings.



P8012-KIT
 Retrofit kit for P8012 decorative recessed trims to fit into Juno® and Halo® housings.



P8585-01 Goof Ring
 O.D. 8-7/8".
 For use with any recessed trim with a 7-3/4" O.D.



P8716-01 Adjustable hangers
 Two 26" adjustable hangers for step lights, complete rounds and squares.



P8773-01 Four mounting clips and screws for T-Bar ceilings for any new construction recessed product using bar hangers.


Emergency Battery Packs



P8641-01

Cat. No.	Watts	Lamp	Length	Width	Height
P8641-01	7, 9, 13w	2 pin Twin & Quad	9-1/2"	2-3/8"	1-1/2"
P8642-01	18 & 26w	2 pin Quad	9-1/2"	2-3/8"	1-1/2"
P8643-01	10-42W	4 pin Quad, Triple, 2D and twins	9-1/2"	2-3/8"	1-1/2"

Emergency battery packs for remote mounting. Can be used with any compact fluorescent fixture. Remote battery must be located within 50 feet of ballast, or 1/2 the recommended distance specified by the AC Ballast manufacturer, whichever is less. Comes with test switch, indicator light, junction box and 4ft of flex.



OUTDOOR & UTILITY SPACES

EVERLUME™
LED LIGHTING



Lakeland LED

Brushed Nickel finish
Etched glass
Modern Craftsman styling
No visible lamps or glare
Warm white light, 3500K color temp.
CRI: 76

P5548-09



P5868-09



P5879-09



P5497-09



P5809-09

Product No.	Finish	Description	Size	Lamp(s)
P5497-09	Brushed Nickel	Post lantern	9-3/4" dia., 17-3/4" ht. Fits 3" post (order separately).	12w LED included
P5548-09	Brushed Nickel	Hanging lantern (additional chain available).	9-11/16" dia., 13-7/8" ht. Overall ht. w/chain 87".	12w LED included
P5809-09	Brushed Nickel	Wall lantern	5-7/8" W., 6-3/4" ht. Extends 7-3/4". H/CTR 2-3/8".	5w LED included
P5868-09	Brushed Nickel	Wall lantern	8-1/4" W., 10" ht. Extends 10-1/2". H/CTR 4".	5w LED included
P5879-09	Brushed Nickel	Wall lantern	9-3/4" W., 11-1/2" ht. Extends 12-1/4".	12w LED included





Greenridge LED

Antique Bronze finish

Etched water seeded glass

Warm white light, 3500K color temp.

CRI: 76




Product No.	Finish	Description	Size	Lamp(s)
P5409-20	Antique Bronze	Post lantern	7-1/2" sq., 14-1/2" ht. Fits 3" post (order separately).	5w LED included
P5509-20	Antique Bronze	Hanging lantern (additional chain available).	7-1/2" sq., 12-3/8" ht. Overall ht. w/ chain 87"; wire 15'.	5w LED included
P5908-20	Antique Bronze	Wall lantern	6" W., 9-5/8" ht. Extends 7". H/CTR 2-1/4"	5w LED included
P5909-20	Antique Bronze	Wall lantern	7-1/2" W., 11" ht. Extends 8-1/2". H/CTR 4-1/2".	5w LED included

Product No.	Finish	Description	Size	Lamp(s)
P5885-108	Oil Rubbed Bronze	Wall lantern	6-1/2" W., 5-1/2" ht. Extends 8-1/8". H/CTR 2-3/4".	5w LED included
P5900-108	Oil Rubbed Bronze	Wall lantern	8-1/4" W., 5-1/2" ht. Extends 9-3/4". H/CTR 2-3/4".	5w LED included
P5901-108	Oil Rubbed Bronze	Wall lantern	10-5/8" W., 5-1/2" ht. Extends 12-1/8". H/CTR 2-3/4".	12w LED included



P5885-108



P5900-108



P5901-108



2007 WINNER

See more Everlume LED fixtures throughout this catalog.

EVERLUME™
LED LIGHTING

Georgian Lanterns

Opaque white art glass

Integrated electronic photocell

with adjustable shield

120V ballast



P5422-71STR



P5632-71STR



P5668-71EB



P5676-71EB

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5422-71STR**	Gilded Iron	One-light post lantern w/photo cell	12" sq., 31-5/8" ht. Fits 3" post (order separately).	120V HPF electronic	1 26w 4-pin Quad, triple tube or spiral. GX24q-3 base
P5632-71STR**	Gilded Iron	One-light wall lantern w/photo cell	12" W., 38-1/2" ht. Extends 15". H/CTR 20-7/8".	120V HPF electronic	1 26w 4-pin Quad, triple tube or spiral. GX24q-3 base
P5668-71EB	Gilded Iron	One-light wall lantern w/photo cell	6-1/2" W., 15-1/2" ht. Extends 8-3/4". H/CTR 10".	120V HPF electronic	1 13w 4-pin triple tube or spiral. GX24q-1 base
P5676-71EB	Gilded Iron	One-light wall lantern w/photo cell	9-7/8" W., 29" ht. Extends 12-5/8". H/CTR 15-1/2".	120V NPF electronic	1 26w 4-pin triple tube or spiral. GX24q-3 base

**Hinged door for relamping.



P5874-31EB




P5874-33EB



P5876-33EB



P5875-31EB



Ashmore Lanterns

Etched water seeded glass

Integral photocell with adjustable shield

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5874-31EB P5874-33EB	Black Cobblestone	One-light wall lantern	6-3/8" W., 14-7/8" ht. Extends 9-1/2". H/CTR 4-1/2".	120V NPF electronic	1 26w spiral or triple tube. GX24q-3 base
P5875-31EB P5875-33EB	Black Cobblestone	One-light wall lantern	8-3/8" W., 17" ht. Extends 10-1/2". H/CTR 4-1/2".	120V NPF electronic	1 26w spiral or triple tube. GX24q-3 base
P5876-31EB P5876-33EB	Black Cobblestone	One-light wall lantern	9-3/8" W., 20-1/4" ht. Extends 12-3/4". H/CTR 5-5/8".	120V NPF electronic	1 26w spiral or triple tube. GX24q-3 base

For Your Safety

Using outdoor lighting with timers and photocells can add another level of security for you and your family. They can provide a "lived in" appearance when you are away, and can also insure your home's exterior is well lit when arriving home after dark.



Fairview Lanterns

Brushed Nickel or
Textured Black finish

Softly etched glass

Integral photocell with
adjustable shield



P5489-09EB



2006 WINNER



P5492-31EB



P5547-09EB



P5496-31EB



P5494-31EB

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5489-09EB P5489-31EB	Brushed Nickel Black	One-light post lantern w/photocell	10-1/2" dia., 18-1/4" ht. Fits 3" post (order separately).	120V NPF electronic	1 26w spiral or triple tube CFL. GX24q-3 base
P5492-09EB P5492-31EB	Brushed Nickel Black	One-light wall lantern w/photocell	6-1/2" W., 11-3/4" ht. Extends 8-1/2". H/CTR 3-3/4".	120V NPF electronic	1 13w spiral or triple tube CFL. GX24q-1 base
P5494-09EB P5494-31EB	Brushed Nickel Black	One-light wall lantern w/photocell	8-3/8" W., 14-1/2" ht. Extends 11-1/4". H/CTR 10".	120V NPF electronic	1 18w spiral or triple tube CFL. GX24q-2 base
P5496-09EB P5496-31EB	Brushed Nickel Black	One-light wall lantern w/photocell	10-1/2" W., 17" ht. Extends 12-1/4". H/CTR 12-1/2".	120V NPF electronic	1 26w spiral or triple tube CFL. GX24q-3 base
P5547-09EB P5547-31EB	Brushed Nickel Black	One-light hanging lantern w/photocell (additional chain available)	10-1/2" dia., 17-1/4" ht. Overall ht. w/chain 92"; wire 15'.	120V NPF electronic	1 26w spiral or triple tube CFL. GX24q-3 base



P5769-33



P5760-33

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5462-33	Cobblestone	Two-light post lantern	14" sq., 13-3/4" ht. Fits 3" post (order separately).	120V NPF	2 13w 2-pin twin CFL. GX23 base
P5760-33	Cobblestone	One-light wall lantern	4-1/2" W., 8-1/2" ht. Extends 4-3/4". H/CTR 5-1/8".	120V NPF	1 7w 2-pin twin CFL. GX23 base
P5769-33	Cobblestone	Two-light wall lantern	13-3/4" W., 11-3/4" ht. Extends 4-1/2". H/CTR 7".	120V NPF	2 13w 2-pin twin CFL. GX23 base

Mission Lanterns

Cobblestone finish



P5462-33



P5886-31



P5485-31EB
P5486-31

Welbourne Lanterns

Textured Black finish

Hexagonal framework with vine-inspired scrolls

White glass chimney

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5485-31EB	Textured Black	One-light post lantern	13" dia., 26" ht. Fits 3" post (order separately).	120V/277V HPF electronic	1 26w, 32w, or 42w 4-pin Quad CFL. GX24q-3/-4 base.
P5486-31	Textured Black	One-light post lantern	13" dia., 26" ht. Fits 3" post (order separately).	120V NPF magnetic	1 100w high pressure sodium E17
P5886-31	Textured Black	One-light wall lantern	9-1/2" W., 31-1/4" ht. Extends 11-3/8". H/CTR 18-5/8".	120V/277V HPF electronic	1 26w, 32w, or 42w 4-pin Quad CFL. GX24q-3/-4 base.

Crawford Lanterns

Black or Cobblestone finishes

Etched glass

Integral photocell with adjustable shield



P5686-33EB



P5685-31EB



P5685-33EB



P5686-31EB

Product No.	Finish	Description	Size	Ballast	Lamp(s)*
P5685-31EB	Black	One-light wall lantern w/photocell	6-1/2" W., 12-1/2" ht. Extends 8-3/4". H/CTR 8".	120V NPF electronic	1 13w 4-pin spiral or triple tube. GX24q-1 base.
P5685-33EB	Cobblestone				
P5686-31EB	Black	One-light wall lantern w/photocell	8-1/2" W., 16-3/4" ht. Extends 11". H/CTR 9-5/8".	120V NPF electronic	1 26w 4-pin spiral or triple tube. GX24q-3 base.
P5686-33EB	Cobblestone				

Cape Cod Lantern

Gilded Iron finish

Etched seeded glass

Integral photocell with adjustable shield



P5679-71STR

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5679-71STR	Gilded Iron	One-light wall lantern with photo cell	11" W., 15-7/8" ht. Extends 11-7/8".	120V NPF electronic	1 4-pin Quad, spiral or triple tube 26/32w CFL. GX24q-3 base.





Andover Lanterns

Antique Bronze finish

Etched glass

Integral photocell with adjustable shield




Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5887-20EB	Antique Bronze	One-light wall lantern w/photo cell	5-1/2" W., 12-5/8" ht. Extends 6-1/4". H/CTR 6-3/8".	120V NPF electronic	1 13w spiral CFL. GX24q-1 base. 
P5888-20EB	Antique Bronze	One-light wall lantern w/photo cell	7-1/2" W., 21-3/8" ht. Extends 8-1/4". H/CTR 7-1/2".	120V NPF electronic	1 26w spiral CFL. GX24q-3 base. 



Arts & Crafts Lanterns

Light honey art glass

Integral photocell with adjustable shield

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5435-46STR	Weathered Bronze	One-light post lantern w/photocell	10" dia., 19-1/8" ht. Fits 3" post (order separately)	120V NPF electronic	1 26w/32w 4-pin Quad, spiral or triple tube CFL. GX24q-3 base. 
P5630-46STR	Weathered Bronze	One-light wall lantern w/photocell	10" W., 15-1/4" ht. Extends 10-3/4". H/CTR 9-7/8".	120V NPF electronic	1 26w/32w 4-pin Quad, spiral or triple tube CFL. GX24q-3 base. 
P5633-46EB	Weathered Bronze	One-light wall lantern w/photocell	6-5/8" W., 10-1/2" ht. Extends 7-1/2". H/CTR 2-1/4".	120V NPF1 electronic	13w 4-pin Quad, spiral or triple tube CFL. GX24q-1 base. 



Roman Coach Lanterns

Etched glass

Integral photocell with adjustable shield



P5985-50EB



P5985-19EB



P5986-33EB



P5986-09EB



P5766-19EB



P5766-31EB



P5770-19EB



P5770-09EB



P5772-31EB
(shown with tail)



P5772-33EB
(shown with tail)

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5985-09EB	Brushed Nickel	One-light wall lantern w/photocell	4-5/8" W., 10" ht. Extends 6-1/8". H/CTR 2-3/4".	120V NPF electronic	1 26w 4-pin spiral or triple tube. GX24q-3 base.
P5985-19EB	Roman Bronze				
P5985-31EB	Black				
P5985-33EB	Cobblestone				
P5985-50EB	Golden Baroque				
P5986-09EB	Brushed Nickel	One-light wall lantern w/photocell	4-5/8" W., 8-1/2" ht. Extends 6-1/8". H/CTR 2-3/4".	120V NPF electronic	1 13w 4-pin spiral or triple tube. GX24q-1 base.
P5986-19EB	Roman Bronze				
P5986-31EB	Black				
P5986-33EB	Cobblestone				
P5986-50EB	Golden Baroque				

Product No.	Finish	Description	Size	Ballast	Lamp(s)*
P5766-09EB	Brushed Nickel	One-light wall lantern w/photocell	6" W., 9-7/8" ht. Extends 7". H/CTR 3-1/2".	120V NPF electronic	1 13w 4-pin spiral or triple tube. GX24q-1 base.
P5766-19EB	Roman Bronze				
P5766-31EB	Black				
P5766-33EB	Cobblestone				
P5770-09EB	Brushed Nickel	One-light wall lantern w/photocell	7" W., 15-3/8" ht. Extends 7-1/4". H/CTR 6-7/8".	120V NPF electronic	1 26w 4-pin spiral or triple tube. GX24q-3 base.
P5770-19EB	Roman Bronze				
P5770-31EB	Black				
P5770-33EB	Cobblestone				
P5772-09EB	Brushed Nickel	One-light wall lantern w/photocell**	7" W., 26-3/8" ht. w/tail 19-1/4" ht. w/o tail. Extends 6-7/8". H/CTR 16-1/4".	120V NPF electronic	1 26w 4-pin spiral or triple tube. GX24q-3 base.
P5772-19EB	Roman Bronze				
P5772-31EB	Black				
P5772-33EB	Cobblestone				

** Can mount with or without tail.

Motion Sensor Lanterns

Senses moving heat sources

Title 24 compliant

Stays on as long as motion is detected

Turns off automatically – integral timer

Includes integral photocell



P5662-31






P5854-31



P5854-33



P5661-71

Product No.	Finish	Description	Size	Lamp(s)
P5661-71	Gilded Iron	One-light Cranbrook motion sensor lantern with seeded water glass	6-1/2" W., 12-3/4" ht, Extends 8". H/CTR 2-3/4".	1 medium base, 60w max. 
P5662-31	Black	One-light motion sensor lantern with clear seeded glass	5-1/2" W., 12-5/8" ht. Extends 6-1/2". H/CTR 6".	1 medium base, 100w max. 
P5854-31 P5854-33	Black Cobblestone	Two-light Ashmore motion sensor lantern with seeded glass	6-5/8" W., 15" ht. Extends 9-5/8". H/CTR 10-1/4".	2 candelabra base, each 60w max. 

Take it Outside

In addition to offering a stronger sense of security for your loved ones, outdoor lighting can make a real difference in how much time you spend *with* your loved ones – on the front porch, on the deck and in your back yard. Extend the day with a variety of outdoor lighting options.

Curb Appeal

Outdoor lighting also is an essential part of curb appeal, as it often foreshadows what is to come inside your home. Use energy-efficient products for indoor and outdoor fixtures to show your commitment to the environment.

NightSaver® Lamp Shield

Environmentally/Dark Sky friendly illumination

Shrouds the light source so no light is emitted above 45°

Use with Progress single lamp lanterns

Will work with CFL and A-lamps



P5627-44
with P8709-44



P8709-19



P8709-44



P8709-33

Product No.	Finish	Description	Size
P8709-19	Roman Bronze	NightSaver® lamp shield	2-7/8" dia., 3-3/8" ht.
P8709-31	Black		
P8709-33	Cobblestone		
P8709-44	Oxford Silver		



P5777-19
with P8709-19



P5664-33
with P8709-33

Path/Spread Light



P5209-38

Product No.	Finish	Description	Size	Lamp(s)
P5209-38	Green	Polypropylene. Clear ribbed liner. 1/2 NPS threaded fitting for permanent or P5233 installation.	6-1/4" dia., 8-3/4" ht.	One 7w twin 2-pin CFL.
P5209-31	Black			

Polymeric Cylinders

Features

- Product is composed of all non-metallic exterior components.
- Only non-corrosive hardware components are used.
- Offered in white or black, up and up/down configurations.
- Down version shields par lamp and bug lights to minimize glare onto beach for turtle law compliance (check with your local turtle enforcement official).
- Existing aluminum lens cover P8799-30/31 works with up/down version.
- UL listed for wet locations.

Benefits


- Non-corrosive components are able to withstand the elements: salt, wind, sand, water, and sun.
- Ideal for coastal locations where salt traditionally makes powder coated products peel and deteriorate.
- Until now there have not been many products available that could both comply with turtle laws and withstand the elements. Progress' shields for plastic cylinders provide the answer to both challenges.

Product No.	Finish	Description	Size	Lamp(s)
P5712-30 P5712-31	Textured White Black	One-light polymeric cylinder	5" W., 7-1/4" ht. Extends 7-3/4".	1 75w PAR-30 or 65w BR-30
P5713-30 P5713-31	Textured White Black	Two-light polymeric cylinder	5" W., 14" ht. Extends 7-3/4".	2 75w PAR-30 or 65w BR-30
P8712-30 P8712-31	Textured White Black	Turtle-friendly accessory shroud	5" dia., 4" ht.	n/a




Sea Turtle Friendly

P8712 accessory provides additional shielding of the light source to achieve "turtle-friendly" illumination.



Why Sea Turtle Friendly Lighting?

For millions of years female sea turtles have been coming ashore to lay their eggs on beaches. There are often many artificial lights near highly populated beaches that can deter females from nesting and disorient hatchling turtles on the way to their ocean home. Turtle-friendly lighting helps to shield these light sources and preserve our dwindling turtle populations.



Non-Metallic Energy Star



P7337-30EB



P7340-30EB



P7341-30EB



P7340-31EB



P7341-31EB



P7339-30EB



P7338-30EB

Welcome Mat

Incorporate a “shoeless house” policy in your home or invest in a good doormat to keep toxins and pollutants out. Imagine what’s on your shoes at the end of the day – oil, antifreeze, pollen, etc. When you bring all these materials into the house, it exposes your children and family pets to them, especially when they spend a lot time at the floor level.

Product No.	Finish	Description	Size	Ballast	Lamp(s)	
P7337-30EB	White	Two-light round wall or ceiling mount. Integral photocell.	11" dia. Extends 6-1/2".	120V NPF electronic	2 13w Quad CFL. GX24q-1 base.	
P7338-30EB	White	Two-light oval wall or ceiling mount. Integral photocell	6-3/4" W., 10-5/8" L., 4" ht.	120V NPF electronic	2 13w Quad CFL. GX24q-1 base.	ADA
P7339-30EB	White	Two-light oval wall or ceiling mount. Integral photocell.	6-3/4" W., 10-5/8" L., 4" ht.	120V NPF electronic	2 13w Quad CFL. GX24q-1 base.	ADA
P7340-30EB P7340-31EB	White Black	One-light close-to-ceiling. Integral photocell.	8-1/4" sq., 4-5/8" ht.	120V NPF electronic	1 Quad CFL. GX24q-3 base.	
P7341-30EB P7341-31EB	White Black	Two-light close-to-ceiling. Integral photocell.	10-1/4" sq., 5-1/2" ht.	120V NPF electronic	2 Quad CFL. GX24q-3 base.	

Non-Metallic Lanterns



P5882-30EB



P5882-31EB



P5843-31EB



P5816-30EB



P5816-31EB



P5881-31EB



P5881-30EB



P5748-30EB



P5748-31EB

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5748-30EB	White	One-light wall lantern w/photocell	8" W., 19-7/8" ht. Extends 8-1/4". H/CTR 10".	120V NPF electronic	1 18w Quad CFL. GX24q-2 base.
P5748-31EB	Black				
P5816-30EB	White	One-light polycarbonate wall lantern w/photocell	6" W., 7-3/4" ht. Extends 6-1/2".	120V NPF electronic	1 18w spiral or triple tube CFL. GX24q-2 base.
P5816-31EB	Black				
P5843-30EB	White	One-light wall lantern w/photocell	8" W., 17" ht. Extends 8-1/2". H/CTR 10-5/8".	120V NPF electronic	1 18w 4-pin spiral or triple tube CFL. GX24q-2 base.
P5843-31EB	Black				
P5881-30EB	White	One-light wall lantern w/ white acrylic and photocell	6" W., 8-7/8" ht. Extends 6-7/8". H/CTR 4/18".	120V NPF electronic	1 18w Quad CFL. GX24q-2 base.
P5881-31EB	Black				
P5882-30EB	White	One-light wall lantern w/white acrylic and photocell	4-1/8" W., 8-1/4" ht. Extends 5-3/4". H/CTR 2-3/8".	120V NPF electronic	1 18w Quad CFL. GX24q-2 base.
P5882-31EB	Black				

Non-Metallic CFL



P7332-30EB



P7333-30EB



P3623-30



P7344-31



P7321-31



P7118-30



P7182-30



P7344-30

Surface Mount

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P7332-30EB	White	One-light round surface mount w/ white acrylic.	10-1/8" dia., 7-1/4" ht. Extends 5-3/4". H/CTR 2-7/8".	120V NPF	1 18w Quad CFL. GX24q-2 base.
P7333-30EB	White	One-light oval surface mount w/ white acrylic.	5-3/4" W., 10-5/8" ht. Extends 3-5/8". H/CTR 5".	120V NPF	1 18w Quad CFL. ADA GX24q-2 base.

Wall & Ceiling

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3623-30	White	One-light ceiling mount with shatter resistant 6" globe.	6" dia., 7-1/4" ht.	120V NPF	1 7w 2-pin twin CFL. G23 base.
P7118-30	White	Two-light	12" sq., 2-1/4" ht.	120V NPF	2 13w 2-pin twin CFL. GX23 base. ADA
P7182-30	White	Two-light	9-1/2" sq., 2" ht.	120V NPF	2 7w or 9w 2-pin twin CFL. G23 base. ADA
P7321-31	Black	One-light polycarbonate wall bracket with 6" acrylic globe	6" dia., 7-3/4" ht., Extends 6-1/2". H/CTR 2-1/2"	120V NPF	1 22w 2-pin Quad CFL. GX32q-2 base.
P7344-30 P7344-31	White Black	One-light polypropylene wall bracket with white acrylic diffuser.	6" W., 8-3/4" ht. Extends 7-1/4". H/CTR 3".	120V NPF	1 13w 2-pin Quad CFL. GX23-2 base.

Walk this Way

With step lights, you can enhance walkways with extra light, making high-traffic areas more visible to keep every one safe during the day – or night.



P7375-31



P7376-31



P7372-30STRWB



P7373-30



P7396-60



P5694-68



P7124-68



P7193-30



P7192-31





P7191-31



P5698-31

Hard-Nox® CFL

Product No.	Finish	Diffuser	Dimensions	UL Listing	Ballast	Lamp(s)	
P5694-60 P5694-68	White	White ribbed polycarbonate Clear prismatic polycarbonate	5-3/4" W., 8-1/4" ht. Extends 4-3/8". H/CTR 4-1/8".	Wet	120V HPF magnetic	1 2-pin twin 9w CFL. G23 base.	
P5698-31	Black	White polycarbonate globe	6" W., 7" ht. Extends 7". H/CTR 3-1/4".	Wet	120V NPF	2 2-pin twin 7w CFL. G23 base.	
P7124-60 P7124-68	White	White ribbed DR acrylic Clear prismatic DR acrylic	4-1/4" W., 12-1/4" ht. Extends 4-1/4". H/CTR 6-1/8".	Damp	120V HPF	1 2-pin twin 13w CFL. GX23 base.	
P7191-31	Black	Clear prismatic polycarbonate	4-1/2" W., 6-3/4" ht. Extends 5-7/8". H/CTR 3-1/4".	Wet	120V HPF	2 2-pin twin 7w CFL. G23 base.	
P7192-31	Black	Clear prismatic polycarbonate	4-3/4" W., 8-1/2" ht. Extends 7-1/4". H/CTR 3-7/8".	Wet	120V NPF	2 2-pin twin 13w CFL. GX23 base.	
P7193-30 P7193-31	White Black	White polycarbonate	4-1/2" W., 8-1/8" ht. Extends 6-1/4". H/CTR 3-7/8".	Wet	120V HPF	1 2-pin PLC-28 Quad CFL. GX 32d-3 base.	
P7372-30	White	White DR acrylic	13-1/4" dia., 3-1/4" ht.	Damp	120V NPF Rapid start	1 22w FC8T9 and 1 32w FC12T9 circline	ADA
P7372-30STRWB	White	White DR acrylic	13-3/4" dia., 3-1/4" ht.	Damp	120V NPF electronic	2 13w 4-pin Quad CFL. G24q-1 base. (incl)	ADA 
P7373-30	White	White DR acrylic	19" dia., 4-1/4" ht.	Damp	120V HPF Rapid start	1 40w FC16T9 and 1 32w FC12T9 circline	
P7375-30 P7375-31	White Black	White DR acrylic	9" dia., 3-1/4" ht.	Damp	120V NPF	2 2-pin twin 7w CFL. G23 base.	ADA
P7375-30STRWB	White	One-light	9" dia., 3-1/4" ht.	Damp	120V NPF electronic	1 13w 4-pin Quad CFL. G24q-1 base. (incl)	ADA 
P7376-30 P7376-31	White Black	White DR acrylic	11" dia. 3-1/4" ht.	Damp	120V NPF	2 2-pin twin 13w CFL. GX23 base.	ADA
P7396-60 P7396-68	White	White ribbed polycarbonate Clear prismatic polycarbonate	10-1/2" sq. Extends 4".	Wet	120V HPF	2 2-pin twin 13w CFL. GX23 base.	ADA

Step Lights

Brick Lights Outdoor & Indoor

Lighting for safety in traffic areas.



P6802-31
P6805-31

Indoor & Protected Outdoor



P6821-30

Timeless Tips

To “green” an existing home without building a new one, consider adding deciduous trees to the south of the house. The trees will provide shade in the summer and light in the winter.

The next time your car needs a good cleaning, take a trip to the local car wash. Sure, washing your car at home can be great exercise, however, car washes are often more efficient. Also, most car washes clean, recycle and treat their water, rather than letting it drain into the street.


Cast aluminum housing with aluminum louver.

Three 1/2" I.P. conduit entries.

For brick, masonry, poured concrete and wood stud installations.

UL listed for wet locations.

P6802
P6805



Spring-held louver faceplate.


Metal housing has 1/2" I.P. conduit entry.

For indoor and protected outdoor use.

UL listed for damp locations.

Sheet rock or dry wall installations.

P6821-30



Product No.	Finish	Size	Lamp(s)
P6802-30	White	See drawing.	One 7w twin CFL.
P6802-31	Black	See drawing.	One 7w twin CFL.
P6805-31	Black	See drawing.	One 13w 4-ppin twin CFL GX24q-1 base.
P6821-30	White	See drawing.	One 7w or 9w twin CFL
P6826-30	White	See drawing. Shatter-resistant white faceplate	One 7w or 9w twin CFL

Growing Green

Compost your leaves and yard trimmings. Your garden will benefit from the resulting mulch and you will help divert material from overburdened landfills.

Plant native grasses, trees and shrubs in your yard. Because they are adapted to local conditions, they won't require extra water or pesticides. And, they will provide food and habitat for birds and butterflies.



P5960-20WB
P5961-20WB
P5962-20WB



P5963-20WB
P5964-20WB
P5965-20WB

Wall Packs

Accent wall sconces for mounting at height of 8 - 12 feet

Shipped as full cutoff, but can be adjusted for uplight

UL and CUL listed



P5891-20

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5960-20WB	Antique Bronze	Two-light round profile w/photocell	14-5/8" W., 5-1/2" ht. Extends 7-3/8".	120V NPF electronic	2 13w triple tube CFL (included)
P5961-20WB	Antique Bronze	Two-light round profile w/photocell	14-5/8" W., 5-1/2" ht. Extends 7-3/8".	120V NPF electronic	1 42w triple tube CFL (included)
P5962-20WB	Antique Bronze	One-light round profile MH	14-5/8" W., 5-1/2" ht. Extends 7-3/8".	120/277/347V NPF	1 70w HID lamp ED17 (included)

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5963-20WB	Antique Bronze	Two-light square profile w/photocell	14-5/8" W., 5-1/2" ht. Extends 6-3/8".	120V NPF	2 13w triple tube CFL (included)
P5964-20WB	Antique Bronze	Two-light square profile w/photocell	14-5/8" W., 5-1/2" ht. Extends 6-3/8".	120V NPF	1 42w triple tube CFL (included)
P5965-20WB	Antique Bronze	One-light square profile MH	14-5/8" W., 5-1/2" ht. Extends 6-3/8".	120/277/347V NPF	1 70w HID lamp ED17

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P5891-20	Black	Two-light CFL w/photocell	5-1/2" W., 14-5/8" ht. Extends 6-3/8".	120V NPF magnetic	2 13w 4-pin CFL. GX23 base



P5972-30



P5972-30
with numbers

Product No.	Finish	Description	Size	Lamp(s)
P5972-30	White	CFL address light. 120V NPF magnetic ballast.	10" W., 4-3/4" ht. Extends 2-7/8".	1 13w 2-pin twin CFL. GX23 base.

Address Lights

4" numbers pre-applied

Housing is constructed from high grade poly-propylene material

Shipped with stainless steel mounting hardware

Lamp included

Fixture holds five letters, numbers or blanks

Compact Fluorescent Lamps



P7822-01
PLC-22 Quad compact fluorescent lamp.
GX32d-2 base.

P7828-01
PLC-28 Quad compact fluorescent lamp.
GX32d-3 base.



P7808-01 26w CFL spiral lamp.
Size: 1-1/4" dia., 4-11/16" L.
GX24q-3 4-pin base. 2700K color temp, 82 CRI, 1750 initial lumens, 67 lumens per watt, 10,000 hr. lamp life.

P7810-01 13w CFL spiral lamp.
Size: 1-3/4" dia., 3-1/2" L.
GX24q-1 4-pin base. 2700k color temp, 83 CRI, 800 initial lumens, 62 lumens per watt, 10,000 hr. lamp life.

P7811-01 18w CFL spiral lamp.
Size: 1-3/4" dia., 4" L.
GX24q-2 4-pin base. 2700k color temp, 83 CRI, 1100 initial lumens, 61 lumens per watt, 10,000 hr. lamp life.



P7815-01 13w CFL triple lamp.
Size: 1-3/4" dia., 4-3/16" L.
GX24q-1 4-pin base. 2700k color temp, 82 CRI, 900 initial lumens, 69 lumens per watt, 12,000 hr. lamp life.

P7816-01 18w CFL triple lamp.
Size: 1-3/4" dia., 4-7/16" L.
GX24q-2 4-pin base. 2700k color temp, 82 CRI, 1200 initial lumens, 67 lumens per watt, 12,000 hr. lamp life.

P7817-01 26w CFL triple lamp.
Size: 1-3/4" dia., 4-7/8" L.
GX24q-3 4-pin base. 2700k color temp, 82 CRI, 1800 initial lumens, 69 lumens per watt, 12,000 hr. lamp life.

Note: GX24q 4-pin lamps such as P7815-01, P7816-01, and P7817-01 are recommended for use in Progress recessed housings.

Wallbox Vacancy Sensor



P8537-30 White
Wallbox vacancy sensor. 40W Min. - 500W Max. incandescent load, 120VAC, single-pole. Manual on/auto off.
Size: 2-1/4" W, 2-3/4" depth, 4" ht.

Meets California Title 24 legislation

P8538-30 White
Wallbox vacancy sensor with dimmer. 40W Min. - 500W Max. incandescent load, 120VAC, single-pole. Manual on/auto off.
Size: 2-1/4" W, 2-3/4" depth, 4" ht.

Meets California Title 24 legislation



P8537-30



P8538-30

Wallbox Occupancy Sensor

P8539-30 White
Wallbox occupancy sensor. 40W Min. - 500W Max. incandescent load, 120VAC, single-pole. Auto on/off.
Size: 2-1/4" W, 2-3/4" depth, 4" ht.

P8540-30 White
Wallbox occupancy sensor with dimmer. 40W Min. - 500W Max. incandescent load, 120VAC, single-pole. Auto on/off.
Size: 2-1/4" W, 2-3/4" depth, 4" ht.



P8539-30



P8540-30

Occupancy Sensor Wall Switch

Manual on/auto off passive infrared occupancy sensor replaces a standard wall switch to provide automatic shut-off of light fixtures when room is left unoccupied. Coverage of 180°, max 900 ft².



P8681-30

P8681-30 White
Includes faceplate. Adjustable time delay up to 30 minutes. 120/277V operation. No minimum load requirement. Incandescent load 800w max. Fluorescent load 1000w max.
Meets California Title 24 legislation.
Size: 2-3/4" W., 4-1/2" L., 1-5/8" ht.

Product Index

P100

P3 40
 P5 40
 P62 69
 P63 70, 71
 P66 70, 71
 P68 70, 71
 P83 65, 67
 P87 62
 P88 67
 P183 65, 67
 P632 73
 P830 62, 68

P2000

P2501 33
 P2503 30
 P2521 32
 P2523 28
 P2620 29
 P2621 29
 P2633 28
 P2854 14
 P2858 14, 23
 P2896 50

P3000

P3153 48
 P3154 48
 P3155 48
 P3156 48
 P3158 48
 P3159 48
 P3186 17, 49
 P3187 49
 P3188 49
 P3468 15, 23
 P3488 16
 P3489 22
 P3490 22
 P3491 22
 P3492 21
 P3493 21
 P3494 21
 P3495 20
 P3496 20
 P3497 24
 P3498 24
 P3499 24
 P3546 25
 P3547 25
 P3548 25
 P3562 22
 P3564 22
 P3566 22
 P3568 21
 P3570 21
 P3572 21
 P3574 20
 P3576 20
 P3623 90
 P3748 23
 P3760 25
 P3761 25
 P3762 25
 P3764 25
 P3765 25
 P3796 17

P4000

P4275 15
 P4276 15
 P4278 16
 P4393 17
 P4420 12
 P4430 13

P5000

P5022 12
 P5031 13
 P5145 15
 P5146 16
 P5148 18
 P5149 18
 P5150 18
 P5151 18
 P5154 18
 P5209 86
 P5409 77
 P5422 78
 P5435 83
 P5462 81
 P5485 81
 P5486 81
 P5489 80
 P5492 80
 P5494 80
 P5496 80
 P5497 76
 P5509 77
 P5547 80
 P5548 76
 P5630 83
 P5632 78
 P5633 83
 P5661 85
 P5662 85
 P5668 78
 P5676 78
 P5679 82
 P5694 91
 P5712 87
 P5713 87
 P5748 89
 P5760 81
 P5766 84
 P5769 81
 P5770 84
 P5772 84
 P5809 76
 P5816 89
 P5843 89
 P5844 85
 P5854 85
 P5868 76
 P5874 79
 P5875 79
 P5876 79
 P5879 76
 P5881 89
 P5882 89
 P5885 77
 P5886 81
 P5887 83
 P5888 83
 P5891 93
 P5900 77
 P5901 77
 P5908 77
 P5909 77
 P5960 93
 P5961 93
 P5962 93
 P5963 93
 P5964 93
 P5965 93
 P5972 93
 P5985 84
 P5986 84

P6000

P6132 71
 P6621 73
 P6622 73

P6623 73
 P6625 73
 P6691 73
 P6692 73
 P6715 73
 P6802 44, 92
 P6805 44, 92
 P6821 44, 92
 P6824 44
 P6825 44
 P6826 44, 92
 P6827 43
 P6828 43
 P6829 43

P7000

P7000 59
 P7004 59
 P7006 59
 P7007 59
 P7008 59
 P7009 59
 P7010 59
 P7011 59
 P7014 59
 P7015 59
 P7016 59
 P7017 59
 P7018 59
 P7019 59
 P7020 58
 P7021 58
 P7022 58
 P7023 58
 P7044 35
 P7047 35
 P7052 35
 P7079 36
 P7083 37
 P7084 37
 P7085 37
 P7089 35
 P7090 34, 38
 P7091 36, 38
 P7092 34, 39
 P7093 34, 39
 P7094 50
 P7095 50
 P7096 50
 P7101 12
 P7102 34, 39
 P7104 42
 P7106 36, 38
 P7107 41
 P7110 42
 P7111 42
 P7113 36, 38
 P7114 53
 P7115 50, 53
 P7116 50, 53
 P7117 34
 P7118 26, 90
 P7120 41
 P7121 41
 P7124 91
 P7129 52
 P7131 52
 P7132 52
 P7133 52
 P7135 39
 P7137 57, 58
 P7138 39
 P7139 49
 P7140 49
 P7141 49
 P7146 34, 39

P7150 41
 P7151 41
 P7152 41
 P7154 57
 P7160 52
 P7164 39
 P7166 41
 P7169 36
 P7171 20, 36, 38
 P7176 20, 36
 P7178 38
 P7182 26, 90
 P7183 55
 P7186 55
 P7189 57
 P7190 37, 42
 P7191 91
 P7192 91
 P7193 91
 P7195 41
 P7196 55
 P7197 52
 P7198 52
 P7199 52
 P7200 40
 P7205 55
 P7206 55
 P7209 16, 36
 P7213 56
 P7214 56
 P7215 56
 P7216 56
 P7225 54
 P7226 54
 P7227 51
 P7228 51
 P7229 51
 P7230 51
 P7231 51
 P7232 51
 P7233 51
 P7234 51
 P7235 51
 P7249 27, 37, 54
 P7250 54
 P7251 54
 P7252 54
 P7258 54
 P7262 56
 P7263 56
 P7264 56
 P7265 57
 P7266 57
 P7267 57
 P7268 57
 P7273 56
 P7274 56
 P7275 56
 P7276 56
 P7278 55
 P7279 55
 P7280 55
 P7285 55
 P7286 56
 P7287 56
 P7288 56
 P7307 26
 P7308 26
 P7309 26
 P7310 26
 P7311 26
 P7312 24
 P7313 24
 P7315 22
 P7316 22
 P7319 21

P7320 21
 P7321 90
 P7322 20
 P7323 20
 P7324 22
 P7325 22
 P7326 22
 P7327 21
 P7328 21
 P7329 21
 P7330 20
 P7332 90
 P7333 90
 P7334 56
 P7335 56
 P7336 56
 P7337 88
 P7338 88
 P7339 88
 P7340 88
 P7341 88
 P7344 90
 P7353 24
 P7359 24
 P7360 24
 P7364 24
 P7372 27, 91
 P7373 27, 91
 P7375 27, 91
 P7376 27, 91
 P7377 27
 P7378 27
 P7379 26
 P7380 26
 P7381 26
 P7382 26
 P7383 27
 P7384 27
 P7385 27
 P7513 60
 P7514 60
 P7515 60
 P7516 60
 P7808 94
 P7810 94
 P7811 94
 P7822 94

P8000

P8007 66
 P8008 64, 66, 69
 P8009 64, 66, 69
 P8012 64, 66, 69, 74
 P8014 71
 P8015 71
 P8016 71
 P8024 23
 P8025 64, 66, 69
 P8027 62, 63
 P8029 64, 66, 69
 P8030 70, 71
 P8031 70, 71
 P8032 70, 71
 P8033 70, 71
 P8034 70, 71
 P8035 70, 71
 P8038 70
 P8052 64, 66, 69
 P8053 64, 66, 69
 P8054 64, 66, 69
 P8058 62, 63
 P8059 62, 63
 P8060 64, 66, 69
 P8062 64, 66, 69
 P8066 64, 66, 69
 P8068 64, 66, 69

P8069 63
 P8070 63
 P8072 64, 66, 69
 P8074 69
 P8075 64, 66, 69
 P8096 66
 P8113 72
 P8114 72
 P8115 72
 P8116 72
 P8130 72
 P8131 72
 P8132 72
 P8135 72
 P8144 68
 P8145 68
 P8170 72
 P8213 72
 P8218 72
 P8226 72
 P8232 72
 P8511 74
 P8537 94
 P8538 94
 P8539 94
 P8540 94
 P8584 74
 P8585 74
 P8587 74
 P8588 74
 P8589 74
 P8593 74
 P8607 74
 P8641 74
 P8642 74
 P8643 74
 P8674 60
 P8675 60
 P8681 94
 P8698 54
 P8700 74
 P8709 86
 P8712 87
 P8716 74
 P8733 58
 P8735 58
 P8737 58
 P8738 58
 P8740 58
 P8743 58
 P8773 74

P9000

P9210 45
 P9211 45
 P9212 45

PE000, PV000

PE001 46
 PE002 46
 PE003 46
 PE004 46
 PV008 53

ENERGY STAR Index

P100	P5661	85	P7196	55
P83	P5662	85	P7197	52
P183	P5668	78	P7198	52
P830	P5676	78	P7199	52
	P5679	82	P7200	40
P2000	P5685	82	P7205	55
P2501	P5686	82	P7206	55
P2503	P5748	89	P7209	16, 36
P2521	P5766	84	P7225	54
P2523	P5770	84	P7226	54
P2620	P5772	84	P7227	51
P2621	P5816	89	P7228	51
P2623	P5843	89	P7229	51
P2854	P5854	85	P7233	51
P2858	P5874	79	P7234	51
P2896	P5875	79	P7235	51
P2897	P5876	79	P7249	27, 37, 54
P2898	P5881	89	P7250	54
P2899	P5882	89	P7251	54
	P5887	83	P7252	54
	P5888	83	P7258	54
P3000	P5985	84	P7262	56
P3153	P5986	84	P7263	56
P3154			P7264	56
P3155	P7000		P7265	57
P3156	P7020	58	P7266	57
P3158	P7021	58	P7267	57
P3159	P7022	58	P7268	57
P3186	P7023	58	P7273	56
P3187	P7044	35	P7274	56
P3188	P7047	35	P7275	56
P3468	P7052	35	P7276	56
P3488	P7079	36	P7278	55
P3497	P7083	37	P7279	55
P3498	P7084	37	P7280	55
P3499	P7085	37	P7285	55
P3547	P7089	35	P7286	56
P3548	P7091	36	P7287	56
P3760	P7092	34	P7288	56
P3761	P7093	34	P7310	26
P3764	P7094	50	P7311	26
P3765	P7095	50	P7312	24
P3796	P7096	50	P7313	24
	P7101	12	P7315	22
	P7102	34	P7316	22
P4000	P7106	36	P7319	21
P4275	P7113	36	P7320	21
P4276	P7114	53	P7322	20
P4278	P7115	53	P7323	20
P4393	P7116	53	P7324	22
P4420	P7117	34	P7325	22
P4430	P7128	52	P7326	22
	P7129	52	P7327	21
P5000	P7130	52	P7328	21
P5022	P7131	52	P7329	21
P5031	P7132	52	P7330	20
P5145	P7133	52	P7334	56
P5146	P7137	57	P7335	56
P5422	P7146	34	P7336	56
P5435	P7154	57	P7337	88
P5489	P7169	36	P7338	88
P5492	P7171	36	P7339	88
P5494	P7176	36	P7340	88
P5496	P7183	55	P7341	88
P5547	P7186	55	P7364	24
P5630	P7189	57	P7372	27, 91
P5632	P7190	37	P7375	27, 91
P5633				

LED Index

P100	P5548	76	P7515	60
P87	P5809	76	P7516	60
P830	P5868	76	P7814	60
	P5879	76		
P4000	P5885	77	P8000	
P4420	P5900	77	P8024	23
P4430	P5901	77	P8027	62, 63
	P5908	77	P8029	62, 63
	P5909	77	P8058	62, 63
P5000			P8059	62, 63
P5022	P6000		P8069	63
P5031	P6827	43	P8070	63
P5148	P6828	43	P8674	60
P5149	P6829	43	P8675	60
P5150				
P5151	P7000			
P5154	P7101	12		
P5409	P7513	60		
P5497	P7514	60		
P5509				

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL Listed or Classified or CSA Certified unless otherwise noted.

Thomasville Lighting® is manufactured by Progress Lighting under a license from and to the quality and design specifications of Thomasville Furniture Industries, Inc.

Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2008

All rights reserved.
International Copyright Secured.

4/08

Progress Lighting
701 Millennium Blvd.
Greenville, South Carolina
29607
www.progresslighting.com



Hubbell Lighting, Inc.