



GREENCREATIVE

Bringing You the Latest in LED Technology


PL:EDGE
SERIES



PL & PLS EDGE SERIES

PL EDGE SERIES PRODUCT FEATURES

PL DIR & PL BYP Installation



The PL EDGE DIRect Series plug & play lamps are compatible with G24q & GX24q (4-pin) installations and run directly off the existing electronic ballast. These lamps feature 0-10V dimming when used with a dimmable ballast. The PL EDGE BYPass Series lamps are hybrid lamps capable of operating with the existing magnetic ballast or line voltage after the ballast has been bypassed. The PL BYP lamps are compatible with G24d / GX24d (2-pin magnetic ballast or bypass) & G24q / GX24q (4-pin bypass) installations.

PL H Adjustable Base




All PL H lamp bases rotate 310° to fit any socket configuration. After installation simply rotate the lamp to achieve maximum light output.

PL V Patented Round Design



GREEN CREATIVE PL V LED Lamp





Other PL V LED Lamp

Compared to other square-shaped PL vertical lamps, the GREEN CREATIVE PL V's patented round diffuser improves the overall light output and aesthetics of the fixture.

PL EDGE DIR SERIES

PL H DIR



REPLACES





**26W
CFL**

60% Energy Savings

- DIRect plug & play - electronic ballast compatible
- Compatible with G24q & GX24q installations
- Suitable for replacing 13W, 18W, 26W, 32W & 42W CFL PL lamps
- 2700K / 3000K / 3500K / 4000K CCT
- HIGH CRI version available in 3000K CCT

PL H 5.5W DIR



5.5W REPLACES




**13-18W
CFL**

60% Energy Savings

- DIRect plug & play - electronic ballast compatible
- Compatible with G24q & GX24q installations
- Suitable for replacing 13W & 18W CFL PL lamps
- 2700K / 3000K / 3500K / 4000K CCT

PL V DIR



REPLACES




**26W
CFL**

60% Energy Savings

- DIRect plug & play - electronic ballast compatible
- Compatible with G24q & GX24q installations
- Suitable for replacing 13W, 18W, 26W, 32W & 42W CFL PL lamps
- 2700K / 3000K / 3500K / 4000K CCT
- HIGH CRI version available in 3000K CCT

PL V 6W DIR



6W REPLACES



**13-18W
CFL**

60% Energy Savings


- DIRect plug & play - electronic ballast compatible
- Compatible with G24q & GX24q installations
- Suitable for replacing 13W & 18W CFL PL lamps
- 2700K / 3000K / 3500K / 4000K CCT

PL EDGE BYP SERIES

PL H 9.5W BYP



G24d & GX24d
(2-Pin CFL)



Horizontal Installation

9.5W REPLACES



**26W
CFL**


60% Energy Savings

- HYBRid installation - DIRect or BYPass
- Compatible with magnetic ballasts or 120-277V line voltage
- Compatible with G24d / GX24d & G24q / GX24q installations
- 2700K / 3000K / 3500K / 4000K CCT

PL H 6W BYP



G24d & GX24d
(2-Pin CFL)



Horizontal Installation

6W REPLACES



**13-18W
CFL**

60% Energy Savings

- HYBRid installation - DIRect or BYPass
- Compatible with magnetic ballasts or 120-277V line voltage
- Compatible with G24d / GX24d & G24q / GX24q installations
- 3500K / 4000K CCT
- E26 & GU24 versions available in 3000K / 3500K / 4000K CCT

PL V 10W BYP



G24d & GX24d
(2-Pin CFL)



Vertical Installation

10W REPLACES



**26W
CFL**

60% Energy Savings

- HYBRid installation - DIRect or BYPass
- Compatible with magnetic ballasts or 120-277V line voltage
- Compatible with G24d / GX24d & G24q / GX24q installations
- 2700K / 3000K / 3500K / 4000K CCT

PL V 6.5W BYP



G24d & GX24d
(2-Pin CFL)



Vertical Installation

6.5W REPLACES



**13-18W
CFL**

60% Energy Savings

- HYBRid installation - DIRect or BYPass
- Compatible with magnetic ballasts or 120-277V line voltage
- Compatible with G24d / GX24d & G24q / GX24q installations
- 3500K / 4000K CCT
















LM 79

LM 80

TM 21



SPECIFICATIONS


	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CRI (typ.)	Dim	Life (hrs)	Voltage	
 PL H 8.5W DIR	8.5PLH/827/DIR	28366	2700K	870	26W	102	110°	82	Yes	50,000	120-277V	✓
	8.5PLH/830/DIR	28367	3000K	950	26W	112	110°	82	Yes	50,000	120-277V	✓
	8.5PLH/835/DIR	28368	3500K	950	26W	112	110°	82	Yes	50,000	120-277V	✓
	8.5PLH/840/DIR	28369	4000K	1020	26W	120	110°	82	Yes	50,000	120-277V	✓
 PL H 10.5W DIR	10.5PLH/930/DIR	57903	3000K	890	26W	85	110°	90	Yes	50,000	120-277V	No
 PL H 5.5W DIR	5.5PLH/827/DIR/R	57895	2700K	520	13-18W	95	110°	82	Yes	50,000	120-277V	No
	5.5PLH/830/DIR/R	57896	3000K	550	13-18W	100	110°	82	Yes	50,000	120-277V	No
	5.5PLH/835/DIR/R	57897	3500K	550	13-18W	100	110°	82	Yes	50,000	120-277V	No
	5.5PLH/840/DIR/R	57898	4000K	560	13-18W	102	110°	82	Yes	50,000	120-277V	No
 PL V 9.5W DIR	9.5PLV/827/DIR	28374	2700K	950	26W	100	120°	82	Yes	50,000	120-277V	✓
	9.5PLV/830/DIR	28375	3000K	1000	26W	105	120°	82	Yes	50,000	120-277V	✓
	9.5PLV/835/DIR	28376	3500K	1000	26W	105	120°	82	Yes	50,000	120-277V	✓
	9.5PLV/840/DIR	28377	4000K	1020	26W	107	120°	82	Yes	50,000	120-277V	✓
 PL V 11W DIR	11PLV/930/DIR	57918	3000K	920	26W	84	120°	90	Yes	50,000	120-277V	No
 PL V 6W DIR	6PLV/827/DIR	28370	2700K	570	13-18W	95	120°	82	Yes	50,000	120-277V	No
	6PLV/830/DIR	28371	3000K	600	13-18W	100	120°	82	Yes	50,000	120-277V	No
	6PLV/835/DIR	28372	3500K	600	13-18W	100	120°	82	Yes	50,000	120-277V	No
	6PLV/840/DIR	28373	4000K	620	13-18W	103	120°	82	Yes	50,000	120-277V	No
 PL H 9.5W BYP	9.5PLH/827/BYP	28354	2700K	870	26W	92	110°	82	No	50,000	120-277V	N.A.
	9.5PLH/830/BYP	28355	3000K	920	26W	97	110°	82	No	50,000	120-277V	N.A.
	9.5PLH/835/BYP	28356	3500K	920	26W	97	110°	82	No	50,000	120-277V	N.A.
	9.5PLH/840/BYP	28357	4000K	935	26W	100	110°	82	No	50,000	120-277V	N.A.
 PL H 6W BYP	6PLH/835/BYP/R	57904	3500K	550	13-18W	92	110°	82	No	50,000	120-277V	N.A.
	6PLH/840/BYP/R	57905	4000K	560	13-18W	93	110°	82	No	50,000	120-277V	N.A.
 PL H 6W BYP E26	6PLH/830/BYP/E26	57925	3000K	550	13W	92	110°	82	No	50,000	120-277V	N.A.
	6PLH/835/BYP/E26	57926	3500K	550	13W	92	110°	82	No	50,000	120-277V	N.A.
	6PLH/840/BYP/E26	57927	4000K	560	13W	93	110°	82	No	50,000	120-277V	N.A.
 PL H 6W BYP GU24	6PLH/830/BYP/GU24/R	57928	3000K	550	13W	92	110°	82	No	50,000	120-277V	N.A.
	6PLH/835/BYP/GU24/R	57929	3500K	550	13W	92	110°	82	No	50,000	120-277V	N.A.
	6PLH/840/BYP/GU24/R	57930	4000K	560	13W	93	110°	82	No	50,000	120-277V	N.A.
 PL V 10W BYP	10PLV/827/BYP	28362	2700K	950	26W	95	120°	82	No	50,000	120-277V	N.A.
	10PLV/830/BYP	28363	3000K	1000	26W	100	120°	82	No	50,000	120-277V	N.A.
	10PLV/835/BYP	28364	3500K	1000	26W	100	120°	82	No	50,000	120-277V	N.A.
	10PLV/840/BYP	28365	4000K	1020	26W	102	120°	82	No	50,000	120-277V	N.A.
 PL V 6.5W BYP	6.5PLV/835/BYP	28360	3500K	600	13-18W	92	120°	82	No	50,000	120-277V	N.A.
	6.5PLV/840/BYP	28361	4000K	620	13-18W	95	120°	82	No	50,000	120-277V	N.A.

* Suitable for damp locations

** Not suitable for use in totally enclosed fixtures

PLS EDGE PRODUCT FEATURES

PLS Base Types



The PLS EDGE Series lamps feature a variety of base types suitable for a wide range of applications. The PLS HYBrid lamps can operate on either existing magnetic ballasts or on 120-277V line voltage. The PLS BYPass lamps require bypassing the ballast during installation and run directly off line voltage.

Extra Wide Beam Design - 180° Rotatable Base



PLS lamp bases rotate 180° to fit any socket configuration. After installation simply rotate the lamp to achieve maximum light output.

PLS V GX23 - Designed for Vertical Applications



GREEN CREATIVE PLS V LED Lamp



Other PLS V LED Lamp

Compared to other PLS vertical lamps, the GREEN CREATIVE PLS V's patented round diffuser improves the overall light output and aesthetics of the fixture.

PLS EDGE SERIES

PLS HYB GX23



GX23 (HYBrid)
Replaces 13W

- HYBrid installation - DIRect or BYPass
- Compatible with magnetic ballast or 120-277V line voltage
- Compatible with GX23 installations
- 2700K / 3000K / 3500K / 4000K CCT

REPLACES

**13W
CFL**

60% Energy Savings

PLS 3.5W HYB G23



G23 (HYBrid)
Replaces 7-9W


- HYBrid installation - DIRect or BYPass
- Compatible with magnetic ballast or 120-277V line voltage
- Compatible with G23 installations
- 2700K / 3500K CCT

3.5W REPLACES

**7-9W
CFL**

60% Energy Savings

PLS 5.5W BYP 2GX7



2GX7 (BYPass)
Replaces 13W


- BYPass installation - requires bypassing the ballast
- Universal voltage 120-277V
- Compatible with 2GX7 installations
- 3500K CCT

5.5W REPLACES

**13W
CFL**

60% Energy Savings

PLS 3.5W BYP 2G7



2G7 (BYPass)
Replaces 7-9W

- BYPass installation - requires bypassing the ballast
- Universal voltage 120-277V
- Compatible with 2G7 installations
- 3500K CCT

3.5W REPLACES

**7-9W
CFL**

60% Energy Savings









LM 79

LM 80

TM 21



SPECIFICATIONS




	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.
 PLS 5.5W HYB GX23	5.5PLS/827/HYB/GX23	57820	2700K	450	13W	82	120°	80	No	50,000	120-277V	Yes
	5.5PLS/830/HYB/GX23	57821	3000K	500	13W	91	120°	80	No	50,000	120-277V	Yes
	5.5PLS/835/HYB/GX23	57822	3500K	500	13W	91	120°	80	No	50,000	120-277V	Yes
	5.5PLS/840/HYB/GX23	57823	4000K	520	13W	95	120°	80	No	50,000	120-277V	Yes
 PLS 6W HYB GX23	6PLS/827/HYB/GX23/R	57962	2700K	520	13W	87	110°	82	No	50,000	120-277V	No
	6PLS/830/HYB/GX23/R	57963	3000K	550	13W	92	110°	82	No	50,000	120-277V	No
	6PLS/835/HYB/GX23/R	57964	3500K	550	13W	92	110°	82	No	50,000	120-277V	No
	6PLS/840/HYB/GX23/R	57965	4000K	560	13W	93	110°	82	No	50,000	120-277V	No
 PLS V 6.5W HYB GX23	6.5PLSV/827/HYB/GX23	28378	2700K	550	13W	88	120°	82	No	50,000	120-277V	No
	6.5PLSV/830/HYB/GX23	28379	3000K	550	13W	92	120°	82	No	50,000	120-277V	No
	6.5PLSV/835/HYB/GX23	28380	3500K	560	13W	92	120°	82	No	50,000	120-277V	No
	6.5PLSV/840/HYB/GX23	28381	4000K	570	13W	95	120°	82	No	50,000	120-277V	No
 PLS 3.5W HYB G23	3.5PLS/827/HYB/G23	57812	2700K	280	7-9W	80	120°	80	No	50,000	120-277V	Yes
	3.5PLS/835/HYB/G23	57814	3500K	300	7-9W	86	120°	80	No	50,000	120-277V	Yes
 PLS 5.5W BYP 2GX7	5.5PLS/835/BYP/2GX7	57826	3500K	500	13W	91	120°	80	No	50,000	120-277V	Yes
 PLS 3.5W BYP 2G7	3.5PLS/835/BYP/2G7	57818	3500K	300	7-9W	86	120°	80	No	50,000	120-277V	Yes

* Suitable for damp loactions



GREEN CREATIVE
 1200 Bayhill Drive, Suite 220
 San Bruno, CA 94066

Tel / Fax: (866) 774-5433
 info@greencreative.com
www.greencreative.com

 / GREENCREATIVELED
 / GClightingLED
 / GREEN CREATIVE