



GREENCREATIVE



PRODUCT CATALOG

May 2017




GREENCREATIVE

LUMINAIRES



2017 LUMINAIRES CATALOG



GREEN CREATIVE, founded in 2010, is a solid state lighting development and manufacturing company based in Silicon Valley, CA. The company offers a comprehensive line of high-performance LED lighting solutions which has been widely adopted by some of the largest companies in the world.



2016 Top 10
MUST SEE Products



A complete line with national & international distribution

GREEN CREATIVE's full product line of ENERGY STAR, DLC, NSF & JA8 certified indoor retrofit and new construction lighting solutions serves the Retail, Hospitality, Food & Beverage, Office, Education & Industrial sectors through multiple distribution centers and sales networks across the USA.




Bringing you the latest in LED technology

Anchored by strong integrated R&D capabilities and patented technology, GREEN CREATIVE innovation, performance and reliability have been recognized year after year by the Illuminating Engineering Society Progress Report, the LEDs Magazine Sapphire Awards, Edison Report, NALD and more.



2017 LUMINAIRES TABLE OF CONTENTS



2017 LUMINAIRES FEATURED PRODUCTS



NEW!



P1-2

CLICK DESIGN SMPS & SMPR

SootheOptic technology
9", 7" & 5.5" form factors
Wet location & high CRI

NEW!



P5-6

NEW CONSTRUCTION DL THINFIT SERIES

New construction installation
Integrated J-box
Edge-lighting technology

NEW!



P11-12

STRIP QWIKLINK SERIES

QWIKLINK connection system
Connect up to 64' of fixtures
QWIKLINK sensor available

NEW!



P13-14

PANEL ELEVATE SERIES

SootheOptic technology UGR<19
Edge lighting technology
Slim body design

NEW!



P15-18

TROFFER & KIT ELEVATE SERIES

Exceptional efficacy >140 LPW
High quality architectural finish
Integrated sensor available

NEW!



P21-22

HIGH BAY HYPERBAY SERIES

Compact 2x2' form factor
3 lumen package options
3 beam distribution options

SURFACE MOUNT CEILING LINE



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet	
 SMPS 9" 20W	20SMPS9DIM/930	58242	3000K	1200	100W	60	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	20SMPS9DIM/940	58243	4000K	1250	100W	63	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
 SMPS 7" 15W	15SMPS7DIM/927	58244	2700K	850	75W	57	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	15SMPS7DIM/930	58245	3000K	850	75W	57	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	15SMPS7DIM/940	58246	4000K	870	75W	58	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
 SMPS 5.5" 10W	10SMPS5.5DIM/927	58247	2700K	550	50W	55	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	10SMPS5.5DIM/930	58248	3000K	550	50W	55	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	10SMPS5.5DIM/940	58249	4000K	560	50W	56	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓

SURFACE MOUNT CEILING LINE

SootheOptic low glare technology reduces visual glare and creates a comfortable lighting environment



Edge Lighting Technology



Unified Glare Rating (UGR) <19

Viewing Angle



- SootheOptic low glare technology
- Innovative CLICK design
- Wet location & high CRI
- Compatible with 4" J-boxes (standard)

SPECIFICATIONS

Model		Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet	
 SMPR 9" 20W	20SMPR9DIM/930 NEW!	58255	3000K	1200	100W	60	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	20SMPR9DIM/940	58256	4000K	1250	100W	63	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
 SMPR 7" 15W	15SMPR7DIM/927 NEW!	58257	2700K	850	75W	57	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	15SMPR7DIM/930	58258	3000K	850	75W	57	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	15SMPR7DIM/940	58259	4000K	870	75W	58	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
 SMPR 5.5" 15W	10SMPR5.5DIM/927 NEW!	58260	2700K	550	50W	55	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	10SMPR5.5DIM/930	58261	3000K	550	50W	55	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
	10SMPR5.5DIM/940	58262	4000K	560	50W	56	100°	N.A.	90	Yes	50,000	120-277V	Yes	✓
 SMP 4" & 6" ACC	SMP/ACC	58033	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

* SMP/ACC - 4" & 6" recessed can accessories for 5.5" & 7" round & square (5.5" for use in 4" can only, 7" for use in 4" or 6" can)

SURFACE MOUNT LINE



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet	
 SMDL 6" 14.5W	14.5SMDL6DIM/927	40842	2700K	920	85W	63	110°	N.A.	90	Yes	40,000	120V	No	✓
	14.5SMDL6DIM/930	40843	3000K	950	85W	66	110°	N.A.	90	Yes	40,000	120V	No	✓
	14.5SMDL6DIM/840	40847	4000K	1050	100W	72	110°	N.A.	82	Yes	40,000	120V	No	✓
 SMDL 6" 11W	11SMDL6DIM/927	58101	2700K	680	65W	62	110°	N.A.	90	Yes	40,000	120V	Yes	✓
	11SMDL6DIM/930	58102	3000K	720	65W	65	110°	N.A.	90	Yes	40,000	120V	Yes	✓
	11SMDL6DIM/940	58103	4000K	750	65W	68	110°	N.A.	90	Yes	40,000	120V	Yes	✓
 SMDL 6" ACC	SMDL6/ACC	57974	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.
 SMDL 4" ACC	SMDL4/ACC	57973	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

* GU24 connector available

SURFACE MOUNT LINE

Wet Location & High CRI




SMDL 6" 11W




- ⌚ **Innovative CLICK design**
- ⌚ **Compatible with 4" J-boxes (standard)**
- ⌚ **4" & 5-6" recessed can accessories sold separately**
- ⌚ **Installs in just minutes – No rewiring**

Seamless Installation




CLICK 6" 14.5W & 11W - High CRI



INSTALLATION GUIDE

4" J-BOX

ACCESSORIES INCLUDED:



- Attach mounting bracket to J-box
- Click downlight into mounting bracket



Mounting Bracket



J-Box Screws




Wire Nuts



LED Adapter

4" CAN

ACCESSORIES SOLD SEPARATELY:




- Connect E26 adapter to the LED adapter
- Insert mounting clips and push downlight up until flush with ceiling



E26 Adapter



LED Adapter




Mounting Bracket



Mounting Clips

5-6" CAN

ACCESSORIES SOLD SEPARATELY:



- Connect E26 adapter to the LED adapter
- Squeeze mounting springs and push downlight up until flush with ceiling



E26 Adapter





LED Adapter



Mounting Springs

NEW CONSTRUCTION DOWNLIGHT LINE



SPECIFICATIONS


	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet	
	11.6DLNC6DIM/827	NEW! 58028	2700K	810	75W	70	100°	N.A.	82	Yes	40,000	120V	No	✓
	11.6DLNC6DIM/830	58029	3000K	830	75W	72	100°	N.A.	82	Yes	40,000	120V	No	✓
	11.6DLNC6DIM/840	58030	4000K	850	75W	73	100°	N.A.	82	Yes	40,000	120V	No	✓
	8.5DLNC4DIM/827	NEW! 58025	2700K	510	50W	60	100°	N.A.	82	Yes	40,000	120V	No	✓
	8.5DLNC4DIM/830	58026	3000K	530	50W	62	100°	N.A.	82	Yes	40,000	120V	No	✓
	8.5DLNC4DIM/840	58027	4000K	550	50W	65	100°	N.A.	82	Yes	40,000	120V	No	✓
	DLNC6GOOF/R	97848	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.
	DLNC4GOOF/R	97847	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

NEW CONSTRUCTION DOWNLIGHT LINE

Integrated J-box with LED quick connectors for quick & easy installation




Edge Lighting Technology



Installs Directly into Ceiling - No Housing Needed


No J-box or Recessed Can Required
IC-Rated




-  For new construction or remodel installation
-  Innovative design saves time & materials
-  Easy to use spring action clips
-  Goof Ring available

INSTALLATION GUIDE


1.




2.




3.




4.




5.



6.




7.



ARCHITECTURAL DOWNLIGHT LINE




SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 CDL 9.5" 48W	48CDL9.5G4DIM/830/277V	97706	3000K	3200	2 X 42W	67	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	48CDL9.5G4DIM/835/277V	97707	3500K	3400	2 X 42W	71	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	48CDL9.5G4DIM/840/277V	97708	4000K	3600	2 X 42W	75	90°	N.A.	80	Yes	40,000	120-277V	No	✓
 CDL 8" 32W	32CDL8G4DIM/830/277V	97696	3000K	2150	2 X 26W	67	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	32CDL8G4DIM/835/277V	97697	3500K	2300	2 X 26W	72	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	32CDL8G4DIM/840/277V	97698	4000K	2450	2 X 26W	77	90°	N.A.	80	Yes	40,000	120-277V	No	✓
 CDL 6" 22W	22CDL6G4DIM/830/277V	97686	3000K	1600	2 X 18W	73	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	22CDL6G4DIM/835/277V	97687	3500K	1650	2 X 18W	75	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	22CDL6G4DIM/840/277V	97688	4000K	1700	2 X 18W	77	90°	N.A.	80	Yes	40,000	120-277V	No	✓
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 22CDL6G4DIM/840/277V/EM													

ARCHITECTURAL DOWNLIGHT LINE

Accessories include a carabiner safety clip that can be used during installation for easy wiring. Two types of retaining clips are also included to secure the fixture if recessed frame does not already have pre-installed clips.



Dimensions


Model	A	B
 48CDL9.5G4DIM/xxx/277V	9.25" (235mm)	6.50" (165mm)
 32CDL8G4DIM/xxx/277V	7.80" (197mm)	5.90" (150mm)
 22CDL6G4DIM/xxx/277V	6.02" (153mm)	5.39" (137mm)

Designed for Commercial Applications



-  Fits existing architectural & commercial housing
-  0-10V dimming – Compatible with 120-277V circuits
-  Easy installation – Quick connector and pre-wired conduit
-  Superior savings and performance over CFL

INSTALLATION GUIDE



COMMERCIAL DOWNLIGHT LINE




SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CRI (typ.)	Dim	Life (hrs)	Voltage	ENERGY STAR
 CDL 9.5" 23.5/32/45W	45CDLA9.5/827/277V	57878	2700K	1860/2325/2975	23.5W - 1x42W/2x26W	79/73/76	110°	80	No	40,000	120-277V	✓
	45CDLA9.5/830/277V	57879	3000K	2000/2500/3200	32W - 1x57W/2x32W	85/78/71	110°	80	No	40,000	120-277V	✓
	45CDLA9.5/835/277V	57880	3500K	2000/2500/3200	45W - 2x42W	85/78/71	110°	80	No	40,000	120-277V	✓
	45CDLA9.5/840/277V	57881	4000K	2000/2500/3200		85/78/71	110°	80	No	40,000	120-277V	✓
 CDL 8" 12/19/27W	27CDLA8/827/277V	57873	2700K	930/1400/1860	12W - 1x26W/2x13W	78/74/69	110°	80	No	40,000	120-277V	✓
	27CDLA8/830/277V	57874	3000K	1000/1500/2000	19W - 1x32W/2x18W	83/79/74	110°	80	No	40,000	120-277V	✓
	27CDLA8/835/277V	57875	3500K	1000/1500/2000	27W - 1x42W/2x26W	83/79/74	110°	80	No	40,000	120-277V	✓
	27CDLA8/840/277V	57876	4000K	1000/1500/2000		83/79/74	110°	80	No	40,000	120-277V	✓
 CDL 6" 8.5/13/21W	21CDLA6/827/277V	57868	2700K	650/930/1400	8.5W - 1x18W	76/69/67	110°	80	No	40,000	120-277V	✓
	21CDLA6/830/277V	57869	3000K	700/1000/1500	13.5W - 1x26W/2x13W	82/74/71	110°	80	No	40,000	120-277V	✓
	21CDLA6/835/277V	57870	3500K	700/1000/1500	21W - 1x32W/2x18W	82/74/71	110°	80	No	40,000	120-277V	✓
	21CDLA6/840/277V	57871	4000K	700/1000/1500		82/74/71	110°	80	No	40,000	120-277V	✓
 CDL 4" 6/9/14W	14CDLA4/827/277V	57863	2700K	465/650/930	6W - 1x13W	78/72/66	110°	80	No	40,000	120-277V	✓
	14CDLA4/830/277V	57864	3000K	500/700/1000	9W - 1x18W	83/78/71	110°	80	No	40,000	120-277V	✓
	14CDLA4/835/277V	57865	3500K	500/700/1000	14W - 1x26W/2x13W	83/78/71	110°	80	No	40,000	120-277V	✓
	14CDLA4/840/277V	57866	4000K	500/700/1000		83/78/71	110°	80	No	40,000	120-277V	✓
 EMERGENCY INVERTER 35W	35EMINVERTER	58012	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

* IC-Rated - 4" & 6" versions

COMMERCIAL DOWNLIGHT LINE

The adjustable housing clips allow for installation in a large range of commercial and architectural housings. These spring-action clips push up easily and fit securely for both retrofit and new construction installations.



Dimensions

Model	Aperture Min.	Aperture Max.
9.5"	8.6" (220mm)	10.4" (265mm)
8"	7.6" (195mm)	9.4" (240mm)
6"	6.0" (153mm)	7.4" (190mm)
4"	3.9" (100mm)	5.1" (130mm)


Adjustable Lumen Output




- For retrofit or new construction installation
- Universal housing compatibility
- Adjustable lumen output – 3 defined light levels
- Easy fit installation – Spring-action housing clips

SIMPLE RETROFIT OR ECONOMICAL NEW CONSTRUCTION INSTALLATION


Retrofit Installation




Attach safety clip




Bypass ballast & wire to j-box



Adjust lumens to desired output




Push clips up & install into fixture




Ensure fixture is flush. Installation is complete


New Construction Installation




Attach safety clip




Wire to j-box



Adjust lumens to desired output



Push clips up & install into opening



Ensure fixture is flush. Installation is complete

STRIP LINE




QWIKLINK Sensor

SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	DLC
 STRIP 4' 38.5W	NEW! 38.5STRIPDIM/830/277V	28321	3000K	4950	129	120°	N.A.	82	Yes	100,000	120-277V	✓
	38.5STRIPDIM/835/277V	28322	3500K	4950	129	120°	N.A.	82	Yes	100,000	120-277V	✓
	38.5STRIPDIM/840/277V	28323	4000K	5050	131	120°	N.A.	82	Yes	100,000	120-277V	✓
	38.5STRIPDIM/850/277V	28324	5000K	5050	131	120°	N.A.	82	Yes	100,000	120-277V	✓
 STRIP 4' 22.5W	NEW! 22.5STRIPDIM/830/277V	28317	3000K	2500	129	120°	N.A.	82	Yes	100,000	120-277V	✓
	22.5STRIPDIM/835/277V	28318	3500K	2500	129	120°	N.A.	82	Yes	100,000	120-277V	✓
	22.5STRIPDIM/840/277V	28319	4000K	2600	131	120°	N.A.	82	Yes	100,000	120-277V	✓
	22.5STRIPDIM/850/277V	28320	5000K	2600	131	120°	N.A.	82	Yes	100,000	120-277V	✓
 STEP DIMMING MODULE 100/50	To order this option add /STEPPDIM after the model number ex. 38.5STRIPDIM/840/277V/STEPPDIM											
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 38.5STRIPDIM/840/277V/EM											
	To order this and emergency add both: ex. 38.5STRIPDIM/840/277V/STEPPDIM/EM											
	To order this and step dimming add both: ex. 38.5STRIPDIM/840/277V/STEPPDIM/EM											


* STRIP 4" 38.5W meets DLC Premium requirements, STRIP 4" 22.5W meets DLC Standard Requirements

The QWIKLINK connection system uses the latest in toolless technology to easily and seamlessly connect up to 64' of fixtures.




-  **Surface mount, pendant or suspended installation**
-  **LED quick connectors for fast & easy wiring**
-  **120-277V & 0-10V dimming control compatible**
-  **100,000-hr lifetime, 10-yr warranty**

QWIKLINK Sensor - Single Fixture or Entire Row



Even Distribution & Uplighting



ACCESSORIES

Model	Product	Description
STPSENSOR	28388	Microwave Sensor QWIKLINK Connection Module 120-277V - Bi-level - Field Adjustable
SENSORRC	97881	Remote Control for STPSENSOR
JBOXPLATE	28384	J-box Cover Plate
STPBACKPLATE	97906	47.80"x5.31" (1214x135mm) Plate for Covering Form Factor of Old Fixture
WIRECON20	28385	7.9" (20cm) QWIKLINK Cable
WIRECON150	28386	5' QWIKLINK Cable
STP6CABLE	28382	6' Aircraft Cable with Y-toggle (Set of 2 Cables Suitable for 1 Fixture)
STP10CABLE	28383	10' Aircraft Cable with Y-toggle (Set of 2 Cables Suitable for 1 Fixture)
STPPLATE4C	28387	Back Plate for Mechanical Connection Between Suspended Fixtures in a Continuous Run (2 Aircraft Cables Per Fixture)
STPPLATE2C	97855	Back Plate for Mechanical Connection Between Suspended Fixtures in a Continuous Run (1 Aircraft Cable Per Fixture)
PC6	97860	6' Power Cord 18/3 (Not Pre-wired to Fixture)
PC12	97861	12' Power Cord 18/3 (Not Pre-wired to Fixture)


PANEL LINE




SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
 PANEL 2X4' 38W	NEW! 38PAN24DIM/830/277V	28349	3000K	4150	109	95°	N.A.	82	Yes	75,000	120-277V	✓
	38PAN24DIM/835/277V	28350	3500K	4150	109	95°	N.A.	82	Yes	75,000	120-277V	✓
	38PAN24DIM/840/277V	28351	4000K	4300	113	95°	N.A.	82	Yes	75,000	120-277V	✓
	38PAN24DIM/850/277V	28352	5000K	4300	113	95°	N.A.	82	Yes	75,000	120-277V	✓
 PANEL 2X2' 30W	NEW! 30PAN22DIM/830/277V	28345	3000K	3350	112	95°	N.A.	82	Yes	75,000	120-277V	✓
	30PAN22DIM/835/277V	28346	3500K	3350	112	95°	N.A.	82	Yes	75,000	120-277V	✓
	30PAN22DIM/840/277V	28347	4000K	3450	115	95°	N.A.	82	Yes	75,000	120-277V	✓
	30PAN22DIM/850/277V	28348	5000K	3450	115	95°	N.A.	82	Yes	75,000	120-277V	✓
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 38PAN24DIM/840/277V/EM											


SootheOptic low glare technology reduces visual glare and creates a comfortable lighting environment



- ⌚ Recessed, surface mount or suspended installation
- ⌚ Integrated J-box for fast & easy wiring
- ⌚ 120-277V & 0-10V dimming control compatible
- ⌚ 75,000-hr lifetime, 10-yr warranty



Unified Glare Rating (UGR) <19





GREEN CREATIVE Panel
UGR <19

- Comfortable light at all viewing angles
- More useful light
- No perceptible discomfort



Standard LED Panel
UGR >23

- Harsh glare at viewing angles >65°
- More wasted light
- Perceptible discomfort

ACCESSORIES		
Model	Product	Description
MOUNTFRAME24	28391	2X4' Surface Mount Frame
MOUNTFRAME22	28390	2X2' Surface Mount Frame
SUSPCABLE24	28393	70.9" (1.8m) Aircraft Suspension Cable (Set of 6 Cables for 1 2X4' Fixture)
SUSPCABLE22	28392	70.9" (1.8m) Aircraft Suspension Cable (Set of 4 Cables for 1 2X2' Fixture)



ELEVATE
SERIES



Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	DLC PREMIUM	
 TROFFER HE 2X4' 30W	30TROF24DIM/830/277V NEW!	28333	3000K	4200	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	30TROF24DIM/835/277V	28334	3500K	4200	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	30TROF24DIM/840/277V	28335	4000K	4300	143	120°	N.A.	82	Yes	50,000	120-277V	✓
 TROFFER HE 2X2' 25W	25TROF22DIM/830/277V NEW!	28329	3000K	3500	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	25TROF22DIM/835/277V	28330	3500K	3500	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	25TROF22DIM/840/277V	28331	4000K	3600	143	120°	N.A.	82	Yes	50,000	120-277V	✓
 TROFFER HE 1X4' 26W	26TROF14DIM/835/277V NEW!	97939	3500K	3250	125	120°	N.A.	82	Yes	50,000	120-277V	✓
	26TROF14DIM/840/277V	97940	4000K	3300	127	120°	N.A.	82	Yes	50,000	120-277V	✓
 STEP DIMMING MODULE 100/50	To order this option add /STEPMOD after the model number ex. 30TROF24DIM/835/277V/STEPMOD											
 SENSOR	To order this option add /OCCDIM after the model number ex. 30TROF24DIM/835/277V/OCCDIM											
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 30TROF24DIM/835/277V/EM											


TROFFER HE LINE

Easy Installation for New Construction or Retrofit



- High performance lighting distribution
- Exceptional efficacy >140 LPW
- 120-277V & 0-10V dimming control compatible
- 100,000-hr lifetime, 10-yr warranty





0-10V Dimmable



Elevate Your Lighting



INSTALLATION GUIDE



TROFFER RETROFIT KIT HE LINE





SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
 RETROFIT KIT HE 2X4' 30W	30TROFKIT24DIM/830/277V NEW!	28341	3000K	4200	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	30TROFKIT24DIM/835/277V	28342	3500K	4200	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	30TROFKIT24DIM/840/277V	28343	4000K	4300	144	120°	N.A.	82	Yes	100,000	120-277V	✓
 RETROFIT KIT HE 2X2' 25W	25TROFKIT22DIM/830/277V NEW!	28337	3000K	3500	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	25TROFKIT22DIM/835/277V	28338	3500K	3500	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	25TROFKIT22DIM/840/277V	28339	4000K	3600	144	120°	N.A.	82	Yes	100,000	120-277V	✓
 STEP DIMMING MODULE 100/50	To order this option add /STEPDIM after the model number ex. 30TROFKIT24DIM/835/277V/STEPDIM											
	To order this and emergency add both: ex. 30TROFKIT24DIM/835/277V/STEPDIM/EM											
 SENSOR	To order this option add /OCCDIM after the model number ex. 30TROFKIT24DIM/835/277V/OCCDIM											
	To order this and emergency add both: ex. 30TROFKIT24DIM/835/277V/OCCDIM/EM											
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 30TROFKIT24DIM/835/277V/EM											
	To order this and step dimming or sensor add both: ex. 30TROFKIT24DIM/835/277V/STEPDIM/EM											


* Remote control available for SENSOR

TROFFER RETROFIT KIT HE LINE

Universally compatible to upgrade 2x2' and 2x4' troffers and louvers while continuing to utilize the existing luminaire housing.



High-Performance Light Distribution




GREEN CREATIVE Retrofit Kit

Other Retrofit Kit







Housing	Retrofit Kit Dimensions	Retrofit Kit Dimensions (w/o brackets)
2x4'	47.83"x23.94"x2.76"(1215x608x70mm)	46.77"x20.59"x2.76"(1188x523x70mm)
2x2'	23.90"x23.94"x2.76"(607x608x70mm)	22.51"x20.59"x2.76"(572x523x70mm)

-  **High performance lighting distribution**
-  **Exceptional efficacy >140 LPW**
-  **120-277V & 0-10V dimming control compatible**
-  **100,000-hr lifetime, 10-yr warranty**

Elevate Your Lighting



INSTALLATION GUIDE

- 
- 
- 
- 
- 
- 

TRACK LINE



TRACK 33W L
TRACK 22W M




SPECIFICATIONS


	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
	33TRLG4DIM/927/W/H	97623	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/W/H	97629	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	33TRLG4DIM/927/W/J	97624	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/W/J	97630	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	33TRLG4DIM/927/B/H •	97626	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/B/H •	97632	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	33TRLG4DIM/927/B/J •	97627	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/B/J •	97633	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/W/H	97587	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/W/H	97599	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/W/J	97588	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/W/J	97600	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/B/H •	97590	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/B/H •	97602	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/B/J •	97591	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/B/J •	97603	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓

* The J and L type adaptors are compatible with single or two-circuit track types. The H type adaptor is only compatible with single-circuit track types
• Black finish


Interchangeable Lens Options (TRACK L & M)



H - Halo Track





J - Juno Track
For use with single and two-circuit
track applications




L - Lightolier Track (MTO)
For use with single and two-circuit
track applications

Dimensions



TRACK L & M - High CRI



- Exceptional color rendering CRI 90
- Tight LED binning – 4-step Macadam ellipse
- Sleek design, integrated driver
- NF & FL optics ship with TRL & TRM versions

SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Energy Star
8TRSG4DIM/827NF30/W/H	16340	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/W/H	16346	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓
8TRSG4DIM/827NF30/W/J	16341	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/W/J	16347	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓
8TRSG4DIM/827NF30/B/H •	16343	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/B/H •	16349	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓
8TRSG4DIM/827NF30/B/J •	16344	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/B/J •	16350	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓

* The J and L type adaptors are compatible with single or two-circuit track types. The H type adaptor is only compatible with single-circuit track types
• Black finish

HIGH BAY LINE



185W Medium Optic (ME) comes standard



130W Medium Optic (ME) comes standard




95W Prismatic Optic (GP) comes standard

SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Dist.	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Max Temp.	
 HIGH BAY 185W	185HBAY/840/GP NEW!	58227	4000K	22,700	400W HID 324W FLUO.	123	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/840/ME	58228	4000K	25,000		135	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/840/AL	58230	4000K	25,000		135	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/850/GP	58232	5000K	22,700		123	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/850/ME	58233	5000K	25,000		135	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/850/AL	58235	5000K	25,000		135	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
 HIGH BAY 130W	130HBAY/840/GP NEW!	58212	4000K	17,200	250W HID 216W FLUO.	132	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/840/ME	58213	4000K	18,900		145	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/840/AL	58215	4000K	18,900		145	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/850/GP	58217	5000K	17,200		132	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/850/ME	58218	5000K	18,900		145	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/850/AL	58220	5000K	18,900		145	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
 HIGH BAY 95W	95HBAY/840/GP NEW!	58197	4000K	11,800	175W HID 162W FLUO.	125	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/840/ME	58198	4000K	13,100		138	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/840/AL	58200	4000K	13,100		138	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/850/GP	58202	5000K	11,900		125	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/850/ME	58203	5000K	13,200		139	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/850/AL	58205	5000K	13,200		139	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
 347/480V TRANSFORMER	To order this option add /347V after the model number ex. 130HBAY/840/ME/347V													
 SENSOR	Up to 20' Mounting Heights - /OCCDIM20 To order this option add either /OCCDIM20 or /OCCDIM40 after the model number Up to 40' Mounting Heights - /OCCDIM40 ex. 130HBAY/840/ME/347V/OCCDIM40													
 EMERGENCY DRIVER 20W	To order this option add /EM after the model number ex. 130HBAY/840/ME/347V/OCCDIM40/EM													
 SURGE PROTECTOR 10KV	To order this option add /SP after the model number ex. 130HBAY/840/ME/347V/OCCDIM40/EM/SP													


* HIGH BAY 185W GP & 95W GP meet DLC Standard requirements. All other models meet DLC Premium requirements.

Customizable optics, installation and accessories optimize fixture performance to meet all low and high bay application needs




-  **Suspended or pendant mount installation**
-  **2x2' compact form factor with flicker-free driver**
-  **120-277V & 0-10V dimming control compatible**
-  **100,000-hr lifetime, 10-yr warranty**

Mounting Height & Equivalence



Light Distribution - Prismatic, Medium & Aisle



ACCESSORIES

Model	Product	Description
HBAYOCCDIMRC	97859	Remote Control for OCCDIM20 & OCCDIM40
HBAYWG4XMOD	58282	130W & 185W High Bay Wire Guard
HBAYWG2XMOD	58281	95W High Bay Wire Guard
HBAYPENDHANG	58283	Rod/Stem Pendant Mount (Rod/Stem Not Included)
HBAY10CABLE	97862	10' Aircraft Cable & Cable Gripper (For Use with V-hooks)
HBAY20CABLE	97863	20' Aircraft Cable & Cable Gripper (For Use with V-hooks)



GREEN CREATIVE

1200 Bayhill Drive, Suite 220

San Bruno, CA 94066

Tel / Fax: (866) 774-5433

info@greencreative.com

www.greencreative.com



/ GREENCREATIVELED



/ GClightingLED



/ GREEN CREATIVE



GREENCREATIVE



GREENCREATIVE

LAMPS



2017 LAMPS CATALOG



GREEN CREATIVE, founded in 2010, is a solid state lighting development and manufacturing company based in Silicon Valley, CA. The company offers a comprehensive line of high-performance LED lighting solutions which has been widely adopted by some of the largest companies in the world.



2016 Top 10
MUST SEE Products



2017 NA
PRODUCT
SPRINT
2017 WINNER



A complete line with national & international distribution

GREEN CREATIVE's full product line of ENERGY STAR, DLC, NSF & JA8 certified indoor retrofit and new construction lighting solutions serves the Retail, Hospitality, Food & Beverage, Office, Education & Industrial sectors through multiple distribution centers and sales networks across the USA.




Bringing you the latest in LED technology

Anchored by strong integrated R&D capabilities and patented technology, GREEN CREATIVE innovation, performance and reliability have been recognized year after year by the Illuminating Engineering Society Progress Report, the LEDs Magazine Sapphire Awards, Edison Report, NAILD and more.



2017 LAMPS TABLE OF CONTENTS



2017 LAMPS FEATURED PRODUCTS



NEW!



P1-2

PAR REFINE SERIES

Patented REFINE three-part optic
Superior candela & CRI
Enclosed fixture rated

NEW!



P3-4

MR16 75W REPLACEMENT

Industry leading CBCP & efficacy
High CRI 92
Enclosed fixture rated

NEW!



P8

T8 DOUBLE END BYPASS

Wired at both ends
Uses existing lampholders
Meets NSF requirements

NEW!



P11-12

DLC QUALIFIED PL LAMPS

Ballast smart control technology
Exceptional efficacy 120 LPW
0-10V dimming

NEW!



P13

HID LED BOLLARD

Compact form factor
ENERGY STAR® certified
Enclosed fixture rated

NEW!



P21-22

WARM DIM DOWNLIGHT

2700K-2200K warm dimming
For use with 5" & 6" housings
GU24 connector available

PAR LINE




SPECIFICATIONS

	Model		Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 PAR38 17W	17PAR38DIM/927SP15	NEW!	58149	2700K	1150	120W	68	15°	12,200	90	Yes	50,000	120V	Yes	May
	17PAR38DIM/927NF25		58150	2700K	1400	120W	82	25°	7300	90	Yes	50,000	120V	Yes	✓
	17PAR38DIM/927FL40		58151	2700K	1400	120W	82	40°	3100	90	Yes	50,000	120V	Yes	✓
	17PAR38DIM/930SP15		58152	3000K	1200	120W	71	15°	12,500	90	Yes	50,000	120V	Yes	May
	17PAR38DIM/930NF25		58153	3000K	1430	120W	84	25°	7500	90	Yes	50,000	120V	Yes	✓
	17PAR38DIM/930FL40		58154	3000K	1430	120W	84	40°	3200	90	Yes	50,000	120V	Yes	✓
	17PAR38DIM/940FL40		58157	4000K	1450	120W	85	40°	3300	90	Yes	50,000	120V	Yes	✓
	17PAR38DIM/930NF25/B •		97904	3000K	1430	120W	84	25°	7500	90	Yes	50,000	120V	Yes	✓
	17PAR38DIM/930FL40/B •		97905	3000K	1430	120W	84	40°	3200	90	Yes	50,000	120V	Yes	✓
 PAR38 17W 277V	17PAR38/930FL40/277V	NEW!	58163	3000K	1430	120W	84	40°	3200	90	No	50,000	120-277V	Yes	✓
	17PAR38/940FL40/277V		58166	4000K	1450	120W	85	40°	3300	90	No	50,000	120-277V	Yes	✓
 PAR30 13W	13PAR30DIM/927SP15	NEW!	58113	2700K	870	75W	67	15°	7800	90	Yes	50,000	120V	Yes	✓
	13PAR30DIM/927NF25		58114	2700K	1000	90W	77	25°	4500	90	Yes	50,000	120V	Yes	✓
	13PAR30DIM/927FL40		58115	2700K	1000	90W	77	40°	2200	90	Yes	50,000	120V	Yes	✓
	13PAR30DIM/930SP15		58116	3000K	880	75W	68	15°	8000	90	Yes	50,000	120V	Yes	✓
	13PAR30DIM/930NF25		58117	3000K	1050	90W	81	25°	4700	90	Yes	50,000	120V	Yes	✓
	13PAR30DIM/930FL40		58118	3000K	1050	90W	81	40°	2300	90	Yes	50,000	120V	Yes	✓
	13PAR30DIM/940FL40		58121	4000K	1100	90W	85	40°	2500	90	Yes	50,000	120V	Yes	✓
	13PAR30DIM/930FL40/B •		97902	3000K	1050	90W	81	40°	2300	90	Yes	50,000	120V	Yes	✓
 PAR30 13W 277V	13PAR30/930FL40/277V	NEW!	58127	3000K	1050	90W	81	40°	2300	90	No	50,000	120-277V	Yes	✓
	13PAR30/940FL40/277V		58130	4000K	1100	90W	85	40°	2500	90	No	50,000	120-277V	Yes	✓

• Black finish

Patented REFINE Optic




SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 PAR30SN 13W	NEW! 13PAR30SNDIM/927SP15	58140	2700K	870	75W	67	15°	7800	90	Yes	50,000	120V	Yes	✓
	13PAR30SNDIM/927NF25	58141	2700K	1000	90W	77	25°	4500	90	Yes	50,000	120V	Yes	✓
	13PAR30SNDIM/927FL40	58142	2700K	1000	90W	77	40°	2200	90	Yes	50,000	120V	Yes	✓
	13PAR30SNDIM/930SP15	58143	3000K	880	75W	68	15°	8000	90	Yes	50,000	120V	Yes	✓
	13PAR30SNDIM/930NF25	58144	3000K	1050	90W	81	25°	4700	90	Yes	50,000	120V	Yes	✓
	13PAR30SNDIM/930FL40	58145	3000K	1050	90W	81	40°	2300	90	Yes	50,000	120V	Yes	✓
	13PAR30SNDIM/940FL40	58148	4000K	1100	90W	85	40°	2500	90	Yes	50,000	120V	Yes	✓
	13PAR30SNDIM/930FL40/B •	97903	3000K	1050	90W	81	40°	2300	90	Yes	50,000	120V	Yes	✓
 PAR20 8W	NEW! 8PAR20DIM/927SP15	58104	2700K	535	50W	67	15°	5300	90	Yes	50,000	120V	Yes	✓
	8PAR20DIM/927NF25	58105	2700K	535	50W	67	25°	2700	90	Yes	50,000	120V	Yes	✓
	8PAR20DIM/927FL40	58106	2700K	535	50W	67	40°	1170	90	Yes	50,000	120V	Yes	✓
	8PAR20DIM/930SP15	58107	3000K	550	50W	69	15°	5400	90	Yes	50,000	120V	Yes	✓
	8PAR20DIM/930NF25	58108	3000K	550	50W	69	25°	2800	90	Yes	50,000	120V	Yes	✓
	8PAR20DIM/930FL40	58109	3000K	550	50W	69	40°	1200	90	Yes	50,000	120V	Yes	✓
	8PAR20DIM/940FL40	58112	4000K	570	50W	71	40°	1250	90	Yes	50,000	120V	Yes	✓
	8PAR20DIM/930FL40/B •	97901	3000K	550	50W	69	40°	1200	90	Yes	50,000	120V	Yes	✓
 PAR38 19W HO 277V	19PAR38HO/827NF25/277V	97769	2700K	1725	250W	91	25°	10,000	80	No	40,000	120-277V	No	✓
	19PAR38HO/830NF25/277V	97772	3000K	1775	250W	93	25°	10,200	80	No	40,000	120-277V	No	✓
	19PAR38HO/830FL40/277V	97773	3000K	1775	250W	93	40°	4300	80	No	40,000	120-277V	No	✓
	19PAR38HO/840NF25/277V	97778	4000K	1850	250W	97	25°	10,400	80	No	40,000	120-277V	No	✓
	19PAR38HO/840FL40/277V	97779	4000K	1850	250W	97	40°	4600	80	No	40,000	120-277V	No	✓

• Black finish

MR16 LINE



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	ENERGY STAR
 MR16 8.5W	NEW! 8.5MR16DIM/927SP15	57975	2700K	550	75W	65	15°	5900	92	Yes	25,000	12V	Yes	✓
	8.5MR16DIM/927NF25	57976	2700K	550	75W	65	25°	2900	92	Yes	25,000	12V	Yes	✓
	8.5MR16DIM/927FL35	57977	2700K	550	75W	65	35°	1650	92	Yes	25,000	12V	Yes	✓
	8.5MR16DIM/930SP15	57978	3000K	580	75W	68	15°	5950	92	Yes	25,000	12V	Yes	✓
	8.5MR16DIM/930NF25	57979	3000K	580	75W	68	25°	2950	92	Yes	25,000	12V	Yes	✓
	8.5MR16DIM/930FL35	57980	3000K	580	75W	68	35°	1700	92	Yes	25,000	12V	Yes	✓
 MR16 6W	NEW! 6MR16DIM/827FL35	57984	2700K	480	50W	80	35°	1350	82	Yes	25,000	12V	Yes	✓
	6MR16DIM/830FL35	57985	3000K	500	50W	83	35°	1400	82	Yes	25,000	12V	Yes	✓
	6MR16DIM/840FL35	57986	4000K	520	50W	86	35°	1450	82	Yes	25,000	12V	Yes	✓


MR16 LINE

True 75W Halogen Replacement

8.5MR16DIM/930SP15




Degree	Candela
0	5950
5	3837
15	682
25	114
35	16
45	12



8.5MR16DIM/930NF25




Degree	Candela
0	2950
5	2623
15	859
25	204
35	67
45	22



8.5MR16DIM/930FL35



Degree	Candela
0	1700
5	1649
15	1016
25	257
35	33
45	12




- Most efficient high CRI MR16 75W halogen replacement
- Exceptional color rendering CRI 92
- Richer reds and natural skin tones (R9 65, R13 93)
- Suitable for use in totally enclosed fixtures

Enclosed Fixture Rated



MR16 8.5W - High CRI




SPECIFICATIONS

Model		Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 MR16 6W	6MR16DIM/827FL35/35W NEW!	58285	2700K	425	35W	71	35°	910	82	Yes	25,000	12V	Yes	✓
	6MR16DIM/830FL35/35W	58286	3000K	450	35W	75	35°	910	82	Yes	25,000	12V	Yes	✓
 GU10 6W	6GU10DIM/827FL35 NEW!	57987	2700K	480	50W	80	35°	1000	82	Yes	25,000	120V	Yes	✓
	6GU10DIM/830FL35	57988	3000K	500	50W	83	35°	1050	82	Yes	25,000	120V	Yes	✓
 PAR16 6W	6PAR16DIM/827FL35 NEW!	57990	2700K	480	50W	80	35°	1000	82	Yes	25,000	120V	Yes	✓
	6PAR16DIM/830FL35	57991	3000K	500	50W	83	35°	1050	82	Yes	25,000	120V	Yes	✓
 MR11 3W	3MR11/827NF30	40713	2700K	200	20W	67	30°	600	80	No	25,000	12V	Yes	N.A.
	3MR11/840NF30	40715	4000K	220	20W	73	30°	620	80	No	25,000	12V	Yes	N.A.

T5 DIR LINE



Compatible with Electronic Ballasts - Dimmable



High Output (HO) & High Efficiency (HE) Versions




-  **Easy to install – Plug and Play Direct**
-  **Instant Start & Programmed Start ballast compatible**
-  **Suitable for use in totally enclosed fixtures**
-  **Dimmable**

SPECIFICATIONS


	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
	24T5HO/4F/830/DIR	57836	3000K	3000	54W	107	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	24T5HO/4F/835/DIR	57837	3500K	3000	54W	107	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	24T5HO/4F/840/DIR	57838	4000K	3050	54W	109	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	24T5HO/4F/850/DIR	57839	5000K	3200	54W	114	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	15T5HE/4F/830/DIR	57859	3000K	1700	28W	113	120°	N.A.	80	Yes	50,000	120-277V	Yes	✓
	15T5HE/4F/835/DIR	57860	3500K	1750	28W	117	120°	N.A.	80	Yes	50,000	120-277V	Yes	✓
	15T5HE/4F/840/DIR	57861	4000K	1800	28W	120	120°	N.A.	80	Yes	50,000	120-277V	Yes	✓
	12T5HE/3F/830/DIR	57954	3000K	1420	21W	118	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	12T5HE/3F/835/DIR	57955	3500K	1420	21W	118	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	12T5HE/3F/840/DIR	57956	4000K	1500	21W	125	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	8T5HE/2F/830/DIR	57958	3000K	950	14W	119	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	8T5HE/2F/835/DIR	57959	3500K	950	14W	119	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	8T5HE/2F/840/DIR	57960	4000K	1020	14W	128	120°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.



Compatible with Electronic Ballasts - Dimmable



Extra Wide Beam Design - End-to-End Lighting



- Easy to install – Plug and Play Direct
- Instant Start & Programmed Start ballast compatible
- Suitable for use in totally enclosed fixtures
- Shatterproof design – meets NSF requirements

SPECIFICATIONS


	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	DLC
	13T8/4F/840/DIR	28403	4000K	2050	32W	158	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	13T8/4F/850/DIR	28404	5000K	2050	32W	158	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	10.5T8/4F/830/DIR	28397	3000K	1650	32W	157	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	10.5T8/4F/835/DIR	28398	3500K	1650	32W	157	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	10.5T8/4F/840/DIR	28399	4000K	1700	32W	162	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	10.5T8/4F/850/DIR	28400	5000K	1700	32W	162	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	8T8/3F/830/DIR	97837	3000K	1100	25W	138	180°	N.A.	82	Yes	50,000	120-277V	Yes	N.A.
	8T8/3F/835/DIR	97838	3500K	1100	25W	138	180°	N.A.	82	Yes	50,000	120-277V	Yes	N.A.
	8T8/3F/840/DIR	97839	4000K	1150	25W	144	180°	N.A.	82	Yes	50,000	120-277V	Yes	N.A.
	8T8/2F/830/DIR	97841	3000K	1300	17W	163	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	8T8/2F/835/DIR	97842	3500K	1300	17W	163	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	8T8/2F/840/DIR	97843	4000K	1300	17W	163	180°	N.A.	82	Yes	50,000	120-277V	Yes	✓
	10T8G4/2F/850/DIR	40803	5000K	1100	17W	110	180°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	16T8U6G4/830/DIR	40707	3000K	1650	32W	103	160°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	16T8U6G4/840/DIR	40848	3500K	1800	32W	113	160°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.
	16T8U6G4/850/DIR	40849	4000K	1800	32W	113	160°	N.A.	80	Yes	50,000	120-277V	Yes	N.A.

* 10T8G4 DIR lamps are not shatterproof and do not meet NSF requirements

T8 BYP LINE



T8 17.5W
4FT. BYP



BYPass



BYPass Installation - Single Ended

~~BALLAST~~

120-277V
UNIVERSAL



UL1598C classification ensures fixture maintains original UL compliance



Extra Wide Beam Design - End-to-End Lighting

Lamp Front View



Lamp Back View



- Built-in universal voltage driver – Bypass installation
- Wide beam design 310° light emitting area
- Suitable for use in totally enclosed fixtures
- Shatterproof design – meets NSF requirements

DLC QUALITY															
Model		Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.		
 T8 16W 4FT. BYP	16T8/4F/840/BYP	NEW!	28411	4000K	2050	32W	128	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	16T8/4F/850/BYP		28412	5000K	2050	32W	128	160°	N.A.	82	No	50,000	120-277V	Yes	✓
 T8 13W 4FT. BYP	13T8/4F/830/BYP	NEW!	28405	3000K	1650	32W	123	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	13T8/4F/835/BYP		28406	3500K	1650	32W	127	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	13T8/4F/840/BYP		28407	4000K	1700	32W	131	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	13T8/4F/850/BYP		28408	5000K	1700	32W	131	160°	N.A.	82	No	50,000	120-277V	Yes	✓
 T8 12W 3FT. BYP	12T8/3F/830/BYP	NEW!	97893	3000K	1500	25W	125	160°	N.A.	82	No	50,000	120-277V	Yes	N.A.
	12T8/3F/835/BYP		97894	3500K	1500	25W	125	160°	N.A.	82	No	50,000	120-277V	Yes	N.A.
	12T8/3F/840/BYP		97895	4000K	1550	25W	129	160°	N.A.	82	No	50,000	120-277V	Yes	N.A.
 T8 8W 2FT. BYP	8T8/2F/830/BYP	NEW!	28413	3000K	1000	17W	125	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	8T8/2F/835/BYP		28414	3500K	1050	17W	131	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	8T8/2F/840/BYP		28415	4000K	1050	17W	131	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	9T8G4/2F/850/BYP		40789	5000K	1000	17W	111	160°	N.A.	80	No	50,000	120-277V	Yes	N.A.
 T8 17.5W 4FT. BYP	17.5T8/4F/GOLD/BYP		57840	N.A.	1100	32W	63	160°	N.A.	80	No	50,000	120-277V	Yes	N.A.

* 9T8G4 BYP lamps are not shatterproof and do not meet NSF requirements



T8 11.5W
4FT. DEB



BYPass



BYPass Installation - Double Ended

~~BALLAST~~

120-277V
UNIVERSAL




UL1598C classification ensures fixture maintains original UL compliance



Utilizes Existing Non-Shunted or Shunted Lampholders



Non-Shunted



Shunted

- Double-ended BYPass installation – wired at both ends
- Utilizes existing lampholders – non-shunted or shunted
- Easy installation – reduced wiring time
- Shatterproof design – meets NSF requirements

SPECIFICATIONS

Model		Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.		
															
 T8 14.5W 4FT. DEB	14.5T8/4F/840/DEB	NEW!	58270	4000K	2100	32W	145	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	14.5T8/4F/850/DEB		58271	5000K	2100	32W	145	160°	N.A.	82	No	50,000	120-277V	Yes	✓
 T8 11.5W 4FT. DEB	11.5T8/4F/830/DEB	NEW!	58272	3000K	1650	32W	143	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	11.5T8/4F/835/DEB		58273	3500K	1650	32W	143	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	11.5T8/4F/840/DEB		58274	4000K	1700	32W	148	160°	N.A.	82	No	50,000	120-277V	Yes	✓
	11.5T8/4F/850/DEB		58275	5000K	1700	32W	148	160°	N.A.	82	No	50,000	120-277V	Yes	✓
 T8 8.5W 2FT. DEB	8.5T8/2F/830/DEB	NEW!	97934	3000K	1050	17W	124	160°	N.A.	82	No	50,000	120-277V	Yes	June
	8.5T8/2F/835/DEB		97935	3500K	1050	17W	124	160°	N.A.	82	No	50,000	120-277V	Yes	June
	8.5T8/2F/840/DEB		97936	4000K	1100	17W	129	160°	N.A.	82	No	50,000	120-277V	Yes	June

PLL LINE



Support Clip Included

Extra Wide Beam Design - Compact Driver Technology



Compatible with Electronic Ballasts - Dimmable



- Easy to install – Plug & Play Direct
- Instant Start & Programmed Start ballast compatible
- Suitable for use in totally enclosed fixtures
- 0-10V dimming

SPECIFICATIONS


	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.
 PLL 17W DIR	17PLL/830/DIR	97745	3000K	2000	40W	118	120°	N.A.	80	Yes	50,000	120-277V	Yes
	17PLL/835/DIR	97746	3500K	2050	40W	121	120°	N.A.	80	Yes	50,000	120-277V	Yes
	17PLL/840/DIR	97747	4000K	2100	40W	124	120°	N.A.	80	Yes	50,000	120-277V	Yes
 PLL 14.5W DIR	14.5PLL/835/DIR	97750	3500K	1550	36W	107	120°	N.A.	80	Yes	50,000	120-277V	Yes




GX23 (HYBrid)
Replaces 13W



G23 (HYBrid)
Replaces 7-9W



2GX7 (BYPass)
Replaces 13W



2G7 (BYPass)
Replaces 7-9W




Extra Wide Beam Design - 180° Rotatable Base



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.
 PLS V 6.5W HYB GX23	7PLSV/827/HYB/GX23	57931	2700K	550	13W	79	120°	N.A.	82	No	50,000	120-277V	No
	6.5PLSV/830/HYB/GX23	28379	3000K	600	13W	92	120°	N.A.	82	No	50,000	120-277V	No
	6.5PLSV/835/HYB/GX23	28380	3500K	600	13W	92	120°	N.A.	82	No	50,000	120-277V	No
	6.5PLSV/840/HYB/GX23	28381	4000K	620	13W	95	120°	N.A.	82	No	50,000	120-277V	No
 PLS 6W HYB GX23	6PLS/827/HYB/GX23/R	57962	2700K	520	13W	87	120°	N.A.	82	No	50,000	120-277V	No
	6PLS/830/HYB/GX23/R	57963	3000K	550	13W	92	120°	N.A.	82	No	50,000	120-277V	No
	6PLS/835/HYB/GX23/R	57964	3500K	550	13W	92	120°	N.A.	82	No	50,000	120-277V	No
	6PLS/840/HYB/GX23/R	57965	4000K	560	13W	93	120°	N.A.	82	No	50,000	120-277V	No
 PLS 5.5W HYB GX23	5.5PLS/827/HYB/GX23	57820	2700K	450	13W	82	120°	N.A.	80	No	50,000	120-277V	Yes
	5.5PLS/830/HYB/GX23	57821	3000K	500	13W	91	120°	N.A.	80	No	50,000	120-277V	Yes
	5.5PLS/835/HYB/GX23	57822	3500K	500	13W	91	120°	N.A.	80	No	50,000	120-277V	Yes
	5.5PLS/840/HYB/GX23	57823	4000K	520	13W	95	120°	N.A.	80	No	50,000	120-277V	Yes
 PLS 3.5W HYB G23	3.5PLS/827/HYB/G23	57812	2700K	280	7-9W	80	120°	N.A.	80	No	50,000	120-277V	Yes
	3.5PLS/835/HYB/G23	57814	3500K	300	7-9W	86	120°	N.A.	80	No	50,000	120-277V	Yes
 PLS 5.5W BYP 2GX7	5.5PLS/835/BYP/2GX7	57826	3500K	500	13W	91	120°	N.A.	80	No	50,000	120-277V	Yes
 PLS 3.5W BYP 2G7	3.5PLS/835/BYP/2G7	57818	3500K	300	7-9W	86	120°	N.A.	80	No	50,000	120-277V	Yes

PL DIR LINE



Horizontal Installation



Vertical Installation



High Performance - Ballast Smart Control


Ballast Type	Lumens	Bare Lamp
13W	600	4.5W
18W	700	5.5W
26W	1020	8.5W

PL H 8.5W DIR



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	DLC
	8.5PLH/827/DIR	28366	2700K	870	26W	102	110°	N.A.	82	Yes	50,000	120-277V	No	✓
	8.5PLH/830/DIR	28367	3000K	950	26W	112	110°	N.A.	82	Yes	50,000	120-277V	No	✓
	8.5PLH/835/DIR	28368	3500K	950	26W	112	110°	N.A.	82	Yes	50,000	120-277V	No	✓
	8.5PLH/840/DIR	28369	4000K	1020	26W	120	110°	N.A.	82	Yes	50,000	120-277V	No	✓
	10.5PLH/930/DIR	57903	3000K	890	26W	85	110°	N.A.	90	Yes	50,000	120-277V	No	N.A.
	5.5PLH/827/DIR/R	57895	2700K	520	13-18W	95	110°	N.A.	82	Yes	50,000	120-277V	No	N.A.
	5.5PLH/830/DIR/R	57896	3000K	550	13-18W	100	110°	N.A.	82	Yes	50,000	120-277V	No	N.A.
	5.5PLH/835/DIR/R	57897	3500K	550	13-18W	100	110°	N.A.	82	Yes	50,000	120-277V	No	N.A.
	5.5PLH/840/DIR/R	57898	4000K	560	13-18W	102	110°	N.A.	82	Yes	50,000	120-277V	No	N.A.
	9.5PLV/827/DIR	28374	2700K	950	26W	100	120°	N.A.	82	Yes	50,000	120-277V	No	✓
	9.5PLV/830/DIR	28375	3000K	1000	26W	105	120°	N.A.	82	Yes	50,000	120-277V	No	✓
	9.5PLV/835/DIR	28376	3500K	1000	26W	105	120°	N.A.	82	Yes	50,000	120-277V	No	✓
	9.5PLV/840/DIR	28377	4000K	1020	26W	107	120°	N.A.	82	Yes	50,000	120-277V	No	✓
	11PLV/930/DIR	57918	3000K	920	26W	84	120°	N.A.	90	Yes	50,000	120-277V	No	N.A.
	6PLV/827/DIR	28370	2700K	570	13-18W	95	120°	N.A.	82	Yes	50,000	120-277V	No	N.A.
	6PLV/830/DIR	28371	3000K	600	13-18W	100	120°	N.A.	82	Yes	50,000	120-277V	No	N.A.
	6PLV/835/DIR	28372	3500K	600	13-18W	100	120°	N.A.	82	Yes	50,000	120-277V	No	N.A.
	6PLV/840/DIR	28373	4000K	620	13-18W	103	120°	N.A.	82	Yes	50,000	120-277V	No	N.A.




Horizontal Installation



Vertical Installation



BYPass Installation - 2-Pin & 4-Pin



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	DLC
	9.5PLH/827/BYP	28354	2700K	870	26W	92	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	9.5PLH/830/BYP	28355	3000K	920	26W	97	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	9.5PLH/835/BYP	28356	3500K	920	26W	97	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	9.5PLH/840/BYP	28357	4000K	950	26W	100	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/835/BYP/R	57904	3500K	550	13-18W	92	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/840/BYP/R	57905	4000K	560	13-18W	93	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/830/BYP/E26	57925	3000K	550	13W	92	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/835/BYP/E26	57926	3500K	550	13W	92	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/840/BYP/E26	57927	4000K	560	13W	93	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/830/BYP/GU24/R	57928	3000K	550	13W	92	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/835/BYP/GU24/R	57929	3500K	550	13W	92	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	6PLH/840/BYP/GU24/R	57930	4000K	560	13W	93	110°	N.A.	82	No	50,000	120-277V	No	N.A.
	10PLV/827/BYP	28362	2700K	950	26W	95	120°	N.A.	82	No	50,000	120-277V	No	N.A.
	10PLV/830/BYP	28363	3000K	1000	26W	100	120°	N.A.	82	No	50,000	120-277V	No	N.A.
	10PLV/835/BYP	28364	3500K	1000	26W	100	120°	N.A.	82	No	50,000	120-277V	No	N.A.
	10PLV/840/BYP	28365	4000K	1020	26W	102	120°	N.A.	82	No	50,000	120-277V	No	N.A.
	6.5PLV/835/BYP	28360	3500K	600	13-18W	92	120°	N.A.	82	No	50,000	120-277V	No	N.A.
	6.5PLV/840/BYP	28361	4000K	620	13-18W	95	120°	N.A.	82	No	50,000	120-277V	No	N.A.

HID BOLLARD LINE



Optional Lamp Extender
Adds 1.30" (33mm) to lamp height
Dia. x MOL: 1.46"(37mm) x 2.36"(60mm)

Designed for Bollard & Post Top Applications



HID Replacement



**50-70W
HID**

120-277V

- Universal voltage 120-277V – Not compatible with ballasts
- E26 base – ENERGY STAR® certified
- Optional lamp extender available for use in larger fixtures
- Suitable for use in totally enclosed fixtures

SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	ENERGY STAR
 HID LED 16.5W HO 277V	NEW! 16.5A21/830/277V	58238	3000K	2000	50-70W HID	121	330°	N.A.	82	No	40,000	120-277V	Yes	✓
	16.5A21/840/277V	58239	4000K	2000	50-70W HID	121	330°	N.A.	82	No	40,000	120-277V	Yes	✓
	16.5A21/850/277V	58240	5000K	2050	50-70W HID	124	330°	N.A.	82	No	40,000	120-277V	Yes	✓
 E26 LAMP EXTENDER	E26 EXTENDER	16325	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.
 SURGE PROTECTOR 10KV	10SUGRE/277V	97718	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

HID POST TOP LINE



E26 Version Available

E26 Version Available

HID Replacement Values

LED	Lumen Output	MH	MV	HPS
98W	12,800	250W	400W	150W
80W	9600	175W	250W	100W
45W	5400	100W	175W	70W
27W	3200	70W	100W	50W

CoolSink Technology

The CoolSink passive cooling system allows air to flow freely through the lamp. This unique design helps to reduce the operating temperature of the LED and power supply, thus resulting in longer lamp life and lumen maintenance.



- Direct line voltage 120-277V – Not compatible with ballasts
- Designed for use in post top applications
- Compatible with EX39 & E39 sockets
- Suitable for use in totally enclosed fixtures

SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	DLC
 HID LED 98W	98HID/840/277V/EX39	58098	4000K	12,250	250-400W HID	125	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	98HID/850/277V/EX39	58099	5000K	12,800	250-400W HID	131	320°	N.A.	80	No	50,000	120-277V	Yes	✓
 HID LED 80W	80HID/840/277V/EX39/R	57948	4000K	9300	175-250W HID	116	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	80HID/850/277V/EX39/R	57949	5000K	9600	175-250W HID	120	320°	N.A.	80	No	50,000	120-277V	Yes	✓
 HID LED 45W	45HID/830/277V/EX39/R	57938	3000K	5040	100-175W HID	112	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	45HID/840/277V/EX39/R	57939	4000K	5350	100-175W HID	119	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	45HID/850/277V/EX39/R	57940	5000K	5400	100-175W HID	120	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	45HID/840/277V/E26	58008	4000K	5350	100-175W HID	119	320°	N.A.	80	No	50,000	120-277V	Yes	N.A.
	45HID/850/277V/E26	57994	5000K	5400	100-175W HID	120	320°	N.A.	80	No	50,000	120-277V	Yes	N.A.
 HID LED 27W	27HID/830/277V/EX39/R	57935	3000K	3020	70-100W HID	112	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	27HID/840/277V/EX39/R	57936	4000K	3150	70-100W HID	117	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	27HID/850/277V/EX39/R	57937	5000K	3200	70-100W HID	118	320°	N.A.	80	No	50,000	120-277V	Yes	✓
	27HID/840/277V/E26	58006	4000K	3150	70-100W HID	117	320°	N.A.	80	No	50,000	120-277V	Yes	N.A.
	27HID/850/277V/E26	57993	5000K	3200	70-100W HID	118	320°	N.A.	80	No	50,000	120-277V	Yes	N.A.

RESIDENTIAL DOWNLIGHT LINE



JA8
DL 5-6" 12W

HIGH CRI
LED TECHNOLOGY
DL 5-6" 12W
DL 4" 12W



SPECIFICATIONS

Model		Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet	
 DL 5-6” 17.5W	17.5DL6DIM/830	97760	3000K	1150	100W	65	100°	N.A.	80	Yes	35,000	120V	No	✓
	17.5DL6DIM/840	97761	4000K	1200	100W	68	100°	N.A.	80	Yes	35,000	120V	No	✓
 DL 5-6” 10W	10DL6DIM/827	97756	3000K	700	65W	65	100°	N.A.	80	Yes	35,000	120V	No	✓
	10DL6DIM/830	97757	4000K	700	65W	65	100°	N.A.	80	Yes	35,000	120V	No	✓


* GU24 connector available

RESIDENTIAL DOWNLIGHT LINE

Adjustable springs to fit 5-6” housings. High CRI versions rated for wet locations.




Easy Installation



- Compatible with 5-6” and 4” housings
- Installs in just minutes – No rewiring
- High output 1150 lumen version
- High CRI versions rated for wet locations

DOWNLIGHT 5-6” - High CRI



SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet		
 DL 5-6” 12W	12DL6DIM/927	97765	2700K	720	65W	60	100°	N.A.	90	Yes	35,000	120V	Yes	✓
	12DL6DIM/930	97766	3000K	750	65W	63	100°	N.A.	90	Yes	35,000	120V	Yes	✓
 DL 4” 12W	12DL4DIM/927	97762	2700K	600	50W	50	85°	N.A.	90	Yes	35,000	120V	Yes	✓
	12DL4DIM/930	97763	3000K	650	50W	54	85°	N.A.	90	Yes	35,000	120V	Yes	✓

* GU24 connector available



LIGHTING
for
tomorrow

BR30 11W GU24



BR30 11W GU24



BR30 8W



BR30 9.5W
BR30 11W GU24



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 BR40 14W	14BR40DIM/827	40636	2700K	1100	85W	79	110°	N.A.	82	Yes	25,000	120V	Yes	✓
	14BR40DIM/830	40637	3000K	1140	85W	81	110°	N.A.	82	Yes	25,000	120V	Yes	✓
 BR40 9W	9BR40G4DIM/824	40626	2400K	650	65W	72	110°	N.A.	80	Yes	25,000	120V	Yes	N.A.
	9BR40G4DIM/827	40627	2700K	700	65W	78	110°	N.A.	82	Yes	25,000	120V	Yes	✓
 BR30 8W	8BR30G4DIM/824	40770	2400K	585	65W	73	110°	N.A.	80	Yes	25,000	120V	Yes	N.A.
	8BR30DIM/827	40771	2700K	650	65W	81	110°	N.A.	82	Yes	25,000	120V	Yes	✓
	8BR30DIM/830	40772	3000K	685	65W	86	110°	N.A.	82	Yes	25,000	120V	Yes	✓
	8BR30DIM/840	40773	4000K	710	65W	89	110°	N.A.	82	Yes	25,000	120V	Yes	✓

High CRI Version Available in E26 and GU24 Bases




Uses 35% Less Material than Previous Generation



- Revolutionary CLOUD design
- 60% lighter due to environmentally friendly construction
- BR30 high CRI & GU24 versions available
- Suitable for use in totally enclosed fixtures

BR30 9.5W - High CRI



SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.		
 BR30 9.5W	9.5BR30DIM/927	58048	2700K	700	65W	74	110°	N.A.	90	Yes	25,000	120V	Yes	
 BR30 11W GU24	11BR30G4DIM/927/GU24	40646	2700K	750	65W	68	110°	N.A.	92	Yes	25,000	120V	Yes	
 R20 6.5W	6.5R20G4DIM/827	40612	2700K	500	45W	77	110°	N.A.	82	Yes	25,000	120V	Yes	

A19 / A21 LINE



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 A21 17W	17A21G4DIM/827/R	16179	2700K	1600	100W	94	330°	N.A.	80	Yes	25,000	120V	Yes	✓
	17A21G4DIM/830/R	16180	3000K	1650	100W	97	330°	N.A.	80	Yes	25,000	120V	Yes	✓
	17A21G4DIM/840/R	16181	4000K	1700	100W	100	330°	N.A.	80	Yes	25,000	120V	Yes	✓
 A21 17W GU24	17A21DIM/827/GU24	16332	2700K	1600	100W	94	330°	N.A.	80	Yes	25,000	120V	Yes	✓
 A19 12W	12A19G4DIM/827/R	16175	2700K	1100	75W	92	330°	N.A.	80	Yes	25,000	120V	Yes	✓
	12A19G4DIM/830/R	16176	3000K	1150	75W	96	330°	N.A.	80	Yes	25,000	120V	Yes	✓
	12A19G4DIM/840/R	16177	4000K	1180	75W	98	330°	N.A.	80	Yes	25,000	120V	Yes	✓
 A19 9W	9A19DIM/827	97780	2700K	800	60W	89	240°	N.A.	80	Yes	25,000	120V	Yes	✓
	9A19DIM/830	97781	3000K	820	60W	91	240°	N.A.	80	Yes	25,000	120V	Yes	✓
	9A19DIM/840	97782	4000K	860	60W	96	240°	N.A.	80	Yes	25,000	120V	Yes	✓
 A19 8.5W	9A19G4DIM/824	40741	2400K	700	60W	78	300°	N.A.	80	Yes	25,000	120V	No	N.A.
	8.5A19DIM/827/R	57856	2700K	800	60W	94	240°	N.A.	80	Yes	25,000	120V	No	✓
	8.5A19DIM/830/R	57857	3000K	800	60W	94	240°	N.A.	80	Yes	25,000	120V	No	✓
	8.5A19DIM/840/R	57858	4000K	850	60W	100	240°	N.A.	80	Yes	25,000	120V	No	✓
 A19 9W GU24	9A19DIM/827/GU24	97908	2700K	800	60W	89	240°	N.A.	80	Yes	25,000	120V	Yes	✓
	9A19DIM/830/GU24	97909	3000K	820	60W	91	240°	N.A.	80	Yes	25,000	120V	Yes	✓
	9A19DIM/840/GU24	97910	4000K	860	60W	96	240°	N.A.	80	Yes	25,000	120V	Yes	✓
 A19 6W	6A19DIM/827/R	97731	2700K	450	40W	75	240°	N.A.	80	Yes	25,000	120V	No	✓
	6A19DIM/830/R	97732	3000K	450	40W	75	240°	N.A.	80	Yes	25,000	120V	No	✓

A19 / A21 LINE

High CRI 100W, 75W, 60W Replacements & GU24 Versions




- Enclosed rated 100W, 75W & 60W replacements
- High CRI 100W, 75W & 60W replacements
- Enclosed rated GU24 100W & 60W replacements
- 120-277V universal voltage 60W replacement

Omnidirectional Lighting




A21 18.5W - High CRI



SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 A21 18.5W	18.5A21DIM/927	16329	2700K	1600	100W	86	330°	N.A.	90	Yes	25,000	120V	Yes	✓
 A21 3-WAY 5.5/10.5/17W	17A21G4/827/3WAY	16335	2700K	500 1000 1600	40W 75W 100W	91 95 94	330°	N.A.	80	No	25,000	120V	No	✓
 A21 15W	15A21DIM/927	16326	2700K	1100	75W	73	330°	N.A.	90	Yes	25,000	120V	Yes	✓
 A19 9W 277V	NEW! 9A19/827/277V	58037	2700K	800	60W	89	240°	N.A.	82	No	25,000	120-277V	Yes	✓
	9A19/830/277V	58038	3000K	820	60W	91	240°	N.A.	82	No	25,000	120-277V	Yes	✓
	9A19/840/277V	58039	4000K	860	60W	96	240°	N.A.	82	No	25,000	120-277V	Yes	✓

WARM DIM LINE



WARM DIM



SPECIFICATIONS


	Model		Product	CCT	Lumens Equiv. (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 DL 11W WARM DIM	11DL6DIM/8CCTD	NEW!	58100	2										

All Warm Dim Lamps Feature 2700K-2200K CCT Dimming




- Smooth dimming from 2700K-2200K CCT
- Traditional incandescent style dimming
- Exceptional efficacy
- Available in Downlight, BR, A19 & Candle lamps

Lighting for Any Occasion



2700K-2200K Warm Dim



CREATE THE PERFECT AMBIENCE



+ 2700K

- 2200K



These GREEN CREATIVE lamps feature 2700K-2200K CCT dimming designed to replicate the warm dimming effect of traditional incandescent light sources. As the lamp dims, its CCT gradually warms, helping to create the perfect ambience for all occasions.

FILAMENT LINE



SPECIFICATIONS

Model		Product	CCT	Lumens (lm)	Equiv. LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Finish		
 A19 7.5W	7.5FA19DIM/827	57891	2700K	800	60W	107	330°	N.A.	80	Yes	15,000	120V	Clear	✓
 A19 4.5W	4.5FA19DIM/827/R	57971	2700K	450	40W	100	330°	N.A.	80	Yes	15,000	120V	Clear	✓
 G25 4.5W	4.5FG25DIM/													

Vintage Incandescent Lighting Effect



Suitable for All Decorative Applications



Micro-Designed Driver - Fully Dimmable



Eligible products meet ENERGY STAR requirements

- Fully omnirectional beam angle
- Micro-designed driver - No heatsink required
- Comfortable warm diffused light
- Smooth dimming with existing installations

SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv. LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Finish	
-------	---------	-----	-------------	------------	------------	-----------	------------	-----	------------	---------	--------	--




- 60W & 40W incandescent replacements
- Innovative crown lens creates unique sparkling effect
- Available in E12 & E26 bases
- Smooth dimming with existing installations

Crown Lens - Omnidirectional Lighting



Suitable for All Decorative Applications



SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	Energy Star	
 G25 6W	6G25DIM/827	97729	2700K	450	40W	75	275°	N.A.	80	Yes	25,000	120V	No	✓
 B11 5.5W E12 & E26	5.5B11DIM/827	97823	2700K	500	60W	91	230°	N.A.	80	Yes	25,000	120V	No	✓
	5.5B11DIM/827/E26	97824	2700K	500	60W	91	230°	N.A.	80	Yes	25,000	120V	No	✓
 B11 5W E12	5B11G4DIM/827/FR	40730	2700K	350	40W	70	275°	N.A.	82	Yes	25,000	120V	No	✓
 B11 4.5W E12 & E26	4.5B11DIM/827/R	97817	2700K	300	40W	64	230°	N.A.	80	Yes	25,000	120V	No	✓
	4.5B11DIM/827/E26	97818	2700K	300	40W	64	230°	N.A.	80	Yes	25,000	120V	No	✓



GREENCREATIVE


Bringing You the Latest in LED Technology



PANEL ELEVATE SERIES

PANEL PRODUCT FEATURES

Edge Lighting Technology



BACK PLATE

FOAM ALIGNING PLATE

REFLECTOR

LIGHT GUIDE PLATE

DIFFUSER

 SootheOptic
LOW GLARE

EDGE LIGHTING

TRIM

The PANEL ELEVATE Series uses the latest in edge lighting technology to produce a smooth uniform lighting effect. These sleek, low glare panels create a comfortable environment and install easily in all ceiling applications.


SootheOptic Low Glare Technology



Glare Control Diffuser

PANEL PRODUCT FEATURES

Unified Glare Rating (UGR) <19



GREEN CREATIVE Panel
UGR <19


- Comfortable light at all viewing angles
- More useful light
- No perceptible discomfort

Standard LED Panel
UGR >23

- Harsh glare at viewing angles >65°
- More wasted light
- Perceptible discomfort



Healthcare





Education





PANEL SERIES

PANEL 2X2' 30W



- 3450lm
- 115 LPW
- Low glare UGR <19
- 120-277V universal voltage
- 0-10V dimming
- 3000K, 3500K & 4000K CCT
- 75,000-hr lifetime 10-yr warranty

PANEL 2X4' 38W





GREENCREATIVE


Bringing You the Latest in LED Technology



STRIP QWIKLINK SERIES

STRIP PRODUCT FEATURES


QWIKLINK Connection System



QWIKLINK Connector

STRIP PRODUCT FEATURES

Even Distribution & Uplighting



STRIP QWIKLINK SERIES

STRIP 4' 22.5W & STRIP 4' 38.5W







GREENCREATIVE

Bringing You the Latest in LED Technology



SURFACE MOUNT DOWNLIGHT PRODUCT FEATURES

Edge Lighting Technology



BACK PLATE

WATERPROOF FOAM</

SURFACE MOUNT CEILING SERIES

9", 7" & 5.5" SQUARE SURFACE MOUNT DOWNLIGHTS



9" 20W


7" 15W

5.5" 10W



- Dimmable
- 9" 1200lm / 7" 850lm / 5.5" 550lm
- High CRI 90, R9 50 & R13 90
- Low glare
- Wet location rated
- 2700K / 3000K / 4000K CCT
- 50,000-hr lifetime

9", 7" & 5.5" ROUND SURFACE MOUNT DOWNLIGHTS



9" 20W

7" 15W

5.5" 10W



- Dimmable
- 9" 1200lm / 7" 850lm / 5.5" 550lm
- High CRI 90, R9 50 & R13 90
- Low glare
- Wet location rated
- 2700K / 3000K / 4000K CCT
- 50,000-hr lifetime

High CRI & Wet Location Rated



Specifications

	Model	Product	CCT	Power (W)	Lumens (lm)	Equiv.	LPW	Beam Angle	CRI (typ.)	Dim	Life (hrs)	Voltage	
	20SMPS9DIM/930	58242	3000K	20	1200	100W	60	100°	90	Yes	50,000	120V	✓
	20SMPS9DIM/940	58243	4000K	20	1250	100W	63	100°	90	Yes	50,000	120V	✓
	15SMPS7DIM/927	58244	2700K	15	850	75W	57	100°	90	Yes	50,000	120V	✓
	15SMPS7DIM/930	58245	3000K	15	850	75W	57	100°	90	Yes	50,000	120V	✓
	15SMPS7DIM/940	58246	4000K	15	870	75W	58	100°	90	Yes	50,000	120V	✓
	10SMPS5.5DIM/927	58247	2700K	10	550	50W	55	100°	90	Yes	50,000	120V	✓
	10SMPS5.5DIM/930	58248	3000K	10	550	50W	55	100°	90	Yes	50,000	120V	✓
	10SMPS5.5DIM/940	58249	4000K	10	560	50W	56	100°	90	Yes	50,000	120V	✓
	20SMPR9DIM/930	58255	3000K	20	1200	100W	60	100°	90	Yes	50,000	120V	✓
	20SMPR9DIM/940	58256	4000K	20	1250	100W	63	100°	90	Yes	50,000	120V	✓
	15SMPR7DIM/927	58257	2700K	15	850	75W	57	100°	90	Yes	50,000	120V	✓
	15SMPR7DIM/930	58258	3000K	15	850	75W	57	100°	90	Yes	50,000	120V	✓
	15SMPR7DIM/940	58259	4000K	15	870	75W	58	100°	90	Yes	50,000	120V	✓
	10SMPR5.5DIM/927	58260	2700K	10	550	50W	55	100°	90	Yes	50,000	120V	✓
	10SMPR5.5DIM/930	58261	3000K	10	550	50W	55	100°	90	Yes	50,000	120V	✓
	10SMPR5.5DIM/940	58262	4000K	10	560	50W	56	100°	90	Yes	50,000	120V	✓

Accessory Ordering Information

Model	Product	Description
SMP/ACC	58033	4" or 6" Recessed Can Accessories for 5.5" & 7" Round & Square (5.5" for Use in 4" Can Only, 7" for Use in 4" or 6" Can)





GREENCREATIVE

Bringing You the Latest in LED Technology



HIGH BAY SERIES

HIGH BAY PRODUCT FEATURES

HYPERBAY Series




CoolSink open air design
with vented housing

Lightweight, sturdy
construction

Flicker-free driver


Aisle, medium &
general light distributions



The 95W, 130W & 185W HIGH BAYS all come in compact 2x2' form factors and are available in three different beam distributions. These low glare and flicker-free luminaires are designed for both low and high bay applications.

Mounting Height & Equivalence


The HYPERBAY SERIES' customizable optics, installation and accessories optimize fixture performance to meet all low and high bay application needs.



HIGH BAY PRODUCT FEATURES


Light Distribution - Low Glare & Flicker Free

PRISMATIC (GP)




Application: Open floor at low to medium mounting heights
Beam Distribution: 100°

MEDIUM (ME)



Application: Open floor at medium to high mounting heights
Beam Distribution: 80°

AISLE (AL)



Application: Aisle or rack at low to high mounting heights
Beam Distribution: 90° (0° viewing angle)
45° (90° viewing angle)

Solutions for Low & High Bay Applications



Manufacturing



Warehouse



Exhibition Hall



Gymnasium

HIGH BAY PRODUCT FEATURES

Warehouse Case Study

GREEN CREATIVE Aisle Optic HIGH BAY 130W

Standard LED without Aisle Optic HIGH BAY 160W

40% LESS FIXTURES REQUIRED
>50% ENERGY SAVINGS





Total Luminaires: 42
Total Load: 5485W




Total Luminaires: 72
Total Load: 11,347W

GREATER FLOOR & SHELVING ILLUMINATION
NO LIGHT WASTED – UNIFORM DISTRIBUTION



Average Floor Surface Lux: 172



Average Floor Surface Lux: 139

GREEN CREATIVE solution:

- ① – Better floor surface illumination
- ② – Consistent shelving illumination, especially on lower shelves
- ③ – Uniform light distribution with no light wasted on higher shelves

Sample Room: Area: 330x100ft. Ceiling Height: 40ft. Mounting Height: 30ft. Rack Height: 20ft.

HIGH BAY SERIES

Options & Accessories



OCCUPANCY SENSORS

- PIR Photo/Motion sensors for 20' or 40' mounting heights
- Options available for all HIGH BAYS (factory installation)

EMERGENCY BACKUP

- 20W emergency backup unit for 90 minutes of illumination
- Option available for all HIGH BAYS (factory installation)




AIRCRAFT CABLE

- 10' and 20' aircraft cable & cable gripper (for use with V-hooks)
- Accessory sold separately for all HIGH BAYS

PENDANT MOUNT

- For rod and stem pendant mounting with adjustable positioning
- Accessory sold separately for all HIGH BAYS



WIRE GUARD


- Single module version available for 95W HIGH BAY
- Double module version available for 130W & 185W HIGH BAYS
- Accessories sold separately for all HIGH BAYS

HIGH BAY SERIES

HIGH BAY 95W



Prismatic Optic (GP) comes standard



Medium Optic (ME) option




Aisle Optic (AL) option

- 11,900lm (GP optic)
- 125 LPW
- 120-277V universal voltage
- 0-10V dimming
- Rated for -22°F/-30°C to 131°F/55°C
- 4000K & 5000K CCT
- 100,000-hr lifetime 10-yr warranty
- V-hooks come standard with fixture

HIGH BAY 130W



Medium Optic (ME) comes standard



Aisle Optic (AL) option




Prismatic Optic (GP) option

- 18,900lm (ME optic)
- 145 LPW
- 120-277V universal voltage
- 0-10V dimming
- Rated for -22°F/-30°C to 131°F/55°C
- 4000K & 5000K CCT
- 100,000-hr lifetime 10-yr warranty
- V-hooks come standard with fixture

HIGH BAY 185W



Medium Optic (ME) comes standard



Aisle Optic (AL) option



Prismatic Optic (GP) option

- 25,000lm (ME optic)
- 135 LPW
- 120-277V universal voltage
- 0-10V dimming
- Rated for -22°F/-30°C to 131°F/55°C
- 4000K & 5000K CCT
- 100,000-hr lifetime 10-yr warranty
- V-hooks come standard with fixture


HIGH BAY PRODUCT FEATURES



95HBAY/850/GP

Zonal Distribution

Luminaire Lumens	12,067
Total Luminaire Efficiency	100%
Luminaire Efficacy	125
Total Luminaire Watts	96.46



Zone	Lumens	%Luminaire
0-20	1963.78	16.3
0-30	4134.4	34.3
0-40	6610.16	54.8
0-60	10,481.59	86.9
0-80	11,938.49	98.9
0-90	12,057.29	99.9

Specifications

Model	CCT	Lumens (lm)	LPW	Distribution	CRI (typ.)	Dim	DLC
95HBAY/840/GP	4000K	11,800	125	100°	82	Yes	Standard
95HBAY/840/ME	4000K	13,100	138	80°	82	Yes	Premium
95HBAY/840/AL	4000K	13,100	138	45°/90°	82	Yes	Premium
95HBAY/850/GP	5000K	11,900	125	100°	82	Yes	Standard
95HBAY/850/ME	5000K	13,200	139	80°	82	Yes	Premium
95HBAY/850/AL	5000K	13,200	139	45°/90°	82	Yes	Premium




HIGH BAY 95W

130HBAY/850/ME

Zonal Distribution


Luminaire Lumens	19,068
Total Luminaire Efficiency	100%
Luminaire Efficacy	145
Total Luminaire Watts	131.32



Zone	Lumens	%Luminaire
0-20	4718.88	24.7
0-30	10,325.48	54.2
0-40	15,746.28	82.6
0-60	18,663.15	97.9
0-80	19,040.13	99.9
0-90	19,055.85	99.9

Specifications

Model	CCT	Lumens (lm)	LPW	Distribution	CRI (typ.)	Dim	DLC
130HBAY/840/GP	4000K	17,200	132	100°	82	Yes	Premium
130HBAY/840/ME	4000K	18,900	145	80°	82	Yes	Premium
130HBAY/840/AL	4000K	18,900	145	45°/90°	82	Yes	Premium
130HBAY/850/GP	5000K	17,200	132	100°	82	Yes	Premium
130HBAY/850/ME	5000K	18,900	145	80°	82	Yes	Premium
130HBAY/850/AL	5000K	18,900	145	45°/90°	82	Yes	Premium




HIGH BAY 130W

185HBAY/850/ME

Zonal Distribution

Luminaire Lumens	25,159
Total Luminaire Efficiency	100%
Luminaire Efficacy	136
Total Luminaire Watts	185.26



Zone	Lumens	%Luminaire
0-20	6210.65	24.7
0-30	13,554.08	53.9
0-40	20,686.36	82.2
0-60	24,626.88	97.9
0-80	25,122.35	99.9
0-90	25,142.98	99.9

Specifications

Model	CCT	Lumens (lm)	LPW	Distribution	CRI (typ.)	Dim	DLC
185HBAY/840/GP	4000K	22,700	123	100°	82	Yes	Standard
185HBAY/840/ME	4000K	25,000	135	80°	82	Yes	Premium
185HBAY/840/AL	4000K	25,000	135	45°/90°	82	Yes	Premium
185HBAY/850/GP	5000K	22,700	123	100°	82	Yes	Standard
185HBAY/850/ME	5000K	25,000	135	80°	82	Yes	Premium
185HBAY/850/AL	5000K	25,000	135	45°/90°	82	Yes	Premium



HIGH BAY 185W

HIGH BAY ORDERING INFORMATION

Product Ordering Information

Must Select				Options (Factory Installation): Select or Leave Blank				
Power	CRI	CCT	Optics	Voltage	Sensor	EM Backup	Surge Protector	Power Cord
95HBAY 95W	8 82	35 3500K (MTO)	GP General Prismatic	(Blank) 120-277V	(Blank) None	(Blank) None	(Blank) None	(Blank) None
130HBAY 130W		40 4000K	ME Medium	347V 347-480V	OCCDIM20 20' Occupancy Dimming	EM 20W EM Backup	SP Surge Protector 10kV	PC6 6' Power Cord
185HBAY 185W		50 5000K	AL Aisle		OCCDIM40 40' Occupancy Dimming			PC12 12' Power Cord

Ex. 185HBAY/850/ME/OCC40/EM/SP/PC12

Accessory Ordering Information

Model	Product	Description
HBAYOCCDIMRC	97859	Remote Control for OCCDIM20 & OCCDIM40
HBAYWG2XMOD	58281	95W High Bay Wire Guard
HBAYWG4XMOD	58282	130W & 185W Wire Guard
HBAYPENDHANG	58283	Rod/Stem Pendant Mount (Rod/Stem Not Included)
HBAY10CABLE	97862	10' Aircraft Cable & Cable Gripper (For Use with V-hooks)
HBAY20CABLE	97863	20' Aircraft Cable & Cable Gripper (For Use with V-hooks)



GREEN CREATIVE
1200 Bayhill Drive, Suite 220
San Bruno, CA 94066

Tel / Fax: (866) 774-5433
info@greencreative.com
www.greencreative.com

f / GREENCREATIVELED
t / GClightingLED
in / GREEN CREATIVE



GREENCREATIVE

Bringing You the Latest in LED Technology


THINFIT
SERIES



NEW CONSTRUCTION THINFIT SERIES

NEW CONSTRUCTION DOWNLIGHT PRODUCT FEATURES

Edge Lighting Technology



INTEGRATED J-BOX

EDGE LIGHTING


REFLECTOR

LIGHT GUIDE PLATE

DIFFUSER

The 6" & 4" NEW CONSTRUCTION DOWNLIGHTS use the latest in edge lighting technology to produce a smooth uniform lighting effect. These naturally low glare downlights integrate seamlessly into all ceiling applications.


Integrated J-box - Pre-installed Wire Clamp & Quick Connects




These downlights install quickly in both new construction and remodel installations. All wiring takes place inside the integrated J-box which features a pre-installed wire clamp, quick connects and an easily removable lid. Save time and materials with these easy to install downlights.

Installs Directly into Ceiling - No J-box or Housing Needed

No J-box or Recessed Can Required





Suitable for Shallow Ceiling Applications
IC-Rated



These downlights install directly into the ceiling without the need for an additional J-box or recessed can. The slim design allows these IC-Rated downlights to fit into any ceiling, including those with shallow ceiling space.

NEW CONSTRUCTION THINFIT SERIES

6" NEW CONSTRUCTION DOWNLIGHT 11.6W



- Dimmable
- 810lm / 830lm / 850lm
- 2700K / 3000K / 4000K CCT
- 40,000-hr lifetime
- Goof Ring available


11.6W REPLACES



**75W
Inc.**

80% Energy Savings

4" NEW CONSTRUCTION DOWNLIGHT 8.5W



- Dimmable
- 510lm / 530lm / 550lm
- 2700K / 3000K / 4000K CCT
- 40,000-hr lifetime
- Goof Ring available

8.5W REPLACES



**50W
Inc.**

80% Energy Savings

New Construction or Remodel Installation



Installation Instructions

fig.1




fig.2




fig.3




fig.4




fig.5




fig.6





fig.7



1. Make sure the **POWER IS TURNED OFF** at the source to the area in which you are installing the product.
2. Using a pencil, trace the provided cardboard cutout on the ceiling (fig. 1). Cut the hole following the inside of the traced circle (fig. 2). If using a hole cutter, set the diameter to 6.3" (160mm) for the 11.6DLNC6DIM/xxx and 4.25" (108mm) for the 8.5DLNC4DIM/xxx.
3. Pull up on the tab to remove the J-box lid on the downlight (fig. 3) and insert the incoming wire through the plastic J-box wire clamp (fig. 4). If using flex conduit, insert through adjacent knockout.
4. Insert wires into the downlight quick connectors (black to black, white to white) and cap off the ground using the provided wire nut (fig. 4). Replace J-box lid and push down on the front tab until it clicks when done (fig. 5).
5. Push up the spring-action clips and insert the downlight into the ceiling (fig. 6). Release the springs and make sure the downlight is secure and sitting flush in the ceiling (fig. 7).
6. Restore power at the source and the installation is complete.



Specifications

	Model	Product	CCT	Power (W)	Lumens (lm)	LPW	Beam Angle	CRI (typ.)	Dim	Life (hrs)	Voltage	
 DLNC 6" 11.6W	11.6DLNC6DIM/827	58028	2700K	11.6	810	70	100°	82	Yes	40,000	120V	✓
	11.6DLNC6DIM/830	58029	3000K	11.6	830	72	100°	82	Yes	40,000	120V	✓
	11.6DLNC6DIM/840	58030	4000K	11.6	850	73	100°	82	Yes	40,000	120V	✓
 DLNC 4" 8.5W	8.5DLNC4DIM/827	58025	2700K	8.5	510	60	100°	82	Yes	40,000	120V	✓
	8.5DLNC4DIM/830	58026	3000K	8.5	530	62	100°	82	Yes	40,000	120V	✓
	8.5DLNC4DIM/840	58027	4000K	8.5	550	65	100°	82	Yes	40,000	120V	✓

Accessory Ordering Information

Model	Product	Description
DLNC4GOOF/R	97847	THINFIT Series 4" Goof Ring
DLNC6GOOF/R	97848	THINFIT Series 6" Goof Ring

* Suitable for damp locations



GREEN CREATIVE
1200 Bayhill Drive, Suite 220
San Bruno, CA 94066

Tel / Fax: (866) 774-5433
info@greencreative.com
www.greencreative.com

f / GREENCREATIVELED
t / GCLightingLED
in / GREEN CREATIVE