



# LED LIGHTING

## CATALOG

02-03 INTELLIBULB LINE

04-09 A-LINE

10-15 DECORATIVE

16-25 REFLECTORS

26-31 RETROFIT KITS

32-33 ORIGINAL VINTAGE

34-37 COLOR & SPECIALTY

38-39 PL & LINEAR

20  
17

Switch to Dim

Color Choice

Dusk to Dawn

Voice Control

Battery Backup

Motion Activated

## LED **intellibulb**™

- Up to 15,000 hours of LED light
- No smart home hardware required
- Intellibulb line includes:
  - Dusk to Dawn
  - Motion Activated
  - Switch to Dim
  - Color Choice
  - Battery Backup
  - Voice Control
- For more information visit [www.feit.com](http://www.feit.com)

# INTELLIBULB LINE

## Dusk to Dawn™



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	DIM
A800/827/DD/LEDI	60	9.5	800	15,000	≥80	240°	E26	2700K	120	4.4"	2.35"	N
A800/850/DD/LEDI	60	9.5	800	15,000	≥80	240°	E26	5000K	120	4.4"	2.35"	N

## Motion Activated™



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	DIM
A450/827/MM/LEDI	40	6	450	15,000	≥80	240°	E26	2700K	120	4.4"	2.35"	N

## Switch to Dim™



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	DIM
A800/3DIM/LEDI	60	9	800	15,000	≥80	240°	E26	2700K	120	4.4"	2.35"	Y*
BR30/827/3DIM/LEDI	65	9.5	650	15,000	≥80	110°	E26	2700K	120	4.4"	2.35"	Y*

\*Dimmable via standard light switch only. May work on a dimmer switch at full brightness. Performance may vary.

## Color Choice™



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	DIM
A800/CCT/LEDI	60	9.5	750	15,000	≥80	240°	E26	27K / 4K / 5K	120	4.4"	2.35"	Y
BR30/CCT/LEDI	65	9	650	15,000	≥80	110°	E26	27K / 4K / 5K	120	4.4"	2.35"	Y

## Battery Backup™



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	DIM
A800/827/BAT/LEDI	40	8.5	600	15,000	≥80	240°	E26	2700K	120	4.4"	2.35"	N

## Voice Control™



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	DIM
A800/827/VCE/LEDI	60	10	800	15,000	≥80	240°	E26	2700K	120	4.4"	2.35"	Y*

\*Dimmable via voice commands only. Works on a standard light switch, may work on a dimmer switch at full brightness. Performance may vary.



# A-LINE

## household lights

- Non-dimmable and dimmable
- Plastic and glass
- White and clear finish
- E26 and GU24 bases
- 2700K, 3000K, 3500K, 4100K and 5000K CCT
- Lasts up to 35,000 hours
- UL or ETL listed

# A-LINE

## 10 Year Non-Dimmable – A-Shape



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
A450/827/10KLED	40	6	450	11,000	≥80	White	E26	2700K	120	4.4"	2.35"	N	
A450/827/10KLED/2	40	6	450	11,000	≥80	White	E26	2700K	120	4.4"	2.35"	N	
A450/827/10KLED/4	40	6	450	11,000	≥80	White	E26	2700K	120	4.4"	2.35"	N	
A450/830/10KLED/3	40	6	450	11,000	≥80	White	E26	3000K	120	4.4"	2.35"	N	
A450/835/10KLED/2	40	5.5	450	11,000	≥80	White	E26	3500K	120	4.4"	2.35"	N	
A450/850/10KLED/2	40	5.5	450	11,000	≥80	White	E26	5000K	120	4.4"	2.35"	N	
A450/850/10KLED/4	40	5.5	450	11,000	≥80	White	E26	5000K	120	4.4"	2.35"	N	
A800/827/10KLED	60	9	800	11,000	≥80	White	E26	2700K	120	4.4"	2.35"	N	
A800/827/10KLED/2	60	9	800	11,000	≥80	White	E26	2700K	120	4.4"	2.35"	N	
A800/827/10KLED/4	60	9	800	11,000	≥80	White	E26	2700K	120	4.4"	2.35"	N	
A800/830/10KLED/3	60	9.5	800	11,000	≥80	White	E26	3000K	120	4.4"	2.35"	N	
A800/830/10KLED/8/CAN	60	9.5	800	11,000	≥80	White	E26	3000K	120	4.4"	2.35"	N	
A800/830/10KLED/10	60	9.5	800	11,000	≥80	White	E26	3000K	120	4.4"	2.35"	N	
A800/835/10KLED	60	8.5	800	11,000	≥80	White	E26	3500K	120	4.4"	2.35"	N	
A800/835/10KLED/2	60	8.5	800	11,000	≥80	White	E26	3500K	120	4.4"	2.35"	N	
A800/835/10KLED/4	60	8.5	800	11,000	≥80	White	E26	3500K	120	4.4"	2.35"	N	
A800/841/10KLED	60	8.5	800	11,000	≥80	White	E26	4100K	120	4.4"	2.35"	N	
A800/850/10KLED	60	8.5	800	11,000	≥80	White	E26	5000K	120	4.4"	2.35"	N	
A800/850/10KLED/2	60	8.5	800	11,000	≥80	White	E26	5000K	120	4.4"	2.35"	N	
A800/850/10KLED/4	60	8.5	800	11,000	≥80	White	E26	5000K	120	4.4"	2.35"	N	
A800/850/10KLED/10	60	9.5	800	11,000	≥80	White	E26	5000K	120	4.4"	2.35"	N	
A1100/827/10KLED	75	11.2	1100	11,000	≥80	White	E26	2700K	120	5.2"	2.7"	N	
A1100/827/10KLED/2	75	11.2	1100	11,000	≥80	White	E26	2700K	120	5.2"	2.7"	N	
A1100/850/10KLED/2	75	11.2	1100	11,000	≥80	White	E26	5000K	120	5.2"	2.7"	N	
A1600/827/10KLED	100	14.7	1500	11,000	≥80	White	E26	2700K	120	5.2"	2.7"	N	
A1600/827/10KLED/2	100	14.7	1500	11,000	≥80	White	E26	2700K	120	5.2"	2.7"	N	
A1600/850/10KLED/2	100	14.5	1500	11,000	≥80	White	E26	5000K	120	5.2"	2.7"	N	

### 13 Year Non-Dimmable & Dimmable – A-Shape



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
OM40/830/15KLED/CAN	40	5.6	450	15,000	≥80	White	E26	3000K	120	4.4"	2.3"	■	Y
OM60/830/15KLED/3	60	9.5	800	15,000	≥80	White	E26	3000K	120	4.4"	2.3"	■	N
OM60/830/15KLED/CAN	60	9.5	800	15,000	≥80	White	E26	3000K	120	4.4"	2.3"	■	Y
OM60830/15KLED/3/CAN	60	9.5	800	15,000	≥80	White	E26	3000K	120	4.4"	2.3"	■	Y



### 13 & 18 Year Dimmable Glass – A-Shape



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
A1940/LED/2	40	4.5	450	20,000	≥80	Frost	E26	2700K	120	4"	2.25"		Y
A1940/CL/LED/2	40	4.5	450	20,000	≥80	Clear	E26	2700K	120	4"	2.25"		Y
BPA1940/CL/LED/2/CAN	40	4.5	450	20,000	≥80	Clear	E26	2700K	120	4"	2.25"		Y
A1960/LED/2	60	7	800	20,000	≥80	Frost	E26	2700K	120	4"	2.25"		Y
A1960/CL/LED/2	60	7	800	20,000	≥80	Clear	E26	2700K	120	4"	2.25"	■	Y
BPA1960/CL/LED/2/CAN	60	7	800	20,000	≥80	Clear	E26	2700K	120	4"	2.25"		Y
A1960/850/LED/2	60	7	800	20,000	≥80	Frost	E26	5000K	120	4"	2.25"		Y
A1960/CL/850/LED/2	60	7	800	20,000	≥80	Clear	E26	5000K	120	4"	2.25"		Y
A1960/827/FILED/3	60	9	750	15,000	≥80	White	E26	2700K	120	4"	2.25"		Y
A1960CL827FILED3/CAN	60	8.5	800	20,000	≥80	Clear	E26	2700K	120	4"	2.25"		Y
A1960CL850FILED3/CAN	60	7	800	20,000	≥80	Clear	E26	5000K	120	4"	2.25"		Y
BPA19100/CL/FILED/2	100	12	1500	15,000	≥80	Clear	E26	2700K	120	4.5"	2.6"		Y
BPA19100CL850FILED/2	100	12	1500	15,000	≥80	Clear	E26	5000K	120	4.5"	2.6"		Y

# A-LINE

## 22 Year Dimmable – A-Shape



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPOM40/830/LED	40	5.6	450	25,000	≥80	White	E26	3000K	120	4.5"	2.35"	■	Y
OM40/830/LED/CAN	40	5.6	450	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
OM40/830/LED/3/CAN	40	5.6	450	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
OM40/830/LED/4	40	5.6	450	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
OM40/830/LEDG2/2	40	5.6	450	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
BPOM40/850/LED	40	5.6	450	25,000	≥80	White	E26	5000K	120	4.5"	2.35"	■	Y
OM40/850/LED/4	40	5.6	450	25,000	≥80	White	E26	5000K	120	4.5"	2.3"	■	Y
OM40/850/LEDG2/2	40	5.6	450	25,000	≥80	White	E26	5000K	120	4.5"	2.3"	■	Y
Ⓜ AOM800/827/LED/HBR	60	9	800	25,000	≥80	White	E26	2700K	120	4.8	2.35		Y*
Ⓜ AOM800827LED/HBR/CAN	60	9	800	25,000	≥80	White	E26	2700K	120	4.8	2.35		Y*
BPOM60/830/LED	60	9.5	800	25,000	≥80	White	E26	3000K	120	4.5"	2.35"	■	Y
OM60/830/LED/CAN	60	9.5	800	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
OM60/830/LED/4	60	9	800	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
OM60830/LED/3/CAN	60	9.5	800	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
OM60/830/LEDG2/2	60	9.5	800	25,000	≥80	White	E26	3000K	120	4.5"	2.3"	■	Y
OM60/841/LED	60	9.5	800	25,000	≥80	White	E26	4100K	120	4.5"	2.3"	■	Y
BPOM60/850/LED	60	9	800	25,000	≥80	White	E26	5000K	120	4.5"	2.35"	■	Y
OM60/850/LED/CAN	60	9.5	800	25,000	≥80	White	E26	5000K	120	4.5"	2.3"	■	Y
OM60/850/LED/3/CAN	60	9.5	800	25,000	≥80	White	E26	5000K	120	4.5"	2.3"	■	Y
OM60/850/LED/4	60	9.5	800	25,000	≥80	White	E26	5000K	120	4.5"	2.3"	■	Y
BPOM60/850/LEDG2	60	9.5	800	25,000	≥80	White	E26	5000K	120	4.5"	2.3"	■	Y
OM60/850/LEDG2/2	60	9.5	800	25,000	≥80	White	E26	5000K	120	4.5"	2.3"	■	Y
BPOM60/927/LED	60	9.8	800	25,000	≥90	White	E26	2700K	120	4.5"	2.3"	■	Y
OM60/927/LED/CAN	60	9.8	800	25,000	≥90	White	E26	2700K	120	4.5"	2.3"	■	Y
OM60/927/LED/2	60	9.8	800	25,000	≥90	White	E26	2700K	120	4.5"	2.3"	■	Y
OM60/830/LEDG2/COLD	60	10	800	25,000	≥80	White	E26	3000K	120	4.5"	2.3"		Y
OM75/827/LED	75	11.5	1100	25,000	≥80	White	E26	2700K	120	4.5"	2.5"	■	Y
BPOM75/830/LEDG2	75	11	1100	25,000	≥80	White	E26	3000K	120	4.5"	2.5"	■	Y
OM75/830/LEDG2	75	11	1100	25,000	≥80	White	E26	3000K	120	5"	2.7"	■	Y
BPOM75/850/LEDG2	75	11	1100	25,000	≥80	White	E26	5000K	120	5"	2.7"	■	Y
OM75/850/LEDG2	75	11	1100	25,000	≥80	White	E26	5000K	120	5"	2.7"	■	Y
OM100/827/LED	100	15	1600	25,000	≥80	White	E26	2700K	120	5"	2.7"	■	Y
OM100/830/LEDG2	100	15	1600	25,000	≥80	White	E26	3000K	120	5"	2.7"	■	Y
OM100/830/LEDG2/CAN	100	15	1600	25,000	≥80	White	E26	3000K	120	5"	2.7"	■	Y

CONTINUE →

## 22 Year Dimmable – A-Shape



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPOM100/830/LEDG2	100	15	1600	25,000	≥80	White	E26	3000K	120	5.2"	2.7"	■	Y
OM100/850/LEDG2	100	15	1600	25,000	≥80	White	E26	5000K	120	5.2"	2.7"	■	Y
BPOM100/850/LEDG2	100	15	1600	25,000	≥80	White	E26	5000K	120	5.2"	2.7"	■	Y
OM100/830/LED/CAN	100	17	1600	25,000	≥80	White	E26	3000K	120	4.7"	2.5"	■	Y
OM100/830/LED/3/CAN	100	17	1600	25,000	≥80	White	E26	3000K	120	4.7"	2.5"	■	Y
OM100/850/LED/CAN	100	17	1600	25,000	≥80	White	E26	5000K	120	4.7"	2.5"	■	Y



## High Lumen

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
A/OM2200/830/LEDG2	150	21	2200	25,000	≥80	180°	E26	3000K	120	5"	2.7"		Y
A/OM2200/850/LEDG2	150	21	2200	25,000	≥80	180°	E26	5000K	120	5"	2.7"		Y
C4000/5K/LED	300	38	4000	35,000	≥80	270°	E26	5000K	120	8.9"	3"		N
C10000/5K/LED	500	100	10000	25,000	≥80	300°	E26	5000K	120	10"	4"		N
C15000/5K/LED	750	125	15000	25,000	≥80	300°	E26	5000K	120	10"	4"		N



## 12 Volt Non-Dimmable – A-Shape

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPA800/830/LED-12	60	10.5	800	15,000	≥80	White	E26	3000K	12	4"	2.25"		N



## 22 Year Dimmable – Squat Bulb

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PU60/830/LED	60	6	800	25,000	≥80	White	E26	3000K	120	2.8"	2.95"		Y
PU60/830/LED/GU24	60	6	800	25,000	≥80	White	GU24	3000K	120	2.8"	2.95"		Y



# A-LINE



## 10 Year Dimmable – GU24

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
A60DM827GU2410KLED/2	60	10	800	11,000	≥80	White	GU24	2700K	120	3.9"	2.3"		Y
A60DM850GU2410KLED/2	60	10	800	11,000	≥80	White	GU24	5000K	120	3.9"	2.3"		Y



## 22 Year Dimmable – GU24

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPA19DM/800/GU24/LED	60	9	800	25,000	≥80	White	GU24	3000K	120	4.25"	2.35"		Y
A19/DM/800/GU24/LED	60	9.9	800	25,000	≥80	White	GU24	3000K	120	4.5"	2.5"		Y
A19DM800GU24/LED/CAN	60	9.9	800	25,000	≥80	White	GU24	3000K	120	4.5"	2.5"		Y
A19DM800GU24/850/LED	60	9.9	800	25,000	≥80	White	GU24	5000K	120	4.5"	2.5"		Y



## 13 Year Glass – 3-WAY

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
A30/100/830/FILED	30/70/100	5/9/12	500/1000/1500	15,000	≥80	White	E26	3000K	120	5"	2.68"		N
A30/100/850/FILED	30/70/100	5/9/12	500/1000/1500	15,000	≥80	White	E26	5000K	120	5"	2.68"		N



## 22 Year – 3-WAY

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
A30/100/LEDG2	30/70/100	5/10/16	500/1050/1600	25,000	≥80	White	E26	2700K	120	4.75"	2.25"		N
A30/100/LEDG2/CAN	30/70/100	5/10/16	500/1050/1600	25,000	≥80	White	E26	2700K	120	4.75"	2.25"		N
A50/150/LEDG2	50/100/150	7/15/21	800/1600/2200	25,000	≥80	White	E26	2700K	120	5"	2.7"		N
A50/150/850/LEDG2	50/100/150	7/15/21	800/1600/22000	25,000	≥80	White	E26	5000K	120	5"	2.7"		N



# A15 LINE

## decorative lights

- Non-dimmable and dimmable
- Plastic and glass
- White, clear and frost finish
- E12, E17 and E26 bases
- 2700K, 3000K and 5000K CCT
- Lasts up to 15,000 hours
- UL or ETL listed

# A15 LINE



## 10 Year Non-Dimmable – A15

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
A1540/10KLED/3	40	5	300	11,000	≥80	White	E26	3000K	120	3.4"	1.9"		N
A1540C/10KLED/3	40	5	300	11,000	≥80	White	E12	3000K	120	3.4"	1.9"		N
A1540C/850/10KLED/3	40	4.5	300	11,000	≥80	White	E12	5000K	120	3.4"	1.9"		N
A1560/10KLED/3	60	8	500	11,000	≥80	White	E26	3000K	120	3.4"	1.9"		N
A1560C/10KLED/3	60	6	500	11,000	≥80	White	E12	3000K	120	3.4"	1.9"		N
A1560C/850/10KLED/3	60	6	500	11,000	≥80	White	E12	5000K	120	3.4"	1.9"		N



## 13 Year Dimmable Glass – A15

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPA1525/827/LED/2	25	3	200	15,000	≥80	Clear	E26	2700K	120	3.1"	1.85"		Y
BPA1540/827/LED/2	40	4.5	300	15,000	≥80	Clear	E26	2700K	120	3.1"	1.85"		Y
BPA1540827LED/2/CAN	40	4.5	300	15,000	≥80	Clear	E26	2700K	120	3.1"	1.85"		Y
BPA1540/850/LED/2	40	4.5	300	15,000	≥80	Clear	E26	5000K	120	3.1"	1.85"		Y
BPA1540850LED/2/CAN	40	4.5	300	15,000	≥80	Clear	E26	5000K	120	3.1"	1.85"		Y
BPA1540/F/827/LED/2	40	4.5	300	15,000	≥80	Frost	E26	2700K	120	3.1"	1.85"		Y
BPA1540C/827/LED/2	40	4.5	300	15,000	≥80	Clear	E12	2700K	120	3.4"	1.85"		Y
BPA1540C827LED/2/CAN	40	4.5	300	15,000	≥80	Clear	E12	2700K	120	3.4"	1.85"		Y
BPA1540C/850/LED/2	40	4.5	300	15,000	≥80	Clear	E12	5000K	120	3.4"	1.85"		Y
BPA1540N/827/LED/2	40	4.5	300	15,000	≥80	Clear	E17	2700K	120	3.4"	1.85"		Y
BPA1560/827/LED/2	60	6	500	15,000	≥80	Clear	E26	2700K	120	3.1"	1.85"		Y
BPA1560827LED/2/CAN	60	6	500	15,000	≥80	Clear	E26	2700K	120	3.1"	1.85"		Y
BPA1560/850/LED/2	60	6	500	15,000	≥80	Clear	E26	5000K	120	3.1"	1.85"		Y
BPA1560C/827/LED/2	60	6	500	15,000	≥80	Clear	E12	2700K	120	3.4"	1.85"		Y
BPA1560C827LED/2/CAN	60	6	500	15,000	≥80	Clear	E12	2700K	120	3.4"	1.85"		Y
BPA1560C/850/LED/2	60	6	500	15,000	≥80	Clear	E12	5000K	120	3.4"	1.85"		Y
BPA1560C850LED/2/CAN	60	6	500	15,000	≥80	Clear	E12	5000K	120	3.4"	1.85"		Y
BPA1560C/F/827/LED/2	60	6	500	15,000	≥80	Frost	E12	2700K	120	3.4"	1.85"		Y
BPA1560N/827/LED/2	60	6	500	15,000	≥80	Clear	E17	2700K	120	3.4"	1.85"		Y

# GLOBE

## decorative lights

- Non-dimmable and dimmable
- Plastic and glass
- White and clear finish
- E12 and E26 bases
- 2700K, 3000K and 5000K CCT
- Lasts up to 15,000 hours
- UL or ETL listed

# GLOBE -G16½ & G25



## 13 Year Dimmable Glass Globe – G16½

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPG1640/827/LED/2	40	4.5	300	15,000	≥80	Clear	E12	2700K	120	3.2"	1.9"		Y
BPG1640827/LED/2/CAN	40	4.5	300	15,000	≥80	Clear	E12	2700K	120	3.2"	1.9"		Y
BPGM40/827/LED/2	40	4.5	300	15,000	≥80	Clear	E26	2700K	120	2.7"	1.9"		Y
BPGM40827/LED/2/CAN	40	4.5	300	15,000	≥80	Clear	E26	2700K	120	2.7"	1.9"		Y
BPG1660/827/LED/2	60	6	500	15,000	≥80	Clear	E12	2700K	120	3.2"	1.9"		Y
BPG1660827/LED/2/CAN	60	6	500	15,000	≥80	Clear	E12	2700K	120	3.2"	1.9"		Y
BPGM60/827/LED/2	60	6	500	15,000	≥80	Clear	E26	2700K	120	2.7"	1.9"		Y



## 10 Year Non-Dimmable Globe – G25

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
G2540/10KLED/3	40	5	350	11,000	≥80	White	E26	3000K	120	4.35"	3.15"		N
G2560/10KLED/3	60	8.5	650	11,000	≥80	White	E26	3000K	120	4.35"	3.15"		N
G2560/850/10KLED/3	60	8.5	650	11,000	≥80	White	E26	5000K	120	4.35"	3.15"		N

## 13 Year Dimmable Glass Globe – G25

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPG2525/827/LED	25	3	200	15,000	≥80	Clear	E26	2700K	120	4.5"	3.1"		Y
BPG2525/F/827/LED	25	3	200	15,000	≥80	White	E26	2700K	120	4.5"	3.1"		Y
BPG2540/827/LED	40	4.5	300	15,000	≥80	Clear	E26	2700K	120	4.5"	3.1"		Y
BPG2540/827/LED/CAN	40	4.5	300	15,000	≥80	Clear	E26	2700K	120	4.5"	3.1"		Y
BPG2540/F/827/LED	40	4.5	300	15,000	≥80	White	E26	2700K	120	4.5"	3.1"		Y
BPG2540F/827/LED/CAN	40	4.5	300	15,000	≥80	White	E26	2700K	120	4.5"	3.1"		Y
BPG2540/850/LED	40	4.5	300	15,000	≥80	Clear	E26	5000K	120	4.5"	3.1"		Y
BPG2540/F/850/LED	40	4.5	300	15,000	≥80	White	E26	5000K	120	4.5"	3.1"		Y
BPG2560/827/LED	60	5.5	500	15,000	≥80	Clear	E26	2700K	120	4.5"	3.1"	■	Y
BPG2560/827/LED/CAN	60	5.5	500	15,000	≥80	Clear	E26	2700K	120	4.5"	3.1"	■	Y
BPG2560/F/827/LED	60	5.5	500	15,000	≥80	White	E26	2700K	120	4.5"	3.1"	■	Y
BPG2560F/827/LED/CAN	60	5	500	15,000	≥80	White	E26	2700K	120	4.5"	3.1"	■	Y
BPG2560/850/LED	60	5.5	500	15,000	≥80	Clear	E26	5000K	120	4.5"	3.1"	■	Y
BPG2560/F/850/LED	60	5.5	500	15,000	≥80	White	E26	5000K	120	4.5"	3.1"	■	Y





# CHANDELIER

## decorative lights

- Non-dimmable and dimmable
- Plastic and glass
- Blunt and flame tip
- Clear and frost finish
- E12 and E26 bases
- 2700K, 3000K and 5000K CCT
- Lasts up to 15,000 hours
- UL or ETL listed

# CHANDELIER

## 10 Year Non-Dimmable Chandelier



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	SHAPE	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
CTF40/10KLED/3	40	4.5	300	11,000	≥80	Blunt	White	E12	3000K	120	3.9"	1.4"		N
ETF40/10KLED/3	40	4.5	300	11,000	≥80	Blunt	White	E26	3000K	120	3.9"	1.4"		N

## 13 Year Dimmable Glass Chandelier & Plastic Bluetooth® Chandelier



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	SHAPE	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPCFC25/827/LED/2	25	3	200	15,000	≥80	Flame	Clear	E12	2700K	120	4.3"	1.3"		Y
BPEFC25/827/LED/2	25	3	200	15,000	≥80	Flame	Clear	E26	2700K	120	3.9"	1.3"		Y
BPCTC25/827/LED/2	25	3	200	15,000	≥80	Blunt	Clear	E12	2700K	120	3.9"	1.3"		Y
BPETC25/827/LED/2	25	3	200	15,000	≥80	Blunt	Clear	E26	2700K	120	3.5"	1.3"		Y
BPCTC25827/LED/2/CAN	25	3	200	15,000	≥80	Blunt	Clear	E12	2700K	120	3.9"	1.3"		Y
BPCTC40/827/LED/2	40	3.8	300	15,000	≥80	Blunt	Clear	E12	2700K	120	3.9"	1.3"	■	Y
BPCTC40827/LED/2/CAN	40	3.8	300	15,000	≥80	Blunt	Clear	E12	2700K	120	3.9"	1.3"	■	Y
BPCTC40/850/LED/2	40	4.5	300	15,000	≥80	Blunt	Clear	E12	5000K	120	3.9"	1.3"		Y
BPETC40/827/LED/2	40	4.5	300	15,000	≥80	Blunt	Clear	E26	2700K	120	3.5"	1.3"		Y
BPETC40827/LED/2/CAN	40	4.5	300	15,000	≥80	Blunt	Clear	E26	2700K	120	3.5"	1.3"		Y
BPETC40/850/LED/2	40	4.5	300	15,000	≥80	Blunt	Clear	E26	5000K	120	3.5"	1.3"		Y
BPCFC40/827/LED/2	40	3.8	300	15,000	≥80	Flame	Clear	E12	2700K	120	4.3"	1.3"	■	Y
BPCFC40/827/LED/4	40	3.8	300	15,000	≥80	Flame	Clear	E12	2700K	120	4.3"	1.3"	■	Y
BPCFC40/850/LED/2	40	4.5	300	15,000	≥80	Flame	Clear	E12	5000K	120	4.3"	1.3"		Y
BPEFC40/827/LED/2	40	4.5	300	15,000	≥80	Flame	Clear	E26	2700K	120	3.9"	1.3"		Y
BPEFC40/850/LED/2	40	4.5	300	15,000	≥80	Flame	Clear	E26	5000K	120	3.9"	1.3"		Y
BPCFF40/827/LED/2	40	4.5	300	15,000	≥80	Flame	Frost	E12	2700K	120	4.3"	1.3"		Y
BPCTC60/827/LED/2	60	5.5	500	15,000	≥80	Blunt	Clear	E12	2700K	120	3.9"	1.3"	■	Y
BPCTC60827/LED/2/CAN	60	5.5	500	15,000	≥80	Blunt	Clear	E12	2700K	120	3.9"	1.3"	■	Y
BPCTC60/850/LED/2	60	5.5	500	15,000	≥80	Blunt	Clear	E12	5000K	120	3.9"	1.3"	■	Y
BPCTC60850/LED/2/CAN	60	6	500	15,000	≥80	Blunt	Clear	E12	5000K	120	3.9"	1.3"		Y
BPETC60/827/LED/2	60	5.5	500	15,000	≥80	Blunt	Clear	E26	2700K	120	3.5"	1.3"	■	Y
BPETC60827/LED/2/CAN	60	5.5	500	15,000	≥80	Blunt	Clear	E26	2700K	120	3.5"	1.3"	■	Y
BPCFC60/827/LED/2	60	5.5	500	15,000	≥80	Flame	Clear	E12	2700K	120	4.3"	1.3"	■	Y
BPCFC60/850/LED/2	60	5.5	500	15,000	≥80	Flame	Clear	E12	5000K	120	4.3"	1.3"	■	Y
BPCFF60/827/LED/2	60	5.5	500	15,000	≥80	Flame	Frost	E12	2700K	120	4.3"	1.3"	■	Y
BPEFC60/827/LED/2	60	5.5	500	15,000	≥80	Flame	Clear	E26	2700K	120	3.9"	1.3"	■	Y
BPEFC60/850/LED/2	60	5.5	500	15,000	≥80	Flame	Clear	E26	5000K	120	3.9"	1.3"	■	Y
BPETC60/850/LED/2	60	5.5	500	15,000	≥80	Flame	Clear	E26	5000K	120	3.5"	1.3"	■	Y
Ⓢ CFC/300/LED/HBR	40	4.5	300	25,000	≥80	Flame	Clear	E26	2700K	120	4.8"	1.6"		Y*
Ⓢ CFC/300/LED/HBR/CAN	40	4.5	300	25,000	≥80	Flame	Clear	E26	2700K	120	4.8"	1.6"		Y*





## R & BR

### flood reflectors

- Non-dimmable and dimmable
- Plastic and glass
- 2700K, 3000K and 5000K CCT
- Lasts up to 25,000 hours
- UL or ETL listed



# FLOOD REFLECTOR LINE

## 22 Year Dimmable – R14 & R16



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPR14DM/LED	40	4.5	300	25,000	≥80	110°	E26	2700K	120	2.2"	1.5"		Y
BPR14DM/LED/CAN	40	4.5	300	25,000	≥80	110°	E26	2700K	120	2.2"	1.5"		Y
BPR16DM/LED	40	6.5	400	25,000	≥80	110°	E26	2700K	120	3.5"	2"		Y
BPR16DM/LED/CAN	40	6.5	400	25,000	≥80	110°	E26	2700K	120	3.5"	2"		Y

## 10 Year Non-Dimmable & Dimmable – R20



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
R20/10KLED/3/CAN	45	7.5	450	11,000	≥80	110°	E26	2700K	120	3.8"	2.5"		N
R20DM/10KLED/2	45	7.5	450	11,000	≥80	110°	E26	2700K	120	3.8"	2.5"		Y
R20DM/10KLED/MP/6	45	7.5	450	11,000	≥80	110°	E26	2700K	120	3.8"	2.5"		Y
R20DM/850/10KLED/2	45	7.5	450	11,000	≥80	110°	E26	5000K	120	3.8"	2.5"		Y

## 13 Year Dimmable Glass – R20



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
R2045/827/FILED/2	45	7	450	15,000	≥80	110°	E26	2700K	120	3.8"	2.5"		Y
R2045/850/FILED/2	45	7	450	15,000	≥80	110°	E26	5000K	120	3.8"	2.5"		Y

## 22 Year Non-Dimmable & Dimmable – R20



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
R20DM45/LED	45	6.8	480	25,000	≥80	110°	E26	2700K	120	3.8"	2.5"	■	Y
R20DM45/LED/2	45	6.8	480	25,000	≥80	110°	E26	2700K	120	3.8"	2.5"	■	Y
R20DM45/LED/CAN	45	6.8	480	25,000	≥80	110°	E26	2700K	120	3.8"	2.5"	■	Y
R20DM45/850/LED	45	6.8	480	25,000	≥80	110°	E26	5000K	120	3.8"	2.5"	■	Y
R20DM45/850/LED/CAN	45	6.8	480	25,000	≥80	110°	E26	5000K	120	3.8"	2.5"	■	Y
R2045/927/LED	45	7.3	450	25,000	≥90	110°	E26	2700K	120	3.8"	2.5"	■	Y
R20HO/LEDG2	65	10	650	25,000	≥80	110°	E26	2700K	120	3.8"	2.5"		Y

## 10 Year Non-Dimmable & Dimmable – BR30



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BR30/10KLED/3	65	8.5	650	11,000	≥80	110°	E26	2700K	120	5"	3.75"		N
BR30/10KLED/3/CAN	65	8.5	650	11,000	≥80	110°	E26	2700K	120	5"	3.75"		N
BR30/850/10KLED/3	65	9.5	650	11,000	≥80	110°	E26	5000K	120	5"	3.75"		N
BR30/DM/10KLED/6	65	10.5	650	11,000	≥80	110°	E26	2700K	120	5"	3.75"		Y
BR30DM/10KLED/2	65	10.5	650	11,000	≥80	110°	E26	2700K	120	5"	3.75"		Y
BR30DM/10KLED/MP/12	65	10.5	650	11,000	≥80	110°	E26	2700K	120	5"	3.75"		Y
BR30DM/850/10KLED/2	65	10.5	650	11,000	≥80	110°	E26	5000K	120	5"	3.75"		Y

## 13 Year Dimmable Glass – BR30



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BR3065/827/FILED/2	65	9	650	15,000	≥80	110°	E26	2700K	120	5"	3.75"		Y
BR3065/850/FILED/2	65	9	650	15,000	≥80	110°	E26	5000K	120	5"	3.75"		Y

## 22 Year Dimmable – BR30



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BR30DM65/LED	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y
BR3065/DM/LED/CAN	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y
BR30/DM/LEDG3/2	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y
BR30DM/LEDG3/2/CAN	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y
BR30DM65/LED/4	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y
BR30DM65/5K/LED/4	65	9	650	25,000	≥80	110°	E26	5000K	120	5"	3.75"	■	Y
BR30DM65/LED/6	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y
BR30DM65/850/LED	65	9	650	25,000	≥80	110°	E26	5000K	120	5"	3.75"	■	Y
BR30DM65/850/LED/CAN	65	9	650	25,000	≥80	110°	E26	5000K	120	5"	3.75"	■	Y
BR30/650/LED/HBR	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"		Y*
BR30/650/LED/HBR/CAN	65	9	650	25,000	≥80	110°	E26	2700K	120	5"	3.75"		Y*
BR3065/927/LED	65	11.5	750	25,000	≥90	110°	E26	2700K	120	5"	3.75"	■	Y
BR30/927/LED/CAN	65	11.5	750	25,000	≥90	110°	E26	2700K	120	5"	3.75"	■	Y
BR30DM/LEDG2/CAN	65	10.5	750	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y
BR30DM85/850/LED	85	16.5	1150	25,000	≥80	110°	E26	5000K	120	5"	3.75"	■	Y
BR30HO/LEDG2	85	16	1100	25,000	≥80	110°	E26	2700K	120	5"	3.75"	■	Y

# FLOOD REFLECTOR LINE



## 10 Year Dimmable – BR40

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BR40DM/10KLED/2	65	12.5	850	11,000	≥80	110°	E26	2700K	120	6.3"	5"		Y
BR40DM/10KLED/MP/12	65	12.5	850	11,000	≥80	110°	E26	2700K	120	6.3"	5"		Y
BR40DM/850/10KLED/2	65	12.5	850	11,000	≥80	110°	E26	2700K	120	6.3"	5"		Y



## 13 Year Dimmable Glass – BR40

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BR4065/827/FILED/2	65	10	850	15,000	≥80	110°	E26	2700K	120	6.3"	5"		Y
BR4065/850/FILED/2	65	10	850	15,000	≥80	110°	E26	5000K	120	6.3"	5"		Y



## 22 Year Dimmable – BR40

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BR40DM75/850/LED	75	13	1000	25,000	≥80	110°	E26	5000K	120	6.3"	5"	■	Y
BR40DM75/850/LED/2	75	13	1000	25,000	≥80	110°	E26	5000K	120	6.3"	5"	■	Y
BR40DM75/LED	75	15	1050	25,000	≥80	110°	E26	2700K	120	6.3"	5"	■	Y
BR40DM75/LED/2	75	15	1050	25,000	≥80	110°	E26	2700K	120	6.3"	5"	■	Y
BR4075/927/LED	75	15.5	1065	25,000	≥90	110°	E26	2700K	120	6.3"	5"	■	Y
BR40HO/LEDG2	120	19	1400	25,000	≥80	110°	E26	2700K	120	6.3"	5"		Y
BR40/DM/2500/3K/LED	250	30	2500	25,000	≥80	110°	E26	3000K	120	6.3"	5"		Y





## PAR & MR

### narrow spot & spot reflectors

- Non-dimmable and dimmable
- White and silver finish
- E26, GU10, GU5.3 and GU4 bases
- 3000K and 5000K CCT
- Lasts up to 25,000 hours
- UL or ETL listed

# NARROW SPOT & SPOT REFLECTOR LINE



## 22 Year Dimmable – PAR16

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR16/830/LEDG11/CAN	45	5	350	25,000	≥80	40°	E26	3000K	120	3"	2"	■	Y
PAR16/850/LEDG11/CAN	45	5	350	25,000	≥80	40°	E26	5000K	120	3"	2"	■	Y



## 10 Year Non-Dimmable & Dimmable – PAR20

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR2050/10KLED/3	50	7	500	11,000	≥80	40°	E26	3000K	120	3.3"	2.5"		N
PAR2050/10KLED/3/CAN	50	7	500	11,000	≥80	40°	E26	3000K	120	3.3"	2.5"		N
PAR2050/850/10KLED/3	50	7	500	11,000	≥80	40°	E26	5000K	120	3.3"	2.5"		N
PAR2050DM/10KLED/6	50	6.5	455	11,000	≥80	40°	E26	3000K	120	3.3"	2.5"		Y

## 22 Year Dimmable – PAR20

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR20/830/LEDG11	50	6.5	455	25,000	≥80	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20/830/LEDG11/2	50	6.5	455	25,000	≥80	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20/850/LEDG11	50	6.5	455	25,000	≥80	40°	E26	5000K	120	3.2"	2.5"	■	Y
PAR20/850/LEDG11/2	50	6.5	455	25,000	≥80	40°	E26	5000K	120	3.2"	2.5"	■	Y
PAR20/830/LEDG11/CAN	50	6.5	455	25,000	≥80	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20/850/LEDG11/CAN	50	6.5	455	25,000	≥80	40°	E26	5000K	120	3.2"	2.5"	■	Y
PAR20/SP/LEDG10	50	7	450	25,000	≥80	28°	E26	3000K	120	3.2"	2.5"	■	Y
Ⓡ PAR20/LED/HBR/CAN	50	7.5	450	25,000	≥80	40°	E26	3000K	120	3.2"	2.5"		Y*
PAR20/930/LEDG11/CAN	50	7.5	460	25,000	≥90	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20830LEDG11/2/CAN	50	6.5	455	25,000	≥80	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20830LEDG11/3/CAN	50	6.5	455	25,000	≥80	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20850LEDG11/2/CAN	50	6.5	455	25,000	≥80	40°	E26	5000K	120	3.2"	2.5"	■	Y
PAR20850LEDG11/3/CAN	50	6.5	455	25,000	≥80	40°	E26	5000K	120	3.2"	2.5"	■	Y
BPPAR20830LEDG11/CAN	50	6.5	455	25,000	≥80	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20/930/LEDG11	50	7.5	460	25,000	≥90	40°	E26	3000K	120	3.2"	2.5"	■	Y
PAR20/930/LEDG11/2	50	7.5	460	25,000	≥90	40°	E26	3000K	120	3.2"	2.5"	■	Y





### 10 Year Non-Dimmable – PAR30

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR30L75/10KLED/3	75	10.5	750	11,000	≥80	40°	E26	3000K	120	4.75"	3.75"		N



### 22 Year Dimmable – PAR30 Short Neck

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR30S/830/LEDG11	75	10.5	750	25,000	≥80	40°	E26	3000K	120	3.55"	3.75"	■	Y
PAR30S/850/LEDG11	75	10.5	750	25,000	≥80	40°	E26	5000K	120	3.55"	3.75"	■	Y

### 22 Year Dimmable – PAR30 Long Neck



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR30L/830/LEDG11	75	10.5	750	25,000	≥80	40°	E26	3000K	120	4.75"	3.75"	■	Y
PAR30L/830/LEDG11/2	75	10.5	750	25,000	≥80	40°	E26	3000K	120	4.75"	3.75"	■	Y
PAR30L/850/LEDG11	75	10.5	750	25,000	≥80	40°	E26	5000K	120	4.75"	3.75"	■	Y
PAR30L/850/LEDG11/2	75	10.5	750	25,000	≥80	40°	E26	5000K	120	4.75"	3.75"	■	Y
PAR30L830/LEDG11/CAN	75	10.5	750	25,000	≥80	40°	E26	3000K	120	4.75"	3.75"	■	Y
PAR30L850/LEDG11/CAN	75	10.5	750	25,000	≥80	40°	E26	5000K	120	4.75"	3.75"	■	Y
PAR30L/SP/LEDG10	75	10.5	750	25,000	≥80	28°	E26	3000K	120	4.75"	3.75"		Y
PAR30L/930/LEDG11	75	12	750	25,000	≥90	40°	E26	3000K	120	4.75"	3.75"	■	Y
PAR30L/930/LEDG11/2	75	12	750	25,000	≥90	40°	E26	3000K	120	4.75"	3.75"	■	Y
PAR30LN/930/LEDG11	75	12	750	25,000	≥90	40°	E26	3000K	120	4.75"	3.75"	■	Y

# NARROW SPOT & SPOT REFLECTOR LINE



## 10 Year Non-Dimmable Weatherproof – PAR38

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR3875/10KLED/2	75	10.5	750	11,000	≥80	40°	E26	3000K	120	5"	4.75"		N
PAR38/10KLED/MP/4	75	10.5	750	11,000	≥80	40°	E26	3000K	120	5"	4.75"		N
PAR3875/850/10KLED/2	75	10.5	750	11,000	≥80	40°	E26	5000K	120	5"	4.75"		N



## 22 Year Dimmable Weatherproof – PAR38

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
PAR38/830/LEDG11	90	13.2	930	25,000	≥80	40°	E26	3000K	120	5"	4.75"	■	Y
PAR38/830/LEDG11/2	90	13.2	930	25,000	≥80	40°	E26	3000K	120	5"	4.75"	■	Y
PAR38/850/LEDG11	90	13.2	930	25,000	≥80	40°	E26	5000K	120	5"	4.75"	■	Y
PAR38/850/LEDG11/2	90	13.2	930	25,000	≥80	40°	E26	5000K	120	5"	4.75"	■	Y
PAR38/830/LEDG11/CAN	90	13.2	930	25,000	≥80	40°	E26	3000K	120	5"	4.75"	■	Y
PAR38/850/LEDG11/CAN	90	13.2	930	25,000	≥80	40°	E26	5000K	120	5"	4.75"	■	Y
PAR38/LEDG2/COLD	90	14	950	25,000	≥80	40°	E26	3000K	120	5"	4.75"		Y
PAR38/930/LED	90	18	950	25,000	≥80	40°	E26	3000K	120	5"	4.75"	■	Y
PAR38/930/LEDG11	90	15	950	25,000	≥80	40°	E26	3000K	120	5"	4.75"	■	Y
PAR38N/930/LEDG11	90	15	950	25,000	≥80	40°	E26	3000K	120	5"	4.75"	■	Y
PAR38/SP/LEDG10	90	15.5	950	25,000	≥80	28°	E26	3000K	120	5"	4.75"		Y
Ⓜ PAR38/LED/HBR	90	16	900	25,000	≥80	40°	E26	3000K	120	5"	4.75"		Y*
Ⓜ PAR38/LED/HBR/CAN	90	16	900	25,000	≥80	40°	E26	3000K	120	5"	4.75"		Y*
PAR381380/LEDG2/COLD	120	20	1400	25,000	≥80	40°	E26	3000K	120	5"	4.75"	■	Y



## 22 Year Non-Dimmable – MR11 12 Volt



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPMR11/LED	25	4	240	25,000	≥80	40°	GU4	3000K	12	1.9"	1.37"		N
BPMR11/LED/CAN	25	4	240	25,000	≥80	40°	GU4	3000K	12	1.9"	1.37"		N

## 22 Year Dimmable – MR11 120 Volt



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPMR11/GU10/LED	25	4	240	25,000	≥80	40°	GU10	3000K	120	1.9"	1.37"		Y
BPMR11/GU10/LED/CAN	25	4	240	25,000	≥80	40°	GU10	3000K	120	1.9"	1.37"		Y

## 10 Year Dimmable – MR16 120 Volt



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
MR16GU10500/10KLED/6	50	7	500	11,000	≥80	40°	GU10	3000K	120	2.2"	1.9"		Y

## 22 Year Dimmable – MR16 12 Volt



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPBAB/LED	20	3.5	200	25,000	≥80	40°	GU5.3	3000K	12	2"	2"		Y
BPFMW/LEDG2	35	5	350	25,000	≥80	40°	GU5.3	3000K	12	2"	2"		Y
BPGFMW/LED	35	5.5	445	25,000	≥80	40°	GU5.3	3000K	12	2"	2"		Y
EXN/DM/LED	35	5	350	25,000	≥80	40°	GU5.3	3000K	12	2"	2"	■	Y
EXNDM/LED/CAN	35	5	350	25,000	≥80	40°	GU5.3	3000K	12	2"	2"	■	Y
BPEXN/500/LED	50	7	500	25,000	≥80	40°	GU5.3	3000K	12	2"	2"	■	Y
BPEXN/500/LED/CAN	50	7	500	25,000	≥80	40°	GU5.3	3000K	12	2"	2"	■	Y
EXN500/LED/3/CAN	50	7	500	25,000	≥80	40°	GU5.3	3000K	12	2"	2"	■	Y
BPEXN/500/5K/LED	50	7	500	25,000	≥80	40°	GU5.3	5000K	12	2"	2"		Y
BPEXN/500/LEDG2	50	5	500	25,000	≥80	40°	GU5.3	3000K	12	2"	2"		Y
BPEXN/500/850/LEDG2	50	5	500	25,000	≥80	40°	GU5.3	5000K	12	2"	2"		Y
BPEYC/LED	75	9	700	25,000	≥80	40°	GU5.3	3000K	12	2"	2"		Y



# MINI REFLECTOR LINE

## 22 Year Dimmable Split Reflector – MR16 120 Volt



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
MR161F/GU10/500/LED	50	6	500	25,000	≥80	40°	GU10	3000K	120	2.4"	2"		Y
MR161FGU10500/5K/LED	50	6	500	25,000	≥80	40°	GU10	5000K	120	2.4"	2"		Y

PATENT PENDING

## 22 Year Dimmable – MR16 120 Volt



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPGMR16/GU10/LED	35	5	350	25,000	≥80	40°	GU10	3000K	120	2.4"	2"		Y
MR16GU10/LEDG2/2/CAN	35	5.2	370	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
MR16GU10/LEDG2/3/CAN	35	5.2	370	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
MR16/GU10DM/LED/CAN	35	5.2	370	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
BPMR16/GU10/LEDG2	35	5.5	350	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
BPMR16GU10500LED/CAN	50	7	500	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
MR16GU10500LED/2/CAN	50	7	500	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
MR16GU10500LED/3/CAN	50	7	500	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
MR16GU10500/930LED/2	50	7	455	25,000	≥90	40°	GU10	3000K	120	2.4"	2"		Y
BPMR16/GU10/500/LEDG2	50	6	500	25,000	≥80	40°	GU10	3000K	120	2.4"	2"	■	Y
BPMR16GU105005KLEDG2	50	6	500	25,000	≥80	40°	GU10	5000K	120	2.4"	2"	■	Y
BPMR16/GU10/800/LED	75	9	790	25,000	≥80	40°	GU10	3000K	120	2.4"	2"		Y
BPXN/500/MED/LED	50	7	500	25,000	≥80	40°	E26	3000K	120	2"	2.2"		Y
EXN500MED/LEDG11/CAN	50	7	500	25,000	≥80	40°	E26	3000K	120	2"	2.2"	■	Y
EXN500MED5KLEDG11/CAN	50	7	500	25,000	≥80	40°	E26	5000K	120	2"	2.2"	■	Y
EXN500MEDLEDG113/CAN	50	7	500	25,000	≥80	40°	E26	3000K	120	2"	2.2"		Y



# RETROFIT KIT

## recessed lighting

- Dimmable
- White finish
- Adjustable flood and spot options
- 2700K, 3000K, 4000K and 5000K CCT
- Lasts up to 50,000 hours
- UL or ETL listed
- Use in residential and commercial applications
- Includes E26 adapter

# DOWNLIGHT RETROFIT KIT



## 4 inch Insta-Trim™ Downlight

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDR4/827/MED	45	9	540	25,000	≥80	110°	E26	2700K	120	3.8"	5"	■	Y
LEDR4/827/MED/2	45	9	540	25,000	≥80	110°	E26	2700K	120	3.8"	5"	■	Y



## 5/6 inch Insta-Trim™ Downlight

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDR56/827/MED	65	12	800	25,000	≥80	110°	E26	2700K	120	5"	7.5"	■	Y
LEDR56/827/MED/2	65	12	800	25,000	≥80	110°	E26	2700K	120	5"	7.5"	■	Y



## 4 inch Adjustable Head Downlight Retrofit Kit

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDG2R4ADJ/830	65	10	600	50,000	≥80	110°	E26*	3000K	120	2.75"	5"		Y
LEDR45CP/930	65	12	720	30,000	≥90	110°	E26*	3000K	120	3.15	5	■	Y
LEDR45CP/930/SP	65	12	720	30,000	≥90	40°	E26*	3000K	120	3.15	5	■	Y



## 5/6 inch Adjustable Head Downlight Retrofit Kit

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDG2R56ADJ/830	75	15	900	50,000	≥80	110°	E26*	3000K	120	3.75"	7.5"		Y
LEDR565CP/930	75	14	850	30,000	≥90	110°	E26*	3000K	120	3.86"	7.5"	■	Y
LEDR565CP/930/SP	75	14	850	30,000	≥90	40°	E26*	3000K	120	3.86"	7.5"	■	Y

### 3 inch Round Downlight Retrofit Kit



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDR3/830	40	7	350	30,000	≥80	110°	E26*	3000K	120	2.6"	5"		Y

### 4 inch Round Downlight Retrofit Kit



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDR4/827	50	9	540	50,000	≥80	110°	E26*	2700K	120	2.6"	5"	■	Y
LEDR4/840	50	9	550	50,000	≥80	110°	E26*	4000K	120	2.6"	5"	■	Y
LEDG2R4/830	50	9	540	50,000	≥80	110°	E26*	3000K	120	2.6"	5"	■	Y
LEDG2R4/830/CAN	50	9	540	50,000	≥80	110°	E26*	3000K	120	2.6"	5"	■	Y
LEDG2R4/850/CAN	50	9	540	50,000	≥80	110°	E26*	5000K	120	2.6"	5"		Y
LEDRT4/927	50	9	540	50,000	≥80	110°	E26*	2700K	120	2.6"	5"	■	Y
LEDR4/927/MP/6	50	9	540	50,000	≥90	110°	E26*	2700K	120	2.6"	5"	■	Y

### 4 inch High Lumen Round Downlight Retrofit Kit



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDG2R4HO/830	75	14.5	775	50,000	≥80	110°	E26*	3000K	120	2.6"	5"		Y
LEDG2R4HO/850	75	14.5	775	50,000	≥80	110°	E26*	5000K	120	2.6"	5"		Y

### 4 inch Square Downlight Retrofit Kit



ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDRSQ4/930†	50	14	700	30,000	≥90	110°	E26*	3000K	120	2.2"	5"		Y

† CALIFORNIA JA8 TITLE 24 COMPLIANT LAMP

# DOWNLIGHT RETROFIT KIT



## 5/6 inch Round Downlight Retrofit Kit


ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDR56/930/30K	65	10.5	650	30,000	≥90	110°	E26*	3000K	120	3.5"	7.3"		Y
LEDR56/650/827	65	10.5	650	50,000	≥80	110°	E26*	2700K	120	3.5"	7.3"	■	Y
LEDR56/840	75	14	925	50,000	≥80	110°	E26*	4000K	120	3.5"	7.3"	■	Y
LEDG2R56/830/CAN	75	14	925	50,000	≥80	110°	E26*	3000K	120	3.5"	7.3"	■	Y
LEDG2R56/850/CAN	75	14	925	50,000	≥80	110°	E26*	5000K	120	3.5"	7.3"	■	Y
LEDG2R56/830	75	14	925	50,000	≥80	110°	E26*	3000K	120	3.5"	7.3"	■	Y
LEDR56/830/HBR	75	14	880	50,000	≥80	110°	E26*	3000K	120	3.5"	7.3"		Y**
LEDR56/830/HBR/CAN	75	14	880	50,000	≥80	110°	E26*	3000K	120	3.5"	7.3"		Y**
LEDG2R5675/927†	75	15	900	50,000	≥90	110°	E26*	2700K	120	3.5"	7.3"	■	Y
LEDR56/927/MP/6†	75	15	900	50,000	≥90	110°	E26*	2700K	120	3.5"	7.3"	■	Y
LEDR56/827	120	21.5	1290	50,000	≥80	110°	E26*	2700K	120	3.5"	7.3"	■	Y
LEDRT56/927	120	21.5	1290	50,000	≥90	110°	E26*	2700K	120	3.5"	7.3"	■	Y

† CALIFORNIA JA8 TITLE 24 COMPLIANT LAMP



## 5/6 inch High Lumen Round Downlight Retrofit Kit

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDG2R56HO/830	120	21.5	1290	50,000	≥80	110°	E26*	3000K	120	3.5"	7.3"	■	Y
LEDG2R56HO/850	120	21.5	1290	50,000	≥80	110°	E26*	5000K	120	3.5"	7.3"	■	Y



## 6 inch Square Downlight Retrofit Kit

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
LEDRSQ6/930†	65	16	850	30,000	≥90	110°	E26*	3000K	120	3.25"	7.5"		Y

† CALIFORNIA JA8 TITLE 24 COMPLIANT LAMP



# COLOR SELECT

## recessed cans & j-box

- Select from three color temperature settings
  - Warm white (3000K)
  - Cool white (4000K)
  - Daylight (5000K)
- Full range dimming
- Choose your color with a standard light switch or before installing
- Lasts up to 50,000 hours
- Recessed cans or standard j-box installation



# COLOR SELECT DOWNLIGHT RETROFIT KIT



## 4 inch & 5/6 inch Downlight Retrofit Kit

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	CCT OPTIONS	VOLTS	MOL	DIA	ES	DIM
LEDR4/4WY*	50	9	540	50,000	≥80	110°	3000K/4000K/5000K	120	2.6"	5"	■	Y
LEDR56/4WY*	75	14	850	50,000	≥80	110°	3000K/4000K/5000K	120	3.5"	7.3"	■	Y

PATENT PENDING


## 4 inch & 5/6 inch Round Flat Panel Downlight Retrofit Kit\*\*



ITEM#	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	CCT OPTIONS	VOLTS	MOL	DIA	ES	DIM
74202	8	500	50,000	≥80	110°	3000K/4000K/5000K	120	1.4"	5"	■	Y
74206	12	800	50,000	≥80	110°	3000K/4000K/5000K	120	1.4"	7.5"	■	Y

PATENT PENDING

## 4 inch & 5/6 inch Square Flat Panel Downlight Retrofit Kit\*\*



ITEM#	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	CCT OPTIONS	VOLTS	MOL	DIA	ES	DIM
74204	8	500	50,000	≥80	110°	3000K/4000K/5000K	120	1.4"	5"	■	Y
74208	12	800	50,000	≥80	110°	3000K/4000K/5000K	120	1.4"	7.5"	■	Y

PATENT PENDING

## 4/5/6 inch Round Disklight Retrofit Kit\*\*



ITEM#	WATTS	LUMENS	HOURS	CRI	BEAM ANGLE	CCT OPTIONS	VOLTS	MOL	DIA	ES	DIM
74006	12	850	50,000	≥80	110°	3000K/4000K/5000K	120	2.5"	7.5"	■	Y

PATENT PENDING



# ORIGINAL

## vintage style

- Dimmable
- Amber and clear finish
- E26 and E12 bases
- 2000-2200K CCT
- Lasts up to 15,000 hours
- UL or ETL listed
- Variety of filament styles and shapes



# VINTAGE STYLE

## Vintage – A-Shape



ITEM#	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPST1525C/VG/LED/2	3	200	15,000	≥80	Clear	E26	2200K	120	3.9"	1.6"		Y
AT19/H/LED	4.5	125	15,000	≥80	Amber	E26	2000K	120	4.2"	2.38"		Y
AT19/S/CL/FILED	6.5	250	15,000	≥80	Clear	E26	2150K	120	4.2"	2.38"		Y
BPAT19/LED	4	309	15,000	≥80	Clear	E26	2200K	120	4.2"	3"		Y
BPAT19/LED/CAN	4	309	15,000	≥80	Clear	E26	2200K	120	4.2"	3"		Y
ST19/S/CL/FILED	6.5	250	15,000	≥80	Clear	E26	2150K	120	5.4"	2.5"		Y
ST19/M/LED	6.5	250	15,000	≥80	Amber	E26	2000K	120	5.4"	2.5"		Y
BPST19/LED	4.8	400	15,000	≥80	Amber	E26	2200K	120	6.2"	3"		Y
BPST19/LED/CAN	4.8	400	15,000	≥80	Amber	E26	2200K	120	6.2"	3"		Y

## Vintage – Chandelier



ITEM#	WATTS	LUMENS	HOURS	CRI	SHAPE	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
CTT/S/CL/FILED	4.5	125	15,000	≥80	Blunt	Clear	E12	2150K	120	3.8"	1.3"		Y
BPCFT/LED	2.5	210	15,000	≥80	Flame	Clear	E12	2200K	120	5.3"	1.7"		Y
BPCFT/LED/CAN	3.5	210	15,000	≥80	Flame	Clear	E26	2200K	120	5.3"	1.7"		Y
BPCFT/LED/2/CAN	3.5	210	15,000	≥80	Flame	Clear	E26	2200K	120	5.3"	1.7"		Y

## Vintage – Tubular



ITEM#	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
BPVT10/LED	4	300	15,000	≥80	Clear	E26	2200K	120	4"	1.5"		Y
BPT1440/VG/LED	4	300	15,000	≥80	Clear	E26	2200K	120	4.8"	1.5"		Y

## Vintage – Globe



ITEM#	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	ES	DIM
G25/S/VG/LED	6.5	250	15,000	≥80	Amber	E26	2000K	120	4.6"	3.15"		Y
G25/S/CL/FILED	6.5	250	15,000	≥80	Clear	E26	2150K	120	4.6"	3.15"		Y
BPG2540/VG/LED	4.5	350	15,000	≥80	Clear	E26	2200K	120	4.6"	3.15"		Y




# COLOR & SPECIALTY

## special applications

- Plastic and glass
- Variety of bases
- Wide range of colors
- Lasts up to 50,000 hours
- Grow lights
- Halogen and special application replacements

# COLOR & SPECIALTY

## Non-Dimmable – Color C7



ITEM#	REPLACEMENT	WATTS	HOURS	FINISH	BASE	COLOR	VOLTS	MOL	DIA	DIM
BPC7/LED	C7	< 1	50,000	White	E12	Cool White	120	2.15"	.95"	N
BPC7/G/LED	C7	< 1	50,000	Green	E12	Green	120	2.15"	.95"	N
BPC7/B/LED	C7	< 1	50,000	Blue	E12	Blue	120	2.15"	.95"	N
BPC7/R/LED	C7	< 1	50,000	Red	E12	Red	120	2.15"	.95"	N

## 18 Year Dimmable Glass – Color A-Shape



Available colors:



GLOW IN THE DARK

ITEM#	REPLACEMENT	WATTS	HOURS	FINISH	BASE	COLOR	VOLTS	MOL	DIA	DIM
A19/TB/LED	A19	4.5	20,000	Clear	E26	Blue	120	4"	2.3"	Y
A19/TG/LED	A19	4.5	20,000	Clear	E26	Green	120	4"	2.3"	Y
A19/TY/LED	A19	4.5	20,000	Clear	E26	Yellow	120	4"	2.3"	Y
A19/TR/LED	A19	4.5	20,000	Clear	E26	Red	120	4"	2.3"	Y
A19/TO/LED	A19	4.5	20,000	Clear	E26	Orange	120	4"	2.3"	Y
A19/TPK/LED	A19	4.5	20,000	Clear	E26	Pink	120	4"	2.3"	Y
A19/TP/LED	A19	4.5	20,000	Clear	E26	Purple	120	4"	2.3"	Y
A19/BLB/LED	A19	7	20,000	Clear	E26	Black Light	120	4"	2.3"	N

## 10 Year Non-Dimmable Plastic – Color A-Shape



Available colors:



ITEM#	REPLACEMENT	WATTS	HOURS	FINISH	BASE	COLOR	VOLTS	MOL	DIA	DIM
A19/B/10KLED	A19	3.5	11,000	Clear	E26	Blue	120	4"	2.3"	Y
A19/G/10KLED	A19	3.5	11,000	Clear	E26	Green	120	4"	2.3"	Y
A19/Y/10KLED	A19	5	11,000	Clear	E26	Yellow	120	4"	2.3"	Y
A19/R/10KLED	A19	3.5	11,000	Clear	E26	Red	120	4"	2.3"	Y
A19/O/10KLED	A19	3.5	11,000	Clear	E26	Orange	120	4"	2.3"	Y

## 10 Year Non-Dimmable Weatherproof – Color PAR38



Available colors:



ITEM#	REPLACEMENT	WATTS	HOURS	FINISH	BASE	COLOR	VOLTS	MOL	DIA	DIM
PAR38/B/10KLED	PAR38	3.5	11,000	Blue	E26	Blue	120	5"	4.75"	N
PAR38/G/10KLED	PAR38	3.5	11,000	Green	E26	Green	120	5"	4.75"	N
PAR38/Y/10KLED	PAR38	3.5	11,000	Yellow	E26	Yellow	120	5"	4.75"	N
PAR38/R/10KLED	PAR38	3.5	11,000	Red	E26	Red	120	5"	4.75"	N



## Color Specialty

ITEM#	REPLACEMENT	WATTS	HOURS	FINISH	BASE	COLOR	VOLTS	MOL	DIA	DIM
A19/HP/LED/PARTY	A19	6.5	30,000	White	E26	Multi-Color	120	4.5"	2.5"	N
A19/LED/PARTY	A19	< 1	100,000	Silver	E26	Multi-Color	120	4.5"	2.3"	N
A19/BUG/LED	A19	5	25,000	Yellow	E26	Yellow	120	4"	2.35"	N
BPA19/BLB/LED	A19	9	25,000	Black	E26	Black Light	120	4.5"	2.2"	N



GLOW IN THE DARK

## Specialty

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	DIM
LWV/LED	20	2	160	15,000	≥80	Clear	Wedge	3000K	12	0.5"	.75"	N
G4/LED	20	2	160	15,000	≥80	Clear	G4	3000K	12	1.75"	.75"	N
G4/LED/CAN	20	2	160	15,000	≥80	Clear	G4	3000K	12	1.75"	.75"	N
G8/LED	20	2	160	15,000	≥80	Clear	G8	3000K	120	1.75"	.75"	N
G9/LED	20	2	160	15,000	≥80	Clear	G9	3000K	120	1.75"	.75"	N
G9/LED/CAN	20	2	160	15,000	≥80	Clear	G9	3000K	120	1.75"	.75"	N
G9HO/LED/CAN	25	2.8	200	15,000	≥80	Clear	G9	3000K	120	1.75"	.75"	N
GY8.6/LED/CAN	20	2.5	160	15,000	≥80	Clear	G8.6	3000K	120	1.75"	.75"	N
GY6.35/LED/CAN	20	2.5	160	15,000	≥80	Clear	G6.35	3000K	120	2"	.75"	N
MC/LED/CAN	20	3	200	15,000	≥80	Clear	E11	3000K	120	2"	.64"	N
DC/LED/CAN	20	3	200	15,000	≥80	Clear	BA15d	3000K	120	2"	.64"	N



## Landscape

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	DIM
BPLVBAB/LED	20	3	200	25,000	≥80	White	GU5.3	3000K	12	2"	2"	N
BPLVMR11/LED	25	4	220	15,000	≥80	White	GU4	3000K	12	2"	2"	N
BPLVEXN/LED	50	7.5	500	25,000	≥80	White	GU5.3	3000K	12	2"	2"	N
BPLVFMW/LED	35	5.5	350	25,000	≥80	White	GU5.3	3000K	12	2"	2"	N
LVG4/LED	20	2	135	15,000	≥80	White	G4	3000K	12	1.75"	.75"	N
LWV10/LED	10	1	85	15,000	≥80	White	Wedge	3000K	12	.5"	.75"	N
LWV18/LED	20	2	85	15,000	≥80	White	Wedge	3000K	12	.5"	.75"	N



# COLOR & SPECIALTY



## Grow Lights

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	FINISH	BASE	CCT	NM. RED	NM. BLUE	MOL	DIA	DIM
A19/GROW/LEDG2	A19	9	95	25,000	Green	E26	1100	655	450	4.5"	2.5"	N
BR30/GROW/LEDG2	BR30	9	95	25,000	Green	E26	1100	655	450	5"	3.75"	N



## 13 Year Dimmable Glass Tubular – T10

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	DIM
BPT1040/827/LED	40	4.5	400	15,000	≥80	Clear	E26	2700K	120	4.3"	1.2"	Y
BPT1040/850/LED	40	4.5	400	15,000	≥80	Clear	E26	5000K	120	4.3"	1.2"	Y



## 13 Year – Special Use

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	DIM
BPJ78/LED	40	5	450	15,000	≥80	Clear	R75	3000K	120	3.25"	1.87"	N
BPJ118/LED	60	8	800	15,000	≥80	Clear	R75	3000K	120	4.68"	1.87"	N
BPT6/SU/LED	15	1.2	50	15,000	≥80	Clear	E12	3000K	120	1.87"	.75"	N
BPS11N/SU/LED	20	1.5	80	15,000	≥80	Clear	E17	3000K	120	2.25"	1.37"	N
BPT7N/SU/LED	15	1.5	80	15,000	≥80	Clear	E17	3000K	120	2"	.68"	N
BPS14/SU/LED	11	1.5	80	15,000	≥80	Clear	S14	3000K	120	3.25"	1.5"	N
BPT61/2/SU/LED	25	2	180	15,000	≥80	Clear	E17	3000K	120	5.3"	.81"	N
BPA15/CL/DM/SU/LED	40	4.8	300	15,000	≥80	Clear	E26	3000K	120	3.2"	1.75"	Y
BPA19/SU/LED	60	10.5	820	15,000	≥80	White	E26	3000K	120	4.4"	2.4"	Y
BPF1560/827/FILED	60	6	500	15,000	≥80	Clear	E26	2700K	120	4.3"	1.8"	Y
BPF1560/850/FILED	60	6	500	15,000	≥80	Clear	E26	5000K	120	4.3"	1.8"	Y



# PL & LINEAR

---

## replacement lamp

- Lasts up to 50,000 hours
- Residential and commercial use
- Low energy consumption
- No flicker or strobing
- Instant full brightness
- Fluorescent replacements

# PL & LINEAR



## PL Replacement Lamp

ITEM#	REPLACEMENT	WATTS	LUMENS	HOURS	CRI	FINISH	BASE	CCT	VOLTS	MOL	DIA	DLC
PL26E/H/841/LED	26	12	1100	25,000	≥80	Frost	GX24Q-3	4100K	120	6.35"	1.15"	
PL26E/V/840/LED	26	11.3	800	25,000	≥80	Frost	GX24Q-3	4100K	120	4.4"	2"	
BPPL13/H/840/LED	13	6	600	25,000	≥80	Frost	GX23	4000K	120	6.9"	1.1"	



## 4ft. T8 & T12 Ballast Bypass Retrofit Kit

ITEM#	REPLACEMENT	LAMP WATTS	INPUT WATTS	LUMENS	HOURS	CRI	BASE	CCT	VOLTS	MOL	DIA	DLC
T4819/840/LEDG2/MP	T8 & T12		18.5	2090	50,000	≥80	G13	4000K	120	4'	1"	
T4819/850/LEDG2/MP	T8 & T12		18.5	2090	50,000	≥80	G13	5000K	100-277	4'	1"	
T4819/LEDIF/41K	T8 & T12		19	1650	50,000	≥80	G13	4100K	100-277	4'	1"	




## 2ft. & 4ft. T8 & T12 Direct Replacement Lamp

ITEM#	REPLACEMENT	LAMP WATTS	INPUT WATTS	LUMENS	HOURS	CRI	BASE	CCT	VOLTS	MOL	DIA	DLC
T848/841/LED/2	T8	18	32	1600	35,000	≥80	G13	4000K	120	4'	1"	
T848/841/LED/MP/10	T8	18	32	1600	35,000	≥80	G13	4000K	120	4'	1"	
T24/841/LED	T8 & T12	10	17	700	50,000	≥80	G13	4100K	120	2'	1"	•
T24/850/LED	T8 & T12	10	17	750	50,000	≥80	G13	4100K	120	2'	1"	•
T48/830/LED	T8 & T12	14	32	1600	50,000	≥80	G13	3000K	120	4'	1"	•
T48/841/LED/RP	T8 & T12	14	32	1700	50,000	≥80	G13	4100K	120	4'	1"	•
T48/841/LED	T8 & T12	14	32	1700	50,000	≥80	G13	4100K	120	4'	1"	•
T48/850/LED	T8 & T12	14	32	1750	50,000	≥80	G13	5000K	120	4'	1"	•



## 8ft. T8 & T12 Direct Replacement Lamp

ITEM#	REPLACEMENT	LAMP WATTS	INPUT WATTS	LUMENS	HOURS	CRI	BASE	CCT	VOLTS	MOL	DIA	DLC
T96/841/LED	T8 & T12	44	75	3200	50,000	≥80	1-PIN	4100K	120	8'	1"	•



**FEIT ELECTRIC COMPANY, INC.**

4901 Gregg Road | Pico Rivera, CA 90660

Telephone [562] 463-BULB [2852]

[800] 543-FEIT [3348] | Fax | [562] 908-6360

[www.feit.com](http://www.feit.com)



All information contained in this catalog is accurate to the best of our knowledge. No liability is assumed by Feit Electric Company, Inc. for inaccuracies or errors. Product specifications and images are subject to change without notice. Please contact our customer service department for current product information.

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth® SIG, Inc. and any use of such marks by Feit Electric Company, Inc. is under license. Other trademarks and trade names are those of their respective owners.

Please visit [www.feit.com](http://www.feit.com) for all terms and conditions.