

## Commercial and Die Cast Fittings

Conduit Fittings . . . . .	E2
Thinwall Conduit Fittings (EMT) . . . . .	E3-E14
Rigid/Intermediate Grade Conduit Fittings . . . . .	E15-E27
Rigid/Aluminum Conduit Bodies, Gaskets and Covers . . . . .	E28-E29
Aluminum Conduit Bodies, Gaskets and Covers . . . . .	E30
Flexible Cord and Power Cable Connectors . . . . .	E31
Liquidtight Flexible Nonmetallic Conduit Connectors and Tubing . . . . .	E32-E33
Liquidtight Fittings . . . . .	E34
Liquidtight Flexible Metal Conduit Connectors . . . . .	E35-E37
Nonmetallic Sheathed Cable and Flexible Cord Connectors . . . . .	E38
Nonmetallic Sheathed Cable Fittings . . . . .	E39-E40
Armored Cable/Flexible Metallic Conduit Fittings . . . . .	E41-E46
Cable Straps, Cable Caps . . . . .	E47
Service Entrance Fittings . . . . .	E48
Grounding Clamps/Connectors . . . . .	E49
Gutter Connectors/Cable Protector and Cable Clip . . . . .	E50
Beam Clamps for Mounting Pipe or Conduit . . . . .	E51
Conduit and Pipe Hangers . . . . .	E52
Beam Clamps/Threaded Rod/ Rod Coupling . . . . .	E53

E

# Steel City®

## Conduit Fittings

Steel City®

Steel City® Conduit Fittings provide long-lasting service in commercial, industrial and residential construction. Our fittings are manufactured within strict tolerances to maintain consistent performance. Installers can be assured that every fitting with the Steel City name will work every time. So when you select Steel City® Conduit Fittings, that means fewer headaches and call-backs.

Steel City® products symbolize the highest quality standards in manufacturing and innovative design, with one of the most complete offerings available. Contact a T&B distributor nearest you to select the right Steel City® product for your requirements.



### Advantages of Steel City Commercial Conduit Fittings

#### Compression Fittings

##### Dependable Pipe Stop

- Strong thick protrusion that does not exceed thickness of EMT. Keeps forcefully inserted conduit from breaking through the opposite side of the coupling while not interfering with the pulling of conductors.

##### Heavy Duty Thick Steel Body/Glands with Continuous Threading

- True hexagonal shape. The non-circular design has actual flats for gripping power using hand or tool force.

##### Extra Thick Electroplated Zinc Finish

- Assures corrosion resistance while the clear chromate coating gives the fittings their quality shine and luster.



#### Couplings and Connectors

##### Superior Quality and Design

- Strict tolerances throughout fitting assures a straight conduit run with no sagging over extreme lengths.
- Chamfered entry provides lead-in for conduit insertion.

##### Dependable Pipe Stop

- 360° groove traveling the circumference assures that conduit forcefully inserted won't break through to the opposite side of the fitting. Also, it does not exceed thickness of EMT and prevents interference with pulling conductors.

##### Extra Large Head Tri-Drive Set-Screw

- Accommodates Phillips, Slotted and Square drives.

##### Enhanced Locknut Construction

- Heavy-duty turned sharp teeth, double-threaded.



### Here's How The Steel City Part Number System Works

#### Easy to identify alphabetical prefixes:

- BG** – Bushings, Grounding
- BI** – Bushings, Insulated
- BL** – Blanks
- BU** – Bushings
- CB** – Clamp Back
- EK** – 3 Piece Coupling
- GA** – Ground Clamp (armored ground wire)
- GC** – Ground Clamp
- HA** – Heavywall Adapter
- HC** – Heavywall Connector
- HK** – Heavywall Coupling
- HO** – Heavywall Offset
- HS** – Heavywall Strap
- LG** – Locknut, Grounding
- LN** – Locknut
- LT** – Liquidtight
- NC** – Nonmetallic Sheathed Cable Connector
- NS** – Nonmetallic Sheathed Cable Strap
- SH** – Service Entrance Fitting
- SL** – Service Ells
- SR** – Sealing Rings
- LS** – Locknut, Sealing
- TC** – Thinwall Connectors
- TK** – Thinwall Couplings
- TO** – Thinwall Offset
- TS** – Thinwall Strap
- TX** – Thinwall to Flexible Metallic Conduit Fitting
- UC** – Utility Connector
- WA** – Washer
- XC** – Armored Cable or Flexible Metallic Conduit Connector
- XK** – Armored Cable or Flexible Metallic Conduit Coupling

#### 1st Digit – Material

- 1** = Steel
- 2** = Die Cast
- 3** = Combination Steel and Die Cast
- 4** = Malleable
- 5** = Plastic
- 6** = Aluminum
- 7** = Steel Insulated
- 8** = Die Cast Insulated
- 9** = Malleable Insulated

#### 2nd Digit – Method

- 1** = Compression
- 2** = Set Screw
- 3** = Other

#### 3rd/4th Digit Size

- 1** = 1/2"
- 2** = 3/4"
- 3** = 1"
- 4** = 1 1/4"
- 5** = 1 1/2"
- 6** = 2"
- 7** = 2 1/2"
- 8** = 3"
- 9** = 3 1/2"
- 10** = 4"
- 11** = 5"
- 12** = 6"

A few examples of the three digit identification system for thinwall fittings are:

- TK-111**      1/2" steel, compression type coupling
- TC-714**      1 1/4" steel insulated compression type connector
- TC-822**      3/4" die cast, insulated, set-screw type connector

# Steel City®

## Thinwall Conduit Fittings (EMT)



E

Steel City®

- Concrete Tight
- Zinc Plated

### Set Screw Connectors, Steel – Non-Insulated

"A" Cat#	Conduit Size	Inner Pack	Outer Pack
TC121A	½"	50	500
TC122A	¾"	50	250
TC123A	1"	25	100
TC124A	1¼"	–	25
TC125A	1½"	–	25
TC126A	2"	–	25
TC127A	2½"	–	10
TC128A	3"	–	5
TC129A	3½"	–	5
TC1210A	4"	–	5

### Set Screw Connectors, Steel – Insulated

"A" Cat#	Conduit Size	Inner Pack	Outer Pack
TC721A	½"	50	500
TC722A	¾"	50	250
TC723A	1"	25	100
TC724A	1¼"	–	25
TC725A	1½"	–	25
TC726A	2"	–	25
TC727A	2½"	–	10
TC728A	3"	–	5
TC729A	3½"	–	5
TC7210A	4"	–	5

U.L. File No. E-16592



- Concrete Tight, when taped
- Zinc Plated



### Set Screw Couplings – Steel

"A" Cat#	Conduit Size	Inner Pack	Outer Pack
TK121A	½"	50	500
TK122A	¾"	50	250
TK123A	1"	25	100
TK124A	1¼"	–	25
TK125A	1½"	–	25
TK126A	2"	–	25
TK127A	2½"	–	10
TK128A	3"	–	5
TK129A	3½"	–	5
TK1210A	4"	–	5

U.L. File No. E-16592

**Thomas & Betts**

# Steel City®

## Thinwall Conduit Fittings (EMT)



- ½" – 4" Concrete Tight
- Zinc Plated

### Compression Connectors, Steel – Non-Insulated

"A" Cat#	Conduit Size	Inner Pack	Outer Pack
TC111A	½"	50	500
TC112A	¾"	50	250
TC113A	1"	25	100
TC114A	1¼"	–	25
TC115A	1½"	–	25
TC116A	2"	–	25
TC117A	2½"	–	10
TC118A	3"	–	5
TC119A	3½"	–	5
TC1110A	4"	–	5

### Compression Connectors, Steel – Insulated

"A" Cat#	Conduit Size	Inner Pack	Outer Pack
TC711A	½"	50	500
TC712A	¾"	50	250
TC713A	1"	25	100
TC714A	1¼"	–	25
TC715A	1½"	–	25
TC716A	2"	–	25
TC717A	2½"	–	10
TC718A	3"	–	5
TC719A	3½"	–	5
TC7110A	4"	–	5

U.L. File No. E-16592




- ½" – 4" Concrete Tight
- Zinc Plated

### Compression Couplings – Steel

"A" Cat#	Conduit Size	Inner Pack	Outer Pack
TK111A	½"	50	250
TK112A	¾"	50	250
TK113A	1"	25	100
TK114A	1¼"	–	25
TK115A	1½"	–	25
TK116A	2"	–	25
TK117A	2½"	–	10
TK118A	3"	–	5
TK119A	3½"	–	5
TK1110A	4"	–	5

U.L. File No. E-16592



### EMT LOK Conduit Connector

Cat. No.	Description	Std. Ctn.
TC-101-SC	1/2" Uninsulated	500
TC-102-SC	3/4" Uninsulated	250
TC-701-SC	1/2" Insulated	500
TC-702-SC	3/4" Insulated	250

U.L. Listing No. E16592, CSA Listing No. LR-12798

Installation using either slotted or Phillips screwdriver head, 35-in-lb of torque onto the EMT.

NOTE: Excessive torque could damage EMT or housing.

E


Steel City®

- Simple, one-piece installation with no locknuts.
- Available in insulated or noninsulated throat.
- Screw designed for exceptional pullout resistance.
- Captive screw ensures that the screw is intact for installation and resists backing out after installation.
- Corrosion-resistant, zinc-chromatic plating.
- Concrete tight.
- Positive grounding.
- Vibration resistant screw design.
- UL listed and CSA certified.

## Additional Commercial Construction Products from Thomas & Betts

### Steel City® Steel Boxes, Covers, & Accessories


- Notched Ears on Switch Boxes provide clearance for the screws that are used to attach wall plates to GFCI or rocker-type light switches.
- Universal Metal Stud Bracket mounts without the use of screws, to the open or closed side of the stud and works on any depth of non-loadbearing metal stud.
- Eccentric Knockouts on Square Boxes provide better contact with conduit fitting and locknut to the box, improves grounding path, stronger than 3/4" knockout.
- Improved 3/4" Knockout Position on Square Boxes requires less labor to install 3/4" conduit to box.
- Raised Ground Screw in Utility Boxes make for quicker surface mounting by eliminating the need to remove the portion of the screw that threads through the back of the box, allows for improved repositioning of grounding conductor.
- Preinstalled Screws are Packaged in raised position eliminates extra step of having to back out the screw during cover installation.




### Steel City® Underfloor Duct, Floor Boxes, & Poke-Throughs

- Steel City conventional underfloor duct offers multi-compartmental duct and junction boxes with built-in tile trim.
- Header duct and access hatch designs of cellular underfloor duct system provide convenient wire and cable access, eliminating junction boxes.
- Accommodate power, voice, or data with Steel City flush floor boxes, available in cast-iron, steel, and nonmetallic constructions.
- Access floor modules blend with any decor and accommodate virtually any raised floor surface.
- Steel City poke-through devices allow the interchange of flush, low-profile, and standard service heads without removing the lower core unit.







• ½" – 4" Concrete Tight



• ½" – 4" Concrete Tight



• ½" – 4" Concrete Tight



### Compression Connectors – Die Cast Zinc, Noninsulated

Cat. No.	Conduit Size	A	B	Std. Ctn.
TC-211-SC	½"	1¼"	1	500
TC-212-SC	¾"	1½ <sup>32</sup> "	1½ <sup>32</sup> "	250
TC-213-SC	1"	1 <sup>29</sup> / <sub>64</sub> "	1 <sup>15</sup> / <sub>32</sub> "	200
TC-214-SC	1¼"	1 <sup>13</sup> / <sub>16</sub> "	1 <sup>27</sup> / <sub>32</sub> "	100
TC-215-SC	1½"	1 <sup>7</sup> / <sub>8</sub> "	2 <sup>1</sup> / <sub>16</sub> "	40
TC-216-SC	2"	2 <sup>5</sup> / <sub>32</sub> "	2 <sup>17</sup> / <sub>32</sub> "	20
TC-217-SC	2½"	2 <sup>49</sup> / <sub>64</sub> "	3¼"	12
TC-218-SC	3"	2 <sup>7</sup> / <sub>8</sub> "	3 <sup>15</sup> / <sub>16</sub> "	12
TC-219-SC	3½"	2 <sup>47</sup> / <sub>64</sub> "	4 <sup>7</sup> / <sub>16</sub> "	10
TC-2110-SC	4"	2 <sup>13</sup> / <sub>16</sub> "	4 <sup>15</sup> / <sub>16</sub> "	6

U.L. File No. E-16592 – ½"-4"  
CSA File No. LR-12798 – ½"-2"



### Compression Connectors – Die Cast Zinc, Insulated

Cat. No.	Conduit Size	A	B	Std. Ctn.
TC-811-SC	½"	1 <sup>23</sup> / <sub>64</sub> "	6 <sup>3</sup> / <sub>64</sub> "	500
TC-812-SC	¾"	1 <sup>15</sup> / <sub>32</sub> "	1 <sup>5</sup> / <sub>16</sub> "	250
TC-813-SC	1"	1 <sup>35</sup> / <sub>64</sub> "	1 <sup>15</sup> / <sub>32</sub> "	200
TC-814-SC	1¼"	1 <sup>29</sup> / <sub>32</sub> "	1 <sup>27</sup> / <sub>32</sub> "	100
TC-815-SC	1½"	1 <sup>31</sup> / <sub>32</sub> "	2 <sup>1</sup> / <sub>16</sub> "	40
TC-816-SC	2"	2 <sup>1</sup> / <sub>4</sub> "	2 <sup>17</sup> / <sub>32</sub> "	20
TC-817-SC	2½"	2 <sup>29</sup> / <sub>32</sub> "	3¼"	12
TC-818-SC	3"	2 <sup>31</sup> / <sub>32</sub> "	3 <sup>15</sup> / <sub>16</sub> "	12
TC-819-SC	3½"	2 <sup>27</sup> / <sub>32</sub> "	4 <sup>7</sup> / <sub>16</sub> "	10
TC-8110-SC	4"	2 <sup>29</sup> / <sub>32</sub> "	4 <sup>15</sup> / <sub>16</sub> "	6

U.L. File No. E-16592 – ½"-4"  
CSA File No. LR-12798 – ½"-2"



### Compression Couplings – Die Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
TK-211-SC	½"	1½"	1 <sup>3</sup> / <sub>32</sub> "	500
TK-212-SC	¾"	1 <sup>5</sup> / <sub>8</sub> "	1 <sup>5</sup> / <sub>16</sub> "	250
TK-213-SC	1"	1 <sup>7</sup> / <sub>8</sub> "	1 <sup>45</sup> / <sub>64</sub> "	200
TK-214-SC	1¼"	1 <sup>13</sup> / <sub>16</sub> "	2 <sup>3</sup> / <sub>32</sub> "	100
TK-215-SC	1½"	2 <sup>9</sup> / <sub>32</sub> "	2 <sup>21</sup> / <sub>64</sub> "	40
TK-216-SC	2"	2 <sup>11</sup> / <sub>32</sub> "	2 <sup>29</sup> / <sub>32</sub> "	20
TK-217-SC	2½"	3 <sup>13</sup> / <sub>64</sub> "	3 <sup>11</sup> / <sub>64</sub> "	12
TK-218-SC	3"	3 <sup>7</sup> / <sub>32</sub> "	4 <sup>1</sup> / <sub>2</sub> "	12
TK-219-SC	3½"	3 <sup>3</sup> / <sub>64</sub> "	5 <sup>1</sup> / <sub>16</sub> "	10
TK-2110-SC	4"	3 <sup>3</sup> / <sub>16</sub> "	5 <sup>4</sup> / <sub>16</sub> "	6

U.L. File No. E-16592 – ½"-4"  
CSA File No. LR-12798 – ½"-1¼", 2½"-4"




### Offset Compression Connectors – Die Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
TO-211SC	¾" offset	½"	1"	200
TO-212	¾" offset	¾"	1.16"	100


U.L. File No. E-16592

# Steel City®


## Thinwall Conduit Fittings (EMT)



• Concrete Tight, when taped



• Concrete Tight, when taped



• Concrete Tight, when taped

### Set Screw Connectors – Die Cast Zinc, Noninsulated

Cat. No.	Conduit Size	A		B	Std. Ctn.
		TC-221 Series	TC-821 Series		
TC-221-SC	1/2"	1 5/32"	1 1/64"	1 5/16"	500
TC-222-SC	3/4"	1 9/32"	1 3/64"	1 5/32"	250
TC-223-SC	1"	1 1/6"	1 21/32"	1 27/64"	200
TC-224-SC	1 1/4"	1 5/16"	2 1/32"	1 13/16"	100
TC-225-SC	1 1/2"	2 3/32"	2 3/8"	2 3/64"	40
TC-226-SC	2"	2 33/64"	2 39/64"	2 17/32"	20
TC-227-SC	2 1/2"	3 3/16"	3 3/32"	3 19/64"	12
TC-228-SC	3"	3 25/64"	3 31/64"	4 1/16"	12
TC-229-SC	3 1/2"	3 31/64"	3 19/32"	4 17/32"	10
TC-2210-SC	4"	3 47/64"	3 53/64"	5 1/16"	6

Noninsulated  
 U.L. File No. E-16592 – 1/2"-2"  
 U.L. File No. E-1275 – 2 1/2"-4"  
 CSA File No. LR-12798 – 1/2"-1", 2 1/2"-4"

### Set Screw Connectors – Die Cast Zinc, Insulated

Cat. No.	Conduit Size	A		B	Std. Ctn.
		TC-221 Series	TC-821 Series		
TC-821-SC	1/2"	1 5/32"	1 1/64"	1 5/16"	500
TC-822-SC	3/4"	1 9/32"	1 3/64"	1 5/32"	250
TC-823-SC	1"	1 1/6"	1 21/32"	1 27/64"	200
TC-824-SC	1 1/4"	1 5/16"	2 1/32"	1 13/16"	100
TC-825-SC	1 1/2"	2 3/32"	2 3/8"	2 3/64"	40
TC-826-SC	2"	2 33/64"	2 39/64"	2 17/32"	20
TC-827-SC	2 1/2"	3 3/16"	3 3/32"	3 19/64"	12
TC-828-SC	3"	3 25/64"	3 31/64"	4 1/16"	12
TC-829-SC	3 1/2"	3 31/64"	3 19/32"	4 17/32"	10
TC-8210-SC	4"	3 47/64"	3 53/64"	5 1/16"	6

Insulated  
 U.L. File No. E-16592 – 1/2"-2"  
 U.L. File No. E-1275 – 2 1/2"-4"  
 CSA File No. LR 12798 – 1/2"-2"



### Set Screw Couplings – Die Cast Zinc


Cat. No.	Conduit Size	A	B	Std. Ctn.
TK-222	3/4"	1 29/32"	1 5/32"	250
TK-223	1"	2"	1 7/16"	200
TK-224	1 1/4"	2 33/64"	1 27/32"	100
TK-225	1 1/2"	2 27/32"	2 1/16"	40
TK-226	2"	3 13/32"	2 1/2"	20
TK-227	2 1/2"	4 7/32"	3 19/64"	12
TK-228	3"	4 11/16"	4 3/64"	12
TK-229	3 1/2"	4 27/32"	4 17/32"	10
TK-2210	4"	5 15/32"	4 9/16"	6

U.L. File No. E-16592 – 1/2"-2"  
 U.L. File No. E-1275 – 2 1/2"-4"  
 CSA File No. LR-12798 – 1/2"-1 1/4", 2 1/2"-4"




# Steel City®

## Thinwall Conduit Fittings (EMT)



### EMT Connectors 90° Angle – Die Cast Zinc

Cat. No.	Trade Size	A	B	C	Std. Ctn.
<b>SET SCREW TYPE</b>					
TC-921	½"	1.27	1.15	.45	200
<b>COMPRESSION TYPE</b>					
TC-911-SC	½"	1.37	1.15	.45	200
TC-912-SC	¾"	1.86	.95	.52	200




• Concrete Tight, when taped

### Capped Corner Couplings – Die-Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
TL-291	½"	1.81"	1.00"	100
TL-292	¾"	2.00"	1.25"	50

U.L. File No. E-16592  
CSA File No. LR-12798




• Concrete Tight, when taped

### Set Screw Connectors – Die-Cast Zinc, Offset

Cat. No.	Offset	Conduit Size	A	B	C	Std. Ctn.
TO-221	⅜"	½"	2.00"	.90"	.37	100
TO-222	¾"	¾"	2.98"	1.16"	.25	100
TO-223	¾"	1"	3.15"	1.42"	.75	100


U.L. File No. E-16592  
CSA File No. LR-18130M57



### EMT to Box Set Screw Type – Die-Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
TL-211	½"	1.31"	.93"	100
TL-212	¾"	1.47"	1.22"	50

U.L. File No. E-1275



### EMT to EMT Set Screw Type – Die-Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
TL-201	½"	1.31"	1.10"	100
TL-202-SC	¾"	1.60"	1.24"	50
TL-203	1"	1.94"	1.59"	25
TL-204	1¼"	2.26"	1.97"	25

U.L. File No. E-1275




E

Steel City®



# Steel City®

## Thinwall Conduit Fittings (EMT)



• Concrete Tight, when taped


### Combination Set Screw Couplings – Die-Cast Zinc Flexible Metal Conduit to EMT

Cat. No.	Conduit Size	A	B	Std. Ctn.
TX-220	3/8" flex to 1/2" EMT	1 5/8"	1/2"	500
TX-221	1/2" flex to 1/2" EMT	1 3/16"	1 3/32"	250
TX-222	3/4" flex to 3/4" EMT	1 31/32"	1 1/32"	150
TX-223	1" flex to 1" EMT	2 7/4"	1 5/8"	150

U.L. File No. E-1275

E

Steel City®




• Concrete Tight, when taped

### Combination Set Screw Couplings – Thinwall to Heavywall – Die-Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
HT-221	1/2" EMT to 1/2" Rigid	1.67"	1.07"	500
HT-222	3/4" EMT to 3/4" Rigid	1.98"	1.29"	250
HT-223	1" EMT to 1" Rigid	2.15"	1.58"	100


U.L. File No. E-1275



• Steel  
• Rain Tight  
• Zinc Plated

### Combination Compression Couplings – Thinwall to Liquidtight Flexible Metal Conduit – Steel


Cat. No.	Conduit Size	A	B	C	Std. Ctn.
LTT-111	1/2" EMT to 1/2" Liquidtight	1 3/4"	1 5/16"	1 1/8"	100
LTT-112	3/4" EMT to 3/4" Liquidtight	1 3/4"	1 11/64"	1 3/8"	50
LTT-113	1" EMT to 1" Liquidtight	1 15/16"	1 1/2"	1 3/4"	25



• Steel  
• Rain Tight  
• Zinc Plated


### Combination Compression Couplings – Heavywall to Liquidtight Flexible Metal Conduit – Steel

Cat. No.	Conduit Size	A	B	C	Std. Ctn.
LTH-111	1/2" Rigid to 1/2" Liquidtight	1 7/8"	1 1/8"	1 1/8"	100




### Combination Couplings – EMT to Flex Compression to Screw-In Type – Die Cast Zinc

Cat. No.	Trade Size	A	B	Std. Ctn.
TX-201	½"	0.84	1.10	500
TX-202	¾"	0.95	1.30	250



### Combination Couplings – EMT to Flex Set Screw Type – Die Cast Zinc


Cat. No.	Fig. #	Trade Size	A-Min	A-Max	B	Std. Ctn.
TX-210	1	½" - ⅜"	0.15	0.61	1.16	250
TX-211	2	½" - ½"	0.60	1.00	1.71	250
TX-212	2	¾" - ¾"	0.78	1.20	1.93	200



- Steel
- Zinc Plated

### One Hole Snap-Straps – Steel

Cat. No.	Conduit Size	A	B	Std. Ctn.
TS-101	½"	0.57"	1.79"	1000
TS-102	¾"	0.62"	1.96"	500
TS-103	1"	0.75"	2.25"	500
TS-104	1¼"	0.88"	2.85"	250
TS-105	1½"	0.99"	3.16"	100
TS-106	2"	1.10"	3.93"	50
HS-107	2½"	1.28"	5.00"	25
HS-108	3"	1.28"	5.55"	25
HS-109	3½"	1.28"	6.37"	10
HS-110	4"	1.28"	6.87"	10




### Pipe Spacers for Thinwall or Heavywall – Die Cast

Cat. No.	Conduit Size	A	B	Std. Ctn.
CB-201	½"	2"	1"	1000
CB-202	¾"	2¾"	1¼"	500
CB-203	1"	2¾"	1⅞"	500
CB-204	1⅞"	2¾"	1½"	250
CB-205	1½"	3⅜"	1⅞"	100
CB-206	2"	4½"	2"	50

# Steel City®


## Thinwall Conduit Fittings (EMT)




- Steel
- Zinc Plated

E


Steel City®



- Stamped Steel
- Zinc Plated



EMT Connector



Space Cap

### Two Hole EMT Straps – Steel

Cat. No.	Conduit Size	A	B	Std. Ctn.
TS-901	1/2"	0.56"	2.20"	250
TS-902	3/4"	0.62"	2.67"	200
TS-903	1"	0.68"	2.97"	100
TS-904	1 1/4"	0.75"	3.67"	50
TS-905	1 1/2"	0.88"	4.22"	200
TS-906	2"	1.00"	4.91"	25

### Nail Strap – Steel

Cat. No.	Rigid/MC Size	EMT Size	Flex Size	A	B	Std. Ctn.
N-101-SC	–	1/2"	3/8"	1 15/16"	1 5/64"	1000
N-102-SC	1/2"	3/4"	1/2"	2 3/16"	1 17/32"	1000
N-103-SC	3/4"	1"	–	2 3/8"	1 15/32"	1000

### EMT Connectors – Two Piece Type – Die Cast Zinc


Cat. No.	Trade Size	A	B	Std. Ctn.
TC-201-SC	1/2"	0.68	1.05	1000

UL File No. E16592

### Space Caps – Plastic

Cat. No.	Conduit Size	A	B	Std. Ctn.
BT-501	1/2"	2 15/32"	1 33/64"	100
BT-502	3/4"	2 15/32"	1 47/64"	100
BT-503	1"	2 15/32"	1 31/32"	100
BT-504	1 1/4"	2 15/32"	2 31/64"	100
BT-505	1 1/2"	2 15/32"	3 1/32"	100

**Thomas & Betts**



TYPE BLR

### Aluminum Conduit Bodies, Covers and Gaskets – LR Style


Cat. No.	Trade Size	A	B	Std. Ctn.
BLR-1	1/2"	3 7/8	2	50
BLR-2	3/4"	4 5/8	2 3/16	50
BLR-3	1"	5 3/8	2 1/2	25
BLR-4	1 1/4"	7 1/4	3 3/8	10
BLR-5	1 1/2"	7 1/4	3 3/8	10
BLR-6	2"	9 1/2	3 15/16	5
BLR-7*	2 1/2"	12 1/4	5 1/2	1
BLR-8*	3"	12 1/4	5 1/2	1
BLR-9*	3 1/2"	15	6 1/2	1
BLR-10*	4"	15	6 1/2	1

\* Shipped with cover. Price includes cost of cover and body.



E

Steel City®




TYPE BLL

### Aluminum Conduit Bodies, Covers and Gaskets – LL Style

Cat. No.	Trade Size	A	B	Std. Ctn.
BLL-1	1/2"	3 7/8	2	50
BLL-2	3/4"	4 5/8	2 5/16	50
BLL-3	1"	5 3/8	2 1/2	25
BLL-4	1 1/4"	7 1/4	3 3/8	10
BLL-5	1 1/2"	7 1/4	3 3/8	10
BLL-6	2"	9 1/2	3 15/16	5
BLL-7*	2 1/2"	12 1/4	5 1/2	1
BLL-8*	3"	12 1/4	5 1/2	1
BLL-9*	3 1/2"	15	6 1/2	1
BLL-10*	4"	15	6 1/2	1

\* Shipped with cover. Price includes cost of cover and body.




TYPE BC

### Aluminum Conduit Bodies, Covers and Gaskets – C Style

Cat. No.	Trade Size	A	B	Std. Ctn.
BC-1-RD	1/2"	3 7/8	1 21/64	50
BC-2-RD	3/4"	4 5/8	1 17/32	50
BC-3	1"	5 3/8	1 3/4	25
BC-4	1 1/4"	7 1/4	2 1/2	10
BC-5	1 1/2"	7 1/4	2 1/2	10
BC-6	2"	9 1/2	3 3/8	5
BC-7*	2 1/2"	12 1/4	4 1/2	1
BC-8*	3"	12 1/4	4 1/2	1
BC-9*	3 1/2"	15	5 1/2	1
BC-10*	4"	15	5 1/2	1

\* Shipped with cover. Price includes cost of cover and body.




TYPE BLB


### Aluminum Conduit Bodies, Covers and Gaskets – LB Style

Cat. No.	Trade Size	A	B	Std. Ctn.
BLB-1	1/2"	3 7/8	2 1/16	50
BLB-2	3/4"	4 5/8	2 7/16	50
BLB-3	1"	5 3/8	2 3/4	25
BLB-4	1 1/4"	7 1/4	3 9/16	10
BLB-5	1 1/2"	7 1/4	3 3/16	10
BLB-6	2"	9 1/2	4 1/2	5
BLB-7*	2 1/2"	12 1/4	5 1/4	1
BLB-8*	3"	12 1/4	5 7/8	1
BLB-9*	3 1/2"	15	6 15/16	1
BLB-10*	4"	15	6 9/16	1

\* Shipped with cover. Price includes cost of cover and body.



TYPE BT



TYPE BLRL

E

Steel City®

### Aluminum Conduit Bodies, Covers and Gaskets – T Style


Cat. No.	Trade Size	A	B	Std. Ctn.
BT-1	1/2"	3 7/8	2 1/16	50
BT-2	3/4"	4 5/8	2 1/32	50
BT-3	1"	5 3/8	2 5/8	25
BT-4	1 1/4"	7 1/4	3 1/32	10
BT-5	1 1/2"	7 1/4	3 1/32	10
BT-6	2"	9 1/2	4	5
BT-7*	2 1/2"	12 1/4	5 25/32	1
BT-8*	3"	12 1/4	5 25/32	1
BT-9*	3 1/2"	15	6 13/16	1
BT-10*	4"	15	6 13/16	1

\* Shipped with cover. Price includes cost of cover and body.

### Aluminum Conduit Bodies, Covers and Gaskets – LR Style

Cat. No.	Trade Size	A	B	Std. Ctn.
BLRL-1	1/2"	3 7/8	2	50
BLRL-2	3/4"	4 5/8	2 5/16	50
BLRL-3	1"	5 3/8	2 1/2	25
BLRL-4	1 1/4"	7 1/4	3 3/8	10
BLRL-5	1 1/2"	7 1/4	3 3/8	10
BLRL-6	2"	9 1/2	3 15/16	5

\* Shipped with cover. Price includes cost of cover and body.



### Aluminum Covers with Stainless Steel Screws

- Stamped aluminum (1/2" thru 2" sizes) or die cast aluminum (2 1/2" thru 4" sizes).
- Steel zinc plated screws.

Cat. No.	Conduit Size	Std. Ctn.
CV-1	1/2"	250
CV-2	3/4"	250
CV-3	1"	250
CV-4	1 1/4" - 1 1/2"	50
CV-5	2"	25
CV-6	2 1/2" - 3"	5
CV-7	3 1/2" - 4"	5
SCV-1	1/2"	250
SCV-2	3/4"	250
SCV-3	1"	250
SCV-4	1 1/4" - 1 1/2"	250
SCV-5	2"	100



Fiber Gasket

### Gaskets – Composition

Cat. No.	Conduit Size	Std. Ctn.
GKV-1	1/2"	100
GKV-2	3/4"	50
GKV-3	1"	25
GKV-4	1 1/4" - 1 1/2"	25
GKV-5	2"	25
GKV-6	2 1/2" - 3"	5
GKV-7	3 1/2" - 4"	5



Neoprene Gasket


- Fiber or neoprene material

### Gaskets – Neoprene



Cat. No.	Conduit Size	Std. Ctn.
GKN-1	1/2"	100
GKN-2	3/4"	50
GKN-3	1"	25
GKN-4	1 1/4" - 1 1/2"	25
GKN-5	2"	25
GKN-6	2 1/2" - 3"	5
GKN-7	3 1/2" - 4"	5

# Steel City®


## Rigid/Intermediate Grade Conduit Fittings



- Steel
- Zinc Plated



- 1/2"-2 1/2" – Steel
- 3"-4" – Malleable Iron/Zinc plated



- 1/2"-2 1/2" – Steel
- 3"-4" – Malleable Iron/Zinc plated

### Snap in Blanks

Cat. No.	Conduit Size	Diameter	Std. Ctn.
BL-111	1/2"	1 5/64"	1000
BL-112	3/4"	1 1/4"	1000
BL-113	1 1/4"	1 1/2"	1000
BL-114	1"	1 13/16"	500
BL-115	1 1/2"	2 7/32"	500
BL-116	2"	2 1 1/16"	250

### Box Spacer – Die-Cast Zinc (1/4" space)

Cat. No.	Conduit Size	A	B	Std. Ctn.
BS-201	1/2"	1 1/8"	1 3/32"	500

U.L. File No. E-1275

### Threadless Compression Connectors

Cat. No.	Conduit Size	Std. Ctn.
HC-401	1/2"	300
HC-402	3/4"	150
HC-403	1"	90
HC-404	1 1/4"	60
HC-405	1 1/2"	30
HC-406	2"	12
HC-407	2 1/2"	12
HC-408	3"	6
HC-409	3 1/2"	6
HC-410	4"	6

Suggested use – rigid conduit only.

U.L. File No. E-1275 1/2" thru 1 1/4"

### Threadless Compression Couplings

Cat. No.	Conduit Size	Std. Ctn.
HK-401	1/2"	300
HK-402	3/4"	150
HK-403	1"	90
HK-404	1 1/4"	60
HK-405	1 1/2"	30
HK-406	2"	6
HK-407	2 1/2"	6
HK-408	3"	4
HK-409	3 1/2"	4
HK-410	4"	4

Suggested use – rigid conduit only.


U.L. File No. E-1275 1/2" thru 1 1/4"

**Thomas & Betts**



# Steel City®

## Rigid/Intermediate Grade Conduit Fittings



- Steel (concrete tight), when taped
- Zinc plated


### Set Screw Connectors

Cat. No.	Conduit Size	A	B	Std. Ctn.
HC-101	1/2"	1 1/8"	1 1/8"	100
HC-102	3/4"	1 3/8"	1 1/2"	50
HC-103	1"	5/8"	1 13/16"	50
HC-104	1 1/4"	2"	2"	25
HC-105	1 1/2"	2 1/2"	2 3/8"	25
HC-106	2"	2 3/4"	2 3/8"	20
HC-107	2 1/2"	3 13/32"	3 3/16"	10
HC-108	3"	4 1/32"	3 7/16"	5
HC-109	3 1/2"	4 9/16"	3 13/16"	5
HC-110	4"	5 3/32"	4 3/32"	5

One Set Screw or Two  
 Two set screws starting at 2" Trade Size  
 Suggested use – rigid conduit only  
 U.L. File No. E-1275 1/2" thru 1 1/4"

E

Steel City®




- Steel (concrete tight), when taped
- Zinc plated

### Set Screw Connectors – Insulated

Cat. No.	Conduit Size	A	B	Std. Ctn.
HC-701	1/2"	1 1/8"	1 1/8"	100
HC-702	3/4"	1 3/8"	1 1/2"	50
HC-703	1"	5/8"	1 13/16"	25
HC-704	1 1/4"	2"	2"	25
HC-705	1 1/2"	2 1/2"	2 3/8"	25
HC-706	2"	2 3/4"	2 3/8"	20
HC-707	2 1/2"	3 13/32"	3 3/16"	10
HC-708	3"	4 1/32"	3 7/16"	5

One Set Screw or Two  
 Two set screws starting at 2" Trade Size  
 Suggested use – rigid conduit only  
 U.L. File No. E-1275 1/2" thru 1 1/4"



- Steel (concrete tight), when taped
- Zinc plated

### Set Screw Couplings


Cat. No.	Conduit Size	A	B	Std. Ctn.
HK-101	1/2"	1 1/8"	2 13/32"	100
HK-102	3/4"	1 3/8"	2 17/32"	50
HK-103	1"	1 3/8"	2 11/16"	25
HK-104	1 1/4"	2"	2 25/32"	25
HK-105	1 1/2"	2 1/4"	3 11/64"	25
HK-106	2"	2 3/4"	3 13/32"	20
HK-107	2 1/2"	3 7/16"	3 29/32"	10
HK-108	3"	4 1/16"	4 5/32"	5
HK-109	3 1/2"	4 9/16"	4 7/8"	5
HK-110	4"	5 1/16"	5 3/8"	5

Two set screws starting at 2".  
 U.L. File No. E-1275


**Thomas & Betts**





## Rigid/Intermediate Grade Conduit Fittings



Rigid Connector



Rigid Coupling



- ½"-2½" – Steel
- 2½"-6" – Malleable Iron
- Zinc plated

### Rigid Connectors – Set Screw Type – Die Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
HC-201	½"	1.34	0.39	250
HC-202	¾"	1.44	0.45	250
HC-203	1"	1.54	0.49	100
<b>WITH INSULATED THROAT</b>				
HC-801	½"	1.34	0.39	250
HC-802	¾"	1.44	0.45	250
HC-803	1"	1.54	0.49	100

### Rigid Couplings – Set Screw Type – Die Cast Zinc

Cat. No.	Trade Size	A	B	Std. Ctn.
HK-201	½"	1.77	1.09	250
HK-202	¾"	2.06	1.34	250
HK-203	1"	2.29	1.61	100

### 90° Short Radius Elbows – Die Cast Zinc

Cat. No.	Size (in.)	Dimensions (in.)		Shf. Ctn./ Ship Qty.
		A	B	
HL-201-SC	½"	.98	.96	50/500
HL-202-SC	¾"	1.17	1.04	25/250

USE: To join rigid or IMC conduit at right angles where lack of room prevents using a standard sweep elbow, or to terminate a run of rigid or IMC conduit at a box.

UL Listing E37148

### Three Piece Couplings


Cat. No.	Conduit Size	Dimensions (in.)		Shf. Ctn./ Ship Qty.
		A (Assembled)	B	
EK-401	½"	1 1/16"	1 1/8"	100
EK-402	¾"	1 1/8"	1 11/32"	50
EK-403	1"	1 3/8"	1 5/8"	25
EK-404	1 1/4"	1 21/32"	2 5/32"	25
EK-405	1 1/2"	1 7/8"	2 23/32"	25
EK-406	2"	2"	3 33/64"	20
EK-407	2 1/2"	2 1/2"	3 29/64"	10
EK-408	3"	3 3/8"	4 23/32"	6
EK-409	3 1/2"	3 3/8"	5 7/32"	5
EK-410	4"	3 29/32"	5 29/32"	5
EK-411	5"	4 7/16"	7"	1
EK-412	6"	4 9/16"	8 1/8"	1

U.L. File No. E-1275 ½" thru 4"



# Steel City®

## Rigid/Intermediate Grade Conduit Fittings




### Rigid Couplings – Three Piece Type – Die Cast Zinc

Cat. No.	Trade Size	A	B	Std. Ctn.
EK-201	½"	1.39	1.31	100
EK-202	¾"	1.53	1.58	50



E


Steel City®



### Pull Corner Elbows – Die Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
HL-601	½"	1.31"	1.10"	100
HL-602	¾"	1.60"	1.24"	50
HL-603	1"	1.95"	1.59"	25
HL-604	1¼"	2.26"	1.97"	30


U.L. File No. E-1275



### Rigid to Box with Gasket – Die-Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
HL-611	½"	1.31"	1.09"	100
HL-612	¾"	1.47"	1.29"	50

U.L. File No. E-1275



H050-SC Series Hub

- The T&B Hub with sealing ring will not fall out.
- Provides superior sealing for exceptional watertight performance.





### The T&B Hub Zinc Die Cast with Insulated Throat\*

Cat. No.	Hub Size	Std. Ctn.
H050-SC	½"	100
H075-SC	¾"	100
H100-SC	1"	25
H125-SC	1¼"	25
H150-SC	1½"	10
H200-SC	2"	5
H250-SC	2½"	5
H300-SC	3"	2
H350-SC	3½"	2
H400-SC	4"	1
H500-SC	5"	1
H600-SC	6"	1

\*Available in Nickel-Chrome plating. Consult customer service for price and delivery.

\*Available with PVC coating. Consult customer service for price and delivery.

**Thomas & Betts**



### Conduit Nipples – Iron/Zinc Plated

Cat. No.	Conduit Size	A	B	Std. Ctn.
841-TB	3/8"	9/16"	1 1/16"	500
HA-401	1/2"	1 1/16"	1 5/16"	500
HA-402	3/4"	1 3/16"	1 7/32"	200
HA-403	1"	7/8"	1 1/16"	100
HA-404	1 1/4"	1 1/8"	1 3/4"	100
HA-405	1 1/2"	1 1/8"	2 1/16"	50
HA-406	2"	1 7/16"	2 3/16"	50
HA-407	2 1/2"	1 1/4"	3"	20
HA-408	3"	1 1/2"	3 7/8"	10
HA-409	3 1/2"	1 3/4"	4 3/8"	5
HA-410	4"	–	–	5
HA-411	5"	–	–	1
HA-412	6"	–	–	1

U.L. File No. E-1275 3/8"-3 1/2"

### Conduit Nipples – Insulated Iron/Zinc Plated

Cat. No.	Conduit Size	A	B	Std. Ctn.
HA-901	1/2"	1 1/16"	1 5/16"	500
HA-902	3/4"	1 3/16"	1 7/32"	200
HA-903	1"	7/8"	1 1/16"	100
HA-904	1 1/4"	1 1/8"	1 3/4"	100
HA-905	1 1/2"	1 1/8"	2 1/16"	50
HA-906	2"	1 7/16"	2 3/16"	50



### Conduit Nipples – Die Cast Zinc – Noninsulated

Cat. No.	Conduit Size	A	B	Std. Ctn.
HA-201	1/2"	0.98"	0.59"	1000
HA-202	3/4"	1.18"	0.70"	500
HA-203	1"	1.50"	0.80"	250
HA-204	1 1/4"	1.75"	1.06"	250
HA-205	1 1/2"	2.11"	1.01"	100
HA-206	2"	2.61"	1.20"	40
HA-207	2 1/2"	3.13"	1.49"	40
HA-208	3"	3.90"	1.65"	40
HA-209	3 1/2"	4.20"	1.68"	40
HA-210	4"	4.79"	1.73"	20


U.L. File No. E-1275 1/2" – 2"



### Conduit Nipples – Die Cast Zinc – Insulated

Cat. No.	Conduit Size	A	B	Std. Ctn.
HA-801	1/2"	0.98"	0.59"	1000
HA-802	3/4"	1.18"	0.70"	500
HA-803	1"	1.50"	0.80"	250
HA-804	1 1/4"	1.75"	1.06"	250
HA-805	1 1/2"	2.11"	1.01"	100
HA-806	2"	2.61"	1.20"	40
HA-807	2 1/2"	3.13"	1.49"	25
HA-808	3"	3.90"	1.65"	10
HA-809	3 1/2"	4.20"	1.68"	10
HA-810	4"	4.79"	1.73"	10

U.L. File No. E-1275 1/2" & 3/4" only




### Conduit Nipples – Die Cast Zinc 1" Long

Cat. No.	Conduit Size	A	B	Std. Ctn.
HA-211	1/2"	1"	1 9/16"	1000
HA-212	3/4"	1"	1 3/8"	500
HA-213	1"	1"	1 7/8"	250

U.L. File No. E-1275 1/2" & 3/4" only

E

Steel City®




### Offset Nipples – Die Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
HO-221	1/2"	2.60"	1.00"	100
HO-222	3/4"	2.62"	1.32"	100
HO-223	1"	2.68"	1.51"	100
HO-224	1 1/4"	2.85"	1.85"	50
HO-225	1 1/2"	2.88"	2.08"	50
HO-226	2"	3.19"	2.71"	20

3/4" offset.


U.L. File No. E-1275



### Locknuts – Steel/Zinc Plated

Cat. No.	Conduit Size	Dimensions (in.)		Std. Ctn.
		A (min.)	B (max.)	
LN-100-SC	3/8"	–	–	1000
LN-101-SC	1/2"	0.125"	1.140"	1000
LN-102	3/4"	0.140"	1.420"	1000
LN-103	1"	0.170"	1.770"	500
LN-104	1 1/4"	0.170"	2.281"	200
LN-105	1 1/2"	0.170"	2.598"	100
LN-106	2"	0.187"	3.175"	50
LN-107	2 1/2"	0.375"	3.562"	30
LN-108	3"	0.375"	4.250"	25
LN-109	3 1/2"	0.438"	4.803"	25
LN-110	4"	0.438"	5.402"	25
LN-111	5"	0.500"	6.674"	10
LN-112	6"	0.561"	7.934"	10


U.L. File No. E-1275



### Thin Construction Locknuts–Steel/Zinc Plated

Cat. No.	Conduit Size	Unit Qty.	Std. Ctn.
SPLN-107	2 1/2"	30	30
SPLN-108	3"	25	25
SPLN-109	3 1/2"	25	25
SPLN-110	4"	25	25

\*Not U.L. Listed




### Locknuts – Die Cast Zinc

Cat. No.	Conduit Size	Dimensions (in.)		Std. Ctn.
		A (min.)	B (max.)	
LN-201	½"	0.125"	1.140"	2000
LN-202	¾"	0.140"	1.420"	1000
LN-203	1"	0.170"	1.770"	1000
LN-204	1¼"	0.170"	2.281"	500
LN-205	1½"	0.170"	2.598"	500
LN-206	2"	0.187"	3.175"	200
LN-207	2½"	0.375"	3.562"	100
LN-208	3"	0.375"	4.250"	100
LN-209	3½"	0.438"	4.803"	40
LN-210	4"	0.438"	5.402"	40

CSA File No. LR-12798

U.L. File No. E-1275




### Locknuts–Nonmetallic

Cat. No.	Trade Size	"A" Dia.	"B" Thd.	Std. Ctn.
LN-501	½"	1.3	½-14	100
LN-502	¾"	1.4	¾-14	100
LN-503	1"	1.7	1-11½	50

Material: Nylon 6/6


Color: Gray



### Sealing Locknuts – Steel/Zinc Plated

Cat. No.	Conduit Size	Dimensions (in.)		Std. Ctn.
		A (min.)	B (max.)	
LS-101	½"	0.26"	1.12"	1000
LS-102	¾"	0.27"	1.37"	1000
LS-103	1"	0.28"	1.75"	500
LS-104	1¼"	0.32"	2.06"	200
LS-105	1½"	0.32"	2.37"	100
LS-106	2"	0.32"	2.87"	50
LS-107	2½"	0.32"	3.43"	50
LS-108	3"	0.32"	4.12"	50
LS-109	3½"	0.32"	4.62"	50
LS-110	4"	0.32"	5.18"	25


U.L. File No. E-1275



### Grounding Locknuts – Malleable Iron/Zinc Plated

Cat. No.	Conduit Size	Dimensions (in.)		Std. Ctn.
		A (min.)	B (max.)	
LG-401	½"	0.125"	1.140"	100
LG-402	¾"	0.140"	1.420"	100
LG-403	1"	0.170"	1.770"	50
LG-404	1¼"	0.170"	2.281"	50
LG-405	1½"	0.170"	2.598"	50
LG-406	2"	0.187"	3.175"	25
LG-407	2½"	0.375"	3.562"	10
LG-408	3"	0.375"	4.250"	10
LG-409	3½"	0.438"	4.803"	50
LG-410	4"	0.438"	5.402"	5


U.L. File No. E-1275



- 105°C thermoplastic liners.
- Heavy reinforced ribs.


### Conduit Bushings Die Cast Zinc – Insulated Metallic

Cat. No.	Conduit Size	A	B	Std. Ctn.
BU-801	½"	1.06	0.43	1000
BU-802	¾"	1.31	0.43	1000
BU-803	1"	1.59	0.48	500
BU-804	1¼"	1.96	0.56	250
BU-805	1½"	2.18	0.60	250
BU-806	2"	2.68	0.56	250
BU-807	2½"	3.25	0.90	50
BU-808	3"	3.87	0.85	25
BU-809	3½"	4.37	0.93	25
BU-810	4"	5.00	0.93	10



### Conduit Bushings Die Cast Zinc – Heavy Reinforced Ribs


Cat. No.	Conduit Size	Dimensions (in.)		Std. Ctn.
		A (min.)	B (max.)	
BU-201	½"	1.05	0.37	1000
BU-202	¾"	1.32	0.37	1000
BU-203	1"	1.58	0.47	500
BU-204	1¼"	1.94	0.50	250
BU-205	1½"	2.20	0.52	250
BU-206	2"	2.69	0.52	250
BU-207	2½"	3.23	0.85	50
BU-208	3"	3.84	0.85	25
BU-209	3½"	4.35	0.85	25
BU-210	4"	5.02	0.85	10



### Insulated Bushings – Thermoplastic

Cat. No.	Conduit Size	A	B	Std. Ctn.
BU-501	½"	1 <sup>3</sup> / <sub>32</sub> "	1 <sup>1</sup> / <sub>16</sub> "	400
BU-502	¾"	1 <sup>3</sup> / <sub>32</sub> "	1 <sup>1</sup> / <sub>8</sub> "	400
BU-503	1"	9 <sup>1</sup> / <sub>16</sub> "	1 <sup>1</sup> / <sub>8</sub> "	200
BU-504	1¼"	9 <sup>1</sup> / <sub>16</sub> "	1 <sup>2</sup> / <sub>32</sub> "	100
BU-505	1½"	9 <sup>1</sup> / <sub>16</sub> "	2 <sup>3</sup> / <sub>16</sub> "	100
BU-506	2"	5 <sup>1</sup> / <sub>8</sub> "	2 <sup>1</sup> / <sub>16</sub> "	60
BU-507	2½"	2 <sup>3</sup> / <sub>32</sub> "	3 <sup>3</sup> / <sub>16</sub> "	20
BU-508	3"	4 <sup>7</sup> / <sub>64</sub> "	3 <sup>2</sup> / <sub>32</sub> "	20
BU-509	3½"	3 <sup>1</sup> / <sub>4</sub> "	4 <sup>2</sup> / <sub>64</sub> "	5
BU-510	4"	2 <sup>5</sup> / <sub>32</sub> "	4 <sup>2</sup> / <sub>32</sub> "	5
BU-511	5"	1"	6 <sup>5</sup> / <sub>16</sub> "	5
BU-512	6"	1"	7 <sup>1</sup> / <sub>16</sub> "	5


U.L. File No. E-1275 ½"-4" only  
Rated 105°C



### Bushings – Iron/Zinc Plated


Cat. No.	Conduit Size	A	B	Std. Ctn.
BU-401	1/2"	1 1/32"	7/16"	1000
BU-402	3/4"	1 1/4"	7/16"	1000
BU-403	1"	1 9/16"	1/2"	500
BU-404	1 1/4"	1 19/16"	1 1/32"	200
BU-405	1 1/2"	2 13/64"	9/16"	100
BU-406	2"	2 49/64"	9/16"	50
BU-407	2 1/2"	3 3/16"	1 9/32"	30
BU-408	3"	3 3/8"	2 3/32"	25
BU-409	3 1/2"	4 1/16"	2 7/32"	25
BU-410	4"	4 2 1/32"	1 5/16"	25
BU-411	5"	4 2 1/32"	1 5/16"	10

U.L. File No. E-1275



### Insulated Bushings – Iron/Zinc Plated


Cat. No.	Conduit Size	A	B	Std. Ctn.
BI-901	1/2"	1 1/32"	1/2"	1000
BI-902	3/4"	1 1/4"	1/2"	1000
BI-903	1"	1 9/16"	9/16"	500
BI-904	1 1/4"	1 19/16"	1 9/32"	200
BI-905	1 1/2"	2 13/64"	5/8"	100
BI-906	2"	2 49/64"	5/8"	50
BI-907	2 1/2"	3 7/32"	4 7/64"	30
BI-908	3"	3 2 7/32"	4 7/64"	25
BI-909	3 1/2"	4 7/16"	7/8"	25
BI-910	4"	4 3 1/32"	2 9/32"	25



### Grounding Bushings Die Cast Zinc – Insulated Metallic – With Aluminum Lay in Type Lug

Cat. No.	Trade Size	Grounding Lug Wire size		Std. Ctn.
		min.	max	
BG-201	1/2"	14	4	500
BG-202	3/4"	14	4	500
BG-203	1"	14	4	250
BG-204A	1 1/4"	14	4	200
BG-204	1 1/4"	8	1/0	200
BG-205A	1 1/2"	11	4	100
BG-205	1 1/2"	8	1/0	50
BG-206A	1"	14	4	100
BG-206	2"	8	1/0	50
BG-207	2 1/2"	8	1/0	50
BG-207A	2 1/2"	6	250 MCM	50
BG-208	3"	8	1/0	50
BG-208A	3"	6	250 MCM	50
BG-209	3 1/2"	8	1/0	10
BG-209A	3 1/2"	6	250 MCM	10
BG-210	4"	8	1/0	10
BG-210A	4"	6	250 MCM	10


- 105°C Thermoplastic liners.
- Heavy reinforced ribs.



### Insulated Grounding Bushings – Malleable Iron/Zinc Plated

Cat. No.	Conduit Size	Grounding Lug Wire Capacity	A	B	Std. Ctn.
BG-801	1/2"		1 1/32"	1/2"	500
BG-802	3/4"	#14-#4 CU	1 1/4"	1/2"	500
BG-803	1"	or	1 9/16"	9/16"	250
BG-804	1 1/4"	#12-#4 AL	1 15/16"	1 9/32"	150
BG-805	1 1/2"		2 13/64"	5/8"	150
BG-806	2"		2 45/64"	5/8"	100
BG-807	2 1/2"	#14-1/0 CU	3 3/16"	4 7/64"	60
BG-808	3"	or #12-1/0 AL	3 5/8"	4 7/64"	30
BG-809	3 1/2"	#6-250 MCM	4 1/16"	7/8"	30
BG-810	4"	CU or AL	4 2 1/32"	2 9/32"	30


U.L. File No. E-19851  
 1/2"-2" Iron  
 2 1/4"-4" Die Cast Zinc



### Grounding Bushings Die Cast Zinc – Insulated Metallic With Aluminum Lug

Cat. No.	Trade Size	Grounding Lug Wire size		Std. Ctn.
		min.	max	
BG-801A	1/2"	14	6	500
BG-802A	3/4"	14	6	500
BG-803A	1"	14	6	250
BG-804A	1 1/4"	14	2	200
BG-805A	1 1/2"	14	2	100
BG-806A	2"	14	2	100
BG-807A	2 1/2"	14	2/0	50
BG-808A	3"	14	2/0	50
BG-809A	3 1/2"	14	2/0	10
BG-810A	4"	14	2/0	10
BG-810B	4"	6	250 MCM	10

U.L. File No. E-19851



### Reducing Bushings



Cat. No.	Conduit Size	A	B	Std. Ctn.
RB-121	3/4"-1/2"	9/16"	7/8"	100
RB-131	1"-1/2"	5/8"	1 1/8"	50
RB-132	1"-3/4"	5/8"	1 1/8"	50
RB-141	1 1/4"-1/2"	1 1/16"	1 7/16"	50
RB-142	1 1/4"-3/4"	1 1/16"	1 7/16"	50
RB-143	1 1/4"-1"	1 1/16"	1 7/16"	50
RB-151	1 1/2"-1/2"	2 3/32"	1 11/16"	50
RB-152	1 1/2"-3/4"	2 3/32"	1 11/16"	50
RB-153	1 1/2"-1"	2 3/32"	1 11/16"	50
RB-154	1 1/2"-1 1/4"	2 3/32"	1 11/16"	50
RB-161	2"-1/2"	2 7/32"	2 3/32"	25
RB-162	2"-3/4"	2 7/32"	2 3/32"	25
RB-163	2"-1"	2 7/32"	2 3/32"	25
RB-164	2"-1 1/4"	2 7/32"	2 3/32"	25
RB-165	2"-1 1/2"	2 7/32"	2 3/32"	25
RB-175	2 1/2"-1 1/2"	7/8"	2 13/16"	25
RB-176	2 1/2"-2"	7/8"	2 13/16"	25
RB-186	3"-2"	2 9/32"	2 7/16"	25
RB-187	3"-2 1/2"	2 9/32"	2 7/16"	25

U.L. File No. E-1275

- For copper or aluminum bare ground wire.
- 105°C thermoplastic liners.
- Heavy reinforced ribs.

- RB-121 thru RB-165 – Steel.
- RB-175 thru RB-187 – Malleable Iron (concrete tight)/ Zinc Plated.





### Reducers and Enlargers – Malleable Iron/Zinc Plated

Cat. No.	Conduit Size	A	B	Std. Ctn.
RB-421	3/4"-1/2"	5/8"	1 3/16"	100
RB-432	1/2"-3/4"	1	1 3/16"	100
RB-443	1"-3/4"	1 1/16"	1 3/16"	50


U.L. File No. E-1275

### Reducing Washers – Steel/Zinc Plated

Cat. No.	Conduit Size	Diameter			Std. Ctn.
		A	B	C	
WA-110	1/2"-3/8"	1 3/16"	1 1/16"	2 7/32"	500
WA-121	3/4"-1/2"	1 1/2"	7/8"	1 1/16"	500
WA-131	1"-1/2"	1 3/4"	7/8"	1 3/16"	500
WA-132	1"-3/4"	1 3/4"	1 3/32"	1 9/16"	500
WA-141	1 1/4"-1/2"	2 3/16"	7/8"	1 11/16"	200
WA-142	1 1/4"-3/4"	2 3/16"	1 3/32"	1 11/16"	200
WA-143	1 1/4"-1"	2 3/16"	1 23/64"	1 11/16"	200
WA-151	1 1/2"-1/2"	2 5/8"	7/8"	1 7/8"	200
WA-152	1 1/2"-3/4"	2 5/8"	1 3/32"	1 7/8"	200
WA-153	1 1/2"-1"	2 5/8"	1 23/64"	1 7/8"	200
WA-154	1 1/2"-1 1/4"	2 5/8"	1 23/32"	1 7/8"	200
WA-161	2"-1/2"	3 1/4"	7/8"	2 3/8"	100
WA-162	2"-3/4"	3 1/4"	1 3/32"	2 3/8"	100
WA-163	2"-1"	3 1/4"	1 23/64"	2 3/8"	100
WA-164	2"-1 1/4"	3 1/4"	1 23/32"	2 3/8"	100
WA-165	2"-1 1/2"	3 1/4"	1 31/32"	2 3/8"	100
WA-171	2 1/2"-1/2"	3 1/4"	7/8"	2 7/8"	100
WA-172	2 1/2"-3/4"	3 1/4"	1 3/32"	2 7/8"	100
WA-173	2 1/2"-1"	3 1/4"	1 23/64"	2 7/8"	100
WA-174	2 1/2"-1 1/4"	3 1/4"	1 23/32"	2 7/8"	100
WA-175	2 1/2"-1 1/2"	3 1/4"	1 31/32"	2 7/8"	100
WA-176	2 1/2"-2"	3 1/4"	2 7/16"	2 7/8"	100
WA-181	3"-1/2"	4 1/2"	7/8"	3 1/2"	100
WA-182	3"-3/4"	4 1/2"	1 23/32"	3 1/2"	100
WA-183	3"-1"	4 1/2"	1 23/64"	3 1/2"	100
WA-184	3"-1 1/4"	4 1/2"	1 23/32"	3 1/2"	100
WA-185	3"-1 1/2"	4 1/2"	1 31/32"	3 1/2"	100
WA-186	3"-2"	4 1/2"	2 7/16"	3 1/2"	100
WA-187	3"-2 1/2"	4 1/2"	2 5/16"	3 1/2"	100


WA-121 thru WA-165 CSA listed.






### One Hole Straps – Steel/Zinc Plated

Cat. No.	Screw Size	Conduit Size	A	B	Std. Ctn.
HS-100-SC	10	3/8"	3/4"	1 7/64"	1000
HS-101	1/4	1/2"	1"	1 15/16"	500
HS-102	1/4	3/4"	1"	2 5/64"	500
HS-103	1/4	1"	1"	2 13/32"	250
HS-104	5/16	1 1/4"	1"	3 3/32"	100
HS-105	3/8	1 1/2"	1 3/16"	3 13/32"	100
HS-106	3/8	2"	1 3/16"	3 27/32"	100
HS-107	7/16	2 1/2"	1 1/4"	5 1/16"	25
HS-108	1/2	3"	1 3/8"	5 7/8"	25
HS-109	1/2	3 1/2"	1 3/8"	6 1/4"	10
HS-110	1/2	4"	1 3/8"	6 7/8"	10



### Pipe Straps – Malleable Iron/Zinc Plated


Cat. No.	Screw Size	Conduit Size	A	B	Std. Ctn.
HS-400	10	3/8"	1 11/16"	1 7/32"	500
HS-401	1/4	1/2"	2 1/64"	5/8"	500
HS-402	1/4	3/4"	2 7/16"	1 3/16"	500
HS-403	1/4	1"	2 7/8"	1 5/16"	100
HS-404-SC	5/16	1 1/4"	3 5/16"	1 1/32"	100
HS-405	3/8	1 1/2"	3 3/4"	1 1/8"	50
HS-406	1/2	2"	4 19/32"	1 5/16"	25
HS-407	5/8	2 1/2"	5 11/16"	1 3/8"	25
HS-408	5/8	3"	6 7/8"	1 7/8"	25
HS-409	5/8	3 1/2"	7 23/32"	2 1/8"	10
HS-410	5/8	4"	8 9/16"	2 3/8"	10
HS-411	5/8	5"	10 3/32"	2 5/8"	5



### Two Hole Strap – Steel/Zinc Plated


Cat. No.	Screw Size	Conduit Size	A	B	C	Std. Ctn.
HS-901	8	1/2"	3/4"	2 7/16"	3/16"	1200
HS-902	10	3/4"	3/4"	2 11/16"	3/16"	900
HS-903	1/4	1"	3/4"	3 7/16"	3/16"	600
HS-904	1/4	1 1/4"	3/4"	3 27/32"	3/16"	450
HS-905	1/4	1 1/2"	3/4"	4 1/16"	3/16"	50
HS-906	1/4	2"	3/4"	4 7/16"	3/16"	150
HS-907	1/4	2 1/2"	1"	5 1/8"	1/4"	150
HS-908	1/2	3"	1"	6 3/16"	1/4"	60
HS-909	1/4	3 1/2"	1"	7 3/16"	1/4"	60
HS-910	1/4	4"	1"	8 11/16"	1/4"	60

CSA Certified




### Nail Strap – Stamped Steel/Zinc Plated

Cat. No.	Rigid/MC Size	EMT Size	Flex Size	A	B	Std. Ctn.
N-101-SC	–	1/2"	3/8"	2 3/32"	1 5/64"	1000
N-102-SC	1/2"	3/4"	1/2"	2 9/16"	1 7/32"	1000
N-103-SC	3/4"	1"	–	2 3/8"	1 5/32"	1000




### Flange Plates – Malleable Iron/Zinc Plated

Cat. No.	Conduit Size	Dia. A	Depth B	Std. Ctn.
FP-401	1/2"	3"	.625	50
FP-402	3/4"	3 3/8"	.656	50
FP-403	1"	3 5/8"	.765	50
FP-404	1 1/4"	4"	.875	25
FP-405	1 1/2"	4 3/8"	.937	25
FP-406	2"	4 7/8"	.843	25




### Pipe Spacers for Rigid/Intermediate or Thinwall – Die Cast Zinc

Cat. No.	Conduit Size	A	B	Std. Ctn.
CB-201	1/2"	2"	1"	1000
CB-202	3/4"	2 3/8"	1 1/16"	500
CB-203	1"	2 3/4"	1 5/16"	500
CB-204	1 1/4"	3 3/8"	1 1/2"	250
CB-205	1 1/2"	3 13/16"	1 5/8"	100
CB-206	2"	4 1/2"	2"	50



### Rigid/Intermediate Space Caps – Plastic

Cat. No.	Conduit Size	A	B	Std. Ctn.
BR-501	1/2"	2 15/32"	1 21/32"	100
BR-502	3/4"	2 15/32"	1 55/64"	100
BR-503	1"	2 15/32"	2 1/8"	100
BR-504	1 1/4"	2 15/32"	2 61/64"	100
BR-505	1 1/2"	2 15/32"	3 13/64"	100



TYPE ALR

E


Steel City®

- Die cast copper free aluminum construction.
- Provide access for pulling, splicing, and maintenance.
- For rigid conduit/IMC applications.
- U.L. Listed.
- Fittings, covers and gaskets are interchangeable with those produced by other leading manufacturers.
- Finish: Powder Coated Urethane.

### Conduit Bodies, Covers and Gaskets – LR Style

Cat. No.	Trade Size	A	B	Std. Ctn.
ALR-1	½"	3⅞	2	50
ALR-2	¾"	4⅝	2⅝ <sub>16</sub>	50
ALR-3	1"	5⅜	2½	25
ALR-4	1¼"	7¼	3⅜	10
ALR-5	1½"	7¼	3⅜	10
ALR-6	2"	9½	3⅝ <sub>16</sub>	5
ALR-7*	2½"	12¼	5½	1
ALR-8*	3"	12¼	5½	1
ALR-9*	3½"	15	6½	1
ALR-10*	4"	15	6½	1

\* Shipped with cover. Price includes cost of cover and body.




TYPE ALL

- Die cast copper free aluminum construction.
- Provide access for pulling, splicing, and maintenance.
- For rigid conduit/IMC applications.
- U.L. Listed.
- Fittings, covers and gaskets are interchangeable with those produced by other leading manufacturers.
- Finish: Powder Coated Urethane.

### Conduit Bodies, Covers and Gaskets – LL Style

Cat. No.	Trade Size	A	B	Std. Ctn.
ALL-1	½"	3⅞	2	50
ALL-2	¾"	4⅝	2⅝ <sub>16</sub>	50
ALL-3	1"	5⅜	2½	25
ALL-4	1¼"	7¼	3⅜	10
ALL-5	1½"	7¼	3⅜	10
ALL-6	2"	9½	3⅝ <sub>16</sub>	5
ALL-7*	2½"	12¼	5½	1
ALL-8*	3"	12¼	5½	1
ALL-9*	3½"	15	6½	1
ALL-10*	4"	15	6½	1

\* Shipped with cover. Price includes cost of cover and body.




TYPE AC

### Conduit Bodies, Covers and Gaskets – C Style

Cat. No.	Trade Size	A	B	Std. Ctn.
AC-1	½"	3⅞	1⅝ <sub>4</sub>	50
AC-2	¾"	4⅝	1⅞ <sub>32</sub>	50
AC-3	1"	5⅜	1¾	25
AC-4	1¼"	7¼	2½	10
AC-5	1½"	7¼	2½	10
AC-6	2"	9½	3⅜	5
AC-7*	2½"	12¼	4½	1
AC-8*	3"	12¼	4½	1
AC-9*	3½"	15	5½	1
AC-10*	4"	15	5½	1

\* Shipped with cover. Price includes cost of cover and body.



TYPE ALB


### Conduit Bodies, Covers and Gaskets – LB Style

Cat. No.	Trade Size	A	B	Std. Ctn.
ALB-1	½"	3⅞	2⅛	50
ALB-2	¾"	4⅝	2⅞	50
ALB-3	1"	5⅜	2¾	25
ALB-4	1¼"	7¼	3⅞	10
ALB-5	1½"	7¼	3⅞	10
ALB-6	2"	9½	4½	5
ALB-7*	2½"	12¼	5¼	1
ALB-8*	3"	12¼	5⅞	1
ALB-9*	3½"	15	6⅞	1
ALB-10*	4"	15	6⅞	1

\* Shipped with cover. Price includes cost of cover and body.

E

Steel City®




TYPE AT

### Conduit Bodies, Covers and Gaskets – C Style

Cat. No.	Trade Size	A	B	Std. Ctn.
AT-1	½"	3⅞	2⅛	50
AT-2	¾"	4⅝	2⅞	50
AT-3	1"	5⅜	2⅞	25
AT-4	1¼"	7¼	3⅞	10
AT-5	1½"	7¼	3⅞	10
AT-6	2"	9½	4	5
AT-7*	2½"	12¼	5⅞	1
AT-8*	3"	12¼	5⅞	1
AT-9*	3½"	15	6⅞	1
AT-10*	4"	15	6⅞	1

\* Shipped with cover. Price includes cost of cover and body.



TYPE ALRL


### Conduit Bodies, Covers and Gaskets – LR Style

Cat. No.	Trade Size	A	B	Std. Ctn.
ALRL-1	½"	3⅞	2	50
ALRL-2	¾"	4⅝	2⅞	50
ALRL-3	1"	5⅜	2½	25
ALRL-4	1¼"	7¼	3⅞	10
ALRL-5	1½"	7¼	3⅞	10
ALRL-6	2"	9½	3⅞	5

\* Shipped with cover. Price includes cost of cover and body.

# Steel City®

## Aluminum Conduit Bodies, Gaskets and Covers



- Stamped aluminum (½" thru 2" sizes) or die cast aluminum (2½" thru 4" sizes).
- Steel zinc plated screws.

E

Steel City®

### Aluminum covers with Stainless Steel Screws

Cat. No.	Conduit Size	Std. Ctn.
CV-1	½"	250
CV-2	¾"	250
CV-3	1"	250
CV-4	1¼" - 1½"	50
CV-5	2"	25
CV-6	2½" - 3"	5
CV-7	3½" - 4"	5
SCV-1	½"	250
SCV-2	¾"	250
SCV-3	1"	250
SCV-4	1¼" - 1½"	250
SCV-5	2"	100



Fiber Gasket

### Gaskets – Composition

Cat. No.	Conduit Size	Std. Ctn.
GKV-1	½"	100
GKV-2	¾"	50
GKV-3	1"	25
GKV-4	1¼" - 1½"	25
GKV-5	2"	25
GKV-6	2½" - 3"	5
GKV-7	3½" - 4"	5



Neoprene Gasket

- Fiber or neoprene material

### Gaskets – Neoprene

Cat. No.	Conduit Size	Std. Ctn.
GKN-1	½"	100
GKN-2	¾"	50
GKN-3	1"	25
GKN-4	1¼" - 1½"	25
GKN-5	2"	25
GKN-6	2½" - 3"	5
GKN-7	3½" - 4"	5

**Thomas & Betts**




### The BLACK BEAUTY™ Nonmetallic Liquidtight Strain Relief Connectors

- Installs on cord by hand.
- Achieves maximum pullout strength without installation tools.
- Each hub size takes a range of cord diameters.
- Non metallic construction provides corrosion resistance.
- Weathers stabilized nylon rated at -34°C to +105°C temperature.



E

Steel City®



E 13938



LR 52391

### Straight

Cat. No.	Trade or Hub Size	Cord Range	Throat Size ± .03	Hex Flat ± .06	A Max.	B ± .06	C ± .06	Std. Ctn.
2671†	3/8"	.125-.275	0.33	.78	2.0	.90	.46	250
2690†	1/2"	.125-.275	0.33	1.00	2.3	.90	.60	100
2672	1/2"	.250-.400	0.55	1.08	2.6	1.27	.60	100
2673*	1/2"	.400-.560	0.55	1.08	2.6	1.27	.60	100
2691*	1/2"	.560-.690	0.54	1.32	3.0	1.57	.60	100
2692*	1/2"	.660-.780	0.54	1.32	3.0	1.57	.60	100
2693	3/4"	.250-.400	0.55	1.22	2.7	1.27	.62	100
2694*	3/4"	.400-.560	0.55	1.22	2.7	1.27	.62	100
2674	3/4"	.560-.690	0.79	1.34	3.0	1.57	.62	100
2675	3/4"	.660-.780	0.79	1.34	3.0	1.57	.62	100
2696*	3/4"	.770-.895	0.76	1.64	3.2	1.89	.62	100
2697	1"	.250-.400	0.54	1.50	2.9	1.27	.77	-
2698*	1"	.400-.560	0.54	1.50	2.9	1.27	.77	100
2695	1"	.560-.690	0.98	1.60	3.1	1.89	.77	100
2676	1"	.660-.780	0.98	1.60	3.3	1.89	.77	100
2677	1"	.770-.895	0.98	1.60	3.3	1.89	.77	100
2678	1"	.870-1.020	0.98	1.60	3.3	1.89	.77	50
2699	1"	.890-1.090	0.98	2.25	4.2	2.58	.77	10
2700	1"	1.080-1.280	0.98	2.25	4.0	2.58	.77	50
2702	1 1/4"	.890-1.090	1.25	2.25	4.2	2.58	.80	10
2703*	1 1/4"	1.080-1.280	1.25	2.25	4.0	2.58	.80	10
2704*	1 1/4"	1.270-1.470	1.25	2.25	4.0	2.58	.80	10
2705-TB	1 1/4"	.890-1.150	1.47	2.65	4.2	2.95	.82	10
2706	1 1/4"	1.140-1.400	1.47	2.65	4.3	2.95	.82	10
2707*	1 1/4"	1.390-1.650	1.47	2.65	4.3	2.95	.82	10
2708	2"	1.190-1.530	1.89	3.13	5.1	3.50	.84	5
2709	2"	1.520-1.860	1.89	3.13	4.9	3.50	.84	5
2710*	2"	1.850-2.190	1.89	3.13	4.9	3.50	.84	5


\*Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

†CSA certified for factory installation.

Material: Weather Stabilized Nylon, Rated at -34°C to 105°C Temperature. For 90° Style See AS-72555.



### 90 Degree Angle



E 13938



LR 52391

Cat. No.	Trade or Hub Size	Cord Range	Throat Size	Hex Flat	A	B	C	D	Std. Ctn.
2680†	3/8"	.125-.275	.33	.62	1.8	.90	.46	1.00	100
2681	1/2"	.250-.400	.55	.83	2.5	1.27	.60	1.35	50
2682*	1/2"	.400-.560	.55	.83	2.5	1.27	.60	1.35	50
2683	3/4"	.560-.690	.78	1.06	2.8	1.57	.62	1.60	50
2684	3/4"	.660-.780	.78	1.06	2.8	1.57	.62	1.60	50
2688	1"	.560-.690	1.00	1.280	3.0	1.89	.77	1.90	25
2685	1"	.660-.780	1.00	1.280	3.0	1.89	.77	1.90	25
2686	1"	.770-.895	1.00	1.280	3.0	1.89	.77	1.90	25
2687*	1"	.870-1.020	1.00	1.280	3.0	1.89	.77	1.90	25

\*Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

†CSA certified for factory installation.




E

Steel City®


### Connectors – Liquidtight Flex for Nonmetallic Conduit

Cat. No.	Trade Size	A± .015 (0.40) Inch (mm)	B* ±.35 (0.90) Inch (mm)	C ±.015 (0.40) Across Corners Inch (mm)	Min. Throat Dia. D. Inch (mm)	E Thread NPT.	F Inch (mm) Approx.	Std. Ctn.
LT-500	3/8"	.570	1.595 (40.51)	1.354	.417	1/2-14	1.880 (47.75)	100
LT-501	1/2"	.570	1.636 (41.55)	1.448	.550	1/2-14	1.986 (50.44)	100
LT-502	3/4"	.582	1.757 (44.63)	1.740	.740	3/4-14	2.212 (56.18)	50
LT-503	1"	.726	1.923 (48.84)	2.068	.940	1-11/12	2.508 (63.70)	50



### 90° Connectors – Liquidtight Flex for Nonmetallic Conduit

Cat. No.	Trade Size	A± .015 (0.40) Inch (mm)	B* ±.35 (0.90) Inch (mm)	C ±.015 (0.40) Across Corners Inch (mm)	Min. Throat Dia. D. Inch (mm)	E Thread NPT.	F Inch (mm) Approx.	Std. Ctn.
LT-590	3/8"	(14.48)	1.380 (35.05)	(34.39)	(10.59)	1/2-14	1.880 (47.75)	50
LT-591	1/2"	(14.48)	1.489 (37.82)	(36.78)	(13.97)	1/2-14	1.986 (50.44)	50
LT-592	3/4"	(14.78)	1.790 (45.47)	(44.20)	(18.80)	3/4-14	2.212 (56.18)	50
LT-593	1"	(18.44)	2.104 (53.44)	(52.53)	(23.88)	1-11/12	2.508 (63.70)	25



#### Standard Material/Finish

- Body/Gland–Nylon-Grey
- “O” Ring–Nitrile (Black)
- Locknut–Nylon
- Temp. Rating–80°C
- Material Flammability Rating: UL94-V2

#### Listed/Certified by:


- U.L. Listed (File # E23018)
- C.S.A. (File # LR52391)

#### Conforms To:

- Watertight requirements for Type 4

### 45° Connectors – Liquidtight Flex for Nonmetallic Conduit

Cat. No.	Trade Size	A± .015 (0.40) Inch (mm)	B* ±.35 (0.90) Inch (mm)	C ±.015 (0.40) Across Corners Inch (mm)	Min. Throat Dia. D. Inch (mm)	E Thread NPT.	F Inch (mm) Approx.	Std. Ctn.
LT-540	3/8"	(14.48)	2.012 (51.10)	(34.39)	(10.59)	1/2-14	1.534 (38.95)	50
LT-541	1/2"	(14.48)	2.092 (53.14)	(36.78)	(13.97)	1/2-14	1.590 (40.39)	50
LT-542	3/4"	(14.78)	2.452 (62.28)	(44.20)	(18.80)	3/4-14	1.821 (46.25)	50
LT-543	1"	(18.44)	2.684 (68.17)	(52.53)	(23.88)	1-11/12	2.034 (51.66)	25





# Steel City®

## Liquidtight Flexible Nonmetallic Conduit Connectors and Tubing



### Liquidtight Flexible Nonmetallic Conduit (Type B) Outdoor XTRAFLEX® Raceway System

Cat. No. Series	Trade Size	I.D. IN.		O.D. IN.		Std. Ctn.
		Min.	Max.	Min.	Max.	
LTC038GY	3/8"	.484	.504	.690	.710	100
LTC050GY	1/2"	.622	.642	.820	.840	100
LTC075GY	3/4"	.820	.840	1.030	1.050	100
LTC100GY	1"	1.041	1.066	1.290	1.315	100
LTC125GY	1 1/4"	1.380	1.410	1.630	1.660	100
LTC150GY	1 1/2"	1.575	1.600	1.865	1.900	50
LTC200GY	2"	2.020	2.045	2.340	2.375	50

Color: Gray

Length: 100 ft. for LTC038GY thru LTC125GY 50 ft. for LTC150GY and LTC200GY

U.L. Listed: File E95745

U.L. Temperature Rating: 80°C dry, 60°C wet, 70°C oil. res. sunlight resistant, outdoor, direct burial.

CSA Certified: File LR 80349-2

CSA Temperature Rating: 75°C to -18°C

For use with Thomas & Betts LT38P, LT38M, LT500 series and Liquidtight Flexible Metal Conduit Fittings.

Material: PVC Helix reinforcement surrounded with flexible PVC.

Voltage Rating: 600V




E

Steel City®



### Liquidtight Whip Assembly

Cat. No.	Conduit Size	Length	Wire Gauge	Std. Ctn.
LTWHIP 12-6-10	1/2"	6'	#10	6
LTWHIP 12-4-10	1/2"	4'	#10	6
LTWHIP 34-6-8	3/4"	6'	#8	6
LTWHIP 34-4-8	3/4"	4'	#8	6
<b>Whip with metallic fittings – one straight, one 90°</b>				
LTWM 12-6-10	1/2"	6'	#10	6
LTWM 12-4-10	1/2"	4'	#10	6
LTWM 34-6-8	3/4"	6'	#8	6
LTWM 34-4-8	3/4"	4'	#8	6







### Conduit Cutter – For Nonmetallic Flexible Conduit

Cat. No.	Description
XF-CUT	For cutting NM flexible conduit up to 1"
XF-BLADE	Replacement blade for XF-CUT

Thomas & Betts

# Steel City®

## Liquidtight Fittings



### Versa Ground™ Liquidtight Fittings

Cat. No.	Trade Size	A	B	Std. Ctn.
5331GR	3/8	1 1/2"	14-4	100
5332GR	1/2	1 9/16"	14-4	100
5333GR	3/4	1 5/8"	14-4	25
5334GR	1	2 1/16"	14-4	50
5231GR	3/8	1 1/2"	14-4	100
5232GR	1/2	1 9/16"	14-4	100
5233GR	3/4	1 5/8"	14-4	25
5234GR	1	2 1/16"	14-4	50
5231ALGR	3/8	1 1/2"	14-4	100
5232ALGR	1/2	1 9/16"	14-4	100
5233ALGR	3/4	1 5/8"	14-4	50
5234ALGR	1	2 1/16"	14-4	50

### Versa Ground™ Liquidtight Fittings – 90° Type

Cat. No.	Trade Size	A	B	C	Std. Ctn.
5351GR	3/8	1 3/8"	1 1/4"	14-4	50
5352GR	1/2	1 9/16"	1 7/16"	14-4	50
5353GR	3/4	1 3/4"	1 13/16"	14-4	50
5354GR	1	2 3/16"	2 1/16"	14-4	25
5251GR	3/8	1 3/8"	1 1/4"	14-4	50
5252GR	1/2	1 9/16"	1 7/16"	14-4	50
5253GR	3/4	1 3/4"	1 13/16"	14-4	50
5254GR	1	2 3/16"	2 1/16"	14-4	25
5251ALGR	3/8	1 3/8"	1 1/4"	14-4	50
5252ALGR	1/2	1 9/16"	1 7/16"	14-4	50
5253ALGR	3/4	1 3/4"	1 13/16"	14-4	50
5254ALGR	1	2 3/16"	2 1/16"	14-4	25

### Versa Ground™ Liquidtight Fittings

Cat. No.	Trade Size	A	B	C	Std. Ctn.
5341GR	3/8	1 9/16"	14-4	1 1/16"	50
5342GR	1/2	1 7/8"	14-4	1 3/8"	50
5343GR	3/4	2 1/8"	14-4	1 3/16"	50
5344GR	1	2 1/4"	14-4	1 3/4"	25
5241GR	3/8	1 9/16"	14-4	1 1/16"	50
5242GR	1/2	1 7/8"	14-4	1 3/8"	50
5243GR	3/4	2 1/8"	14-4	1 3/16"	50
5244GR	1	2 1/4"	14-4	1 3/4"	25


### Liquidtight to Rigid External Ground Adapter

Cat. No.	Trade Size	A	B	Std. Ctn.
5271GR	3/8	1 5/32"	14-4	50
5272GR	1/2	1 3/8"	14-4	50
5273GR	3/4	1 21/32"	14-4	50
5274GR	1	1 7/8"	14-4	25

**Thomas & Betts**

# Steel City®

## Liquidtight Flexible Metal Conduit Connectors



- 3/8"-1" – Steel.
- 1 1/4"-2" – Malleable Iron/Zinc Plated.


### Straight Connectors

Cat. No.	Conduit Size	Diameter			Std. Ctn.
		A	B	C	
LT-100	3/8"	1 1/16"	1/2"	1 3/16"	100
LT-101	1/2"	1 3/16"	39/64"	1 7/8"	100
LT-102	3/4"	1 7/16"	9/16"	2 1/32"	50
LT-103	1"	1 3/4"	5/8"	2 9/32"	50
LT-104	1 1/4"	2 7/16"	1 1/16"	2 19/32"	25
LT-105	1 1/2"	2 3/4"	25/32"	2 29/32"	10
LT-106	2"	3 17/32"	25/32"	3 7/32"	5

CSA File No. LR-12798  
U.L. File No. E-1275 -3/8"-4"



### Straight Connectors




- 3/8"-1" – Steel.
- 1 1/4"-2" – Malleable Iron/Zinc Plated (with insulated throat).

Cat. No.	Conduit Size	Diameter			Std. Ctn.
		A	B	C	
LT-700	3/8"	1 1/16"	1/2"	1 29/32"	100
LT-701	1/2"	1 3/16"	39/64"	1 3 1/2"	100
LT-702	3/4"	1 7/16"	9/16"	2 1/8"	50
LT-703	1"	1 3/4"	5/8"	2 3/8"	50
LT-704	1 1/4"	2 7/16"	1 1/16"	2 1 1/8"	25
LT-705	1 1/2"	2 3/4"	25/32"	2 7/8"	10
LT-706	2"	3 17/32"	25/32"	3 5/16"	5




### 45° Connectors – Malleable Iron/Zinc Plated




Cat. No.	Conduit Size	Dimensions				Std. Ctn.
		E	F	G	H	
LT-450	3/8"	1 1/16"	1/2"	1 9/16"	3 1/32"	50
LT-451	1/2"	1 3/16"	1/2"	1 5/8"	1"	50
LT-452	3/4"	1 7/16"	9/16"	1 7/8"	1 3/32"	50
LT-453	1"	1 3/4"	5/8"	2 1/8"	1 9/32"	25

CSA File No. LR-12798  
U.L. File No. E-1275

### 45° Connectors – Malleable Iron/Zinc Plated (with insulated throat)



Cat. No.	Conduit Size	Dimensions				Std. Ctn.
		E	F	G	I	
LT-950	3/8"	1 1/16"	1/2"	1 9/16"	1 1/16"	50
LT-951	1/2"	1 3/16"	1/2"	1 5/8"	1 3/32"	50
LT-952	3/4"	1 7/16"	9/16"	1 7/8"	1 3/16"	50
LT-953	1"	1 3/4"	5/8"	2 1/8"	1 3/8"	25



### 90° Connectors – Malleable Iron/Zinc Plated


Cat. No.	Conduit Size	Dimensions				Std. Ctn.
		J	K	L	M	
LT-490	3/8"	1 1/16"	1/2"	1 7/8"	1 3/8"	50
LT-491	1/2"	1 3/16"	1/2"	2"	1 9/32"	50
LT-492	3/4"	1 7/16"	9/16"	2 3/16"	1 21/32"	50
LT-493	1"	1 3/4"	5/8"	2 9/16"	1 7/8"	25

CSA File No. LR-12798

U.L. File No. E-1275


E

Steel City®



### 90° Connectors – Malleable Iron/Zinc Plated (with insulated throat)


Cat. No.	Conduit Size	Dimensions				Std. Ctn.
		J	K	L	N	
LT-990	3/8"	1 1/16"	1/2"	1 7/8"	1 15/32"	50
LT-991	1/2"	1 3/16"	1/2"	2"	1 1/2"	50
LT-992	3/4"	1 7/16"	9/16"	2 3/16"	1 3/4"	50
LT-993	1"	1 3/4"	5/8"	2 9/16"	1 31/32"	25



### Straight Connectors – Die-Cast Zinc

Cat. No.	Conduit Size	Diameter			Std. Ctn.
		A	B	C	
LT-200	3/8"	1.81"	0.50"	1.06"	100
LT-201	1/2"	1.88"	0.61"	1.19"	200
LT-202	3/4"	2.03"	0.56"	1.44"	100
LT-203	1"	2.28"	0.63"	1.75"	50
LT-205	1 1/2"	2.78"	0.78"	2.75"	20
LT-206	2"	3.22"	0.78"	3.53"	20
LT-207	2 1/2"	3.53"	0.84"	4.28"	1
LT-208	3"	3.91"	0.88"	4.72"	1
LT-209	3 1/2"	4.04"	0.91"	5.42"	1
LT-210	4"	4.16"	0.94"	5.91"	1


U.L. File No. E-1275



### Straight Connectors – Die Cast Zinc (with insulated throat)

Cat. No.	Conduit Size	Diameter			Std. Ctn.
		A	B	C	
LT-800	3/8"	1 7/64"	3 3/64"	1 19/32"	100
LT-801	1/2"	1 7/64"	3 3/64"	1 19/32"	100
LT-802	3/4"	2 1/64"	3 3/64"	1 9/8"	100
LT-803	1"	2 37/64"	4 3/64"	1 11/64"	50

CSA File No. LR-12798




### 90° Connectors – Die-Cast Zinc

Cat. No.	Conduit Size	Diameter			Std. Ctn.
		A	B	C	
LT-290	3/8"	1.88"	1.38"	0.50"	100
LT-291	1/2"	2.00"	1.41"	0.50"	100
LT-292	3/4"	2.19"	1.66"	0.56"	100
LT-293	1"	2.56"	1.88"	0.63"	50
LT-294	1 1/4"	3.00"	2.00"	0.69"	40
LT-295	1 1/2"	3.38"	2.56"	0.78"	20
LT-296	2"	4.06"	3.00"	0.78"	10

U.L. File No. E-1275


E

Steel City®



### 90° Connectors – Die-Cast Zinc (with insulated throat)

Cat. No.	Conduit Size	Diameter			Std. Ctn.
		A	B	C	
LT-890	3/8"	1.88"	1.38"	0.50"	100
LT-891	1/2"	2.00"	1.41"	0.50"	100
LT-892	3/4"	2.19"	1.66"	0.56"	100
LT-893	1"	2.56"	1.88"	0.63"	50



### Sealing "O" Rings

Cat. No.	Conduit Size	Std. Ctn.
SR-101	1/2"	500
SR-102	3/4"	500
SR-103	1"	500
SR-104	1 1/4"	250
SR-105	1 1/2"	250
SR-106	2"	250

Material: Neoprene

# Steel City®

## Nonmetallic Sheathed Cable and Flexible Cord Connectors



E


Steel City®



Snap captive locking wedge into connector's cavity.



Press locking wedge into cavity which locks onto cable.



Cat. No. 3201 is ideal for multiple flexible cords and cable.

### All Plastic Connector for NM Cable and Flexible Cord

Cat. No.	Size Range	K.O. Size	Fig.	A	B	C	D	E	F Max. Thk. Enclosure	H	Std. Ctn.
3300	For use with 10-2, 12-2 and 14-2 NM cables; 18-2 and 18-3 SJ and SJO cords and 18-2 SV, SVO, SJT and SJTO cords, single or multiple; cord capacity .125-.300 diameter	1/2"	2	1 1/32	1 5/16	3/8	.880	.795	.080	5/16 x 9/16	500
3201	For use with 10-3, 12-3, 14-3, 10-2, 12-2, 4-2 NM cables; multiple (2) 12-2 and 14-2 NM cables; single and multiple flexible cords in wire range .300 in. to .600 in.	1/2"	1	1 1/32	1	7/16	.880	.795	.080	2 1/2 dia.	500
3202	For use with 8-3 and 6-3 NM cables; (2) 14-3, 14-2, 12-2 and 10-2 NM cables; single and multiple flexible cords in wire range .500 in. to .850 in.	3/4"	1	1 1/2	1 5/16	7/16	1.100	1.005	.090	7/8 dia.	250

Temperature Rating: 105°C  
 CSA File Nos. 584 and 2884  
 U.L. File No. E-23017




Figure 1






Figure 2


- High impact thermoplastic. U.L. 94-V1.
- Features push-in design.
- Captive locking wedge secures cable with single squeeze of standard electrician's pliers.
- Provides excellent insulation, strain-relief and high pull-out value.




NC501-SC



NC501DBL-SC




NC502-SC



SB1216-SC

### Hit Lock Connectors


Cat. No.	Description	Std. Ctn.
NC501-SC	½" Hit Lock Connector	500
NC501DBL-SC	½" Double Hit Lock Connector	500
NC502-SC	¾" Hit Lock Connector	100
SB1216-SC	Twist It Bushing For Metal Studs	50



### NM Clamp Type Connector – Die Cast Zinc

Cat. No.	Conduit Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
NC-201	¾"	0.40"	0.95"	1.87"	250
NC-202	¾"	0.50"	1.10"	1.84"	200
NC-203	1"	0.62"	1.14"	2.00"	100
NC-204	1¼"	0.50"	1.38"	2.28"	100
NC-205	1¾"	0.75"	1.61"	2.49"	50
NC-206	2"	0.90"	2.04"	3.35"	50

CSA File No. LR-12798  
U.L. File No. E-17583




### Clamp Type Connector – Die Cast Zinc

Cat. No.	Conduit Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
NC-301	¾" (½"KO)	0.18"	0.64"	1.16"	1000
NC-302	¾"	0.41"	0.82"	1.87"	500
NC-303	1"	0.34"	0.94"	2.01"	250

CSA File No. LR-12798  
U.L. File No. E-17583





### Connectors Clamp Type, Non-Watertight – Die Cast Zinc


Cat. No.	Conduit Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
NC-041	1¼"	0.27"	0.75"	2.02"	100
NC-051	1½"	0.54"	0.95"	2.50"	50
NC-061	2"	0.75"	1.12"	3.41"	40

U.L. File No. E-15170-1¼"-1½"

U.L. File No. E-17583-2"

E

Steel City®



For use with aluminum smooth extruded metal clad cable. (min. dia. .410) – (max. dia. .500)





### Duplex Clamp Type Connector – Die Cast Zinc

Cat. No.	Conduit Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
XC-210	¾" (½" KO)	0.13"	0.65"	1.56"	250
XC-211-SC	¾"	0.24"	0.63"	1.59"	200
XC-222-SC	¾"	0.24"	0.63"	1.59"	200

Conduit/Cable	FMC	AC	MCC	MCI	NM
MAX. SIZE	¾"	10/2	.565	.565	10/2
MIN. SIZE	¾"	14/2	.425	.425	14/2

CSA File No. LR-12798

U.L. File No. E-17909




### NM Saddle Type Connectors – Die Cast Zinc

Cat. No.	Size	Dimensions (in.)		Std. Ctn.
		A (min.)	A (max.)	
XC-2200-C	¾"	0.12"	0.63"	500

### Tilt In Connector Metallic Steel – Electro-Galvanized


Cat. No.	Conduit Size	A	B	C	D	E	Std. Ctn.
NC-851	¾"-1"	.050	1.250	1.750	.760	8-32 x 1	500
NC-852	1-¼"	.062	1.625	2.125	.760	10-32 x 1	250
NC-853	1-½"	.062	1.970	2.500	.785	10-32 x 12	100







### Straight Connectors




#### Straight Squeeze Type Connectors— Malleable Iron or Stamped Steel / Zinc Plated

Cat. No.	Conduit Size	Unit Qty.	Std. Ctn.
<b>XC-400</b>	3/8" (1/2" K.O.)	50	100
<b>XC-401</b>	1/2"	25	100
<b>XC-402</b>	3/4"	25	100
<b>XC-403</b>	1"	25	100
<b>XC-404</b>	1 1/4"	5	10
<b>XC-405</b>	1 1/2"	10	10
<b>XC-406</b>	2"	10	10
<b>XC-407</b>	2 1/2"	5	5
<b>XC-408</b>	3"	5	5

UL File No. E-17909 1/2"-3/4"

UL File No. E-1275 1"-3"

3/8"-3/4"-STEEL




#### Straight Squeeze Type Connectors— Insulated Malleable Iron or Stamped Steel / Zinc Plated

Cat. No.	Conduit Size	Unit Qty.	Std. Ctn.
<b>XC-901</b>	1/2"	25	100
<b>XC-902</b>	3/4"	25	100
<b>XC-903</b>	1"	25	100
<b>XC-904</b>	1 1/4"	5	10
<b>XC-905</b>	1 1/2"	10	10
<b>XC-906</b>	2"	10	10
<b>XC-907</b>	2 1/2"	5	5
<b>XC-908</b>	3"	5	5

1/2"-3/4"-STEEL

### Clamp Straight Set, 90°, and Duplex Connectors



#### 90° Angle Squeeze Type Connectors—Steel or Malleable Iron / Zinc Plated


Cat. No.	Conduit Size	Unit Qty.	Std. Ctn.
<b>XC-490</b>	3/8" (1/2" K.O.)	50	100
<b>XC-491</b>	1/2"	25	100
<b>XC-492</b>	3/4"	25	50
<b>XC-493</b>	1"	25	25
<b>XC-494</b>	1 1/4"	10	10
<b>XC-495</b>	1 1/2"	10	10
<b>XC-496</b>	2"	5	5
<b>XC-497</b>	2 1/2"	1	1
<b>XC-498</b>	3"	1	1

For die cast armored cable/flexible metallic conduit fittings and combination fittings refer to the Steel City® Die Cast Conduit Fittings section.

UL File No. E-17909 3/8" & 3/4"

UL File No. E-1275 1"-3"

3/8"-3/4"-STEEL



### Straight Squeeze Type Connectors – Die Cast Zinc

Cat. No.	Fig.	Size	Dimensions (in.)			Std. Ctn.
			A (min.)	A (max.)	B	
<b>XC-269</b>	1	3/8" (1/2" KO)	0.45"	0.60"	0.96"	500
<b>XC-270</b>	1	1/2"	0.74"	0.92"	1.43"	250
<b>XC-272</b>	1	3/4"	0.88"	1.10"	1.59"	250
<b>XC-273</b>	2	1"	1.10"	1.35"	1.60"	100
<b>XC-274</b>	2	1 1/4"	1.48"	1.65"	1.91"	100
<b>XC-275</b>	2	1 1/2"	1.68"	2.00"	2.12"	50
<b>XC-276</b>	3	2"	2.12"	2.47"	2.54"	40
<b>XC-277</b>	3	2 1/2"	2.71"	3.08"	2.88"	10
<b>XC-278</b>	3	3"	3.15"	3.60"	3.88"	5
<b>XC-278A</b>	3	3 1/2"	3.20"	4.03"	5.04"	1
<b>XC-2710</b>	3	4"	3.15"	4.25"	5.04"	1

U.L. File No. E-17909 3/8" & 1"

U.L. File No. E-1275 1 1/4"-2"

CSA File No. LR-12798 3/8"-1"



### Straight Squeeze Type Connectors – Insulated Die Cast Zinc

Cat. No.	Fig.	Size	Dimensions (in.)			Std. Ctn.
			A (min.)	A (max.)	B	
<b>XC-870</b>	1	1/2"	0.74"	0.92"	1.43"	250
<b>XC-872</b>	1	3/4"	0.88"	1.10"	1.59"	250
<b>XC-873</b>	2	1"	1.10"	1.35"	1.60"	100
<b>XC-874</b>	2	1 1/4"	1.48"	1.65"	1.91"	50
<b>XC-875</b>	2	1 1/2"	1.68"	2.00"	2.12"	50
<b>XC-876</b>	3	2"	2.12"	2.47"	2.54"	10
<b>XC-877</b>	3	2 1/2"	2.71"	3.08"	2.88"	10
<b>XC-878</b>	3	3"	3.15"	3.60"	3.88"	5
<b>XC-879</b>	3	3 1/2"	3.20"	4.03"	5.04"	1
<b>XC-8710</b>	3	4"	3.15"	4.25"	5.04"	1

U.L. File No. E-17909-1/2"-3/4"

U.L. File No. E-1275-1 1/4"

CSA File No. LR-12798




Figure 1





Figure 2





Figure 3

# Steel City®

## Armored Cable/Flexible Metallic Conduit Fittings



- Simple, one-piece installation with no locknuts.
- Screw designed for exceptional pullout resistance.
- Captive screw ensures that the screw is intact for installation and resists backing out after installation.
- Corrosion-resistant, zinc-chromatic plating.
- Positive grounding.
- Vibration resistant screw design.
- UL listed and CSA certified.

### Steel City® Cable Lok


Cat. No.	Size Range	AC Steel	AC Aluminum Interlocked	MC (I) Steel	MC (I) Aluminum	Flex RW	Std. Ctn.
<b>XC-730</b> ½" K.O.	.450"/.610"	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	¾ Steel & AL	50
		12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4		
<b>XC-731</b> ½" K.O.	.450"/.610"	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	-	50
		12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4		
<b>XC-732</b> ¾" K.O.	.610"/.875"	10/3 10/4 10/5	-	10/4 10/5	-	¾ Steel & AL	25
		8/3 8/4	6/2	8/3 8/4	6/2		
<b>XC-7300</b> ½" K.O.	.450"/.610"	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	14/2 14/3 14/4	-	25
		12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4	12/2 12/3 12/4		

U.L. File No. E-17909  
CSA File No. LR-12798

Simple, fast steps to installing the Steel City® Cable Lok.



**1.**  
*Simply snap into place. No locknuts required!*



**2.**  
*Insert cord and twist set screw. Connector tightens as screw is set.*



E

Steel City®

**Thomas & Betts**




Figure 1




Figure 2




Figure 3




Figure 4




Figure 5

### 90° Clamp Type Connectors – Die Cast Zinc

Cat. No.	Fig.	Conduit Size	Dimensions (in.)			Std. Ctn.
			A (min.)	A (max.)	B	
<b>XC-290</b>	1	3/8" (1/2" KO)	0.40"	0.63"	1.80"	500
<b>XC-291</b>	1	1/2"	0.65"	1.00"	2.08"	250
<b>XC-292</b>	1	3/4"	0.83"	1.25"	2.27"	100
<b>XC-293</b>	2	1"	1.27"	1.50"	2.60"	50
<b>XC-294</b>	2	1 1/4"	1.49"	1.85"	3.10"	30
<b>XC-295</b>	3	1 1/2"	1.51"	2.47"	6.05"	5
<b>XC-296</b>	3	2"	1.51"	2.47"	6.05"	5
<b>XC-297</b>	4	2 1/2"	2.45"	3.50"	7.75"	2
<b>XC-298</b>	5	3"	3.07"	4.02"	8.88"	1
<b>XC-299</b>	4	3 1/2"	3.63"	4.34"	12.75"	1
<b>XC-2910</b>	4	4"	3.68"	5.17"	12.75"	1

U.L. File No. E-17909


CSA File No. LR-18130M57

### Insulated Die Cast Zinc

Cat. No.	Fig.	Conduit Size	Dimensions (in.)			Std. Ctn.
			A (min.)	A (max.)	B	
<b>XC-890</b>	1	3/8"	0.40"	0.63"	1.81"	500
<b>XC-891</b>	1	1/2"	0.65"	0.97"	2.18"	250
<b>XC-892</b>	1	3/4"	0.77"	1.12"	2.38"	100
<b>XC-893</b>	2	1"	1.06"	1.40"	2.87"	50
<b>XC-894</b>	2	1 1/4"	1.34"	1.65"	3.93"	30
<b>XC-895</b>	3	1 1/2"	1.51"	2.47"	6.05"	5
<b>XC-896</b>	3	2"	1.51"	2.47"	6.05"	5
<b>XC-897</b>	4	2 1/2"	2.45"	3.50"	7.75"	2
<b>XC-898</b>	5	3"	3.07"	4.02"	8.88"	1
<b>XC-899</b>	4	3 1/2"	3.63"	4.34"	12.75"	1
<b>XC-8910</b>	4	4"	3.68"	5.17"	12.75"	1

U.L. File No. E-17909

CSA File No. LR-12798



For use with metal clad cable.

### Clamp Type Connector – Die Cast Zinc



Cat. No.	Conduit Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
<b>XC-280</b>	3/8" (1/2" KO)	0.18"	0.64"	1.16"	1000

U.L. File No. E-17909  
CSA File No. LR-18130M57

### Duplex Clamp Type Connector – Die Cast Zinc

Cat. No.	Conduit Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
<b>XC-210</b>	3/8" (1/2" KO)	0.13"	0.65"	1.56"	250

CSA File No. LR-18130M57




- No locknut required.
- No special tools required.
- High impact thermoplastic with steel insert.

### Cable Range

Cat. No.	Continuous Corrugated and Corrugated		Aluminum Smooth Extruded		Std. Ctn.
	min. dia.	max. dia.	min. dia.	max. dia.	
<b>XC-280</b>	–	.510"	.345"	.525"	1000
<b>XC-210</b>	–	–	.410"	.500"	250

### Snap-In Connector for Flexible Metal Conduit – 105°C Rated

Cat. No.	Conduit Size	K.O. Size	Unit Qty.	Std. Ctn.
<b>100-TB</b>	3/8"	1/2"	50	500
<b>100BP</b>	3/8"	1/2"	250	1000




- Packed in polybags.
- Available bulk packed-10,000 per carton.
- Plastic.

### BX Flex Bushings – Anti-Short

Cat. No.	Fits Standard Cable Range	Size	Unit Qty.	Std. Ctn.
<b>IT-100-SC</b>	14/2-14/3-12/2	0	100	100
<b>IT-101</b>	14/4-12/3-6/1-4/1	1	100	35
<b>IT-102</b>	12/4-10/2-10/3-2/1	2	50	50
<b>IT-103</b>	10/4-8/2-8/3-1/1	3	50	50
<b>IT-104</b>	8/4-6/2-6/3-4/2-4/3-6/4	4	50	50

For die cast armored cable/flexible metallic conduit fittings and combination fittings refer to the Steel City® Die Cast Conduit Fittings section.

Ordered by Bags



### Straight Set Screw Connectors – Die Cast Zinc – Noninsulated


Cat. No.	Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
<b>XC-220</b>	3/8" (1/2" KO)	0.38"	0.63"	0.84"	1000
<b>XC-221</b>	1/2"	0.74"	0.94"	1.46"	250
<b>XC-821</b>	1/2"	0.74"	0.94"	1.46"	250

XC-220 and XC-221: U.L. File No. E-17909 3/8"  
U.L. File No. E-1275 1/2"

XC-821: U.L. File No. E-1275 1/2"

E

Steel City®




### BX Flex Connectors, Saddle Type – Die Cast Zinc

Cat. No.	Size	Dimensions (in.)			Std. Ctn.
		A (min.)	A (max.)	B	
<b>XC-2200-C</b>	3/8"	0.12"	0.63"	0.98"	500




### Screw-In Connectors – Die Cast Zinc – Noninsulated



Cat. No.	Size	Dimensions (in.)		Std. Ctn.
		A	B	
<b>XC-240</b>	3/8" (1/2" KO)	1.31"	0.92"	500
<b>XC-241</b>	1/2"	1.38"	0.92"	500
<b>XC-242</b>	3/4"	1.62"	1.12"	125
<b>XC-243</b>	1"	1.94"	1.37"	125
<b>XC-244</b>	1 1/4"	2.12"	1.75"	50
<b>XC-245</b>	1 1/2"	2.31"	2.13"	50
<b>XC-246</b>	2"	2.58"	2.67"	50


U.L. File No. E-1275  
CSA File No. LR-18130M57 3/8"-1/2"



### Screw-In Connectors – Die Cast Zinc – Insulated

Cat. No.	Size	Dimensions (in.)		Std. Ctn.
		A	B	
<b>XC-840</b>	3/8" (1/2" KO)	1.31"	0.92"	500
<b>XC-841</b>	1/2"	1.38"	0.92"	500
<b>XC-842</b>	3/4"	1.62"	1.12"	125
<b>XC-843</b>	1"	1.94"	1.37"	125
<b>XC-844</b>	1 1/4"	2.12"	1.75"	50
<b>XC-845</b>	1 1/2"	2.31"	2.13"	50
<b>XC-846</b>	2"	2.58"	2.67"	50

U.L. File No. E-1275  
CSA File No. LR-18130M57 3/8"-1/2"




### Screw-In Couplings – Die Cast Zinc

Cat. No.	Size	Dimensions (in.)		Std. Ctn.
		A	B	
<b>XK-241</b>	1/2"	1.81"	0.92"	250
<b>XK-242</b>	3/4"	2.09"	1.12"	250
<b>XK-243</b>	1"	2.41"	1.37"	125
<b>XK-244</b>	1 1/4"	2.75"	1.81"	50
<b>XK-245</b>	1 1/2"	3.05"	2.12"	50
<b>XK-246</b>	2"	3.28"	2.67"	50

U.L. File No. E-1275


# Steel City®

## Cable Straps, Cable Caps




### Service Cable Straps – One Hole

Cat. No.	Fits Cable	Shelf Ctn.	Ship Case	Std. Ctn.
SE100	3#8, 3#6, 3#4	100	1000	1000
SE101	3#3, 3#2	100	1000	1000
SE102	3#1, 3#0, 3#1/0, 3#2/0	25	250	250
SE103	3#3/0, 3#4/0	25	250	250



### Service Cable Straps – Two Hole


Cat. No.	Fits Cable	Shelf Ctn.	Ship Case	Std. Ctn.
SE900	3#8, 3#6, 3#4	100	1000	1000
SE901	3#3, 3#2	100	1000	1000
SE902	3#1, 3#0, 3#1/0, 3#2/0	25	250	250
SE903	3#3/0, 3#4/0	25	250	250



### Service Cable Caps – Oval

Cat. No.	Fits Cable	Dimensions (Inches)			Std. Ctn.
		A	B	C	
50130	To 2/0-3	5.00	3.31	4.75	10
50130A	To 4/0-3	6.75	4.62	6.00	5
<b>With Split Insulator</b>					
SC1000	3#3-2	2.37	2.12	2.25	25
SC2001	3#3/0-4/0	4.93	3.12	3.75	10

Extra Large Body for Additional Wiring Space.




E

Steel City®

# Steel City®

## Service Entrance Fittings




### Aluminum Service Caps – Clamp Type for Rigid/Intermediate or Thinwall

Cat. No.	Conduit Size	No. Hole	Size	Std. Ctn.
SH-101	1/2"	4	1 9/64"	50
SH-102	3/4"	5	2 (3/8") 3 (13/32")	50
SH-103	1"	5	2 (7/16") 3 (1/2")	10
SH-104	1 1/4"	5	2 (2 7/64") 3 (5/8")	10
SH-105	1 1/2"	6	2 (1 9/32") 1 (7/16") 3 (9/4")	5
SH-106	2"	6	2 (3/4") 3 (1") 1 (1 1/32")	5
SH-107	2 1/2"	7	3 (7/8") 1 (1") 3 (1 5/16")	1
SH-108	3"	7	4 (1 1/8") 3 (1 3/4")	1
SH-109	3 1/2"	4	4 (1 3/4") 2 (1/8")	1
SH-110	4"	4	4 (1 3/4") 2 (1 1/8")	1

CSA File No. LR-12798  
U.L. File No. E-22753


E

Steel City®



### Service Entrance Fittings

Cat. No.	Trade Size	A	B	Std. Ctn.
ASLB-1	1/2"	3 1/16	1 9/16	50
ASLB-2	3/4"	3 9/16	1 3/4	50
ASLB-3	1"	4 1/4	2 3/16	25
ASLB-4	1 1/4"	5 1/2	3	10
ASLB-5	1 1/2"	6 1/4	3 1/4	10
ASLB-6	2"	6 3/4	4	5
DASLB-1	1/2"	3 1/16	1 9/16	24
DASLB-2	3/4"	3 9/16	1 3/4	20
DASLB-3	1"	4 1/4	2 3/16	8



TYPE LB

### Service Entrance Fittings – Standard 1/2" - 2"

Cat. No.	Trade Size	A	B	Std. Ctn.
ASLB-1	1/2"	3 1/16	1 9/16	50
ASLB-2	3/4"	3 9/16	1 3/4	50
ASLB-3	1"	4 1/4	2 3/16	25
ASLB-4	1 1/4"	5 1/2	3	10
ASLB-5	1 1/2"	6 1/4	3 1/4	10
ASLB-6	2"	6 3/4	4	5

### Service Entrance Fittings – Standard 1/2" - 4"

Cat. No.	Trade Size	A	B	Std. Ctn.
SALB-7	2 1/2"	3 1/16	1 9/16	50
SALB-8	3"	3 9/16	1 3/4	50
SALB-9	3 1/2"	4 1/4	2 3/16	25
SALB-10	4"	5 1/2	3	10

**Thomas & Betts**





Two-screw ground connection for armored ground wire.

### Ground Clamps – Die Cast Zinc Alloy for Armored Ground Wire

Cat. No.	Conduit Conduit Size	Std. Ctn.
GA-203	½", ¾", 1"	250


U.L. File No. E-10661

### Ground Clamps – Die Cast Zinc, Brass Colored

Cat. No.	Conduit Conduit Size	Std. Ctn.
GC-203-B	½", 1"	200

E

Steel City®



• For Type SE, Style U, Flat; 2 Insulating Conductors, 1 Bare.

### Water-Tight Connectors

Cat. No.	Trade Size	Fits Cable	Rubber Grommet Opening		Std. Ctn.
			A	B	
WT-203A	1"	3#8	.500	.750	100
WT-203B	1"	3#6	.563	.844	100
WT-203C	1"	3#4	.625	.938	100
WT-204A	1¼"	3#3	.625	1.000	50
WT-204B	1¼"	3#2	.580	.960	50
WT-204C	1¼"	3#1	.660	1.090	50
WT-204D	1¼"	3#1/0	.750	1.125	50
WT-205A	1½"	3#1/0 & 3#2/0	.735	1.240	20
WT-205B	1½"	3#2/0 & 3#3/0	.875	1.375	20
WT-205C	1½"	3#2/0 & 3#3/0	.938	1.438	20
WT-206A	2"	3#1/0 & 3#2/0	.735	1.240	20
WT-206B	2"	3#2/0 & 3#3/0	.875	1.375	20
WT-206C	2"	3#2/0 & 3#3/0	.938	1.438	20
WT-206D	2"	3#4/0	.890	1.550	20
WT-206E	2"	3#4/0	1.063	1.688	20




#### For Underground Feeder Cable

UF-201	½"	2#14	.210	.440	250
UF-202	¾"	3#14	.220	.660	250



# Steel City®

## Gutter Connectors/Cable Protector and Cable Clip

Steel City®



3 Pieces  
Steel/Zinc Plated



### Gutter Connectors

Replaces conventional method of nipple, locknuts and bushings to interconnect panel boxes and other type enclosures to troughs or gutters. Gutter connectors provide automatic uniform 1" spacing with no threads showing.

Conventional installation requires that a nipple be used with double locknuts at

both ends or with a bushing and locknut at each end. Also, when using two or more nipples, time is consumed adjusting the nipples for straight alignment of the enclosure. Gutter connectors eliminate these time consuming methods. The three piece connector requires the tightening of only one locknut.



### Gutter Connectors Straight

Cat. No.	Conduit Size	A Dia.	Std. Ctn.
UC-101	1/2"	1 1/8"	250
UC-102	3/4"	1 7/16"	250
UC-103	1"	1 3/4"	150
UC-104	1 1/4"	2 1/8"	90
UC-105	1 1/2"	2 1/2"	50
UC-106	2"	2 5/16"	30


U.L. File No. E-1275

### Cable Protector

Cat. No.	Description	Std. Ctn.
CP-1	Steel	100

### Cable Clip


Cat. No.	Description	Std. Ctn.
NS-100	Steel	1000



**Thomas & Betts**


# Steel City®

## Beam Clamps for Mounting Pipe or Conduit




RCS Series

- For mounting pipe or conduit at right angles to the beam.
- SS316 Suffix Stainless Steel.
- HDG Suffix – Hot Dip Galvanized.



EC Series

- For mounting pipe or conduit vertically across the beam.
- HDG Suffix – Hot Dip Galvanized.



PC Series

- For mounting pipe or conduit parallel to the beam.
- HDG Suffix – Hot Dip Galvanized.

### Conduit/Pipe to Beam Clamps


Cat. No. & Size	Dimensions in Inches		Std. Ctn.
	O.D. of Conduit or Pipe	Nom. Conduit or Pipe Size	
<b>RCS Clamp – Steel</b>			
RCS-1/2	.840	½	50
RCS-3/4	1.050	¾	50
RCS-1	1.315	1	50
RCS-1-1/4	1.660	1¼	50
RCS-1-1/2	1.900	1½	50
RCS-2	2.375	2	50
<b>RC Clamp – Malleable Iron</b>			
RC-3/8	.675	⅜	50
RC-1/2	.840	½	50
RC-3/4	1.050	¾	50
RC-1	1.315	1	50
RC-1-1/4	1.660	1¼	50
RC-1-1/2	1.900	1½	50
RC-2-SC	2.375	2	50
RC-2-1/2	2.875	2½	25
RC-3	3.500	3	25
RC-3-1/2	4.000	3½	25
RC-4-SC	4.500	4	20
<b>EC Clamp – Malleable Iron</b>			
EC-1/2	.840	½	50
EC-3/4	1.050	¾	50
EC-1	1.315	1	25
EC-1-1/4	1.660	1¼	25
EC-1-1/2	1.900	1½	25
EC-2	2.375	2	25
EC-2-1/2	2.875	2½	10
<b>PC Clamp – Malleable Iron</b>			
PC-3/8	.675	⅜	50
PC-1/2	.840	½	50
PC-3/4	1.050	¾	50
PC-1	1.315	1	50
PC-1-1/4	1.660	1¼	25
PC-1-1/2	1.900	1½	25
PC-2	2.375	2	25
PC-2-1/2	2.875	2½	25
PC-3	3.500	3	10
PC-3-1/2	4.000	3½	10
PC-4	4.500	4	10

E

Steel City®

# Steel City®

## Conduit and Pipe Hangers



Without Bolt

All Steel City 6H Hanger Bolts include a combination Slot-Phillips Head.

*For hanging conduit (rigid or EMT) and pipe. The 6H series hangers are fast, easy and economical to use. May be fastened directly to a #500 beam clamp through a hole in the base of the hanger by means of a 1/4-20 stove bolt or suspended on 1/4" hanger rod.*

### 6H Series Conduit and Pipe Hangers – Without Bolt

Cat. No.	Size (in.)		Dimensions (in.)				Load Rating	Std. Ctn.
	Rigid Conduit or Pipe	EMT	A	B	C	D (dia.)		
6H0	3/8 - 1/2	1/2	3/4	.045	1 21/32	9/32	500	100
6H0-T	3/8 - 1/2	1/2	3/4	.045	1 27/32	9/32	500	100
6H1	3/4	3/4	7/8	.045	1 31/32	9/32	500	100
6H1-T	3/4	3/4	7/8	.045	2 9/32	9/32	500	100
6H2	1	1	7/8	.045	2 9/32	9/32	500	100
6H2-1/2	–	1 1/4	7/8	.045	2 23/32	9/32	500	100
6H3-SC	1 1/4	1 1/2	7/8	.045	2 7/8	9/32	500	100
6H4	1 1/2	–	1	.071	3 3/8	1 1/32	500	100
6H5	2	2	1 1/4	.071	3 29/32	1 1/32	500	50
6H6	2 1/2	–	1 1/4	.071	4 9/32	1 1/32	500	50
6H7	3	–	1 1/4	.071	5 3/16	1 1/32	500	25
6H8	3 1/2	–	1 1/4	.071	5 7/16	1 1/32	500	25
6H9	4	4	1 1/4	.071	5 7/8	1 1/32	500	10

\* Add SS suffix to part number for stainless steel.

Load rating is 500 lbs. with a safety factor of 3. Available with or without closure bolt. Standard finishes: electrogalvanized and Type 302 Stainless Steel.




### 6H Series Conduit and Pipe Hangers – With Bolt


Cat. No.	Size (in.)		Dimensions (in.)				Load Rating	Std. Ctn.
	Rigid Conduit or Pipe	EMT	A	B	C	D (dia.)		
6H0-B	3/8 - 1/2	1/2	3/4	.045	1 21/32	9/32	500	100
6H0-TB	3/8 - 1/2	1/2	3/4	.045	1 27/32	9/32	500	100
6H1-B	3/4	3/4	7/8	.045	1 31/32	9/32	500	100
6H1-TB	3/4	3/4	7/8	.045	2 9/32	9/32	500	100
6H2-B	1	1	7/8	.045	2 9/32	9/32	500	100
6H2-1/2-B	–	1 1/4	7/8	.045	2 23/32	9/32	500	100
6H3-SC-B	1 1/4	1 1/2	7/8	.045	2 7/8	9/32	500	100
6H4-B	1 1/2	–	1	.071	3 3/8	1 1/32	500	100
6H5-B	2	2	1 1/4	.071	3 29/32	1 1/32	500	50
6H6-B	2 1/2	–	1 1/4	.071	4 9/32	1 1/32	500	50
6H7-B	3	–	1 1/4	.071	5 3/16	1 1/32	500	25
6H8-B	3 1/2	–	1 1/4	.071	5 7/16	1 1/32	500	25
6H9-B	4	4	1 1/4	.071	5 7/8	1 1/32	500	10

\* Add SS suffix to part number for stainless steel. (not UL listed.)

Load rating is 500 lbs. with a safety factor of 3. Available with or without closure bolt. Standard finishes: electrogalvanized and Type 302 Stainless Steel.



5/16-18 x 1 3/8" HEX HEAD, CUP POINT, HARDENED STEEL, CAP SCREW NOTE!



### Beam Clamp


Cat. No.	Size	Tapped	Std. Ctn.
BC1-TB	1	1/4-20	250
BC2-TB	2 15/16	3/8-16	–

Material: Steel  
Finish: Zinc Plated

**Thomas & Betts**

# Steel City®

## Beam Clamps/Threaded Rod/Rod Coupling



### Beam Clamps – Malleable Iron, Electroplated Finish

Cat. No.	Base Size Inches		Jaw Opening Inches	Tapping of Base and Back Holes	Load Rating†	Std. Ctn.
	A	B				
510	27/32	1 1/8	5/8	1/4-20	400	100
511-SC	27/32	1 1/8	5/8	10-24	400	100
500-SC	1	1 1/4	15/16	1/4-20	450	50
509	1	1 1/4	15/16	10-24	375	100
501	1 1/2	1 5/8	7/8	3/8-18	800	50
502	2	2	1	3/8-16	1300	50
503-SC	2 5/8	2 1/2	1	1/2-13	1300	20
507	2 1/2	2 3/8	1 3/8	1/2-13	1700	20
508	2 1/2	2 3/8	2 1/8	1/2-13	1700	10

†Safety Factor of 3.

Load Ratings based on bottom hole of Beam Clamp.


CSA File No. LR-52208



### R-Series Continuous Thread Rod – Galvanized

Cat. No.	Rod Size	Ultimate‡ Load in Lbs.	Root Area Thread	Data for Pressure Piping		Std. Ctn.
				Nominal Pipe Size	Max. Safe Load at 450°	
R628-6 ft.	1/4-20	900	.027			300
R638-6 ft.	3/8-16	1900	.068	3/4" to 2"	610	150
R648-6 ft.	1/2-13	3500	.126	2 1/2" to 3 1/2"	1130	60
R1028-10 ft.	1/4-20	900	.027			500
R1038-10 ft.	3/8-16	1900	.068	3/4" to 2"	610	250
R1048-10 ft.	1/2-13	3500	.126	2 1/2" to 3 1/2"	1130	100

‡Load Ratings based on safety factor of three.



### H-195 Steel Rod Coupling

Cat. No.	Rod Size	Dimensions in Inches		Std. Ctn.
		A	B	
H-195-1/4	1/4	3/4	3/8	1000
H-195-3/8	3/8	1	1/2	500
H-195-1/2	1/2	1	5/8	500
H-195-5/8	5/8	1 1/2	3/4	50

Steel City®

# *Steel City®... Building on a century of trust!*



You've told us what your customers say ... how they work ... and what they need for a better, faster, easier job. And we've used your feedback to make Steel City® the most versatile and trusted brand in the industry!

And now the line is bigger and stronger than ever. Steel City® boxes now include exclusive new features to help simplify and speed up installations. We've upgraded the extensive line of



#### **SH2346 Box-to-Stud Bracket**

Unique side brace allows one part number to attach boxes to 2 1/2," 3 1/2," 4," or 6" metal or wood studs. (Competition needs three.)

Steel City Fittings for added convenience and reliability. And we've added a new line of over 600 Steel City Spring Steel Fasteners that meet all the current UL test requirements.

Thomas & Betts and you – together we're building on a century of trust. For technical information about any product in the Steel City line, call **1-888-862-3289**.



#### **CK Series Conduit to Drop Wire Fasteners**

Larger finger tab, better leverage, makes it easier to secure MC/AC cables and conduit to drop wire, plain and threaded rods, and flanges.

Steel City® • Red•Dot® • Superstrut® • Union® • Bowers®

**Thomas & Betts**