



# PQ & P12Q SERIES

Steel Housing 6V up to 200W & 12V up to 200W Capacities Lead-Calcium battery

#### **FEATURES**

### **Housing**

- 20 gauge steel housing with removable front access panel
- Corrosion-resistant baked enamel mist white finish standard, black optional
- Provision for mounting up to 3 lighting heads
- Various choices of lighting head styles and lamp types

### Mounting

- Wall Mount
- 1/2" conduit knock-outs, rear keyhole slots and universal knock-outs to mount to any standard 4" junction box

#### **Electronics**

- Automatic, temperature compensated, pulse-type charger
- High capacity, automatic, dust-tight instantaneous transfer relay
- Low voltage disconnect prevents over discharge of battery
- Automatic brownout protection is provided
- Battery lock-out prevents battery discharge during installation
- Fused output circuit

### **Improved Diagnostics option**

 Units equipped with Improved Diagnostics shall self-test, by simulating a power failure, in accordance with NFPA101, Life Safety Code one minute monthly, 30 minutes every six months and 90 minutes annually. For complete information refer to page 8.

## **NEXUS®** option

• Units equipped with NEXUS® self-testing monitoring system circuitry shall self-test, in accordance with NFPA101 Life Safety Code for a minimum of 30 seconds monthly, 30 minutes every six months and 90 minutes annually as well as keep a history of all testing logs, plus feature real-time diagnostics, and provide the exact fixture location while notifying service personnel of the status of the fixture via email. For complete information refer to page 4-5.

#### **Controls**

- Red charger monitor LED indicates charging of the battery
- Amber AC-ON LED indicates AC power is on
- · Momentary test switch allows for quick operational check of entire system

#### **Choice of Sealed Maintenance-Free Battery**

6V or 12V Lead-Calcium battery

### **Approvals**

UL 924 Standard

**Warranty** (subject to proper installation and maintenance)

- Unit has a three year full warranty (excluding lamps and fuses)<sup>1</sup>
- Lead-Calcium battery has a three year full, plus three year pro-rata warranty

## **ACCESSORIES** (Order as a separate item)

Wire Guard	WG3-L
Mounting Platform (B cabinet)	MP-PQA
Mounting Platform (C cabinet)	MP-PQB

### **SPECIFICATIONS**

Supply and install Lightalarms® PQ, P12Q Series.

The emergency lighting unit shall be a self-contained fixture including a sealed maintenance-free Lead-Calcium battery of 6V or 12V of wattage as specified on the unit rating chart. The unit shall supply the rated wattage load for a minimum of 90 minutes to 87-1/2% of rated battery voltage. The unit shall be rated 120/277VAC, 60Hz and be UL 924 listed.

The unit charger shall utilize an integrated circuit which samples the battery in relation to temperature, state of charge and input voltage fluctuations. The charger shall be current limited, temperature compensated, short-circuit protected and reverse polarity protected. The unit shall be furnished with an electronic lockout circuit which will connect the battery when the AC circuit is activated, and an electronic brownout circuit which will activate the unit when utility power dips below 80-85% of nominal voltage. A low voltage battery protection circuit shall be provided and will disconnect the load and circuitry from the battery when it reaches 87-1/2% of its nominal voltage. The unit shall be capable of full recharge in compliance with UL 924 specifications. The unit shall be furnished with sealed dust-tight relay, a test switch and dual diagnostic LED indicator lights (hi-charge and AC pilot). The cabinet shall be 20 gauge steel with a removable front panel. Unit shall have 1/2" conduit knock-outs, rear keyhole slots and universal knock-outs to mount to any standard 4" junction box with provision for mounting up to 3 heads on top of cabinet.

Units specified with Improved Diagnostics (audible or non-audible) will continuously monitor every critical function of the unit, attached remote lighting heads and/or attached AC/DC Exit Signs. Operational status of the battery, charger and lamps are indicated by individual LED status indicators. Once a malfunction is detected, if audible, a high-pitch audible alarm will sound, and the appropriate LED status indicator will illuminate alerting of the unit malfunction. If non-audible, only the LED status indicator will illuminate alerting of the unit malfunction. The microcontroller shall automatically self-test, by simulating a power failure, in accordance with NFPA101 Life Safety Code for one minute monthly, 30 minutes every six months and 90 minutes annually

Every **PQ**, **P12Q** Series unit shall be fully warranted for three years, subject to proper installation and maintenance.

Unit shall be Lightalarms® catalog number\_\_\_\_\_

### **HEAD STYLE WITH LAMP TYPE CHOICES**

LAMP TYPE	HEAD STYLE							
	<b>ELF645</b> (pg.108)	<b>ELF2</b> (pg.105)	<b>ELF3</b> (pg.106)	<b>DR1130</b> (pg.104)	<b>ELF623</b> (pg.107)			
Wedge Based Incandescent	Х	Х			Х			
Bi-Pin Halogen	X	X			X			
PAR36 Sealed Beam Incand.	Х							
PAR36 Sealed Beam Halogen	Х							
MR16 Halogen			Х	Χ				
MR16 LED			Χ	Χ				



<sup>&</sup>lt;sup>1</sup> For LED lamps warranty, refer to page 168 paragraph 3.2


ELF645







Performance along with the extra battery capacity to power up to two 50W mounted heads or numerous matching remote heads



## **DIMENSIONS**

CATALOG # \_\_\_\_\_

TYPE \_

NOTES \_\_\_

Dimensions are approximate and subject to change.



ELF2/ELF3







/ELF3



100W unit use B Cabinet dimensions 200W unit use C Cabinet dimensions

CABINET	DIMENSIONS				
	а	b	С	d	
В	16-3/8" (41.59cm)// 14-3/4"	16-1/8" (40.95cm)	5-7/16" (13.81cm)	10-1/4" (26.03cm)	
C	18-3/8" (46.67cm)// 16 3/4" (42.54cm)	16-1/2" (41.91cm)	7-1/4" (18.41cm)	12-1/4" (32.38cm)	

## **POWER CONSUMPTION / UNIT RATING CHART**

SERIES	DC SPECS					AC SPECS		
	BATTERY TYPE	DC VOLTAGE	87.5% BATTERY CAPACITY (IN WATTS) <sup>1</sup>			/ATTS)1	UNITS DUAL VOLTAGE <sup>2</sup>	CURRENT MAXIMUM
	DATTERT THE	DO VOLINGE	90 MIN.	2 HRS.	3 HRS.	4 HRS.	ONTO DOAL TOLIAGE	CONTIENT MAXIMOM
PQ2	Lead-Calcium	6V	100	75	50	36	120VAC 277VAC	.3A .15A
PQ3		6V	200	150	100	72		
P12Q1		12V	100	75	50	36		
P12Q2		12V	200	150	100	72		

<sup>1</sup> National Electrical Code Specification <sup>2</sup> All units 120/277 dual voltage, information based on wiring to specific voltage type

## ORDERING FORMAT

# OF HEADS	SERIES/CAPACITY	HEAD STYLE	LAMP TYPE	COLOR	OPTIONS
0= No heads 1= One head 2= Two heads 3= Three heads	PQ2= 6V-100W PQ3= 6V-200W P12Q1= 12V-100W P12Q2= 12V-200W	/Blank= ELF645 (PAR36, Plastic) /ELF2= ELF2 (PAR18, Plastic) /ELF3= ELF3 (MR16, Plastic)	Add lamp suffix to indicate lamp type, voltage and wattage.  For available Lamp Types within a specified Head Style, refer to that Head Style page for proper lamp suffix with Blank (ELF645), page 108 with ELF2, page 105 with ELF3, page 106 with DR1130, page 104 with ELF623, page 107  Lamp Type MUST:  1) Match Battery Voltage 2) Total of all lamps wattage must not exceed battery watt capacity for 90 min.	-M= Mist White -B= Black	Blank= No Options  -ID= Improved Diagnostics (audible)¹  -IDNA= Improved Diagnostics (non audible)¹  -NEX= Nexus® Wireds Compatible²  -NEXF= Nexus® Wireds Compatible²  -T1= Time Delay (5 minute)  -T2= Time Delay (10 minute)  -T3= Time Delay (15 minute)  -A= Ammeter³  -V= Voltmeter³  -DS= Lamp Disconnect Switch  -VS= Vandal-Resistant Screws  -3CP= 120V Cord & Plug, 3 wire, 3ft long⁴  ¹-ID & -IDNA include a time delay feature that can be enabled/ disabled in the field or set by the factory by including -ID-TD* or -IDNA-TD*. Not available with P1202 series ² Consult your sales representative ³-A & -V not available with -ID, -IDNA, -NEX, -NEXRF option ⁴-3CP & -3CP277 custom lengths available. Consult your sales representative

EXAMPLE: 2P12Q1/DR1130M50-M

