



GREENCREATIVE

LUMINAIRES



2017 LUMINAIRES CATALOG



GREENCREATIVE

GREEN CREATIVE, founded in 2010, is a solid state lighting development and manufacturing company based in Silicon Valley, CA. The company offers a comprehensive line of high-performance LED lighting solutions which has been widely adopted by some of the largest companies in the world.



2016 Top 10
MUST SEE Products



2017
PRODUCT
SPRINT
2017 WINNER



A complete line with national & international distribution

GREEN CREATIVE's full product line of ENERGY STAR, DLC, NSF & JA8 certified indoor retrofit and new construction lighting solutions serves the Retail, Hospitality, Food & Beverage, Office, Education & Industrial sectors through multiple distribution centers and sales networks across the USA.




Bringing you the latest in LED technology

Anchored by strong integrated R&D capabilities and patented technology, GREEN CREATIVE innovation, performance and reliability have been recognized year after year by the Illuminating Engineering Society Progress Report, the LEDs Magazine Sapphire Awards, Edison Report, NAILD and more.



2017 LUMINAIRES TABLE OF CONTENTS



2017 LUMINAIRES FEATURED PRODUCTS



NEW!



P1-2

CLICK DESIGN SMPS & SMPR

SootheOptic technology
9", 7" & 5.5" form factors
Wet location & high CRI

NEW!



P5-6

NEW CONSTRUCTION DL THINFIT SERIES

New construction installation
Integrated J-box
Edge-lighting technology

NEW!



P11-12

STRIP QWIKLINK SERIES

QWIKLINK connection system
Connect up to 64' of fixtures
QWIKLINK sensor available

NEW!



P13-14

PANEL ELEVATE SERIES

SootheOptic technology UGR<19
Edge lighting technology
Slim body design

NEW!



P15-18

TROFFER & KIT ELEVATE SERIES

Exceptional efficacy >140 LPW
High quality architectural finish
Integrated sensor available

NEW!



P21-22





HIGH BAY HYPERBAY SERIES

Compact 2x2' form factor
3 lumen package options
3 beam distribution options

SURFACE MOUNT CEILING LINE





SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv. LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet			
 SMPS 9" 20W	NEW! 20SMPS9DIM/930	58242	3000K	1200	100W	60	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	20SMPS9DIM/940	58243	4000K	1250	100W	63	100°	N.A.	90	Yes	50,000	120V	Yes	✓
 SMPS 7" 15W	NEW! 15SMPS7DIM/927	58244	2700K	850	75W	57	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	15SMPS7DIM/930	58245	3000K	850	75W	57	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	15SMPS7DIM/940	58246	4000K	870	75W	58	100°	N.A.	90	Yes	50,000	120V	Yes	✓
 SMPS 5.5" 10W	NEW! 10SMPS5.5DIM/927	58247	2700K	550	50W	55	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	10SMPS5.5DIM/930	58248	3000K	550	50W	55	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	10SMPS5.5DIM/940	58249	4000K	560	50W	56	100°	N.A.	90	Yes	50,000	120V	Yes	✓

SURFACE MOUNT CEILING LINE

SootheOptic low glare technology reduces visual glare and creates a comfortable lighting environment




- ⌚ SootheOptic low glare technology
- ⌚ Innovative CLICK design
- ⌚ Wet location & high CRI
- ⌚ Compatible with 4" J-boxes (standard)

SPECIFICATIONS






Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet		
	NEW! 20SMPR9DIM/930	58255	3000K	1200	100W	60	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	20SMPR9DIM/940	58256	4000K	1250	100W	63	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	NEW! 15SMPR7DIM/927	58257	2700K	850	75W	57	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	15SMPR7DIM/930	58258	3000K	850	75W	57	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	15SMPR7DIM/940	58259	4000K	870	75W	58	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	NEW! 10SMPR5.5DIM/927	58260	2700K	550	50W	55	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	10SMPR5.5DIM/930	58261	3000K	550	50W	55	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	10SMPR5.5DIM/940	58262	4000K	560	50W	56	100°	N.A.	90	Yes	50,000	120V	Yes	✓
	SMP/ACC	58033	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

* SMP/ACC - 4" & 6" recessed can accessories for 5.5" & 7" round & square (5.5" for use in 4" can only, 7" for use in 4" or 6" can)

SURFACE MOUNT LINE



SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet		
 SMDL 6" 14.5W	14.5SMDL6DIM/927	40842	2700K	920	85W	63	110°	N.A.	90	Yes	40,000	120V	No	✓
	14.5SMDL6DIM/930	40843	3000K	950	85W	66	110°	N.A.	90	Yes	40,000	120V	No	✓
	14.5SMDL6DIM/840	40847	4000K	1050	100W	72	110°	N.A.	82	Yes	40,000	120V	No	✓
 SMDL 6" 11W	11SMDL6DIM/927	58101	2700K	680	65W	62	110°	N.A.	90	Yes	40,000	120V	Yes	✓
	11SMDL6DIM/930	58102	3000K	720	65W	65	110°	N.A.	90	Yes	40,000	120V	Yes	✓
	11SMDL6DIM/940	58103	4000K	750	65W	68	110°	N.A.	90	Yes	40,000	120V	Yes	✓
 SMDL 6" ACC	SMDL6/ACC	57974	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.
 SMDL 4" ACC	SMDL4/ACC	57973	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

* GU24 connector available

Wet Location & High CRI



SMDL 6" 11W




Seamless Installation



- Innovative CLICK design
- Compatible with 4" J-boxes (standard)
- 4" & 5-6" recessed can accessories sold separately
- Installs in just minutes – No rewiring


CLICK 6" 14.5W & 11W - High CRI



INSTALLATION GUIDE

4" J-BOX

ACCESSORIES INCLUDED:



- Attach mounting bracket to J-box
- Click downlight into mounting bracket



Mounting Bracket



J-Box Screws




Wire Nuts



LED Adapter

4" CAN

ACCESSORIES SOLD SEPARATELY:




- Connect E26 adapter to the LED adapter
- Insert mounting clips and push downlight up until flush with ceiling



E26 Adapter



LED Adapter




Mounting Bracket



Mounting Clips

5-6" CAN

ACCESSORIES SOLD SEPARATELY:



- Connect E26 adapter to the LED adapter
- Squeeze mounting springs and push downlight up until flush with ceiling



E26 Adapter



LED Adapter



Mounting Springs

NEW CONSTRUCTION DOWNLIGHT LINE









SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Wet		
 DLNC 6" 11.6W	NEW! 11.6DLNC6DIM/827	58028	2700K	810	75W	70	100°	N.A.	82	Yes	40,000	120V	No	✓
	11.6DLNC6DIM/830	58029	3000K	830	75W	72	100°	N.A.	82	Yes	40,000	120V	No	✓
	11.6DLNC6DIM/840	58030	4000K	850	75W	73	100°	N.A.	82	Yes	40,000	120V	No	✓
 DLNC 4" 8.5W	NEW! 8.5DLNC4DIM/827	58025	2700K	510	50W	60	100°	N.A.	82	Yes	40,000	120V	No	✓
	8.5DLNC4DIM/830	58026	3000K	530	50W	62	100°	N.A.	82	Yes	40,000	120V	No	✓
	8.5DLNC4DIM/840	58027	4000K	550	50W	65	100°	N.A.	82	Yes	40,000	120V	No	✓
 6" GOOF RING	DLNC6GOOF/R	97848	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.
 4" GOOF RING	DLNC4GOOF/R	97847	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.


NEW CONSTRUCTION DOWNLIGHT LINE

Integrated J-box with LED quick connectors for quick & easy installation



-  For new construction or remodel installation
-  Innovative design saves time & materials
-  Easy to use spring action clips
-  Goof Ring available





INSTALLATION GUIDE



ARCHITECTURAL DOWNLIGHT LINE




SPECIFICATIONS




	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Encl.	
 CDL 9.5\" data-bbox="60 718 115 740"/> 48W	48CDL9.5G4DIM/830/277V	97706	3000K	3200	2 X 42W	67	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	48CDL9.5G4DIM/835/277V	97707	3500K	3400	2 X 42W	71	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	48CDL9.5G4DIM/840/277V	97708	4000K	3600	2 X 42W	75	90°	N.A.	80	Yes	40,000	120-277V	No	✓
 CDL 8\" data-bbox="60 798 115 820"/> 32W	32CDL8G4DIM/830/277V	97696	3000K	2150	2 X 26W	67	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	32CDL8G4DIM/835/277V	97697	3500K	2300	2 X 26W	72	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	32CDL8G4DIM/840/277V	97698	4000K	2450	2 X 26W	77	90°	N.A.	80	Yes	40,000	120-277V	No	✓
 CDL 6\" data-bbox="60 873 115 895"/> 22W	22CDL6G4DIM/830/277V	97686	3000K	1600	2 X 18W	73	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	22CDL6G4DIM/835/277V	97687	3500K	1650	2 X 18W	75	90°	N.A.	80	Yes	40,000	120-277V	No	✓
	22CDL6G4DIM/840/277V	97688	4000K	1700	2 X 18W	77	90°	N.A.	80	Yes	40,000	120-277V	No	✓








To order this option add /EM after the model number
ex. 22CDL6G4DIM/840/277V/EM

Accessories include a carabiner safety clip that can be used during installation for easy wiring. Two types of retaining clips are also included to secure the fixture if recessed frame does not already have pre-installed clips.




Dimensions		
Model	A	B
 48CDL9.5G4DIM/xxx/277V	9.25" (235mm)	6.50" (165mm)
 32CDL8G4DIM/xxx/277V	7.80" (197mm)	5.90" (150mm)
 22CDL6G4DIM/xxx/277V	6.02" (153mm)	5.39" (137mm)



-  Fits existing architectural & commercial housing
-  0-10V dimming – Compatible with 120-277V circuits
-  Easy installation – Quick connector and pre-wired conduit
-  Superior savings and performance over CFL

INSTALLATION GUIDE









COMMERCIAL DOWNLIGHT LINE



2016 Top 10
MUST SEE Products




SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CRI (typ.)	Dim	Life (hrs)	Voltage	
 CDL 9.5" 23.5/32/45W	45CDLA9.5/827/277V	57878	2700K	1860/2325/2975	23.5W - 1x42W/2x26W 32W - 1x57W/2x32W 45W - 2x42W	79/73/76	110°	80	No	40,000	120-277V	✓
	45CDLA9.5/830/277V	57879	3000K	2000/2500/3200		85/78/71	110°	80	No	40,000	120-277V	✓
	45CDLA9.5/835/277V	57880	3500K	2000/2500/3200		85/78/71	110°	80	No	40,000	120-277V	✓
	45CDLA9.5/840/277V	57881	4000K	2000/2500/3200		85/78/71	110°	80	No	40,000	120-277V	✓
 CDL 8" 12/19/27W	27CDLA8/827/277V	57873	2700K	930/1400/1860	12W - 1x26W/2x13W 19W - 1x32W/2x18W 27W - 1x42W/2x26W	78/74/69	110°	80	No	40,000	120-277V	✓
	27CDLA8/830/277V	57874	3000K	1000/1500/2000		83/79/74	110°	80	No	40,000	120-277V	✓
	27CDLA8/835/277V	57875	3500K	1000/1500/2000		83/79/74	110°	80	No	40,000	120-277V	✓
	27CDLA8/840/277V	57876	4000K	1000/1500/2000		83/79/74	110°	80	No	40,000	120-277V	✓
 CDL 6" 8.5/13/21W	21CDLA6/827/277V	57868	2700K	650/930/1400	8.5W - 1x18W 13.5W - 1x26W/2x13W 21W - 1x32W/2x18W	76/69/67	110°	80	No	40,000	120-277V	✓
	21CDLA6/830/277V	57869	3000K	700/1000/1500		82/74/71	110°	80	No	40,000	120-277V	✓
	21CDLA6/835/277V	57870	3500K	700/1000/1500		82/74/71	110°	80	No	40,000	120-277V	✓
	21CDLA6/840/277V	57871	4000K	700/1000/1500		82/74/71	110°	80	No	40,000	120-277V	✓
 CDL 4" 6/9/14W	14CDLA4/827/277V	57863	2700K	465/650/930	6W - 1x13W 9W - 1x18W 14W - 1x26W/2x13W	78/72/66	110°	80	No	40,000	120-277V	✓
	14CDLA4/830/277V	57864	3000K	500/700/1000		83/78/71	110°	80	No	40,000	120-277V	✓
	14CDLA4/835/277V	57865	3500K	500/700/1000		83/78/71	110°	80	No	40,000	120-277V	✓
	14CDLA4/840/277V	57866	4000K	500/700/1000		83/78/71	110°	80	No	40,000	120-277V	✓
 EMERGENCY INVERTER 35W	35EMINVERTER	58012	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.	N.A.

* IC-Rated - 4" & 6" versions


COMMERCIAL DOWNLIGHT LINE


The adjustable housing clips allow for installation in a large range of commercial and architectural housings. These spring-action clips push up easily and fit securely for both retrofit and new construction installations.








Dimensions		
Model	Aperture Min.	Aperture Max.
9.5"	8.6" (220mm)	10.4" (265mm)
8"	7.6" (195mm)	9.4" (240mm)
6"	6.0" (153mm)	7.4" (190mm)
4"	3.9" (100mm)	5.1" (130mm)

Adjustable Lumen Output









-  **For retrofit or new construction installation**
-  **Universal housing compatibility**
-  **Adjustable lumen output – 3 defined light levels**
-  **Easy fit installation – Spring-action housing clips**

SIMPLE RETROFIT OR ECONOMICAL NEW CONSTRUCTION INSTALLATION


Retrofit Installation




Attach safety clip




Bypass ballast & wire to j-box



Adjust lumens to desired output




Push clips up & install into fixture




Ensure fixture is flush. Installation is complete


New Construction Installation




Attach safety clip




Wire to j-box



Adjust lumens to desired output



Push clips up & install into opening







Ensure fixture is flush. Installation is complete

STRIP LINE






QWIKLINK Sensor





SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	DLC
 STRIP 4' 38.5W		NEW!										
	38.5STRIPDIM/830/277V	28321	3000K	4950	129	120°	N.A.	82	Yes	100,000	120-277V	✓
	38.5STRIPDIM/835/277V	28322	3500K	4950	129	120°	N.A.	82	Yes	100,000	120-277V	✓
	38.5STRIPDIM/840/277V	28323	4000K	5050	131	120°	N.A.	82	Yes	100,000	120-277V	✓
	38.5STRIPDIM/850/277V	28324	5000K	5050	131	120°	N.A.	82	Yes	100,000	120-277V	✓
 STRIP 4' 22.5W		NEW!										
	22.5STRIPDIM/830/277V	28317	3000K	2500	111	120°	N.A.	82	Yes	100,000	120-277V	✓
	22.5STRIPDIM/835/277V	28318	3500K	2500	111	120°	N.A.	82	Yes	100,000	120-277V	✓
	22.5STRIPDIM/840/277V	28319	4000K	2600	115	120°	N.A.	82	Yes	100,000	120-277V	✓
	22.5STRIPDIM/850/277V	28320	5000K	2600	115	120°	N.A.	82	Yes	100,000	120-277V	✓
 STEP DIMMING MODULE 100/50	To order this option add /STEPDIM after the model number ex. 38.5STRIPDIM/840/277V/STEPDIM						To order this and emergency add both: ex. 38.5STRIPDIM/840/277V/STEPDIM/EM					
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 38.5STRIPDIM/840/277V/EM						To order this and step dimming add both: ex. 38.5STRIPDIM/840/277V/STEPDIM/EM					

* STRIP 4" 38.5W meets DLC Premium requirements, STRIP 4" 22.5W meets DLC Standard Requirements

The QWIKLINK connection system uses the latest in toolless technology to easily and seamlessly connect up to 64' of fixtures.



-  Surface mount, pendant or suspended installation
-  LED quick connectors for fast & easy wiring
-  120-277V & 0-10V dimming control compatible
-  100,000-hr lifetime, 10-yr warranty





ACCESSORIES

Model	Product	Description
STPSENSOR	28388	Microwave Sensor QWIKLINK Connection Module 120-277V - Bi-level - Field Adjustable
SENSORRC	97881	Remote Control for STPSENSOR
JBOXPLATE	28384	J-box Cover Plate
STPBACKPLATE	97906	47.80"x5.31" (1214x135mm) Plate for Covering Form Factor of Old Fixture
WIRECON20	28385	7.9" (20cm) QWIKLINK Cable
WIRECON150	28386	5' QWIKLINK Cable
STP6CABLE	28382	6' Aircraft Cable with Y-toggle (Set of 2 Cables Suitable for 1 Fixture)
STP10CABLE	28383	10' Aircraft Cable with Y-toggle (Set of 2 Cables Suitable for 1 Fixture)
STPPLATE4C	28387	Back Plate for Mechanical Connection Between Suspended Fixtures in a Continuous Run (2 Aircraft Cables Per Fixture)
STPPLATE2C	97885	Back Plate for Mechanical Connection Between Suspended Fixtures in a Continuous Run (1 Aircraft Cable Per Fixture)
PC6	97860	6' Power Cord 18/3 (Not Pre-wired to Fixture)
PC12	97861	12' Power Cord 18/3 (Not Pre-wired to Fixture)


PANEL LINE




SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
 PANEL 2X4' 38W		NEW!										
	38PAN24DIM/830/277V	28349	3000K	4150	109	95°	N.A.	82	Yes	75,000	120-277V	✓
	38PAN24DIM/835/277V	28350	3500K	4150	109	95°	N.A.	82	Yes	75,000	120-277V	✓
	38PAN24DIM/840/277V	28351	4000K	4300	113	95°	N.A.	82	Yes	75,000	120-277V	✓
	38PAN24DIM/850/277V	28352	5000K	4300	113	95°	N.A.	82	Yes	75,000	120-277V	✓
 PANEL 2X2' 30W		NEW!										
	30PAN22DIM/830/277V	28345	3000K	3350	112	95°	N.A.	82	Yes	75,000	120-277V	✓
	30PAN22DIM/835/277V	28346	3500K	3350	112	95°	N.A.	82	Yes	75,000	120-277V	✓
	30PAN22DIM/840/277V	28347	4000K	3450	115	95°	N.A.	82	Yes	75,000	120-277V	✓
	30PAN22DIM/850/277V	28348	5000K	3450	115	95°	N.A.	82	Yes	75,000	120-277V	✓
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 38PAN24DIM/840/277V/EM											

SootheOptic low glare technology reduces visual glare and creates a comfortable lighting environment



- Recessed, surface mount or suspended installation**
- Integrated J-box for fast & easy wiring**
- 120-277V & 0-10V dimming control compatible**
- 75,000-hr lifetime, 10-yr warranty**



Unified Glare Rating (UGR) <19

Technology	UGR	Characteristics
SootheOptic LOW GLARE	GREEN CREATIVE Panel UGR <19	<ul style="list-style-type: none"> • Comfortable light at all viewing angles • More useful light • No perceptible discomfort
Standard LED Panel	UGR >23	<ul style="list-style-type: none"> • Harsh glare at viewing angles >65° • More wasted light • Perceptible discomfort








ACCESSORIES

Model	Product	Description
MOUNTFRAME24	28391	2X4' Surface Mount Frame
MOUNTFRAME22	28390	2X2' Surface Mount Frame
SUSPCABLE24	28393	70.9" (1.8m) Aircraft Suspension Cable (Set of 6 Cables for 1 2X4' Fixture)
SUSPCABLE22	28392	70.9" (1.8m) Aircraft Suspension Cable (Set of 4 Cables for 1 2X2' Fixture)



TROFFER HE LINE








SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
 TROFFER HE 2X4' 30W	NEW! 30TROF24DIM/830/277V	28333	3000K	4200	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	30TROF24DIM/835/277V	28334	3500K	4200	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	30TROF24DIM/840/277V	28335	4000K	4300	143	120°	N.A.	82	Yes	50,000	120-277V	✓
 TROFFER HE 2X2' 25W	NEW! 25TROF22DIM/830/277V	28329	3000K	3500	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	25TROF22DIM/835/277V	28330	3500K	3500	140	120°	N.A.	82	Yes	50,000	120-277V	✓
	25TROF22DIM/840/277V	28331	4000K	3600	143	120°	N.A.	82	Yes	50,000	120-277V	✓
 TROFFER HE 1X4' 26W	NEW! 26TROF14DIM/835/277V	97939	3500K	3250	125	120°	N.A.	82	Yes	50,000	120-277V	✓
	26TROF14DIM/840/277V	97940	4000K	3300	127	120°	N.A.	82	Yes	50,000	120-277V	✓
 STEP DIMMING MODULE 100/50	To order this option add /STEPDIM after the model number ex. 30TROF24DIM/835/277V/STEPDIM		To order this and emergency add both: ex. 30TROF24DIM/835/277V/STEPDIM/EM									
 SENSOR	To order this option add /OCCDIM after the model number ex. 30TROF24DIM/835/277V/OCCDIM		To order this and emergency add both: ex. 30TROF24DIM/835/277V/OCCDIM/EM									
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 30TROF24DIM/835/277V/EM		To order this and step dimming or sensor add both: ex. 30TROF24DIM/835/277V/STEPDIM/EM									





Easy Installation for New Construction or Retrofit



-  **High performance lighting distribution**
-  **Exceptional efficacy >140 LPW**
-  **120-277V & 0-10V dimming control compatible**
-  **100,000-hr lifetime, 10-yr warranty**









INSTALLATION GUIDE



TROFFER RETROFIT KIT HE LINE





SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
 RETROFIT KIT HE 2X4' 30W	30TROFKIT24DIM/830/277V NEW!	28341	3000K	4200	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	30TROFKIT24DIM/835/277V	28342	3500K	4200	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	30TROFKIT24DIM/840/277V	28343	4000K	4300	144	120°	N.A.	82	Yes	100,000	120-277V	✓
 RETROFIT KIT HE 2X2' 25W	25TROFKIT22DIM/830/277V NEW!	28337	3000K	3500	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	25TROFKIT22DIM/835/277V	28338	3500K	3500	140	120°	N.A.	82	Yes	100,000	120-277V	✓
	25TROFKIT22DIM/840/277V	28339	4000K	3600	144	120°	N.A.	82	Yes	100,000	120-277V	✓
 STEP DIMMING MODULE 100/50	To order this option add /STEPDIM after the model number ex. 30TROFKIT24DIM/835/277V/STEPDIM		To order this and emergency add both: ex. 30TROFKIT24DIM/835/277V/STEPDIM/EM									
 SENSOR	To order this option add /OCCDIM after the model number ex. 30TROFKIT24DIM/835/277V/OCCDIM		To order this and emergency add both: ex. 30TROFKIT24DIM/835/277V/OCCDIM/EM									
 EMERGENCY DRIVER 10W	To order this option add /EM after the model number ex. 30TROFKIT24DIM/835/277V/EM		To order this and step dimming or sensor add both: ex. 30TROFKIT24DIM/835/277V/STEPDIM/EM									


* Remote control available for SENSOR

TROFFER RETROFIT KIT HE LINE

Universally compatible to upgrade 2x2' and 2x4' troffers and louvers while continuing to utilize the existing luminaire housing.



High-Performance Light Distribution







GREEN CREATIVE Retrofit Kit

Other Retrofit Kit





Housing	Retrofit Kit Dimensions	Retrofit Kit Dimensions (w/o brackets)
2x4'	47.83"x23.94"x2.76"(1215x608x70mm)	46.77"x20.59"x2.76"(1188x523x70mm)
2x2'	23.90"x23.94"x2.76"(607x608x70mm)	22.51"x20.59"x2.76"(572x523x70mm)

Elevate Your Lighting





-  **High performance lighting distribution**
-  **Exceptional efficacy >140 LPW**
-  **120-277V & 0-10V dimming control compatible**
-  **100,000-hr lifetime, 10-yr warranty**

INSTALLATION GUIDE

1. 
2. 
3. 
4. 

Power

Ground

Dimming
5. 
6. 

TRACK LINE



TRACK 33W L
TRACK 22W M





SPECIFICATIONS


	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
	33TRLG4DIM/927/W/H	97623	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/W/H	97629	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	33TRLG4DIM/927/W/J	97624	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/W/J	97630	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	33TRLG4DIM/927/B/H ●	97626	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/B/H ●	97632	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	33TRLG4DIM/927/B/J ●	97627	2700K	2200	39W HID	65	25°/38°	10,000/5150	90	Yes	40,000	120V	✓
	33TRLG4DIM/930/B/J ●	97633	3000K	2300	39W HID	68	25°/38°	10,350/5250	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/W/H	97587	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/W/H	97599	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/W/J	97588	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/W/J	97600	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/B/H ●	97590	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/B/H ●	97602	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓
	22TRMG4DIM/927/B/J ●	97591	2700K	1200	20W HID	55	25°/38°/15°	6300/3250/12,200	90	Yes	40,000	120V	✓
	22TRMG4DIM/930/B/J ●	97603	3000K	1250	20W HID	57	25°/38°/15°	6700/3450/13,000	90	Yes	40,000	120V	✓

* The J and L type adaptors are compatible with single or two-circuit track types. The H type adaptor is only compatible with single-circuit track types
● Black finish


Interchangeable Lens Options (TRACK L & M)



H - Halo Track





J - Juno Track
For use with single and two-circuit track applications




L - Lightolier Track (MTO)
For use with single and two-circuit track applications

Dimensions



- Exceptional color rendering CRI 90
- Tight LED binning – 4-step Macadam ellipse
- Sleek design, integrated driver
- NF & FL optics ship with TRL & TRM versions

TRACK L & M - High CRI



SPECIFICATIONS

Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Angle	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	
8TRSG4DIM/827NF30/W/H	16340	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/W/H	16346	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓
8TRSG4DIM/827NF30/W/J	16341	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/W/J	16347	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓
8TRSG4DIM/827NF30/B/H ●	16343	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/B/H ●	16349	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓
8TRSG4DIM/827NF30/B/J ●	16344	2700K	600	75W Hal	68	30°	1905	80	Yes	40,000	120V	✓
8TRSG4DIM/830NF30/B/J ●	16350	3000K	625	75W Hal	71	30°	1950	80	Yes	40,000	120V	✓

* The J and L type adaptors are compatible with single or two-circuit track types. The H type adaptor is only compatible with single-circuit track types
● Black finish

HIGH BAY LINE



185W Medium Optic (ME) comes standard



130W Medium Optic (ME) comes standard






95W Prismatic Optic (GP) comes standard





SPECIFICATIONS

	Model	Product	CCT	Lumens (lm)	Equiv.	LPW	Beam Dist.	CBCP (cd)	CRI (typ.)	Dim	Life (hrs)	Voltage	Max Temp.	
 HIGH BAY 185W	185HBAY/840/GP <small>NEW!</small>	58227	4000K	22,700	400W HID 324W FLUO.	123	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/840/ME	58228	4000K	25,000		135	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/840/AL	58230	4000K	25,000		135	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/850/GP	58232	5000K	22,700		123	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/850/ME	58233	5000K	25,000		135	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	185HBAY/850/AL	58235	5000K	25,000		135	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
 HIGH BAY 130W	130HBAY/840/GP <small>NEW!</small>	58212	4000K	17,200	250W HID 216W FLUO.	132	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/840/ME	58213	4000K	18,900		145	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/840/AL	58215	4000K	18,900		145	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/850/GP	58217	5000K	17,200		132	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/850/ME	58218	5000K	18,900		145	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	130HBAY/850/AL	58220	5000K	18,900		145	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
 HIGH BAY 95W	95HBAY/840/GP <small>NEW!</small>	58197	4000K	11,800	175W HID 162W FLUO.	125	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/840/ME	58198	4000K	13,100		138	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/840/AL	58200	4000K	13,100		138	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/850/GP	58202	5000K	11,900		125	100°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/850/ME	58203	5000K	13,200		139	80°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
	95HBAY/850/AL	58205	5000K	13,200		139	45°/90°	N.A.	82	Yes	100,000	120-277V	131°F/55°C	✓
 347/480V TRANSFORMER	To order this option add /347V after the model number ex. 130HBAY/840/ME/347V													
 SENSOR	Up to 20' Mounting Heights - /OCCDIM20 To order this option add either /OCCDIM20 or /OCCDIM40 after the model number Up to 40' Mounting Heights - /OCCDIM40 ex. 130HBAY/840/ME/347V/OCCDIM40													
 EMERGENCY DRIVER 20W	To order this option add /EM after the model number ex. 130HBAY/840/ME/347V/OCCDIM40/EM													
 SURGE PROTECTOR 10KV	To order this option add /SP after the model number ex. 130HBAY/840/ME/347V/OCCDIM40/EM/SP													

* HIGH BAY 185W GP & 95W GP meet DLC Standard requirements. All other models meet DLC Premium requirements.

Customizable optics, installation and accessories optimize fixture performance to meet all low and high bay application needs



-  **Suspended or pendant mount installation**
-  **2x2' compact form factor with flicker-free driver**
-  **120-277V & 0-10V dimming control compatible**
-  **100,000-hr lifetime, 10-yr warranty**

ACCESSORIES

Model	Product	Description
HBAYOCCDIMRC	97859	Remote Control for OCCDIM20 & OCCDIM40
HBAYWG4XMOD	58282	130W & 185W High Bay Wire Guard
HBAYWG2XMOD	58281	95W High Bay Wire Guard
HBAYPENDHANG	58283	Rod/Stem Pendant Mount (Rod/Stem Not Included)
HBAY10CABLE	97862	10' Aircraft Cable & Cable Gripper (For Use with V-hooks)
HBAY20CABLE	97863	20' Aircraft Cable & Cable Gripper (For Use with V-hooks)



GREEN CREATIVE

1200 Bayhill Drive, Suite 220
San Bruno, CA 94066
Tel / Fax: (866) 774-5433
info@greencreative.com

www.greencreative.com



/ GREENCREATIVELED



/ GClightingLED



/ GREEN CREATIVE



GREENCREATIVE