

Traditional Lighting

FLUORESCENT

HID

HALOGEN

INCANDESCENT

SPECIALTY

EiIKC 



watch > like > follow >



selection.solutions.simplicity.eiko.com

Contents

Fluorescent 4

A-Shaped Decorative CFLi Lamps	4
B10 Decorative CFLi Lamps	4
B13 Decorative CFLi Lamps	4
G25 Decorative CFLi Lamps	5
High Watt CFLi Lamps	5
PAR CFLi Lamps	5
R-Shaped CFLi Lamps	5
Dimmable Spiral CFLi Lamps	6
GU24 Based Spiral CFLi Lamps	6
Medium Based Spiral CFLi Lamps	6
Mogul Based Spiral CFLi Lamps	7
4-Pin Based Spiral CFL Lamps	7
Duo-Tube CFL Lamps	8
Triple-Tube CFL Lamps	9
Quad-Tube CFL Lamps	9
FML CFL Lamps	10
Programmed Start T5 Linear Fluorescent Lamps	11
Preheat T5 Linear Fluorescent Lamps	12
Blacklight T5 Linear Fluorescent Lamps	12
T8 Linear Fluorescent Lamps	12
CEE Specified T8 Linear Fluorescent Lamps	12
Energy Saving T8 Linear Fluorescent Lamps	13
Long Life T8 Linear Fluorescent Lamps	13
High Lumen T8 Linear Fluorescent Lamps	13
Preheat T8 Linear Fluorescent Lamps	14
Blacklight T8 Linear Fluorescent Lamps	14
Safety Coated T8 Linear Fluorescent Lamps	14
T12 Linear Fluorescent Lamps	14
Circular Fluorescent Lamps	14
T8 U-Bend Fluorescent Lamps	15
PowerMaster™ Ballasts	15
Fluorescent Starters	15

HID 16

ColorMaster PRO™ Ceramic Metal Halide PAR Lamps	16
ColorMaster PRO™ Ceramic Metal Halide MR16 Lamps	17
ColorMaster PRO™ Ceramic Metal Halide EDX17 Lamps	17
ColorMaster PRO™ Ceramic Metal Halide Bi-Pin Lamps	17
ColorMaster PRO™ Ceramic Metal Halide Double Ended Lamps	17
Medium & Mogul Based Metal Halide Lamps	18
Open Fixture Rated Metal Halide Lamps	18
Single Ended Metal Halide Lamps	19
Double Ended Metal Halide Lamps	19
Pulse Start Metal Halide Lamps	19
High Pressure Sodium Lamps	20
Non-Cycling High Pressure Sodium Lamps	21
Mercury Vapor Lamps	21

Halogen..... 22

EiKON™ Energy Efficient Halogen IR PAR30	22
EiKON™ Energy Efficient Halogen IR PAR30LN	22
EiKON™ Energy Efficient Halogen IR PAR38	22
EiKON™ Energy Efficient Halogen Silver PAR20	23
EiKON™ Energy Efficient Halogen Silver PAR30	23
EiKON™ Energy Efficient Halogen Silver PAR30LN	23
EiKON™ Energy Efficient Halogen Silver PAR38	23
EiKON™ Energy Efficient Halogen A-Line	23
Classic BT15 Halogen Lamps	24
MR8 Halogen Lamps	24
MR8 Supreme Halogen Lamps	24
MR11 Halogen Lamps	24
MR16 Halogen Lamps	24
MR16 Screw Base Halogen Lamps	25
MR16 Line Voltage Halogen Lamps	26
37mm Diameter Aluminized Reflector Lamps	26
56mm Diameter Aluminized Reflector Lamps	26
Single Ended Halogen Lamps	26
Double Ended Halogen Lamps	27
Double Ended Short Halogen Lamps	27
G4 Base 2-Pin Halogen Lamps	28
G6.35 Base 2-Pin Halogen Lamps	28
Bi-Pin Line Voltage Halogen Lamps	28
Halogen Heat Lamps	29
SoLux® MR16 3500K Halogen Lamps	29
SoLux® MR16 4100K Halogen Lamps	29
SoLux® MR16 4700K Halogen Lamps	29

Incandescent 30

A-Shaped Incandescent Lamps	30
Rough Service Incandescent Lamps	30
C-Shaped Incandescent Lamps	31
R&BR Incandescent Lamps	31
S-Shaped Incandescent Lamps	31
T-Shaped Incandescent Lamps	32








Specialty 33

ArcMaster™ SSTV Discharge Lamps	33
ColorMaster™ Digital Imaging Lamps	33
HPL Lamps	33
Enlarger Lamps	34
Modeling Lamps	34
PhotoFlood Lamps	35
Healthcare, Medical & Scientific Lamps	35
Germicidal Lamps	37
ANSI Coded Lamps	37

Miniature 42

LED Miniature Lamps	42
Miniature Lamps	43

General Lighting > Common Base Types

 <p>2G11 4-Pin, Twin Tube</p>	 <p>BA15d DC Bayonet</p>	 <p>BA15s SC Bayonet</p>	 <p>BAY15d DC Index Bayonet</p>	 <p>E10 Miniature Screw</p>	 <p>E11 Mini Candelabra Screw</p>	 <p>E12 Candelabra Screw</p>
 <p>E17 Intermediate Screw</p>	 <p>E26 Medium Screw</p>	 <p>E39/E40 Mogul Screw</p>	 <p>EX39 Mogul Screw w/ Long Prong</p>	 <p>G4 Sub-Mini 2-Pin</p>	 <p>G5 Bi-Pin Cap</p>	 <p>G6.35 Bi-Pin Base</p>
 <p>G9.5 Bi-Pin Cap</p>	 <p>G12 12mm Bi-Pin</p>	 <p>G13 1/2" Bi-Pin</p>	 <p>G23 Bi-Pin Cap</p>	 <p>G24d-1 2-Pin</p>	 <p>G24d-2 2-Pin</p>	 <p>G24d-3 2-Pin</p>
 <p>G24q-1 4-Pin</p>	 <p>G24q-2 4-Pin</p>	 <p>G24q-3 4-Pin</p>	 <p>GU4 Bi-Pin</p>	 <p>GU5.3 Bi-Pin</p>	 <p>GU10 Bi-Pin</p>	 <p>GU24 Bi-Pin</p>
 <p>GX5.3 Bi-Pin</p>	 <p>GX23 Bi-Pin Cap</p>	 <p>GX23-2 Bi-Pin</p>	 <p>GX24q-2 4-Pin</p>	 <p>GX24q-3 4-Pin</p>	 <p>GX24q-4 4-Pin</p>	 <p>GY5.3 Bi-Pin</p>
 <p>GY9.5 Bi-Pin</p>	 <p>GZ4 Bi-Pin</p>	 <p>GZ6.35 Bi-Pin</p>	 <p>RGLP Rigid Loop</p>	 <p>Rx7s Recessed Single Contact</p>	 <p>SV8.5mm Festoon</p>	 <p>T5 Miniature Bi-Pin</p>
 <p>T8 Medium Bi-Pin</p>	 <p>T9 Circular</p>	 <p>T12 Medium Bi-Pin</p>	 <p>T5.5 Slide Base #5</p>	 <p>W2x4.6d Sub-Miniature Wedge</p>	 <p>W2.1x9.5d Miniature Wedge</p>	 <p>Wedge Glass Wedge T5</p>

Cross Referencing

for General Lighting & Automotive/Miniature

Cross referencing a lamp can be done in two ways:


- By matching the known part number of your lamp to a part number of another manufacturer known to have the same specifications.
- By matching the specifications of your lamp to the specifications of a known part number.

Step 1: What is the lamp family and sub-family? (For General Lighting lamps)

Use the chart opposite to determine to which family and sub-family your lamp belongs.

Step 2: What is the bulb shape?

“Bulb” refers to the glass portion of the lamp. Refer to the diagram to the right for common bulb shapes.



Step 3: What is the base type?

The base supports the lamp in the socket and conducts electricity to the filament. Refer to the charts on pages 6-7 for common General Lighting and Automotive Miniature base types.

Step 4: What is the voltage and wattage?

This information can usually be found stamped on the base of the bulb. If only given amps, remember this conversion: Amps x Volts = Watts.

Step 4: What is the color temperature? (For General Lighting lamps)

Color temperature is usually represented in one of three ways:

- Descriptive
“Warm White” (WW), “Cool White” (CW), “Daylight” (D), etc.
- Degrees Kelvin (by hundreds)
27, 41, 65, etc. (27=2700° Kelvin)
- Color Rendering Index (CRI) + Degrees Kelvin
735, 841, etc. (735 = a CRI of approx. 75% and a color temp of 3500° Kelvin)

Step 5: What is the beam spread (light pattern)? (For PAR and MR Type lamps)

Narrow Spot (NSP) = 10°	Spot (SP) = 17°
Narrow Flood (NFL) = 24°	Medium Flood (MFL) = 26°
Flood (FL) = 36°	Wide Flood (WFL) = 55°



Compact Fluorescent Lamps

Eiko's selection of compact fluorescent (CFL) and self-ballasted compact fluorescent (CFLi) lamps features long life, high quality tri-phosphor blends, and many options with environmentally-friendly ratings such as TCLP, CEE, and ENERGY STAR. Our selection includes duo tube, triple tube, quad tube, FML, spiral, PAR, R and decorative shapes in various wattages and color temperatures.

A-Shaped Decorative CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #	ENERGY STAR®
06445	SP9A19/27K	9	120	E26	470	>80	2700	4.213/107	1.6	10,000	1	
06446	SP9A19/41K	9	120	E26	470	>80	4100	4.213/107	1.6	10,000	1	
06447	SP13A19/27K	13	120	E26	800	>80	2700	4.84/123	3	10,000	1	★
07710	SP15A/27K-GU24*	13	120	GU24	800	>80	2700	4.45/113	1.6	10,000	1	★
06448	SP13A19/41K*	14	120	E26	750	>80	4100	4.88/123	3	10,000	1	

Lamps contain mercury - please dispose of properly.

B10 Decorative CFLi Lamps


Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #	ENERGY STAR®
06435	SP5B10/E12/27K	5	120	E12	220	>80	2700	4.331/110	1.6	10,000	2	
06442	SP7B10/E12/27K	7	120	E12	320	>80	2700	4.685/119	1.6	10,000	2	
06449	SP7B10/E12/41K	7	120	E12	320	>80	4100	4.685/119	1.6	10,000	2	

Lamps contain mercury - please dispose of properly.

B13 Decorative CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #	ENERGY STAR®
06452	SP5B13/E26/27K	5	120	E26	220	>80	2700	4.45/113	1.6	10,000	3	
06453	SP5B13/E26/41K*	5	120	E26	220	>80	4100	4.45/113	1.6	10,000	3	

Lamps contain mercury - please dispose of properly.



G25 Decorative CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
06550	SP9G25/27K	9	120	E26	500	>80	2700	4.33/110	1.6	10,000	4	
07870	SP15G25/27K	15	120	E26	820	>80	2700	4.72/120	1.6	10,000	4	★
07734	SP15G25/27K-GU24*	15	120	GU24	740	>80	2700	4.45/113	1.6	10,000	4	★
07871	SP15G25/41K	15	120	E26	820	>80	4100	4.72/120	1.6	10,000	4	

Lamps contain mercury - please dispose of properly.

High Watt CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
05293	SP65/41/MED	65	120	E26	4300	>80	4100	9.45/240	4.8	10,000	5	
06659	SP65/50/MED	65	120	E26	4000	>80	5000	9.45/240	4.8	10,000	5	
81183	SP85/41/MED	85	120	E26	5700	>80	4100	9.96/253	4.8	10,000	5	
81181	SP85/50/MED	85	120	E26	5350	>80	5000	9.96/253	4.8	10,000	5	
81184	SP105/41/MED	105	120	E26	7000	>80	4100	10.75/273	4.8	10,000	5	
81185	SP105/41/MOG	105	120	E39	7000	>80	4100	11.26/286	4.8	10,000	5	
04412	SP105/41/MOG-277V	105	277	E39	7000	>80	4100	11.26/286	4.8	10,000	5	
81180	SP105/50/MED	105	120	E26	6600	>80	5000	10.75/273	4.8	10,000	5	

Lamps contain mercury - please dispose of properly.

PAR CFLi Lamps


Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
01519	PAR20/9/35K*	9	120	E26	272	>80	3500	3.82/97	1.35	8,000	6	
06282	PAR20/9/41K*	9	120	E26	270	>80	4100	3.82/97	1.35	8,000	6	★
01521	PAR20/9/50K*	9	120	E26	258	>80	5000	3.82/97	1.35	8,000	6	
06279	PAR30LN/15/30K	15	120	E26	750	>80	3000	5.12/130	1.93	8,000	7	
01522	PAR30LN/15/35K	15	120	E26	728	>80	3500	5.12/130	1.93	8,000	7	
06280	PAR30LN/15/41K	15	120	E26	725	>80	4100	5.12/130	1.93	8,000	7	★
01523	PAR30LN/15/50K	15	120	E26	745	>80	5000	5.12/130	1.93	8,000	7	★
01046	PAR38/23/27K	23	120	E26	1250	>80	2700	5.51/140	2.31	8,000	8	
06277	PAR38/23/30	23	120	E26	1200	>80	3000	5.51/140	2.31	8,000	8	★
07856	PAR38/23/35	23	120	E26	1200	>80	3500	5.51/140	2.31	8,000	8	
06278	PAR38/23/41K	23	120	E26	1210	>80	4100	5.51/140	2.31	8,000	8	★
01531	PAR38/23/50K	23	120	E26	1200	>80	5000	5.51/140	2.31	8,000	8	

Lamps contain mercury - please dispose of properly.

R-Shaped CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
06390	SP14/R20/27K	14	120	E26	500	>80	2700	4.88/124	3	10,000	9	★
06391	SP14/R20/41K	14	120	E26	450	>80	4100	4.88/124	3	8,000	9	
49365	SP15/R30/27K	15	120	E26	700	>80	2700	5.4/137	1.6	10,000	10	
07879	SP15/R30/27K-DIM*	15	120	E26	680	>80	2700	6.10/155	1.6	10,000	10	
07733	SP15/R30/27K-GU24*	15	120	GU24	690	>80	2700	4.45/113	1.6	10,000	10	★

Continued on next page >>>



*Closeout item: available while supplies last.

Fluorescent

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
49366	SP15/R30/41K	15	120	E26	700	>80	4100	5.4/137	1.6	10,000	10	
07880	SP15/R30/41K-DIM*	15	120	E26	680	>80	4100	6.102/155	1.6	10,000	10	
07881	SP15/R30/50K-DIM*	15	120	E26	680	>80	5000	6.102/155	1.6	10,000	10	
49367	SP15/R30/65K	15	120	E26	650	>80	6500	5.4/137	1.6	10,000	10	
07882	SP15/R30/65K-DIM*	15	120	E26	640	>80	6500	6.102/155	1.6	10,000	10	
49371	SP23/R40/27K	23	120	E26	1090	>80	2700	6.5/165	1.6	10,000	11	
07704	SP23/R40/27K-DIM*	23	120	E26	1090	>80	2700	7.01/178	1.6	10,000	11	
49372	SP23/R40/41K	23	120	E26	1090	>80	4100	6.5/165	1.6	10,000	11	
07705	SP23/R40/41K-DIM*	23	120	E26	1090	>80	4100	7.01/178	1.6	10,000	11	
07706	SP23/R40/50K-DIM*	23	120	E26	1050	>80	5000	7.01/178	1.6	10,000	11	

Lamps contain mercury - please dispose of properly.

Dimmable Spiral CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
06392	SP13/27K-DIM	13	120	E26	900	>80	2700	4.92/125	2	8,000	12	
06393	SP13/41K-DIM*	13	120	E26	850	>80	4100	4.92/125	2	8,000	12	
06394	SP19/27K-DIM*	18	120	E26	1350	>80	2700	5.12/130	2	8,000	12	
06395	SP19/41K-DIM*	20	120	E26	1300	>80	4100	5.12/130	2	8,000	12	
06396	SP23/27K-DIM*	23	120	E26	1550	>80	2700	5.47/139	2	8,000	12	

Lamps contain mercury - please dispose of properly.

GU24 Based Spiral CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
05255	SP13/27-GU24	13	120	GU24	800	>80	2700	3.622/92	1.6	10,000	13	★
07749	SP13/41-GU24	13	120	GU24	900	>80	4100	3.74/95	1.6	10,000	13	
05256	SP18/27-GU24	18	120	GU24	1200	>80	2700	4.0/103	1.6	10,000	13	★
07702	SP18/27K-GU24-DIM*	18	120	GU24	1200	>80	2700	4.37/111	1.6	10,000	13	
07750	SP18/41-GU24	18	120	GU24	1100	>80	4100	4.33/110	1.6	10,000	13	
07751	SP23/27-GU24	23	120	GU24	1600	>80	2700	4.409/112	1.6	10,000	13	★
07703	SP23/27K-GU24-DIM*	23	120	GU24	1600	>80	2700	4.84/123	1.6	10,000	13	
07752	SP23/41-GU24	23	120	GU24	1600	>80	4100	4.409/112	1.6	10,000	13	
05258	SP26/27-GU24	27	120	GU24	1900	>80	2700	4.73/123	3	10,000	13	★

Lamps contain mercury - please dispose of properly.

Medium Based Spiral CFLi Lamps

Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/ Hrs	Photo #	ENERGY STAR®
00031	SP13/27K	13	120	E26	900	>80	2700	4.50/114	2	10,000	14	★
00032	SP13/35K	13	120	E26	800	>80	3500	4.10/104	2	8,000	14	
00033	SP13/41K	13	120	E26	900	>80	4100	4.10/104	2	10,000	14	
05667	SP13/50K	13	120	E26	800	>80	5000	4.10/104	2	10,000	14	
06131	SP13/65K	13	120	E26	900	>80	6500	4.10/104	2	10,000	14	
00034	SP19/27K	18	120	E26	1200	>80	2700	4.528/115	1.6	10,000	14	★
00035	SP19/35K	18	120	E26	1200	>80	3500	4.528/115	1.6	10,000	14	

Continued on next page >>>



Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #	ENERGY STAR®
00036	SP19/41K	18	120	E26	1200	>80	4100	4.528/115	1.6	10,000	14	
05668	SP19/50K	18	120	E26	1200	>80	5000	4.528/115	1.6	10,000	14	
49324	SP19/65K*	18	120	E26	1100	>80	6500	4.528/115	1.6	10,000	14	
49325	SP23/27K	23	120	E26	1600	>80	2700	4.882/124	1.6	10,000	14	★
81171	SP23/35K	23	120	E26	1600	>80	3500	4.882/124	1.6	10,000	14	
49326	SP23/41K	23	120	E26	1600	>80	4100	4.882/124	1.6	10,000	14	
81172	SP23/50K	23	120	E26	1600	>80	5000	4.882/124	1.6	10,000	14	
49327	SP23/65K	23	120	E26	1600	>80	6500	4.882/124	1.6	10,000	14	
05412	SP27/27K	26	120	E26	1700	>80	2700	5.079/129	1.6	10,000	14	★
05413	SP27/35K	26	120	E26	1700	>80	3500	5.08/129	1.6	10,000	14	
05414	SP27/41K	26	120	E26	1700	>80	4100	5.079/129	1.6	10,000	14	
05415	SP27/50K	26	120	E26	1700	>80	5000	5.079/129	1.6	10,000	14	
05416	SP32/27K	32	120	E26	2000	>80	2700	5.71/145	3.2	10,000	14	
05417	SP32/35K	32	120	E26	2050	>80	3500	5.63/143	3.2	8,000	14	
05418	SP32/41K	32	120	E26	2050	>80	4100	5.63/143	3.2	8,000	14	
05419	SP32/50K	32	120	E26	2000	>80	5000	5.71/145	3.2	10,000	14	
05420	SP42/27K	40	120	E26	2600	>80	2700	7.283/185	3.2	10,000	14	
05421	SP42/35K	40	120	E26	2600	>80	3500	7.283/185	3.2	10,000	14	
05422	SP42/41K	40	120	E26	2600	>80	4100	7.13/181	3.2	10,000	14	
05423	SP42/50K	40	120	E26	2600	>80	5000	7.283/185	3.2	10,000	14	
05293	SP65/41/MED	65	120	E26	4300	>80	4100	9.45/240	4.8	10,000	14	
06659	SP65/50/MED	65	120	E26	4000	>80	5000	9.45/240	4.8	10,000	14	
81183	SP85/41/MED	85	120	E26	5700	>80	4100	9.96/253	4.8	10,000	14	
81181	SP85/50/MED	85	120	E26	5350	>80	5000	9.96/253	4.8	10,000	14	
81184	SP105/41/MED	105	120	E26	7000	>80	4100	10.75/273	4.8	10,000	14	
81180	SP105/50/MED	105	120	E26	6600	>80	5000	10.75/273	4.8	10,000	14	

Lamps contain mercury - please dispose of properly.

Mogul Based Spiral CFLi Lamps


Order Code	Item	W	V	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #	ENERGY STAR®
81185	SP105/41/MOG	105	120	E39	7000	>80	4100	11.26/286	4.8	10,000	15	
04412	SP105/41/MOG-277V	105	277	E39	7000	>80	4100	11.26/286	4.8	10,000	15	

Lamps contain mercury - please dispose of properly.

4-Pin Based Spiral CFL Lamps

Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
05251	SP13/27-4P	13	G24q-1	900	80	2700	3.74/95	2.5	10,000	16
05250	SP18/27-4P	18	GX24q-2	1100	82	2700	4.41/112	2.5	10,000	16
05252	SP26/27-4P	26	GX24q-3	1800	82	2700	4.72/120	2.5	10,000	16

Lamps contain mercury - please dispose of properly.



Fluorescent

Duo-Tube CFL Lamps

Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
15554	DT5/27	5	G23	250	82	2700	4.2/107	2.2	10,000	17
49205	DT5/41	5	G23	250	82	4100	4.2/107	2.2	10,000	17
49207	DT5/65*	5	G23	250	82	6500	4.2/107	2.2	10,000	17
15556	DT7/27	7	G23	400	82	2700	5.3/135	2.2	10,000	17
49208	DT7/35	7	G23	400	82	3500	5.3/135	2.2	10,000	17
49209	DT7/41	7	G23	400	82	4100	5.3/135	2.2	10,000	17
49210	DT7/50	7	G23	400	82	5000	5.3/135	2.2	10,000	17
49211	DT7/65	7	G23	400	82	6500	5.3/135	2.2	10,000	17
15558	DT9/27	9	G23	600	82	2700	6.6/168	2.2	10,000	17
49212	DT9/35	9	G23	600	82	3500	6.6/168	2.2	10,000	17
49213	DT9/41	9	G23	600	82	4100	6.6/168	2.2	10,000	17
49214	DT9/50	9	G23	600	82	5000	6.6/168	2.2	10,000	17
49215	DT9/65	9	G23	600	82	6500	6.6/168	2.2	10,000	17
15560	DT13/27	13	GX23	825	82	2700	7.3/185	2.2	10,000	17
49216	DT13/30*	13	GX23	825	82	3000	7.3/185	2.2	10,000	17
15575	DT13/35	13	GX23	825	82	3500	7.3/185	2.2	10,000	17
49217	DT13/41	13	GX23	825	82	4100	7.3/185	2.2	10,000	17
49218	DT13/50	13	GX23	825	82	5000	7.3/185	2.2	10,000	17
49219	DT13/65	13	GX23	825	82	6500	7.3/185	2.2	10,000	17
49283	DT18/30/RS	18	2G11	1250	82	3000	9.0/229	2.2	20,000	17
49284	DT18/35/RS	18	2G11	1250	82	3500	9.0/229	2.2	20,000	17
49285	DT18/41/RS	18	2G11	1250	82	4100	9.0/229	2.2	20,000	17
49286	DT18/50/RS	18	2G11	1250	82	5000	9.0/229	2.2	20,000	17
49288	DT24/30/RS	24	2G11	1800	82	3000	12.9/328	2.2	20,000	17
49289	DT24/35/RS	24	2G11	1800	82	3500	12.9/328	2.2	20,000	17
49290	DT24/41/RS	24	2G11	1800	82	4100	12.9/328	2.2	20,000	17
49291	DT24/50/RS	24	2G11	1800	82	5000	12.9/328	2.2	20,000	17
49292	DT24/65/RS	24	2G11	1800	82	6500	12.9/328	2.2	20,000	17
49293	DT36/30/RS	36	2G11	2900	82	3000	16.6/422	2.2	20,000	17
49294	DT36/35/RS	36	2G11	2900	82	3500	16.6/422	2.2	20,000	17
49295	DT36/41/RS	36	2G11	2900	82	4100	16.6/422	2.2	20,000	17
49296	DT36/50/RS	36	2G11	2900	82	5000	16.6/422	2.2	20,000	17
49297	DT36/65/RS	36	2G11	2900	82	6500	16.6/422	2.2	20,000	17
49298	DT40/30/RS	40	2G11	3300	82	3000	22.5/572	2.2	20,000	17
49299	DT40/35/RS	40	2G11	3300	82	3500	22.5/572	2.2	20,000	17
49300	DT40/41/RS	40	2G11	3300	82	4100	22.5/572	2.2	20,000	17
49301	DT40/50/RS	40	2G11	3300	82	5000	22.5/572	2.2	20,000	17
49302	DT40/65/RS	40	2G11	3300	82	6500	22.5/572	2.2	20,000	17
49303	DT50/30/RS*	50	2G11	4300	82	3000	22.5/572	2.2	18,000	17
49304	DT50/35/RS	50	2G11	4300	82	3500	22.5/572	2.2	18,000	17
49305	DT50/41/RS	50	2G11	4300	82	4100	22.5/572	2.2	18,000	17
49306	DT50/50/RS	50	2G11	4300	82	5000	22.5/572	2.2	18,000	17
49308	DT55/30/RS	55	2G11	4800	82	3000	21.5/546	2.2	18,000	17
49309	DT55/35/RS	55	2G11	4800	82	3500	21.5/546	2.2	18,000	17
49310	DT55/41/RS	55	2G11	4800	82	4100	21.5/546	2.2	18,000	17

Continued on next page >>>



Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
49311	DT55/50/RS	55	2G11	4800	82	5000	21.5/546	2.2	18,000	17
49312	DT55/65/RS	55	2G11	4800	82	6500	21.5/546	2.2	18,000	17

Lamps contain mercury - please dispose of properly.

Triple-Tube CFL Lamps


Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
49259	TT18/27	18	GX24q-2	1200	82	2700	4.8/122	2.2	10,000	18
49260	TT18/30	18	GX24q-2	1200	82	3000	4.8/122	2.2	10,000	18
49261	TT18/35	18	GX24q-2	1200	82	3500	4.8/122	2.2	10,000	18
49262	TT18/41	18	GX24q-2	1200	82	4100	4.8/122	2.2	10,000	18
49264	TT18/65	18	GX24q-2	1200	82	6500	4.8/122	2.2	10,000	18
49265	TT26/27	26	GX24q-3	1800	82	2700	5.2/132	2.2	10,000	18
49266	TT26/30	26	GX24q-3	1800	82	3000	5.2/132	2.2	10,000	18
49267	TT26/35	26	GX24q-3	1800	82	3500	5.2/132	2.2	10,000	18
49268	TT26/41	26	GX24q-3	1800	82	4100	5.2/132	2.2	10,000	18
49269	TT26/50	26	GX24q-3	1800	82	5000	5.2/132	2.2	10,000	18
49270	TT26/65	26	GX24q-3	1800	82	6500	5.2/132	2.2	10,000	18
49271	TT32/27	32	GX24q-3	2200	82	2700	5.8/147	2.2	10,000	18
49272	TT32/30	32	GX24q-3	2200	82	3000	5.8/147	2.2	10,000	18
49273	TT32/35	32	GX24q-3	2200	82	3500	5.8/147	2.2	10,000	18
49274	TT32/41	32	GX24q-3	2200	82	4100	5.8/147	2.2	10,000	18
49275	TT32/50	32	GX24q-3	2200	82	5000	5.8/147	2.2	10,000	18
49276	TT32/65	32	GX24q-3	2200	82	6500	5.8/147	2.2	10,000	18
49277	TT42/27	42	GX24q-4	3200	82	2700	6.4/163	2.2	10,000	18
49278	TT42/30	42	GX24q-4	3200	82	3000	6.4/163	2.2	10,000	18
49279	TT42/35	42	GX24q-4	3200	82	3500	6.4/163	2.2	10,000	18
49280	TT42/41	42	GX24q-4	3200	82	4100	6.4/163	2.2	10,000	18
49281	TT42/50	42	GX24q-4	3200	82	5000	6.4/163	2.2	10,000	18
49282	TT42/65	42	GX24q-4	3200	82	6500	6.4/163	2.2	10,000	18

Lamps contain mercury - please dispose of properly.

Quad-Tube CFL Lamps

Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
15562	QT9/27	9	G23-2	550	82	2700	4.3/109	2.2	10,000	19
49558	QT9/41	9	G23-2	550	82	4100	4.3/109	2.2	10,000	19
15564	QT13/27	13	GX23-2	810	82	2700	4.6/117	2.2	10,000	19
49241	QT13/27-4P	13	G24q-1	900	82	2700	5/127	2.2	10,000	19
49242	QT13/30-4P	13	G24q-1	900	82	3000	5/127	2.2	10,000	19
15576	QT13/35	13	GX23-2	810	82	3500	4.6/117	2.2	10,000	19
49243	QT13/35-4P	13	G24q-1	900	82	3500	5/127	2.2	10,000	19
49084	QT13/41	13	GX23-2	810	82	4100	4.6/117	2.2	10,000	19
49244	QT13/41-4P	13	G24q-1	900	82	4100	5/127	2.2	10,000	19
49223	QT13/50	13	GX23-2	810	82	5000	4.6/117	2.2	10,000	19
49245	QT13/50-4P	13	G24q-1	900	82	5000	5/127	2.2	10,000	19

Continued on next page >>>



Fluorescent

Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
49224	QT13/65	13	GX23-2	810	82	6500	4.6/117	2.2	10,000	19
49246	QT13/65-4P	13	G24q-1	900	82	6500	5/127	2.2	10,000	19
15566	QT18/27	18	G24d-2	1150	82	2700	5.9/150	2.2	10,000	19
49247	QT18/27-4P	18	G24q-2	1150	82	2700	5.8/147	2.2	10,000	19
49248	QT18/30-4P	18	G24q-2	1150	82	3000	5.8/147	2.2	10,000	19
49232	QT18/35	18	G24d-2	1150	82	3500	5.9/150	2.2	10,000	19
49249	QT18/35-4P	18	G24q-2	1150	82	3500	5.8/147	2.2	10,000	19
49233	QT18/41	18	G24d-2	1150	82	4100	5.9/150	2.2	10,000	19
49250	QT18/41-4P	18	G24q-2	1150	82	4100	5.8/147	2.2	10,000	19
49234	QT18/50	18	G24d-2	1150	82	5000	5.9/150	2.2	10,000	19
49251	QT18/50-4P	18	G24q-2	1150	82	5000	5.8/147	2.2	10,000	19
15568	QT26/27	26	G24d-3	1710	82	2700	6.7/170	2.2	10,000	19
49253	QT26/27-4P	26	G24q-3	1710	82	2700	6.4/163	2.2	10,000	19
49236	QT26/30	26	G24d-3	1710	82	3000	6.7/170	2.2	10,000	19
49254	QT26/30-4P	26	G24q-3	1710	82	3000	6.4/163	2.2	10,000	19
49237	QT26/35	26	G24d-3	1710	82	3500	6.7/170	2.2	10,000	19
49255	QT26/35-4P	26	G24q-3	1710	82	3500	6.4/163	2.2	10,000	19
49238	QT26/41	26	G24d-3	1710	82	4100	6.7/170	2.2	10,000	19
49256	QT26/41-4P	26	G24q-3	1710	82	4100	6.4/163	2.2	10,000	19
49239	QT26/50	26	G24d-3	1710	82	5000	6.7/170	2.2	10,000	19
49257	QT26/50-4P	26	G24q-3	1710	82	5000	6.4/163	2.2	10,000	19
49240	QT26/65*	26	G24d-3	1710	82	6500	6.7/170	2.2	10,000	19
49258	QT26/65-4P	26	G24q-3	1710	82	6500	6.4/163	2.2	10,000	19

Lamps contain mercury - please dispose of properly.

FML CFL Lamps

Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
05148	FML18/65	18	GX10q-4	1080	82	6500	5.1/129	2.5	10,000	20
49313	FML27/27	27	GX10q-4	1400	82	2700	5.7/145	2.5	10,000	20
49314	FML27/41	27	GX10q-4	1400	82	4100	5.7/145	2.5	10,000	20
49315	FML27/65	27	GX10q-4	1400	82	6500	5.7/145	2.5	10,000	20

Lamps contain mercury - please dispose of properly.






Linear Fluorescent Lamps

EIKO's entire line of linear fluorescent lamps features long life, high quality tri-phosphor blends and a variety of environmentally-friendly TCLP and CEE ratings. Our selection includes linear, circuline and u-bend fluorescents in various sizes, wattages and color temperatures.

Programmed Start T5 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
81147	F14T5/835	14	G5	1350	1256	85	3500	22/559	2.7	25,000	35,000	1
81148	F14T5/841	14	G5	1200		85	4000	22/559	2.7	25,000	35,000	1
07151	F14T5/865*	14	G5	1300	1210	85	6500	22/559	4.25	25,000	35,000	1
81149	F21T5/835	21	G5	2100	1953	85	3500	34/864	2.7	25,000	35,000	1
81150	F21T5/841	21	G5	1900		85	4000	34/864	2.7	25,000	35,000	1
81154	F24T5/HO/835	24	G5	1750	1625	85	3500	22/559	4.25	25,000	35,000	1
81155	F24T5/HO/841	24	G5	1750	1625	85	4100	22/559	4.25	25,000	35,000	1
81151	F28T5/835	28	G5	2900		85	3000	46/1169	2.7	25,000	35,000	1
81152	F28T5/841	28	G5	2900		85	4000	46/1169	2.7	25,000	35,000	1
81153	F28T5/850	28	G5	2675		85	5000	46/1169	2.7	25,000	35,000	1
07150	F28T5/865	28	G5	2675	2650	85	6500	46/1169	2.7	25,000	35,000	1
04727	F35T5/830	35	G5	3300		85	3000	57/1463	2.7	25,000	35,000	1
81156	F39T5/HO/835	39	G5	3200	2975	85	3500	34/864	4.25	25,000	35,000	1
81157	F39T5/HO/841	39	G5	3200	2975	85	4100	34/864	4.25	25,000	35,000	1
00973	F49T5/HO/835*	49	G5	4900	4750	85	3500	46/1169	2.7	25,000	35,000	1
00976	F49T5/HO/841	49	G5	4900	4750	85	4000	46/1169	2.7	25,000	35,000	1
00981	F49T5/HO/850	49	G5	4800	4625	85	5000	46/1169	2.7	25,000	35,000	1
00982	F49T5/HO/865	49	G5	4800	4625	85	6500	46/1169	2.7	25,000	35,000	1
07376	F54T5/HO/830	54	G5	5000	4650	85	3000	46/1169	2.7	25,000	35,000	1
81158	F54T5/HO/835	54	G5	5000	4650	85	3500	46/1169	2.7	25,000	35,000	1
81159	F54T5/HO/841	54	G5	5000	4650	85	4100	46/1169	2.7	25,000	35,000	1
81160	F54T5/HO/850	54	G5	4850	4500	85	5000	46/1169	2.7	25,000	35,000	1
06854	F54T5/HO/865	54	G5	4850	4500	85	6500	46/1169	2.7	25,000	35,000	1

Lamps contain mercury - please dispose of properly.



*Closeout item: available while supplies last.

Fluorescent

Preheat T5 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
15500	F4T5/CW	4	G5	135	100	60	4100	6.0/152	2.72	6,000	1
15501	F4T5/D	4	G5	115	92	75	6500	6.0/152	2.75	6,000	1
15505	F6T5/CW	6	G5	295	235	60	4100	9.0/229	2.75	7,500	1
15506	F6T5/D	6	G5	230	185	75	6500	9.0/229	2.75	7,500	1
15507	F6T5/WW*	6	G5	275	220	52	3000	9.0/229	2.75	7,500	1
15510	F8T5/CW	8	G5	400	320	60	4100	12.0/305	2.75	7,500	1
15511	F8T5/D	8	G5	330	265	75	6500	12.0/305	2.75	7,500	1
15512	F8T5/WW	8	G5	410	330	52	3000	12.0/305	2.75	7,500	1
15517	F13T5/CW	13	G5	850	705	60	4100	21.0/533	2.75	7,500	1
15531	F13T5/D	13	G5	700	460	75	6500	21.0/533	2.75	7,500	1
15518	F13T5/WW	13	G5	870	720	60	3000	21.0/533	2.75	7,500	1

Lamps contain mercury - please dispose of properly.

Blacklight T5 Linear Fluorescent Lamps

Order Code	Item	W	Base	MOL in/mm	MOD in/mm	mg Hg	Life/Hrs	Photo #
15503	F4T5/BL	4	G5	6.0/152	0.63/16	2.75	6,000	1
15504	F4T5/BLB	4	G5	6.0/152	0.63/16	2.75	6,000	2
15515	F8T5/BL	8	G5	12.0/305	0.63/16	2.75	7,500	1
15516	F8T5/BLB	8	G5	12.0/305	0.63/16	2.75	7,500	2

Lamps contain mercury - please dispose of properly.

T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
49575	F17T8/830K	17	G13	1400	1300	85	3000	24.0/610	3	20,000	25,000	3
49576	F17T8/835K	17	G13	1400	1300	85	3500	24.0/610	3	20,000	25,000	3
49577	F17T8/841K	17	G13	1400	1300	85	4100	24.0/610	3	20,000	25,000	3
48055	F17T8/850K	17	G13	1400	1300	85	5000	24.0/610	3	20,000	25,000	3
49581	F25T8/830K	25	G13	2225	2050	85	3000	36.0/915	3	20,000	25,000	3
49582	F25T8/835K	25	G13	2225	2050	85	3500	36.0/915	3	20,000	25,000	3
49583	F25T8/841K	25	G13	2225	2050	85	4100	36.0/915	3	20,000	25,000	3
49587	F32T8/830K	32	G13	2950	2800	85	3000	48.0/1219	3	24,000	30,000	3
49588	F32T8/835K	32	G13	2950	2800	85	3500	48.0/1219	3	24,000	30,000	3
49589	F32T8/841K	32	G13	2950	2800	85	4100	48.0/1219	3	24,000	30,000	3
81174	F32T8/850K	32	G13	2950	2773	85	5000	48.0/1219	3	24,000	30,000	3
07147	F32T8/865K	32	G13	2900	2725	85	6500	48.0/1219	3	24,000	30,000	3

Lamps contain mercury - please dispose of properly.

CEE Specified T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
06748	F32T8/830/ES/25W*	25	G13	2400	2260	85	3000	48.0/1219	3	24,000	30,000	3
06750	F32T8/841/ES/25W	25	G13	2400	2260	85	4100	48.0/1219	3	24,000	30,000	3

Continued on next page >>>



Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
06751	F32T8/850/ES/25W	25	G13	2350	2200	85	5000	48.0/1219	3	24,000	30,000	3
07149	F32T8/865/ES/25W*	25	G13	2350	2200	85	6500	48.0/1219	3	24,000	30,000	3
06603	F28T8/830/ES	28	G13	2800	2635	85	3000	48.0/1219	3	24,000	30,000	3
06604	F28T8/835/ES	28	G13	2800	2635	85	3500	48.0/1219	3	24,000	30,000	3
06605	F28T8/841/ES	28	G13	2800	2635	85	4100	48.0/1219	3	24,000	30,000	3
06606	F28T8/850/ES	28	G13	2800	2635	85	5000	48.0/1219	3	24,000	30,000	3
07146	F28T8/865/ES	28	G13	2750	2585	85	6500	48.0/1219	3	24,000	30,000	3
06568	F32T8/830K/HL*	32	G13	3100	2915	85	3000	48.0/1219	3	24,000	30,000	3
06569	F32T8/835K/HL	32	G13	3100	2915	85	3500	48.0/1219	3	24,000	30,000	3
06570	F32T8/841K/HL	32	G13	3100	2915	85	4100	48.0/1219	3	24,000	30,000	3
81174	F32T8/850K	32	G13	2950	2773	85	5000	48.0/1219	3	24000	24000	3
06571	F32T8/850K/HL	32	G13	3000	2820	85	5000	48.0/1219	3	24,000	30,000	3
07476	F32T8/850K/XL*	32	G13	2950	2810	85	5000	48.0/1219	3.5	44,000	55,000	3
07148	F32T8/865K/HL	32	G13	3000	2820	85	6500	48.0/1219	3	24,000	30,000	3

Lamps contain mercury - please dispose of properly.

Energy Saving T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
49581	F25T8/830K	25	G13	2225	2050	85	3000	36.0/915	3	20,000	25,000	3
49582	F25T8/835K	25	G13	2225	2050	85	3500	36.0/915	3	20,000	25,000	3
49583	F25T8/841K	25	G13	2225	2050	85	4100	36.0/915	3	20,000	25,000	3
06748	F32T8/830/ES/25W*	25	G13	2400	2260	85	3000	48.0/1219	3	24,000	30,000	3
06750	F32T8/841/ES/25W	25	G13	2400	2260	85	4100	48.0/1219	3	24,000	30,000	3
06751	F32T8/850/ES/25W	25	G13	2350	2200	85	5000	48.0/1219	3	24,000	30,000	3
07149	F32T8/865/ES/25W*	25	G13	2350	2200	85	6500	48.0/1219	3	24,000	30,000	3
06603	F28T8/830/ES	28	G13	2800	2635	85	3000	48.0/1219	3	24,000	30,000	3
06604	F28T8/835/ES	28	G13	2800	2635	85	3500	48.0/1219	3	24,000	30,000	3
06605	F28T8/841/ES	28	G13	2800	2635	85	4100	48.0/1219	3	24,000	30,000	3
06606	F28T8/850/ES	28	G13	2800	2635	85	5000	48.0/1219	3	24,000	30,000	3
07146	F28T8/865/ES	28	G13	2750	2585	85	6500	48.0/1219	3	24,000	30,000	3

Lamps contain mercury - please dispose of properly.

Long Life T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
07437	F32T8/830K/XL*	32	G13	2950	2810	83	3000	48.0/1219	3.5	44,000	55,000	3
07833	F32T8/835K/XL*	32	G13	2950	2810	83	3500	48.0/1219	3.5	44,000	55,000	3
07789	F32T8/841K/XL*	32	G13	2950	2810	83	4100	48.0/1219	3.5	44,000	55,000	3
07476	F32T8/850K/XL*	32	G13	2950	2810	85	5000	48.0/1219	3.5	44,000	55,000	3
07592	F32T8/865K/XL*	32	G13	2850	2710	83	6500	48.0/1219	3.5	44,000	55,000	3

Lamps contain mercury - please dispose of properly.

High Lumen T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
06568	F32T8/830K/HL*	32	G13	3100	2915	85	3000	48.0/1219	3	24,000	30,000	3
06569	F32T8/835K/HL	32	G13	3100	2915	85	3500	48.0/1219	3	24,000	30,000	3

Continued on next page >>>



Fluorescent

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
06570	F32T8/841K/HL	32	G13	3100	2915	85	4100	48.0/1219	3	24,000	30,000	3
06571	F32T8/850K/HL	32	G13	3000	2820	85	5000	48.0/1219	3	24,000	30,000	3
07148	F32T8/865K/HL	32	G13	3000	2820	85	6500	48.0/1219	3	24,000	30,000	3

Lamps contain mercury - please dispose of properly.

Preheat T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life/Hrs	Photo #
15524	F10T8/CW	10	G13	480	425	60	4100	13.6/346	2.75	7,500	3
15545	F13T8/CW*	13	G13	565	480	60	4100	12.0/305	2.75	7,500	3
15519	F14T8/CW	14	G13	685	580	60	4100	15.0/381	2.75	7,500	3
15520	F14T8/D	14	G13	645	545	75	6500	15.0/381	2.75	7,500	3
15521	F15T8/CW	15	G13	825	725	60	4100	18.0/457	2.75	7,500	3
15522	F15T8/D	15	G13	700	615	75	6500	18.0/457	2.75	7,500	3
15523	F15T8/WW	15	G13	845	745	52	3000	18.0/457	2.75	7,500	3

Lamps contain mercury - please dispose of properly.

Blacklight T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	MOL in/mm	MOD in/mm	mg Hg	Life/Hrs	Photo #
15526	F15T8/BL	15	G13	18.0/457	1.0/26	2.75	7,500	3
15527	F15T8/BLB	15	G13	18.0/457	1.0/26	2.75	7,500	4

Lamps contain mercury - please dispose of properly.

Safety Coated T8 Linear Fluorescent Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	mg Hg	Life 3hr Start	Life 12hr Start	Photo #
06788	F32T8/841K-C	32	G13	2950	2800	83	4100	48.0/1219	3.5	20,000	25,000	3
06845	F32T8/850K-C	32	G13	2950	2800	85	5000	48.0/1219	3.5	20,000	25,000	3

Lamps contain mercury - please dispose of properly.

T12 Linear Fluorescent Lamps

Order Code	Item	W	Base	MOL in/mm	MOD in/mm	mg Hg	Life/Hrs	Photo #
08293	F40T12/CW/HE	140	G13	47.78/1213.6	1.59/40.4	7	24,000	5

For applications requiring superior color rendering. Lamps contain mercury - please dispose of properly.

Circular Fluorescent Lamps

Order Code	Item	W	Base	MOL in/mm	mg Hg	Life/Hrs	Photo #
15604	FC8T9/CW	22	G10q	8.25/215	7.5	12,000	6
15532	FC8T9/D	22	G10q	8.25/215	7.5	12,000	6
15606	FC12T9/CW	32	G10q	12.0/305	7.5	12,000	6
15533	FC12T9/D	32	G10q	12.0/305	7.5	12,000	6
15534	FC16T9/CW	40	G10q	16.0/406	7.5	12,000	6

Lamps contain mercury - please dispose of properly.



T8 U-Bend Fluorescent Lamps

Order Code	Item	W	Base	MOL in/mm	MOD in/mm	mg Hg	Life/Hrs	Photo #
05287	F31T8/830/U*	31	G13	22.5/571	1.0/26	7.5	20,000	7
05288	F31T8/835/U	31	G13	22.5/571	1.0/26	7.5	20,000	7
05289	F31T8/841/U	31	G13	22.5/571	1.0/26	7.5	20,000	7
05290	F31T8/850/U	31	G13	22.5/571	1.0/26	7.5	20,000	7
02403	F32T8/835K/U6	32	G13	22.5/571	1.0/26	7.5	20,000	8
02404	F32T8/841K/U6	32	G13	22.5/571	1.0/26	7.5	20,000	8
02405	F32T8/850K/U6	32	G13	22.5/571	1.0/26	7.5	20,000	8

Lamps contain mercury - please dispose of properly.

PowerMaster™ Ballasts

Order Code	Item	V	Photo #
07825	PM-2X32T8-UNV-IS	120-277VAC	9
07873	PM-2X32T8-UNV-IS-H	120-277VAC	9
07872	PM-2X32T8-UNV-IS-L	120-277VAC	9
07827	PM-2X54T5-UNV-PS	120-277VAC	9
07868	PM-3X32T8-UNV-IS	120-277VAC	9
07875	PM-3X32T8-UNV-IS-H	120-277VAC	9
07874	PM-3X32T8-UNV-IS-L*	120-277VAC	9
07826	PM-4X32T8-UNV-IS	120-277VAC	9
07876	PM-4X32T8-UNV-IS-L	120-277VAC	9
07828	PM-4X54T5-UNV-PS	120-277VAC	9

Fluorescent Starters

Order Code	Item	Description	Photo #
49554	FS-U-120V	Aluminum case	10
49552	FS-5	Aluminum case	10
49551	FS-4*	Aluminum case	10
49550	FS-2	Aluminum case	10



*Closeout item: available while supplies last.



HID Lamps

EIKO commercial grade HID lamps are manufactured with the professional in mind. High-quality components, heavy-duty construction, durable packaging and a full warranty result in a lamp you can install with confidence. With many options to choose from, including pulse start, clear and coated, open fixture rated and our new ColorMaster PRO™ ceramic metal halides, EIKO's HID's are a high quality, flexible option.

WARNING: HID lamps can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available.

ColorMaster PRO™ Ceramic Metal Halide PAR Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	Bm	Approx Initial Max Beam CP	ANSI Ballast	Life/Hrs	Photo #
07172	CMP20/PAR20/FL	20	E26	1200	900	85+	3000	3.74/95	30	3500	M156/0	9,000	1
07165	CMP20/PAR20/SP	20	E26	1200	900	85+	3000	3.74/95	10	15000	M156/0	9,000	1
07174	CMP20/PAR30LN/FL	20	E26	1200	900	85+	3000	4.92/125	30	4000	M156/0	9,000	1
06774	CMP35/PAR20/FL	35	E26	2000	1660	85+	3000	3.74/95	30	5000	M130/0	10,000	2
06773	CMP35/PAR20/SP*	35	E26	2000	1660	85+	3000	3.74/95	10	23000	M130/0	10,000	2
06776	CMP35/PAR30LN/FL	35	E26	2400	1990	85+	3000	4.92/125	30	7500	M130/0	10,000	2
07829	CMP35/PAR30LN/FL/842	35	E26	2400	1990	85+	4200	4.92/125	30	7500	M130/0	10,000	2
06775	CMP35/PAR30LN/SP	35	E26	2400	1990	85+	3000	4.92/125	10	44000	M130/0	10,000	2
07166	CMP70/PAR30LN/FL	70	E26	4850	3640	85+	3000	4.92/125	40	10500	M139/M98/M143/0	10,000	3
07175	CMP70/PAR30LN/SP*	70	E26	4850	3640	85+	3000	4.92/125	10	68000	M139/M98/M143/0	10,000	3
07177	CMP70/PAR38/FL	70	E26	4800	3600	85+	3000	5.43/138	25	20000	M139/M98/M143/0	10,000	3
07176	CMP70/PAR38/SP*	70	E26	4800	3600	85+	3000	5.43/138	15	53000	M139/M98/M143/0	10,000	3

Lamps contain mercury - please dispose of properly.



ColorMaster PRO™ Ceramic Metal Halide MR16 Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	Bm	Approx Initial Max Beam CP	ANSI Ballast	Life/Hrs	Photo #
07178	CMP-MR16/20W/NFL/830	20	GX10	1200	900	85+	3000	2.56/65	25	2900	M156/0	9,000	4
07171	CMP-MR16/20W/SP/830*	20	GX10	1200	900	85+	3000	2.56/65	12	9000	M156/0	9,000	4
08286	CMP-MR16/39W/NFL/830	35	GX10	2100	1470	88+	3000	2.56/65	25	5500		10,000	4

Lamps contain mercury - please dispose of properly.

ColorMaster PRO™ Ceramic Metal Halide EDX17 Lamps

Order Code	Item	W	Base	Approx Init Lm	CRI	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
07284	CMP70/C/MP/4K*	70	E26	5200	90+	4000	5.43/138	M139/M98/M143/0	20,000	5
07278	CMP70/MP/3K	70	E26	5900	90+	3000	5.43/138	M139/M98/M143/0	16,000	5
07277	CMP70/MP/4K	70	E26	5800	92+	4000	5.43/138	M139/M98/M143/0	20,000	5
07280	CMP100/C/MP/3K	100	E26	7900	92+	3000	5.43/138	M140/M90/0	16,000	5
07283	CMP100/C/MP/4K	100	E26	7500	92+	4000	5.43/138	M140/M90/0	20,000	5
07279	CMP100/MP/3K*	100	E26	8600	92+	3000	5.43/138	M140/M90/0	16,000	5
07276	CMP100/MP/4K*	100	E26	8200	92+	4000	5.43/138	M140/M90/0	20,000	5
07285	CMP150/MP/3K*	150	E26	12900	90+	3000	5.43/138	M142/M102/0	16,000	5
07282	CMP150/MP/4K	150	E26	12000	93+	4000	5.43/138	M142/M102/0	20,000	5

Lamps contain mercury - please dispose of properly.

ColorMaster PRO™ Ceramic Metal Halide Bi-Pin Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
07164	CMP20/TC/930	20	G8.5	1750	1320	90	3000	3.15/80	M156/E	10,000	6
07167	CMP20/TM/930	20	GU6.5	1750	1320	90	3000	2.05/52	M156/E	10,000	6
06630	CMP35/T6/930	35	G12	3700	3070	90	3000	4.33/110	M130/E	12,000	6
06777	CMP35/T6/942	35	G12	3700	3070	90+	4200	4.33/110	M130/E	12,000	6
06955	CMP35/TC/930	35	G8.5	3700	3070	90	3000	3.15/80	M130/E	12,000	6
06632	CMP70/T6/930	70	G12	7200	5980	90	3000	4.33/110	M139/M98/M143/E	12,000	6
06633	CMP70/T6/942	70	G12	7100	5890	90+	4200	4.33/110	M139/M98/M143/E	12,000	6
06634	CMP70/TC/930	70	G8.5	7200	5980	90	3000	3.15/80	M139/M98/M143/E	12,000	6
06629	CMP150/T6/930	150	G12	15000	12450	90+	3000	4.33/110	M142/E	12,000	6
07168	CMP150/T6/942	150	G12	13000	9750	95	4000	4.33/110	M142/E	10,000	6

Lamps contain mercury - please dispose of properly.

ColorMaster PRO™ Ceramic Metal Halide Double Ended Lamps

Order Code	Item	W	Base	Approx Init Lm	Approx Mean Lm	CRI	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
07169	CMP70/TD/930	70	Rx7s	6500	4875	90	3000	4.69/119	M139/M98/M143/E	12,000	7
06732	CMP70/TD/942*	70	Rx7s	7100	5890	90+	4200	4.72/120	M139/M98/M143/E	15,000	7

Lamps contain mercury - please dispose of properly.



*Closeout item: available while supplies last.

Medium & Mogul Based Metal Halide Lamps


Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
49187	MH50/C/U/MED	50	ED-17	E26	3000	3700	5.50/139.7	M110	10,000	8
49188	MH50/U/MED	50	ED-17	E26	3400	4000	5.50/139.7	M110	10,000	8
49189	MH70/C/U/MED	70	ED-17	E26	5300	3700	5.50/139.7	M98	15,000	8
15410	MH70/U/MED	70	ED-17	E26	5600	4000	5.50/139.7	M98	15,000	8
49190	MH100/C/U/MED	100	ED-17	E26	8500	3700	5.50/139.7	M90/M140	15,000	8
15411	MH100/U/MED	100	ED-17	E26	9000	4000	5.50/139.7	M90/M140	15,000	8
49191	MH150/C/U/MED*	150	ED-17	E26	13300	3700	5.50/139.7	M102	15,000	8
15413	MH150/U/MED	150	ED-17	E26	14000	4000	5.50/139.7	M102	15,000	8
49194	MH175/C/U	175	ED-28	E39	13300	3700	8.3/211.2	M57	10,000	9
49192	MH175/C/U/MED	175	ED-17	E26	13300	3700	5.50/139.7	M57	10,000	8
49193	MH175/U	175	ED-28	E39	14000	4000	8.3/211.2	M57	10,000	9
15414	MH175/U/MED	175	ED-17	E26	14000	4000	5.50/139.7	M57	10,000	8
49530	MH200/C/U*	200	ED-28	E39	20000	3700	8.3/211.2	M136	15,000	9
49529	MH200/U	200	ED-28	E39	21000	4000	8.3/211.2	M136	15,000	9
49196	MH250/C/U	250	ED-28	E39	20000	3700	8.3/211.2	M58	10,000	9
49195	MH250/U	250	ED-28	E39	21000	4000	8.3/211.2	M58	10,000	9
49531	MH250/U/T15	250	T-15	E39	21000	4000	9.75/247.7	M58	10,000	10
81052	MH320/U	320	ED-28	E39	31000	4000	8.3/211.2	M154/M132/E	20,000	9
49532	MH350/HOR	350	ED-28	E39	33000	4000	8.3/211.2	M131	20,000	9
49198	MH400/C/U	400	ED-37	E39	34000	3700	11.5/292.1	M59	20,000	12
49556	MH400/C/U/ED28	400	ED-28	E39	34000	3700	8.3/211.2	M59	20,000	9
49197	MH400/U	400	ED-37	E39	36000	4000	11.5/292.1	M59	20,000	12
49463	MH400/U/ED28	400	ED-28	E39	36000	4000	8.3/211.2	M59	20,000	9
49534	MH400/U/T15	400	T-15	E39	36000	4000	9.75/247.7	M59	15,000	10
49199	MH1000/U	1000	BT-56	E39	110000	4000	15.5/393.7	M47	12,000	11
49557	MH1000/U/BT37	1000	BT-37	E39	110000	4000	11.5/292.1	M47	12,000	12
49201	MH1500/U	1500	BT-56	E39	155000	4000	15.5/393.7	M48	3,500	11

Lamps contain mercury - please dispose of properly.

Open Fixture Rated Metal Halide Lamps

Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
44501	MP50/U/MED/3K	50	EDX-17	E26	3200	3200	5.5/139.7	M110	10,000	13
49506	MP70/C/U/MED/3K	70	EDX-17	E26	5000	3200	5.5/139.7	M98	15,000	13
49508	MP70/C/U/MED/4K	70	EDX-17	E26	5000	3700	5.5/139.7	M98	15,000	13
49507	MP70/U/MED/3K	70	EDX-17	E26	5300	3200	5.5/139.7	M98	15,000	13
49509	MP70/U/MED/4K	70	EDX-17	E26	5300	4000	5.5/139.7	M98	15,000	13
49511	MP100/C/U/MED/3K	100	EDX-17	E26	8100	3200	5.5/139.7	M90	15,000	13
49513	MP100/C/U/MED/4K	100	EDX-17	E26	8100	3700	5.5/139.7	M90	15,000	13
49512	MP100/U/MED/3K	100	EDX-17	E26	8500	3200	5.5/139.7	M90	15,000	13
49514	MP100/U/MED/4K	100	EDX-17	E26	8500	4000	5.5/139.7	M90	15,000	13
49516	MP150/C/U/MED/3K*	150	EDX-17	E26	12600	3200	5.5/139.7	M102	15,000	13
49518	MP150/C/U/MED/4K*	150	EDX-17	E26	12600	3700	5.5/139.7	M102	15,000	13
49517	MP150/U/MED/3K	150	EDX-17	E26	13300	3200	5.5/139.7	M102	15,000	13

Continued on next page >>>



Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/ Hrs	Photo #
49519	MP150/U/MED/4K	150	EDX-17	E26	13300	4000	5.5/139.7	M102	15,000	13
06683	MP250/BU/P	250	ED-28	EX39	25000	4000	8.3/211.2	M153/M138/0	12,000	9
81053	MP320/BU	320	ED-28	EX39	31000	4000	8.3/211.2	M154/M132/0	20,000	9
49538	MP350/BU	350	ED-28	EX39	35000	4000	8.3/211.2	M131	20,000	9
06479	MP400/BU/ED28/P	400	ED-28	EX39	41000	4000	8.86/225	M155/M128/M135/0	20,000	9
06276	MP400/BU/P	400	ED-37	EX39	41000	4000	11.73/296	M155/M128/M135/0	20,000	12

Lamps contain mercury - please dispose of properly.

Single Ended Metal Halide Lamps

Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/ Hrs	Photo #
49183	MH-SE70/UVS/3K	70	T-7	G12	5600	3000	4.25/108.0	M85/M98	10,000	14
49185	MH-SE150/UVS/3K	150	T-7	G12	14000	3000	4.25/108.0	M81/M102	10,000	14
49186	MH-SE150/UVS/4K	150	T-7	G12	14000	4000	4.25/108.0	M81/M102	10,000	14

Lamps contain mercury - please dispose of properly.

Double Ended Metal Halide Lamps

Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/ Hrs	Photo #
15406	MH-DE70/TD/UVS/3K	70	T-6	R7s	5200	3000	4.50/114.3	M85/M98	10,000	15
15407	MH-DE70/TD/UVS/4K	70	T-6	R7s	5500	4200	4.50/114.3	M85/M98	10,000	15
15408	MH-DE150/TD/UVS/3K	150	T-7	R7s	11250	3000	5.19/131.8	M81/M102	10,000	15
15409	MH-DE150/TD/UVS/4K	150	T-7	R7s	11250	4200	5.19/131.8	M81/M102	10,000	15

Lamps contain mercury - please dispose of properly.

Pulse Start Metal Halide Lamps

Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Description	Life/ Hrs	Photo #
49187	MH50/C/U/MED	50	ED-17	E26	3000	3700	5.50/139.7	M110	Pulse Start	10,000	8
49188	MH50/U/MED	50	ED-17	E26	3400	4000	5.50/139.7	M110	Pulse Start	10,000	8
44501	MP50/U/MED/3K	50	EDX-17	E26	3200	3200	5.5/139.7	M110	Pulse Start & UV Shielded	10,000	13
15406	MH-DE70/TD/UVS/3K	70	T-6	R7s	5200	3000	4.50/114.3	M85/M98	Pulse Start & UV Shielded	10,000	15
15407	MH-DE70/TD/UVS/4K	70	T-6	R7s	5500	4200	4.50/114.3	M85/M98	Pulse Start & UV Shielded	10,000	15
49183	MH-SE70/UVS/3K	70	T-7	G12	5600	3000	4.25/108.0	M85/M98	Pulse Start & UV Shielded	10,000	15
49189	MH70/C/U/MED	70	ED-17	E26	5300	3700	5.50/139.7	M98	Pulse Start	15,000	8
15410	MH70/U/MED	70	ED-17	E26	5600	4000	5.50/139.7	M98	Pulse Start	15,000	8
49506	MP70/C/U/MED/3K	70	EDX-17	E26	5000	3200	5.5/139.7	M98	Pulse Start & UV Shielded	15,000	13
49508	MP70/C/U/MED/4K	70	EDX-17	E26	5000	3700	5.5/139.7	M98	Pulse Start & UV Shielded	15,000	13
49509	MP70/U/MED/4K	70	EDX-17	E26	5300	4000	5.5/139.7	M98	Pulse Start & UV Shielded	15,000	13
49190	MH100/C/U/MED	100	ED-17	E26	8500	3700	5.50/139.7	M90/M140	Pulse Start	15,000	8
15411	MH100/U/MED	100	ED-17	E26	9000	4000	5.50/139.7	M90/M140	Pulse Start	15,000	8
49511	MP100/C/U/MED/3K	100	EDX-17	E26	8100	3200	5.5/139.7	M90	Pulse Start & UV Shielded	15,000	13
49513	MP100/C/U/MED/4K	100	EDX-17	E26	8100	3700	5.5/139.7	M90	Pulse Start & UV Shielded	15,000	13
49512	MP100/U/MED/3K	100	EDX-17	E26	8500	3200	5.5/139.7	M90	Pulse Start & UV Shielded	15,000	13
49514	MP100/U/MED/4K	100	EDX-17	E26	8500	4000	5.5/139.7	M90	Pulse Start & UV Shielded	15,000	13

Continued on next page >>>



HID


Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Description	Life/Hrs	Photo #
15409	MH-DE150/TD/UVS/4K	150	T-7	R7s	11250	4200	5.19/131.8	M81/M102	Pulse Start & UV Shielded	10,000	15
49185	MH-SE150/UVS/3K	150	T-7	G12	14000	3000	4.25/108.0	M81/M102	Pulse Start & UV Shielded	10,000	15
49186	MH-SE150/UVS/4K	150	T-7	G12	14000	4000	4.25/108.0	M81/M102	Pulse Start & UV Shielded	10,000	15
49191	MH150/C/U/MED*	150	ED-17	E26	13300	3700	5.50/139.7	M102	Pulse Start	15,000	8
15413	MH150/U/MED	150	ED-17	E26	14000	4000	5.50/139.7	M102	Pulse Start	15,000	8
49516	MP150/C/U/MED/3K*	150	EDX-17	E26	12600	3200	5.5/139.7	M102	Pulse Start & UV Shielded	15,000	13
49518	MP150/C/U/MED/4K*	150	EDX-17	E26	12600	3700	5.5/139.7	M102	Pulse Start & UV Shielded	15,000	13
49530	MH200/C/U*	200	ED-28	E39	20000	3700	8.3/211.2	M136	Pulse Start	15,000	9
49529	MH200/U	200	ED-28	E39	21000	4000	8.3/211.2	M136	Pulse Start	15,000	9
06745	MH250/BU/PS	250	ED-28	E39	25000	4000	8.3/211.2	M153/M138/E	Pulse Start	12,000	9
06683	MP250/BU/P	250	ED-28	EX39	25000	4000	8.3/211.2	M153/M138/O	Pulse Start & UV Shielded	12,000	9
81052	MH320/U	320	ED-28	E39	31000	4000	8.3/211.2	M154/M132/E	Pulse Start	20,000	9
81053	MP320/BU	320	ED-28	EX39	31000	4000	8.3/211.2	M154/M132/O	Pulse Start & UV Shielded	20,000	9
49533	MH350/C/HOR	350	ED-28	E39	31000	3700	8.3/211.2	M131	Pulse Start	20,000	9
49532	MH350/HOR	350	ED-28	E39	33000	4000	8.3/211.2	M131	Pulse Start	20,000	9
49538	MP350/BU	350	ED-28	EX39	35000	4000	8.3/211.2	M131	Pulse Start & UV Shielded	20,000	9
06746	MH400/BU/PS	400	ED-37	E39	41000	4000	11.5/292.1	M155/M128/M135/E	Pulse Start	20,000	12
06747	MH400/C/BU/PS	400	ED-37	E39	41000	3700	11.5/292.1	M155/M128/M135/E	Pulse Start	20,000	12
06479	MP400/BU/ED28/P	400	ED-28	EX39	41000	4000	8.86/225	M155/M128/M135/O	Pulse Start & UV Shielded	20,000	9
06276	MP400/BU/P	400	ED-37	EX39	41000	4000	11.73/296	M155/M128/M135/O	Pulse Start & UV Shielded	20,000	12

Lamps contain mercury - please dispose of properly.

High Pressure Sodium Lamps

Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
15300	LU35/MED	35	ED-17	E26	2250	2100	5.44/138.0	S76	16,000	17
15304	LU50	50	ED-23.5	E39	4000	2100	7.75/196.9	S68	24,000	18
15302	LU50/MED	50	ED-17	E26	4000	2100	5.44/138.0	S68	24,000	17
15308	LU70	70	ED-23.5	E39	6300	2100	7.75/196.9	S62	24,000	18
49157	LU70/D/MED*	70	ED-17	E26	5860	2100	5.44/138.0	S62	24,000	17
15306	LU70/MED	70	ED-17	E26	6300	2100	5.44/138.0	S62	24,000	17
15312	LU100	100	ED-23.5	E39	9500	2100	7.75/196.9	S54	24,000	18
15310	LU100/MED	100	ED-17	E26	9500	2100	5.44/138.0	S54	24,000	17
15318	LU150/100	150	ED-28	E39	16000	2100	8.3/211.1	S56	24,000	19
15316	LU150/55	150	ED-23.5	E39	16000	2100	7.75/196.9	S55	24,000	18
15314	LU150/55/MED	150	ED-17	E26	16000	2100	5.44/138.0	S55	24,000	17
15319	LU200*	200	ED-18	E39	22000	2100	9.75/247.6	S66	24,000	20
15320	LU250	250	ED-18	E39	28500	2100	9.75/247.6	S50	24,000	20
49164	LU250/D*	250	ED-28	E39	26000	2100	8.3/211.1	S50	24,000	19
15322	LU400	400	ED-18	E39	50000	2100	9.75/247.6	S51	24,000	20
49167	LU600	600	T-14.5	E39	90000	2100	11.13/282.6	S106	24,000	21
15324	LU1000	1000	E-25	E39	140000	2100	15.06/382.6	S52	24,000	22

Lamps contain mercury - please dispose of properly.



Non-Cycling High Pressure Sodium Lamps

Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
08233	LU250/NC*	250	ED-28	E39	29000	2100	8.7/221	S50	24,000	19
08234	LU400/ED28/NC*	400	ED-28	E39	49000	2100	10.7/271.8	S51	24,000	19

Lamps contain mercury - please dispose of properly.

Mercury Vapor Lamps

Order Code	Item	W	Shape	Base	Approx Init Lm	CCT	MOL in/mm	ANSI Ballast	Life/Hrs	Photo #
49564	H43AV-75/DX	75	ED-17	E26	2700	3200	5.44/138.0	H43	10,000	23
00332	H38AV-100/DX	100	ED-17	E26	4000	3900	5.44/138.0	H38	12,000	23
15353	H38JA-100/DX	100	ED-23.5	E39	4100	3200	7.50/190.5	H38	12,000	24
49168	H38MP-100/DX*	100	A-23	E26	4000	3700	5.44/138.0	H38	12,000	25
15356	H39KB-175	175	ED-28	E39	7350	6800	8.31/211.1	H39	12,000	26
15355	H39KC-175/DX	175	ED-28	E39	7665	3700	8.31/211.1	H39	12,000	26
15358	H37KB-250	250	ED-28	E39	11000	6700	8.31/211.1	H37	18,000	26
15357	H37KC-250/DX	250	ED-28	E39	11550	3700	8.31/211.1	H37	18,000	26
15360	H33CD-400	400	ED-37	E39	21000	6500	11.50/292.1	H33	18,000	27
15359	H33GL-400/DX	400	ED-37	E39	22050	3700	11.50/292.1	H33	18,000	27
15350	H46DL-40/50/DX	40/50	ED-17	E26	1570	3200	5.12/130.0	H45/46	8,000	23

Lamps contain mercury - please dispose of properly.



*Closeout item: available while supplies last.



Halogen Lamps

EIKO's commercial grade Halogen Lamps feature high-grade, heavy-gauge glass, high output halogen burners, premium gas mixtures, quality reflector coatings, linear beam patterns, and superior construction quality. The result? A reliable, high performance product that lowers your overall cost. Halogen lamps provide a whiter, brighter light that saves up to 30% in energy costs when compared to incandescent lamps.

EiKON™ Energy Efficient Halogen IR PAR30

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
08206	IR53PAR30/FL	53	120	E26	CC-8	1050	3.66/93	3.74/95	35	4,000	1
08205	IR53PAR30/NFL	53	120	E26	CC-8	1050	3.66/93	3.74/95	25	4,000	1
08204	IR53PAR30/SP	53	120	E26	CC-8	1050	3.66/93	3.74/95	10	4,000	1

EiKON™ Energy Efficient Halogen IR PAR30LN

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
08208	IR53PAR30LN/NFL	53	120	E26	CC-8	930	4.76/121	3.74/95	25	4,000	2
08209	IR53PAR30LN/WFL	53	120	E26	CC-8	930	4.76/121	3.74/95	50	4,000	2
08207	IR53PAR30LN/SP*	53	120	E26	CC-8	930	4.76/121	3.74/95	10	4,000	2

EiKON™ Energy Efficient Halogen IR PAR38

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
08210	IR53PAR38/FL	53	120	E26	CC-8	960	5.51/140	4.80/122	25	4,000	3
08211	IR71PAR38/FL	71	120	E26	CC-8	1370	5.51/140	4.80/122	25	4,000	3
08212	IR71PAR38/SP*	71	120	E26	CC-8	1370	5.51/140	4.80/122	10	4,000	3



EiKON™ Energy Efficient Halogen Silver PAR20

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
08019	35PAR20/H/NFL-120V	35	120	E26	CC-8	530	3.11/79	2.48/63	30	1,500	4
08020	35PAR20/H/SP-120V	35	120	E26	CC-8	530	3.11/79	2.48/63	15	1,500	4

EiKON™ Energy Efficient Halogen Silver PAR30

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
08021	35PAR30/H/FL-120V	35	120	E26	CC-8	530	3.54/90	3.74/95	30	1,500	5
08137	60PAR30/H/FL-120V	60	120	E26	CC-8	1070	3.54/90	3.74/95	30	1,500	5
08138	60PAR30/H/NFL-120V	60	120	E26	CC-8	1070	3.54/90	3.74/95	25	1,500	5
08139	60PAR30/H/SP-120V	60	120	E26	CC-8	1070	3.54/90	3.74/95	15	1,500	5

EiKON™ Energy Efficient Halogen Silver PAR30LN

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
08023	35PAR30LN/H/FL-120V	35	120	E26	CC-8	530	4.69/119	3.74/95	30	1,500	6
08024	35PAR30LN/H/NFL-120V	35	120	E26	CC-8	530	4.69/119	3.74/95	25	1,500	6
08025	35PAR30LN/H/SP-120V*	35	120	E26	CC-8	530	4.69/119	3.74/95	15	1,500	6
08140	60PAR30LN/H/FL-120V	60	120	E26	CC-8	1070	4.69/119	3.74/95	30	1,500	6
08141	60PAR30LN/H/NFL-120V	60	120	E26	CC-8	1070	4.69/119	3.74/95	25	1,500	6
08142	60PAR30LN/H/SP-120V	60	120	E26	CC-8	1070	4.69/119	3.74/95	15	1,500	6

EiKON™ Energy Efficient Halogen Silver PAR38

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
08018	35PAR38/H/FL-120V	35	120	E26	CC-8	530	5.2/132	4.8/122	30	1,500	7
08026	35PAR38/H/SP-120V*	35	120	E26	CC-8	530	5.2/132	4.8/122	15	1,500	7
08143	60PAR38/H/FL-120V	60	120	E26	CC-8	1070	5.2/132	4.8/122	30	1,500	7
08144	60PAR38/H/SP-120V	60	120	E26	CC-8	1070	5.2/132	4.8/122	15	1,500	7
08145	60PAR38/H/WFL-120V	60	120	E26	CC-8	1070	5.2/132	4.8/122	50	1,500	7
08187	70PAR38/H/FL-120V	70	120	E26	CC-8	1305	5.2/132	4.8/122	30	1,500	7
08152	70PAR38/H/SP-120V	70	120	E26	CC-8	1305	5.2/132	4.8/122	15	1,500	7
08153	70PAR38/H/WFL-120V	70	120	E26	CC-8	1305	5.2/132	4.8/122	50	1,500	7

EiKON™ Energy Efficient Halogen A-Line

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
07757	29A/CL/H-120V*	29	120	E26	CC-8	430	4.25/108	2.36/60	1,000	8
07758	43A/CL/H-120V*	43	120	E26	CC-8	750	4.25/108	2.36/60	1,000	8
07759	53A/CL/H-120V	53	120	E26	CC-8	1050	4.25/108	2.36/60	1,000	8
07760	72A/CL/H-120V	72	120	E26	CC-8	1490	4.25/108	2.36/60	1,000	8



Halogen

Classic BT15 Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
81141	150BT15/H/W	150	120	E26	CC-8	2850	4.0/101	1.9/48.3	1,500	9

MR8 Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
05042	Q20MR8/NFL/CG*	20	12	GU4	C-8	156/39.5	0.99/25.2	20	2,000	10

MR8 Supreme Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
49407	49407*	20	12	GU4	C-8	156/39.5	0.99/25.2	10	2,000	10
49408	49408	20	12	GU4	C-8	156/39.5	0.99/25.2	23	2,000	10

MR11 Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15115	FTA	12	12	GU4	C-8	138/35.0	1.39/35.3	10	2,000	11
15120	FTB	20	12	GU4	C-8	138/35.0	1.39/35.3	10	2,000	11
15140	FTB-FG	20	12	GU4	C-8	156/39.5	1.41/35.8	10	2,000	11
15122	FTC	20	12	GU4	C-8	138/35.0	1.39/35.3	20	2,000	11
15142	FTC-FG	20	12	GU4	C-8	156/39.5	1.41/35.8	20	2,000	11
15124	FTD	20	12	GU4	C-8	138/35.0	1.39/35.3	30	2,000	11
15144	FTD-FG	20	12	GU4	C-8	156/39.5	1.41/35.8	30	2,000	11
15126	FTE	35	12	GU4	C-8	138/35.0	1.39/35.3	10	2,000	11
15146	FTE-FG	35	12	GU4	C-8	156/39.5	1.41/35.8	10	2,000	11
15128	FTF	35	12	GU4	C-8	138/35.0	1.39/35.3	20	2,000	11
15148	FTF-FG	35	12	GU4	C-8	156/39.5	1.41/35.8	20	2,000	11
15130	FTH	35	12	GU4	C-8	138/35.0	1.39/35.3	30	2,000	11
15150	FTH-FG	35	12	GU4	C-8	156/39.5	1.41/35.8	30	2,000	11

MR16 Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15030	BAB	20	12	GU5.3	C-8	181/46.0	2.00/50.8	38	3,000	12
81109	BAB-BLACK	20	12	GU5.3	C-8	181/46.0	2.00/50.8	38	3,000	12
15070	BAB-FG	20	12	GU5.3	C-8	199/50.5	2.00/50.8	38	3,000	12
05373	BAB-FG-GU10-120V	20	120	GU10	8-Style	2.20/56	2.00/51	38	3,000	12
81108	BAB-SILVER	20	12	GU5.3	C-8	181/46.0	2.00/50.8	38	3,000	12
15032	ESX	20	12	GU5.3	C-8	1.75/44.5	2.00/50.8	12	3,000	12
15072	ESX-FG	20	12	GU5.3	C-8	199/50.5	2.00/50.8	12	3,000	12
15047	FMT	35	12	GU5.3	C-8	181/46.0	2.00/50.8	12	4,000	12
15053	FMT-FG	35	12	GU5.3	C-8	199/50.5	2.00/50.8	12	4,000	12
15049	FMV	35	12	GU5.3	C-8	181/46.0	2.00/50.8	24	4,000	12
15055	FMV-FG	35	12	GU5.3	C-8	199/50.5	2.00/50.8	24	4,000	12

Continued on next page >>>



Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15051	FMW	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	38	4,000	12
81111	FMW-BLACK	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	38	4,000	12
15057	FMW-FG	35	12	GU5.3	C-8	1.99/50.5	2.00/50.8	38	4,000	12
00009	FMW-FG-GU10-130V	35	130	GU10	8-Style	2.20/56	2.20/50.8	38	2,000	12
81110	FMW-SILVER	35	12	GU5.3	C-8	1.81/46.0	2.00/50.8	38	4,000	12
49433	FRA-FG	35	12	GU5.3	C-8	1.99/50.5	2.00/50.8	18	4,000	12
15038	EYS	42	12	GU5.3	C-8	1.75/44.5	2.00/50.8	24	4,000	12
15040	ENL	50	12	GU5.3	C-8	1.75/44.5	2.00/50.8	24	4,000	12
15042	EXN	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	38	4,000	12
81115	EXN-BLACK	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	38	4,000	12
15080	EXN-FG	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	38	4,000	12
49565	EXN-FG-24V	50	24	GU5.3	C-8	1.99/50.5	2.00/50.8	38	4,000	12
00305	EXN-FG-GU10-130V	50	130	GU10	8-Style	2.20/56	2.20/50.8	38	3,500	12
81114	EXN-SILVER	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	38	4,000	12
15044	EXT	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	12	4,000	12
15082	EXT-FG	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	12	4,000	12
49566	EXT-FG-24V	50	24	GU5.3	C-8	1.99/50.5	2.00/50.8	12	4,000	12
15046	EXZ	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	24	4,000	12
81113	EXZ-BLACK	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	24	4,000	12
15084	EXZ-FG	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	24	4,000	12
81112	EXZ-SILVER*	50	12	GU5.3	C-8	1.77/45.0	2.00/50.8	24	4,000	12
15048	FNC-FG*	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	12	4,000	12
15050	FND-FG	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	12	4,000	12
15052	FNE-FG	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	12	4,000	12
15054	FNF-FG	50	12	GU5.3	C-8	1.99/50.5	2.00/50.8	12	4,000	12
00296	FNV	50	12	GU5.3	C-8	1.75/44.5	2.00/50.8	60	3,000	12
00297	FNV-FG	50	12	GU5.3	C-8	1.75/44.5	2.00/50.8	60	3,000	12
15056	FPA	65	12	GU5.3	C-8	1.81/46.0	2.00/50.8	12	4,000	12
15086	FPA-FG	65	12	GU5.3	C-8	1.99/50.5	2.00/50.8	12	4,000	12
15058	FPB	65	12	GU5.3	C-8	1.81/46.0	2.00/50.8	38	4,000	12
15088	FPB-FG	65	12	GU5.3	C-8	1.99/50.5	2.00/50.8	38	4,000	12
15060	FPC	65	12	GU5.3	C-8	1.81/46.0	2.00/50.8	24	4,000	12
15090	FPC-FG	65	12	GU5.3	C-8	1.85/47.0	2.00/50.8	24	4,000	12
15062	EYC	75	12	GU5.3	C-8	1.75/44.5	2.00/50.8	38	4,000	12
15092	EYC-FG	75	12	GU5.3	C-8	1.99/50.5	2.00/50.8	38	4,000	12
15064	EYF	75	12	GU5.3	C-8	1.75/44.5	2.00/50.8	12	4,000	12
15066	EYJ	75	12	GU5.3	C-8	1.75/44.5	2.00/50.8	24	4,000	12

MR16 Screw Base Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
00211	JDR130V50W	50	130	E26	C-6Z	2.84/72.0	2.00/50.8	30	2,000	13
15100	FSA	75	120	E17	CC-8	2.75/69.9	2.00/50.8	12	2,000	13
15102	FSB	75	120	E17	CC-8	2.75/69.9	2.00/50.8	20	2,000	13
15106	FSD	75	120	E17	CC-8	2.75/69.9	2.00/50.8	30	2,000	13
10453	JDR75/FL	75	120	E26	CC-8	2.84/72.0	2.00/50.8	30	2,000	13
10452	JDR75/MF	75	120	E26	CC-8	2.84/72.0	2.00/50.8	20	2,000	13
10451	JDR75/SP	75	120	E26	CC-8	2.84/72.0	2.00/50.8	12	2,000	13
15104	FSC	100	120	E17	CC-8	2.75/69.9	2.00/50.8	12	2,000	13
15108	FSE	100	120	E17	CC-8	2.75/69.9	2.00/50.8	20	2,000	13
15110	FSF	100	120	E17	CC-8	2.75/69.9	2.00/50.8	30	2,000	13
05426	JDR100/FL	100	120	E26	CC-8	2.84/72.0	2.00/50.8	30	1,500	13

Halogen

MR16 Line Voltage Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
05373	BAB-FG-GU10-120V	20	120	GU10	8-Style	2.20/56	2.00/51	38	3,000	14
00009	FMW-FG-GU10-130V	35	130	GU10	8-Style	2.20/56	2.20/50.8	38	2,000	14
00305	EXN-FG-GU10-130V	50	130	GU10	8-Style	2.20/56	2.20/50.8	38	3,500	14

37mm Diameter Aluminized Reflector Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
49861	GBD	20	12	BA15d	C-8	1.63/41.4	1.39/35.3	6	2,000	15
49862	GBE	20	12	BA15d	C-8	1.63/41.4	1.39/35.3	18	2,000	15
49664	GBF	20	12	BA15d	C-8	1.63/41.4	1.39/35.3	32	2,000	15
49665	GBF-FR	20	12	BA15d	C-8	1.63/41.4	1.39/35.3	32	2,000	15

56mm Diameter Aluminized Reflector Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
49863	GBJ*	50	12	BA15d	C-8	2.25/57.2	2.25/57.2	10	2,000	15

Single Ended Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
00212	Q50CL/DC-130V	50	130	BA15d	CC-8	650	2.18/55.4	0.52/13.0	2,000	16
00213	Q50CL/MC-130V	50	130	E11	CC-8	650	2.56/65.0	0.52/13.0	2,000	16
15215	Q75CL-120V	75	120	E11	CC-8	1200	2.50/63.5	0.44/11.0	2,000	16
49567	Q75CL-130V	75	130	E11	CC-8	1200	2.50/63.5	0.44/11.0	2,000	16
15217	Q75CL/DC-120V	75	120	BA15d	CC-8	1350	2.38/60.3	0.47/12.0	2,000	16
15287	Q75MC-120V	75	120	E11	C-8	1170	2.56/65.0	0.52/13.0	1,000	16
15220	Q100/DC-120V	100	120	BA15d	CC-8	1500	2.44/61.9	0.52/13.0	2,000	16
15234	Q100/MC-120V	100	120	E11	CC-8	1500	2.84/72.0	0.52/13.0	2,000	16
15219	Q100CL/DC-120V	100	120	BA15d	CC-8	1500	2.44/61.9	0.52/13.0	2,000	16
49600	Q100CL/DC/2V-120V	100	120	BA15d	CC-2V	1500	2.44/61.9	0.55/14.0	1,000	16
15230	Q100CL/DC/2V-130V	100	130	BA15d	CC-2V	1500	2.44/61.9	0.52/13.0	2,000	16
15232	Q100CL/MC-120V	100	120	E11	CC-8	1500	2.84/72.0	0.52/13.0	2,000	16
15236	Q100CL/MC/2V-130V	100	130	E11	CC-2V	1500	2.84/72.0	0.52/13.0	2,000	16
49596	Q100DC/2V-120V	100	120	BA15d	CC-2V	1500	2.44/61.9	0.52/13.0	2,000	16
49604	Q150CL/DC-120V	150	120	BA15d	CC-8	2800	2.44/61.9	0.52/13.0	2,000	16
15250	Q150CL/DC-130V	150	130	BA15d	CC-8	2800	2.44/61.9	0.52/13.0	2,000	16
49601	Q150CL/MC-120V	150	120	E11	CC-8	2600	3.00/76.2	0.55/14.0	2,000	16
15239	Q150CL/MC-130V	150	130	E11	CC-8	2600	3.00/76.2	0.55/14.0	2,000	16
15252	Q150CL/MC/2V-130V	150	130	E11	CC-2V	2800	2.84/72.0	0.52/13.0	1,000	16
49602	Q150DC-120V	150	120	BA15d	CC-8	2700	2.68/68.0	0.52/13.0	2,000	16
49610	Q250CL/DC-120V	250	120	BA15d	CC-8	5000	3.15/80.0	0.55/14.0	2,000	16
15264	Q250CL/DC-130V	250	130	BA15d	CC-8	5000	3.00/76.2	0.52/13.0	2,000	16
49609	Q250CL/MC-120V	250	120	E11	CC-8	5000	3.15/80.0	0.52/13.0	2,000	16

Continued on next page >>>



Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15268	Q250CL/MC-130V	250	130	E11	CC-8	5000	3.15/80.0	0.52/13.0	2,000	16
49607	Q250DC-120V	250	120	BA15d	CC-8	4700	3.15/80.0	0.55/14.0	2,000	16
15266	Q250DC-130V*	250	130	BA15d	CC-8	4800	3.00/76.2	0.52/13.0	2,000	16
49608	Q250MC-120V	250	120	E11	CC-8	4800	3.19/81.0	0.52/13.0	2,000	16
15270	Q250MC-130V	250	130	E11	CC-8	4800	3.19/81.0	0.52/13.0	2,000	16
49612	Q500/MC-120V	500	120	E11	CC-8	8800	3.75/95.3	0.52/13.0	1,700	16
49614	Q500/MC-130V	500	130	E11	CC-8	8800	3.75/95.3	0.52/13.0	1,700	16
15282	Q500CL/DC-120V	500	120	BA15d	CC-8	8800	3.75/95.3	0.59/15.0	1,700	16
49613	Q500CL/MC-120V	500	120	E11	CC-8	8800	3.75/95.3	0.55/14.0	1,700	16
49615	Q500CL/MC-130V	500	130	E11	CC-8	8800	3.75/95.3	0.52/13.0	1,700	16

Double Ended Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15161	Q150T3/CL/120V	150	120	R7s	CC-8	2200	4.69/119.1	0.40/10.0	2,000	17
15162	Q250T3/CL/120V	250	120	R7s	C-8	3500	4.69/119.1	0.40/10.0	2,000	17
15164	Q300T3/CL/120V	300	120	R7s	C-8	4800	4.69/119.1	0.40/10.0	2,000	17
15166	Q300T3/CL/130V	300	130	R7s	C-8	4800	4.69/119.1	0.40/10.0	2,000	17
15168	Q300T3/CL/220V	300	220	R7s	C-8	4500	4.69/119.1	0.40/10.0	2,000	17
00196	Q300T3/CL/240V	300	240	R7s	C-8	4500	4.69/119.1	0.40/10.0	2,000	17
15170	Q500T3/CL/120V	500	120	R7s	C-8	10000	4.69/119.1	0.40/10.0	2,000	17
15172	Q500T3/CL/130V	500	130	R7s	C-8	9500	4.69/119.1	0.40/10.0	2,000	17
15174	Q500T3/CL/220V	500	220	R7s	C-8	9000	4.69/119.1	0.40/10.0	2,000	17
15176	Q500T3/CL/240V	500	240	R7s	C-8	9000	4.69/119.1	0.40/10.0	2,000	17
49568	Q750T3/CL/120V	750	120	R7s	C-8	15000	7.50/190.5	0.40/10.0	2,000	17
15180	Q750T3/CL/240V	750	240	R7s	C-8	16500	7.50/190.5	0.40/10.0	2,000	17
49569	Q1000T3/CL/120V	1000	120	R7s	C-8	22000	10.06/255.6	0.40/10.0	2,000	17
15184	Q1000T3/CL/240V	1000	240	R7s	C-8	21000	10.06/255.6	0.40/10.0	2,000	17
15186	Q1000T3/CL/277V	1000	277	R7s	C-8	22000	10.06/255.6	0.40/10.0	2,000	17
49570	Q1500T3/CL/120V	1500	120	R7s	CC-8	33000	10.06/255.6	0.40/10.0	2,000	17
15188	Q1500T3/CL/208V	1500	208	R7s	C-8	32000	10.06/255.6	0.40/10.0	2,000	17
15190	Q1500T3/CL/220V	1500	220	R7s	CC-8	32000	10.06/255.6	0.40/10.0	2,000	17
15192	Q1500T3/CL/240V	1500	240	R7s	CC-8	32000	10.06/255.6	0.40/10.0	2,000	17
15194	Q1500T3/CL/277V	1500	277	R7s	CC-8	34000	10.06/255.6	0.40/10.0	2,000	17

Double Ended Short Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15200	Q100W/S120V	100	120	R7s	C-8	1300	3.15/80.0	0.315/8.0	2,000	17
15202	Q100W/S130V	100	130	R7s	C-8	1300	3.15/80.0	0.315/8.0	2,000	17
15206	Q150W/S120V	150	120	R7s	C-8	2200	3.15/80.0	0.344/8.74	2,000	17
15208	Q150W/S130V	150	130	R7s	C-8	2200	3.15/80.0	0.344/8.74	2,000	17
15211	Q200W/S120V	200	120	R7s	C-8	3000	3.15/80.0	0.344/8.74	2,000	17
15213	Q200W/S130V	200	130	R7s	C-8	3000	3.15/80.0	0.344/8.74	2,000	17
15209	Q200W/S220V	200	220	R7s	CC-8	3000	3.15/80.0	0.344/8.74	2,000	17
49571	Q250W/S120V	250	120	R7s	CC-8	3500	3.15/80.0	0.360/9.13	2,000	17
00019	Q300W/S120V	300	120	R7s	CC-8	4100	3.15/80.0	0.360/9.13	2,000	17
15216	Q300W/S130V	300	130	R7s	CC-8	4100	3.15/80.0	0.360/9.13	2,000	17
15221	Q400W/S130V*	400	130	R7s	C-8	5500	3.15/80.0	0.406/10.32	2,000	17

Halogen

G4 Base 2-Pin Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
81120	JCD12V5W-FR	5	12	G4	C-6	60	1.38/35.0	0.36/9.0	2,000	18
15005	JCD12V5WH20	5	12	G4	C-6	60	1.22/31.0	0.32/8.2	2,000	18
15007	JCD12V10WH20	10	12	G4	C-6	150	1.22/31.0	0.36/9.0	2,000	18
15001	JCD6V10WH20	10	6	G4	C-6	150	1.22/31.0	0.36/9.0	2,000	18
03510	JCD12V20W	20	12	G4	C-6	350	1.38/35.0	0.36/9.0	50	18
15009	JCD12V20WH20	20	12	G4	C-6	300	1.22/31.0	0.36/9.0	2,000	18
15011	JCD24V20WH20	20	24	G4	CC-6	280	1.22/31.0	0.32/8.2	2,000	18
15003	JCD6V20WH20	20	6	G4	C-6	300	1.22/31.0	0.36/9.0	2,000	18
03520	JCD12V30W	30	12	G4	C-6	800	1.22/31.0	0.36/9.0	50	18
49561	JCD12V35WH20	35	12	G4	CC-6	650	1.22/31.0	0.36/9.0	2,000	18

G6.35 Base 2-Pin Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15013	JCD12V20WH20	20	12	G6.35	C-6	350	1.73/44.0	0.46/11.5	2,000	19
15015	JCD12V30WH20	30	12	G6.35	C-6	560	1.73/44.0	0.46/11.5	2,000	19
15017	JCD12V35WH20	35	12	G6.35	C-6	600	1.73/44.0	0.46/11.5	2,000	19
15019	JCD12V50WH20	50	12	G6.35	C-8	950	1.73/44.0	0.46/11.5	2,000	19
15021	JCD12V75WH20	75	12	G6.35	C-6	1600	1.73/44.0	0.46/11.5	2,000	19
15023	JCD12V100WH20	100	12	G6.35	C-6	2000	1.73/44.0	0.51/13.0	1,200	19

Bi-Pin Line Voltage Halogen Lamps

Order Code	Item	W	V	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
00307	JCD130V20WG6.35	20	130	G6.35	CC-6V	130	1.44/36.5	0.52/13	1,500	20
00314	JCD130V20WG8	20	130	G8	CC-6V	130	1.44/36.5	0.52/13	1,500	20
00308	JCD130V25WG6.35	25	130	G6.35	CC-6V	170	1.44/36.5	0.52/13	1,500	20
00315	JCD130V25WG8	25	130	G8	CC-6V	170	1.44/36.5	0.52/13	1,500	20
00321	JCD130V25WG9	25	130	G9	4-Style	180	1.81/46	0.52/13	2,000	20
00326	JCD130V25WG9/F	25	130	G9	4-Style	170	1.81/46	0.52/13	2,000	20
00309	JCD130V35WG6.35	35	130	G6.35	CC-6V	380	1.77/45	0.52/13	2,000	20
00316	JCD130V35WG8	35	130	G8	CC-6V	380	1.77/45	0.52/13	2,000	20
00322	JCD130V40WG9	40	130	G9	4-Style	400	1.81/46	0.52/13	2,000	20
00327	JCD130V40WG9/F	40	130	G9	4-Style	380	1.81/46	0.52/13	2,000	20
00311	JCD130V50WG6.35	50	130	G6.35	CC-2V	600	1.77/45	0.52/13	2,000	20
00317	JCD130V50WG8	50	130	G8	CC-2V	600	1.77/45	0.52/13	2,000	20
00323	JCD130V50WG9	50	130	G9	4-Style	550	1.81/46	0.52/13	2,000	20
00328	JCD130V50WG9/F	50	130	G9	4-Style	500	1.81/46	0.52/13	2,000	20
00324	JCD130V60WG9	60	130	G9	4-Style	720	1.93/49	0.52/13	1,500	20
00329	JCD130V60WG9/F	60	130	G9	4-Style	680	1.93/49	0.52/13	1,500	20
00312	JCD130V75WG6.35*	75	130	G6.35	CC-7A	930	1.77/45	0.52/13	2,000	20
00318	JCD130V75WG8	75	130	G8	CC-7A	930	1.77/45	0.52/13	2,000	20
00325	JCD130V75WG9	75	130	G9	4-Style	900	1.93/49	0.52/13	1,500	20
00331	JCD130V75WG9/F	75	130	G9	4-Style	850	1.93/49	0.52/13	1,500	20
00319	JCD130V100WG8	100	130	G8	CC-7A	1450	1.97/50	0.53/13.5	1,500	20



Halogen Heat Lamps

Order Code	Item	W	V	Base	Fil	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
17002	17002*	375	115-125	6 in Leads	C-8	8.82/224.0	0.40/10.0	5,000	21
17004	17004	375	115-125	R7s	C-8	8.70/221.0	0.40/10.0	5,000	21
17006	17006*	500	115-125	6 in Leads	C-8	8.82/224.0	0.40/10.0	5,000	21
17008	17008	500	115-125	6 in Leads	C-8	8.82/224.0	0.40/10.0	5,000	21
17010	17010	500	115-125	R7s	C-8	8.70/221.0	0.40/10.0	5,000	21
17012	17012*	1000	200-220	6 in Leads	C-8	13.78/350.0	0.40/10.0	5,000	21
17014	17014	1000	230-250	6 in Leads	C-8	13.78/350.0	0.40/10.0	5,000	21
17016	17016	1000	230-250	6 in Leads	C-8	11.89/302.0	0.40/10.0	5,000	21
17018	17018*	1000	230-250	6 in Leads	C-8	13.78/350.0	0.40/10.0	5,000	21
17022	17022*	1200	144	6 in Leads	C-8	8.82/224.0	0.40/10.0	5,000	21
17030	17030	1600	230-250	6 in Leads	C-8	19.80/503.0	0.40/10.0	5,000	21
17032	17032*	1600	200-220	R7s	C-8	19.63/498.5	0.40/10.0	5,000	21
17040	17040	2000	230-250	6 in Leads	C-8	13.78/350.0	0.40/10.0	5,000	21
17042	17042*	2500	460-500	6 in Leads	C-8	28.82/732	0.40/10.0	5,000	21
17046	17046	2500	460-500	6 in Leads	C-8	28.82/732	0.40/10.0	5,000	21
17048	17048	3650	480	6 in Leads	C-8	41.6/1057	0.40/10.0	5,000	21
17050	17050*	3800	550-600	6 in Leads	C-8	41.8/1062	0.40/10.0	5,000	21
17052	17052*	3800	550-600	6 in Leads	C-8	41.8/1062	0.40/10.0	5,000	21

SoLux® MR16 3500K Halogen Lamps

Order Code	Item	W	V	Base	Fil	CRI	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
35006	35006*	35	12	GU5.3	C-8	98+	1.77/45	1.97/50	10	4,000	22
35008	35008	35	12	GU5.3	C-8	98+	1.77/45	1.97/50	36	4,000	22
18007	18007	50	12	GU5.3	C-8	98+	1.77/45	1.97/50	17	4,000	22
18008	18008	50	12	GU5.3	C-8	98+	1.77/45	1.97/50	36	4,000	22
18009	18009	50	12	GU5.3	C-8	98+	1.77/45	1.97/50	24	4,000	22

SoLux® MR16 4100K Halogen Lamps

Order Code	Item	W	V	Base	Fil	CRI	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
35011	35011*	35	12	GU5.3	C-8	98+	1.77/45	1.97/50	10	4,000	22
35012	35012*	35	12	GU5.3	C-8	98+	1.77/45	1.97/50	17	4,000	22
18011	18011*	50	12	GU5.3	C-8	98+	1.77/45	1.97/50	10	4,000	22
18012	18012	50	12	GU5.3	C-8	98+	1.77/45	1.97/50	17	4,000	22
18014	18014	50	12	GU5.3	C-8	98+	1.77/45	1.97/50	24	4,000	22

SoLux® MR16 4700K Halogen Lamps

Order Code	Item	W	V	Base	Fil	CRI	MOL in/mm	MOD in/mm	Bm	Life/Hrs	Photo #
35001	35001*	35	12	GU5.3	C-8	99+	1.77/45	1.97/50	10	4,000	22
35002	35002*	35	12	GU5.3	C-8	99+	1.77/45	1.97/50	17	4,000	22
35003	35003	35	12	GU5.3	C-8	99+	1.77/45	1.97/50	36	4,000	22
35004	35004*	35	12	GU5.3	C-8	99+	1.77/45	1.97/50	24	4,000	22
18002	18002*	50	12	GU5.3	C-8	99+	1.77/45	1.97/50	17	4,000	22
18003	18003	50	12	GU5.3	C-8	99+	1.77/45	1.97/50	36	4,000	22



Incandescent Lamps

Incandescent lamps are still commonly used in homes and businesses, and with our wide selection, we have enough shapes, wattages, and finishes to fit almost every application and need. Many of our incandescent lamps are also available in an extended life, 130 volt version, with even more energy efficient alternatives coming soon!

A-Shaped Incandescent Appliance Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
44390	40A15-130V	40	130	A-15	E26	C-2V	435	3.5/89	1.9/48	1,500	1
44394	40A15-230/250V	40	230-250	A-15	E26	C-2F	435	3.5/89	1.9/48	1,500	1
44392	40A15/F-130V	40	130	A-15	E26	C-2V	435	3.5/89	1.9/48	1,500	1
44396	40A15/F-230/250V	40	230-250	A-15	E26	2CC-9	435	3.5/89	1.9/48	1,500	1

Rough Service Incandescent Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
15800	50A/RS	50	130	A-19	E26	C-9	380	4.44/112.8	2.38/60.3	5,000	2
15812	50A/RS-12V	50	12	A-19	E26	C-6	500	4.44/112.8	2.38/60.3	2,500	2
15806	50A/RS/TF	50	130	A-19	E26	C-9	350	4.44/112.8	2.38/60.3	5,000	2
15802	75A/RS	75	130	A-19	E26	C-9	700	4.44/112.8	2.38/60.3	5,000	2
15814	75A/RS-12V	75	12	A-19	E26	C-6	750	4.44/112.8	2.38/60.3	2,500	2
15808	75A/RS/TF	75	130	A-19	E26	C-9	660	4.44/112.8	2.38/60.3	5,000	2
15804	100A/RS	100	130	A-19	E26	C-9	1050	4.44/112.8	2.38/60.3	5,000	2
15816	100A/RS-12V	100	12	A-19	E26	C-6	1100	4.44/112.8	2.38/60.3	2,500	2
15810	100A/RS/TF	100	130	A-19	E26	C-9	1000	4.44/112.8	2.38/60.3	5,000	2
00008	150A/RS	150	130	A-21	E26	C-9	1650	4.96/126	2.63/66.7	5,000	2
01863	150A/RS/TF	150	130	A-21	E26	C-9	1650	4.96/126	2.63/66.7	5,000	2



C-Shaped Incandescent Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
40353	4C7/120V	4	120	C-7	E12	C-7A	20	2.30/58.4	0.88/22.3	3,000	3
40351	4C7/130V	4	130	C-7	E12	C-7A	15	2.30/58.4	0.88/22.3	3,000	3
40874	7C7/120V	7	120	C-7	E12	C-7A	37	2.30/58.4	0.88/22.3	3,000	3
40875	7C7/130V	7	130	C-7	E12	C-7A	35	2.30/58.4	0.88/22.3	3,000	3
44318	7C7/130V-W	7	130	C-7	E12	C-7A	n/a	2.30/58.4	0.88/22.3	3,000	3
01709	7C9-120V-INT	7	120	C-9	E17	C-5A	45	3.9/99	1.15/29.2	3,000	3
40073	10C7/120V	10	120	C-7	E12	C-7A	64	2.30/58.4	0.88/22.3	5000+	3
40154	10C7DC/120V	10	120	C-7	BA15d	C-7A	64	2.13/54.1	0.88/22.3	5000+	3

R&BR Incandescent Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	Life/Hrs	Photo #
49792	30R20/FL-130V	30	130	R-20	E26	CC-6	245	3.94/100	5000 Hrs at 120v	4
49797	45BR30/FL-120V	45	120	BR-30	E26	CC-6	390	5.38/136.7	2,000	5
05986	45R20/FL-120V	45	120	R-20	E26	CC-6	360	3.94/100	2,000	4
05987	45R20/FL-130V	45	130	R-20	E26	CC-6	340	3.94/100	5000 Hrs at 120v	4
49798	65BR30/FL-120V	65	120	BR-30	E26	CC-6	620	5.38/136.7	2,000	5
49799	65BR30/FL-130V	65	130	BR-30	E26	CC-6	620	5.38/136.7	5000 Hrs at 120v	5
49811	65BR30/SP-120V	65	120	BR-30	E26	CC-6	620	5.38/136.7	2,000	5
49800	65BR30/SP-130V	65	130	BR-30	E26	CC-6	620	5.38/136.7	5000 Hrs at 120v	5
49801	65BR40/FL-120V	65	120	BR-40	E26	CC-6	620	6.56/166.6	2,000	6
49802	65BR40/FL-130V	65	130	BR-40	E26	CC-6	620	6.56/166.6	5000 Hrs at 120v	6

S-Shaped Incandescent Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
40552	3S6/5-120V	3	120	S-6	E12	C-7A	11.31	1.88/47.8	0.75/19.1	1,500	7
40554	3S6/5-130V	3	130	S-6	E12	C-7A	11.31	1.88/47.8	0.75/19.1	1,500	7
40556	3S6/5DC-120V	3	120	S-6	BA15d	C-7A	11.31	1.82/46.2	0.75/19.1	3,000	7
40786	6S6/120V	6	120	S-6	E12	C-7A	39	1.88/47.8	0.75/19.1	1,500	7
40784	6S6/12V	6	12	S-6	E12	C-6	48	1.88/47.8	0.75/19.1	1,500	7
40788	6S6/130V	6	130	S-6	E12	C-7A	38	1.88/47.8	0.75/19.1	1,500	7
40789	6S6/145V	6	145	S-6	E12	C-7A	17.60	1.88/47.8	0.75/19.1	1,500	7
40790	6S6/155V	6	155	S-6	E12	C-7A	33	1.88/47.8	0.75/19.1	1,500	7
49717	6S6/18V	6	18	S-6	E12	C-6	50	1.88/47.8	0.75/19.1	1,500	7
40791	6S6/230V	6	230	S-6	E12	C-7A	11.31	1.88/47.8	0.75/19.1	1,500	7
40792	6S6/24V	6	24	S-6	E12	C-6	53	1.88/47.8	0.75/19.1	1,500	7
40794	6S6/30V	6	30	S-6	E12	C-6	52	1.88/47.8	0.75/19.1	1,500	7
40796	6S6/48V	6	48	S-6	E12	C-6	47	1.88/47.8	0.75/19.1	1,500	7
40800	6S6/60V	6	60	S-6	E12	C-7A	43	1.88/47.8	0.75/19.1	1,500	7
40798	6S6/6V	6	6	S-6	E12	C-6	54	1.88/47.8	0.75/19.1	1,500	7
40804	6S6DC/120V	6	120	S-6	BA15d	C-7A	39	1.82/46.2	0.75/19.1	1,500	7
40802	6S6DC/12V	6	12	S-6	BA15d	C-6	48	1.82/46.2	0.75/19.1	1,500	7
40806	6S6DC/130V	6	130	S-6	BA15d	C-7A	38	1.82/46.2	0.75/19.1	1,500	7

Continued on next page >>>




Incandescent

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
40807	6S6DC/145V	6	145	S-6	BA15d	C-7A	17.60	1.82/46.2	0.75/19.1	1,500	7
40808	6S6DC/24V	6	24	S-6	BA15d	C-6	53	1.82/46.2	0.75/19.1	1,500	7
40810	6S6DC/30V	6	30	S-6	BA15d	C-6	52	1.82/46.2	0.75/19.1	1,500	7
40811	6S6DC/32V	6	32	S-6	BA15d	C-6	50	1.82/46.2	0.75/19.1	1,500	7
40812	6S6DC/48V	6	48	S-6	BA15d	C-6	47	1.82/46.2	0.75/19.1	1,500	7
40814	6S6DC/6V*	6	6	S-6	BA15d	C-6	54	1.82/46.2	0.75/19.1	1,500	7
00020	10S6/120V	10	120	S-6	E12	C-7A	60	1.88/47.8	0.75/19.1	1,500	7
42446	10S6/230V	10	230	S-6	E12	C-7A	60	1.88/47.8	0.75/19.1	1,500	7
16013	10S6/250V	10	250	S-6	E12	C-7A	60	1.88/47.8	0.75/19.1	1,500	7
40149	10S6DC/250V	10	250	S-6	BA15d	C-7A	60	1.82/46.2	0.75/19.1	1,500	7

T-Shaped Incandescent Lamps

Order Code	Item	Usage	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
16017	15T4C-130V		15	130	T-4	E12	C-7A	90	1.97/50.0	0.54/39.1	1,500	8
81134	15T6C-120V		15	120	T-6	E12	C-7A	90	3.06/77.7	0.77/19.6	2,000	8
43000	15T6C-130V		15	130	T-6	E12	C-7A	90	3.06/77.7	0.77/19.6	2,000	8
43002	15T6C-145V	Med/Sci	15	145	T-6	E12	C-7A	90	3.06/77.7	0.77/19.6	2000, (7500 @ 120V)	8
43006	15T7C-130V		15	130	T-7	E12	C-7A	90	2.25/57.2	0.89/22.6	1,500	8
43008	15T7DC-130V		15	130	T-7	BA15d	C-7A	90	2.25/57.2	0.89/22.6	1,500	8
43004	15T7N-130V		15	130	T-7	E17	C-7A	90	2.25/57.2	0.89/22.6	1,500	8
43014	20T6-1/2DC-130V		20	130	T-6 1/2	BA15d	C-8	180	5.56/141.2	0.83/21.1	3,000	8
43012	20T6-1/2F-130V		20	130	T-6 1/2	E17	C-8	170	5.5/139.7	0.83/21.1	3,000	8
43010	20T6-1/2N-130V		20	130	T-6 1/2	E17	C-8	180	5.5/139.7	0.83/21.1	3,000	8
44402	20T6-1/2N-145V		20	145	T-6 1/2	E17	C-8	170	5.5/139.7	0.83/21.1	3,000	8
43016	20T6.5DC/F-130V		20	130	T-6 1/2	BA15d	C-8	170	5.56/141.2	0.83/21.1	3,000	8
43034	25T10-130V		25	130	T-10	E26	C-5V	180	5.19/131.8	1.25/31.8	2,000	8
43036	25T10/F-130V		25	130	T-10	E26	C-8	200	5.19/131.8	1.25/31.8	1,500	8
43024	25T6-1/2DC-130V		25	130	T-6 1/2	BA15d	C-8	210	5.5/139.7	0.83/21.1	3,000	8
43020	25T6-1/2N-130V		25	130	T-6 1/2	E17	C-8	210	5.5/139.7	0.83/21.1	3,000	8
43022	25T6.5N/F-130V		25	130	T-6 1/2	E17	C-8	200	5.5/139.7	0.83/21.1	3,000	8
43018	25T6C-120V		25	120	T-6	E12	C-7A	190	3.06/77.7	0.77/19.6	2,000	8
43028	25T8C-120V	Appliance	25	120	T-8	E12	C-7A	180	2.63/66.8	1.04/26.4	1,500	8
49563	25T8DC-120V		25	120	T-8	BA15d	C-7A	180	2.63/66.8	1.04/26.4	1,500	8
43032	25T8DC-130V		25	130	T-8	BA15d	C-7A	180	2.63/66.8	1.04/26.4	1,500	8
43030	25T8N-130V	Appliance	25	130	T-8	E17	C-7A	180	2.63/66.8	1.04/26.4	1,500	8
43042	40T10-130V		40	130	T-10	E26	C-8	320	5.19/131.8	1.25/31.8	1,500	8
43044	40T10/F-130V		40	130	T-10	E26	C-8	310	5.19/131.8	1.25/31.8	1,500	8
43038	40T6-1/2N-130V		40	130	T-6 1/2	E17	C-8	330	5.5/139.7	0.83/21.1	1,500	8





Specialty Lamps

Our long-term reputation for high quality products ensures customers that our AV and photographic lamps - including modeling, photoflood, enlarger/printer lamps and flashtubes - and our healthcare, medical and scientific lamps - including hard-to-find lamps for microscopes, bronchoscopes, otoscopes, cystoscopes, esophagoscopes, ophthalmoscopes and retinoscopes - meet the exacting standards required by precision equipment.

ArcMaster™ SSTV Discharge Lamps

Order Code	Item	W	V	Base	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
04006	ESD250-SE-D*	250	95	GY9.5	18800	4.25/108	0.91/23	2,000	1
04007	ESD575-SE-D*	575	95	GX9.5	49000	4.92/125	1.18/30	2,000	1
04009	ESD575/2-SE-D7.2*	575	95	GX9.5	45000	4.92/125	1.18/30	1,000	N/A
04017	ESI575-DE*	575	95	SFc 10-4	49000	5.35/136	0.83/21	750	N/A
04013	ESR575-SE-HR*	575	95	G22	49000	5.71/145	1.18/30	750	2
04014	ESR800-SE-HR*	800	95	G22	64000	5.71/145	1.22/31	1,000	2
04018	ESI1200-DE*	1200	100	SFc 15.5-6	110000	8.66/220	1.1/28	750	N/A
04003	ESR1200-SE-NHR*	1200	100	G22	110000	6.89/175	1.57/40	750	3

ColorMaster™ Digital Imaging Lamps


Order Code	Item	W	V	Shape	Base	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
48045	SP30/955K	30	120	T-4	E26	6.3/160	2.76/70	10,000	4

Lamps contain mercury - please dispose of properly.

HPL Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
05913	HPL375/115V	375	115	T-6	G9.5 w/ Heatsink	4-C8	10540	3.86/98	0.72/18.4	300	5
05914	HPL375LL/115V	375	115	T-6	G9.5 w/ Heatsink	4-C8	8000	3.86/98	0.72/18.4	1,000	5

Continued on next page >>>



Specialty

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
05641	HPL550/77V*	550	77	T-6	G9.5 w/ Heatsink	4-C8	16170	3.86/98	0.72/18.4	300	5
05915	HPL550LL/77V*	550	77	T-6	G9.5 w/ Heatsink	4-C8	12160	3.86/98	0.72/18.4	2,000	5
10415	HPL575/115V	575	115	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300	5
05152	HPL575/120V	575	120	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300	5
05916	HPL575/230V*	575	230	T-6	G9.5 w/ Heatsink	6-C8	14900	3.86/98	0.72/18.4	400	5
10416	HPL575LL/115V	575	115	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2,000	5
05918	HPL575LL/120V	575	120	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2,000	5
10417	HPL750/115V	750	115	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300	5
05921	HPL750/120V	750	120	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300	5
05922	HPL750/230V*	750	230	T-6	G9.5 w/ Heatsink	6-C8	19750	4.09/104	0.72/18.4	300	5
05642	HPL750/77V*	750	77	T-6	G9.5 w/ Heatsink	4-C8	22950	3.86/98	0.72/18.4	300	5
05924	HPL750LL/115V*	750	115	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	1,500	5
05925	HPL750LL/120V*	750	120	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	2,000	5
05926	HPL750LL/230V*	750	230	T-6	G9.5 w/ Heatsink	6-C8	15600	4.09/104	0.72/18.4	1,500	5



Enlarger Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
03650	PH/111A*	75	120	S-11	BA15s	CC-2V	1120	2.38/60.3	1.38/35.0	25	6
03662	PH/140	75	120	S-14	E26	CC-2V	1150	3.38/86.0	1.73/44.0	50	7
03663	PH/211	75	115-125	A-21	E26	CC-2V	1000	4.94/125.4	2.60/66.0	100	8
02770	ESJ	85	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	40	9
02290	EJV	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40	9
02750	ESD	150	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	12	9
03664	PH/212	150	115-125	A-21	E26	CC-2V	2300	4.94/125.4	2.60/66.0	100	8
02260	EJL	200	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50	9
02940	EYA*	200	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50	9
02400	ELC	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50	9
02420	ELC/E*	250	24	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50	9
02570	ENH	250	120	MR16	GY5.3	CC-8	15000	1.75/44.5	2.00/50.8	175	9
02820	EVW	250	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50	9
02450	ELH	300	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	35	9
03020	FAL*	420	120	T-4	R7s	CC-8	11000	2.63/66.7	0.55/14.0	90	10

Modeling Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
03750	25T8/DC	25	120	T-8	BA15d	C-7A	195	2.63/66.7	0.99/25.0	200	11
15222	ESN	100	120	T-4	E11	CC-2V	1900	2.80/71.0	0.52/13.0	750	12
15226	ESR	100	120	T-4	BA15d	CC-2V	1900	2.44/61.9	0.55/14.0	1,000	12
15224	ETE	100	120	T-4	E11	CC-2V	1750	2.80/71.0	0.52/13.0	750	12
00251	150T10/H/F	150	120	T-10	E26	CC-8	2850	4.0/101	1.25/31.8	1,500	13
15240	ESL	150	120	T-4	E11	CC-2V	2800	2.80/71.0	0.52/13.0	1,000	12
15246	ESP	150	120	T-4	BA15d	CC-8	2400	2.44/61.9	0.55/14.0	1,000	12
15244	ETC	150	120	T-4	BA15d	CC-8	2800	2.44/61.9	0.52/13.0	2,000	12
15238	ETG	150	120	T-4	E11	CC-8	2600	3.00/76.2	0.55/14.0	2,000	12

Continued on next page >>>



Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
00197	250T10/H/F	250	120	T-10	E26	CC-8	4600	4.0/101	1.25/31.8	1,500	13
15256	EHT	250	120	T-4	E11	CC-8	5000	3.15/80.0	0.52/13.0	2,000	12
15258	ESM	250	120	T-4	E11	CC-8	4800	3.19/81.0	0.52/13.0	2,000	12
15260	ESS	250	120	T-4	BA15d	CC-8	5000	3.15/80.0	0.55/14.0	2,000	12
15262	ETB	250	120	T-4	BA15d	CC-8	4700	3.15/80.0	0.55/14.0	2,000	12
15278	EVR	500	120	T-4	E11	CC-8	10000	3.75/95.3	0.55/14.0	2,000	12
01930	EAJ*	35 / 25	12 / 12	T-6 1/2	BA15d	C-6/C-6	620 / 420	3.97/100.8	0.83/21.0	300/300	14

Photoflood Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
00040	BBA	250	120	A-21	E26	C-9	8500	4.77/121.2	2.68/68.0	3	15
00050	BCA	250	120	A-21	E26	C-9	5000	4.94/125.4	2.68/68.0	3	16
01970	ECA	250	120	A-23	E26	C-9	6500	5.52/140.2	2.76/70.0	20	17
07015	ECA-LN	250	120	A-23	E26	C-9	6500	5.87/149	2.76/70.0	20	17
01950	EBV	500	120	PS-25	E26	C-9	17000	6.10/155	3.15/80.0	6	17
06940	EBV-LN	500	120	PS-25	E26	C-9	17800	6.85/174	3.15/80.0	8	18
01960	EBW	500	120	PS-25	E26	C-9	10500	6.10/155	3.15/80.0	6	17
01980	ECT	500	120	PS-25	E26	C-9	13650	6.10/155	3.15/80.0	60	17
06906	ECT-LN	500	120	PS-25	E26	C-9	13650	6.85/174	3.15/80.0	60	18

Healthcare, Medical & Scientific Lamps

Order Code	Item	Usage	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
41338	41338		12	6	T-1 1/2	5.5 x 15 (M4.5 x 0.5)	C-2R	9	1/25	0.2/5	500	N/A
41314	41314		2.4	6	G-4 1/2	E10	C-2R	12	1/28	0.57/14.5	200	N/A
41240	04900*		2.5	3.5	TL-1 1/2	Flange	C-2R		0.90/22.9	0.31/7.9	20	N/A
41320	41320		3	6	G-3 1/2	E10	C-2R	15	0.94/24	0.43/11	300	N/A
41568	GTL-3		3	10.5	T-6	E17			2.5/63	0.79/20	2,000	N/A
41324	41324		5	6	G-6	BA15d	C-2R	70	1.38/35	0.75/19	600	N/A
41508	80-A*		7	60	T-4	4 Pin		40	1.32/33.5	3.23/82	3,000	N/A
41530	10S11NF	Lensometer	10	120	S-11	E17	C-7A	79	2.31/58.7	1.36/34.4	1,500	N/A
41364	41364		10	6	T-2 1/2	Special Base	C-6	200	1.06/27	0.31/8	100	N/A
41402	787*		10	6	T-2 1/4	G4	C-6	16	1.00/25.4	0.30/7.6	100	N/A
41085	8013		10	6	G-25mm	BA15d	C-6	150	1.81/46.0	0.99/25.0	200	N/A
41076	EL-2B		12	8	G-5 1/2	BA9s	C-2R	160	1.25/32.0	0.71/18.0	100	N/A
41077	EL-3B		12	8	G-5 1/2	BA9s	C-2R	160	1.25/32.0	0.71/18.0	100	N/A
41512	15S11-F	Lensometer	15	120	S-11	E12	C-7A	137	2.28/58	1.38/35	250	N/A
41099	15S11/102CL		15	120	S-11	E26	C-5	150	2.20/56.0	1.38/35.0	500	N/A
04411	15S11/102IF		15	120	S-11	E26	C-5		2.20/56.0	1.38/35.0	500	N/A
41308	41308		15	6	T-6	P25d	C-6Z	130	2.13/54	0.75/19	100	N/A
41310	41310		15	6	G-6	BA15d	C-8Z	130	1.46/37	0.75/19	100	N/A
41348	41348		15	120	G-11	E26	C-5	100	2.2/56	1.38/35	600	N/A
41350	41350		15	120	G-11	E26	C-10	100	2.2/56	1.38/35	600	N/A
41360	41360		15	110	G-11	E26	C-5	150	2.2/56	1.38/35	500	N/A

Continued on next page >>>



Specialty

Order Code	Item	Usage	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
41092	76907		15	6	G-19mm	BA15d	C BAR 6	150	1.40/35.6	0.75/19.1	100	N/A
41100	77903		15	6	T-19mm	PI5d30	C BAR 6	130	2.16/55.0	0.75/19	200	N/A
41087	8017*		15	6	T-19mm	BA15d	C BAR 6	145	2.12/54.0	0.75/19.1	1,000	N/A
41088	8018		15	6	T-19mm	BA15d	C BAR 6	210	2.05/52.0	0.75/19.1	100	N/A
41091	EI-77Z		15	6	T-6	DC w/ Special Flange	C BAR 6	130	2.05/52.0	0.75/19.1	100	N/A
41078	EL-12B		15	6	G-5 1/2	BA9s	C BAR 6	180	1.25/32.0	0.71/18.0	100	N/A
40279	1460		18	6.5	S-8	P30d	C-6	289	2.00/50.8	1.04/26.4	100	N/A
40281	1460X		18	6.5	S-8	P30d	C-6	289	2.00/50.8	1.04/26.4	100	N/A
40311	1630		18	6.5	S-8	P30d	C-6	289	2.00/50.8	1.04/26.4	100	N/A
40312	1631X		18	6.5	S-8	P30d	C-6	289	2.00/50.8	1.04/26.4	100	N/A
41094	77910		18	6	G-18mm	P25d	C BAR 6	180	1.40/35.6	0.75/19.1	50	N/A
41540	11143		20	6	T-2 1/2	G4	C-6	570	1.1/28	0.35/9	2,000	N/A
40313	1634		20	20	S-8	P30d	CC-6	302	2.00/50.8	1.04/26.4	200	N/A
41368	41368		20	6	T-2 1/2	G4	C-6	475	1.22/31	0.35/9	100	N/A
41400	778*		20	6	T-2 3/4	G4	C-6	400	1.05/26.7	0.38/9.6	100	N/A
41082	EI-2201		20	115	S-9 1/2	BA15d	C-5	150	2.08/53.0	1.18/30.0	500	N/A
41083	EI-886		20	120	G-9 1/2	BA15d	CC-7A	150	2.08/53.0	1.18/30.0	400	N/A
41096	EI-B153		20	120	S-11	BA15d	CC-2V	150	2.36/60.0	1.38/35.0	300	N/A
10330	ESB/FHE		20	6	T-2 3/4	G4	C-6	450	1.18/30.0	0.36/9.0	100	N/A
41520	25S11-2C	Ophthalmic	25	120	S-11	E12	C-7A	200	2.28/58	1.38/35	500	N/A
41518	25S11-5C	Ophthalmic	25	120	S-11	E12	C-7A	190	2.28/58	1.38/35	500	N/A
41344	41344		25	6	T-7	BA20d/26	C-8	330	2.36/60	0.88/22	100	N/A
41346	41346	Lensometer	25	120	S-11	E17	C-5	150	2.32/59	1.38/35	600	N/A
41432	56016164		25	24	G-13	BA15d	C-6		2.52/64.0	1.57/40	700	N/A
10012	BFM*		25	120	T-8	E14	CC-6V	300	2.62/66.6	1.03/26.0	500	N/A
41084	8001		26.1	6	S-35mm	E14	C-6	410	2.56/65.0	1.38/35.0	100	N/A
40401	1096		27	6	S-8	P30d	C-2R	375	2.00/50.8	1.04/26.4	500	N/A
40403	1096X*		27	6	S-8	P30d	C-2R	375	2.00/50.8	1.04/26.4	500	N/A
40405	1468X		27	6	S-8	P30d	C-2R	375	2.00/50.8	1.04/26.4	500	N/A
41318	41318		27	6	G-12 1/2	P44s	C-6	360	2.64/67	1.57/40	100	N/A
41328	41328		27	6	S-11	E14 w/ Special Prefocus Flange	C-6U	300	2.64/67	1.38/35	100	N/A
41340	41340		27	6	S-11	P44s	C-6	360	2.52/64	1.38/35	100	N/A
41306	41306		30	6	T-8	BA15d	C-6Z	230	2.2/56	1/25	200	N/A
41334	41334		30	12	T-3 1/4	G6.35	C-6	570	1.73/44	0.43/11	1,000	N/A
41546	64260		30	12	T-3	PG22d-b	C BAR 6	800	1.57/40	0.35/9	50	N/A
41093	77904		30	6	T-25	BA15d	C BAR 6	250	2.16/55.0	0.99/25.0	200	N/A
41089	8100		30	6	S-35mm	E14	C-6	260	2.56/65.0	1.38/35.0	600	N/A
41079	EI-722		30	120	S-9 1/2	BA15d	C-5	250	2.08/53.0	1.18/30.0	500	N/A
41081	EI-738		30	6	T-25	BA15d	C BAR 6	250	2.16/55.0	0.99/25.0	100	N/A
41326	41326*		33	6	S-8	SC Bayonet Prefocus w/ Triangle Flange	C-8Z	430	2/50	1/25	80	N/A
41366	41366*		33	6	T-8	DC w/ Special Flange	C-8Z	430	3/75	1/25	80	N/A
41312	41312		35	7	S-8	BA15d	C-8Z	460	2/50	1/25	100	N/A
40294	1507		37.5	12.5	RP-11	PI5s30	C-2V	625	2.2/56	1.42/36	300	N/A
41556	A1-010-28	Medical	40	24	T-4	E11	CC-6	720	2.36/60.0	0.51/13	600	N/A
41552	56018566*		50	22.8	T-3 1/2	G6.35	CC-6	1000	1.73/44.0		1,000	N/A
41090	8022		50	12	S-35mm	BA20d	CC-6	1000	2.71/69.0	1.38/35.0	50	N/A
41390	B1-010-28		50	24	T-4 1/2	G8	C BAR 6	1100	2.20/56.0	0.51/13	100	N/A
00602	BZW*		50	120	T-8	BA15s	CC-2V	850	3.13/79.4	0.99/25.0	50	N/A
00780	CAX		50	120	T-8	BA15d	CC-13	775	3.13/79.4	1.00/25.4	50	N/A
00790	CAX-130V		50	130	T-8	BA15d	CC-13	775	3.13/79.4	1.00/25.4	50	N/A
06312	CAX-130V-HAL		50	130	T-4	BA15d	C-2V	800	2.36/60	0.53/13.5	500	N/A

Continued on next page >>>

Order Code	Item	Usage	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs	Photo #
41558	A1-420-10		60	24	T-4	E10	CC-6	1100	2.36/60.0	0.51/13	800	N/A
41095	71818		70	10	G-50mm	P28s	C BAR 6	1100	3.31/84.1	1.97/50.0	100	N/A
16073	16073		80	12	MR11	G5.3-4.8	CC-8		1.46/37.0	1.41/35.8	50	N/A
10272	EJY		80	19	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25	N/A
41562	B5-011-32		100	24	T-4 1/2	G8	C BAR 6	2700	2.20/56.0	0.51/13	100	N/A
00730	CDD		100	120	T-8	BA15s	CC-2V	2000	3.13/79.4	1.00/25.4	50	N/A
10348	EVA		100	12	T-3 1/2	GY6.35	C BAR 6	2400	1.73/44.0	0.46/11.5	1,000	N/A
10403	FCR		100	12	T-3 1/2	GY6.35	C BAR 6	2900	1.73/44.0	0.46/11.5	50	N/A
41394	EI-74000		120	24	T-4 1/2	X514	CC-6	3000	1.81/46.0		200	N/A
81118	150P25/10		150	120	P-25	E26	C-7A	2100	4.75/120.7	3.13/79.4	200	N/A
10404	FCS		150	24	T-4	G6.35	C BAR 6	4500	1.97/50.0	0.53/13.5	50	N/A
41392	Q235T4/3-33V		235	33	T-4	GY9.5	CC-6	5000	2.44/62.0	0.51/13	500	N/A
41097	EI-M102		6-12	3-6	G-6	BA15s	C BAR 6	125	1.40/35.6	0.75/19.1	100	N/A

Germicidal Lamps

Order Code	Item	Shape	Base	MOL in/mm	Description	UV Output Watts	Life/Hrs	Photo #
41568	GTL-3	T-6	E17	2.5/63	Germicidal (254nm), Preheat, Ozoneless	0.18	2,000	N/A
41300	G4T5	T-5	G5	5.3/134.5	Germicidal (254nm), Preheat, Ozoneless	0.8	6,000	N/A
41302	G6T5*	T-5	G5	8.3/210.5	Germicidal (254nm), Preheat, Ozoneless	1.7	6,000	N/A
41384	G8T5	T-5	G5	11.3/287.0	Germicidal (254nm), Preheat, Ozoneless	2.5	6,000	N/A
41386	G10T8	T-8	G13	13/330	Germicidal (254nm), Preheat, Ozoneless	2.7	6,000	N/A
00219	G14T5/4P*	T-5	4 Pin	11.3/287	Germicidal (254nm), Preheat, Ozoneless	3	8,000	N/A
41388	G15T8	T-8	G13	17.2/436	Germicidal (254nm), Preheat, Ozoneless	4.9	8,000	N/A
00205	G10T5L	T-5	Single Pin 7.9mm	14/357	Germicidal (254nm), Preheat, Ozoneless	5.3	9,000	N/A
00202	G20T10*	T-10	G13	23.2/588.5	Germicidal (254nm), Preheat, Ozoneless	7.5	8,000	N/A
00222	G20T5	T-5	G5	15.8/400	Germicidal (254nm), Preheat, Ozoneless	5.5	8,000	N/A
00203	G25T8*	T-8	G13	17.2/436	Germicidal (254nm), Preheat, Ozoneless	6.9	8,000	N/A
00204	G30T8	T-8	G13	35.2/893	Germicidal (254nm), Preheat, Ozoneless	13.4	8,000	N/A
00223	G36T5/4P*	T-5	4 Pin	33.2/842	Germicidal (254nm), Preheat, Ozoneless	12	9,000	N/A
00206	G36T5L*	T-5	Single Pin 7.9mm	33.2/842	Germicidal (254nm), Preheat, Ozoneless	12	9,000	N/A
00214	G40T10*	T-10	G13	47.2/1198	Germicidal (254nm), Preheat, Ozoneless	19.8	8,000	N/A
00224	G55T8*	T-8	G13	35.2/893	Germicidal (254nm), Preheat, Ozoneless	18	8,000	N/A
00207	G64T5L	T-5	Single Pin 7.9mm	61.2/1554	Germicidal (254nm), Preheat, Ozoneless	25	9,000	N/A

Lamps contain mercury - please dispose of properly.

ANSI Coded Lamps

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs
03750	25T8/DC	25	120	T-8	BA15d	C-7A	195	2.63/66.7	0.99/25.0	200
00140	BKV*	30	120	S-11	BA15s	CC-2V	400	2.38/60.3	1.40/35.5	50
10020	BLC	30	120	S-11	BA15d	CC-2V	400	2.38/60.3	1.40/35.5	50
01890	DZA*	30	10.8	T-3 1/2	G5.3	C-6	800	2.00/50.8	0.46/11.5	400
02370	EKZ	30	10.8	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	200
02660	EPN	35	12	MR16	GX5.3	C-6		1.75/44.5	2.00/50.8	50
03625	JCR/M14V35W*	35	14	MR11	GZ4	CC-8		1.65/42.0	1.50/38.0	50
00170	BLR*	50	120	S-11	BA15s	CC-2V	780	2.38/60.3	1.40/35.5	50
10033	BRL	50	12	T-3 1/2	G6.35	C BAR 6	1400	1.73/44.0	0.46/11.5	50

Continued on next page >>>



Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs
01990	EFM	50	8	MR16	GZ6.35	C-6		1.65/42.0	1.97/50.0	50
02620	ENZ	50	30	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25
02720	EPZ	50	13.8	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	1,000
00220	BNF	75	120	S-11	BA15d	CC-2V	1300	2.38/60.3	1.40/35.5	25
00580	BXE	75	10	T-8	BA15s	C-8	1700	3.13/79.4	0.99/25.0	100
00720	CBX/CBS*	75	120	T-8	BA15d	CC-13	1200	3.13/79.4	0.99/25.0	50
10234	EFN*	75	12	MR16	GZ6.35	C-8		1.65/42.0	1.97/50.0	50
03623	JCR/M12V75W	75	12	MR11	G5.3-4.8	C-8	300	1.46/37.0	1.41/35.8	50
03650	PH/111A*	75	120	S-11	BA15s	CC-2V	1120	2.38/60.3	1.38/35.0	25
03662	PH/140	75	120	S-14	E26	CC-2V	1150	3.38/86.0	1.73/44.0	50
03663	PH/211	75	115-125	A-21	E26	CC-2V	1000	4.94/125.4	2.60/66.0	100
15210	Q75CL-28V	75	28	T-3 1/2	EZ10	CC-6	1200	2.50/63.5	0.44/11.0	2,000
01230	DDJ/DZZ	80	10	T-3	GY9.5	C BAR 6	1700	2.00/50.8	0.44/11.0	1,000
01250	DDM*	80	19	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
01290	DDS	80	21	MR16	GX5.3	CC-6	165	1.75/44.5	2.00/50.8	1,000
10272	EJY	80	19	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25
02350	EKP/ENA	80	30	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	25
02390	ELB	80	30	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	15
02440	ELE*	80	30	MR14	GX7.9	CC-6		1.60/40.7	1.75/44.5	20
02760	ESH*	85	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	250
02770	ESJ	85	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	40
00740	CDJ*	100	120	T-8	BA15d	CC-2V	2000	3.13/79.4	0.99/25.0	50
00750	CDS/CDX*	100	120	T-8	BA15s	CC-13	1800	3.13/79.4	0.99/25.0	50
00760	CEA/CEB/CDK*	100	120	T-8	BA15d	CC-13	2000	3.13/79.4	0.99/25.0	50
10235	EFP	100	12	MR16	GZ6.35	C-8		1.65/42.0	1.97/50.0	50
15222	ESN	100	120	T-4	E11	CC-2V	1900	2.80/71.0	0.52/13.0	750
15226	ESR	100	120	T-4	BA15d	CC-2V	1900	2.44/61.9	0.55/14.0	1,000
15224	ETE*	100	120	T-4	E11	CC-2V	1750	2.80/71.0	0.52/13.0	750
02880	EXV*	100	12	MR16	GX5.3	CC-6	3300	1.75/44.5	2.00/50.8	50
10403	FCR	100	12	T-3 1/2	GY6.35	C BAR 6	2900	1.73/44.0	0.46/11.5	50
03220	FDT	100	12	T-3 1/4	GZ9.5	C BAR 6	2900	2.25/57.2	0.44/11.0	50
03624	JCR/M12V100W*	100	12	MR11	G5.3-4.8	C-8		1.46/37.0	1.41/35.8	50
00770	CEM*	120	120	T-8	BA15s	CC-2V	1950	3.13/79.4	0.99/25.0	200
03666	125T10P*	125	120	T-10	P28s	C-13B	1740	5.75/146.1	1.26/32.0	500
00251	150T10/H/F	150	120	T-10	E26	CC-8	2850	4.0/101	1.25/31.8	1,500
00800	CEW/CFC*	150	120	T-8	BA15s	2CC-8	3500	3.63/92.1	0.99/25.0	25
00820	CHK*	150	120	T-8	BA15s	CC-13	2995	3.63/92.1	0.99/25.0	500
10146	DDL	150	20	MR16	GX5.3	C-8		1.75/44.5	2.00/50.8	500
01490	DNF	150	21	MR16	GX7.9	C-6		2.00/50.8	2.25/57.2	25
49451	DZE/FDS	150	24	T-4	GY9.5	C BAR 6	4600	2.25/57.2	0.55/14.0	100
10236	EFR	150	15	MR16	GZ6.35	C-8		1.65/42.0	1.97/50.0	50
10264	EJA	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
02280	EJM	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
02290	EJV	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
10275	EKE	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	200
02430	ELD/EJN	150	21	MR16	GX5.3	CC-6		1.75/44.5	2.00/50.8	40
02750	ESD	150	120	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	12
15240	ESL	150	120	T-4	E11	CC-2V	2800	2.80/71.0	0.52/13.0	1,000
15246	ESP	150	120	T-4	BA15d	CC-8	2400	2.44/61.9	0.55/14.0	1,000
02780	ESY	150	120	T-4	G6.35	CC-6	3300	1.97/50.0	0.53/13.5	200
15244	ETC	150	120	T-4	BA15d	CC-8	2800	2.44/61.9	0.52/13.0	2,000
15238	ETG	150	120	T-4	E11	CC-8	2600	3.00/76.2	0.55/14.0	2,000

Continued on next page >>>

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs
10404	FCS	150	24	T-4	G6.35	C BAR 6	4500	1.97/50.0	0.53/13.5	50
03230	FDV	150	24	T-4	G6.35	C BAR 6	4300	2.00/50.8	0.55/14.0	100
03640	JCR120V150WB	150	120	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	100
03664	PH/212	150	115-125	A-21	E26	CC-2V	2300	4.94/125.4	2.60/66.0	100
15204	Q150T4/CL/25	150	25	T-4	R7s	C-8	2700	2.48/63.0	0.52/13.0	3,000
02260	EJL	200	24	MRI6	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
02940	EYA*	200	82	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
15254	FEV	200	120	T-4	BA15d	CC-2V	5500	2.44/61.9	0.55/14.0	50
00197	250T10/H/F	250	120	T-10	E26	CC-8	4600	4.0/101	1.25/31.8	1,500
00040	BBA	250	120	A-21	E26	C-9	8500	4.77/121.2	2.68/68.0	3
00050	BCA	250	120	A-21	E26	C-9	5000	4.94/125.4	2.68/68.0	3
01970	ECA	250	120	A-23	E26	C-9	6500	5.52/140.2	2.76/70.0	20
07015	ECA-LN	250	120	A-23	E26	C-9	6500	5.87/149	2.76/70.0	20
10257	EHJ	250	24	T-4	G6.35	C BAR 6	8000	2.16/55.0	0.53/13.5	50
15256	EHT	250	120	T-4	E11	CC-8	5000	3.15/80.0	0.52/13.0	2,000
02400	ELC	250	24	MRI6	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
02410	ELC/5*	250	24	MRI6	GX5.3	CC-6		1.75/44.5	2.00/50.8	100
49423	ELC/5H	250	24	MRI6	GX5.3	CC-6		1.75/44.5	2.00/50.8	500
02420	ELC/E*	250	24	MRI6	GX5.3	CC-6		1.75/44.5	2.00/50.8	50
02530	EMM/EKS*	250	24	MRI4	GX7.9	CC-6		1.87/47.5	1.75/44.5	50
02570	ENH	250	120	MRI6	GY5.3	CC-8	15000	1.75/44.5	2.00/50.8	175
15258	ESM	250	120	T-4	E11	CC-8	4800	3.19/81.0	0.52/13.0	2,000
15260	ESS	250	120	T-4	BA15d	CC-8	5000	3.15/80.0	0.55/14.0	2,000
15262	ETB	250	120	T-4	BA15d	CC-8	4700	3.15/80.0	0.55/14.0	2,000
02790	ETJ	250	120	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	175
02800	EVC/FGX*	250	24	T-4	G6.35	C BAR 6	8400	2.25/57.2	0.57/14.5	200
02820	EVW	250	82	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
02920	EXY*	250	82	MRI3	GX5.3	CC-8		1.75/44.5	1.66/42.1	200
02970	EYH/FKT	250	120	G-6	G5.3	CC-6	5400	2.48/63.0	0.87/22.0	200
03503	GCA	250	120	T-3 1/2	G5.3	CC-8	6000	2.25/57.2	0.46/11.5	200
03500	FNT*	275	24	T-4	G6.35	C BAR 6	10000	2.16/55.0	0.55/14.0	75
03655	64514	300	120	T-6	GX6.35	CC-2F	7700	2.26/57.5	0.74/18.8	75
00830	CLS/CLC*	300	120	T-8 1/2	BA15s	C-13	7600	4.12/104.8	1.06/27.0	25
00850	CMV/CMT*	300	120	T-8 1/2	BA15s	C-13D	7300	4.12/104.8	1.06/27.0	25
01030	CXK*	300	120	T-10	P28s	C-13	7500	5.75/146.1	1.26/32.0	25
01070	CYC*	300	120	T-10	BA15s	C-13	7400	3.19/81.0	1.14/29.0	25
01580	DRA	300	120	T-5	G6.35	CC-6	6900	1.97/50.0	0.63/16.0	300
02180	EHM	300	120	T-3	R7s	C-8	6000	4.72/119.9	0.40/10.0	2,000
15214	EHP	300	120	T-4	R7s	CC-8	5000	3.17/80.6	0.52/13.0	2,000
02230	EHZ*	300	120	T-3	R7s	C-8	6000	4.72/119.9	0.36/9.0	2,000
02450	ELH	300	120	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	35
02460	ELH/5*	300	120	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	70
02550	ENG*	300	120	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	15
02850	EXR	300	82	MRI3	GX5.3	CC-8		1.75/44.5	1.66/42.1	35
02860	EXR/5*	300	82	MRI3	GX5.3	CC-8		1.75/44.5	1.66/42.1	70
02980	EYK*	300	120	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	60
03420	FHS	300	82	MRI3	GX5.3	CC-8		1.75/44.5	1.66/42.1	70
03455	FKW	300	120	T-6	GY9.5	C-13	7800	3.54/90.0	0.75/19.1	200
03480	FLW	300	24	T-4	GY6.35	C BAR 6	10200	2.16/55.0	0.55/14.0	50
03530	JC24V300W	300	24	T-4 1/2	G6.35	C-6	9900	2.16/55.0	0.55/14.0	50
02600	ENX	360	82	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	75
02610	ENX/5	360	82	MRI6	GY5.3	CC-8		1.75/44.5	2.00/50.8	150

Continued on next page >>>

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs
02950	EYB	360	82	T-31/2	G5.3	CC-8	10000	2.25/57.2	0.46/11.5	75
02960	EYB/5	360	82	T-31/2	G5.3	CC-8	10000	2.25/57.2	0.46/11.5	150
05913	HPL375/115V	375	115	T-6	G9.5 w/ Heatsink	4-C8	10540	3.86/98	0.72/18.4	300
05914	HPL375LL/115V	375	115	T-6	G9.5 w/ Heatsink	4-C8	8000	3.86/98	0.72/18.4	1,000
15218	EHR	400	120	T-4	R7s	CC-8	7750	3.17/80.6	0.52/13.0	2,000
02810	EVD	400	36	T-6	G6.35	C BAR 6	14500	2.38/60.3	0.75/19.1	50
03501	FXL	410	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	50
49116	FXL/5*	410	82	MR16	GY5.3	CC-8		1.75/44.5	2.00/50.8	100
02300	EKB	420	120	G-7	GZ9.5	CC-6	11000	2.50/63.5	0.87/22.0	75
03020	FAL*	420	120	T-4	R7s	CC-8	11000	2.63/66.7	0.55/14.0	90
00060	BCK	500	120	T-6	G17t	C-13D P.R.		3.22/82.0	0.77/19.5	50
00390	BTL	500	120	T-6	P28s	C-13D	11000	5.00/127.0	0.77/19.5	500
00690	CBA	500	120	T-6	G17q	C-13D P.R.		3.63/92.1	0.77/19.5	50
01130	CZX/DAB*	500	120	T-10	P28s	C-13D	12500	5.75/146.1	1.26/32.0	25
01470	DMX*	500	120	T-20	P28s	C-13	13200	5.75/146.1	2.52/64.0	50
01880	DYY/EGH	500	120	T-6	G17t	C-13D	14000	3.22/82.0	0.77/19.5	50
01950	EBV	500	120	PS-25	E26	C-9	17000	6.10/155	3.15/80.0	6
06940	EBV-LN	500	120	PS-25	E26	C-9	17800	6.85/174	3.15/80.0	8
01960	EBW	500	120	PS-25	E26	C-9	10500	6.10/155	3.15/80.0	6
01980	ECT	500	120	PS-25	E26	C-9	13650	6.10/155	3.15/80.0	60
06906	ECT-LN	500	120	PS-25	E26	C-9	13650	6.85/174	3.15/80.0	60
02010	EGE	500	120	T-4 1/2	P28s	CC-8	10000	6.00/152.4	0.55/14.0	2,000
02070	EGN	500	120	T-6	G22	C-13D	13000	5.50/139.7	0.77/19.5	100
02120	EHA*	500	120	T-6	GY9.5	C-13 P.R.		3.00/76.2	0.77/19.5	50
02140	EHC/EHB	500	120	T-4	G9.5	CC-8	13000	3.75/95.3	0.55/14.0	300
02150	EHD	500	120	T-5	G9.5	CC-8	10000	4.00/101.6	0.55/14.0	2,000
15278	EVR	500	120	T-4	E11	CC-8	10000	3.75/95.3	0.55/14.0	2,000
15276	EYV*	500	130	T-4	E11	CC-8	10000	3.75/95.3	0.52/13.0	2,000
15280	EYW	500	130	T-4	E11	CC-8	10000	3.75/95.3	0.52/13.0	2,000
15274	EYX	500	120	T-4	E11	CC-8	10000	3.75/95.3	0.52/13.0	2,000
03130	FCL	500	120	T-3	R7s	C-8	10000	4.72/119.9	0.44/11.0	2,000
03160	FCZ*	500	120	T-3	R7s	C-8	10800	4.72/119.9	0.44/11.0	2,000
03200	FDN*	500	120	T-3	R7s	C-8	12500	4.72/119.9	0.44/11.0	400
15097	FTK	500	120	T-6	GY9.5	CC-6	13500	2.57/65.3	0.75/19.1	200
03507	GDA*	500	120	T-4	R7s	C-8	11000	5.25/133.3	0.48/12.0	100
05641	HPL550/77V*	550	77	T-6	G9.5 w/ Heatsink	4-C8	16170	3.86/98	0.72/18.4	300
05915	HPL550LL/77V*	550	77	T-6	G9.5 w/ Heatsink	4-C8	12160	3.86/98	0.72/18.4	2,000
03475	FLK	575	120	T-6	G9.5	CC-8	16500	3.97/100.8	0.75/19.1	300
10418	GLA	575	115	T-7	G9.5	C-13D	13000	4.00/101.6	0.87/22.0	1,500
10419	GLC	575	115	T-7	G9.5	C-13D	15500	4.00/101.6	0.87/22.0	400
10415	HPL575/115V	575	115	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300
05152	HPL575/120V	575	120	T-6	G9.5 w/ Heatsink	4-C8	16520	3.86/98	0.72/18.4	300
05916	HPL575/230V*	575	230	T-6	G9.5 w/ Heatsink	6-C8	14900	3.86/98	0.72/18.4	400
10416	HPL575LL/115V	575	115	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2,000
05918	HPL575LL/120V	575	120	T-6	G9.5 w/ Heatsink	4-C8	12360	3.86/98	0.72/18.4	2,000
01810	DYH	600	120	G-7	G5.3	CC-6	17000	2.50/63.5	0.87/22.0	75
01850	DYS/DYV/BHC	600	120	T-6	GZ9.5	CC-6	17000	2.50/63.5	0.87/22.0	75
01860	DYS/DYV/BHC/5	600	120	T-6	GZ9.5	CC-6	17000	2.50/63.5	0.87/22.0	150
01700	DVY*	650	120	G-6	G5.3	CC-6	20000	2.48/63.0	0.79/20.0	25
02310	EKD*	650	120	G-6	GZ9.5	CC-6	20000	2.60/66.0	0.78/19.9	25
03010	FAD	650	120	T-4	R7s	CC-8	16500	3.17/80.6	0.55/14.0	100
15095	FRK*	650	120	T-7	GY9.5	C-13	16900	3.54/90.0	0.87/22.0	200
00100	BFK/BFL*	750	120	T-20	P28s	C-13	13500	5.75/146.1	2.52/64.0	200

Continued on next page >>>

Order Code	Item	W	V	Shape	Base	Fil	Lm	MOL in/mm	MOD in/mm	Life/Hrs
00410	BTN	750	120	T-7	P28s	C-13D	17000	5.00/127.0	0.91/23.0	500
00420	BTP	750	120	T-7	P28s	C-13D	20000	5.00/127.0	0.91/23.0	200
02020	EGF*	750	120	T-5	P28s	CC-8	20000	6.00/152.4	0.63/16.0	250
02030	EGG	750	120	T-5	P28s	CC-8	15000	6.00/152.4	0.63/16.0	2,000
02080	EGR	750	120	T-7	G22	C-13D	20000	5.50/139.7	0.91/23.0	200
02160	EHF	750	120	T-5	G9.5	CC-8	20400	4.12/104.8	0.73/18.5	300
02170	EHG	750	120	T-5	G9.5	CC-8	15000	4.12/104.8	0.73/18.5	2,000
02250	EJG	750	120	T-3	R7s	C-8	20600	4.72/119.9	0.48/12.0	400
02520	EMD*	750	120	T-3	R7s	C-8	19500	4.72/119.9	0.44/11.0	400
10417	HPL750/115V	750	115	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300
05921	HPL750/120V	750	120	T-6	G9.5 w/ Heatsink	4-C8	21900	4.09/104	0.72/18.4	300
05922	HPL750/230V*	750	230	T-6	G9.5 w/ Heatsink	6-C8	19750	4.09/104	0.72/18.4	300
05642	HPL750/77V*	750	77	T-6	G9.5 w/ Heatsink	4-C8	22950	3.86/98	0.72/18.4	300
05924	HPL750LL/115V*	750	115	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	1,500
05925	HPL750LL/120V*	750	120	T-6	G9.5 w/ Heatsink	4-C8	16400	4.09/104	0.72/18.4	2,000
05926	HPL750LL/230V*	750	230	T-6	G9.5 w/ Heatsink	6-C8	15600	4.09/104	0.72/18.4	1,500
00250	BRH*	1000	120	T-5	R7s	CC-8	30000	3.75/95.3	0.63/16.0	75
00430	BTR	1000	120	T-7	P28s	C-13D	27500	5.00/127.0	0.91/23.0	200
00500	BVT	1000	120	T-7	P40s	C-13D	23000	7.00/178.0	0.91/23.0	500
01550	DPT*	1000	120	T-20	E39	C-13	28000	9.06/230.2	2.52/64.0	50
01560	DPW*	1000	120	T-20	P40s	C-13	28000	9.50/241.3	2.52/64.0	50
01600	DRB/DRC*	1000	120	T-20	P28s	C-13	28000	5.75/146.1	2.52/64.0	25
01620	DRS*	1000	120	T-20	P28s	C-13D	29000	5.75/146.1	2.52/64.0	25
01640	DRW*	1000	120	T-20	E39	C-13D	27400	9.06/230.2	2.52/64.0	25
01720	DWT*	1000	120	T-6	R7s	CC-8	23400	5.67/144.1	0.75/19.1	2,000
02090	EGT	1000	120	T-7	G22	C-13D	27500	5.50/139.7	0.91/23.0	200
03140	FCM	1000	120	T-3	R7s	C-8	27000	4.72/119.9	0.44/11.0	300
03240	FEL	1000	120	T-6	G9.5	CC-8	27000	4.00/101.6	0.77/19.5	300
03320	FFN	1000	120	PAR 64	GX16d	CC-6	11000	6.03/153.1	8.35/212.0	800
03330	FFP	1000	120	PAR 64	GX16d	CC-6	12000	6.03/153.1	8.35/212.0	800
03340	FFR	1000	120	PAR 64	GX16d	CC-6	14000	6.03/153.1	8.35/212.0	800
03350	FFS	1000	120	PAR 64	GX16d	CC-6	19000	6.03/153.1	8.35/212.0	800
03360	FFT	1000	120	T-3 1/4	R7s	C-8	26400	6.61/167.9	0.44/11.0	300
00380	BTC*	1200	120	T-7	G17t	C-13D	38200	3.75/95.3	0.91/23.0	20
01670	DTJ*	1500	120	T-20	P40s	C-13D	42500	9.50/241.3	2.52/64.0	25
00520	BVW*	2000	120	T-11	P40s	C-13	59000	8.00/203.2	1.38/35.0	200
00530	BWA	2000	120	T-8	G38	CC-8	54000	8.00/203.2	0.99/25.0	500
00540	BWF	2000	120	T-9	E39	CC-8	54000	7.50/190.5	0.99/25.0	500
01930	EAJ*	35 / 25	12 / 12	T-6 1/2	BA15d	C-6/C-6	620 / 420	3.97/100.8	0.83/21.0	300 / 300
01570	DPY*	5000	120	T-17	G38	C-13	145000	11.00/279.4	2.38/60.5	500



Miniature Lamps

EIKO offers one of the widest lines of miniature lamps in the industry. Featuring quality construction with durable design, our lamps meet or exceed SAE and/or ANSI specifications for lumen output and lifetime hours and are known for their long-term reliability. Our in-house testing facilities ensure product quality. Available in traditional incandescent lamps or energy-efficient LED lamps that feature extraordinary long life.

LED Miniature Lamps

Order Code	Item	Volts	Base	Bulb	MOL in/ mm	MOD in/ mm	Lumens	Life/Hrs
02697	LED-24-MF-R*	24~28 VAC/DC	Midget Flanged (SX6s)	T-13/4	0.63/16	0.24/6	0.7	30,000
02698	LED-24-MF-W	24~28 VAC/DC	Midget Flanged (SX6s)	T-13/4	0.63/16	0.24/6	3.2	30,000
02702	LED-24-MG-W	24~28 VAC/DC	Midget Grooved (S5.7s)	T-13/4	0.63/16	0.24/6	1.1	30,000
02688	LED-14-BA9S-R	14 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	0.75	30,000
02687	LED-14-BA9S-G	14 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	1.5	30,000
02689	LED-14-BA9S-W	14 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	2.4	30,000
02694	LED-24-BA9S-R	24~28 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	0.7	30,000
02696	LED-24-BA9S-Y	24~28 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	0.6	30,000
02693	LED-24-BA9S-G	24~28 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	1.5	30,000
02695	LED-24-BA9S-W	24~28 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	2.4	30,000
02679	LED-120-MB-R	110~130 VAC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	0.2	30,000
02682	LED-120-MB-Y	110~130 VAC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	0.2	30,000
02678	LED-120-MB-G	110~130 VAC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	0.5	30,000
02681	LED-120-MB-W	110~130 VAC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	0.6	30,000
02705	LED-24-PSB-R	24~28 VAC/DC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	0.4	30,000
02706	LED-24-PSB-W	24~28 VAC/DC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	1.1	30,000
02707	LED-24-PSB-Y	24~28 VAC/DC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	0.4	30,000
02704	LED-24-PSB-G	24~28 VAC/DC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	0.9	30,000
02684	LED-120-PSB-R	110~130 VAC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	0.2	30,000
02686	LED-120-PSB-Y	110~130 VAC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	0.2	30,000
02683	LED-120-PSB-G	110~130 VAC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	0.6	30,000
02685	LED-120-PSB-W	110~130 VAC	Slide Base 5 (TS5)	T-2	1.1/28	0.27/6.8	0.9	30,000
02691	LED-14-T1.75 WEDGE-W	14 VAC/DC	Sub-Miniature Wedge (W2.1x4.6d)	T-13/4	0.77/19.4	0.22/5.5	1.1	30,000
02709	LED-24-T1.75 WEDGE-R*	24~28 VAC/DC	Sub-Miniature Wedge (W2.1x4.6d)	T-13/4	0.77/19.4	0.22/5.5	0.1	30,000
02711	LED-24-T1.75 WEDGE-W	24~28 VAC/DC	Sub-Miniature Wedge (W2.1x4.6d)	T-13/4	0.77/19.4	0.22/5.5	1.1	30,000
02712	LED-24-T1.75 WEDGE-Y*	24~28 VAC/DC	Sub-Miniature Wedge (W2.1x4.6d)	T-13/4	0.77/19.4	0.22/5.5	.3	30,000
05394	LED-12-SCBAY-W	12 VAC/DC	SC Bayonet (BA15s)	S-8	1.28/32.6	0.73/18.5	21.6	10,000
05379	LED-12-DCBAY-W	12 VAC/DC	DC Index Bayonet (BAY15d)	S-8	1.81/46	1.0/25	21.6/7.8	10,000

Continued on next page >>>

Order Code	Item	Volts	Base	Bulb	MOL in/ mm	MOD in/ mm	Lumens	Life/Hrs
05378	LED-12-DCBAY-R	12 VAC/DC	DC Index Bayonet (BAY15d)	S-8	1.81/46	1.0/25	7.9/2.7	10,000
00345	LED-194-W	14 VAC/DC	Miniature Wedge (W2.1x9.5d)	T-3 1/4	1.1/28	0.40/10	2.8	30,000
05385	LED-12-FESTOON-W	12 VDC	SV8.5mm	Festoon 10mm	1.73/44	0.43/11	17	30,000
05377	LED-24-FESTOON-W	24 VDC	SV8.5mm	Festoon 10mm	1.73/44	0.43/11	17	30,000
05742	LED-6-BA9S-W	6 VAC/DC	Miniature Bayonet (BA9s)	T-3 1/4	1.0/25	0.40/10	2.4	30,000
07797	LEDP-1383/30K	12 VAC/DC	SC Bayonet (BA15s)	MR11	2.5/63	1.375/34.8	100	30,000

Miniature Lamps

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/ mm	MOD in/ mm	Lumens	Life/Hrs
40864	6833*		5	0.06	Wire Leads (WL)	T-3/4	C-2R	0.20/5.1	0.09/2.3	0.63	25,000
40115	11411F		12.8	1.6	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4		1,000
40190	1156		12.8	2.1	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	400	1,200
44030	1156A		12.8	2.1	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4		1,200
48000	A-62		6.75	0.49	Miniature Bayonet (BA9s)	G-3 1/2	C-2R	0.94/23.9	0.43/11.0	12.57	
40640	363		14	0.2	Miniature Bayonet (BA9s)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	25	250
40761	53		14.4	0.12	Miniature Bayonet (BA9s)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	12.57	1,000
40698	407		4.9	0.3	Miniature Screw (E10)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	15.08	50
40702	425		5	0.5	Miniature Screw (E10)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	29	15
40750	502		5.1	0.15	Miniature Screw (E10)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	7.54	100
40574	31		6.15	0.3	Miniature Screw (E10)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	25	15
40826	605		6.15	0.5	Miniature Screw (E10)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	43	15
40704	428		12.5	0.25	Miniature Screw (E10)	G-4 1/2	C-2V	1.07/27.2	0.59/15.0	30	250
40194	1157		12.8/14	2.1/0.59	DC Index Bayonet (BAY15d)	S-8	C-6/C-6	2.00/50.8	1.04/26.4	400/38	1,200/5,000
41400	778		6	3.33	G4 (Sub-Miniature 2-Pin)	T-2 3/4	C-6	1.05/26.7	0.38/9.6	400	100
40204	1176		12.8/14	1.34/0.59	DC Bayonet (BA15d)	S-8	C-6/C-6	2.00/50.8	1.04/26.4	265/75	300/1,500
40232	1203		28	0.71	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	265	400
40242	1251		28	0.23	SC Bayonet (BA15s)	G-6	C-6/C-6	1.44/36.6	0.75/19.1	38	2,000
40322	1683		28	1.02	SC Bayonet (BA15s)	S-8	2C-6	2.00/50.8	1.04/26.4	400	500
40324	1691		28	0.61	SC Bayonet (BA15s)	S-8	2C-6	2.00/50.8	1.04/26.4	190	1,000
40326	1692		28	0.61	DC Bayonet (BA15d)	S-8	2C-6	2.00/50.8	1.04/26.4	190	1,000
40342	1768		6	0.2	Midget Screw (E5)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	7.54	1,000
42058	563		13.5	0.52	Rigid Loop (RGLP)	T-3	C-8	1.72/43.7	0.39/9.9	50	1,000
49019	1250X		13.5	0.37	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	63	500
40344	1769		2.5	0.2	Midget Screw (E5)	T-1 3/4	C-2R	0.72/18.3	0.23/5.9	2.51	500
40346	1775		6.3	0.075	Midget Screw (E5)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	2.90	1,000
40356	1810		6.3	0.4	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	17.60	3,000
40358	1813		14.4	0.1	Miniature Bayonet (BA9s)	T-3 1/4	C-2V	1.19/30.2	0.43/11.0	10.81	1,000
40360	1815		14	0.2	Miniature Bayonet (BA9s)	T-3 1/4	C-2V	1.19/30.2	0.43/11.0	17.60	3,000
40362	1816		13	0.33	Miniature Bayonet (BA9s)	T-3 1/4	C-2V	1.19/30.2	0.43/11.0	38	1,000
40364	1818		24	0.17	Miniature Bayonet (BA9s)	T-3 1/4	C-2V	1.19/30.2	0.43/11.0	41	250
40366	1819		28	0.04	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	4.27	2,500
40368	1820		28	0.1	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	20.11	1,000
40370	1821		28	0.17	Miniature Screw (E10)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	43	500
40372	1822		36	0.1	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	26	1,000
40380	1828		37.5	0.05	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	8.17	3,000
40382	1829		28	0.07	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	12.57	1,000
40386	1835		55	0.05	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	13.83	5,000
42510	912LL		12.8	1.0	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	150	2,000
49023	1250X-2		13.5	0.37	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	50	2,000
40824	6022		5	0.02	Wire Leads (WL)	T-1	C-2R	0.25/6.4	0.13/3.2	0.38	10,000
40896	7327		28	0.04	Bi-Pin .125 (G3.17)	T-1 3/4	C-2F	0.60/15.2	0.23/5.9	4.27	4,000

Continued on next page >>>

Miniature

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
42400	7328		6	0.2	Bi-Pin .125 (G3.17)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	7.54	1,000
40910	7371		12	0.04	Bi-Pin .125 (G3.17)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	1.51	10,000
40912	7373		14	0.1	Bi-Pin .125 (G3.17)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	6.29	10,000
40920	7381		6.3	0.2	Bi-Pin .125 (G3.17)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	5.03	20,000
40922	7382		14	0.08	Bi-Pin .125 (G3.17)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	3.77	40,000
40926	7387		28	0.04	Bi-Pin .125 (G3.17)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	3.77	25,000
42232	2821		13.5	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	22.12	1,000
40938	7632		28	0.04	Bi-Pin .100 (G2.54)	T-1 1/4	C-2F	0.60/15.2	0.17/4.3	4.02	1,000
40944	7683		5	0.06	Bi-Pin .050 (G1.27)	T-1	C-2R	0.38/9.7	0.13/3.2	0.63	25,000
40946	7714		5	0.075	Bi-Pin .050 (G1.27)	T-1	C-2R	0.38/9.7	0.13/3.2	1.13	25,000
40948	7715		5	0.115	Bi-Pin .050 (G1.27)	T-1	C-2R	0.38/9.7	0.13/3.2	1.89	40,000
40422	1906		5	0.07	Miniature Bayonet (BA9s)	T-3 1/4	C-6	1.19/30.2	0.43/11.0	2.39	1,000
40950	7839		28	0.024	Bi-Pin .050 (G1.27)	T-1	CC-2F	0.38/9.7	0.13/3.2	1.89	40,000
40960	8111		14	0.065	Wire Leads (WL)	T-1	C-2F	0.25/6.4	0.13/3.2	1.89	10,000
42418	8362		14	0.08	Midget Screw (E5)	T-1 3/4	C-2F	0.69/17.5	0.23/5.9	3.77	15,000
40978	8627		28	0.04	Wire Leads (WL)	T-1 1/4	C-2F	0.46/11.7	0.17/4.3	4.02	1,000
40982	8640		14	0.08	Wire Leads (WL)	T-1 1/4	C-2F	0.46/11.7	0.17/4.3	6.29	1,000
49025	1250X-5		13.5	0.37	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	38	5,000
49031	1450X*		14	0.357	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	25	5,000
40100	PR2		2.38	0.5	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	10.06	18
40104	PR3		3.57	0.5	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	18.86	15
40108	PR4		2.33 V	0.27	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	5.03	10
40112	PR6		2.47	0.3	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	5.66	30
44018	24E2		24	0.035	Slide Base 2 (TS2)	T-2	C-2F	1.69/42.9	0.27/6.9		7,000
44003	KPR4		2.2 V	0.47	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	6.91	15
40788	6S6/130V		130	0.046	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	38	1,500
40789	6S6/145V		145	0.041	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	17.60	1,500
43008	15T7DC-130V		130	0.12	DC Bayonet (BA15d)	T-7	C-7A	2.25/57.2	0.89/22.6	90	1,500
40076	NE51H-R		110	0.0012	Miniature Bayonet (BA9s)	T-3	Neon	1.19/30.2	0.38/9.6		25,000
40074	NE51-R		110	0.0003	Miniature Bayonet (BA9s)	T-3	Neon	1.19/30.2	0.38/9.6		25,000
43006	15T7C-130V		130	0.12	Candelabra Screw (E12)	T-7	C-7A	2.25/57.2	0.89/22.6	90	1,500
40045	KPR13		4.75	0.5	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	31	10
40061	K15		4.8	0.7	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	50	15
40059	K12*		5.95	0.7	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	45	15
44023	796		12.8	2.73	SC Bayonet (BA15s)	T-4	C-6	2.50/63.5	0.48/12.2	755	300
44019	795		12.8	3.91	SC Bayonet (BA15s)	T-4	C-6	2.50/63.5	0.48/12.2	1355	200
40812	6S6DC/48V		48	0.125	DC Bayonet (BA15d)	S-6	C-6	1.82/46.2	0.75/19.1	47	1,500
40811	6S6DC/32V		32	0.1875	DC Bayonet (BA15d)	S-6	C-6	1.82/46.2	0.75/19.1	50	1,500
40806	6S6DC/130V		130	0.046	DC Bayonet (BA15d)	S-6	C-7A	1.82/46.2	0.75/19.1	38	1,500
40807	6S6DC/145V		145	0.041	DC Bayonet (BA15d)	S-6	C-7A	1.82/46.2	0.75/19.1	17.60	1,500
41402	787		6	1.67	G4 (Sub-Miniature 2-Pin)	T-2 1/4	C-6	1.00/25.4	0.30/7.6	16	100
40874	7C7/120V		120	0.0583	Candelabra Screw (E12)	C-7	C-7A	2.30/58.4	0.88/22.3	37	3,000
40875	7C7/130V		130	0.0538	Candelabra Screw (E12)	C-7	C-7A	2.30/58.4	0.88/22.3	35	3,000
40154	10C7DC/120V		120	0.083	DC Bayonet (BA15d)	C-7	C-7A	2.13/54.1	0.88/22.3	64	5,000 +
42446	10S6/230V		230	0.043	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	60	1,500
40149	10S6DC/250V		250	0.04	DC Bayonet (BA15d)	S-6	C-7A	1.82/46.2	0.75/19.1	60	1,500
40174	1133		6.2	3.91	SC Bayonet (BA15s)	RP-11	C-6	2.25/57.2	1.42/36.1	400	200
40829	624		28	0.37	DC Bayonet (BA15d)	G-6	2C-6	1.44/36.6	0.75/19.1	75	1,000
40832	631		14	0.63	SC Bayonet (BA15s)	G-6	C-6/C-6	1.44/36.6	0.75/19.1	75	1,000
40020	B7A		110	0.002	Candelabra Screw (E12)	T-4	Neon	1.38/35.0	0.50/12.7		7,500
40636	356		28	0.17	Miniature Bayonet (BA9s)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	44	500
40552	356/5-120V		120	0.025	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	11.31	1,500

Continued on next page >>>

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
40554	3S6/5-130V		130	0.023	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	11.31	1,500
40556	3S6/5DC-120V		120	0.025	DC Bayonet (BA15d)	S-6	C-7A	1.82/46.2	0.75/19.1	11.31	3,000
40353	4C7/120V		120	0.033	Candelabra Screw (E12)	C-7	C-7A	2.30/58.4	0.88/22.3	20	3,000
40777	6MB		6	0.14	Miniature Bayonet (BA9s)	T-2 1/2	C-2V	1.19/30.2	0.33/8.4	1.51	20,000
40778	6PSB5		6	0.14	Slide Base 5 (TS5)	T-2	C-2V	1.11/28.2	0.27/6.9		20,000
40798	6S6/6V		6	1.0	Candelabra Screw (E12)	S-6	C-6	1.88/47.8	0.75/19.1	54	1,500
00233	7511		28	1.0	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	440	350
00234	7537		28/28	1.0/0.36	DC Index Bayonet (BAY15d)	S-8	C-6/C-6	2.00/50.8	1.04/26.4	440/38	300/2,000
43016	20T6.5DC/F-130V		130	0.15	DC Bayonet (BA15d)	T-6 1/2	C-8	5.56/141.2	0.83/21.1	170	3,000
43012	20T6-1/2F-130V		130	0.15	Intermediate Screw (E17)	T-6 1/2	C-8	5.5/139.7	0.83/21.1	170	3,000
43010	20T6-1/2N-130V		130	0.15	Intermediate Screw (E17)	T-6 1/2	C-8	5.5/139.7	0.83/21.1	180	3,000
42240	24		14	0.24	Sub-Miniature Wedge (W2x4.6d)	T-2 3/4	C-2V	0.91/23.1	0.34/8.7	25	1,500
40513	24CSB		24	0.017	Slide Base 5 (TS5)	T-2	C-2F	0.92/23.4	0.27/6.9		15,000
40509	24E3		24	0.035	Slide Base 3 (TS3)	T-2	C-2F	1.69/42.9	0.27/6.9		7,000
40507	24ESB5		24	0.04	Slide Base 5 (TS5)	T-2	C-2F	0.92/23.4	0.27/6.9		8,000
44020	24EX		24	0.035	Slide Base 2 (TS2)	T-2	C-2F	1.69/42.9	0.27/6.9		8,000
40510	24MB		24	0.073	Miniature Bayonet (BA9s)	T-2 1/2	C-2F	1.19/30.2	0.33/8.4	6.29	10,000
40512	24PSB5		24	0.073	Slide Base 5 (TS5)	T-2	C-2F	1.11/28.2	0.27/6.9		10,000
40351	4C7/130V		130	0.031	Candelabra Screw (E12)	C-7	C-7A	2.30/58.4	0.88/22.3	15	3,000
43032	25T8DC-130V		130	0.19	DC Bayonet (BA15d)	T-8	C-7A	2.63/66.8	1.04/26.4	180	1,500
43030	25T8N-130V	Appliance	130	0.19	Intermediate Screw (E17)	T-8	C-7A	2.63/66.8	1.04/26.4	180	1,500
40539	27		4.9	0.3	Miniature Screw (E10)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	17.60	30
40544	28ESB5		28	0.04	Slide Base 5 (TS5)	T-2	C-2F	0.92/23.4	0.27/6.9		6,000
40546	28MB		28	0.04	Miniature Bayonet (BA9s)	T-2 1/2	C-2F	1.19/30.2	0.33/8.4	3.65	5,000
40548	28PSB5		28	0.04	Slide Base 5 (TS5)	T-2	C-2F	1.11/28.2	0.27/6.9		5,000
43038	40T6-1/2N-130V		130	0.31	Intermediate Screw (E17)	T-6 1/2	C-8	5.5/139.7	0.83/21.1	330	1,500
43042	40T10-130V		130	0.31	Medium Screw (E26)	T-10	C-8	5.19/131.8	1.25/31.8	320	1,500
43044	40T10/F-130V		130	0.31	Medium Screw (E26)	T-10	C-8	5.19/131.8	1.25/31.8	310	1,500
40802	6S6DC/12V		12	0.5	DC Bayonet (BA15d)	S-6	C-6	1.82/46.2	0.75/19.1	48	1,500
40808	6S6DC/24V		24	0.25	DC Bayonet (BA15d)	S-6	C-6	1.82/46.2	0.75/19.1	53	1,500
40810	6S6DC/30V		30	0.2	DC Bayonet (BA15d)	S-6	C-6	1.82/46.2	0.75/19.1	52	1,500
40578	313		28	0.17	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	44	500
40703	1495*		28	0.3	Miniature Bayonet (BA9s)	T-4 1/2	C-2F	1.38/35.1	0.59/15.0	75	500
40596	327		28	0.04	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	4.27	4,000
40598	328		6	0.2	Midget Flanged (SX6s)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	7.54	1,000
40599	330		14	0.08	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	6.29	1,500
40606	334		28	0.04	Midget Grooved (S5.7s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	4.27	4,000
40616	337		6.3	0.2	Midget Grooved (S5.7s)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	7.54	1,000
40622	344		10	0.014	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	0.025	50,000
40650	370		18	0.04	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	1.89	10,000
40654	373		14	0.08	Midget Screw (E5)	T-1 3/4	C-2F	0.72/18.3	0.23/5.9	6.29	1,500
40844	6615F		14	0.08	Double End Cap (SF6/6)	T-2	C-8	1.26/32.0	0.24/6.1	3.77	10,000
40658	376		28	0.06	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	4.27	25,000
40660	377		6.3	0.075	Midget Flanged (SX6s)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	2.90	1,000
40662	378		6.3	0.2	Midget Screw (E5)	T-1 3/4	C-2F	0.72/18.3	0.23/5.9	5.03	20,000
40664	379*		6.3	0.2	Midget Grooved (S5.7s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	5.03	20,000
40668	381		6.3	0.2	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	5.03	20,000
40670	382		14	0.08	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	3.77	15,000
40672	385		28	0.04	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	1.89	20,000
40674	386		14	0.08	Midget Grooved (S5.7s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	3.77	40,000
40678	387		28	0.04	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	3.77	10,000
40680	388		28	0.04	Midget Grooved (S5.7s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	3.77	25,000

Continued on next page >>>

Miniature

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
40686	394		12	0.04	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	151	20,000
40692	399		28	0.04	Midget Screw (E5)	T-1 3/4	C-2F	0.72/18.3	0.23/5.9	3.77	7,000
40696	400		28	0.1	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	20.11	1,000
40012	A3C		110	0.0018	Wire Leads (WL) [2" Leads]	T-2	Neon	0.75/19.1	0.25/6.4		25,000
40720	455		6.5	0.5	Miniature Bayonet (BA9s)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	23.88	500
40464	2114		6	0.06	Wire Leads (WL)	T-1 1/4	C-2R	0.46/11.7	0.17/4.3	1.63	3,000
41704	77A/S8		12	0.77	Sngl Cont Prefocus Flange (PI5s30)	S-8	C-8S	2.09/53.1	1.04/26.4	120	500
44326	56		5	0.115	Sub-Mini Wedge (W2.1x4.9d)	T-1 3/4	C-2R	0.80/20.3	0.23/5.9	1.89	20,000
40468	2162		14	0.1	Wire Leads (WL)	T-1 3/4	C-2F	0.52/13.2	0.23/5.9	6.29	10,000
40470	2174		12	0.04	Wire Leads (WL)	T-1 3/4	C-2F	0.52/13.2	0.23/5.9	1.26	10,000
40472	2176		24	0.05	Wire Leads (WL)	T-1 3/4	C-2F	0.52/13.2	0.23/5.9	6.29	1,000
40478	2182		14	0.08	Wire Leads (WL)	T-1 3/4	C-2F	0.52/13.2	0.23/5.9	3.77	40,000
40484	2187		28	0.04	Wire Leads (WL)	T-1 3/4	C-2F	0.52/13.2	0.23/5.9	3.77	10,000
40488	2200		5	0.06	Wire Leads (WL)	T-1 3/4	C-2R	0.52/13.2	0.23/5.9	0.63	25,000
42384	2232		28	0.643	SC Bayonet (BA15s)	S-8	CC-8	2.00/50.8	1.04/26.4	225	2,000
42386	2233		28	0.766	SC Bayonet (BA15s)	S-8	CC-8	2.00/50.8	1.04/26.4	265	2,000
42231	2721		12	0.1	Sub-Miniature Wedge (W2x4.6d)	T-1 1/2	C-2V	0.80/20.3	0.20/5.1	6.03	1,000
40637	2825		13.5	0.4	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	50	750
40114	PR7		3.7	0.3	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	11.31	30
40084	PR12		5.95	0.5	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	38	15
40086	PR13		4.75	0.5	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	28	15
40090	PR15		4.82	0.5	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	25	30
40092	PR16		12.5	0.25	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	34	50
40096	PR18		7.2	0.55	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	69	3
40102	PR20		8.63	0.5	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	63	15
44011	P21/5W*		13.5/13.5	1.86/0.44	DC Index Bayonet (BAY15d)	S-8	C-6/C-6	2.06/52.5	1.05/26.5	440/35	300/2,000
50114	JF02XE		6	0.833	Rigid Loop (RGLP)	T-3 1/4	C-8	1.72/43.7	0.40/10.0	55	20,000
40106	PR30		3.75	0.86	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	28	40
40446	2		5	0.021	Wire Leads (WL)	T-3/4	C-2R	0.20/5.1	0.09/2.3	0.38	10,000
50118	JF03XE*		12	0.417	Rigid Loop (RGLP)	T-3 1/4	C-8	1.72/43.7	0.40/10.0	60	3,000
40784	6S6/12V		12	0.5	Candelabra Screw (E12)	S-6	C-6	1.88/47.8	0.75/19.1	48	1,500
40792	6S6/24V		24	0.25	Candelabra Screw (E12)	S-6	C-6	1.88/47.8	0.75/19.1	53	1,500
40794	6S6/30V		30	0.2	Candelabra Screw (E12)	S-6	C-6	1.88/47.8	0.75/19.1	52	1,500
40796	6S6/48V		48	0.125	Candelabra Screw (E12)	S-6	C-6	1.88/47.8	0.75/19.1	47	1,500
40800	6S6/60V		60	0.1	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	43	1,500
40786	6S6/120V		120	0.05	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	39	1,500
40790	6S6/155V		155	0.039	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	33	1,500
40791	6S6/230V		230	0.026	Candelabra Screw (E12)	S-6	C-7A	1.88/47.8	0.75/19.1	11.31	1,500
43004	15T7N-130V	Med/Sci	130	0.12	Intermediate Screw (E17)	T-7	C-7A	2.25/57.2	0.89/22.6	90	1,500
40218	12ESB5*		12	0.04	Slide Base 5 (TS5)	T-2	C-2V	0.92/23.4	0.27/6.9		7,500
40220	12MB		12	0.17	Miniature Bayonet (BA9s)	T-2 1/2	C-2F	1.19/30.2	0.33/8.4	4.40	12,000
40222	12PSB5		12	0.17	Slide Base 5 (TS5)	T-2	C-2F	1.11/28.2	0.27/6.9		12,000
43000	15T6C-130V		130	0.12	Candelabra Screw (E12)	T-6	C-7A	3.06/77.7	0.77/19.6	90	2,000
43002	15T6C-145V		145	0.1	Candelabra Screw (E12)	T-6	C-7A	3.06/77.7	0.77/19.6	90	2,000/7,500@120V
40291	16ESB5		16	0.04	Slide Base 5 (TS5)	T-2	C-2F	0.92/23.4	0.27/6.9		7,500
44322	17		28	0.065	Sub-Mini Wedge (W2.1x4.9d)	T-1 3/4	C-2F	0.80/20.3	0.23/5.9	8.17	5,000
43014	20T6-1/2DC-130V		130	0.15	DC Bayonet (BA15d)	T-6 1/2	C-8	5.56/141.2	0.83/21.1	180	3,000
41002	8918		14	0.1	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	6.29	10,000
42005	42005		135 V	0.32	Bi-Pin .050 (G1.27)	T-1	C-2R	0.38/9.7	0.13/3.2	214	5
42003	42003		2.7	0.32	Bi-Pin .050 (G1.27)	T-1	C-2R	0.38/9.7	0.13/3.2	8.80	5
42006	42006		2.7	0.32	Bi-Pin .050 (G1.27)	T-1	C-2R	0.38/9.7	0.13/3.2	8.80	5
40010	A2B		110	0.0007	Wire Leads (WL) [2" Leads]	T-2	Neon	0.75/19.1	0.25/6.4		25,000

Continued on next page >>>

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
40814	6S6DC/6V		6	1.0	DC Bayonet (BA15d)	S-6	C-6	1.82/46.2	0.75/19.1	54	1,500
40986	87		6.8	1.91	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	190	300
43036	25T10/F-130V		130	0.19	Medium Screw (E26)	T-10	C-8	5.19/131.8	1.25/31.8	200	1,500
50124	JF07XE		12	0.833	Rigid Loop (RGLP)	T-3 1/4	C-8	1.72/43.7	0.40/10.0	100	20,000
43022	25T6.5N/F-130V		130	0.19	Intermediate Screw (E17)	T-6 1/2	C-8	5.5/139.7	0.83/21.1	200	3,000
43020	25T6-1/2N-130V		130	0.19	Intermediate Screw (E17)	T-6 1/2	C-8	5.5/139.7	0.83/21.1	210	3,000
50132	JF13XE*		24	0.208	Rigid Loop (RGLP)	T-3 1/4	C-8	1.72/43.7	0.40/10.0	55	3,000
05833	6614F		14	0.05	Double End Cap (SF6/6)	T-2	C-8	1.26/32.0	0.24/6.1	2.01	10,000
40841	6612F		12	0.25	Double End Cap (SF6/6)	T-2	C-8	1.26/32.0	0.24/6.1	12.57	5,000
42382	1662		28/28	0.93/0.34	DC Index Bayonet (BA15d)	S-8	CC-6/C-6	2.00/50.8	1.04/26.4	400/75	400/1,000
44402	20T6-1/2N-145V		145	0.14	Intermediate Screw (E17)	T-6 1/2	C-8	5.5/139.7	0.83/21.1	170	3,000
40000	A1A		110	0.0006	Wire Leads (WL) (1.25" Leads)	T-2	Neon	1.00/25.4	0.25/6.4		25,000
44021	795X		12.8	3.91	SC Bayonet (BA15s)	T-4	C-8	2.50/63.5	0.48/12.2	1355	200
40492	222		2.25 V	0.25	Miniature Screw (E10)	TL-3	C-2R	0.93/23.6	0.38/9.6		5
40520	243		2.33 V	0.27	Miniature Screw (E10)	TL-3	C-6	0.93/23.6	0.38/9.6		10
40534	259		6.3	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2	8.17	5,000
40550	293		14	0.33	Miniature Bayonet (BA9s)	G-4 1/2	C-2F	1.07/27.2	0.59/15.0	25	5,000
40562	303		28	0.3	SC Bayonet (BA15s)	G-6	CC-6	1.44/36.6	0.75/19.1	75	500
40566	306		28	0.51	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	190	300
40568	307		28	0.67	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	265	300
40570	308		28	0.67	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	265	300
40576	311		28	1.29	SC Bayonet (BA15s)	S-11	CC-2V	2.38/60.5	1.35/34.3	630	300
40728	464		28	0.17	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	38	1,500
40752	503		5.1	0.15	Miniature Bayonet (BA9s)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	7.54	100
40225	120MB-NEON		120	0.004	Miniature Bayonet (BA9s)	T-3	Neon	1.19/30.2	0.38/9.6		10,000
40754	509K		24	0.18	Candelabra Screw (E12)	G-6	C-2F	1.38/35.1	0.75/19.1	35	1,000
40783	555		6.3	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2	11.31	3,000
40769	558		13	0.33	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2		500
40759	585		28	0.04	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	3.77	7,000
40828	623		28	0.37	SC Bayonet (BA15s)	G-6	2C-6	1.44/36.6	0.75/19.1	75	1,000
40165	1073		12.8	1.8	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	400	200
40167	1076		12.8	1.8	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	400	200
40172	1130		6.4	2.63	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	265	200
40176	1141		12.8	1.6	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	265	1,500
40178	1142		12.8	1.6	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	265	1,000
40244	1252		28	0.23	DC Bayonet (BA15d)	G-6	C-6/C-6	1.44/36.6	0.75/19.1	38	2,000
40250	1309		28	0.52	SC Bayonet (BA15s)	B-6	2C-6	1.75/44.5	0.79/20.1	190	300
40258	1383		13	1.5	SC Bayonet (BA15s)	R-12	C-8	2.63/66.8	1.55/39.4	200	300
40262	1385		28	0.72	SC Bayonet (BA15s)	R-12	CC-8	2.63/66.8	1.55/39.4	165	300
49013	1236X		12	0.3	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	45	20,000
49015	1210X		12	0.833	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	125	2,000
40268	1408		10	0.13	Miniature Bayonet (BA9s)	T-3 1/4	C-2V	1.19/30.2	0.43/11.0	10.68	250
40276	1449		14	0.2	Miniature Screw (E10)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	25	250
40282	1477		24	0.17	Miniature Screw (E10)	T-3	C-2V	1.25/31.8	0.40/10.2	41	250
40701	1493		6.4	2.75	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	290	100
49017	1211X		12	0.917	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	125	5,000
40002	A1B		110	0.0003	Wire Leads (WL) (1" Leads)	T-2	Neon	0.50/12.7	0.25/6.4		25,000
40006	A1H		110	0.0012	Midget Flanged (SX6s)	T-1 3/4	Neon	0.63/16	0.23/5.9		25,000
40014	A9A		110	0.007	Wire Leads (WL) (2" Leads)	T-2	Neon	1.00/25.4	0.25/6.4		25,000
40016	B1A		110	0.003	Miniature Bayonet (BA9s)	T-3	Neon	1.19/30.2	0.38/9.6		25,000
40018	B2A		110	0.0012	Miniature Bayonet (BA9s)	T-3	Neon	1.19/30.2	0.38/9.6		25,000
40041	KPR2		2.38	0.5	SC Miniature Flanged (PI3.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	10.06	20

Continued on next page >>>

Miniature

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
40390	1847		6.3	0.15	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	4.78	5,000
40394	1850		5	0.09	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	3.14	1,500
40398	1864		28	0.17	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	38	1,500
40400	1866		6.3	0.25	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	8.17	5,000
40404	1873		28	0.2	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	38	7,000
40406	1888		7	0.5	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	25	1,500
40408	1889		14	0.27	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	25	2,000
40409	1891		14	0.24	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	25	500
40412	1892		14.4	0.12	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	9.43	1,000
40413	1893		14	0.33	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	25	7,500
40416	1895		14	0.27	Miniature Bayonet (BA9s)	G-4 1/2	C-2F	1.07/27.2	0.59/15.0	25	2,000
41702	55A/S8		12	0.55	Sngl Cont Prefocus Flange (PI5s30)	S-8	C-8S	2.09/53.1	1.04/26.4	70	500
40866	6838		28	0.024	Wire Leads (WL)	T-1	CC-2F	0.25/6.4	0.13/3.2	1.89	16,000
40868	6839		28	0.024	Sub-Midget Flanged (SX4s)	T-1	CC-2F	0.38/9.7	0.13/3.2	1.89	16,000
42390	7219		12	0.06	Wire Leads (WL)	T-1	C-2F	0.25/6.4	0.13/3.2	1.89	10,000
40168	112		1.2 V	0.25	Miniature Screw (E10)	TL-3	S-2	0.93/23.6	0.38/9.6		5
50030	2450X		24	0.208	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	55	500
50032	2470X		24	0.3	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	55	12,000
50036	2475X-1		24	0.313	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	65	10,000
50038	2410X-1		24	0.417	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	90	10,000
40732	48		2 V	0.06	Miniature Screw (E10)	T-3 1/4	S-2	1.19/30.2	0.43/11.0	0.50	1,000
40700	41		2.5	0.5	Miniature Screw (E10)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	6.29	3,000
40694	40		6.3	0.15	Miniature Screw (E10)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	6.54	3,000
40726	46		6.3	0.25	Miniature Screw (E10)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	11.31	3,000
40284	1487		14	0.2	Miniature Screw (E10)	T-3 1/4	C-2V	1.19/30.2	0.43/11.0	17.60	3,000
40247	13		3.7	0.3	Miniature Screw (E10)	G-3 1/2	C-2R	0.94/23.9	0.43/11.0	12.32	15
40264	14		2.47	0.3	Miniature Screw (E10)	G-3 1/2	C-2R	0.94/23.9	0.43/11.0	6.29	15
50042	2860X		28	0.214	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	50	1,000
40516	24X		24	0.035	Slide Base 2 (TS2)	T-2	C-2F	1.69/42.9	0.27/6.9		8,000
43018	25T6C-120V		120	0.21	Candelabra Screw (E12)	T-6	C-7A	3.06/77.7	0.77/19.6	190	2,000
43034	25T10-130V		130	0.19	Medium Screw (E26)	T-10	C-5V	5.19/131.8	1.25/31.8	180	2,000
43024	25T6-1/2DC-130V		130	0.19	DC Bayonet (BA15d)	T-6 1/2	C-8	5.5/139.7	0.83/21.1	210	3,000
43028	25T8C-120V	Appliance	120	0.21	Candelabra Screw (E12)	T-8	C-7A	2.63/66.8	1.04/26.4	180	1,500
50072	KL20XE*		26	0.192	SV8.5mm	Festoon 10mm	C-8	1.45/37.0	0.40/10.0	50	5,000
40706	43		2.5	0.5	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	6.29	3,000
40716	44		6.3	0.25	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	11.31	3,000
40730	47		6.3	0.15	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	6.29	3,000
40738	48ESB5		48	0.04	Slide Base 5 (TS5)	T-2	CC-2F	0.92/23.4	0.27/6.9		5,000
50086	KO10XE*		13.5	0.37	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	50	5,000
50090	KO16XE*		13.5	0.74	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	120	5,000
40740	48MB		48	0.05	Miniature Bayonet (BA9s)	T-2 1/2	C-2F	1.19/30.2	0.33/8.4	6.29	10,000
40742	48PSB5		48	0.05	Slide Base 5 (TS5)	T-2	C-7A	1.11/28.2	0.27/6.9		10,000
40744	49		2 V	0.06	Miniature Bayonet (BA9s)	T-3 1/4	C-6	1.19/30.2	0.43/11.0	0.50	1,000
40746	50		7.5	0.22	Miniature Screw (E10)	G-3 1/2	C-2R	0.94/23.9	0.43/11.0	12.57	1,000
40760	52		14.4	0.1	Miniature Screw (E10)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	9.43	1,000
50092	KO20XE*		26	0.192	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	50	5,000
50094	KO23XE*		26	0.385	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	120	3,000
50044	16120X		12.8	1.35	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.53/38.9	0.62/15.8	200	10,000
40024	C2A		110	0.0018	Wire Leads (WL) (1.25" Leads)	T-2	Neon	0.75/19.1	0.25/6.4		25,000
40029	C7A		110	0.007	Midget Flanged (SX6s)	T-1 3/4	Neon	0.94/23.9	0.23/5.9		25,000
40030	C9A		110	0.0018	Midget Flanged (SX6s)	T-1 3/4	Neon	0.94/23.9	0.23/5.9		25,000
40034	HPR44		4	1.0	SC Miniature Flanged (PI3.5s)	T-3	C-6	1.25/31.8	0.38/9.6	54	300

Continued on next page >>>

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
40766	55		7	0.41	Miniature Bayonet (BA9s)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0	25	200
40768	55C3*		55	0.05	Slide Base 3 (TS3)	T-2	CC-2F	1.69/42.9	0.27/6.9		5,000
40771	57		14	0.24	Miniature Bayonet (BA9s)	G-4 1/2	C-2V	1.07/27.2	0.59/15.0	25	500
40820	60MB		60	0.05	Miniature Bayonet (BA9s)	T-2 1/2	CC-2F	1.19/30.2	0.33/8.4	9.18	7,500
40822	60PSB5		60	0.05	Slide Base 5 (TS5)	T-2	CC-2F	1.11/28.2	0.27/6.9		7,500
50046	921X		12.8	1.4	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.53/38.9	0.62/15.8	265	3,000
50050	1524X		24	0.3	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.53/38.9	0.62/15.8	68	2,500
40974	86		6.3	0.2	Sub-Miniature Wedge (W2.1x4.9d)	T-1 3/4	C-2F	0.80/20.3	0.23/5.9	5.03	20,000
40992	88		6.8	1.91	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	190	300
40995	89		13	0.58	SC Bayonet (BA15s)	G-6	C-6	1.44/36.6	0.75/19.1	75	750
41005	90		13	0.58	DC Bayonet (BA15d)	G-6	C-6	1.44/36.6	0.75/19.1	75	750
40886	90MB		90	0.03	Miniature Bayonet (BA9s)	T-2 1/2	CC-7A	1.19/30.2	0.33/8.4	4.65	5,000
41033	93		12.8	1.04	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	190	700
41037	94		12.8	1.04	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	190	700
50054	2410X-2		24	0.417	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.53/38.9	0.62/15.8	100	3,000
40835	64		7	0.63	DC Bayonet (BA15d)	G-6	C-6	1.44/36.6	0.75/19.1	38	1,000
40850	68		13.5	0.59	DC Bayonet (BA15d)	G-6	C-6	1.44/36.6	0.75/19.1	50	5,000
40876	70		14	0.15	Sub-Miniature Wedge (W2.1x4.9d)	T-1 3/4	C-2F	0.80/20.3	0.23/5.9	18.86	100
40040	HPR50		5.2	0.85	SC Miniature Flanged (P13.5s)	T-3	C-6	1.25/31.8	0.38/9.6	85	25
40046	HPR51		6.5	0.7	SC Miniature Flanged (P13.5s)	T-3	C-6	1.25/31.8	0.38/9.6	90	25
40052	HPR52		2.8	0.85	SC Miniature Flanged (P13.5s)	T-3	C-6	1.25/31.8	0.38/9.6	35	10
40063	K222		2.33 V	0.6	Miniature Screw (E10)	TL-3	C-2R	0.93/23.6	0.38/9.6	11.82	5
40047	KPR102		2.4	0.7	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	16.34	15
40049	KPR103		3.6	0.75	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	34	15
40051	KPR118		7.2	0.55	SC Miniature Flanged (P13.5s)	B-3 1/2	C-2R	1.25/31.8	0.45/11.5	65	20
40898	73		14	0.08	Sub-Miniature Wedge (W2.1x4.9d)	T-1 3/4	C-2F	0.80/20.3	0.23/5.9	3.77	15,000
40928	74		14	0.1	Sub-Miniature Wedge (W2.1x4.9d)	T-1 3/4	C-2F	0.80/20.3	0.23/5.9	8.80	1,000
44328	79		6	0.2	Sub-Miniature Wedge (W2.1x4.9d)	T-1 3/4	C-2R	0.80/20.3	0.23/5.9	7.54	1,000
40958	81		6.5	1.02	SC Bayonet (BA15s)	G-6	C-6	1.44/36.6	0.75/19.1	75	500
40964	82		6.5	1.02	DC Bayonet (BA15d)	G-6	C-6	1.44/36.6	0.75/19.1	75	500
40972	85		28	0.04	Sub-Miniature Wedge (W2.1x4.9d)	T-1 3/4	C-2F	0.80/20.3	0.23/5.9	3.77	7,000
41048	98		13	0.62	SC Bayonet (BA15s)	G-6	C-6	1.44/36.6	0.75/19.1	75	800
40226	120MB		120	0.025	Miniature Bayonet (BA9s)	T-2 1/2	CC-7A	1.19/30.2	0.33/8.4	4.53	10,000
44022	120MB/6		120	0.052	Miniature Bayonet (BA9s)	T-2 1/2	CC-7A	1.19/30.2	0.33/8.4	17.98	3,000
40230	120PSB5		120	0.025	Slide Base 5 (TS5)	T-2	CC-7A	1.11/28.2	0.27/6.9		10,000
40229	120PSB5-NEON		120	0.0035	Slide Base 5 (TS5)	T-2	Neon	1.12/28.5	0.27/6.9		10,000
40253	120RC*		120	0.025	Candelabra Screw (E12)	T-2	CC-7A	1.22/31.0	0.91/23.1		7,500
40058	HPR53		4	0.85	SC Miniature Flanged (P13.5s)	T-3	C-6	1.25/31.8	0.38/9.6	48	25
40237	123		1.25 V	0.3	Miniature Screw (E10)	G-3 1/2	S-2	0.94/23.9	0.43/11.0	1.26	10
40238	124		14	0.27	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	18.86	5,000
40249	130MB		130	0.025	Miniature Bayonet (BA9s)	T-2 1/2	CC-7A	1.19/30.2	0.33/8.4	4.53	10,000
40252	131		1.3 V	0.1	Miniature Screw (E10)	G-3 1/2	S-2	0.94/23.9	0.43/11.0	0.38	50
40278	147		7	0.43	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2	25	1,500
40296	155MB		155	0.025	Miniature Bayonet (BA9s)	T-2 1/2	CC-7A	1.19/30.2	0.33/8.4	5.03	10,000

Continued on next page >>>

Miniature

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
40031	HPR36		5.5	1.0	SC Miniature Flanged (P13.5s)	T-3	C-6	125/31.8	0.38/9.6	93	40
44000	HPR40		6	0.67	SC Miniature Flanged (P13.5s)	T-3	C-6	125/31.8	0.38/9.6	75	50
40298	155PSB5		155	0.025	Slide Base 5 (TS5)	T-2	CC-7A	1.11/28.2	0.27/6.9		10,000
40303	159		6.3	0.15	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2	4.27	5,000
40304	161		14	0.19	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	12.57	4,000
40317	168		14	0.35	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	38	1,500
40424	192		13	0.33	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	38	1,000
40426	193		14	0.33	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	25	15,000
40427	194		14	0.27	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	25	2,500
43210	901R		12.8	0.31	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
42442	194R		14	0.27	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2		2,500
40454	210		6.5	1.78	DC Bayonet (BA15d)	B-6	C-6	1.75/44.5	0.79/20.1	190	100
42312	211-2/F		12.8	0.97	SV8.5mm	Festoon 10mm	C-8	1.72/43.7	0.42/10.54	150	1,000
40836	656		28	0.06	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	7.79	2,500
40837	657		28	0.08	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	7.79	15,000
42272	658		14	0.08	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	3.90	15,000
40852	680		5	0.06	Wire Leads (WL)	T-1	C-2R	0.25/6.4	0.13/3.2	0.38	60,000
40856	683		5	0.06	Wire Leads (WL)	T-1	C-2R	0.25/6.4	0.13/3.2	0.63	25,000
40872	685		5	0.06	Sub-Midget Flanged (SX4s)	T-1	C-2R	0.38/9.7	0.13/3.2	0.63	25,000
40884	715		5	0.115	Wire Leads (WL)	T-1	C-2R	0.25/6.4	0.13/3.2	1.89	40,000
40932	755		6.3	0.15	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	4.15	20,000
40934	756		14	0.08	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	3.90	15,000
40936	757		28	0.08	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.40/10.2	7.79	15,000
41004	895		40	0.53	DC Bayonet (BA15d)	S-8	CC-6	2.00/50.8	1.04/26.4	175	3,800
42141	901		12.8	0.31	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	36	500
43201	901A		12.8	0.31	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
43204	901B		12.8	0.31	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
43207	901C		12.8	0.31	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
41014	908		6	1.5	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	150	50
41016	909		6	0.62	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	38	50
41017	912		12.8	1.0	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	150	1,000
41021	915		12	0.75	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	140	50
41024	917		12	1.2	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.49/37.9	0.62/15.8	125	1,200
41025	918		12.8	0.56	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	82	500
43302	918A		12.8	0.56	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
43305	918B		12.8	0.56	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
43308	918C		12.8	0.56	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
43311	918R		12.8	0.56	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		500
41026	921		12.8	1.4	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	265	1,000
42512	921LL		12.8	1.4	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	265	2,000
41031	923		12.8	0.91	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	155	500
41032	928		28	0.3	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.49/37.9	0.62/15.8	75	500
40158	1004		12.8	0.94	DC Bayonet (BA15d)	B-6	C-6	1.75/44.5	0.79/20.1	190	200
44318	7C7/130V-W		130	0.0538	Candelabra Screw (E12)	C-7	C-7A	2.30/58.4	0.88/22.3	n/a	3,000
40259	1383TF		13	1.5	SC Bayonet (BA15s)	R-12	CC-8	2.63/66.8	1.55/39.4		300
40607	335		28	0.04	Midget Screw (E5)	T-1 3/4	C-2F	0.72/18.3	0.23/5.9	4.27	4,000
49458	E85		28	0.04	Sub-Miniature Wedge (W2x4.6d)	T-1 1/2	C-2F	0.80/20.3	0.20/5.1	3.77	7,000
49454	E73		14	0.08	Sub-Miniature Wedge (W2x4.6d)	T-1 1/2	C-2F	0.80/20.3	0.20/5.1	3.77	15,000
49453	E37		14	0.09	Sub-Miniature Wedge (W2x4.6d)	T-1 1/2	C-2F	0.80/20.3	0.20/5.1	6.29	2,500

Continued on next page >>>

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
49620	655		28	0.2	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2F	1.06/26.9	0.40/10.2	38	7,000
49635	1143		12.5	1.98	SC Bayonet (BA15s)	RP-11	C-2R	2.25/57.2	1.42/36.1	400	400
49636	1143IF*		12.5	1.98	SC Bayonet (BA15s)	RP-11	C-2R	2.25/57.2	1.42/36.1		400
40756	51		7.5	0.22	Miniature Bayonet (BA9s)	G-3 1/2	C-2R	0.94/23.9	0.43/11.0	12.57	1,000
49695	1414		14	0.46	Miniature Bayonet (BA9s)	T-4 1/2	C-2R	1.38/35.0	0.59/15.0	75	500
49697	1464		22	0.25	Miniature Bayonet (BA9s)	G-5	C-6	1.19/30.2	0.62/15.8	48	250
49106	2181		6.3	0.2	Wire Leads (WL)	T-1 3/4	C-2F	0.52/13.2	0.23/5.9	5.03	20,000
49701	219		6.3	0.25	Miniature Bayonet (BA9s)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	6.29	5,000
49703	245		2.46	0.5	Miniature Screw (E10)	G-3 1/2	C-2R	0.94/23.9	0.43/11.0	11.31	15
49707	265		28	0.08	Miniature Bayonet (BA9s)	G-3 1/2	C-2F	0.94/23.9	0.43/11.0	9.43	5,000
49448	301		28	0.17	SC Bayonet (BA15s)	G-5	C-2F	1.38/35.1	0.62/15.8	38	500
49787	359		1.35 V	0.06	Miniature Screw (E10)	G-3 1/2	S-2	0.94/23.9	0.43/11.0	0.25	50
49712	7374		28	0.04	Bi-Pin .125 (G3.17)	T-1 3/4	C-2F	0.60/15.2	0.23/5.9	1.89	10,000
49683	939		6	0.9	Miniature Wedge (W2.1x9.5d)	T-5	C-6	1.49/37.9	0.62/15.8	63	75
49621	949		130	0.022	Miniature Bayonet (BA9s)	T-3 1/4	2C-2F	1.19/30.2	0.43/11.0	5.03	7,000
49080	1204		28	0.71	DC Bayonet (BA15d)	S-8	C-6	2.00/50.8	1.04/26.4	265	400
40234	1224		32	0.16	DC Bayonet (BA15d)	G-6	C-2F	1.44/36.6	0.75/19.1	48	200
49696	1447		18	0.15	Miniature Screw (E10)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	18.86	250
00647	1638		28	1.02	DC Bayonet (BA15d)	S-8	2C-6	2.00/50.8	1.04/26.4	400	500
49563	25T8DC-120V		120	0.21	DC Bayonet (BA15d)	T-8	C-7A	2.63/66.8	1.04/26.4	180	1,500
44300	8-3995		120	0.025	Miniature Bayonet (BA9s)	T-3 1/4	CC-7A	1.19/30.2	0.43/10.9	4.53	7,500
49056	7377		6.3	0.075	Bi-Pin .125 (G3.17)	T-1 3/4	C-2R	0.60/15.2	0.23/5.9	2.90	1,000
49713	7646		14	0.08	Bi-Pin .100 (G2.54)	T-1 1/4	C-2R	0.60/15.2	0.17/4.3	6.29	1,000
49562	921-FR*		12.8	1.4	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8		1,000
49622	967		120	0.025	Miniature Bayonet (BA9s)	T-3 1/4	CC-7A	1.19/30.2	0.43/11.0	4.53	7,500
49709	367		10	0.04	Midget Flanged (SX6s)	T-1 3/4	C-2F	0.63/16.0	0.23/5.9	1.00	5,000
49549	48C2		48	0.035	Slide Base 2 (TS2)	T-2	C-2F	1.69/42.9	0.27/6.9		10,000
49717	656/18V		18	0.33	Candelabra Screw (E12)	S-6	C-6	1.88/47.8	0.75/19.1	50	1,500
49618	1062		40	0.92	DC Bayonet (BA15d)	RP-11	C-2V	2.25/57.2	1.42/36.1	630	100
49624	1450		24	0.035	Miniature Bayonet (BA9s)	G-3 1/2	C-2F	0.94/23.9	0.43/11.0	2.90	3,000
49790	1820BTS		28	0.1	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	20.11	1,000
44014	10ESB5*		10	0.035	Slide Base 5 (TS5)	T-2	C-6	0.92/23.4	0.27/6.9		10,000
40765	55C2		55	0.05	Slide Base 2 (TS2)	T-2	C-2F	1.69/42.9	0.27/6.9		5,000
49671	130		6.3	0.15	Miniature Bayonet (BA9s)	G-3 1/2	C-2R	0.94/23.9	0.43/11.0	4.02	5,000
49674	257		14	0.27	Miniature Bayonet (BA9s)	G-4 1/2	C-2R	1.07/27.2	0.59/15.0		500
49726	432		18	0.25	Miniature Screw (E10)	G-4 1/2	C-2V	1.07/27.2	0.59/15.0	44	250
49682	927		6	1.2	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	100	50
00198	2741MF		24	0.05	MF Series (B8.5d)	T-1 1/2	C-2V	0.925/23.5	0.20/5.1	6.03	1,000
42223	2741		24	0.05	Sub-Miniature Wedge (W2x4.6d)	T-1 1/2	C-2V	0.80/20.3	0.20/5.1	6.03	1,000
16043	555-B		6.3	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2		3,000
16044	555-G		6.3	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2		3,000
16045	555-R		6.3	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2		3,000
16046	555-Y		6.3	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2		3,000
44017	24E1		24	0.035	Slide Base 1 (TS1)	T-2	C-2F	1.69/42.9	0.27/6.9	1.89	10,000
49731	1028.09.527-501		130	0.02	Miniature Bayonet (BA9s)	T-3 1/4	2C-2F	1.19/30.2	0.43/11.0	4.02	20,000
00025	47-B		6.3	0.15	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
00027	47-R		6.3	0.15	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
00028	47-Y		6.3	0.15	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
00356	906G*		13	0.69	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.49/37.9	0.62/15.8		1,000
00357	906R		13	0.69	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.49/37.9	0.62/15.8		1,000
00358	906B		13	0.69	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.49/37.9	0.62/15.8		1,000

Continued on next page >>>

Miniature

Order Code	Item	Usage	Volts	Amps	Base	Bulb	Filament	MOL in/mm	MOD in/mm	Lumens	Life/Hrs
05584	K010XE/F*		13.5	0.37	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	50	5,000
05586	K016XE/F*		13.5	0.74	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	120	5,000
05588	K020XE/F*		26	0.192	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	50	5,000
49503	7362		5	0.115	Bi-Pin .125 (G3.17)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	1.89	40,000
00613	1446		12	0.2	Miniature Screw (E10)	G-3 1/2	C-2V	0.94/23.9	0.43/11.0	21.37	250
00618	1480		18	0.17	Candelabra Screw (E12)	T-4	C-7A	1.97/50.0	0.54/39.1	25	1,500
49627	1680		6	4.1	SC Bayonet (BA15s)	S-8	C-6	2.00/50.8	1.04/26.4	400	300
06431	PC37		14	0.09	Printed Circuit socket (P8.25d)	T-1 3/4	C-2F	0.82/20.8	0.23/5.9	6.29	2,500
05590	K023XE/F*		26	0.385	SV8.5mm	Festoon 10mm	C-8	1.73/44.0	0.40/10.0	120	3,000
16026	2102		18	0.04	Wire Leads (WL)	T-1 3/4	C-2F	0.52/13.2	0.23/5.9	1.89	10,000
01034	267		6.3	0.15	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0	4.15	5,000
16024	20-99		13	1.08	SC Bayonet (BA15s)	G-16.5	C-6	3.00/76.2	2.12/53.9	150	1,000
16025	20-99F		13	1.08	SC Bayonet (BA15s)	G-16.5	C-6	3.00/76.2	2.12/53.9		1,000
49053	2841		24	0.125	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2V	1.06/26.9	0.40/10.2	22.12	1,000
01183	338		2.7	0.06	Midget Flanged (SX6s)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	0.50	6,000
01185	342		6	0.04	Midget Screw (E5)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	0.38	10,000
49460	35A2		35	0.04	Slide Base 2 (TS2)	T-2	C-2F	1.69/42.9	0.27/6.9		7,500
05198	44-A		6.3	0.25	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
01347	44-B		6.3	0.25	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
01349	44-G		6.3	0.25	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
01351	44-R		6.3	0.25	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
49634	456		28	0.17	Miniature Bayonet (BA9s)	G-4 1/2	C-2F	1.07/27.2	0.59/15.0	25	5,000
49462	45675		14	0.046	Bi-Pin .100 (G2.54)	T-1 1/4	C-2F	0.60/15.2	0.17/4.3	1.51	
05223	45685		14	0.06	Bi-Pin .100 (G2.54)	T-1 1/2	C-2F	0.60/15.2	0.19/4.8	0.38	
05203	555-P		6.3	0.25	Miniature Wedge (W2.1x9.5d)	T-3 1/4	C-2R	1.06/26.9	0.40/10.2		3,000
81173	718		5	0.115	Sub-Midget Flanged (SX4s)	T-1	C-2R	0.38/9.7	0.13/3.2	1.89	40,000
81145	7333		5	0.06	Midget Flanged (SX6s)	T-1 3/4	C-2R	0.63/16.0	0.23/5.9	0.63	25,000
01785	89K		13	0.58	Candelabra Screw (E12)	G-6	C-2R	1.38/35.1	0.75/19.1	75	750
01353	44-Y		6.3	0.25	Miniature Bayonet (BA9s)	T-3 1/4	C-2R	1.19/30.2	0.43/11.0		3,000
07753	PC119		14	0.15	Printed Circuit socket (P8.25d)	T-2 1/4	C-2V	2.28/58	0.28/7.14	15.08	3,000
07999	PC579		12.8	0.8	Printed Circuit socket (B10d)	T-5	C-2R		0.62/15.8	115	200
49724	6614F-BP		14	0.05	Double End Cap (SF6/6)	T-2	C-8	1.26/32.0	0.24/6.1	2.01	10,000
43300	918-BP		12.8	0.56	Miniature Wedge (W2.1x9.5d)	T-5	C-2R	1.49/37.9	0.62/15.8	82	500
08305	949-BP		130	0.022	Miniature Bayonet (BA9s)	T-3 1/4	2C-2F	1.19/30.2	0.43/11.0	5.03	7,000
01763	8623		28	0.04		T-1 1/4					
01814	906A		13	0.69	Miniature Wedge (W2.1x9.5d)	T-5	C-2F	1.49/37.9	0.62/15.8	75	1,000
00723	1820R		28	0.1	Miniature Bayonet (BA9s)	T-3 1/4	C-2F	1.19/30.2	0.43/11.0	20.11	1,000

2	46	24X	48	60PAR30LN/H/FL-120V	23	259	47
3S6/5-120V	31, 45	25S11-2C	36	60PAR30LN/H/NFL-120V	23	265	51
3S6/5-130V	31, 45	25S11-5C	36	60PAR30LN/H/SP-120V	23	267	52
3S6/5DC-120V	31, 45	25T6-1/2DC-130V	32, 48	60PAR38/H/FL-120V	23	293	47
4C7/120V	31, 45	25T6-1/2N-130V	32, 47	60PAR38/H/SP-120V	23	301	51
4C7/130V	31, 45	25T6.5N/F-130V	32, 47	60PAR38/H/WFL-120V	23	303	47
6MB	45	25T6C-120V	32, 48	60PSB5	49	306	47
6PSB5	45	25T8C-120V	32, 48	64	49	307	47
6S6/6V	31, 45	25T8/DC	34, 37	65BR30/FL-120V	31	308	47
6S6/12V	31, 46	25T8DC-120V	32, 51	65BR30/FL-130V	31	311	47
6S6/18V	31, 51	25T8DC-130V	32, 45	65BR30/SP-120V	31	313	45
6S6/24V	31, 46	25T8N-130V	32, 45	65BR30/SP-130V	31	327	45
6S6/30V	31, 46	25T10-130V	32, 48	65BR40/FL-120V	31	328	45
6S6/48V	31, 46	25T10/F-130V	32, 47	65BR40/FL-130V	31	330	45
6S6/60V	31, 46	27	45	68	49	334	45
6S6/120V	31, 46	28ESB5	45	70	49	335	51
6S6/130V	31, 44	28MB	45	70PAR38/H/FL-120V	23	337	45
6S6/145V	31, 44	28PSB5	45	70PAR38/H/SP-120V	23	338	52
6S6/155V	31, 46	29A/CL/H-120V	23	70PAR38/H/WFL-120V	23	342	52
6S6/230V	31, 46	30R20/FL-130V	31	72A/CL/H-120V	23	344	45
6S6DC/6V	47	31	43	73	49	356	45
6S6DC/6V	32	35A2	52	74	49	359	51
6S6DC/12V	31, 45	35PAR20/H/NFL-120V	23	75A/RS	30	363	43
6S6DC/24V	32, 45	35PAR20/H/SP-120V	23	75A/RS-12V	30	367	51
6S6DC/30V	32, 45	35PAR30/H/FL-120V	23	75A/RS/TF	30	370	45
6S6DC/32V	32, 44	35PAR30LN/H/FL-120V	23	77A/S8	46	373	45
6S6DC/48V	32, 44	35PAR30LN/H/NFL-120V	23	79	49	376	45
6S6DC/120V	31	35PAR30LN/H/SP-120V	23	80-A	35	377	45
6S6DC/130V	31, 44	35PAR38/H/FL-120V	23	81	49	378	45
6S6DC/145V	32, 44	35PAR38/H/SP-120V	23	82	49	379	45
7C7/120V	31, 44	40	48	85	49	381	45
7C7/130V	31, 44	40A15-130V	30	86	49	382	45
7C7/130V-W	31, 51	40A15-230/250V	30	87	47	385	46
7C9-120V-INT	31	40A15/F-130V	30	88	49	386	46
8-3995	51	40A15/F-230/250V	30	89	49	387	46
10C7/120V	31	40S11N	32	89K	52	388	46
10C7DC/120V	31, 44	40T6-1/2N-130V	32, 45	90	49	394	46
10ESB5	51	40T10-130V	32, 45	90MB	49	399	46
10S6/120V	32	40T10/F-130V	32, 45	93	49	400	46
10S6/230V	32, 44	41	48	94	49	407	43
10S6/250V	32	43	48	98	49	425	43
10S6DC/250V	32, 44	43A/CL/H-120V	23	100A/RS	30	428	43
10S11N	35	44	48	100A/RS-12V	30	432	51
10S11NF	35	44-A	52	100A/RS/TF	30	455	46
12ESB5	46	44-B	52	112	48	456	52
12MB	46	44-G	52	120MB	50	464	47
12PSB5	46	44-R	52	120MB/6	50	502	43
13	48	44-Y	52	120MB-NEON	47	503	47
14	48	45BR30/FL-120V	31	120PSB5	50	509K	47
15S11-13	35	45R20/FL-120V	31	120PSB5-NEON	50	555	47
15S11-14	35	45R20/FL-130V	31	120RC	50	555-B	51
15S11-87	35	46	48	123	50	555-G	52
15S11/102CL	35	47	48	124	50	555-P	52
15S11/102IF	35	47-B	52	125T10P	38	555-R	52
15S11-F	35	47-R	52	130	51	555-Y	52
15T4C-130V	32	47-Y	52	130MB	50	558	47
15T6C-120V	32	48	48	131	50	563	43
15T6C-130V	32, 47	48C2	51	147	50	585	47
15T6C-145V	32, 47	48ESB5	48	150A/RS	30	605	43
15T7C-130V	32, 44	48MB	49	150A/RS/TF	30	623	47
15T7DC-130V	32, 44	48PSB5	49	150BT15/H/W	24	624	44
15T7N-130V	32, 46	49	49	150P25/10	37	631	45
16ESB5	47	50	49	150T10/H/F	34, 38	655	51
17	47	50A/RS	30	155MB	50	656	50
20-99	52	50A/RS-12V	30	155PSB5	50	657	50
20-99F	52	50A/RS/TF	30	159	50	658	50
20T6-1/2DC-130V	32, 47	51	51	161	50	680	50
20T6-1/2F-130V	32, 45	52	49	168	50	683	50
20T6-1/2N-130V	32, 45	53	43	192	50	685	50
20T6-1/2N-145V	32, 47	53A/CL/H-120V	23	193	50	715	50
20T6.5DC/F-130V	32, 45	55	49	194	50	718	52
24	45	55A/S8	48	194R	50	755	50
24CSB	45	55C2	51	210	50	756	50
24E1	52	55C3	49	211-2/F	50	757	50
24E2	44	56	46	219	51	778	43
24E3	45	57	49	222	47	778	36
24ESB5	45	60MB	49	243	47	787	44
24EX	45	60PAR30/H/FL-120V	23	245	51	787	35
24MB	45	60PAR30/H/NFL-120V	23	250T10/H/F	35, 39	795	44
24PSB5	45	60PAR30/H/SP-120V	23	257	51	795X	47

Index

796	44	1487	48	7371	44	41348	36
895	50	1493	48	7373	44	41350	36
901	50	1495	45	7374	51	41360	36
901A	50	1507	36	7377	51	41364	35
901B	50	1524X	49	7381	44	41366	36
901G	50	1630	36	7382	44	41368	36
901R	50	1631X	36	7387	44	42003	47
906A	52	1634	36	7511	45	42005	47
906B	52	1638	51	7537	45	42006	47
906G	52	1662	47	7632	44	45675	52
906R	52	1680	52	7646	51	45685	52
908	50	1683	43	7683	44	49407	24
909	50	1691	43	7714	44	49408	24
912	50	1692	43	7715	44	64260	36
912LL	43	1768	43	7839	44	64514	39
915	50	1769	43	8001	36	71818	37
917	50	1775	43	8013	35	76907	36
918	50	1810	43	8017	36	77903	36
918A	50	1813	43	8018	36	77904	36
918B	50	1815	43	8022	36	77910	36
918-BP	52	1816	43	8100	36	56016164	36
918G	50	1818	43	8111	44	56018566	36
918R	50	1819	43	8362	44	AI-010-28	36
921	50	1820	43	8623	52	AI-420-10	37
921-FR	51	1820BTS	51	8627	44	AIA	47
921LL	51	1820R	52	8640	44	AIB	48
921X	49	1821	43	8918	47	AIH	48
923	51	1822	43	11143	36	A2B	47
927	51	1828	43	16073	37	A3C	46
928	51	1829	43	16120X	49	A9A	48
939	51	1835	43	17002	29	A-62	43
949	51	1847	48	17004	29	BI-010-28	36
949-BP	52	1850	48	17006	29	BIA	48
967	51	1864	48	17008	29	B2A	48
1004	51	1866	48	17010	29	B5-011-32	37
1028.09.527-501	52	1873	48	17012	29	B7A	45
1062	51	1888	48	17014	29	BAB	24
1073	47	1889	48	17016	29	BAB-BLACK	24
1076	47	1891	48	17018	29	BAB-FG	24
1096	36	1892	48	17022	29	BAB-FG-GUI0-120V	24, 26
1096X	36	1893	48	17030	29	BAB-SILVER	24
1130	47	1895	48	17032	29	BBA	35, 39
1133	44	1906	44	17040	29	BCA	35, 39
1141	47	2102	52	17042	29	BCK	40
1141IF	43	2114	46	17046	29	BFK/BFL	41
1142	47	2162	46	17048	29	BFM	36
1143	51	2174	46	17050	29	BKV	37
1143IF	51	2176	46	17052	29	BLC	37
1156	43	2181	51	18002	29	BLR	38
1156A	43	2182	46	18003	29	BNF	38
1157	43	2187	46	18007	29	BRH	41
1176	43	2200	46	18008	29	BRL	38
1203	43	2232	46	18009	29	BTG	41
1204	51	2233	46	18011	29	BTL	40
1210X	47	2410X-1	48	18012	29	BTN	41
1211X	48	2410X-2	49	18014	29	BTP	41
1224	51	2450X	48	35001	29	BTR	41
1236X	47	2470X	48	35002	29	BVT	41
1250X	43	2475X-1	48	35003	29	BVW	41
1250X-2	43	2721	46	35004	29	BWA	41
1250X-5	44	2741	51	35006	29	BWF	41
1251	43	2741MF	51	35008	29	BXE	38
1252	47	2821	44	35011	29	BZW	37
1309	47	2825	46	35012	29	C2A	49
1383	47	2841	52	41304	35	C7A	49
1383TF	51	2860X	48	41306	36	C9A	49
1385	47	04900	35	41308	35	CAX	37
1408	48	6022	43	41310	36	CAX-130V	37
1414	51	6612F	47	41312	36	CAX-130V-HAL	37
1446	52	6614F	47	41314	35	CBA	40
1447	51	6614F-BP	52	41318	36	CBX/CBS	38
1449	48	6615F	45	41320	35	CDD	37
1450	51	6833	43	41324	35	CDJ	38
1450X	44	6838	48	41326	36	CDS/CDX	38
1460	36	6839	48	41328	36	CEA/CEB/CDK	38
1460X	36	7219	48	41334	36	CEM	38
1464	51	7327	43	41338	35	CEW/CFC	38
1468X	36	7328	44	41340	36	CHK	38
1477	48	7333	52	41344	36	CLS/CLG	39
1480	52	7362	52	41346	36	CMP20/PAR20/FL	16

CMP20/PAR20/SP.....	16	DT36/30/RS.....	8	EL-3B.....	35	EYV.....	40
CMP20/PAR30LN/FL.....	16	DT36/35/RS.....	8	EL-12B.....	36	EYW.....	40
CMP20/TC/930.....	17	DT36/41/RS.....	8	ELB.....	38	EYX.....	40
CMP20/TM/930.....	17	DT36/50/RS.....	8	ELC.....	34, 39	F4T5/BL.....	12
CMP35/PAR20/FL.....	16	DT36/65/RS.....	8	ELC/5.....	39	F4T5/BLB.....	12
CMP35/PAR20/SP.....	16	DT40/30/RS.....	8	ELC/5H.....	39	F4T5/CW.....	12
CMP35/PAR30LN/FL.....	16	DT40/35/RS.....	8	ELC/E.....	34, 39	F4T5/D.....	12
CMP35/PAR30LN/FL/842.....	16	DT40/41/RS.....	8	ELD/EJN.....	38	F6T5/CW.....	12
CMP35/PAR30LN/SP.....	16	DT40/50/RS.....	8	ELE.....	38	F6T5/D.....	12
CMP35/T6/930.....	17	DT40/65/RS.....	8	ELH.....	34, 39	F6T5/WW.....	12
CMP35/T6/942.....	17	DT50/30/RS.....	8	ELH/5.....	39	F8T5/BL.....	12
CMP35/TC/930.....	17	DT50/35/RS.....	8	EMD.....	41	F8T5/BLB.....	12
CMP70/C/MP/4K.....	17	DT50/41/RS.....	8	EMM/EKS.....	39	F8T5/CW.....	12
CMP70/MP/3K.....	17	DT50/50/RS.....	8	ENG.....	39	F8T5/D.....	12
CMP70/MP/4K.....	17	DT55/30/RS.....	8	ENH.....	34, 39	F8T5/WW.....	12
CMP70/PAR30LN/FL.....	16	DT55/35/RS.....	8	ENL.....	25	F10T8/CW.....	14
CMP70/PAR30LN/SP.....	16	DT55/41/RS.....	8	ENX.....	40	F13T5/CW.....	12
CMP70/PAR38/FL.....	16	DT55/50/RS.....	9	ENX/5.....	40	F13T5/D.....	12
CMP70/PAR38/SP.....	16	DT55/65/RS.....	9	ENZ.....	38	F13T5/WW.....	12
CMP70/T6/930.....	17	DTJ.....	41	EPN.....	38	F13T8/CW.....	14
CMP70/T6/942.....	17	DVY.....	40	EPZ.....	38	F14T5/835.....	11
CMP70/TC/930.....	17	DWT.....	41	ESB/FHE.....	36	F14T5/841.....	11
CMP70/TD/930.....	17	DYH.....	40	ESD.....	34, 38	F14T5/865.....	11
CMP70/TD/942.....	17	DYS/DYV/BHC.....	40	ESD250-SE-D.....	33	F14T8/CW.....	14
CMP100/C/MP/3K.....	17	DYS/DYV/BHC/5.....	40	ESD575/2-SE-D7.2.....	33	F14T8/D.....	14
CMP100/C/MP/4K.....	17	DYY/EGH.....	40	ESD575-SE-D.....	33	F15T8/BL.....	14
CMP100/MP/3K.....	17	DZA.....	37	ESH.....	38	F15T8/BLB.....	14
CMP100/MP/4K.....	17	DZE/FDS.....	38	ESI575-DE.....	33	F15T8/CW.....	14
CMP150/MP/3K.....	17	E37.....	51	ESI200-DE.....	33	F15T8/D.....	14
CMP150/MP/4K.....	17	E73.....	51	ESJ.....	34, 38	F15T8/WW.....	14
CMP150/T6/930.....	17	E85.....	51	ESL.....	34, 38	F17T8/830K.....	12
CMP150/T6/942.....	17	EAJ.....	35, 41	ESM.....	35, 39	F17T8/835K.....	12
CMP-MR16/20W/NFL/830.....	17	EBV.....	35, 40	ESN.....	34, 38	F17T8/841K.....	12
CMP-MR16/20W/SP/830.....	17	EBV-LN.....	35, 40	ESP.....	34, 39	F17T8/850K.....	12
CMP-MR16/39W/NFL/830.....	17	EBW.....	35, 40	ESR.....	34, 38	F21T5/835.....	11
CMV/CMT.....	39	ECA.....	35, 39	ESR575-SE-HR.....	33	F21T5/841.....	11
CXK.....	39	ECA-LN.....	35, 39	ESR800-SE-HR.....	33	F24T5/H0/835.....	11
CYC.....	39	ECT.....	35, 40	ESR1200-SE-NHR.....	33	F24T5/H0/841.....	11
CZX/DAB.....	40	ECT-LN.....	35, 40	ESS.....	35, 39	F25T8/830K.....	12, 13
DDJ/DZZ.....	38	EFM.....	38	ESX.....	24	F25T8/835K.....	12, 13
DDL.....	38	EFN.....	38	ESX-FG.....	24	F25T8/841K.....	12, 13
DDM.....	38	EFP.....	38	ESY.....	39	F28T5/835.....	11
DDS.....	38	EFR.....	38	ETB.....	35, 39	F28T5/841.....	11
DMX.....	40	EGE.....	40	ETC.....	34, 39	F28T5/850.....	11
DNF.....	38	EGF.....	41	ETE.....	34	F28T5/865.....	11
DPT.....	41	EGG.....	41	ETE.....	38	F28T8/830/ES.....	13
DPW.....	41	EGN.....	40	ETG.....	34, 39	F28T8/835/ES.....	13
DPY.....	41	EGR.....	41	ETJ.....	39	F28T8/841/ES.....	13
DRA.....	39	EGT.....	41	EVA.....	37	F28T8/850/ES.....	13
DRB/DRC.....	41	EHA.....	40	EVC/FGX.....	39	F28T8/865/ES.....	13
DRS.....	41	EHC/EHB.....	40	EVD.....	40	F31T8/830/U.....	15
DRW.....	41	EHD.....	40	EVR.....	35, 40	F31T8/835/U.....	15
DT5/27.....	8	EHF.....	41	EVW.....	34, 39	F31T8/841/U.....	15
DT5/41.....	8	EHG.....	41	EXN.....	25	F31T8/850/U.....	15
DT5/65.....	8	EHJ.....	39	EXN-BLACK.....	25	F32T8/830/ES/25W.....	12, 13
DT7/27.....	8	EHM.....	39	EXN-FG.....	25	F32T8/830K.....	12
DT7/35.....	8	EHP.....	39	EXN-FG-24V.....	25	F32T8/830K/HL.....	13
DT7/41.....	8	EHR.....	40	EXN-FG-GUI0-130V.....	25, 26	F32T8/830K/XL.....	13
DT7/50.....	8	EHT.....	35, 39	EXN-SILVER.....	25	F32T8/835K.....	12
DT7/65.....	8	EHZ.....	39	EXR.....	39	F32T8/835K/HL.....	13
DT9/27.....	8	EI-77Z.....	36	EXR/5.....	39	F32T8/835K/U6.....	15
DT9/35.....	8	EI-722.....	36	EXT.....	25	F32T8/835K/XL.....	13
DT9/41.....	8	EI-738.....	36	EXT-FG.....	25	F32T8/841/ES/25W.....	12, 13
DT9/50.....	8	EI-886.....	36	EXT-FG-24V.....	25	F32T8/841K.....	12
DT9/65.....	8	EI-2201.....	36	EXV.....	38	F32T8/841K-C.....	14
DT13/27.....	8	EI-74000.....	37	EYX.....	39	F32T8/841K/HL.....	13, 14
DT13/30.....	8	EI-B153.....	36	EXZ.....	25	F32T8/841K/U6.....	15
DT13/35.....	8	EI-M102.....	37	EXZ-BLACK.....	25	F32T8/841K/XL.....	13
DT13/41.....	8	EJA.....	38	EXZ-FG.....	25	F32T8/850/ES/25W.....	13
DT13/50.....	8	EJG.....	41	EXZ-SILVER.....	25	F32T8/850K.....	12, 13
DT13/65.....	8	EJL.....	34, 39	EYA.....	34, 39	F32T8/850K-C.....	14
DT18/30/RS.....	8	EJM.....	38	EYB.....	40	F32T8/850K/HL.....	13, 14
DT18/35/RS.....	8	EJV.....	34, 38	EYB/5.....	40	F32T8/850K/U6.....	15
DT18/41/RS.....	8	EJY.....	37, 38	EYC.....	25	F32T8/850K/XL.....	13
DT18/50/RS.....	8	EKB.....	40	EYC-FG.....	25	F32T8/865/ES/25W.....	13
DT24/30/RS.....	8	EKD.....	41	EYF.....	25	F32T8/865K.....	12
DT24/35/RS.....	8	EKE.....	38	EYH/FKT.....	39	F32T8/865K/HL.....	13, 14
DT24/41/RS.....	8	EKP/ENA.....	38	EVJ.....	25	F32T8/865K/XL.....	13
DT24/50/RS.....	8	EKZ.....	37	EYK.....	39	F35T5/830.....	11
DT24/65/RS.....	8	EL-2B.....	35	EYS.....	25	F39T5/H0/835.....	11

Index

F39T5/H0/841	11	FTD	24	JC12V5W-FR	28	LED-24-BA9S-W	42
F40T12/CW/HE	14	FTD-FG	24	JC12V20W	28	LED-24-BA9S-Y	42
F49T5/H0/835	11	FTE	24	JC12V20WH20	28	LED-24-FESTOON-W	43
F49T5/H0/841	11	FTE-FG	24	JC12V30W	28	LED-24-MF-R	42
F49T5/H0/850	11	FTF	24	JC12V30WH20	28	LED-24-MF-W	42
F49T5/H0/865	11	FTF-FG	24	JC12V35WH20	28	LED-24-MG-W	42
F54T5/H0/830	11	FTH	24	JC12V50WH20	28	LED-24-PSB-G	42
F54T5/H0/835	11	FTH-FG	24	JC12V75WH20	28	LED-24-PSB-R	42
F54T5/H0/841	11	FTK	40	JC12V100WH20	28	LED-24-PSB-W	42
F54T5/H0/850	11	FXL	40	JC24V300W	40	LED-24-PSB-Y	42
F54T5/H0/865	11	FXL/5	40	JCD6V10WH20	28	LED-24-T1.75 WEDGE-R	42
FAD	41	G4T5	37	JCD6V20WH20	28	LED-24-T1.75 WEDGE-W	42
FAL	34, 40	G6T5	37	JCD12V5WH20	28	LED-24-T1.75 WEDGE-Y	42
FC8T9/CW	14	G8T5	37	JCD12V10WH20	28	LED-120-MB-G	42
FC8T9/D	14	G10T5L	37	JCD12V20WH20	28	LED-120-MB-R	42
FC12T9/CW	14	G10T8	37	JCD12V35WH20	28	LED-120-MB-W	42
FC12T9/D	14	G14T5/4P	37	JCD24V20WH20	28	LED-120-MB-Y	42
FC16T9/CW	14	G15T8	37	JCD130V20WG6.35	28	LED-120-PSB-G	42
FCL	40	G20T5	37	JCD130V20WG8	28	LED-120-PSB-R	42
FCM	41	G20T10	37	JCD130V25WG6.35	28	LED-120-PSB-W	42
FCR	37, 38	G25T8	37	JCD130V25WG8	28	LED-120-PSB-Y	42
FCS	37, 39	G30T8	37	JCD130V25WG9	28	LED-194-W	43
FCZ	40	G36T5/4P	37	JCD130V25WG9/F	28	LEDP-1383/30K	43
FDN	40	G36T5L	37	JCD130V35WG6.35	28	LU35/MED	20
FDT	38	G40T10	37	JCD130V35WG8	28	LU50	20
FDV	39	G55T8	37	JCD130V40WG9	28	LU50/MED	20
FEL	41	G64T5L	37	JCD130V40WG9/F	28	LU70	20
FEV	39	GBD	26	JCD130V50WG6.35	28	LU70/D/MED	20
FFN	41	GBE	26	JCD130V50WG8	28	LU70/MED	20
FFP	41	GBF	26	JCD130V50WG9	28	LU100	20
FFR	41	GBF-FR	26	JCD130V50WG9/F	28	LU100/MED	20
FFS	41	GBJ	26	JCD130V60WG9	28	LU150/55	20
FFT	41	GCA	39	JCD130V60WG9/F	28	LU150/55/MED	20
FHS	39	GDA	40	JCD130V75WG6.35	28	LU150/100	20
FKW	39	GLA	40	JCD130V75WG8	28	LU200	20
FLK	40	GLC	40	JCD130V75WG9	28	LU250	20
FLW	40	GTL-3	35, 37	JCD130V75WG9/F	28	LU250/D	20
FML18/65	10	H33CD-400	21	JCD130V100WG8	28	LU250/NC	21
FML27/27	10	H33GL-400/DX	21	JCR120V150WB	39	LU400	20
FML27/41	10	H37KB-250	21	JCR/M12V75W	38	LU400/ED28/NC	21
FML27/65	10	H37KC-250/DX	21	JCR/M12V100W	38	LU600	20
FMT	24	H38AV-100/DX	21	JCR/M14V35W	38	LU1000	20
FMT-FG	24	H38JA-100/DX	21	JDR75/FL	25	MH50/C/U/MED	18, 19
FMV	24	H38MP-100/DX	21	JDR75/MF	25	MH50/U/MED	18, 19
FMV-FG	24	H39KB-175	21	JDR75/SP	25	MH70/C/U/MED	18, 19
FMW	25	H39KC-175/DX	21	JDR100/FL	25	MH70/U/MED	18, 19
FMW-BLACK	25	H43AV-75/DX	21	JDR130V50W	25	MH100/C/U/MED	18, 19
FMW-FG	25	H46DL-40/50/DX	21	JF02XE	46	MH100/U/MED	18, 19
FMW-FG-GU10-130V	25, 26	HPL375/115V	33, 40	JF03XE	46	MH150/C/U/MED	18, 20
FMW-SILVER	25	HPL375LL/115V	33, 40	JF07XE	47	MH150/U/MED	18, 20
FNC-FG	25	HPL550/77V	34, 40	JF13XE	47	MH175/C/U	18
FND-FG	25	HPL550LL/77V	34, 40	K12	44	MH175/C/U/MED	18
FNE-FG	25	HPL575/115V	34, 40	K15	44	MH175/U	18
FNF-FG	25	HPL575/120V	34, 40	K222	49	MH175/U/MED	18
FNT	39	HPL575/230V	34, 40	KL20XE	48	MH200/C/U	18, 20
FNV	25	HPL575LL/115V	34, 40	KO10XE	48	MH200/U	18, 20
FNV-FG	25	HPL575LL/120V	34, 40	KO10XE/F	52	MH250/BU/PS	20
FPA	25	HPL750/77V	34, 41	KO16XE	48	MH250/C/U	18
FPA-FG	25	HPL750/115V	34, 41	KO16XE/F	52	MH250/U	18
FPB	25	HPL750/120V	34, 41	KO20XE	49	MH250/U/T15	18
FPB-FG	25	HPL750/230V	34, 41	KO20XE/F	52	MH320/U	18, 20
FPC	25	HPL750LL/115V	34, 41	KO23XE	49	MH350/C/HOR	20
FPC-FG	25	HPL750LL/120V	34, 41	KO23XE/F	52	MH350/HOR	18, 20
FRA-FG	25	HPL750LL/230V	34, 41	KPR2	48	MH400/BU/PS	20
FRK	41	HPR36	50	KPR4	44	MH400/C/BU/PS	20
FS-2	15	HPR40	50	KPR13	44	MH400/C/U	18
FS-4	15	HPR44	49	KPR102	49	MH400/C/U/ED28	18
FS-5	15	HPR50	49	KPR103	49	MH400/U	18
FSA	25	HPR51	49	KPR118	49	MH400/U/ED28	18
FSB	25	HPR52	49	LED-6-BA9S-W	43	MH400/U/T15	18
FSC	25	HPR53	50	LED-12-DCBAY-R	43	MH1000/U	18
FSD	25	IR53PAR30/FL	22	LED-12-DCBAY-W	42	MH1000/U/BT37	18
FSE	25	IR53PAR30LN/NFL	22	LED-12-FESTOON-W	43	MH1500/U	18
FSF	25	IR53PAR30LN/SP	22	LED-12-SCBAY-W	42	MH-DE70/TD/UVS/3K	19
FS-U-120V	15	IR53PAR30LN/WFL	22	LED-14-BA9S-G	42	MH-DE70/TD/UVS/4K	19
FTA	24	IR53PAR30/NFL	22	LED-14-BA9S-R	42	MH-DE150/TD/UVS/3K	19
FTB	24	IR53PAR30/SP	22	LED-14-BA9S-W	42	MH-DE150/TD/UVS/4K	19, 20
FTB-FG	24	IR53PAR38/FL	22	LED-14-T1.75 WEDGE-W	42	MH-SE70/UVS/3K	19
FTC	24	IR71PAR38/FL	22	LED-24-BA9S-G	42	MH-SE150/UVS/3K	19, 20
FTC-FG	24	IR71PAR38/SP	22	LED-24-BA9S-R	42	MH-SE150/UVS/4K	19, 20

MP50/U/MED/3K.....	18, 19	Q150CL/DC-120V.....	26	QT26/50.....	10	SP85/41/MED.....	5, 7
MP70/C/U/MED/3K.....	18, 19	Q150CL/DC-130V.....	26	QT26/50-4P.....	10	SP85/50/MED.....	5, 7
MP70/C/U/MED/4K.....	18, 19	Q150CL/MC/2V-130V.....	26	QT26/65.....	10	SP105/41/MED.....	5, 7
MP70/U/MED/3K.....	18	Q150CL/MC-120V.....	26	QT26/65-4P.....	10	SP105/41/MOG.....	5, 7
MP70/U/MED/4K.....	18, 19	Q150CL/MC-130V.....	26	SP5B10/E12/27K.....	4	SP105/41/MOG-277V.....	5, 7
MP100/C/U/MED/3K.....	18, 19	Q150DC-120V.....	26	SP5B13/E26/27K.....	4	SP105/50/MED.....	5, 7
MP100/C/U/MED/4K.....	18, 19	Q150T3/CL/120V.....	27	SP5B13/E26/41K.....	4	TT18/27.....	9
MP100/U/MED/3K.....	18, 19	Q150T4/CL/25.....	39	SP7B10/E12/27K.....	4	TT18/30.....	9
MP100/U/MED/4K.....	18, 19	Q150W/S120V.....	27	SP7B10/E12/41K.....	4	TT18/35.....	9
MP150/C/U/MED/3K.....	18, 20	Q150W/S130V.....	27	SP9A19/27K.....	4	TT18/41.....	9
MP150/C/U/MED/4K.....	18, 20	Q200W/S120V.....	27	SP9A19/41K.....	4	TT18/65.....	9
MP150/U/MED/3K.....	18	Q200W/S130V.....	27	SP9G25/27K.....	5	TT26/27.....	9
MP150/U/MED/4K.....	19	Q200W/S220V.....	27	SP13/27-4P.....	7	TT26/30.....	9
MP250/BU/P.....	19, 20	Q235T4/3-33V.....	37	SP13/27-GU24.....	6	TT26/35.....	9
MP320/BU.....	19, 20	Q250CL/DC-120V.....	26	SP13/27K.....	6	TT26/41.....	9
MP350/BU.....	19, 20	Q250CL/DC-130V.....	26	SP13/27K-DIM.....	6	TT26/50.....	9
MP400/BU/ED28/P.....	19, 20	Q250CL/MC-120V.....	26	SP13/35K.....	6	TT26/65.....	9
MP400/BU/P.....	19, 20	Q250CL/MC-130V.....	27	SP13/41-GU24.....	6	TT32/27.....	9
NE51H-R.....	44	Q250DC-120V.....	27	SP13/41K.....	6	TT32/30.....	9
NE51-R.....	44	Q250DC-130V.....	27	SP13/41K-DIM.....	6	TT32/35.....	9
P21/5W.....	46	Q250MC-120V.....	27	SP13/50K.....	6	TT32/41.....	9
PAR20/9/35K.....	5	Q250MC-130V.....	27	SP13/65K.....	6	TT32/50.....	9
PAR20/9/41K.....	5	Q250T3/CL/120V.....	27	SP13A19/27K.....	4	TT32/65.....	9
PAR20/9/50K.....	5	Q250W/S120V.....	27	SP13A19/41K.....	4	TT42/27.....	9
PAR30LN/15/30K.....	5	Q300T3/CL/120V.....	27	SP14/R20/27K.....	5	TT42/30.....	9
PAR30LN/15/35K.....	5	Q300T3/CL/130V.....	27	SP14/R20/41K.....	5	TT42/35.....	9
PAR30LN/15/41K.....	5	Q300T3/CL/220V.....	27	SP15A/27K-GU24.....	4	TT42/41.....	9
PAR30LN/15/50K.....	5	Q300T3/CL/240V.....	27	SP15G25/27K.....	5	TT42/50.....	9
PAR38/23/27K.....	5	Q300W/S120V.....	27	SP15G25/27K-GU24.....	5	TT42/65.....	9
PAR38/23/30.....	5	Q300W/S130V.....	27	SP15G25/41K.....	5		
PAR38/23/35.....	5	Q400W/S130V.....	27	SP15/R30/27K.....	5		
PAR38/23/41K.....	5	Q500CL/DC-120V.....	27	SP15/R30/27K-DIM.....	5		
PAR38/23/50K.....	5	Q500CL/MC-120V.....	27	SP15/R30/27K-GU24.....	5		
PC37.....	52	Q500CL/MC-130V.....	27	SP15/R30/41K.....	6		
PC119.....	52	Q500/MC-120V.....	27	SP15/R30/41K-DIM.....	6		
PC579.....	52	Q500/MC-130V.....	27	SP15/R30/50K-DIM.....	6		
PH/111A.....	34, 38	Q500T3/CL/120V.....	27	SP15/R30/65K.....	6		
PH/140.....	34, 38	Q500T3/CL/130V.....	27	SP15/R30/65K-DIM.....	6		
PH/211.....	34, 38	Q500T3/CL/220V.....	27	SP18/27-4P.....	7		
PH/212.....	34, 39	Q500T3/CL/240V.....	27	SP18/27-GU24.....	6		
PM-2X32T8-UNV-IS.....	15	Q750T3/CL/120V.....	27	SP18/27K-GU24-DIM.....	6		
PM-2X32T8-UNV-IS-H.....	15	Q750T3/CL/240V.....	27	SP18/41-GU24.....	6		
PM-2X32T8-UNV-IS-L.....	15	Q1000T3/CL/120V.....	27	SP19/27K.....	6		
PM-2X54T5-UNV-PS.....	15	Q1000T3/CL/240V.....	27	SP19/27K-DIM.....	6		
PM-3X32T8-UNV-IS.....	15	Q1000T3/CL/277V.....	27	SP19/35K.....	6		
PM-3X32T8-UNV-IS-H.....	15	Q1500T3/CL/120V.....	27	SP19/41K.....	7		
PM-3X32T8-UNV-IS-L.....	15	Q1500T3/CL/208V.....	27	SP19/41K-DIM.....	6		
PM-4X32T8-UNV-IS.....	15	Q1500T3/CL/220V.....	27	SP19/50K.....	7		
PM-4X32T8-UNV-IS-L.....	15	Q1500T3/CL/240V.....	27	SP19/65K.....	7		
PM-4X54T5-UNV-PS.....	15	Q1500T3/CL/277V.....	27	SP23/27-GU24.....	6		
PR2.....	44	QT9/27.....	9	SP23/27K.....	7		
PR3.....	44	QT9/41.....	9	SP23/27K-DIM.....	6		
PR4.....	44	QT13/27.....	9	SP23/27K-GU24-DIM.....	6		
PR6.....	44	QT13/27-4P.....	9	SP23/35K.....	7		
PR7.....	46	QT13/30-4P.....	9	SP23/41-GU24.....	6		
PRI2.....	46	QT13/35.....	9	SP23/41K.....	7		
PRI3.....	46	QT13/35-4P.....	9	SP23/50K.....	7		
PRI5.....	46	QT13/41.....	9	SP23/65K.....	7		
PRI6.....	46	QT13/41-4P.....	9	SP23/R40/27K.....	6		
PRI8.....	46	QT13/50.....	9	SP23/R40/27K-DIM.....	6		
PR20.....	46	QT13/50-4P.....	9	SP23/R40/41K.....	6		
PR30.....	46	QT13/65.....	10	SP23/R40/41K-DIM.....	6		
Q20MR8/NFL/CG.....	24	QT13/65-4P.....	10	SP23/R40/50K-DIM.....	6		
Q50CL/DC-130V.....	26	QT18/27.....	10	SP26/27-4P.....	7		
Q50CL/MC-130V.....	26	QT18/27-4P.....	10	SP26/27-GU24.....	6		
Q75CL-28V.....	38	QT18/30-4P.....	10	SP27/27K.....	7		
Q75CL-120V.....	26	QT18/35.....	10	SP27/35K.....	7		
Q75CL-130V.....	26	QT18/35-4P.....	10	SP27/41K.....	7		
Q75CL/DC-120V.....	26	QT18/41.....	10	SP27/50K.....	7		
Q75MC-120V.....	26	QT18/41-4P.....	10	SP30/955K.....	33		
Q100CL/DC/2V-120V.....	26	QT18/50.....	10	SP32/27K.....	7		
Q100CL/DC/2V-130V.....	26	QT18/50-4P.....	10	SP32/35K.....	7		
Q100CL/DC-120V.....	26	QT26/27.....	10	SP32/41K.....	7		
Q100CL/MC/2V-130V.....	26	QT26/27-4P.....	10	SP32/50K.....	7		
Q100CL/MC-120V.....	26	QT26/30.....	10	SP42/27K.....	7		
Q100DC/2V-120V.....	26	QT26/30-4P.....	10	SP42/35K.....	7		
Q100/DC-120V.....	26	QT26/35.....	10	SP42/41K.....	7		
Q100/MC-120V.....	26	QT26/35-4P.....	10	SP42/50K.....	7		
Q100W/S120V.....	27	QT26/41.....	10	SP65/41/MED.....	5, 7		
Q100W/S130V.....	27	QT26/41-4P.....	10	SP65/50/MED.....	5, 7		

EiKO USA: Terms, Conditions, & Shipping Procedures

Effective: January 15, 2018.

Supersedes all past terms and conditions of Price books and Sales Supplements.

Prices: As Shown and subject to change without notice.

Distributor Status: Distributors must purchase a minimum of \$3,500 annually in order to maintain distributor status.

Small Order Charge: Orders under \$250 will be assessed a \$15 small order charge (SOC).

Payment Terms: Net 30 days, from date of shipment as it appears on invoice. Postmark date on envelope will determine if payment has been made within terms. All orders received are subject to review and approval by our credit department. Orders received from customers with delinquent accounts may be subject to shipping delays, so please keep your account current.

Freight: NOTE: SoLux and EiKO products may be combined to meet prepaid freight requirements. EiKO Global, LLC will select the carrier of its choice.

1. All orders of \$1,000 or more will be shipped FREE FREIGHT F.O.B. destination via regular ground UPS, FedEx or USPS within the continental United States. Orders less than \$1,000 will be shipped F.O.B. origin.
2. UPS Second Day Air Blue - At the request of the distributor, orders will be billed at the UPS Second Day Air Rate.
3. UPS Next Day Air Red Label - At the request of the distributors, orders will be billed at the UPS Red Label Air rate.
4. Shipments made at the choice of the distributors, other than above, will be shipped F.O.B. shipping point.
5. Additional charges will apply for residential delivery.
6. Alaska, Hawaii and Puerto Rico - Orders of \$1,000 or more will be shipped free freight F.O.B. to a freight forwarder.
7. EiKO will no longer ship freight collect using the customer's account number.

We will cover the above items under normal Continental United States Policy. Therefore, you can achieve free freight to a border destination and then pick up the expense of forwarding the freight to your destination in Alaska, Hawaii or Puerto Rico. As an example, if you are a customer in Hawaii, you can have the goods for orders over \$1,000 shipped free freight to a freight forwarder. It would then be your responsibility to cover the freight to Hawaii.

Return Authorization:

1. You must contact EiKO Global, LLC for authorization to return defective products and shipment errors.
2. Return authorization will not be issued unless the distributor provides a valid invoice number showing when goods were purchased. A copy of this invoice must be included with the return.
3. Goods must be an active item and be less than one year old to be eligible for return. Clearance and closeout items are not eligible for return.
4. Where the request for return is neither defective merchandise nor error made by EiKO Global, LLC, the following policy will apply:
A restocking charge of 20% will be charged on all authorized and acceptable goods. If goods are not returned in resalable condition they will be returned to the sender at the expense of the sender and no credit will be issued.

NOTE: All returns must have a return number on the outside of the box or they will be refused.

Shipment Discrepancies: All shipment discrepancies, damage, etc, must be reported within 10 days of the shipment date shown on the invoice.

General: We reserve the right to, at any time and without notice, discontinue or substitute brands.

Minimum Order Requirements for Linear Fluorescent Lamps: In order to avoid breakage, the minimum order quantity for T8 & T12 linear fluorescent lamps four feet or longer is 360. The minimum order quantity for programmed start T5 linear fluorescent lamps is 100. Mixing SKUs to meet the minimum order is allowed. Orders under \$1,000 will be charged \$70 LTL freight.

***Important Note About Minimum Advertised Pricing (MAPP):** In order to avoid predatory pricing and to maintain the integrity of the products, SoLux products purchased through EiKO Global, LLC may not be advertised for sale (Internet, electronic, print media, mailings or otherwise) by you, a sub-distributor or any other agent, below the minimum advertised price established in the current Distributor Net Price Schedule. This minimum advertised price will be known as and referred to as the MAPP price. Failure to comply with MAPP pricing requirements will result in the loss of your access to SoLux products.

EiKO Global, LLC: 23220 W. 84th St, Shawnee, KS 66227 • Ph: 1.800.852.2217 • F: 1.913.441.6679 • Email: orders@eiko.com

eiko.com

EiKO Canada: Terms, Conditions, & Shipping Procedures

Effective: May 1, 2018.

Supersedes all previously issued copies.

Ordering: All orders should be emailed to orderdesk@eiko.com or faxed to EiKO at 1-888-705-1335.

All orders received are subject to review and approval by our credit department.

Distributor Status: Distributors must purchase a minimum of \$2500.00 annually to maintain distributor status.

Prices: All prices are payable in Canadian funds. Prices are subject to change without notice and do not include applicable taxes. Any applicable taxes will be added to the invoice.

Minimum Order: \$75.00 minimum order requirement.

Payment Terms: Net 30 Days, from date of shipment as it appears on the invoice. Postmark date on envelope will determine if payment has been made within terms. All payments must be made in Canadian funds and mailed to below. EFT is available upon request.

EiKO Global, LLC (Canada)

81 King Street

Barrie, Ontario, L4N 6B5

Freight Terms: All pre-paid orders will be shipped F.O.B. destination via ground service and the carrier will be determined by Eiko Canada Ltd. Orders that do not meet the pre-paid amount will be shipped at customer's expense. At the request and expense of customer, orders can be shipped via air service. At the request of customer, orders can be drop shipped and pre-paid amounts will apply to shipping destination.

F.O.B Barrie, pre-paid as follows (before taxes):

British Columbia	\$500.00	New Brunswick	\$1,000.00
Alberta	\$500.00	Nova Scotia	\$1,000.00
Saskatchewan	\$500.00	Prince Edward Island	\$1,000.00
Manitoba	\$750.00	Newfoundland and Labrador	\$1,500.00
Ontario	\$500.00	Yukon	\$1,500.00
Montreal (Metropolitan Area)	\$500.00	Northwest Territories	\$1,500.00
All other points in Quebec	\$750.00	Nunavut	\$1,500.00

NOTE: - Pre-paid freight is \$1,000.00 in Ontario, Quebec and Manitoba when ordering Fluorescent or LED tubes 4 feet or longer.

- Expedited ground freight is available upon request for Western Canada. Pre-paid freight is \$2000.00.

Shipment Discrepancies/Damages: EiKO will credit or replace product found to arrive in damaged or broken condition on all pre-paid freight orders. All shipment discrepancies, damage, etc., must be reported within 10 days of the shipment date shown on the invoice.

Return Authorizations: You must contact EiKO within 90 days of delivery for a Return Authorization number. An RA number will only be provided if the customer has a valid invoice showing when the goods were purchased from EiKO. Goods must be an active item and less than one year old to be eligible for return. Clearance and closeout items are not eligible for return. All returns must be shipped pre-paid with a copy of the invoice and RA included. A restocking charge of 25% will be charged on all authorized and acceptable goods. An order of 2 times the return value will be accepted as an offset to the restocking charge. Goods returned not in original packaging and not in resalable condition will be returned to sender, at the expense of the sender, and no credit will be issued.

General: EiKO reserves the right to discontinue and substitute brands at any time without notice.

EiKO Global Canada, LLC: 81 King St, Barrie, ON L4N 6B5 • Ph: 1.888.410.8151 • F: 1.888.705.1335 • Email: orderdesk@eiko.com

eiko.com

General Lighting Limited Warranty

EiKO brand lamps are warranted to be free of defective materials and workmanship for the period listed below. EiKO will replace or credit the distributor only for the cost of any lamp that fails under normal operating conditions and the use and operation conditions below due to defective materials or workmanship.

This warranty is limited to the replacement or credit of the lamp itself. This is buyer's exclusive remedy. Any other warranty, express or implied, including any warranty of merchantability or fitness for a particular purpose, is excluded and disclaimed. EiKO shall not be liable for any special, incidental or consequential damage including labor, loss of use, lost profits or injury to persons or property.

EiKO reserves the right to examine all lamps prior to the determination of warranty status. All lamps must be retained for warranty claims. The warranty period starts on the date of installation. If the date of installation is unknown or undetermined the warranty period will start at the wholesale purchase date.

Lamp Category	Warranty Period
LitespanLED® Line	60 months
Advantage™ Line	36 months
Metal Halide, High-Pressure Sodium, Mercury Vapor	15 months
Compact Fluorescent	12 months
Self Ballasted Compact Fluorescent	12 months
Linear Fluorescent (below 14 watt)	12 months
Linear Fluorescent (14 watt and above)	24 months
LCD	120 days

Credit is calculated as follows:

Credit (\$) = Invoiced Purchase Price (\$) x Unexpired Original Warranty Period (months)/Warranty Period

Use and Operating Conditions: Lamps must be used in UL approved fixtures with UL approved ballasts and installed according to local and national codes and standards. Use of occupancy sensors, dimmers or programmable systems with the lamp may void the warranty.

HID Lamps: Warranty is based on 5,000 hours per year maximum operation with a minimum of 8 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.

Fluorescent Lamps: Warranty is based on 4,000 hours per year maximum operation with a minimum of 3 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.

Large Lamps: Warranty is in effect for sales and installations on and after January 1, 2006.

LED: Warranty is in effect for sales and installations on and after July 1, 2010.

LCD: Warranty is in effect for sales and installations on and after July 1, 2009.



watch > like > follow >



23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 · (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 · (F) 1.888.705.1335