

**MaxLite**<sup>®</sup>

A NEW WAVE OF LIGHT

---

**LIGHT SOURCES**

---

JAN2018

# Why Work with MaxLite as Your Supplier for Light Sources?

## Deal directly with MaxLite

As a lighting fixture manufacturer, you always have direct contact with MaxLite customer support, and never have to go through a distributor.

## Delivery in China or USA

MaxLite can supply you with products in China from our China factories, or in the United States from one of our three warehouses (New Jersey, Indiana and California). We offer excellent customer support through our China offices and U.S. support teams.

## Complete Line of Certified Efficient Solutions, including ENERGY STAR®

MaxLite maintains one of the industry's largest offerings of third-party certified lighting solutions. Certifications include ENERGY STAR, Certified Subcomponent Database (CSD), JA8, Title 20, DLC, and others. Certified solutions are available in LED and fluorescent technologies in lamps, modules, light engines, and retrofit kits.

## 25 years of Lighting Expertise

MaxLite has been committed to providing energy efficient lighting products since 1993, and was one of the first movers into LED technology in the industry. MaxLite products have a history of performance and reliability, and have earned the respect of engineers, designers, architects, facility managers and related professionals worldwide.

## Our Vision: Transform the way people experience light

MaxLite has 25 years of experience providing certified energy-efficient lighting solutions to the commercial building, residential and OEM markets. One of the first movers into LED technology in the industry, MaxLite offers an extensive line of indoor and outdoor LED lamps and luminaires under the MaxLED brand. We are a three-time recipient of the prestigious ENERGY STAR® Partner of the Year Award for our industry leadership, and continue to be at the forefront of energy efficient technologies through the innovative research and development capabilities of our facilities and teams in New Jersey and California.

## Our Mission:

To advance our leadership position as a trustworthy lighting solutions provider that connects and empowers our customers. We will leverage our efficiency, scale and capabilities in lighting and controls to create and respond to real market opportunities, ahead of the curve. Our purpose is to create innovative lighting; our passion is in providing superior service and support.

## Our Products:

MaxLite supports its products with the highest standards of quality assurance and customer support. Most MaxLite LED products are certified by ENERGY STAR® and DesignLights Consortium® (DLC), rendering them eligible for utility rebate programs. MaxLite also offers a large selection of lamps and luminaires that meet California Title 24 requirements. We keep our products in stock and available for immediate purchase and delivery, shipping within the United States in one to three business days on standard orders.

## Our Services:

We work with our customers to ensure that our products meet the needs of their installation by providing a full range of complimentary services, including:

- Facility audits
- Lighting layouts
- ROI calculations
- Utility rebate assistance
- Local representation
- Lifetime product support



West Caldwell, NJ



Greenwood, IN



Anaheim, CA



## Recent Accolades:

As a result of our commitment to innovation, MaxLite has received numerous honors, including:

### 2017:

- Environmental Protection Agency ENERGY STAR® Partner of the Year - Sustained Excellence Award
- Consulting-Specifying Engineer Product of the Year Bronze Award - *BayMAX HL Series Linear High Bay*
- Architectural SSL Product Innovation Award - *MPulse Surface Mount Luminaire*
- Lighting for Tomorrow Honorable Mention - *JA8 A21 Lamp*
- ADEX Platinum Award: *BayMAX HL Series Linear High Bay, MR16 Lamps*
- ADEX Gold Award: *Enclosed Omnidirectional A-Lamp, Dim-to-Warm BR30 Lamp, 3-way Omnidirectional A-Lamp, Acrylic High Bay Pendant*



Five-time ENERGY STAR® Partner of the Year  
2009, 2014, 2015, 2016, 2017

## LED LIGHT ENGINES, MODULES & RETROFITS

LED Light Engines/Retrofit Kits.....	2	LED Round Light Engines.....	3
Socket Source® LED Light Engine.....	2	LED Linear Linkable Light Engines.....	3
LED Round Ring Light Engines.....	3	LED Linear Modules.....	3

## LED LAMPS

LED G4 & Wedge Retrofit Lamps.....	4	LED DirectFit T5 Linear Lamps (Ballast Compatible).....	15
LED G9 Retrofit Lamps.....	4	LED Internal Driver T8 Linear Lamps (Ballast Bypass).....	16-17
LED Filament Lamps.....	4-5	LED External Driver T8 Linear Lamps.....	17
LED Puck Lamps.....	6	External Drivers.....	18
LED Omni-Directional A Lamps.....	7-9	Low Profile Non-Shunted Lamp Holder.....	17
LED Omni-Directional 3-Way A Lamps.....	9	T8 Lamp Wiring Harness.....	17
LED Globe Lamps.....	10	T5 Lamp Wiring Harness.....	18
LED MR16 Lamps.....	10-11	LED PL Retrofit Lamps.....	18
LED PAR Lamps.....	11-12	LED PL DirectFit Retrofit Lamps.....	19
LED BR Lamps.....	13	LED Post Top Lamps.....	20
LED DirectFit T8 U-Bend Lamps.....	14	LED Area Lamps.....	20
LED DirectFit T8 Linear Lamps (Ballast Compatible).....	14-15		

## HORTICULTURE LAMPS

PhotonMAX™ Horticulture T8 Linear Lamp.....	21
PhotonMAX™ Horticulture Ceramic Metal Halide Lamp.....	21

## SIGNAGE LAMPS & MODULES

LED Marquee Lamps.....	22	12V LED Power Supply.....	22
LED Double-Sided T8 Linear Lamp.....	22	LED Channel Letter Moduls.....	23

## FLUORESCENT LAMPS

Compact Fluorescent Spiral Lamps.....	24	Fluorescent T5 Linear Lamps.....	25
HighMax® High Output Compact Fluorescent Lamps.....	24	Fluorescent T8 Linear Lamps.....	25
		Linear Fluorescent Ballasts.....	25

## LED LIGHTBARS

Sockets and Brackets.....	26
Step Down Transformer.....	26

## CONTROLS

IntelliMax® Gateway.....	27	IntelliMax® Relay Node.....	27
IntelliMax® Gateway Mini Hub.....	27	IntelliMax® Occupancy Sensor.....	27
IntelliMax® Range Extender.....	27		

## GU24 ACCESSORIES

Sockets and Brackets.....	28
Step Down Transformer.....	28

LED Light Engines/Retrofit Kits  
- Generation 2



	3"	4"	5.5"	7"
<b>MODEL NUMBER</b>	FRK10X3-930/V2	FRK17X4-930/V2	FRK23X5.5-930/V2	FRK28X7-930/V2
<b>ORDER CODE</b>	1409572	1409573	1409574	1409575
Input Wattage	10.4W	16.3W	23.2W	28.2W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	800 lm	1,200 lm	1,750 lm	2,240 lm
Efficacy (lm/W)	77 lm/W	74 lm/W	75 lm/W	80 lm/W
Color Rendering Index (CRI)	93	93	93	93
Color Temperature (CCT)	3000K	3000K	3000K	3000K
Replacement	1x60W INC, 1x13WCFL	75W INC	100W INC	125W INC
Dimming Compatible	Triac	Triac	Triac	Triac
Lumen Maintenance (L70)	40,000 hours	40,000 hours	40,000 hours	40,000 hours
<b>CERTIFICATIONS</b>	Classified cULus, ENERGY STAR®	Classified cULus, ENERGY STAR®	Classified cULus, ENERGY STAR®	Classified cULus, ENERGY STAR®

Socket Source®  
LED Light Engine



	LESKTC0827C	LESKTC0830C
<b>MODEL NUMBER</b>	LESKTC0827C	LESKTC0830C
<b>ORDER CODE</b>	107347	107348
Input Wattage	8W	8W
Voltage	120V	120V
Delivered Lumens (lm)	550 lm	600 lm
Efficacy (lm/W)	69 lm/W	75 lm/W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	3000K
Replacement	40W INC	40W INC
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	UL Recognized	UL Recognized




New Linkable Linear  
LED Light Engines

Driver on-board

**COMING SOON!**



## LED Round Ring Light Engines



3000K options also available.  
Note: Isolation barriers (required for safety listing) available for all engines above.

MODEL NUMBER	5.5"	5.5"	7"	7"
	LER5.5A1727	LER5.5A1727C	LER7.0A1727	LER7.0A1727C
ORDER CODE	74902	74903	74816	74832
Input Wattage	17W	17W	23W	23W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	1,500 lm	1,430 lm	2,500 lm	2,145 lm
Efficacy (lm/W)	87 lm/W	82 lm/W	95 lm/W	90 lm/W
Color Rendering Index (CRI)	80	90	80	90
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	2x60W INC	2x60W INC	2x75W INC	2x75W INC
Dimming Compatible	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	UL Recognized	UL Recognized	UL Recognized	UL Recognized

## LED Round Light Engines



Note: Isolation barriers (required for safety listing) available for all engines above.

MODEL NUMBER	2.2"	2.2"
	LER2.2A0830C	LER2.2A1230C
ORDER CODE	77598	96505
Input Wattage	8W	12W
Voltage	120V	120V
Delivered Lumens (lm)	670 lm	930 lm
Efficacy (lm/W)	84 lm/W	78 lm/W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Replacement	60W INC	75W INC
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	UL Recognized	UL Recognized

## LED Linear Linkable Light Engines



3000K options also available.  
Note: Isolation barriers (required for safety listing) available for all engines above.

MODEL NUMBER	5.5"	11.5"	23"
	LEL5.5A0527C	LEL11.5A0827C	LEL23A1627C
ORDER CODE	77599	77601	77603
Input Wattage	3W	8W	23W
Voltage	120V	120V	120V
Delivered Lumens (lm)	387 lm	690 lm	1,430 lm
Efficacy (lm/W)	120 lm/W	100 lm/W	100 lm/W
Color Rendering Index (CRI)	90	90	90
Color Temperature (CCT)	2700K	2700K	2700K
Replacement	40W INC	50-60W INC	75-100W INC
Dimming Compatible	Yes	Yes	Yes
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	UL Recognized	UL Recognized	UL Recognized

## LED Linear Modules



Note: Requires remote 24V DC constant voltage driver.

MODEL NUMBER	10.85"	10.85"
	LEL12A0341	LEL12A0350
ORDER CODE	73074	73075
Input Wattage	3W	3W
Voltage	24V	24V
Delivered Lumens (lm)	300 lm	300 lm
Efficacy (lm/W)	100 lm/W	100 lm/W
Color Rendering Index (CRI)	82	82
Color Temperature (CCT)	4100K	5000K
Replacement	-	-
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	15,000 hours
CERTIFICATIONS	UL Recognized	UL Recognized

## LED G4 & Wedge Retrofit Lamps



	12V (BI-PIN BASE)	12V (WEDGE BASE)
<b>MODEL NUMBER</b>	<b>2.5G4LED27</b>	<b>2.5WDGLED27</b>
<b>ORDER CODE</b>	<b>74107</b>	<b>74108</b>
Input Wattage	2.5W	2.5W
Voltage	12V AC/DC	12V AC/DC
Delivered Lumens (lm)	180 lm	180 lm
Efficacy (lm/W)	72 lm/W	72 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Replacement	20W HAL	20W HAL
Dimming Compatible	No	No
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	TUV	TUV

## LED G9 Retrofit Lamps



	NON-DIM (G9 BASE)
<b>MODEL NUMBER</b>	<b>SKG0905LED27</b>
<b>ORDER CODE</b>	<b>74011</b>
Input Wattage	5W
Voltage	120V
Delivered Lumens (lm)	430 lm
Efficacy (lm/W)	86 lm/W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Replacement	40W HAL
Dimming Compatible	No
Lumen Maintenance (L70)	25,000 hours
<b>CERTIFICATIONS</b>	TUV

## LED G9 Retrofit Lamps - Generation 2



	NON-DIM (G9 BASE)	DIM (G9 BASE)	NON-DIM (G9 BASE)	DIM (G9 BASE)
<b>MODEL NUMBER</b>	<b>3G9LED27</b>	<b>3G9DLED27</b>	<b>5G9LED27</b>	<b>5G9DLED27</b>
<b>ORDER CODE</b>	<b>108071</b>	<b>108072</b>	<b>108073</b>	<b>108074</b>
Input Wattage	3W	3W	5W	5W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	270 lm	270 lm	480 lm	360 lm
Efficacy (lm/W)	90 lm/W	90 lm/W	96 lm/W	72 lm/W
Color Rendering Index (CRI)	80	80	80	80
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	25W INC	25W INC	40W INC	40W INC
Dimming Compatible	No	Yes	No	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	TUV	TUV	TUV	TUV

## LED Filament Lamps



	B10 (E12 BASE)	B10 3-PACK (E12 BASE)	BA10 (E12 BASE)
<b>MODEL NUMBER</b>	<b>F4B10DLED27/G2</b>	<b>F4B10DLED27/G2/3P</b>	<b>F4BA10DLED27/G2</b>
<b>ORDER CODE</b>	<b>1409964</b>	<b>1409967</b>	<b>1409966</b>
Input Wattage	4W	4W	4W
Voltage	120V	120V	120V
Delivered Lumens (lm)	330 lm	330 lm	330 lm
Efficacy (lm/W)	82 lm/W	82 lm/W	82 lm/W
Color Rendering Index (CRI)	82	82	82
Color Temperature (CCT)	2700K	2700K	2700K
Replacement	40W INC	40W INC	40W INC
Dimming Compatible	Yes	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	15,000 hours	15,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0

Sample part numbers shown, other part numbers may be available for various color temperatures. Updated versions of all of these products may be available. Consult your MaxLite representative for latest info.

## LED Vintage Filament Lamps



MODEL NUMBER	SILVER BOWL A19 (E26 BASE)	TORPEDO (E26 BASE)
	SB6.5A19DLED27	V2.5B11DLED22E
ORDER CODE	76530	76531
Input Wattage	6.5W	2.5W
Voltage	120V	120V
Delivered Lumens (lm)	700 lm	250 lm
Efficacy (lm/W)	108 lm/W	100 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2200K
Replacement	60W	25W
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	15,000 hours
CERTIFICATIONS	cULus	cULus

## LED Vintage Filament Lamps



MODEL NUMBER	A19 (E26 BASE)	T14 (E26 BASE)
	V4.5A19DLED22	V4.5T14DLED22
ORDER CODE	76543	76542
Input Wattage	4.5W	4.5W
Voltage	120V	120V
Delivered Lumens (lm)	400 lm	400 lm
Efficacy (lm/W)	89 lm/W	89 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2200K	2200K
Replacement	40W	40W
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	15,000 hours
CERTIFICATIONS	cULus	cULus

## Energy Star LED Filament Lamps



MODEL NUMBER	A19 (E26 BASE)	G25 (E26 BASE)	ST19 (E26 BASE)
	F7A19DLED27/G2	F7G25DLED27/G2	V5ST19DLED22
ORDER CODE	1409420	1409965	107199
Input Wattage	7W	7W	5W
Voltage	120V	120V	120V
Delivered Lumens (lm)	800 lm	800 lm	320 lm
Efficacy (lm/W)	114 lm/W	114 lm/W	64 lm/W
Color Rendering Index (CRI)	84	80	81
Color Temperature (CCT)	2700K	2700K	2200K
Replacement	60W INC	100W INC	40W INC
Dimming Compatible	Yes	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	15,000 hours	15,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®

## LED Vintage JA8 Certified Filament Lamps



MODEL NUMBER	B10 (E12 BASE)	T10 (E26 BASE)	ST19 (E26 BASE)	A19 (E26 BASE)
	F4B10DLED927/JA8	F4T10DLED927/JA8	V6.5ST19DLED922/JA8	F8.5A19DLED927/JA8
ORDER CODE	1408340	1409894	1409893	1408914
Input Wattage	4W	4W	6.5W	8.5W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	300 lm	300 lm	450 lm	800 lm
Efficacy (lm/W)	75 lm/W	75 lm/W	69 lm/W	94 lm/W
Color Rendering Index (CRI)	94	91	96	91
Color Temperature (CCT)	2700K	2700K	2200K	2700K
Replacement	40W INC	40W INC	40W INC	60W INC
Dimming Compatible	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	15,000 hours	15,000 hours	15,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®

## LED Dimmable Puck Lamps



	PUCK (E26 BASE)	PUCK (GU24 BASE)
<b>MODEL NUMBER</b>	<b>9PUADLED27</b>	<b>9PUAGULED27</b>
<b>ORDER CODE</b>	<b>76899</b>	<b>76901</b>
Input Wattage	9W	9W
Voltage	120V	120V
Delivered Lumens (lm)	800 lm	800 lm
Efficacy (lm/W)	89 lm/W	89 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Replacement	60W	60W
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus (Wet Listed)	cULus (Wet Listed)

3000K options also available.

## LED Non-Dimmable Puck Lamps



	PUCK (E26 BASE)	PUCK (GU24 BASE)
<b>MODEL NUMBER</b>	<b>10PUBLED27</b>	<b>10PUAGULED27</b>
<b>ORDER CODE</b>	<b>1408990</b>	<b>76905</b>
Input Wattage	10W	10W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	800 lm	850 lm
Efficacy (lm/W)	80 lm/W	85 lm/W
Color Rendering Index (CRI)	83	80
Color Temperature (CCT)	2700K	2700K
Replacement	60W	60W
Dimming Compatible	No	No
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus (Wet Listed - 120V)	cULus (Wet Listed - 120V)

3000K options also available.

## LED Non-Dimmable Compact Puck Lamps



	PUCK (E26 BASE)	PUCK (GU24 BASE)
<b>MODEL NUMBER</b>	<b>10CPUALED27</b>	<b>10CPUAGULED27</b>
<b>ORDER CODE</b>	<b>76907</b>	<b>76909</b>
Input Wattage	10W	10W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	900 lm	900 lm
Efficacy (lm/W)	90 lm/W	90 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Replacement	60W	60W
Dimming Compatible	No	No
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus (Wet Listed - 120V)	cULus (Wet Listed - 120V)

3000K options also available.

## LED Omni-Directional A Lamps E26 Base



	A19 (E26 BASE)	A19 (E26 BASE)	A19 (E26 BASE)	A19 (E26 BASE)
<b>MODEL NUMBER</b>	<b>6A19DLED27/G5</b>	<b>9A19DLED27/G5</b>	<b>11A19DLED27/G5</b>	<b>15A19DLED27/G5</b>
<b>ORDER CODE</b>	<b>107589</b>	<b>107584</b>	<b>107585</b>	<b>107720</b>
Input Wattage	6W	9W	11W	15W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	480 lm	800 lm	1,100 lm	1,600 lm
Efficacy (lm/W)	80 lm/W	89 lm/W	100 lm/W	106 lm/W
Color Rendering Index (CRI)	82	82	84	83
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	40W INC	60W INC	75W INC	100W INC
Dimming Compatible	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0

3000K and 4000K options also available.

## LED Omni-Directional A Lamps GU24 Base



	A19 (GU24 BASE)	A19 (GU24 BASE)	A19 (GU24 BASE)	A19 (GU24 BASE)
<b>MODEL NUMBER</b>	<b>6A19GUDLED27/G5</b>	<b>9A19GUDLED27/G5</b>	<b>11A19GUDLED27/G5</b>	<b>15A19GUDLED27/G5</b>
<b>ORDER CODE</b>	<b>1409336</b>	<b>1409408</b>	<b>1409339</b>	<b>1409341</b>
Input Wattage	6W	9W	11W	15W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	480 lm	800 lm	1,100 lm	1,600 lm
Efficacy (lm/W)	80 lm/W	88 lm/W	100 lm/W	106 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80	≥80
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	40W INC	60W INC	75W INC	100W INC
Dimming Compatible	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0

3000K and 4000K options also available.

## LED Omni-Directional Enclosed Rated A Lamps



	A19 (GU24 BASE)
<b>MODEL NUMBER</b>	<b>E9A19GUDLED27/G2</b>
<b>ORDER CODE</b>	<b>102171</b>
Input Wattage	9W
Voltage	120V
Delivered Lumens (lm)	800 lm
Efficacy (lm/W)	89 lm/W
Color Rendering Index (CRI)	81
Color Temperature (CCT)	2700K
Replacement	60W INC
Dimming Compatible	Yes
Lumen Maintenance (L70)	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0

3000K and 5000K options also available.

## LED Omni-Directional Non-Dimmable Enclosed Rated A Lamps



A19 (E26 BASE)	
<b>MODEL NUMBER</b>	<b>E9A19ND27-149</b>
<b>ORDER CODE</b>	<b>1409959</b>
Input Wattage	9W
Voltage	120V
Delivered Lumens (lm)	800 lm
Efficacy (lm/W)	89 lm/W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	2700K
Replacement	60W INC
Dimming Compatible	No
Lumen Maintenance (L70)	15,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0

3000K and 5000K options also available.

## LED Omni-Directional Non-Dimmable A Lamps



	A19 (E26 BASE)	A19 (E26 BASE)	A19 4-PACK (E26 BASE)
<b>MODEL NUMBER</b>	<b>9A19ND27/G2</b>	<b>15A19ND27/G2</b>	<b>15A19ND27/G2/4P</b>
<b>ORDER CODE</b>	<b>107812</b>	<b>107816</b>	<b>1409418</b>
Input Wattage	9W	15W	15W
Voltage	120V	120V	120V
Delivered Lumens (lm)	800 lm	1,600 lm	1,600 lm
Efficacy (lm/W)	89 lm/W	106 lm/W	106 lm/W
Color Rendering Index (CRI)	82	84	84
Color Temperature (CCT)	2700K	2700K	2700K
Replacement	60W INC	100W INC	100W INC
Dimming Compatible	No	No	No
Lumen Maintenance (L70)	15,000 hours	15,000 hours	15,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0

3000K options also available.

## LED Omni-Directional JA8 Certified A Lamps



	A19 (E26 BASE)	A19 (E26 BASE)	A21 (E26 BASE)	A21 (E26 BASE)
<b>MODEL NUMBER</b>	<b>10A19DLED927/G2/JA8</b>	<b>12A19DLED927/JA8</b>	<b>17A21DLED927/JA8</b>	<b>17A21DLED927/G2/JA8</b>
<b>ORDER CODE</b>	<b>1408959</b>	<b>1408961</b>	<b>1408663</b>	<b>1408962</b>
Input Wattage	10W	12W	17W	17W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	800 lm	1,100 lm	1,600 lm	1,600 lm
Efficacy (lm/W)	80 lm/W	91 lm/W	94 lm/W	94 lm/W
Color Rendering Index (CRI)	92	92	90	92
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	60W INC	75W INC	100W INC	100W INC
Dimming Compatible	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus, JA8, ENERGY STAR® V2.0	cULus, JA8, ENERGY STAR® V2.0	cULus, JA8, ENERGY STAR® V2.0	cULus, JA8, ENERGY STAR® V2.0

3000K options also available.



# LED Omni-Directional JA8 Certified, Enclosed Rated A Lamps



	A19 (E26 BASE)	A19 (E26 BASE)	A19 (GU24 BASE)	A19 (E26 BASE)	A21 (E26 BASE)
<b>MODEL NUMBER</b>	E6A19DLED927/JA8	E10A19DLED927/JA8*	E10A19GUD927/G2/JA8*	E12A19DLED927/JA8	E17A21DLED927/JA8*
<b>ORDER CODE</b>	1408963	107624	1409883	1408671	1409885
Input Wattage	6W	10W	10W	12W	17W
Voltage	120V	120V	120V	120V	120V
Delivered Lumens (lm)	450 lm	800 lm	800 lm	1,100 lm	1,600 lm
Efficacy (lm/W)	75 lm/W	80 lm/W	80 lm/W	91 lm/W	94 lm/W
Color Rendering Index (CRI)	93	92	92	92	90
Color Temperature (CCT)	2700K	2700K	2700K	2700K	2700K
Replacement	40W INC	60W INC	60W INC	75W INC	100W INC
Dimming Compatible	Yes	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	25,000 hours	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus, JA8, ENERGY STAR® V2.0	cULus, JA8, ENERGY STAR® V2.0	cULus, JA8, ENERGY STAR® V2.0	cULus, JA8, ENERGY STAR® V2.0	cULus, JA8, ENERGY STAR® V2.0

\*3000K options also available.

# LED Omni-Directional 3-Way A Lamps



	A21 (E26 BASE)	A19 (E26 BASE)
<b>MODEL NUMBER</b>	16A21/3WLED27/G2	14A19/3WLED27
<b>ORDER CODE</b>	1408218	1409401
Input Wattage	5.5/9/16W	4/8/14W
Voltage	120V	120V
Delivered Lumens (lm)	450/800/1,600 lm	500/1,000/1,500 lm
Efficacy (lm/W)	100 lm/W	107 lm/W
Color Rendering Index (CRI)	80	81
Color Temperature (CCT)	2700K	2700K
Replacement	40/60/100W INC	40/60/100W INC
Dimming Compatible	No	No
Lumen Maintenance (L70)	15,000 hours	15,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0

3000K options also available.



MaxLite is the industry leader in JA8 solutions for Title 24, and products certified for Title 20 and ENERGY STAR.



## New JA8/T20 Certified Light Source Solutions

# COMING SOON!

Omni-Directional 3-Way, Puck Lamps, Expanded Filament Lamps ...and more!



## LED Globe Lamps



	<b>G16 (E26 BASE)</b>	<b>G25 (E26 BASE)</b>	<b>G40 (E26 BASE)</b>
<b>MODEL NUMBER</b>	<b>5G16.5DLED27</b>	<b>6G25DLED27/G2*</b>	<b>12G40DLED30</b>
<b>ORDER CODE</b>	<b>101459</b>	<b>107505</b>	<b>1410218</b>
Input Wattage	5W	6W	12W
Voltage	120	120V	120V
Delivered Lumens (lm)	350 lm	450 lm	950 lm
Efficacy (lm/W)	70 lm/W	75 lm/W	79 lm/W
Color Rendering Index (CRI)	82	84	83
Color Temperature (CCT)	2700K	2700K	3000K
Replacement	40W INC	40W INC	100W INC
Dimming Compatible	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	ETL, ENERGY STAR® V2.0	cULus, ENERGY STAR® V2.0	ETL, ENERGY STAR® V2.0

**\*3-Pack Available**

## LED JA8 Certified Globe Lamps



	<b>G25 (E26 BASE)</b>
<b>MODEL NUMBER</b>	<b>10G25DLED927/JA8</b>
<b>ORDER CODE</b>	<b>1409460</b>
Input Wattage	10W
Voltage	120V
Delivered Lumens (lm)	800 lm
Efficacy (lm/W)	80 lm/W
Color Rendering Index (CRI)	92
Color Temperature (CCT)	2700K
Replacement	100W INC
Dimming Compatible	Yes
Lumen Maintenance (L70)	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0, JA8



**New MR16 & GU10  
COMING SOON!**

## LED High CRI MR16 Lamp



MR16 (GU10 BASE)	
<b>MODEL NUMBER</b>	<b>6MR16GUDLED930FL</b>
<b>ORDER CODE</b>	<b>101468</b>
Input Wattage	6W
Voltage	120V
Delivered Lumens (lm)	400 lm
Efficacy (lm/W)	67 lm/W
Color Rendering Index (CRI)	91
Color Temperature (CCT)	50W
Replacement	3000K
Dimming Compatible	Yes
Lumen Maintenance (L70)	40,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0

## LED JA8 Certified MR16 Lamp



	MR16 (GU5.3 BASE)	MR16 (GU10 BASE)
<b>MODEL NUMBER</b>	<b>7MR16DLED930FL/JA8</b>	<b>7MR16GUDLED930FL/JA8</b>
<b>ORDER CODE</b>	<b>1408943</b>	<b>1408944</b>
Input Wattage	7W	7W
Voltage	12V	120V
Delivered Lumens (lm)	500 lm	500 lm
Efficacy (lm/W)	71 lm/W	71 lm/W
Color Rendering Index (CRI)	91	91
Color Temperature (CCT)	50W	50W
Replacement	3000K	3000K
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus, JAB	cULus, JAB

## LED 277V PAR Lamps



	277V PAR30 LONG NECK (E26 BASE)	277V PAR38 (E26 BASE)
<b>MODEL NUMBER</b>	<b>13P30LNLED230FL</b>	<b>17P38LED230FL</b>
<b>ORDER CODE</b>	<b>74686</b>	<b>74687</b>
Input Wattage	13W	17W
Voltage	277V	277V
Delivered Lumens (lm)	1,000 lm	1,700 lm
Efficacy (lm/W)	77 lm/W	100 lm/W
Color Rendering Index (CRI)	82	82
Color Temperature (CCT)	3000K	3000K
Replacement	90W	120W
Dimming Compatible	No	No
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cRUus	cRUus

4000K options also available.

## LED Wet Listed PAR Lamps



	PAR38 WET LISTED (E26 BASE)	PAR38 WET LISTED (E26 BASE)
<b>MODEL NUMBER</b>	15P38WDLED27FL*	17P38DLED41FL**
<b>ORDER CODE</b>	1408269	73658
Input Wattage	15W	17W
Voltage	120V	120V
Delivered Lumens (lm)	1,250 lm	1,300 lm
Efficacy (lm/W)	86 lm/W	76 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Replacement	120W	150W
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus (Wet Listed), ENERGY STAR®	cULus (Wet Listed)

\*3000K options also available.  
\*\*5000K options also available.

## LED PAR Lamps



	PAR20 (E26 BASE)	PAR30 SHORT NECK (E26 BASE)	PAR30 LONG NECK (E26 BASE)	PAR38 (E26 BASE)
<b>MODEL NUMBER</b>	6P20DLED27FL	10P30DLED27FL	10P30LNDLED27FL	13P38DLED27FL
<b>ORDER CODE</b>	102174	102176	102178	102180
Input Wattage	6W	10W	10W	13W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	450 lm	750 lm	750 lm	950 lm
Efficacy (lm/W)	75 lm/W	75 lm/W	75 lm/W	73 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80	≥80
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	50W INC	75W INC	75W INC	90W INC
Dimming Compatible	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cETLus, ENERGY STAR® V2.0	cETLus, ENERGY STAR® V2.0	cETLus, ENERGY STAR® V2.0	cETLus, ENERGY STAR® V2.0

3000K & 4000K options also available. Flood 35° and Narrow Flood 25° beam angles available.

## LED JA8 Certified PAR Lamps



	PAR20 (E26 BASE)	PAR30 LONG NECK (E26 BASE)	PAR38 (E26 BASE)
<b>MODEL NUMBER</b>	7P20DLED927FL/JA8	12P30LNDLED927FL/JA8	15P38DLED927FL/JA8
<b>ORDER CODE</b>	1410039	1410041	1410043
Input Wattage	7W	12W	10W
Voltage	120V	120V	120V
Delivered Lumens (lm)	525 lm	900 lm	1,150 lm
Efficacy (lm/W)	75 lm/W	75 lm/W	76 lm/W
Color Rendering Index (CRI)	91	91	92
Color Temperature (CCT)	2700K	2700K	2700K
Replacement	50W INC	75W INC	100W INC
Dimming Compatible	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR® V2.0, JA8	cULus, ENERGY STAR® V2.0, JA8	cULus, ENERGY STAR® V2.0, JA8

3000K options also available.

## LED BR Lamps



	BR20 (E26 BASE)	BR30 (E26 BASE)	BR30 (E26 BASE)	BR40 (E26 BASE)
<b>MODEL NUMBER</b>	<b>7BR20DLED27/G2*</b>	<b>8BR30DLED27/G2*</b>	<b>11BR30DLED27/G2*</b>	<b>17BR40DLED27/G2*</b>
<b>ORDER CODE</b>	<b>77056</b>	<b>76557</b>	<b>77630</b>	<b>77633</b>
Input Wattage	7W	8W	11W	17W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	550 lm	650 lm	850 lm	1,400 lm
Efficacy (lm/W)	79 lm/W	81 lm/W	77 lm/W	82 lm/W
Color Rendering Index (CRI)	≥82	≥82	≥82	≥80
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	50W	65W	65W	100W
Dimming Compatible	Yes	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR*	cULus, ENERGY STAR*	cULus, ENERGY STAR*	cULus, ENERGY STAR*

3000K and 4000K options also available.

LED High CRI,  
JA8 Certified BR Lamps

	BR30 (E26 BASE)
<b>MODEL NUMBER</b>	<b>11BR30DLED927/G4</b>
<b>ORDER CODE</b>	<b>107608</b>
Input Wattage	11W
Voltage	120V
Delivered Lumens (lm)	800 lm
Efficacy (lm/W)	72 lm/W
Color Rendering Index (CRI)	92
Color Temperature (CCT)	2700K
Replacement	65W INC
Dimming Compatible	Yes
Lumen Maintenance (L70)	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR* V2.0

3000K options also available.

LED Warm-On-Dim  
BR Lamps

	BR30 (E26 BASE)
<b>MODEL NUMBER</b>	<b>9BR30SDLED30</b>
<b>ORDER CODE</b>	<b>101363</b>
Input Wattage	9W
Voltage	120V
Delivered Lumens (lm)	650 lm
Efficacy (lm/W)	72 lm/W
Color Rendering Index (CRI)	85
Color Temperature (CCT)	3000K
Replacement	65W INC
Dimming Compatible	Yes, 3000K - 2200K
Lumen Maintenance (L70)	25,000 hours
<b>CERTIFICATIONS</b>	cULus, ENERGY STAR*

## LED DirectFit T8 U-Bend Lamps (UL-A) Ballast Compatible



	T8 U-BEND (G13 PIN BASE)	T8 U-BEND (G13 PIN BASE)
MODEL NUMBER	U13T8DF235	U16T8DF235
ORDER CODE	1409015	76914
Input Wattage	13W (Bare Lamp)	16W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	1,800 lm	1,800 lm
Color Rendering Index (CRI)	83	85
Color Temperature (CCT)	3500K	3500K
Replacement	32W FLUOR	32W FLUOR
Dimming Compatible	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, DLC	cULus

4000K and 5000K options also available.

## LED DirectFit 2-FT T8 Linear Lamps (UL-A) Ballast Compatible



	2' T8 (COATED GLASS, G13 PIN BASE)	2' T8 (COATED GLASS, G13 PIN BASE)
MODEL NUMBER	L9T8DF240-CG4	L9T8DF250-CG4
ORDER CODE	107769	107770
Input Wattage	9W (Bare Lamp)	9W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	1,350 lm	1,400 lm
Efficacy (lm/W)	150 lm/W	155 lm/W
Color Rendering Index (CRI)	82	82
Color Temperature (CCT)	4000K	5000K
Replacement	17W FLUOR	17W FLUOR
Dimming Compatible	Yes (Ballast Dependent)	Yes (Ballast Dependent)
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, ETL Sanitation, DLC	cULus, ETL Sanitation, DLC

## LED DirectFit 3-FT T8 Linear Lamps (UL-A) Ballast Compatible



	3' T8 (COATED GLASS, G13 PIN BASE)	3' T8 (COATED GLASS, G13 PIN BASE)	3' T8 (COATED GLASS, G13 PIN BASE)
MODEL NUMBER	L14T8DF335-CG4	L14T8DF340-CG4	L14T8DF350-CG4
ORDER CODE	107771	107772	107773
Input Wattage	14W (Bare Lamp)	14W (Bare Lamp)	14W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	1,700 lm	1,750 lm	1,800 lm
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3500K	4000K	5000K
Replacement	25W FLUOR	25W FLUOR	25W FLUOR
Dimming Compatible	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, ETL Sanitation	cULus, ETL Sanitation	cULus, ETL Sanitation



## LED DirectFit 4-FT T8 Linear Lamps (UL-A) Ballast Compatible



(COATED GLASS, G13 PIN BASE) (COATED GLASS, G13 PIN BASE) (COATED GLASS, G13 PIN BASE)

MODEL NUMBER	L13T8DF435-CG4	L13T8DF440-CG4	L13T8DF450-CG4
ORDER CODE	107221	107222	107223
Input Wattage	13W (Bare Lamp)	13W (Bare Lamp)	13W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	1,800 lm	1,900 lm	2,000 lm
Efficacy (lm/W)	110 lm/W	112 lm/W	115 lm/W
Color Rendering Index (CRI)	83	83	83
Color Temperature (CCT)	3500K	4000K	5000K
Replacement	32W FLUOR	32W FLUOR	32W FLUOR
Dimming Compatible	Yes (Ballast Dependent)	Yes (Ballast Dependent)	Yes (Ballast Dependent)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, ETL Sanitation, DLC	cULus, ETL Sanitation, DLC	cULus, ETL Sanitation, DLC

## LED DirectFit 4-FT T8 Linear Lamps (UL-A) Ballast Compatible



4' T8 (PLASTIC, G13 PIN BASE) 4' T8 (PLASTIC, G13 PIN BASE) 4' T8 (PLASTIC, G13 PIN BASE)

MODEL NUMBER	L17T8DF435	L17T8DF440	L17T8DF450
ORDER CODE	107206	107207	107208
Input Wattage	17W (Bare Lamp)	17W (Bare Lamp)	17W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	2,200 lm	2,200 lm	2,200 lm
Efficacy (lm/W)	113 lm/W	113 lm/W	113 lm/W
Color Rendering Index (CRI)	84	84	84
Color Temperature (CCT)	3500K	4000K	5000K
Replacement	32W FLUOR	32W FLUOR	32W FLUOR
Dimming Compatible	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETL, DLC	cETL, DLC	cETL, DLC

## LED DirectFit 4-FT T5 Linear Lamps (UL-A) Ballast Compatible



4' T5 (COATED GLASS, G5 PIN BASE) 4' T5 (COATED GLASS, G5 PIN BASE)

MODEL NUMBER	L25T5DF440-CG4	L25T5DF450-CG5
ORDER CODE	107340	1409173
Input Wattage	25W (Bare Lamp)	25W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	3,200 lm	3,200 lm
Efficacy (lm/W)	112 lm/W	115 lm/W
Color Rendering Index (CRI)	83	83
Color Temperature (CCT)	4000K	5000K
Replacement	54W T5HO	54W T5HO
Dimming Compatible	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, ETL Sanitation, DLC	cULus, ETL Sanitation, DLC

## LED Internal Driver T8 Linear Lamps (UL-B) Ballast Bypass



	2' T8 (GLASS, G13 PIN BASE)	3' T8 (GLASS, G13 PIN BASE)	5' T8 (GLASS, G13 PIN BASE)	6' T8 (GLASS, G13 PIN BASE)
<b>MODEL NUMBER</b>	<b>L9T8SE240-G*</b>	<b>L12T8SE340-G</b>	<b>L19T8SE540-G</b>	<b>L30T8SE640-G</b>
<b>ORDER CODE</b>	<b>101598</b>	<b>101600</b>	<b>101601</b>	<b>101602</b>
Input Wattage	9W	12W	19W	30W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	1,150 lm	1,450 lm	2,500 lm	3,600 lm
Efficacy (lm/W)	127 lm/W	120 lm/W	131 lm/W	120 lm/W
Color Rendering Index (CRI)	≥82	≥82	≥82	≥82
Color Temperature (CCT)	4000K	4000K	4000K	4000K
Replacement	17W FLUOR	32W FLUOR	40W FLUOR	70W FLUOR
Dimming Compatible	No	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	UL Classified, NSF, DLC	cULus, NSF	UL Classified, NSF, DLC	cULus, NSF, RoHS

\*3000K, 3500K & 5000K options also available.

## LED Internal Driver 4-FT T8 Linear Lamps (UL-B) Ballast Bypass



	4' T8 (COATED GLASS, G13 PIN BASE)	4' T8 (COATED GLASS, G13 PIN BASE)
<b>MODEL NUMBER</b>	<b>L15T8SE435-CG4</b>	<b>L18T8SE435-CG4</b>
<b>ORDER CODE</b>	<b>1408919</b>	<b>1408922</b>
Input Wattage	15W	18W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	1,800 lm	2,200 lm
Efficacy (lm/W)	120 lm/W	122 lm/W
Color Rendering Index (CRI)	82	82
Color Temperature (CCT)	3500K	3500K
Replacement	32W FLUOR	32W FLUOR
Dimming Compatible	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	ETL Sanitation, DLC, UL Classified	ETL Sanitation, DLC, UL Classified

4000K and 5000K options also available.

## LED Internal Driver 4-FT T8 Linear Lamps (UL-B) Ballast Bypass



	4' T8 (GLASS, G13 PIN BASE)	4' T8 (GLASS, G13 PIN BASE)
<b>MODEL NUMBER</b>	<b>L12.5T8SE435-G*</b>	<b>L16.5T8SE440-G**</b>
<b>ORDER CODE</b>	<b>99898</b>	<b>101298</b>
Input Wattage	12.5W	16.5W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	1,800 lm	2,200 lm
Efficacy (lm/W)	144 lm/W	133 lm/W
Color Rendering Index (CRI)	85	85
Color Temperature (CCT)	3500K	4000K
Replacement	32W FLUOR	40W FLUOR
Dimming Compatible	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	DLC, UL Classified	DLC, UL Classified

\*4000K and 5000K options also available. \*\*5000K options also available. 10-Year options also available.

## LED Internal Driver T8 Linear Lamps (UL-B) Ballast Bypass



Intertek  
2' T8 (COATED GLASS, G13 PIN BASE)    3' T8 (COATED GLASS, G13 PIN BASE)    4' T8 (COATED GLASS, G13 PIN BASE)

MODEL NUMBER	L9T8DE235-CG4	L12T8DE335-CG4	L11.5T8DE435-CG4
ORDER CODE	1409552	1409555	1409558
Input Wattage	9W	12W	11.5W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	1,125 lm	1,225 lm	1,650 lm
Efficacy (lm/W)	125 lm/W	102 lm/W	143 lm/W
Color Rendering Index (CRI)	83	82	83
Color Temperature (CCT)	3500K	3500K	3500K
Replacement	17W FLUOR	25W FLUOR	32W FLUOR
Dimming Compatible	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	UL Classified, ETL Sanitation, DLC	UL Classified, ETL Sanitation, DLC	UL Classified, ETL Sanitation, DLC

**4000K & 5000K options also available.**

## LED Internal Driver T5 Linear Lamps (UL-B) Ballast Bypass



Intertek  
2' T5 (COATED GLASS, G13 PIN BASE)    3' T5 (COATED GLASS, G13 PIN BASE)    4' T5 (COATED GLASS, G13 PIN BASE)    4' T5 (COATED GLASS, G13 PIN BASE)

MODEL NUMBER	L12T5SE235-CG	L16T5SE335-CG	L13T5SE435-CG	L25T5SE435-CG
ORDER CODE	1409907	1409910	1409889	1409601
Input Wattage	9W	16W	13W	25W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	1,125 lm	1,800 lm	1,600 lm	3,200 lm
Efficacy (lm/W)	125 lm/W	112 lm/W	123 lm/W	128 lm/W
Color Rendering Index (CRI)	83	83	83	82
Color Temperature (CCT)	3500K	3500K	3500K	3500K
Replacement	24W T5HO	39W T5HO	28W T5HE	54W T5HO
Dimming Compatible	No	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	UL Classified, cRUus, ETL Sanitation, DLC	UL Classified, cRUus, ETL Sanitation, DLC	UL Classified, cRUus, ETL Sanitation, DLC	UL Classified, cRUus, ETL Sanitation, DLC

## LED External Driver 4-FT T8 Linear Lamps (UL-C)



4' T8 (PLASTIC, G13 PIN BASE)    4' T8 (PLASTIC, G13 PIN BASE)    4' T8 (PLASTIC, G13 PIN BASE)

MODEL NUMBER	L19T8EX435	L19T8EX440	L19T8EX450
ORDER CODE	107289	107290	107291
Input Wattage	19W	19W	19W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2,350 lm	2,350 lm	2,350 lm
Efficacy (lm/W)	124 lm/W	124 lm/W	124 lm/W
Color Rendering Index (CRI)	82	82	82
Color Temperature (CCT)	3500K	4000K	5000K
Replacement	32W FLUOR	32W FLUOR	32W FLUOR
Dimming Compatible	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	UL Classified, DLC	UL Classified, DLC	UL Classified, DLC

## External Driver for L13T8EX4xx Tubes



	2 LAMP DRIVER	4 LAMP DRIVER
<b>MODEL NUMBER</b>	<b>DDR2L13</b>	<b>DDR4L13</b>
<b>ORDER CODE</b>	<b>1409620</b>	<b>1409621</b>
Input Voltage (V)	120-277V	120-277V
Input Frequency (Hz)	50/60 Hz	50/60 Hz
Max Input Power (W)	26W	52W
Min Power Factor (%)	0.98% (277Vac)	0.98% (277Vac)
Inrush Current	10Apk-pk	10Apk-pk
Output Channel	2	4
Max Output Voltage (V)	45V	45V
Max Output Current (mA)	283 x 1 mA	283 x 1 mA

## External Driver for L18T8EX4xx Tubes



	2 LAMP DRIVER	4 LAMP DRIVER
<b>MODEL NUMBER</b>	<b>DDR2L18</b>	<b>DDR4L18</b>
<b>ORDER CODE</b>	<b>1409902</b>	<b>1409903</b>
Input Voltage (V)	120-277V	120-277V
Input Frequency (Hz)	50/60 Hz	50/60 Hz
Max Input Power (W)	36W	72W
Min Power Factor (%)	0.99% (277Vac)	0.99% (277Vac)
Inrush Current	10Apk-pk	10Apk-pk
Output Channel	2	4
Max Output Voltage (V)	45V	45V
Max Output Current (mA)	390 x 2 mA	390 x 2 mA

## External Driver for L19T8EX4xx Tubes



	1 LAMP DRIVER	2 LAMP DRIVER	3 LAMP DRIVER	4 LAMP DRIVER
<b>MODEL NUMBER</b>	<b>DR1L</b>	<b>DR2L</b>	<b>DR3L</b>	<b>DR4L</b>
<b>ORDER CODE</b>	<b>107292</b>	<b>107293</b>	<b>107294</b>	<b>107295</b>
Input Voltage (V)	120-277V	120-277V	120-277V	120-277V
Input Frequency (Hz)	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
Max Input Power (W)	22W	44W	66W	88W
Min Power Factor (%)	0.87% (277Vac)	0.87% (277Vac)	0.87% (277Vac)	0.87% (277Vac)
Inrush Current	50Apk-pk	50Apk-pk	50Apk-pk	50Apk-pk
Output Channel	1	2	3	4
Max Output Voltage (V)	67V	67V	67V	67V
Max Output Current (mA)	310 x 1 mA	310 x 1 mA	310 x 1 mA	310 x 1 mA

## Low Profile Non-Shunted Lamp Holder



<b>MODEL NUMBER</b>	<b>G13LPNS</b>
<b>ORDER CODE</b>	<b>73978</b>

## T8 Lamp Wiring Harness



	1 LAMP WIRING HARNESS	2 LAMP WIRING HARNESS	3 LAMP WIRING HARNESS	4 LAMP WIRING HARNESS
<b>MODEL NUMBER</b>	<b>G13KIT1</b>	<b>G13KIT2</b>	<b>G13KIT3</b>	<b>G13KIT4</b>
<b>ORDER CODE</b>	<b>1409026</b>	<b>1409027</b>	<b>1409028</b>	<b>1409029</b>

## T5 Lamp Wiring Harness



	1 LAMP WIRING HARNESS	2 LAMP WIRING HARNESS	4 LAMP WIRING HARNESS	6 LAMP WIRING HARNESS
<b>MODEL NUMBER</b>	<b>G5KIT1</b>	<b>G5KIT2</b>	<b>G5KIT4</b>	<b>G5KIT6</b>
<b>ORDER CODE</b>	<b>14098784</b>	<b>14098785</b>	<b>14098786</b>	<b>14098787</b>

## LED PL Retrofit Lamps



	E26 BASE	G24Q BASE	GU24 BASE	GX23 BASE
<b>MODEL NUMBER</b>	<b>6PLE26LED27*</b>	<b>6PLG24QLED27**</b>	<b>6PLGU24LED27**</b>	<b>6PLGX23LED27****</b>
<b>ORDER CODE</b>	<b>76606</b>	<b>76608</b>	<b>76613</b>	<b>76616</b>
Input Wattage	6W	6W	6W	6W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	500 lm	500 lm	500 lm	500 lm
Efficacy (lm/W)	83 lm/W	83 lm/W	83 lm/W	83 lm/W
Color Rendering Index (CRI)	≥81	85	85	85
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	13W CFL	13W CFL	13W CFL	13W CFL
Dimming Compatible	No	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cULus	UL Classified	cULus	UL Classified

\*3000K options also available. \*\*3000K, 3500K, 4000K and 5000K options also available.  
 \*\*\*3000K and 4000K options also available. \*\*\*\*3500K, 4000K and 5000K options also available.

## LED PL Retrofit Lamps



	E26 BASE	G24Q BASE	GU24 BASE	GX23 BASE
<b>MODEL NUMBER</b>	<b>8PLE26LED27*</b>	<b>8PLG24QLED27**</b>	<b>8PLGU24LED27***</b>	<b>8PLGX23LED27****</b>
<b>ORDER CODE</b>	<b>76620</b>	<b>76488</b>	<b>76622</b>	<b>76625</b>
Input Wattage	8W	8W	8W	8W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	675 lm	675 lm	675 lm	675 lm
Efficacy (lm/W)	84 lm/W	84 lm/W	84 lm/W	84 lm/W
Color Rendering Index (CRI)	85	85	85	85
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Replacement	18W CFL	18W CFL	18W CFL	18W CFL
Dimming Compatible	No	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cULus	UL Classified	cULus	UL Classified

\*3000K options also available. \*\*3000K, 3500K, 4000K and 5000K options also available.  
 \*\*\*3000K and 4000K options also available. \*\*\*\*3500K, 4000K and 5000K options also available.

## LED PL DirectFit Retrofit Lamps



	HORIZONTAL PL (G24q BASE)	VERTICAL PL (G24q BASE)
<b>MODEL NUMBER</b>	<b>12PLG24QHLED27</b>	<b>12PLG24QVLED27</b>
<b>ORDER CODE</b>	<b>1408684</b>	<b>1408687</b>
Input Wattage	12W (Bare Lamp)	12W (Bare Lamp)
Voltage	(Ballast Dependent)	(Ballast Dependent)
Delivered Lumens (lm)	900 lm	900 lm
Efficacy (lm/W)	75 lm/W	75 lm/W
Color Rendering Index (CRI)	82	82
Color Temperature (CCT)	2700K	2700K
Replacement	26W CFL	26W CFL
Dimming Compatible	No	No
Lumen Maintenance (L70)	25,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	Classified UL, DLC V4.1	Classified UL, DLC V4.1

3000K & 4000K options also available.

## LED Post Top Lamps



	POST TOP (E26 BASE)	POST TOP (E26 BASE)	POST TOP (E26 BASE)	POST TOP (E26 BASE)
<b>MODEL NUMBER</b>	<b>SKPT12LEDU30E26</b>	<b>SKPT12LEDU50E26</b>	<b>SKPT20LEDU30E26</b>	<b>SKPT20LEDU50E26</b>
<b>ORDER CODE</b>	<b>73447</b>	<b>73448</b>	<b>73449</b>	<b>73450</b>
Input Wattage	12W	12W	20W	20W
Voltage	120V-277V	120V-277V	120V-277V	120V-277V
Delivered Lumens (lm)	1,100 lm	1,100 lm	1,800 lm	1,800 lm
Efficacy (lm/W)	92 lm/W	92 lm/W	90 lm/W	90 lm/W
Color Rendering Index (CRI)	82	82	82	82
Color Temperature (CCT)	3000K	5100K	3000K	5100K
Replacement	50W MH	50W MH	75W MH	75W MH
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cULus	cULus	cULus	cULus

## LED Post Top Lamps



	POST TOP (E39 BASE)	POST TOP (E39 BASE)	POST TOP (E39 BASE)	POST TOP (E39 BASE)
<b>MODEL NUMBER</b>	<b>SKPT30LEDU30E39</b>	<b>SKPT30LEDU50E39</b>	<b>SKPT50LEDU30E39</b>	<b>SKPT50LEDU50E39</b>
<b>ORDER CODE</b>	<b>95378</b>	<b>95379</b>	<b>95380</b>	<b>95381</b>
Input Wattage	30W	30W	50W	50W
Voltage	120V-277V	120V-277V	120V-277V	120V-277V
Delivered Lumens (lm)	3,000 lm	3,400 lm	5,000 lm	5,600 lm
Efficacy (lm/W)	100 lm/W	100 lm/W	100 lm/W	100 lm/W
Color Rendering Index (CRI)	80	80	80	80
Color Temperature (CCT)	3000K	5000K	3000K	5000K
Replacement	125W MH	125W MH	175W MH	175W MH
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	DLC, cULus	DLC, cULus	DLC, cULus	DLC, cULus

## LED Area Lamps



	AREA (E39 BASE)	AREA (E39 BASE)
<b>MODEL NUMBER</b>	<b>AR40LED50</b>	<b>AR100LED50</b>
<b>ORDER CODE</b>	<b>101621</b>	<b>101497</b>
Input Wattage	40W	105W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	5,400 lm	10,500 lm
Efficacy (lm/W)	135 lm/W	105 lm/W
Color Rendering Index (CRI)	82	83
Color Temperature (CCT)	5000K	5000K
Replacement	175W MH	400W MH
Dimming Compatible	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cULus, DLC	cULus, DLC



## PhotonMAX™ Horticulture T8 Linear Lamp



4' T8 (RED/BLUE SPECTRUM)

<b>MODEL NUMBER</b>	<b>L18T8SE415</b>
<b>ORDER CODE</b>	<b>102185</b>
Input Wattage	18W
Voltage	120-277V
Coverage Area (m <sup>2</sup> )	0.4M, 1.3ft mounting height = 1.66 m <sup>2</sup>
PAR Output (μmol/s)	25 μmol/s
PPFD (μmol/m <sup>2</sup> /s)	0.4M, 1.3ft mounting height = 25 μmol/m <sup>2</sup> /s
Replacement	32W FLUOR
Lumen Maintenance (L70)	25,000 hours
<b>CERTIFICATIONS</b>	UL Classified (Damp Listed)

## PhotonMAX™ Horticulture Ceramic Metal Halide Lamp



PGZ18 BASE

<b>MODEL NUMBER</b>	<b>PH-MHL315130</b>
<b>ORDER CODE</b>	<b>107826</b>
Input Wattage	315W
Voltage	100/115V
Coverage Area (m <sup>2</sup> )	FULL SPECTRUM
PPFD (μmol/m <sup>2</sup> /s)	0.4M, 1.3ft mounting height = 1.58 μmol/m <sup>2</sup> /s
Lumen Maintenance (L70)	>50,000 hours
<b>CERTIFICATIONS</b>	IP42, CE

## LED Marquee Lamps



	<b>CLEAR (E26 BASE)</b>	<b>FROSTED (E26 BASE)</b>
<b>MODEL NUMBER</b>	<b>SKBC2.5DLED27</b>	<b>SKBF2.5DLED27</b>
<b>ORDER CODE</b>	<b>73414</b>	<b>73415</b>
Input Wattage	2.5W	2.5W
Voltage	120V	120V
Delivered Lumens (lm)	125 lm	125 lm
Efficacy (lm/W)	50 lm/W	50 lm/W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Replacement	10-15W	10-15W
Dimming Compatible	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cETLus (Wet Listed)	cETLus (Wet Listed)

## LED Double-Sided T8 Linear Lamp



	<b>4' T8</b>	<b>5' T8</b>	<b>6' T8</b>	<b>8' T8</b>
<b>MODEL NUMBER</b>	<b>DSL25T8SE465</b>	<b>DSL30T8SE565</b>	<b>DSL42T8SE665</b>	<b>DSL53T8SE865</b>
<b>ORDER CODE</b>	<b>1408295</b>	<b>1408995</b>	<b>1408996</b>	<b>1408997</b>
Input Wattage	25W	30W	42W	53W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2,500 lm	3,900 lm	5,450 lm	6,900 lm
Color Rendering Index (CRI)	≥80	≥80	≥80	≥80
Color Temperature (CCT)	6500K	6500K	6500K	6500K
Beam Angle	330°	330°	330°	330°
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cRUus	cRUus	cRUus	cRUus

## 12V LED Power Supply



<b>MODEL NUMBER</b>	<b>OT60W/12V/UNV</b>
<b>ORDER CODE</b>	<b>1408885</b>
Nominal Input Voltage (V)	120V-277V
Nominal Input Current (A)	0.60A/0.26A
Power Factor	0.99
Nominal Input Power (W)	71W
Output Voltage (Vdc)	12 Vdc
Output Power Range (W)	1-60W

## LED Channel Letter 2-LED Modules



	2-LED MODULES	2-LED MODULES
<b>MODEL NUMBER</b>	<b>SM0.7DC2WT65</b>	<b>SM0.9DC2WT65</b>
<b>ORDER CODE</b>	<b>107996</b>	<b>107995</b>
Input Wattage	0.72W	0.9W
# LEDs per Module	2	2
Voltage	12V DC	12V DC
Beam Angle	160° Batwing Optic	160° Batwing Optic
Color Temperature (CCT)	6500K	6500K
Color Rendering Index (CRI)	80	80
<b>CERTIFICATIONS</b>	cRUus, CE, IP68	cRUus, CE, IP68

## LED Channel Letter 3-LED Modules



	3-LED MODULES	3-LED MODULES	3-LED MODULES (RED)
<b>MODEL NUMBER</b>	<b>SM0.7DC3WT65</b>	<b>SM1.0DC3WT65</b>	<b>SM0.7DC3RD</b>
<b>ORDER CODE</b>	<b>107994</b>	<b>107993</b>	<b>108112</b>
Input Wattage	0.72W	1W	0.72W
# LEDs per Module	3	3	3
Voltage	12V DC	12V DC	12V DC
Beam Angle	160° Batwing Optic	160° Batwing Optic	160° Batwing Optic
Color Temperature (CCT)	6500K	6500K	Red Color
Color Rendering Index (CRI)	80	80	80
<b>CERTIFICATIONS</b>	cRUus, CE, IP68	cRUus, CE, IP68	cRUus, CE, IP68

## LED Channel Letter 4-LED Modules



	4-LED MODULES
<b>MODEL NUMBER</b>	<b>SM1.8DC4WT65</b>
<b>ORDER CODE</b>	<b>107997</b>
Input Wattage	1.8W
# LEDs per Module	4
Voltage	12V DC
Beam Angle	160° Batwing Optic
Color Temperature (CCT)	6500K
Color Rendering Index (CRI)	80
<b>CERTIFICATIONS</b>	cRUus, CE, IP68

## Compact Fluorescent Spiral Lamps



E26 BASE	
<b>MODEL NUMBER</b>	<b>MLS32T4WW</b>
<b>ORDER CODE</b>	<b>1408621</b>
Input Wattage	32.5W
Delivered Lumens (lm)	2,600 lm
Equivalent Wattage	Approx. 150W INC
Efficacy (lm/W)	80 lm/W
Color Temperature (CCT)	2700K
Color Rendering Index (CRI)	82

## Compact Fluorescent Spiral Lamps



GU24 & E26 BASE	
<b>MODEL NUMBER</b>	<b>PLEASE CONTACT MAXLITE**</b>
<b>ORDER CODE</b>	<b>**Special order only</b>
Input Wattage	13W, 18W, 26W
Delivered Lumens (lm)	900 - 1,650 lm
Equivalent Wattage	Approx. 60W - 100W INC
Efficacy (lm/W)	63 - 69 lm/W
Color Temperature (CCT)	2700K
Color Rendering Index (CRI)	80

## Compact Fluorescent Squat Spiral Lamps



GU24 BASE	
<b>MODEL NUMBER</b>	<b>PLEASE CONTACT MAXLITE**</b>
<b>ORDER CODE</b>	<b>**Special order only</b>
Input Wattage	13W, 18W, 26W
Delivered Lumens (lm)	900 - 1,650 lm
Equivalent Wattage	Approx. 60W - 100W INC
Efficacy (lm/W)	63 - 69 lm/W
Color Temperature (CCT)	2700K
Color Rendering Index (CRI)	80

## HighMax® High Output Compact Fluorescent Lamps



	E26 BASE	E26 BASE	E26 BASE	E39 BASE	E39 BASE	E39 BASE
<b>MODEL NUMBER</b>	<b>SKQ40EA50</b>	<b>SKQ60EA50</b>	<b>SKQ80EA50</b>	<b>SKQ100EA50</b>	<b>SKO150EA50</b>	<b>SKO200EA50</b>
<b>ORDER CODE</b>	<b>11211</b>	<b>11271</b>	<b>11274</b>	<b>35840</b>	<b>35861</b>	<b>35871</b>
Input Wattage	40W	60W	80W	100W	150W	200W
Delivered Lumens (lm)	3,000 lm	4,200 lm	5,500 lm	6,900 lm	9,200 lm	12,000 lm
Equivalent Wattage	Approx. 100W MH	Approx. 175W MH	Approx. 175W MH	Approx. 250W MH	Approx. 250-400W MH	Approx. 400W MH
Efficacy (lm/W)	75 lm/W	70 lm/W	68 lm/W	69 lm/W	61 lm/W	60 lm/W
Color Temperature (CCT)	5000K	5000K	5000K	5000K	5000K	5000K
Color Rendering Index (CRI)	84	84	84	84	84	84

277V and 347V options also available.

## Fluorescent 4-FT T5 Linear Lamps



4' T5 (G13 PIN BASE)	
<b>MODEL NUMBER</b>	<b>F54T5HO/841</b>
<b>ORDER CODE</b>	<b>51421</b>
Input Wattage	54W
Delivered Lumens (lm)	5,000 lm
Equivalent Wattage	n/a
Efficacy (lm/W)	92 lm/W
Color Temperature (CCT)	4100K
Color Rendering Index (CRI)	85

5000K options also available.

## Fluorescent 4-FT T8 Linear Lamps



4' T8 (G13 PIN BASE)	
<b>MODEL NUMBER</b>	<b>F32T8/841XL</b>
<b>ORDER CODE</b>	<b>51050</b>
Input Wattage	32W
Delivered Lumens (lm)	3200 lm
Equivalent Wattage	n/a
Efficacy (lm/W)	100 lm/W
Color Temperature (CCT)	4100K
Color Rendering Index (CRI)	85

5000K options also available.

## T8 Linear Fluorescent Ballasts



	2-LAMP	4-LAMP
<b>MODEL NUMBER</b>	<b>MLEU322HE/SC</b>	<b>MLEU324HE/SC2</b>
<b>ORDER CODE</b>	-	-
Input Voltage	120V-277V	120V-277V
Types	Electronic, Instant Start	Electronic, Instant Start

## T5 Linear Fluorescent Ballasts



	2-LAMP	4-LAMP
<b>MODEL NUMBER</b>	<b>MLEU542HOP/SC</b>	<b>MLEU544HOP/SC</b>
<b>ORDER CODE</b>	-	-
Input Voltage	120V-277V	120V-277V
Types	Electronic, Programmed Start	Electronic, Programmed Start

## LED Plug-and-Play Lightbars



	6"	12"	12" (AMBIENT OUTPUT W/ DIFFUSER)	12" (HIGH OUTPUT W/ DIFFUSER)
<b>MODEL NUMBER</b>	<b>6LB27</b>	<b>12LB27</b>	<b>12LB27AO</b>	<b>12LB27HO</b>
<b>ORDER CODE</b>	<b>74938</b>	<b>74946</b>	<b>74941</b>	<b>74949</b>
Input Wattage	3W	7W	5W	10W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	150 lm	370 lm	250 lm	650 lm
Efficacy (lm/W)	51 lm/W	58 lm/W	58 lm/W	60 lm/W
Color Rendering Index (CRI)	≥90	≥90	≥90	≥90
Color Temperature (CCT)	2700K	2700K	2700K	2700K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cETLus (Damp Listed), NSF, ENERGY STAR®	cETLus (Damp Listed), NSF, ENERGY STAR®	cETLus (Damp Listed), NSF, ENERGY STAR®	cETLus (Damp Listed), NSF, ENERGY STAR®

3500K and 5000K options also available. 3500K and 5000K options have 80 CRI.

## LED Plug-and-Play Lightbars



	24"	48"	72"
<b>MODEL NUMBER</b>	<b>24LB27</b>	<b>48LB27</b>	<b>72LB27</b>
<b>ORDER CODE</b>	<b>74952</b>	<b>74958</b>	<b>74964</b>
Input Wattage	11W	24W	36W
Voltage	120V	120V	120V
Delivered Lumens (lm)	650 lm	1,380 lm	1,980 lm
Efficacy (lm/W)	60 lm/W	59 lm/W	56 lm/W
Color Rendering Index (CRI)	≥90	≥90	≥90
Color Temperature (CCT)	2700K	2700K	2700K
Dimming Compatible	Triac (120V only)	Triac (120V only)	Triac (120V only)
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cETLus (Damp Listed), NSF, ENERGY STAR®	cETLus (Damp Listed), NSF, ENERGY STAR®	cETLus (Damp Listed), NSF, ENERGY STAR®

3500K and 5000K options also available. 3500K and 5000K options have 80 CRI. \*72" models available only on special order basis and will not support inventory

## LED Low Voltage Light Bars



	12"	24"	36"	48"
<b>MODEL NUMBER</b>	<b>12LBLV40</b>	<b>24LBLV40</b>	<b>36LBLV40</b>	<b>48LBLV40</b>
<b>ORDER CODE</b>	<b>96478</b>	<b>96480</b>	<b>96482</b>	<b>96484</b>
Input Wattage	6W	10W	15W	18W
Voltage	24V DC	24V DC	24V DC	24V DC
Delivered Lumens (lm)	300 lm	580 lm	850 lm	1,020 lm
Efficacy (lm/W)	56 lm/W	59 lm/W	58 lm/W	57 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80	≥80
Color Temperature (CCT)	4000K	4000K	4000K	4000K
Dimming Compatible	Proprietary Dimmer Accessory	Proprietary Dimmer Accessory	Proprietary Dimmer Accessory	Proprietary Dimmer Accessory
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
<b>CERTIFICATIONS</b>	cULus (Damp Listed), RoHS	cULus (Damp Listed), RoHS	cULus (Damp Listed), RoHS	cULus (Damp Listed), RoHS



## IntelliMax™ Gateway



<b>MODEL NUMBER</b>	<b>IM-GWE1100W</b>
<b>ORDER CODE</b>	<b>1408934</b>
Smart Building & Lighting Use	GROUP CONTROLLER
Device Network Interface	ZIGBEE
IP Interface	ETHERNET
Supported Wireless Protocols	ZigBee, Thread, Proprietary 15.4
Ethernet Connection	RJ45 (w/ PoE)
Operating System	LINUX w/ OTA Support
USB Extension	X2 (USB 2.0)
Zigbee Max Data Rate	250kbps
Antenna Type	INTERNAL, OMNI DIRECTIONAL
<b>CERTIFICATIONS</b>	FCC, IC

## IntelliMax™ Gateway Mini Hub



<b>MODEL NUMBER</b>	<b>IM-HBE100W</b>
<b>ORDER CODE</b>	<b>1408936</b>
Smart Building & Lighting Use	LOCAL CONTROLLER
Device Network Interface	ZIGBEE
IP Interface	ETHERNET
Supported Wireless Protocols	ZigBee, Thread, Proprietary 15.4
Ethernet Connection	RJ45
Zigbee Max Data Rate	250kbps
Antenna Type	INTERNAL, OMNI DIRECTIONAL
<b>CERTIFICATIONS</b>	FCC, IC

## IntelliMax™ Range Extender



<b>MODEL NUMBER</b>	<b>IM-REEZ10W</b>
<b>ORDER CODE</b>	<b>1408938</b>
Smart Building & Lighting Use	RANGE EXTENDER
Device Network Interface	ZIGBEE
Supported Wireless Protocols	ZigBee, Thread, Proprietary 15.4
Zigbee Max Data Rate	250kbps
Power Supply Type	INTERNAL, WALL-PLUGGABLE
Mounting Features	OUTLET MOUNTING TAB
Antenna Type	INTERNAL, OMNI DIRECTIONAL
<b>CERTIFICATIONS</b>	FCC, IC, UL

## IntelliMax™ Relay Node



<b>MODEL NUMBER</b>	<b>IM-NODE</b>
<b>ORDER CODE</b>	<b>1408940</b>
Smart Building & Lighting Use	FIXTURE CONTROLLER
Device Network Interface	ZIGBEE
Supply Voltage	100-277VAC, 50/60Hz
Max Load	5 AMPS ALL LOADS (LED, INDUCTION, FLUORESCENT, OTHER) 0-10V SINK @ 100mA 0-10V SOURCE @ 1mA
Power Supply	< 0.5W STANDBY POWER
Commissioning	REMOTE COMMISSIONING
<b>CERTIFICATIONS</b>	FCC, IC, UL

## IntelliMax™ Occupancy and Daylight Sensors



	<b>OCCUPANCY</b>	<b>DAYLIGHT</b>
<b>MODEL NUMBER</b>	<b>IM-MSZSC15</b>	<b>IM-PCLURPC-OCW</b>
<b>ORDER CODE</b>	<b>1408945</b>	<b>1409568</b>
Device Type	WIRELESS PIR SENSOR	WIRELESS DAYLIGHT HARVESTING PHOTOCELL
Smart Building & Lighting Use	RF OCCUPANCY SENSOR	DAYLIGHT MONITORING
Device Network Interface	ZIGBEE	ZIGBEE
Frequency	2.4GHz	2.4GHz
Range	UP TO 75' BETWEEN OTHER RF DEVICES	UP TO 75' BETWEEN OTHER RF DEVICES
Battery Life	7-10 YEARS	7-10 YEARS
Mounting Height	8-12'	8-12'
Usage	INDOORS ONLY	INDOORS ONLY
<b>CERTIFICATIONS</b>	FCC, IEEE 802.15.4, UL, CA TITLE 24	FCC, IEEE 802.15.4, UL, CA TITLE 24



IntelliMax is compatible with Leviton® wall switches, dimmers and daylight harvesting sensors, and certified components from other leading manufacturers.



GU24 SOCKET WITH IPS BRACKET

<b>MODEL NUMBER</b>	<b>MLGSIBB</b>	<b>MLGSIB3</b>	<b>MLGSHBS</b>
<b>ORDER CODE</b>	<b>11336</b>	<b>11335</b>	<b>11339</b>



GU24 SOCKET WITH IPS INSERT BACK, 3 CONDUCTORS



GU24 SOCKET WITH IPS SIDE MOUNT BRACKET



GU24 SOCKET WITH SIDE MOUNT IPS BRACKET



GU24 SOCKET WITH SIDE MOUNT STRAP BRACKET



GU24 SOCKET WITH IPS INSERT BACK

<b>MODEL NUMBER</b>	<b>MLGSIBS</b>	<b>MLGSSBS</b>	<b>MLGSIBB</b>
<b>ORDER CODE</b>	<b>11337</b>	<b>11338</b>	<b>11334</b>



GU24 LOCKING ADAPTER FOR E26 SOCKETS



GU24 SOCKET WITH THREADED RING IPS BACK THREAD BRACKET



GU24 DOUBLE SOCKET WITH DOUBLE IPS BRACKETS

<b>MODEL NUMBER</b>	<b>MLGSML</b>	<b>MLGSIBBT</b>	<b>MLGSIBD</b>
<b>ORDER CODE</b>	<b>11341</b>	<b>11340</b>	<b>11380</b>


## Step Down Transformer



<b>MODEL NUMBER</b>	<b>2561F-13</b>
<b>ORDER CODE</b>	<b>77495</b>
Input Voltage	277V
Output Voltage	120V
Min & Max Load	26W

# MaxLite Tools & Resources

## support.maxlite.com



My Profile | My Order | Inventory | Sales Analysis

## MaxLite.com



Product Datasheets | Case Studies | Catalogs & Brochures | ROI Calculator | Utility Rebate Finder | ENERGY STAR

## Utility Rebates on MaxLite.com



Utility Rebate Finder | Custom Rebate Calculator

## MaxLiteUniversity.com



Free online lighting degree program | Eligible for ALA Credit Hours

## Social Media (Follow us on...)



LinkedIn

Twitter @MaxLite

Facebook

**Contact:**

**USA:**

**Chris Primous**

T: 862-485-9878

E: cprimous@maxlite.com

**CHINA:**

**Alex Shen**

T: 86-769-87380921 x806

E: ashen@maxlite.com

**MaxLite<sup>®</sup>**

A NEW WAVE OF LIGHT

[www.maxlite.com](http://www.maxlite.com)

Find, like and follow us on social media.



**Corporate Headquarters**

12 York Ave.  
West Caldwell, NJ 07006  
T: 1-800-555-5629  
F: 973-244-7333

**Indiana Facility**

998 Gerdt Court  
Greenwood, IN 46143

**California Facility**

1148 North Ocean Circle  
Anaheim, CA 92806  
T: 1-800-793-1212  
F: 714-678-5096